

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998259

Luminaire Tested: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998259
REPORT IS A COMBINATION OF REPORTS P983999 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3768.0 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33		
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35	29		
2	86	79	73	69	78	72	67	63	58	54	51	45	42	40	33	31	30	25		
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	27	26	21		
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19		
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16		
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	19	18	14		
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13		
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12		
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11		
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9026	9026	9026	9026
5°	9047	9623	9082	7656
10°	8942	10506	8998	6312
15°	8725	11080	8846	5317
20°	8589	10405	8589	4622
25°	8316	8938	8353	4132
30°	7865	7027	8014	3744
35°	7466	4859	7591	3424
40°	7007	3669	7088	3171
45°	6443	3015	6548	2896
50°	5952	2646	5964	2652
55°	5396	2254	5430	2386
60°	4801	1883	4867	2082
65°	4269	1532	4348	1779
70°	3737	1201	3833	1435
75°	3138	873	3261	1039
80°	2451	553	2627	618
85°	1610	277	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9330 cd/sqm

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	1.4
10°-20°	158.1	4.2
20°-30°	229.4	6.1
30°-40°	241.8	6.4
40°-50°	214.0	5.7
50°-60°	170.9	4.5
60°-70°	116.1	3.1
70°-80°	59.4	1.6
80°-90°	16.6	0.4
90°-100°	55.5	1.5
100°-110°	176.4	4.7
110°-120°	301.8	8.0
120°-130°	396.9	10.5
130°-140°	445.5	11.8
140°-150°	436.9	11.6
150°-160°	366.5	9.7
160°-170°	243.1	6.5
170°-180°	84.9	2.3
0°-30°	441.8	11.7
0°-40°	683.6	18.1
0°-60°	1068.5	28.4
0°-90°	1260.6	33.5
90°-120°	533.6	14.2
90°-150°	1812.9	48.1
90°-180°	2507.0	66.5
0°-180°	3768.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	570	570	570	570	570	
5°	571	637	573	507	571	54
15°	536	783	543	376	536	151
25°	482	652	484	302	482	220
35°	393	355	400	250	393	246
45°	295	214	300	206	295	229
55°	202	150	204	159	202	181
65°	120	92	122	107	120	119
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	1	26	1	26	1	3
95°	39	47	39	47	39	44
105°	163	168	163	168	163	172
115°	303	303	303	303	303	300
125°	440	442	440	442	440	394
135°	570	577	570	577	570	440
145°	692	699	692	699	692	432
155°	791	797	791	797	791	364
165°	860	861	860	861	860	243
175°	895	892	895	892	895	85
180°	897	897	897	897	897	

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	573.3	574.6	576.8	577.2	581.6	585.1	589.0	589.0	590.3	589.9	586.4
5°	570.6	574.6	580.3	585.1	593.0	596.5	601.7	605.7	609.2	611.8	611.4
7.5°	566.2	573.3	581.6	590.8	601.3	607.4	614.9	621.9	626.7	631.1	634.2
10°	558.8	570.6	582.0	594.3	607.9	616.2	625.0	634.2	641.6	649.9	657.8
12.5°	548.7	565.8	579.8	596.0	612.7	621.9	635.9	642.9	657.4	678.4	684.1
15°	536.0	559.2	572.4	593.0	614.9	622.3	641.6	653.0	682.8	696.0	711.7
17.5°	524.2	550.0	567.6	591.2	612.7	627.2	646.0	669.2	694.2	713.1	730.6
20°	514.5	539.5	560.5	586.8	614.0	632.4	652.1	680.2	707.4	726.6	740.2
22.5°	492.6	524.6	549.1	578.5	611.4	636.8	655.6	686.3	715.7	727.5	739.4
25°	481.7	509.3	537.8	571.1	609.6	639.9	656.1	690.3	716.1	720.5	723.1
27.5°	461.5	492.6	525.9	564.0	609.2	634.6	655.2	686.3	706.9	703.9	696.0
30°	436.5	474.6	511.5	552.7	603.1	630.7	649.9	678.4	689.0	673.2	659.2
32.5°	418.1	454.0	494.8	542.6	596.0	622.3	641.2	663.5	665.7	637.2	613.6
35°	393.1	433.0	479.0	529.4	584.2	607.9	625.4	639.0	628.5	588.6	560.5
37.5°	370.8	410.2	459.3	510.6	568.0	591.2	605.2	607.4	581.6	546.5	505.3
40°	346.2	387.0	438.3	492.2	550.0	570.2	578.9	572.4	535.1	494.4	446.6
42.5°	321.7	362.0	417.2	472.5	527.2	544.3	547.8	529.9	484.3	436.5	381.3
45°	295.0	337.0	392.2	447.9	500.9	510.6	511.0	485.2	431.3	381.3	330.0
47.5°	273.0	312.0	366.8	422.5	467.2	473.8	471.1	441.3	382.6	326.5	281.8
50°	248.9	286.2	340.5	395.3	433.4	435.2	428.6	386.1	328.7	277.4	241.9
52.5°	223.1	260.8	310.7	363.3	397.5	394.9	382.2	336.6	282.7	240.2	213.0
55°	202.5	235.8	282.7	334.0	358.1	350.6	336.6	290.1	247.6	211.7	188.0
57.5°	179.7	209.1	255.1	299.8	313.8	306.8	292.8	249.4	209.9	182.8	167.0
60°	158.2	184.9	225.3	262.5	273.5	266.0	249.8	210.8	182.3	159.5	147.7
62.5°	138.5	161.7	195.5	229.7	234.0	226.6	212.6	181.0	156.5	138.5	129.7
65°	120.1	142.0	169.2	195.0	199.0	191.1	176.6	153.8	133.2	121.8	113.5
67.5°	102.1	119.6	143.8	162.6	164.8	157.3	145.5	127.1	114.4	102.1	96.0
70°	86.3	99.5	118.3	133.7	134.5	127.5	121.4	104.7	95.1	86.3	81.5
72.5°	71.0	80.2	94.7	106.1	106.5	102.1	96.4	85.9	77.6	71.4	66.6
75°	56.1	64.0	72.8	82.8	82.4	78.9	74.5	67.9	60.9	57.0	54.8
77.5°	43.0	47.8	54.8	61.4	61.4	59.6	57.0	52.2	47.8	43.8	41.6
80°	30.7	33.7	39.4	41.6	42.5	42.1	39.9	36.4	34.6	31.6	30.7
82.5°	19.7	21.9	24.5	26.7	28.0	27.2	26.7	25.0	22.4	21.5	20.6
85°	11.4	12.3	13.6	14.9	15.3	14.9	15.8	14.5	13.1	13.1	12.7
87.5°	4.8	5.3	6.1	6.1	6.6	6.6	6.1	6.6	6.6	6.1	5.7
90°	0.8	2.8	4.8	6.8	8.8	9.8	11.7	15.4	19.1	22.8	26.5
92.5°	16.7	18.0	19.4	20.7	22.0	22.7	22.8	23.0	23.1	23.3	23.5
95°	39.4	41.1	42.7	44.4	46.1	46.9	47.1	47.4	47.7	48.1	48.4
97.5°	65.8	67.3	68.9	70.4	71.9	72.7	73.0	73.7	74.4	75.0	75.7
100°	96.1	97.5	98.8	100.2	101.5	102.2	102.4	102.9	103.4	103.9	104.4
102.5°	127.9	128.9	129.9	130.9	131.9	132.4	132.7	133.4	134.1	134.8	135.5
105°	162.7	163.2	163.7	164.2	164.7	165.0	165.2	165.5	165.8	166.2	166.5
107.5°	197.5	198.2	198.9	199.6	200.3	200.6	200.6	200.6	200.6	200.6	200.6
110°	230.8	231.8	232.8	233.9	234.9	235.4	235.4	235.4	235.4	235.4	235.4



TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	267.2	268.2	269.2	270.2	271.2	271.7	271.6	271.4	271.3	271.1	270.9
115°	302.7	303.7	304.7	305.8	306.8	307.3	307.1	306.8	306.5	306.1	305.8
117.5°	338.3	339.7	341.0	342.4	343.7	344.4	344.0	343.1	342.3	341.4	340.6
120°	373.9	375.2	376.6	377.9	379.2	379.9	379.2	377.9	376.6	375.2	373.9
122.5°	406.4	408.1	409.8	411.5	413.2	414.0	413.6	412.7	411.9	411.0	410.2
125°	440.5	442.0	443.5	445.0	446.5	447.3	447.0	446.5	446.0	445.5	445.0
127.5°	473.8	475.6	477.5	479.3	481.2	482.1	481.8	481.1	480.4	479.8	479.1
130°	504.8	507.0	509.2	511.4	513.6	514.7	514.5	514.2	513.8	513.5	513.1
132.5°	539.6	541.3	543.0	544.7	546.4	547.2	547.3	547.5	547.6	547.8	548.0
135°	569.9	571.7	573.6	575.4	577.3	578.2	578.4	578.7	579.0	579.4	579.7
137.5°	603.2	604.7	606.2	607.7	609.2	610.0	610.2	610.5	610.8	611.2	611.5
140°	632.7	634.2	635.7	637.2	638.7	639.5	639.9	640.8	641.6	642.5	643.3
142.5°	663.0	664.5	666.0	667.5	669.0	669.8	670.1	670.6	671.1	671.6	672.1
145°	691.8	693.0	694.2	695.3	696.5	697.1	697.6	698.6	699.6	700.6	701.6
147.5°	717.5	719.0	720.5	722.0	723.5	724.3	724.6	725.3	726.0	726.6	727.3
150°	744.0	745.0	746.0	747.0	748.0	748.5	748.8	749.5	750.2	750.8	751.5
152.5°	767.4	768.4	769.4	770.5	771.5	772.0	772.4	773.3	774.1	775.0	775.8
155°	790.9	791.4	791.9	792.4	792.9	793.2	793.4	793.9	794.4	794.9	795.4
157.5°	811.3	811.6	812.0	812.3	812.6	812.8	813.0	813.3	813.7	814.0	814.4
160°	829.5	829.8	830.2	830.5	830.8	831.0	831.1	831.3	831.4	831.6	831.8
162.5°	846.2	846.2	846.2	846.2	846.2	846.2	846.3	846.4	846.6	846.7	846.9
165°	860.5	860.3	860.2	860.0	859.9	859.8	859.8	859.8	859.8	859.8	859.8
167.5°	873.4	872.9	872.4	871.9	871.4	871.1	871.1	871.1	871.1	871.1	871.1
170°	883.2	882.7	882.2	881.7	881.2	881.0	880.9	880.7	880.6	880.4	880.2
172.5°	890.0	889.5	889.0	888.5	888.0	887.8	887.7	887.5	887.4	887.2	887.0
175°	895.3	894.8	894.3	893.8	893.3	893.1	892.9	892.6	892.3	891.9	891.6
177.5°	898.4	897.9	897.4	896.9	896.4	896.1	895.9	895.6	895.3	894.9	894.6
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	592.5	593.0	593.9	598.2	600.4	600.9	599.1	603.1	604.4	603.1	602.2
5°	620.6	623.2	628.5	634.2	633.7	634.2	636.8	639.4	640.3	636.8	638.1
7.5°	645.1	650.4	656.1	664.8	664.8	669.2	671.0	673.2	678.4	675.8	674.9
10°	673.2	680.2	690.7	704.7	705.2	709.6	713.9	720.9	723.1	721.4	722.3
12.5°	708.2	721.8	722.7	738.0	745.1	745.9	752.9	751.6	756.0	756.0	763.5
15°	723.6	744.6	756.4	771.3	775.7	770.5	776.2	782.3	782.7	782.7	782.3
17.5°	751.2	759.5	771.3	779.2	781.0	781.0	781.4	784.1	782.3	778.8	781.4
20°	756.9	760.4	764.8	763.9	764.8	760.4	756.0	751.6	752.1	749.9	756.4
22.5°	746.4	745.5	735.4	728.8	728.8	720.1	711.7	707.8	703.9	705.2	707.4
25°	720.1	706.5	694.2	684.6	682.4	668.4	657.0	653.5	646.9	652.1	653.0
27.5°	678.0	662.7	642.9	634.6	623.2	617.5	609.6	599.1	585.5	593.4	592.1
30°	632.9	610.1	593.9	573.7	555.7	554.4	539.5	522.0	515.0	515.0	518.9
32.5°	582.5	552.2	528.5	500.1	482.5	475.1	457.1	439.6	443.5	430.4	435.2
35°	523.7	483.8	454.0	426.4	413.3	404.5	381.3	371.6	361.1	355.0	366.4
37.5°	467.6	421.6	383.5	353.2	348.4	332.6	316.9	310.7	304.6	307.2	306.8
40°	399.3	358.5	324.3	300.7	292.3	284.9	274.4	266.9	263.0	265.2	265.6
42.5°	337.5	303.3	277.9	261.2	254.2	248.9	243.7	237.5	236.2	236.2	238.0
45°	289.7	261.6	244.6	231.0	227.0	223.1	219.1	216.5	215.6	213.9	215.2
47.5°	251.6	229.2	218.7	208.6	204.2	203.4	199.8	198.5	196.8	196.3	196.8
50°	219.6	205.5	195.9	190.2	187.1	185.8	184.1	181.4	180.6	182.8	181.9
52.5°	197.2	184.1	178.8	173.1	171.4	169.6	167.0	167.4	167.0	166.1	166.1
55°	174.9	166.5	161.3	156.9	156.5	154.7	152.5	151.6	151.2	150.3	151.6
57.5°	156.9	150.3	145.5	141.6	139.8	139.8	137.6	135.9	135.9	135.4	135.9
60°	138.9	132.4	129.3	125.3	124.0	123.6	122.3	121.4	120.1	120.1	120.1
62.5°	122.3	117.0	113.5	110.0	110.4	108.3	106.5	105.6	105.6	106.1	106.1
65°	106.5	103.0	98.6	95.5	94.7	94.2	93.4	92.9	91.6	92.5	92.5
67.5°	92.0	87.2	84.6	83.3	82.0	81.5	80.6	79.8	79.3	78.9	79.8
70°	77.6	73.6	71.4	70.6	69.2	68.8	68.4	67.1	67.5	67.9	68.4
72.5°	64.4	60.9	60.5	57.9	57.9	57.9	56.1	57.0	56.5	55.7	56.5
75°	50.8	49.1	48.2	46.9	47.3	46.9	46.5	45.1	45.1	45.6	46.0
77.5°	40.3	38.6	38.1	36.8	35.9	36.8	35.9	35.5	35.5	35.9	35.9
80°	29.8	28.9	27.6	27.6	27.6	27.2	27.2	27.2	26.7	26.3	26.7
82.5°	19.7	19.7	19.3	18.8	19.3	18.4	18.8	18.8	18.8	18.8	18.8
85°	12.7	12.3	12.3	11.8	11.8	11.8	12.3	11.4	11.4	11.8	11.8
87.5°	5.7	5.7	5.7	6.1	5.7	5.7	5.7	6.1	5.7	5.7	5.7
90°	26.2	25.8	25.5	25.2	25.0	25.1	25.2	25.4	25.5	25.7	25.5
92.5°	23.7	23.8	24.0	24.1	24.2	24.2	24.2	24.2	24.2	24.2	24.2
95°	48.4	48.4	48.4	48.4	48.4	48.2	47.9	47.6	47.2	46.9	47.2
97.5°	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7
100°	104.4	104.4	104.4	104.4	104.4	104.3	104.2	104.0	103.9	103.7	103.9
102.5°	135.7	135.8	136.0	136.1	136.2	136.1	136.0	135.8	135.7	135.5	135.7
105°	166.8	167.2	167.5	167.8	168.0	168.0	168.0	168.0	168.0	168.0	168.0
107.5°	200.8	200.9	201.1	201.2	201.3	200.9	200.0	199.2	198.3	197.5	198.3
110°	235.4	235.4	235.4	235.4	235.4	235.1	234.6	234.1	233.6	233.1	233.6

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	270.4	269.9	269.4	268.9	268.7	268.5	268.2	267.9	267.5	267.2	267.5
115°	305.6	305.4	305.3	305.1	305.0	304.7	304.2	303.7	303.2	302.7	303.2
117.5°	340.1	339.6	339.1	338.6	338.3	338.0	337.5	337.0	336.5	336.0	336.5
120°	373.9	373.9	373.9	373.9	373.9	373.6	373.1	372.6	372.1	371.6	372.1
122.5°	409.7	409.2	408.7	408.2	407.9	407.7	407.4	407.1	406.7	406.4	406.7
125°	444.5	444.0	443.5	443.0	442.8	442.7	442.5	442.4	442.2	442.0	442.2
127.5°	478.4	477.8	477.1	476.4	476.1	475.8	475.3	474.8	474.3	473.8	474.3
130°	512.8	512.4	512.1	511.8	511.6	511.3	510.6	509.9	509.3	508.6	509.3
132.5°	547.2	546.3	545.5	544.6	544.2	543.9	543.4	542.9	542.4	541.9	542.4
135°	579.5	579.4	579.2	579.1	579.0	578.7	578.2	577.7	577.2	576.7	577.2
137.5°	611.3	611.2	611.0	610.9	610.8	610.5	609.8	609.1	608.4	607.7	608.4
140°	643.3	643.3	643.3	643.3	643.3	643.0	642.3	641.6	641.0	640.3	641.0
142.5°	672.3	672.4	672.6	672.7	672.8	672.5	671.8	671.1	670.5	669.8	670.5
145°	701.8	702.0	702.1	702.3	702.4	702.1	701.4	700.7	700.0	699.3	700.0
147.5°	727.6	728.0	728.3	728.6	728.8	728.5	727.8	727.1	726.5	725.8	726.5
150°	752.0	752.5	753.0	753.5	753.8	753.5	753.0	752.5	752.0	751.5	752.0
152.5°	776.5	777.1	777.8	778.5	778.8	778.5	777.8	777.1	776.5	775.8	776.5
155°	796.2	797.1	797.9	798.8	799.2	799.0	798.5	798.0	797.5	797.0	797.5
157.5°	815.6	816.8	817.9	819.1	819.7	819.3	818.4	817.6	816.7	815.9	816.7
160°	832.8	833.8	834.8	835.8	836.3	836.0	835.3	834.6	834.0	833.3	834.0
162.5°	848.1	849.3	850.4	851.6	852.2	851.8	850.9	850.1	849.2	848.4	849.2
165°	861.0	862.2	863.3	864.5	865.1	864.7	863.8	863.0	862.1	861.3	862.1
167.5°	872.3	873.5	874.6	875.8	876.4	876.0	875.1	874.3	873.4	872.6	873.4
170°	881.4	882.6	883.7	884.9	885.5	885.0	884.0	883.0	882.0	881.0	882.0
172.5°	888.2	889.4	890.5	891.7	892.3	891.8	890.8	889.8	888.8	887.8	888.8
175°	892.8	894.0	895.1	896.3	896.9	896.4	895.4	894.3	893.3	892.3	893.3
177.5°	895.6	896.6	897.6	898.6	899.1	898.6	897.6	896.6	895.6	894.6	895.6
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	604.4	601.3	598.7	599.1	601.3	599.5	595.2	589.5	587.3	584.6	587.3
5°	640.7	638.1	632.9	633.3	632.0	630.2	623.2	614.4	614.4	607.4	606.6
7.5°	676.7	672.7	669.2	668.4	663.5	660.0	653.9	641.6	636.8	628.5	623.7
10°	717.0	713.9	710.0	705.2	702.5	696.4	686.3	668.4	659.6	648.2	639.9
12.5°	757.8	757.3	748.6	738.9	738.5	728.8	721.8	697.7	685.9	670.5	650.8
15°	783.6	781.4	776.6	771.8	773.1	762.6	746.8	718.3	710.4	692.0	671.0
17.5°	783.2	783.2	781.9	781.0	779.7	776.6	767.8	749.0	736.3	713.1	693.3
20°	758.2	763.9	765.2	764.8	769.2	771.3	770.9	759.1	749.0	728.4	708.2
22.5°	708.2	721.4	727.1	730.6	739.8	744.6	756.0	751.6	749.0	733.7	716.6
25°	661.8	666.2	683.3	684.1	696.8	708.7	720.1	727.5	737.2	731.5	717.0
27.5°	601.7	611.8	624.1	633.3	635.9	660.0	678.9	692.9	714.8	716.6	711.7
30°	533.8	538.6	558.8	571.1	585.1	602.6	629.8	653.9	673.6	691.6	697.7
32.5°	451.0	470.7	482.5	497.4	509.7	540.8	574.1	605.2	628.0	658.3	671.4
35°	375.2	390.5	410.7	416.8	439.1	465.4	508.8	548.7	583.3	614.0	640.7
37.5°	312.5	324.8	346.2	355.9	369.0	402.8	439.1	488.7	530.3	568.0	601.3
40°	269.5	278.7	295.0	298.0	309.0	339.7	369.0	415.5	470.7	521.5	557.9
42.5°	240.2	244.6	255.5	259.5	266.5	287.1	313.4	357.2	408.5	461.1	512.3
45°	219.1	222.2	228.8	232.3	241.0	250.2	271.7	306.8	347.1	400.1	455.4
47.5°	200.3	204.2	206.9	209.1	213.9	224.0	238.0	263.8	302.4	351.1	404.5
50°	184.5	185.8	190.6	191.1	194.2	200.7	213.9	229.7	260.3	299.8	351.5
52.5°	168.7	170.0	173.1	176.2	177.5	182.8	191.5	204.7	227.5	258.6	304.6
55°	153.0	154.7	157.8	160.0	161.3	165.7	170.9	183.6	201.6	223.5	261.2
57.5°	137.2	141.1	142.0	143.3	145.5	150.3	155.1	162.6	176.6	196.8	224.4
60°	122.3	123.6	126.7	128.0	130.2	132.8	138.9	144.6	154.7	170.5	195.5
62.5°	106.9	110.0	111.3	112.6	114.4	117.5	121.4	127.5	136.3	149.0	168.7
65°	93.8	94.2	96.9	98.6	100.4	102.6	106.5	112.2	117.5	129.3	143.8
67.5°	81.1	82.0	82.8	84.6	86.8	89.0	92.5	95.5	102.1	110.0	121.4
70°	68.8	68.8	71.0	72.3	71.9	74.5	77.1	80.6	85.5	92.9	102.1
72.5°	57.9	57.4	59.2	59.6	60.5	62.2	64.0	67.5	70.1	75.8	82.8
75°	46.0	46.9	47.8	47.8	49.1	50.4	52.2	53.9	57.0	60.5	65.7
77.5°	36.4	36.4	37.3	37.7	39.0	38.6	40.3	42.1	44.3	47.3	51.3
80°	26.7	27.6	27.6	27.6	28.0	28.5	30.2	31.6	32.9	35.1	36.8
82.5°	18.8	18.8	19.7	19.7	19.7	20.6	20.6	21.0	21.9	23.2	24.5
85°	11.8	11.8	11.8	12.3	11.8	12.3	13.1	12.7	13.1	14.0	14.0
87.5°	5.7	5.7	5.7	5.7	5.7	6.1	5.7	6.1	6.6	6.6	6.6
90°	25.4	25.2	25.1	25.0	25.2	25.5	25.8	26.2	26.5	22.8	19.1
92.5°	24.2	24.2	24.2	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
95°	47.6	47.9	48.2	48.4	48.4	48.4	48.4	48.4	48.4	48.1	47.7
97.5°	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.0	74.4
100°	104.0	104.2	104.3	104.4	104.4	104.4	104.4	104.4	104.4	103.9	103.4
102.5°	135.8	136.0	136.1	136.2	136.1	136.0	135.8	135.7	135.5	134.8	134.1
105°	168.0	168.0	168.0	168.0	167.8	167.5	167.2	166.8	166.5	166.2	165.8
107.5°	199.2	200.0	200.9	201.3	201.2	201.1	200.9	200.8	200.6	200.6	200.6
110°	234.1	234.6	235.1	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	267.9	268.2	268.5	268.7	268.9	269.4	269.9	270.4	270.9	271.1	271.3
115°	303.7	304.2	304.7	305.0	305.1	305.3	305.4	305.6	305.8	306.1	306.5
117.5°	337.0	337.5	338.0	338.3	338.6	339.1	339.6	340.1	340.6	341.4	342.3
120°	372.6	373.1	373.6	373.9	373.9	373.9	373.9	373.9	373.9	375.2	376.6
122.5°	407.1	407.4	407.7	407.9	408.2	408.7	409.2	409.7	410.2	411.0	411.9
125°	442.4	442.5	442.7	442.8	443.0	443.5	444.0	444.5	445.0	445.5	446.0
127.5°	474.8	475.3	475.8	476.1	476.4	477.1	477.8	478.4	479.1	479.8	480.4
130°	509.9	510.6	511.3	511.6	511.8	512.1	512.4	512.8	513.1	513.5	513.8
132.5°	542.9	543.4	543.9	544.2	544.6	545.5	546.3	547.2	548.0	547.8	547.6
135°	577.7	578.2	578.7	579.0	579.1	579.2	579.4	579.5	579.7	579.4	579.0
137.5°	609.1	609.8	610.5	610.8	610.9	611.0	611.2	611.3	611.5	611.2	610.8
140°	641.6	642.3	643.0	643.3	643.3	643.3	643.3	643.3	643.3	642.5	641.6
142.5°	671.1	671.8	672.5	672.8	672.7	672.6	672.4	672.3	672.1	671.6	671.1
145°	700.7	701.4	702.1	702.4	702.3	702.1	702.0	701.8	701.6	700.6	699.6
147.5°	727.1	727.8	728.5	728.8	728.6	728.3	728.0	727.6	727.3	726.6	726.0
150°	752.5	753.0	753.5	753.8	753.5	753.0	752.5	752.0	751.5	750.8	750.2
152.5°	777.1	777.8	778.5	778.8	778.5	777.8	777.1	776.5	775.8	775.0	774.1
155°	798.0	798.5	799.0	799.2	798.8	797.9	797.1	796.2	795.4	794.9	794.4
157.5°	817.6	818.4	819.3	819.7	819.1	817.9	816.8	815.6	814.4	814.0	813.7
160°	834.6	835.3	836.0	836.3	835.8	834.8	833.8	832.8	831.8	831.6	831.4
162.5°	850.1	850.9	851.8	852.2	851.6	850.4	849.3	848.1	846.9	846.7	846.6
165°	863.0	863.8	864.7	865.1	864.5	863.3	862.2	861.0	859.8	859.8	859.8
167.5°	874.3	875.1	876.0	876.4	875.8	874.6	873.5	872.3	871.1	871.1	871.1
170°	883.0	884.0	885.0	885.5	884.9	883.7	882.6	881.4	880.2	880.4	880.6
172.5°	889.8	890.8	891.8	892.3	891.7	890.5	889.4	888.2	887.0	887.2	887.4
175°	894.3	895.4	896.4	896.9	896.3	895.1	894.0	892.8	891.6	891.9	892.3
177.5°	896.6	897.6	898.6	899.1	898.6	897.6	896.6	895.6	894.6	894.9	895.3
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	585.1	582.9	581.6	582.5	579.8	573.3	573.3	575.4	572.8	570.2	566.2
5°	601.3	596.9	594.3	593.9	587.7	577.2	575.0	572.8	567.1	561.0	554.4
7.5°	617.1	609.2	604.8	601.7	593.0	579.4	573.7	568.9	559.7	550.5	542.1
10°	630.2	618.8	613.6	608.8	597.4	580.3	571.1	562.3	550.5	538.6	528.1
12.5°	640.7	627.6	621.0	614.0	600.0	577.6	566.2	552.2	540.4	524.6	514.1
15°	658.3	631.1	625.0	618.4	603.9	573.3	559.2	543.4	527.2	506.2	494.8
17.5°	672.3	635.9	635.5	621.5	602.6	571.5	550.0	529.4	511.9	490.9	472.9
20°	680.6	643.4	636.4	621.9	598.2	559.7	537.3	514.5	495.7	470.3	452.3
22.5°	687.6	653.9	635.5	618.0	589.0	555.7	522.9	501.4	475.5	447.9	430.8
25°	690.3	656.1	636.8	616.6	582.5	544.3	507.1	483.8	454.9	429.9	406.7
27.5°	690.7	655.6	632.0	610.9	573.3	529.4	491.3	466.8	434.8	405.8	382.6
30°	686.3	650.8	629.4	606.6	564.5	515.8	472.0	444.8	410.7	381.7	357.6
32.5°	673.2	641.2	623.7	598.7	553.1	497.0	453.6	423.4	387.4	358.9	335.7
35°	651.3	629.4	610.1	586.8	538.2	479.5	435.2	399.7	363.3	336.2	314.2
37.5°	624.1	612.3	594.3	571.5	521.1	463.7	414.6	375.2	338.8	312.5	291.0
40°	587.3	590.3	572.8	552.2	500.9	442.2	387.9	350.2	316.0	291.4	270.4
42.5°	547.4	560.1	550.0	530.3	478.6	418.5	368.1	326.5	293.2	267.8	250.2
45°	504.4	526.4	520.2	505.8	455.4	393.6	340.1	299.8	270.4	245.9	230.5
47.5°	457.5	488.7	488.7	478.1	429.5	368.6	316.0	274.8	245.9	228.3	213.4
50°	409.8	444.8	450.5	443.5	400.6	340.1	286.6	249.4	224.4	207.3	196.3
52.5°	359.8	400.6	411.1	407.6	369.9	312.9	262.5	226.1	203.4	188.5	178.8
55°	312.0	359.4	370.8	372.1	337.0	283.1	235.8	203.8	181.9	171.8	163.5
57.5°	266.9	312.5	325.2	327.4	303.7	255.9	210.8	182.8	163.0	154.7	148.1
60°	228.3	266.5	283.1	287.9	267.3	224.4	187.6	160.4	145.5	137.6	131.5
62.5°	196.8	227.5	245.0	246.3	237.1	196.8	163.5	140.7	128.0	121.0	117.9
65°	166.1	193.7	204.2	209.5	202.0	170.5	141.1	122.3	112.2	106.1	103.0
67.5°	141.6	159.1	167.9	174.9	167.4	143.8	120.1	104.7	97.3	91.2	89.4
70°	116.1	130.6	137.2	144.2	137.6	119.6	102.6	88.5	82.0	77.1	74.9
72.5°	92.9	104.3	110.4	114.8	110.9	96.0	82.0	72.3	67.5	64.0	62.7
75°	73.6	81.5	85.0	88.1	86.3	74.9	66.2	58.3	53.9	50.8	50.0
77.5°	56.1	61.8	65.7	66.6	64.4	57.0	49.5	44.7	41.2	39.4	38.6
80°	39.9	43.4	45.6	46.9	44.7	41.6	36.4	32.9	29.8	27.6	27.2
82.5°	26.7	28.5	30.2	29.8	28.9	26.3	23.2	21.5	20.2	18.4	18.4
85°	15.3	15.8	16.7	17.1	16.7	14.9	13.1	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	3.9
90°	15.4	11.7	9.8	8.8	6.8	4.8	2.8	0.8	2.8	4.8	6.8
92.5°	23.0	22.8	22.7	22.0	20.7	19.4	18.0	16.7	18.0	19.4	20.7
95°	47.4	47.1	46.9	46.1	44.4	42.7	41.1	39.4	41.1	42.7	44.4
97.5°	73.7	73.0	72.7	71.9	70.4	68.9	67.3	65.8	67.3	68.9	70.4
100°	102.9	102.4	102.2	101.5	100.2	98.8	97.5	96.1	97.5	98.8	100.2
102.5°	133.4	132.7	132.4	131.9	130.9	129.9	128.9	127.9	128.9	129.9	130.9
105°	165.5	165.2	165.0	164.7	164.2	163.7	163.2	162.7	163.2	163.7	164.2
107.5°	200.6	200.6	200.6	200.3	199.6	198.9	198.2	197.5	198.2	198.9	199.6
110°	235.4	235.4	235.4	234.9	233.9	232.8	231.8	230.8	231.8	232.8	233.9

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	271.4	271.6	271.7	271.2	270.2	269.2	268.2	267.2	268.2	269.2	270.2
115°	306.8	307.1	307.3	306.8	305.8	304.7	303.7	302.7	303.7	304.7	305.8
117.5°	343.1	344.0	344.4	343.7	342.4	341.0	339.7	338.3	339.7	341.0	342.4
120°	377.9	379.2	379.9	379.2	377.9	376.6	375.2	373.9	375.2	376.6	377.9
122.5°	412.7	413.6	414.0	413.2	411.5	409.8	408.1	406.4	408.1	409.8	411.5
125°	446.5	447.0	447.3	446.5	445.0	443.5	442.0	440.5	442.0	443.5	445.0
127.5°	481.1	481.8	482.1	481.2	479.3	477.5	475.6	473.8	475.6	477.5	479.3
130°	514.2	514.5	514.7	513.6	511.4	509.2	507.0	504.8	507.0	509.2	511.4
132.5°	547.5	547.3	547.2	546.4	544.7	543.0	541.3	539.6	541.3	543.0	544.7
135°	578.7	578.4	578.2	577.3	575.4	573.6	571.7	569.9	571.7	573.6	575.4
137.5°	610.5	610.2	610.0	609.2	607.7	606.2	604.7	603.2	604.7	606.2	607.7
140°	640.8	639.9	639.5	638.7	637.2	635.7	634.2	632.7	634.2	635.7	637.2
142.5°	670.6	670.1	669.8	669.0	667.5	666.0	664.5	663.0	664.5	666.0	667.5
145°	698.6	697.6	697.1	696.5	695.3	694.2	693.0	691.8	693.0	694.2	695.3
147.5°	725.3	724.6	724.3	723.5	722.0	720.5	719.0	717.5	719.0	720.5	722.0
150°	749.5	748.8	748.5	748.0	747.0	746.0	745.0	744.0	745.0	746.0	747.0
152.5°	773.3	772.4	772.0	771.5	770.5	769.4	768.4	767.4	768.4	769.4	770.5
155°	793.9	793.4	793.2	792.9	792.4	791.9	791.4	790.9	791.4	791.9	792.4
157.5°	813.3	813.0	812.8	812.6	812.3	812.0	811.6	811.3	811.6	812.0	812.3
160°	831.3	831.1	831.0	830.8	830.5	830.2	829.8	829.5	829.8	830.2	830.5
162.5°	846.4	846.3	846.2	846.2	846.2	846.2	846.2	846.2	846.2	846.2	846.2
165°	859.8	859.8	859.8	859.9	860.0	860.2	860.3	860.5	860.3	860.2	860.0
167.5°	871.1	871.1	871.1	871.4	871.9	872.4	872.9	873.4	872.9	872.4	871.9
170°	880.7	880.9	881.0	881.2	881.7	882.2	882.7	883.2	882.7	882.2	881.7
172.5°	887.5	887.7	887.8	888.0	888.5	889.0	889.5	890.0	889.5	889.0	888.5
175°	892.6	892.9	893.1	893.3	893.8	894.3	894.8	895.3	894.8	894.3	893.8
177.5°	895.6	895.9	896.1	896.4	896.9	897.4	897.9	898.4	897.9	897.4	896.9
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	564.0	566.2	565.8	561.4	556.6	552.7	545.2	546.1	543.4	543.9	546.5
5°	550.0	550.0	548.3	542.1	534.2	529.9	521.5	519.3	514.1	513.6	513.2
7.5°	535.1	532.9	530.7	522.0	512.3	505.3	493.9	491.3	486.0	482.5	480.8
10°	517.6	514.5	510.1	500.1	488.2	479.5	467.6	464.1	454.0	449.7	447.0
12.5°	498.3	496.6	489.5	481.2	461.9	452.3	435.2	438.7	428.6	419.9	418.5
15°	479.0	472.5	468.5	454.9	431.7	427.3	413.7	406.7	397.5	390.5	390.5
17.5°	460.2	450.1	441.3	426.9	409.8	397.5	387.4	383.9	372.5	365.5	364.2
20°	435.2	423.8	421.6	401.0	389.2	375.6	366.0	357.2	348.9	345.8	343.6
22.5°	411.5	398.4	394.9	377.3	365.5	351.9	342.3	336.2	330.0	327.8	323.9
25°	386.1	378.2	373.0	354.1	341.0	328.3	321.7	317.3	311.6	311.2	308.5
27.5°	361.6	354.1	348.9	330.9	321.2	309.4	304.2	299.3	296.3	295.0	293.6
30°	340.5	332.2	326.1	312.9	301.1	291.4	287.1	284.0	282.2	280.1	279.6
32.5°	317.3	312.5	304.2	294.1	284.9	275.7	273.0	270.8	268.2	267.3	266.9
35°	297.6	291.0	285.7	274.4	270.4	262.5	259.5	257.7	254.2	253.3	252.4
37.5°	278.3	272.2	266.5	259.5	252.0	247.6	245.9	243.2	241.5	241.9	241.0
40°	259.0	254.2	249.8	242.4	238.0	235.8	232.3	229.7	228.8	229.2	228.8
42.5°	240.2	235.8	233.2	227.5	223.1	220.9	218.7	216.1	217.4	217.4	218.7
45°	223.1	219.1	217.4	213.0	210.4	206.9	204.7	204.2	206.0	205.5	205.5
47.5°	205.5	204.2	202.0	198.1	194.6	192.4	192.0	192.0	193.7	194.6	194.2
50°	192.0	189.3	186.7	183.6	181.0	180.1	178.8	179.7	181.4	181.4	182.3
52.5°	174.9	173.1	172.2	169.6	167.9	167.9	167.9	168.3	169.6	170.9	170.5
55°	160.0	158.7	157.8	156.5	154.3	154.7	154.3	155.1	156.5	157.8	158.7
57.5°	144.2	143.8	142.9	140.7	140.7	140.2	141.6	142.0	144.2	145.1	146.4
60°	130.2	128.9	128.9	127.1	127.1	127.1	128.4	129.7	131.5	131.9	132.8
62.5°	115.3	115.3	114.8	113.5	113.5	114.8	115.3	117.0	117.9	117.9	119.2
65°	101.2	100.8	100.4	100.8	101.2	101.2	102.6	103.4	104.3	104.7	105.2
67.5°	87.2	86.8	87.7	87.2	88.1	89.8	89.4	90.7	92.0	92.0	92.5
70°	74.1	74.9	74.5	75.4	74.9	75.8	77.1	77.6	77.6	78.0	79.3
72.5°	61.8	61.8	61.8	61.4	61.8	62.7	63.5	64.0	64.9	65.3	66.6
75°	50.0	50.0	49.1	50.0	50.0	50.8	51.7	51.7	51.7	52.6	53.9
77.5°	37.7	38.1	37.7	38.6	38.6	39.0	39.9	39.4	40.3	40.8	41.2
80°	27.6	27.2	27.2	27.2	27.6	27.6	28.5	28.9	28.9	30.2	29.4
82.5°	17.5	18.0	17.5	18.0	18.0	18.4	18.0	18.4	18.8	19.7	19.3
85°	10.1	9.6	9.6	10.1	9.6	9.6	10.1	9.6	10.1	9.6	10.1
87.5°	3.9	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	8.8	9.8	11.7	15.4	19.1	22.8	26.5	26.2	25.8	25.5	25.2
92.5°	22.0	22.7	22.8	23.0	23.1	23.3	23.5	23.7	23.8	24.0	24.1
95°	46.1	46.9	47.1	47.4	47.7	48.1	48.4	48.4	48.4	48.4	48.4
97.5°	71.9	72.7	73.0	73.7	74.4	75.0	75.7	75.7	75.7	75.7	75.7
100°	101.5	102.2	102.4	102.9	103.4	103.9	104.4	104.4	104.4	104.4	104.4
102.5°	131.9	132.4	132.7	133.4	134.1	134.8	135.5	135.7	135.8	136.0	136.1
105°	164.7	165.0	165.2	165.5	165.8	166.2	166.5	166.8	167.2	167.5	167.8
107.5°	200.3	200.6	200.6	200.6	200.6	200.6	200.6	200.8	200.9	201.1	201.2
110°	234.9	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	271.2	271.7	271.6	271.4	271.3	271.1	270.9	270.4	269.9	269.4	268.9
115°	306.8	307.3	307.1	306.8	306.5	306.1	305.8	305.6	305.4	305.3	305.1
117.5°	343.7	344.4	344.0	343.1	342.3	341.4	340.6	340.1	339.6	339.1	338.6
120°	379.2	379.9	379.2	377.9	376.6	375.2	373.9	373.9	373.9	373.9	373.9
122.5°	413.2	414.0	413.6	412.7	411.9	411.0	410.2	409.7	409.2	408.7	408.2
125°	446.5	447.3	447.0	446.5	446.0	445.5	445.0	444.5	444.0	443.5	443.0
127.5°	481.2	482.1	481.8	481.1	480.4	479.8	479.1	478.4	477.8	477.1	476.4
130°	513.6	514.7	514.5	514.2	513.8	513.5	513.1	512.8	512.4	512.1	511.8
132.5°	546.4	547.2	547.3	547.5	547.6	547.8	548.0	547.2	546.3	545.5	544.6
135°	577.3	578.2	578.4	578.7	579.0	579.4	579.7	579.5	579.4	579.2	579.1
137.5°	609.2	610.0	610.2	610.5	610.8	611.2	611.5	611.3	611.2	611.0	610.9
140°	638.7	639.5	639.9	640.8	641.6	642.5	643.3	643.3	643.3	643.3	643.3
142.5°	669.0	669.8	670.1	670.6	671.1	671.6	672.1	672.3	672.4	672.6	672.7
145°	696.5	697.1	697.6	698.6	699.6	700.6	701.6	701.8	702.0	702.1	702.3
147.5°	723.5	724.3	724.6	725.3	726.0	726.6	727.3	727.6	728.0	728.3	728.6
150°	748.0	748.5	748.8	749.5	750.2	750.8	751.5	752.0	752.5	753.0	753.5
152.5°	771.5	772.0	772.4	773.3	774.1	775.0	775.8	776.5	777.1	777.8	778.5
155°	792.9	793.2	793.4	793.9	794.4	794.9	795.4	796.2	797.1	797.9	798.8
157.5°	812.6	812.8	813.0	813.3	813.7	814.0	814.4	815.6	816.8	817.9	819.1
160°	830.8	831.0	831.1	831.3	831.4	831.6	831.8	832.8	833.8	834.8	835.8
162.5°	846.2	846.2	846.3	846.4	846.6	846.7	846.9	848.1	849.3	850.4	851.6
165°	859.9	859.8	859.8	859.8	859.8	859.8	859.8	861.0	862.2	863.3	864.5
167.5°	871.4	871.1	871.1	871.1	871.1	871.1	871.1	872.3	873.5	874.6	875.8
170°	881.2	881.0	880.9	880.7	880.6	880.4	880.2	881.4	882.6	883.7	884.9
172.5°	888.0	887.8	887.7	887.5	887.4	887.2	887.0	888.2	889.4	890.5	891.7
175°	893.3	893.1	892.9	892.6	892.3	891.9	891.6	892.8	894.0	895.1	896.3
177.5°	896.4	896.1	895.9	895.6	895.3	894.9	894.6	895.6	896.6	897.6	898.6
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	543.4	544.8	541.7	540.8	541.7	538.6	539.5	540.4	540.4	541.7	542.6
5°	511.9	510.1	507.1	506.2	505.3	506.6	505.8	507.1	507.5	510.6	511.0
7.5°	480.8	478.1	475.5	472.9	472.0	469.8	472.0	472.0	475.1	474.2	476.4
10°	444.0	443.5	440.0	438.7	437.0	433.4	438.3	437.0	439.1	443.1	444.0
12.5°	416.8	412.0	414.2	408.0	410.2	406.7	407.1	407.1	410.7	411.1	410.2
15°	390.9	387.0	381.3	378.7	377.3	375.6	381.3	381.7	379.1	385.2	383.0
17.5°	364.6	364.6	359.4	358.1	354.6	356.3	355.4	355.9	355.0	359.4	361.6
20°	341.8	339.7	337.9	338.3	334.0	333.1	332.2	333.1	336.2	339.2	340.1
22.5°	323.4	322.1	317.7	318.6	315.1	316.4	315.6	317.7	318.2	318.2	321.2
25°	305.9	304.2	304.6	302.8	301.5	301.5	300.2	301.5	303.3	304.2	304.6
27.5°	292.8	291.4	289.3	287.9	288.8	286.6	288.4	289.7	289.7	288.8	289.7
30°	277.0	277.9	277.9	273.5	275.2	274.4	275.7	276.5	276.5	277.0	276.1
32.5°	266.5	263.8	263.4	263.0	263.0	261.2	261.2	262.5	263.0	263.4	264.7
35°	252.4	252.4	250.2	251.6	249.8	250.2	249.8	250.2	251.1	249.8	251.1
37.5°	239.7	240.2	239.3	240.2	240.6	239.7	238.9	240.6	239.7	239.7	238.9
40°	228.8	228.3	228.8	228.8	228.8	229.2	228.3	228.3	228.3	227.5	226.6
42.5°	219.6	216.9	217.8	218.3	216.9	216.9	217.4	216.9	218.3	215.6	215.6
45°	206.4	205.5	206.0	206.0	206.9	205.5	206.4	206.9	205.5	205.1	204.2
47.5°	194.6	195.5	194.6	195.5	195.5	196.3	194.6	195.0	195.5	193.7	192.4
50°	182.8	182.8	184.1	183.6	184.1	183.2	183.2	182.8	183.2	182.3	181.0
52.5°	171.8	170.5	172.7	172.2	171.8	171.4	170.9	171.4	170.5	169.6	169.6
55°	158.2	158.2	159.5	160.0	160.0	159.1	158.2	158.7	158.2	157.8	157.3
57.5°	147.3	145.5	146.4	146.8	146.8	145.5	146.4	145.5	145.5	145.9	144.6
60°	133.2	133.2	132.4	133.7	133.7	132.8	132.8	133.2	132.4	131.9	131.5
62.5°	118.3	118.8	120.1	120.5	121.0	120.1	119.2	119.6	119.6	118.3	118.8
65°	105.6	106.5	108.3	107.8	106.9	107.4	106.5	106.9	105.6	106.1	104.7
67.5°	93.4	92.9	93.4	93.4	94.2	93.8	92.9	92.9	92.5	93.8	92.5
70°	80.2	80.2	80.2	80.2	80.6	81.1	80.2	79.3	79.8	78.9	78.4
72.5°	66.6	67.1	66.6	67.5	66.2	67.1	67.1	66.6	66.2	66.2	66.2
75°	53.9	54.8	53.5	53.9	53.5	54.3	53.9	53.9	53.0	52.6	53.0
77.5°	41.2	41.6	40.8	41.2	40.8	41.2	41.2	40.8	40.8	40.8	40.8
80°	29.4	29.8	29.4	28.9	28.5	29.4	28.5	28.9	29.4	28.9	29.8
82.5°	18.8	18.8	18.4	18.8	18.0	18.0	18.4	18.4	18.0	18.8	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.6	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	25.0	25.1	25.2	25.4	25.5	25.7	25.5	25.4	25.2	25.1	25.0
92.5°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2
95°	48.4	48.2	47.9	47.6	47.2	46.9	47.2	47.6	47.9	48.2	48.4
97.5°	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7
100°	104.4	104.3	104.2	104.0	103.9	103.7	103.9	104.0	104.2	104.3	104.4
102.5°	136.2	136.1	136.0	135.8	135.7	135.5	135.7	135.8	136.0	136.1	136.2
105°	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0
107.5°	201.3	200.9	200.0	199.2	198.3	197.5	198.3	199.2	200.0	200.9	201.3
110°	235.4	235.1	234.6	234.1	233.6	233.1	233.6	234.1	234.6	235.1	235.4

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	268.7	268.5	268.2	267.9	267.5	267.2	267.5	267.9	268.2	268.5	268.7
115°	305.0	304.7	304.2	303.7	303.2	302.7	303.2	303.7	304.2	304.7	305.0
117.5°	338.3	338.0	337.5	337.0	336.5	336.0	336.5	337.0	337.5	338.0	338.3
120°	373.9	373.6	373.1	372.6	372.1	371.6	372.1	372.6	373.1	373.6	373.9
122.5°	407.9	407.7	407.4	407.1	406.7	406.4	406.7	407.1	407.4	407.7	407.9
125°	442.8	442.7	442.5	442.4	442.2	442.0	442.2	442.4	442.5	442.7	442.8
127.5°	476.1	475.8	475.3	474.8	474.3	473.8	474.3	474.8	475.3	475.8	476.1
130°	511.6	511.3	510.6	509.9	509.3	508.6	509.3	509.9	510.6	511.3	511.6
132.5°	544.2	543.9	543.4	542.9	542.4	541.9	542.4	542.9	543.4	543.9	544.2
135°	579.0	578.7	578.2	577.7	577.2	576.7	577.2	577.7	578.2	578.7	579.0
137.5°	610.8	610.5	609.8	609.1	608.4	607.7	608.4	609.1	609.8	610.5	610.8
140°	643.3	643.0	642.3	641.6	641.0	640.3	641.0	641.6	642.3	643.0	643.3
142.5°	672.8	672.5	671.8	671.1	670.5	669.8	670.5	671.1	671.8	672.5	672.8
145°	702.4	702.1	701.4	700.7	700.0	699.3	700.0	700.7	701.4	702.1	702.4
147.5°	728.8	728.5	727.8	727.1	726.5	725.8	726.5	727.1	727.8	728.5	728.8
150°	753.8	753.5	753.0	752.5	752.0	751.5	752.0	752.5	753.0	753.5	753.8
152.5°	778.8	778.5	777.8	777.1	776.5	775.8	776.5	777.1	777.8	778.5	778.8
155°	799.2	799.0	798.5	798.0	797.5	797.0	797.5	798.0	798.5	799.0	799.2
157.5°	819.7	819.3	818.4	817.6	816.7	815.9	816.7	817.6	818.4	819.3	819.7
160°	836.3	836.0	835.3	834.6	834.0	833.3	834.0	834.6	835.3	836.0	836.3
162.5°	852.2	851.8	850.9	850.1	849.2	848.4	849.2	850.1	850.9	851.8	852.2
165°	865.1	864.7	863.8	863.0	862.1	861.3	862.1	863.0	863.8	864.7	865.1
167.5°	876.4	876.0	875.1	874.3	873.4	872.6	873.4	874.3	875.1	876.0	876.4
170°	885.5	885.0	884.0	883.0	882.0	881.0	882.0	883.0	884.0	885.0	885.5
172.5°	892.3	891.8	890.8	889.8	888.8	887.8	888.8	889.8	890.8	891.8	892.3
175°	896.9	896.4	895.4	894.3	893.3	892.3	893.3	894.3	895.4	896.4	896.9
177.5°	899.1	898.6	897.6	896.6	895.6	894.6	895.6	896.6	897.6	898.6	899.1
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	541.3	544.8	543.4	538.6	544.3	544.3	548.3	548.3	553.1	554.8	557.5
5°	510.6	513.2	515.4	513.2	517.2	523.3	526.8	529.9	536.4	539.1	543.0
7.5°	477.7	482.5	484.7	484.7	491.3	498.3	505.3	509.7	518.9	522.4	526.4
10°	445.7	451.4	455.8	455.4	466.3	470.7	479.5	489.5	498.7	504.0	509.7
12.5°	412.0	415.0	421.2	429.9	432.6	440.5	450.5	463.2	479.9	484.7	493.0
15°	383.9	392.2	397.1	401.0	407.1	414.6	425.6	437.8	454.5	465.0	473.8
17.5°	360.3	371.2	374.3	373.4	381.3	392.7	405.4	414.6	429.5	442.2	450.5
20°	341.0	345.4	350.6	352.8	358.9	371.2	383.5	394.0	406.3	416.4	426.0
22.5°	321.7	325.2	329.6	333.5	338.3	345.4	357.2	370.3	382.2	391.8	402.8
25°	305.9	308.1	312.0	315.1	320.4	325.2	333.5	348.0	362.0	367.7	377.3
27.5°	290.6	292.3	295.0	298.5	301.1	305.9	313.4	325.2	339.7	345.4	358.5
30°	277.0	278.3	280.9	282.7	284.0	289.7	295.4	304.6	315.6	323.4	333.1
32.5°	264.3	265.6	268.2	268.7	270.4	273.5	278.7	287.1	296.7	303.3	311.6
35°	250.2	251.1	253.8	254.6	255.9	258.6	262.5	268.7	277.4	282.2	289.7
37.5°	239.3	238.9	240.6	241.9	243.7	245.0	246.3	252.4	259.0	263.4	269.1
40°	227.5	226.6	227.0	228.8	229.7	231.4	231.4	237.5	241.9	245.4	249.8
42.5°	215.6	215.2	214.3	215.2	216.1	216.5	216.9	221.3	225.7	228.8	233.6
45°	203.8	203.4	202.5	202.9	202.9	203.8	205.1	206.9	209.9	212.6	215.2
47.5°	192.8	192.0	190.6	190.2	191.1	191.1	191.1	192.8	195.9	196.8	199.4
50°	181.4	180.1	178.4	177.5	177.5	177.1	177.9	178.4	181.0	181.9	184.1
52.5°	169.2	168.3	166.5	164.8	165.2	164.3	164.8	165.2	166.1	167.4	168.7
55°	156.9	155.1	153.8	153.4	152.1	152.1	150.8	152.5	152.1	152.5	154.3
57.5°	145.1	143.3	141.1	140.2	138.9	138.5	137.6	137.2	137.6	138.9	140.2
60°	131.0	130.2	128.9	127.5	126.7	125.3	124.5	124.5	124.0	124.0	124.5
62.5°	117.5	117.0	115.3	114.8	113.9	113.1	111.8	110.9	110.9	111.8	112.2
65°	104.3	103.9	102.6	102.1	99.9	99.0	98.6	98.2	97.3	97.3	97.3
67.5°	92.0	90.7	90.7	88.5	86.8	85.9	85.0	84.6	84.6	84.6	85.0
70°	78.4	78.4	77.1	75.8	74.1	74.5	73.2	71.9	71.9	71.0	71.4
72.5°	65.3	64.9	63.5	63.1	61.8	60.5	59.6	60.5	59.2	58.7	59.2
75°	52.6	52.2	51.3	50.4	50.8	49.5	48.2	47.8	47.8	46.9	46.9
77.5°	40.3	41.2	39.4	39.0	38.1	37.3	36.8	36.4	36.4	36.4	37.3
80°	28.0	28.5	28.5	27.6	28.0	26.7	26.7	26.7	25.4	25.9	26.3
82.5°	18.0	18.0	17.5	18.0	17.5	17.5	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.6	9.2	10.1	9.6	9.6	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	25.2	25.5	25.8	26.2	26.5	22.8	19.1	15.4	11.7	9.8	8.8
92.5°	24.1	24.0	23.8	23.7	23.5	23.3	23.1	23.0	22.8	22.7	22.0
95°	48.4	48.4	48.4	48.4	48.4	48.1	47.7	47.4	47.1	46.9	46.1
97.5°	75.7	75.7	75.7	75.7	75.7	75.0	74.4	73.7	73.0	72.7	71.9
100°	104.4	104.4	104.4	104.4	104.4	103.9	103.4	102.9	102.4	102.2	101.5
102.5°	136.1	136.0	135.8	135.7	135.5	134.8	134.1	133.4	132.7	132.4	131.9
105°	167.8	167.5	167.2	166.8	166.5	166.2	165.8	165.5	165.2	165.0	164.7
107.5°	201.2	201.1	200.9	200.8	200.6	200.6	200.6	200.6	200.6	200.6	200.3
110°	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	234.9

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	268.9	269.4	269.9	270.4	270.9	271.1	271.3	271.4	271.6	271.7	271.2
115°	305.1	305.3	305.4	305.6	305.8	306.1	306.5	306.8	307.1	307.3	306.8
117.5°	338.6	339.1	339.6	340.1	340.6	341.4	342.3	343.1	344.0	344.4	343.7
120°	373.9	373.9	373.9	373.9	373.9	375.2	376.6	377.9	379.2	379.9	379.2
122.5°	408.2	408.7	409.2	409.7	410.2	411.0	411.9	412.7	413.6	414.0	413.2
125°	443.0	443.5	444.0	444.5	445.0	445.5	446.0	446.5	447.0	447.3	446.5
127.5°	476.4	477.1	477.8	478.4	479.1	479.8	480.4	481.1	481.8	482.1	481.2
130°	511.8	512.1	512.4	512.8	513.1	513.5	513.8	514.2	514.5	514.7	513.6
132.5°	544.6	545.5	546.3	547.2	548.0	547.8	547.6	547.5	547.3	547.2	546.4
135°	579.1	579.2	579.4	579.5	579.7	579.4	579.0	578.7	578.4	578.2	577.3
137.5°	610.9	611.0	611.2	611.3	611.5	611.2	610.8	610.5	610.2	610.0	609.2
140°	643.3	643.3	643.3	643.3	643.3	642.5	641.6	640.8	639.9	639.5	638.7
142.5°	672.7	672.6	672.4	672.3	672.1	671.6	671.1	670.6	670.1	669.8	669.0
145°	702.3	702.1	702.0	701.8	701.6	700.6	699.6	698.6	697.6	697.1	696.5
147.5°	728.6	728.3	728.0	727.6	727.3	726.6	726.0	725.3	724.6	724.3	723.5
150°	753.5	753.0	752.5	752.0	751.5	750.8	750.2	749.5	748.8	748.5	748.0
152.5°	778.5	777.8	777.1	776.5	775.8	775.0	774.1	773.3	772.4	772.0	771.5
155°	798.8	797.9	797.1	796.2	795.4	794.9	794.4	793.9	793.4	793.2	792.9
157.5°	819.1	817.9	816.8	815.6	814.4	814.0	813.7	813.3	813.0	812.8	812.6
160°	835.8	834.8	833.8	832.8	831.8	831.6	831.4	831.3	831.1	831.0	830.8
162.5°	851.6	850.4	849.3	848.1	846.9	846.7	846.6	846.4	846.3	846.2	846.2
165°	864.5	863.3	862.2	861.0	859.8	859.8	859.8	859.8	859.8	859.8	859.9
167.5°	875.8	874.6	873.5	872.3	871.1	871.1	871.1	871.1	871.1	871.1	871.4
170°	884.9	883.7	882.6	881.4	880.2	880.4	880.6	880.7	880.9	881.0	881.2
172.5°	891.7	890.5	889.4	888.2	887.0	887.2	887.4	887.5	887.7	887.8	888.0
175°	896.3	895.1	894.0	892.8	891.6	891.9	892.3	892.6	892.9	893.1	893.3
177.5°	898.6	897.6	896.6	895.6	894.6	894.9	895.3	895.6	895.9	896.1	896.4
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	570.2	570.2	570.2	570.2
2.5°	559.7	559.7	566.2	573.3
5°	547.4	550.5	561.0	570.6
7.5°	535.6	540.8	554.0	566.2
10°	521.1	528.1	544.3	558.8
12.5°	507.1	513.6	532.5	548.7
15°	487.4	495.7	515.8	536.0
17.5°	467.6	476.0	500.5	524.2
20°	444.4	455.4	483.0	514.5
22.5°	422.9	436.5	467.2	492.6
25°	399.3	420.3	448.8	481.7
27.5°	378.2	399.3	428.2	461.5
30°	354.6	376.0	405.8	436.5
32.5°	331.8	351.5	380.4	418.1
35°	308.1	326.9	355.0	393.1
37.5°	286.6	305.0	335.7	370.8
40°	265.6	284.9	311.2	346.2
42.5°	245.9	263.0	286.6	321.7
45°	227.9	240.2	262.1	295.0
47.5°	209.1	220.0	240.2	273.0
50°	191.5	200.7	218.3	248.9
52.5°	174.4	182.3	198.5	223.1
55°	159.1	166.5	178.4	202.5
57.5°	143.3	149.0	160.4	179.7
60°	128.0	133.2	142.4	158.2
62.5°	112.6	117.0	125.8	138.5
65°	99.0	102.6	109.1	120.1
67.5°	85.9	88.1	93.4	102.1
70°	73.2	74.9	79.3	86.3
72.5°	59.6	61.4	66.2	71.0
75°	48.2	48.6	52.2	56.1
77.5°	37.7	37.3	39.9	43.0
80°	25.9	27.2	29.4	30.7
82.5°	17.5	18.0	18.8	19.7
85°	9.6	10.1	10.1	11.4
87.5°	3.9	4.4	4.4	4.8
90°	6.8	4.8	2.8	0.8
92.5°	20.7	19.4	18.0	16.7
95°	44.4	42.7	41.1	39.4
97.5°	70.4	68.9	67.3	65.8
100°	100.2	98.8	97.5	96.1
102.5°	130.9	129.9	128.9	127.9
105°	164.2	163.7	163.2	162.7
107.5°	199.6	198.9	198.2	197.5
110°	233.9	232.8	231.8	230.8

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	270.2	269.2	268.2	267.2
115°	305.8	304.7	303.7	302.7
117.5°	342.4	341.0	339.7	338.3
120°	377.9	376.6	375.2	373.9
122.5°	411.5	409.8	408.1	406.4
125°	445.0	443.5	442.0	440.5
127.5°	479.3	477.5	475.6	473.8
130°	511.4	509.2	507.0	504.8
132.5°	544.7	543.0	541.3	539.6
135°	575.4	573.6	571.7	569.9
137.5°	607.7	606.2	604.7	603.2
140°	637.2	635.7	634.2	632.7
142.5°	667.5	666.0	664.5	663.0
145°	695.3	694.2	693.0	691.8
147.5°	722.0	720.5	719.0	717.5
150°	747.0	746.0	745.0	744.0
152.5°	770.5	769.4	768.4	767.4
155°	792.4	791.9	791.4	790.9
157.5°	812.3	812.0	811.6	811.3
160°	830.5	830.2	829.8	829.5
162.5°	846.2	846.2	846.2	846.2
165°	860.0	860.2	860.3	860.5
167.5°	871.9	872.4	872.9	873.4
170°	881.7	882.2	882.7	883.2
172.5°	888.5	889.0	889.5	890.0
175°	893.8	894.3	894.8	895.3
177.5°	896.9	897.4	897.9	898.4
180°	896.9	896.9	896.9	896.9

TEST NUMBER: P998259

CATALOG NUMBER: SA2XXDIP-B290D725UB27-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.71	12.42	12.80	13.50	14.99	9.20	9.91	10.29	11.00	12.49
	3H	12.51	13.14	13.61	14.24	15.75	10.53	11.17	11.63	12.26	13.77
	4H	12.67	13.27	13.78	14.37	15.88	10.99	11.59	12.10	12.69	14.20
	6H	12.71	13.26	13.83	14.36	15.89	11.29	11.84	12.41	12.94	14.47
	8H	12.68	13.21	13.80	14.32	15.84	11.37	11.89	12.49	13.01	14.53
	12H	12.64	13.14	13.77	14.25	15.79	11.40	11.90	12.53	13.01	14.55
4H	2H	11.73	12.33	12.85	13.43	14.94	9.63	10.23	10.75	11.33	12.84
	3H	12.70	13.20	13.82	14.32	15.85	11.07	11.58	12.20	12.70	14.23
	4H	12.97	13.43	14.10	14.54	16.09	11.60	12.06	12.73	13.18	14.72
	6H	13.09	13.48	14.22	14.62	16.16	11.97	12.37	13.11	13.50	15.04
	8H	13.08	13.45	14.22	14.58	16.13	12.08	12.45	13.21	13.58	15.13
	12H	13.04	13.37	14.19	14.51	16.07	12.13	12.46	13.28	13.60	15.16
8H	4H	12.96	13.33	14.10	14.46	16.02	11.73	12.10	12.87	13.23	14.78
	6H	13.14	13.44	14.29	14.61	16.16	12.16	12.47	13.32	13.64	15.19
	8H	13.17	13.43	14.33	14.58	16.15	12.31	12.58	13.47	13.73	15.30
	12H	13.14	13.38	14.31	14.52	16.13	12.40	12.63	13.56	13.78	15.38
12H	4H	12.91	13.25	14.07	14.39	15.95	11.70	12.03	12.85	13.17	14.73
	6H	13.12	13.38	14.28	14.53	16.10	12.16	12.43	13.32	13.58	15.15
	8H	13.14	13.37	14.31	14.52	16.13	12.31	12.54	13.48	13.69	15.30