

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999222

Luminaire Tested: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999222
REPORT IS A COMBINATION OF REPORTS P984971 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7164.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	46	44	42
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	23	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26115	26115	26115	26115
5°	26178	27845	26278	22153
10°	25874	30397	26037	18265
15°	25247	32063	25598	15385
20°	24853	30104	24853	13372
25°	24061	25863	24170	11959
30°	22757	20330	23191	10831
35°	21603	14059	21964	9910
40°	20276	10614	20506	9175
45°	18638	8722	18944	8382
50°	17225	7655	17256	7674
55°	15612	6524	15713	6904
60°	13892	5449	14083	6025
65°	12353	4432	12577	5146
70°	10818	3478	11095	4150
75°	9079	2525	9437	3009
80°	7090	1600	7593	1787
85°	4661	804	5015	597

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 26997 cd/sqm

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.1	2.2
10°-20°	457.4	6.4
20°-30°	663.8	9.3
30°-40°	699.8	9.8
40°-50°	619.2	8.6
50°-60°	494.4	6.9
60°-70°	335.8	4.7
70°-80°	171.8	2.4
80°-90°	42.7	0.6
90°-100°	39.6	0.6
100°-110°	147.7	2.1
110°-120°	391.6	5.5
120°-130°	649.6	9.1
130°-140°	690.0	9.6
140°-150°	641.3	9.0
150°-160°	515.6	7.2
160°-170°	332.2	4.6
170°-180°	114.3	1.6
0°-30°	1278.3	17.8
0°-40°	1978.1	27.6
0°-60°	3091.7	43.2
0°-90°	3642.1	50.8
90°-120°	578.9	8.1
90°-150°	2559.8	35.7
90°-180°	3522.0	49.2
0°-180°	7164.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1650	1650	1650	1650	1650	
5°	1651	1843	1657	1466	1651	157
15°	1551	2265	1572	1087	1551	438
25°	1394	1887	1400	872	1394	637
35°	1138	1027	1156	724	1138	712
45°	853	619	867	595	853	662
55°	586	435	590	460	586	523
65°	348	268	354	311	348	345
75°	162	132	169	157	162	174
85°	33	34	36	25	33	38
90°	1	24	1	24	1	5
95°	56	37	56	37	56	67
105°	264	66	264	66	264	282
115°	500	71	500	71	500	492
125°	707	743	707	743	707	630
135°	874	903	874	903	874	676
145°	1014	1030	1014	1030	1014	634
155°	1117	1118	1117	1118	1117	515
165°	1177	1174	1177	1174	1177	333
175°	1204	1197	1204	1197	1204	115
180°	1201	1201	1201	1201	1201	

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1658.7	1662.5	1668.8	1670.1	1682.8	1692.9	1704.3	1704.3	1708.2	1706.9	1696.7
5°	1651.1	1662.5	1679.0	1692.9	1715.8	1725.9	1741.1	1752.5	1762.7	1770.3	1769.0
7.5°	1638.4	1658.7	1682.8	1709.4	1739.9	1757.6	1779.2	1799.5	1813.4	1826.1	1835.0
10°	1616.8	1651.1	1684.1	1719.6	1758.9	1783.0	1808.3	1835.0	1856.5	1880.6	1903.4
12.5°	1587.7	1637.1	1677.7	1724.6	1772.8	1799.5	1840.0	1860.3	1902.2	1963.0	1979.5
15°	1550.9	1618.1	1656.2	1715.8	1779.2	1800.7	1856.5	1889.5	1975.7	2013.8	2059.4
17.5°	1516.7	1591.5	1642.2	1710.7	1772.8	1814.7	1869.2	1936.4	2008.7	2063.2	2113.9
20°	1488.8	1561.0	1621.9	1698.0	1776.6	1829.9	1887.0	1968.1	2046.7	2102.5	2141.8
22.5°	1425.4	1517.9	1588.9	1673.9	1769.0	1842.6	1897.1	1985.9	2070.8	2105.1	2139.3
25°	1393.7	1473.5	1556.0	1652.4	1763.9	1851.4	1898.4	1997.3	2072.1	2084.8	2092.4
27.5°	1335.3	1425.4	1521.7	1632.1	1762.7	1836.2	1895.8	1985.9	2045.5	2036.6	2013.8
30°	1263.0	1373.4	1479.9	1599.1	1744.9	1824.8	1880.6	1963.0	1993.5	1947.8	1907.2
32.5°	1209.8	1313.8	1431.7	1569.9	1724.6	1800.7	1855.3	1919.9	1926.3	1843.8	1775.4
35°	1137.5	1252.9	1386.0	1531.9	1690.4	1758.9	1809.6	1848.9	1818.5	1703.1	1621.9
37.5°	1072.8	1187.0	1329.0	1477.4	1643.5	1710.7	1751.3	1757.6	1682.8	1581.3	1462.1
40°	1001.8	1119.7	1268.1	1424.1	1591.5	1649.8	1675.2	1656.2	1548.4	1430.4	1292.2
42.5°	930.8	1047.5	1207.2	1367.0	1525.5	1575.0	1585.1	1533.2	1401.3	1263.0	1103.3
45°	853.4	975.2	1135.0	1296.0	1449.5	1477.4	1478.6	1403.8	1247.8	1103.3	954.9
47.5°	790.0	902.9	1061.4	1222.5	1351.8	1370.8	1363.2	1277.0	1107.1	944.7	815.4
50°	720.3	828.1	985.3	1143.8	1254.2	1259.2	1240.2	1117.2	951.1	802.7	700.0
52.5°	645.5	754.5	899.1	1051.3	1150.2	1142.6	1105.8	973.9	817.9	694.9	616.3
55°	585.9	682.2	817.9	966.3	1036.0	1014.5	973.9	839.5	716.5	612.5	544.0
57.5°	519.9	604.9	738.0	867.4	908.0	887.7	847.1	721.6	607.4	528.8	483.2
60°	457.8	535.1	651.8	759.6	791.3	769.7	722.8	610.0	527.5	461.6	427.4
62.5°	400.7	467.9	565.6	664.5	677.2	655.6	615.0	523.7	452.7	400.7	375.4
65°	347.5	410.9	489.5	564.3	575.7	552.9	511.1	445.1	385.5	352.5	328.4
67.5°	295.5	346.2	415.9	470.5	476.8	455.3	421.0	367.8	331.0	295.5	277.7
70°	249.8	287.9	342.4	386.8	389.3	369.0	351.3	303.1	275.2	249.8	235.9
72.5°	205.4	232.1	273.9	306.9	308.2	295.5	279.0	248.6	224.5	206.7	192.8
75°	162.3	185.1	210.5	239.7	238.4	228.3	215.6	196.6	176.3	164.9	158.5
77.5°	124.3	138.2	158.5	177.5	177.5	172.5	164.9	150.9	138.2	126.8	120.5
80°	88.8	97.6	114.1	120.5	123.0	121.7	115.4	105.3	100.2	91.3	88.8
82.5°	57.1	63.4	71.0	77.4	81.2	78.6	77.4	72.3	64.7	62.1	59.6
85°	33.0	35.5	39.3	43.1	44.4	43.1	45.7	41.8	38.0	38.0	36.8
87.5°	13.9	15.2	17.8	17.8	19.0	19.0	17.8	19.0	19.0	17.8	16.5
90°	0.9	3.0	5.1	7.2	9.3	10.4	11.2	12.7	14.3	15.8	17.4
92.5°	21.7	20.9	20.2	19.4	18.7	18.3	18.6	19.2	19.7	20.3	20.9
95°	56.5	50.1	43.7	37.4	31.0	27.8	28.5	29.8	31.2	32.5	33.9
97.5°	101.7	85.9	70.0	54.2	38.3	30.4	31.9	35.0	38.1	41.2	44.3
100°	153.9	127.4	101.0	74.5	48.0	34.8	36.4	39.7	43.0	46.2	49.5
102.5°	211.2	210.8	210.4	210.1	209.7	209.5	191.9	156.8	121.6	86.5	51.3
105°	264.3	270.1	275.9	281.6	287.4	290.3	263.9	211.2	158.5	105.7	53.0
107.5°	326.0	330.8	335.6	340.5	345.3	347.7	315.2	250.1	185.0	119.9	54.8
110°	385.1	389.1	393.2	397.2	401.3	403.3	375.4	319.6	263.7	207.9	152.1

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	440.7	444.2	447.7	451.2	454.7	456.4	454.8	451.5	448.2	444.9	441.6
115°	499.8	503.1	506.4	509.7	513.0	514.6	517.0	521.8	526.7	531.5	536.3
117.5°	551.1	555.0	558.8	562.7	566.6	568.5	570.1	573.4	576.7	580.0	583.3
120°	608.5	611.4	614.3	617.2	620.1	621.5	623.2	626.7	630.2	633.7	637.2
122.5°	657.2	660.3	663.4	666.5	669.6	671.1	673.0	676.9	680.8	684.6	688.5
125°	706.7	709.2	711.7	714.2	716.7	718.0	719.8	723.5	727.2	730.8	734.5
127.5°	751.9	754.6	757.3	760.0	762.7	764.1	765.5	768.4	771.3	774.2	777.1
130°	794.5	797.6	800.7	803.8	806.9	808.4	809.5	811.6	813.7	815.9	818.0
132.5°	838.0	840.5	843.0	845.5	848.0	849.3	850.4	852.5	854.6	856.7	858.8
135°	874.5	877.6	880.7	883.8	886.9	888.4	889.3	891.0	892.7	894.5	896.2
137.5°	912.7	915.0	917.4	919.7	922.0	923.2	924.2	926.1	928.0	930.0	931.9
140°	950.1	951.7	953.2	954.8	956.3	957.1	958.2	960.3	962.4	964.5	966.6
142.5°	981.4	982.8	984.1	985.5	986.8	987.5	988.8	991.3	993.8	996.3	998.8
145°	1014.4	1014.2	1014.0	1013.9	1013.7	1013.6	1015.2	1018.5	1021.8	1025.0	1028.3
147.5°	1043.1	1042.5	1041.9	1041.4	1040.8	1040.5	1042.1	1045.4	1048.7	1052.0	1055.3
150°	1070.9	1069.6	1068.2	1066.9	1065.6	1064.9	1066.4	1069.5	1072.6	1075.7	1078.8
152.5°	1094.4	1092.9	1091.3	1089.8	1088.3	1087.5	1088.9	1091.8	1094.7	1097.6	1100.5
155°	1117.0	1115.3	1113.5	1111.8	1110.1	1109.2	1110.4	1112.7	1115.0	1117.3	1119.6
157.5°	1135.3	1133.7	1132.2	1130.6	1129.1	1128.3	1129.2	1130.9	1132.6	1134.4	1136.1
160°	1150.9	1149.7	1148.6	1147.4	1146.3	1145.7	1146.3	1147.4	1148.6	1149.7	1150.9
162.5°	1164.8	1163.6	1162.5	1161.3	1160.2	1159.6	1160.1	1161.1	1162.0	1163.0	1164.0
165°	1177.0	1175.8	1174.7	1173.5	1172.4	1171.8	1172.1	1172.7	1173.2	1173.8	1174.4
167.5°	1186.6	1185.4	1184.2	1183.1	1181.9	1181.3	1181.6	1182.2	1182.7	1183.3	1183.9
170°	1194.4	1193.2	1192.1	1190.9	1189.8	1189.2	1189.4	1189.8	1190.1	1190.5	1190.9
172.5°	1199.6	1198.4	1197.3	1196.1	1195.0	1194.4	1194.6	1195.0	1195.3	1195.7	1196.1
175°	1203.9	1202.6	1201.2	1199.9	1198.6	1197.9	1198.1	1198.5	1198.8	1199.2	1199.6
177.5°	1205.7	1204.3	1203.0	1201.6	1200.3	1199.6	1199.7	1199.9	1200.1	1200.3	1200.5
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1714.5	1715.8	1718.3	1731.0	1737.3	1738.6	1733.5	1744.9	1748.7	1744.9	1742.4
5°	1795.7	1803.3	1818.5	1835.0	1833.7	1835.0	1842.6	1850.2	1852.7	1842.6	1846.4
7.5°	1866.7	1881.9	1898.4	1923.7	1923.7	1936.4	1941.5	1947.8	1963.0	1955.4	1952.9
10°	1947.8	1968.1	1998.5	2039.1	2040.4	2053.1	2065.8	2086.0	2092.4	2087.3	2089.9
12.5°	2049.3	2088.6	2091.1	2135.5	2155.8	2158.3	2178.6	2174.8	2187.5	2187.5	2209.1
15°	2093.7	2154.5	2188.8	2231.9	2244.6	2229.3	2245.8	2263.6	2264.9	2264.9	2263.6
17.5°	2173.5	2197.6	2231.9	2254.7	2259.8	2259.8	2261.0	2268.7	2263.6	2253.4	2261.0
20°	2190.0	2200.2	2212.9	2210.3	2212.9	2200.2	2187.5	2174.8	2176.1	2169.7	2188.8
22.5°	2159.6	2157.1	2127.9	2108.9	2108.9	2083.5	2059.4	2048.0	2036.6	2040.4	2046.7
25°	2083.5	2044.2	2008.7	1980.8	1974.5	1933.9	1900.9	1890.8	1871.7	1887.0	1889.5
27.5°	1961.8	1917.4	1860.3	1836.2	1803.3	1786.8	1763.9	1733.5	1694.2	1717.0	1713.2
30°	1831.2	1765.2	1718.3	1660.0	1608.0	1604.2	1561.0	1510.3	1490.0	1490.0	1501.4
32.5°	1685.3	1597.8	1529.3	1446.9	1396.2	1374.6	1322.6	1271.9	1283.3	1245.3	1259.2
35°	1515.4	1400.0	1313.8	1233.9	1195.8	1170.5	1103.3	1075.4	1044.9	1027.2	1060.1
37.5°	1353.1	1219.9	1109.6	1022.1	1008.2	962.5	916.8	899.1	881.3	888.9	887.7
40°	1155.3	1037.3	938.4	869.9	845.8	824.3	793.8	772.3	760.9	767.2	768.5
42.5°	976.4	877.5	804.0	755.8	735.5	720.3	705.1	687.3	683.5	683.5	688.6
45°	838.2	757.1	707.6	668.3	656.9	645.5	634.1	626.4	623.9	618.8	622.6
47.5°	727.9	663.2	632.8	603.6	590.9	588.4	578.3	574.5	569.4	568.1	569.4
50°	635.3	594.7	566.8	550.4	541.5	537.7	532.6	525.0	522.5	528.8	526.3
52.5°	570.7	532.6	517.4	500.9	495.8	490.8	483.2	484.4	483.2	480.6	480.6
55°	506.0	481.9	466.7	454.0	452.7	447.6	441.3	438.8	437.5	435.0	438.8
57.5°	454.0	435.0	421.0	409.6	404.5	404.5	398.2	393.1	393.1	391.8	393.1
60°	402.0	383.0	374.1	362.7	358.9	357.6	353.8	351.3	347.5	347.5	347.5
62.5°	353.8	338.6	328.4	318.3	319.6	313.2	308.2	305.6	305.6	306.9	306.9
65°	308.2	298.0	285.3	276.4	273.9	272.6	270.1	268.8	265.0	267.6	267.6
67.5°	266.3	252.4	244.7	240.9	237.1	235.9	233.3	230.8	229.5	228.3	230.8
70°	224.5	213.0	206.7	204.2	200.4	199.1	197.8	194.0	195.3	196.6	197.8
72.5°	186.4	176.3	175.0	167.4	167.4	167.4	162.3	164.9	163.6	161.1	163.6
75°	147.1	142.0	139.5	135.7	137.0	135.7	134.4	130.6	130.6	131.9	133.2
77.5°	116.7	111.6	110.3	106.5	104.0	106.5	104.0	102.7	102.7	104.0	104.0
80°	86.2	83.7	79.9	79.9	79.9	78.6	78.6	78.6	77.4	76.1	77.4
82.5°	57.1	57.1	55.8	54.5	55.8	53.3	54.5	54.5	54.5	54.5	54.5
85°	36.8	35.5	35.5	34.2	34.2	34.2	35.5	33.0	33.0	34.2	34.2
87.5°	16.5	16.5	16.5	17.8	16.5	16.5	16.5	17.8	16.5	16.5	16.5
90°	18.4	19.3	20.3	21.2	21.7	21.9	22.3	22.7	23.1	23.5	23.1
92.5°	21.3	21.7	22.0	22.4	22.6	22.7	22.9	23.1	23.3	23.5	23.3
95°	34.9	35.8	36.8	37.7	38.2	38.1	37.9	37.8	37.6	37.4	37.6
97.5°	44.9	45.5	46.0	46.6	46.9	47.0	47.2	47.4	47.6	47.8	47.6
100°	51.1	52.6	54.2	55.7	56.5	56.7	57.1	57.4	57.8	58.2	57.8
102.5°	53.4	55.5	57.6	59.7	60.8	61.1	61.7	62.3	62.9	63.5	62.9
105°	55.1	57.3	59.4	61.5	62.6	63.0	63.8	64.5	65.3	66.1	65.3
107.5°	56.9	59.0	61.1	63.2	64.3	64.7	65.5	66.2	67.0	67.8	67.0
110°	132.8	113.5	94.2	74.9	65.2	65.6	66.4	67.1	67.9	68.7	67.9

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	358.3	275.1	191.8	108.5	66.9	67.2	67.8	68.3	68.9	69.5	68.9
115°	446.9	357.5	268.0	178.6	133.9	126.9	113.0	99.1	85.2	71.3	85.2
117.5°	555.7	528.1	500.4	472.8	459.0	433.7	383.1	332.4	281.8	231.2	281.8
120°	639.5	641.8	644.1	646.4	647.6	634.6	608.5	582.4	556.4	530.3	556.4
122.5°	689.7	690.8	692.0	693.1	693.7	693.8	694.0	694.1	694.3	694.5	694.3
125°	735.9	737.2	738.6	739.9	740.6	740.9	741.5	742.0	742.6	743.2	742.6
127.5°	779.0	781.0	782.9	784.8	785.8	785.9	786.1	786.3	786.5	786.7	786.5
130°	820.1	822.2	824.3	826.4	827.5	827.4	827.2	827.1	826.9	826.7	826.9
132.5°	860.6	862.3	864.1	865.8	866.7	866.6	866.4	866.2	866.0	865.8	866.0
135°	898.1	900.1	902.0	903.9	904.9	904.7	904.3	904.0	903.6	903.2	903.6
137.5°	933.8	935.8	937.7	939.6	940.6	940.3	939.7	939.1	938.5	937.9	938.5
140°	968.4	970.1	971.9	973.6	974.5	974.0	973.0	972.1	971.1	970.1	971.1
142.5°	1000.3	1001.9	1003.4	1004.9	1005.7	1005.2	1004.3	1003.3	1002.4	1001.4	1002.4
145°	1029.7	1031.0	1032.4	1033.7	1034.4	1033.9	1033.0	1032.0	1031.1	1030.1	1031.1
147.5°	1056.3	1057.2	1058.2	1059.1	1059.6	1059.2	1058.5	1057.7	1057.0	1056.2	1057.0
150°	1080.0	1081.1	1082.3	1083.4	1084.0	1083.5	1082.5	1081.6	1080.6	1079.6	1080.6
152.5°	1101.7	1102.8	1104.0	1105.1	1105.7	1105.0	1103.7	1102.3	1101.0	1099.6	1101.0
155°	1120.8	1121.9	1123.1	1124.2	1124.8	1124.0	1122.5	1121.0	1119.4	1117.9	1119.4
157.5°	1137.5	1138.8	1140.2	1141.5	1142.2	1141.4	1139.9	1138.4	1136.8	1135.3	1136.8
160°	1152.1	1153.2	1154.4	1155.5	1156.1	1155.4	1154.1	1152.7	1151.4	1150.0	1151.4
162.5°	1165.3	1166.7	1168.0	1169.3	1170.0	1169.1	1167.4	1165.7	1163.9	1162.2	1163.9
165°	1175.8	1177.1	1178.5	1179.8	1180.5	1179.8	1178.5	1177.1	1175.8	1174.4	1175.8
167.5°	1185.3	1186.6	1188.0	1189.3	1190.0	1189.1	1187.4	1185.7	1183.9	1182.2	1183.9
170°	1192.3	1193.6	1195.0	1196.3	1197.0	1196.1	1194.4	1192.7	1190.9	1189.2	1190.9
172.5°	1197.5	1198.8	1200.2	1201.5	1202.2	1201.3	1199.6	1197.9	1196.1	1194.4	1196.1
175°	1201.0	1202.3	1203.7	1205.0	1205.7	1204.7	1202.8	1200.9	1198.9	1197.0	1198.9
177.5°	1201.8	1203.2	1204.5	1205.8	1206.5	1205.6	1203.9	1202.2	1200.4	1198.7	1200.4
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1748.7	1739.9	1732.2	1733.5	1739.9	1734.8	1722.1	1705.6	1699.3	1691.7	1699.3
5°	1854.0	1846.4	1831.2	1832.4	1828.6	1823.5	1803.3	1777.9	1777.9	1757.6	1755.1
7.5°	1958.0	1946.6	1936.4	1933.9	1919.9	1909.8	1892.0	1856.5	1842.6	1818.5	1804.5
10°	2074.6	2065.8	2054.3	2040.4	2032.8	2015.0	1985.9	1933.9	1908.5	1875.5	1851.4
12.5°	2192.6	2191.3	2165.9	2138.0	2136.8	2108.9	2088.6	2018.8	1984.6	1940.2	1883.2
15°	2267.4	2261.0	2247.1	2233.2	2237.0	2206.5	2160.9	2078.4	2055.6	2002.4	1941.5
17.5°	2266.1	2266.1	2262.3	2259.8	2256.0	2247.1	2221.7	2167.2	2130.4	2063.2	2006.2
20°	2193.8	2210.3	2214.1	2212.9	2225.5	2231.9	2230.6	2196.4	2167.2	2107.6	2049.3
22.5°	2049.3	2087.3	2103.8	2113.9	2140.6	2154.5	2187.5	2174.8	2167.2	2122.8	2073.4
25°	1914.9	1927.5	1977.0	1979.5	2016.3	2050.5	2083.5	2105.1	2133.0	2116.5	2074.6
27.5°	1741.1	1770.3	1805.8	1832.4	1840.0	1909.8	1964.3	2004.9	2068.3	2073.4	2059.4
30°	1544.6	1558.5	1616.8	1652.4	1692.9	1743.7	1822.3	1892.0	1949.1	2001.1	2018.8
32.5°	1304.9	1362.0	1396.2	1439.3	1474.8	1564.9	1661.2	1751.3	1817.2	1904.7	1942.8
35°	1085.5	1129.9	1188.2	1206.0	1270.7	1346.7	1472.3	1587.7	1687.9	1776.6	1854.0
37.5°	904.2	939.7	1001.8	1029.7	1067.8	1165.4	1270.7	1413.9	1534.4	1643.5	1739.9
40°	779.9	806.5	853.4	862.3	894.0	982.8	1067.8	1202.2	1362.0	1509.1	1614.3
42.5°	694.9	707.6	739.3	750.7	771.0	830.6	906.7	1033.5	1181.9	1334.1	1482.4
45°	634.1	642.9	662.0	672.1	697.5	724.1	786.2	887.7	1004.3	1157.8	1317.6
47.5°	579.5	590.9	598.6	604.9	618.8	648.0	688.6	763.4	875.0	1015.8	1170.5
50°	533.9	537.7	551.6	552.9	561.8	580.8	618.8	664.5	753.3	867.4	1017.0
52.5°	488.2	492.0	500.9	509.8	513.6	528.8	554.2	592.2	658.2	748.2	881.3
55°	442.6	447.6	456.5	462.9	466.7	479.3	494.6	531.3	583.3	646.7	755.8
57.5°	396.9	408.3	410.9	414.7	421.0	435.0	448.9	470.5	511.1	569.4	649.3
60°	353.8	357.6	366.5	370.3	376.6	384.2	402.0	418.5	447.6	493.3	565.6
62.5°	309.4	318.3	322.1	325.9	331.0	339.9	351.3	369.0	394.4	431.2	488.2
65°	271.4	272.6	280.3	285.3	290.4	296.7	308.2	324.6	339.9	374.1	415.9
67.5°	234.6	237.1	239.7	244.7	251.1	257.4	267.6	276.4	295.5	318.3	351.3
70°	199.1	199.1	205.4	209.2	208.0	215.6	223.2	233.3	247.3	268.8	295.5
72.5°	167.4	166.1	171.2	172.5	175.0	180.1	185.1	195.3	202.9	219.4	239.7
75°	133.2	135.7	138.2	138.2	142.0	145.8	150.9	156.0	164.9	175.0	190.2
77.5°	105.3	105.3	107.8	109.1	112.9	111.6	116.7	121.7	128.1	137.0	148.4
80°	77.4	79.9	79.9	79.9	81.2	82.4	87.5	91.3	95.1	101.4	106.5
82.5°	54.5	54.5	57.1	57.1	57.1	59.6	59.6	60.9	63.4	67.2	71.0
85°	34.2	34.2	34.2	35.5	34.2	35.5	38.0	36.8	38.0	40.6	40.6
87.5°	16.5	16.5	16.5	16.5	16.5	17.8	16.5	17.8	19.0	19.0	19.0
90°	22.7	22.3	21.9	21.7	21.2	20.3	19.3	18.4	17.4	15.8	14.3
92.5°	23.1	22.9	22.7	22.6	22.4	22.0	21.7	21.3	20.9	20.3	19.7
95°	37.8	37.9	38.1	38.2	37.7	36.8	35.8	34.9	33.9	32.5	31.2
97.5°	47.4	47.2	47.0	46.9	46.6	46.0	45.5	44.9	44.3	41.2	38.1
100°	57.4	57.1	56.7	56.5	55.7	54.2	52.6	51.1	49.5	46.2	43.0
102.5°	62.3	61.7	61.1	60.8	59.7	57.6	55.5	53.4	51.3	46.5	121.6
105°	64.5	63.8	63.0	62.6	61.5	59.4	57.3	55.1	53.0	105.7	158.5
107.5°	66.2	65.5	64.7	64.3	63.2	61.1	59.0	56.9	54.8	119.9	185.0
110°	67.1	66.4	65.6	65.2	74.9	94.2	113.5	132.8	152.1	207.9	263.7

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	68.3	67.8	67.2	66.9	108.5	191.8	275.1	358.3	441.6	444.9	448.2
115°	99.1	113.0	126.9	133.9	178.6	268.0	357.5	446.9	536.3	531.5	526.7
117.5°	332.4	383.1	433.7	459.0	472.8	500.4	528.1	555.7	583.3	580.0	576.7
120°	582.4	608.5	634.6	647.6	646.4	644.1	641.8	639.5	637.2	633.7	630.2
122.5°	694.1	694.0	693.8	693.7	693.1	692.0	690.8	689.7	688.5	684.6	680.8
125°	742.0	741.5	740.9	740.6	739.9	738.6	737.2	735.9	734.5	730.8	727.2
127.5°	786.3	786.1	785.9	785.8	784.8	782.9	781.0	779.0	777.1	774.2	771.3
130°	827.1	827.2	827.4	827.5	826.4	824.3	822.2	820.1	818.0	815.9	813.7
132.5°	866.2	866.4	866.6	866.7	865.8	864.1	862.3	860.6	858.8	856.7	854.6
135°	904.0	904.3	904.7	904.9	903.9	902.0	900.1	898.1	896.2	894.5	892.7
137.5°	939.1	939.7	940.3	940.6	939.6	937.7	935.8	933.8	931.9	930.0	928.0
140°	972.1	973.0	974.0	974.5	973.6	971.9	970.1	968.4	966.6	964.5	962.4
142.5°	1003.3	1004.3	1005.2	1005.7	1004.9	1003.4	1001.9	1000.3	998.8	996.3	993.8
145°	1032.0	1033.0	1033.9	1034.4	1033.7	1032.4	1031.0	1029.7	1028.3	1025.0	1021.8
147.5°	1057.7	1058.5	1059.2	1059.6	1059.1	1058.2	1057.2	1056.3	1055.3	1052.0	1048.7
150°	1081.6	1082.5	1083.5	1084.0	1083.4	1082.3	1081.1	1080.0	1078.8	1075.7	1072.6
152.5°	1102.3	1103.7	1105.0	1105.7	1105.1	1104.0	1102.8	1101.7	1100.5	1097.6	1094.7
155°	1121.0	1122.5	1124.0	1124.8	1124.2	1123.1	1121.9	1120.8	1119.6	1117.3	1115.0
157.5°	1138.4	1139.9	1141.4	1142.2	1141.5	1140.2	1138.8	1137.5	1136.1	1134.4	1132.6
160°	1152.7	1154.1	1155.4	1156.1	1155.5	1154.4	1153.2	1152.1	1150.9	1149.7	1148.6
162.5°	1165.7	1167.4	1169.1	1170.0	1169.3	1168.0	1166.7	1165.3	1164.0	1163.0	1162.0
165°	1177.1	1178.5	1179.8	1180.5	1179.8	1178.5	1177.1	1175.8	1174.4	1173.8	1173.2
167.5°	1185.7	1187.4	1189.1	1190.0	1189.3	1188.0	1186.6	1185.3	1183.9	1183.3	1182.7
170°	1192.7	1194.4	1196.1	1197.0	1196.3	1195.0	1193.6	1192.3	1190.9	1190.5	1190.1
172.5°	1197.9	1199.6	1201.3	1202.2	1201.5	1200.2	1198.8	1197.5	1196.1	1195.7	1195.3
175°	1200.9	1202.8	1204.7	1205.7	1205.0	1203.7	1202.3	1201.0	1199.6	1199.2	1198.8
177.5°	1202.2	1203.9	1205.6	1206.5	1205.8	1204.5	1203.2	1201.8	1200.5	1200.3	1200.1
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1692.9	1686.6	1682.8	1685.3	1677.7	1658.7	1658.7	1665.0	1657.4	1649.8	1638.4
5°	1739.9	1727.2	1719.6	1718.3	1700.5	1670.1	1663.8	1657.4	1640.9	1623.2	1604.2
7.5°	1785.5	1762.7	1750.0	1741.1	1715.8	1676.4	1660.0	1646.0	1619.4	1592.8	1568.7
10°	1823.5	1790.6	1775.4	1761.4	1728.4	1679.0	1652.4	1627.0	1592.8	1558.5	1528.1
12.5°	1854.0	1815.9	1796.9	1776.6	1736.0	1671.4	1638.4	1597.8	1563.6	1517.9	1487.5
15°	1904.7	1826.1	1808.3	1789.3	1747.5	1658.7	1618.1	1572.5	1525.5	1464.7	1431.7
17.5°	1945.3	1840.0	1838.8	1798.2	1743.7	1653.6	1591.5	1531.9	1481.2	1420.3	1368.3
20°	1969.4	1861.6	1841.3	1799.5	1731.0	1619.4	1554.7	1488.8	1434.2	1360.7	1308.7
22.5°	1989.7	1892.0	1838.8	1788.0	1704.3	1608.0	1512.9	1450.7	1375.9	1296.0	1246.6
25°	1997.3	1898.4	1842.6	1784.2	1685.3	1575.0	1467.2	1400.0	1316.3	1244.0	1176.8
27.5°	1998.5	1897.1	1828.6	1767.8	1658.7	1531.9	1421.6	1350.5	1258.0	1174.3	1107.1
30°	1985.9	1883.2	1821.0	1755.1	1633.3	1492.6	1365.8	1287.1	1188.2	1104.5	1034.8
32.5°	1947.8	1855.3	1804.5	1732.2	1600.4	1438.0	1312.5	1225.0	1121.0	1038.6	971.4
35°	1884.4	1821.0	1765.2	1698.0	1557.2	1387.3	1259.2	1156.5	1051.3	972.6	909.2
37.5°	1805.8	1771.6	1719.6	1653.6	1507.8	1341.7	1199.6	1085.5	980.3	904.2	842.0
40°	1699.3	1708.2	1657.4	1597.8	1449.5	1279.5	1122.3	1013.2	914.3	843.3	782.4
42.5°	1583.9	1620.7	1591.5	1534.4	1384.8	1211.0	1065.2	944.7	848.4	774.8	724.1
45°	1459.6	1523.0	1505.3	1463.4	1317.6	1138.8	984.1	867.4	782.4	711.4	667.0
47.5°	1323.9	1413.9	1413.9	1383.5	1242.8	1066.5	914.3	795.1	711.4	660.7	617.6
50°	1185.7	1287.1	1303.6	1283.3	1159.1	984.1	829.3	721.6	649.3	599.8	568.1
52.5°	1041.1	1159.1	1189.5	1179.3	1070.3	905.4	759.6	654.3	588.4	545.3	517.4
55°	902.9	1039.9	1072.8	1076.6	975.2	819.2	682.2	589.7	526.3	497.1	473.0
57.5°	772.3	904.2	940.9	947.3	878.8	740.6	610.0	528.8	471.7	447.6	428.6
60°	660.7	771.0	819.2	833.2	773.6	649.3	542.8	464.1	421.0	398.2	380.4
62.5°	569.4	658.2	708.9	712.7	686.1	569.4	473.0	407.1	370.3	350.0	341.1
65°	480.6	560.5	590.9	606.2	584.6	493.3	408.3	353.8	324.6	306.9	298.0
67.5°	409.6	460.3	485.7	506.0	484.4	415.9	347.5	303.1	281.5	263.8	258.7
70°	336.1	377.9	396.9	417.2	398.2	346.2	296.7	256.2	237.1	223.2	216.8
72.5°	268.8	301.8	319.6	332.2	320.8	277.7	237.1	209.2	195.3	185.1	181.3
75°	213.0	235.9	246.0	254.9	249.8	216.8	191.5	168.7	156.0	147.1	144.6
77.5°	162.3	178.8	190.2	192.8	186.4	164.9	143.3	129.3	119.2	114.1	111.6
80°	115.4	125.5	131.9	135.7	129.3	120.5	105.3	95.1	86.2	79.9	78.6
82.5°	77.4	82.4	87.5	86.2	83.7	76.1	67.2	62.1	58.3	53.3	53.3
85°	44.4	45.7	48.2	49.5	48.2	43.1	38.0	35.5	33.0	29.2	29.2
87.5°	19.0	20.3	20.3	21.6	19.0	19.0	16.5	13.9	13.9	12.7	11.4
90°	12.7	11.2	10.4	9.3	7.2	5.1	3.0	0.9	3.0	5.1	7.2
92.5°	19.2	18.6	18.3	18.7	19.4	20.2	20.9	21.7	20.9	20.2	19.4
95°	29.8	28.5	27.8	31.0	37.4	43.7	50.1	56.5	50.1	43.7	37.4
97.5°	35.0	31.9	30.4	38.3	54.2	70.0	85.9	101.7	85.9	70.0	54.2
100°	39.7	36.4	34.8	48.0	74.5	101.0	127.4	153.9	127.4	101.0	74.5
102.5°	156.8	191.9	209.5	209.7	210.1	210.4	210.8	211.2	210.8	210.4	210.1
105°	211.2	263.9	290.3	287.4	281.6	275.9	270.1	264.3	270.1	275.9	281.6
107.5°	250.1	315.2	347.7	345.3	340.5	335.6	330.8	326.0	330.8	335.6	340.5
110°	319.6	375.4	403.3	401.3	397.2	393.2	389.1	385.1	389.1	393.2	397.2

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	451.5	454.8	456.4	454.7	451.2	447.7	444.2	440.7	444.2	447.7	451.2
115°	521.8	517.0	514.6	513.0	509.7	506.4	503.1	499.8	503.1	506.4	509.7
117.5°	573.4	570.1	568.5	566.6	562.7	558.8	555.0	551.1	555.0	558.8	562.7
120°	626.7	623.2	621.5	620.1	617.2	614.3	611.4	608.5	611.4	614.3	617.2
122.5°	676.9	673.0	671.1	669.6	666.5	663.4	660.3	657.2	660.3	663.4	666.5
125°	723.5	719.8	718.0	716.7	714.2	711.7	709.2	706.7	709.2	711.7	714.2
127.5°	768.4	765.5	764.1	762.7	760.0	757.3	754.6	751.9	754.6	757.3	760.0
130°	811.6	809.5	808.4	806.9	803.8	800.7	797.6	794.5	797.6	800.7	803.8
132.5°	852.5	850.4	849.3	848.0	845.5	843.0	840.5	838.0	840.5	843.0	845.5
135°	891.0	889.3	888.4	886.9	883.8	880.7	877.6	874.5	877.6	880.7	883.8
137.5°	926.1	924.2	923.2	922.0	919.7	917.4	915.0	912.7	915.0	917.4	919.7
140°	960.3	958.2	957.1	956.3	954.8	953.2	951.7	950.1	951.7	953.2	954.8
142.5°	991.3	988.8	987.5	986.8	985.5	984.1	982.8	981.4	982.8	984.1	985.5
145°	1018.5	1015.2	1013.6	1013.7	1013.9	1014.0	1014.2	1014.4	1014.2	1014.0	1013.9
147.5°	1045.4	1042.1	1040.5	1040.8	1041.4	1041.9	1042.5	1043.1	1042.5	1041.9	1041.4
150°	1069.5	1066.4	1064.9	1065.6	1066.9	1068.2	1069.6	1070.9	1069.6	1068.2	1066.9
152.5°	1091.8	1088.9	1087.5	1088.3	1089.8	1091.3	1092.9	1094.4	1092.9	1091.3	1089.8
155°	1112.7	1110.4	1109.2	1110.1	1111.8	1113.5	1115.3	1117.0	1115.3	1113.5	1111.8
157.5°	1130.9	1129.2	1128.3	1129.1	1130.6	1132.2	1133.7	1135.3	1133.7	1132.2	1130.6
160°	1147.4	1146.3	1145.7	1146.3	1147.4	1148.6	1149.7	1150.9	1149.7	1148.6	1147.4
162.5°	1161.1	1160.1	1159.6	1160.2	1161.3	1162.5	1163.6	1164.8	1163.6	1162.5	1161.3
165°	1172.7	1172.1	1171.8	1172.4	1173.5	1174.7	1175.8	1177.0	1175.8	1174.7	1173.5
167.5°	1182.2	1181.6	1181.3	1181.9	1183.1	1184.2	1185.4	1186.6	1185.4	1184.2	1183.1
170°	1189.8	1189.4	1189.2	1189.8	1190.9	1192.1	1193.2	1194.4	1193.2	1192.1	1190.9
172.5°	1195.0	1194.6	1194.4	1195.0	1196.1	1197.3	1198.4	1199.6	1198.4	1197.3	1196.1
175°	1198.5	1198.1	1197.9	1198.6	1199.9	1201.2	1202.6	1203.9	1202.6	1201.2	1199.9
177.5°	1199.9	1199.7	1199.6	1200.3	1201.6	1203.0	1204.3	1205.7	1204.3	1203.0	1201.6
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1632.1	1638.4	1637.1	1624.5	1610.5	1599.1	1577.5	1580.1	1572.5	1573.7	1581.3
5°	1591.5	1591.5	1586.4	1568.7	1545.8	1533.2	1509.1	1502.7	1487.5	1486.2	1485.0
7.5°	1548.4	1542.0	1535.7	1510.3	1482.4	1462.1	1429.2	1421.6	1406.3	1396.2	1391.1
10°	1497.6	1488.8	1476.1	1446.9	1412.7	1387.3	1353.1	1342.9	1313.8	1301.1	1293.5
12.5°	1441.8	1436.8	1416.5	1392.4	1336.6	1308.7	1259.2	1269.4	1240.2	1214.9	1211.0
15°	1386.0	1367.0	1355.6	1316.3	1249.1	1236.4	1197.1	1176.8	1150.2	1129.9	1129.9
17.5°	1331.5	1302.4	1277.0	1235.1	1185.7	1150.2	1121.0	1110.9	1077.9	1057.6	1053.8
20°	1259.2	1226.3	1219.9	1160.3	1126.1	1086.8	1058.9	1033.5	1009.4	1000.5	994.2
22.5°	1190.8	1152.7	1142.6	1091.8	1057.6	1018.3	990.4	972.6	954.9	948.5	937.1
25°	1117.2	1094.4	1079.2	1024.6	986.6	949.8	930.8	918.1	901.6	900.4	892.8
27.5°	1046.2	1024.6	1009.4	957.4	929.5	895.3	880.1	866.1	857.2	853.4	849.6
30°	985.3	961.2	943.5	905.4	871.2	843.3	830.6	821.7	816.7	810.3	809.1
32.5°	918.1	904.2	880.1	850.9	824.3	797.6	790.0	783.7	776.1	773.6	772.3
35°	861.1	842.0	826.8	793.8	782.4	759.6	750.7	745.7	735.5	733.0	730.4
37.5°	805.3	787.5	771.0	750.7	729.2	716.5	711.4	703.8	698.7	700.0	697.5
40°	749.5	735.5	722.8	701.3	688.6	682.2	672.1	664.5	662.0	663.2	662.0
42.5°	694.9	682.2	674.6	658.2	645.5	639.1	632.8	625.2	629.0	629.0	632.8
45°	645.5	634.1	629.0	616.3	608.7	598.6	592.2	590.9	596.0	594.7	594.7
47.5°	594.7	590.9	584.6	573.2	563.0	556.7	555.4	555.4	560.5	563.0	561.8
50°	555.4	547.8	540.2	531.3	523.7	521.2	517.4	519.9	525.0	525.0	527.5
52.5°	506.0	500.9	498.4	490.8	485.7	485.7	485.7	487.0	490.8	494.6	493.3
55°	462.9	459.1	456.5	452.7	446.4	447.6	446.4	448.9	452.7	456.5	459.1
57.5°	417.2	415.9	413.4	407.1	407.1	405.8	409.6	410.9	417.2	419.7	423.6
60°	376.6	372.8	372.8	367.8	367.8	367.8	371.6	375.4	380.4	381.7	384.2
62.5°	333.5	333.5	332.2	328.4	328.4	332.2	333.5	338.6	341.1	341.1	344.9
65°	292.9	291.7	290.4	291.7	292.9	292.9	296.7	299.3	301.8	303.1	304.3
67.5°	252.4	251.1	253.6	252.4	254.9	260.0	258.7	262.5	266.3	266.3	267.6
70°	214.3	216.8	215.6	218.1	216.8	219.4	223.2	224.5	224.5	225.7	229.5
72.5°	178.8	178.8	178.8	177.5	178.8	181.3	183.9	185.1	187.7	188.9	192.8
75°	144.6	144.6	142.0	144.6	144.6	147.1	149.6	149.6	149.6	152.2	156.0
77.5°	109.1	110.3	109.1	111.6	111.6	112.9	115.4	114.1	116.7	117.9	119.2
80°	79.9	78.6	78.6	78.6	79.9	79.9	82.4	83.7	83.7	87.5	85.0
82.5°	50.7	52.0	50.7	52.0	52.0	53.3	52.0	53.3	54.5	57.1	55.8
85°	29.2	27.9	27.9	29.2	27.9	27.9	29.2	27.9	29.2	27.9	29.2
87.5°	11.4	10.1	10.1	10.1	10.1	8.9	8.9	7.6	7.6	7.6	6.3
90°	9.3	10.4	11.2	12.7	14.3	15.8	17.4	18.4	19.3	20.3	21.2
92.5°	18.7	18.3	18.6	19.2	19.7	20.3	20.9	21.3	21.7	22.0	22.4
95°	31.0	27.8	28.5	29.8	31.2	32.5	33.9	34.9	35.8	36.8	37.7
97.5°	38.3	30.4	31.9	35.0	38.1	41.2	44.3	44.9	45.5	46.0	46.6
100°	48.0	34.8	36.4	39.7	43.0	46.2	49.5	51.1	52.6	54.2	55.7
102.5°	209.7	209.5	191.9	156.8	121.6	86.5	51.3	53.4	55.5	57.6	59.7
105°	287.4	290.3	263.9	211.2	158.5	105.7	53.0	55.1	57.3	59.4	61.5
107.5°	345.3	347.7	315.2	250.1	185.0	119.9	54.8	56.9	59.0	61.1	63.2
110°	401.3	403.3	375.4	319.6	263.7	207.9	152.1	132.8	113.5	94.2	74.9

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	454.7	456.4	454.8	451.5	448.2	444.9	441.6	358.3	275.1	191.8	108.5
115°	513.0	514.6	517.0	521.8	526.7	531.5	536.3	446.9	357.5	268.0	178.6
117.5°	566.6	568.5	570.1	573.4	576.7	580.0	583.3	555.7	528.1	500.4	472.8
120°	620.1	621.5	623.2	626.7	630.2	633.7	637.2	639.5	641.8	644.1	646.4
122.5°	669.6	671.1	673.0	676.9	680.8	684.6	688.5	689.7	690.8	692.0	693.1
125°	716.7	718.0	719.8	723.5	727.2	730.8	734.5	735.9	737.2	738.6	739.9
127.5°	762.7	764.1	765.5	768.4	771.3	774.2	777.1	779.0	781.0	782.9	784.8
130°	806.9	808.4	809.5	811.6	813.7	815.9	818.0	820.1	822.2	824.3	826.4
132.5°	848.0	849.3	850.4	852.5	854.6	856.7	858.8	860.6	862.3	864.1	865.8
135°	886.9	888.4	889.3	891.0	892.7	894.5	896.2	898.1	900.1	902.0	903.9
137.5°	922.0	923.2	924.2	926.1	928.0	930.0	931.9	933.8	935.8	937.7	939.6
140°	956.3	957.1	958.2	960.3	962.4	964.5	966.6	968.4	970.1	971.9	973.6
142.5°	986.8	987.5	988.8	991.3	993.8	996.3	998.8	1000.3	1001.9	1003.4	1004.9
145°	1013.7	1013.6	1015.2	1018.5	1021.8	1025.0	1028.3	1029.7	1031.0	1032.4	1033.7
147.5°	1040.8	1040.5	1042.1	1045.4	1048.7	1052.0	1055.3	1056.3	1057.2	1058.2	1059.1
150°	1065.6	1064.9	1066.4	1069.5	1072.6	1075.7	1078.8	1080.0	1081.1	1082.3	1083.4
152.5°	1088.3	1087.5	1088.9	1091.8	1094.7	1097.6	1100.5	1101.7	1102.8	1104.0	1105.1
155°	1110.1	1109.2	1110.4	1112.7	1115.0	1117.3	1119.6	1120.8	1121.9	1123.1	1124.2
157.5°	1129.1	1128.3	1129.2	1130.9	1132.6	1134.4	1136.1	1137.5	1138.8	1140.2	1141.5
160°	1146.3	1145.7	1146.3	1147.4	1148.6	1149.7	1150.9	1152.1	1153.2	1154.4	1155.5
162.5°	1160.2	1159.6	1160.1	1161.1	1162.0	1163.0	1164.0	1165.3	1166.7	1168.0	1169.3
165°	1172.4	1171.8	1172.1	1172.7	1173.2	1173.8	1174.4	1175.8	1177.1	1178.5	1179.8
167.5°	1181.9	1181.3	1181.6	1182.2	1182.7	1183.3	1183.9	1185.3	1186.6	1188.0	1189.3
170°	1189.8	1189.2	1189.4	1189.8	1190.1	1190.5	1190.9	1192.3	1193.6	1195.0	1196.3
172.5°	1195.0	1194.4	1194.6	1195.0	1195.3	1195.7	1196.1	1197.5	1198.8	1200.2	1201.5
175°	1198.6	1197.9	1198.1	1198.5	1198.8	1199.2	1199.6	1201.0	1202.3	1203.7	1205.0
177.5°	1200.3	1199.6	1199.7	1199.9	1200.1	1200.3	1200.5	1201.8	1203.2	1204.5	1205.8
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1572.5	1576.3	1567.4	1564.9	1567.4	1558.5	1561.0	1563.6	1563.6	1567.4	1569.9
5°	1481.2	1476.1	1467.2	1464.7	1462.1	1465.9	1463.4	1467.2	1468.5	1477.4	1478.6
7.5°	1391.1	1383.5	1375.9	1368.3	1365.8	1359.4	1365.8	1365.8	1374.6	1372.1	1378.4
10°	1284.6	1283.3	1273.2	1269.4	1264.3	1254.2	1268.1	1264.3	1270.7	1282.1	1284.6
12.5°	1206.0	1192.0	1198.4	1180.6	1187.0	1176.8	1178.1	1178.1	1188.2	1189.5	1187.0
15°	1131.2	1119.7	1103.3	1095.7	1091.8	1086.8	1103.3	1104.5	1096.9	1114.7	1108.3
17.5°	1055.1	1055.1	1039.9	1036.0	1025.9	1031.0	1028.4	1029.7	1027.2	1039.9	1046.2
20°	989.1	982.8	977.7	979.0	966.3	963.8	961.2	963.8	972.6	981.5	984.1
22.5°	935.9	932.1	919.4	921.9	911.8	915.6	913.0	919.4	920.7	920.7	929.5
25°	885.1	880.1	881.3	876.3	872.5	872.5	868.7	872.5	877.5	880.1	881.3
27.5°	847.1	843.3	837.0	833.2	835.7	829.3	834.4	838.2	838.2	835.7	838.2
30°	801.4	804.0	804.0	791.3	796.4	793.8	797.6	800.2	800.2	801.4	798.9
32.5°	771.0	763.4	762.1	760.9	760.9	755.8	755.8	759.6	760.9	762.1	765.9
35°	730.4	730.4	724.1	727.9	722.8	724.1	722.8	724.1	726.6	722.8	726.6
37.5°	693.7	694.9	692.4	694.9	696.2	693.7	691.1	696.2	693.7	693.7	691.1
40°	662.0	660.7	662.0	662.0	662.0	663.2	660.7	660.7	660.7	658.2	655.6
42.5°	635.3	627.7	630.3	631.5	627.7	627.7	629.0	627.7	631.5	623.9	623.9
45°	597.3	594.7	596.0	596.0	598.6	594.7	597.3	598.6	594.7	593.5	590.9
47.5°	563.0	565.6	563.0	565.6	565.6	568.1	563.0	564.3	565.6	560.5	556.7
50°	528.8	528.8	532.6	531.3	532.6	530.1	530.1	528.8	530.1	527.5	523.7
52.5°	497.1	493.3	499.6	498.4	497.1	495.8	494.6	495.8	493.3	490.8	490.8
55°	457.8	457.8	461.6	462.9	462.9	460.3	457.8	459.1	457.8	456.5	455.3
57.5°	426.1	421.0	423.6	424.8	424.8	421.0	423.6	421.0	421.0	422.3	418.5
60°	385.5	385.5	383.0	386.8	386.8	384.2	384.2	385.5	383.0	381.7	380.4
62.5°	342.4	343.7	347.5	348.7	350.0	347.5	344.9	346.2	346.2	342.4	343.7
65°	305.6	308.2	313.2	312.0	309.4	310.7	308.2	309.4	305.6	306.9	303.1
67.5°	270.1	268.8	270.1	270.1	272.6	271.4	268.8	268.8	267.6	271.4	267.6
70°	232.1	232.1	232.1	232.1	233.3	234.6	232.1	229.5	230.8	228.3	227.0
72.5°	192.8	194.0	192.8	195.3	191.5	194.0	194.0	192.8	191.5	191.5	191.5
75°	156.0	158.5	154.7	156.0	154.7	157.2	156.0	156.0	153.4	152.2	153.4
77.5°	119.2	120.5	117.9	119.2	117.9	119.2	119.2	117.9	117.9	117.9	117.9
80°	85.0	86.2	85.0	83.7	82.4	85.0	82.4	83.7	85.0	83.7	86.2
82.5°	54.5	54.5	53.3	54.5	52.0	52.0	53.3	53.3	52.0	54.5	52.0
85°	26.6	26.6	29.2	26.6	25.4	25.4	25.4	26.6	25.4	27.9	26.6
87.5°	6.3	5.1	6.3	6.3	5.1	5.1	6.3	5.1	6.3	7.6	5.1
90°	21.7	21.9	22.3	22.7	23.1	23.5	23.1	22.7	22.3	21.9	21.7
92.5°	22.6	22.7	22.9	23.1	23.3	23.5	23.3	23.1	22.9	22.7	22.6
95°	38.2	38.1	37.9	37.8	37.6	37.4	37.6	37.8	37.9	38.1	38.2
97.5°	46.9	47.0	47.2	47.4	47.6	47.8	47.6	47.4	47.2	47.0	46.9
100°	56.5	56.7	57.1	57.4	57.8	58.2	57.8	57.4	57.1	56.7	56.5
102.5°	60.8	61.1	61.7	62.3	62.9	63.5	62.9	62.3	61.7	61.1	60.8
105°	62.6	63.0	63.8	64.5	65.3	66.1	65.3	64.5	63.8	63.0	62.6
107.5°	64.3	64.7	65.5	66.2	67.0	67.8	67.0	66.2	65.5	64.7	64.3
110°	65.2	65.6	66.4	67.1	67.9	68.7	67.9	67.1	66.4	65.6	65.2

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	66.9	67.2	67.8	68.3	68.9	69.5	68.9	68.3	67.8	67.2	66.9
115°	133.9	126.9	113.0	99.1	85.2	71.3	85.2	99.1	113.0	126.9	133.9
117.5°	459.0	433.7	383.1	332.4	281.8	231.2	281.8	332.4	383.1	433.7	459.0
120°	647.6	634.6	608.5	582.4	556.4	530.3	556.4	582.4	608.5	634.6	647.6
122.5°	693.7	693.8	694.0	694.1	694.3	694.5	694.3	694.1	694.0	693.8	693.7
125°	740.6	740.9	741.5	742.0	742.6	743.2	742.6	742.0	741.5	740.9	740.6
127.5°	785.8	785.9	786.1	786.3	786.5	786.7	786.5	786.3	786.1	785.9	785.8
130°	827.5	827.4	827.2	827.1	826.9	826.7	826.9	827.1	827.2	827.4	827.5
132.5°	866.7	866.6	866.4	866.2	866.0	865.8	866.0	866.2	866.4	866.6	866.7
135°	904.9	904.7	904.3	904.0	903.6	903.2	903.6	904.0	904.3	904.7	904.9
137.5°	940.6	940.3	939.7	939.1	938.5	937.9	938.5	939.1	939.7	940.3	940.6
140°	974.5	974.0	973.0	972.1	971.1	970.1	971.1	972.1	973.0	974.0	974.5
142.5°	1005.7	1005.2	1004.3	1003.3	1002.4	1001.4	1002.4	1003.3	1004.3	1005.2	1005.7
145°	1034.4	1033.9	1033.0	1032.0	1031.1	1030.1	1031.1	1032.0	1033.0	1033.9	1034.4
147.5°	1059.6	1059.2	1058.5	1057.7	1057.0	1056.2	1057.0	1057.7	1058.5	1059.2	1059.6
150°	1084.0	1083.5	1082.5	1081.6	1080.6	1079.6	1080.6	1081.6	1082.5	1083.5	1084.0
152.5°	1105.7	1105.0	1103.7	1102.3	1101.0	1099.6	1101.0	1102.3	1103.7	1105.0	1105.7
155°	1124.8	1124.0	1122.5	1121.0	1119.4	1117.9	1119.4	1121.0	1122.5	1124.0	1124.8
157.5°	1142.2	1141.4	1139.9	1138.4	1136.8	1135.3	1136.8	1138.4	1139.9	1141.4	1142.2
160°	1156.1	1155.4	1154.1	1152.7	1151.4	1150.0	1151.4	1152.7	1154.1	1155.4	1156.1
162.5°	1170.0	1169.1	1167.4	1165.7	1163.9	1162.2	1163.9	1165.7	1167.4	1169.1	1170.0
165°	1180.5	1179.8	1178.5	1177.1	1175.8	1174.4	1175.8	1177.1	1178.5	1179.8	1180.5
167.5°	1190.0	1189.1	1187.4	1185.7	1183.9	1182.2	1183.9	1185.7	1187.4	1189.1	1190.0
170°	1197.0	1196.1	1194.4	1192.7	1190.9	1189.2	1190.9	1192.7	1194.4	1196.1	1197.0
172.5°	1202.2	1201.3	1199.6	1197.9	1196.1	1194.4	1196.1	1197.9	1199.6	1201.3	1202.2
175°	1205.7	1204.7	1202.8	1200.9	1198.9	1197.0	1198.9	1200.9	1202.8	1204.7	1205.7
177.5°	1206.5	1205.6	1203.9	1202.2	1200.4	1198.7	1200.4	1202.2	1203.9	1205.6	1206.5
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1566.1	1576.3	1572.5	1558.5	1575.0	1575.0	1586.4	1586.4	1600.4	1605.4	1613.0
5°	1477.4	1485.0	1491.3	1485.0	1496.4	1514.1	1524.3	1533.2	1552.2	1559.8	1571.2
7.5°	1382.2	1396.2	1402.5	1402.5	1421.6	1441.8	1462.1	1474.8	1501.4	1511.6	1523.0
10°	1289.7	1306.2	1318.8	1317.6	1349.3	1362.0	1387.3	1416.5	1443.1	1458.3	1474.8
12.5°	1192.0	1200.9	1218.7	1244.0	1251.6	1274.5	1303.6	1340.4	1388.6	1402.5	1426.6
15°	1110.9	1135.0	1148.9	1160.3	1178.1	1199.6	1231.3	1266.8	1315.0	1345.5	1370.8
17.5°	1042.4	1074.1	1083.0	1080.4	1103.3	1136.2	1173.0	1199.6	1242.8	1279.5	1303.6
20°	986.6	999.3	1014.5	1020.8	1038.6	1074.1	1109.6	1140.0	1175.5	1204.7	1232.6
22.5°	930.8	940.9	953.6	965.0	979.0	999.3	1033.5	1071.6	1105.8	1133.7	1165.4
25°	885.1	891.5	902.9	911.8	927.0	940.9	965.0	1006.9	1047.5	1063.9	1091.8
27.5°	840.8	845.8	853.4	863.6	871.2	885.1	906.7	940.9	982.8	999.3	1037.3
30°	801.4	805.3	812.9	817.9	821.7	838.2	854.7	881.3	913.0	935.9	963.8
32.5°	764.7	768.5	776.1	777.4	782.4	791.3	806.5	830.6	858.5	877.5	901.6
35°	724.1	726.6	734.2	736.8	740.6	748.2	759.6	777.4	802.7	816.7	838.2
37.5°	692.4	691.1	696.2	700.0	705.1	708.9	712.7	730.4	749.5	762.1	778.6
40°	658.2	655.6	656.9	662.0	664.5	669.6	669.6	687.3	700.0	710.1	722.8
42.5°	623.9	622.6	620.1	622.6	625.2	626.4	627.7	640.4	653.1	662.0	675.9
45°	589.7	588.4	585.9	587.1	587.1	589.7	593.5	598.6	607.4	615.0	622.6
47.5°	558.0	555.4	551.6	550.4	552.9	552.9	552.9	558.0	566.8	569.4	577.0
50°	525.0	521.2	516.1	513.6	513.6	512.3	514.9	516.1	523.7	526.3	532.6
52.5°	489.5	487.0	481.9	476.8	478.1	475.5	476.8	478.1	480.6	484.4	488.2
55°	454.0	448.9	445.1	443.8	440.0	440.0	436.2	441.3	440.0	441.3	446.4
57.5°	419.7	414.7	408.3	405.8	402.0	400.7	398.2	396.9	398.2	402.0	405.8
60°	379.2	376.6	372.8	369.0	366.5	362.7	360.1	360.1	358.9	358.9	360.1
62.5°	339.9	338.6	333.5	332.2	329.7	327.2	323.4	320.8	320.8	323.4	324.6
65°	301.8	300.5	296.7	295.5	289.1	286.6	285.3	284.1	281.5	281.5	281.5
67.5°	266.3	262.5	262.5	256.2	251.1	248.6	246.0	244.7	244.7	244.7	246.0
70°	227.0	227.0	223.2	219.4	214.3	215.6	211.8	208.0	208.0	205.4	206.7
72.5°	188.9	187.7	183.9	182.6	178.8	175.0	172.5	175.0	171.2	169.9	171.2
75°	152.2	150.9	148.4	145.8	147.1	143.3	139.5	138.2	138.2	135.7	135.7
77.5°	116.7	119.2	114.1	112.9	110.3	107.8	106.5	105.3	105.3	105.3	107.8
80°	81.2	82.4	82.4	79.9	81.2	77.4	77.4	77.4	73.6	74.8	76.1
82.5°	52.0	52.0	50.7	52.0	50.7	50.7	49.5	49.5	48.2	48.2	49.5
85°	29.2	27.9	26.6	29.2	27.9	27.9	26.6	26.6	26.6	26.6	26.6
87.5°	6.3	7.6	7.6	7.6	7.6	8.9	8.9	8.9	10.1	10.1	10.1
90°	21.2	20.3	19.3	18.4	17.4	15.8	14.3	12.7	11.2	10.4	9.3
92.5°	22.4	22.0	21.7	21.3	20.9	20.3	19.7	19.2	18.6	18.3	18.7
95°	37.7	36.8	35.8	34.9	33.9	32.5	31.2	29.8	28.5	27.8	31.0
97.5°	46.6	46.0	45.5	44.9	44.3	41.2	38.1	35.0	31.9	30.4	38.3
100°	55.7	54.2	52.6	51.1	49.5	46.2	43.0	39.7	36.4	34.8	48.0
102.5°	59.7	57.6	55.5	53.4	51.3	86.5	121.6	156.8	191.9	209.5	209.7
105°	61.5	59.4	57.3	55.1	53.0	105.7	158.5	211.2	263.9	290.3	287.4
107.5°	63.2	61.1	59.0	56.9	54.8	119.9	185.0	250.1	315.2	347.7	345.3
110°	74.9	94.2	113.5	132.8	152.1	207.9	263.7	319.6	375.4	403.3	401.3

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	108.5	191.8	275.1	358.3	441.6	444.9	448.2	451.5	454.8	456.4	454.7
115°	178.6	268.0	357.5	446.9	536.3	531.5	526.7	521.8	517.0	514.6	513.0
117.5°	472.8	500.4	528.1	555.7	583.3	580.0	576.7	573.4	570.1	568.5	566.6
120°	646.4	644.1	641.8	639.5	637.2	633.7	630.2	626.7	623.2	621.5	620.1
122.5°	693.1	692.0	690.8	689.7	688.5	684.6	680.8	676.9	673.0	671.1	669.6
125°	739.9	738.6	737.2	735.9	734.5	730.8	727.2	723.5	719.8	718.0	716.7
127.5°	784.8	782.9	781.0	779.0	777.1	774.2	771.3	768.4	765.5	764.1	762.7
130°	826.4	824.3	822.2	820.1	818.0	815.9	813.7	811.6	809.5	808.4	806.9
132.5°	865.8	864.1	862.3	860.6	858.8	856.7	854.6	852.5	850.4	849.3	848.0
135°	903.9	902.0	900.1	898.1	896.2	894.5	892.7	891.0	889.3	888.4	886.9
137.5°	939.6	937.7	935.8	933.8	931.9	930.0	928.0	926.1	924.2	923.2	922.0
140°	973.6	971.9	970.1	968.4	966.6	964.5	962.4	960.3	958.2	957.1	956.3
142.5°	1004.9	1003.4	1001.9	1000.3	998.8	996.3	993.8	991.3	988.8	987.5	986.8
145°	1033.7	1032.4	1031.0	1029.7	1028.3	1025.0	1021.8	1018.5	1015.2	1013.6	1013.7
147.5°	1059.1	1058.2	1057.2	1056.3	1055.3	1052.0	1048.7	1045.4	1042.1	1040.5	1040.8
150°	1083.4	1082.3	1081.1	1080.0	1078.8	1075.7	1072.6	1069.5	1066.4	1064.9	1065.6
152.5°	1105.1	1104.0	1102.8	1101.7	1100.5	1097.6	1094.7	1091.8	1088.9	1087.5	1088.3
155°	1124.2	1123.1	1121.9	1120.8	1119.6	1117.3	1115.0	1112.7	1110.4	1109.2	1110.1
157.5°	1141.5	1140.2	1138.8	1137.5	1136.1	1134.4	1132.6	1130.9	1129.2	1128.3	1129.1
160°	1155.5	1154.4	1153.2	1152.1	1150.9	1149.7	1148.6	1147.4	1146.3	1145.7	1146.3
162.5°	1169.3	1168.0	1166.7	1165.3	1164.0	1163.0	1162.0	1161.1	1160.1	1159.6	1160.2
165°	1179.8	1178.5	1177.1	1175.8	1174.4	1173.8	1173.2	1172.7	1172.1	1171.8	1172.4
167.5°	1189.3	1188.0	1186.6	1185.3	1183.9	1183.3	1182.7	1182.2	1181.6	1181.3	1181.9
170°	1196.3	1195.0	1193.6	1192.3	1190.9	1190.5	1190.1	1189.8	1189.4	1189.2	1189.8
172.5°	1201.5	1200.2	1198.8	1197.5	1196.1	1195.7	1195.3	1195.0	1194.6	1194.4	1195.0
175°	1205.0	1203.7	1202.3	1201.0	1199.6	1199.2	1198.8	1198.5	1198.1	1197.9	1198.6
177.5°	1205.8	1204.5	1203.2	1201.8	1200.5	1200.3	1200.1	1199.9	1199.7	1199.6	1200.3
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1649.8	1649.8	1649.8	1649.8
2.5°	1619.4	1619.4	1638.4	1658.7
5°	1583.9	1592.8	1623.2	1651.1
7.5°	1549.6	1564.9	1602.9	1638.4
10°	1507.8	1528.1	1575.0	1616.8
12.5°	1467.2	1486.2	1540.8	1587.7
15°	1410.1	1434.2	1492.6	1550.9
17.5°	1353.1	1377.2	1448.2	1516.7
20°	1285.9	1317.6	1397.5	1488.8
22.5°	1223.7	1263.0	1351.8	1425.4
25°	1155.3	1216.1	1298.5	1393.7
27.5°	1094.4	1155.3	1238.9	1335.3
30°	1025.9	1088.0	1174.3	1263.0
32.5°	960.0	1017.0	1100.7	1209.8
35°	891.5	946.0	1027.2	1137.5
37.5°	829.3	882.6	971.4	1072.8
40°	768.5	824.3	900.4	1001.8
42.5°	711.4	760.9	829.3	930.8
45°	659.4	694.9	758.3	853.4
47.5°	604.9	636.6	694.9	790.0
50°	554.2	580.8	631.5	720.3
52.5°	504.7	527.5	574.5	645.5
55°	460.3	481.9	516.1	585.9
57.5°	414.7	431.2	464.1	519.9
60°	370.3	385.5	412.1	457.8
62.5°	325.9	338.6	363.9	400.7
65°	286.6	296.7	315.8	347.5
67.5°	248.6	254.9	270.1	295.5
70°	211.8	216.8	229.5	249.8
72.5°	172.5	177.5	191.5	205.4
75°	139.5	140.8	150.9	162.3
77.5°	109.1	107.8	115.4	124.3
80°	74.8	78.6	85.0	88.8
82.5°	50.7	52.0	54.5	57.1
85°	27.9	29.2	29.2	33.0
87.5°	11.4	12.7	12.7	13.9
90°	7.2	5.1	3.0	0.9
92.5°	19.4	20.2	20.9	21.7
95°	37.4	43.7	50.1	56.5
97.5°	54.2	70.0	85.9	101.7
100°	74.5	101.0	127.4	153.9
102.5°	210.1	210.4	210.8	211.2
105°	281.6	275.9	270.1	264.3
107.5°	340.5	335.6	330.8	326.0
110°	397.2	393.2	389.1	385.1



TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	451.2	447.7	444.2	440.7
115°	509.7	506.4	503.1	499.8
117.5°	562.7	558.8	555.0	551.1
120°	617.2	614.3	611.4	608.5
122.5°	666.5	663.4	660.3	657.2
125°	714.2	711.7	709.2	706.7
127.5°	760.0	757.3	754.6	751.9
130°	803.8	800.7	797.6	794.5
132.5°	845.5	843.0	840.5	838.0
135°	883.8	880.7	877.6	874.5
137.5°	919.7	917.4	915.0	912.7
140°	954.8	953.2	951.7	950.1
142.5°	985.5	984.1	982.8	981.4
145°	1013.9	1014.0	1014.2	1014.4
147.5°	1041.4	1041.9	1042.5	1043.1
150°	1066.9	1068.2	1069.6	1070.9
152.5°	1089.8	1091.3	1092.9	1094.4
155°	1111.8	1113.5	1115.3	1117.0
157.5°	1130.6	1132.2	1133.7	1135.3
160°	1147.4	1148.6	1149.7	1150.9
162.5°	1161.3	1162.5	1163.6	1164.8
165°	1173.5	1174.7	1175.8	1177.0
167.5°	1183.1	1184.2	1185.4	1186.6
170°	1190.9	1192.1	1193.2	1194.4
172.5°	1196.1	1197.3	1198.4	1199.6
175°	1199.9	1201.2	1202.6	1203.9
177.5°	1201.6	1203.0	1204.3	1205.7
180°	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P999222

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.26	18.09	18.21	19.06	20.32	14.75	15.59	15.71	16.55	17.82
	3H	18.07	18.81	19.04	19.79	21.08	16.09	16.84	17.06	17.82	19.10
	4H	18.23	18.94	19.22	19.92	21.22	16.55	17.26	17.54	18.24	19.54
	6H	18.28	18.93	19.27	19.91	21.22	16.86	17.51	17.85	18.50	19.80
	8H	18.26	18.88	19.26	19.88	21.18	16.94	17.56	17.94	18.56	19.87
	12H	18.22	18.81	19.22	19.80	21.13	16.99	17.57	17.99	18.57	19.90
4H	2H	17.30	18.00	18.28	18.98	20.28	15.19	15.90	16.18	16.88	18.17
	3H	18.27	18.86	19.27	19.87	21.18	16.65	17.24	17.65	18.25	19.56
	4H	18.55	19.09	19.56	20.09	21.42	17.19	17.72	18.19	18.73	20.06
	6H	18.68	19.14	19.70	20.17	21.49	17.56	18.02	18.58	19.05	20.38
	8H	18.68	19.11	19.69	20.13	21.47	17.67	18.10	18.69	19.12	20.47
	12H	18.64	19.03	19.68	20.06	21.41	17.73	18.12	18.76	19.15	20.50
8H	4H	18.56	18.99	19.57	20.01	21.35	17.33	17.76	18.34	18.78	20.12
	6H	18.74	19.09	19.78	20.15	21.49	17.76	18.11	18.80	19.18	20.52
	8H	18.77	19.08	19.81	20.12	21.48	17.91	18.22	18.96	19.27	20.63
	12H	18.75	19.02	19.80	20.06	21.47	18.00	18.28	19.05	19.32	20.72
12H	4H	18.51	18.90	19.55	19.94	21.28	17.30	17.69	18.33	18.72	20.07
	6H	18.71	19.03	19.76	20.07	21.43	17.76	18.07	18.81	19.12	20.48
	8H	18.75	19.02	19.80	20.06	21.46	17.92	18.19	18.97	19.23	20.63