

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999278

Luminaire Tested: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999278
REPORT IS A COMBINATION OF REPORTS P987827 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8080.0 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53			47
1	98	94	90	87	90	86	83	81	73	70	69	60	59	57	48	47	46			41
2	90	83	77	72	82	76	72	67	65	61	58	54	51	49	43	42	40			36
3	82	74	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35			31
4	76	66	58	53	70	61	54	49	52	47	43	43	40	37	36	33	31			28
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	33	30	28			24
6	65	53	46	40	59	50	43	38	43	37	33	36	32	29	30	27	25			22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	22			20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	24	26	23	20			18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19			17
10	49	37	30	26	45	35	29	25	30	25	22	26	22	20	22	19	17			15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34790	34790	34790	34790
5°	34870	36952	34991	29520
10°	34486	39056	34731	24377
15°	33737	39069	34309	18313
20°	32837	32295	33552	15109
25°	31746	20180	32433	12854
30°	30353	12920	31178	11065
35°	28658	9930	29585	9470
40°	26768	8347	27912	8283
45°	24749	7104	25784	6953
50°	22680	6036	23739	6014
55°	20390	5245	21487	5177
60°	18352	4000	19326	3952
65°	16452	3009	17430	3415
70°	14352	2404	15478	2783
75°	12133	1841	13241	2105
80°	9636	1253	10363	1381
85°	6681	647	7331	682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 31825 cd/sqm

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.5	2.6
10°-20°	581.9	7.2
20°-30°	748.9	9.3
30°-40°	710.4	8.8
40°-50°	608.9	7.5
50°-60°	463.7	5.7
60°-70°	292.4	3.6
70°-80°	145.9	1.8
80°-90°	40.1	0.5
90°-100°	48.2	0.6
100°-110°	179.4	2.2
110°-120°	475.9	5.9
120°-130°	789.3	9.8
130°-140°	838.4	10.4
140°-150°	779.2	9.6
150°-160°	626.5	7.8
160°-170°	403.7	5.0
170°-180°	138.9	1.7
0°-30°	1539.2	19.0
0°-40°	2249.6	27.8
0°-60°	3322.2	41.1
0°-90°	3800.6	47.0
90°-120°	703.5	8.7
90°-150°	3110.4	38.5
90°-180°	4279.0	53.0
0°-180°	8080.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2198	2198	2198	2198	2198	
5°	2199	2445	2207	1953	2199	209
15°	2072	2760	2108	1294	2072	583
25°	1839	1472	1879	938	1839	844
35°	1509	726	1558	692	1509	944
45°	1133	504	1181	493	1133	875
55°	765	350	806	345	765	690
65°	463	182	490	206	463	459
75°	217	96	237	110	217	235
85°	47	28	52	29	47	54
90°	1	28	1	28	1	7
95°	69	45	69	45	69	81
105°	321	80	321	80	321	343
115°	607	87	607	87	607	598
125°	859	903	859	903	859	766
135°	1063	1097	1063	1097	1063	821
145°	1233	1252	1233	1252	1233	771
155°	1357	1358	1357	1358	1357	625
165°	1430	1427	1430	1427	1430	404
175°	1463	1454	1463	1454	1463	139
180°	1460	1460	1460	1460	1460	

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2211.5	2220.7	2225.2	2231.4	2245.1	2254.3	2268.0	2271.1	2269.5	2275.7	2258.9
5°	2199.3	2219.1	2237.5	2252.7	2277.2	2292.5	2309.3	2329.1	2333.7	2356.6	2342.9
7.5°	2182.5	2211.5	2237.5	2268.0	2304.7	2324.5	2350.5	2381.0	2394.8	2422.3	2429.9
10°	2155.0	2196.2	2240.5	2272.6	2323.0	2358.1	2382.6	2431.4	2463.5	2504.7	2498.6
12.5°	2110.7	2164.2	2223.7	2277.2	2342.9	2365.8	2411.6	2462.0	2503.2	2541.4	2575.0
15°	2072.5	2133.6	2199.3	2265.0	2339.8	2382.6	2428.4	2494.1	2538.3	2605.5	2634.6
17.5°	2020.6	2098.5	2176.4	2249.7	2338.3	2387.1	2443.7	2507.8	2573.5	2637.6	2660.5
20°	1967.1	2051.1	2135.1	2234.4	2335.2	2382.6	2440.6	2520.0	2584.2	2634.6	2634.6
22.5°	1903.0	2005.3	2101.5	2196.2	2306.2	2374.9	2434.5	2527.7	2573.5	2584.2	2542.9
25°	1838.8	1941.2	2046.6	2164.2	2289.4	2350.5	2417.7	2504.7	2520.0	2477.3	2370.3
27.5°	1762.5	1877.0	1996.2	2122.9	2254.3	2330.6	2391.7	2449.8	2420.7	2306.2	2139.7
30°	1684.6	1808.3	1942.7	2063.4	2222.2	2292.5	2344.4	2361.2	2269.5	2083.2	1867.9
32.5°	1603.6	1724.3	1866.3	2011.4	2171.8	2239.0	2272.6	2228.3	2060.3	1825.1	1562.4
35°	1509.0	1644.9	1793.0	1944.2	2103.1	2153.5	2173.3	2064.9	1849.5	1545.6	1284.4
37.5°	1423.4	1559.4	1718.2	1872.4	2026.7	2054.2	2034.3	1864.8	1591.4	1290.6	1035.5
40°	1322.6	1467.7	1623.5	1796.1	1922.8	1930.5	1881.6	1661.7	1322.6	1040.1	882.8
42.5°	1229.5	1376.1	1531.9	1707.5	1803.7	1777.8	1712.1	1423.4	1104.2	896.5	769.8
45°	1133.2	1272.2	1440.2	1596.0	1664.7	1603.6	1504.4	1197.4	927.1	771.3	673.5
47.5°	1040.1	1169.9	1336.4	1486.0	1498.3	1429.5	1311.9	1003.4	803.4	678.1	598.7
50°	948.4	1078.3	1234.0	1357.8	1345.5	1250.8	1118.0	872.1	698.0	598.7	533.0
52.5°	856.8	974.4	1125.6	1223.4	1171.4	1079.8	948.4	739.2	609.4	522.3	471.9
55°	765.2	875.1	1005.0	1085.9	1003.4	898.0	804.9	633.8	528.4	458.2	420.0
57.5°	688.8	775.9	895.0	943.9	844.6	762.1	681.2	545.2	458.2	407.8	363.5
60°	604.8	684.2	782.0	811.0	708.7	641.5	572.7	461.2	392.5	348.2	319.2
62.5°	533.0	598.7	673.5	673.5	583.4	533.0	481.1	386.4	329.9	294.8	281.0
65°	462.8	510.1	563.6	557.5	481.1	436.8	395.6	319.2	276.4	252.0	238.3
67.5°	394.0	430.7	465.8	444.4	389.5	351.3	313.1	258.1	229.1	212.3	194.0
70°	331.4	360.4	378.8	358.9	303.9	271.9	244.4	207.7	184.8	163.4	152.7
72.5°	278.0	290.2	296.3	271.9	226.0	207.7	187.9	161.9	142.0	131.3	128.3
75°	216.9	227.6	223.0	204.7	166.5	152.7	137.5	119.1	114.5	108.4	105.4
77.5°	169.5	169.5	161.9	145.1	119.1	108.4	102.3	93.2	88.6	87.1	84.0
80°	120.7	119.1	114.5	96.2	80.9	74.8	74.8	68.7	67.2	64.1	64.1
82.5°	79.4	79.4	73.3	58.0	53.5	51.9	50.4	47.3	47.3	45.8	45.8
85°	47.3	44.3	36.7	32.1	30.5	30.5	29.0	27.5	29.0	27.5	27.5
87.5°	21.4	16.8	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
90°	1.1	3.7	6.3	8.8	11.4	12.7	13.6	15.5	17.4	19.2	21.1
92.5°	26.4	25.5	24.5	23.6	22.7	22.2	22.5	23.2	23.9	24.6	25.3
95°	68.7	60.9	53.2	45.4	37.7	33.8	34.6	36.3	37.9	39.6	41.2
97.5°	123.6	104.4	85.1	65.9	46.6	37.0	38.9	42.6	46.4	50.1	53.9
100°	187.0	154.8	122.6	90.5	58.3	42.2	44.2	48.2	52.2	56.2	60.2
102.5°	256.7	256.2	255.8	255.3	254.8	254.6	233.2	190.5	147.8	105.0	62.3
105°	321.1	328.1	335.2	342.2	349.3	352.8	320.8	256.7	192.6	128.5	64.4
107.5°	396.1	402.0	407.8	413.7	419.6	422.5	382.9	303.8	224.7	145.6	66.5
110°	467.9	472.8	477.8	482.7	487.6	490.1	456.2	388.3	320.5	252.6	184.8

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	535.5	539.7	543.9	548.2	552.4	554.5	552.5	548.5	544.6	540.6	536.6
115°	607.3	611.3	615.3	619.3	623.3	625.3	628.2	634.1	640.0	645.8	651.7
117.5°	669.7	674.4	679.1	683.8	688.5	690.8	692.8	696.8	700.7	704.7	708.7
120°	739.4	742.9	746.4	749.9	753.4	755.2	757.3	761.5	765.8	770.0	774.2
122.5°	798.5	802.3	806.0	809.8	813.5	815.4	817.7	822.4	827.1	831.8	836.5
125°	858.7	861.8	864.8	867.9	871.0	872.5	874.7	879.2	883.6	888.1	892.5
127.5°	913.7	917.0	920.2	923.5	926.8	928.4	930.2	933.7	937.2	940.8	944.3
130°	965.4	969.2	972.9	976.7	980.4	982.3	983.6	986.2	988.7	991.3	993.9
132.5°	1018.2	1021.3	1024.3	1027.4	1030.5	1032.0	1033.3	1035.9	1038.4	1041.0	1043.6
135°	1062.6	1066.4	1070.1	1073.9	1077.6	1079.5	1080.6	1082.7	1084.8	1086.9	1089.0
137.5°	1109.1	1111.9	1114.7	1117.5	1120.3	1121.7	1122.9	1125.2	1127.6	1129.9	1132.3
140°	1154.5	1156.4	1158.2	1160.1	1162.0	1162.9	1164.2	1166.8	1169.3	1171.9	1174.5
142.5°	1192.5	1194.1	1195.8	1197.4	1199.1	1199.9	1201.4	1204.5	1207.5	1210.6	1213.6
145°	1232.6	1232.4	1232.2	1231.9	1231.7	1231.6	1233.6	1237.6	1241.5	1245.5	1249.5
147.5°	1267.5	1266.8	1266.1	1265.4	1264.7	1264.3	1266.3	1270.3	1274.3	1278.3	1282.3
150°	1301.3	1299.7	1298.0	1296.4	1294.7	1293.9	1295.8	1299.5	1303.3	1307.0	1310.8
152.5°	1329.8	1327.9	1326.1	1324.2	1322.3	1321.4	1323.2	1326.7	1330.2	1333.7	1337.2
155°	1357.3	1355.2	1353.1	1351.0	1348.9	1347.8	1349.2	1352.0	1354.8	1357.6	1360.4
157.5°	1379.5	1377.6	1375.7	1373.8	1371.9	1371.0	1372.1	1374.2	1376.3	1378.4	1380.5
160°	1398.5	1397.1	1395.7	1394.2	1392.8	1392.1	1392.8	1394.2	1395.7	1397.1	1398.5
162.5°	1415.4	1414.0	1412.6	1411.1	1409.7	1409.0	1409.6	1410.8	1411.9	1413.1	1414.3
165°	1430.2	1428.8	1427.4	1425.9	1424.5	1423.8	1424.2	1424.9	1425.6	1426.3	1427.0
167.5°	1441.8	1440.4	1439.0	1437.5	1436.1	1435.4	1435.8	1436.5	1437.2	1437.9	1438.6
170°	1451.3	1449.9	1448.5	1447.0	1445.6	1444.9	1445.1	1445.6	1446.1	1446.6	1447.1
172.5°	1457.6	1456.2	1454.8	1453.4	1452.0	1451.3	1451.5	1452.0	1452.5	1452.9	1453.4
175°	1462.9	1461.3	1459.6	1458.0	1456.3	1455.5	1455.7	1456.2	1456.7	1457.1	1457.6
177.5°	1465.0	1463.4	1461.7	1460.1	1458.4	1457.6	1457.7	1458.0	1458.2	1458.5	1458.7
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2275.7	2278.7	2283.3	2304.7	2307.7	2313.8	2310.8	2310.8	2312.3	2309.3	2310.8
5°	2373.4	2378.0	2400.9	2426.9	2433.0	2426.9	2434.5	2445.2	2445.2	2445.2	2442.1
7.5°	2465.0	2481.8	2507.8	2546.0	2553.6	2561.3	2575.0	2565.8	2568.9	2582.6	2578.1
10°	2553.6	2578.1	2607.1	2639.1	2655.9	2666.6	2672.7	2686.5	2718.6	2681.9	2695.7
12.5°	2637.6	2672.7	2703.3	2738.4	2750.6	2764.4	2769.0	2781.2	2781.2	2779.7	2790.3
15°	2692.6	2724.7	2752.2	2775.1	2778.1	2775.1	2772.0	2773.5	2778.1	2759.8	2770.5
17.5°	2704.8	2707.9	2717.0	2707.9	2709.4	2677.3	2659.0	2654.4	2611.7	2613.2	2648.3
20°	2645.3	2593.3	2579.6	2529.2	2498.6	2416.2	2413.1	2390.2	2300.1	2327.6	2321.5
22.5°	2481.8	2393.3	2275.7	2217.6	2188.6	2101.5	2034.3	1987.0	1954.9	1922.8	1909.1
25°	2266.5	2122.9	1956.4	1841.9	1825.1	1744.2	1620.4	1562.4	1493.7	1472.3	1509.0
27.5°	1988.5	1802.2	1614.3	1438.7	1406.6	1333.3	1270.7	1229.5	1150.0	1145.5	1148.5
30°	1611.3	1423.4	1266.1	1151.6	1072.2	1038.6	997.3	966.8	934.7	946.9	950.0
32.5°	1324.2	1145.5	998.8	937.8	901.1	879.7	844.6	824.7	811.0	806.4	804.9
35°	1052.3	933.2	867.5	807.9	786.6	771.3	745.3	736.1	723.9	725.5	725.5
37.5°	901.1	801.8	753.0	722.4	702.5	694.9	678.1	668.9	661.3	658.3	662.8
40°	777.4	708.7	678.1	650.6	633.8	630.8	621.6	610.9	601.7	603.3	607.9
42.5°	687.3	647.6	610.9	589.5	577.3	572.7	565.1	557.5	557.5	552.9	551.3
45°	615.5	583.4	552.9	533.0	525.4	519.3	510.1	508.6	502.5	504.0	505.5
47.5°	551.3	525.4	502.5	482.6	475.0	473.5	464.3	458.2	458.2	456.7	455.1
50°	493.3	467.3	447.5	436.8	426.1	423.1	421.5	420.0	416.9	416.9	418.5
52.5°	446.0	420.0	404.7	395.6	389.5	386.4	386.4	384.9	384.9	384.9	383.3
55°	394.0	372.7	360.4	357.4	354.3	352.8	351.3	348.2	346.7	349.7	346.7
57.5°	345.2	337.5	326.8	323.8	316.1	316.1	311.6	308.5	305.5	308.5	308.5
60°	307.0	296.3	290.2	281.0	274.9	268.8	261.2	259.6	256.6	255.1	253.5
62.5°	267.3	258.1	242.8	229.1	219.9	213.8	210.8	209.2	209.2	207.7	207.7
65°	223.0	201.6	194.0	189.4	187.9	186.3	183.3	181.7	183.3	181.7	183.3
67.5°	174.1	171.1	166.5	163.4	161.9	160.4	160.4	158.8	158.8	158.8	158.8
70°	151.2	143.6	142.0	139.0	139.0	137.5	137.5	137.5	137.5	135.9	139.0
72.5°	125.2	120.7	119.1	117.6	117.6	117.6	116.1	116.1	116.1	114.5	116.1
75°	102.3	100.8	97.7	97.7	96.2	97.7	96.2	96.2	94.7	96.2	96.2
77.5°	82.5	80.9	79.4	79.4	77.9	77.9	77.9	77.9	77.9	77.9	79.4
80°	62.6	61.1	59.6	61.1	59.6	61.1	59.6	59.6	61.1	59.6	59.6
82.5°	45.8	44.3	44.3	42.8	42.8	42.8	42.8	42.8	42.8	42.8	42.8
85°	27.5	26.0	26.0	27.5	26.0	27.5	26.0	26.0	26.0	27.5	27.5
87.5°	12.2	13.7	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	13.7
90°	22.3	23.5	24.6	25.8	26.4	26.6	27.1	27.6	28.0	28.5	28.0
92.5°	25.8	26.3	26.8	27.3	27.5	27.6	27.8	28.1	28.3	28.5	28.3
95°	42.4	43.6	44.7	45.9	46.5	46.4	46.1	45.9	45.6	45.4	45.6
97.5°	54.6	55.3	56.0	56.7	57.0	57.1	57.4	57.6	57.9	58.1	57.9
100°	62.1	64.0	65.9	67.8	68.7	68.9	69.4	69.9	70.3	70.8	70.3
102.5°	64.9	67.5	70.0	72.6	73.9	74.3	75.0	75.7	76.4	77.1	76.4
105°	67.0	69.6	72.1	74.7	76.0	76.5	77.4	78.4	79.3	80.3	79.3
107.5°	69.1	71.7	74.3	76.9	78.2	78.7	79.6	80.5	81.5	82.4	81.5
110°	161.3	137.9	114.4	90.9	79.2	79.7	80.6	81.5	82.5	83.4	82.5

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	435.4	334.2	233.1	131.9	81.3	81.7	82.4	83.1	83.8	84.5	83.8
115°	543.0	434.4	325.7	217.0	162.7	154.2	137.3	120.4	103.5	86.6	103.5
117.5°	675.1	641.6	608.0	574.5	557.7	527.0	465.5	404.0	342.5	281.0	342.5
120°	777.0	779.8	782.7	785.5	786.9	771.1	739.4	707.7	676.0	644.3	676.0
122.5°	837.9	839.3	840.8	842.2	842.9	843.0	843.2	843.5	843.7	843.9	843.7
125°	894.1	895.8	897.4	899.1	899.9	900.3	901.0	901.7	902.4	903.1	902.4
127.5°	946.6	949.0	951.3	953.6	954.8	954.9	955.2	955.4	955.7	955.9	955.7
130°	996.5	999.1	1001.6	1004.2	1005.5	1005.4	1005.2	1004.9	1004.7	1004.5	1004.7
132.5°	1045.7	1047.8	1049.9	1052.0	1053.1	1053.0	1052.7	1052.5	1052.2	1052.0	1052.2
135°	1091.4	1093.7	1096.1	1098.4	1099.6	1099.4	1098.9	1098.4	1097.9	1097.4	1097.9
137.5°	1134.7	1137.0	1139.4	1141.7	1142.9	1142.5	1141.8	1141.1	1140.4	1139.7	1140.4
140°	1176.6	1178.8	1180.9	1183.0	1184.1	1183.5	1182.3	1181.2	1180.0	1178.8	1180.0
142.5°	1215.5	1217.4	1219.3	1221.2	1222.1	1221.5	1220.3	1219.2	1218.0	1216.8	1218.0
145°	1251.1	1252.8	1254.4	1256.1	1256.9	1256.3	1255.2	1254.0	1252.9	1251.7	1252.9
147.5°	1283.5	1284.7	1285.8	1287.0	1287.6	1287.1	1286.2	1285.2	1284.3	1283.3	1284.3
150°	1312.2	1313.6	1315.0	1316.4	1317.1	1316.5	1315.4	1314.2	1313.1	1311.9	1313.1
152.5°	1338.6	1340.0	1341.4	1342.8	1343.5	1342.7	1341.1	1339.4	1337.8	1336.2	1337.8
155°	1361.8	1363.2	1364.7	1366.1	1366.8	1365.9	1364.0	1362.1	1360.2	1358.3	1360.2
157.5°	1382.1	1383.8	1385.4	1387.1	1387.9	1387.0	1385.1	1383.2	1381.4	1379.5	1381.4
160°	1399.9	1401.3	1402.7	1404.1	1404.8	1404.0	1402.3	1400.7	1399.0	1397.4	1399.0
162.5°	1415.9	1417.6	1419.2	1420.9	1421.7	1420.6	1418.5	1416.4	1414.3	1412.2	1414.3
165°	1428.6	1430.3	1431.9	1433.6	1434.4	1433.6	1431.9	1430.3	1428.6	1427.0	1428.6
167.5°	1440.2	1441.9	1443.5	1445.2	1446.0	1444.9	1442.8	1440.7	1438.6	1436.5	1438.6
170°	1448.7	1450.4	1452.0	1453.7	1454.5	1453.4	1451.3	1449.2	1447.0	1444.9	1447.0
172.5°	1455.0	1456.7	1458.3	1460.0	1460.8	1459.7	1457.6	1455.5	1453.4	1451.3	1453.4
175°	1459.2	1460.9	1462.5	1464.2	1465.0	1463.8	1461.5	1459.2	1456.8	1454.5	1456.8
177.5°	1460.3	1462.0	1463.6	1465.3	1466.1	1465.0	1462.9	1460.8	1458.7	1456.6	1458.7
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2316.9	2306.2	2303.1	2306.2	2303.1	2304.7	2294.0	2254.3	2265.0	2248.2	2257.3
5°	2448.2	2439.1	2419.2	2416.2	2413.1	2410.1	2394.8	2359.7	2345.9	2323.0	2321.5
7.5°	2573.5	2573.5	2558.2	2547.5	2533.8	2523.1	2503.2	2451.3	2429.9	2402.4	2387.1
10°	2697.2	2657.5	2674.3	2663.6	2630.0	2623.9	2587.2	2556.7	2515.4	2487.9	2463.5
12.5°	2785.8	2773.5	2758.3	2749.1	2739.9	2720.1	2695.7	2617.8	2596.4	2541.4	2513.9
15°	2782.7	2775.1	2779.7	2779.7	2776.6	2772.0	2752.2	2695.7	2659.0	2605.5	2558.2
17.5°	2633.0	2652.9	2672.7	2686.5	2717.0	2730.8	2749.1	2715.5	2692.6	2646.8	2596.4
20°	2371.9	2420.7	2478.8	2491.0	2518.5	2599.4	2636.1	2665.1	2674.3	2659.0	2617.8
22.5°	2008.4	2049.6	2190.1	2187.1	2226.8	2323.0	2429.9	2517.0	2585.7	2623.9	2608.6
25°	1573.1	1631.1	1706.0	1762.5	1892.3	2035.9	2168.7	2307.7	2426.9	2532.2	2558.2
27.5°	1189.8	1266.1	1325.7	1400.5	1466.2	1635.7	1806.8	2023.6	2162.6	2362.7	2466.6
30°	962.2	997.3	1056.9	1092.0	1124.1	1253.9	1447.9	1661.7	1906.0	2136.7	2315.4
32.5°	821.7	846.1	890.4	905.7	939.3	1026.3	1148.5	1344.0	1596.0	1875.5	2110.7
35°	737.7	763.6	772.8	786.6	814.0	869.0	953.0	1095.1	1322.6	1596.0	1877.0
37.5°	665.9	679.6	705.6	714.8	723.9	765.2	821.7	921.0	1072.2	1296.7	1608.2
40°	615.5	623.1	636.9	644.5	650.6	679.6	730.0	797.2	908.7	1079.8	1366.9
42.5°	562.0	571.2	580.4	589.5	597.2	620.1	650.6	714.8	789.6	919.4	1127.1
45°	510.1	516.2	526.9	533.0	543.7	562.0	589.5	633.8	701.0	783.5	951.5
47.5°	462.8	470.4	475.0	482.6	490.3	510.1	536.1	565.1	620.1	701.0	823.2
50°	420.0	429.2	435.3	436.8	442.9	461.2	482.6	514.7	549.8	612.4	719.3
52.5°	389.5	391.0	395.6	401.7	400.1	410.8	430.7	455.1	491.8	542.2	620.1
55°	354.3	358.9	362.0	363.5	363.5	372.7	383.3	406.3	435.3	476.5	542.2
57.5°	310.0	314.6	323.8	326.8	331.4	336.0	340.6	355.9	380.3	420.0	473.5
60°	264.2	267.3	276.4	282.5	285.6	297.8	303.9	316.1	329.9	358.9	409.3
62.5°	212.3	215.3	219.9	226.0	232.1	250.5	265.7	278.0	288.7	308.5	349.7
65°	184.8	186.3	189.4	190.9	192.4	200.1	213.8	230.6	250.5	265.7	290.2
67.5°	160.4	161.9	163.4	166.5	168.0	169.5	175.6	180.2	200.1	221.5	239.8
70°	137.5	140.5	142.0	142.0	143.6	146.6	149.7	155.8	161.9	172.6	195.5
72.5°	116.1	117.6	120.7	120.7	120.7	123.7	126.8	129.8	132.9	139.0	148.1
75°	96.2	99.3	99.3	99.3	100.8	100.8	103.9	106.9	110.0	114.5	117.6
77.5°	79.4	79.4	79.4	79.4	80.9	80.9	82.5	85.5	87.1	88.6	91.6
80°	59.6	61.1	61.1	61.1	62.6	62.6	62.6	65.7	67.2	67.2	70.3
82.5°	44.3	44.3	44.3	45.8	44.3	45.8	45.8	47.3	45.8	47.3	48.9
85°	27.5	27.5	27.5	29.0	29.0	29.0	29.0	29.0	29.0	29.0	30.5
87.5°	13.7	13.7	13.7	13.7	13.7	13.7	13.7	13.7	15.3	13.7	13.7
90°	27.6	27.1	26.6	26.4	25.8	24.6	23.5	22.3	21.1	19.2	17.4
92.5°	28.1	27.8	27.6	27.5	27.3	26.8	26.3	25.8	25.3	24.6	23.9
95°	45.9	46.1	46.4	46.5	45.9	44.7	43.6	42.4	41.2	39.6	37.9
97.5°	57.6	57.4	57.1	57.0	56.7	56.0	55.3	54.6	53.9	50.1	46.4
100°	69.9	69.4	68.9	68.7	67.8	65.9	64.0	62.1	60.2	56.2	52.2
102.5°	75.7	75.0	74.3	73.9	72.6	70.0	67.5	64.9	62.3	105.0	147.8
105°	78.4	77.4	76.5	76.0	74.7	72.1	69.6	67.0	64.4	128.5	192.6
107.5°	80.5	79.6	78.7	78.2	76.9	74.3	71.7	69.1	66.5	145.6	224.7
110°	81.5	80.6	79.7	79.2	90.9	114.4	137.9	161.3	184.8	252.6	320.5

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	83.1	82.4	81.7	81.3	131.9	233.1	334.2	435.4	536.6	540.6	544.6
115°	120.4	137.3	154.2	162.7	217.0	325.7	434.4	543.0	651.7	645.8	640.0
117.5°	404.0	465.5	527.0	557.7	574.5	608.0	641.6	675.1	708.7	704.7	700.7
120°	707.7	739.4	771.1	786.9	785.5	782.7	779.8	777.0	774.2	770.0	765.8
122.5°	843.5	843.2	843.0	842.9	842.2	840.8	839.3	837.9	836.5	831.8	827.1
125°	901.7	901.0	900.3	899.9	899.1	897.4	895.8	894.1	892.5	888.1	883.6
127.5°	955.4	955.2	954.9	954.8	953.6	951.3	949.0	946.6	944.3	940.8	937.2
130°	1004.9	1005.2	1005.4	1005.5	1004.2	1001.6	999.1	996.5	993.9	991.3	988.7
132.5°	1052.5	1052.7	1053.0	1053.1	1052.0	1049.9	1047.8	1045.7	1043.6	1041.0	1038.4
135°	1098.4	1098.9	1099.4	1099.6	1098.4	1096.1	1093.7	1091.4	1089.0	1086.9	1084.8
137.5°	1141.1	1141.8	1142.5	1142.9	1141.7	1139.4	1137.0	1134.7	1132.3	1129.9	1127.6
140°	1181.2	1182.3	1183.5	1184.1	1183.0	1180.9	1178.8	1176.6	1174.5	1171.9	1169.3
142.5°	1219.2	1220.3	1221.5	1222.1	1221.2	1219.3	1217.4	1215.5	1213.6	1210.6	1207.5
145°	1254.0	1255.2	1256.3	1256.9	1256.1	1254.4	1252.8	1251.1	1249.5	1245.5	1241.5
147.5°	1285.2	1286.2	1287.1	1287.6	1287.0	1285.8	1284.7	1283.5	1282.3	1278.3	1274.3
150°	1314.2	1315.4	1316.5	1317.1	1316.4	1315.0	1313.6	1312.2	1310.8	1307.0	1303.3
152.5°	1339.4	1341.1	1342.7	1343.5	1342.8	1341.4	1340.0	1338.6	1337.2	1333.7	1330.2
155°	1362.1	1364.0	1365.9	1366.8	1366.1	1364.7	1363.2	1361.8	1360.4	1357.6	1354.8
157.5°	1383.2	1385.1	1387.0	1387.9	1387.1	1385.4	1383.8	1382.1	1380.5	1378.4	1376.3
160°	1400.7	1402.3	1404.0	1404.8	1404.1	1402.7	1401.3	1399.9	1398.5	1397.1	1395.7
162.5°	1416.4	1418.5	1420.6	1421.7	1420.9	1419.2	1417.6	1415.9	1414.3	1413.1	1411.9
165°	1430.3	1431.9	1433.6	1434.4	1433.6	1431.9	1430.3	1428.6	1427.0	1426.3	1425.6
167.5°	1440.7	1442.8	1444.9	1446.0	1445.2	1443.5	1441.9	1440.2	1438.6	1437.9	1437.2
170°	1449.2	1451.3	1453.4	1454.5	1453.7	1452.0	1450.4	1448.7	1447.1	1446.6	1446.1
172.5°	1455.5	1457.6	1459.7	1460.8	1460.0	1458.3	1456.7	1455.0	1453.4	1452.9	1452.5
175°	1459.2	1461.5	1463.8	1465.0	1464.2	1462.5	1460.9	1459.2	1457.6	1457.1	1456.7
177.5°	1460.8	1462.9	1465.0	1466.1	1465.3	1463.6	1462.0	1460.3	1458.7	1458.5	1458.2
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2243.6	2235.9	2235.9	2231.4	2231.4	2206.9	2206.9	2214.6	2205.4	2194.7	2179.4
5°	2301.6	2284.8	2280.2	2274.1	2254.3	2223.7	2211.5	2206.9	2188.6	2165.7	2139.7
7.5°	2356.6	2329.1	2315.4	2301.6	2275.7	2232.9	2208.4	2191.6	2164.2	2129.0	2095.4
10°	2410.1	2374.9	2339.8	2323.0	2286.3	2232.9	2197.8	2170.3	2130.6	2083.2	2035.9
12.5°	2458.9	2385.6	2379.5	2345.9	2292.5	2231.4	2177.9	2138.2	2087.8	2032.8	1977.8
15°	2501.7	2426.9	2390.2	2359.7	2289.4	2213.0	2156.5	2107.6	2040.4	1977.8	1910.6
17.5°	2523.1	2442.1	2417.7	2367.3	2295.5	2196.2	2119.9	2060.3	1987.0	1912.2	1835.8
20°	2544.5	2449.8	2410.1	2374.9	2277.2	2164.2	2078.6	2009.9	1929.0	1840.4	1756.4
22.5°	2555.1	2449.8	2402.4	2353.5	2258.9	2129.0	2028.2	1947.3	1852.6	1762.5	1661.7
25°	2536.8	2440.6	2384.1	2333.7	2226.8	2086.3	1970.2	1878.6	1777.8	1675.4	1573.1
27.5°	2491.0	2419.2	2353.5	2301.6	2182.5	2031.3	1909.1	1805.2	1701.4	1586.8	1483.0
30°	2405.5	2373.4	2321.5	2263.4	2133.6	1982.4	1837.3	1730.4	1615.9	1501.3	1392.9
32.5°	2272.6	2300.1	2266.5	2216.1	2075.6	1915.2	1761.0	1652.5	1527.3	1403.6	1304.3
35°	2110.7	2208.4	2190.1	2155.0	2014.5	1843.4	1689.2	1557.8	1432.6	1307.4	1208.1
37.5°	1933.5	2081.7	2097.0	2075.6	1944.2	1770.1	1600.6	1472.3	1344.0	1217.2	1116.4
40°	1690.7	1918.3	1967.1	1976.3	1870.9	1681.5	1504.4	1379.1	1252.4	1128.7	1006.5
42.5°	1467.7	1754.8	1815.9	1854.1	1777.8	1594.5	1415.8	1276.8	1151.6	1040.1	917.9
45°	1258.5	1557.8	1657.1	1706.0	1672.4	1495.2	1310.4	1180.6	1066.0	963.7	846.1
47.5°	1043.1	1344.0	1483.0	1560.9	1560.9	1394.4	1209.6	1081.3	971.4	884.3	780.4
50°	899.6	1150.0	1293.6	1395.9	1423.4	1292.1	1118.0	992.7	888.9	794.2	714.8
52.5°	766.7	991.2	1110.3	1217.2	1296.7	1182.1	1015.6	902.6	800.3	711.7	649.1
55°	662.8	830.8	939.3	1056.9	1145.5	1070.6	916.4	806.4	717.8	644.5	591.1
57.5°	563.6	710.2	798.8	902.6	997.3	940.8	817.1	722.4	644.5	580.4	533.0
60°	479.6	598.7	667.4	748.4	866.0	826.3	723.9	636.9	574.3	516.2	476.5
62.5°	407.8	502.5	560.5	618.5	725.5	707.1	627.7	560.5	507.1	458.2	424.6
65°	334.5	412.4	458.2	508.6	594.1	601.7	537.6	490.3	441.4	398.6	368.1
67.5°	270.3	331.4	372.7	415.4	484.1	505.5	461.2	421.5	380.3	345.2	317.7
70°	218.4	261.2	291.7	325.3	381.8	407.8	384.9	357.4	323.8	294.8	270.3
72.5°	172.6	200.1	218.4	244.4	290.2	316.1	314.6	290.2	265.7	245.9	226.0
75°	126.8	148.1	163.4	180.2	216.9	241.3	247.4	236.7	212.3	197.0	181.7
77.5°	96.2	108.4	116.1	128.3	154.3	175.6	184.8	181.7	164.9	152.7	142.0
80°	73.3	76.4	79.4	84.0	105.4	125.2	131.3	129.8	120.7	116.1	103.9
82.5°	51.9	53.5	55.0	56.5	64.1	80.9	87.1	90.1	82.5	77.9	67.2
85°	30.5	32.1	32.1	35.1	36.7	41.2	51.9	51.9	50.4	44.3	42.8
87.5°	15.3	15.3	13.7	13.7	15.3	16.8	19.9	22.9	19.9	18.3	16.8
90°	15.5	13.6	12.7	11.4	8.8	6.3	3.7	1.1	3.7	6.3	8.8
92.5°	23.2	22.5	22.2	22.7	23.6	24.5	25.5	26.4	25.5	24.5	23.6
95°	36.3	34.6	33.8	37.7	45.4	53.2	60.9	68.7	60.9	53.2	45.4
97.5°	42.6	38.9	37.0	46.6	65.9	85.1	104.4	123.6	104.4	85.1	65.9
100°	48.2	44.2	42.2	58.3	90.5	122.6	154.8	187.0	154.8	122.6	90.5
102.5°	190.5	233.2	254.6	254.8	255.3	255.8	256.2	256.7	256.2	255.8	255.3
105°	256.7	320.8	352.8	349.3	342.2	335.2	328.1	321.1	328.1	335.2	342.2
107.5°	303.8	382.9	422.5	419.6	413.7	407.8	402.0	396.1	402.0	407.8	413.7
110°	388.3	456.2	490.1	487.6	482.7	477.8	472.8	467.9	472.8	477.8	482.7

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	548.5	552.5	554.5	552.4	548.2	543.9	539.7	535.5	539.7	543.9	548.2
115°	634.1	628.2	625.3	623.3	619.3	615.3	611.3	607.3	611.3	615.3	619.3
117.5°	696.8	692.8	690.8	688.5	683.8	679.1	674.4	669.7	674.4	679.1	683.8
120°	761.5	757.3	755.2	753.4	749.9	746.4	742.9	739.4	742.9	746.4	749.9
122.5°	822.4	817.7	815.4	813.5	809.8	806.0	802.3	798.5	802.3	806.0	809.8
125°	879.2	874.7	872.5	871.0	867.9	864.8	861.8	858.7	861.8	864.8	867.9
127.5°	933.7	930.2	928.4	926.8	923.5	920.2	917.0	913.7	917.0	920.2	923.5
130°	986.2	983.6	982.3	980.4	976.7	972.9	969.2	965.4	969.2	972.9	976.7
132.5°	1035.9	1033.3	1032.0	1030.5	1027.4	1024.3	1021.3	1018.2	1021.3	1024.3	1027.4
135°	1082.7	1080.6	1079.5	1077.6	1073.9	1070.1	1066.4	1062.6	1066.4	1070.1	1073.9
137.5°	1125.2	1122.9	1121.7	1120.3	1117.5	1114.7	1111.9	1109.1	1111.9	1114.7	1117.5
140°	1166.8	1164.2	1162.9	1162.0	1160.1	1158.2	1156.4	1154.5	1156.4	1158.2	1160.1
142.5°	1204.5	1201.4	1199.9	1199.1	1197.4	1195.8	1194.1	1192.5	1194.1	1195.8	1197.4
145°	1237.6	1233.6	1231.6	1231.7	1231.9	1232.2	1232.4	1232.6	1232.4	1232.2	1231.9
147.5°	1270.3	1266.3	1264.3	1264.7	1265.4	1266.1	1266.8	1267.5	1266.8	1266.1	1265.4
150°	1299.5	1295.8	1293.9	1294.7	1296.4	1298.0	1299.7	1301.3	1299.7	1298.0	1296.4
152.5°	1326.7	1323.2	1321.4	1322.3	1324.2	1326.1	1327.9	1329.8	1327.9	1326.1	1324.2
155°	1352.0	1349.2	1347.8	1348.9	1351.0	1353.1	1355.2	1357.3	1355.2	1353.1	1351.0
157.5°	1374.2	1372.1	1371.0	1371.9	1373.8	1375.7	1377.6	1379.5	1377.6	1375.7	1373.8
160°	1394.2	1392.8	1392.1	1392.8	1394.2	1395.7	1397.1	1398.5	1397.1	1395.7	1394.2
162.5°	1410.8	1409.6	1409.0	1409.7	1411.1	1412.6	1414.0	1415.4	1414.0	1412.6	1411.1
165°	1424.9	1424.2	1423.8	1424.5	1425.9	1427.4	1428.8	1430.2	1428.8	1427.4	1425.9
167.5°	1436.5	1435.8	1435.4	1436.1	1437.5	1439.0	1440.4	1441.8	1440.4	1439.0	1437.5
170°	1445.6	1445.1	1444.9	1445.6	1447.0	1448.5	1449.9	1451.3	1449.9	1448.5	1447.0
172.5°	1452.0	1451.5	1451.3	1452.0	1453.4	1454.8	1456.2	1457.6	1456.2	1454.8	1453.4
175°	1456.2	1455.7	1455.5	1456.3	1458.0	1459.6	1461.3	1462.9	1461.3	1459.6	1458.0
177.5°	1458.0	1457.7	1457.6	1458.4	1460.1	1461.7	1463.4	1465.0	1463.4	1461.7	1460.1
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2173.3	2174.8	2179.4	2165.7	2144.3	2135.1	2107.6	2103.1	2098.5	2098.5	2103.1
5°	2124.4	2118.3	2119.9	2093.9	2063.4	2045.0	2006.8	2013.0	1993.1	1980.9	1983.9
7.5°	2071.0	2054.2	2052.7	2019.1	1980.9	1947.3	1907.6	1898.4	1880.1	1858.7	1849.5
10°	2003.8	1991.6	1968.7	1930.5	1881.6	1854.1	1800.7	1768.6	1764.0	1731.9	1719.7
12.5°	1935.1	1913.7	1890.8	1837.3	1782.3	1738.0	1698.3	1663.2	1638.8	1611.3	1593.0
15°	1855.6	1829.7	1803.7	1747.2	1683.1	1638.8	1579.2	1527.3	1455.5	1399.0	1366.9
17.5°	1768.6	1739.6	1704.4	1641.8	1579.2	1518.1	1408.2	1347.1	1296.7	1263.1	1243.2
20°	1678.5	1646.4	1611.3	1548.7	1440.2	1333.3	1272.2	1224.9	1194.3	1160.7	1136.3
22.5°	1583.8	1550.2	1512.0	1414.3	1299.7	1224.9	1177.5	1133.2	1089.0	1070.6	1058.4
25°	1495.2	1464.7	1415.8	1282.9	1192.8	1124.1	1070.6	1041.6	1018.7	994.3	971.4
27.5°	1403.6	1347.1	1278.3	1166.8	1110.3	1040.1	1001.9	980.5	940.8	924.0	913.3
30°	1293.6	1231.0	1165.3	1085.9	1020.2	971.4	936.2	901.1	878.2	861.4	843.1
32.5°	1182.1	1122.6	1081.3	998.8	950.0	899.6	866.0	844.6	811.0	800.3	792.7
35°	1085.9	1035.5	998.8	931.6	885.8	840.0	815.6	783.5	762.1	742.3	730.0
37.5°	991.2	963.7	925.5	869.0	820.2	783.5	749.9	739.2	710.2	699.5	687.3
40°	925.5	884.3	852.2	803.4	762.1	722.4	701.0	676.6	656.7	639.9	635.3
42.5°	846.1	815.6	797.2	743.8	701.0	678.1	652.1	624.7	609.4	595.6	578.8
45°	786.6	759.1	733.1	690.3	652.1	623.1	600.2	581.9	555.9	549.8	523.9
47.5°	723.9	696.4	676.6	633.8	598.7	571.2	554.4	530.0	508.6	494.8	482.6
50°	661.3	638.4	620.1	583.4	552.9	523.9	500.9	476.5	467.3	444.4	436.8
52.5°	601.7	586.5	566.6	531.5	500.9	476.5	452.1	432.2	418.5	406.3	397.1
55°	551.3	526.9	517.7	479.6	453.6	427.6	406.3	394.0	377.2	369.6	362.0
57.5°	494.8	481.1	465.8	436.8	407.8	383.3	368.1	349.7	340.6	331.4	325.3
60°	446.0	426.1	413.9	389.5	363.5	340.6	326.8	313.1	300.9	293.2	281.0
62.5°	389.5	374.2	366.5	340.6	319.2	297.8	285.6	271.9	262.7	248.9	233.7
65°	340.6	328.4	319.2	297.8	278.0	258.1	245.9	229.1	216.9	209.2	207.7
67.5°	297.8	288.7	274.9	255.1	235.2	219.9	206.2	192.4	190.9	187.9	187.9
70°	250.5	241.3	233.7	212.3	195.5	178.7	175.6	171.1	166.5	164.9	161.9
72.5°	209.2	201.6	192.4	174.1	157.3	152.7	149.7	146.6	142.0	140.5	139.0
75°	169.5	158.8	152.7	135.9	131.3	128.3	125.2	120.7	117.6	116.1	113.0
77.5°	129.8	119.1	119.1	110.0	106.9	102.3	99.3	96.2	94.7	91.6	91.6
80°	91.6	91.6	88.6	84.0	79.4	77.9	73.3	71.8	70.3	71.8	68.7
82.5°	67.2	61.1	61.1	58.0	55.0	53.5	50.4	50.4	48.9	48.9	48.9
85°	38.2	38.2	36.7	33.6	32.1	32.1	30.5	30.5	29.0	29.0	27.5
87.5°	15.3	13.7	15.3	13.7	13.7	12.2	12.2	12.2	10.7	12.2	10.7
90°	11.4	12.7	13.6	15.5	17.4	19.2	21.1	22.3	23.5	24.6	25.8
92.5°	22.7	22.2	22.5	23.2	23.9	24.6	25.3	25.8	26.3	26.8	27.3
95°	37.7	33.8	34.6	36.3	37.9	39.6	41.2	42.4	43.6	44.7	45.9
97.5°	46.6	37.0	38.9	42.6	46.4	50.1	53.9	54.6	55.3	56.0	56.7
100°	58.3	42.2	44.2	48.2	52.2	56.2	60.2	62.1	64.0	65.9	67.8
102.5°	254.8	254.6	233.2	190.5	147.8	105.0	62.3	64.9	67.5	70.0	72.6
105°	349.3	352.8	320.8	256.7	192.6	128.5	64.4	67.0	69.6	72.1	74.7
107.5°	419.6	422.5	382.9	303.8	224.7	145.6	66.5	69.1	71.7	74.3	76.9
110°	487.6	490.1	456.2	388.3	320.5	252.6	184.8	161.3	137.9	114.4	90.9

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	552.4	554.5	552.5	548.5	544.6	540.6	536.6	435.4	334.2	233.1	131.9
115°	623.3	625.3	628.2	634.1	640.0	645.8	651.7	543.0	434.4	325.7	217.0
117.5°	688.5	690.8	692.8	696.8	700.7	704.7	708.7	675.1	641.6	608.0	574.5
120°	753.4	755.2	757.3	761.5	765.8	770.0	774.2	777.0	779.8	782.7	785.5
122.5°	813.5	815.4	817.7	822.4	827.1	831.8	836.5	837.9	839.3	840.8	842.2
125°	871.0	872.5	874.7	879.2	883.6	888.1	892.5	894.1	895.8	897.4	899.1
127.5°	926.8	928.4	930.2	933.7	937.2	940.8	944.3	946.6	949.0	951.3	953.6
130°	980.4	982.3	983.6	986.2	988.7	991.3	993.9	996.5	999.1	1001.6	1004.2
132.5°	1030.5	1032.0	1033.3	1035.9	1038.4	1041.0	1043.6	1045.7	1047.8	1049.9	1052.0
135°	1077.6	1079.5	1080.6	1082.7	1084.8	1086.9	1089.0	1091.4	1093.7	1096.1	1098.4
137.5°	1120.3	1121.7	1122.9	1125.2	1127.6	1129.9	1132.3	1134.7	1137.0	1139.4	1141.7
140°	1162.0	1162.9	1164.2	1166.8	1169.3	1171.9	1174.5	1176.6	1178.8	1180.9	1183.0
142.5°	1199.1	1199.9	1201.4	1204.5	1207.5	1210.6	1213.6	1215.5	1217.4	1219.3	1221.2
145°	1231.7	1231.6	1233.6	1237.6	1241.5	1245.5	1249.5	1251.1	1252.8	1254.4	1256.1
147.5°	1264.7	1264.3	1266.3	1270.3	1274.3	1278.3	1282.3	1283.5	1284.7	1285.8	1287.0
150°	1294.7	1293.9	1295.8	1299.5	1303.3	1307.0	1310.8	1312.2	1313.6	1315.0	1316.4
152.5°	1322.3	1321.4	1323.2	1326.7	1330.2	1333.7	1337.2	1338.6	1340.0	1341.4	1342.8
155°	1348.9	1347.8	1349.2	1352.0	1354.8	1357.6	1360.4	1361.8	1363.2	1364.7	1366.1
157.5°	1371.9	1371.0	1372.1	1374.2	1376.3	1378.4	1380.5	1382.1	1383.8	1385.4	1387.1
160°	1392.8	1392.1	1392.8	1394.2	1395.7	1397.1	1398.5	1399.9	1401.3	1402.7	1404.1
162.5°	1409.7	1409.0	1409.6	1410.8	1411.9	1413.1	1414.3	1415.9	1417.6	1419.2	1420.9
165°	1424.5	1423.8	1424.2	1424.9	1425.6	1426.3	1427.0	1428.6	1430.3	1431.9	1433.6
167.5°	1436.1	1435.4	1435.8	1436.5	1437.2	1437.9	1438.6	1440.2	1441.9	1443.5	1445.2
170°	1445.6	1444.9	1445.1	1445.6	1446.1	1446.6	1447.1	1448.7	1450.4	1452.0	1453.7
172.5°	1452.0	1451.3	1451.5	1452.0	1452.5	1452.9	1453.4	1455.0	1456.7	1458.3	1460.0
175°	1456.3	1455.5	1455.7	1456.2	1456.7	1457.1	1457.6	1459.2	1460.9	1462.5	1464.2
177.5°	1458.4	1457.6	1457.7	1458.0	1458.2	1458.5	1458.7	1460.3	1462.0	1463.6	1465.3
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2103.1	2100.0	2090.8	2093.9	2089.3	2089.3	2086.3	2086.3	2086.3	2093.9	2089.3
5°	1988.5	1977.8	1967.1	1962.6	1958.0	1953.4	1953.4	1951.9	1965.6	1962.6	1974.8
7.5°	1846.5	1843.4	1822.0	1822.0	1814.4	1811.4	1819.0	1820.5	1822.0	1825.1	1832.7
10°	1719.7	1712.1	1681.5	1684.6	1680.0	1673.9	1678.5	1675.4	1686.1	1689.2	1686.1
12.5°	1570.0	1556.3	1522.7	1505.9	1487.6	1473.8	1490.6	1478.4	1521.2	1533.4	1567.0
15°	1371.5	1345.5	1322.6	1322.6	1305.8	1293.6	1301.2	1315.0	1324.2	1337.9	1344.0
17.5°	1238.6	1227.9	1209.6	1198.9	1194.3	1189.8	1189.8	1195.9	1215.7	1214.2	1226.4
20°	1125.6	1119.5	1110.3	1096.6	1092.0	1089.0	1089.0	1089.0	1102.7	1114.9	1122.6
22.5°	1047.7	1043.1	1037.0	1018.7	1009.5	1006.5	1014.1	1018.7	1029.4	1038.6	1046.2
25°	969.8	959.1	948.4	942.3	937.8	937.8	940.8	942.3	946.9	951.5	960.7
27.5°	905.7	898.0	882.8	866.0	866.0	861.4	864.4	867.5	878.2	893.5	901.1
30°	833.9	832.4	826.3	820.2	814.0	811.0	817.1	821.7	823.2	830.8	830.8
32.5°	782.0	771.3	760.6	754.5	751.4	749.9	751.4	757.5	757.5	766.7	777.4
35°	730.0	723.9	713.2	702.5	699.5	691.9	698.0	704.1	714.8	719.3	723.9
37.5°	673.5	665.9	661.3	658.3	652.1	653.7	649.1	658.3	667.4	665.9	668.9
40°	630.8	617.0	603.3	601.7	600.2	598.7	598.7	600.2	606.3	612.4	621.6
42.5°	575.8	571.2	559.0	546.8	543.7	540.7	537.6	543.7	555.9	566.6	571.2
45°	519.3	513.2	510.1	500.9	494.8	493.3	490.3	497.9	508.6	513.2	516.2
47.5°	467.3	465.8	456.7	458.2	453.6	455.1	453.6	458.2	458.2	462.8	465.8
50°	432.2	427.6	423.1	420.0	415.4	415.4	413.9	415.4	421.5	427.6	426.1
52.5°	397.1	389.5	387.9	386.4	383.3	386.4	381.8	383.3	389.5	392.5	391.0
55°	355.9	354.3	351.3	348.2	346.7	345.2	345.2	345.2	351.3	355.9	357.4
57.5°	323.8	316.1	310.0	310.0	303.9	302.4	305.5	307.0	311.6	314.6	317.7
60°	279.5	276.4	267.3	262.7	253.5	252.0	252.0	258.1	265.7	276.4	279.5
62.5°	232.1	227.6	226.0	226.0	226.0	226.0	226.0	226.0	226.0	227.6	227.6
65°	206.2	207.7	206.2	204.7	206.2	206.2	204.7	204.7	204.7	206.2	207.7
67.5°	184.8	183.3	184.8	183.3	181.7	181.7	180.2	181.7	183.3	184.8	184.8
70°	160.4	160.4	158.8	160.4	158.8	157.3	155.8	155.8	158.8	160.4	160.4
72.5°	137.5	137.5	135.9	135.9	132.9	132.9	134.4	132.9	132.9	137.5	137.5
75°	114.5	113.0	111.5	111.5	110.0	110.0	110.0	108.4	111.5	111.5	113.0
77.5°	90.1	90.1	90.1	88.6	88.6	87.1	87.1	88.6	88.6	88.6	90.1
80°	68.7	68.7	68.7	67.2	65.7	65.7	65.7	65.7	65.7	67.2	65.7
82.5°	47.3	47.3	47.3	47.3	47.3	45.8	45.8	45.8	47.3	47.3	45.8
85°	29.0	27.5	29.0	29.0	27.5	29.0	27.5	27.5	26.0	26.0	27.5
87.5°	12.2	10.7	9.2	9.2	10.7	9.2	9.2	9.2	10.7	9.2	9.2
90°	26.4	26.6	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.6	26.4
92.5°	27.5	27.6	27.8	28.1	28.3	28.5	28.3	28.1	27.8	27.6	27.5
95°	46.5	46.4	46.1	45.9	45.6	45.4	45.6	45.9	46.1	46.4	46.5
97.5°	57.0	57.1	57.4	57.6	57.9	58.1	57.9	57.6	57.4	57.1	57.0
100°	68.7	68.9	69.4	69.9	70.3	70.8	70.3	69.9	69.4	68.9	68.7
102.5°	73.9	74.3	75.0	75.7	76.4	77.1	76.4	75.7	75.0	74.3	73.9
105°	76.0	76.5	77.4	78.4	79.3	80.3	79.3	78.4	77.4	76.5	76.0
107.5°	78.2	78.7	79.6	80.5	81.5	82.4	81.5	80.5	79.6	78.7	78.2
110°	79.2	79.7	80.6	81.5	82.5	83.4	82.5	81.5	80.6	79.7	79.2

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	81.3	81.7	82.4	83.1	83.8	84.5	83.8	83.1	82.4	81.7	81.3
115°	162.7	154.2	137.3	120.4	103.5	86.6	103.5	120.4	137.3	154.2	162.7
117.5°	557.7	527.0	465.5	404.0	342.5	281.0	342.5	404.0	465.5	527.0	557.7
120°	786.9	771.1	739.4	707.7	676.0	644.3	676.0	707.7	739.4	771.1	786.9
122.5°	842.9	843.0	843.2	843.5	843.7	843.9	843.7	843.5	843.2	843.0	842.9
125°	899.9	900.3	901.0	901.7	902.4	903.1	902.4	901.7	901.0	900.3	899.9
127.5°	954.8	954.9	955.2	955.4	955.7	955.9	955.7	955.4	955.2	954.9	954.8
130°	1005.5	1005.4	1005.2	1004.9	1004.7	1004.5	1004.7	1004.9	1005.2	1005.4	1005.5
132.5°	1053.1	1053.0	1052.7	1052.5	1052.2	1052.0	1052.2	1052.5	1052.7	1053.0	1053.1
135°	1099.6	1099.4	1098.9	1098.4	1097.9	1097.4	1097.9	1098.4	1098.9	1099.4	1099.6
137.5°	1142.9	1142.5	1141.8	1141.1	1140.4	1139.7	1140.4	1141.1	1141.8	1142.5	1142.9
140°	1184.1	1183.5	1182.3	1181.2	1180.0	1178.8	1180.0	1181.2	1182.3	1183.5	1184.1
142.5°	1222.1	1221.5	1220.3	1219.2	1218.0	1216.8	1218.0	1219.2	1220.3	1221.5	1222.1
145°	1256.9	1256.3	1255.2	1254.0	1252.9	1251.7	1252.9	1254.0	1255.2	1256.3	1256.9
147.5°	1287.6	1287.1	1286.2	1285.2	1284.3	1283.3	1284.3	1285.2	1286.2	1287.1	1287.6
150°	1317.1	1316.5	1315.4	1314.2	1313.1	1311.9	1313.1	1314.2	1315.4	1316.5	1317.1
152.5°	1343.5	1342.7	1341.1	1339.4	1337.8	1336.2	1337.8	1339.4	1341.1	1342.7	1343.5
155°	1366.8	1365.9	1364.0	1362.1	1360.2	1358.3	1360.2	1362.1	1364.0	1365.9	1366.8
157.5°	1387.9	1387.0	1385.1	1383.2	1381.4	1379.5	1381.4	1383.2	1385.1	1387.0	1387.9
160°	1404.8	1404.0	1402.3	1400.7	1399.0	1397.4	1399.0	1400.7	1402.3	1404.0	1404.8
162.5°	1421.7	1420.6	1418.5	1416.4	1414.3	1412.2	1414.3	1416.4	1418.5	1420.6	1421.7
165°	1434.4	1433.6	1431.9	1430.3	1428.6	1427.0	1428.6	1430.3	1431.9	1433.6	1434.4
167.5°	1446.0	1444.9	1442.8	1440.7	1438.6	1436.5	1438.6	1440.7	1442.8	1444.9	1446.0
170°	1454.5	1453.4	1451.3	1449.2	1447.0	1444.9	1447.0	1449.2	1451.3	1453.4	1454.5
172.5°	1460.8	1459.7	1457.6	1455.5	1453.4	1451.3	1453.4	1455.5	1457.6	1459.7	1460.8
175°	1465.0	1463.8	1461.5	1459.2	1456.8	1454.5	1456.8	1459.2	1461.5	1463.8	1465.0
177.5°	1466.1	1465.0	1462.9	1460.8	1458.7	1456.6	1458.7	1460.8	1462.9	1465.0	1466.1
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2093.9	2101.5	2098.5	2081.7	2098.5	2103.1	2112.2	2121.4	2127.5	2136.7	2144.3
5°	1962.6	1977.8	1987.0	1977.8	2008.4	2013.0	2034.3	2046.6	2064.9	2080.2	2092.4
7.5°	1838.8	1851.1	1869.4	1872.4	1890.8	1912.2	1942.7	1973.2	2002.3	2017.5	2031.3
10°	1706.0	1727.4	1754.8	1748.7	1776.2	1809.8	1841.9	1890.8	1915.2	1942.7	1967.1
12.5°	1573.1	1586.8	1623.5	1635.7	1675.4	1701.4	1745.7	1776.2	1837.3	1869.4	1890.8
15°	1341.0	1397.5	1443.3	1498.3	1550.2	1599.1	1638.8	1693.8	1747.2	1771.6	1806.8
17.5°	1235.6	1261.5	1289.0	1316.5	1383.7	1470.8	1541.0	1600.6	1646.4	1678.5	1719.7
20°	1125.6	1151.6	1182.1	1208.1	1249.3	1311.9	1399.0	1501.3	1556.3	1589.9	1629.6
22.5°	1047.7	1072.2	1092.0	1114.9	1147.0	1192.8	1258.5	1385.2	1458.6	1499.8	1534.9
25°	963.7	994.3	1015.6	1032.4	1058.4	1108.8	1162.3	1234.0	1365.4	1397.5	1446.3
27.5°	905.7	914.8	939.3	965.2	991.2	1018.7	1073.7	1134.8	1223.4	1293.6	1353.2
30°	837.0	859.9	882.8	893.5	916.4	956.1	989.7	1055.4	1124.1	1179.1	1250.8
32.5°	785.0	798.8	814.0	840.0	861.4	888.9	922.5	977.5	1035.5	1070.6	1125.6
35°	727.0	736.1	768.2	778.9	800.3	827.8	861.4	904.2	966.8	994.3	1034.0
37.5°	672.0	693.4	702.5	727.0	746.8	774.3	798.8	847.6	888.9	921.0	957.6
40°	629.2	638.4	655.2	676.6	693.4	714.8	745.3	780.4	824.7	850.7	882.8
42.5°	577.3	584.9	606.3	618.5	646.0	665.9	684.2	727.0	766.7	786.6	818.6
45°	520.8	539.1	552.9	577.3	592.6	617.0	639.9	670.5	707.1	730.0	748.4
47.5°	471.9	490.3	504.0	526.9	551.3	562.0	586.5	618.5	652.1	670.5	696.4
50°	432.2	438.3	464.3	475.0	500.9	522.3	539.1	566.6	603.3	614.0	635.3
52.5°	394.0	398.6	415.4	429.2	452.1	470.4	491.8	517.7	548.3	565.1	581.9
55°	360.4	363.5	371.1	386.4	401.7	424.6	444.4	468.9	494.8	513.2	528.4
57.5°	322.3	328.4	334.5	343.6	358.9	380.3	401.7	424.6	446.0	458.2	478.0
60°	278.0	287.1	297.8	308.5	319.2	334.5	358.9	380.3	400.1	410.8	426.1
62.5°	230.6	248.9	258.1	270.3	279.5	293.2	311.6	336.0	349.7	363.5	375.7
65°	207.7	209.2	210.8	223.0	239.8	253.5	270.3	288.7	310.0	319.2	328.4
67.5°	184.8	186.3	189.4	190.9	197.0	212.3	230.6	250.5	267.3	273.4	282.5
70°	161.9	161.9	168.0	169.5	171.1	172.6	187.9	207.7	223.0	230.6	241.3
72.5°	137.5	139.0	142.0	143.6	146.6	149.7	154.3	164.9	183.3	190.9	203.1
75°	113.0	114.5	116.1	117.6	122.2	123.7	128.3	134.4	142.0	151.2	158.8
77.5°	90.1	90.1	91.6	94.7	97.7	99.3	103.9	106.9	110.0	114.5	120.7
80°	67.2	68.7	68.7	71.8	71.8	73.3	74.8	79.4	82.5	85.5	88.6
82.5°	45.8	48.9	48.9	48.9	50.4	51.9	53.5	53.5	56.5	58.0	62.6
85°	27.5	29.0	29.0	29.0	27.5	30.5	30.5	32.1	32.1	32.1	33.6
87.5°	10.7	9.2	10.7	10.7	10.7	12.2	10.7	10.7	12.2	13.7	13.7
90°	25.8	24.6	23.5	22.3	21.1	19.2	17.4	15.5	13.6	12.7	11.4
92.5°	27.3	26.8	26.3	25.8	25.3	24.6	23.9	23.2	22.5	22.2	22.7
95°	45.9	44.7	43.6	42.4	41.2	39.6	37.9	36.3	34.6	33.8	37.7
97.5°	56.7	56.0	55.3	54.6	53.9	50.1	46.4	42.6	38.9	37.0	46.6
100°	67.8	65.9	64.0	62.1	60.2	56.2	52.2	48.2	44.2	42.2	58.3
102.5°	72.6	70.0	67.5	64.9	62.3	105.0	147.8	190.5	233.2	254.6	254.8
105°	74.7	72.1	69.6	67.0	64.4	128.5	192.6	256.7	320.8	352.8	349.3
107.5°	76.9	74.3	71.7	69.1	66.5	145.6	224.7	303.8	382.9	422.5	419.6
110°	90.9	114.4	137.9	161.3	184.8	252.6	320.5	388.3	456.2	490.1	487.6

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	131.9	233.1	334.2	435.4	536.6	540.6	544.6	548.5	552.5	554.5	552.4
115°	217.0	325.7	434.4	543.0	651.7	645.8	640.0	634.1	628.2	625.3	623.3
117.5°	574.5	608.0	641.6	675.1	708.7	704.7	700.7	696.8	692.8	690.8	688.5
120°	785.5	782.7	779.8	777.0	774.2	770.0	765.8	761.5	757.3	755.2	753.4
122.5°	842.2	840.8	839.3	837.9	836.5	831.8	827.1	822.4	817.7	815.4	813.5
125°	899.1	897.4	895.8	894.1	892.5	888.1	883.6	879.2	874.7	872.5	871.0
127.5°	953.6	951.3	949.0	946.6	944.3	940.8	937.2	933.7	930.2	928.4	926.8
130°	1004.2	1001.6	999.1	996.5	993.9	991.3	988.7	986.2	983.6	982.3	980.4
132.5°	1052.0	1049.9	1047.8	1045.7	1043.6	1041.0	1038.4	1035.9	1033.3	1032.0	1030.5
135°	1098.4	1096.1	1093.7	1091.4	1089.0	1086.9	1084.8	1082.7	1080.6	1079.5	1077.6
137.5°	1141.7	1139.4	1137.0	1134.7	1132.3	1129.9	1127.6	1125.2	1122.9	1121.7	1120.3
140°	1183.0	1180.9	1178.8	1176.6	1174.5	1171.9	1169.3	1166.8	1164.2	1162.9	1162.0
142.5°	1221.2	1219.3	1217.4	1215.5	1213.6	1210.6	1207.5	1204.5	1201.4	1199.9	1199.1
145°	1256.1	1254.4	1252.8	1251.1	1249.5	1245.5	1241.5	1237.6	1233.6	1231.6	1231.7
147.5°	1287.0	1285.8	1284.7	1283.5	1282.3	1278.3	1274.3	1270.3	1266.3	1264.3	1264.7
150°	1316.4	1315.0	1313.6	1312.2	1310.8	1307.0	1303.3	1299.5	1295.8	1293.9	1294.7
152.5°	1342.8	1341.4	1340.0	1338.6	1337.2	1333.7	1330.2	1326.7	1323.2	1321.4	1322.3
155°	1366.1	1364.7	1363.2	1361.8	1360.4	1357.6	1354.8	1352.0	1349.2	1347.8	1348.9
157.5°	1387.1	1385.4	1383.8	1382.1	1380.5	1378.4	1376.3	1374.2	1372.1	1371.0	1371.9
160°	1404.1	1402.7	1401.3	1399.9	1398.5	1397.1	1395.7	1394.2	1392.8	1392.1	1392.8
162.5°	1420.9	1419.2	1417.6	1415.9	1414.3	1413.1	1411.9	1410.8	1409.6	1409.0	1409.7
165°	1433.6	1431.9	1430.3	1428.6	1427.0	1426.3	1425.6	1424.9	1424.2	1423.8	1424.5
167.5°	1445.2	1443.5	1441.9	1440.2	1438.6	1437.9	1437.2	1436.5	1435.8	1435.4	1436.1
170°	1453.7	1452.0	1450.4	1448.7	1447.1	1446.6	1446.1	1445.6	1445.1	1444.9	1445.6
172.5°	1460.0	1458.3	1456.7	1455.0	1453.4	1452.9	1452.5	1452.0	1451.5	1451.3	1452.0
175°	1464.2	1462.5	1460.9	1459.2	1457.6	1457.1	1456.7	1456.2	1455.7	1455.5	1456.3
177.5°	1465.3	1463.6	1462.0	1460.3	1458.7	1458.5	1458.2	1458.0	1457.7	1457.6	1458.4
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2197.8	2197.8	2197.8	2197.8
2.5°	2158.0	2153.5	2181.0	2211.5
5°	2113.8	2121.4	2156.5	2199.3
7.5°	2067.9	2084.7	2126.0	2182.5
10°	2003.8	2034.3	2097.0	2155.0
12.5°	1941.2	1982.4	2042.0	2110.7
15°	1870.9	1916.7	1990.0	2072.5
17.5°	1793.0	1845.0	1930.5	2020.6
20°	1710.6	1779.3	1869.4	1967.1
22.5°	1618.9	1701.4	1794.6	1903.0
25°	1530.3	1620.4	1713.6	1838.8
27.5°	1443.3	1531.9	1635.7	1762.5
30°	1356.2	1437.2	1548.7	1684.6
32.5°	1263.1	1347.1	1464.7	1603.6
35°	1177.5	1261.5	1371.5	1509.0
37.5°	1085.9	1176.0	1281.4	1423.4
40°	979.0	1084.4	1186.7	1322.6
42.5°	890.4	1001.9	1101.2	1229.5
45°	820.2	925.5	1008.0	1133.2
47.5°	754.5	840.0	924.0	1040.1
50°	691.9	757.5	844.6	948.4
52.5°	627.7	684.2	759.1	856.8
55°	569.7	623.1	690.3	765.2
57.5°	516.2	554.4	621.6	688.8
60°	456.7	496.4	548.3	604.8
62.5°	406.3	436.8	485.7	533.0
65°	352.8	381.8	418.5	462.8
67.5°	303.9	329.9	358.9	394.0
70°	259.6	279.5	300.9	331.4
72.5°	212.3	233.7	253.5	278.0
75°	174.1	183.3	200.1	216.9
77.5°	134.4	146.6	155.8	169.5
80°	96.2	106.9	110.0	120.7
82.5°	64.1	70.3	76.4	79.4
85°	36.7	39.7	45.8	47.3
87.5°	13.7	15.3	18.3	21.4
90°	8.8	6.3	3.7	1.1
92.5°	23.6	24.5	25.5	26.4
95°	45.4	53.2	60.9	68.7
97.5°	65.9	85.1	104.4	123.6
100°	90.5	122.6	154.8	187.0
102.5°	255.3	255.8	256.2	256.7
105°	342.2	335.2	328.1	321.1
107.5°	413.7	407.8	402.0	396.1
110°	482.7	477.8	472.8	467.9

TEST NUMBER: P999278

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	548.2	543.9	539.7	535.5
115°	619.3	615.3	611.3	607.3
117.5°	683.8	679.1	674.4	669.7
120°	749.9	746.4	742.9	739.4
122.5°	809.8	806.0	802.3	798.5
125°	867.9	864.8	861.8	858.7
127.5°	923.5	920.2	917.0	913.7
130°	976.7	972.9	969.2	965.4
132.5°	1027.4	1024.3	1021.3	1018.2
135°	1073.9	1070.1	1066.4	1062.6
137.5°	1117.5	1114.7	1111.9	1109.1
140°	1160.1	1158.2	1156.4	1154.5
142.5°	1197.4	1195.8	1194.1	1192.5
145°	1231.9	1232.2	1232.4	1232.6
147.5°	1265.4	1266.1	1266.8	1267.5
150°	1296.4	1298.0	1299.7	1301.3
152.5°	1324.2	1326.1	1327.9	1329.8
155°	1351.0	1353.1	1355.2	1357.3
157.5°	1373.8	1375.7	1377.6	1379.5
160°	1394.2	1395.7	1397.1	1398.5
162.5°	1411.1	1412.6	1414.0	1415.4
165°	1425.9	1427.4	1428.8	1430.2
167.5°	1437.5	1439.0	1440.4	1441.8
170°	1447.0	1448.5	1449.9	1451.3
172.5°	1453.4	1454.8	1456.2	1457.6
175°	1458.0	1459.6	1461.3	1462.9
177.5°	1460.1	1461.7	1463.4	1465.0
180°	1459.7	1459.7	1459.7	1459.7

(END OF REPORT)