

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998371

Luminaire Tested: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998371
REPORT IS A COMBINATION OF REPORTS P984111 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4665.0 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	29
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	24	23	22
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	34	30	26	26	23	20	18	16	15
7	55	44	36	31	49	39	33	28	31	26	23	24	20	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8760	8760	8760	8760
5°	8781	9341	8815	7431
10°	8680	10197	8734	6127
15°	8468	10755	8587	5160
20°	8337	10098	8337	4486
25°	8071	8676	8107	4012
30°	7634	6819	7780	3633
35°	7247	4716	7367	3324
40°	6800	3561	6879	3078
45°	6253	2926	6355	2812
50°	5778	2568	5787	2574
55°	5236	2188	5271	2316
60°	4661	1828	4725	2021
65°	4145	1487	4220	1726
70°	3629	1166	3720	1392
75°	3043	846	3166	1009
80°	2379	536	2547	599
85°	1568	270	1681	200

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9055 cd/sqm

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.7	1.1
10°-20°	153.4	3.3
20°-30°	222.7	4.8
30°-40°	234.7	5.0
40°-50°	207.7	4.5
50°-60°	165.9	3.6
60°-70°	112.7	2.4
70°-80°	57.6	1.2
80°-90°	16.8	0.4
90°-100°	192.6	4.1
100°-110°	678.3	14.5
110°-120°	712.4	15.3
120°-130°	586.1	12.6
130°-140°	470.8	10.1
140°-150°	355.6	7.6
150°-160°	250.0	5.4
160°-170°	147.2	3.2
170°-180°	47.9	1.0
0°-30°	428.8	9.2
0°-40°	663.5	14.2
0°-60°	1037.1	22.2
0°-90°	1224.2	26.2
90°-120°	1583.3	33.9
90°-150°	2995.8	64.2
90°-180°	3441.0	73.8
0°-180°	4665.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	553	553	553	553	553	
5°	554	618	556	492	554	53
15°	520	760	528	364	520	147
25°	468	633	470	293	468	214
35°	382	345	388	243	382	239
45°	286	208	291	200	286	222
55°	196	146	198	154	196	175
65°	117	90	119	104	117	116
75°	54	44	57	53	54	58
85°	11	12	12	8	11	13
90°	1	31	1	31	1	3
95°	33	108	33	108	33	34
105°	116	1071	116	1071	116	123
115°	204	1409	204	1409	204	203
125°	285	1143	285	1143	285	253
135°	334	947	334	947	334	258
145°	382	756	382	756	382	240
155°	434	636	434	636	434	200
165°	473	558	473	558	473	133
175°	493	503	493	503	493	47
180°	494	494	494	494	494	

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	556.4	557.7	559.8	560.2	564.5	567.9	571.7	571.7	573.0	572.6	569.2
5°	553.8	557.7	563.2	567.9	575.5	578.9	584.0	587.9	591.3	593.8	593.4
7.5°	549.6	556.4	564.5	573.4	583.6	589.6	596.8	603.6	608.3	612.5	615.5
10°	542.4	553.8	564.9	576.8	590.0	598.1	606.6	615.5	622.8	630.8	638.5
12.5°	532.6	549.2	562.8	578.5	594.7	603.6	617.2	624.0	638.1	658.5	664.0
15°	520.2	542.8	555.5	575.5	596.8	604.0	622.8	633.8	662.7	675.5	690.8
17.5°	508.7	533.8	550.9	573.8	594.7	608.7	627.0	649.5	673.8	692.1	709.1
20°	499.4	523.6	544.1	569.6	596.0	613.8	633.0	660.2	686.6	705.3	718.5
22.5°	478.1	509.2	533.0	561.5	593.4	618.1	636.4	666.1	694.6	706.1	717.6
25°	467.5	494.3	521.9	554.3	591.7	621.0	636.8	670.0	695.1	699.3	701.9
27.5°	447.9	478.1	510.5	547.5	591.3	615.9	635.9	666.1	686.1	683.2	675.5
30°	423.7	460.7	496.4	536.4	585.3	612.1	630.8	658.5	668.7	653.4	639.8
32.5°	405.8	440.7	480.2	526.6	578.5	604.0	622.3	644.0	646.1	618.5	595.5
35°	381.6	420.3	464.9	513.9	567.0	590.0	607.0	620.2	610.0	571.3	544.1
37.5°	359.9	398.2	445.8	495.6	551.3	573.8	587.4	589.6	564.5	530.4	490.5
40°	336.0	375.6	425.4	477.7	533.8	553.4	561.9	555.5	519.4	479.8	433.5
42.5°	312.2	351.4	405.0	458.6	511.7	528.3	531.7	514.3	470.0	423.7	370.1
45°	286.3	327.1	380.7	434.7	486.2	495.6	496.0	470.9	418.6	370.1	320.3
47.5°	265.0	302.9	356.0	410.1	453.5	459.8	457.3	428.4	371.4	316.9	273.5
50°	241.6	277.8	330.5	383.7	420.7	422.4	416.0	374.8	319.0	269.3	234.8
52.5°	216.5	253.1	301.6	352.6	385.8	383.3	370.9	326.7	274.4	233.1	206.7
55°	196.5	228.9	274.4	324.1	347.5	340.3	326.7	281.6	240.3	205.5	182.5
57.5°	174.4	202.9	247.6	291.0	304.6	297.8	284.2	242.0	203.8	177.4	162.1
60°	153.6	179.5	218.6	254.8	265.4	258.2	242.5	204.6	177.0	154.8	143.4
62.5°	134.4	157.0	189.7	222.9	227.2	219.9	206.3	175.7	151.9	134.4	125.9
65°	116.6	137.8	164.2	189.3	193.1	185.5	171.4	149.3	129.3	118.3	110.2
67.5°	99.1	116.1	139.5	157.8	159.9	152.7	141.2	123.4	111.0	99.1	93.2
70°	83.8	96.6	114.9	129.7	130.6	123.8	117.8	101.7	92.3	83.8	79.1
72.5°	68.9	77.8	91.9	102.9	103.4	99.1	93.6	83.4	75.3	69.3	64.7
75°	54.4	62.1	70.6	80.4	80.0	76.6	72.3	65.9	59.1	55.3	53.2
77.5°	41.7	46.4	53.2	59.6	59.6	57.9	55.3	50.6	46.4	42.5	40.4
80°	29.8	32.8	38.3	40.4	41.3	40.8	38.7	35.3	33.6	30.6	29.8
82.5°	19.1	21.3	23.8	25.9	27.2	26.4	25.9	24.2	21.7	20.8	20.0
85°	11.1	11.9	13.2	14.5	14.9	14.5	15.3	14.0	12.8	12.8	12.3
87.5°	4.7	5.1	6.0	6.0	6.4	6.4	6.0	6.4	6.4	6.0	5.5
90°	1.0	3.8	7.6	9.5	11.4	12.8	14.3	19.0	25.7	31.4	32.3
92.5°	14.3	20.0	27.6	32.3	39.9	45.2	50.4	76.0	112.1	144.4	146.3
95°	33.3	37.1	46.6	55.1	70.3	81.7	93.1	136.8	219.5	329.7	372.5
97.5°	49.4	55.1	65.6	77.9	95.0	107.8	120.7	176.7	291.7	469.4	607.2
100°	73.2	76.0	84.6	99.8	118.8	132.1	145.4	195.7	311.7	516.9	750.6
102.5°	95.0	96.9	105.5	120.7	140.6	153.9	167.2	212.8	312.6	498.8	755.4
105°	115.9	119.7	126.4	140.6	161.5	174.8	188.1	232.8	317.4	474.1	704.1
107.5°	138.7	141.6	148.2	161.5	182.4	195.7	209.0	252.7	327.8	460.8	656.6
110°	161.5	165.3	171.0	183.4	203.3	217.1	230.9	272.7	341.1	457.0	624.3

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	182.4	186.2	192.9	204.3	223.3	237.6	251.8	291.7	355.4	458.0	603.4
115°	204.3	209.0	214.7	226.1	245.1	258.0	270.8	311.7	369.6	461.8	589.1
117.5°	227.1	230.9	236.6	247.0	265.1	278.4	291.7	329.7	384.8	467.5	581.5
120°	248.0	251.8	257.5	266.0	285.0	298.4	311.7	348.7	400.0	473.2	574.8
122.5°	267.9	270.8	276.5	286.0	305.0	318.8	332.6	366.8	413.3	479.8	571.0
125°	285.0	287.9	293.6	305.0	324.0	337.3	350.6	384.8	427.6	486.5	566.3
127.5°	299.3	303.1	310.7	323.1	341.1	354.9	368.7	401.9	440.9	493.1	563.4
130°	311.7	315.5	325.0	338.3	357.3	370.6	383.9	417.1	453.2	500.7	561.5
132.5°	323.1	327.8	338.3	352.5	372.5	385.8	399.1	430.4	465.6	508.3	560.6
135°	334.5	338.3	349.7	363.9	385.8	399.1	412.4	442.8	476.0	514.0	559.6
137.5°	344.9	349.7	361.1	376.3	398.1	410.4	422.8	453.2	484.6	519.7	559.6
140°	357.3	361.1	372.5	387.7	408.6	421.0	433.3	461.8	491.2	523.5	558.7
142.5°	369.6	372.5	382.9	398.1	418.1	429.5	440.9	468.4	496.9	526.4	558.7
145°	382.0	385.8	395.3	409.5	428.5	439.0	449.4	475.1	501.7	528.3	556.8
147.5°	395.3	398.1	407.6	420.9	437.1	446.6	456.1	480.8	504.5	529.2	553.9
150°	408.6	411.4	419.0	431.4	445.6	454.2	462.7	484.6	506.4	528.3	551.1
152.5°	421.9	422.8	430.4	440.9	454.2	461.8	469.4	488.4	507.4	526.4	546.3
155°	434.2	435.2	440.9	451.3	461.8	468.9	476.0	492.2	508.3	524.5	540.6
157.5°	444.7	445.6	450.4	459.9	468.4	474.6	480.8	495.0	508.3	520.7	534.9
160°	455.1	456.1	459.9	467.5	475.1	480.3	485.5	496.9	508.3	517.8	529.2
162.5°	465.6	464.6	468.4	474.1	480.8	484.6	488.4	497.9	507.4	515.0	524.5
165°	473.2	472.2	474.1	479.8	484.6	487.4	490.3	498.8	505.5	511.2	517.8
167.5°	479.8	478.9	480.8	484.6	488.4	490.3	492.2	498.8	504.5	507.4	512.1
170°	486.5	484.6	485.5	488.4	490.3	491.7	493.1	497.9	502.6	504.5	507.4
172.5°	490.3	489.3	488.4	491.2	492.2	493.2	494.1	496.9	499.8	500.7	501.7
175°	493.1	492.2	491.2	493.1	493.1	493.6	494.1	496.0	497.9	496.9	497.9
177.5°	495.0	493.1	492.2	494.1	494.1	494.1	494.1	495.0	496.9	495.0	494.1
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	575.1	575.5	576.4	580.6	582.8	583.2	581.5	585.3	586.6	585.3	584.5
5°	602.3	604.9	610.0	615.5	615.1	615.5	618.1	620.6	621.5	618.1	619.3
7.5°	626.2	631.3	636.8	645.3	645.3	649.5	651.3	653.4	658.5	655.9	655.1
10°	653.4	660.2	670.4	684.0	684.4	688.7	692.9	699.7	701.9	700.2	701.0
12.5°	687.4	700.6	701.4	716.3	723.1	724.0	730.8	729.5	733.8	733.8	741.0
15°	702.3	722.7	734.2	748.7	752.9	747.8	753.3	759.3	759.7	759.7	759.3
17.5°	729.1	737.2	748.7	756.3	758.0	758.0	758.4	761.0	759.3	755.9	758.4
20°	734.6	738.0	742.3	741.4	742.3	738.0	733.8	729.5	729.9	727.8	734.2
22.5°	724.4	723.6	713.8	707.4	707.4	698.9	690.8	687.0	683.2	684.4	686.6
25°	698.9	685.7	673.8	664.4	662.3	648.7	637.6	634.2	627.9	633.0	633.8
27.5°	658.1	643.2	624.0	615.9	604.9	599.4	591.7	581.5	568.3	576.0	574.7
30°	614.2	592.1	576.4	556.8	539.4	538.1	523.6	506.6	499.8	499.8	503.6
32.5°	565.3	536.0	513.0	485.4	468.3	461.1	443.7	426.7	430.5	417.7	422.4
35°	508.3	469.6	440.7	413.9	401.1	392.6	370.1	360.7	350.5	344.6	355.6
37.5°	453.9	409.2	372.2	342.9	338.2	322.9	307.5	301.6	295.6	298.2	297.8
40°	387.5	348.0	314.8	291.8	283.7	276.5	266.3	259.1	255.2	257.4	257.8
42.5°	327.5	294.4	269.7	253.5	246.7	241.6	236.5	230.6	229.3	229.3	231.0
45°	281.2	253.9	237.4	224.2	220.3	216.5	212.7	210.1	209.3	207.6	208.9
47.5°	244.2	222.5	212.3	202.5	198.2	197.4	194.0	192.7	191.0	190.6	191.0
50°	213.1	199.5	190.1	184.6	181.6	180.4	178.7	176.1	175.3	177.4	176.5
52.5°	191.4	178.7	173.6	168.0	166.3	164.6	162.1	162.5	162.1	161.2	161.2
55°	169.7	161.6	156.5	152.3	151.9	150.2	148.0	147.2	146.8	145.9	147.2
57.5°	152.3	145.9	141.2	137.4	135.7	135.7	133.6	131.9	131.9	131.4	131.9
60°	134.8	128.5	125.5	121.7	120.4	120.0	118.7	117.8	116.6	116.6	116.6
62.5°	118.7	113.6	110.2	106.8	107.2	105.1	103.4	102.5	102.5	102.9	102.9
65°	103.4	100.0	95.7	92.7	91.9	91.5	90.6	90.2	88.9	89.8	89.8
67.5°	89.3	84.6	82.1	80.8	79.5	79.1	78.3	77.4	77.0	76.6	77.4
70°	75.3	71.5	69.3	68.5	67.2	66.8	66.4	65.1	65.5	65.9	66.4
72.5°	62.5	59.1	58.7	56.1	56.1	56.1	54.4	55.3	54.9	54.0	54.9
75°	49.3	47.6	46.8	45.5	45.9	45.5	45.1	43.8	43.8	44.2	44.7
77.5°	39.1	37.4	37.0	35.7	34.9	35.7	34.9	34.5	34.5	34.9	34.9
80°	28.9	28.1	26.8	26.8	26.8	26.4	26.4	26.4	25.9	25.5	25.9
82.5°	19.1	19.1	18.7	18.3	18.7	17.9	18.3	18.3	18.3	18.3	18.3
85°	12.3	11.9	11.9	11.5	11.5	11.5	11.9	11.1	11.1	11.5	11.5
87.5°	5.5	5.5	5.5	6.0	5.5	5.5	5.5	6.0	5.5	5.5	5.5
90°	31.4	30.4	28.5	30.4	30.9	31.4	31.4	31.4	31.4	31.4	31.4
92.5°	122.6	96.0	81.7	71.3	67.5	63.7	62.7	58.9	59.9	58.0	59.9
95°	325.9	248.9	191.0	151.1	140.6	130.2	117.8	110.2	107.4	108.3	107.4
97.5°	611.9	509.3	406.7	310.7	282.2	253.7	216.6	197.6	187.2	181.5	187.2
100°	887.5	867.5	749.7	619.5	562.0	504.5	425.7	384.8	357.3	340.2	357.3
102.5°	990.1	1102.2	1098.4	1011.9	950.2	888.4	801.0	724.0	687.9	663.2	687.9
105°	956.8	1154.4	1261.8	1274.2	1258.5	1242.8	1183.9	1125.0	1084.1	1070.8	1084.1
107.5°	886.5	1098.4	1258.0	1351.1	1370.1	1389.1	1388.2	1379.6	1367.3	1345.4	1367.3
110°	820.9	1021.4	1191.5	1313.1	1352.0	1391.0	1431.9	1450.0	1458.5	1457.6	1458.5

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	775.3	951.1	1112.6	1244.7	1290.8	1336.9	1397.7	1430.9	1449.0	1455.7	1449.0
115°	739.2	896.0	1042.3	1166.8	1215.8	1264.7	1332.1	1375.8	1400.5	1409.1	1400.5
117.5°	714.5	850.4	981.5	1097.4	1144.0	1190.6	1259.9	1306.5	1332.1	1338.8	1332.1
120°	695.5	818.1	935.9	1036.6	1079.8	1123.1	1189.6	1234.3	1261.8	1271.3	1261.8
122.5°	679.4	792.4	897.9	992.0	1030.0	1068.0	1125.9	1169.7	1193.4	1201.0	1193.4
125°	664.2	767.7	865.6	949.2	984.8	1020.5	1075.6	1111.7	1135.4	1143.0	1135.4
127.5°	649.9	743.0	833.3	913.1	946.4	979.6	1028.1	1062.3	1083.2	1088.9	1083.2
130°	635.7	719.3	801.0	876.1	907.4	938.8	985.3	1017.6	1036.6	1044.2	1036.6
132.5°	624.3	696.5	770.6	838.0	867.0	896.0	941.6	973.9	991.0	997.7	991.0
135°	613.8	675.6	738.3	801.0	827.6	854.2	895.1	926.4	943.5	947.3	943.5
137.5°	606.2	658.5	712.6	763.9	787.6	811.4	850.4	878.0	893.2	898.9	893.2
140°	599.6	642.3	687.9	731.6	752.5	773.4	803.8	828.5	842.8	848.5	842.8
142.5°	592.9	629.0	666.1	702.2	718.8	735.4	763.9	785.8	798.1	798.1	798.1
145°	587.2	616.7	648.0	677.5	691.2	705.0	727.8	744.0	753.5	756.3	753.5
147.5°	581.5	607.2	632.8	656.6	667.0	677.5	697.4	710.7	717.4	719.3	717.4
150°	573.9	596.7	617.6	637.6	646.2	654.7	668.9	680.3	686.0	687.0	686.0
152.5°	567.2	586.3	605.3	621.4	628.6	635.7	646.1	655.6	659.4	659.4	659.4
155°	558.7	576.7	592.0	606.2	611.4	616.7	627.1	633.8	637.6	635.7	637.6
157.5°	551.1	565.3	578.7	591.0	595.3	599.6	607.2	612.9	614.8	614.8	614.8
160°	542.5	554.9	565.3	575.8	579.2	582.5	589.1	593.9	594.8	594.8	594.8
162.5°	534.9	544.4	553.0	561.5	563.9	566.3	572.9	575.8	576.7	575.8	576.7
165°	526.4	534.0	540.6	547.3	549.2	551.1	554.9	558.7	558.7	557.7	558.7
167.5°	517.8	523.5	529.2	534.0	535.9	537.8	539.7	541.6	541.6	540.6	541.6
170°	511.2	515.9	518.8	522.6	523.6	524.5	525.4	528.3	527.3	525.4	527.3
172.5°	504.5	507.4	509.3	512.1	512.6	513.1	514.0	515.0	514.0	513.1	514.0
175°	498.8	501.7	502.6	503.6	504.0	504.5	504.5	505.5	504.5	502.6	504.5
177.5°	495.0	496.9	496.9	497.9	497.9	497.9	497.9	497.9	496.9	495.0	496.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	586.6	583.6	581.1	581.5	583.6	581.9	577.7	572.1	570.0	567.5	570.0
5°	621.9	619.3	614.2	614.7	613.4	611.7	604.9	596.4	596.4	589.6	588.7
7.5°	656.8	653.0	649.5	648.7	644.0	640.6	634.7	622.8	618.1	610.0	605.3
10°	695.9	692.9	689.1	684.4	681.9	675.9	666.1	648.7	640.2	629.1	621.0
12.5°	735.5	735.0	726.5	717.2	716.8	707.4	700.6	677.2	665.7	650.8	631.7
15°	760.6	758.4	753.8	749.1	750.4	740.2	724.8	697.2	689.5	671.7	651.3
17.5°	760.1	760.1	758.9	758.0	756.7	753.8	745.3	727.0	714.6	692.1	672.9
20°	735.9	741.4	742.7	742.3	746.5	748.7	748.2	736.8	727.0	707.0	687.4
22.5°	687.4	700.2	705.7	709.1	718.0	722.7	733.8	729.5	727.0	712.1	695.5
25°	642.3	646.6	663.2	664.0	676.3	687.8	698.9	706.1	715.5	710.0	695.9
27.5°	584.0	593.8	605.7	614.7	617.2	640.6	658.9	672.5	693.8	695.5	690.8
30°	518.1	522.8	542.4	554.3	567.9	584.9	611.3	634.7	653.8	671.2	677.2
32.5°	437.7	456.9	468.3	482.8	494.7	524.9	557.2	587.4	609.6	638.9	651.7
35°	364.1	379.0	398.6	404.5	426.2	451.7	493.9	532.6	566.2	596.0	621.9
37.5°	303.3	315.2	336.0	345.4	358.2	390.9	426.2	474.3	514.7	551.3	583.6
40°	261.6	270.5	286.3	289.3	299.9	329.7	358.2	403.3	456.9	506.2	541.5
42.5°	233.1	237.4	248.0	251.8	258.6	278.6	304.1	346.7	396.5	447.5	497.3
45°	212.7	215.7	222.0	225.4	234.0	242.9	263.7	297.8	336.9	388.4	442.0
47.5°	194.4	198.2	200.8	202.9	207.6	217.4	231.0	256.1	293.5	340.7	392.6
50°	179.1	180.4	185.0	185.5	188.4	194.8	207.6	222.9	252.7	291.0	341.2
52.5°	163.8	165.0	168.0	171.0	172.3	177.4	185.9	198.7	220.8	251.0	295.6
55°	148.5	150.2	153.1	155.3	156.5	160.8	165.9	178.2	195.7	216.9	253.5
57.5°	133.1	137.0	137.8	139.1	141.2	145.9	150.6	157.8	171.4	191.0	217.8
60°	118.7	120.0	122.9	124.2	126.3	128.9	134.8	140.4	150.2	165.5	189.7
62.5°	103.8	106.8	108.0	109.3	111.0	114.0	117.8	123.8	132.3	144.6	163.8
65°	91.0	91.5	94.0	95.7	97.4	99.5	103.4	108.9	114.0	125.5	139.5
67.5°	78.7	79.5	80.4	82.1	84.2	86.4	89.8	92.7	99.1	106.8	117.8
70°	66.8	66.8	68.9	70.2	69.8	72.3	74.9	78.3	82.9	90.2	99.1
72.5°	56.1	55.7	57.4	57.9	58.7	60.4	62.1	65.5	68.1	73.6	80.4
75°	44.7	45.5	46.4	46.4	47.6	48.9	50.6	52.3	55.3	58.7	63.8
77.5°	35.3	35.3	36.2	36.6	37.9	37.4	39.1	40.8	43.0	45.9	49.8
80°	25.9	26.8	26.8	26.8	27.2	27.6	29.4	30.6	31.9	34.0	35.7
82.5°	18.3	18.3	19.1	19.1	19.1	20.0	20.0	20.4	21.3	22.5	23.8
85°	11.5	11.5	11.5	11.9	11.5	11.9	12.8	12.3	12.8	13.6	13.6
87.5°	5.5	5.5	5.5	5.5	5.5	6.0	5.5	6.0	6.4	6.4	6.4
90°	31.4	31.4	31.4	30.9	30.4	28.5	30.4	31.4	32.3	31.4	25.7
92.5°	58.9	62.7	63.7	67.5	71.3	81.7	96.0	122.6	146.3	144.4	112.1
95°	110.2	117.8	130.2	140.6	151.1	191.0	248.9	325.9	372.5	329.7	219.5
97.5°	197.6	216.6	253.7	282.2	310.7	406.7	509.3	611.9	607.2	469.4	291.7
100°	384.8	425.7	504.5	562.0	619.5	749.7	867.5	887.5	750.6	516.9	311.7
102.5°	724.0	801.0	888.4	950.2	1011.9	1098.4	1102.2	990.1	755.4	498.8	312.6
105°	1125.0	1183.9	1242.8	1258.5	1274.2	1261.8	1154.4	956.8	704.1	474.1	317.4
107.5°	1379.6	1388.2	1389.1	1370.1	1351.1	1258.0	1098.4	886.5	656.6	460.8	327.8
110°	1450.0	1431.9	1391.0	1352.0	1313.1	1191.5	1021.4	820.9	624.3	457.0	341.1

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1430.9	1397.7	1336.9	1290.8	1244.7	1112.6	951.1	775.3	603.4	458.0	355.4
115°	1375.8	1332.1	1264.7	1215.8	1166.8	1042.3	896.0	739.2	589.1	461.8	369.6
117.5°	1306.5	1259.9	1190.6	1144.0	1097.4	981.5	850.4	714.5	581.5	467.5	384.8
120°	1234.3	1189.6	1123.1	1079.8	1036.6	935.9	818.1	695.5	574.8	473.2	400.0
122.5°	1169.7	1125.9	1068.0	1030.0	992.0	897.9	792.4	679.4	571.0	479.8	413.3
125°	1111.7	1075.6	1020.5	984.8	949.2	865.6	767.7	664.2	566.3	486.5	427.6
127.5°	1062.3	1028.1	979.6	946.4	913.1	833.3	743.0	649.9	563.4	493.1	440.9
130°	1017.6	985.3	938.8	907.4	876.1	801.0	719.3	635.7	561.5	500.7	453.2
132.5°	973.9	941.6	896.0	867.0	838.0	770.6	696.5	624.3	560.6	508.3	465.6
135°	926.4	895.1	854.2	827.6	801.0	738.3	675.6	613.8	559.6	514.0	476.0
137.5°	878.0	850.4	811.4	787.6	763.9	712.6	658.5	606.2	559.6	519.7	484.6
140°	828.5	803.8	773.4	752.5	731.6	687.9	642.3	599.6	558.7	523.5	491.2
142.5°	785.8	763.9	735.4	718.8	702.2	666.1	629.0	592.9	558.7	526.4	496.9
145°	744.0	727.8	705.0	691.2	677.5	648.0	616.7	587.2	556.8	528.3	501.7
147.5°	710.7	697.4	677.5	667.0	656.6	632.8	607.2	581.5	553.9	529.2	504.5
150°	680.3	668.9	654.7	646.2	637.6	617.6	596.7	573.9	551.1	528.3	506.4
152.5°	655.6	646.1	635.7	628.6	621.4	605.3	586.3	567.2	546.3	526.4	507.4
155°	633.8	627.1	616.7	611.4	606.2	592.0	576.7	558.7	540.6	524.5	508.3
157.5°	612.9	607.2	599.6	595.3	591.0	578.7	565.3	551.1	534.9	520.7	508.3
160°	593.9	589.1	582.5	579.2	575.8	565.3	554.9	542.5	529.2	517.8	508.3
162.5°	575.8	572.9	566.3	563.9	561.5	553.0	544.4	534.9	524.5	515.0	507.4
165°	558.7	554.9	551.1	549.2	547.3	540.6	534.0	526.4	517.8	511.2	505.5
167.5°	541.6	539.7	537.8	535.9	534.0	529.2	523.5	517.8	512.1	507.4	504.5
170°	528.3	525.4	524.5	523.6	522.6	518.8	515.9	511.2	507.4	504.5	502.6
172.5°	515.0	514.0	513.1	512.6	512.1	509.3	507.4	504.5	501.7	500.7	499.8
175°	505.5	504.5	504.5	504.0	503.6	502.6	501.7	498.8	497.9	496.9	497.9
177.5°	497.9	497.9	497.9	497.9	497.9	496.9	496.9	495.0	494.1	495.0	496.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	567.9	565.7	564.5	565.3	562.8	556.4	556.4	558.5	556.0	553.4	549.6
5°	583.6	579.4	576.8	576.4	570.4	560.2	558.1	556.0	550.4	544.5	538.1
7.5°	598.9	591.3	587.0	584.0	575.5	562.3	556.8	552.1	543.2	534.3	526.2
10°	611.7	600.6	595.5	590.8	579.8	563.2	554.3	545.8	534.3	522.8	512.6
12.5°	621.9	609.1	602.8	596.0	582.3	560.6	549.6	536.0	524.5	509.2	499.0
15°	638.9	612.5	606.6	600.2	586.2	556.4	542.8	527.5	511.7	491.3	480.2
17.5°	652.5	617.2	616.8	603.2	584.9	554.7	533.8	513.9	496.8	476.4	459.0
20°	660.6	624.5	617.6	603.6	580.6	543.2	521.5	499.4	481.1	456.4	439.0
22.5°	667.4	634.7	616.8	599.8	571.7	539.4	507.5	486.6	461.5	434.7	418.1
25°	670.0	636.8	618.1	598.5	565.3	528.3	492.2	469.6	441.5	417.3	394.7
27.5°	670.4	636.4	613.4	593.0	556.4	513.9	476.8	453.0	422.0	393.9	371.4
30°	666.1	631.7	610.8	588.7	547.9	500.7	458.1	431.8	398.6	370.5	347.1
32.5°	653.4	622.3	605.3	581.1	536.8	482.4	440.3	410.9	376.0	348.4	325.8
35°	632.1	610.8	592.1	569.6	522.4	465.4	422.4	387.9	352.6	326.3	305.0
37.5°	605.7	594.3	576.8	554.7	505.8	450.0	402.4	364.1	328.8	303.3	282.4
40°	570.0	573.0	556.0	536.0	486.2	429.2	376.5	339.9	306.7	282.9	262.5
42.5°	531.3	543.6	533.8	514.7	464.5	406.2	357.3	316.9	284.6	259.9	242.9
45°	489.6	510.9	504.9	490.9	442.0	382.0	330.1	291.0	262.5	238.6	223.7
47.5°	444.1	474.3	474.3	464.1	416.9	357.7	306.7	266.7	238.6	221.6	207.2
50°	397.7	431.8	437.3	430.5	388.8	330.1	278.2	242.0	217.8	201.2	190.6
52.5°	349.2	388.8	399.0	395.6	359.0	303.7	254.8	219.5	197.4	182.9	173.6
55°	302.9	348.8	359.9	361.1	327.1	274.8	228.9	197.8	176.5	166.7	158.7
57.5°	259.1	303.3	315.6	317.8	294.8	248.4	204.6	177.4	158.2	150.2	143.8
60°	221.6	258.6	274.8	279.5	259.5	217.8	182.1	155.7	141.2	133.6	127.6
62.5°	191.0	220.8	237.8	239.1	230.1	191.0	158.7	136.5	124.2	117.4	114.4
65°	161.2	188.0	198.2	203.3	196.1	165.5	137.0	118.7	108.9	102.9	100.0
67.5°	137.4	154.4	162.9	169.7	162.5	139.5	116.6	101.7	94.4	88.5	86.8
70°	112.7	126.8	133.1	139.9	133.6	116.1	99.5	85.9	79.5	74.9	72.7
72.5°	90.2	101.2	107.2	111.4	107.6	93.2	79.5	70.2	65.5	62.1	60.8
75°	71.5	79.1	82.5	85.5	83.8	72.7	64.2	56.6	52.3	49.3	48.5
77.5°	54.4	60.0	63.8	64.7	62.5	55.3	48.1	43.4	40.0	38.3	37.4
80°	38.7	42.1	44.2	45.5	43.4	40.4	35.3	31.9	28.9	26.8	26.4
82.5°	25.9	27.6	29.4	28.9	28.1	25.5	22.5	20.8	19.6	17.9	17.9
85°	14.9	15.3	16.2	16.6	16.2	14.5	12.8	11.9	11.1	9.8	9.8
87.5°	6.4	6.8	6.8	7.2	6.4	6.4	5.5	4.7	4.7	4.3	3.8
90°	19.0	14.3	12.8	11.4	9.5	7.6	3.8	1.0	3.8	7.6	9.5
92.5°	76.0	50.4	45.2	39.9	32.3	27.6	20.0	14.3	20.0	27.6	32.3
95°	136.8	93.1	81.7	70.3	55.1	46.6	37.1	33.3	37.1	46.6	55.1
97.5°	176.7	120.7	107.8	95.0	77.9	65.6	55.1	49.4	55.1	65.6	77.9
100°	195.7	145.4	132.1	118.8	99.8	84.6	76.0	73.2	76.0	84.6	99.8
102.5°	212.8	167.2	153.9	140.6	120.7	105.5	96.9	95.0	96.9	105.5	120.7
105°	232.8	188.1	174.8	161.5	140.6	126.4	119.7	115.9	119.7	126.4	140.6
107.5°	252.7	209.0	195.7	182.4	161.5	148.2	141.6	138.7	141.6	148.2	161.5
110°	272.7	230.9	217.1	203.3	183.4	171.0	165.3	161.5	165.3	171.0	183.4

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	291.7	251.8	237.6	223.3	204.3	192.9	186.2	182.4	186.2	192.9	204.3
115°	311.7	270.8	258.0	245.1	226.1	214.7	209.0	204.3	209.0	214.7	226.1
117.5°	329.7	291.7	278.4	265.1	247.0	236.6	230.9	227.1	230.9	236.6	247.0
120°	348.7	311.7	298.4	285.0	266.0	257.5	251.8	248.0	251.8	257.5	266.0
122.5°	366.8	332.6	318.8	305.0	286.0	276.5	270.8	267.9	270.8	276.5	286.0
125°	384.8	350.6	337.3	324.0	305.0	293.6	287.9	285.0	287.9	293.6	305.0
127.5°	401.9	368.7	354.9	341.1	323.1	310.7	303.1	299.3	303.1	310.7	323.1
130°	417.1	383.9	370.6	357.3	338.3	325.0	315.5	311.7	315.5	325.0	338.3
132.5°	430.4	399.1	385.8	372.5	352.5	338.3	327.8	323.1	327.8	338.3	352.5
135°	442.8	412.4	399.1	385.8	363.9	349.7	338.3	334.5	338.3	349.7	363.9
137.5°	453.2	422.8	410.4	398.1	376.3	361.1	349.7	344.9	349.7	361.1	376.3
140°	461.8	433.3	421.0	408.6	387.7	372.5	361.1	357.3	361.1	372.5	387.7
142.5°	468.4	440.9	429.5	418.1	398.1	382.9	372.5	369.6	372.5	382.9	398.1
145°	475.1	449.4	439.0	428.5	409.5	395.3	385.8	382.0	385.8	395.3	409.5
147.5°	480.8	456.1	446.6	437.1	420.9	407.6	398.1	395.3	398.1	407.6	420.9
150°	484.6	462.7	454.2	445.6	431.4	419.0	411.4	408.6	411.4	419.0	431.4
152.5°	488.4	469.4	461.8	454.2	440.9	430.4	422.8	421.9	422.8	430.4	440.9
155°	492.2	476.0	468.9	461.8	451.3	440.9	435.2	434.2	435.2	440.9	451.3
157.5°	495.0	480.8	474.6	468.4	459.9	450.4	445.6	444.7	445.6	450.4	459.9
160°	496.9	485.5	480.3	475.1	467.5	459.9	456.1	455.1	456.1	459.9	467.5
162.5°	497.9	488.4	484.6	480.8	474.1	468.4	464.6	465.6	464.6	468.4	474.1
165°	498.8	490.3	487.4	484.6	479.8	474.1	472.2	473.2	472.2	474.1	479.8
167.5°	498.8	492.2	490.3	488.4	484.6	480.8	478.9	479.8	478.9	480.8	484.6
170°	497.9	493.1	491.7	490.3	488.4	485.5	484.6	486.5	484.6	485.5	488.4
172.5°	496.9	494.1	493.2	492.2	491.2	488.4	489.3	490.3	489.3	488.4	491.2
175°	496.0	494.1	493.6	493.1	493.1	491.2	492.2	493.1	492.2	491.2	493.1
177.5°	495.0	494.1	494.1	494.1	494.1	492.2	493.1	495.0	493.1	492.2	494.1
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	547.5	549.6	549.2	544.9	540.2	536.4	529.2	530.0	527.5	527.9	530.4
5°	533.8	533.8	532.1	526.2	518.5	514.3	506.2	504.1	499.0	498.5	498.1
7.5°	519.4	517.3	515.1	506.6	497.3	490.5	479.4	476.8	471.7	468.3	466.6
10°	502.4	499.4	495.1	485.4	473.9	465.4	453.9	450.5	440.7	436.4	433.9
12.5°	483.7	482.0	475.1	467.1	448.3	439.0	422.4	425.8	416.0	407.5	406.2
15°	464.9	458.6	454.7	441.5	419.0	414.7	401.6	394.7	385.8	379.0	379.0
17.5°	446.6	436.9	428.4	414.3	397.7	385.8	376.0	372.6	361.6	354.8	353.5
20°	422.4	411.3	409.2	389.2	377.7	364.5	355.2	346.7	338.6	335.6	333.5
22.5°	399.4	386.7	383.3	366.2	354.8	341.6	332.2	326.3	320.3	318.2	314.4
25°	374.8	367.1	362.0	343.7	330.9	318.6	312.2	308.0	302.4	302.0	299.5
27.5°	350.9	343.7	338.6	321.2	311.8	300.3	295.2	290.5	287.6	286.3	285.0
30°	330.5	322.4	316.5	303.7	292.2	282.9	278.6	275.6	273.9	271.8	271.4
32.5°	308.0	303.3	295.2	285.4	276.5	267.6	265.0	262.9	260.3	259.5	259.1
35°	288.8	282.4	277.3	266.3	262.5	254.8	251.8	250.1	246.7	245.9	245.0
37.5°	270.1	264.2	258.6	251.8	244.6	240.3	238.6	236.1	234.4	234.8	234.0
40°	251.4	246.7	242.5	235.2	231.0	228.9	225.4	222.9	222.0	222.5	222.0
42.5°	233.1	228.9	226.3	220.8	216.5	214.4	212.3	209.7	211.0	211.0	212.3
45°	216.5	212.7	211.0	206.7	204.2	200.8	198.7	198.2	199.9	199.5	199.5
47.5°	199.5	198.2	196.1	192.3	188.9	186.7	186.3	186.3	188.0	188.9	188.4
50°	186.3	183.8	181.2	178.2	175.7	174.8	173.6	174.4	176.1	176.1	177.0
52.5°	169.7	168.0	167.2	164.6	162.9	162.9	162.9	163.3	164.6	165.9	165.5
55°	155.3	154.0	153.1	151.9	149.7	150.2	149.7	150.6	151.9	153.1	154.0
57.5°	139.9	139.5	138.7	136.5	136.5	136.1	137.4	137.8	139.9	140.8	142.1
60°	126.3	125.1	125.1	123.4	123.4	123.4	124.6	125.9	127.6	128.0	128.9
62.5°	111.9	111.9	111.4	110.2	110.2	111.4	111.9	113.6	114.4	114.4	115.7
65°	98.3	97.8	97.4	97.8	98.3	98.3	99.5	100.4	101.2	101.7	102.1
67.5°	84.6	84.2	85.1	84.6	85.5	87.2	86.8	88.1	89.3	89.3	89.8
70°	71.9	72.7	72.3	73.2	72.7	73.6	74.9	75.3	75.3	75.7	77.0
72.5°	60.0	60.0	60.0	59.6	60.0	60.8	61.7	62.1	63.0	63.4	64.7
75°	48.5	48.5	47.6	48.5	48.5	49.3	50.2	50.2	50.2	51.0	52.3
77.5°	36.6	37.0	36.6	37.4	37.4	37.9	38.7	38.3	39.1	39.6	40.0
80°	26.8	26.4	26.4	26.4	26.8	26.8	27.6	28.1	28.1	29.4	28.5
82.5°	17.0	17.4	17.0	17.4	17.4	17.9	17.4	17.9	18.3	19.1	18.7
85°	9.8	9.4	9.4	9.8	9.4	9.4	9.8	9.4	9.8	9.4	9.8
87.5°	3.8	3.4	3.4	3.4	3.4	3.0	3.0	2.6	2.6	2.6	2.1
90°	11.4	12.8	14.3	19.0	25.7	31.4	32.3	31.4	30.4	28.5	30.4
92.5°	39.9	45.2	50.4	76.0	112.1	144.4	146.3	122.6	96.0	81.7	71.3
95°	70.3	81.7	93.1	136.8	219.5	329.7	372.5	325.9	248.9	191.0	151.1
97.5°	95.0	107.8	120.7	176.7	291.7	469.4	607.2	611.9	509.3	406.7	310.7
100°	118.8	132.1	145.4	195.7	311.7	516.9	750.6	887.5	867.5	749.7	619.5
102.5°	140.6	153.9	167.2	212.8	312.6	498.8	755.4	990.1	1102.2	1098.4	1011.9
105°	161.5	174.8	188.1	232.8	317.4	474.1	704.1	956.8	1154.4	1261.8	1274.2
107.5°	182.4	195.7	209.0	252.7	327.8	460.8	656.6	886.5	1098.4	1258.0	1351.1
110°	203.3	217.1	230.9	272.7	341.1	457.0	624.3	820.9	1021.4	1191.5	1313.1

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	223.3	237.6	251.8	291.7	355.4	458.0	603.4	775.3	951.1	1112.6	1244.7
115°	245.1	258.0	270.8	311.7	369.6	461.8	589.1	739.2	896.0	1042.3	1166.8
117.5°	265.1	278.4	291.7	329.7	384.8	467.5	581.5	714.5	850.4	981.5	1097.4
120°	285.0	298.4	311.7	348.7	400.0	473.2	574.8	695.5	818.1	935.9	1036.6
122.5°	305.0	318.8	332.6	366.8	413.3	479.8	571.0	679.4	792.4	897.9	992.0
125°	324.0	337.3	350.6	384.8	427.6	486.5	566.3	664.2	767.7	865.6	949.2
127.5°	341.1	354.9	368.7	401.9	440.9	493.1	563.4	649.9	743.0	833.3	913.1
130°	357.3	370.6	383.9	417.1	453.2	500.7	561.5	635.7	719.3	801.0	876.1
132.5°	372.5	385.8	399.1	430.4	465.6	508.3	560.6	624.3	696.5	770.6	838.0
135°	385.8	399.1	412.4	442.8	476.0	514.0	559.6	613.8	675.6	738.3	801.0
137.5°	398.1	410.4	422.8	453.2	484.6	519.7	559.6	606.2	658.5	712.6	763.9
140°	408.6	421.0	433.3	461.8	491.2	523.5	558.7	599.6	642.3	687.9	731.6
142.5°	418.1	429.5	440.9	468.4	496.9	526.4	558.7	592.9	629.0	666.1	702.2
145°	428.5	439.0	449.4	475.1	501.7	528.3	556.8	587.2	616.7	648.0	677.5
147.5°	437.1	446.6	456.1	480.8	504.5	529.2	553.9	581.5	607.2	632.8	656.6
150°	445.6	454.2	462.7	484.6	506.4	528.3	551.1	573.9	596.7	617.6	637.6
152.5°	454.2	461.8	469.4	488.4	507.4	526.4	546.3	567.2	586.3	605.3	621.4
155°	461.8	468.9	476.0	492.2	508.3	524.5	540.6	558.7	576.7	592.0	606.2
157.5°	468.4	474.6	480.8	495.0	508.3	520.7	534.9	551.1	565.3	578.7	591.0
160°	475.1	480.3	485.5	496.9	508.3	517.8	529.2	542.5	554.9	565.3	575.8
162.5°	480.8	484.6	488.4	497.9	507.4	515.0	524.5	534.9	544.4	553.0	561.5
165°	484.6	487.4	490.3	498.8	505.5	511.2	517.8	526.4	534.0	540.6	547.3
167.5°	488.4	490.3	492.2	498.8	504.5	507.4	512.1	517.8	523.5	529.2	534.0
170°	490.3	491.7	493.1	497.9	502.6	504.5	507.4	511.2	515.9	518.8	522.6
172.5°	492.2	493.2	494.1	496.9	499.8	500.7	501.7	504.5	507.4	509.3	512.1
175°	493.1	493.6	494.1	496.0	497.9	496.9	497.9	498.8	501.7	502.6	503.6
177.5°	494.1	494.1	494.1	495.0	496.9	495.0	494.1	495.0	496.9	496.9	497.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	527.5	528.7	525.8	524.9	525.8	522.8	523.6	524.5	524.5	525.8	526.6
5°	496.8	495.1	492.2	491.3	490.5	491.7	490.9	492.2	492.6	495.6	496.0
7.5°	466.6	464.1	461.5	459.0	458.1	456.0	458.1	458.1	461.1	460.3	462.4
10°	430.9	430.5	427.1	425.8	424.1	420.7	425.4	424.1	426.2	430.1	430.9
12.5°	404.5	399.9	402.0	396.0	398.2	394.7	395.2	395.2	398.6	399.0	398.2
15°	379.4	375.6	370.1	367.5	366.2	364.5	370.1	370.5	368.0	373.9	371.8
17.5°	353.9	353.9	348.8	347.5	344.1	345.8	345.0	345.4	344.6	348.8	350.9
20°	331.8	329.7	328.0	328.4	324.1	323.3	322.4	323.3	326.3	329.2	330.1
22.5°	313.9	312.7	308.4	309.2	305.8	307.1	306.3	308.4	308.8	308.8	311.8
25°	296.9	295.2	295.6	293.9	292.7	292.7	291.4	292.7	294.4	295.2	295.6
27.5°	284.2	282.9	280.7	279.5	280.3	278.2	279.9	281.2	281.2	280.3	281.2
30°	268.8	269.7	269.7	265.4	267.1	266.3	267.6	268.4	268.4	268.8	268.0
32.5°	258.6	256.1	255.7	255.2	255.2	253.5	253.5	254.8	255.2	255.7	256.9
35°	245.0	245.0	242.9	244.2	242.5	242.9	242.5	242.9	243.7	242.5	243.7
37.5°	232.7	233.1	232.3	233.1	233.5	232.7	231.8	233.5	232.7	232.7	231.8
40°	222.0	221.6	222.0	222.0	222.0	222.5	221.6	221.6	221.6	220.8	219.9
42.5°	213.1	210.6	211.4	211.8	210.6	210.6	211.0	210.6	211.8	209.3	209.3
45°	200.4	199.5	199.9	199.9	200.8	199.5	200.4	200.8	199.5	199.1	198.2
47.5°	188.9	189.7	188.9	189.7	189.7	190.6	188.9	189.3	189.7	188.0	186.7
50°	177.4	177.4	178.7	178.2	178.7	177.8	177.8	177.4	177.8	177.0	175.7
52.5°	166.7	165.5	167.6	167.2	166.7	166.3	165.9	166.3	165.5	164.6	164.6
55°	153.6	153.6	154.8	155.3	155.3	154.4	153.6	154.0	153.6	153.1	152.7
57.5°	142.9	141.2	142.1	142.5	142.5	141.2	142.1	141.2	141.2	141.7	140.4
60°	129.3	129.3	128.5	129.7	129.7	128.9	128.9	129.3	128.5	128.0	127.6
62.5°	114.9	115.3	116.6	117.0	117.4	116.6	115.7	116.1	116.1	114.9	115.3
65°	102.5	103.4	105.1	104.6	103.8	104.2	103.4	103.8	102.5	102.9	101.7
67.5°	90.6	90.2	90.6	90.6	91.5	91.0	90.2	90.2	89.8	91.0	89.8
70°	77.8	77.8	77.8	77.8	78.3	78.7	77.8	77.0	77.4	76.6	76.1
72.5°	64.7	65.1	64.7	65.5	64.2	65.1	65.1	64.7	64.2	64.2	64.2
75°	52.3	53.2	51.9	52.3	51.9	52.7	52.3	52.3	51.5	51.0	51.5
77.5°	40.0	40.4	39.6	40.0	39.6	40.0	40.0	39.6	39.6	39.6	39.6
80°	28.5	28.9	28.5	28.1	27.6	28.5	27.6	28.1	28.5	28.1	28.9
82.5°	18.3	18.3	17.9	18.3	17.4	17.4	17.9	17.9	17.4	18.3	17.4
85°	8.9	8.9	9.8	8.9	8.5	8.5	8.5	8.9	8.5	9.4	8.9
87.5°	2.1	1.7	2.1	2.1	1.7	1.7	2.1	1.7	2.1	2.6	1.7
90°	30.9	31.4	31.4	31.4	31.4	31.4	31.4	31.4	31.4	31.4	30.9
92.5°	67.5	63.7	62.7	58.9	59.9	58.0	59.9	58.9	62.7	63.7	67.5
95°	140.6	130.2	117.8	110.2	107.4	108.3	107.4	110.2	117.8	130.2	140.6
97.5°	282.2	253.7	216.6	197.6	187.2	181.5	187.2	197.6	216.6	253.7	282.2
100°	562.0	504.5	425.7	384.8	357.3	340.2	357.3	384.8	425.7	504.5	562.0
102.5°	950.2	888.4	801.0	724.0	687.9	663.2	687.9	724.0	801.0	888.4	950.2
105°	1258.5	1242.8	1183.9	1125.0	1084.1	1070.8	1084.1	1125.0	1183.9	1242.8	1258.5
107.5°	1370.1	1389.1	1388.2	1379.6	1367.3	1345.4	1367.3	1379.6	1388.2	1389.1	1370.1
110°	1352.0	1391.0	1431.9	1450.0	1458.5	1457.6	1458.5	1450.0	1431.9	1391.0	1352.0

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1290.8	1336.9	1397.7	1430.9	1449.0	1455.7	1449.0	1430.9	1397.7	1336.9	1290.8
115°	1215.8	1264.7	1332.1	1375.8	1400.5	1409.1	1400.5	1375.8	1332.1	1264.7	1215.8
117.5°	1144.0	1190.6	1259.9	1306.5	1332.1	1338.8	1332.1	1306.5	1259.9	1190.6	1144.0
120°	1079.8	1123.1	1189.6	1234.3	1261.8	1271.3	1261.8	1234.3	1189.6	1123.1	1079.8
122.5°	1030.0	1068.0	1125.9	1169.7	1193.4	1201.0	1193.4	1169.7	1125.9	1068.0	1030.0
125°	984.8	1020.5	1075.6	1111.7	1135.4	1143.0	1135.4	1111.7	1075.6	1020.5	984.8
127.5°	946.4	979.6	1028.1	1062.3	1083.2	1088.9	1083.2	1062.3	1028.1	979.6	946.4
130°	907.4	938.8	985.3	1017.6	1036.6	1044.2	1036.6	1017.6	985.3	938.8	907.4
132.5°	867.0	896.0	941.6	973.9	991.0	997.7	991.0	973.9	941.6	896.0	867.0
135°	827.6	854.2	895.1	926.4	943.5	947.3	943.5	926.4	895.1	854.2	827.6
137.5°	787.6	811.4	850.4	878.0	893.2	898.9	893.2	878.0	850.4	811.4	787.6
140°	752.5	773.4	803.8	828.5	842.8	848.5	842.8	828.5	803.8	773.4	752.5
142.5°	718.8	735.4	763.9	785.8	798.1	798.1	798.1	785.8	763.9	735.4	718.8
145°	691.2	705.0	727.8	744.0	753.5	756.3	753.5	744.0	727.8	705.0	691.2
147.5°	667.0	677.5	697.4	710.7	717.4	719.3	717.4	710.7	697.4	677.5	667.0
150°	646.2	654.7	668.9	680.3	686.0	687.0	686.0	680.3	668.9	654.7	646.2
152.5°	628.6	635.7	646.1	655.6	659.4	659.4	659.4	655.6	646.1	635.7	628.6
155°	611.4	616.7	627.1	633.8	637.6	635.7	637.6	633.8	627.1	616.7	611.4
157.5°	595.3	599.6	607.2	612.9	614.8	614.8	614.8	612.9	607.2	599.6	595.3
160°	579.2	582.5	589.1	593.9	594.8	594.8	594.8	593.9	589.1	582.5	579.2
162.5°	563.9	566.3	572.9	575.8	576.7	575.8	576.7	575.8	572.9	566.3	563.9
165°	549.2	551.1	554.9	558.7	558.7	557.7	558.7	558.7	554.9	551.1	549.2
167.5°	535.9	537.8	539.7	541.6	541.6	540.6	541.6	541.6	539.7	537.8	535.9
170°	523.6	524.5	525.4	528.3	527.3	525.4	527.3	528.3	525.4	524.5	523.6
172.5°	512.6	513.1	514.0	515.0	514.0	513.1	514.0	515.0	514.0	513.1	512.6
175°	504.0	504.5	504.5	505.5	504.5	502.6	504.5	505.5	504.5	504.5	504.0
177.5°	497.9	497.9	497.9	497.9	496.9	495.0	496.9	497.9	497.9	497.9	497.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	525.3	528.7	527.5	522.8	528.3	528.3	532.1	532.1	536.8	538.5	541.1
5°	495.6	498.1	500.2	498.1	501.9	507.9	511.3	514.3	520.7	523.2	527.0
7.5°	463.7	468.3	470.5	470.5	476.8	483.7	490.5	494.7	503.6	507.0	510.9
10°	432.6	438.1	442.4	442.0	452.6	456.9	465.4	475.1	484.1	489.2	494.7
12.5°	399.9	402.8	408.8	417.3	419.8	427.5	437.3	449.6	465.8	470.5	478.5
15°	372.6	380.7	385.4	389.2	395.2	402.4	413.0	425.0	441.1	451.3	459.8
17.5°	349.7	360.3	363.3	362.4	370.1	381.1	393.5	402.4	416.9	429.2	437.3
20°	330.9	335.2	340.3	342.4	348.4	360.3	372.2	382.4	394.3	404.1	413.5
22.5°	312.2	315.6	319.9	323.7	328.4	335.2	346.7	359.4	370.9	380.3	390.9
25°	296.9	299.0	302.9	305.8	310.9	315.6	323.7	337.7	351.4	356.9	366.2
27.5°	282.0	283.7	286.3	289.7	292.2	296.9	304.1	315.6	329.7	335.2	348.0
30°	268.8	270.1	272.7	274.4	275.6	281.2	286.7	295.6	306.3	313.9	323.3
32.5°	256.5	257.8	260.3	260.8	262.5	265.4	270.5	278.6	288.0	294.4	302.4
35°	242.9	243.7	246.3	247.1	248.4	251.0	254.8	260.8	269.3	273.9	281.2
37.5°	232.3	231.8	233.5	234.8	236.5	237.8	239.1	245.0	251.4	255.7	261.2
40°	220.8	219.9	220.3	222.0	222.9	224.6	224.6	230.6	234.8	238.2	242.5
42.5°	209.3	208.9	208.0	208.9	209.7	210.1	210.6	214.8	219.1	222.0	226.7
45°	197.8	197.4	196.5	196.9	196.9	197.8	199.1	200.8	203.8	206.3	208.9
47.5°	187.2	186.3	185.0	184.6	185.5	185.5	185.5	187.2	190.1	191.0	193.5
50°	176.1	174.8	173.1	172.3	172.3	171.9	172.7	173.1	175.7	176.5	178.7
52.5°	164.2	163.3	161.6	159.9	160.4	159.5	159.9	160.4	161.2	162.5	163.8
55°	152.3	150.6	149.3	148.9	147.6	147.6	146.3	148.0	147.6	148.0	149.7
57.5°	140.8	139.1	137.0	136.1	134.8	134.4	133.6	133.1	133.6	134.8	136.1
60°	127.2	126.3	125.1	123.8	122.9	121.7	120.8	120.8	120.4	120.4	120.8
62.5°	114.0	113.6	111.9	111.4	110.6	109.7	108.5	107.6	107.6	108.5	108.9
65°	101.2	100.8	99.5	99.1	97.0	96.1	95.7	95.3	94.4	94.4	94.4
67.5°	89.3	88.1	88.1	85.9	84.2	83.4	82.5	82.1	82.1	82.1	82.5
70°	76.1	76.1	74.9	73.6	71.9	72.3	71.0	69.8	69.8	68.9	69.3
72.5°	63.4	63.0	61.7	61.3	60.0	58.7	57.9	58.7	57.4	57.0	57.4
75°	51.0	50.6	49.8	48.9	49.3	48.1	46.8	46.4	46.4	45.5	45.5
77.5°	39.1	40.0	38.3	37.9	37.0	36.2	35.7	35.3	35.3	35.3	36.2
80°	27.2	27.6	27.6	26.8	27.2	25.9	25.9	25.9	24.7	25.1	25.5
82.5°	17.4	17.4	17.0	17.4	17.0	17.0	16.6	16.6	16.2	16.2	16.6
85°	9.8	9.4	8.9	9.8	9.4	9.4	8.9	8.9	8.9	8.9	8.9
87.5°	2.1	2.6	2.6	2.6	2.6	3.0	3.0	3.0	3.4	3.4	3.4
90°	30.4	28.5	30.4	31.4	32.3	31.4	25.7	19.0	14.3	12.8	11.4
92.5°	71.3	81.7	96.0	122.6	146.3	144.4	112.1	76.0	50.4	45.2	39.9
95°	151.1	191.0	248.9	325.9	372.5	329.7	219.5	136.8	93.1	81.7	70.3
97.5°	310.7	406.7	509.3	611.9	607.2	469.4	291.7	176.7	120.7	107.8	95.0
100°	619.5	749.7	867.5	887.5	750.6	516.9	311.7	195.7	145.4	132.1	118.8
102.5°	1011.9	1098.4	1102.2	990.1	755.4	498.8	312.6	212.8	167.2	153.9	140.6
105°	1274.2	1261.8	1154.4	956.8	704.1	474.1	317.4	232.8	188.1	174.8	161.5
107.5°	1351.1	1258.0	1098.4	886.5	656.6	460.8	327.8	252.7	209.0	195.7	182.4
110°	1313.1	1191.5	1021.4	820.9	624.3	457.0	341.1	272.7	230.9	217.1	203.3

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1244.7	1112.6	951.1	775.3	603.4	458.0	355.4	291.7	251.8	237.6	223.3
115°	1166.8	1042.3	896.0	739.2	589.1	461.8	369.6	311.7	270.8	258.0	245.1
117.5°	1097.4	981.5	850.4	714.5	581.5	467.5	384.8	329.7	291.7	278.4	265.1
120°	1036.6	935.9	818.1	695.5	574.8	473.2	400.0	348.7	311.7	298.4	285.0
122.5°	992.0	897.9	792.4	679.4	571.0	479.8	413.3	366.8	332.6	318.8	305.0
125°	949.2	865.6	767.7	664.2	566.3	486.5	427.6	384.8	350.6	337.3	324.0
127.5°	913.1	833.3	743.0	649.9	563.4	493.1	440.9	401.9	368.7	354.9	341.1
130°	876.1	801.0	719.3	635.7	561.5	500.7	453.2	417.1	383.9	370.6	357.3
132.5°	838.0	770.6	696.5	624.3	560.6	508.3	465.6	430.4	399.1	385.8	372.5
135°	801.0	738.3	675.6	613.8	559.6	514.0	476.0	442.8	412.4	399.1	385.8
137.5°	763.9	712.6	658.5	606.2	559.6	519.7	484.6	453.2	422.8	410.4	398.1
140°	731.6	687.9	642.3	599.6	558.7	523.5	491.2	461.8	433.3	421.0	408.6
142.5°	702.2	666.1	629.0	592.9	558.7	526.4	496.9	468.4	440.9	429.5	418.1
145°	677.5	648.0	616.7	587.2	556.8	528.3	501.7	475.1	449.4	439.0	428.5
147.5°	656.6	632.8	607.2	581.5	553.9	529.2	504.5	480.8	456.1	446.6	437.1
150°	637.6	617.6	596.7	573.9	551.1	528.3	506.4	484.6	462.7	454.2	445.6
152.5°	621.4	605.3	586.3	567.2	546.3	526.4	507.4	488.4	469.4	461.8	454.2
155°	606.2	592.0	576.7	558.7	540.6	524.5	508.3	492.2	476.0	468.9	461.8
157.5°	591.0	578.7	565.3	551.1	534.9	520.7	508.3	495.0	480.8	474.6	468.4
160°	575.8	565.3	554.9	542.5	529.2	517.8	508.3	496.9	485.5	480.3	475.1
162.5°	561.5	553.0	544.4	534.9	524.5	515.0	507.4	497.9	488.4	484.6	480.8
165°	547.3	540.6	534.0	526.4	517.8	511.2	505.5	498.8	490.3	487.4	484.6
167.5°	534.0	529.2	523.5	517.8	512.1	507.4	504.5	498.8	492.2	490.3	488.4
170°	522.6	518.8	515.9	511.2	507.4	504.5	502.6	497.9	493.1	491.7	490.3
172.5°	512.1	509.3	507.4	504.5	501.7	500.7	499.8	496.9	494.1	493.2	492.2
175°	503.6	502.6	501.7	498.8	497.9	496.9	497.9	496.0	494.1	493.6	493.1
177.5°	497.9	496.9	496.9	495.0	494.1	495.0	496.9	495.0	494.1	494.1	494.1
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	553.4	553.4	553.4	553.4
2.5°	543.2	543.2	549.6	556.4
5°	531.3	534.3	544.5	553.8
7.5°	519.8	524.9	537.7	549.6
10°	505.8	512.6	528.3	542.4
12.5°	492.2	498.5	516.8	532.6
15°	473.0	481.1	500.7	520.2
17.5°	453.9	462.0	485.8	508.7
20°	431.3	442.0	468.8	499.4
22.5°	410.5	423.7	453.5	478.1
25°	387.5	407.9	435.6	467.5
27.5°	367.1	387.5	415.6	447.9
30°	344.1	365.0	393.9	423.7
32.5°	322.0	341.2	369.2	405.8
35°	299.0	317.3	344.6	381.6
37.5°	278.2	296.1	325.8	359.9
40°	257.8	276.5	302.0	336.0
42.5°	238.6	255.2	278.2	312.2
45°	221.2	233.1	254.4	286.3
47.5°	202.9	213.5	233.1	265.0
50°	185.9	194.8	211.8	241.6
52.5°	169.3	177.0	192.7	216.5
55°	154.4	161.6	173.1	196.5
57.5°	139.1	144.6	155.7	174.4
60°	124.2	129.3	138.2	153.6
62.5°	109.3	113.6	122.1	134.4
65°	96.1	99.5	105.9	116.6
67.5°	83.4	85.5	90.6	99.1
70°	71.0	72.7	77.0	83.8
72.5°	57.9	59.6	64.2	68.9
75°	46.8	47.2	50.6	54.4
77.5°	36.6	36.2	38.7	41.7
80°	25.1	26.4	28.5	29.8
82.5°	17.0	17.4	18.3	19.1
85°	9.4	9.8	9.8	11.1
87.5°	3.8	4.3	4.3	4.7
90°	9.5	7.6	3.8	1.0
92.5°	32.3	27.6	20.0	14.3
95°	55.1	46.6	37.1	33.3
97.5°	77.9	65.6	55.1	49.4
100°	99.8	84.6	76.0	73.2
102.5°	120.7	105.5	96.9	95.0
105°	140.6	126.4	119.7	115.9
107.5°	161.5	148.2	141.6	138.7
110°	183.4	171.0	165.3	161.5

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	204.3	192.9	186.2	182.4
115°	226.1	214.7	209.0	204.3
117.5°	247.0	236.6	230.9	227.1
120°	266.0	257.5	251.8	248.0
122.5°	286.0	276.5	270.8	267.9
125°	305.0	293.6	287.9	285.0
127.5°	323.1	310.7	303.1	299.3
130°	338.3	325.0	315.5	311.7
132.5°	352.5	338.3	327.8	323.1
135°	363.9	349.7	338.3	334.5
137.5°	376.3	361.1	349.7	344.9
140°	387.7	372.5	361.1	357.3
142.5°	398.1	382.9	372.5	369.6
145°	409.5	395.3	385.8	382.0
147.5°	420.9	407.6	398.1	395.3
150°	431.4	419.0	411.4	408.6
152.5°	440.9	430.4	422.8	421.9
155°	451.3	440.9	435.2	434.2
157.5°	459.9	450.4	445.6	444.7
160°	467.5	459.9	456.1	455.1
162.5°	474.1	468.4	464.6	465.6
165°	479.8	474.1	472.2	473.2
167.5°	484.6	480.8	478.9	479.8
170°	488.4	485.5	484.6	486.5
172.5°	491.2	488.4	489.3	490.3
175°	493.1	491.2	492.2	493.1
177.5°	494.1	492.2	493.1	495.0
180°	494.1	494.1	494.1	494.1

TEST NUMBER: P998371

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.60	11.27	11.75	12.40	13.97	8.10	8.76	9.24	9.89	11.47
	3H	11.40	12.00	12.55	13.13	14.72	9.43	10.02	10.58	11.16	12.75
	4H	11.56	12.13	12.72	13.26	14.86	9.88	10.45	11.04	11.58	13.18
	6H	11.59	12.12	12.76	13.26	14.86	10.18	10.70	11.34	11.84	13.44
	8H	11.57	12.06	12.74	13.22	14.82	10.25	10.75	11.42	11.90	13.50
	12H	11.52	11.99	12.70	13.14	14.76	10.29	10.76	11.46	11.91	13.53
4H	2H	10.62	11.19	11.79	12.32	13.92	8.52	9.08	9.68	10.22	11.82
	3H	11.58	12.06	12.75	13.22	14.83	9.96	10.43	11.13	11.60	13.20
	4H	11.85	12.29	13.03	13.44	15.07	10.49	10.92	11.66	12.07	13.70
	6H	11.97	12.34	13.15	13.52	15.13	10.86	11.23	12.03	12.40	14.02
	8H	11.97	12.31	13.14	13.48	15.11	10.96	11.31	12.14	12.48	14.11
	12H	11.92	12.24	13.11	13.41	15.05	11.01	11.33	12.20	12.50	14.14
8H	4H	11.85	12.19	13.02	13.36	14.99	10.62	10.96	11.79	12.13	13.76
	6H	12.02	12.30	13.21	13.51	15.14	11.04	11.33	12.24	12.54	14.17
	8H	12.05	12.30	13.25	13.48	15.13	11.19	11.44	12.39	12.63	14.28
	12H	12.02	12.24	13.23	13.42	15.11	11.28	11.49	12.48	12.68	14.36
12H	4H	11.80	12.11	12.99	13.29	14.92	10.58	10.90	11.77	12.07	13.71
	6H	12.00	12.25	13.20	13.43	15.08	11.04	11.29	12.24	12.48	14.13
	8H	12.02	12.24	13.22	13.42	15.10	11.19	11.41	12.40	12.59	14.28