

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998380

Luminaire Tested: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998380
REPORT IS A COMBINATION OF REPORTS P984120 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6289.0 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	87	83	85	82	79	76	65	63	61	51	49	48	37	36	35
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	31	30
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	20	18
7	57	45	37	32	51	41	34	30	33	29	25	27	23	20	20	18	16
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15188	15188	15188	15188
5°	15226	16194	15283	12885
10°	15048	17679	15142	10622
15°	14683	18647	14887	8948
20°	14455	17508	14455	7777
25°	13993	15041	14057	6954
30°	13236	11824	13488	6300
35°	12565	8176	12774	5763
40°	11791	6173	11927	5336
45°	10841	5073	11018	4875
50°	10017	4452	10037	4463
55°	9078	3794	9140	4015
60°	8078	3169	8190	3505
65°	7185	2577	7316	2993
70°	6293	2022	6453	2413
75°	5281	1468	5488	1751
80°	4120	931	4415	1039
85°	2712	468	2924	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15700 cd/sqm

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.5
10°-20°	266.0	4.2
20°-30°	386.1	6.1
30°-40°	407.0	6.5
40°-50°	360.1	5.7
50°-60°	287.6	4.6
60°-70°	195.3	3.1
70°-80°	99.9	1.6
80°-90°	27.5	0.4
90°-100°	233.3	3.7
100°-110°	821.7	13.1
110°-120°	863.0	13.7
120°-130°	709.9	11.3
130°-140°	570.3	9.1
140°-150°	430.8	6.9
150°-160°	302.9	4.8
160°-170°	178.3	2.8
170°-180°	58.0	0.9
0°-30°	743.5	11.8
0°-40°	1150.4	18.3
0°-60°	1798.1	28.6
0°-90°	2120.9	33.7
90°-120°	1918.0	30.5
90°-150°	3629.0	57.7
90°-180°	4168.0	66.3
0°-180°	6289.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	960	960	960	960	960	
5°	960	1072	964	853	960	91
15°	902	1317	914	632	902	255
25°	810	1097	814	507	810	371
35°	662	597	673	421	662	414
45°	496	360	504	346	496	385
55°	341	253	343	268	341	304
65°	202	156	206	181	202	201
75°	94	77	98	92	94	101
85°	19	20	21	15	19	22
90°	1	38	1	38	1	4
95°	40	131	40	131	40	42
105°	140	1297	140	1297	140	149
115°	248	1707	248	1707	248	245
125°	345	1385	345	1385	345	307
135°	405	1148	405	1148	405	313
145°	463	916	463	916	463	290
155°	526	770	526	770	526	242
165°	573	676	573	676	573	162
175°	597	609	597	609	597	57
180°	598	598	598	598	598	

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	964.7	966.9	970.6	971.3	978.7	984.6	991.2	991.2	993.4	992.7	986.8
5°	960.3	966.9	976.5	984.6	997.9	1003.8	1012.6	1019.3	1025.2	1029.6	1028.9
7.5°	952.9	964.7	978.7	994.2	1011.9	1022.2	1034.8	1046.6	1054.7	1062.0	1067.2
10°	940.3	960.3	979.4	1000.1	1023.0	1037.0	1051.7	1067.2	1079.7	1093.8	1107.0
12.5°	923.4	952.1	975.7	1003.0	1031.1	1046.6	1070.2	1082.0	1106.3	1141.7	1151.3
15°	902.0	941.1	963.2	997.9	1034.8	1047.3	1079.7	1098.9	1149.1	1171.2	1197.7
17.5°	882.1	925.6	955.1	994.9	1031.1	1055.4	1087.1	1126.2	1168.2	1200.0	1229.5
20°	865.9	907.9	943.3	987.5	1033.3	1064.3	1097.4	1144.6	1190.4	1222.8	1245.7
22.5°	829.0	882.8	924.1	973.5	1028.9	1071.6	1103.3	1155.0	1204.4	1224.3	1244.2
25°	810.5	857.0	904.9	961.0	1025.9	1076.8	1104.1	1161.6	1205.1	1212.5	1216.9
27.5°	776.6	829.0	885.0	949.2	1025.2	1067.9	1102.6	1155.0	1189.6	1184.5	1171.2
30°	734.6	798.7	860.7	930.0	1014.8	1061.3	1093.8	1141.7	1159.4	1132.8	1109.2
32.5°	703.6	764.1	832.7	913.1	1003.0	1047.3	1079.0	1116.6	1120.3	1072.4	1032.5
35°	661.6	728.7	806.1	890.9	983.1	1023.0	1052.5	1075.3	1057.6	990.5	943.3
37.5°	623.9	690.3	772.9	859.2	955.8	994.9	1018.5	1022.2	978.7	919.7	850.4
40°	582.6	651.2	737.5	828.2	925.6	959.5	974.3	963.2	900.5	831.9	751.5
42.5°	541.3	609.2	702.1	795.1	887.2	916.0	921.9	891.7	815.0	734.6	641.6
45°	496.4	567.2	660.1	753.8	843.0	859.2	860.0	816.4	725.7	641.6	555.4
47.5°	459.5	525.1	617.3	711.0	786.2	797.3	792.8	742.7	643.9	549.5	474.2
50°	418.9	481.6	573.1	665.2	729.4	732.4	721.3	649.8	553.1	466.9	407.1
52.5°	375.4	438.8	522.9	611.4	668.9	664.5	643.1	566.4	475.7	404.2	358.4
55°	340.7	396.8	475.7	562.0	602.6	590.0	566.4	488.2	416.7	356.2	316.4
57.5°	302.4	351.8	429.2	504.5	528.1	516.3	492.7	419.7	353.3	307.5	281.0
60°	266.2	311.2	379.1	441.8	460.2	447.7	420.4	354.8	306.8	268.5	248.5
62.5°	233.1	272.1	328.9	386.5	393.8	381.3	357.7	304.6	263.3	233.1	218.3
65°	202.1	239.0	284.7	328.2	334.8	321.6	297.2	258.9	224.2	205.0	191.0
67.5°	171.8	201.3	241.9	273.6	277.3	264.8	244.9	213.9	192.5	171.8	161.5
70°	145.3	167.4	199.1	224.9	226.4	214.6	204.3	176.3	160.0	145.3	137.2
72.5°	119.5	135.0	159.3	178.5	179.2	171.8	162.3	144.6	130.5	120.2	112.1
75°	94.4	107.7	122.4	139.4	138.7	132.8	125.4	114.3	102.5	95.9	92.2
77.5°	72.3	80.4	92.2	103.3	103.3	100.3	95.9	87.8	80.4	73.8	70.1
80°	51.6	56.8	66.4	70.1	71.5	70.8	67.1	61.2	58.3	53.1	51.6
82.5°	33.2	36.9	41.3	45.0	47.2	45.7	45.0	42.0	37.6	36.1	34.7
85°	19.2	20.7	22.9	25.1	25.8	25.1	26.6	24.3	22.1	22.1	21.4
87.5°	8.1	8.9	10.3	10.3	11.1	11.1	10.3	11.1	11.1	10.3	9.6
90°	1.2	4.6	9.2	11.5	13.8	15.6	17.3	23.0	31.1	38.0	39.1
92.5°	17.3	24.2	33.4	39.1	48.3	54.6	61.0	92.1	135.8	175.0	177.3
95°	40.3	44.9	56.4	66.8	85.2	99.0	112.8	165.7	265.9	399.4	451.2
97.5°	59.9	66.8	79.4	94.4	115.1	130.6	146.2	214.1	353.4	568.6	735.5
100°	88.6	92.1	102.4	120.9	143.9	160.0	176.1	237.1	377.5	626.2	909.3
102.5°	115.1	117.4	127.8	146.2	170.3	186.4	202.6	257.8	378.7	604.3	915.1
105°	140.4	145.0	153.1	170.3	195.7	211.8	227.9	282.0	384.4	574.4	852.9
107.5°	168.0	171.5	179.6	195.7	221.0	237.1	253.2	306.2	397.1	558.2	795.3
110°	195.7	200.3	207.2	222.1	246.3	263.0	279.7	330.3	413.2	553.6	756.2

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	221.0	225.6	233.7	247.5	270.5	287.8	305.0	353.4	430.5	554.8	730.9
115°	247.5	253.2	260.1	273.9	297.0	312.5	328.0	377.5	447.7	559.4	713.6
117.5°	275.1	279.7	286.6	299.3	321.1	337.2	353.4	399.4	466.2	566.3	704.4
120°	300.4	305.0	311.9	322.3	345.3	361.4	377.5	422.4	484.6	573.2	696.4
122.5°	324.6	328.0	334.9	346.5	369.5	386.2	402.9	444.3	500.7	581.3	691.8
125°	345.3	348.8	355.7	369.5	392.5	408.6	424.7	466.2	518.0	589.3	686.0
127.5°	362.6	367.2	376.4	391.3	413.2	429.9	446.6	486.9	534.1	597.4	682.6
130°	377.5	382.1	393.6	409.8	432.8	448.9	465.0	505.3	549.0	606.6	680.2
132.5°	391.3	397.1	409.8	427.0	451.2	467.3	483.4	521.4	564.0	615.8	679.1
135°	405.2	409.8	423.6	440.8	467.3	483.4	499.5	536.4	576.7	622.7	677.9
137.5°	417.8	423.6	437.4	455.8	482.3	497.2	512.2	549.0	587.0	629.6	677.9
140°	432.8	437.4	451.2	469.6	494.9	509.9	524.9	559.4	595.1	634.2	676.8
142.5°	447.7	451.2	463.9	482.3	506.4	520.2	534.1	567.4	602.0	637.7	676.8
145°	462.7	467.3	478.8	496.1	519.1	531.8	544.4	575.5	607.7	640.0	674.5
147.5°	478.8	482.3	493.8	509.9	529.5	541.0	552.5	582.4	611.2	641.1	671.0
150°	494.9	498.4	507.6	522.6	539.8	550.2	560.5	587.0	613.5	640.0	667.6
152.5°	511.0	512.2	521.4	534.1	550.2	559.4	568.6	591.6	614.6	637.7	661.8
155°	526.0	527.2	534.1	546.7	559.4	568.0	576.7	596.2	615.8	635.4	654.9
157.5°	538.7	539.8	545.6	557.1	567.4	574.9	582.4	599.7	615.8	630.8	648.0
160°	551.3	552.5	557.1	566.3	575.5	581.8	588.2	602.0	615.8	627.3	641.1
162.5°	564.0	562.8	567.4	574.4	582.4	587.0	591.6	603.1	614.6	623.8	635.4
165°	573.2	572.1	574.4	581.3	587.0	590.4	593.9	604.3	612.3	619.2	627.3
167.5°	581.3	580.1	582.4	587.0	591.6	593.9	596.2	604.3	611.2	614.6	620.4
170°	589.3	587.0	588.2	591.6	593.9	595.6	597.4	603.1	608.9	611.2	614.6
172.5°	593.9	592.8	591.6	595.1	596.2	597.4	598.5	602.0	605.4	606.6	607.7
175°	597.4	596.2	595.1	597.4	597.4	598.0	598.5	600.8	603.1	602.0	603.1
177.5°	599.7	597.4	596.2	598.5	598.5	598.5	598.5	599.7	602.0	599.7	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	997.1	997.9	999.3	1006.7	1010.4	1011.1	1008.2	1014.8	1017.1	1014.8	1013.4
5°	1044.3	1048.8	1057.6	1067.2	1066.5	1067.2	1071.6	1076.1	1077.5	1071.6	1073.8
7.5°	1085.6	1094.5	1104.1	1118.8	1118.8	1126.2	1129.2	1132.8	1141.7	1137.3	1135.8
10°	1132.8	1144.6	1162.3	1185.9	1186.7	1194.1	1201.4	1213.2	1216.9	1214.0	1215.4
12.5°	1191.8	1214.7	1216.2	1242.0	1253.8	1255.3	1267.1	1264.9	1272.2	1272.2	1284.8
15°	1217.7	1253.1	1273.0	1298.0	1305.4	1296.6	1306.2	1316.5	1317.2	1317.2	1316.5
17.5°	1264.1	1278.1	1298.0	1311.3	1314.3	1314.3	1315.0	1319.4	1316.5	1310.6	1315.0
20°	1273.7	1279.6	1287.0	1285.5	1287.0	1279.6	1272.2	1264.9	1265.6	1261.9	1273.0
22.5°	1256.0	1254.5	1237.6	1226.5	1226.5	1211.8	1197.7	1191.1	1184.5	1186.7	1190.4
25°	1211.8	1188.9	1168.2	1152.0	1148.3	1124.7	1105.6	1099.7	1088.6	1097.4	1098.9
27.5°	1141.0	1115.1	1082.0	1067.9	1048.8	1039.2	1025.9	1008.2	985.3	998.6	996.4
30°	1065.0	1026.6	999.3	965.4	935.2	933.0	907.9	878.4	866.6	866.6	873.2
32.5°	980.2	929.3	889.5	841.5	812.0	799.5	769.2	739.7	746.4	724.3	732.4
35°	881.3	814.2	764.1	717.6	695.5	680.7	641.6	625.4	607.7	597.4	616.6
37.5°	786.9	709.5	645.3	594.4	586.3	559.8	533.2	522.9	512.6	517.0	516.3
40°	671.9	603.3	545.8	505.9	491.9	479.4	461.7	449.2	442.5	446.2	446.9
42.5°	567.9	510.4	467.6	439.6	427.8	418.9	410.1	399.7	397.5	397.5	400.5
45°	487.5	440.3	411.5	388.7	382.0	375.4	368.8	364.3	362.9	359.9	362.1
47.5°	423.3	385.7	368.0	351.1	343.7	342.2	336.3	334.1	331.1	330.4	331.1
50°	369.5	345.9	329.7	320.1	314.9	312.7	309.8	305.3	303.9	307.5	306.1
52.5°	331.9	309.8	300.9	291.3	288.4	285.4	281.0	281.7	281.0	279.5	279.5
55°	294.3	280.3	271.4	264.0	263.3	260.3	256.7	255.2	254.4	253.0	255.2
57.5°	264.0	253.0	244.9	238.2	235.3	235.3	231.6	228.6	228.6	227.9	228.6
60°	233.8	222.7	217.6	210.9	208.7	208.0	205.8	204.3	202.1	202.1	202.1
62.5°	205.8	196.9	191.0	185.1	185.9	182.2	179.2	177.7	177.7	178.5	178.5
65°	179.2	173.3	165.9	160.8	159.3	158.6	157.1	156.4	154.1	155.6	155.6
67.5°	154.9	146.8	142.3	140.1	137.9	137.2	135.7	134.2	133.5	132.8	134.2
70°	130.5	123.9	120.2	118.7	116.5	115.8	115.1	112.8	113.6	114.3	115.1
72.5°	108.4	102.5	101.8	97.4	97.4	97.4	94.4	95.9	95.1	93.7	95.1
75°	85.6	82.6	81.1	78.9	79.7	78.9	78.2	76.0	76.0	76.7	77.4
77.5°	67.9	64.9	64.2	62.0	60.5	62.0	60.5	59.7	59.7	60.5	60.5
80°	50.2	48.7	46.5	46.5	46.5	45.7	45.7	45.7	45.0	44.3	45.0
82.5°	33.2	33.2	32.5	31.7	32.5	31.0	31.7	31.7	31.7	31.7	31.7
85°	21.4	20.7	20.7	19.9	19.9	19.9	20.7	19.2	19.2	19.9	19.9
87.5°	9.6	9.6	9.6	10.3	9.6	9.6	9.6	10.3	9.6	9.6	9.6
90°	38.0	36.8	34.5	36.8	37.4	38.0	38.0	38.0	38.0	38.0	38.0
92.5°	148.5	116.3	99.0	86.3	81.7	77.1	76.0	71.4	72.5	70.2	72.5
95°	394.8	301.6	231.4	183.0	170.4	157.7	142.7	133.5	130.1	131.2	130.1
97.5°	741.3	616.9	492.6	376.4	341.8	307.3	262.4	239.4	226.7	219.8	226.7
100°	1075.0	1050.9	908.1	750.5	680.8	611.2	515.7	466.2	432.8	412.1	432.8
102.5°	1199.4	1335.2	1330.6	1225.8	1151.0	1076.2	970.3	877.1	833.3	803.4	833.3
105°	1159.1	1398.5	1528.5	1543.5	1524.5	1505.5	1434.2	1362.8	1313.3	1297.2	1313.3
107.5°	1073.9	1330.6	1523.9	1636.7	1659.8	1682.8	1681.6	1671.3	1656.3	1629.8	1656.3
110°	994.5	1237.3	1443.4	1590.7	1637.9	1685.1	1734.6	1756.4	1766.8	1765.7	1766.8

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	939.2	1152.2	1347.8	1507.8	1563.6	1619.5	1693.1	1733.4	1755.3	1763.4	1755.3
115°	895.5	1085.4	1262.7	1413.4	1472.7	1532.0	1613.7	1666.7	1696.6	1707.0	1696.6
117.5°	865.6	1030.2	1189.0	1329.4	1385.8	1442.2	1526.2	1582.6	1613.7	1621.8	1613.7
120°	842.5	991.0	1133.7	1255.8	1308.2	1360.5	1441.1	1495.2	1528.5	1540.1	1528.5
122.5°	823.0	959.9	1087.7	1201.7	1247.7	1293.7	1363.9	1416.9	1445.7	1454.9	1445.7
125°	804.6	930.0	1048.6	1149.9	1193.1	1236.2	1302.9	1346.7	1375.5	1384.7	1375.5
127.5°	787.3	900.1	1009.4	1106.1	1146.4	1186.7	1245.4	1286.8	1312.2	1319.1	1312.2
130°	770.0	871.3	970.3	1061.2	1099.2	1137.2	1193.6	1232.7	1255.8	1265.0	1255.8
132.5°	756.2	843.7	933.5	1015.2	1050.3	1085.4	1140.7	1179.8	1200.5	1208.6	1200.5
135°	743.6	818.4	894.3	970.3	1002.6	1034.8	1084.3	1122.2	1143.0	1147.6	1143.0
137.5°	734.3	797.7	863.3	925.4	954.2	983.0	1030.2	1063.5	1082.0	1088.9	1082.0
140°	726.3	778.1	833.3	886.3	911.6	936.9	973.8	1003.7	1020.9	1027.9	1020.9
142.5°	718.2	762.0	806.9	850.6	870.8	890.9	925.4	951.9	966.9	966.9	966.9
145°	711.3	747.0	785.0	820.7	837.4	854.1	881.7	901.2	912.8	916.2	912.8
147.5°	704.4	735.5	766.6	795.3	808.0	820.7	844.8	861.0	869.0	871.3	869.0
150°	695.2	722.8	748.2	772.3	782.6	793.0	810.3	824.1	831.0	832.2	831.0
152.5°	687.2	710.2	733.2	752.8	761.4	770.0	782.7	794.2	798.8	798.8	798.8
155°	676.8	698.7	717.1	734.3	740.6	747.0	759.7	767.7	772.3	770.0	772.3
157.5°	667.6	684.9	701.0	715.9	721.1	726.3	735.5	742.4	744.7	744.7	744.7
160°	657.2	672.2	684.9	697.5	701.6	705.6	713.6	719.4	720.5	720.5	720.5
162.5°	648.0	659.5	669.9	680.2	683.1	686.0	694.1	697.5	698.7	697.5	698.7
165°	637.7	646.9	654.9	663.0	665.3	667.6	672.2	676.8	676.8	675.6	676.8
167.5°	627.3	634.2	641.1	646.9	649.2	651.5	653.8	656.1	656.1	654.9	656.1
170°	619.2	625.0	628.5	633.1	634.2	635.4	636.5	640.0	638.8	636.5	638.8
172.5°	611.2	614.6	616.9	620.4	621.0	621.5	622.7	623.8	622.7	621.5	622.7
175°	604.3	607.7	608.9	610.0	610.6	611.2	611.2	612.3	611.2	608.9	611.2
177.5°	599.7	602.0	602.0	603.1	603.1	603.1	603.1	603.1	602.0	599.7	602.0
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	1017.1	1011.9	1007.5	1008.2	1011.9	1008.9	1001.6	992.0	988.3	983.9	988.3
5°	1078.3	1073.8	1065.0	1065.7	1063.5	1060.6	1048.8	1034.0	1034.0	1022.2	1020.7
7.5°	1138.7	1132.1	1126.2	1124.7	1116.6	1110.7	1100.4	1079.7	1071.6	1057.6	1049.5
10°	1206.6	1201.4	1194.8	1186.7	1182.3	1171.9	1155.0	1124.7	1110.0	1090.8	1076.8
12.5°	1275.2	1274.4	1259.7	1243.5	1242.7	1226.5	1214.7	1174.1	1154.2	1128.4	1095.2
15°	1318.7	1315.0	1306.9	1298.8	1301.0	1283.3	1256.7	1208.8	1195.5	1164.6	1129.2
17.5°	1318.0	1318.0	1315.7	1314.3	1312.1	1306.9	1292.1	1260.4	1239.0	1200.0	1166.8
20°	1275.9	1285.5	1287.7	1287.0	1294.4	1298.0	1297.3	1277.4	1260.4	1225.8	1191.8
22.5°	1191.8	1214.0	1223.6	1229.5	1244.9	1253.1	1272.2	1264.9	1260.4	1234.6	1205.9
25°	1113.7	1121.0	1149.8	1151.3	1172.7	1192.6	1211.8	1224.3	1240.5	1230.9	1206.6
27.5°	1012.6	1029.6	1050.2	1065.7	1070.2	1110.7	1142.4	1166.0	1202.9	1205.9	1197.7
30°	898.3	906.4	940.3	961.0	984.6	1014.1	1059.8	1100.4	1133.6	1163.8	1174.1
32.5°	758.9	792.1	812.0	837.1	857.7	910.1	966.2	1018.5	1056.9	1107.8	1129.9
35°	631.3	657.1	691.1	701.4	739.0	783.3	856.3	923.4	981.6	1033.3	1078.3
37.5°	525.9	546.5	582.6	598.9	621.0	677.8	739.0	822.3	892.4	955.8	1011.9
40°	453.6	469.1	496.4	501.5	520.0	571.6	621.0	699.2	792.1	877.7	938.9
42.5°	404.2	411.5	430.0	436.6	448.4	483.1	527.3	601.1	687.4	775.9	862.2
45°	368.8	373.9	385.0	390.9	405.6	421.1	457.3	516.3	584.1	673.4	766.3
47.5°	337.0	343.7	348.1	351.8	359.9	376.9	400.5	444.0	508.9	590.8	680.7
50°	310.5	312.7	320.8	321.6	326.7	337.8	359.9	386.5	438.1	504.5	591.5
52.5°	283.9	286.2	291.3	296.5	298.7	307.5	322.3	344.4	382.8	435.1	512.6
55°	257.4	260.3	265.5	269.2	271.4	278.8	287.6	309.0	339.3	376.1	439.6
57.5°	230.8	237.5	239.0	241.2	244.9	253.0	261.1	273.6	297.2	331.1	377.6
60°	205.8	208.0	213.1	215.4	219.0	223.5	233.8	243.4	260.3	286.9	328.9
62.5°	180.0	185.1	187.3	189.5	192.5	197.7	204.3	214.6	229.4	250.8	283.9
65°	157.8	158.6	163.0	165.9	168.9	172.6	179.2	188.8	197.7	217.6	241.9
67.5°	136.4	137.9	139.4	142.3	146.0	149.7	155.6	160.8	171.8	185.1	204.3
70°	115.8	115.8	119.5	121.7	121.0	125.4	129.8	135.7	143.8	156.4	171.8
72.5°	97.4	96.6	99.6	100.3	101.8	104.7	107.7	113.6	118.0	127.6	139.4
75°	77.4	78.9	80.4	80.4	82.6	84.8	87.8	90.7	95.9	101.8	110.6
77.5°	61.2	61.2	62.7	63.4	65.6	64.9	67.9	70.8	74.5	79.7	86.3
80°	45.0	46.5	46.5	46.5	47.2	47.9	50.9	53.1	55.3	59.0	62.0
82.5°	31.7	31.7	33.2	33.2	33.2	34.7	34.7	35.4	36.9	39.1	41.3
85°	19.9	19.9	19.9	20.7	19.9	20.7	22.1	21.4	22.1	23.6	23.6
87.5°	9.6	9.6	9.6	9.6	9.6	10.3	9.6	10.3	11.1	11.1	11.1
90°	38.0	38.0	38.0	37.4	36.8	34.5	36.8	38.0	39.1	38.0	31.1
92.5°	71.4	76.0	77.1	81.7	86.3	99.0	116.3	148.5	177.3	175.0	135.8
95°	133.5	142.7	157.7	170.4	183.0	231.4	301.6	394.8	451.2	399.4	265.9
97.5°	239.4	262.4	307.3	341.8	376.4	492.6	616.9	741.3	735.5	568.6	353.4
100°	466.2	515.7	611.2	680.8	750.5	908.1	1050.9	1075.0	909.3	626.2	377.5
102.5°	877.1	970.3	1076.2	1151.0	1225.8	1330.6	1335.2	1199.4	915.1	604.3	378.7
105°	1362.8	1434.2	1505.5	1524.5	1543.5	1528.5	1398.5	1159.1	852.9	574.4	384.4
107.5°	1671.3	1681.6	1682.8	1659.8	1636.7	1523.9	1330.6	1073.9	795.3	558.2	397.1
110°	1756.4	1734.6	1685.1	1637.9	1590.7	1443.4	1237.3	994.5	756.2	553.6	413.2

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1733.4	1693.1	1619.5	1563.6	1507.8	1347.8	1152.2	939.2	730.9	554.8	430.5
115°	1666.7	1613.7	1532.0	1472.7	1413.4	1262.7	1085.4	895.5	713.6	559.4	447.7
117.5°	1582.6	1526.2	1442.2	1385.8	1329.4	1189.0	1030.2	865.6	704.4	566.3	466.2
120°	1495.2	1441.1	1360.5	1308.2	1255.8	1133.7	991.0	842.5	696.4	573.2	484.6
122.5°	1416.9	1363.9	1293.7	1247.7	1201.7	1087.7	959.9	823.0	691.8	581.3	500.7
125°	1346.7	1302.9	1236.2	1193.1	1149.9	1048.6	930.0	804.6	686.0	589.3	518.0
127.5°	1286.8	1245.4	1186.7	1146.4	1106.1	1009.4	900.1	787.3	682.6	597.4	534.1
130°	1232.7	1193.6	1137.2	1099.2	1061.2	970.3	871.3	770.0	680.2	606.6	549.0
132.5°	1179.8	1140.7	1085.4	1050.3	1015.2	933.5	843.7	756.2	679.1	615.8	564.0
135°	1122.2	1084.3	1034.8	1002.6	970.3	894.3	818.4	743.6	677.9	622.7	576.7
137.5°	1063.5	1030.2	983.0	954.2	925.4	863.3	797.7	734.3	677.9	629.6	587.0
140°	1003.7	973.8	936.9	911.6	886.3	833.3	778.1	726.3	676.8	634.2	595.1
142.5°	951.9	925.4	890.9	870.8	850.6	806.9	762.0	718.2	676.8	637.7	602.0
145°	901.2	881.7	854.1	837.4	820.7	785.0	747.0	711.3	674.5	640.0	607.7
147.5°	861.0	844.8	820.7	808.0	795.3	766.6	735.5	704.4	671.0	641.1	611.2
150°	824.1	810.3	793.0	782.6	772.3	748.2	722.8	695.2	667.6	640.0	613.5
152.5°	794.2	782.7	770.0	761.4	752.8	733.2	710.2	687.2	661.8	637.7	614.6
155°	767.7	759.7	747.0	740.6	734.3	717.1	698.7	676.8	654.9	635.4	615.8
157.5°	742.4	735.5	726.3	721.1	715.9	701.0	684.9	667.6	648.0	630.8	615.8
160°	719.4	713.6	705.6	701.6	697.5	684.9	672.2	657.2	641.1	627.3	615.8
162.5°	697.5	694.1	686.0	683.1	680.2	669.9	659.5	648.0	635.4	623.8	614.6
165°	676.8	672.2	667.6	665.3	663.0	654.9	646.9	637.7	627.3	619.2	612.3
167.5°	656.1	653.8	651.5	649.2	646.9	641.1	634.2	627.3	620.4	614.6	611.2
170°	640.0	636.5	635.4	634.2	633.1	628.5	625.0	619.2	614.6	611.2	608.9
172.5°	623.8	622.7	621.5	621.0	620.4	616.9	614.6	611.2	607.7	606.6	605.4
175°	612.3	611.2	611.2	610.6	610.0	608.9	607.7	604.3	603.1	602.0	603.1
177.5°	603.1	603.1	603.1	603.1	603.1	602.0	602.0	599.7	598.5	599.7	602.0
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	984.6	980.9	978.7	980.2	975.7	964.7	964.7	968.4	963.9	959.5	952.9
5°	1011.9	1004.5	1000.1	999.3	989.0	971.3	967.6	963.9	954.4	944.0	933.0
7.5°	1038.4	1025.2	1017.8	1012.6	997.9	975.0	965.4	957.3	941.8	926.3	912.3
10°	1060.6	1041.4	1032.5	1024.4	1005.2	976.5	961.0	946.2	926.3	906.4	888.7
12.5°	1078.3	1056.1	1045.1	1033.3	1009.7	972.1	952.9	929.3	909.4	882.8	865.1
15°	1107.8	1062.0	1051.7	1040.7	1016.3	964.7	941.1	914.5	887.2	851.8	832.7
17.5°	1131.4	1070.2	1069.4	1045.8	1014.1	961.7	925.6	890.9	861.4	826.0	795.8
20°	1145.4	1082.7	1070.9	1046.6	1006.7	941.8	904.2	865.9	834.1	791.4	761.1
22.5°	1157.2	1100.4	1069.4	1039.9	991.2	935.2	879.9	843.7	800.2	753.8	725.0
25°	1161.6	1104.1	1071.6	1037.7	980.2	916.0	853.3	814.2	765.6	723.5	684.4
27.5°	1162.3	1103.3	1063.5	1028.1	964.7	890.9	826.8	785.5	731.6	683.0	643.9
30°	1155.0	1095.2	1059.1	1020.7	949.9	868.1	794.3	748.6	691.1	642.4	601.8
32.5°	1132.8	1079.0	1049.5	1007.5	930.8	836.4	763.3	712.5	652.0	604.0	564.9
35°	1096.0	1059.1	1026.6	987.5	905.7	806.9	732.4	672.6	611.4	565.7	528.8
37.5°	1050.2	1030.3	1000.1	961.7	876.9	780.3	697.7	631.3	570.1	525.9	489.7
40°	988.3	993.4	963.9	929.3	843.0	744.2	652.7	589.3	531.8	490.5	455.1
42.5°	921.2	942.6	925.6	892.4	805.4	704.3	619.5	549.5	493.4	450.6	421.1
45°	848.9	885.8	875.4	851.1	766.3	662.3	572.3	504.5	455.1	413.8	387.9
47.5°	770.0	822.3	822.3	804.6	722.8	620.3	531.8	462.4	413.8	384.3	359.2
50°	689.6	748.6	758.2	746.4	674.1	572.3	482.3	419.7	377.6	348.9	330.4
52.5°	605.5	674.1	691.8	685.9	622.5	526.6	441.8	380.6	342.2	317.1	300.9
55°	525.1	604.8	623.9	626.2	567.2	476.4	396.8	343.0	306.1	289.1	275.1
57.5°	449.2	525.9	547.2	550.9	511.1	430.7	354.8	307.5	274.4	260.3	249.3
60°	384.3	448.4	476.4	484.6	449.9	377.6	315.7	269.9	244.9	231.6	221.3
62.5°	331.1	382.8	412.3	414.5	399.0	331.1	275.1	236.7	215.4	203.6	198.4
65°	279.5	326.0	343.7	352.5	340.0	286.9	237.5	205.8	188.8	178.5	173.3
67.5°	238.2	267.7	282.5	294.3	281.7	241.9	202.1	176.3	163.7	153.4	150.5
70°	195.4	219.8	230.8	242.6	231.6	201.3	172.6	149.0	137.9	129.8	126.1
72.5°	156.4	175.5	185.9	193.2	186.6	161.5	137.9	121.7	113.6	107.7	105.5
75°	123.9	137.2	143.1	148.2	145.3	126.1	111.4	98.1	90.7	85.6	84.1
77.5°	94.4	104.0	110.6	112.1	108.4	95.9	83.3	75.2	69.3	66.4	64.9
80°	67.1	73.0	76.7	78.9	75.2	70.1	61.2	55.3	50.2	46.5	45.7
82.5°	45.0	47.9	50.9	50.2	48.7	44.3	39.1	36.1	33.9	31.0	31.0
85°	25.8	26.6	28.0	28.8	28.0	25.1	22.1	20.7	19.2	17.0	17.0
87.5°	11.1	11.8	11.8	12.5	11.1	11.1	9.6	8.1	8.1	7.4	6.6
90°	23.0	17.3	15.6	13.8	11.5	9.2	4.6	1.2	4.6	9.2	11.5
92.5°	92.1	61.0	54.6	48.3	39.1	33.4	24.2	17.3	24.2	33.4	39.1
95°	165.7	112.8	99.0	85.2	66.8	56.4	44.9	40.3	44.9	56.4	66.8
97.5°	214.1	146.2	130.6	115.1	94.4	79.4	66.8	59.9	66.8	79.4	94.4
100°	237.1	176.1	160.0	143.9	120.9	102.4	92.1	88.6	92.1	102.4	120.9
102.5°	257.8	202.6	186.4	170.3	146.2	127.8	117.4	115.1	117.4	127.8	146.2
105°	282.0	227.9	211.8	195.7	170.3	153.1	145.0	140.4	145.0	153.1	170.3
107.5°	306.2	253.2	237.1	221.0	195.7	179.6	171.5	168.0	171.5	179.6	195.7
110°	330.3	279.7	263.0	246.3	222.1	207.2	200.3	195.7	200.3	207.2	222.1

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	353.4	305.0	287.8	270.5	247.5	233.7	225.6	221.0	225.6	233.7	247.5
115°	377.5	328.0	312.5	297.0	273.9	260.1	253.2	247.5	253.2	260.1	273.9
117.5°	399.4	353.4	337.2	321.1	299.3	286.6	279.7	275.1	279.7	286.6	299.3
120°	422.4	377.5	361.4	345.3	322.3	311.9	305.0	300.4	305.0	311.9	322.3
122.5°	444.3	402.9	386.2	369.5	346.5	334.9	328.0	324.6	328.0	334.9	346.5
125°	466.2	424.7	408.6	392.5	369.5	355.7	348.8	345.3	348.8	355.7	369.5
127.5°	486.9	446.6	429.9	413.2	391.3	376.4	367.2	362.6	367.2	376.4	391.3
130°	505.3	465.0	448.9	432.8	409.8	393.6	382.1	377.5	382.1	393.6	409.8
132.5°	521.4	483.4	467.3	451.2	427.0	409.8	397.1	391.3	397.1	409.8	427.0
135°	536.4	499.5	483.4	467.3	440.8	423.6	409.8	405.2	409.8	423.6	440.8
137.5°	549.0	512.2	497.2	482.3	455.8	437.4	423.6	417.8	423.6	437.4	455.8
140°	559.4	524.9	509.9	494.9	469.6	451.2	437.4	432.8	437.4	451.2	469.6
142.5°	567.4	534.1	520.2	506.4	482.3	463.9	451.2	447.7	451.2	463.9	482.3
145°	575.5	544.4	531.8	519.1	496.1	478.8	467.3	462.7	467.3	478.8	496.1
147.5°	582.4	552.5	541.0	529.5	509.9	493.8	482.3	478.8	482.3	493.8	509.9
150°	587.0	560.5	550.2	539.8	522.6	507.6	498.4	494.9	498.4	507.6	522.6
152.5°	591.6	568.6	559.4	550.2	534.1	521.4	512.2	511.0	512.2	521.4	534.1
155°	596.2	576.7	568.0	559.4	546.7	534.1	527.2	526.0	527.2	534.1	546.7
157.5°	599.7	582.4	574.9	567.4	557.1	545.6	539.8	538.7	539.8	545.6	557.1
160°	602.0	588.2	581.8	575.5	566.3	557.1	552.5	551.3	552.5	557.1	566.3
162.5°	603.1	591.6	587.0	582.4	574.4	567.4	562.8	564.0	562.8	567.4	574.4
165°	604.3	593.9	590.4	587.0	581.3	574.4	572.1	573.2	572.1	574.4	581.3
167.5°	604.3	596.2	593.9	591.6	587.0	582.4	580.1	581.3	580.1	582.4	587.0
170°	603.1	597.4	595.6	593.9	591.6	588.2	587.0	589.3	587.0	588.2	591.6
172.5°	602.0	598.5	597.4	596.2	595.1	591.6	592.8	593.9	592.8	591.6	595.1
175°	600.8	598.5	598.0	597.4	597.4	595.1	596.2	597.4	596.2	595.1	597.4
177.5°	599.7	598.5	598.5	598.5	598.5	596.2	597.4	599.7	597.4	596.2	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	949.2	952.9	952.1	944.8	936.7	930.0	917.5	919.0	914.5	915.3	919.7
5°	925.6	925.6	922.6	912.3	899.0	891.7	877.7	874.0	865.1	864.4	863.6
7.5°	900.5	896.8	893.1	878.4	862.2	850.4	831.2	826.8	817.9	812.0	809.1
10°	871.0	865.9	858.5	841.5	821.6	806.9	786.9	781.0	764.1	756.7	752.3
12.5°	838.6	835.6	823.8	809.8	777.4	761.1	732.4	738.3	721.3	706.6	704.3
15°	806.1	795.1	788.4	765.6	726.5	719.1	696.2	684.4	668.9	657.1	657.1
17.5°	774.4	757.4	742.7	718.4	689.6	668.9	652.0	646.1	626.9	615.1	612.9
20°	732.4	713.2	709.5	674.8	654.9	632.1	615.8	601.1	587.1	581.9	578.2
22.5°	692.5	670.4	664.5	635.0	615.1	592.2	576.0	565.7	555.4	551.7	545.0
25°	649.8	636.5	627.6	595.9	573.8	552.4	541.3	534.0	524.4	523.6	519.2
27.5°	608.5	595.9	587.1	556.8	540.6	520.7	511.8	503.7	498.6	496.4	494.1
30°	573.1	559.0	548.7	526.6	506.7	490.5	483.1	477.9	475.0	471.3	470.5
32.5°	534.0	525.9	511.8	494.9	479.4	463.9	459.5	455.8	451.4	449.9	449.2
35°	500.8	489.7	480.9	461.7	455.1	441.8	436.6	433.7	427.8	426.3	424.8
37.5°	468.3	458.0	448.4	436.6	424.1	416.7	413.8	409.3	406.4	407.1	405.6
40°	435.9	427.8	420.4	407.9	400.5	396.8	390.9	386.5	385.0	385.7	385.0
42.5°	404.2	396.8	392.4	382.8	375.4	371.7	368.0	363.6	365.8	365.8	368.0
45°	375.4	368.8	365.8	358.4	354.0	348.1	344.4	343.7	346.6	345.9	345.9
47.5°	345.9	343.7	340.0	333.4	327.5	323.8	323.0	323.0	326.0	327.5	326.7
50°	323.0	318.6	314.2	309.0	304.6	303.1	300.9	302.4	305.3	305.3	306.8
52.5°	294.3	291.3	289.8	285.4	282.5	282.5	282.5	283.2	285.4	287.6	286.9
55°	269.2	267.0	265.5	263.3	259.6	260.3	259.6	261.1	263.3	265.5	267.0
57.5°	242.6	241.9	240.4	236.7	236.7	236.0	238.2	239.0	242.6	244.1	246.3
60°	219.0	216.8	216.8	213.9	213.9	213.9	216.1	218.3	221.3	222.0	223.5
62.5°	194.0	194.0	193.2	191.0	191.0	193.2	194.0	196.9	198.4	198.4	200.6
65°	170.4	169.6	168.9	169.6	170.4	170.4	172.6	174.1	175.5	176.3	177.0
67.5°	146.8	146.0	147.5	146.8	148.2	151.2	150.5	152.7	154.9	154.9	155.6
70°	124.6	126.1	125.4	126.9	126.1	127.6	129.8	130.5	130.5	131.3	133.5
72.5°	104.0	104.0	104.0	103.3	104.0	105.5	106.9	107.7	109.2	109.9	112.1
75°	84.1	84.1	82.6	84.1	84.1	85.6	87.0	87.0	87.0	88.5	90.7
77.5°	63.4	64.2	63.4	64.9	64.9	65.6	67.1	66.4	67.9	68.6	69.3
80°	46.5	45.7	45.7	45.7	46.5	46.5	47.9	48.7	48.7	50.9	49.4
82.5°	29.5	30.2	29.5	30.2	30.2	31.0	30.2	31.0	31.7	33.2	32.5
85°	17.0	16.2	16.2	17.0	16.2	16.2	17.0	16.2	17.0	16.2	17.0
87.5°	6.6	5.9	5.9	5.9	5.9	5.2	5.2	4.4	4.4	4.4	3.7
90°	13.8	15.6	17.3	23.0	31.1	38.0	39.1	38.0	36.8	34.5	36.8
92.5°	48.3	54.6	61.0	92.1	135.8	175.0	177.3	148.5	116.3	99.0	86.3
95°	85.2	99.0	112.8	165.7	265.9	399.4	451.2	394.8	301.6	231.4	183.0
97.5°	115.1	130.6	146.2	214.1	353.4	568.6	735.5	741.3	616.9	492.6	376.4
100°	143.9	160.0	176.1	237.1	377.5	626.2	909.3	1075.0	1050.9	908.1	750.5
102.5°	170.3	186.4	202.6	257.8	378.7	604.3	915.1	1199.4	1335.2	1330.6	1225.8
105°	195.7	211.8	227.9	282.0	384.4	574.4	852.9	1159.1	1398.5	1528.5	1543.5
107.5°	221.0	237.1	253.2	306.2	397.1	558.2	795.3	1073.9	1330.6	1523.9	1636.7
110°	246.3	263.0	279.7	330.3	413.2	553.6	756.2	994.5	1237.3	1443.4	1590.7

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	270.5	287.8	305.0	353.4	430.5	554.8	730.9	939.2	1152.2	1347.8	1507.8
115°	297.0	312.5	328.0	377.5	447.7	559.4	713.6	895.5	1085.4	1262.7	1413.4
117.5°	321.1	337.2	353.4	399.4	466.2	566.3	704.4	865.6	1030.2	1189.0	1329.4
120°	345.3	361.4	377.5	422.4	484.6	573.2	696.4	842.5	991.0	1133.7	1255.8
122.5°	369.5	386.2	402.9	444.3	500.7	581.3	691.8	823.0	959.9	1087.7	1201.7
125°	392.5	408.6	424.7	466.2	518.0	589.3	686.0	804.6	930.0	1048.6	1149.9
127.5°	413.2	429.9	446.6	486.9	534.1	597.4	682.6	787.3	900.1	1009.4	1106.1
130°	432.8	448.9	465.0	505.3	549.0	606.6	680.2	770.0	871.3	970.3	1061.2
132.5°	451.2	467.3	483.4	521.4	564.0	615.8	679.1	756.2	843.7	933.5	1015.2
135°	467.3	483.4	499.5	536.4	576.7	622.7	677.9	743.6	818.4	894.3	970.3
137.5°	482.3	497.2	512.2	549.0	587.0	629.6	677.9	734.3	797.7	863.3	925.4
140°	494.9	509.9	524.9	559.4	595.1	634.2	676.8	726.3	778.1	833.3	886.3
142.5°	506.4	520.2	534.1	567.4	602.0	637.7	676.8	718.2	762.0	806.9	850.6
145°	519.1	531.8	544.4	575.5	607.7	640.0	674.5	711.3	747.0	785.0	820.7
147.5°	529.5	541.0	552.5	582.4	611.2	641.1	671.0	704.4	735.5	766.6	795.3
150°	539.8	550.2	560.5	587.0	613.5	640.0	667.6	695.2	722.8	748.2	772.3
152.5°	550.2	559.4	568.6	591.6	614.6	637.7	661.8	687.2	710.2	733.2	752.8
155°	559.4	568.0	576.7	596.2	615.8	635.4	654.9	676.8	698.7	717.1	734.3
157.5°	567.4	574.9	582.4	599.7	615.8	630.8	648.0	667.6	684.9	701.0	715.9
160°	575.5	581.8	588.2	602.0	615.8	627.3	641.1	657.2	672.2	684.9	697.5
162.5°	582.4	587.0	591.6	603.1	614.6	623.8	635.4	648.0	659.5	669.9	680.2
165°	587.0	590.4	593.9	604.3	612.3	619.2	627.3	637.7	646.9	654.9	663.0
167.5°	591.6	593.9	596.2	604.3	611.2	614.6	620.4	627.3	634.2	641.1	646.9
170°	593.9	595.6	597.4	603.1	608.9	611.2	614.6	619.2	625.0	628.5	633.1
172.5°	596.2	597.4	598.5	602.0	605.4	606.6	607.7	611.2	614.6	616.9	620.4
175°	597.4	598.0	598.5	600.8	603.1	602.0	603.1	604.3	607.7	608.9	610.0
177.5°	598.5	598.5	598.5	599.7	602.0	599.7	598.5	599.7	602.0	602.0	603.1
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	914.5	916.7	911.6	910.1	911.6	906.4	907.9	909.4	909.4	911.6	913.1
5°	861.4	858.5	853.3	851.8	850.4	852.6	851.1	853.3	854.1	859.2	860.0
7.5°	809.1	804.6	800.2	795.8	794.3	790.6	794.3	794.3	799.5	798.0	801.7
10°	747.1	746.4	740.5	738.3	735.3	729.4	737.5	735.3	739.0	745.6	747.1
12.5°	701.4	693.3	697.0	686.6	690.3	684.4	685.2	685.2	691.1	691.8	690.3
15°	657.9	651.2	641.6	637.2	635.0	632.1	641.6	642.4	638.0	648.3	644.6
17.5°	613.6	613.6	604.8	602.6	596.7	599.6	598.1	598.9	597.4	604.8	608.5
20°	575.3	571.6	568.6	569.4	562.0	560.5	559.0	560.5	565.7	570.8	572.3
22.5°	544.3	542.1	534.7	536.2	530.3	532.5	531.0	534.7	535.4	535.4	540.6
25°	514.8	511.8	512.6	509.6	507.4	507.4	505.2	507.4	510.4	511.8	512.6
27.5°	492.7	490.5	486.8	484.6	486.0	482.3	485.3	487.5	487.5	486.0	487.5
30°	466.1	467.6	467.6	460.2	463.2	461.7	463.9	465.4	465.4	466.1	464.6
32.5°	448.4	444.0	443.3	442.5	442.5	439.6	439.6	441.8	442.5	443.3	445.5
35°	424.8	424.8	421.1	423.3	420.4	421.1	420.4	421.1	422.6	420.4	422.6
37.5°	403.4	404.2	402.7	404.2	404.9	403.4	402.0	404.9	403.4	403.4	402.0
40°	385.0	384.3	385.0	385.0	385.0	385.7	384.3	384.3	384.3	382.8	381.3
42.5°	369.5	365.1	366.6	367.3	365.1	365.1	365.8	365.1	367.3	362.9	362.9
45°	347.4	345.9	346.6	346.6	348.1	345.9	347.4	348.1	345.9	345.2	343.7
47.5°	327.5	328.9	327.5	328.9	328.9	330.4	327.5	328.2	328.9	326.0	323.8
50°	307.5	307.5	309.8	309.0	309.8	308.3	308.3	307.5	308.3	306.8	304.6
52.5°	289.1	286.9	290.6	289.8	289.1	288.4	287.6	288.4	286.9	285.4	285.4
55°	266.2	266.2	268.5	269.2	269.2	267.7	266.2	267.0	266.2	265.5	264.8
57.5°	247.8	244.9	246.3	247.1	247.1	244.9	246.3	244.9	244.9	245.6	243.4
60°	224.2	224.2	222.7	224.9	224.9	223.5	223.5	224.2	222.7	222.0	221.3
62.5°	199.1	199.9	202.1	202.8	203.6	202.1	200.6	201.3	201.3	199.1	199.9
65°	177.7	179.2	182.2	181.4	180.0	180.7	179.2	180.0	177.7	178.5	176.3
67.5°	157.1	156.4	157.1	157.1	158.6	157.8	156.4	156.4	155.6	157.8	155.6
70°	135.0	135.0	135.0	135.0	135.7	136.4	135.0	133.5	134.2	132.8	132.0
72.5°	112.1	112.8	112.1	113.6	111.4	112.8	112.8	112.1	111.4	111.4	111.4
75°	90.7	92.2	90.0	90.7	90.0	91.5	90.7	90.7	89.2	88.5	89.2
77.5°	69.3	70.1	68.6	69.3	68.6	69.3	69.3	68.6	68.6	68.6	68.6
80°	49.4	50.2	49.4	48.7	47.9	49.4	47.9	48.7	49.4	48.7	50.2
82.5°	31.7	31.7	31.0	31.7	30.2	30.2	31.0	31.0	30.2	31.7	30.2
85°	15.5	15.5	17.0	15.5	14.8	14.8	14.8	15.5	14.8	16.2	15.5
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.4	3.0
90°	37.4	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.4
92.5°	81.7	77.1	76.0	71.4	72.5	70.2	72.5	71.4	76.0	77.1	81.7
95°	170.4	157.7	142.7	133.5	130.1	131.2	130.1	133.5	142.7	157.7	170.4
97.5°	341.8	307.3	262.4	239.4	226.7	219.8	226.7	239.4	262.4	307.3	341.8
100°	680.8	611.2	515.7	466.2	432.8	412.1	432.8	466.2	515.7	611.2	680.8
102.5°	1151.0	1076.2	970.3	877.1	833.3	803.4	833.3	877.1	970.3	1076.2	1151.0
105°	1524.5	1505.5	1434.2	1362.8	1313.3	1297.2	1313.3	1362.8	1434.2	1505.5	1524.5
107.5°	1659.8	1682.8	1681.6	1671.3	1656.3	1629.8	1656.3	1671.3	1681.6	1682.8	1659.8
110°	1637.9	1685.1	1734.6	1756.4	1766.8	1765.7	1766.8	1756.4	1734.6	1685.1	1637.9

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1563.6	1619.5	1693.1	1733.4	1755.3	1763.4	1755.3	1733.4	1693.1	1619.5	1563.6
115°	1472.7	1532.0	1613.7	1666.7	1696.6	1707.0	1696.6	1666.7	1613.7	1532.0	1472.7
117.5°	1385.8	1442.2	1526.2	1582.6	1613.7	1621.8	1613.7	1582.6	1526.2	1442.2	1385.8
120°	1308.2	1360.5	1441.1	1495.2	1528.5	1540.1	1528.5	1495.2	1441.1	1360.5	1308.2
122.5°	1247.7	1293.7	1363.9	1416.9	1445.7	1454.9	1445.7	1416.9	1363.9	1293.7	1247.7
125°	1193.1	1236.2	1302.9	1346.7	1375.5	1384.7	1375.5	1346.7	1302.9	1236.2	1193.1
127.5°	1146.4	1186.7	1245.4	1286.8	1312.2	1319.1	1312.2	1286.8	1245.4	1186.7	1146.4
130°	1099.2	1137.2	1193.6	1232.7	1255.8	1265.0	1255.8	1232.7	1193.6	1137.2	1099.2
132.5°	1050.3	1085.4	1140.7	1179.8	1200.5	1208.6	1200.5	1179.8	1140.7	1085.4	1050.3
135°	1002.6	1034.8	1084.3	1122.2	1143.0	1147.6	1143.0	1122.2	1084.3	1034.8	1002.6
137.5°	954.2	983.0	1030.2	1063.5	1082.0	1088.9	1082.0	1063.5	1030.2	983.0	954.2
140°	911.6	936.9	973.8	1003.7	1020.9	1027.9	1020.9	1003.7	973.8	936.9	911.6
142.5°	870.8	890.9	925.4	951.9	966.9	966.9	966.9	951.9	925.4	890.9	870.8
145°	837.4	854.1	881.7	901.2	912.8	916.2	912.8	901.2	881.7	854.1	837.4
147.5°	808.0	820.7	844.8	861.0	869.0	871.3	869.0	861.0	844.8	820.7	808.0
150°	782.6	793.0	810.3	824.1	831.0	832.2	831.0	824.1	810.3	793.0	782.6
152.5°	761.4	770.0	782.7	794.2	798.8	798.8	798.8	794.2	782.7	770.0	761.4
155°	740.6	747.0	759.7	767.7	772.3	770.0	772.3	767.7	759.7	747.0	740.6
157.5°	721.1	726.3	735.5	742.4	744.7	744.7	744.7	742.4	735.5	726.3	721.1
160°	701.6	705.6	713.6	719.4	720.5	720.5	720.5	719.4	713.6	705.6	701.6
162.5°	683.1	686.0	694.1	697.5	698.7	697.5	698.7	697.5	694.1	686.0	683.1
165°	665.3	667.6	672.2	676.8	676.8	675.6	676.8	676.8	672.2	667.6	665.3
167.5°	649.2	651.5	653.8	656.1	656.1	654.9	656.1	656.1	653.8	651.5	649.2
170°	634.2	635.4	636.5	640.0	638.8	636.5	638.8	640.0	636.5	635.4	634.2
172.5°	621.0	621.5	622.7	623.8	622.7	621.5	622.7	623.8	622.7	621.5	621.0
175°	610.6	611.2	611.2	612.3	611.2	608.9	611.2	612.3	611.2	611.2	610.6
177.5°	603.1	603.1	603.1	603.1	602.0	599.7	602.0	603.1	603.1	603.1	603.1
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	910.8	916.7	914.5	906.4	916.0	916.0	922.6	922.6	930.8	933.7	938.1
5°	859.2	863.6	867.3	863.6	870.3	880.6	886.5	891.7	902.7	907.2	913.8
7.5°	803.9	812.0	815.7	815.7	826.8	838.6	850.4	857.7	873.2	879.1	885.8
10°	750.1	759.7	767.0	766.3	784.7	792.1	806.9	823.8	839.3	848.2	857.7
12.5°	693.3	698.4	708.8	723.5	727.9	741.2	758.2	779.6	807.6	815.7	829.7
15°	646.1	660.1	668.2	674.8	685.2	697.7	716.1	736.8	764.8	782.5	797.3
17.5°	606.2	624.7	629.8	628.4	641.6	660.8	682.2	697.7	722.8	744.2	758.2
20°	573.8	581.2	590.0	593.7	604.0	624.7	645.3	663.0	683.7	700.7	716.9
22.5°	541.3	547.2	554.6	561.3	569.4	581.2	601.1	623.2	643.1	659.3	677.8
25°	514.8	518.5	525.1	530.3	539.1	547.2	561.3	585.6	609.2	618.8	635.0
27.5°	489.0	491.9	496.4	502.3	506.7	514.8	527.3	547.2	571.6	581.2	603.3
30°	466.1	468.3	472.8	475.7	477.9	487.5	497.1	512.6	531.0	544.3	560.5
32.5°	444.7	446.9	451.4	452.1	455.1	460.2	469.1	483.1	499.3	510.4	524.4
35°	421.1	422.6	427.0	428.5	430.7	435.1	441.8	452.1	466.9	475.0	487.5
37.5°	402.7	402.0	404.9	407.1	410.1	412.3	414.5	424.8	435.9	443.3	452.8
40°	382.8	381.3	382.0	385.0	386.5	389.4	389.4	399.7	407.1	413.0	420.4
42.5°	362.9	362.1	360.7	362.1	363.6	364.3	365.1	372.5	379.8	385.0	393.1
45°	343.0	342.2	340.7	341.5	341.5	343.0	345.2	348.1	353.3	357.7	362.1
47.5°	324.5	323.0	320.8	320.1	321.6	321.6	321.6	324.5	329.7	331.1	335.6
50°	305.3	303.1	300.2	298.7	298.7	298.0	299.4	300.2	304.6	306.1	309.8
52.5°	284.7	283.2	280.3	277.3	278.0	276.6	277.3	278.0	279.5	281.7	283.9
55°	264.0	261.1	258.9	258.1	255.9	255.9	253.7	256.7	255.9	256.7	259.6
57.5°	244.1	241.2	237.5	236.0	233.8	233.1	231.6	230.8	231.6	233.8	236.0
60°	220.5	219.0	216.8	214.6	213.1	210.9	209.5	209.5	208.7	208.7	209.5
62.5°	197.7	196.9	194.0	193.2	191.8	190.3	188.1	186.6	186.6	188.1	188.8
65°	175.5	174.8	172.6	171.8	168.2	166.7	165.9	165.2	163.7	163.7	163.7
67.5°	154.9	152.7	152.7	149.0	146.0	144.6	143.1	142.3	142.3	142.3	143.1
70°	132.0	132.0	129.8	127.6	124.6	125.4	123.2	121.0	121.0	119.5	120.2
72.5°	109.9	109.2	106.9	106.2	104.0	101.8	100.3	101.8	99.6	98.8	99.6
75°	88.5	87.8	86.3	84.8	85.6	83.3	81.1	80.4	80.4	78.9	78.9
77.5°	67.9	69.3	66.4	65.6	64.2	62.7	62.0	61.2	61.2	61.2	62.7
80°	47.2	47.9	47.9	46.5	47.2	45.0	45.0	45.0	42.8	43.5	44.3
82.5°	30.2	30.2	29.5	30.2	29.5	29.5	28.8	28.8	28.0	28.0	28.8
85°	17.0	16.2	15.5	17.0	16.2	16.2	15.5	15.5	15.5	15.5	15.5
87.5°	3.7	4.4	4.4	4.4	4.4	5.2	5.2	5.2	5.9	5.9	5.9
90°	36.8	34.5	36.8	38.0	39.1	38.0	31.1	23.0	17.3	15.6	13.8
92.5°	86.3	99.0	116.3	148.5	177.3	175.0	135.8	92.1	61.0	54.6	48.3
95°	183.0	231.4	301.6	394.8	451.2	399.4	265.9	165.7	112.8	99.0	85.2
97.5°	376.4	492.6	616.9	741.3	735.5	568.6	353.4	214.1	146.2	130.6	115.1
100°	750.5	908.1	1050.9	1075.0	909.3	626.2	377.5	237.1	176.1	160.0	143.9
102.5°	1225.8	1330.6	1335.2	1199.4	915.1	604.3	378.7	257.8	202.6	186.4	170.3
105°	1543.5	1528.5	1398.5	1159.1	852.9	574.4	384.4	282.0	227.9	211.8	195.7
107.5°	1636.7	1523.9	1330.6	1073.9	795.3	558.2	397.1	306.2	253.2	237.1	221.0
110°	1590.7	1443.4	1237.3	994.5	756.2	553.6	413.2	330.3	279.7	263.0	246.3

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1507.8	1347.8	1152.2	939.2	730.9	554.8	430.5	353.4	305.0	287.8	270.5
115°	1413.4	1262.7	1085.4	895.5	713.6	559.4	447.7	377.5	328.0	312.5	297.0
117.5°	1329.4	1189.0	1030.2	865.6	704.4	566.3	466.2	399.4	353.4	337.2	321.1
120°	1255.8	1133.7	991.0	842.5	696.4	573.2	484.6	422.4	377.5	361.4	345.3
122.5°	1201.7	1087.7	959.9	823.0	691.8	581.3	500.7	444.3	402.9	386.2	369.5
125°	1149.9	1048.6	930.0	804.6	686.0	589.3	518.0	466.2	424.7	408.6	392.5
127.5°	1106.1	1009.4	900.1	787.3	682.6	597.4	534.1	486.9	446.6	429.9	413.2
130°	1061.2	970.3	871.3	770.0	680.2	606.6	549.0	505.3	465.0	448.9	432.8
132.5°	1015.2	933.5	843.7	756.2	679.1	615.8	564.0	521.4	483.4	467.3	451.2
135°	970.3	894.3	818.4	743.6	677.9	622.7	576.7	536.4	499.5	483.4	467.3
137.5°	925.4	863.3	797.7	734.3	677.9	629.6	587.0	549.0	512.2	497.2	482.3
140°	886.3	833.3	778.1	726.3	676.8	634.2	595.1	559.4	524.9	509.9	494.9
142.5°	850.6	806.9	762.0	718.2	676.8	637.7	602.0	567.4	534.1	520.2	506.4
145°	820.7	785.0	747.0	711.3	674.5	640.0	607.7	575.5	544.4	531.8	519.1
147.5°	795.3	766.6	735.5	704.4	671.0	641.1	611.2	582.4	552.5	541.0	529.5
150°	772.3	748.2	722.8	695.2	667.6	640.0	613.5	587.0	560.5	550.2	539.8
152.5°	752.8	733.2	710.2	687.2	661.8	637.7	614.6	591.6	568.6	559.4	550.2
155°	734.3	717.1	698.7	676.8	654.9	635.4	615.8	596.2	576.7	568.0	559.4
157.5°	715.9	701.0	684.9	667.6	648.0	630.8	615.8	599.7	582.4	574.9	567.4
160°	697.5	684.9	672.2	657.2	641.1	627.3	615.8	602.0	588.2	581.8	575.5
162.5°	680.2	669.9	659.5	648.0	635.4	623.8	614.6	603.1	591.6	587.0	582.4
165°	663.0	654.9	646.9	637.7	627.3	619.2	612.3	604.3	593.9	590.4	587.0
167.5°	646.9	641.1	634.2	627.3	620.4	614.6	611.2	604.3	596.2	593.9	591.6
170°	633.1	628.5	625.0	619.2	614.6	611.2	608.9	603.1	597.4	595.6	593.9
172.5°	620.4	616.9	614.6	611.2	607.7	606.6	605.4	602.0	598.5	597.4	596.2
175°	610.0	608.9	607.7	604.3	603.1	602.0	603.1	600.8	598.5	598.0	597.4
177.5°	603.1	602.0	602.0	599.7	598.5	599.7	602.0	599.7	598.5	598.5	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	959.5	959.5	959.5	959.5
2.5°	941.8	941.8	952.9	964.7
5°	921.2	926.3	944.0	960.3
7.5°	901.3	910.1	932.2	952.9
10°	876.9	888.7	916.0	940.3
12.5°	853.3	864.4	896.1	923.4
15°	820.1	834.1	868.1	902.0
17.5°	786.9	801.0	842.3	882.1
20°	747.9	766.3	812.8	865.9
22.5°	711.7	734.6	786.2	829.0
25°	671.9	707.3	755.2	810.5
27.5°	636.5	671.9	720.6	776.6
30°	596.7	632.8	683.0	734.6
32.5°	558.3	591.5	640.2	703.6
35°	518.5	550.2	597.4	661.6
37.5°	482.3	513.3	564.9	623.9
40°	446.9	479.4	523.6	582.6
42.5°	413.8	442.5	482.3	541.3
45°	383.5	404.2	441.0	496.4
47.5°	351.8	370.2	404.2	459.5
50°	322.3	337.8	367.3	418.9
52.5°	293.5	306.8	334.1	375.4
55°	267.7	280.3	300.2	340.7
57.5°	241.2	250.8	269.9	302.4
60°	215.4	224.2	239.7	266.2
62.5°	189.5	196.9	211.7	233.1
65°	166.7	172.6	183.6	202.1
67.5°	144.6	148.2	157.1	171.8
70°	123.2	126.1	133.5	145.3
72.5°	100.3	103.3	111.4	119.5
75°	81.1	81.9	87.8	94.4
77.5°	63.4	62.7	67.1	72.3
80°	43.5	45.7	49.4	51.6
82.5°	29.5	30.2	31.7	33.2
85°	16.2	17.0	17.0	19.2
87.5°	6.6	7.4	7.4	8.1
90°	11.5	9.2	4.6	1.2
92.5°	39.1	33.4	24.2	17.3
95°	66.8	56.4	44.9	40.3
97.5°	94.4	79.4	66.8	59.9
100°	120.9	102.4	92.1	88.6
102.5°	146.2	127.8	117.4	115.1
105°	170.3	153.1	145.0	140.4
107.5°	195.7	179.6	171.5	168.0
110°	222.1	207.2	200.3	195.7



TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	247.5	233.7	225.6	221.0
115°	273.9	260.1	253.2	247.5
117.5°	299.3	286.6	279.7	275.1
120°	322.3	311.9	305.0	300.4
122.5°	346.5	334.9	328.0	324.6
125°	369.5	355.7	348.8	345.3
127.5°	391.3	376.4	367.2	362.6
130°	409.8	393.6	382.1	377.5
132.5°	427.0	409.8	397.1	391.3
135°	440.8	423.6	409.8	405.2
137.5°	455.8	437.4	423.6	417.8
140°	469.6	451.2	437.4	432.8
142.5°	482.3	463.9	451.2	447.7
145°	496.1	478.8	467.3	462.7
147.5°	509.9	493.8	482.3	478.8
150°	522.6	507.6	498.4	494.9
152.5°	534.1	521.4	512.2	511.0
155°	546.7	534.1	527.2	526.0
157.5°	557.1	545.6	539.8	538.7
160°	566.3	557.1	552.5	551.3
162.5°	574.4	567.4	562.8	564.0
165°	581.3	574.4	572.1	573.2
167.5°	587.0	582.4	580.1	581.3
170°	591.6	588.2	587.0	589.3
172.5°	595.1	591.6	592.8	593.9
175°	597.4	595.1	596.2	597.4
177.5°	598.5	596.2	597.4	599.7
180°	598.5	598.5	598.5	598.5

TEST NUMBER: P998380

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.55	14.26	14.64	15.35	16.83	11.04	11.75	12.13	12.84	14.33
	3H	14.35	14.99	15.45	16.08	17.59	12.38	13.01	13.47	14.11	15.61
	4H	14.51	15.11	15.62	16.21	17.72	12.83	13.43	13.94	14.53	16.04
	6H	14.55	15.10	15.67	16.20	17.73	13.13	13.69	14.25	14.78	16.31
	8H	14.52	15.05	15.65	16.17	17.68	13.21	13.74	14.33	14.85	16.37
	12H	14.48	14.98	15.61	16.09	17.63	13.25	13.75	14.37	14.86	16.39
4H	2H	13.57	14.18	14.69	15.27	16.78	11.47	12.07	12.59	13.17	14.68
	3H	14.54	15.04	15.66	16.16	17.69	12.92	13.42	14.04	14.54	16.07
	4H	14.81	15.27	15.94	16.38	17.93	13.45	13.91	14.57	15.02	16.56
	6H	14.93	15.33	16.07	16.46	18.00	13.82	14.21	14.95	15.35	16.88
	8H	14.93	15.30	16.06	16.42	17.97	13.92	14.29	15.06	15.42	16.97
	12H	14.88	15.22	16.03	16.36	17.91	13.97	14.31	15.12	15.45	17.00
8H	4H	14.81	15.18	15.94	16.30	17.85	13.58	13.95	14.71	15.07	16.62
	6H	14.98	15.28	16.13	16.45	18.00	14.01	14.31	15.16	15.48	17.03
	8H	15.01	15.28	16.17	16.42	17.99	14.16	14.42	15.32	15.57	17.14
	12H	14.99	15.22	16.15	16.37	17.97	14.24	14.47	15.40	15.62	17.22
12H	4H	14.76	15.09	15.91	16.23	17.79	13.54	13.88	14.69	15.02	16.57
	6H	14.96	15.22	16.12	16.37	17.94	14.01	14.27	15.17	15.42	16.99
	8H	14.99	15.22	16.15	16.36	17.97	14.16	14.39	15.32	15.53	17.14