

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998386

Luminaire Tested: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998386
REPORT IS A COMBINATION OF REPORTS P984126 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6127.8 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998386

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P998386

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	53	50	43	41	39	31	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	21
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12139	12139	12139
5°	12159	11571	11488
10°	12060	11044	10825
15°	11883	10512	10125
20°	11644	9934	9464
25°	11407	9330	8802
30°	11106	8764	8109
35°	10825	8165	7428
40°	10476	7574	6783
45°	10129	6989	6152
50°	9752	6394	5497
55°	9353	5755	4877
60°	8906	5066	4232
65°	8415	4365	3554
70°	7791	3597	2869
75°	6931	2773	2216
80°	5884	1884	1425
85°	4266	878	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10129 cd/sqm

TEST NUMBER: P998386

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	1.2
10°-20°	203.1	3.3
20°-30°	298.4	4.9
30°-40°	346.6	5.7
40°-50°	346.2	5.6
50°-60°	301.9	4.9
60°-70°	223.1	3.6
70°-80°	126.3	2.1
80°-90°	37.1	0.6
90°-100°	242.6	4.0
100°-110°	820.3	13.4
110°-120°	862.2	14.1
120°-130°	709.0	11.6
130°-140°	569.7	9.3
140°-150°	430.4	7.0
150°-160°	302.6	4.9
160°-170°	178.2	2.9
170°-180°	58.0	0.9
0°-30°	573.7	9.4
0°-40°	920.3	15.0
0°-60°	1568.3	25.6
0°-90°	1954.8	31.9
90°-120°	1925.1	31.4
90°-150°	3634.3	59.3
90°-180°	4173.0	68.1
0°-180°	6127.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	767	764	756	762	760	73
15°	730	726	716	719	715	206
25°	661	655	642	644	642	304
35°	570	563	551	546	543	356
45°	464	459	448	440	436	358
55°	351	347	338	329	325	314
65°	237	232	225	218	215	234
75°	124	122	119	114	116	132
85°	30	30	29	26	26	34
90°	1	16	39	37	38	5
95°	40	99	451	170	131	42
105°	140	212	853	1524	1297	149
115°	248	312	714	1473	1707	245
125°	345	409	686	1193	1385	307
135°	405	483	678	1003	1148	313
145°	463	532	674	837	916	290
155°	526	568	655	741	770	242
165°	573	590	627	665	676	162
175°	597	598	603	611	609	57
180°	598	598	598	598	598	

TEST NUMBER: P998386

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	766.9	766.9	766.9	766.9	766.9
2.5°	771.3	767.6	759.5	766.9	765.4
5°	766.9	763.9	755.8	761.7	760.2
7.5°	761.7	757.3	749.2	755.1	753.6
10°	753.6	748.4	739.6	745.5	743.3
12.5°	742.5	738.1	729.2	732.9	731.5
15°	730.0	725.6	716.0	718.9	715.2
17.5°	714.5	710.1	700.5	704.2	700.5
20°	697.5	693.1	682.8	685.0	682.1
22.5°	680.6	673.9	664.4	664.4	662.9
25°	660.7	654.8	642.2	643.7	642.2
27.5°	638.6	633.4	623.8	621.6	617.9
30°	616.4	610.5	599.5	597.3	594.3
32.5°	592.8	588.4	576.6	572.2	569.2
35°	570.0	562.6	550.8	546.4	542.7
37.5°	544.2	537.5	525.7	520.6	516.9
40°	517.6	511.7	499.9	493.3	490.3
42.5°	491.8	485.9	474.1	466.7	462.3
45°	463.8	458.6	447.6	439.5	436.5
47.5°	436.5	431.4	419.6	411.4	407.0
50°	407.8	404.1	393.8	383.4	379.7
52.5°	379.7	374.6	365.0	356.9	351.7
55°	351.0	346.6	337.7	328.9	325.2
57.5°	322.2	318.5	309.0	300.1	297.2
60°	293.5	290.5	280.2	272.1	269.9
62.5°	265.4	260.3	252.9	245.5	242.6
65°	236.7	232.3	224.9	218.3	214.6
67.5°	207.2	203.5	196.9	191.7	188.8
70°	179.9	177.0	170.3	165.2	162.2
72.5°	151.9	148.9	145.3	140.1	137.9
75°	123.9	122.4	118.7	114.3	115.8
77.5°	98.8	95.9	94.4	92.2	90.0
80°	73.7	73.0	71.5	69.3	67.8
82.5°	50.1	50.1	49.4	46.5	46.5
85°	30.2	29.5	28.8	26.5	25.8
87.5°	13.3	11.8	10.3	8.1	7.4
90°	1.2	15.6	39.1	37.4	38.0
92.5°	17.3	54.6	177.3	81.7	70.2
95°	40.3	99.0	451.2	170.4	131.2
97.5°	59.9	130.6	735.5	341.8	219.8
100°	88.6	160.0	909.3	680.8	412.1
102.5°	115.1	186.4	915.1	1151.0	803.4
105°	140.4	211.8	852.9	1524.5	1297.2
107.5°	168.0	237.1	795.3	1659.8	1629.8
110°	195.7	263.0	756.2	1637.9	1765.7

TEST NUMBER: P998386

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.0	287.8	730.9	1563.6	1763.4
115°	247.5	312.5	713.6	1472.7	1707.0
117.5°	275.1	337.2	704.4	1385.8	1621.8
120°	300.4	361.4	696.4	1308.2	1540.1
122.5°	324.6	386.2	691.8	1247.7	1454.9
125°	345.3	408.6	686.0	1193.1	1384.7
127.5°	362.6	429.9	682.6	1146.4	1319.1
130°	377.5	448.9	680.2	1099.2	1265.0
132.5°	391.3	467.3	679.1	1050.3	1208.6
135°	405.2	483.4	677.9	1002.6	1147.6
137.5°	417.8	497.2	677.9	954.2	1088.9
140°	432.8	509.9	676.8	911.6	1027.9
142.5°	447.7	520.2	676.8	870.8	966.9
145°	462.7	531.8	674.5	837.4	916.2
147.5°	478.8	541.0	671.0	808.0	871.3
150°	494.9	550.2	667.6	782.6	832.2
152.5°	511.0	559.4	661.8	761.4	798.8
155°	526.0	568.0	654.9	740.6	770.0
157.5°	538.7	574.9	648.0	721.1	744.7
160°	551.3	581.8	641.1	701.6	720.5
162.5°	564.0	587.0	635.4	683.1	697.5
165°	573.2	590.4	627.3	665.3	675.6
167.5°	581.3	593.9	620.4	649.2	654.9
170°	589.3	595.6	614.6	634.2	636.5
172.5°	593.9	597.4	607.7	621.0	621.5
175°	597.4	598.0	603.1	610.6	608.9
177.5°	599.7	598.5	598.5	603.1	599.7
180°	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998386

CATALOG NUMBER: SA2XXDIP-B485D1080UB27-4F0-XX-W2A-F4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.95	12.67	13.04	13.76	15.27	12.73	13.45	13.83	14.54	16.05
	3H	13.27	13.92	14.38	15.02	16.55	14.34	14.99	15.45	16.09	17.62
	4H	13.67	14.28	14.79	15.39	16.92	14.93	15.54	16.05	16.65	18.18
	6H	13.88	14.45	15.01	15.55	17.10	15.33	15.89	16.45	17.00	18.54
	8H	13.91	14.44	15.04	15.57	17.10	15.43	15.97	16.56	17.09	18.62
	12H	13.90	14.40	15.03	15.52	17.08	15.47	15.98	16.60	17.10	18.65
4H	2H	12.40	13.01	13.52	14.11	15.64	13.04	13.65	14.17	14.76	16.29
	3H	13.90	14.41	15.03	15.54	17.09	14.81	15.32	15.94	16.45	17.99
	4H	14.40	14.87	15.54	15.99	17.56	15.48	15.95	16.62	17.07	18.64
	6H	14.70	15.10	15.84	16.24	17.80	15.97	16.37	17.11	17.52	19.07
	8H	14.75	15.13	15.89	16.26	17.83	16.11	16.49	17.25	17.62	19.19
	12H	14.74	15.08	15.90	16.23	17.81	16.17	16.51	17.32	17.65	19.23
8H	4H	14.57	14.94	15.71	16.08	17.65	15.56	15.93	16.70	17.07	18.64
	6H	14.94	15.25	16.10	16.43	18.00	16.12	16.43	17.28	17.61	19.18
	8H	15.04	15.32	16.21	16.47	18.06	16.31	16.58	17.48	17.74	19.32
	12H	15.07	15.31	16.24	16.46	18.08	16.40	16.64	17.57	17.79	19.41
12H	4H	14.54	14.88	15.70	16.03	17.61	15.52	15.86	16.67	17.00	18.58
	6H	14.96	15.23	16.13	16.39	17.98	16.11	16.38	17.28	17.54	19.13
	8H	15.07	15.30	16.24	16.46	18.08	16.30	16.54	17.47	17.69	19.32

END OF REPORT