

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998412

Luminaire Tested: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998412
REPORT IS A COMBINATION OF REPORTS P984152 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6010.0 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36		
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	39	38	37	31		
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26		
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23		
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20		
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17		
6	61	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	15		
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	19	17	14		
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15	13		
9	49	37	30	25	45	34	28	24	29	24	20	23	19	17	18	15	14	11		
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15383	15383	15383	15383
5°	15419	16401	15478	13049
10°	15240	17905	15336	10758
15°	14871	18885	15077	9062
20°	14638	17732	14638	7877
25°	14172	15233	14236	7044
30°	13404	11974	13659	6380
35°	12724	8280	12937	5837
40°	11943	6252	12079	5404
45°	10979	5138	11158	4937
50°	10147	4510	10163	4520
55°	9196	3842	9254	4066
60°	8181	3210	8296	3549
65°	7277	2610	7408	3031
70°	6370	2049	6535	2445
75°	5348	1487	5555	1772
80°	4176	942	4471	1051
85°	2740	475	2952	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15901 cd/sqm

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	1.5
10°-20°	269.4	4.5
20°-30°	391.0	6.5
30°-40°	412.2	6.9
40°-50°	364.7	6.1
50°-60°	291.2	4.8
60°-70°	197.8	3.3
70°-80°	101.2	1.7
80°-90°	27.9	0.5
90°-100°	85.5	1.4
100°-110°	271.7	4.5
110°-120°	464.8	7.7
120°-130°	611.3	10.2
130°-140°	686.2	11.4
140°-150°	672.9	11.2
150°-160°	564.5	9.4
160°-170°	374.4	6.2
170°-180°	130.8	2.2
0°-30°	752.9	12.5
0°-40°	1165.1	19.4
0°-60°	1821.1	30.3
0°-90°	2147.9	35.7
90°-120°	822.0	13.7
90°-150°	2792.4	46.5
90°-180°	3862.0	64.3
0°-180°	6010.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	972	1085	976	864	972	92
15°	914	1334	926	640	914	258
25°	821	1111	825	514	821	375
35°	670	605	681	426	670	419
45°	503	364	511	350	503	390
55°	345	256	347	271	345	308
65°	205	158	208	183	205	203
75°	96	78	99	93	96	103
85°	19	20	21	15	19	23
90°	1	40	1	40	1	5
95°	61	72	61	72	61	68
105°	251	259	251	259	251	265
115°	466	466	466	466	466	461
125°	678	681	678	681	678	606
135°	878	888	878	888	878	678
145°	1066	1077	1066	1077	1066	666
155°	1218	1228	1218	1228	1218	561
165°	1325	1327	1325	1327	1325	374
175°	1379	1374	1379	1374	1379	131
180°	1381	1381	1381	1381	1381	

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	977.0	979.2	983.0	983.7	991.2	997.2	1003.9	1003.9	1006.1	1005.4	999.4
5°	972.5	979.2	988.9	997.2	1010.6	1016.6	1025.5	1032.3	1038.2	1042.7	1042.0
7.5°	965.0	977.0	991.2	1006.9	1024.8	1035.3	1047.9	1059.9	1068.1	1075.6	1080.8
10°	952.3	972.5	991.9	1012.8	1036.0	1050.2	1065.1	1080.8	1093.5	1107.7	1121.1
12.5°	935.2	964.3	988.2	1015.8	1044.2	1059.9	1083.8	1095.8	1120.4	1156.3	1166.0
15°	913.5	953.1	975.5	1010.6	1047.9	1060.6	1093.5	1112.9	1163.7	1186.1	1213.0
17.5°	893.3	937.4	967.3	1007.6	1044.2	1068.9	1101.0	1140.6	1183.1	1215.3	1245.1
20°	876.9	919.5	955.3	1000.1	1046.5	1077.8	1111.4	1159.2	1205.6	1238.4	1261.6
22.5°	839.6	894.1	935.9	986.0	1042.0	1085.3	1117.4	1169.7	1219.7	1239.9	1260.1
25°	820.9	867.9	916.5	973.3	1039.0	1090.5	1118.2	1176.4	1220.5	1228.0	1232.4
27.5°	786.5	839.6	896.3	961.3	1038.2	1081.6	1116.7	1169.7	1204.8	1199.6	1186.1
30°	743.9	808.9	871.7	941.9	1027.8	1074.8	1107.7	1156.3	1174.2	1147.3	1123.4
32.5°	712.6	773.8	843.3	924.7	1015.8	1060.6	1092.8	1130.9	1134.6	1086.0	1045.7
35°	670.0	738.0	816.4	902.3	995.7	1036.0	1065.9	1089.0	1071.1	1003.1	955.3
37.5°	631.9	699.1	782.8	870.2	968.0	1007.6	1031.5	1035.3	991.2	931.4	861.2
40°	590.1	659.5	746.9	838.8	937.4	971.8	986.7	975.5	912.0	842.5	761.1
42.5°	548.2	617.0	711.1	805.2	898.6	927.7	933.7	903.0	825.4	743.9	649.8
45°	502.7	574.4	668.5	763.4	853.7	870.2	870.9	826.9	735.0	649.8	562.4
47.5°	465.3	531.8	625.2	720.0	796.2	807.4	803.0	752.2	652.1	556.5	480.3
50°	424.3	487.7	580.4	673.7	738.7	741.7	730.5	658.0	560.2	472.8	412.3
52.5°	380.2	444.4	529.6	619.2	677.5	673.0	651.3	573.6	481.8	409.3	363.0
55°	345.1	401.9	481.8	569.2	610.2	597.5	573.6	494.5	422.0	360.8	320.4
57.5°	306.2	356.3	434.7	510.9	534.8	522.9	499.0	425.0	357.8	311.5	284.6
60°	269.6	315.2	383.9	447.4	466.1	453.4	425.8	359.3	310.7	271.9	251.7
62.5°	236.0	275.6	333.1	391.4	398.9	386.2	362.3	308.5	266.7	236.0	221.1
65°	204.7	242.0	288.3	332.4	339.1	325.7	301.0	262.2	227.1	207.6	193.5
67.5°	174.0	203.9	245.0	277.1	280.8	268.1	248.0	216.6	194.9	174.0	163.6
70°	147.1	169.6	201.7	227.8	229.3	217.4	206.9	178.5	162.1	147.1	138.9
72.5°	121.0	136.7	161.3	180.8	181.5	174.0	164.3	146.4	132.2	121.8	113.5
75°	95.6	109.1	124.0	141.2	140.4	134.4	127.0	115.8	103.8	97.1	93.4
77.5°	73.2	81.4	93.4	104.6	104.6	101.6	97.1	88.9	81.4	74.7	71.0
80°	52.3	57.5	67.2	71.0	72.5	71.7	68.0	62.0	59.0	53.8	52.3
82.5°	33.6	37.3	41.8	45.6	47.8	46.3	45.6	42.6	38.1	36.6	35.1
85°	19.4	20.9	23.2	25.4	26.1	25.4	26.9	24.6	22.4	22.4	21.7
87.5°	8.2	9.0	10.5	10.5	11.2	11.2	10.5	11.2	11.2	10.5	9.7
90°	1.2	4.3	7.4	10.5	13.6	15.2	18.0	23.7	29.4	35.1	40.8
92.5°	25.6	27.7	29.8	31.9	34.0	35.0	35.1	35.4	35.6	35.9	36.1
95°	60.6	63.2	65.8	68.4	71.0	72.3	72.6	73.1	73.6	74.1	74.6
97.5°	101.4	103.7	106.1	108.4	110.7	111.9	112.4	113.5	114.5	115.6	116.6
100°	148.0	150.1	152.2	154.3	156.4	157.4	157.8	158.6	159.3	160.1	160.9
102.5°	197.0	198.6	200.1	201.7	203.2	204.0	204.5	205.6	206.6	207.7	208.7
105°	250.6	251.4	252.2	252.9	253.7	254.1	254.4	254.9	255.4	256.0	256.5
107.5°	304.3	305.3	306.3	307.4	308.4	308.9	308.9	308.9	308.9	308.9	308.9
110°	355.5	357.1	358.6	360.2	361.7	362.5	362.5	362.5	362.5	362.5	362.5

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	411.5	413.1	414.6	416.2	417.7	418.5	418.4	418.1	417.8	417.6	417.3
115°	466.3	467.9	469.4	471.0	472.5	473.3	473.0	472.5	472.0	471.5	471.0
117.5°	521.1	523.2	525.2	527.3	529.4	530.4	529.8	528.5	527.2	525.9	524.6
120°	575.9	578.0	580.0	582.1	584.2	585.2	584.2	582.1	580.0	578.0	575.9
122.5°	626.0	628.6	631.2	633.7	636.3	637.6	637.0	635.7	634.4	633.1	631.8
125°	678.4	680.7	683.1	685.4	687.7	688.9	688.5	687.7	687.0	686.2	685.4
127.5°	729.7	732.6	735.4	738.3	741.2	742.6	742.1	741.0	740.0	738.9	737.9
130°	777.5	780.9	784.3	787.6	791.0	792.7	792.4	791.9	791.4	790.9	790.4
132.5°	831.2	833.8	836.4	838.9	841.5	842.8	842.9	843.2	843.5	843.7	844.0
135°	877.8	880.6	883.5	886.3	889.2	890.6	890.9	891.4	891.9	892.4	892.9
137.5°	929.1	931.4	933.8	936.1	938.4	939.6	939.9	940.4	940.9	941.4	941.9
140°	974.5	976.8	979.2	981.5	983.8	985.0	985.7	987.0	988.3	989.6	990.9
142.5°	1021.2	1023.5	1025.9	1028.2	1030.5	1031.7	1032.1	1032.9	1033.6	1034.4	1035.2
145°	1065.5	1067.3	1069.1	1070.9	1072.7	1073.6	1074.4	1075.9	1077.5	1079.0	1080.6
147.5°	1105.1	1107.4	1109.8	1112.1	1114.4	1115.6	1116.1	1117.2	1118.2	1119.3	1120.3
150°	1145.9	1147.5	1149.0	1150.6	1152.1	1152.9	1153.4	1154.5	1155.5	1156.6	1157.6
152.5°	1182.0	1183.6	1185.1	1186.7	1188.2	1189.0	1189.7	1191.0	1192.3	1193.6	1194.9
155°	1218.2	1219.0	1219.8	1220.5	1221.3	1221.7	1222.1	1222.9	1223.6	1224.4	1225.2
157.5°	1249.7	1250.2	1250.7	1251.2	1251.7	1252.0	1252.3	1252.8	1253.3	1253.8	1254.3
160°	1277.6	1278.1	1278.7	1279.2	1279.7	1280.0	1280.1	1280.4	1280.6	1280.9	1281.1
162.5°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.4	1303.7	1303.9	1304.2	1304.4
165°	1325.4	1325.2	1324.9	1324.7	1324.4	1324.3	1324.3	1324.3	1324.3	1324.3	1324.3
167.5°	1345.2	1344.4	1343.6	1342.9	1342.1	1341.7	1341.7	1341.7	1341.7	1341.7	1341.7
170°	1360.4	1359.6	1358.8	1358.1	1357.3	1356.9	1356.8	1356.5	1356.2	1356.0	1355.7
172.5°	1370.9	1370.1	1369.3	1368.6	1367.8	1367.4	1367.3	1367.0	1366.7	1366.5	1366.2
175°	1379.0	1378.2	1377.4	1376.7	1375.9	1375.5	1375.2	1374.7	1374.2	1373.7	1373.2
177.5°	1383.7	1382.9	1382.1	1381.4	1380.6	1380.2	1379.9	1379.4	1378.9	1378.4	1377.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1009.9	1010.6	1012.1	1019.6	1023.3	1024.0	1021.1	1027.8	1030.0	1027.8	1026.3
5°	1057.7	1062.1	1071.1	1080.8	1080.1	1080.8	1085.3	1089.8	1091.3	1085.3	1087.5
7.5°	1099.5	1108.4	1118.2	1133.1	1133.1	1140.6	1143.6	1147.3	1156.3	1151.8	1150.3
10°	1147.3	1159.2	1177.2	1201.1	1201.8	1209.3	1216.8	1228.7	1232.4	1229.5	1230.9
12.5°	1207.0	1230.2	1231.7	1257.8	1269.8	1271.3	1283.2	1281.0	1288.5	1288.5	1301.2
15°	1233.2	1269.0	1289.2	1314.6	1322.1	1313.1	1322.8	1333.3	1334.0	1334.0	1333.3
17.5°	1280.2	1294.4	1314.6	1328.0	1331.0	1331.0	1331.8	1336.3	1333.3	1327.3	1331.8
20°	1290.0	1295.9	1303.4	1301.9	1303.4	1295.9	1288.5	1281.0	1281.7	1278.0	1289.2
22.5°	1272.0	1270.5	1253.4	1242.2	1242.2	1227.2	1213.0	1206.3	1199.6	1201.8	1205.6
25°	1227.2	1204.1	1183.1	1166.7	1163.0	1139.1	1119.7	1113.7	1102.5	1111.4	1112.9
27.5°	1155.5	1129.4	1095.8	1081.6	1062.1	1052.4	1039.0	1021.1	997.9	1011.3	1009.1
30°	1078.6	1039.7	1012.1	977.7	947.1	944.9	919.5	889.6	877.6	877.6	884.4
32.5°	992.7	941.1	900.8	852.3	822.4	809.7	779.1	749.2	755.9	733.5	741.7
35°	892.6	824.6	773.8	726.8	704.4	689.4	649.8	633.4	615.5	605.0	624.4
37.5°	797.0	718.6	653.6	602.0	593.8	566.9	540.0	529.6	519.1	523.6	522.9
40°	680.5	611.0	552.7	512.4	498.2	485.5	467.6	454.9	448.2	451.9	452.6
42.5°	575.1	516.9	473.6	445.2	433.2	424.3	415.3	404.8	402.6	402.6	405.6
45°	493.7	445.9	416.8	393.6	386.9	380.2	373.5	369.0	367.5	364.5	366.7
47.5°	428.7	390.6	372.7	355.5	348.1	346.6	340.6	338.4	335.4	334.6	335.4
50°	374.2	350.3	333.9	324.2	318.9	316.7	313.7	309.2	307.7	311.5	310.0
52.5°	336.1	313.7	304.7	295.0	292.1	289.1	284.6	285.3	284.6	283.1	283.1
55°	298.0	283.8	274.9	267.4	266.7	263.7	259.9	258.4	257.7	256.2	258.4
57.5°	267.4	256.2	248.0	241.3	238.3	238.3	234.5	231.5	231.5	230.8	231.5
60°	236.8	225.6	220.3	213.6	211.4	210.6	208.4	206.9	204.7	204.7	204.7
62.5°	208.4	199.4	193.5	187.5	188.2	184.5	181.5	180.0	180.0	180.8	180.8
65°	181.5	175.5	168.1	162.8	161.3	160.6	159.1	158.3	156.1	157.6	157.6
67.5°	156.9	148.6	144.2	141.9	139.7	138.9	137.4	135.9	135.2	134.4	135.9
70°	132.2	125.5	121.8	120.3	118.0	117.3	116.5	114.3	115.0	115.8	116.5
72.5°	109.8	103.8	103.1	98.6	98.6	98.6	95.6	97.1	96.4	94.9	96.4
75°	86.6	83.7	82.2	79.9	80.7	79.9	79.2	76.9	76.9	77.7	78.4
77.5°	68.7	65.7	65.0	62.7	61.2	62.7	61.2	60.5	60.5	61.2	61.2
80°	50.8	49.3	47.1	47.1	47.1	46.3	46.3	46.3	45.6	44.8	45.6
82.5°	33.6	33.6	32.9	32.1	32.9	31.4	32.1	32.1	32.1	32.1	32.1
85°	21.7	20.9	20.9	20.2	20.2	20.2	20.9	19.4	19.4	20.2	20.2
87.5°	9.7	9.7	9.7	10.5	9.7	9.7	9.7	10.5	9.7	9.7	9.7
90°	40.3	39.8	39.3	38.8	38.5	38.6	38.9	39.1	39.4	39.6	39.4
92.5°	36.4	36.6	36.9	37.2	37.3	37.3	37.3	37.3	37.3	37.3	37.3
95°	74.6	74.6	74.6	74.6	74.6	74.3	73.8	73.3	72.8	72.3	72.8
97.5°	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6
100°	160.9	160.9	160.9	160.9	160.9	160.8	160.5	160.2	160.0	159.7	160.0
102.5°	208.9	209.2	209.4	209.7	209.8	209.7	209.4	209.2	208.9	208.7	208.9
105°	257.0	257.5	258.0	258.5	258.8	258.8	258.8	258.8	258.8	258.8	258.8
107.5°	309.2	309.4	309.7	310.0	310.1	309.5	308.2	306.9	305.6	304.3	305.6
110°	362.5	362.5	362.5	362.5	362.5	362.1	361.3	360.6	359.8	359.0	359.8

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	416.5	415.7	415.0	414.2	413.8	413.5	413.0	412.5	412.0	411.5	412.0
115°	470.7	470.5	470.2	469.9	469.8	469.4	468.6	467.9	467.1	466.3	467.1
117.5°	523.8	523.0	522.3	521.5	521.1	520.7	519.9	519.2	518.4	517.6	518.4
120°	575.9	575.9	575.9	575.9	575.9	575.5	574.7	574.0	573.2	572.4	573.2
122.5°	631.0	630.2	629.5	628.7	628.3	628.0	627.5	627.0	626.5	626.0	626.5
125°	684.6	683.8	683.1	682.3	681.9	681.8	681.5	681.3	681.0	680.8	681.0
127.5°	736.9	735.8	734.8	733.7	733.2	732.8	732.0	731.3	730.5	729.7	730.5
130°	789.9	789.3	788.8	788.3	788.0	787.5	786.5	785.4	784.4	783.4	784.4
132.5°	842.7	841.4	840.1	838.8	838.2	837.8	837.0	836.3	835.5	834.7	835.5
135°	892.7	892.4	892.2	891.9	891.8	891.4	890.6	889.9	889.1	888.3	889.1
137.5°	941.6	941.4	941.1	940.8	940.7	940.2	939.2	938.1	937.1	936.1	937.1
140°	990.9	990.9	990.9	990.9	990.9	990.4	989.3	988.3	987.2	986.2	987.2
142.5°	1035.4	1035.7	1035.9	1036.2	1036.3	1035.8	1034.8	1033.7	1032.7	1031.7	1032.7
145°	1080.9	1081.1	1081.4	1081.7	1081.8	1081.3	1080.2	1079.2	1078.1	1077.1	1078.1
147.5°	1120.8	1121.3	1121.8	1122.3	1122.6	1122.1	1121.0	1120.0	1118.9	1117.9	1118.9
150°	1158.4	1159.2	1159.9	1160.7	1161.1	1160.7	1159.9	1159.2	1158.4	1157.6	1158.4
152.5°	1195.9	1196.9	1198.0	1199.0	1199.5	1199.0	1198.0	1196.9	1195.9	1194.9	1195.9
155°	1226.5	1227.8	1229.1	1230.4	1231.0	1230.6	1229.8	1229.1	1228.3	1227.5	1228.3
157.5°	1256.1	1257.9	1259.8	1261.6	1262.5	1261.8	1260.5	1259.2	1257.9	1256.6	1257.9
160°	1282.7	1284.2	1285.8	1287.3	1288.1	1287.6	1286.6	1285.5	1284.5	1283.5	1284.5
162.5°	1306.2	1308.0	1309.9	1311.7	1312.6	1312.0	1310.7	1309.4	1308.1	1306.8	1308.1
165°	1326.1	1327.9	1329.7	1331.5	1332.4	1331.8	1330.5	1329.2	1327.9	1326.6	1327.9
167.5°	1343.5	1345.3	1347.2	1349.0	1349.9	1349.3	1348.0	1346.7	1345.4	1344.1	1345.4
170°	1357.5	1359.3	1361.2	1363.0	1363.9	1363.1	1361.6	1360.0	1358.5	1356.9	1358.5
172.5°	1368.0	1369.8	1371.7	1373.5	1374.4	1373.6	1372.1	1370.5	1369.0	1367.4	1369.0
175°	1375.0	1376.8	1378.7	1380.5	1381.4	1380.6	1379.1	1377.5	1376.0	1374.4	1376.0
177.5°	1379.5	1381.0	1382.6	1384.1	1384.9	1384.1	1382.6	1381.0	1379.5	1377.9	1379.5
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1030.0	1024.8	1020.3	1021.1	1024.8	1021.8	1014.3	1004.6	1000.9	996.4	1000.9
5°	1092.0	1087.5	1078.6	1079.3	1077.1	1074.1	1062.1	1047.2	1047.2	1035.3	1033.8
7.5°	1153.3	1146.5	1140.6	1139.1	1130.9	1124.9	1114.4	1093.5	1085.3	1071.1	1062.9
10°	1222.0	1216.8	1210.0	1201.8	1197.3	1186.9	1169.7	1139.1	1124.1	1104.7	1090.5
12.5°	1291.4	1290.7	1275.8	1259.3	1258.6	1242.2	1230.2	1189.1	1169.0	1142.8	1109.2
15°	1335.5	1331.8	1323.6	1315.4	1317.6	1299.7	1272.8	1224.2	1210.8	1179.4	1143.6
17.5°	1334.8	1334.8	1332.5	1331.0	1328.8	1323.6	1308.6	1276.5	1254.8	1215.3	1181.6
20°	1292.2	1301.9	1304.1	1303.4	1310.9	1314.6	1313.9	1293.7	1276.5	1241.4	1207.0
22.5°	1207.0	1229.5	1239.2	1245.1	1260.8	1269.0	1288.5	1281.0	1276.5	1250.4	1221.2
25°	1127.9	1135.3	1164.5	1166.0	1187.6	1207.8	1227.2	1239.9	1256.3	1246.6	1222.0
27.5°	1025.5	1042.7	1063.6	1079.3	1083.8	1124.9	1157.0	1180.9	1218.2	1221.2	1213.0
30°	909.8	918.0	952.3	973.3	997.2	1027.0	1073.3	1114.4	1148.0	1178.7	1189.1
32.5°	768.6	802.2	822.4	847.8	868.7	921.7	978.5	1031.5	1070.4	1121.9	1144.3
35°	639.4	665.5	699.9	710.3	748.4	793.2	867.2	935.2	994.2	1046.5	1092.0
37.5°	532.6	553.5	590.1	606.5	628.9	686.4	748.4	832.8	903.8	968.0	1024.8
40°	459.4	475.0	502.7	507.9	526.6	578.9	628.9	708.1	802.2	888.9	950.8
42.5°	409.3	416.8	435.5	442.2	454.1	489.2	534.1	608.8	696.1	785.8	873.2
45°	373.5	378.7	389.9	395.9	410.8	426.5	463.1	522.9	591.6	682.0	776.1
47.5°	341.3	348.1	352.6	356.3	364.5	381.7	405.6	449.7	515.4	598.3	689.4
50°	314.5	316.7	324.9	325.7	330.9	342.1	364.5	391.4	443.7	510.9	599.0
52.5°	287.6	289.8	295.0	300.3	302.5	311.5	326.4	348.8	387.7	440.7	519.1
55°	260.7	263.7	268.9	272.6	274.9	282.3	291.3	313.0	343.6	380.9	445.2
57.5°	233.8	240.5	242.0	244.2	248.0	256.2	264.4	277.1	301.0	335.4	382.4
60°	208.4	210.6	215.9	218.1	221.8	226.3	236.8	246.5	263.7	290.6	333.1
62.5°	182.3	187.5	189.7	192.0	194.9	200.2	206.9	217.4	232.3	254.0	287.6
65°	159.8	160.6	165.1	168.1	171.0	174.8	181.5	191.2	200.2	220.3	245.0
67.5°	138.2	139.7	141.2	144.2	147.9	151.6	157.6	162.8	174.0	187.5	206.9
70°	117.3	117.3	121.0	123.2	122.5	127.0	131.5	137.4	145.7	158.3	174.0
72.5°	98.6	97.8	100.8	101.6	103.1	106.1	109.1	115.0	119.5	129.2	141.2
75°	78.4	79.9	81.4	81.4	83.7	85.9	88.9	91.9	97.1	103.1	112.0
77.5°	62.0	62.0	63.5	64.2	66.5	65.7	68.7	71.7	75.4	80.7	87.4
80°	45.6	47.1	47.1	47.1	47.8	48.6	51.5	53.8	56.0	59.8	62.7
82.5°	32.1	32.1	33.6	33.6	33.6	35.1	35.1	35.9	37.3	39.6	41.8
85°	20.2	20.2	20.2	20.9	20.2	20.9	22.4	21.7	22.4	23.9	23.9
87.5°	9.7	9.7	9.7	9.7	9.7	10.5	9.7	10.5	11.2	11.2	11.2
90°	39.1	38.9	38.6	38.5	38.8	39.3	39.8	40.3	40.8	35.1	29.4
92.5°	37.3	37.3	37.3	37.3	37.2	36.9	36.6	36.4	36.1	35.9	35.6
95°	73.3	73.8	74.3	74.6	74.6	74.6	74.6	74.6	74.6	74.1	73.6
97.5°	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	115.6	114.5
100°	160.2	160.5	160.8	160.9	160.9	160.9	160.9	160.9	160.9	160.1	159.3
102.5°	209.2	209.4	209.7	209.8	209.7	209.4	209.2	208.9	208.7	207.7	206.6
105°	258.8	258.8	258.8	258.8	258.5	258.0	257.5	257.0	256.5	256.0	255.4
107.5°	306.9	308.2	309.5	310.1	310.0	309.7	309.4	309.2	308.9	308.9	308.9
110°	360.6	361.3	362.1	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	412.5	413.0	413.5	413.8	414.2	415.0	415.7	416.5	417.3	417.6	417.8
115°	467.9	468.6	469.4	469.8	469.9	470.2	470.5	470.7	471.0	471.5	472.0
117.5°	519.2	519.9	520.7	521.1	521.5	522.3	523.0	523.8	524.6	525.9	527.2
120°	574.0	574.7	575.5	575.9	575.9	575.9	575.9	575.9	575.9	578.0	580.0
122.5°	627.0	627.5	628.0	628.3	628.7	629.5	630.2	631.0	631.8	633.1	634.4
125°	681.3	681.5	681.8	681.9	682.3	683.1	683.8	684.6	685.4	686.2	687.0
127.5°	731.3	732.0	732.8	733.2	733.7	734.8	735.8	736.9	737.9	738.9	740.0
130°	785.4	786.5	787.5	788.0	788.3	788.8	789.3	789.9	790.4	790.9	791.4
132.5°	836.3	837.0	837.8	838.2	838.8	840.1	841.4	842.7	844.0	843.7	843.5
135°	889.9	890.6	891.4	891.8	891.9	892.2	892.4	892.7	892.9	892.4	891.9
137.5°	938.1	939.2	940.2	940.7	940.8	941.1	941.4	941.6	941.9	941.4	940.9
140°	988.3	989.3	990.4	990.9	990.9	990.9	990.9	990.9	990.9	989.6	988.3
142.5°	1033.7	1034.8	1035.8	1036.3	1036.2	1035.9	1035.7	1035.4	1035.2	1034.4	1033.6
145°	1079.2	1080.2	1081.3	1081.8	1081.7	1081.4	1081.1	1080.9	1080.6	1079.0	1077.5
147.5°	1120.0	1121.0	1122.1	1122.6	1122.3	1121.8	1121.3	1120.8	1120.3	1119.3	1118.2
150°	1159.2	1159.9	1160.7	1161.1	1160.7	1159.9	1159.2	1158.4	1157.6	1156.6	1155.5
152.5°	1196.9	1198.0	1199.0	1199.5	1199.0	1198.0	1196.9	1195.9	1194.9	1193.6	1192.3
155°	1229.1	1229.8	1230.6	1231.0	1230.4	1229.1	1227.8	1226.5	1225.2	1224.4	1223.6
157.5°	1259.2	1260.5	1261.8	1262.5	1261.6	1259.8	1257.9	1256.1	1254.3	1253.8	1253.3
160°	1285.5	1286.6	1287.6	1288.1	1287.3	1285.8	1284.2	1282.7	1281.1	1280.9	1280.6
162.5°	1309.4	1310.7	1312.0	1312.6	1311.7	1309.9	1308.0	1306.2	1304.4	1304.2	1303.9
165°	1329.2	1330.5	1331.8	1332.4	1331.5	1329.7	1327.9	1326.1	1324.3	1324.3	1324.3
167.5°	1346.7	1348.0	1349.3	1349.9	1349.0	1347.2	1345.3	1343.5	1341.7	1341.7	1341.7
170°	1360.0	1361.6	1363.1	1363.9	1363.0	1361.2	1359.3	1357.5	1355.7	1356.0	1356.2
172.5°	1370.5	1372.1	1373.6	1374.4	1373.5	1371.7	1369.8	1368.0	1366.2	1366.5	1366.7
175°	1377.5	1379.1	1380.6	1381.4	1380.5	1378.7	1376.8	1375.0	1373.2	1373.7	1374.2
177.5°	1381.0	1382.6	1384.1	1384.9	1384.1	1382.6	1381.0	1379.5	1377.9	1378.4	1378.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	997.2	993.4	991.2	992.7	988.2	977.0	977.0	980.7	976.2	971.8	965.0
5°	1024.8	1017.3	1012.8	1012.1	1001.6	983.7	980.0	976.2	966.5	956.1	944.9
7.5°	1051.7	1038.2	1030.8	1025.5	1010.6	987.4	977.7	969.5	953.8	938.1	924.0
10°	1074.1	1054.7	1045.7	1037.5	1018.1	988.9	973.3	958.3	938.1	918.0	900.1
12.5°	1092.0	1069.6	1058.4	1046.5	1022.6	984.5	965.0	941.1	921.0	894.1	876.2
15°	1121.9	1075.6	1065.1	1053.9	1029.3	977.0	953.1	926.2	898.6	862.7	843.3
17.5°	1145.8	1083.8	1083.1	1059.2	1027.0	974.0	937.4	902.3	872.4	836.6	805.9
20°	1160.0	1096.5	1084.5	1059.9	1019.6	953.8	915.7	876.9	844.8	801.5	770.8
22.5°	1171.9	1114.4	1083.1	1053.2	1003.9	947.1	891.1	854.5	810.4	763.4	734.2
25°	1176.4	1118.2	1085.3	1050.9	992.7	927.7	864.2	824.6	775.3	732.7	693.2
27.5°	1177.2	1117.4	1077.1	1041.2	977.0	902.3	837.3	795.5	741.0	691.7	652.1
30°	1169.7	1109.2	1072.6	1033.8	962.1	879.1	804.4	758.1	699.9	650.6	609.5
32.5°	1147.3	1092.8	1062.9	1020.3	942.6	847.0	773.1	721.5	660.3	611.7	572.2
35°	1109.9	1072.6	1039.7	1000.1	917.2	817.1	741.7	681.2	619.2	572.9	535.6
37.5°	1063.6	1043.5	1012.8	974.0	888.1	790.3	706.6	639.4	577.4	532.6	496.0
40°	1000.9	1006.1	976.2	941.1	853.7	753.7	661.0	596.8	538.5	496.7	460.9
42.5°	932.9	954.6	937.4	903.8	815.7	713.3	627.4	556.5	499.7	456.4	426.5
45°	859.7	897.1	886.6	862.0	776.1	670.7	579.6	510.9	460.9	419.0	392.9
47.5°	779.8	832.8	832.8	814.9	732.0	628.2	538.5	468.3	419.0	389.2	363.8
50°	698.4	758.1	767.8	755.9	682.7	579.6	488.5	425.0	382.4	353.3	334.6
52.5°	613.2	682.7	700.6	694.6	630.4	533.3	447.4	385.4	346.6	321.2	304.7
55°	531.8	612.5	631.9	634.1	574.4	482.5	401.9	347.3	310.0	292.8	278.6
57.5°	454.9	532.6	554.2	558.0	517.6	436.2	359.3	311.5	277.9	263.7	252.5
60°	389.2	454.1	482.5	490.7	455.6	382.4	319.7	273.4	248.0	234.5	224.1
62.5°	335.4	387.7	417.5	419.8	404.1	335.4	278.6	239.8	218.1	206.2	200.9
65°	283.1	330.1	348.1	357.0	344.3	290.6	240.5	208.4	191.2	180.8	175.5
67.5°	241.3	271.1	286.1	298.0	285.3	245.0	204.7	178.5	165.8	155.4	152.4
70°	197.9	222.6	233.8	245.7	234.5	203.9	174.8	150.9	139.7	131.5	127.7
72.5°	158.3	177.8	188.2	195.7	189.0	163.6	139.7	123.2	115.0	109.1	106.8
75°	125.5	138.9	144.9	150.1	147.1	127.7	112.8	99.3	91.9	86.6	85.2
77.5°	95.6	105.3	112.0	113.5	109.8	97.1	84.4	76.2	70.2	67.2	65.7
80°	68.0	73.9	77.7	79.9	76.2	71.0	62.0	56.0	50.8	47.1	46.3
82.5°	45.6	48.6	51.5	50.8	49.3	44.8	39.6	36.6	34.4	31.4	31.4
85°	26.1	26.9	28.4	29.1	28.4	25.4	22.4	20.9	19.4	17.2	17.2
87.5°	11.2	12.0	12.0	12.7	11.2	11.2	9.7	8.2	8.2	7.5	6.7
90°	23.7	18.0	15.2	13.6	10.5	7.4	4.3	1.2	4.3	7.4	10.5
92.5°	35.4	35.1	35.0	34.0	31.9	29.8	27.7	25.6	27.7	29.8	31.9
95°	73.1	72.6	72.3	71.0	68.4	65.8	63.2	60.6	63.2	65.8	68.4
97.5°	113.5	112.4	111.9	110.7	108.4	106.1	103.7	101.4	103.7	106.1	108.4
100°	158.6	157.8	157.4	156.4	154.3	152.2	150.1	148.0	150.1	152.2	154.3
102.5°	205.6	204.5	204.0	203.2	201.7	200.1	198.6	197.0	198.6	200.1	201.7
105°	254.9	254.4	254.1	253.7	252.9	252.2	251.4	250.6	251.4	252.2	252.9
107.5°	308.9	308.9	308.9	308.4	307.4	306.3	305.3	304.3	305.3	306.3	307.4
110°	362.5	362.5	362.5	361.7	360.2	358.6	357.1	355.5	357.1	358.6	360.2

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	418.1	418.4	418.5	417.7	416.2	414.6	413.1	411.5	413.1	414.6	416.2
115°	472.5	473.0	473.3	472.5	471.0	469.4	467.9	466.3	467.9	469.4	471.0
117.5°	528.5	529.8	530.4	529.4	527.3	525.2	523.2	521.1	523.2	525.2	527.3
120°	582.1	584.2	585.2	584.2	582.1	580.0	578.0	575.9	578.0	580.0	582.1
122.5°	635.7	637.0	637.6	636.3	633.7	631.2	628.6	626.0	628.6	631.2	633.7
125°	687.7	688.5	688.9	687.7	685.4	683.1	680.7	678.4	680.7	683.1	685.4
127.5°	741.0	742.1	742.6	741.2	738.3	735.4	732.6	729.7	732.6	735.4	738.3
130°	791.9	792.4	792.7	791.0	787.6	784.3	780.9	777.5	780.9	784.3	787.6
132.5°	843.2	842.9	842.8	841.5	838.9	836.4	833.8	831.2	833.8	836.4	838.9
135°	891.4	890.9	890.6	889.2	886.3	883.5	880.6	877.8	880.6	883.5	886.3
137.5°	940.4	939.9	939.6	938.4	936.1	933.8	931.4	929.1	931.4	933.8	936.1
140°	987.0	985.7	985.0	983.8	981.5	979.2	976.8	974.5	976.8	979.2	981.5
142.5°	1032.9	1032.1	1031.7	1030.5	1028.2	1025.9	1023.5	1021.2	1023.5	1025.9	1028.2
145°	1075.9	1074.4	1073.6	1072.7	1070.9	1069.1	1067.3	1065.5	1067.3	1069.1	1070.9
147.5°	1117.2	1116.1	1115.6	1114.4	1112.1	1109.8	1107.4	1105.1	1107.4	1109.8	1112.1
150°	1154.5	1153.4	1152.9	1152.1	1150.6	1149.0	1147.5	1145.9	1147.5	1149.0	1150.6
152.5°	1191.0	1189.7	1189.0	1188.2	1186.7	1185.1	1183.6	1182.0	1183.6	1185.1	1186.7
155°	1222.9	1222.1	1221.7	1221.3	1220.5	1219.8	1219.0	1218.2	1219.0	1219.8	1220.5
157.5°	1252.8	1252.3	1252.0	1251.7	1251.2	1250.7	1250.2	1249.7	1250.2	1250.7	1251.2
160°	1280.4	1280.1	1280.0	1279.7	1279.2	1278.7	1278.1	1277.6	1278.1	1278.7	1279.2
162.5°	1303.7	1303.4	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3
165°	1324.3	1324.3	1324.3	1324.4	1324.7	1324.9	1325.2	1325.4	1325.2	1324.9	1324.7
167.5°	1341.7	1341.7	1341.7	1342.1	1342.9	1343.6	1344.4	1345.2	1344.4	1343.6	1342.9
170°	1356.5	1356.8	1356.9	1357.3	1358.1	1358.8	1359.6	1360.4	1359.6	1358.8	1358.1
172.5°	1367.0	1367.3	1367.4	1367.8	1368.6	1369.3	1370.1	1370.9	1370.1	1369.3	1368.6
175°	1374.7	1375.2	1375.5	1375.9	1376.7	1377.4	1378.2	1379.0	1378.2	1377.4	1376.7
177.5°	1379.4	1379.9	1380.2	1380.6	1381.4	1382.1	1382.9	1383.7	1382.9	1382.1	1381.4
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	961.3	965.0	964.3	956.8	948.6	941.9	929.2	930.7	926.2	926.9	931.4
5°	937.4	937.4	934.4	924.0	910.5	903.0	888.9	885.1	876.2	875.4	874.7
7.5°	912.0	908.3	904.5	889.6	873.2	861.2	841.8	837.3	828.3	822.4	819.4
10°	882.1	876.9	869.4	852.3	832.1	817.1	797.0	791.0	773.8	766.4	761.9
12.5°	849.3	846.3	834.3	820.1	787.3	770.8	741.7	747.7	730.5	715.6	713.3
15°	816.4	805.2	798.5	775.3	735.7	728.3	705.1	693.2	677.5	665.5	665.5
17.5°	784.3	767.1	752.2	727.5	698.4	677.5	660.3	654.3	634.9	622.9	620.7
20°	741.7	722.3	718.6	683.4	663.3	640.1	623.7	608.8	594.6	589.3	585.6
22.5°	701.4	679.0	673.0	643.1	622.9	599.8	583.4	572.9	562.4	558.7	552.0
25°	658.0	644.6	635.6	603.5	581.1	559.5	548.2	540.8	531.1	530.3	525.8
27.5°	616.2	603.5	594.6	563.9	547.5	527.3	518.4	510.2	504.9	502.7	500.4
30°	580.4	566.2	555.7	533.3	513.1	496.7	489.2	484.0	481.0	477.3	476.5
32.5°	540.8	532.6	518.4	501.2	485.5	469.8	465.3	461.6	457.1	455.6	454.9
35°	507.2	496.0	487.0	467.6	460.9	447.4	442.2	439.2	433.2	431.7	430.2
37.5°	474.3	463.8	454.1	442.2	429.5	422.0	419.0	414.5	411.6	412.3	410.8
40°	441.4	433.2	425.8	413.1	405.6	401.9	395.9	391.4	389.9	390.6	389.9
42.5°	409.3	401.9	397.4	387.7	380.2	376.5	372.7	368.2	370.5	370.5	372.7
45°	380.2	373.5	370.5	363.0	358.5	352.6	348.8	348.1	351.1	350.3	350.3
47.5°	350.3	348.1	344.3	337.6	331.6	327.9	327.2	327.2	330.1	331.6	330.9
50°	327.2	322.7	318.2	313.0	308.5	307.0	304.7	306.2	309.2	309.2	310.7
52.5°	298.0	295.0	293.5	289.1	286.1	286.1	286.1	286.8	289.1	291.3	290.6
55°	272.6	270.4	268.9	266.7	262.9	263.7	262.9	264.4	266.7	268.9	270.4
57.5°	245.7	245.0	243.5	239.8	239.8	239.0	241.3	242.0	245.7	247.2	249.5
60°	221.8	219.6	219.6	216.6	216.6	216.6	218.9	221.1	224.1	224.8	226.3
62.5°	196.4	196.4	195.7	193.5	193.5	195.7	196.4	199.4	200.9	200.9	203.2
65°	172.5	171.8	171.0	171.8	172.5	172.5	174.8	176.3	177.8	178.5	179.3
67.5°	148.6	147.9	149.4	148.6	150.1	153.1	152.4	154.6	156.9	156.9	157.6
70°	126.2	127.7	127.0	128.5	127.7	129.2	131.5	132.2	132.2	133.0	135.2
72.5°	105.3	105.3	105.3	104.6	105.3	106.8	108.3	109.1	110.5	111.3	113.5
75°	85.2	85.2	83.7	85.2	85.2	86.6	88.1	88.1	88.1	89.6	91.9
77.5°	64.2	65.0	64.2	65.7	65.7	66.5	68.0	67.2	68.7	69.5	70.2
80°	47.1	46.3	46.3	46.3	47.1	47.1	48.6	49.3	49.3	51.5	50.0
82.5°	29.9	30.6	29.9	30.6	30.6	31.4	30.6	31.4	32.1	33.6	32.9
85°	17.2	16.4	16.4	17.2	16.4	16.4	17.2	16.4	17.2	16.4	17.2
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	13.6	15.2	18.0	23.7	29.4	35.1	40.8	40.3	39.8	39.3	38.8
92.5°	34.0	35.0	35.1	35.4	35.6	35.9	36.1	36.4	36.6	36.9	37.2
95°	71.0	72.3	72.6	73.1	73.6	74.1	74.6	74.6	74.6	74.6	74.6
97.5°	110.7	111.9	112.4	113.5	114.5	115.6	116.6	116.6	116.6	116.6	116.6
100°	156.4	157.4	157.8	158.6	159.3	160.1	160.9	160.9	160.9	160.9	160.9
102.5°	203.2	204.0	204.5	205.6	206.6	207.7	208.7	208.9	209.2	209.4	209.7
105°	253.7	254.1	254.4	254.9	255.4	256.0	256.5	257.0	257.5	258.0	258.5
107.5°	308.4	308.9	308.9	308.9	308.9	308.9	308.9	309.2	309.4	309.7	310.0
110°	361.7	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	417.7	418.5	418.4	418.1	417.8	417.6	417.3	416.5	415.7	415.0	414.2
115°	472.5	473.3	473.0	472.5	472.0	471.5	471.0	470.7	470.5	470.2	469.9
117.5°	529.4	530.4	529.8	528.5	527.2	525.9	524.6	523.8	523.0	522.3	521.5
120°	584.2	585.2	584.2	582.1	580.0	578.0	575.9	575.9	575.9	575.9	575.9
122.5°	636.3	637.6	637.0	635.7	634.4	633.1	631.8	631.0	630.2	629.5	628.7
125°	687.7	688.9	688.5	687.7	687.0	686.2	685.4	684.6	683.8	683.1	682.3
127.5°	741.2	742.6	742.1	741.0	740.0	738.9	737.9	736.9	735.8	734.8	733.7
130°	791.0	792.7	792.4	791.9	791.4	790.9	790.4	789.9	789.3	788.8	788.3
132.5°	841.5	842.8	842.9	843.2	843.5	843.7	844.0	842.7	841.4	840.1	838.8
135°	889.2	890.6	890.9	891.4	891.9	892.4	892.9	892.7	892.4	892.2	891.9
137.5°	938.4	939.6	939.9	940.4	940.9	941.4	941.9	941.6	941.4	941.1	940.8
140°	983.8	985.0	985.7	987.0	988.3	989.6	990.9	990.9	990.9	990.9	990.9
142.5°	1030.5	1031.7	1032.1	1032.9	1033.6	1034.4	1035.2	1035.4	1035.7	1035.9	1036.2
145°	1072.7	1073.6	1074.4	1075.9	1077.5	1079.0	1080.6	1080.9	1081.1	1081.4	1081.7
147.5°	1114.4	1115.6	1116.1	1117.2	1118.2	1119.3	1120.3	1120.8	1121.3	1121.8	1122.3
150°	1152.1	1152.9	1153.4	1154.5	1155.5	1156.6	1157.6	1158.4	1159.2	1159.9	1160.7
152.5°	1188.2	1189.0	1189.7	1191.0	1192.3	1193.6	1194.9	1195.9	1196.9	1198.0	1199.0
155°	1221.3	1221.7	1222.1	1222.9	1223.6	1224.4	1225.2	1226.5	1227.8	1229.1	1230.4
157.5°	1251.7	1252.0	1252.3	1252.8	1253.3	1253.8	1254.3	1256.1	1257.9	1259.8	1261.6
160°	1279.7	1280.0	1280.1	1280.4	1280.6	1280.9	1281.1	1282.7	1284.2	1285.8	1287.3
162.5°	1303.3	1303.3	1303.4	1303.7	1303.9	1304.2	1304.4	1306.2	1308.0	1309.9	1311.7
165°	1324.4	1324.3	1324.3	1324.3	1324.3	1324.3	1324.3	1326.1	1327.9	1329.7	1331.5
167.5°	1342.1	1341.7	1341.7	1341.7	1341.7	1341.7	1341.7	1343.5	1345.3	1347.2	1349.0
170°	1357.3	1356.9	1356.8	1356.5	1356.2	1356.0	1355.7	1357.5	1359.3	1361.2	1363.0
172.5°	1367.8	1367.4	1367.3	1367.0	1366.7	1366.5	1366.2	1368.0	1369.8	1371.7	1373.5
175°	1375.9	1375.5	1375.2	1374.7	1374.2	1373.7	1373.2	1375.0	1376.8	1378.7	1380.5
177.5°	1380.6	1380.2	1379.9	1379.4	1378.9	1378.4	1377.9	1379.5	1381.0	1382.6	1384.1
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	926.2	928.4	923.2	921.7	923.2	918.0	919.5	921.0	921.0	923.2	924.7
5°	872.4	869.4	864.2	862.7	861.2	863.5	862.0	864.2	864.9	870.2	870.9
7.5°	819.4	814.9	810.4	805.9	804.4	800.7	804.4	804.4	809.7	808.2	811.9
10°	756.6	755.9	749.9	747.7	744.7	738.7	746.9	744.7	748.4	755.1	756.6
12.5°	710.3	702.1	705.9	695.4	699.1	693.2	693.9	693.9	699.9	700.6	699.1
15°	666.3	659.5	649.8	645.4	643.1	640.1	649.8	650.6	646.1	656.6	652.8
17.5°	621.4	621.4	612.5	610.2	604.3	607.3	605.8	606.5	605.0	612.5	616.2
20°	582.6	578.9	575.9	576.6	569.2	567.7	566.2	567.7	572.9	578.1	579.6
22.5°	551.2	549.0	541.5	543.0	537.0	539.3	537.8	541.5	542.3	542.3	547.5
25°	521.4	518.4	519.1	516.1	513.9	513.9	511.6	513.9	516.9	518.4	519.1
27.5°	499.0	496.7	493.0	490.7	492.2	488.5	491.5	493.7	493.7	492.2	493.7
30°	472.1	473.6	473.6	466.1	469.1	467.6	469.8	471.3	471.3	472.1	470.6
32.5°	454.1	449.7	448.9	448.2	448.2	445.2	445.2	447.4	448.2	448.9	451.1
35°	430.2	430.2	426.5	428.7	425.8	426.5	425.8	426.5	428.0	425.8	428.0
37.5°	408.6	409.3	407.8	409.3	410.1	408.6	407.1	410.1	408.6	408.6	407.1
40°	389.9	389.2	389.9	389.9	389.9	390.6	389.2	389.2	389.2	387.7	386.2
42.5°	374.2	369.7	371.2	372.0	369.7	369.7	370.5	369.7	372.0	367.5	367.5
45°	351.8	350.3	351.1	351.1	352.6	350.3	351.8	352.6	350.3	349.6	348.1
47.5°	331.6	333.1	331.6	333.1	333.1	334.6	331.6	332.4	333.1	330.1	327.9
50°	311.5	311.5	313.7	313.0	313.7	312.2	312.2	311.5	312.2	310.7	308.5
52.5°	292.8	290.6	294.3	293.5	292.8	292.1	291.3	292.1	290.6	289.1	289.1
55°	269.6	269.6	271.9	272.6	272.6	271.1	269.6	270.4	269.6	268.9	268.1
57.5°	251.0	248.0	249.5	250.2	250.2	248.0	249.5	248.0	248.0	248.7	246.5
60°	227.1	227.1	225.6	227.8	227.8	226.3	226.3	227.1	225.6	224.8	224.1
62.5°	201.7	202.4	204.7	205.4	206.2	204.7	203.2	203.9	203.9	201.7	202.4
65°	180.0	181.5	184.5	183.7	182.3	183.0	181.5	182.3	180.0	180.8	178.5
67.5°	159.1	158.3	159.1	159.1	160.6	159.8	158.3	158.3	157.6	159.8	157.6
70°	136.7	136.7	136.7	136.7	137.4	138.2	136.7	135.2	135.9	134.4	133.7
72.5°	113.5	114.3	113.5	115.0	112.8	114.3	114.3	113.5	112.8	112.8	112.8
75°	91.9	93.4	91.1	91.9	91.1	92.6	91.9	91.9	90.4	89.6	90.4
77.5°	70.2	71.0	69.5	70.2	69.5	70.2	70.2	69.5	69.5	69.5	69.5
80°	50.0	50.8	50.0	49.3	48.6	50.0	48.6	49.3	50.0	49.3	50.8
82.5°	32.1	32.1	31.4	32.1	30.6	30.6	31.4	31.4	30.6	32.1	30.6
85°	15.7	15.7	17.2	15.7	14.9	14.9	14.9	15.7	14.9	16.4	15.7
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	38.5	38.6	38.9	39.1	39.4	39.6	39.4	39.1	38.9	38.6	38.5
92.5°	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3
95°	74.6	74.3	73.8	73.3	72.8	72.3	72.8	73.3	73.8	74.3	74.6
97.5°	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6
100°	160.9	160.8	160.5	160.2	160.0	159.7	160.0	160.2	160.5	160.8	160.9
102.5°	209.8	209.7	209.4	209.2	208.9	208.7	208.9	209.2	209.4	209.7	209.8
105°	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8
107.5°	310.1	309.5	308.2	306.9	305.6	304.3	305.6	306.9	308.2	309.5	310.1
110°	362.5	362.1	361.3	360.6	359.8	359.0	359.8	360.6	361.3	362.1	362.5

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	413.8	413.5	413.0	412.5	412.0	411.5	412.0	412.5	413.0	413.5	413.8
115°	469.8	469.4	468.6	467.9	467.1	466.3	467.1	467.9	468.6	469.4	469.8
117.5°	521.1	520.7	519.9	519.2	518.4	517.6	518.4	519.2	519.9	520.7	521.1
120°	575.9	575.5	574.7	574.0	573.2	572.4	573.2	574.0	574.7	575.5	575.9
122.5°	628.3	628.0	627.5	627.0	626.5	626.0	626.5	627.0	627.5	628.0	628.3
125°	681.9	681.8	681.5	681.3	681.0	680.8	681.0	681.3	681.5	681.8	681.9
127.5°	733.2	732.8	732.0	731.3	730.5	729.7	730.5	731.3	732.0	732.8	733.2
130°	788.0	787.5	786.5	785.4	784.4	783.4	784.4	785.4	786.5	787.5	788.0
132.5°	838.2	837.8	837.0	836.3	835.5	834.7	835.5	836.3	837.0	837.8	838.2
135°	891.8	891.4	890.6	889.9	889.1	888.3	889.1	889.9	890.6	891.4	891.8
137.5°	940.7	940.2	939.2	938.1	937.1	936.1	937.1	938.1	939.2	940.2	940.7
140°	990.9	990.4	989.3	988.3	987.2	986.2	987.2	988.3	989.3	990.4	990.9
142.5°	1036.3	1035.8	1034.8	1033.7	1032.7	1031.7	1032.7	1033.7	1034.8	1035.8	1036.3
145°	1081.8	1081.3	1080.2	1079.2	1078.1	1077.1	1078.1	1079.2	1080.2	1081.3	1081.8
147.5°	1122.6	1122.1	1121.0	1120.0	1118.9	1117.9	1118.9	1120.0	1121.0	1122.1	1122.6
150°	1161.1	1160.7	1159.9	1159.2	1158.4	1157.6	1158.4	1159.2	1159.9	1160.7	1161.1
152.5°	1199.5	1199.0	1198.0	1196.9	1195.9	1194.9	1195.9	1196.9	1198.0	1199.0	1199.5
155°	1231.0	1230.6	1229.8	1229.1	1228.3	1227.5	1228.3	1229.1	1229.8	1230.6	1231.0
157.5°	1262.5	1261.8	1260.5	1259.2	1257.9	1256.6	1257.9	1259.2	1260.5	1261.8	1262.5
160°	1288.1	1287.6	1286.6	1285.5	1284.5	1283.5	1284.5	1285.5	1286.6	1287.6	1288.1
162.5°	1312.6	1312.0	1310.7	1309.4	1308.1	1306.8	1308.1	1309.4	1310.7	1312.0	1312.6
165°	1332.4	1331.8	1330.5	1329.2	1327.9	1326.6	1327.9	1329.2	1330.5	1331.8	1332.4
167.5°	1349.9	1349.3	1348.0	1346.7	1345.4	1344.1	1345.4	1346.7	1348.0	1349.3	1349.9
170°	1363.9	1363.1	1361.6	1360.0	1358.5	1356.9	1358.5	1360.0	1361.6	1363.1	1363.9
172.5°	1374.4	1373.6	1372.1	1370.5	1369.0	1367.4	1369.0	1370.5	1372.1	1373.6	1374.4
175°	1381.4	1380.6	1379.1	1377.5	1376.0	1374.4	1376.0	1377.5	1379.1	1380.6	1381.4
177.5°	1384.9	1384.1	1382.6	1381.0	1379.5	1377.9	1379.5	1381.0	1382.6	1384.1	1384.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	922.5	928.4	926.2	918.0	927.7	927.7	934.4	934.4	942.6	945.6	950.1
5°	870.2	874.7	878.4	874.7	881.4	891.8	897.8	903.0	914.2	918.7	925.5
7.5°	814.2	822.4	826.1	826.1	837.3	849.3	861.2	868.7	884.4	890.3	897.1
10°	759.6	769.3	776.8	776.1	794.7	802.2	817.1	834.3	850.0	859.0	868.7
12.5°	702.1	707.3	717.8	732.7	737.2	750.7	767.8	789.5	817.9	826.1	840.3
15°	654.3	668.5	676.7	683.4	693.9	706.6	725.3	746.2	774.6	792.5	807.4
17.5°	614.0	632.7	637.9	636.4	649.8	669.3	690.9	706.6	732.0	753.7	767.8
20°	581.1	588.6	597.5	601.3	611.7	632.7	653.6	671.5	692.4	709.6	726.0
22.5°	548.2	554.2	561.7	568.4	576.6	588.6	608.8	631.2	651.3	667.8	686.4
25°	521.4	525.1	531.8	537.0	546.0	554.2	568.4	593.1	617.0	626.7	643.1
27.5°	495.2	498.2	502.7	508.7	513.1	521.4	534.1	554.2	578.9	588.6	611.0
30°	472.1	474.3	478.8	481.8	484.0	493.7	503.4	519.1	537.8	551.2	567.7
32.5°	450.4	452.6	457.1	457.9	460.9	466.1	475.0	489.2	505.7	516.9	531.1
35°	426.5	428.0	432.5	434.0	436.2	440.7	447.4	457.9	472.8	481.0	493.7
37.5°	407.8	407.1	410.1	412.3	415.3	417.5	419.8	430.2	441.4	448.9	458.6
40°	387.7	386.2	386.9	389.9	391.4	394.4	394.4	404.8	412.3	418.3	425.8
42.5°	367.5	366.7	365.3	366.7	368.2	369.0	369.7	377.2	384.7	389.9	398.1
45°	347.3	346.6	345.1	345.8	345.8	347.3	349.6	352.6	357.8	362.3	366.7
47.5°	328.7	327.2	324.9	324.2	325.7	325.7	325.7	328.7	333.9	335.4	339.9
50°	309.2	307.0	304.0	302.5	302.5	301.8	303.3	304.0	308.5	310.0	313.7
52.5°	288.3	286.8	283.8	280.8	281.6	280.1	280.8	281.6	283.1	285.3	287.6
55°	267.4	264.4	262.2	261.4	259.2	259.2	256.9	259.9	259.2	259.9	262.9
57.5°	247.2	244.2	240.5	239.0	236.8	236.0	234.5	233.8	234.5	236.8	239.0
60°	223.3	221.8	219.6	217.4	215.9	213.6	212.1	212.1	211.4	211.4	212.1
62.5°	200.2	199.4	196.4	195.7	194.2	192.7	190.5	189.0	189.0	190.5	191.2
65°	177.8	177.0	174.8	174.0	170.3	168.8	168.1	167.3	165.8	165.8	165.8
67.5°	156.9	154.6	154.6	150.9	147.9	146.4	144.9	144.2	144.2	144.2	144.9
70°	133.7	133.7	131.5	129.2	126.2	127.0	124.7	122.5	122.5	121.0	121.8
72.5°	111.3	110.5	108.3	107.6	105.3	103.1	101.6	103.1	100.8	100.1	100.8
75°	89.6	88.9	87.4	85.9	86.6	84.4	82.2	81.4	81.4	79.9	79.9
77.5°	68.7	70.2	67.2	66.5	65.0	63.5	62.7	62.0	62.0	62.0	63.5
80°	47.8	48.6	48.6	47.1	47.8	45.6	45.6	45.6	43.3	44.1	44.8
82.5°	30.6	30.6	29.9	30.6	29.9	29.9	29.1	29.1	28.4	28.4	29.1
85°	17.2	16.4	15.7	17.2	16.4	16.4	15.7	15.7	15.7	15.7	15.7
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	38.8	39.3	39.8	40.3	40.8	35.1	29.4	23.7	18.0	15.2	13.6
92.5°	37.2	36.9	36.6	36.4	36.1	35.9	35.6	35.4	35.1	35.0	34.0
95°	74.6	74.6	74.6	74.6	74.6	74.1	73.6	73.1	72.6	72.3	71.0
97.5°	116.6	116.6	116.6	116.6	116.6	115.6	114.5	113.5	112.4	111.9	110.7
100°	160.9	160.9	160.9	160.9	160.9	160.1	159.3	158.6	157.8	157.4	156.4
102.5°	209.7	209.4	209.2	208.9	208.7	207.7	206.6	205.6	204.5	204.0	203.2
105°	258.5	258.0	257.5	257.0	256.5	256.0	255.4	254.9	254.4	254.1	253.7
107.5°	310.0	309.7	309.4	309.2	308.9	308.9	308.9	308.9	308.9	308.9	308.4
110°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	361.7

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	414.2	415.0	415.7	416.5	417.3	417.6	417.8	418.1	418.4	418.5	417.7
115°	469.9	470.2	470.5	470.7	471.0	471.5	472.0	472.5	473.0	473.3	472.5
117.5°	521.5	522.3	523.0	523.8	524.6	525.9	527.2	528.5	529.8	530.4	529.4
120°	575.9	575.9	575.9	575.9	575.9	578.0	580.0	582.1	584.2	585.2	584.2
122.5°	628.7	629.5	630.2	631.0	631.8	633.1	634.4	635.7	637.0	637.6	636.3
125°	682.3	683.1	683.8	684.6	685.4	686.2	687.0	687.7	688.5	688.9	687.7
127.5°	733.7	734.8	735.8	736.9	737.9	738.9	740.0	741.0	742.1	742.6	741.2
130°	788.3	788.8	789.3	789.9	790.4	790.9	791.4	791.9	792.4	792.7	791.0
132.5°	838.8	840.1	841.4	842.7	844.0	843.7	843.5	843.2	842.9	842.8	841.5
135°	891.9	892.2	892.4	892.7	892.9	892.4	891.9	891.4	890.9	890.6	889.2
137.5°	940.8	941.1	941.4	941.6	941.9	941.4	940.9	940.4	939.9	939.6	938.4
140°	990.9	990.9	990.9	990.9	990.9	989.6	988.3	987.0	985.7	985.0	983.8
142.5°	1036.2	1035.9	1035.7	1035.4	1035.2	1034.4	1033.6	1032.9	1032.1	1031.7	1030.5
145°	1081.7	1081.4	1081.1	1080.9	1080.6	1079.0	1077.5	1075.9	1074.4	1073.6	1072.7
147.5°	1122.3	1121.8	1121.3	1120.8	1120.3	1119.3	1118.2	1117.2	1116.1	1115.6	1114.4
150°	1160.7	1159.9	1159.2	1158.4	1157.6	1156.6	1155.5	1154.5	1153.4	1152.9	1152.1
152.5°	1199.0	1198.0	1196.9	1195.9	1194.9	1193.6	1192.3	1191.0	1189.7	1189.0	1188.2
155°	1230.4	1229.1	1227.8	1226.5	1225.2	1224.4	1223.6	1222.9	1222.1	1221.7	1221.3
157.5°	1261.6	1259.8	1257.9	1256.1	1254.3	1253.8	1253.3	1252.8	1252.3	1252.0	1251.7
160°	1287.3	1285.8	1284.2	1282.7	1281.1	1280.9	1280.6	1280.4	1280.1	1280.0	1279.7
162.5°	1311.7	1309.9	1308.0	1306.2	1304.4	1304.2	1303.9	1303.7	1303.4	1303.3	1303.3
165°	1331.5	1329.7	1327.9	1326.1	1324.3	1324.3	1324.3	1324.3	1324.3	1324.3	1324.4
167.5°	1349.0	1347.2	1345.3	1343.5	1341.7	1341.7	1341.7	1341.7	1341.7	1341.7	1342.1
170°	1363.0	1361.2	1359.3	1357.5	1355.7	1356.0	1356.2	1356.5	1356.8	1356.9	1357.3
172.5°	1373.5	1371.7	1369.8	1368.0	1366.2	1366.5	1366.7	1367.0	1367.3	1367.4	1367.8
175°	1380.5	1378.7	1376.8	1375.0	1373.2	1373.7	1374.2	1374.7	1375.2	1375.5	1375.9
177.5°	1384.1	1382.6	1381.0	1379.5	1377.9	1378.4	1378.9	1379.4	1379.9	1380.2	1380.6
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	971.8	971.8	971.8	971.8
2.5°	953.8	953.8	965.0	977.0
5°	932.9	938.1	956.1	972.5
7.5°	912.8	921.7	944.1	965.0
10°	888.1	900.1	927.7	952.3
12.5°	864.2	875.4	907.5	935.2
15°	830.6	844.8	879.1	913.5
17.5°	797.0	811.2	853.0	893.3
20°	757.4	776.1	823.1	876.9
22.5°	720.8	743.9	796.2	839.6
25°	680.5	716.3	764.9	820.9
27.5°	644.6	680.5	729.8	786.5
30°	604.3	640.9	691.7	743.9
32.5°	565.4	599.0	648.3	712.6
35°	525.1	557.2	605.0	670.0
37.5°	488.5	519.9	572.2	631.9
40°	452.6	485.5	530.3	590.1
42.5°	419.0	448.2	488.5	548.2
45°	388.4	409.3	446.7	502.7
47.5°	356.3	375.0	409.3	465.3
50°	326.4	342.1	372.0	424.3
52.5°	297.3	310.7	338.4	380.2
55°	271.1	283.8	304.0	345.1
57.5°	244.2	254.0	273.4	306.2
60°	218.1	227.1	242.8	269.6
62.5°	192.0	199.4	214.4	236.0
65°	168.8	174.8	186.0	204.7
67.5°	146.4	150.1	159.1	174.0
70°	124.7	127.7	135.2	147.1
72.5°	101.6	104.6	112.8	121.0
75°	82.2	82.9	88.9	95.6
77.5°	64.2	63.5	68.0	73.2
80°	44.1	46.3	50.0	52.3
82.5°	29.9	30.6	32.1	33.6
85°	16.4	17.2	17.2	19.4
87.5°	6.7	7.5	7.5	8.2
90°	10.5	7.4	4.3	1.2
92.5°	31.9	29.8	27.7	25.6
95°	68.4	65.8	63.2	60.6
97.5°	108.4	106.1	103.7	101.4
100°	154.3	152.2	150.1	148.0
102.5°	201.7	200.1	198.6	197.0
105°	252.9	252.2	251.4	250.6
107.5°	307.4	306.3	305.3	304.3
110°	360.2	358.6	357.1	355.5

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	416.2	414.6	413.1	411.5
115°	471.0	469.4	467.9	466.3
117.5°	527.3	525.2	523.2	521.1
120°	582.1	580.0	578.0	575.9
122.5°	633.7	631.2	628.6	626.0
125°	685.4	683.1	680.7	678.4
127.5°	738.3	735.4	732.6	729.7
130°	787.6	784.3	780.9	777.5
132.5°	838.9	836.4	833.8	831.2
135°	886.3	883.5	880.6	877.8
137.5°	936.1	933.8	931.4	929.1
140°	981.5	979.2	976.8	974.5
142.5°	1028.2	1025.9	1023.5	1021.2
145°	1070.9	1069.1	1067.3	1065.5
147.5°	1112.1	1109.8	1107.4	1105.1
150°	1150.6	1149.0	1147.5	1145.9
152.5°	1186.7	1185.1	1183.6	1182.0
155°	1220.5	1219.8	1219.0	1218.2
157.5°	1251.2	1250.7	1250.2	1249.7
160°	1279.2	1278.7	1278.1	1277.6
162.5°	1303.3	1303.3	1303.3	1303.3
165°	1324.7	1324.9	1325.2	1325.4
167.5°	1342.9	1343.6	1344.4	1345.2
170°	1358.1	1358.8	1359.6	1360.4
172.5°	1368.6	1369.3	1370.1	1370.9
175°	1376.7	1377.4	1378.2	1379.0
177.5°	1381.4	1382.1	1382.9	1383.7
180°	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P998412

CATALOG NUMBER: SA2XXDIP-B485D1080UB35-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.84	14.56	14.91	15.64	17.10	11.33	12.06	12.41	13.13	14.59
	3H	14.64	15.29	15.73	16.37	17.85	12.67	13.31	13.75	14.40	15.88
	4H	14.80	15.42	15.90	16.50	17.99	13.12	13.74	14.22	14.82	16.31
	6H	14.84	15.41	15.95	16.49	17.99	13.42	13.99	14.53	15.07	16.57
	8H	14.82	15.35	15.92	16.46	17.95	13.50	14.04	14.61	15.14	16.63
	12H	14.77	15.28	15.89	16.38	17.90	13.54	14.05	14.65	15.15	16.66
4H	2H	13.86	14.48	14.97	15.56	17.05	11.76	12.38	12.86	13.46	14.95
	3H	14.83	15.34	15.94	16.45	17.95	13.21	13.72	14.32	14.83	16.33
	4H	15.10	15.57	16.22	16.67	18.19	13.74	14.21	14.85	15.31	16.83
	6H	15.23	15.63	16.35	16.75	18.26	14.11	14.51	15.23	15.64	17.15
	8H	15.22	15.60	16.34	16.71	18.24	14.22	14.59	15.34	15.71	17.24
	12H	15.18	15.52	16.32	16.65	18.18	14.27	14.61	15.41	15.74	17.27
8H	4H	15.10	15.48	16.22	16.59	18.12	13.87	14.25	14.99	15.36	16.89
	6H	15.28	15.58	16.42	16.74	18.27	14.30	14.61	15.44	15.77	17.29
	8H	15.31	15.58	16.45	16.71	18.26	14.45	14.72	15.60	15.86	17.40
	12H	15.28	15.52	16.43	16.66	18.24	14.54	14.77	15.69	15.91	17.49
12H	4H	15.05	15.39	16.19	16.52	18.05	13.84	14.18	14.98	15.31	16.84
	6H	15.25	15.52	16.40	16.66	18.21	14.30	14.57	15.45	15.71	17.25
	8H	15.28	15.52	16.43	16.65	18.23	14.45	14.69	15.60	15.82	17.41