

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998420

Luminaire Tested: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998420
REPORT IS A COMBINATION OF REPORTS P984161 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5951.0 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36		
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	39	38	37	31		
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26		
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23		
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20		
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17		
6	61	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	15		
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	19	17	14		
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15	13		
9	49	37	30	25	45	34	28	24	29	24	20	23	19	17	18	15	14	11		
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15231	15231	15231	15231
5°	15268	16241	15327	12921
10°	15091	17729	15185	10653
15°	14726	18701	14929	8974
20°	14495	17558	14495	7799
25°	14033	15085	14096	6975
30°	13274	11858	13526	6317
35°	12599	8200	12810	5780
40°	11826	6191	11961	5351
45°	10872	5087	11049	4890
50°	10046	4465	10063	4476
55°	9105	3805	9164	4027
60°	8102	3179	8214	3514
65°	7206	2585	7337	3001
70°	6310	2027	6470	2420
75°	5298	1472	5505	1755
80°	4136	933	4431	1043
85°	2712	470	2924	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15745 cd/sqm

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.7	1.5
10°-20°	266.8	4.5
20°-30°	387.2	6.5
30°-40°	408.1	6.9
40°-50°	361.2	6.1
50°-60°	288.4	4.8
60°-70°	195.9	3.3
70°-80°	100.2	1.7
80°-90°	27.6	0.5
90°-100°	84.6	1.4
100°-110°	269.0	4.5
110°-120°	460.3	7.7
120°-130°	605.3	10.2
130°-140°	679.5	11.4
140°-150°	666.3	11.2
150°-160°	558.9	9.4
160°-170°	370.7	6.2
170°-180°	129.6	2.2
0°-30°	745.6	12.5
0°-40°	1153.7	19.4
0°-60°	1803.2	30.3
0°-90°	2126.9	35.7
90°-120°	813.9	13.7
90°-150°	2764.9	46.5
90°-180°	3824.0	64.3
0°-180°	5951.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	962	962	962	962	962	
5°	963	1075	967	855	963	91
15°	905	1321	917	634	905	255
25°	813	1101	816	509	813	372
35°	663	599	674	422	663	415
45°	498	361	506	347	498	386
55°	342	254	344	268	342	305
65°	203	156	206	181	203	201
75°	95	77	98	92	95	102
85°	19	20	21	15	19	22
90°	1	39	1	39	1	5
95°	60	72	60	72	60	67
105°	248	256	248	256	248	262
115°	462	462	462	462	462	457
125°	672	674	672	674	672	600
135°	869	880	869	880	869	672
145°	1055	1066	1055	1066	1055	659
155°	1206	1215	1206	1215	1206	555
165°	1312	1314	1312	1314	1312	370
175°	1366	1361	1366	1361	1366	130
180°	1368	1368	1368	1368	1368	

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	967.4	969.6	973.3	974.1	981.5	987.4	994.0	994.0	996.3	995.5	989.6
5°	963.0	969.6	979.3	987.4	1000.7	1006.6	1015.5	1022.2	1028.1	1032.5	1031.8
7.5°	955.6	967.4	981.5	997.0	1014.8	1025.1	1037.7	1049.5	1057.7	1065.0	1070.2
10°	943.0	963.0	982.2	1002.9	1025.8	1039.9	1054.7	1070.2	1082.8	1096.9	1110.2
12.5°	926.0	954.8	978.5	1005.9	1034.0	1049.5	1073.2	1085.0	1109.4	1144.9	1154.5
15°	904.6	943.8	965.9	1000.7	1037.7	1050.3	1082.8	1102.0	1152.3	1174.5	1201.1
17.5°	884.6	928.2	957.8	997.7	1034.0	1058.4	1090.2	1129.4	1171.6	1203.4	1232.9
20°	868.3	910.5	946.0	990.3	1036.2	1067.3	1100.6	1147.9	1193.7	1226.3	1249.2
22.5°	831.3	885.3	926.7	976.3	1031.8	1074.7	1106.5	1158.2	1207.8	1227.8	1247.7
25°	812.8	859.4	907.5	963.7	1028.8	1079.8	1107.2	1164.9	1208.5	1215.9	1220.4
27.5°	778.8	831.3	887.5	951.9	1028.1	1071.0	1105.7	1158.2	1193.0	1187.8	1174.5
30°	736.7	801.0	863.1	932.7	1017.7	1064.3	1096.9	1144.9	1162.7	1136.1	1112.4
32.5°	705.6	766.2	835.0	915.6	1005.9	1050.3	1082.1	1119.8	1123.5	1075.4	1035.5
35°	663.4	730.7	808.4	893.5	985.9	1025.8	1055.4	1078.4	1060.6	993.3	946.0
37.5°	625.7	692.3	775.1	861.7	958.5	997.7	1021.4	1025.1	981.5	922.3	852.8
40°	584.3	653.1	739.6	830.6	928.2	962.2	977.0	965.9	903.1	834.3	753.7
42.5°	542.9	610.9	704.1	797.3	889.8	918.6	924.5	894.2	817.3	736.7	643.5
45°	497.8	568.8	662.0	755.9	845.4	861.7	862.4	818.8	727.8	643.5	556.9
47.5°	460.8	526.6	619.1	713.0	788.4	799.5	795.1	744.8	645.7	551.0	475.6
50°	420.1	483.0	574.7	667.1	731.5	734.4	723.3	651.6	554.7	468.2	408.3
52.5°	376.5	440.1	524.4	613.1	670.8	666.4	644.9	568.0	477.1	405.3	359.5
55°	341.7	397.9	477.1	563.6	604.3	591.7	568.0	489.6	417.9	357.2	317.3
57.5°	303.2	352.8	430.5	505.9	529.6	517.7	494.1	420.8	354.3	308.4	281.8
60°	267.0	312.1	380.2	443.0	461.5	448.9	421.6	355.8	307.7	269.2	249.3
62.5°	233.7	272.9	329.9	387.6	395.0	382.4	358.7	305.5	264.0	233.7	218.9
65°	202.7	239.6	285.5	329.1	335.8	322.5	298.1	259.6	224.8	205.6	191.6
67.5°	172.3	201.9	242.6	274.4	278.1	265.5	245.6	214.5	193.0	172.3	162.0
70°	145.7	167.9	199.7	225.6	227.1	215.2	204.9	176.8	160.5	145.7	137.6
72.5°	119.8	135.4	159.8	179.0	179.7	172.3	162.7	145.0	130.9	120.6	112.4
75°	94.7	108.0	122.8	139.8	139.0	133.1	125.7	114.6	102.8	96.2	92.5
77.5°	72.5	80.6	92.5	103.5	103.5	100.6	96.2	88.0	80.6	74.0	70.3
80°	51.8	57.0	66.6	70.3	71.7	71.0	67.3	61.4	58.4	53.3	51.8
82.5°	33.3	37.0	41.4	45.1	47.3	45.9	45.1	42.2	37.7	36.2	34.8
85°	19.2	20.7	22.9	25.1	25.9	25.1	26.6	24.4	22.2	22.2	21.4
87.5°	8.1	8.9	10.4	10.4	11.1	11.1	10.4	11.1	11.1	10.4	9.6
90°	1.2	4.3	7.3	10.4	13.5	15.0	17.8	23.5	29.1	34.8	40.4
92.5°	25.4	27.4	29.5	31.5	33.6	34.6	34.7	35.0	35.3	35.5	35.8
95°	60.0	62.6	65.2	67.7	70.3	71.6	71.9	72.4	72.9	73.4	73.9
97.5°	100.4	102.7	105.0	107.3	109.6	110.8	111.3	112.3	113.4	114.4	115.4
100°	146.6	148.6	150.7	152.7	154.8	155.8	156.2	157.0	157.7	158.5	159.3
102.5°	195.1	196.6	198.2	199.7	201.2	202.0	202.5	203.5	204.6	205.6	206.6
105°	248.2	249.0	249.7	250.5	251.2	251.6	251.9	252.4	252.9	253.4	253.9
107.5°	301.3	302.3	303.3	304.4	305.4	305.9	305.9	305.9	305.9	305.9	305.9
110°	352.0	353.6	355.1	356.7	358.2	359.0	359.0	359.0	359.0	359.0	359.0

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	407.5	409.0	410.6	412.1	413.6	414.4	414.3	414.0	413.7	413.5	413.2
115°	461.7	463.2	464.8	466.3	467.8	468.6	468.3	467.8	467.3	466.8	466.3
117.5°	516.0	518.0	520.1	522.1	524.2	525.2	524.6	523.3	522.0	520.7	519.4
120°	570.2	572.2	574.3	576.3	578.4	579.4	578.4	576.3	574.3	572.2	570.2
122.5°	619.8	622.4	625.0	627.5	630.1	631.4	630.8	629.5	628.2	626.9	625.6
125°	671.8	674.1	676.4	678.7	681.0	682.2	681.8	681.0	680.3	679.5	678.7
127.5°	722.6	725.4	728.2	731.1	733.9	735.3	734.8	733.7	732.7	731.6	730.6
130°	769.9	773.2	776.6	779.9	783.2	784.9	784.6	784.1	783.6	783.1	782.6
132.5°	823.0	825.6	828.1	830.7	833.2	834.5	834.6	834.9	835.2	835.4	835.7
135°	869.2	872.0	874.8	877.7	880.5	881.9	882.2	882.7	883.2	883.7	884.2
137.5°	919.9	922.2	924.5	926.8	929.1	930.3	930.6	931.1	931.6	932.1	932.6
140°	965.0	967.3	969.6	971.9	974.2	975.4	976.0	977.3	978.6	979.8	981.1
142.5°	1011.1	1013.4	1015.7	1018.0	1020.3	1021.5	1021.9	1022.7	1023.4	1024.2	1025.0
145°	1055.0	1056.8	1058.6	1060.4	1062.2	1063.1	1063.9	1065.4	1066.9	1068.5	1070.0
147.5°	1094.2	1096.5	1098.8	1101.1	1103.4	1104.6	1105.1	1106.1	1107.2	1108.2	1109.2
150°	1134.6	1136.2	1137.7	1139.3	1140.8	1141.6	1142.1	1143.1	1144.2	1145.2	1146.2
152.5°	1170.4	1171.9	1173.5	1175.0	1176.5	1177.3	1177.9	1179.2	1180.5	1181.8	1183.1
155°	1206.2	1207.0	1207.8	1208.5	1209.3	1209.7	1210.1	1210.8	1211.6	1212.3	1213.1
157.5°	1237.4	1237.9	1238.4	1238.9	1239.4	1239.7	1240.0	1240.5	1241.0	1241.5	1242.0
160°	1265.1	1265.6	1266.1	1266.6	1267.1	1267.4	1267.5	1267.8	1268.0	1268.3	1268.5
162.5°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.6	1290.9	1291.1	1291.4	1291.6
165°	1312.4	1312.1	1311.9	1311.6	1311.3	1311.2	1311.2	1311.2	1311.2	1311.2	1311.2
167.5°	1332.0	1331.2	1330.5	1329.7	1329.0	1328.6	1328.6	1328.6	1328.6	1328.6	1328.6
170°	1347.0	1346.2	1345.5	1344.7	1344.0	1343.6	1343.5	1343.2	1342.9	1342.7	1342.4
172.5°	1357.4	1356.6	1355.8	1355.1	1354.3	1353.9	1353.8	1353.5	1353.3	1353.0	1352.8
175°	1365.5	1364.7	1363.9	1363.2	1362.4	1362.0	1361.7	1361.2	1360.7	1360.2	1359.7
177.5°	1370.1	1369.3	1368.5	1367.8	1367.0	1366.6	1366.3	1365.8	1365.3	1364.8	1364.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	1000.0	1000.7	1002.2	1009.6	1013.3	1014.0	1011.1	1017.7	1019.9	1017.7	1016.2
5°	1047.3	1051.7	1060.6	1070.2	1069.5	1070.2	1074.7	1079.1	1080.6	1074.7	1076.9
7.5°	1088.7	1097.6	1107.2	1122.0	1122.0	1129.4	1132.4	1136.1	1144.9	1140.5	1139.0
10°	1136.1	1147.9	1165.6	1189.3	1190.0	1197.4	1204.8	1216.7	1220.4	1217.4	1218.9
12.5°	1195.2	1218.2	1219.6	1245.5	1257.3	1258.8	1270.7	1268.4	1275.8	1275.8	1288.4
15°	1221.1	1256.6	1276.6	1301.7	1309.1	1300.2	1309.9	1320.2	1321.0	1321.0	1320.2
17.5°	1267.7	1281.8	1301.7	1315.0	1318.0	1318.0	1318.7	1323.2	1320.2	1314.3	1318.7
20°	1277.3	1283.2	1290.6	1289.2	1290.6	1283.2	1275.8	1268.4	1269.2	1265.5	1276.6
22.5°	1259.6	1258.1	1241.1	1230.0	1230.0	1215.2	1201.1	1194.5	1187.8	1190.0	1193.7
25°	1215.2	1192.3	1171.6	1155.3	1151.6	1127.9	1108.7	1102.8	1091.7	1100.6	1102.0
27.5°	1144.2	1118.3	1085.0	1071.0	1051.7	1042.1	1028.8	1011.1	988.1	1001.4	999.2
30°	1068.0	1029.5	1002.2	968.2	937.8	935.6	910.5	880.9	869.1	869.1	875.7
32.5°	983.0	931.9	892.0	843.9	814.3	801.7	771.4	741.8	748.5	726.3	734.4
35°	883.8	816.5	766.2	719.6	697.5	682.7	643.5	627.2	609.4	599.1	618.3
37.5°	789.2	711.5	647.2	596.1	588.0	561.4	534.7	524.4	514.0	518.5	517.7
40°	673.8	605.0	547.3	507.4	493.3	480.8	463.0	450.4	443.8	447.5	448.2
42.5°	569.5	511.8	468.9	440.8	429.0	420.1	411.2	400.9	398.7	398.7	401.6
45°	488.9	441.6	412.7	389.8	383.1	376.5	369.8	365.4	363.9	360.9	363.2
47.5°	424.5	386.8	369.1	352.1	344.7	343.2	337.3	335.0	332.1	331.3	332.1
50°	370.5	346.9	330.6	321.0	315.8	313.6	310.6	306.2	304.7	308.4	306.9
52.5°	332.8	310.6	301.8	292.1	289.2	286.2	281.8	282.5	281.8	280.3	280.3
55°	295.1	281.1	272.2	264.8	264.0	261.1	257.4	255.9	255.2	253.7	255.9
57.5°	264.8	253.7	245.6	238.9	235.9	235.9	232.2	229.3	229.3	228.5	229.3
60°	234.5	223.4	218.2	211.5	209.3	208.6	206.4	204.9	202.7	202.7	202.7
62.5°	206.4	197.5	191.6	185.6	186.4	182.7	179.7	178.2	178.2	179.0	179.0
65°	179.7	173.8	166.4	161.2	159.8	159.0	157.5	156.8	154.6	156.1	156.1
67.5°	155.3	147.2	142.7	140.5	138.3	137.6	136.1	134.6	133.9	133.1	134.6
70°	130.9	124.3	120.6	119.1	116.9	116.1	115.4	113.2	113.9	114.6	115.4
72.5°	108.7	102.8	102.1	97.6	97.6	97.6	94.7	96.2	95.4	93.9	95.4
75°	85.8	82.8	81.4	79.1	79.9	79.1	78.4	76.2	76.2	76.9	77.7
77.5°	68.0	65.1	64.3	62.1	60.6	62.1	60.6	59.9	59.9	60.6	60.6
80°	50.3	48.8	46.6	46.6	46.6	45.9	45.9	45.9	45.1	44.4	45.1
82.5°	33.3	33.3	32.5	31.8	32.5	31.1	31.8	31.8	31.8	31.8	31.8
85°	21.4	20.7	20.7	20.0	20.0	20.0	20.7	19.2	19.2	20.0	20.0
87.5°	9.6	9.6	9.6	10.4	9.6	9.6	9.6	10.4	9.6	9.6	9.6
90°	39.9	39.4	38.9	38.4	38.1	38.2	38.5	38.7	39.0	39.2	39.0
92.5°	36.0	36.3	36.5	36.8	36.9	36.9	36.9	36.9	36.9	36.9	36.9
95°	73.9	73.9	73.9	73.9	73.9	73.6	73.1	72.6	72.1	71.6	72.1
97.5°	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4
100°	159.3	159.3	159.3	159.3	159.3	159.2	158.9	158.6	158.4	158.1	158.4
102.5°	206.9	207.1	207.4	207.7	207.8	207.7	207.4	207.1	206.9	206.6	206.9
105°	254.4	254.9	255.4	255.9	256.2	256.2	256.2	256.2	256.2	256.2	256.2
107.5°	306.1	306.4	306.6	306.9	307.0	306.4	305.1	303.8	302.6	301.3	302.6
110°	359.0	359.0	359.0	359.0	359.0	358.6	357.8	357.1	356.3	355.5	356.3

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	412.4	411.7	410.9	410.2	409.8	409.5	409.0	408.5	408.0	407.5	408.0
115°	466.1	465.8	465.6	465.3	465.2	464.8	464.0	463.3	462.5	461.7	462.5
117.5°	518.6	517.9	517.1	516.4	516.0	515.6	514.8	514.1	513.3	512.5	513.3
120°	570.2	570.2	570.2	570.2	570.2	569.8	569.0	568.3	567.5	566.7	567.5
122.5°	624.8	624.0	623.3	622.5	622.1	621.8	621.3	620.8	620.3	619.8	620.3
125°	677.9	677.1	676.4	675.6	675.2	675.1	674.8	674.6	674.3	674.1	674.3
127.5°	729.6	728.6	727.5	726.5	726.0	725.6	724.9	724.1	723.4	722.6	723.4
130°	782.1	781.6	781.1	780.6	780.3	779.8	778.8	777.7	776.7	775.7	776.7
132.5°	834.4	833.1	831.8	830.5	829.9	829.5	828.8	828.0	827.3	826.5	827.3
135°	883.9	883.7	883.4	883.1	883.0	882.6	881.8	881.1	880.3	879.5	880.3
137.5°	932.4	932.1	931.9	931.6	931.5	931.0	930.0	928.9	927.9	926.9	927.9
140°	981.1	981.1	981.1	981.1	981.1	980.6	979.6	978.5	977.5	976.5	977.5
142.5°	1025.2	1025.5	1025.7	1026.0	1026.1	1025.6	1024.6	1023.5	1022.5	1021.5	1022.5
145°	1070.3	1070.5	1070.8	1071.1	1071.2	1070.7	1069.6	1068.6	1067.5	1066.5	1067.5
147.5°	1109.7	1110.3	1110.8	1111.3	1111.6	1111.1	1110.0	1109.0	1107.9	1106.9	1107.9
150°	1147.0	1147.7	1148.5	1149.2	1149.6	1149.2	1148.5	1147.7	1147.0	1146.2	1147.0
152.5°	1184.1	1185.1	1186.2	1187.2	1187.7	1187.2	1186.2	1185.1	1184.1	1183.1	1184.1
155°	1214.4	1215.7	1217.0	1218.3	1218.9	1218.5	1217.7	1217.0	1216.2	1215.4	1216.2
157.5°	1243.8	1245.6	1247.4	1249.2	1250.1	1249.5	1248.2	1246.9	1245.6	1244.3	1245.6
160°	1270.1	1271.6	1273.2	1274.7	1275.5	1275.0	1273.9	1272.9	1271.8	1270.8	1271.8
162.5°	1293.4	1295.2	1297.0	1298.8	1299.7	1299.1	1297.8	1296.5	1295.2	1293.9	1295.2
165°	1313.0	1314.8	1316.6	1318.4	1319.3	1318.7	1317.4	1316.1	1314.8	1313.5	1314.8
167.5°	1330.4	1332.2	1333.9	1335.7	1336.6	1336.0	1334.7	1333.4	1332.2	1330.9	1332.2
170°	1344.2	1346.0	1347.8	1349.6	1350.5	1349.7	1348.2	1346.7	1345.1	1343.6	1345.1
172.5°	1354.6	1356.4	1358.2	1360.0	1360.9	1360.1	1358.6	1357.0	1355.5	1353.9	1355.5
175°	1361.5	1363.3	1365.1	1366.9	1367.8	1367.0	1365.5	1364.0	1362.4	1360.9	1362.4
177.5°	1365.9	1367.4	1369.0	1370.5	1371.3	1370.5	1369.0	1367.4	1365.9	1364.3	1365.9
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	1019.9	1014.8	1010.3	1011.1	1014.8	1011.8	1004.4	994.8	991.1	986.6	991.1
5°	1081.3	1076.9	1068.0	1068.7	1066.5	1063.6	1051.7	1036.9	1036.9	1025.1	1023.6
7.5°	1142.0	1135.3	1129.4	1127.9	1119.8	1113.9	1103.5	1082.8	1074.7	1060.6	1052.5
10°	1210.0	1204.8	1198.2	1190.0	1185.6	1175.3	1158.2	1127.9	1113.1	1093.9	1079.8
12.5°	1278.8	1278.1	1263.3	1247.0	1246.3	1230.0	1218.2	1177.5	1157.5	1131.6	1098.3
15°	1322.4	1318.7	1310.6	1302.5	1304.7	1286.9	1260.3	1212.2	1198.9	1167.9	1132.4
17.5°	1321.7	1321.7	1319.5	1318.0	1315.8	1310.6	1295.8	1264.0	1242.6	1203.4	1170.1
20°	1279.5	1289.2	1291.4	1290.6	1298.0	1301.7	1301.0	1281.0	1264.0	1229.2	1195.2
22.5°	1195.2	1217.4	1227.0	1232.9	1248.5	1256.6	1275.8	1268.4	1264.0	1238.1	1209.3
25°	1116.8	1124.2	1153.1	1154.5	1176.0	1196.0	1215.2	1227.8	1244.0	1234.4	1210.0
27.5°	1015.5	1032.5	1053.2	1068.7	1073.2	1113.9	1145.7	1169.3	1206.3	1209.3	1201.1
30°	900.9	909.0	943.0	963.7	987.4	1017.0	1062.8	1103.5	1136.8	1167.1	1177.5
32.5°	761.1	794.3	814.3	839.5	860.2	912.7	968.9	1021.4	1059.9	1110.9	1133.1
35°	633.1	659.0	693.0	703.4	741.1	785.5	858.7	926.0	984.4	1036.2	1081.3
37.5°	527.3	548.1	584.3	600.6	622.8	679.7	741.1	824.7	894.9	958.5	1014.8
40°	454.9	470.4	497.8	502.9	521.4	573.2	622.8	701.2	794.3	880.1	941.5
42.5°	405.3	412.7	431.2	437.9	449.7	484.4	528.8	602.8	689.3	778.1	864.6
45°	369.8	375.0	386.1	392.0	406.8	422.3	458.6	517.7	585.8	675.3	768.5
47.5°	338.0	344.7	349.1	352.8	360.9	377.9	401.6	445.2	510.3	592.4	682.7
50°	311.4	313.6	321.7	322.5	327.7	338.7	360.9	387.6	439.3	505.9	593.2
52.5°	284.8	287.0	292.1	297.3	299.5	308.4	323.2	345.4	383.9	436.4	514.0
55°	258.1	261.1	266.3	270.0	272.2	279.6	288.5	309.9	340.2	377.2	440.8
57.5°	231.5	238.2	239.6	241.9	245.6	253.7	261.8	274.4	298.1	332.1	378.7
60°	206.4	208.6	213.7	216.0	219.7	224.1	234.5	244.1	261.1	287.7	329.9
62.5°	180.5	185.6	187.9	190.1	193.0	198.2	204.9	215.2	230.0	251.5	284.8
65°	158.3	159.0	163.5	166.4	169.4	173.1	179.7	189.3	198.2	218.2	242.6
67.5°	136.8	138.3	139.8	142.7	146.4	150.1	156.1	161.2	172.3	185.6	204.9
70°	116.1	116.1	119.8	122.0	121.3	125.7	130.2	136.1	144.2	156.8	172.3
72.5°	97.6	96.9	99.8	100.6	102.1	105.0	108.0	113.9	118.3	128.0	139.8
75°	77.7	79.1	80.6	80.6	82.8	85.1	88.0	91.0	96.2	102.1	110.9
77.5°	61.4	61.4	62.9	63.6	65.8	65.1	68.0	71.0	74.7	79.9	86.5
80°	45.1	46.6	46.6	46.6	47.3	48.1	51.0	53.3	55.5	59.2	62.1
82.5°	31.8	31.8	33.3	33.3	33.3	34.8	34.8	35.5	37.0	39.2	41.4
85°	20.0	20.0	20.0	20.7	20.0	20.7	22.2	21.4	22.2	23.7	23.7
87.5°	9.6	9.6	9.6	9.6	9.6	10.4	9.6	10.4	11.1	11.1	11.1
90°	38.7	38.5	38.2	38.1	38.4	38.9	39.4	39.9	40.4	34.8	29.1
92.5°	36.9	36.9	36.9	36.9	36.8	36.5	36.3	36.0	35.8	35.5	35.3
95°	72.6	73.1	73.6	73.9	73.9	73.9	73.9	73.9	73.9	73.4	72.9
97.5°	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	114.4	113.4
100°	158.6	158.9	159.2	159.3	159.3	159.3	159.3	159.3	159.3	158.5	157.7
102.5°	207.1	207.4	207.7	207.8	207.7	207.4	207.1	206.9	206.6	205.6	204.6
105°	256.2	256.2	256.2	256.2	255.9	255.4	254.9	254.4	253.9	253.4	252.9
107.5°	303.8	305.1	306.4	307.0	306.9	306.6	306.4	306.1	305.9	305.9	305.9
110°	357.1	357.8	358.6	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	408.5	409.0	409.5	409.8	410.2	410.9	411.7	412.4	413.2	413.5	413.7
115°	463.3	464.0	464.8	465.2	465.3	465.6	465.8	466.1	466.3	466.8	467.3
117.5°	514.1	514.8	515.6	516.0	516.4	517.1	517.9	518.6	519.4	520.7	522.0
120°	568.3	569.0	569.8	570.2	570.2	570.2	570.2	570.2	570.2	572.2	574.3
122.5°	620.8	621.3	621.8	622.1	622.5	623.3	624.0	624.8	625.6	626.9	628.2
125°	674.6	674.8	675.1	675.2	675.6	676.4	677.1	677.9	678.7	679.5	680.3
127.5°	724.1	724.9	725.6	726.0	726.5	727.5	728.6	729.6	730.6	731.6	732.7
130°	777.7	778.8	779.8	780.3	780.6	781.1	781.6	782.1	782.6	783.1	783.6
132.5°	828.0	828.8	829.5	829.9	830.5	831.8	833.1	834.4	835.7	835.4	835.2
135°	881.1	881.8	882.6	883.0	883.1	883.4	883.7	883.9	884.2	883.7	883.2
137.5°	928.9	930.0	931.0	931.5	931.6	931.9	932.1	932.4	932.6	932.1	931.6
140°	978.5	979.6	980.6	981.1	981.1	981.1	981.1	981.1	981.1	979.8	978.6
142.5°	1023.5	1024.6	1025.6	1026.1	1026.0	1025.7	1025.5	1025.2	1025.0	1024.2	1023.4
145°	1068.6	1069.6	1070.7	1071.2	1071.1	1070.8	1070.5	1070.3	1070.0	1068.5	1066.9
147.5°	1109.0	1110.0	1111.1	1111.6	1111.3	1110.8	1110.3	1109.7	1109.2	1108.2	1107.2
150°	1147.7	1148.5	1149.2	1149.6	1149.2	1148.5	1147.7	1147.0	1146.2	1145.2	1144.2
152.5°	1185.1	1186.2	1187.2	1187.7	1187.2	1186.2	1185.1	1184.1	1183.1	1181.8	1180.5
155°	1217.0	1217.7	1218.5	1218.9	1218.3	1217.0	1215.7	1214.4	1213.1	1212.3	1211.6
157.5°	1246.9	1248.2	1249.5	1250.1	1249.2	1247.4	1245.6	1243.8	1242.0	1241.5	1241.0
160°	1272.9	1273.9	1275.0	1275.5	1274.7	1273.2	1271.6	1270.1	1268.5	1268.3	1268.0
162.5°	1296.5	1297.8	1299.1	1299.7	1298.8	1297.0	1295.2	1293.4	1291.6	1291.4	1291.1
165°	1316.1	1317.4	1318.7	1319.3	1318.4	1316.6	1314.8	1313.0	1311.2	1311.2	1311.2
167.5°	1333.4	1334.7	1336.0	1336.6	1335.7	1333.9	1332.2	1330.4	1328.6	1328.6	1328.6
170°	1346.7	1348.2	1349.7	1350.5	1349.6	1347.8	1346.0	1344.2	1342.4	1342.7	1342.9
172.5°	1357.0	1358.6	1360.1	1360.9	1360.0	1358.2	1356.4	1354.6	1352.8	1353.0	1353.3
175°	1364.0	1365.5	1367.0	1367.8	1366.9	1365.1	1363.3	1361.5	1359.7	1360.2	1360.7
177.5°	1367.4	1369.0	1370.5	1371.3	1370.5	1369.0	1367.4	1365.9	1364.3	1364.8	1365.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	987.4	983.7	981.5	983.0	978.5	967.4	967.4	971.1	966.7	962.2	955.6
5°	1014.8	1007.4	1002.9	1002.2	991.8	974.1	970.4	966.7	957.1	946.7	935.6
7.5°	1041.4	1028.1	1020.7	1015.5	1000.7	977.8	968.2	960.0	944.5	929.0	914.9
10°	1063.6	1044.3	1035.5	1027.3	1008.1	979.3	963.7	948.9	929.0	909.0	891.2
12.5°	1081.3	1059.1	1048.0	1036.2	1012.5	974.8	955.6	931.9	911.9	885.3	867.6
15°	1110.9	1065.0	1054.7	1043.6	1019.2	967.4	943.8	917.1	889.8	854.3	835.0
17.5°	1134.6	1073.2	1072.4	1048.8	1017.0	964.5	928.2	893.5	863.9	828.4	798.0
20°	1148.6	1085.8	1073.9	1049.5	1009.6	944.5	906.8	868.3	836.5	793.6	763.3
22.5°	1160.5	1103.5	1072.4	1042.9	994.0	937.8	882.4	846.1	802.5	755.9	727.0
25°	1164.9	1107.2	1074.7	1040.6	983.0	918.6	855.7	816.5	767.7	725.6	686.4
27.5°	1165.6	1106.5	1066.5	1031.0	967.4	893.5	829.1	787.7	733.7	684.9	645.7
30°	1158.2	1098.3	1062.1	1023.6	952.6	870.5	796.6	750.7	693.0	644.2	603.5
32.5°	1136.1	1082.1	1052.5	1010.3	933.4	838.7	765.5	714.5	653.8	605.7	566.5
35°	1099.1	1062.1	1029.5	990.3	908.3	809.1	734.4	674.5	613.1	567.3	530.3
37.5°	1053.2	1033.2	1002.9	964.5	879.4	782.5	699.7	633.1	571.7	527.3	491.1
40°	991.1	996.3	966.7	931.9	845.4	746.3	654.6	591.0	533.3	491.8	456.3
42.5°	923.8	945.2	928.2	894.9	807.7	706.3	621.3	551.0	494.8	451.9	422.3
45°	851.3	888.3	877.9	853.5	768.5	664.2	573.9	505.9	456.3	414.9	389.0
47.5°	772.2	824.7	824.7	806.9	724.8	622.0	533.3	463.7	414.9	385.3	360.2
50°	691.5	750.7	760.3	748.5	676.0	573.9	483.7	420.8	378.7	349.8	331.3
52.5°	607.2	676.0	693.8	687.8	624.2	528.1	443.0	381.6	343.2	318.0	301.8
55°	526.6	606.5	625.7	627.9	568.8	477.8	397.9	343.9	306.9	289.9	275.9
57.5°	450.4	527.3	548.8	552.5	512.6	431.9	355.8	308.4	275.1	261.1	250.0
60°	385.3	449.7	477.8	485.9	451.2	378.7	316.6	270.7	245.6	232.2	221.9
62.5°	332.1	383.9	413.4	415.7	400.1	332.1	275.9	237.4	216.0	204.1	199.0
65°	280.3	326.9	344.7	353.5	341.0	287.7	238.2	206.4	189.3	179.0	173.8
67.5°	238.9	268.5	283.3	295.1	282.5	242.6	202.7	176.8	164.2	153.8	150.9
70°	196.0	220.4	231.5	243.3	232.2	201.9	173.1	149.4	138.3	130.2	126.5
72.5°	156.8	176.0	186.4	193.8	187.1	162.0	138.3	122.0	113.9	108.0	105.8
75°	124.3	137.6	143.5	148.7	145.7	126.5	111.7	98.4	91.0	85.8	84.3
77.5°	94.7	104.3	110.9	112.4	108.7	96.2	83.6	75.4	69.5	66.6	65.1
80°	67.3	73.2	76.9	79.1	75.4	70.3	61.4	55.5	50.3	46.6	45.9
82.5°	45.1	48.1	51.0	50.3	48.8	44.4	39.2	36.2	34.0	31.1	31.1
85°	25.9	26.6	28.1	28.8	28.1	25.1	22.2	20.7	19.2	17.0	17.0
87.5°	11.1	11.8	11.8	12.6	11.1	11.1	9.6	8.1	8.1	7.4	6.7
90°	23.5	17.8	15.0	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	35.0	34.7	34.6	33.6	31.5	29.5	27.4	25.4	27.4	29.5	31.5
95°	72.4	71.9	71.6	70.3	67.7	65.2	62.6	60.0	62.6	65.2	67.7
97.5°	112.3	111.3	110.8	109.6	107.3	105.0	102.7	100.4	102.7	105.0	107.3
100°	157.0	156.2	155.8	154.8	152.7	150.7	148.6	146.6	148.6	150.7	152.7
102.5°	203.5	202.5	202.0	201.2	199.7	198.2	196.6	195.1	196.6	198.2	199.7
105°	252.4	251.9	251.6	251.2	250.5	249.7	249.0	248.2	249.0	249.7	250.5
107.5°	305.9	305.9	305.9	305.4	304.4	303.3	302.3	301.3	302.3	303.3	304.4
110°	359.0	359.0	359.0	358.2	356.7	355.1	353.6	352.0	353.6	355.1	356.7

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	414.0	414.3	414.4	413.6	412.1	410.6	409.0	407.5	409.0	410.6	412.1
115°	467.8	468.3	468.6	467.8	466.3	464.8	463.2	461.7	463.2	464.8	466.3
117.5°	523.3	524.6	525.2	524.2	522.1	520.1	518.0	516.0	518.0	520.1	522.1
120°	576.3	578.4	579.4	578.4	576.3	574.3	572.2	570.2	572.2	574.3	576.3
122.5°	629.5	630.8	631.4	630.1	627.5	625.0	622.4	619.8	622.4	625.0	627.5
125°	681.0	681.8	682.2	681.0	678.7	676.4	674.1	671.8	674.1	676.4	678.7
127.5°	733.7	734.8	735.3	733.9	731.1	728.2	725.4	722.6	725.4	728.2	731.1
130°	784.1	784.6	784.9	783.2	779.9	776.6	773.2	769.9	773.2	776.6	779.9
132.5°	834.9	834.6	834.5	833.2	830.7	828.1	825.6	823.0	825.6	828.1	830.7
135°	882.7	882.2	881.9	880.5	877.7	874.8	872.0	869.2	872.0	874.8	877.7
137.5°	931.1	930.6	930.3	929.1	926.8	924.5	922.2	919.9	922.2	924.5	926.8
140°	977.3	976.0	975.4	974.2	971.9	969.6	967.3	965.0	967.3	969.6	971.9
142.5°	1022.7	1021.9	1021.5	1020.3	1018.0	1015.7	1013.4	1011.1	1013.4	1015.7	1018.0
145°	1065.4	1063.9	1063.1	1062.2	1060.4	1058.6	1056.8	1055.0	1056.8	1058.6	1060.4
147.5°	1106.1	1105.1	1104.6	1103.4	1101.1	1098.8	1096.5	1094.2	1096.5	1098.8	1101.1
150°	1143.1	1142.1	1141.6	1140.8	1139.3	1137.7	1136.2	1134.6	1136.2	1137.7	1139.3
152.5°	1179.2	1177.9	1177.3	1176.5	1175.0	1173.5	1171.9	1170.4	1171.9	1173.5	1175.0
155°	1210.8	1210.1	1209.7	1209.3	1208.5	1207.8	1207.0	1206.2	1207.0	1207.8	1208.5
157.5°	1240.5	1240.0	1239.7	1239.4	1238.9	1238.4	1237.9	1237.4	1237.9	1238.4	1238.9
160°	1267.8	1267.5	1267.4	1267.1	1266.6	1266.1	1265.6	1265.1	1265.6	1266.1	1266.6
162.5°	1290.9	1290.6	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
165°	1311.2	1311.2	1311.2	1311.3	1311.6	1311.9	1312.1	1312.4	1312.1	1311.9	1311.6
167.5°	1328.6	1328.6	1328.6	1329.0	1329.7	1330.5	1331.2	1332.0	1331.2	1330.5	1329.7
170°	1343.2	1343.5	1343.6	1344.0	1344.7	1345.5	1346.2	1347.0	1346.2	1345.5	1344.7
172.5°	1353.5	1353.8	1353.9	1354.3	1355.1	1355.8	1356.6	1357.4	1356.6	1355.8	1355.1
175°	1361.2	1361.7	1362.0	1362.4	1363.2	1363.9	1364.7	1365.5	1364.7	1363.9	1363.2
177.5°	1365.8	1366.3	1366.6	1367.0	1367.8	1368.5	1369.3	1370.1	1369.3	1368.5	1367.8
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	951.9	955.6	954.8	947.5	939.3	932.7	920.1	921.6	917.1	917.9	922.3
5°	928.2	928.2	925.3	914.9	901.6	894.2	880.1	876.4	867.6	866.8	866.1
7.5°	903.1	899.4	895.7	880.9	864.6	852.8	833.5	829.1	820.2	814.3	811.4
10°	873.5	868.3	860.9	843.9	823.9	809.1	789.2	783.3	766.2	758.8	754.4
12.5°	840.9	838.0	826.2	812.1	779.6	763.3	734.4	740.4	723.3	708.6	706.3
15°	808.4	797.3	790.7	767.7	728.5	721.1	698.2	686.4	670.8	659.0	659.0
17.5°	776.6	759.6	744.8	720.4	691.5	670.8	653.8	647.9	628.7	616.8	614.6
20°	734.4	715.2	711.5	676.8	656.8	633.9	617.6	602.8	588.7	583.6	579.9
22.5°	694.5	672.3	666.4	636.8	616.8	593.9	577.6	567.3	556.9	553.2	546.6
25°	651.6	638.3	629.4	597.6	575.4	554.0	542.9	535.5	525.9	525.1	520.7
27.5°	610.2	597.6	588.7	558.4	542.1	522.2	513.3	505.2	500.0	497.8	495.5
30°	574.7	560.6	550.3	528.1	508.1	491.8	484.4	479.3	476.3	472.6	471.9
32.5°	535.5	527.3	513.3	496.3	480.8	465.2	460.8	457.1	452.6	451.2	450.4
35°	502.2	491.1	482.2	463.0	456.3	443.0	437.9	434.9	429.0	427.5	426.0
37.5°	469.7	459.3	449.7	437.9	425.3	417.9	414.9	410.5	407.5	408.3	406.8
40°	437.1	429.0	421.6	409.0	401.6	397.9	392.0	387.6	386.1	386.8	386.1
42.5°	405.3	397.9	393.5	383.9	376.5	372.8	369.1	364.6	366.9	366.9	369.1
45°	376.5	369.8	366.9	359.5	355.0	349.1	345.4	344.7	347.6	346.9	346.9
47.5°	346.9	344.7	341.0	334.3	328.4	324.7	324.0	324.0	326.9	328.4	327.7
50°	324.0	319.5	315.1	309.9	305.5	304.0	301.8	303.2	306.2	306.2	307.7
52.5°	295.1	292.1	290.7	286.2	283.3	283.3	283.3	284.0	286.2	288.5	287.7
55°	270.0	267.7	266.3	264.0	260.3	261.1	260.3	261.8	264.0	266.3	267.7
57.5°	243.3	242.6	241.1	237.4	237.4	236.7	238.9	239.6	243.3	244.8	247.0
60°	219.7	217.4	217.4	214.5	214.5	214.5	216.7	218.9	221.9	222.6	224.1
62.5°	194.5	194.5	193.8	191.6	191.6	193.8	194.5	197.5	199.0	199.0	201.2
65°	170.9	170.1	169.4	170.1	170.9	170.9	173.1	174.5	176.0	176.8	177.5
67.5°	147.2	146.4	147.9	147.2	148.7	151.6	150.9	153.1	155.3	155.3	156.1
70°	125.0	126.5	125.7	127.2	126.5	128.0	130.2	130.9	130.9	131.7	133.9
72.5°	104.3	104.3	104.3	103.5	104.3	105.8	107.2	108.0	109.5	110.2	112.4
75°	84.3	84.3	82.8	84.3	84.3	85.8	87.3	87.3	87.3	88.8	91.0
77.5°	63.6	64.3	63.6	65.1	65.1	65.8	67.3	66.6	68.0	68.8	69.5
80°	46.6	45.9	45.9	45.9	46.6	46.6	48.1	48.8	48.8	51.0	49.6
82.5°	29.6	30.3	29.6	30.3	30.3	31.1	30.3	31.1	31.8	33.3	32.5
85°	17.0	16.3	16.3	17.0	16.3	16.3	17.0	16.3	17.0	16.3	17.0
87.5°	6.7	5.9	5.9	5.9	5.9	5.2	5.2	4.4	4.4	4.4	3.7
90°	13.5	15.0	17.8	23.5	29.1	34.8	40.4	39.9	39.4	38.9	38.4
92.5°	33.6	34.6	34.7	35.0	35.3	35.5	35.8	36.0	36.3	36.5	36.8
95°	70.3	71.6	71.9	72.4	72.9	73.4	73.9	73.9	73.9	73.9	73.9
97.5°	109.6	110.8	111.3	112.3	113.4	114.4	115.4	115.4	115.4	115.4	115.4
100°	154.8	155.8	156.2	157.0	157.7	158.5	159.3	159.3	159.3	159.3	159.3
102.5°	201.2	202.0	202.5	203.5	204.6	205.6	206.6	206.9	207.1	207.4	207.7
105°	251.2	251.6	251.9	252.4	252.9	253.4	253.9	254.4	254.9	255.4	255.9
107.5°	305.4	305.9	305.9	305.9	305.9	305.9	305.9	306.1	306.4	306.6	306.9
110°	358.2	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	413.6	414.4	414.3	414.0	413.7	413.5	413.2	412.4	411.7	410.9	410.2
115°	467.8	468.6	468.3	467.8	467.3	466.8	466.3	466.1	465.8	465.6	465.3
117.5°	524.2	525.2	524.6	523.3	522.0	520.7	519.4	518.6	517.9	517.1	516.4
120°	578.4	579.4	578.4	576.3	574.3	572.2	570.2	570.2	570.2	570.2	570.2
122.5°	630.1	631.4	630.8	629.5	628.2	626.9	625.6	624.8	624.0	623.3	622.5
125°	681.0	682.2	681.8	681.0	680.3	679.5	678.7	677.9	677.1	676.4	675.6
127.5°	733.9	735.3	734.8	733.7	732.7	731.6	730.6	729.6	728.6	727.5	726.5
130°	783.2	784.9	784.6	784.1	783.6	783.1	782.6	782.1	781.6	781.1	780.6
132.5°	833.2	834.5	834.6	834.9	835.2	835.4	835.7	834.4	833.1	831.8	830.5
135°	880.5	881.9	882.2	882.7	883.2	883.7	884.2	883.9	883.7	883.4	883.1
137.5°	929.1	930.3	930.6	931.1	931.6	932.1	932.6	932.4	932.1	931.9	931.6
140°	974.2	975.4	976.0	977.3	978.6	979.8	981.1	981.1	981.1	981.1	981.1
142.5°	1020.3	1021.5	1021.9	1022.7	1023.4	1024.2	1025.0	1025.2	1025.5	1025.7	1026.0
145°	1062.2	1063.1	1063.9	1065.4	1066.9	1068.5	1070.0	1070.3	1070.5	1070.8	1071.1
147.5°	1103.4	1104.6	1105.1	1106.1	1107.2	1108.2	1109.2	1109.7	1110.3	1110.8	1111.3
150°	1140.8	1141.6	1142.1	1143.1	1144.2	1145.2	1146.2	1147.0	1147.7	1148.5	1149.2
152.5°	1176.5	1177.3	1177.9	1179.2	1180.5	1181.8	1183.1	1184.1	1185.1	1186.2	1187.2
155°	1209.3	1209.7	1210.1	1210.8	1211.6	1212.3	1213.1	1214.4	1215.7	1217.0	1218.3
157.5°	1239.4	1239.7	1240.0	1240.5	1241.0	1241.5	1242.0	1243.8	1245.6	1247.4	1249.2
160°	1267.1	1267.4	1267.5	1267.8	1268.0	1268.3	1268.5	1270.1	1271.6	1273.2	1274.7
162.5°	1290.5	1290.5	1290.6	1290.9	1291.1	1291.4	1291.6	1293.4	1295.2	1297.0	1298.8
165°	1311.3	1311.2	1311.2	1311.2	1311.2	1311.2	1311.2	1313.0	1314.8	1316.6	1318.4
167.5°	1329.0	1328.6	1328.6	1328.6	1328.6	1328.6	1328.6	1330.4	1332.2	1333.9	1335.7
170°	1344.0	1343.6	1343.5	1343.2	1342.9	1342.7	1342.4	1344.2	1346.0	1347.8	1349.6
172.5°	1354.3	1353.9	1353.8	1353.5	1353.3	1353.0	1352.8	1354.6	1356.4	1358.2	1360.0
175°	1362.4	1362.0	1361.7	1361.2	1360.7	1360.2	1359.7	1361.5	1363.3	1365.1	1366.9
177.5°	1367.0	1366.6	1366.3	1365.8	1365.3	1364.8	1364.3	1365.9	1367.4	1369.0	1370.5
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	917.1	919.3	914.2	912.7	914.2	909.0	910.5	911.9	911.9	914.2	915.6
5°	863.9	860.9	855.7	854.3	852.8	855.0	853.5	855.7	856.5	861.7	862.4
7.5°	811.4	806.9	802.5	798.0	796.6	792.9	796.6	796.6	801.7	800.3	804.0
10°	749.2	748.5	742.6	740.4	737.4	731.5	739.6	737.4	741.1	747.8	749.2
12.5°	703.4	695.2	698.9	688.6	692.3	686.4	687.1	687.1	693.0	693.8	692.3
15°	659.7	653.1	643.5	639.0	636.8	633.9	643.5	644.2	639.8	650.1	646.4
17.5°	615.4	615.4	606.5	604.3	598.4	601.3	599.8	600.6	599.1	606.5	610.2
20°	576.9	573.2	570.2	571.0	563.6	562.1	560.6	562.1	567.3	572.5	573.9
22.5°	545.8	543.6	536.2	537.7	531.8	534.0	532.5	536.2	537.0	537.0	542.1
25°	516.3	513.3	514.0	511.1	508.9	508.9	506.6	508.9	511.8	513.3	514.0
27.5°	494.1	491.8	488.1	485.9	487.4	483.7	486.7	488.9	488.9	487.4	488.9
30°	467.4	468.9	468.9	461.5	464.5	463.0	465.2	466.7	466.7	467.4	466.0
32.5°	449.7	445.2	444.5	443.8	443.8	440.8	440.8	443.0	443.8	444.5	446.7
35°	426.0	426.0	422.3	424.5	421.6	422.3	421.6	422.3	423.8	421.6	423.8
37.5°	404.6	405.3	403.8	405.3	406.1	404.6	403.1	406.1	404.6	404.6	403.1
40°	386.1	385.3	386.1	386.1	386.1	386.8	385.3	385.3	385.3	383.9	382.4
42.5°	370.5	366.1	367.6	368.3	366.1	366.1	366.9	366.1	368.3	363.9	363.9
45°	348.4	346.9	347.6	347.6	349.1	346.9	348.4	349.1	346.9	346.1	344.7
47.5°	328.4	329.9	328.4	329.9	329.9	331.3	328.4	329.1	329.9	326.9	324.7
50°	308.4	308.4	310.6	309.9	310.6	309.2	309.2	308.4	309.2	307.7	305.5
52.5°	289.9	287.7	291.4	290.7	289.9	289.2	288.5	289.2	287.7	286.2	286.2
55°	267.0	267.0	269.2	270.0	270.0	268.5	267.0	267.7	267.0	266.3	265.5
57.5°	248.5	245.6	247.0	247.8	247.8	245.6	247.0	245.6	245.6	246.3	244.1
60°	224.8	224.8	223.4	225.6	225.6	224.1	224.1	224.8	223.4	222.6	221.9
62.5°	199.7	200.4	202.7	203.4	204.1	202.7	201.2	201.9	201.9	199.7	200.4
65°	178.2	179.7	182.7	181.9	180.5	181.2	179.7	180.5	178.2	179.0	176.8
67.5°	157.5	156.8	157.5	157.5	159.0	158.3	156.8	156.8	156.1	158.3	156.1
70°	135.4	135.4	135.4	135.4	136.1	136.8	135.4	133.9	134.6	133.1	132.4
72.5°	112.4	113.2	112.4	113.9	111.7	113.2	113.2	112.4	111.7	111.7	111.7
75°	91.0	92.5	90.2	91.0	90.2	91.7	91.0	91.0	89.5	88.8	89.5
77.5°	69.5	70.3	68.8	69.5	68.8	69.5	69.5	68.8	68.8	68.8	68.8
80°	49.6	50.3	49.6	48.8	48.1	49.6	48.1	48.8	49.6	48.8	50.3
82.5°	31.8	31.8	31.1	31.8	30.3	30.3	31.1	31.1	30.3	31.8	30.3
85°	15.5	15.5	17.0	15.5	14.8	14.8	14.8	15.5	14.8	16.3	15.5
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.4	3.0
90°	38.1	38.2	38.5	38.7	39.0	39.2	39.0	38.7	38.5	38.2	38.1
92.5°	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9
95°	73.9	73.6	73.1	72.6	72.1	71.6	72.1	72.6	73.1	73.6	73.9
97.5°	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4
100°	159.3	159.2	158.9	158.6	158.4	158.1	158.4	158.6	158.9	159.2	159.3
102.5°	207.8	207.7	207.4	207.1	206.9	206.6	206.9	207.1	207.4	207.7	207.8
105°	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2
107.5°	307.0	306.4	305.1	303.8	302.6	301.3	302.6	303.8	305.1	306.4	307.0
110°	359.0	358.6	357.8	357.1	356.3	355.5	356.3	357.1	357.8	358.6	359.0

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	409.8	409.5	409.0	408.5	408.0	407.5	408.0	408.5	409.0	409.5	409.8
115°	465.2	464.8	464.0	463.3	462.5	461.7	462.5	463.3	464.0	464.8	465.2
117.5°	516.0	515.6	514.8	514.1	513.3	512.5	513.3	514.1	514.8	515.6	516.0
120°	570.2	569.8	569.0	568.3	567.5	566.7	567.5	568.3	569.0	569.8	570.2
122.5°	622.1	621.8	621.3	620.8	620.3	619.8	620.3	620.8	621.3	621.8	622.1
125°	675.2	675.1	674.8	674.6	674.3	674.1	674.3	674.6	674.8	675.1	675.2
127.5°	726.0	725.6	724.9	724.1	723.4	722.6	723.4	724.1	724.9	725.6	726.0
130°	780.3	779.8	778.8	777.7	776.7	775.7	776.7	777.7	778.8	779.8	780.3
132.5°	829.9	829.5	828.8	828.0	827.3	826.5	827.3	828.0	828.8	829.5	829.9
135°	883.0	882.6	881.8	881.1	880.3	879.5	880.3	881.1	881.8	882.6	883.0
137.5°	931.5	931.0	930.0	928.9	927.9	926.9	927.9	928.9	930.0	931.0	931.5
140°	981.1	980.6	979.6	978.5	977.5	976.5	977.5	978.5	979.6	980.6	981.1
142.5°	1026.1	1025.6	1024.6	1023.5	1022.5	1021.5	1022.5	1023.5	1024.6	1025.6	1026.1
145°	1071.2	1070.7	1069.6	1068.6	1067.5	1066.5	1067.5	1068.6	1069.6	1070.7	1071.2
147.5°	1111.6	1111.1	1110.0	1109.0	1107.9	1106.9	1107.9	1109.0	1110.0	1111.1	1111.6
150°	1149.6	1149.2	1148.5	1147.7	1147.0	1146.2	1147.0	1147.7	1148.5	1149.2	1149.6
152.5°	1187.7	1187.2	1186.2	1185.1	1184.1	1183.1	1184.1	1185.1	1186.2	1187.2	1187.7
155°	1218.9	1218.5	1217.7	1217.0	1216.2	1215.4	1216.2	1217.0	1217.7	1218.5	1218.9
157.5°	1250.1	1249.5	1248.2	1246.9	1245.6	1244.3	1245.6	1246.9	1248.2	1249.5	1250.1
160°	1275.5	1275.0	1273.9	1272.9	1271.8	1270.8	1271.8	1272.9	1273.9	1275.0	1275.5
162.5°	1299.7	1299.1	1297.8	1296.5	1295.2	1293.9	1295.2	1296.5	1297.8	1299.1	1299.7
165°	1319.3	1318.7	1317.4	1316.1	1314.8	1313.5	1314.8	1316.1	1317.4	1318.7	1319.3
167.5°	1336.6	1336.0	1334.7	1333.4	1332.2	1330.9	1332.2	1333.4	1334.7	1336.0	1336.6
170°	1350.5	1349.7	1348.2	1346.7	1345.1	1343.6	1345.1	1346.7	1348.2	1349.7	1350.5
172.5°	1360.9	1360.1	1358.6	1357.0	1355.5	1353.9	1355.5	1357.0	1358.6	1360.1	1360.9
175°	1367.8	1367.0	1365.5	1364.0	1362.4	1360.9	1362.4	1364.0	1365.5	1367.0	1367.8
177.5°	1371.3	1370.5	1369.0	1367.4	1365.9	1364.3	1365.9	1367.4	1369.0	1370.5	1371.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	913.4	919.3	917.1	909.0	918.6	918.6	925.3	925.3	933.4	936.4	940.8
5°	861.7	866.1	869.8	866.1	872.7	883.1	889.0	894.2	905.3	909.7	916.4
7.5°	806.2	814.3	818.0	818.0	829.1	840.9	852.8	860.2	875.7	881.6	888.3
10°	752.2	761.8	769.2	768.5	787.0	794.3	809.1	826.2	841.7	850.6	860.2
12.5°	695.2	700.4	710.8	725.6	730.0	743.3	760.3	781.8	809.9	818.0	832.1
15°	647.9	662.0	670.1	676.8	687.1	699.7	718.2	738.9	767.0	784.7	799.5
17.5°	608.0	626.5	631.6	630.2	643.5	662.7	684.1	699.7	724.8	746.3	760.3
20°	575.4	582.8	591.7	595.4	605.7	626.5	647.2	664.9	685.6	702.6	718.9
22.5°	542.9	548.8	556.2	562.8	571.0	582.8	602.8	625.0	644.9	661.2	679.7
25°	516.3	520.0	526.6	531.8	540.7	548.8	562.8	587.3	610.9	620.5	636.8
27.5°	490.4	493.3	497.8	503.7	508.1	516.3	528.8	548.8	573.2	582.8	605.0
30°	467.4	469.7	474.1	477.1	479.3	488.9	498.5	514.0	532.5	545.8	562.1
32.5°	446.0	448.2	452.6	453.4	456.3	461.5	470.4	484.4	500.7	511.8	525.9
35°	422.3	423.8	428.2	429.7	431.9	436.4	443.0	453.4	468.2	476.3	488.9
37.5°	403.8	403.1	406.1	408.3	411.2	413.4	415.7	426.0	437.1	444.5	454.1
40°	383.9	382.4	383.1	386.1	387.6	390.5	390.5	400.9	408.3	414.2	421.6
42.5°	363.9	363.2	361.7	363.2	364.6	365.4	366.1	373.5	380.9	386.1	394.2
45°	343.9	343.2	341.7	342.4	342.4	343.9	346.1	349.1	354.3	358.7	363.2
47.5°	325.4	324.0	321.7	321.0	322.5	322.5	322.5	325.4	330.6	332.1	336.5
50°	306.2	304.0	301.0	299.5	299.5	298.8	300.3	301.0	305.5	306.9	310.6
52.5°	285.5	284.0	281.1	278.1	278.8	277.4	278.1	278.8	280.3	282.5	284.8
55°	264.8	261.8	259.6	258.9	256.6	256.6	254.4	257.4	256.6	257.4	260.3
57.5°	244.8	241.9	238.2	236.7	234.5	233.7	232.2	231.5	232.2	234.5	236.7
60°	221.1	219.7	217.4	215.2	213.7	211.5	210.1	210.1	209.3	209.3	210.1
62.5°	198.2	197.5	194.5	193.8	192.3	190.8	188.6	187.1	187.1	188.6	189.3
65°	176.0	175.3	173.1	172.3	168.6	167.2	166.4	165.7	164.2	164.2	164.2
67.5°	155.3	153.1	153.1	149.4	146.4	145.0	143.5	142.7	142.7	142.7	143.5
70°	132.4	132.4	130.2	128.0	125.0	125.7	123.5	121.3	121.3	119.8	120.6
72.5°	110.2	109.5	107.2	106.5	104.3	102.1	100.6	102.1	99.8	99.1	99.8
75°	88.8	88.0	86.5	85.1	85.8	83.6	81.4	80.6	80.6	79.1	79.1
77.5°	68.0	69.5	66.6	65.8	64.3	62.9	62.1	61.4	61.4	61.4	62.9
80°	47.3	48.1	48.1	46.6	47.3	45.1	45.1	45.1	42.9	43.6	44.4
82.5°	30.3	30.3	29.6	30.3	29.6	29.6	28.8	28.8	28.1	28.1	28.8
85°	17.0	16.3	15.5	17.0	16.3	16.3	15.5	15.5	15.5	15.5	15.5
87.5°	3.7	4.4	4.4	4.4	4.4	5.2	5.2	5.2	5.9	5.9	5.9
90°	38.4	38.9	39.4	39.9	40.4	34.8	29.1	23.5	17.8	15.0	13.5
92.5°	36.8	36.5	36.3	36.0	35.8	35.5	35.3	35.0	34.7	34.6	33.6
95°	73.9	73.9	73.9	73.9	73.9	73.4	72.9	72.4	71.9	71.6	70.3
97.5°	115.4	115.4	115.4	115.4	115.4	114.4	113.4	112.3	111.3	110.8	109.6
100°	159.3	159.3	159.3	159.3	159.3	158.5	157.7	157.0	156.2	155.8	154.8
102.5°	207.7	207.4	207.1	206.9	206.6	205.6	204.6	203.5	202.5	202.0	201.2
105°	255.9	255.4	254.9	254.4	253.9	253.4	252.9	252.4	251.9	251.6	251.2
107.5°	306.9	306.6	306.4	306.1	305.9	305.9	305.9	305.9	305.9	305.9	305.4
110°	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	358.2

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	410.2	410.9	411.7	412.4	413.2	413.5	413.7	414.0	414.3	414.4	413.6
115°	465.3	465.6	465.8	466.1	466.3	466.8	467.3	467.8	468.3	468.6	467.8
117.5°	516.4	517.1	517.9	518.6	519.4	520.7	522.0	523.3	524.6	525.2	524.2
120°	570.2	570.2	570.2	570.2	570.2	572.2	574.3	576.3	578.4	579.4	578.4
122.5°	622.5	623.3	624.0	624.8	625.6	626.9	628.2	629.5	630.8	631.4	630.1
125°	675.6	676.4	677.1	677.9	678.7	679.5	680.3	681.0	681.8	682.2	681.0
127.5°	726.5	727.5	728.6	729.6	730.6	731.6	732.7	733.7	734.8	735.3	733.9
130°	780.6	781.1	781.6	782.1	782.6	783.1	783.6	784.1	784.6	784.9	783.2
132.5°	830.5	831.8	833.1	834.4	835.7	835.4	835.2	834.9	834.6	834.5	833.2
135°	883.1	883.4	883.7	883.9	884.2	883.7	883.2	882.7	882.2	881.9	880.5
137.5°	931.6	931.9	932.1	932.4	932.6	932.1	931.6	931.1	930.6	930.3	929.1
140°	981.1	981.1	981.1	981.1	981.1	979.8	978.6	977.3	976.0	975.4	974.2
142.5°	1026.0	1025.7	1025.5	1025.2	1025.0	1024.2	1023.4	1022.7	1021.9	1021.5	1020.3
145°	1071.1	1070.8	1070.5	1070.3	1070.0	1068.5	1066.9	1065.4	1063.9	1063.1	1062.2
147.5°	1111.3	1110.8	1110.3	1109.7	1109.2	1108.2	1107.2	1106.1	1105.1	1104.6	1103.4
150°	1149.2	1148.5	1147.7	1147.0	1146.2	1145.2	1144.2	1143.1	1142.1	1141.6	1140.8
152.5°	1187.2	1186.2	1185.1	1184.1	1183.1	1181.8	1180.5	1179.2	1177.9	1177.3	1176.5
155°	1218.3	1217.0	1215.7	1214.4	1213.1	1212.3	1211.6	1210.8	1210.1	1209.7	1209.3
157.5°	1249.2	1247.4	1245.6	1243.8	1242.0	1241.5	1241.0	1240.5	1240.0	1239.7	1239.4
160°	1274.7	1273.2	1271.6	1270.1	1268.5	1268.3	1268.0	1267.8	1267.5	1267.4	1267.1
162.5°	1298.8	1297.0	1295.2	1293.4	1291.6	1291.4	1291.1	1290.9	1290.6	1290.5	1290.5
165°	1318.4	1316.6	1314.8	1313.0	1311.2	1311.2	1311.2	1311.2	1311.2	1311.2	1311.3
167.5°	1335.7	1333.9	1332.2	1330.4	1328.6	1328.6	1328.6	1328.6	1328.6	1328.6	1329.0
170°	1349.6	1347.8	1346.0	1344.2	1342.4	1342.7	1342.9	1343.2	1343.5	1343.6	1344.0
172.5°	1360.0	1358.2	1356.4	1354.6	1352.8	1353.0	1353.3	1353.5	1353.8	1353.9	1354.3
175°	1366.9	1365.1	1363.3	1361.5	1359.7	1360.2	1360.7	1361.2	1361.7	1362.0	1362.4
177.5°	1370.5	1369.0	1367.4	1365.9	1364.3	1364.8	1365.3	1365.8	1366.3	1366.6	1367.0
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	962.2	962.2	962.2	962.2
2.5°	944.5	944.5	955.6	967.4
5°	923.8	929.0	946.7	963.0
7.5°	903.8	912.7	934.9	955.6
10°	879.4	891.2	918.6	943.0
12.5°	855.7	866.8	898.6	926.0
15°	822.5	836.5	870.5	904.6
17.5°	789.2	803.2	844.6	884.6
20°	750.0	768.5	815.1	868.3
22.5°	713.7	736.7	788.4	831.3
25°	673.8	709.3	757.4	812.8
27.5°	638.3	673.8	722.6	778.8
30°	598.4	634.6	684.9	736.7
32.5°	559.9	593.2	642.0	705.6
35°	520.0	551.8	599.1	663.4
37.5°	483.7	514.8	566.5	625.7
40°	448.2	480.8	525.1	584.3
42.5°	414.9	443.8	483.7	542.9
45°	384.6	405.3	442.3	497.8
47.5°	352.8	371.3	405.3	460.8
50°	323.2	338.7	368.3	420.1
52.5°	294.4	307.7	335.0	376.5
55°	268.5	281.1	301.0	341.7
57.5°	241.9	251.5	270.7	303.2
60°	216.0	224.8	240.4	267.0
62.5°	190.1	197.5	212.3	233.7
65°	167.2	173.1	184.2	202.7
67.5°	145.0	148.7	157.5	172.3
70°	123.5	126.5	133.9	145.7
72.5°	100.6	103.5	111.7	119.8
75°	81.4	82.1	88.0	94.7
77.5°	63.6	62.9	67.3	72.5
80°	43.6	45.9	49.6	51.8
82.5°	29.6	30.3	31.8	33.3
85°	16.3	17.0	17.0	19.2
87.5°	6.7	7.4	7.4	8.1
90°	10.4	7.3	4.3	1.2
92.5°	31.5	29.5	27.4	25.4
95°	67.7	65.2	62.6	60.0
97.5°	107.3	105.0	102.7	100.4
100°	152.7	150.7	148.6	146.6
102.5°	199.7	198.2	196.6	195.1
105°	250.5	249.7	249.0	248.2
107.5°	304.4	303.3	302.3	301.3
110°	356.7	355.1	353.6	352.0

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	412.1	410.6	409.0	407.5
115°	466.3	464.8	463.2	461.7
117.5°	522.1	520.1	518.0	516.0
120°	576.3	574.3	572.2	570.2
122.5°	627.5	625.0	622.4	619.8
125°	678.7	676.4	674.1	671.8
127.5°	731.1	728.2	725.4	722.6
130°	779.9	776.6	773.2	769.9
132.5°	830.7	828.1	825.6	823.0
135°	877.7	874.8	872.0	869.2
137.5°	926.8	924.5	922.2	919.9
140°	971.9	969.6	967.3	965.0
142.5°	1018.0	1015.7	1013.4	1011.1
145°	1060.4	1058.6	1056.8	1055.0
147.5°	1101.1	1098.8	1096.5	1094.2
150°	1139.3	1137.7	1136.2	1134.6
152.5°	1175.0	1173.5	1171.9	1170.4
155°	1208.5	1207.8	1207.0	1206.2
157.5°	1238.9	1238.4	1237.9	1237.4
160°	1266.6	1266.1	1265.6	1265.1
162.5°	1290.5	1290.5	1290.5	1290.5
165°	1311.6	1311.9	1312.1	1312.4
167.5°	1329.7	1330.5	1331.2	1332.0
170°	1344.7	1345.5	1346.2	1347.0
172.5°	1355.1	1355.8	1356.6	1357.4
175°	1363.2	1363.9	1364.7	1365.5
177.5°	1367.8	1368.5	1369.3	1370.1
180°	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998420

CATALOG NUMBER: SA2XXDIP-B485D1080UB40-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.80	14.53	14.88	15.60	17.07	11.30	12.02	12.37	13.09	14.56
	3H	14.61	15.25	15.69	16.34	17.82	12.63	13.28	13.72	14.36	15.84
	4H	14.77	15.38	15.86	16.47	17.95	13.09	13.70	14.18	14.79	16.27
	6H	14.81	15.37	15.91	16.46	17.96	13.39	13.95	14.49	15.04	16.54
	8H	14.78	15.32	15.89	16.42	17.92	13.47	14.00	14.58	15.11	16.60
	12H	14.74	15.25	15.85	16.35	17.86	13.51	14.02	14.62	15.11	16.63
4H	2H	13.83	14.44	14.93	15.53	17.02	11.73	12.34	12.83	13.42	14.91
	3H	14.80	15.31	15.91	16.42	17.92	13.18	13.69	14.28	14.80	16.30
	4H	15.07	15.54	16.18	16.64	18.16	13.70	14.17	14.82	15.27	16.79
	6H	15.19	15.59	16.31	16.72	18.23	14.08	14.48	15.20	15.60	17.11
	8H	15.19	15.56	16.31	16.68	18.21	14.18	14.56	15.30	15.67	17.20
	12H	15.15	15.49	16.28	16.61	18.15	14.23	14.57	15.37	15.70	17.24
8H	4H	15.07	15.44	16.19	16.56	18.09	13.84	14.21	14.96	15.33	16.86
	6H	15.24	15.55	16.38	16.71	18.23	14.27	14.58	15.41	15.73	17.26
	8H	15.27	15.54	16.42	16.68	18.23	14.42	14.69	15.56	15.82	17.37
	12H	15.25	15.49	16.40	16.62	18.20	14.50	14.74	15.65	15.87	17.46
12H	4H	15.02	15.36	16.16	16.49	18.02	13.80	14.14	14.94	15.27	16.81
	6H	15.22	15.49	16.37	16.63	18.17	14.27	14.54	15.41	15.67	17.22
	8H	15.25	15.48	16.40	16.62	18.20	14.42	14.65	15.57	15.79	17.37