

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998461

Luminaire Tested: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998461
REPORT IS A COMBINATION OF REPORTS P984204 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3423.0 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	97	93	90	95	91	88	85	80	78	75	70	68	67	61	59	58
2	93	85	79	74	87	80	75	71	71	67	63	62	59	57	54	52	50
3	85	76	68	63	79	71	65	60	63	58	54	56	52	49	48	46	43
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	40	38
5	72	60	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33
6	67	55	47	41	62	52	44	39	46	40	36	41	36	33	36	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24
9	54	41	34	29	50	39	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15318	15318	15318	15318
5°	15354	16332	15413	12993
10°	15176	17829	15272	10713
15°	14809	18805	15014	9023
20°	14577	17657	14577	7843
25°	14112	15170	14178	7013
30°	13348	11925	13604	6353
35°	12671	8246	12882	5813
40°	11892	6226	12028	5382
45°	10933	5116	11112	4916
50°	10103	4491	10120	4501
55°	9156	3826	9217	4049
60°	8148	3196	8260	3535
65°	7245	2599	7376	3018
70°	6344	2040	6505	2434
75°	5326	1481	5533	1765
80°	4160	938	4455	1047
85°	2726	473	2938	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15834 cd/sqm

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	2.7
10°-20°	268.3	7.8
20°-30°	389.3	11.4
30°-40°	410.4	12.0
40°-50°	363.2	10.6
50°-60°	290.0	8.5
60°-70°	197.0	5.8
70°-80°	100.8	2.9
80°-90°	25.0	0.7
90°-100°	72.0	2.1
100°-110°	253.7	7.4
110°-120°	266.4	7.8
120°-130°	219.2	6.4
130°-140°	176.1	5.1
140°-150°	133.0	3.9
150°-160°	93.5	2.7
160°-170°	55.0	1.6
170°-180°	17.9	0.5
0°-30°	749.8	21.9
0°-40°	1160.2	33.9
0°-60°	1813.4	53.0
0°-90°	2136.2	62.4
90°-120°	592.1	17.3
90°-150°	1120.4	32.7
90°-180°	1287.0	37.6
0°-180°	3423.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	968	968	968	968	968	
5°	968	1081	972	860	968	92
15°	910	1328	922	637	910	257
25°	817	1107	821	512	817	374
35°	667	602	678	425	667	417
45°	501	363	509	349	501	388
55°	344	255	346	270	344	307
65°	204	157	208	182	204	203
75°	95	77	99	92	95	102
85°	19	20	21	15	19	23
90°	0	12	0	12	0	2
95°	12	40	12	40	12	13
105°	43	400	43	400	43	46
115°	76	527	76	527	76	76
125°	107	428	107	428	107	95
135°	125	354	125	354	125	97
145°	143	283	143	283	143	90
155°	162	238	162	238	162	75
165°	177	209	177	209	177	50
175°	184	188	184	188	184	18
180°	185	185	185	185	185	

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	972.9	975.1	978.8	979.6	987.0	993.0	999.7	999.7	1001.9	1001.2	995.2
5°	968.4	975.1	984.8	993.0	1006.4	1012.3	1021.2	1027.9	1033.9	1038.3	1037.6
7.5°	961.0	972.9	987.0	1002.6	1020.5	1030.9	1043.5	1055.4	1063.6	1071.1	1076.3
10°	948.3	968.4	987.8	1008.6	1031.6	1045.8	1060.7	1076.3	1088.9	1103.1	1116.4
12.5°	931.2	960.2	984.0	1011.6	1039.8	1055.4	1079.3	1091.2	1115.7	1151.4	1161.1
15°	909.7	949.1	971.4	1006.4	1043.5	1056.2	1088.9	1108.3	1158.8	1181.2	1207.9
17.5°	889.6	933.5	963.2	1003.4	1039.8	1064.4	1096.4	1135.8	1178.2	1210.2	1239.9
20°	873.2	915.6	951.3	995.9	1042.1	1073.3	1106.8	1154.4	1200.5	1233.2	1256.3
22.5°	836.0	890.3	932.0	981.8	1037.6	1080.7	1112.7	1164.8	1214.6	1234.7	1254.8
25°	817.4	864.3	912.6	969.2	1034.6	1085.9	1113.5	1171.5	1215.4	1222.8	1227.3
27.5°	783.2	836.0	892.6	957.3	1033.9	1077.0	1112.0	1164.8	1199.7	1194.5	1181.2
30°	740.8	805.5	868.0	937.9	1023.5	1070.3	1103.1	1151.4	1169.3	1142.5	1118.7
32.5°	709.6	770.6	839.7	920.8	1011.6	1056.2	1088.2	1126.1	1129.8	1081.5	1041.3
35°	667.2	734.9	813.0	898.5	991.5	1031.6	1061.4	1084.5	1066.6	998.9	951.3
37.5°	629.3	696.2	779.5	866.5	964.0	1003.4	1027.2	1030.9	987.0	927.5	857.6
40°	587.6	656.8	743.8	835.3	933.5	967.7	982.6	971.4	908.2	839.0	757.9
42.5°	545.9	614.4	708.1	801.8	894.8	923.8	929.7	899.3	821.9	740.8	647.1
45°	500.6	572.0	665.7	760.2	850.2	866.5	867.3	823.4	731.9	647.1	560.1
47.5°	463.4	529.6	622.6	717.0	792.9	804.0	799.6	749.0	649.3	554.1	478.3
50°	422.5	485.7	577.9	670.9	735.6	738.6	727.4	655.3	557.8	470.8	410.6
52.5°	378.6	442.6	527.4	616.6	674.6	670.2	648.6	571.2	479.7	407.6	361.5
55°	343.6	400.2	479.7	566.8	607.7	595.0	571.2	492.4	420.2	359.3	319.1
57.5°	305.0	354.8	432.9	508.8	532.6	520.7	496.9	423.2	356.3	310.2	283.4
60°	268.5	313.9	382.3	445.5	464.1	451.5	424.0	357.8	309.4	270.7	250.7
62.5°	235.0	274.5	331.7	389.8	397.2	384.5	360.7	307.2	265.5	235.0	220.2
65°	203.8	241.0	287.1	331.0	337.7	324.3	299.8	261.1	226.1	206.8	192.6
67.5°	173.3	203.1	244.0	275.9	279.7	267.0	246.9	215.7	194.1	173.3	162.9
70°	146.5	168.8	200.8	226.9	228.3	216.4	206.0	177.8	161.4	146.5	138.3
72.5°	120.5	136.1	160.7	180.0	180.7	173.3	163.6	145.8	131.7	121.2	113.1
75°	95.2	108.6	123.5	140.6	139.8	133.9	126.4	115.3	103.4	96.7	93.0
77.5°	72.9	81.1	93.0	104.1	104.1	101.2	96.7	88.5	81.1	74.4	70.7
80°	52.1	57.3	66.9	70.7	72.1	71.4	67.7	61.7	58.8	53.6	52.1
82.5°	33.5	37.2	41.7	45.4	47.6	46.1	45.4	42.4	37.9	36.4	35.0
85°	19.3	20.8	23.1	25.3	26.0	25.3	26.8	24.5	22.3	22.3	21.6
87.5°	8.2	8.9	10.4	10.4	11.2	11.2	10.4	11.2	11.2	10.4	9.7
90°	0.4	1.4	2.8	3.6	4.3	4.8	5.3	7.1	9.6	11.7	12.1
92.5°	5.3	7.5	10.3	12.1	14.9	16.8	18.8	28.4	41.9	54.0	54.7
95°	12.4	13.9	17.4	20.6	26.3	30.6	34.8	51.2	82.1	123.3	139.3
97.5°	18.5	20.6	24.5	29.1	35.5	40.3	45.1	66.1	109.1	175.5	227.1
100°	27.4	28.4	31.6	37.3	44.4	49.4	54.4	73.2	116.6	193.3	280.7
102.5°	35.5	36.2	39.4	45.1	52.6	57.6	62.5	79.6	116.9	186.6	282.5
105°	43.4	44.8	47.3	52.6	60.4	65.4	70.4	87.1	118.7	177.3	263.3
107.5°	51.9	52.9	55.4	60.4	68.2	73.2	78.2	94.5	122.6	172.3	245.5
110°	60.4	61.8	64.0	68.6	76.0	81.2	86.3	102.0	127.6	170.9	233.5

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	68.2	69.6	72.1	76.4	83.5	88.8	94.2	109.1	132.9	171.3	225.6
115°	76.4	78.2	80.3	84.6	91.7	96.5	101.3	116.6	138.2	172.7	220.3
117.5°	84.9	86.3	88.5	92.4	99.1	104.1	109.1	123.3	143.9	174.8	217.5
120°	92.7	94.2	96.3	99.5	106.6	111.6	116.6	130.4	149.6	177.0	215.0
122.5°	100.2	101.3	103.4	107.0	114.1	119.2	124.4	137.2	154.6	179.4	213.6
125°	106.6	107.7	109.8	114.1	121.2	126.2	131.1	143.9	159.9	181.9	211.8
127.5°	111.9	113.4	116.2	120.8	127.6	132.8	137.9	150.3	164.9	184.4	210.7
130°	116.6	118.0	121.5	126.5	133.6	138.6	143.6	156.0	169.5	187.3	210.0
132.5°	120.8	122.6	126.5	131.8	139.3	144.2	149.2	161.0	174.1	190.1	209.7
135°	125.1	126.5	130.8	136.1	144.3	149.2	154.2	165.6	178.0	192.2	209.3
137.5°	129.0	130.8	135.0	140.7	148.9	153.5	158.1	169.5	181.2	194.4	209.3
140°	133.6	135.0	139.3	145.0	152.8	157.4	162.0	172.7	183.7	195.8	208.9
142.5°	138.2	139.3	143.2	148.9	156.4	160.6	164.9	175.2	185.8	196.9	208.9
145°	142.8	144.3	147.8	153.2	160.3	164.2	168.1	177.7	187.6	197.6	208.2
147.5°	147.8	148.9	152.4	157.4	163.5	167.0	170.6	179.8	188.7	197.9	207.2
150°	152.8	153.9	156.7	161.3	166.7	169.9	173.1	181.2	189.4	197.6	206.1
152.5°	157.8	158.1	161.0	164.9	169.9	172.7	175.5	182.6	189.8	196.9	204.3
155°	162.4	162.7	164.9	168.8	172.7	175.4	178.0	184.1	190.1	196.2	202.2
157.5°	166.3	166.7	168.4	172.0	175.2	177.5	179.8	185.1	190.1	194.7	200.1
160°	170.2	170.6	172.0	174.8	177.7	179.6	181.6	185.8	190.1	193.7	197.9
162.5°	174.1	173.8	175.2	177.3	179.8	181.2	182.6	186.2	189.8	192.6	196.2
165°	177.0	176.6	177.3	179.4	181.2	182.3	183.4	186.6	189.0	191.2	193.7
167.5°	179.4	179.1	179.8	181.2	182.6	183.4	184.1	186.6	188.7	189.8	191.5
170°	181.9	181.2	181.6	182.6	183.4	183.9	184.4	186.2	188.0	188.7	189.8
172.5°	183.4	183.0	182.6	183.7	184.1	184.4	184.8	185.8	186.9	187.3	187.6
175°	184.4	184.1	183.7	184.4	184.4	184.6	184.8	185.5	186.2	185.8	186.2
177.5°	185.1	184.4	184.1	184.8	184.8	184.8	184.8	185.1	185.8	185.1	184.8
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1005.6	1006.4	1007.8	1015.3	1019.0	1019.7	1016.8	1023.5	1025.7	1023.5	1022.0
5°	1053.2	1057.7	1066.6	1076.3	1075.5	1076.3	1080.7	1085.2	1086.7	1080.7	1083.0
7.5°	1094.9	1103.8	1113.5	1128.3	1128.3	1135.8	1138.8	1142.5	1151.4	1146.9	1145.4
10°	1142.5	1154.4	1172.2	1196.0	1196.8	1204.2	1211.6	1223.5	1227.3	1224.3	1225.8
12.5°	1202.0	1225.0	1226.5	1252.6	1264.5	1265.9	1277.8	1275.6	1283.1	1283.1	1295.7
15°	1228.0	1263.7	1283.8	1309.1	1316.5	1307.6	1317.3	1327.7	1328.4	1328.4	1327.7
17.5°	1274.9	1289.0	1309.1	1322.5	1325.4	1325.4	1326.2	1330.7	1327.7	1321.7	1326.2
20°	1284.5	1290.5	1297.9	1296.4	1297.9	1290.5	1283.1	1275.6	1276.4	1272.6	1283.8
22.5°	1266.7	1265.2	1248.1	1236.9	1236.9	1222.1	1207.9	1201.2	1194.5	1196.8	1200.5
25°	1222.1	1199.0	1178.2	1161.8	1158.1	1134.3	1115.0	1109.0	1097.8	1106.8	1108.3
27.5°	1150.7	1124.6	1091.2	1077.0	1057.7	1048.0	1034.6	1016.8	993.7	1007.1	1004.9
30°	1074.0	1035.4	1007.8	973.6	943.1	940.9	915.6	885.9	874.0	874.0	880.7
32.5°	988.5	937.2	897.0	848.7	818.9	806.3	775.8	746.0	752.7	730.4	738.6
35°	888.8	821.2	770.6	723.7	701.4	686.5	647.1	630.7	612.9	602.5	621.8
37.5°	793.6	715.5	650.8	599.5	591.3	564.5	537.8	527.4	516.9	521.4	520.7
40°	677.6	608.4	550.4	510.2	496.1	483.5	465.6	453.0	446.3	450.0	450.7
42.5°	572.7	514.7	471.6	443.3	431.4	422.5	413.6	403.1	400.9	400.9	403.9
45°	491.7	444.0	415.0	392.0	385.3	378.6	371.9	367.4	365.9	363.0	365.2
47.5°	426.9	389.0	371.2	354.0	346.6	345.1	339.2	336.9	334.0	333.2	334.0
50°	372.6	348.8	332.5	322.8	317.6	315.4	312.4	307.9	306.4	310.2	308.7
52.5°	334.7	312.4	303.5	293.8	290.8	287.8	283.4	284.1	283.4	281.9	281.9
55°	296.8	282.6	273.7	266.3	265.5	262.6	258.8	257.4	256.6	255.1	257.4
57.5°	266.3	255.1	246.9	240.2	237.3	237.3	233.6	230.6	230.6	229.8	230.6
60°	235.8	224.6	219.4	212.7	210.5	209.8	207.5	206.0	203.8	203.8	203.8
62.5°	207.5	198.6	192.6	186.7	187.4	183.7	180.7	179.3	179.3	180.0	180.0
65°	180.7	174.8	167.4	162.1	160.7	159.9	158.4	157.7	155.5	156.9	156.9
67.5°	156.2	148.0	143.6	141.3	139.1	138.3	136.9	135.4	134.6	133.9	135.4
70°	131.7	125.0	121.2	119.8	117.5	116.8	116.0	113.8	114.5	115.3	116.0
72.5°	109.3	103.4	102.6	98.2	98.2	98.2	95.2	96.7	95.9	94.5	95.9
75°	86.3	83.3	81.8	79.6	80.3	79.6	78.8	76.6	76.6	77.4	78.1
77.5°	68.4	65.5	64.7	62.5	61.0	62.5	61.0	60.2	60.2	61.0	61.0
80°	50.6	49.1	46.9	46.9	46.9	46.1	46.1	46.1	45.4	44.6	45.4
82.5°	33.5	33.5	32.7	32.0	32.7	31.2	32.0	32.0	32.0	32.0	32.0
85°	21.6	20.8	20.8	20.1	20.1	20.1	20.8	19.3	19.3	20.1	20.1
87.5°	9.7	9.7	9.7	10.4	9.7	9.7	9.7	10.4	9.7	9.7	9.7
90°	11.7	11.4	10.7	11.4	11.6	11.7	11.7	11.7	11.7	11.7	11.7
92.5°	45.8	35.9	30.6	26.7	25.2	23.8	23.5	22.0	22.4	21.7	22.4
95°	121.9	93.1	71.4	56.5	52.6	48.7	44.1	41.2	40.2	40.5	40.2
97.5°	228.8	190.5	152.1	116.2	105.6	94.9	81.0	73.9	70.0	67.9	70.0
100°	331.9	324.4	280.4	231.7	210.2	188.7	159.2	143.9	133.6	127.2	133.6
102.5°	370.3	412.2	410.8	378.4	355.3	332.2	299.6	270.8	257.3	248.0	257.3
105°	357.8	431.7	471.9	476.5	470.6	464.8	442.8	420.7	405.4	400.5	405.4
107.5°	331.5	410.8	470.5	505.3	512.4	519.5	519.2	516.0	511.3	503.2	511.3
110°	307.0	382.0	445.6	491.1	505.6	520.2	535.5	542.3	545.5	545.1	545.5

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	290.0	355.7	416.1	465.5	482.8	500.0	522.7	535.2	541.9	544.4	541.9
115°	276.5	335.1	389.8	436.4	454.7	473.0	498.2	514.5	523.8	527.0	523.8
117.5°	267.2	318.0	367.1	410.4	427.8	445.2	471.2	488.6	498.2	500.7	498.2
120°	260.1	306.0	350.0	387.7	403.8	420.0	444.9	461.6	471.9	475.5	471.9
122.5°	254.1	296.4	335.8	371.0	385.2	399.4	421.1	437.4	446.3	449.2	446.3
125°	248.4	287.1	323.7	355.0	368.3	381.6	402.3	415.8	424.6	427.5	424.6
127.5°	243.1	277.9	311.6	341.5	354.0	366.4	384.5	397.3	405.1	407.2	405.1
130°	237.7	269.0	299.6	327.6	339.4	351.1	368.5	380.6	387.7	390.5	387.7
132.5°	233.5	260.5	288.2	313.4	324.2	335.1	352.1	364.2	370.6	373.1	370.6
135°	229.6	252.7	276.1	299.6	309.6	319.5	334.7	346.5	352.9	354.3	352.9
137.5°	226.7	246.3	266.5	285.7	294.6	303.5	318.0	328.3	334.0	336.2	334.0
140°	224.2	240.2	257.3	273.6	281.5	289.3	300.6	309.9	315.2	317.3	315.2
142.5°	221.7	235.2	249.1	262.6	268.8	275.0	285.7	293.9	298.5	298.5	298.5
145°	219.6	230.6	242.3	253.4	258.6	263.7	272.2	278.2	281.8	282.9	281.8
147.5°	217.5	227.1	236.7	245.5	249.4	253.4	260.8	265.8	268.3	269.0	268.3
150°	214.6	223.2	231.0	238.4	241.6	244.8	250.2	254.4	256.6	256.9	256.6
152.5°	212.1	219.2	226.4	232.4	235.0	237.7	241.6	245.2	246.6	246.6	246.6
155°	208.9	215.7	221.4	226.7	228.6	230.6	234.5	237.0	238.4	237.7	238.4
157.5°	206.1	211.4	216.4	221.0	222.6	224.2	227.1	229.2	229.9	229.9	229.9
160°	202.9	207.5	211.4	215.3	216.6	217.8	220.3	222.1	222.4	222.4	222.4
162.5°	200.1	203.6	206.8	210.0	210.9	211.8	214.3	215.3	215.7	215.3	215.7
165°	196.9	199.7	202.2	204.7	205.4	206.1	207.5	208.9	208.9	208.6	208.9
167.5°	193.7	195.8	197.9	199.7	200.4	201.1	201.8	202.5	202.5	202.2	202.5
170°	191.2	193.0	194.0	195.4	195.8	196.2	196.5	197.6	197.2	196.5	197.2
172.5°	188.7	189.8	190.5	191.5	191.7	191.9	192.2	192.6	192.2	191.9	192.2
175°	186.6	187.6	188.0	188.3	188.5	188.7	188.7	189.0	188.7	188.0	188.7
177.5°	185.1	185.8	185.8	186.2	186.2	186.2	186.2	186.2	185.8	185.1	185.8
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1025.7	1020.5	1016.0	1016.8	1020.5	1017.5	1010.1	1000.4	996.7	992.2	996.7
5°	1087.4	1083.0	1074.0	1074.8	1072.6	1069.6	1057.7	1042.8	1042.8	1030.9	1029.4
7.5°	1148.4	1141.7	1135.8	1134.3	1126.1	1120.2	1109.7	1088.9	1080.7	1066.6	1058.4
10°	1216.9	1211.6	1205.0	1196.8	1192.3	1181.9	1164.8	1134.3	1119.4	1100.1	1085.9
12.5°	1286.0	1285.3	1270.4	1254.0	1253.3	1236.9	1225.0	1184.1	1164.0	1138.0	1104.5
15°	1329.9	1326.2	1318.0	1309.8	1312.1	1294.2	1267.4	1219.1	1205.7	1174.5	1138.8
17.5°	1329.2	1329.2	1326.9	1325.4	1323.2	1318.0	1303.1	1271.2	1249.6	1210.2	1176.7
20°	1286.8	1296.4	1298.7	1297.9	1305.4	1309.1	1308.3	1288.3	1271.2	1236.2	1202.0
22.5°	1202.0	1224.3	1234.0	1239.9	1255.5	1263.7	1283.1	1275.6	1271.2	1245.1	1216.1
25°	1123.1	1130.6	1159.6	1161.1	1182.6	1202.7	1222.1	1234.7	1251.1	1241.4	1216.9
27.5°	1021.2	1038.3	1059.2	1074.8	1079.3	1120.2	1152.1	1175.9	1213.1	1216.1	1207.9
30°	905.9	914.1	948.3	969.2	993.0	1022.7	1068.8	1109.7	1143.2	1173.7	1184.1
32.5°	765.4	798.8	818.9	844.2	865.0	917.8	974.4	1027.2	1065.9	1117.2	1139.5
35°	636.7	662.7	696.9	707.4	745.3	789.9	863.5	931.2	990.0	1042.1	1087.4
37.5°	530.3	551.2	587.6	604.0	626.3	683.6	745.3	829.3	900.0	964.0	1020.5
40°	457.4	473.1	500.6	505.8	524.4	576.4	626.3	705.1	798.8	885.1	946.9
42.5°	407.6	415.0	433.6	440.3	452.2	487.2	531.8	606.2	693.2	782.5	869.5
45°	371.9	377.1	388.3	394.2	409.1	424.7	461.2	520.7	589.1	679.1	772.8
47.5°	339.9	346.6	351.1	354.8	363.0	380.1	403.9	447.8	513.2	595.8	686.5
50°	313.1	315.4	323.6	324.3	329.5	340.7	363.0	389.8	441.8	508.8	596.5
52.5°	286.4	288.6	293.8	299.0	301.2	310.2	325.0	347.4	386.0	438.8	516.9
55°	259.6	262.6	267.8	271.5	273.7	281.2	290.1	311.7	342.1	379.3	443.3
57.5°	232.8	239.5	241.0	243.2	246.9	255.1	263.3	275.9	299.8	334.0	380.8
60°	207.5	209.8	215.0	217.2	220.9	225.4	235.8	245.5	262.6	289.3	331.7
62.5°	181.5	186.7	188.9	191.2	194.1	199.3	206.0	216.4	231.3	252.9	286.4
65°	159.2	159.9	164.4	167.4	170.3	174.0	180.7	190.4	199.3	219.4	244.0
67.5°	137.6	139.1	140.6	143.6	147.3	151.0	156.9	162.1	173.3	186.7	206.0
70°	116.8	116.8	120.5	122.7	122.0	126.4	130.9	136.9	145.0	157.7	173.3
72.5°	98.2	97.4	100.4	101.2	102.6	105.6	108.6	114.5	119.0	128.7	140.6
75°	78.1	79.6	81.1	81.1	83.3	85.5	88.5	91.5	96.7	102.6	111.6
77.5°	61.7	61.7	63.2	64.0	66.2	65.5	68.4	71.4	75.1	80.3	87.0
80°	45.4	46.9	46.9	46.9	47.6	48.3	51.3	53.6	55.8	59.5	62.5
82.5°	32.0	32.0	33.5	33.5	33.5	35.0	35.0	35.7	37.2	39.4	41.7
85°	20.1	20.1	20.1	20.8	20.1	20.8	22.3	21.6	22.3	23.8	23.8
87.5°	9.7	9.7	9.7	9.7	9.7	10.4	9.7	10.4	11.2	11.2	11.2
90°	11.7	11.7	11.7	11.6	11.4	10.7	11.4	11.7	12.1	11.7	9.6
92.5°	22.0	23.5	23.8	25.2	26.7	30.6	35.9	45.8	54.7	54.0	41.9
95°	41.2	44.1	48.7	52.6	56.5	71.4	93.1	121.9	139.3	123.3	82.1
97.5°	73.9	81.0	94.9	105.6	116.2	152.1	190.5	228.8	227.1	175.5	109.1
100°	143.9	159.2	188.7	210.2	231.7	280.4	324.4	331.9	280.7	193.3	116.6
102.5°	270.8	299.6	332.2	355.3	378.4	410.8	412.2	370.3	282.5	186.6	116.9
105°	420.7	442.8	464.8	470.6	476.5	471.9	431.7	357.8	263.3	177.3	118.7
107.5°	516.0	519.2	519.5	512.4	505.3	470.5	410.8	331.5	245.5	172.3	122.6
110°	542.3	535.5	520.2	505.6	491.1	445.6	382.0	307.0	233.5	170.9	127.6

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	535.2	522.7	500.0	482.8	465.5	416.1	355.7	290.0	225.6	171.3	132.9
115°	514.5	498.2	473.0	454.7	436.4	389.8	335.1	276.5	220.3	172.7	138.2
117.5°	488.6	471.2	445.2	427.8	410.4	367.1	318.0	267.2	217.5	174.8	143.9
120°	461.6	444.9	420.0	403.8	387.7	350.0	306.0	260.1	215.0	177.0	149.6
122.5°	437.4	421.1	399.4	385.2	371.0	335.8	296.4	254.1	213.6	179.4	154.6
125°	415.8	402.3	381.6	368.3	355.0	323.7	287.1	248.4	211.8	181.9	159.9
127.5°	397.3	384.5	366.4	354.0	341.5	311.6	277.9	243.1	210.7	184.4	164.9
130°	380.6	368.5	351.1	339.4	327.6	299.6	269.0	237.7	210.0	187.3	169.5
132.5°	364.2	352.1	335.1	324.2	313.4	288.2	260.5	233.5	209.7	190.1	174.1
135°	346.5	334.7	319.5	309.6	299.6	276.1	252.7	229.6	209.3	192.2	178.0
137.5°	328.3	318.0	303.5	294.6	285.7	266.5	246.3	226.7	209.3	194.4	181.2
140°	309.9	300.6	289.3	281.5	273.6	257.3	240.2	224.2	208.9	195.8	183.7
142.5°	293.9	285.7	275.0	268.8	262.6	249.1	235.2	221.7	208.9	196.9	185.8
145°	278.2	272.2	263.7	258.6	253.4	242.3	230.6	219.6	208.2	197.6	187.6
147.5°	265.8	260.8	253.4	249.4	245.5	236.7	227.1	217.5	207.2	197.9	188.7
150°	254.4	250.2	244.8	241.6	238.4	231.0	223.2	214.6	206.1	197.6	189.4
152.5°	245.2	241.6	237.7	235.0	232.4	226.4	219.2	212.1	204.3	196.9	189.8
155°	237.0	234.5	230.6	228.6	226.7	221.4	215.7	208.9	202.2	196.2	190.1
157.5°	229.2	227.1	224.2	222.6	221.0	216.4	211.4	206.1	200.1	194.7	190.1
160°	222.1	220.3	217.8	216.6	215.3	211.4	207.5	202.9	197.9	193.7	190.1
162.5°	215.3	214.3	211.8	210.9	210.0	206.8	203.6	200.1	196.2	192.6	189.8
165°	208.9	207.5	206.1	205.4	204.7	202.2	199.7	196.9	193.7	191.2	189.0
167.5°	202.5	201.8	201.1	200.4	199.7	197.9	195.8	193.7	191.5	189.8	188.7
170°	197.6	196.5	196.2	195.8	195.4	194.0	193.0	191.2	189.8	188.7	188.0
172.5°	192.6	192.2	191.9	191.7	191.5	190.5	189.8	188.7	187.6	187.3	186.9
175°	189.0	188.7	188.7	188.5	188.3	188.0	187.6	186.6	186.2	185.8	186.2
177.5°	186.2	186.2	186.2	186.2	186.2	185.8	185.8	185.1	184.8	185.1	185.8
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	993.0	989.3	987.0	988.5	984.0	972.9	972.9	976.6	972.1	967.7	961.0
5°	1020.5	1013.1	1008.6	1007.8	997.4	979.6	975.9	972.1	962.5	952.1	940.9
7.5°	1047.3	1033.9	1026.4	1021.2	1006.4	983.3	973.6	965.5	949.8	934.2	920.1
10°	1069.6	1050.2	1041.3	1033.1	1013.8	984.8	969.2	954.3	934.2	914.1	896.3
12.5°	1087.4	1065.1	1054.0	1042.1	1018.3	980.3	961.0	937.2	917.1	890.3	872.5
15°	1117.2	1071.1	1060.7	1049.5	1025.0	972.9	949.1	922.3	894.8	859.1	839.7
17.5°	1141.0	1079.3	1078.5	1054.7	1022.7	969.9	933.5	898.5	868.8	833.1	802.6
20°	1155.1	1091.9	1080.0	1055.4	1015.3	949.8	911.9	873.2	841.2	798.1	767.6
22.5°	1167.0	1109.7	1078.5	1048.8	999.7	943.1	887.4	850.9	807.0	760.2	731.2
25°	1171.5	1113.5	1080.7	1046.5	988.5	923.8	860.6	821.2	772.1	729.7	690.2
27.5°	1172.2	1112.7	1072.6	1036.9	972.9	898.5	833.8	792.1	737.8	688.8	649.3
30°	1164.8	1104.5	1068.1	1029.4	958.0	875.5	801.1	755.0	696.9	647.8	606.9
32.5°	1142.5	1088.2	1058.4	1016.0	938.7	843.5	769.8	718.5	657.5	609.2	569.7
35°	1105.3	1068.1	1035.4	995.9	913.4	813.7	738.6	678.3	616.6	570.5	533.3
37.5°	1059.2	1039.1	1008.6	969.9	884.4	786.9	703.6	636.7	575.0	530.3	493.9
40°	996.7	1001.9	972.1	937.2	850.2	750.5	658.3	594.3	536.3	494.6	458.9
42.5°	929.0	950.6	933.5	900.0	812.2	710.3	624.8	554.1	497.6	454.5	424.7
45°	856.1	893.3	882.9	858.3	772.8	667.9	577.2	508.8	458.9	417.3	391.2
47.5°	776.5	829.3	829.3	811.5	728.9	625.5	536.3	466.4	417.3	387.5	362.2
50°	695.5	755.0	764.6	752.7	679.8	577.2	486.4	423.2	380.8	351.8	333.2
52.5°	610.7	679.8	697.7	691.7	627.8	531.1	445.5	383.8	345.1	319.8	303.5
55°	529.6	609.9	629.3	631.5	572.0	480.5	400.2	345.9	308.7	291.6	277.4
57.5°	453.0	530.3	551.9	555.6	515.5	434.4	357.8	310.2	276.7	262.6	251.4
60°	387.5	452.2	480.5	488.7	453.7	380.8	318.3	272.2	246.9	233.6	223.1
62.5°	334.0	386.0	415.8	418.0	402.4	334.0	277.4	238.8	217.2	205.3	200.1
65°	281.9	328.8	346.6	355.5	342.9	289.3	239.5	207.5	190.4	180.0	174.8
67.5°	240.2	270.0	284.9	296.8	284.1	244.0	203.8	177.8	165.1	154.7	151.7
70°	197.1	221.7	232.8	244.7	233.6	203.1	174.0	150.2	139.1	130.9	127.2
72.5°	157.7	177.0	187.4	194.9	188.2	162.9	139.1	122.7	114.5	108.6	106.4
75°	125.0	138.3	144.3	149.5	146.5	127.2	112.3	98.9	91.5	86.3	84.8
77.5°	95.2	104.9	111.6	113.1	109.3	96.7	84.0	75.9	69.9	66.9	65.5
80°	67.7	73.6	77.4	79.6	75.9	70.7	61.7	55.8	50.6	46.9	46.1
82.5°	45.4	48.3	51.3	50.6	49.1	44.6	39.4	36.4	34.2	31.2	31.2
85°	26.0	26.8	28.3	29.0	28.3	25.3	22.3	20.8	19.3	17.1	17.1
87.5°	11.2	11.9	11.9	12.6	11.2	11.2	9.7	8.2	8.2	7.4	6.7
90°	7.1	5.3	4.8	4.3	3.6	2.8	1.4	0.4	1.4	2.8	3.6
92.5°	28.4	18.8	16.8	14.9	12.1	10.3	7.5	5.3	7.5	10.3	12.1
95°	51.2	34.8	30.6	26.3	20.6	17.4	13.9	12.4	13.9	17.4	20.6
97.5°	66.1	45.1	40.3	35.5	29.1	24.5	20.6	18.5	20.6	24.5	29.1
100°	73.2	54.4	49.4	44.4	37.3	31.6	28.4	27.4	28.4	31.6	37.3
102.5°	79.6	62.5	57.6	52.6	45.1	39.4	36.2	35.5	36.2	39.4	45.1
105°	87.1	70.4	65.4	60.4	52.6	47.3	44.8	43.4	44.8	47.3	52.6
107.5°	94.5	78.2	73.2	68.2	60.4	55.4	52.9	51.9	52.9	55.4	60.4
110°	102.0	86.3	81.2	76.0	68.6	64.0	61.8	60.4	61.8	64.0	68.6

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	109.1	94.2	88.8	83.5	76.4	72.1	69.6	68.2	69.6	72.1	76.4
115°	116.6	101.3	96.5	91.7	84.6	80.3	78.2	76.4	78.2	80.3	84.6
117.5°	123.3	109.1	104.1	99.1	92.4	88.5	86.3	84.9	86.3	88.5	92.4
120°	130.4	116.6	111.6	106.6	99.5	96.3	94.2	92.7	94.2	96.3	99.5
122.5°	137.2	124.4	119.2	114.1	107.0	103.4	101.3	100.2	101.3	103.4	107.0
125°	143.9	131.1	126.2	121.2	114.1	109.8	107.7	106.6	107.7	109.8	114.1
127.5°	150.3	137.9	132.8	127.6	120.8	116.2	113.4	111.9	113.4	116.2	120.8
130°	156.0	143.6	138.6	133.6	126.5	121.5	118.0	116.6	118.0	121.5	126.5
132.5°	161.0	149.2	144.2	139.3	131.8	126.5	122.6	120.8	122.6	126.5	131.8
135°	165.6	154.2	149.2	144.3	136.1	130.8	126.5	125.1	126.5	130.8	136.1
137.5°	169.5	158.1	153.5	148.9	140.7	135.0	130.8	129.0	130.8	135.0	140.7
140°	172.7	162.0	157.4	152.8	145.0	139.3	135.0	133.6	135.0	139.3	145.0
142.5°	175.2	164.9	160.6	156.4	148.9	143.2	139.3	138.2	139.3	143.2	148.9
145°	177.7	168.1	164.2	160.3	153.2	147.8	144.3	142.8	144.3	147.8	153.2
147.5°	179.8	170.6	167.0	163.5	157.4	152.4	148.9	147.8	148.9	152.4	157.4
150°	181.2	173.1	169.9	166.7	161.3	156.7	153.9	152.8	153.9	156.7	161.3
152.5°	182.6	175.5	172.7	169.9	164.9	161.0	158.1	157.8	158.1	161.0	164.9
155°	184.1	178.0	175.4	172.7	168.8	164.9	162.7	162.4	162.7	164.9	168.8
157.5°	185.1	179.8	177.5	175.2	172.0	168.4	166.7	166.3	166.7	168.4	172.0
160°	185.8	181.6	179.6	177.7	174.8	172.0	170.6	170.2	170.6	172.0	174.8
162.5°	186.2	182.6	181.2	179.8	177.3	175.2	173.8	174.1	173.8	175.2	177.3
165°	186.6	183.4	182.3	181.2	179.4	177.3	176.6	177.0	176.6	177.3	179.4
167.5°	186.6	184.1	183.4	182.6	181.2	179.8	179.1	179.4	179.1	179.8	181.2
170°	186.2	184.4	183.9	183.4	182.6	181.6	181.2	181.9	181.2	181.6	182.6
172.5°	185.8	184.8	184.4	184.1	183.7	182.6	183.0	183.4	183.0	182.6	183.7
175°	185.5	184.8	184.6	184.4	184.4	183.7	184.1	184.4	184.1	183.7	184.4
177.5°	185.1	184.8	184.8	184.8	184.8	184.1	184.4	185.1	184.4	184.1	184.8
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	957.3	961.0	960.2	952.8	944.6	937.9	925.3	926.8	922.3	923.1	927.5
5°	933.5	933.5	930.5	920.1	906.7	899.3	885.1	881.4	872.5	871.7	871.0
7.5°	908.2	904.5	900.7	885.9	869.5	857.6	838.3	833.8	824.9	818.9	815.9
10°	878.4	873.2	865.8	848.7	828.6	813.7	793.6	787.7	770.6	763.1	758.7
12.5°	845.7	842.7	830.8	816.7	784.0	767.6	738.6	744.5	727.4	712.6	710.3
15°	813.0	801.8	795.1	772.1	732.6	725.2	702.1	690.2	674.6	662.7	662.7
17.5°	781.0	763.9	749.0	724.5	695.5	674.6	657.5	651.6	632.2	620.3	618.1
20°	738.6	719.3	715.5	680.6	660.5	637.4	621.1	606.2	592.1	586.9	583.1
22.5°	698.4	676.1	670.2	640.4	620.3	597.3	580.9	570.5	560.1	556.4	549.7
25°	655.3	641.9	633.0	601.0	578.7	557.1	545.9	538.5	528.8	528.1	523.6
27.5°	613.6	601.0	592.1	561.6	545.2	525.1	516.2	508.0	502.8	500.6	498.3
30°	577.9	563.8	553.4	531.1	511.0	494.6	487.2	482.0	479.0	475.3	474.5
32.5°	538.5	530.3	516.2	499.1	483.5	467.8	463.4	459.7	455.2	453.7	453.0
35°	505.0	493.9	485.0	465.6	458.9	445.5	440.3	437.4	431.4	429.9	428.4
37.5°	472.3	461.9	452.2	440.3	427.7	420.2	417.3	412.8	409.8	410.6	409.1
40°	439.6	431.4	424.0	411.3	403.9	400.2	394.2	389.8	388.3	389.0	388.3
42.5°	407.6	400.2	395.7	386.0	378.6	374.9	371.2	366.7	368.9	368.9	371.2
45°	378.6	371.9	368.9	361.5	357.0	351.1	347.4	346.6	349.6	348.8	348.8
47.5°	348.8	346.6	342.9	336.2	330.2	326.5	325.8	325.8	328.8	330.2	329.5
50°	325.8	321.3	316.9	311.7	307.2	305.7	303.5	305.0	307.9	307.9	309.4
52.5°	296.8	293.8	292.3	287.8	284.9	284.9	284.9	285.6	287.8	290.1	289.3
55°	271.5	269.3	267.8	265.5	261.8	262.6	261.8	263.3	265.5	267.8	269.3
57.5°	244.7	244.0	242.5	238.8	238.8	238.0	240.2	241.0	244.7	246.2	248.4
60°	220.9	218.7	218.7	215.7	215.7	215.7	217.9	220.2	223.1	223.9	225.4
62.5°	195.6	195.6	194.9	192.6	192.6	194.9	195.6	198.6	200.1	200.1	202.3
65°	171.8	171.1	170.3	171.1	171.8	171.8	174.0	175.5	177.0	177.8	178.5
67.5°	148.0	147.3	148.8	148.0	149.5	152.5	151.7	154.0	156.2	156.2	156.9
70°	125.7	127.2	126.4	127.9	127.2	128.7	130.9	131.7	131.7	132.4	134.6
72.5°	104.9	104.9	104.9	104.1	104.9	106.4	107.9	108.6	110.1	110.8	113.1
75°	84.8	84.8	83.3	84.8	84.8	86.3	87.8	87.8	87.8	89.3	91.5
77.5°	64.0	64.7	64.0	65.5	65.5	66.2	67.7	66.9	68.4	69.2	69.9
80°	46.9	46.1	46.1	46.1	46.9	46.9	48.3	49.1	49.1	51.3	49.8
82.5°	29.8	30.5	29.8	30.5	30.5	31.2	30.5	31.2	32.0	33.5	32.7
85°	17.1	16.4	16.4	17.1	16.4	16.4	17.1	16.4	17.1	16.4	17.1
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	4.3	4.8	5.3	7.1	9.6	11.7	12.1	11.7	11.4	10.7	11.4
92.5°	14.9	16.8	18.8	28.4	41.9	54.0	54.7	45.8	35.9	30.6	26.7
95°	26.3	30.6	34.8	51.2	82.1	123.3	139.3	121.9	93.1	71.4	56.5
97.5°	35.5	40.3	45.1	66.1	109.1	175.5	227.1	228.8	190.5	152.1	116.2
100°	44.4	49.4	54.4	73.2	116.6	193.3	280.7	331.9	324.4	280.4	231.7
102.5°	52.6	57.6	62.5	79.6	116.9	186.6	282.5	370.3	412.2	410.8	378.4
105°	60.4	65.4	70.4	87.1	118.7	177.3	263.3	357.8	431.7	471.9	476.5
107.5°	68.2	73.2	78.2	94.5	122.6	172.3	245.5	331.5	410.8	470.5	505.3
110°	76.0	81.2	86.3	102.0	127.6	170.9	233.5	307.0	382.0	445.6	491.1

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	83.5	88.8	94.2	109.1	132.9	171.3	225.6	290.0	355.7	416.1	465.5
115°	91.7	96.5	101.3	116.6	138.2	172.7	220.3	276.5	335.1	389.8	436.4
117.5°	99.1	104.1	109.1	123.3	143.9	174.8	217.5	267.2	318.0	367.1	410.4
120°	106.6	111.6	116.6	130.4	149.6	177.0	215.0	260.1	306.0	350.0	387.7
122.5°	114.1	119.2	124.4	137.2	154.6	179.4	213.6	254.1	296.4	335.8	371.0
125°	121.2	126.2	131.1	143.9	159.9	181.9	211.8	248.4	287.1	323.7	355.0
127.5°	127.6	132.8	137.9	150.3	164.9	184.4	210.7	243.1	277.9	311.6	341.5
130°	133.6	138.6	143.6	156.0	169.5	187.3	210.0	237.7	269.0	299.6	327.6
132.5°	139.3	144.2	149.2	161.0	174.1	190.1	209.7	233.5	260.5	288.2	313.4
135°	144.3	149.2	154.2	165.6	178.0	192.2	209.3	229.6	252.7	276.1	299.6
137.5°	148.9	153.5	158.1	169.5	181.2	194.4	209.3	226.7	246.3	266.5	285.7
140°	152.8	157.4	162.0	172.7	183.7	195.8	208.9	224.2	240.2	257.3	273.6
142.5°	156.4	160.6	164.9	175.2	185.8	196.9	208.9	221.7	235.2	249.1	262.6
145°	160.3	164.2	168.1	177.7	187.6	197.6	208.2	219.6	230.6	242.3	253.4
147.5°	163.5	167.0	170.6	179.8	188.7	197.9	207.2	217.5	227.1	236.7	245.5
150°	166.7	169.9	173.1	181.2	189.4	197.6	206.1	214.6	223.2	231.0	238.4
152.5°	169.9	172.7	175.5	182.6	189.8	196.9	204.3	212.1	219.2	226.4	232.4
155°	172.7	175.4	178.0	184.1	190.1	196.2	202.2	208.9	215.7	221.4	226.7
157.5°	175.2	177.5	179.8	185.1	190.1	194.7	200.1	206.1	211.4	216.4	221.0
160°	177.7	179.6	181.6	185.8	190.1	193.7	197.9	202.9	207.5	211.4	215.3
162.5°	179.8	181.2	182.6	186.2	189.8	192.6	196.2	200.1	203.6	206.8	210.0
165°	181.2	182.3	183.4	186.6	189.0	191.2	193.7	196.9	199.7	202.2	204.7
167.5°	182.6	183.4	184.1	186.6	188.7	189.8	191.5	193.7	195.8	197.9	199.7
170°	183.4	183.9	184.4	186.2	188.0	188.7	189.8	191.2	193.0	194.0	195.4
172.5°	184.1	184.4	184.8	185.8	186.9	187.3	187.6	188.7	189.8	190.5	191.5
175°	184.4	184.6	184.8	185.5	186.2	185.8	186.2	186.6	187.6	188.0	188.3
177.5°	184.8	184.8	184.8	185.1	185.8	185.1	184.8	185.1	185.8	185.8	186.2
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	922.3	924.5	919.3	917.8	919.3	914.1	915.6	917.1	917.1	919.3	920.8
5°	868.8	865.8	860.6	859.1	857.6	859.8	858.3	860.6	861.3	866.5	867.3
7.5°	815.9	811.5	807.0	802.6	801.1	797.4	801.1	801.1	806.3	804.8	808.5
10°	753.5	752.7	746.8	744.5	741.6	735.6	743.8	741.6	745.3	752.0	753.5
12.5°	707.4	699.2	702.9	692.5	696.2	690.2	691.0	691.0	696.9	697.7	696.2
15°	663.5	656.8	647.1	642.6	640.4	637.4	647.1	647.8	643.4	653.8	650.1
17.5°	618.8	618.8	609.9	607.7	601.7	604.7	603.2	604.0	602.5	609.9	613.6
20°	580.2	576.4	573.5	574.2	566.8	565.3	563.8	565.3	570.5	575.7	577.2
22.5°	548.9	546.7	539.3	540.7	534.8	537.0	535.5	539.3	540.0	540.0	545.2
25°	519.2	516.2	516.9	514.0	511.7	511.7	509.5	511.7	514.7	516.2	516.9
27.5°	496.9	494.6	490.9	488.7	490.2	486.4	489.4	491.7	491.7	490.2	491.7
30°	470.1	471.6	471.6	464.1	467.1	465.6	467.8	469.3	469.3	470.1	468.6
32.5°	452.2	447.8	447.0	446.3	446.3	443.3	443.3	445.5	446.3	447.0	449.3
35°	428.4	428.4	424.7	426.9	424.0	424.7	424.0	424.7	426.2	424.0	426.2
37.5°	406.9	407.6	406.1	407.6	408.3	406.9	405.4	408.3	406.9	406.9	405.4
40°	388.3	387.5	388.3	388.3	388.3	389.0	387.5	387.5	387.5	386.0	384.5
42.5°	372.6	368.2	369.7	370.4	368.2	368.2	368.9	368.2	370.4	365.9	365.9
45°	350.3	348.8	349.6	349.6	351.1	348.8	350.3	351.1	348.8	348.1	346.6
47.5°	330.2	331.7	330.2	331.7	331.7	333.2	330.2	331.0	331.7	328.8	326.5
50°	310.2	310.2	312.4	311.7	312.4	310.9	310.9	310.2	310.9	309.4	307.2
52.5°	291.6	289.3	293.1	292.3	291.6	290.8	290.1	290.8	289.3	287.8	287.8
55°	268.5	268.5	270.7	271.5	271.5	270.0	268.5	269.3	268.5	267.8	267.0
57.5°	249.9	246.9	248.4	249.2	249.2	246.9	248.4	246.9	246.9	247.7	245.5
60°	226.1	226.1	224.6	226.9	226.9	225.4	225.4	226.1	224.6	223.9	223.1
62.5°	200.8	201.6	203.8	204.5	205.3	203.8	202.3	203.1	203.1	200.8	201.6
65°	179.3	180.7	183.7	183.0	181.5	182.2	180.7	181.5	179.3	180.0	177.8
67.5°	158.4	157.7	158.4	158.4	159.9	159.2	157.7	157.7	156.9	159.2	156.9
70°	136.1	136.1	136.1	136.1	136.9	137.6	136.1	134.6	135.4	133.9	133.1
72.5°	113.1	113.8	113.1	114.5	112.3	113.8	113.8	113.1	112.3	112.3	112.3
75°	91.5	93.0	90.7	91.5	90.7	92.2	91.5	91.5	90.0	89.3	90.0
77.5°	69.9	70.7	69.2	69.9	69.2	69.9	69.9	69.2	69.2	69.2	69.2
80°	49.8	50.6	49.8	49.1	48.3	49.8	48.3	49.1	49.8	49.1	50.6
82.5°	32.0	32.0	31.2	32.0	30.5	30.5	31.2	31.2	30.5	32.0	30.5
85°	15.6	15.6	17.1	15.6	14.9	14.9	14.9	15.6	14.9	16.4	15.6
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	11.6	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.6
92.5°	25.2	23.8	23.5	22.0	22.4	21.7	22.4	22.0	23.5	23.8	25.2
95°	52.6	48.7	44.1	41.2	40.2	40.5	40.2	41.2	44.1	48.7	52.6
97.5°	105.6	94.9	81.0	73.9	70.0	67.9	70.0	73.9	81.0	94.9	105.6
100°	210.2	188.7	159.2	143.9	133.6	127.2	133.6	143.9	159.2	188.7	210.2
102.5°	355.3	332.2	299.6	270.8	257.3	248.0	257.3	270.8	299.6	332.2	355.3
105°	470.6	464.8	442.8	420.7	405.4	400.5	405.4	420.7	442.8	464.8	470.6
107.5°	512.4	519.5	519.2	516.0	511.3	503.2	511.3	516.0	519.2	519.5	512.4
110°	505.6	520.2	535.5	542.3	545.5	545.1	545.5	542.3	535.5	520.2	505.6

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	482.8	500.0	522.7	535.2	541.9	544.4	541.9	535.2	522.7	500.0	482.8
115°	454.7	473.0	498.2	514.5	523.8	527.0	523.8	514.5	498.2	473.0	454.7
117.5°	427.8	445.2	471.2	488.6	498.2	500.7	498.2	488.6	471.2	445.2	427.8
120°	403.8	420.0	444.9	461.6	471.9	475.5	471.9	461.6	444.9	420.0	403.8
122.5°	385.2	399.4	421.1	437.4	446.3	449.2	446.3	437.4	421.1	399.4	385.2
125°	368.3	381.6	402.3	415.8	424.6	427.5	424.6	415.8	402.3	381.6	368.3
127.5°	354.0	366.4	384.5	397.3	405.1	407.2	405.1	397.3	384.5	366.4	354.0
130°	339.4	351.1	368.5	380.6	387.7	390.5	387.7	380.6	368.5	351.1	339.4
132.5°	324.2	335.1	352.1	364.2	370.6	373.1	370.6	364.2	352.1	335.1	324.2
135°	309.6	319.5	334.7	346.5	352.9	354.3	352.9	346.5	334.7	319.5	309.6
137.5°	294.6	303.5	318.0	328.3	334.0	336.2	334.0	328.3	318.0	303.5	294.6
140°	281.5	289.3	300.6	309.9	315.2	317.3	315.2	309.9	300.6	289.3	281.5
142.5°	268.8	275.0	285.7	293.9	298.5	298.5	298.5	293.9	285.7	275.0	268.8
145°	258.6	263.7	272.2	278.2	281.8	282.9	281.8	278.2	272.2	263.7	258.6
147.5°	249.4	253.4	260.8	265.8	268.3	269.0	268.3	265.8	260.8	253.4	249.4
150°	241.6	244.8	250.2	254.4	256.6	256.9	256.6	254.4	250.2	244.8	241.6
152.5°	235.0	237.7	241.6	245.2	246.6	246.6	246.6	245.2	241.6	237.7	235.0
155°	228.6	230.6	234.5	237.0	238.4	237.7	238.4	237.0	234.5	230.6	228.6
157.5°	222.6	224.2	227.1	229.2	229.9	229.9	229.9	229.2	227.1	224.2	222.6
160°	216.6	217.8	220.3	222.1	222.4	222.4	222.4	222.1	220.3	217.8	216.6
162.5°	210.9	211.8	214.3	215.3	215.7	215.3	215.7	215.3	214.3	211.8	210.9
165°	205.4	206.1	207.5	208.9	208.9	208.6	208.9	208.9	207.5	206.1	205.4
167.5°	200.4	201.1	201.8	202.5	202.5	202.2	202.5	202.5	201.8	201.1	200.4
170°	195.8	196.2	196.5	197.6	197.2	196.5	197.2	197.6	196.5	196.2	195.8
172.5°	191.7	191.9	192.2	192.6	192.2	191.9	192.2	192.6	192.2	191.9	191.7
175°	188.5	188.7	188.7	189.0	188.7	188.0	188.7	189.0	188.7	188.7	188.5
177.5°	186.2	186.2	186.2	186.2	185.8	185.1	185.8	186.2	186.2	186.2	186.2
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	918.6	924.5	922.3	914.1	923.8	923.8	930.5	930.5	938.7	941.6	946.1
5°	866.5	871.0	874.7	871.0	877.7	888.1	894.0	899.3	910.4	914.9	921.6
7.5°	810.7	818.9	822.6	822.6	833.8	845.7	857.6	865.0	880.7	886.6	893.3
10°	756.4	766.1	773.6	772.8	791.4	798.8	813.7	830.8	846.4	855.4	865.0
12.5°	699.2	704.4	714.8	729.7	734.1	747.5	764.6	786.2	814.5	822.6	836.8
15°	651.6	665.7	673.9	680.6	691.0	703.6	722.2	743.1	771.3	789.2	804.0
17.5°	611.4	630.0	635.2	633.7	647.1	666.4	688.0	703.6	728.9	750.5	764.6
20°	578.7	586.1	595.0	598.8	609.2	630.0	650.8	668.7	689.5	706.6	723.0
22.5°	545.9	551.9	559.3	566.0	574.2	586.1	606.2	628.5	648.6	665.0	683.6
25°	519.2	522.9	529.6	534.8	543.7	551.9	566.0	590.6	614.4	624.0	640.4
27.5°	493.1	496.1	500.6	506.5	511.0	519.2	531.8	551.9	576.4	586.1	608.4
30°	470.1	472.3	476.8	479.7	482.0	491.7	501.3	516.9	535.5	548.9	565.3
32.5°	448.5	450.7	455.2	455.9	458.9	464.1	473.1	487.2	503.6	514.7	528.8
35°	424.7	426.2	430.7	432.1	434.4	438.8	445.5	455.9	470.8	479.0	491.7
37.5°	406.1	405.4	408.3	410.6	413.6	415.8	418.0	428.4	439.6	447.0	456.7
40°	386.0	384.5	385.3	388.3	389.8	392.7	392.7	403.1	410.6	416.5	424.0
42.5°	365.9	365.2	363.7	365.2	366.7	367.4	368.2	375.6	383.1	388.3	396.4
45°	345.9	345.1	343.6	344.4	344.4	345.9	348.1	351.1	356.3	360.7	365.2
47.5°	327.3	325.8	323.6	322.8	324.3	324.3	324.3	327.3	332.5	334.0	338.4
50°	307.9	305.7	302.7	301.2	301.2	300.5	302.0	302.7	307.2	308.7	312.4
52.5°	287.1	285.6	282.6	279.7	280.4	278.9	279.7	280.4	281.9	284.1	286.4
55°	266.3	263.3	261.1	260.3	258.1	258.1	255.9	258.8	258.1	258.8	261.8
57.5°	246.2	243.2	239.5	238.0	235.8	235.0	233.6	232.8	233.6	235.8	238.0
60°	222.4	220.9	218.7	216.4	215.0	212.7	211.2	211.2	210.5	210.5	211.2
62.5°	199.3	198.6	195.6	194.9	193.4	191.9	189.7	188.2	188.2	189.7	190.4
65°	177.0	176.3	174.0	173.3	169.6	168.1	167.4	166.6	165.1	165.1	165.1
67.5°	156.2	154.0	154.0	150.2	147.3	145.8	144.3	143.6	143.6	143.6	144.3
70°	133.1	133.1	130.9	128.7	125.7	126.4	124.2	122.0	122.0	120.5	121.2
72.5°	110.8	110.1	107.9	107.1	104.9	102.6	101.2	102.6	100.4	99.7	100.4
75°	89.3	88.5	87.0	85.5	86.3	84.0	81.8	81.1	81.1	79.6	79.6
77.5°	68.4	69.9	66.9	66.2	64.7	63.2	62.5	61.7	61.7	61.7	63.2
80°	47.6	48.3	48.3	46.9	47.6	45.4	45.4	45.4	43.1	43.9	44.6
82.5°	30.5	30.5	29.8	30.5	29.8	29.8	29.0	29.0	28.3	28.3	29.0
85°	17.1	16.4	15.6	17.1	16.4	16.4	15.6	15.6	15.6	15.6	15.6
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	11.4	10.7	11.4	11.7	12.1	11.7	9.6	7.1	5.3	4.8	4.3
92.5°	26.7	30.6	35.9	45.8	54.7	54.0	41.9	28.4	18.8	16.8	14.9
95°	56.5	71.4	93.1	121.9	139.3	123.3	82.1	51.2	34.8	30.6	26.3
97.5°	116.2	152.1	190.5	228.8	227.1	175.5	109.1	66.1	45.1	40.3	35.5
100°	231.7	280.4	324.4	331.9	280.7	193.3	116.6	73.2	54.4	49.4	44.4
102.5°	378.4	410.8	412.2	370.3	282.5	186.6	116.9	79.6	62.5	57.6	52.6
105°	476.5	471.9	431.7	357.8	263.3	177.3	118.7	87.1	70.4	65.4	60.4
107.5°	505.3	470.5	410.8	331.5	245.5	172.3	122.6	94.5	78.2	73.2	68.2
110°	491.1	445.6	382.0	307.0	233.5	170.9	127.6	102.0	86.3	81.2	76.0

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	465.5	416.1	355.7	290.0	225.6	171.3	132.9	109.1	94.2	88.8	83.5
115°	436.4	389.8	335.1	276.5	220.3	172.7	138.2	116.6	101.3	96.5	91.7
117.5°	410.4	367.1	318.0	267.2	217.5	174.8	143.9	123.3	109.1	104.1	99.1
120°	387.7	350.0	306.0	260.1	215.0	177.0	149.6	130.4	116.6	111.6	106.6
122.5°	371.0	335.8	296.4	254.1	213.6	179.4	154.6	137.2	124.4	119.2	114.1
125°	355.0	323.7	287.1	248.4	211.8	181.9	159.9	143.9	131.1	126.2	121.2
127.5°	341.5	311.6	277.9	243.1	210.7	184.4	164.9	150.3	137.9	132.8	127.6
130°	327.6	299.6	269.0	237.7	210.0	187.3	169.5	156.0	143.6	138.6	133.6
132.5°	313.4	288.2	260.5	233.5	209.7	190.1	174.1	161.0	149.2	144.2	139.3
135°	299.6	276.1	252.7	229.6	209.3	192.2	178.0	165.6	154.2	149.2	144.3
137.5°	285.7	266.5	246.3	226.7	209.3	194.4	181.2	169.5	158.1	153.5	148.9
140°	273.6	257.3	240.2	224.2	208.9	195.8	183.7	172.7	162.0	157.4	152.8
142.5°	262.6	249.1	235.2	221.7	208.9	196.9	185.8	175.2	164.9	160.6	156.4
145°	253.4	242.3	230.6	219.6	208.2	197.6	187.6	177.7	168.1	164.2	160.3
147.5°	245.5	236.7	227.1	217.5	207.2	197.9	188.7	179.8	170.6	167.0	163.5
150°	238.4	231.0	223.2	214.6	206.1	197.6	189.4	181.2	173.1	169.9	166.7
152.5°	232.4	226.4	219.2	212.1	204.3	196.9	189.8	182.6	175.5	172.7	169.9
155°	226.7	221.4	215.7	208.9	202.2	196.2	190.1	184.1	178.0	175.4	172.7
157.5°	221.0	216.4	211.4	206.1	200.1	194.7	190.1	185.1	179.8	177.5	175.2
160°	215.3	211.4	207.5	202.9	197.9	193.7	190.1	185.8	181.6	179.6	177.7
162.5°	210.0	206.8	203.6	200.1	196.2	192.6	189.8	186.2	182.6	181.2	179.8
165°	204.7	202.2	199.7	196.9	193.7	191.2	189.0	186.6	183.4	182.3	181.2
167.5°	199.7	197.9	195.8	193.7	191.5	189.8	188.7	186.6	184.1	183.4	182.6
170°	195.4	194.0	193.0	191.2	189.8	188.7	188.0	186.2	184.4	183.9	183.4
172.5°	191.5	190.5	189.8	188.7	187.6	187.3	186.9	185.8	184.8	184.4	184.1
175°	188.3	188.0	187.6	186.6	186.2	185.8	186.2	185.5	184.8	184.6	184.4
177.5°	186.2	185.8	185.8	185.1	184.8	185.1	185.8	185.1	184.8	184.8	184.8
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	967.7	967.7	967.7	967.7
2.5°	949.8	949.8	961.0	972.9
5°	929.0	934.2	952.1	968.4
7.5°	908.9	917.8	940.2	961.0
10°	884.4	896.3	923.8	948.3
12.5°	860.6	871.7	903.7	931.2
15°	827.1	841.2	875.5	909.7
17.5°	793.6	807.8	849.4	889.6
20°	754.2	772.8	819.7	873.2
22.5°	717.8	740.8	792.9	836.0
25°	677.6	713.3	761.6	817.4
27.5°	641.9	677.6	726.7	783.2
30°	601.7	638.2	688.8	740.8
32.5°	563.1	596.5	645.6	709.6
35°	522.9	554.9	602.5	667.2
37.5°	486.4	517.7	569.7	629.3
40°	450.7	483.5	528.1	587.6
42.5°	417.3	446.3	486.4	545.9
45°	386.8	407.6	444.8	500.6
47.5°	354.8	373.4	407.6	463.4
50°	325.0	340.7	370.4	422.5
52.5°	296.0	309.4	336.9	378.6
55°	270.0	282.6	302.7	343.6
57.5°	243.2	252.9	272.2	305.0
60°	217.2	226.1	241.7	268.5
62.5°	191.2	198.6	213.5	235.0
65°	168.1	174.0	185.2	203.8
67.5°	145.8	149.5	158.4	173.3
70°	124.2	127.2	134.6	146.5
72.5°	101.2	104.1	112.3	120.5
75°	81.8	82.6	88.5	95.2
77.5°	64.0	63.2	67.7	72.9
80°	43.9	46.1	49.8	52.1
82.5°	29.8	30.5	32.0	33.5
85°	16.4	17.1	17.1	19.3
87.5°	6.7	7.4	7.4	8.2
90°	3.6	2.8	1.4	0.4
92.5°	12.1	10.3	7.5	5.3
95°	20.6	17.4	13.9	12.4
97.5°	29.1	24.5	20.6	18.5
100°	37.3	31.6	28.4	27.4
102.5°	45.1	39.4	36.2	35.5
105°	52.6	47.3	44.8	43.4
107.5°	60.4	55.4	52.9	51.9
110°	68.6	64.0	61.8	60.4

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	76.4	72.1	69.6	68.2
115°	84.6	80.3	78.2	76.4
117.5°	92.4	88.5	86.3	84.9
120°	99.5	96.3	94.2	92.7
122.5°	107.0	103.4	101.3	100.2
125°	114.1	109.8	107.7	106.6
127.5°	120.8	116.2	113.4	111.9
130°	126.5	121.5	118.0	116.6
132.5°	131.8	126.5	122.6	120.8
135°	136.1	130.8	126.5	125.1
137.5°	140.7	135.0	130.8	129.0
140°	145.0	139.3	135.0	133.6
142.5°	148.9	143.2	139.3	138.2
145°	153.2	147.8	144.3	142.8
147.5°	157.4	152.4	148.9	147.8
150°	161.3	156.7	153.9	152.8
152.5°	164.9	161.0	158.1	157.8
155°	168.8	164.9	162.7	162.4
157.5°	172.0	168.4	166.7	166.3
160°	174.8	172.0	170.6	170.2
162.5°	177.3	175.2	173.8	174.1
165°	179.4	177.3	176.6	177.0
167.5°	181.2	179.8	179.1	179.4
170°	182.6	181.6	181.2	181.9
172.5°	183.7	182.6	183.0	183.4
175°	184.4	183.7	184.1	184.4
177.5°	184.8	184.1	184.4	185.1
180°	184.8	184.8	184.8	184.8

TEST NUMBER: P998461

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.41	17.35	17.26	18.22	19.30	13.90	14.85	14.76	15.71	16.80
	3H	17.23	18.07	18.09	18.95	20.06	15.26	16.10	16.12	16.97	18.09
	4H	17.40	18.20	18.28	19.08	20.20	15.72	16.52	16.60	17.40	18.52
	6H	17.45	18.18	18.34	19.07	20.21	16.03	16.76	16.92	17.65	18.79
	8H	17.43	18.13	18.33	19.04	20.17	16.12	16.81	17.02	17.72	18.86
	12H	17.40	18.06	18.30	18.96	20.12	16.16	16.83	17.07	17.73	18.89
4H	2H	16.46	17.26	17.35	18.14	19.26	14.36	15.15	15.24	16.04	17.16
	3H	17.45	18.11	18.35	19.03	20.16	15.83	16.49	16.72	17.40	18.54
	4H	17.73	18.33	18.64	19.24	20.41	16.37	16.97	17.27	17.88	19.04
	6H	17.86	18.38	18.79	19.32	20.48	16.75	17.27	17.67	18.20	19.37
	8H	17.86	18.35	18.79	19.28	20.45	16.86	17.34	17.78	18.27	19.45
	12H	17.83	18.27	18.77	19.21	20.40	16.92	17.36	17.86	18.30	19.49
8H	4H	17.74	18.23	18.67	19.16	20.34	16.51	17.00	17.44	17.93	19.10
	6H	17.93	18.33	18.88	19.30	20.47	16.95	17.35	17.90	18.32	19.50
	8H	17.96	18.31	18.92	19.27	20.47	17.10	17.45	18.06	18.42	19.61
	12H	17.95	18.26	18.91	19.21	20.45	17.20	17.51	18.16	18.46	19.71
12H	4H	17.71	18.14	18.65	19.09	20.27	16.49	16.93	17.43	17.87	19.06
	6H	17.91	18.26	18.86	19.22	20.42	16.95	17.30	17.91	18.27	19.46
	8H	17.94	18.25	18.90	19.21	20.45	17.11	17.42	18.07	18.38	19.62