

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998462

Luminaire Tested: SA2XXDIP-B485D330UB30-4F0-XX-W2A-D

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998462
REPORT IS A COMBINATION OF REPORTS P984205 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D330UB30-4F0-XX-W2A-D
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3277.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998462

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-D

Luminous Intensity Polar Plot



TEST NUMBER: P998462

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	97	92	87	83	89	85	81	78	72	69	67	60	58	56	50	48	47
2	88	79	72	67	81	73	67	62	62	58	54	52	49	46	43	40	38
3	80	69	61	55	73	64	57	51	54	49	45	46	41	38	37	34	32
4	73	61	52	46	67	56	49	43	48	42	38	40	36	32	33	30	27
5	66	54	45	39	61	50	42	37	43	37	32	36	31	28	30	26	23
6	61	48	40	34	56	45	37	32	38	32	28	32	28	24	27	23	20
7	56	44	35	29	52	41	33	28	35	29	24	29	25	21	24	21	18
8	52	39	31	26	48	37	29	24	32	26	22	27	22	19	22	19	16
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	14
10	45	33	25	21	42	31	24	19	27	21	17	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8122	8122	8122
5°	8159	7775	7733
10°	8105	7506	7397
15°	7990	7228	7054
20°	7846	6935	6728
25°	7703	6655	6432
30°	7505	6371	6139
35°	7302	6097	5924
40°	7090	5859	5711
45°	6886	5643	5524
50°	6669	5445	5341
55°	6440	5234	5153
60°	6160	5015	4957
65°	5869	4763	4730
70°	5539	4492	4486
75°	5119	4221	4257
80°	4455	3940	4018
85°	3786	3674	3812

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6886 cd/sqm

TEST NUMBER: P998462

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.6	1.5
10°-20°	139.5	4.3
20°-30°	211.4	6.5
30°-40°	257.4	7.9
40°-50°	277.0	8.5
50°-60°	269.0	8.2
60°-70°	234.9	7.2
70°-80°	180.8	5.5
80°-90°	121.9	3.7
90°-100°	98.4	3.0
100°-110°	116.3	3.5
110°-120°	186.9	5.7
120°-130°	265.6	8.1
130°-140°	267.7	8.2
140°-150°	241.6	7.4
150°-160°	193.0	5.9
160°-170°	124.3	3.8
170°-180°	42.8	1.3
0°-30°	399.6	12.2
0°-40°	657.0	20.0
0°-60°	1202.9	36.7
0°-90°	1740.5	53.1
90°-120°	401.5	12.3
90°-150°	1176.4	35.9
90°-180°	1536.0	46.9
0°-180°	3277.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	513	513	513	513	513	
5°	515	512	508	512	512	49
15°	491	492	492	499	498	138
25°	446	451	458	467	469	205
35°	384	397	411	428	433	240
45°	315	335	361	384	392	243
55°	242	268	307	334	344	216
65°	165	202	245	276	286	164
75°	92	133	181	213	222	97
85°	27	73	120	152	162	28
90°	8	54	105	136	146	6
95°	27	51	98	128	137	30
105°	103	134	84	113	123	110
115°	190	204	245	117	102	187
125°	266	270	300	323	330	238
135°	328	333	344	362	368	254
145°	380	379	385	392	394	238
155°	418	415	419	421	418	193
165°	440	439	440	442	440	124
175°	451	448	449	451	448	43
180°	450	450	450	450	450	

TEST NUMBER: P998462

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-D

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	513.1	513.1	513.1	513.1	513.1
2.5°	516.9	514.6	509.4	513.1	511.7
5°	514.6	512.4	507.9	512.4	511.7
7.5°	510.9	509.4	505.7	510.9	510.2
10°	506.5	505.0	502.7	508.7	507.9
12.5°	499.0	499.8	498.3	504.2	503.5
15°	490.8	492.3	492.3	499.0	498.3
17.5°	480.4	483.4	485.6	492.3	492.3
20°	470.0	473.7	476.7	484.9	484.9
22.5°	458.9	463.3	467.8	476.0	477.5
25°	446.2	451.4	458.1	467.0	469.3
27.5°	431.3	439.5	447.0	458.1	459.6
30°	416.5	426.1	435.8	447.7	449.9
32.5°	400.1	411.3	423.2	437.3	441.8
35°	384.5	397.1	411.3	427.6	432.8
37.5°	367.4	381.5	399.4	417.2	422.4
40°	350.3	366.6	386.7	406.1	412.8
42.5°	333.9	350.3	374.1	395.6	402.3
45°	315.3	335.4	361.4	384.5	391.9
47.5°	297.5	319.0	348.8	372.6	380.8
50°	278.9	301.9	335.4	360.7	368.9
52.5°	261.0	285.6	321.3	347.3	356.2
55°	241.7	268.5	307.1	333.9	343.6
57.5°	223.1	252.9	291.5	320.5	330.2
60°	203.0	235.0	277.4	305.7	316.1
62.5°	185.2	218.6	261.0	291.5	301.2
65°	165.1	201.5	245.4	275.9	285.6
67.5°	147.3	185.2	229.8	260.3	270.7
70°	127.9	166.6	212.7	244.7	253.6
72.5°	110.1	150.2	197.1	228.3	239.5
75°	91.5	133.1	180.7	212.7	222.4
77.5°	73.6	116.8	165.1	197.1	207.5
80°	55.8	101.1	149.5	180.7	191.1
82.5°	40.9	85.5	134.6	165.8	175.5
85°	26.8	72.9	120.5	151.7	162.1
87.5°	16.4	61.0	108.6	139.1	148.7
90°	7.7	54.5	104.7	136.0	145.6
92.5°	14.8	52.9	99.3	129.0	138.2
95°	27.0	51.3	98.2	128.1	136.7
97.5°	43.3	48.6	96.9	125.4	134.7
100°	62.8	45.7	92.9	123.0	131.9
102.5°	83.6	107.4	88.4	118.7	127.9
105°	102.6	134.0	83.8	113.4	122.9
107.5°	125.7	151.7	79.3	108.1	117.6
110°	147.1	168.8	111.2	102.5	112.0

TEST NUMBER: P998462

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-D

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	168.0	185.7	214.4	98.0	107.1
115°	190.1	203.8	245.3	117.0	101.8
117.5°	208.5	221.0	257.7	233.5	155.7
120°	230.0	237.8	273.5	298.2	262.5
122.5°	248.2	254.2	288.2	310.2	317.3
125°	266.0	270.2	300.2	322.6	330.3
127.5°	282.9	286.7	311.7	333.5	340.6
130°	298.9	303.3	322.6	343.9	349.6
132.5°	315.1	318.6	333.4	353.4	359.1
135°	328.0	333.2	343.6	362.5	367.7
137.5°	342.3	346.2	353.3	370.6	374.9
140°	356.3	358.2	363.3	378.1	380.9
142.5°	368.0	369.6	373.8	385.3	387.4
145°	379.7	379.4	384.9	391.7	393.8
147.5°	390.4	389.5	395.0	397.3	398.3
150°	400.8	398.6	403.8	405.7	404.1
152.5°	409.6	407.0	411.9	413.9	411.6
155°	418.1	415.2	419.1	421.0	418.4
157.5°	424.9	422.3	425.2	427.5	424.9
160°	430.8	428.8	430.8	432.7	430.5
162.5°	436.0	434.0	435.7	437.9	435.0
165°	440.5	438.6	439.6	441.8	439.6
167.5°	444.1	442.2	443.1	445.4	442.5
170°	447.0	445.1	445.7	448.0	445.1
172.5°	449.0	447.0	447.7	450.0	447.0
175°	450.6	448.3	449.0	451.3	448.0
177.5°	451.3	449.0	449.3	451.6	448.7
180°	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P998462

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-D

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.77	13.71	13.68	14.65	15.88	15.84	16.78	16.76	17.73	18.95
	3H	14.23	15.09	15.16	16.04	17.28	18.43	19.29	19.36	20.24	21.49
	4H	14.71	15.52	15.65	16.48	17.73	19.69	20.50	20.63	21.46	22.71
	6H	15.00	15.75	15.95	16.71	17.98	20.99	21.74	21.95	22.71	23.97
	8H	15.06	15.78	16.02	16.76	18.02	21.65	22.37	22.61	23.35	24.62
	12H	15.08	15.77	16.05	16.74	18.03	22.38	23.07	23.35	24.04	25.33
4H	2H	13.82	14.64	14.77	15.60	16.85	16.18	16.99	17.13	17.95	19.20
	3H	15.54	16.23	16.50	17.22	18.48	18.98	19.67	19.93	20.65	21.92
	4H	16.16	16.80	17.13	17.78	19.07	20.39	21.03	21.36	22.01	23.30
	6H	16.58	17.14	17.56	18.14	19.43	21.87	22.42	22.85	23.43	24.71
	8H	16.69	17.21	17.67	18.21	19.52	22.63	23.15	23.61	24.15	25.45
	12H	16.74	17.21	17.74	18.23	19.54	23.46	23.93	24.46	24.95	26.26
8H	4H	16.96	17.48	17.94	18.48	19.78	20.55	21.07	21.53	22.07	23.37
	6H	17.60	18.03	18.60	19.07	20.37	22.18	22.62	23.18	23.66	24.96
	8H	17.82	18.21	18.83	19.23	20.55	23.07	23.46	24.08	24.49	25.80
	12H	17.96	18.30	18.98	19.32	20.69	24.07	24.41	25.09	25.43	26.80
12H	4H	17.16	17.64	18.16	18.65	19.96	20.52	21.00	21.53	22.01	23.32
	6H	17.93	18.32	18.94	19.35	20.67	22.20	22.59	23.22	23.62	24.94
	8H	18.24	18.59	19.26	19.61	20.97	23.14	23.48	24.16	24.50	25.87