

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998472

Luminaire Tested: SA2XXDIP-B485D330UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998472
REPORT IS A COMBINATION OF REPORTS P984215 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D330UB35-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3151.0 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998472

CATALOG NUMBER: SA2XXDIP-B485D330UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P998472

CATALOG NUMBER: SA2XXDIP-B485D330UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	97	92	88	84	90	86	82	78	73	70	68	62	60	58	51	50	48
2	88	80	73	67	81	74	68	63	63	59	55	53	50	47	44	42	39
3	80	69	61	55	74	65	57	52	55	50	45	47	42	39	39	36	33
4	73	61	53	46	67	57	49	43	49	43	38	41	37	33	34	31	28
5	67	54	46	39	61	51	43	37	43	37	33	37	32	28	31	27	24
6	61	49	40	34	57	45	38	32	39	33	28	33	28	25	28	24	21
7	57	44	35	29	52	41	33	28	35	29	25	30	25	22	25	21	18
8	53	40	32	26	49	37	30	25	32	26	22	28	23	19	23	19	16
9	49	36	28	23	45	34	27	22	29	24	19	25	21	17	21	18	15
10	46	33	26	21	42	31	24	20	27	21	17	23	19	15	20	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8160	8160	8160
5°	8197	7812	7768
10°	8142	7541	7431
15°	8027	7262	7087
20°	7883	6968	6758
25°	7740	6686	6461
30°	7539	6400	6167
35°	7336	6125	5951
40°	7122	5886	5736
45°	6919	5670	5549
50°	6701	5470	5365
55°	6470	5260	5177
60°	6190	5039	4979
65°	5898	4784	4752
70°	5565	4513	4508
75°	5141	4240	4276
80°	4471	3958	4036
85°	3800	3690	3831

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6919 cd/sqm

TEST NUMBER: P998472

CATALOG NUMBER: SA2XXDIP-B485D330UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.9	1.6
10°-20°	140.2	4.4
20°-30°	212.4	6.7
30°-40°	258.6	8.2
40°-50°	278.2	8.8
50°-60°	270.2	8.6
60°-70°	236.0	7.5
70°-80°	181.6	5.8
80°-90°	122.8	3.9
90°-100°	110.1	3.5
100°-110°	144.5	4.6
110°-120°	182.8	5.8
120°-130°	209.8	6.7
130°-140°	219.6	7.0
140°-150°	207.7	6.6
150°-160°	172.9	5.5
160°-170°	114.7	3.6
170°-180°	40.1	1.3
0°-30°	401.4	12.7
0°-40°	660.0	20.9
0°-60°	1208.5	38.4
0°-90°	1748.9	55.5
90°-120°	437.4	13.9
90°-150°	1074.5	34.1
90°-180°	1402.0	44.5
0°-180°	3151.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	516	516	516	516	516	
5°	517	515	510	515	514	49
15°	493	495	495	501	501	139
25°	448	454	460	469	471	206
35°	386	399	413	430	435	241
45°	317	337	363	386	394	245
55°	243	270	309	336	345	217
65°	166	202	246	277	287	165
75°	92	134	182	214	223	97
85°	27	73	121	152	163	28
90°	8	55	111	140	150	6
95°	25	63	109	137	145	25
105°	80	103	143	170	178	85
115°	146	156	189	211	218	144
125°	209	212	235	254	261	187
135°	270	274	282	297	302	209
145°	326	329	331	336	338	204
155°	373	374	375	377	376	172
165°	406	406	406	408	406	115
175°	422	421	421	423	421	40
180°	423	423	423	423	423	

TEST NUMBER: P998472

CATALOG NUMBER: SA2XXDIP-B485D330UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	515.5	515.5	515.5	515.5	515.5
2.5°	519.2	517.0	511.8	515.5	514.0
5°	517.0	514.8	510.3	514.8	514.0
7.5°	513.3	511.8	508.0	513.3	512.5
10°	508.8	507.3	505.0	511.0	510.3
12.5°	501.3	502.1	500.6	506.5	505.8
15°	493.1	494.6	494.6	501.3	500.6
17.5°	482.6	485.6	487.9	494.6	494.6
20°	472.2	475.9	478.9	487.1	487.1
22.5°	461.0	465.5	469.9	478.2	479.6
25°	448.3	453.5	460.2	469.2	471.4
27.5°	433.3	441.5	449.0	460.2	461.7
30°	418.4	428.1	437.8	449.8	452.0
32.5°	401.9	413.2	425.1	439.3	443.8
35°	386.3	399.0	413.2	429.6	434.8
37.5°	369.1	383.3	401.2	419.1	424.4
40°	351.9	368.3	388.5	407.9	414.6
42.5°	335.5	351.9	375.8	397.5	404.2
45°	316.8	336.9	363.1	386.3	393.7
47.5°	298.8	320.5	350.4	374.3	382.5
50°	280.2	303.3	336.9	362.4	370.6
52.5°	262.2	286.9	322.8	348.9	357.9
55°	242.8	269.7	308.6	335.5	345.2
57.5°	224.1	254.0	292.9	322.0	331.7
60°	204.0	236.1	278.7	307.1	317.5
62.5°	186.0	219.7	262.2	292.9	302.6
65°	165.9	202.5	246.5	277.2	286.9
67.5°	147.9	186.0	230.9	261.5	271.9
70°	128.5	167.4	213.7	245.8	254.8
72.5°	110.6	150.9	198.0	229.4	240.6
75°	91.9	133.7	181.5	213.7	223.4
77.5°	74.0	117.3	165.9	198.0	208.4
80°	56.0	101.6	150.2	181.5	192.0
82.5°	41.1	85.9	135.2	166.6	176.3
85°	26.9	73.2	121.0	152.4	162.9
87.5°	16.4	61.3	109.1	139.7	149.4
90°	7.9	55.4	111.1	140.3	149.6
92.5°	14.6	57.0	103.0	132.4	141.4
95°	24.6	63.2	108.7	137.1	145.4
97.5°	36.3	71.7	116.4	144.0	153.0
100°	50.5	81.1	124.0	151.7	159.5
102.5°	64.8	91.6	133.4	160.7	168.5
105°	80.5	103.2	142.8	169.7	177.9
107.5°	96.9	116.3	153.6	179.4	185.8
110°	111.9	128.9	165.5	189.4	196.7



TEST NUMBER: P998472

CATALOG NUMBER: SA2XXDIP-B485D330UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	129.0	143.1	177.1	199.9	207.4
115°	145.8	156.1	189.0	211.1	218.3
117.5°	161.8	170.6	200.3	221.6	228.0
120°	178.6	184.4	211.5	232.4	239.6
122.5°	193.9	198.3	224.1	243.2	249.2
125°	209.3	212.5	235.3	254.5	260.8
127.5°	225.0	228.1	246.9	264.2	269.8
130°	239.6	243.5	258.5	275.7	280.2
132.5°	256.1	258.8	270.5	285.8	290.7
135°	269.5	273.5	281.7	297.0	301.9
137.5°	285.2	288.5	293.0	306.8	310.6
140°	299.2	301.7	305.0	316.9	319.9
142.5°	313.4	316.0	317.0	326.4	328.7
145°	326.3	328.8	331.0	335.8	338.1
147.5°	338.4	341.7	343.1	344.5	345.4
150°	350.9	353.1	354.5	355.6	354.5
152.5°	362.0	364.2	365.9	367.4	365.9
155°	373.1	374.1	375.2	377.0	375.9
157.5°	382.7	383.4	384.1	386.6	384.9
160°	391.3	392.0	392.4	394.5	393.1
162.5°	399.1	399.1	399.5	402.0	400.2
165°	405.9	405.6	405.6	408.1	406.3
167.5°	412.0	410.9	410.9	413.4	411.6
170°	416.6	415.6	415.2	417.7	415.6
172.5°	419.8	418.8	418.4	420.9	418.8
175°	422.3	421.3	420.6	423.1	420.9
177.5°	423.8	422.7	422.0	424.1	422.0
180°	423.1	423.1	423.1	423.1	423.1

TEST NUMBER: P998472

CATALOG NUMBER: SA2XXDIP-B485D330UB35-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.99	13.96	13.88	14.88	16.07	16.06	17.03	16.96	17.96	19.14
	3H	14.45	15.33	15.36	16.27	17.48	18.66	19.54	19.56	20.47	21.68
	4H	14.93	15.77	15.85	16.71	17.93	19.91	20.75	20.84	21.69	22.91
	6H	15.22	16.00	16.16	16.94	18.17	21.22	21.99	22.15	22.94	24.17
	8H	15.28	16.02	16.22	16.99	18.22	21.88	22.62	22.82	23.58	24.81
	12H	15.30	16.01	16.25	16.97	18.22	22.61	23.31	23.55	24.27	25.53
4H	2H	14.05	14.88	14.97	15.82	17.04	16.40	17.24	17.33	18.18	19.39
	3H	15.76	16.47	16.70	17.44	18.67	19.20	19.91	20.14	20.88	22.11
	4H	16.39	17.04	17.34	18.01	19.26	20.62	21.28	21.57	22.24	23.50
	6H	16.81	17.38	17.77	18.37	19.62	22.10	22.67	23.05	23.65	24.91
	8H	16.92	17.46	17.88	18.44	19.71	22.86	23.39	23.82	24.37	25.64
	12H	16.97	17.46	17.95	18.45	19.73	23.69	24.18	24.67	25.17	26.45
8H	4H	17.19	17.72	18.15	18.70	19.98	20.77	21.31	21.74	22.29	23.56
	6H	17.82	18.28	18.81	19.30	20.57	22.41	22.86	23.40	23.88	25.15
	8H	18.05	18.45	19.04	19.46	20.75	23.30	23.70	24.29	24.71	26.00
	12H	18.19	18.54	19.19	19.55	20.88	24.30	24.66	25.30	25.66	26.99
12H	4H	17.39	17.88	18.37	18.88	20.15	20.75	21.24	21.74	22.24	23.52
	6H	18.16	18.56	19.16	19.57	20.86	22.43	22.84	23.43	23.85	25.13
	8H	18.47	18.83	19.47	19.83	21.16	23.37	23.73	24.37	24.73	26.06

END OF REPORT