

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998488

Luminaire Tested: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998488
REPORT IS A COMBINATION OF REPORTS P984231 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3292.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	68	68	68
1	101	97	93	90	95	91	88	85	80	78	75	70	68	67	61	59	58	58	58	54
2	93	85	79	74	87	80	75	71	71	67	63	62	59	57	54	52	50	50	50	46
3	85	76	68	63	79	71	65	60	63	58	54	56	52	49	48	46	43	43	43	40
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	40	38	38	38	35
5	72	60	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33	33	33	30
6	67	55	47	41	62	52	44	39	46	40	36	41	36	33	36	33	30	30	30	27
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27	27	27	24
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24	24	24	22
9	54	41	34	29	50	39	33	28	36	30	26	32	27	24	29	25	22	22	22	20
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14729	14729	14729	14729
5°	14764	15704	14821	12495
10°	14593	17145	14684	10302
15°	14239	18083	14438	8678
20°	14017	16980	14017	7542
25°	13570	14587	13632	6745
30°	12836	11467	13081	6109
35°	12185	7929	12388	5590
40°	11435	5986	11567	5176
45°	10514	4919	10684	4727
50°	9716	4319	9733	4329
55°	8804	3679	8863	3893
60°	7835	3074	7944	3398
65°	6968	2499	7092	2902
70°	6102	1962	6258	2340
75°	5119	1424	5320	1698
80°	4000	902	4279	1007
85°	2627	454	2825	336

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15226 cd/sqm

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.6	2.7
10°-20°	258.0	7.8
20°-30°	374.4	11.4
30°-40°	394.7	12.0
40°-50°	349.2	10.6
50°-60°	278.9	8.5
60°-70°	189.4	5.8
70°-80°	96.9	2.9
80°-90°	24.0	0.7
90°-100°	69.3	2.1
100°-110°	244.0	7.4
110°-120°	256.3	7.8
120°-130°	210.8	6.4
130°-140°	169.4	5.1
140°-150°	127.9	3.9
150°-160°	89.9	2.7
160°-170°	52.9	1.6
170°-180°	17.2	0.5
0°-30°	721.0	21.9
0°-40°	1115.7	33.9
0°-60°	1743.8	53.0
0°-90°	2054.1	62.4
90°-120°	569.6	17.3
90°-150°	1077.7	32.7
90°-180°	1238.0	37.6
0°-180°	3292.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	931	1039	935	827	931	88
15°	875	1277	887	613	875	247
25°	786	1064	790	492	786	359
35°	642	579	652	408	642	401
45°	481	349	489	335	481	373
55°	330	245	333	260	330	295
65°	196	151	200	175	196	195
75°	92	74	95	89	92	98
85°	19	19	20	14	19	22
90°	0	11	0	11	0	2
95°	12	39	12	39	12	12
105°	42	385	42	385	42	44
115°	74	507	74	507	74	73
125°	102	411	102	411	102	91
135°	120	341	120	341	120	93
145°	137	272	137	272	137	86
155°	156	229	156	229	156	72
165°	170	201	170	201	170	48
175°	177	181	177	181	177	17
180°	178	178	178	178	178	

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	935.5	937.7	941.2	942.0	949.1	954.8	961.3	961.3	963.4	962.7	957.0
5°	931.2	937.7	947.0	954.8	967.7	973.4	982.0	988.4	994.2	998.5	997.7
7.5°	924.1	935.5	949.1	964.1	981.3	991.3	1003.5	1014.9	1022.8	1029.9	1034.9
10°	911.9	931.2	949.8	969.9	992.0	1005.6	1019.9	1034.9	1047.1	1060.7	1073.6
12.5°	895.5	923.4	946.3	972.7	999.9	1014.9	1037.8	1049.2	1072.8	1107.2	1116.5
15°	874.7	912.6	934.1	967.7	1003.5	1015.6	1047.1	1065.7	1114.3	1135.8	1161.5
17.5°	855.4	897.6	926.2	964.8	999.9	1023.5	1054.3	1092.2	1132.9	1163.7	1192.3
20°	839.7	880.4	914.8	957.7	1002.0	1032.1	1064.3	1110.0	1154.4	1185.9	1208.0
22.5°	803.9	856.1	896.2	944.1	997.7	1039.2	1070.0	1120.1	1168.0	1187.3	1206.6
25°	786.0	831.1	877.6	931.9	994.9	1044.2	1070.7	1126.5	1168.7	1175.8	1180.1
27.5°	753.1	803.9	858.3	920.5	994.2	1035.7	1069.3	1120.1	1153.7	1148.7	1135.8
30°	712.4	774.6	834.7	901.9	984.2	1029.2	1060.7	1107.2	1124.3	1098.6	1075.7
32.5°	682.3	741.0	807.5	885.5	972.7	1015.6	1046.4	1082.9	1086.4	1039.9	1001.3
35°	641.6	706.6	781.7	864.0	953.4	992.0	1020.6	1042.8	1025.6	960.6	914.8
37.5°	605.1	669.5	749.6	833.2	926.9	964.8	987.7	991.3	949.1	891.9	824.7
40°	565.0	631.5	715.2	803.2	897.6	930.5	944.8	934.1	873.3	806.8	728.8
42.5°	525.0	590.8	680.9	771.0	860.4	888.3	894.0	864.7	790.3	712.4	622.3
45°	481.4	550.0	640.1	731.0	817.5	833.2	834.0	791.8	703.8	622.3	538.6
47.5°	445.6	509.2	598.6	689.5	762.4	773.2	768.9	720.2	624.4	532.8	459.9
50°	406.3	467.0	555.7	645.1	707.4	710.2	699.5	630.1	536.4	452.7	394.8
52.5°	364.1	425.6	507.1	592.9	648.7	644.4	623.7	549.3	461.3	391.9	347.6
55°	330.4	384.8	461.3	545.0	584.3	572.2	549.3	473.5	404.1	345.5	306.8
57.5°	293.2	341.2	416.3	489.2	512.1	500.7	477.8	407.0	342.6	298.3	272.5
60°	258.2	301.8	367.6	428.4	446.3	434.1	407.7	344.0	297.5	260.3	241.0
62.5°	226.0	263.9	319.0	374.8	381.9	369.8	346.9	295.4	255.3	226.0	211.7
65°	196.0	231.7	276.1	318.3	324.7	311.8	288.2	251.0	217.4	198.8	185.2
67.5°	166.6	195.3	234.6	265.4	268.9	256.8	237.5	207.4	186.7	166.6	156.6
70°	140.9	162.4	193.1	218.1	219.6	208.1	198.1	170.9	155.2	140.9	133.0
72.5°	115.9	130.9	154.5	173.1	173.8	166.6	157.4	140.2	126.6	116.6	108.7
75°	91.5	104.4	118.7	135.2	134.5	128.7	121.6	110.9	99.4	93.0	89.4
77.5°	70.1	78.0	89.4	100.1	100.1	97.3	93.0	85.1	78.0	71.5	67.9
80°	50.1	55.1	64.4	67.9	69.4	68.7	65.1	59.4	56.5	51.5	50.1
82.5°	32.2	35.8	40.1	43.6	45.8	44.3	43.6	40.8	36.5	35.0	33.6
85°	18.6	20.0	22.2	24.3	25.0	24.3	25.7	23.6	21.5	21.5	20.7
87.5°	7.9	8.6	10.0	10.0	10.7	10.7	10.0	10.7	10.7	10.0	9.3
90°	0.3	1.4	2.7	3.4	4.1	4.6	5.1	6.8	9.2	11.3	11.6
92.5°	5.1	7.2	9.9	11.6	14.4	16.2	18.1	27.3	40.3	52.0	52.6
95°	12.0	13.3	16.7	19.8	25.3	29.4	33.5	49.2	79.0	118.6	134.0
97.5°	17.8	19.8	23.6	28.0	34.2	38.8	43.4	63.6	104.9	168.9	218.4
100°	26.3	27.3	30.4	35.9	42.7	47.5	52.3	70.4	112.1	186.0	270.0
102.5°	34.2	34.9	37.9	43.4	50.6	55.4	60.2	76.6	112.5	179.5	271.8
105°	41.7	43.1	45.5	50.6	58.1	62.9	67.7	83.7	114.2	170.6	253.3
107.5°	49.9	50.9	53.3	58.1	65.6	70.4	75.2	90.9	117.9	165.8	236.2
110°	58.1	59.5	61.5	66.0	73.2	78.2	83.1	98.1	122.7	164.4	224.6

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	65.6	67.0	69.4	73.5	80.3	85.4	90.6	104.9	127.8	164.8	217.1
115°	73.5	75.2	77.3	81.4	88.2	92.8	97.4	112.1	133.0	166.1	211.9
117.5°	81.7	83.1	85.1	88.9	95.4	100.2	104.9	118.6	138.4	168.2	209.2
120°	89.2	90.6	92.6	95.7	102.5	107.3	112.1	125.5	143.9	170.2	206.8
122.5°	96.4	97.4	99.5	102.9	109.7	114.6	119.6	131.9	148.7	172.6	205.4
125°	102.5	103.6	105.6	109.7	116.6	121.4	126.1	138.4	153.8	175.0	203.7
127.5°	107.7	109.0	111.8	116.2	122.7	127.6	132.6	144.6	158.6	177.4	202.7
130°	112.1	113.5	116.9	121.7	128.5	133.3	138.1	150.1	163.1	180.1	202.0
132.5°	116.2	117.9	121.7	126.8	134.0	138.8	143.6	154.8	167.5	182.9	201.7
135°	120.3	121.7	125.8	130.9	138.8	143.6	148.4	159.3	171.3	184.9	201.3
137.5°	124.1	125.8	129.9	135.4	143.2	147.6	152.1	163.1	174.3	187.0	201.3
140°	128.5	129.9	134.0	139.5	147.0	151.4	155.9	166.1	176.7	188.3	201.0
142.5°	133.0	134.0	137.8	143.2	150.4	154.5	158.6	168.5	178.8	189.4	201.0
145°	137.4	138.8	142.2	147.3	154.2	158.0	161.7	170.9	180.5	190.1	200.3
147.5°	142.2	143.2	146.6	151.4	157.2	160.6	164.1	173.0	181.5	190.4	199.3
150°	147.0	148.0	150.7	155.2	160.3	163.4	166.5	174.3	182.2	190.1	198.3
152.5°	151.8	152.1	154.8	158.6	163.4	166.2	168.9	175.7	182.5	189.4	196.6
155°	156.2	156.6	158.6	162.4	166.1	168.7	171.3	177.1	182.9	188.7	194.5
157.5°	160.0	160.3	162.0	165.4	168.5	170.8	173.0	178.1	182.9	187.3	192.4
160°	163.7	164.1	165.4	168.2	170.9	172.8	174.7	178.8	182.9	186.3	190.4
162.5°	167.5	167.2	168.5	170.6	173.0	174.4	175.7	179.1	182.5	185.3	188.7
165°	170.2	169.9	170.6	172.6	174.3	175.4	176.4	179.5	181.9	183.9	186.3
167.5°	172.6	172.3	173.0	174.3	175.7	176.4	177.1	179.5	181.5	182.5	184.2
170°	175.0	174.3	174.7	175.7	176.4	176.9	177.4	179.1	180.8	181.5	182.5
172.5°	176.4	176.0	175.7	176.7	177.1	177.4	177.8	178.8	179.8	180.1	180.5
175°	177.4	177.1	176.7	177.4	177.4	177.6	177.8	178.4	179.1	178.8	179.1
177.5°	178.1	177.4	177.1	177.8	177.8	177.8	177.8	178.1	178.8	178.1	177.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	967.0	967.7	969.1	976.3	979.9	980.6	977.7	984.2	986.3	984.2	982.7
5°	1012.8	1017.1	1025.6	1034.9	1034.2	1034.9	1039.2	1043.5	1045.0	1039.2	1041.4
7.5°	1052.8	1061.4	1070.7	1085.0	1085.0	1092.2	1095.0	1098.6	1107.2	1102.9	1101.5
10°	1098.6	1110.0	1127.2	1150.1	1150.8	1158.0	1165.1	1176.6	1180.1	1177.3	1178.7
12.5°	1155.8	1178.0	1179.4	1204.4	1215.9	1217.3	1228.8	1226.6	1233.8	1233.8	1245.9
15°	1180.8	1215.2	1234.5	1258.8	1266.0	1257.4	1266.7	1276.7	1277.4	1277.4	1276.7
17.5°	1225.9	1239.5	1258.8	1271.7	1274.5	1274.5	1275.3	1279.5	1276.7	1271.0	1275.3
20°	1235.2	1240.9	1248.1	1246.6	1248.1	1240.9	1233.8	1226.6	1227.3	1223.8	1234.5
22.5°	1218.0	1216.6	1200.2	1189.4	1189.4	1175.1	1161.5	1155.1	1148.7	1150.8	1154.4
25°	1175.1	1153.0	1132.9	1117.2	1113.6	1090.7	1072.1	1066.4	1055.7	1064.3	1065.7
27.5°	1106.5	1081.4	1049.2	1035.7	1017.1	1007.8	994.9	977.7	955.5	968.4	966.3
30°	1032.8	995.6	969.1	936.2	906.9	904.8	880.4	851.8	840.4	840.4	846.8
32.5°	950.5	901.2	862.6	816.1	787.5	775.3	746.0	717.4	723.8	702.4	710.2
35°	854.7	789.6	741.0	695.9	674.5	660.2	622.3	606.5	589.4	579.3	597.9
37.5°	763.2	688.1	625.8	576.5	568.6	542.9	517.1	507.1	497.1	501.4	500.7
40°	651.6	585.1	529.3	490.6	477.1	464.9	447.7	435.6	429.1	432.7	433.4
42.5°	550.7	494.9	453.5	426.3	414.8	406.3	397.7	387.7	385.5	385.5	388.4
45°	472.8	427.0	399.1	376.9	370.5	364.1	357.6	353.3	351.9	349.0	351.2
47.5°	410.5	374.1	356.9	340.4	333.3	331.9	326.1	324.0	321.1	320.4	321.1
50°	358.3	335.4	319.7	310.4	305.4	303.3	300.4	296.1	294.7	298.3	296.8
52.5°	321.9	300.4	291.8	282.5	279.7	276.8	272.5	273.2	272.5	271.1	271.1
55°	285.4	271.8	263.2	256.1	255.3	252.5	248.9	247.5	246.8	245.3	247.5
57.5°	256.1	245.3	237.5	231.0	228.2	228.2	224.6	221.7	221.7	221.0	221.7
60°	226.7	216.0	211.0	204.6	202.4	201.7	199.5	198.1	196.0	196.0	196.0
62.5°	199.5	191.0	185.2	179.5	180.2	176.7	173.8	172.4	172.4	173.1	173.1
65°	173.8	168.1	160.9	155.9	154.5	153.8	152.3	151.6	149.5	150.9	150.9
67.5°	150.2	142.3	138.0	135.9	133.7	133.0	131.6	130.2	129.5	128.7	130.2
70°	126.6	120.2	116.6	115.2	113.0	112.3	111.6	109.4	110.1	110.9	111.6
72.5°	105.1	99.4	98.7	94.4	94.4	94.4	91.5	93.0	92.3	90.8	92.3
75°	83.0	80.1	78.7	76.5	77.2	76.5	75.8	73.7	73.7	74.4	75.1
77.5°	65.8	62.9	62.2	60.1	58.6	60.1	58.6	57.9	57.9	58.6	58.6
80°	48.6	47.2	45.1	45.1	45.1	44.3	44.3	44.3	43.6	42.9	43.6
82.5°	32.2	32.2	31.5	30.8	31.5	30.0	30.8	30.8	30.8	30.8	30.8
85°	20.7	20.0	20.0	19.3	19.3	19.3	20.0	18.6	18.6	19.3	19.3
87.5°	9.3	9.3	9.3	10.0	9.3	9.3	9.3	10.0	9.3	9.3	9.3
90°	11.3	10.9	10.3	10.9	11.1	11.3	11.3	11.3	11.3	11.3	11.3
92.5°	44.1	34.5	29.4	25.6	24.2	22.9	22.6	21.2	21.5	20.9	21.5
95°	117.2	89.6	68.7	54.4	50.6	46.8	42.4	39.7	38.6	39.0	38.6
97.5°	220.1	183.2	146.3	111.8	101.6	91.3	77.9	71.1	67.3	65.3	67.3
100°	319.3	312.1	269.7	222.9	202.2	181.5	153.1	138.4	128.5	122.4	128.5
102.5°	356.2	396.5	395.2	364.0	341.8	319.6	288.2	260.5	247.5	238.6	247.5
105°	344.2	415.3	453.9	458.4	452.8	447.1	425.9	404.7	390.0	385.2	390.0
107.5°	318.9	395.2	452.6	486.1	493.0	499.8	499.4	496.3	491.9	484.0	491.9
110°	295.3	367.5	428.7	472.4	486.4	500.4	515.1	521.6	524.7	524.4	524.7

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	278.9	342.2	400.3	447.8	464.4	481.0	502.8	514.8	521.3	523.7	521.3
115°	265.9	322.3	375.0	419.8	437.4	455.0	479.2	495.0	503.9	506.9	503.9
117.5°	257.1	305.9	353.1	394.8	411.6	428.3	453.3	470.0	479.2	481.6	479.2
120°	250.2	294.3	336.7	372.9	388.4	404.0	428.0	444.0	453.9	457.4	453.9
122.5°	244.4	285.1	323.0	356.9	370.5	384.2	405.1	420.8	429.3	432.1	429.3
125°	238.9	276.2	311.4	341.5	354.3	367.1	386.9	399.9	408.5	411.2	408.5
127.5°	233.8	267.3	299.8	328.5	340.4	352.4	369.9	382.2	389.7	391.7	389.7
130°	228.7	258.8	288.2	315.2	326.4	337.7	354.5	366.1	372.9	375.7	372.9
132.5°	224.6	250.6	277.2	301.5	311.9	322.3	338.8	350.4	356.5	358.9	356.5
135°	220.8	243.0	265.6	288.2	297.8	307.3	322.0	333.3	339.4	340.8	339.4
137.5°	218.1	236.9	256.4	274.8	283.4	291.9	305.9	315.8	321.3	323.4	321.3
140°	215.7	231.1	247.5	263.2	270.7	278.2	289.2	298.1	303.2	305.3	303.2
142.5°	213.3	226.3	239.6	252.6	258.6	264.6	274.8	282.7	287.1	287.1	287.1
145°	211.2	221.8	233.1	243.7	248.6	253.6	261.8	267.7	271.1	272.1	271.1
147.5°	209.2	218.4	227.7	236.2	240.0	243.7	250.9	255.7	258.1	258.8	258.1
150°	206.5	214.7	222.2	229.4	232.4	235.5	240.6	244.7	246.8	247.1	246.8
152.5°	204.1	210.9	217.7	223.6	226.2	228.7	232.4	235.9	237.2	237.2	237.2
155°	201.0	207.5	213.0	218.1	220.0	221.8	225.6	228.0	229.4	228.7	229.4
157.5°	198.3	203.4	208.2	212.6	214.2	215.7	218.4	220.5	221.2	221.2	221.2
160°	195.2	199.6	203.4	207.1	208.3	209.5	211.9	213.6	214.0	214.0	214.0
162.5°	192.4	195.9	198.9	202.0	202.8	203.7	206.1	207.1	207.5	207.1	207.5
165°	189.4	192.1	194.5	196.9	197.6	198.3	199.6	201.0	201.0	200.7	201.0
167.5°	186.3	188.3	190.4	192.1	192.8	193.5	194.2	194.8	194.8	194.5	194.8
170°	183.9	185.6	186.6	188.0	188.4	188.7	189.0	190.1	189.7	189.0	189.7
172.5°	181.5	182.5	183.2	184.2	184.4	184.6	184.9	185.3	184.9	184.6	184.9
175°	179.5	180.5	180.8	181.2	181.4	181.5	181.5	181.9	181.5	180.8	181.5
177.5°	178.1	178.8	178.8	179.1	179.1	179.1	179.1	179.1	178.8	178.1	178.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	986.3	981.3	977.0	977.7	981.3	978.4	971.3	962.0	958.4	954.1	958.4
5°	1045.7	1041.4	1032.8	1033.5	1031.4	1028.5	1017.1	1002.8	1002.8	991.3	989.9
7.5°	1104.3	1097.9	1092.2	1090.7	1082.9	1077.1	1067.1	1047.1	1039.2	1025.6	1017.8
10°	1170.1	1165.1	1158.7	1150.8	1146.5	1136.5	1120.1	1090.7	1076.4	1057.8	1044.2
12.5°	1236.6	1235.9	1221.6	1205.9	1205.2	1189.4	1178.0	1138.6	1119.3	1094.3	1062.1
15°	1278.8	1275.3	1267.4	1259.5	1261.7	1244.5	1218.8	1172.3	1159.4	1129.3	1095.0
17.5°	1278.1	1278.1	1276.0	1274.5	1272.4	1267.4	1253.1	1222.3	1201.6	1163.7	1131.5
20°	1237.3	1246.6	1248.8	1248.1	1255.2	1258.8	1258.1	1238.8	1222.3	1188.7	1155.8
22.5°	1155.8	1177.3	1186.6	1192.3	1207.3	1215.2	1233.8	1226.6	1222.3	1197.3	1169.4
25°	1080.0	1087.2	1115.0	1116.5	1137.2	1156.5	1175.1	1187.3	1203.0	1193.7	1170.1
27.5°	982.0	998.5	1018.5	1033.5	1037.8	1077.1	1107.9	1130.8	1166.5	1169.4	1161.5
30°	871.2	879.0	911.9	931.9	954.8	983.4	1027.8	1067.1	1099.3	1128.6	1138.6
32.5°	736.0	768.2	787.5	811.8	831.8	882.6	937.0	987.7	1024.9	1074.3	1095.7
35°	612.2	637.3	670.2	680.2	716.7	759.6	830.4	895.5	952.0	1002.0	1045.7
37.5°	510.0	530.0	565.0	580.8	602.2	657.3	716.7	797.5	865.4	926.9	981.3
40°	439.9	454.9	481.4	486.4	504.2	554.3	602.2	678.0	768.2	851.1	910.5
42.5°	391.9	399.1	417.0	423.4	434.9	468.5	511.4	582.9	666.6	752.4	836.1
45°	357.6	362.6	373.4	379.1	393.4	408.4	443.4	500.7	566.5	653.0	743.1
47.5°	326.9	333.3	337.6	341.2	349.0	365.5	388.4	430.6	493.5	572.9	660.2
50°	301.1	303.3	311.1	311.8	316.8	327.6	349.0	374.8	424.8	489.2	573.6
52.5°	275.4	277.5	282.5	287.5	289.7	298.3	312.6	334.0	371.2	422.0	497.1
55°	249.6	252.5	257.5	261.1	263.2	270.4	278.9	299.7	329.0	364.8	426.3
57.5°	223.9	230.3	231.7	233.9	237.5	245.3	253.2	265.4	288.2	321.1	366.2
60°	199.5	201.7	206.7	208.8	212.4	216.7	226.7	236.0	252.5	278.2	319.0
62.5°	174.5	179.5	181.7	183.8	186.7	191.7	198.1	208.1	222.4	243.2	275.4
65°	153.1	153.8	158.1	160.9	163.8	167.4	173.8	183.1	191.7	211.0	234.6
67.5°	132.3	133.7	135.2	138.0	141.6	145.2	150.9	155.9	166.6	179.5	198.1
70°	112.3	112.3	115.9	118.0	117.3	121.6	125.9	131.6	139.5	151.6	166.6
72.5°	94.4	93.7	96.6	97.3	98.7	101.6	104.4	110.1	114.4	123.7	135.2
75°	75.1	76.5	78.0	78.0	80.1	82.3	85.1	88.0	93.0	98.7	107.3
77.5°	59.4	59.4	60.8	61.5	63.7	62.9	65.8	68.7	72.2	77.2	83.7
80°	43.6	45.1	45.1	45.1	45.8	46.5	49.4	51.5	53.6	57.2	60.1
82.5°	30.8	30.8	32.2	32.2	32.2	33.6	33.6	34.3	35.8	37.9	40.1
85°	19.3	19.3	19.3	20.0	19.3	20.0	21.5	20.7	21.5	22.9	22.9
87.5°	9.3	9.3	9.3	9.3	9.3	10.0	9.3	10.0	10.7	10.7	10.7
90°	11.3	11.3	11.3	11.1	10.9	10.3	10.9	11.3	11.6	11.3	9.2
92.5°	21.2	22.6	22.9	24.2	25.6	29.4	34.5	44.1	52.6	52.0	40.3
95°	39.7	42.4	46.8	50.6	54.4	68.7	89.6	117.2	134.0	118.6	79.0
97.5°	71.1	77.9	91.3	101.6	111.8	146.3	183.2	220.1	218.4	168.9	104.9
100°	138.4	153.1	181.5	202.2	222.9	269.7	312.1	319.3	270.0	186.0	112.1
102.5°	260.5	288.2	319.6	341.8	364.0	395.2	396.5	356.2	271.8	179.5	112.5
105°	404.7	425.9	447.1	452.8	458.4	453.9	415.3	344.2	253.3	170.6	114.2
107.5°	496.3	499.4	499.8	493.0	486.1	452.6	395.2	318.9	236.2	165.8	117.9
110°	521.6	515.1	500.4	486.4	472.4	428.7	367.5	295.3	224.6	164.4	122.7

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	514.8	502.8	481.0	464.4	447.8	400.3	342.2	278.9	217.1	164.8	127.8
115°	495.0	479.2	455.0	437.4	419.8	375.0	322.3	265.9	211.9	166.1	133.0
117.5°	470.0	453.3	428.3	411.6	394.8	353.1	305.9	257.1	209.2	168.2	138.4
120°	444.0	428.0	404.0	388.4	372.9	336.7	294.3	250.2	206.8	170.2	143.9
122.5°	420.8	405.1	384.2	370.5	356.9	323.0	285.1	244.4	205.4	172.6	148.7
125°	399.9	386.9	367.1	354.3	341.5	311.4	276.2	238.9	203.7	175.0	153.8
127.5°	382.2	369.9	352.4	340.4	328.5	299.8	267.3	233.8	202.7	177.4	158.6
130°	366.1	354.5	337.7	326.4	315.2	288.2	258.8	228.7	202.0	180.1	163.1
132.5°	350.4	338.8	322.3	311.9	301.5	277.2	250.6	224.6	201.7	182.9	167.5
135°	333.3	322.0	307.3	297.8	288.2	265.6	243.0	220.8	201.3	184.9	171.3
137.5°	315.8	305.9	291.9	283.4	274.8	256.4	236.9	218.1	201.3	187.0	174.3
140°	298.1	289.2	278.2	270.7	263.2	247.5	231.1	215.7	201.0	188.3	176.7
142.5°	282.7	274.8	264.6	258.6	252.6	239.6	226.3	213.3	201.0	189.4	178.8
145°	267.7	261.8	253.6	248.6	243.7	233.1	221.8	211.2	200.3	190.1	180.5
147.5°	255.7	250.9	243.7	240.0	236.2	227.7	218.4	209.2	199.3	190.4	181.5
150°	244.7	240.6	235.5	232.4	229.4	222.2	214.7	206.5	198.3	190.1	182.2
152.5°	235.9	232.4	228.7	226.2	223.6	217.7	210.9	204.1	196.6	189.4	182.5
155°	228.0	225.6	221.8	220.0	218.1	213.0	207.5	201.0	194.5	188.7	182.9
157.5°	220.5	218.4	215.7	214.2	212.6	208.2	203.4	198.3	192.4	187.3	182.9
160°	213.6	211.9	209.5	208.3	207.1	203.4	199.6	195.2	190.4	186.3	182.9
162.5°	207.1	206.1	203.7	202.8	202.0	198.9	195.9	192.4	188.7	185.3	182.5
165°	201.0	199.6	198.3	197.6	196.9	194.5	192.1	189.4	186.3	183.9	181.9
167.5°	194.8	194.2	193.5	192.8	192.1	190.4	188.3	186.3	184.2	182.5	181.5
170°	190.1	189.0	188.7	188.4	188.0	186.6	185.6	183.9	182.5	181.5	180.8
172.5°	185.3	184.9	184.6	184.4	184.2	183.2	182.5	181.5	180.5	180.1	179.8
175°	181.9	181.5	181.5	181.4	181.2	180.8	180.5	179.5	179.1	178.8	179.1
177.5°	179.1	179.1	179.1	179.1	179.1	178.8	178.8	178.1	177.8	178.1	178.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	954.8	951.3	949.1	950.5	946.3	935.5	935.5	939.1	934.8	930.5	924.1
5°	981.3	974.1	969.9	969.1	959.1	942.0	938.4	934.8	925.5	915.5	904.8
7.5°	1007.0	994.2	987.0	982.0	967.7	945.5	936.2	928.4	913.3	898.3	884.7
10°	1028.5	1009.9	1001.3	993.5	974.9	947.0	931.9	917.6	898.3	879.0	861.9
12.5°	1045.7	1024.2	1013.5	1002.0	979.2	942.7	924.1	901.2	881.9	856.1	839.0
15°	1074.3	1029.9	1019.9	1009.2	985.6	935.5	912.6	886.9	860.4	826.1	807.5
17.5°	1097.2	1037.8	1037.1	1014.2	983.4	932.7	897.6	864.0	835.4	801.1	771.7
20°	1110.8	1050.0	1038.5	1014.9	976.3	913.3	876.9	839.7	808.9	767.4	738.1
22.5°	1122.2	1067.1	1037.1	1008.5	961.3	906.9	853.3	818.2	776.0	731.0	703.1
25°	1126.5	1070.7	1039.2	1006.3	950.5	888.3	827.5	789.6	742.4	701.6	663.7
27.5°	1127.2	1070.0	1031.4	997.0	935.5	864.0	801.8	761.7	709.5	662.3	624.4
30°	1120.1	1062.1	1027.1	989.9	921.2	841.8	770.3	726.0	670.2	623.0	583.6
32.5°	1098.6	1046.4	1017.8	977.0	902.6	811.1	740.3	690.9	632.3	585.8	547.9
35°	1062.8	1027.1	995.6	957.7	878.3	782.5	710.2	652.3	592.9	548.6	512.8
37.5°	1018.5	999.2	969.9	932.7	850.4	756.7	676.6	612.2	552.9	510.0	474.9
40°	958.4	963.4	934.8	901.2	817.5	721.7	633.0	571.5	515.7	475.6	441.3
42.5°	893.3	914.1	897.6	865.4	781.0	683.0	600.8	532.8	478.5	437.0	408.4
45°	823.2	859.0	849.0	825.4	743.1	642.3	555.0	489.2	441.3	401.2	376.2
47.5°	746.7	797.5	797.5	780.3	700.9	601.5	515.7	448.4	401.2	372.6	348.3
50°	668.7	726.0	735.3	723.8	653.7	555.0	467.8	407.0	366.2	338.3	320.4
52.5°	587.2	653.7	670.9	665.2	603.7	510.7	428.4	369.1	331.9	307.5	291.8
55°	509.2	586.5	605.1	607.2	550.0	462.0	384.8	332.6	296.8	280.4	266.8
57.5°	435.6	510.0	530.7	534.3	495.7	417.7	344.0	298.3	266.1	252.5	241.7
60°	372.6	434.9	462.0	469.9	436.3	366.2	306.1	261.8	237.5	224.6	214.6
62.5°	321.1	371.2	399.8	402.0	386.9	321.1	266.8	229.6	208.8	197.4	192.4
65°	271.1	316.1	333.3	341.9	329.7	278.2	230.3	199.5	183.1	173.1	168.1
67.5°	231.0	259.6	273.9	285.4	273.2	234.6	196.0	170.9	158.8	148.8	145.9
70°	189.5	213.1	223.9	235.3	224.6	195.3	167.4	144.5	133.7	125.9	122.3
72.5°	151.6	170.2	180.2	187.4	181.0	156.6	133.7	118.0	110.1	104.4	102.3
75°	120.2	133.0	138.8	143.8	140.9	122.3	108.0	95.1	88.0	83.0	81.5
77.5°	91.5	100.8	107.3	108.7	105.1	93.0	80.8	73.0	67.2	64.4	62.9
80°	65.1	70.8	74.4	76.5	73.0	67.9	59.4	53.6	48.6	45.1	44.3
82.5°	43.6	46.5	49.4	48.6	47.2	42.9	37.9	35.0	32.9	30.0	30.0
85°	25.0	25.7	27.2	27.9	27.2	24.3	21.5	20.0	18.6	16.5	16.5
87.5°	10.7	11.4	11.4	12.2	10.7	10.7	9.3	7.9	7.9	7.2	6.4
90°	6.8	5.1	4.6	4.1	3.4	2.7	1.4	0.3	1.4	2.7	3.4
92.5°	27.3	18.1	16.2	14.4	11.6	9.9	7.2	5.1	7.2	9.9	11.6
95°	49.2	33.5	29.4	25.3	19.8	16.7	13.3	12.0	13.3	16.7	19.8
97.5°	63.6	43.4	38.8	34.2	28.0	23.6	19.8	17.8	19.8	23.6	28.0
100°	70.4	52.3	47.5	42.7	35.9	30.4	27.3	26.3	27.3	30.4	35.9
102.5°	76.6	60.2	55.4	50.6	43.4	37.9	34.9	34.2	34.9	37.9	43.4
105°	83.7	67.7	62.9	58.1	50.6	45.5	43.1	41.7	43.1	45.5	50.6
107.5°	90.9	75.2	70.4	65.6	58.1	53.3	50.9	49.9	50.9	53.3	58.1
110°	98.1	83.1	78.2	73.2	66.0	61.5	59.5	58.1	59.5	61.5	66.0

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	104.9	90.6	85.4	80.3	73.5	69.4	67.0	65.6	67.0	69.4	73.5
115°	112.1	97.4	92.8	88.2	81.4	77.3	75.2	73.5	75.2	77.3	81.4
117.5°	118.6	104.9	100.2	95.4	88.9	85.1	83.1	81.7	83.1	85.1	88.9
120°	125.5	112.1	107.3	102.5	95.7	92.6	90.6	89.2	90.6	92.6	95.7
122.5°	131.9	119.6	114.6	109.7	102.9	99.5	97.4	96.4	97.4	99.5	102.9
125°	138.4	126.1	121.4	116.6	109.7	105.6	103.6	102.5	103.6	105.6	109.7
127.5°	144.6	132.6	127.6	122.7	116.2	111.8	109.0	107.7	109.0	111.8	116.2
130°	150.1	138.1	133.3	128.5	121.7	116.9	113.5	112.1	113.5	116.9	121.7
132.5°	154.8	143.6	138.8	134.0	126.8	121.7	117.9	116.2	117.9	121.7	126.8
135°	159.3	148.4	143.6	138.8	130.9	125.8	121.7	120.3	121.7	125.8	130.9
137.5°	163.1	152.1	147.6	143.2	135.4	129.9	125.8	124.1	125.8	129.9	135.4
140°	166.1	155.9	151.4	147.0	139.5	134.0	129.9	128.5	129.9	134.0	139.5
142.5°	168.5	158.6	154.5	150.4	143.2	137.8	134.0	133.0	134.0	137.8	143.2
145°	170.9	161.7	158.0	154.2	147.3	142.2	138.8	137.4	138.8	142.2	147.3
147.5°	173.0	164.1	160.6	157.2	151.4	146.6	143.2	142.2	143.2	146.6	151.4
150°	174.3	166.5	163.4	160.3	155.2	150.7	148.0	147.0	148.0	150.7	155.2
152.5°	175.7	168.9	166.2	163.4	158.6	154.8	152.1	151.8	152.1	154.8	158.6
155°	177.1	171.3	168.7	166.1	162.4	158.6	156.6	156.2	156.6	158.6	162.4
157.5°	178.1	173.0	170.8	168.5	165.4	162.0	160.3	160.0	160.3	162.0	165.4
160°	178.8	174.7	172.8	170.9	168.2	165.4	164.1	163.7	164.1	165.4	168.2
162.5°	179.1	175.7	174.4	173.0	170.6	168.5	167.2	167.5	167.2	168.5	170.6
165°	179.5	176.4	175.4	174.3	172.6	170.6	169.9	170.2	169.9	170.6	172.6
167.5°	179.5	177.1	176.4	175.7	174.3	173.0	172.3	172.6	172.3	173.0	174.3
170°	179.1	177.4	176.9	176.4	175.7	174.7	174.3	175.0	174.3	174.7	175.7
172.5°	178.8	177.8	177.4	177.1	176.7	175.7	176.0	176.4	176.0	175.7	176.7
175°	178.4	177.8	177.6	177.4	177.4	176.7	177.1	177.4	177.1	176.7	177.4
177.5°	178.1	177.8	177.8	177.8	177.8	177.1	177.4	178.1	177.4	177.1	177.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	920.5	924.1	923.4	916.2	908.3	901.9	889.7	891.2	886.9	887.6	891.9
5°	897.6	897.6	894.8	884.7	871.9	864.7	851.1	847.5	839.0	838.3	837.5
7.5°	873.3	869.7	866.1	851.8	836.1	824.7	806.1	801.8	793.2	787.5	784.6
10°	844.7	839.7	832.5	816.1	796.8	782.5	763.2	757.4	741.0	733.8	729.5
12.5°	813.2	810.4	798.9	785.3	753.9	738.1	710.2	715.9	699.5	685.2	683.0
15°	781.7	771.0	764.6	742.4	704.5	697.3	675.2	663.7	648.7	637.3	637.3
17.5°	751.0	734.5	720.2	696.6	668.7	648.7	632.3	626.5	607.9	596.5	594.4
20°	710.2	691.6	688.1	654.4	635.1	613.0	597.2	582.9	569.3	564.3	560.7
22.5°	671.6	650.1	644.4	615.8	596.5	574.3	558.6	548.6	538.6	535.0	528.6
25°	630.1	617.2	608.7	577.9	556.4	535.7	525.0	517.8	508.5	507.8	503.5
27.5°	590.1	577.9	569.3	540.0	524.3	505.0	496.4	488.5	483.5	481.4	479.2
30°	555.7	542.1	532.1	510.7	491.4	475.6	468.5	463.5	460.6	457.0	456.3
32.5°	517.8	510.0	496.4	479.9	464.9	449.9	445.6	442.0	437.7	436.3	435.6
35°	485.6	474.9	466.3	447.7	441.3	428.4	423.4	420.6	414.8	413.4	412.0
37.5°	454.2	444.2	434.9	423.4	411.3	404.1	401.2	397.0	394.1	394.8	393.4
40°	422.7	414.8	407.7	395.5	388.4	384.8	379.1	374.8	373.4	374.1	373.4
42.5°	391.9	384.8	380.5	371.2	364.1	360.5	356.9	352.6	354.8	354.8	356.9
45°	364.1	357.6	354.8	347.6	343.3	337.6	334.0	333.3	336.2	335.4	335.4
47.5°	335.4	333.3	329.7	323.3	317.6	314.0	313.3	313.3	316.1	317.6	316.8
50°	313.3	309.0	304.7	299.7	295.4	294.0	291.8	293.2	296.1	296.1	297.5
52.5°	285.4	282.5	281.1	276.8	273.9	273.9	273.9	274.6	276.8	278.9	278.2
55°	261.1	258.9	257.5	255.3	251.8	252.5	251.8	253.2	255.3	257.5	258.9
57.5°	235.3	234.6	233.2	229.6	229.6	228.9	231.0	231.7	235.3	236.7	238.9
60°	212.4	210.3	210.3	207.4	207.4	207.4	209.6	211.7	214.6	215.3	216.7
62.5°	188.1	188.1	187.4	185.2	185.2	187.4	188.1	191.0	192.4	192.4	194.5
65°	165.2	164.5	163.8	164.5	165.2	165.2	167.4	168.8	170.2	170.9	171.7
67.5°	142.3	141.6	143.0	142.3	143.8	146.6	145.9	148.1	150.2	150.2	150.9
70°	120.9	122.3	121.6	123.0	122.3	123.7	125.9	126.6	126.6	127.3	129.5
72.5°	100.8	100.8	100.8	100.1	100.8	102.3	103.7	104.4	105.9	106.6	108.7
75°	81.5	81.5	80.1	81.5	81.5	83.0	84.4	84.4	84.4	85.8	88.0
77.5°	61.5	62.2	61.5	62.9	62.9	63.7	65.1	64.4	65.8	66.5	67.2
80°	45.1	44.3	44.3	44.3	45.1	45.1	46.5	47.2	47.2	49.4	47.9
82.5°	28.6	29.3	28.6	29.3	29.3	30.0	29.3	30.0	30.8	32.2	31.5
85°	16.5	15.7	15.7	16.5	15.7	15.7	16.5	15.7	16.5	15.7	16.5
87.5°	6.4	5.7	5.7	5.7	5.7	5.0	5.0	4.3	4.3	4.3	3.6
90°	4.1	4.6	5.1	6.8	9.2	11.3	11.6	11.3	10.9	10.3	10.9
92.5°	14.4	16.2	18.1	27.3	40.3	52.0	52.6	44.1	34.5	29.4	25.6
95°	25.3	29.4	33.5	49.2	79.0	118.6	134.0	117.2	89.6	68.7	54.4
97.5°	34.2	38.8	43.4	63.6	104.9	168.9	218.4	220.1	183.2	146.3	111.8
100°	42.7	47.5	52.3	70.4	112.1	186.0	270.0	319.3	312.1	269.7	222.9
102.5°	50.6	55.4	60.2	76.6	112.5	179.5	271.8	356.2	396.5	395.2	364.0
105°	58.1	62.9	67.7	83.7	114.2	170.6	253.3	344.2	415.3	453.9	458.4
107.5°	65.6	70.4	75.2	90.9	117.9	165.8	236.2	318.9	395.2	452.6	486.1
110°	73.2	78.2	83.1	98.1	122.7	164.4	224.6	295.3	367.5	428.7	472.4

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	80.3	85.4	90.6	104.9	127.8	164.8	217.1	278.9	342.2	400.3	447.8
115°	88.2	92.8	97.4	112.1	133.0	166.1	211.9	265.9	322.3	375.0	419.8
117.5°	95.4	100.2	104.9	118.6	138.4	168.2	209.2	257.1	305.9	353.1	394.8
120°	102.5	107.3	112.1	125.5	143.9	170.2	206.8	250.2	294.3	336.7	372.9
122.5°	109.7	114.6	119.6	131.9	148.7	172.6	205.4	244.4	285.1	323.0	356.9
125°	116.6	121.4	126.1	138.4	153.8	175.0	203.7	238.9	276.2	311.4	341.5
127.5°	122.7	127.6	132.6	144.6	158.6	177.4	202.7	233.8	267.3	299.8	328.5
130°	128.5	133.3	138.1	150.1	163.1	180.1	202.0	228.7	258.8	288.2	315.2
132.5°	134.0	138.8	143.6	154.8	167.5	182.9	201.7	224.6	250.6	277.2	301.5
135°	138.8	143.6	148.4	159.3	171.3	184.9	201.3	220.8	243.0	265.6	288.2
137.5°	143.2	147.6	152.1	163.1	174.3	187.0	201.3	218.1	236.9	256.4	274.8
140°	147.0	151.4	155.9	166.1	176.7	188.3	201.0	215.7	231.1	247.5	263.2
142.5°	150.4	154.5	158.6	168.5	178.8	189.4	201.0	213.3	226.3	239.6	252.6
145°	154.2	158.0	161.7	170.9	180.5	190.1	200.3	211.2	221.8	233.1	243.7
147.5°	157.2	160.6	164.1	173.0	181.5	190.4	199.3	209.2	218.4	227.7	236.2
150°	160.3	163.4	166.5	174.3	182.2	190.1	198.3	206.5	214.7	222.2	229.4
152.5°	163.4	166.2	168.9	175.7	182.5	189.4	196.6	204.1	210.9	217.7	223.6
155°	166.1	168.7	171.3	177.1	182.9	188.7	194.5	201.0	207.5	213.0	218.1
157.5°	168.5	170.8	173.0	178.1	182.9	187.3	192.4	198.3	203.4	208.2	212.6
160°	170.9	172.8	174.7	178.8	182.9	186.3	190.4	195.2	199.6	203.4	207.1
162.5°	173.0	174.4	175.7	179.1	182.5	185.3	188.7	192.4	195.9	198.9	202.0
165°	174.3	175.4	176.4	179.5	181.9	183.9	186.3	189.4	192.1	194.5	196.9
167.5°	175.7	176.4	177.1	179.5	181.5	182.5	184.2	186.3	188.3	190.4	192.1
170°	176.4	176.9	177.4	179.1	180.8	181.5	182.5	183.9	185.6	186.6	188.0
172.5°	177.1	177.4	177.8	178.8	179.8	180.1	180.5	181.5	182.5	183.2	184.2
175°	177.4	177.6	177.8	178.4	179.1	178.8	179.1	179.5	180.5	180.8	181.2
177.5°	177.8	177.8	177.8	178.1	178.8	178.1	177.8	178.1	178.8	178.8	179.1
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	886.9	889.0	884.0	882.6	884.0	879.0	880.4	881.9	881.9	884.0	885.5
5°	835.4	832.5	827.5	826.1	824.7	826.8	825.4	827.5	828.2	833.2	834.0
7.5°	784.6	780.3	776.0	771.7	770.3	766.7	770.3	770.3	775.3	773.9	777.5
10°	724.5	723.8	718.1	715.9	713.1	707.4	715.2	713.1	716.7	723.1	724.5
12.5°	680.2	672.3	675.9	665.9	669.5	663.7	664.4	664.4	670.2	670.9	669.5
15°	638.0	631.5	622.3	618.0	615.8	613.0	622.3	623.0	618.7	628.7	625.1
17.5°	595.1	595.1	586.5	584.3	578.6	581.5	580.1	580.8	579.3	586.5	590.1
20°	557.9	554.3	551.4	552.2	545.0	543.6	542.1	543.6	548.6	553.6	555.0
22.5°	527.8	525.7	518.5	520.0	514.3	516.4	515.0	518.5	519.3	519.3	524.3
25°	499.2	496.4	497.1	494.2	492.1	492.1	489.9	492.1	494.9	496.4	497.1
27.5°	477.8	475.6	472.1	469.9	471.3	467.8	470.6	472.8	472.8	471.3	472.8
30°	452.0	453.5	453.5	446.3	449.2	447.7	449.9	451.3	451.3	452.0	450.6
32.5°	434.9	430.6	429.9	429.1	429.1	426.3	426.3	428.4	429.1	429.9	432.0
35°	412.0	412.0	408.4	410.5	407.7	408.4	407.7	408.4	409.8	407.7	409.8
37.5°	391.2	391.9	390.5	391.9	392.7	391.2	389.8	392.7	391.2	391.2	389.8
40°	373.4	372.6	373.4	373.4	373.4	374.1	372.6	372.6	372.6	371.2	369.8
42.5°	358.3	354.0	355.5	356.2	354.0	354.0	354.8	354.0	356.2	351.9	351.9
45°	336.9	335.4	336.2	336.2	337.6	335.4	336.9	337.6	335.4	334.7	333.3
47.5°	317.6	319.0	317.6	319.0	319.0	320.4	317.6	318.3	319.0	316.1	314.0
50°	298.3	298.3	300.4	299.7	300.4	299.0	299.0	298.3	299.0	297.5	295.4
52.5°	280.4	278.2	281.8	281.1	280.4	279.7	278.9	279.7	278.2	276.8	276.8
55°	258.2	258.2	260.3	261.1	261.1	259.6	258.2	258.9	258.2	257.5	256.8
57.5°	240.3	237.5	238.9	239.6	239.6	237.5	238.9	237.5	237.5	238.2	236.0
60°	217.4	217.4	216.0	218.1	218.1	216.7	216.7	217.4	216.0	215.3	214.6
62.5°	193.1	193.8	196.0	196.7	197.4	196.0	194.5	195.3	195.3	193.1	193.8
65°	172.4	173.8	176.7	175.9	174.5	175.2	173.8	174.5	172.4	173.1	170.9
67.5°	152.3	151.6	152.3	152.3	153.8	153.1	151.6	151.6	150.9	153.1	150.9
70°	130.9	130.9	130.9	130.9	131.6	132.3	130.9	129.5	130.2	128.7	128.0
72.5°	108.7	109.4	108.7	110.1	108.0	109.4	109.4	108.7	108.0	108.0	108.0
75°	88.0	89.4	87.3	88.0	87.3	88.7	88.0	88.0	86.5	85.8	86.5
77.5°	67.2	67.9	66.5	67.2	66.5	67.2	67.2	66.5	66.5	66.5	66.5
80°	47.9	48.6	47.9	47.2	46.5	47.9	46.5	47.2	47.9	47.2	48.6
82.5°	30.8	30.8	30.0	30.8	29.3	29.3	30.0	30.0	29.3	30.8	29.3
85°	15.0	15.0	16.5	15.0	14.3	14.3	14.3	15.0	14.3	15.7	15.0
87.5°	3.6	2.9	3.6	3.6	2.9	2.9	3.6	2.9	3.6	4.3	2.9
90°	11.1	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.1
92.5°	24.2	22.9	22.6	21.2	21.5	20.9	21.5	21.2	22.6	22.9	24.2
95°	50.6	46.8	42.4	39.7	38.6	39.0	38.6	39.7	42.4	46.8	50.6
97.5°	101.6	91.3	77.9	71.1	67.3	65.3	67.3	71.1	77.9	91.3	101.6
100°	202.2	181.5	153.1	138.4	128.5	122.4	128.5	138.4	153.1	181.5	202.2
102.5°	341.8	319.6	288.2	260.5	247.5	238.6	247.5	260.5	288.2	319.6	341.8
105°	452.8	447.1	425.9	404.7	390.0	385.2	390.0	404.7	425.9	447.1	452.8
107.5°	493.0	499.8	499.4	496.3	491.9	484.0	491.9	496.3	499.4	499.8	493.0
110°	486.4	500.4	515.1	521.6	524.7	524.4	524.7	521.6	515.1	500.4	486.4

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	464.4	481.0	502.8	514.8	521.3	523.7	521.3	514.8	502.8	481.0	464.4
115°	437.4	455.0	479.2	495.0	503.9	506.9	503.9	495.0	479.2	455.0	437.4
117.5°	411.6	428.3	453.3	470.0	479.2	481.6	479.2	470.0	453.3	428.3	411.6
120°	388.4	404.0	428.0	444.0	453.9	457.4	453.9	444.0	428.0	404.0	388.4
122.5°	370.5	384.2	405.1	420.8	429.3	432.1	429.3	420.8	405.1	384.2	370.5
125°	354.3	367.1	386.9	399.9	408.5	411.2	408.5	399.9	386.9	367.1	354.3
127.5°	340.4	352.4	369.9	382.2	389.7	391.7	389.7	382.2	369.9	352.4	340.4
130°	326.4	337.7	354.5	366.1	372.9	375.7	372.9	366.1	354.5	337.7	326.4
132.5°	311.9	322.3	338.8	350.4	356.5	358.9	356.5	350.4	338.8	322.3	311.9
135°	297.8	307.3	322.0	333.3	339.4	340.8	339.4	333.3	322.0	307.3	297.8
137.5°	283.4	291.9	305.9	315.8	321.3	323.4	321.3	315.8	305.9	291.9	283.4
140°	270.7	278.2	289.2	298.1	303.2	305.3	303.2	298.1	289.2	278.2	270.7
142.5°	258.6	264.6	274.8	282.7	287.1	287.1	287.1	282.7	274.8	264.6	258.6
145°	248.6	253.6	261.8	267.7	271.1	272.1	271.1	267.7	261.8	253.6	248.6
147.5°	240.0	243.7	250.9	255.7	258.1	258.8	258.1	255.7	250.9	243.7	240.0
150°	232.4	235.5	240.6	244.7	246.8	247.1	246.8	244.7	240.6	235.5	232.4
152.5°	226.2	228.7	232.4	235.9	237.2	237.2	237.2	235.9	232.4	228.7	226.2
155°	220.0	221.8	225.6	228.0	229.4	228.7	229.4	228.0	225.6	221.8	220.0
157.5°	214.2	215.7	218.4	220.5	221.2	221.2	221.2	220.5	218.4	215.7	214.2
160°	208.3	209.5	211.9	213.6	214.0	214.0	214.0	213.6	211.9	209.5	208.3
162.5°	202.8	203.7	206.1	207.1	207.5	207.1	207.5	207.1	206.1	203.7	202.8
165°	197.6	198.3	199.6	201.0	201.0	200.7	201.0	201.0	199.6	198.3	197.6
167.5°	192.8	193.5	194.2	194.8	194.8	194.5	194.8	194.8	194.2	193.5	192.8
170°	188.4	188.7	189.0	190.1	189.7	189.0	189.7	190.1	189.0	188.7	188.4
172.5°	184.4	184.6	184.9	185.3	184.9	184.6	184.9	185.3	184.9	184.6	184.4
175°	181.4	181.5	181.5	181.9	181.5	180.8	181.5	181.9	181.5	181.5	181.4
177.5°	179.1	179.1	179.1	179.1	178.8	178.1	178.8	179.1	179.1	179.1	179.1
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	883.3	889.0	886.9	879.0	888.3	888.3	894.8	894.8	902.6	905.5	909.8
5°	833.2	837.5	841.1	837.5	844.0	854.0	859.7	864.7	875.4	879.7	886.2
7.5°	779.6	787.5	791.0	791.0	801.8	813.2	824.7	831.8	846.8	852.6	859.0
10°	727.4	736.7	743.8	743.1	761.0	768.2	782.5	798.9	813.9	822.5	831.8
12.5°	672.3	677.3	687.3	701.6	705.9	718.8	735.3	756.0	783.2	791.0	804.6
15°	626.5	640.1	648.0	654.4	664.4	676.6	694.5	714.5	741.7	758.9	773.2
17.5°	587.9	605.8	610.8	609.4	622.3	640.8	661.6	676.6	700.9	721.7	735.3
20°	556.4	563.6	572.2	575.8	585.8	605.8	625.8	643.0	663.0	679.5	695.2
22.5°	525.0	530.7	537.9	544.3	552.2	563.6	582.9	604.4	623.7	639.4	657.3
25°	499.2	502.8	509.2	514.3	522.8	530.7	544.3	567.9	590.8	600.1	615.8
27.5°	474.2	477.1	481.4	487.1	491.4	499.2	511.4	530.7	554.3	563.6	585.1
30°	452.0	454.2	458.5	461.3	463.5	472.8	482.1	497.1	515.0	527.8	543.6
32.5°	431.3	433.4	437.7	438.4	441.3	446.3	454.9	468.5	484.2	494.9	508.5
35°	408.4	409.8	414.1	415.5	417.7	422.0	428.4	438.4	452.7	460.6	472.8
37.5°	390.5	389.8	392.7	394.8	397.7	399.8	402.0	412.0	422.7	429.9	439.2
40°	371.2	369.8	370.5	373.4	374.8	377.6	377.6	387.7	394.8	400.5	407.7
42.5°	351.9	351.2	349.7	351.2	352.6	353.3	354.0	361.2	368.3	373.4	381.2
45°	332.6	331.9	330.4	331.2	331.2	332.6	334.7	337.6	342.6	346.9	351.2
47.5°	314.7	313.3	311.1	310.4	311.8	311.8	311.8	314.7	319.7	321.1	325.4
50°	296.1	294.0	291.1	289.7	289.7	289.0	290.4	291.1	295.4	296.8	300.4
52.5°	276.1	274.6	271.8	268.9	269.6	268.2	268.9	269.6	271.1	273.2	275.4
55°	256.1	253.2	251.0	250.3	248.2	248.2	246.0	248.9	248.2	248.9	251.8
57.5°	236.7	233.9	230.3	228.9	226.7	226.0	224.6	223.9	224.6	226.7	228.9
60°	213.9	212.4	210.3	208.1	206.7	204.6	203.1	203.1	202.4	202.4	203.1
62.5°	191.7	191.0	188.1	187.4	186.0	184.5	182.4	181.0	181.0	182.4	183.1
65°	170.2	169.5	167.4	166.6	163.1	161.6	160.9	160.2	158.8	158.8	158.8
67.5°	150.2	148.1	148.1	144.5	141.6	140.2	138.8	138.0	138.0	138.0	138.8
70°	128.0	128.0	125.9	123.7	120.9	121.6	119.4	117.3	117.3	115.9	116.6
72.5°	106.6	105.9	103.7	103.0	100.8	98.7	97.3	98.7	96.6	95.8	96.6
75°	85.8	85.1	83.7	82.3	83.0	80.8	78.7	78.0	78.0	76.5	76.5
77.5°	65.8	67.2	64.4	63.7	62.2	60.8	60.1	59.4	59.4	59.4	60.8
80°	45.8	46.5	46.5	45.1	45.8	43.6	43.6	43.6	41.5	42.2	42.9
82.5°	29.3	29.3	28.6	29.3	28.6	28.6	27.9	27.9	27.2	27.2	27.9
85°	16.5	15.7	15.0	16.5	15.7	15.7	15.0	15.0	15.0	15.0	15.0
87.5°	3.6	4.3	4.3	4.3	4.3	5.0	5.0	5.0	5.7	5.7	5.7
90°	10.9	10.3	10.9	11.3	11.6	11.3	9.2	6.8	5.1	4.6	4.1
92.5°	25.6	29.4	34.5	44.1	52.6	52.0	40.3	27.3	18.1	16.2	14.4
95°	54.4	68.7	89.6	117.2	134.0	118.6	79.0	49.2	33.5	29.4	25.3
97.5°	111.8	146.3	183.2	220.1	218.4	168.9	104.9	63.6	43.4	38.8	34.2
100°	222.9	269.7	312.1	319.3	270.0	186.0	112.1	70.4	52.3	47.5	42.7
102.5°	364.0	395.2	396.5	356.2	271.8	179.5	112.5	76.6	60.2	55.4	50.6
105°	458.4	453.9	415.3	344.2	253.3	170.6	114.2	83.7	67.7	62.9	58.1
107.5°	486.1	452.6	395.2	318.9	236.2	165.8	117.9	90.9	75.2	70.4	65.6
110°	472.4	428.7	367.5	295.3	224.6	164.4	122.7	98.1	83.1	78.2	73.2

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	447.8	400.3	342.2	278.9	217.1	164.8	127.8	104.9	90.6	85.4	80.3
115°	419.8	375.0	322.3	265.9	211.9	166.1	133.0	112.1	97.4	92.8	88.2
117.5°	394.8	353.1	305.9	257.1	209.2	168.2	138.4	118.6	104.9	100.2	95.4
120°	372.9	336.7	294.3	250.2	206.8	170.2	143.9	125.5	112.1	107.3	102.5
122.5°	356.9	323.0	285.1	244.4	205.4	172.6	148.7	131.9	119.6	114.6	109.7
125°	341.5	311.4	276.2	238.9	203.7	175.0	153.8	138.4	126.1	121.4	116.6
127.5°	328.5	299.8	267.3	233.8	202.7	177.4	158.6	144.6	132.6	127.6	122.7
130°	315.2	288.2	258.8	228.7	202.0	180.1	163.1	150.1	138.1	133.3	128.5
132.5°	301.5	277.2	250.6	224.6	201.7	182.9	167.5	154.8	143.6	138.8	134.0
135°	288.2	265.6	243.0	220.8	201.3	184.9	171.3	159.3	148.4	143.6	138.8
137.5°	274.8	256.4	236.9	218.1	201.3	187.0	174.3	163.1	152.1	147.6	143.2
140°	263.2	247.5	231.1	215.7	201.0	188.3	176.7	166.1	155.9	151.4	147.0
142.5°	252.6	239.6	226.3	213.3	201.0	189.4	178.8	168.5	158.6	154.5	150.4
145°	243.7	233.1	221.8	211.2	200.3	190.1	180.5	170.9	161.7	158.0	154.2
147.5°	236.2	227.7	218.4	209.2	199.3	190.4	181.5	173.0	164.1	160.6	157.2
150°	229.4	222.2	214.7	206.5	198.3	190.1	182.2	174.3	166.5	163.4	160.3
152.5°	223.6	217.7	210.9	204.1	196.6	189.4	182.5	175.7	168.9	166.2	163.4
155°	218.1	213.0	207.5	201.0	194.5	188.7	182.9	177.1	171.3	168.7	166.1
157.5°	212.6	208.2	203.4	198.3	192.4	187.3	182.9	178.1	173.0	170.8	168.5
160°	207.1	203.4	199.6	195.2	190.4	186.3	182.9	178.8	174.7	172.8	170.9
162.5°	202.0	198.9	195.9	192.4	188.7	185.3	182.5	179.1	175.7	174.4	173.0
165°	196.9	194.5	192.1	189.4	186.3	183.9	181.9	179.5	176.4	175.4	174.3
167.5°	192.1	190.4	188.3	186.3	184.2	182.5	181.5	179.5	177.1	176.4	175.7
170°	188.0	186.6	185.6	183.9	182.5	181.5	180.8	179.1	177.4	176.9	176.4
172.5°	184.2	183.2	182.5	181.5	180.5	180.1	179.8	178.8	177.8	177.4	177.1
175°	181.2	180.8	180.5	179.5	179.1	178.8	179.1	178.4	177.8	177.6	177.4
177.5°	179.1	178.8	178.8	178.1	177.8	178.1	178.8	178.1	177.8	177.8	177.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	930.5	930.5	930.5	930.5
2.5°	913.3	913.3	924.1	935.5
5°	893.3	898.3	915.5	931.2
7.5°	874.0	882.6	904.1	924.1
10°	850.4	861.9	888.3	911.9
12.5°	827.5	838.3	869.0	895.5
15°	795.3	808.9	841.8	874.7
17.5°	763.2	776.7	816.8	855.4
20°	725.2	743.1	788.2	839.7
22.5°	690.2	712.4	762.4	803.9
25°	651.6	685.9	732.4	786.0
27.5°	617.2	651.6	698.8	753.1
30°	578.6	613.7	662.3	712.4
32.5°	541.4	573.6	620.8	682.3
35°	502.8	533.6	579.3	641.6
37.5°	467.8	497.8	547.9	605.1
40°	433.4	464.9	507.8	565.0
42.5°	401.2	429.1	467.8	525.0
45°	371.9	391.9	427.7	481.4
47.5°	341.2	359.0	391.9	445.6
50°	312.6	327.6	356.2	406.3
52.5°	284.7	297.5	324.0	364.1
55°	259.6	271.8	291.1	330.4
57.5°	233.9	243.2	261.8	293.2
60°	208.8	217.4	232.4	258.2
62.5°	183.8	191.0	205.3	226.0
65°	161.6	167.4	178.1	196.0
67.5°	140.2	143.8	152.3	166.6
70°	119.4	122.3	129.5	140.9
72.5°	97.3	100.1	108.0	115.9
75°	78.7	79.4	85.1	91.5
77.5°	61.5	60.8	65.1	70.1
80°	42.2	44.3	47.9	50.1
82.5°	28.6	29.3	30.8	32.2
85°	15.7	16.5	16.5	18.6
87.5°	6.4	7.2	7.2	7.9
90°	3.4	2.7	1.4	0.3
92.5°	11.6	9.9	7.2	5.1
95°	19.8	16.7	13.3	12.0
97.5°	28.0	23.6	19.8	17.8
100°	35.9	30.4	27.3	26.3
102.5°	43.4	37.9	34.9	34.2
105°	50.6	45.5	43.1	41.7
107.5°	58.1	53.3	50.9	49.9
110°	66.0	61.5	59.5	58.1

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	73.5	69.4	67.0	65.6
115°	81.4	77.3	75.2	73.5
117.5°	88.9	85.1	83.1	81.7
120°	95.7	92.6	90.6	89.2
122.5°	102.9	99.5	97.4	96.4
125°	109.7	105.6	103.6	102.5
127.5°	116.2	111.8	109.0	107.7
130°	121.7	116.9	113.5	112.1
132.5°	126.8	121.7	117.9	116.2
135°	130.9	125.8	121.7	120.3
137.5°	135.4	129.9	125.8	124.1
140°	139.5	134.0	129.9	128.5
142.5°	143.2	137.8	134.0	133.0
145°	147.3	142.2	138.8	137.4
147.5°	151.4	146.6	143.2	142.2
150°	155.2	150.7	148.0	147.0
152.5°	158.6	154.8	152.1	151.8
155°	162.4	158.6	156.6	156.2
157.5°	165.4	162.0	160.3	160.0
160°	168.2	165.4	164.1	163.7
162.5°	170.6	168.5	167.2	167.5
165°	172.6	170.6	169.9	170.2
167.5°	174.3	173.0	172.3	172.6
170°	175.7	174.7	174.3	175.0
172.5°	176.7	175.7	176.0	176.4
175°	177.4	176.7	177.1	177.4
177.5°	177.8	177.1	177.4	178.1
180°	177.8	177.8	177.8	177.8

TEST NUMBER: P998488

CATALOG NUMBER: SA2XXDIP-B485D330UB50-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.27	17.21	17.13	18.08	19.17	13.77	14.71	14.62	15.57	16.66
	3H	17.09	17.93	17.96	18.81	19.92	15.12	15.96	15.98	16.84	17.95
	4H	17.26	18.06	18.14	18.94	20.06	15.58	16.38	16.46	17.26	18.38
	6H	17.31	18.04	18.21	18.93	20.07	15.90	16.63	16.79	17.52	18.65
	8H	17.30	17.99	18.19	18.90	20.03	15.98	16.68	16.88	17.58	18.72
	12H	17.26	17.92	18.16	18.82	19.98	16.03	16.69	16.93	17.59	18.75
4H	2H	16.33	17.12	17.21	18.00	19.13	14.22	15.02	15.11	15.90	17.02
	3H	17.31	17.97	18.21	18.89	20.03	15.69	16.35	16.59	17.27	18.40
	4H	17.59	18.19	18.50	19.10	20.27	16.23	16.83	17.14	17.74	18.90
	6H	17.73	18.24	18.65	19.18	20.35	16.61	17.13	17.53	18.06	19.23
	8H	17.73	18.21	18.65	19.14	20.32	16.72	17.21	17.65	18.14	19.32
	12H	17.70	18.13	18.64	19.08	20.26	16.79	17.22	17.73	18.17	19.35
8H	4H	17.61	18.09	18.53	19.02	20.20	16.38	16.86	17.30	17.79	18.97
	6H	17.79	18.19	18.74	19.16	20.34	16.81	17.21	17.76	18.18	19.36
	8H	17.82	18.17	18.78	19.13	20.33	16.97	17.32	17.92	18.28	19.48
	12H	17.81	18.12	18.77	19.07	20.32	17.06	17.37	18.02	18.33	19.57
12H	4H	17.57	18.00	18.51	18.95	20.13	16.35	16.79	17.30	17.74	18.92
	6H	17.77	18.12	18.73	19.08	20.28	16.81	17.17	17.77	18.13	19.32
	8H	17.80	18.11	18.77	19.07	20.31	16.98	17.29	17.94	18.24	19.49