

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999557

Luminaire Tested: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999557
REPORT IS A COMBINATION OF REPORTS P988110 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3125.0 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999557

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P999557

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29
3	79	70	63	57	70	63	57	52	51	46	43	39	36	34	28	27	25
4	72	62	54	49	65	56	50	45	45	40	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	31	28	25	23	21	19
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	22	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14
9	49	37	30	25	44	34	27	23	28	23	19	22	18	16	16	14	12
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7736	7736	7736
5°	7748	7359	7305
10°	7672	6979	6750
15°	7566	6532	6117
20°	7427	6022	5454
25°	7284	5499	4849
30°	7092	4991	4187
35°	6903	4477	3620
40°	6713	3973	3034
45°	6491	3452	2524
50°	6261	2952	2056
55°	6022	2449	1632
60°	5744	1958	1234
65°	5425	1492	1004
70°	5037	1083	798
75°	4554	827	609
80°	3848	559	410
85°	2684	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6491 cd/sqm

TEST NUMBER: P999557

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	1.5
10°-20°	125.7	4.0
20°-30°	176.5	5.6
30°-40°	192.4	6.2
40°-50°	176.8	5.7
50°-60°	138.9	4.4
60°-70°	90.4	2.9
70°-80°	46.5	1.5
80°-90°	13.1	0.4
90°-100°	23.8	0.8
100°-110°	88.8	2.8
110°-120°	235.6	7.5
120°-130°	390.8	12.5
130°-140°	415.1	13.3
140°-150°	385.8	12.3
150°-160°	310.2	9.9
160°-170°	199.9	6.4
170°-180°	68.8	2.2
0°-30°	348.0	11.1
0°-40°	540.4	17.3
0°-60°	856.2	27.4
0°-90°	1006.3	32.2
90°-120°	348.3	11.1
90°-150°	1539.9	49.3
90°-180°	2119.0	67.8
0°-180°	3125.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	489	489	489	489	489	
5°	489	486	481	485	483	46
15°	465	460	445	436	432	131
25°	422	408	378	360	354	194
35°	364	341	302	274	264	228
45°	297	268	221	190	179	230
55°	226	192	144	117	109	202
65°	153	117	77	62	61	151
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	0	6	10	13	14	3
95°	34	17	20	23	22	40
105°	159	175	32	38	40	170
115°	301	310	323	80	43	296
125°	425	432	442	446	447	379
135°	526	534	539	544	543	406
145°	610	610	619	622	620	382
155°	672	667	674	677	672	310
165°	708	705	706	710	706	200
175°	724	721	722	725	720	69
180°	723	723	723	723	723	

TEST NUMBER: P999557

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	488.7	488.7	488.7	488.7	488.7
2.5°	490.9	488.7	483.8	488.2	487.3
5°	488.7	486.5	480.7	484.7	483.4
7.5°	484.7	482.0	475.8	477.6	475.4
10°	479.4	476.3	467.4	466.1	463.5
12.5°	472.7	468.8	456.8	454.2	449.3
15°	464.8	459.9	444.9	436.5	432.1
17.5°	455.5	448.4	429.8	420.1	413.0
20°	444.9	436.0	413.9	402.9	393.1
22.5°	433.4	423.2	397.6	382.5	375.9
25°	421.9	407.7	378.5	360.4	353.8
27.5°	408.2	393.1	360.9	340.1	329.9
30°	393.6	376.8	341.4	318.8	306.9
32.5°	379.4	359.1	322.8	296.3	285.2
35°	363.5	341.0	302.0	274.2	264.5
37.5°	348.0	323.7	282.6	252.1	241.0
40°	331.7	305.1	262.2	230.8	219.3
42.5°	314.9	286.6	241.9	209.2	198.1
45°	297.2	267.5	221.1	189.7	179.1
47.5°	280.4	249.0	201.2	169.8	160.1
50°	261.8	230.4	181.8	151.2	142.0
52.5°	243.7	210.5	163.2	134.0	125.6
55°	226.0	191.5	143.7	117.2	108.8
57.5°	207.8	172.5	126.5	101.7	94.6
60°	189.3	153.9	108.3	85.8	78.7
62.5°	171.1	135.8	92.9	71.6	68.1
65°	152.6	116.7	76.9	61.9	60.6
67.5°	134.9	99.1	61.9	54.4	53.1
70°	116.3	81.8	51.3	46.9	45.1
72.5°	98.6	65.9	42.9	39.4	38.5
75°	81.4	50.4	35.4	32.3	31.8
77.5°	64.1	35.8	27.9	26.1	25.2
80°	48.2	25.6	21.2	19.5	19.5
82.5°	33.6	17.2	14.6	13.7	13.7
85°	19.0	9.7	8.4	8.4	8.4
87.5°	7.1	3.5	3.5	3.1	3.1
90°	0.5	6.3	10.5	13.1	14.1
92.5°	13.1	11.0	12.6	13.6	14.1
95°	34.0	16.7	20.4	23.0	22.5
97.5°	61.2	18.3	26.7	28.2	28.8
100°	92.6	20.9	29.8	34.0	35.0
102.5°	127.1	126.0	30.9	36.6	38.2
105°	159.0	174.7	31.9	37.7	39.7
107.5°	196.1	209.2	32.9	38.7	40.8
110°	231.7	242.6	91.5	39.2	41.3



TEST NUMBER: P999557

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	265.1	274.5	265.7	40.3	41.8
115°	300.7	309.6	322.7	80.5	42.9
117.5°	331.5	342.0	350.9	276.1	139.1
120°	366.1	373.9	383.3	389.6	319.0
122.5°	395.3	403.7	414.2	417.3	417.8
125°	425.2	432.0	441.9	445.5	447.1
127.5°	452.3	459.7	467.5	472.7	473.3
130°	478.0	486.3	492.1	497.8	497.3
132.5°	504.1	510.9	516.7	521.4	520.9
135°	526.1	534.4	539.2	544.4	543.3
137.5°	549.1	555.4	560.6	565.8	564.3
140°	571.6	575.8	581.5	586.2	583.6
142.5°	590.4	594.1	600.9	605.0	602.4
145°	610.3	609.8	618.6	622.3	619.7
147.5°	627.5	626.0	634.9	637.5	635.4
150°	644.3	640.6	649.0	652.1	649.5
152.5°	658.4	654.2	662.0	665.2	661.5
155°	672.0	667.3	673.6	676.7	672.5
157.5°	683.0	678.8	683.5	687.1	683.0
160°	692.4	689.2	692.4	695.5	691.9
162.5°	700.7	697.6	700.2	703.9	699.2
165°	708.1	704.9	706.5	710.2	706.5
167.5°	713.8	710.7	712.2	715.9	711.2
170°	718.5	715.4	716.4	720.1	715.4
172.5°	721.7	718.5	719.6	723.2	718.5
175°	724.3	720.6	721.7	725.3	720.1
177.5°	725.3	721.7	722.2	725.8	721.1
180°	722.7	722.7	722.7	722.7	722.7

(END OF REPORT)