

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999560

Luminaire Tested: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999560
REPORT IS A COMBINATION OF REPORTS P988113 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3004.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999560

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P999560

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29
3	79	70	63	57	70	63	57	52	51	46	43	39	36	34	28	27	25
4	72	62	54	48	65	56	50	45	45	40	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	31	28	25	23	21	19
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	22	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14
9	49	37	30	25	44	34	27	23	28	23	19	22	18	16	16	14	12
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7435	7435	7435
5°	7447	7073	7021
10°	7374	6709	6488
15°	7272	6278	5879
20°	7138	5789	5243
25°	7001	5287	4661
30°	6816	4798	4025
35°	6636	4303	3479
40°	6452	3820	2916
45°	6238	3318	2427
50°	6017	2836	1975
55°	5788	2354	1569
60°	5520	1882	1187
65°	5212	1436	964
70°	4842	1041	768
75°	4375	794	586
80°	3696	538	393
85°	2585	247	190

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6238 cd/sqm

TEST NUMBER: P999560

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.5
10°-20°	120.8	4.0
20°-30°	169.7	5.6
30°-40°	184.9	6.2
40°-50°	170.0	5.7
50°-60°	133.5	4.4
60°-70°	86.9	2.9
70°-80°	44.7	1.5
80°-90°	12.7	0.4
90°-100°	22.9	0.8
100°-110°	85.4	2.8
110°-120°	226.5	7.5
120°-130°	375.7	12.5
130°-140°	399.0	13.3
140°-150°	370.9	12.3
150°-160°	298.2	9.9
160°-170°	192.1	6.4
170°-180°	66.1	2.2
0°-30°	334.5	11.1
0°-40°	519.5	17.3
0°-60°	823.0	27.4
0°-90°	967.2	32.2
90°-120°	334.8	11.1
90°-150°	1480.4	49.3
90°-180°	2037.0	67.8
0°-180°	3004.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	470	470	470	470	470	
5°	470	468	462	466	465	45
15°	447	442	428	420	415	126
25°	406	392	364	346	340	186
35°	349	328	290	264	254	219
45°	286	257	212	182	172	221
55°	217	184	138	113	105	194
65°	147	112	74	60	58	145
75°	78	48	34	31	31	83
85°	18	9	8	8	8	21
90°	0	6	10	13	14	3
95°	33	16	20	22	22	39
105°	153	168	31	36	38	163
115°	289	298	310	77	41	285
125°	409	415	425	428	430	365
135°	506	514	518	523	522	391
145°	587	586	595	598	596	367
155°	646	642	648	650	646	298
165°	681	678	679	683	679	192
175°	696	693	694	697	692	66
180°	695	695	695	695	695	

TEST NUMBER: P999560

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	469.7	469.7	469.7	469.7	469.7
2.5°	471.8	469.7	465.0	469.3	468.4
5°	469.7	467.6	462.0	465.9	464.6
7.5°	465.9	463.3	457.4	459.1	456.9
10°	460.8	457.8	449.3	448.0	445.5
12.5°	454.4	450.6	439.1	436.5	431.9
15°	446.7	442.1	427.6	419.5	415.3
17.5°	437.8	431.0	413.2	403.8	397.0
20°	427.6	419.1	397.9	387.2	377.9
22.5°	416.6	406.8	382.1	367.7	361.3
25°	405.5	391.9	363.9	346.4	340.1
27.5°	392.3	377.9	346.9	326.9	317.1
30°	378.3	362.2	328.2	306.5	295.0
32.5°	364.7	345.2	310.3	284.8	274.2
35°	349.4	327.7	290.3	263.5	254.2
37.5°	334.5	311.2	271.6	242.3	231.7
40°	318.8	293.3	252.1	221.9	210.8
42.5°	302.6	275.4	232.5	201.1	190.4
45°	285.6	257.2	212.5	182.4	172.2
47.5°	269.5	239.3	193.4	163.2	153.9
50°	251.6	221.5	174.7	145.4	136.4
52.5°	234.2	202.3	156.9	128.8	120.7
55°	217.2	184.1	138.1	112.6	104.6
57.5°	199.8	165.8	121.6	97.8	91.0
60°	181.9	147.9	104.1	82.5	75.7
62.5°	164.5	130.5	89.3	68.9	65.5
65°	146.6	112.2	74.0	59.5	58.2
67.5°	129.6	95.2	59.5	52.3	51.0
70°	111.8	78.6	49.3	45.1	43.4
72.5°	94.8	63.3	41.2	37.8	37.0
75°	78.2	48.5	34.0	31.0	30.6
77.5°	61.6	34.4	26.8	25.1	24.2
80°	46.3	24.7	20.4	18.7	18.7
82.5°	32.3	16.6	14.0	13.2	13.2
85°	18.3	9.4	8.1	8.1	8.1
87.5°	6.8	3.4	3.4	3.0	3.0
90°	0.5	6.0	10.1	12.6	13.6
92.5°	12.6	10.6	12.1	13.1	13.6
95°	32.7	16.1	19.6	22.1	21.6
97.5°	58.8	17.6	25.6	27.1	27.6
100°	89.0	20.1	28.7	32.7	33.7
102.5°	122.2	121.2	29.7	35.2	36.7
105°	152.8	167.9	30.7	36.2	38.2
107.5°	188.5	201.1	31.7	37.2	39.2
110°	222.7	233.3	88.0	37.7	39.7

TEST NUMBER: P999560

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	254.9	263.9	255.4	38.7	40.2
115°	289.1	297.6	310.2	77.4	41.2
117.5°	318.7	328.8	337.3	265.4	133.7
120°	351.9	359.4	368.5	374.5	306.7
122.5°	380.1	388.1	398.2	401.2	401.7
125°	408.7	415.2	424.8	428.3	429.8
127.5°	434.9	441.9	449.4	454.5	455.0
130°	459.5	467.5	473.1	478.6	478.1
132.5°	484.6	491.2	496.7	501.2	500.7
135°	505.7	513.8	518.3	523.3	522.3
137.5°	527.9	533.9	538.9	543.9	542.4
140°	549.5	553.5	559.0	563.5	561.0
142.5°	567.6	571.1	577.6	581.6	579.1
145°	586.7	586.2	594.7	598.2	595.7
147.5°	603.3	601.8	610.3	612.8	610.8
150°	619.3	615.8	623.9	626.9	624.4
152.5°	632.9	628.9	636.4	639.5	635.9
155°	646.0	641.5	647.5	650.5	646.5
157.5°	656.5	652.5	657.1	660.6	656.5
160°	665.6	662.6	665.6	668.6	665.1
162.5°	673.6	670.6	673.1	676.7	672.1
165°	680.7	677.7	679.2	682.7	679.2
167.5°	686.2	683.2	684.7	688.2	683.7
170°	690.7	687.7	688.7	692.2	687.7
172.5°	693.7	690.7	691.7	695.3	690.7
175°	696.3	692.7	693.7	697.3	692.2
177.5°	697.3	693.7	694.3	697.8	693.2
180°	694.8	694.8	694.8	694.8	694.8

(END OF REPORT)