

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999677

Luminaire Tested: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999677
REPORT IS A COMBINATION OF REPORTS P988230 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5997.0 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999677

CATALOG NUMBER: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P999677

CATALOG NUMBER: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	38	29	28	26
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23
4	71	61	53	48	63	55	49	44	44	39	35	33	30	28	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	15
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13007	13007	13007
5°	13028	12374	12283
10°	12900	11736	11349
15°	12723	10983	10285
20°	12488	10128	9173
25°	12247	9249	8154
30°	11924	8392	7042
35°	11610	7529	6086
40°	11287	6682	5104
45°	10913	5806	4245
50°	10527	4962	3456
55°	10126	4119	2743
60°	9659	3294	2076
65°	9122	2511	1688
70°	8471	1823	1343
75°	7653	1390	1024
80°	6475	941	687
85°	4520	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10913 cd/sqm

TEST NUMBER: P999677

CATALOG NUMBER: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	1.3
10°-20°	211.4	3.5
20°-30°	296.8	4.9
30°-40°	323.6	5.4
40°-50°	297.4	5.0
50°-60°	233.5	3.9
60°-70°	152.0	2.5
70°-80°	78.3	1.3
80°-90°	22.6	0.4
90°-100°	48.4	0.8
100°-110°	180.5	3.0
110°-120°	478.7	8.0
120°-130°	793.9	13.2
130°-140°	843.3	14.1
140°-150°	783.8	13.1
150°-160°	630.1	10.5
160°-170°	406.0	6.8
170°-180°	139.7	2.3
0°-30°	585.3	9.8
0°-40°	908.8	15.2
0°-60°	1439.7	24.0
0°-90°	1692.6	28.2
90°-120°	707.6	11.8
90°-150°	3128.5	52.2
90°-180°	4304.0	71.8
0°-180°	5997.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	822	822	822	822	822	
5°	822	818	808	815	813	78
15°	782	773	748	734	726	220
25°	709	686	637	606	595	326
35°	611	573	508	461	445	383
45°	500	450	372	319	301	386
55°	380	322	242	197	183	340
65°	257	196	129	104	102	254
75°	137	85	60	54	54	145
85°	32	16	14	14	14	37
90°	1	13	21	27	29	6
95°	69	34	41	47	46	82
105°	323	355	65	76	81	345
115°	611	629	656	164	87	601
125°	864	878	898	905	908	770
135°	1069	1086	1095	1106	1104	826
145°	1240	1239	1257	1264	1259	775
155°	1365	1356	1368	1375	1366	629
165°	1438	1432	1435	1443	1435	406
175°	1471	1464	1466	1474	1463	140
180°	1468	1468	1468	1468	1468	

TEST NUMBER: P999677

CATALOG NUMBER: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	821.7	821.7	821.7	821.7	821.7
2.5°	825.5	821.7	813.6	821.0	819.5
5°	821.7	818.0	808.3	815.0	812.8
7.5°	815.0	810.6	800.2	803.1	799.4
10°	806.1	800.9	786.0	783.8	779.3
12.5°	795.0	788.3	768.2	763.7	755.5
15°	781.6	773.4	748.1	734.0	726.5
17.5°	766.0	754.1	722.8	706.5	694.6
20°	748.1	733.2	696.1	677.5	661.1
22.5°	728.8	711.7	668.5	643.3	632.1
25°	709.4	685.6	636.6	606.1	594.9
27.5°	686.4	661.1	606.8	571.9	554.8
30°	661.8	633.6	574.1	536.2	516.1
32.5°	638.1	603.8	542.9	498.2	479.7
35°	611.3	573.4	507.9	461.1	444.7
37.5°	585.3	544.4	475.2	423.9	405.3
40°	557.7	513.1	441.0	388.2	368.9
42.5°	529.5	481.9	406.8	351.7	333.2
45°	499.7	449.9	371.8	319.0	301.2
47.5°	471.5	418.7	338.4	285.6	269.2
50°	440.2	387.4	305.6	254.3	238.7
52.5°	409.8	354.0	274.4	225.3	211.2
55°	380.0	322.0	241.7	197.1	182.9
57.5°	349.5	290.0	212.7	171.0	159.1
60°	318.3	258.8	182.2	144.3	132.4
62.5°	287.8	228.3	156.2	120.5	114.5
65°	256.6	196.3	129.4	104.1	101.9
67.5°	226.8	166.6	104.1	91.5	89.2
70°	195.6	137.6	86.3	78.8	75.9
72.5°	165.8	110.8	72.1	66.2	64.7
75°	136.8	84.8	59.5	54.3	53.5
77.5°	107.8	60.2	46.8	43.9	42.4
80°	81.1	43.1	35.7	32.7	32.7
82.5°	56.5	29.0	24.5	23.1	23.1
85°	32.0	16.4	14.1	14.1	14.1
87.5°	11.9	5.9	5.9	5.2	5.2
90°	1.1	12.7	21.2	26.6	28.7
92.5°	26.6	22.3	25.5	27.6	28.7
95°	69.1	34.0	41.4	46.7	45.7
97.5°	124.3	37.2	54.2	57.4	58.4
100°	188.0	42.5	60.6	69.1	71.2
102.5°	258.2	256.0	62.7	74.4	77.6
105°	323.0	354.8	64.8	76.5	80.7
107.5°	398.4	425.0	66.9	78.6	82.9
110°	470.6	493.0	185.9	79.7	83.9

TEST NUMBER: P999677

CATALOG NUMBER: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	538.6	557.8	539.7	81.8	85.0
115°	610.9	628.9	655.5	163.6	87.1
117.5°	673.6	694.8	712.9	561.0	282.6
120°	743.7	759.6	778.8	791.5	648.1
122.5°	803.2	820.2	841.4	847.8	848.9
125°	863.7	877.6	897.7	905.2	908.4
127.5°	919.0	933.9	949.8	960.4	961.5
130°	971.0	988.0	999.7	1011.4	1010.4
132.5°	1024.2	1038.0	1049.7	1059.2	1058.2
135°	1068.8	1085.8	1095.3	1106.0	1103.8
137.5°	1115.5	1128.3	1138.9	1149.5	1146.3
140°	1161.2	1169.7	1181.4	1191.0	1185.7
142.5°	1199.5	1206.9	1220.7	1229.2	1223.9
145°	1239.8	1238.8	1256.8	1264.3	1259.0
147.5°	1274.9	1271.7	1289.8	1295.1	1290.8
150°	1308.9	1301.5	1318.5	1324.8	1319.5
152.5°	1337.6	1329.1	1345.0	1351.4	1344.0
155°	1365.2	1355.6	1368.4	1374.8	1366.3
157.5°	1387.5	1379.0	1388.6	1396.0	1387.5
160°	1406.6	1400.3	1406.6	1413.0	1405.6
162.5°	1423.6	1417.3	1422.6	1430.0	1420.4
165°	1438.5	1432.1	1435.3	1442.8	1435.3
167.5°	1450.2	1443.8	1447.0	1454.4	1444.9
170°	1459.8	1453.4	1455.5	1462.9	1453.4
172.5°	1466.1	1459.8	1461.9	1469.3	1459.8
175°	1471.4	1464.0	1466.1	1473.6	1462.9
177.5°	1473.6	1466.1	1467.2	1474.6	1465.1
180°	1468.3	1468.3	1468.3	1468.3	1468.3

(END OF REPORT)