

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998547

Luminaire Tested: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998547
REPORT IS A COMBINATION OF REPORTS P984290 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3875.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51
2	91	83	77	73	84	78	72	68	67	63	60	56	54	51	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29
6	65	53	45	39	60	50	43	37	43	38	33	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19
10	49	37	30	25	45	35	28	24	31	25	22	27	22	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14729	14729	14729	14729
5°	14764	15704	14821	12495
10°	14593	17145	14684	10302
15°	14239	18083	14438	8678
20°	14017	16980	14017	7542
25°	13570	14587	13632	6745
30°	12836	11467	13081	6109
35°	12185	7929	12388	5590
40°	11435	5986	11567	5176
45°	10514	4919	10684	4727
50°	9716	4319	9733	4329
55°	8804	3679	8863	3893
60°	7835	3074	7944	3398
65°	6968	2499	7092	2902
70°	6102	1962	6258	2340
75°	5119	1424	5320	1698
80°	4000	902	4279	1007
85°	2627	454	2825	336

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15226 cd/sqm

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.6	2.3
10°-20°	258.0	6.7
20°-30°	374.4	9.7
30°-40°	394.7	10.2
40°-50°	349.2	9.0
50°-60°	278.9	7.2
60°-70°	189.4	4.9
70°-80°	96.9	2.5
80°-90°	24.7	0.6
90°-100°	40.3	1.0
100°-110°	128.0	3.3
110°-120°	219.1	5.7
120°-130°	288.1	7.4
130°-140°	323.4	8.3
140°-150°	317.1	8.2
150°-160°	266.0	6.9
160°-170°	176.4	4.6
170°-180°	61.7	1.6
0°-30°	721.0	18.6
0°-40°	1115.7	28.8
0°-60°	1743.8	45.0
0°-90°	2054.8	53.0
90°-120°	387.4	10.0
90°-150°	1316.0	34.0
90°-180°	1820.0	47.0
0°-180°	3875.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	931	1039	935	827	931	88
15°	875	1277	887	613	875	247
25°	786	1064	790	492	786	359
35°	642	579	652	408	642	401
45°	481	349	489	335	481	373
55°	330	245	333	260	330	295
65°	196	151	200	175	196	195
75°	92	74	95	89	92	98
85°	19	19	20	14	19	22
90°	0	19	0	19	0	3
95°	29	34	29	34	29	32
105°	118	122	118	122	118	125
115°	220	220	220	220	220	217
125°	320	321	320	321	320	286
135°	414	419	414	419	414	320
145°	502	508	502	508	502	314
155°	574	578	574	578	574	264
165°	625	625	625	625	625	176
175°	650	648	650	648	650	62
180°	651	651	651	651	651	

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	935.5	937.7	941.2	942.0	949.1	954.8	961.3	961.3	963.4	962.7	957.0
5°	931.2	937.7	947.0	954.8	967.7	973.4	982.0	988.4	994.2	998.5	997.7
7.5°	924.1	935.5	949.1	964.1	981.3	991.3	1003.5	1014.9	1022.8	1029.9	1034.9
10°	911.9	931.2	949.8	969.9	992.0	1005.6	1019.9	1034.9	1047.1	1060.7	1073.6
12.5°	895.5	923.4	946.3	972.7	999.9	1014.9	1037.8	1049.2	1072.8	1107.2	1116.5
15°	874.7	912.6	934.1	967.7	1003.5	1015.6	1047.1	1065.7	1114.3	1135.8	1161.5
17.5°	855.4	897.6	926.2	964.8	999.9	1023.5	1054.3	1092.2	1132.9	1163.7	1192.3
20°	839.7	880.4	914.8	957.7	1002.0	1032.1	1064.3	1110.0	1154.4	1185.9	1208.0
22.5°	803.9	856.1	896.2	944.1	997.7	1039.2	1070.0	1120.1	1168.0	1187.3	1206.6
25°	786.0	831.1	877.6	931.9	994.9	1044.2	1070.7	1126.5	1168.7	1175.8	1180.1
27.5°	753.1	803.9	858.3	920.5	994.2	1035.7	1069.3	1120.1	1153.7	1148.7	1135.8
30°	712.4	774.6	834.7	901.9	984.2	1029.2	1060.7	1107.2	1124.3	1098.6	1075.7
32.5°	682.3	741.0	807.5	885.5	972.7	1015.6	1046.4	1082.9	1086.4	1039.9	1001.3
35°	641.6	706.6	781.7	864.0	953.4	992.0	1020.6	1042.8	1025.6	960.6	914.8
37.5°	605.1	669.5	749.6	833.2	926.9	964.8	987.7	991.3	949.1	891.9	824.7
40°	565.0	631.5	715.2	803.2	897.6	930.5	944.8	934.1	873.3	806.8	728.8
42.5°	525.0	590.8	680.9	771.0	860.4	888.3	894.0	864.7	790.3	712.4	622.3
45°	481.4	550.0	640.1	731.0	817.5	833.2	834.0	791.8	703.8	622.3	538.6
47.5°	445.6	509.2	598.6	689.5	762.4	773.2	768.9	720.2	624.4	532.8	459.9
50°	406.3	467.0	555.7	645.1	707.4	710.2	699.5	630.1	536.4	452.7	394.8
52.5°	364.1	425.6	507.1	592.9	648.7	644.4	623.7	549.3	461.3	391.9	347.6
55°	330.4	384.8	461.3	545.0	584.3	572.2	549.3	473.5	404.1	345.5	306.8
57.5°	293.2	341.2	416.3	489.2	512.1	500.7	477.8	407.0	342.6	298.3	272.5
60°	258.2	301.8	367.6	428.4	446.3	434.1	407.7	344.0	297.5	260.3	241.0
62.5°	226.0	263.9	319.0	374.8	381.9	369.8	346.9	295.4	255.3	226.0	211.7
65°	196.0	231.7	276.1	318.3	324.7	311.8	288.2	251.0	217.4	198.8	185.2
67.5°	166.6	195.3	234.6	265.4	268.9	256.8	237.5	207.4	186.7	166.6	156.6
70°	140.9	162.4	193.1	218.1	219.6	208.1	198.1	170.9	155.2	140.9	133.0
72.5°	115.9	130.9	154.5	173.1	173.8	166.6	157.4	140.2	126.6	116.6	108.7
75°	91.5	104.4	118.7	135.2	134.5	128.7	121.6	110.9	99.4	93.0	89.4
77.5°	70.1	78.0	89.4	100.1	100.1	97.3	93.0	85.1	78.0	71.5	67.9
80°	50.1	55.1	64.4	67.9	69.4	68.7	65.1	59.4	56.5	51.5	50.1
82.5°	32.2	35.8	40.1	43.6	45.8	44.3	43.6	40.8	36.5	35.0	33.6
85°	18.6	20.0	22.2	24.3	25.0	24.3	25.7	23.6	21.5	21.5	20.7
87.5°	7.9	8.6	10.0	10.0	10.7	10.7	10.0	10.7	10.7	10.0	9.3
90°	0.5	2.0	3.4	4.9	6.4	7.1	8.4	11.1	13.8	16.5	19.2
92.5°	12.1	13.1	14.1	15.0	16.0	16.5	16.6	16.7	16.8	16.9	17.0
95°	28.6	29.8	31.0	32.3	33.5	34.1	34.2	34.5	34.7	35.0	35.2
97.5°	47.8	48.9	50.0	51.1	52.2	52.7	52.9	53.4	53.9	54.4	54.9
100°	69.8	70.8	71.8	72.7	73.7	74.2	74.4	74.7	75.1	75.4	75.8
102.5°	92.8	93.5	94.3	95.0	95.7	96.1	96.3	96.8	97.3	97.8	98.3
105°	118.1	118.5	118.9	119.2	119.6	119.8	119.9	120.2	120.4	120.7	120.9
107.5°	143.4	143.9	144.4	144.9	145.4	145.6	145.6	145.6	145.6	145.6	145.6
110°	167.6	168.3	169.1	169.8	170.5	170.9	170.9	170.9	170.9	170.9	170.9

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	193.9	194.6	195.4	196.1	196.8	197.2	197.1	197.0	196.9	196.8	196.7
115°	219.8	220.5	221.3	222.0	222.7	223.1	223.0	222.7	222.5	222.2	222.0
117.5°	245.6	246.6	247.6	248.5	249.5	250.0	249.7	249.1	248.4	247.8	247.2
120°	271.4	272.4	273.4	274.3	275.3	275.8	275.3	274.3	273.4	272.4	271.4
122.5°	295.0	296.2	297.4	298.7	299.9	300.5	300.2	299.6	299.0	298.4	297.8
125°	319.7	320.8	321.9	323.0	324.1	324.7	324.5	324.1	323.8	323.4	323.0
127.5°	343.9	345.3	346.6	348.0	349.3	350.0	349.8	349.3	348.8	348.3	347.8
130°	366.4	368.0	369.6	371.2	372.8	373.6	373.5	373.2	373.0	372.7	372.5
132.5°	391.7	392.9	394.1	395.4	396.6	397.2	397.3	397.4	397.5	397.7	397.8
135°	413.7	415.0	416.4	417.7	419.0	419.7	419.8	420.1	420.3	420.6	420.8
137.5°	437.9	439.0	440.1	441.2	442.3	442.8	442.9	443.2	443.4	443.7	443.9
140°	459.3	460.4	461.5	462.6	463.7	464.2	464.5	465.1	465.8	466.4	467.0
142.5°	481.3	482.4	483.5	484.6	485.7	486.2	486.4	486.8	487.1	487.5	487.9
145°	502.1	503.0	503.8	504.7	505.6	506.0	506.4	507.1	507.8	508.6	509.3
147.5°	520.8	521.9	523.0	524.1	525.2	525.8	526.0	526.5	527.0	527.5	528.0
150°	540.1	540.8	541.5	542.2	542.9	543.3	543.5	544.0	544.5	545.0	545.5
152.5°	557.1	557.8	558.6	559.3	560.0	560.4	560.7	561.3	561.9	562.5	563.1
155°	574.1	574.5	574.9	575.2	575.6	575.8	576.0	576.3	576.7	577.0	577.4
157.5°	588.9	589.1	589.4	589.6	589.9	590.0	590.1	590.4	590.6	590.9	591.1
160°	602.1	602.3	602.6	602.8	603.1	603.2	603.3	603.4	603.5	603.7	603.8
162.5°	614.2	614.2	614.2	614.2	614.2	614.2	614.3	614.4	614.5	614.7	614.8
165°	624.7	624.6	624.4	624.3	624.2	624.1	624.1	624.1	624.1	624.1	624.1
167.5°	634.0	633.6	633.2	632.9	632.5	632.3	632.3	632.3	632.3	632.3	632.3
170°	641.1	640.7	640.4	640.0	639.7	639.5	639.4	639.3	639.2	639.0	638.9
172.5°	646.1	645.7	645.3	645.0	644.6	644.4	644.3	644.2	644.1	644.0	643.9
175°	649.9	649.5	649.2	648.8	648.5	648.3	648.2	647.9	647.7	647.4	647.2
177.5°	652.1	651.7	651.4	651.0	650.7	650.5	650.4	650.1	649.9	649.6	649.4
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	967.0	967.7	969.1	976.3	979.9	980.6	977.7	984.2	986.3	984.2	982.7
5°	1012.8	1017.1	1025.6	1034.9	1034.2	1034.9	1039.2	1043.5	1045.0	1039.2	1041.4
7.5°	1052.8	1061.4	1070.7	1085.0	1085.0	1092.2	1095.0	1098.6	1107.2	1102.9	1101.5
10°	1098.6	1110.0	1127.2	1150.1	1150.8	1158.0	1165.1	1176.6	1180.1	1177.3	1178.7
12.5°	1155.8	1178.0	1179.4	1204.4	1215.9	1217.3	1228.8	1226.6	1233.8	1233.8	1245.9
15°	1180.8	1215.2	1234.5	1258.8	1266.0	1257.4	1266.7	1276.7	1277.4	1277.4	1276.7
17.5°	1225.9	1239.5	1258.8	1271.7	1274.5	1274.5	1275.3	1279.5	1276.7	1271.0	1275.3
20°	1235.2	1240.9	1248.1	1246.6	1248.1	1240.9	1233.8	1226.6	1227.3	1223.8	1234.5
22.5°	1218.0	1216.6	1200.2	1189.4	1189.4	1175.1	1161.5	1155.1	1148.7	1150.8	1154.4
25°	1175.1	1153.0	1132.9	1117.2	1113.6	1090.7	1072.1	1066.4	1055.7	1064.3	1065.7
27.5°	1106.5	1081.4	1049.2	1035.7	1017.1	1007.8	994.9	977.7	955.5	968.4	966.3
30°	1032.8	995.6	969.1	936.2	906.9	904.8	880.4	851.8	840.4	840.4	846.8
32.5°	950.5	901.2	862.6	816.1	787.5	775.3	746.0	717.4	723.8	702.4	710.2
35°	854.7	789.6	741.0	695.9	674.5	660.2	622.3	606.5	589.4	579.3	597.9
37.5°	763.2	688.1	625.8	576.5	568.6	542.9	517.1	507.1	497.1	501.4	500.7
40°	651.6	585.1	529.3	490.6	477.1	464.9	447.7	435.6	429.1	432.7	433.4
42.5°	550.7	494.9	453.5	426.3	414.8	406.3	397.7	387.7	385.5	385.5	388.4
45°	472.8	427.0	399.1	376.9	370.5	364.1	357.6	353.3	351.9	349.0	351.2
47.5°	410.5	374.1	356.9	340.4	333.3	331.9	326.1	324.0	321.1	320.4	321.1
50°	358.3	335.4	319.7	310.4	305.4	303.3	300.4	296.1	294.7	298.3	296.8
52.5°	321.9	300.4	291.8	282.5	279.7	276.8	272.5	273.2	272.5	271.1	271.1
55°	285.4	271.8	263.2	256.1	255.3	252.5	248.9	247.5	246.8	245.3	247.5
57.5°	256.1	245.3	237.5	231.0	228.2	228.2	224.6	221.7	221.7	221.0	221.7
60°	226.7	216.0	211.0	204.6	202.4	201.7	199.5	198.1	196.0	196.0	196.0
62.5°	199.5	191.0	185.2	179.5	180.2	176.7	173.8	172.4	172.4	173.1	173.1
65°	173.8	168.1	160.9	155.9	154.5	153.8	152.3	151.6	149.5	150.9	150.9
67.5°	150.2	142.3	138.0	135.9	133.7	133.0	131.6	130.2	129.5	128.7	130.2
70°	126.6	120.2	116.6	115.2	113.0	112.3	111.6	109.4	110.1	110.9	111.6
72.5°	105.1	99.4	98.7	94.4	94.4	94.4	91.5	93.0	92.3	90.8	92.3
75°	83.0	80.1	78.7	76.5	77.2	76.5	75.8	73.7	73.7	74.4	75.1
77.5°	65.8	62.9	62.2	60.1	58.6	60.1	58.6	57.9	57.9	58.6	58.6
80°	48.6	47.2	45.1	45.1	45.1	44.3	44.3	44.3	43.6	42.9	43.6
82.5°	32.2	32.2	31.5	30.8	31.5	30.0	30.8	30.8	30.8	30.8	30.8
85°	20.7	20.0	20.0	19.3	19.3	19.3	20.0	18.6	18.6	19.3	19.3
87.5°	9.3	9.3	9.3	10.0	9.3	9.3	9.3	10.0	9.3	9.3	9.3
90°	19.0	18.7	18.5	18.2	18.1	18.2	18.3	18.4	18.6	18.7	18.6
92.5°	17.1	17.3	17.4	17.5	17.6	17.6	17.6	17.6	17.6	17.6	17.6
95°	35.2	35.2	35.2	35.2	35.2	35.1	34.8	34.6	34.3	34.1	34.3
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9
100°	75.8	75.8	75.8	75.8	75.8	75.7	75.6	75.5	75.4	75.3	75.4
102.5°	98.4	98.6	98.7	98.8	98.9	98.8	98.7	98.6	98.4	98.3	98.4
105°	121.1	121.4	121.6	121.9	122.0	122.0	122.0	122.0	122.0	122.0	122.0
107.5°	145.7	145.8	145.9	146.0	146.1	145.8	145.2	144.6	144.0	143.4	144.0
110°	170.9	170.9	170.9	170.9	170.9	170.7	170.3	170.0	169.6	169.2	169.6

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	196.3	195.9	195.6	195.2	195.0	194.9	194.6	194.4	194.1	193.9	194.1
115°	221.9	221.7	221.6	221.5	221.4	221.2	220.9	220.5	220.2	219.8	220.2
117.5°	246.8	246.5	246.1	245.8	245.6	245.4	245.0	244.7	244.3	243.9	244.3
120°	271.4	271.4	271.4	271.4	271.4	271.2	270.9	270.5	270.2	269.8	270.2
122.5°	297.4	297.0	296.7	296.3	296.1	296.0	295.7	295.5	295.2	295.0	295.2
125°	322.6	322.3	321.9	321.6	321.4	321.3	321.2	321.1	320.9	320.8	320.9
127.5°	347.3	346.8	346.3	345.8	345.6	345.4	345.0	344.7	344.3	343.9	344.3
130°	372.3	372.0	371.8	371.5	371.4	371.2	370.7	370.2	369.7	369.2	369.7
132.5°	397.2	396.6	395.9	395.3	395.0	394.8	394.5	394.1	393.8	393.4	393.8
135°	420.7	420.6	420.5	420.4	420.3	420.1	419.7	419.4	419.0	418.6	419.0
137.5°	443.8	443.7	443.6	443.5	443.4	443.2	442.7	442.2	441.7	441.2	441.7
140°	467.0	467.0	467.0	467.0	467.0	466.8	466.3	465.8	465.3	464.8	465.3
142.5°	488.0	488.1	488.2	488.3	488.4	488.2	487.7	487.2	486.7	486.2	486.7
145°	509.4	509.5	509.6	509.7	509.8	509.6	509.1	508.6	508.1	507.6	508.1
147.5°	528.2	528.5	528.7	529.0	529.1	528.9	528.4	527.9	527.4	526.9	527.4
150°	545.9	546.3	546.6	547.0	547.2	547.0	546.6	546.3	545.9	545.5	545.9
152.5°	563.6	564.1	564.6	565.1	565.3	565.1	564.6	564.1	563.6	563.1	563.6
155°	578.0	578.6	579.3	579.9	580.2	580.0	579.6	579.3	578.9	578.5	578.9
157.5°	592.0	592.8	593.7	594.6	595.0	594.7	594.1	593.4	592.8	592.2	592.8
160°	604.5	605.3	606.0	606.7	607.1	606.9	606.4	605.9	605.4	604.9	605.4
162.5°	615.6	616.5	617.3	618.2	618.6	618.3	617.7	617.1	616.5	615.9	616.5
165°	625.0	625.8	626.7	627.6	628.0	627.7	627.1	626.4	625.8	625.2	625.8
167.5°	633.2	634.0	634.9	635.8	636.2	635.9	635.3	634.6	634.0	633.4	634.0
170°	639.8	640.6	641.5	642.4	642.8	642.4	641.7	641.0	640.2	639.5	640.2
172.5°	644.7	645.6	646.4	647.3	647.7	647.3	646.6	645.9	645.1	644.4	645.1
175°	648.0	648.9	649.7	650.6	651.0	650.6	649.9	649.2	648.4	647.7	648.4
177.5°	650.1	650.9	651.6	652.3	652.7	652.3	651.6	650.9	650.1	649.4	650.1
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	986.3	981.3	977.0	977.7	981.3	978.4	971.3	962.0	958.4	954.1	958.4
5°	1045.7	1041.4	1032.8	1033.5	1031.4	1028.5	1017.1	1002.8	1002.8	991.3	989.9
7.5°	1104.3	1097.9	1092.2	1090.7	1082.9	1077.1	1067.1	1047.1	1039.2	1025.6	1017.8
10°	1170.1	1165.1	1158.7	1150.8	1146.5	1136.5	1120.1	1090.7	1076.4	1057.8	1044.2
12.5°	1236.6	1235.9	1221.6	1205.9	1205.2	1189.4	1178.0	1138.6	1119.3	1094.3	1062.1
15°	1278.8	1275.3	1267.4	1259.5	1261.7	1244.5	1218.8	1172.3	1159.4	1129.3	1095.0
17.5°	1278.1	1278.1	1276.0	1274.5	1272.4	1267.4	1253.1	1222.3	1201.6	1163.7	1131.5
20°	1237.3	1246.6	1248.8	1248.1	1255.2	1258.8	1258.1	1238.8	1222.3	1188.7	1155.8
22.5°	1155.8	1177.3	1186.6	1192.3	1207.3	1215.2	1233.8	1226.6	1222.3	1197.3	1169.4
25°	1080.0	1087.2	1115.0	1116.5	1137.2	1156.5	1175.1	1187.3	1203.0	1193.7	1170.1
27.5°	982.0	998.5	1018.5	1033.5	1037.8	1077.1	1107.9	1130.8	1166.5	1169.4	1161.5
30°	871.2	879.0	911.9	931.9	954.8	983.4	1027.8	1067.1	1099.3	1128.6	1138.6
32.5°	736.0	768.2	787.5	811.8	831.8	882.6	937.0	987.7	1024.9	1074.3	1095.7
35°	612.2	637.3	670.2	680.2	716.7	759.6	830.4	895.5	952.0	1002.0	1045.7
37.5°	510.0	530.0	565.0	580.8	602.2	657.3	716.7	797.5	865.4	926.9	981.3
40°	439.9	454.9	481.4	486.4	504.2	554.3	602.2	678.0	768.2	851.1	910.5
42.5°	391.9	399.1	417.0	423.4	434.9	468.5	511.4	582.9	666.6	752.4	836.1
45°	357.6	362.6	373.4	379.1	393.4	408.4	443.4	500.7	566.5	653.0	743.1
47.5°	326.9	333.3	337.6	341.2	349.0	365.5	388.4	430.6	493.5	572.9	660.2
50°	301.1	303.3	311.1	311.8	316.8	327.6	349.0	374.8	424.8	489.2	573.6
52.5°	275.4	277.5	282.5	287.5	289.7	298.3	312.6	334.0	371.2	422.0	497.1
55°	249.6	252.5	257.5	261.1	263.2	270.4	278.9	299.7	329.0	364.8	426.3
57.5°	223.9	230.3	231.7	233.9	237.5	245.3	253.2	265.4	288.2	321.1	366.2
60°	199.5	201.7	206.7	208.8	212.4	216.7	226.7	236.0	252.5	278.2	319.0
62.5°	174.5	179.5	181.7	183.8	186.7	191.7	198.1	208.1	222.4	243.2	275.4
65°	153.1	153.8	158.1	160.9	163.8	167.4	173.8	183.1	191.7	211.0	234.6
67.5°	132.3	133.7	135.2	138.0	141.6	145.2	150.9	155.9	166.6	179.5	198.1
70°	112.3	112.3	115.9	118.0	117.3	121.6	125.9	131.6	139.5	151.6	166.6
72.5°	94.4	93.7	96.6	97.3	98.7	101.6	104.4	110.1	114.4	123.7	135.2
75°	75.1	76.5	78.0	78.0	80.1	82.3	85.1	88.0	93.0	98.7	107.3
77.5°	59.4	59.4	60.8	61.5	63.7	62.9	65.8	68.7	72.2	77.2	83.7
80°	43.6	45.1	45.1	45.1	45.8	46.5	49.4	51.5	53.6	57.2	60.1
82.5°	30.8	30.8	32.2	32.2	32.2	33.6	33.6	34.3	35.8	37.9	40.1
85°	19.3	19.3	19.3	20.0	19.3	20.0	21.5	20.7	21.5	22.9	22.9
87.5°	9.3	9.3	9.3	9.3	9.3	10.0	9.3	10.0	10.7	10.7	10.7
90°	18.4	18.3	18.2	18.1	18.2	18.5	18.7	19.0	19.2	16.5	13.8
92.5°	17.6	17.6	17.6	17.6	17.5	17.4	17.3	17.1	17.0	16.9	16.8
95°	34.6	34.8	35.1	35.2	35.2	35.2	35.2	35.2	35.2	35.0	34.7
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.4	53.9
100°	75.5	75.6	75.7	75.8	75.8	75.8	75.8	75.8	75.8	75.4	75.1
102.5°	98.6	98.7	98.8	98.9	98.8	98.7	98.6	98.4	98.3	97.8	97.3
105°	122.0	122.0	122.0	122.0	121.9	121.6	121.4	121.1	120.9	120.7	120.4
107.5°	144.6	145.2	145.8	146.1	146.0	145.9	145.8	145.7	145.6	145.6	145.6
110°	170.0	170.3	170.7	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9



TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	194.4	194.6	194.9	195.0	195.2	195.6	195.9	196.3	196.7	196.8	196.9
115°	220.5	220.9	221.2	221.4	221.5	221.6	221.7	221.9	222.0	222.2	222.5
117.5°	244.7	245.0	245.4	245.6	245.8	246.1	246.5	246.8	247.2	247.8	248.4
120°	270.5	270.9	271.2	271.4	271.4	271.4	271.4	271.4	271.4	272.4	273.4
122.5°	295.5	295.7	296.0	296.1	296.3	296.7	297.0	297.4	297.8	298.4	299.0
125°	321.1	321.2	321.3	321.4	321.6	321.9	322.3	322.6	323.0	323.4	323.8
127.5°	344.7	345.0	345.4	345.6	345.8	346.3	346.8	347.3	347.8	348.3	348.8
130°	370.2	370.7	371.2	371.4	371.5	371.8	372.0	372.3	372.5	372.7	373.0
132.5°	394.1	394.5	394.8	395.0	395.3	395.9	396.6	397.2	397.8	397.7	397.5
135°	419.4	419.7	420.1	420.3	420.4	420.5	420.6	420.7	420.8	420.6	420.3
137.5°	442.2	442.7	443.2	443.4	443.5	443.6	443.7	443.8	443.9	443.7	443.4
140°	465.8	466.3	466.8	467.0	467.0	467.0	467.0	467.0	467.0	466.4	465.8
142.5°	487.2	487.7	488.2	488.4	488.3	488.2	488.1	488.0	487.9	487.5	487.1
145°	508.6	509.1	509.6	509.8	509.7	509.6	509.5	509.4	509.3	508.6	507.8
147.5°	527.9	528.4	528.9	529.1	529.0	528.7	528.5	528.2	528.0	527.5	527.0
150°	546.3	546.6	547.0	547.2	547.0	546.6	546.3	545.9	545.5	545.0	544.5
152.5°	564.1	564.6	565.1	565.3	565.1	564.6	564.1	563.6	563.1	562.5	561.9
155°	579.3	579.6	580.0	580.2	579.9	579.3	578.6	578.0	577.4	577.0	576.7
157.5°	593.4	594.1	594.7	595.0	594.6	593.7	592.8	592.0	591.1	590.9	590.6
160°	605.9	606.4	606.9	607.1	606.7	606.0	605.3	604.5	603.8	603.7	603.5
162.5°	617.1	617.7	618.3	618.6	618.2	617.3	616.5	615.6	614.8	614.7	614.5
165°	626.4	627.1	627.7	628.0	627.6	626.7	625.8	625.0	624.1	624.1	624.1
167.5°	634.6	635.3	635.9	636.2	635.8	634.9	634.0	633.2	632.3	632.3	632.3
170°	641.0	641.7	642.4	642.8	642.4	641.5	640.6	639.8	638.9	639.0	639.2
172.5°	645.9	646.6	647.3	647.7	647.3	646.4	645.6	644.7	643.9	644.0	644.1
175°	649.2	649.9	650.6	651.0	650.6	649.7	648.9	648.0	647.2	647.4	647.7
177.5°	650.9	651.6	652.3	652.7	652.3	651.6	650.9	650.1	649.4	649.6	649.9
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	954.8	951.3	949.1	950.5	946.3	935.5	935.5	939.1	934.8	930.5	924.1
5°	981.3	974.1	969.9	969.1	959.1	942.0	938.4	934.8	925.5	915.5	904.8
7.5°	1007.0	994.2	987.0	982.0	967.7	945.5	936.2	928.4	913.3	898.3	884.7
10°	1028.5	1009.9	1001.3	993.5	974.9	947.0	931.9	917.6	898.3	879.0	861.9
12.5°	1045.7	1024.2	1013.5	1002.0	979.2	942.7	924.1	901.2	881.9	856.1	839.0
15°	1074.3	1029.9	1019.9	1009.2	985.6	935.5	912.6	886.9	860.4	826.1	807.5
17.5°	1097.2	1037.8	1037.1	1014.2	983.4	932.7	897.6	864.0	835.4	801.1	771.7
20°	1110.8	1050.0	1038.5	1014.9	976.3	913.3	876.9	839.7	808.9	767.4	738.1
22.5°	1122.2	1067.1	1037.1	1008.5	961.3	906.9	853.3	818.2	776.0	731.0	703.1
25°	1126.5	1070.7	1039.2	1006.3	950.5	888.3	827.5	789.6	742.4	701.6	663.7
27.5°	1127.2	1070.0	1031.4	997.0	935.5	864.0	801.8	761.7	709.5	662.3	624.4
30°	1120.1	1062.1	1027.1	989.9	921.2	841.8	770.3	726.0	670.2	623.0	583.6
32.5°	1098.6	1046.4	1017.8	977.0	902.6	811.1	740.3	690.9	632.3	585.8	547.9
35°	1062.8	1027.1	995.6	957.7	878.3	782.5	710.2	652.3	592.9	548.6	512.8
37.5°	1018.5	999.2	969.9	932.7	850.4	756.7	676.6	612.2	552.9	510.0	474.9
40°	958.4	963.4	934.8	901.2	817.5	721.7	633.0	571.5	515.7	475.6	441.3
42.5°	893.3	914.1	897.6	865.4	781.0	683.0	600.8	532.8	478.5	437.0	408.4
45°	823.2	859.0	849.0	825.4	743.1	642.3	555.0	489.2	441.3	401.2	376.2
47.5°	746.7	797.5	797.5	780.3	700.9	601.5	515.7	448.4	401.2	372.6	348.3
50°	668.7	726.0	735.3	723.8	653.7	555.0	467.8	407.0	366.2	338.3	320.4
52.5°	587.2	653.7	670.9	665.2	603.7	510.7	428.4	369.1	331.9	307.5	291.8
55°	509.2	586.5	605.1	607.2	550.0	462.0	384.8	332.6	296.8	280.4	266.8
57.5°	435.6	510.0	530.7	534.3	495.7	417.7	344.0	298.3	266.1	252.5	241.7
60°	372.6	434.9	462.0	469.9	436.3	366.2	306.1	261.8	237.5	224.6	214.6
62.5°	321.1	371.2	399.8	402.0	386.9	321.1	266.8	229.6	208.8	197.4	192.4
65°	271.1	316.1	333.3	341.9	329.7	278.2	230.3	199.5	183.1	173.1	168.1
67.5°	231.0	259.6	273.9	285.4	273.2	234.6	196.0	170.9	158.8	148.8	145.9
70°	189.5	213.1	223.9	235.3	224.6	195.3	167.4	144.5	133.7	125.9	122.3
72.5°	151.6	170.2	180.2	187.4	181.0	156.6	133.7	118.0	110.1	104.4	102.3
75°	120.2	133.0	138.8	143.8	140.9	122.3	108.0	95.1	88.0	83.0	81.5
77.5°	91.5	100.8	107.3	108.7	105.1	93.0	80.8	73.0	67.2	64.4	62.9
80°	65.1	70.8	74.4	76.5	73.0	67.9	59.4	53.6	48.6	45.1	44.3
82.5°	43.6	46.5	49.4	48.6	47.2	42.9	37.9	35.0	32.9	30.0	30.0
85°	25.0	25.7	27.2	27.9	27.2	24.3	21.5	20.0	18.6	16.5	16.5
87.5°	10.7	11.4	11.4	12.2	10.7	10.7	9.3	7.9	7.9	7.2	6.4
90°	11.1	8.4	7.1	6.4	4.9	3.4	2.0	0.5	2.0	3.4	4.9
92.5°	16.7	16.6	16.5	16.0	15.0	14.1	13.1	12.1	13.1	14.1	15.0
95°	34.5	34.2	34.1	33.5	32.3	31.0	29.8	28.6	29.8	31.0	32.3
97.5°	53.4	52.9	52.7	52.2	51.1	50.0	48.9	47.8	48.9	50.0	51.1
100°	74.7	74.4	74.2	73.7	72.7	71.8	70.8	69.8	70.8	71.8	72.7
102.5°	96.8	96.3	96.1	95.7	95.0	94.3	93.5	92.8	93.5	94.3	95.0
105°	120.2	119.9	119.8	119.6	119.2	118.9	118.5	118.1	118.5	118.9	119.2
107.5°	145.6	145.6	145.6	145.4	144.9	144.4	143.9	143.4	143.9	144.4	144.9
110°	170.9	170.9	170.9	170.5	169.8	169.1	168.3	167.6	168.3	169.1	169.8

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	197.0	197.1	197.2	196.8	196.1	195.4	194.6	193.9	194.6	195.4	196.1
115°	222.7	223.0	223.1	222.7	222.0	221.3	220.5	219.8	220.5	221.3	222.0
117.5°	249.1	249.7	250.0	249.5	248.5	247.6	246.6	245.6	246.6	247.6	248.5
120°	274.3	275.3	275.8	275.3	274.3	273.4	272.4	271.4	272.4	273.4	274.3
122.5°	299.6	300.2	300.5	299.9	298.7	297.4	296.2	295.0	296.2	297.4	298.7
125°	324.1	324.5	324.7	324.1	323.0	321.9	320.8	319.7	320.8	321.9	323.0
127.5°	349.3	349.8	350.0	349.3	348.0	346.6	345.3	343.9	345.3	346.6	348.0
130°	373.2	373.5	373.6	372.8	371.2	369.6	368.0	366.4	368.0	369.6	371.2
132.5°	397.4	397.3	397.2	396.6	395.4	394.1	392.9	391.7	392.9	394.1	395.4
135°	420.1	419.8	419.7	419.0	417.7	416.4	415.0	413.7	415.0	416.4	417.7
137.5°	443.2	442.9	442.8	442.3	441.2	440.1	439.0	437.9	439.0	440.1	441.2
140°	465.1	464.5	464.2	463.7	462.6	461.5	460.4	459.3	460.4	461.5	462.6
142.5°	486.8	486.4	486.2	485.7	484.6	483.5	482.4	481.3	482.4	483.5	484.6
145°	507.1	506.4	506.0	505.6	504.7	503.8	503.0	502.1	503.0	503.8	504.7
147.5°	526.5	526.0	525.8	525.2	524.1	523.0	521.9	520.8	521.9	523.0	524.1
150°	544.0	543.5	543.3	542.9	542.2	541.5	540.8	540.1	540.8	541.5	542.2
152.5°	561.3	560.7	560.4	560.0	559.3	558.6	557.8	557.1	557.8	558.6	559.3
155°	576.3	576.0	575.8	575.6	575.2	574.9	574.5	574.1	574.5	574.9	575.2
157.5°	590.4	590.1	590.0	589.9	589.6	589.4	589.1	588.9	589.1	589.4	589.6
160°	603.4	603.3	603.2	603.1	602.8	602.6	602.3	602.1	602.3	602.6	602.8
162.5°	614.4	614.3	614.2	614.2	614.2	614.2	614.2	614.2	614.2	614.2	614.2
165°	624.1	624.1	624.1	624.2	624.3	624.4	624.6	624.7	624.6	624.4	624.3
167.5°	632.3	632.3	632.3	632.5	632.9	633.2	633.6	634.0	633.6	633.2	632.9
170°	639.3	639.4	639.5	639.7	640.0	640.4	640.7	641.1	640.7	640.4	640.0
172.5°	644.2	644.3	644.4	644.6	645.0	645.3	645.7	646.1	645.7	645.3	645.0
175°	647.9	648.2	648.3	648.5	648.8	649.2	649.5	649.9	649.5	649.2	648.8
177.5°	650.1	650.4	650.5	650.7	651.0	651.4	651.7	652.1	651.7	651.4	651.0
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	920.5	924.1	923.4	916.2	908.3	901.9	889.7	891.2	886.9	887.6	891.9
5°	897.6	897.6	894.8	884.7	871.9	864.7	851.1	847.5	839.0	838.3	837.5
7.5°	873.3	869.7	866.1	851.8	836.1	824.7	806.1	801.8	793.2	787.5	784.6
10°	844.7	839.7	832.5	816.1	796.8	782.5	763.2	757.4	741.0	733.8	729.5
12.5°	813.2	810.4	798.9	785.3	753.9	738.1	710.2	715.9	699.5	685.2	683.0
15°	781.7	771.0	764.6	742.4	704.5	697.3	675.2	663.7	648.7	637.3	637.3
17.5°	751.0	734.5	720.2	696.6	668.7	648.7	632.3	626.5	607.9	596.5	594.4
20°	710.2	691.6	688.1	654.4	635.1	613.0	597.2	582.9	569.3	564.3	560.7
22.5°	671.6	650.1	644.4	615.8	596.5	574.3	558.6	548.6	538.6	535.0	528.6
25°	630.1	617.2	608.7	577.9	556.4	535.7	525.0	517.8	508.5	507.8	503.5
27.5°	590.1	577.9	569.3	540.0	524.3	505.0	496.4	488.5	483.5	481.4	479.2
30°	555.7	542.1	532.1	510.7	491.4	475.6	468.5	463.5	460.6	457.0	456.3
32.5°	517.8	510.0	496.4	479.9	464.9	449.9	445.6	442.0	437.7	436.3	435.6
35°	485.6	474.9	466.3	447.7	441.3	428.4	423.4	420.6	414.8	413.4	412.0
37.5°	454.2	444.2	434.9	423.4	411.3	404.1	401.2	397.0	394.1	394.8	393.4
40°	422.7	414.8	407.7	395.5	388.4	384.8	379.1	374.8	373.4	374.1	373.4
42.5°	391.9	384.8	380.5	371.2	364.1	360.5	356.9	352.6	354.8	354.8	356.9
45°	364.1	357.6	354.8	347.6	343.3	337.6	334.0	333.3	336.2	335.4	335.4
47.5°	335.4	333.3	329.7	323.3	317.6	314.0	313.3	313.3	316.1	317.6	316.8
50°	313.3	309.0	304.7	299.7	295.4	294.0	291.8	293.2	296.1	296.1	297.5
52.5°	285.4	282.5	281.1	276.8	273.9	273.9	273.9	274.6	276.8	278.9	278.2
55°	261.1	258.9	257.5	255.3	251.8	252.5	251.8	253.2	255.3	257.5	258.9
57.5°	235.3	234.6	233.2	229.6	229.6	228.9	231.0	231.7	235.3	236.7	238.9
60°	212.4	210.3	210.3	207.4	207.4	207.4	209.6	211.7	214.6	215.3	216.7
62.5°	188.1	188.1	187.4	185.2	185.2	187.4	188.1	191.0	192.4	192.4	194.5
65°	165.2	164.5	163.8	164.5	165.2	165.2	167.4	168.8	170.2	170.9	171.7
67.5°	142.3	141.6	143.0	142.3	143.8	146.6	145.9	148.1	150.2	150.2	150.9
70°	120.9	122.3	121.6	123.0	122.3	123.7	125.9	126.6	126.6	127.3	129.5
72.5°	100.8	100.8	100.8	100.1	100.8	102.3	103.7	104.4	105.9	106.6	108.7
75°	81.5	81.5	80.1	81.5	81.5	83.0	84.4	84.4	84.4	85.8	88.0
77.5°	61.5	62.2	61.5	62.9	62.9	63.7	65.1	64.4	65.8	66.5	67.2
80°	45.1	44.3	44.3	44.3	45.1	45.1	46.5	47.2	47.2	49.4	47.9
82.5°	28.6	29.3	28.6	29.3	29.3	30.0	29.3	30.0	30.8	32.2	31.5
85°	16.5	15.7	15.7	16.5	15.7	15.7	16.5	15.7	16.5	15.7	16.5
87.5°	6.4	5.7	5.7	5.7	5.7	5.0	5.0	4.3	4.3	4.3	3.6
90°	6.4	7.1	8.4	11.1	13.8	16.5	19.2	19.0	18.7	18.5	18.2
92.5°	16.0	16.5	16.6	16.7	16.8	16.9	17.0	17.1	17.3	17.4	17.5
95°	33.5	34.1	34.2	34.5	34.7	35.0	35.2	35.2	35.2	35.2	35.2
97.5°	52.2	52.7	52.9	53.4	53.9	54.4	54.9	54.9	54.9	54.9	54.9
100°	73.7	74.2	74.4	74.7	75.1	75.4	75.8	75.8	75.8	75.8	75.8
102.5°	95.7	96.1	96.3	96.8	97.3	97.8	98.3	98.4	98.6	98.7	98.8
105°	119.6	119.8	119.9	120.2	120.4	120.7	120.9	121.1	121.4	121.6	121.9
107.5°	145.4	145.6	145.6	145.6	145.6	145.6	145.6	145.7	145.8	145.9	146.0
110°	170.5	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	196.8	197.2	197.1	197.0	196.9	196.8	196.7	196.3	195.9	195.6	195.2
115°	222.7	223.1	223.0	222.7	222.5	222.2	222.0	221.9	221.7	221.6	221.5
117.5°	249.5	250.0	249.7	249.1	248.4	247.8	247.2	246.8	246.5	246.1	245.8
120°	275.3	275.8	275.3	274.3	273.4	272.4	271.4	271.4	271.4	271.4	271.4
122.5°	299.9	300.5	300.2	299.6	299.0	298.4	297.8	297.4	297.0	296.7	296.3
125°	324.1	324.7	324.5	324.1	323.8	323.4	323.0	322.6	322.3	321.9	321.6
127.5°	349.3	350.0	349.8	349.3	348.8	348.3	347.8	347.3	346.8	346.3	345.8
130°	372.8	373.6	373.5	373.2	373.0	372.7	372.5	372.3	372.0	371.8	371.5
132.5°	396.6	397.2	397.3	397.4	397.5	397.7	397.8	397.2	396.6	395.9	395.3
135°	419.0	419.7	419.8	420.1	420.3	420.6	420.8	420.7	420.6	420.5	420.4
137.5°	442.3	442.8	442.9	443.2	443.4	443.7	443.9	443.8	443.7	443.6	443.5
140°	463.7	464.2	464.5	465.1	465.8	466.4	467.0	467.0	467.0	467.0	467.0
142.5°	485.7	486.2	486.4	486.8	487.1	487.5	487.9	488.0	488.1	488.2	488.3
145°	505.6	506.0	506.4	507.1	507.8	508.6	509.3	509.4	509.5	509.6	509.7
147.5°	525.2	525.8	526.0	526.5	527.0	527.5	528.0	528.2	528.5	528.7	529.0
150°	542.9	543.3	543.5	544.0	544.5	545.0	545.5	545.9	546.3	546.6	547.0
152.5°	560.0	560.4	560.7	561.3	561.9	562.5	563.1	563.6	564.1	564.6	565.1
155°	575.6	575.8	576.0	576.3	576.7	577.0	577.4	578.0	578.6	579.3	579.9
157.5°	589.9	590.0	590.1	590.4	590.6	590.9	591.1	592.0	592.8	593.7	594.6
160°	603.1	603.2	603.3	603.4	603.5	603.7	603.8	604.5	605.3	606.0	606.7
162.5°	614.2	614.2	614.3	614.4	614.5	614.7	614.8	615.6	616.5	617.3	618.2
165°	624.2	624.1	624.1	624.1	624.1	624.1	624.1	625.0	625.8	626.7	627.6
167.5°	632.5	632.3	632.3	632.3	632.3	632.3	632.3	633.2	634.0	634.9	635.8
170°	639.7	639.5	639.4	639.3	639.2	639.0	638.9	639.8	640.6	641.5	642.4
172.5°	644.6	644.4	644.3	644.2	644.1	644.0	643.9	644.7	645.6	646.4	647.3
175°	648.5	648.3	648.2	647.9	647.7	647.4	647.2	648.0	648.9	649.7	650.6
177.5°	650.7	650.5	650.4	650.1	649.9	649.6	649.4	650.1	650.9	651.6	652.3
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	886.9	889.0	884.0	882.6	884.0	879.0	880.4	881.9	881.9	884.0	885.5
5°	835.4	832.5	827.5	826.1	824.7	826.8	825.4	827.5	828.2	833.2	834.0
7.5°	784.6	780.3	776.0	771.7	770.3	766.7	770.3	770.3	775.3	773.9	777.5
10°	724.5	723.8	718.1	715.9	713.1	707.4	715.2	713.1	716.7	723.1	724.5
12.5°	680.2	672.3	675.9	665.9	669.5	663.7	664.4	664.4	670.2	670.9	669.5
15°	638.0	631.5	622.3	618.0	615.8	613.0	622.3	623.0	618.7	628.7	625.1
17.5°	595.1	595.1	586.5	584.3	578.6	581.5	580.1	580.8	579.3	586.5	590.1
20°	557.9	554.3	551.4	552.2	545.0	543.6	542.1	543.6	548.6	553.6	555.0
22.5°	527.8	525.7	518.5	520.0	514.3	516.4	515.0	518.5	519.3	519.3	524.3
25°	499.2	496.4	497.1	494.2	492.1	492.1	489.9	492.1	494.9	496.4	497.1
27.5°	477.8	475.6	472.1	469.9	471.3	467.8	470.6	472.8	472.8	471.3	472.8
30°	452.0	453.5	453.5	446.3	449.2	447.7	449.9	451.3	451.3	452.0	450.6
32.5°	434.9	430.6	429.9	429.1	429.1	426.3	426.3	428.4	429.1	429.9	432.0
35°	412.0	412.0	408.4	410.5	407.7	408.4	407.7	408.4	409.8	407.7	409.8
37.5°	391.2	391.9	390.5	391.9	392.7	391.2	389.8	392.7	391.2	391.2	389.8
40°	373.4	372.6	373.4	373.4	373.4	374.1	372.6	372.6	372.6	371.2	369.8
42.5°	358.3	354.0	355.5	356.2	354.0	354.0	354.8	354.0	356.2	351.9	351.9
45°	336.9	335.4	336.2	336.2	337.6	335.4	336.9	337.6	335.4	334.7	333.3
47.5°	317.6	319.0	317.6	319.0	319.0	320.4	317.6	318.3	319.0	316.1	314.0
50°	298.3	298.3	300.4	299.7	300.4	299.0	299.0	298.3	299.0	297.5	295.4
52.5°	280.4	278.2	281.8	281.1	280.4	279.7	278.9	279.7	278.2	276.8	276.8
55°	258.2	258.2	260.3	261.1	261.1	259.6	258.2	258.9	258.2	257.5	256.8
57.5°	240.3	237.5	238.9	239.6	239.6	237.5	238.9	237.5	237.5	238.2	236.0
60°	217.4	217.4	216.0	218.1	218.1	216.7	216.7	217.4	216.0	215.3	214.6
62.5°	193.1	193.8	196.0	196.7	197.4	196.0	194.5	195.3	195.3	193.1	193.8
65°	172.4	173.8	176.7	175.9	174.5	175.2	173.8	174.5	172.4	173.1	170.9
67.5°	152.3	151.6	152.3	152.3	153.8	153.1	151.6	151.6	150.9	153.1	150.9
70°	130.9	130.9	130.9	130.9	131.6	132.3	130.9	129.5	130.2	128.7	128.0
72.5°	108.7	109.4	108.7	110.1	108.0	109.4	109.4	108.7	108.0	108.0	108.0
75°	88.0	89.4	87.3	88.0	87.3	88.7	88.0	88.0	86.5	85.8	86.5
77.5°	67.2	67.9	66.5	67.2	66.5	67.2	67.2	66.5	66.5	66.5	66.5
80°	47.9	48.6	47.9	47.2	46.5	47.9	46.5	47.2	47.9	47.2	48.6
82.5°	30.8	30.8	30.0	30.8	29.3	29.3	30.0	30.0	29.3	30.8	29.3
85°	15.0	15.0	16.5	15.0	14.3	14.3	14.3	15.0	14.3	15.7	15.0
87.5°	3.6	2.9	3.6	3.6	2.9	2.9	3.6	2.9	3.6	4.3	2.9
90°	18.1	18.2	18.3	18.4	18.6	18.7	18.6	18.4	18.3	18.2	18.1
92.5°	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6
95°	35.2	35.1	34.8	34.6	34.3	34.1	34.3	34.6	34.8	35.1	35.2
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9
100°	75.8	75.7	75.6	75.5	75.4	75.3	75.4	75.5	75.6	75.7	75.8
102.5°	98.9	98.8	98.7	98.6	98.4	98.3	98.4	98.6	98.7	98.8	98.9
105°	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0
107.5°	146.1	145.8	145.2	144.6	144.0	143.4	144.0	144.6	145.2	145.8	146.1
110°	170.9	170.7	170.3	170.0	169.6	169.2	169.6	170.0	170.3	170.7	170.9

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	195.0	194.9	194.6	194.4	194.1	193.9	194.1	194.4	194.6	194.9	195.0
115°	221.4	221.2	220.9	220.5	220.2	219.8	220.2	220.5	220.9	221.2	221.4
117.5°	245.6	245.4	245.0	244.7	244.3	243.9	244.3	244.7	245.0	245.4	245.6
120°	271.4	271.2	270.9	270.5	270.2	269.8	270.2	270.5	270.9	271.2	271.4
122.5°	296.1	296.0	295.7	295.5	295.2	295.0	295.2	295.5	295.7	296.0	296.1
125°	321.4	321.3	321.2	321.1	320.9	320.8	320.9	321.1	321.2	321.3	321.4
127.5°	345.6	345.4	345.0	344.7	344.3	343.9	344.3	344.7	345.0	345.4	345.6
130°	371.4	371.2	370.7	370.2	369.7	369.2	369.7	370.2	370.7	371.2	371.4
132.5°	395.0	394.8	394.5	394.1	393.8	393.4	393.8	394.1	394.5	394.8	395.0
135°	420.3	420.1	419.7	419.4	419.0	418.6	419.0	419.4	419.7	420.1	420.3
137.5°	443.4	443.2	442.7	442.2	441.7	441.2	441.7	442.2	442.7	443.2	443.4
140°	467.0	466.8	466.3	465.8	465.3	464.8	465.3	465.8	466.3	466.8	467.0
142.5°	488.4	488.2	487.7	487.2	486.7	486.2	486.7	487.2	487.7	488.2	488.4
145°	509.8	509.6	509.1	508.6	508.1	507.6	508.1	508.6	509.1	509.6	509.8
147.5°	529.1	528.9	528.4	527.9	527.4	526.9	527.4	527.9	528.4	528.9	529.1
150°	547.2	547.0	546.6	546.3	545.9	545.5	545.9	546.3	546.6	547.0	547.2
152.5°	565.3	565.1	564.6	564.1	563.6	563.1	563.6	564.1	564.6	565.1	565.3
155°	580.2	580.0	579.6	579.3	578.9	578.5	578.9	579.3	579.6	580.0	580.2
157.5°	595.0	594.7	594.1	593.4	592.8	592.2	592.8	593.4	594.1	594.7	595.0
160°	607.1	606.9	606.4	605.9	605.4	604.9	605.4	605.9	606.4	606.9	607.1
162.5°	618.6	618.3	617.7	617.1	616.5	615.9	616.5	617.1	617.7	618.3	618.6
165°	628.0	627.7	627.1	626.4	625.8	625.2	625.8	626.4	627.1	627.7	628.0
167.5°	636.2	635.9	635.3	634.6	634.0	633.4	634.0	634.6	635.3	635.9	636.2
170°	642.8	642.4	641.7	641.0	640.2	639.5	640.2	641.0	641.7	642.4	642.8
172.5°	647.7	647.3	646.6	645.9	645.1	644.4	645.1	645.9	646.6	647.3	647.7
175°	651.0	650.6	649.9	649.2	648.4	647.7	648.4	649.2	649.9	650.6	651.0
177.5°	652.7	652.3	651.6	650.9	650.1	649.4	650.1	650.9	651.6	652.3	652.7
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	883.3	889.0	886.9	879.0	888.3	888.3	894.8	894.8	902.6	905.5	909.8
5°	833.2	837.5	841.1	837.5	844.0	854.0	859.7	864.7	875.4	879.7	886.2
7.5°	779.6	787.5	791.0	791.0	801.8	813.2	824.7	831.8	846.8	852.6	859.0
10°	727.4	736.7	743.8	743.1	761.0	768.2	782.5	798.9	813.9	822.5	831.8
12.5°	672.3	677.3	687.3	701.6	705.9	718.8	735.3	756.0	783.2	791.0	804.6
15°	626.5	640.1	648.0	654.4	664.4	676.6	694.5	714.5	741.7	758.9	773.2
17.5°	587.9	605.8	610.8	609.4	622.3	640.8	661.6	676.6	700.9	721.7	735.3
20°	556.4	563.6	572.2	575.8	585.8	605.8	625.8	643.0	663.0	679.5	695.2
22.5°	525.0	530.7	537.9	544.3	552.2	563.6	582.9	604.4	623.7	639.4	657.3
25°	499.2	502.8	509.2	514.3	522.8	530.7	544.3	567.9	590.8	600.1	615.8
27.5°	474.2	477.1	481.4	487.1	491.4	499.2	511.4	530.7	554.3	563.6	585.1
30°	452.0	454.2	458.5	461.3	463.5	472.8	482.1	497.1	515.0	527.8	543.6
32.5°	431.3	433.4	437.7	438.4	441.3	446.3	454.9	468.5	484.2	494.9	508.5
35°	408.4	409.8	414.1	415.5	417.7	422.0	428.4	438.4	452.7	460.6	472.8
37.5°	390.5	389.8	392.7	394.8	397.7	399.8	402.0	412.0	422.7	429.9	439.2
40°	371.2	369.8	370.5	373.4	374.8	377.6	377.6	387.7	394.8	400.5	407.7
42.5°	351.9	351.2	349.7	351.2	352.6	353.3	354.0	361.2	368.3	373.4	381.2
45°	332.6	331.9	330.4	331.2	331.2	332.6	334.7	337.6	342.6	346.9	351.2
47.5°	314.7	313.3	311.1	310.4	311.8	311.8	311.8	314.7	319.7	321.1	325.4
50°	296.1	294.0	291.1	289.7	289.7	289.0	290.4	291.1	295.4	296.8	300.4
52.5°	276.1	274.6	271.8	268.9	269.6	268.2	268.9	269.6	271.1	273.2	275.4
55°	256.1	253.2	251.0	250.3	248.2	248.2	246.0	248.9	248.2	248.9	251.8
57.5°	236.7	233.9	230.3	228.9	226.7	226.0	224.6	223.9	224.6	226.7	228.9
60°	213.9	212.4	210.3	208.1	206.7	204.6	203.1	203.1	202.4	202.4	203.1
62.5°	191.7	191.0	188.1	187.4	186.0	184.5	182.4	181.0	181.0	182.4	183.1
65°	170.2	169.5	167.4	166.6	163.1	161.6	160.9	160.2	158.8	158.8	158.8
67.5°	150.2	148.1	148.1	144.5	141.6	140.2	138.8	138.0	138.0	138.0	138.8
70°	128.0	128.0	125.9	123.7	120.9	121.6	119.4	117.3	117.3	115.9	116.6
72.5°	106.6	105.9	103.7	103.0	100.8	98.7	97.3	98.7	96.6	95.8	96.6
75°	85.8	85.1	83.7	82.3	83.0	80.8	78.7	78.0	78.0	76.5	76.5
77.5°	65.8	67.2	64.4	63.7	62.2	60.8	60.1	59.4	59.4	59.4	60.8
80°	45.8	46.5	46.5	45.1	45.8	43.6	43.6	43.6	41.5	42.2	42.9
82.5°	29.3	29.3	28.6	29.3	28.6	28.6	27.9	27.9	27.2	27.2	27.9
85°	16.5	15.7	15.0	16.5	15.7	15.7	15.0	15.0	15.0	15.0	15.0
87.5°	3.6	4.3	4.3	4.3	4.3	5.0	5.0	5.0	5.7	5.7	5.7
90°	18.2	18.5	18.7	19.0	19.2	16.5	13.8	11.1	8.4	7.1	6.4
92.5°	17.5	17.4	17.3	17.1	17.0	16.9	16.8	16.7	16.6	16.5	16.0
95°	35.2	35.2	35.2	35.2	35.2	35.0	34.7	34.5	34.2	34.1	33.5
97.5°	54.9	54.9	54.9	54.9	54.9	54.4	53.9	53.4	52.9	52.7	52.2
100°	75.8	75.8	75.8	75.8	75.8	75.4	75.1	74.7	74.4	74.2	73.7
102.5°	98.8	98.7	98.6	98.4	98.3	97.8	97.3	96.8	96.3	96.1	95.7
105°	121.9	121.6	121.4	121.1	120.9	120.7	120.4	120.2	119.9	119.8	119.6
107.5°	146.0	145.9	145.8	145.7	145.6	145.6	145.6	145.6	145.6	145.6	145.4
110°	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.5

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	195.2	195.6	195.9	196.3	196.7	196.8	196.9	197.0	197.1	197.2	196.8
115°	221.5	221.6	221.7	221.9	222.0	222.2	222.5	222.7	223.0	223.1	222.7
117.5°	245.8	246.1	246.5	246.8	247.2	247.8	248.4	249.1	249.7	250.0	249.5
120°	271.4	271.4	271.4	271.4	271.4	272.4	273.4	274.3	275.3	275.8	275.3
122.5°	296.3	296.7	297.0	297.4	297.8	298.4	299.0	299.6	300.2	300.5	299.9
125°	321.6	321.9	322.3	322.6	323.0	323.4	323.8	324.1	324.5	324.7	324.1
127.5°	345.8	346.3	346.8	347.3	347.8	348.3	348.8	349.3	349.8	350.0	349.3
130°	371.5	371.8	372.0	372.3	372.5	372.7	373.0	373.2	373.5	373.6	372.8
132.5°	395.3	395.9	396.6	397.2	397.8	397.7	397.5	397.4	397.3	397.2	396.6
135°	420.4	420.5	420.6	420.7	420.8	420.6	420.3	420.1	419.8	419.7	419.0
137.5°	443.5	443.6	443.7	443.8	443.9	443.7	443.4	443.2	442.9	442.8	442.3
140°	467.0	467.0	467.0	467.0	467.0	466.4	465.8	465.1	464.5	464.2	463.7
142.5°	488.3	488.2	488.1	488.0	487.9	487.5	487.1	486.8	486.4	486.2	485.7
145°	509.7	509.6	509.5	509.4	509.3	508.6	507.8	507.1	506.4	506.0	505.6
147.5°	529.0	528.7	528.5	528.2	528.0	527.5	527.0	526.5	526.0	525.8	525.2
150°	547.0	546.6	546.3	545.9	545.5	545.0	544.5	544.0	543.5	543.3	542.9
152.5°	565.1	564.6	564.1	563.6	563.1	562.5	561.9	561.3	560.7	560.4	560.0
155°	579.9	579.3	578.6	578.0	577.4	577.0	576.7	576.3	576.0	575.8	575.6
157.5°	594.6	593.7	592.8	592.0	591.1	590.9	590.6	590.4	590.1	590.0	589.9
160°	606.7	606.0	605.3	604.5	603.8	603.7	603.5	603.4	603.3	603.2	603.1
162.5°	618.2	617.3	616.5	615.6	614.8	614.7	614.5	614.4	614.3	614.2	614.2
165°	627.6	626.7	625.8	625.0	624.1	624.1	624.1	624.1	624.1	624.1	624.2
167.5°	635.8	634.9	634.0	633.2	632.3	632.3	632.3	632.3	632.3	632.3	632.5
170°	642.4	641.5	640.6	639.8	638.9	639.0	639.2	639.3	639.4	639.5	639.7
172.5°	647.3	646.4	645.6	644.7	643.9	644.0	644.1	644.2	644.3	644.4	644.6
175°	650.6	649.7	648.9	648.0	647.2	647.4	647.7	647.9	648.2	648.3	648.5
177.5°	652.3	651.6	650.9	650.1	649.4	649.6	649.9	650.1	650.4	650.5	650.7
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	930.5	930.5	930.5	930.5
2.5°	913.3	913.3	924.1	935.5
5°	893.3	898.3	915.5	931.2
7.5°	874.0	882.6	904.1	924.1
10°	850.4	861.9	888.3	911.9
12.5°	827.5	838.3	869.0	895.5
15°	795.3	808.9	841.8	874.7
17.5°	763.2	776.7	816.8	855.4
20°	725.2	743.1	788.2	839.7
22.5°	690.2	712.4	762.4	803.9
25°	651.6	685.9	732.4	786.0
27.5°	617.2	651.6	698.8	753.1
30°	578.6	613.7	662.3	712.4
32.5°	541.4	573.6	620.8	682.3
35°	502.8	533.6	579.3	641.6
37.5°	467.8	497.8	547.9	605.1
40°	433.4	464.9	507.8	565.0
42.5°	401.2	429.1	467.8	525.0
45°	371.9	391.9	427.7	481.4
47.5°	341.2	359.0	391.9	445.6
50°	312.6	327.6	356.2	406.3
52.5°	284.7	297.5	324.0	364.1
55°	259.6	271.8	291.1	330.4
57.5°	233.9	243.2	261.8	293.2
60°	208.8	217.4	232.4	258.2
62.5°	183.8	191.0	205.3	226.0
65°	161.6	167.4	178.1	196.0
67.5°	140.2	143.8	152.3	166.6
70°	119.4	122.3	129.5	140.9
72.5°	97.3	100.1	108.0	115.9
75°	78.7	79.4	85.1	91.5
77.5°	61.5	60.8	65.1	70.1
80°	42.2	44.3	47.9	50.1
82.5°	28.6	29.3	30.8	32.2
85°	15.7	16.5	16.5	18.6
87.5°	6.4	7.2	7.2	7.9
90°	4.9	3.4	2.0	0.5
92.5°	15.0	14.1	13.1	12.1
95°	32.3	31.0	29.8	28.6
97.5°	51.1	50.0	48.9	47.8
100°	72.7	71.8	70.8	69.8
102.5°	95.0	94.3	93.5	92.8
105°	119.2	118.9	118.5	118.1
107.5°	144.9	144.4	143.9	143.4
110°	169.8	169.1	168.3	167.6

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	196.1	195.4	194.6	193.9
115°	222.0	221.3	220.5	219.8
117.5°	248.5	247.6	246.6	245.6
120°	274.3	273.4	272.4	271.4
122.5°	298.7	297.4	296.2	295.0
125°	323.0	321.9	320.8	319.7
127.5°	348.0	346.6	345.3	343.9
130°	371.2	369.6	368.0	366.4
132.5°	395.4	394.1	392.9	391.7
135°	417.7	416.4	415.0	413.7
137.5°	441.2	440.1	439.0	437.9
140°	462.6	461.5	460.4	459.3
142.5°	484.6	483.5	482.4	481.3
145°	504.7	503.8	503.0	502.1
147.5°	524.1	523.0	521.9	520.8
150°	542.2	541.5	540.8	540.1
152.5°	559.3	558.6	557.8	557.1
155°	575.2	574.9	574.5	574.1
157.5°	589.6	589.4	589.1	588.9
160°	602.8	602.6	602.3	602.1
162.5°	614.2	614.2	614.2	614.2
165°	624.3	624.4	624.6	624.7
167.5°	632.9	633.2	633.6	634.0
170°	640.0	640.4	640.7	641.1
172.5°	645.0	645.3	645.7	646.1
175°	648.8	649.2	649.5	649.9
177.5°	651.0	651.4	651.7	652.1
180°	651.0	651.0	651.0	651.0

TEST NUMBER: P998547

CATALOG NUMBER: SA2XXDIP-B485D530UB50-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.47	16.32	16.40	17.27	18.50	12.96	13.81	13.90	14.76	15.99
	3H	16.28	17.04	17.23	18.00	19.25	14.30	15.07	15.25	16.03	17.28
	4H	16.45	17.17	17.41	18.13	19.39	14.77	15.49	15.73	16.45	17.71
	6H	16.49	17.16	17.47	18.12	19.40	15.07	15.74	16.05	16.71	17.98
	8H	16.47	17.10	17.45	18.09	19.36	15.16	15.79	16.14	16.77	18.05
	12H	16.43	17.03	17.42	18.01	19.31	15.20	15.80	16.18	16.78	18.08
4H	2H	15.51	16.23	16.48	17.19	18.46	13.41	14.13	14.37	15.09	16.35
	3H	16.49	17.09	17.47	18.08	19.36	14.87	15.47	15.84	16.46	17.74
	4H	16.76	17.31	17.75	18.30	19.60	15.40	15.95	16.39	16.93	18.24
	6H	16.89	17.36	17.89	18.37	19.67	15.78	16.25	16.78	17.26	18.56
	8H	16.89	17.33	17.89	18.33	19.65	15.89	16.33	16.89	17.33	18.65
	12H	16.86	17.25	17.87	18.27	19.59	15.95	16.34	16.96	17.36	18.68
8H	4H	16.77	17.21	17.77	18.22	19.53	15.54	15.98	16.54	16.98	18.30
	6H	16.95	17.31	17.98	18.36	19.67	15.98	16.34	17.00	17.38	18.69
	8H	16.98	17.30	18.01	18.33	19.66	16.13	16.45	17.16	17.48	18.81
	12H	16.97	17.25	18.00	18.27	19.65	16.22	16.50	17.25	17.53	18.90
12H	4H	16.73	17.13	17.75	18.14	19.46	15.52	15.91	16.53	16.93	18.25
	6H	16.93	17.25	17.96	18.28	19.61	15.98	16.30	17.01	17.33	18.66
	8H	16.96	17.24	18.00	18.27	19.64	16.13	16.41	17.17	17.44	18.81