

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999717

Luminaire Tested: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999717
REPORT IS A COMBINATION OF REPORTS P988272 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2992.0 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999717

CATALOG NUMBER: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P999717

CATALOG NUMBER: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	39	34	38	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12939	12939	12939
5°	12960	12308	12218
10°	12831	11675	11289
15°	12655	10925	10231
20°	12421	10072	9124
25°	12184	9199	8111
30°	11861	8347	7004
35°	11547	7489	6054
40°	11229	6645	5076
45°	10857	5774	4223
50°	10472	4936	3437
55°	10072	4097	2730
60°	9607	3276	2065
65°	9072	2498	1678
70°	8423	1812	1334
75°	7613	1383	1020
80°	6435	936	683
85°	4492	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10857 cd/sqm

TEST NUMBER: P999717

CATALOG NUMBER: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.6	2.6
10°-20°	210.3	7.0
20°-30°	295.2	9.9
30°-40°	321.8	10.8
40°-50°	295.8	9.9
50°-60°	232.3	7.8
60°-70°	151.2	5.1
70°-80°	77.8	2.6
80°-90°	20.7	0.7
90°-100°	14.7	0.5
100°-110°	54.9	1.8
110°-120°	145.7	4.9
120°-130°	241.7	8.1
130°-140°	256.7	8.6
140°-150°	238.6	8.0
150°-160°	191.8	6.4
160°-170°	123.6	4.1
170°-180°	42.5	1.4
0°-30°	582.1	19.5
0°-40°	904.0	30.2
0°-60°	1432.1	47.9
0°-90°	1681.8	56.2
90°-120°	215.4	7.2
90°-150°	952.3	31.8
90°-180°	1310.0	43.8
0°-180°	2992.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	817	817	817	817	817	
5°	817	814	804	811	808	78
15°	777	769	744	730	723	219
25°	706	682	633	603	592	325
35°	608	570	505	459	442	381
45°	497	448	370	317	300	384
55°	378	320	240	196	182	338
65°	255	195	129	104	101	253
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	0	4	6	8	9	3
95°	21	10	13	14	14	25
105°	98	108	20	23	25	105
115°	186	191	200	50	26	183
125°	263	267	273	276	276	234
135°	325	330	333	337	336	251
145°	377	377	383	385	383	236
155°	416	413	416	418	416	191
165°	438	436	437	439	437	124
175°	448	446	446	448	445	43
180°	447	447	447	447	447	

TEST NUMBER: P999717

CATALOG NUMBER: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	817.4	817.4	817.4	817.4	817.4
2.5°	821.1	817.4	809.2	816.6	815.1
5°	817.4	813.7	804.0	810.7	808.5
7.5°	810.7	806.3	795.9	798.9	795.2
10°	801.8	796.6	781.9	779.6	775.2
12.5°	790.7	784.1	764.1	759.7	751.5
15°	777.4	769.3	744.1	730.1	722.7
17.5°	761.9	750.0	719.0	702.7	690.9
20°	744.1	729.3	692.3	673.9	657.6
22.5°	724.9	707.9	665.0	639.8	628.7
25°	705.7	682.0	633.2	602.8	591.8
27.5°	682.7	657.6	603.6	568.8	551.8
30°	658.3	630.2	571.0	533.3	513.3
32.5°	634.7	600.6	540.0	495.6	477.1
35°	608.0	570.3	505.2	458.6	442.3
37.5°	582.1	541.5	472.7	421.6	403.1
40°	554.8	510.4	438.6	386.1	366.9
42.5°	526.7	479.3	404.6	349.9	331.4
45°	497.1	447.5	369.8	317.3	299.6
47.5°	469.0	416.4	336.6	284.0	267.8
50°	437.9	385.4	304.0	253.0	237.4
52.5°	407.6	352.1	272.9	224.1	210.1
55°	378.0	320.3	240.4	196.0	182.0
57.5°	347.7	288.5	211.6	170.1	158.3
60°	316.6	257.4	181.2	143.5	131.7
62.5°	286.3	227.1	155.3	119.8	113.9
65°	255.2	195.3	128.7	103.6	101.3
67.5°	225.6	165.7	103.6	91.0	88.8
70°	194.5	136.8	85.8	78.4	75.4
72.5°	165.0	110.2	71.7	65.8	64.4
75°	136.1	84.3	59.2	54.0	53.3
77.5°	107.3	59.9	46.6	43.6	42.2
80°	80.6	42.9	35.5	32.5	32.5
82.5°	56.2	28.8	24.4	22.9	22.9
85°	31.8	16.3	14.1	14.1	14.1
87.5°	11.8	5.9	5.9	5.2	5.2
90°	0.3	3.9	6.5	8.1	8.7
92.5°	8.1	6.8	7.8	8.4	8.7
95°	21.0	10.3	12.6	14.2	13.9
97.5°	37.8	11.3	16.5	17.5	17.8
100°	57.2	12.9	18.4	21.0	21.7
102.5°	78.6	77.9	19.1	22.6	23.6
105°	98.3	108.0	19.7	23.3	24.6
107.5°	121.3	129.4	20.4	23.9	25.2
110°	143.3	150.1	56.6	24.3	25.5

TEST NUMBER: P999717

CATALOG NUMBER: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.0	169.8	164.3	24.9	25.9
115°	185.9	191.4	199.5	49.8	26.5
117.5°	205.0	211.5	217.0	170.7	86.0
120°	226.4	231.2	237.0	240.9	197.3
122.5°	244.5	249.7	256.1	258.1	258.4
125°	262.9	267.1	273.3	275.5	276.5
127.5°	279.7	284.3	289.1	292.3	292.7
130°	295.6	300.7	304.3	307.9	307.5
132.5°	311.7	315.9	319.5	322.4	322.1
135°	325.3	330.5	333.4	336.6	336.0
137.5°	339.6	343.4	346.7	349.9	348.9
140°	353.5	356.0	359.6	362.5	360.9
142.5°	365.1	367.4	371.6	374.2	372.5
145°	377.4	377.1	382.6	384.8	383.2
147.5°	388.1	387.1	392.6	394.2	392.9
150°	398.4	396.1	401.3	403.3	401.6
152.5°	407.1	404.6	409.4	411.3	409.1
155°	415.6	412.6	416.5	418.5	415.9
157.5°	422.3	419.8	422.7	424.9	422.3
160°	428.2	426.2	428.2	430.1	427.8
162.5°	433.3	431.4	433.0	435.3	432.4
165°	437.9	435.9	436.9	439.2	436.9
167.5°	441.4	439.5	440.5	442.7	439.8
170°	444.3	442.4	443.0	445.3	442.4
172.5°	446.3	444.3	445.0	447.2	444.3
175°	447.9	445.6	446.3	448.5	445.3
177.5°	448.5	446.3	446.6	448.9	446.0
180°	446.9	446.9	446.9	446.9	446.9

(END OF REPORT)