

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998580

Luminaire Tested: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998580
REPORT IS A COMBINATION OF REPORTS P984323 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4667.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	86	83	80	72	69	67	59	57	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39
3	81	72	65	60	74	67	61	56	56	52	48	46	43	41	37	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	24	21	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15318	15318	15318	15318
5°	15354	16332	15413	12993
10°	15176	17829	15272	10713
15°	14809	18805	15014	9023
20°	14577	17657	14577	7843
25°	14112	15170	14178	7013
30°	13348	11925	13604	6353
35°	12671	8246	12882	5813
40°	11892	6226	12028	5382
45°	10933	5116	11112	4916
50°	10103	4491	10120	4501
55°	9156	3826	9217	4049
60°	8148	3196	8260	3535
65°	7245	2599	7376	3018
70°	6344	2040	6505	2434
75°	5326	1481	5533	1765
80°	4160	938	4455	1047
85°	2726	473	2938	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15834 cd/sqm

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	2.0
10°-20°	268.3	5.7
20°-30°	389.3	8.3
30°-40°	410.4	8.8
40°-50°	363.2	7.8
50°-60°	290.0	6.2
60°-70°	197.0	4.2
70°-80°	100.8	2.2
80°-90°	26.4	0.6
90°-100°	56.0	1.2
100°-110°	177.9	3.8
110°-120°	304.4	6.5
120°-130°	400.4	8.6
130°-140°	449.4	9.6
140°-150°	440.7	9.4
150°-160°	369.7	7.9
160°-170°	245.2	5.3
170°-180°	85.7	1.8
0°-30°	749.8	16.1
0°-40°	1160.2	24.9
0°-60°	1813.4	38.9
0°-90°	2137.6	45.8
90°-120°	538.3	11.5
90°-150°	1828.9	39.2
90°-180°	2529.0	54.2
0°-180°	4667.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	968	968	968	968	968	
5°	968	1081	972	860	968	92
15°	910	1328	922	637	910	257
25°	817	1107	821	512	817	374
35°	667	602	678	425	667	417
45°	501	363	509	349	501	388
55°	344	255	346	270	344	307
65°	204	157	208	182	204	203
75°	95	77	99	92	95	102
85°	19	20	21	15	19	23
90°	1	26	1	26	1	4
95°	40	47	40	47	40	44
105°	164	170	164	170	164	173
115°	305	305	305	305	305	302
125°	444	446	444	446	444	397
135°	575	582	575	582	575	444
145°	698	706	698	706	698	436
155°	798	804	798	804	798	367
165°	868	869	868	869	868	245
175°	903	900	903	900	903	86
180°	905	905	905	905	905	

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	972.9	975.1	978.8	979.6	987.0	993.0	999.7	999.7	1001.9	1001.2	995.2
5°	968.4	975.1	984.8	993.0	1006.4	1012.3	1021.2	1027.9	1033.9	1038.3	1037.6
7.5°	961.0	972.9	987.0	1002.6	1020.5	1030.9	1043.5	1055.4	1063.6	1071.1	1076.3
10°	948.3	968.4	987.8	1008.6	1031.6	1045.8	1060.7	1076.3	1088.9	1103.1	1116.4
12.5°	931.2	960.2	984.0	1011.6	1039.8	1055.4	1079.3	1091.2	1115.7	1151.4	1161.1
15°	909.7	949.1	971.4	1006.4	1043.5	1056.2	1088.9	1108.3	1158.8	1181.2	1207.9
17.5°	889.6	933.5	963.2	1003.4	1039.8	1064.4	1096.4	1135.8	1178.2	1210.2	1239.9
20°	873.2	915.6	951.3	995.9	1042.1	1073.3	1106.8	1154.4	1200.5	1233.2	1256.3
22.5°	836.0	890.3	932.0	981.8	1037.6	1080.7	1112.7	1164.8	1214.6	1234.7	1254.8
25°	817.4	864.3	912.6	969.2	1034.6	1085.9	1113.5	1171.5	1215.4	1222.8	1227.3
27.5°	783.2	836.0	892.6	957.3	1033.9	1077.0	1112.0	1164.8	1199.7	1194.5	1181.2
30°	740.8	805.5	868.0	937.9	1023.5	1070.3	1103.1	1151.4	1169.3	1142.5	1118.7
32.5°	709.6	770.6	839.7	920.8	1011.6	1056.2	1088.2	1126.1	1129.8	1081.5	1041.3
35°	667.2	734.9	813.0	898.5	991.5	1031.6	1061.4	1084.5	1066.6	998.9	951.3
37.5°	629.3	696.2	779.5	866.5	964.0	1003.4	1027.2	1030.9	987.0	927.5	857.6
40°	587.6	656.8	743.8	835.3	933.5	967.7	982.6	971.4	908.2	839.0	757.9
42.5°	545.9	614.4	708.1	801.8	894.8	923.8	929.7	899.3	821.9	740.8	647.1
45°	500.6	572.0	665.7	760.2	850.2	866.5	867.3	823.4	731.9	647.1	560.1
47.5°	463.4	529.6	622.6	717.0	792.9	804.0	799.6	749.0	649.3	554.1	478.3
50°	422.5	485.7	577.9	670.9	735.6	738.6	727.4	655.3	557.8	470.8	410.6
52.5°	378.6	442.6	527.4	616.6	674.6	670.2	648.6	571.2	479.7	407.6	361.5
55°	343.6	400.2	479.7	566.8	607.7	595.0	571.2	492.4	420.2	359.3	319.1
57.5°	305.0	354.8	432.9	508.8	532.6	520.7	496.9	423.2	356.3	310.2	283.4
60°	268.5	313.9	382.3	445.5	464.1	451.5	424.0	357.8	309.4	270.7	250.7
62.5°	235.0	274.5	331.7	389.8	397.2	384.5	360.7	307.2	265.5	235.0	220.2
65°	203.8	241.0	287.1	331.0	337.7	324.3	299.8	261.1	226.1	206.8	192.6
67.5°	173.3	203.1	244.0	275.9	279.7	267.0	246.9	215.7	194.1	173.3	162.9
70°	146.5	168.8	200.8	226.9	228.3	216.4	206.0	177.8	161.4	146.5	138.3
72.5°	120.5	136.1	160.7	180.0	180.7	173.3	163.6	145.8	131.7	121.2	113.1
75°	95.2	108.6	123.5	140.6	139.8	133.9	126.4	115.3	103.4	96.7	93.0
77.5°	72.9	81.1	93.0	104.1	104.1	101.2	96.7	88.5	81.1	74.4	70.7
80°	52.1	57.3	66.9	70.7	72.1	71.4	67.7	61.7	58.8	53.6	52.1
82.5°	33.5	37.2	41.7	45.4	47.6	46.1	45.4	42.4	37.9	36.4	35.0
85°	19.3	20.8	23.1	25.3	26.0	25.3	26.8	24.5	22.3	22.3	21.6
87.5°	8.2	8.9	10.4	10.4	11.2	11.2	10.4	11.2	11.2	10.4	9.7
90°	0.8	2.8	4.8	6.9	8.9	9.9	11.8	15.5	19.2	23.0	26.7
92.5°	16.8	18.2	19.5	20.9	22.2	22.9	23.0	23.2	23.3	23.5	23.7
95°	39.7	41.4	43.1	44.8	46.5	47.3	47.5	47.8	48.2	48.5	48.9
97.5°	66.4	67.9	69.5	71.0	72.5	73.3	73.6	74.3	75.0	75.6	76.3
100°	97.0	98.4	99.7	101.1	102.4	103.1	103.4	103.9	104.4	104.9	105.4
102.5°	129.0	130.0	131.0	132.1	133.1	133.6	133.9	134.6	135.3	136.0	136.7
105°	164.1	164.6	165.1	165.6	166.1	166.4	166.6	166.9	167.3	167.6	168.0
107.5°	199.3	200.0	200.6	201.3	202.0	202.3	202.3	202.3	202.3	202.3	202.3
110°	232.9	233.9	234.9	235.9	236.9	237.4	237.4	237.4	237.4	237.4	237.4

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	269.5	270.5	271.5	272.6	273.6	274.1	274.0	273.8	273.7	273.5	273.3
115°	305.4	306.4	307.4	308.5	309.5	310.0	309.8	309.5	309.1	308.8	308.4
117.5°	341.3	342.7	344.0	345.4	346.7	347.4	347.0	346.1	345.3	344.4	343.6
120°	377.2	378.6	379.9	381.3	382.6	383.3	382.6	381.3	379.9	378.6	377.2
122.5°	410.0	411.7	413.4	415.1	416.8	417.6	417.2	416.3	415.5	414.6	413.8
125°	444.3	445.8	447.4	448.9	450.4	451.2	450.9	450.4	449.9	449.4	448.9
127.5°	477.9	479.8	481.6	483.5	485.4	486.3	486.0	485.3	484.6	484.0	483.3
130°	509.2	511.4	513.6	515.9	518.1	519.2	519.0	518.7	518.3	518.0	517.6
132.5°	544.4	546.1	547.8	549.5	551.2	552.0	552.1	552.3	552.4	552.6	552.8
135°	574.9	576.8	578.6	580.5	582.4	583.3	583.5	583.8	584.1	584.5	584.8
137.5°	608.5	610.0	611.6	613.1	614.6	615.4	615.6	615.9	616.2	616.6	616.9
140°	638.3	639.8	641.3	642.8	644.3	645.1	645.5	646.4	647.3	648.1	649.0
142.5°	668.8	670.3	671.9	673.4	674.9	675.7	676.0	676.5	677.0	677.5	678.0
145°	697.8	699.0	700.2	701.4	702.6	703.2	703.7	704.7	705.7	706.7	707.7
147.5°	723.8	725.3	726.8	728.3	729.8	730.6	730.9	731.6	732.3	733.0	733.7
150°	750.5	751.5	752.5	753.6	754.6	755.1	755.4	756.1	756.8	757.4	758.1
152.5°	774.2	775.2	776.2	777.2	778.2	778.7	779.1	780.0	780.9	781.7	782.6
155°	797.8	798.3	798.8	799.3	799.8	800.1	800.4	800.9	801.4	801.9	802.4
157.5°	818.4	818.8	819.1	819.5	819.8	820.0	820.2	820.5	820.8	821.2	821.5
160°	836.8	837.1	837.5	837.8	838.1	838.3	838.4	838.6	838.7	838.9	839.1
162.5°	853.6	853.6	853.6	853.6	853.6	853.6	853.7	853.8	854.0	854.1	854.3
165°	868.1	867.9	867.7	867.6	867.4	867.3	867.3	867.3	867.3	867.3	867.3
167.5°	881.1	880.6	880.1	879.6	879.1	878.8	878.8	878.8	878.8	878.8	878.8
170°	891.0	890.5	890.0	889.5	889.0	888.7	888.6	888.4	888.3	888.1	887.9
172.5°	897.8	897.3	896.8	896.3	895.8	895.6	895.5	895.3	895.2	895.0	894.8
175°	903.2	902.7	902.2	901.7	901.2	900.9	900.7	900.4	900.1	899.7	899.4
177.5°	906.2	905.7	905.2	904.7	904.2	904.0	903.8	903.5	903.1	902.8	902.4
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1005.6	1006.4	1007.8	1015.3	1019.0	1019.7	1016.8	1023.5	1025.7	1023.5	1022.0
5°	1053.2	1057.7	1066.6	1076.3	1075.5	1076.3	1080.7	1085.2	1086.7	1080.7	1083.0
7.5°	1094.9	1103.8	1113.5	1128.3	1128.3	1135.8	1138.8	1142.5	1151.4	1146.9	1145.4
10°	1142.5	1154.4	1172.2	1196.0	1196.8	1204.2	1211.6	1223.5	1227.3	1224.3	1225.8
12.5°	1202.0	1225.0	1226.5	1252.6	1264.5	1265.9	1277.8	1275.6	1283.1	1283.1	1295.7
15°	1228.0	1263.7	1283.8	1309.1	1316.5	1307.6	1317.3	1327.7	1328.4	1328.4	1327.7
17.5°	1274.9	1289.0	1309.1	1322.5	1325.4	1325.4	1326.2	1330.7	1327.7	1321.7	1326.2
20°	1284.5	1290.5	1297.9	1296.4	1297.9	1290.5	1283.1	1275.6	1276.4	1272.6	1283.8
22.5°	1266.7	1265.2	1248.1	1236.9	1236.9	1222.1	1207.9	1201.2	1194.5	1196.8	1200.5
25°	1222.1	1199.0	1178.2	1161.8	1158.1	1134.3	1115.0	1109.0	1097.8	1106.8	1108.3
27.5°	1150.7	1124.6	1091.2	1077.0	1057.7	1048.0	1034.6	1016.8	993.7	1007.1	1004.9
30°	1074.0	1035.4	1007.8	973.6	943.1	940.9	915.6	885.9	874.0	874.0	880.7
32.5°	988.5	937.2	897.0	848.7	818.9	806.3	775.8	746.0	752.7	730.4	738.6
35°	888.8	821.2	770.6	723.7	701.4	686.5	647.1	630.7	612.9	602.5	621.8
37.5°	793.6	715.5	650.8	599.5	591.3	564.5	537.8	527.4	516.9	521.4	520.7
40°	677.6	608.4	550.4	510.2	496.1	483.5	465.6	453.0	446.3	450.0	450.7
42.5°	572.7	514.7	471.6	443.3	431.4	422.5	413.6	403.1	400.9	400.9	403.9
45°	491.7	444.0	415.0	392.0	385.3	378.6	371.9	367.4	365.9	363.0	365.2
47.5°	426.9	389.0	371.2	354.0	346.6	345.1	339.2	336.9	334.0	333.2	334.0
50°	372.6	348.8	332.5	322.8	317.6	315.4	312.4	307.9	306.4	310.2	308.7
52.5°	334.7	312.4	303.5	293.8	290.8	287.8	283.4	284.1	283.4	281.9	281.9
55°	296.8	282.6	273.7	266.3	265.5	262.6	258.8	257.4	256.6	255.1	257.4
57.5°	266.3	255.1	246.9	240.2	237.3	237.3	233.6	230.6	230.6	229.8	230.6
60°	235.8	224.6	219.4	212.7	210.5	209.8	207.5	206.0	203.8	203.8	203.8
62.5°	207.5	198.6	192.6	186.7	187.4	183.7	180.7	179.3	179.3	180.0	180.0
65°	180.7	174.8	167.4	162.1	160.7	159.9	158.4	157.7	155.5	156.9	156.9
67.5°	156.2	148.0	143.6	141.3	139.1	138.3	136.9	135.4	134.6	133.9	135.4
70°	131.7	125.0	121.2	119.8	117.5	116.8	116.0	113.8	114.5	115.3	116.0
72.5°	109.3	103.4	102.6	98.2	98.2	98.2	95.2	96.7	95.9	94.5	95.9
75°	86.3	83.3	81.8	79.6	80.3	79.6	78.8	76.6	76.6	77.4	78.1
77.5°	68.4	65.5	64.7	62.5	61.0	62.5	61.0	60.2	60.2	61.0	61.0
80°	50.6	49.1	46.9	46.9	46.9	46.1	46.1	46.1	45.4	44.6	45.4
82.5°	33.5	33.5	32.7	32.0	32.7	31.2	32.0	32.0	32.0	32.0	32.0
85°	21.6	20.8	20.8	20.1	20.1	20.1	20.8	19.3	19.3	20.1	20.1
87.5°	9.7	9.7	9.7	10.4	9.7	9.7	9.7	10.4	9.7	9.7	9.7
90°	26.4	26.0	25.7	25.4	25.2	25.3	25.5	25.6	25.8	26.0	25.8
92.5°	23.9	24.0	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.4	24.4
95°	48.9	48.9	48.9	48.9	48.9	48.7	48.4	48.0	47.7	47.3	47.7
97.5°	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3
100°	105.4	105.4	105.4	105.4	105.4	105.3	105.1	105.0	104.8	104.6	104.8
102.5°	136.9	137.0	137.2	137.3	137.4	137.3	137.2	137.0	136.9	136.7	136.9
105°	168.3	168.7	169.0	169.3	169.5	169.5	169.5	169.5	169.5	169.5	169.5
107.5°	202.5	202.7	202.8	203.0	203.1	202.7	201.8	201.0	200.1	199.3	200.1
110°	237.4	237.4	237.4	237.4	237.4	237.2	236.7	236.2	235.7	235.2	235.7

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	272.8	272.3	271.8	271.3	271.0	270.8	270.5	270.2	269.8	269.5	269.8
115°	308.2	308.1	307.9	307.8	307.7	307.4	306.9	306.4	305.9	305.4	305.9
117.5°	343.1	342.6	342.1	341.6	341.3	341.0	340.5	340.0	339.5	339.0	339.5
120°	377.2	377.2	377.2	377.2	377.2	376.9	376.4	375.9	375.4	374.9	375.4
122.5°	413.3	412.8	412.3	411.8	411.5	411.3	411.0	410.7	410.3	410.0	410.3
125°	448.4	447.9	447.4	446.9	446.6	446.5	446.4	446.2	446.1	445.9	446.1
127.5°	482.6	481.9	481.2	480.5	480.2	479.9	479.4	478.9	478.4	477.9	478.4
130°	517.3	516.9	516.6	516.3	516.1	515.8	515.1	514.4	513.8	513.1	513.8
132.5°	551.9	551.1	550.2	549.3	548.9	548.6	548.1	547.6	547.1	546.6	547.1
135°	584.6	584.5	584.3	584.2	584.1	583.8	583.3	582.8	582.3	581.8	582.3
137.5°	616.7	616.5	616.4	616.2	616.1	615.8	615.1	614.4	613.8	613.1	613.8
140°	649.0	649.0	649.0	649.0	649.0	648.7	648.0	647.3	646.6	645.9	646.6
142.5°	678.2	678.3	678.5	678.6	678.7	678.4	677.7	677.0	676.4	675.7	676.4
145°	707.9	708.1	708.2	708.4	708.5	708.2	707.5	706.8	706.2	705.5	706.2
147.5°	734.0	734.4	734.7	735.0	735.2	734.9	734.2	733.5	732.9	732.2	732.9
150°	758.6	759.1	759.6	760.1	760.4	760.1	759.6	759.1	758.6	758.1	758.6
152.5°	783.3	783.9	784.6	785.3	785.6	785.3	784.6	783.9	783.3	782.6	783.3
155°	803.2	804.1	804.9	805.8	806.2	805.9	805.4	804.9	804.4	803.9	804.4
157.5°	822.7	823.9	825.0	826.2	826.8	826.4	825.5	824.7	823.8	823.0	823.8
160°	840.1	841.1	842.1	843.1	843.6	843.3	842.6	841.9	841.3	840.6	841.3
162.5°	855.5	856.7	857.9	859.1	859.7	859.3	858.4	857.6	856.7	855.9	856.7
165°	868.5	869.7	870.9	872.1	872.7	872.3	871.4	870.5	869.7	868.8	869.7
167.5°	880.0	881.2	882.3	883.5	884.1	883.7	882.8	882.0	881.1	880.3	881.1
170°	889.1	890.3	891.5	892.7	893.3	892.8	891.8	890.7	889.7	888.7	889.7
172.5°	896.0	897.2	898.3	899.5	900.1	899.6	898.6	897.6	896.6	895.6	896.6
175°	900.6	901.8	902.9	904.1	904.7	904.2	903.2	902.1	901.1	900.1	901.1
177.5°	903.4	904.4	905.5	906.5	907.0	906.5	905.5	904.4	903.4	902.4	903.4
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1025.7	1020.5	1016.0	1016.8	1020.5	1017.5	1010.1	1000.4	996.7	992.2	996.7
5°	1087.4	1083.0	1074.0	1074.8	1072.6	1069.6	1057.7	1042.8	1042.8	1030.9	1029.4
7.5°	1148.4	1141.7	1135.8	1134.3	1126.1	1120.2	1109.7	1088.9	1080.7	1066.6	1058.4
10°	1216.9	1211.6	1205.0	1196.8	1192.3	1181.9	1164.8	1134.3	1119.4	1100.1	1085.9
12.5°	1286.0	1285.3	1270.4	1254.0	1253.3	1236.9	1225.0	1184.1	1164.0	1138.0	1104.5
15°	1329.9	1326.2	1318.0	1309.8	1312.1	1294.2	1267.4	1219.1	1205.7	1174.5	1138.8
17.5°	1329.2	1329.2	1326.9	1325.4	1323.2	1318.0	1303.1	1271.2	1249.6	1210.2	1176.7
20°	1286.8	1296.4	1298.7	1297.9	1305.4	1309.1	1308.3	1288.3	1271.2	1236.2	1202.0
22.5°	1202.0	1224.3	1234.0	1239.9	1255.5	1263.7	1283.1	1275.6	1271.2	1245.1	1216.1
25°	1123.1	1130.6	1159.6	1161.1	1182.6	1202.7	1222.1	1234.7	1251.1	1241.4	1216.9
27.5°	1021.2	1038.3	1059.2	1074.8	1079.3	1120.2	1152.1	1175.9	1213.1	1216.1	1207.9
30°	905.9	914.1	948.3	969.2	993.0	1022.7	1068.8	1109.7	1143.2	1173.7	1184.1
32.5°	765.4	798.8	818.9	844.2	865.0	917.8	974.4	1027.2	1065.9	1117.2	1139.5
35°	636.7	662.7	696.9	707.4	745.3	789.9	863.5	931.2	990.0	1042.1	1087.4
37.5°	530.3	551.2	587.6	604.0	626.3	683.6	745.3	829.3	900.0	964.0	1020.5
40°	457.4	473.1	500.6	505.8	524.4	576.4	626.3	705.1	798.8	885.1	946.9
42.5°	407.6	415.0	433.6	440.3	452.2	487.2	531.8	606.2	693.2	782.5	869.5
45°	371.9	377.1	388.3	394.2	409.1	424.7	461.2	520.7	589.1	679.1	772.8
47.5°	339.9	346.6	351.1	354.8	363.0	380.1	403.9	447.8	513.2	595.8	686.5
50°	313.1	315.4	323.6	324.3	329.5	340.7	363.0	389.8	441.8	508.8	596.5
52.5°	286.4	288.6	293.8	299.0	301.2	310.2	325.0	347.4	386.0	438.8	516.9
55°	259.6	262.6	267.8	271.5	273.7	281.2	290.1	311.7	342.1	379.3	443.3
57.5°	232.8	239.5	241.0	243.2	246.9	255.1	263.3	275.9	299.8	334.0	380.8
60°	207.5	209.8	215.0	217.2	220.9	225.4	235.8	245.5	262.6	289.3	331.7
62.5°	181.5	186.7	188.9	191.2	194.1	199.3	206.0	216.4	231.3	252.9	286.4
65°	159.2	159.9	164.4	167.4	170.3	174.0	180.7	190.4	199.3	219.4	244.0
67.5°	137.6	139.1	140.6	143.6	147.3	151.0	156.9	162.1	173.3	186.7	206.0
70°	116.8	116.8	120.5	122.7	122.0	126.4	130.9	136.9	145.0	157.7	173.3
72.5°	98.2	97.4	100.4	101.2	102.6	105.6	108.6	114.5	119.0	128.7	140.6
75°	78.1	79.6	81.1	81.1	83.3	85.5	88.5	91.5	96.7	102.6	111.6
77.5°	61.7	61.7	63.2	64.0	66.2	65.5	68.4	71.4	75.1	80.3	87.0
80°	45.4	46.9	46.9	46.9	47.6	48.3	51.3	53.6	55.8	59.5	62.5
82.5°	32.0	32.0	33.5	33.5	33.5	35.0	35.0	35.7	37.2	39.4	41.7
85°	20.1	20.1	20.1	20.8	20.1	20.8	22.3	21.6	22.3	23.8	23.8
87.5°	9.7	9.7	9.7	9.7	9.7	10.4	9.7	10.4	11.2	11.2	11.2
90°	25.6	25.5	25.3	25.2	25.4	25.7	26.0	26.4	26.7	23.0	19.2
92.5°	24.4	24.4	24.4	24.4	24.3	24.2	24.0	23.9	23.7	23.5	23.3
95°	48.0	48.4	48.7	48.9	48.9	48.9	48.9	48.9	48.9	48.5	48.2
97.5°	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	75.6	75.0
100°	105.0	105.1	105.3	105.4	105.4	105.4	105.4	105.4	105.4	104.9	104.4
102.5°	137.0	137.2	137.3	137.4	137.3	137.2	137.0	136.9	136.7	136.0	135.3
105°	169.5	169.5	169.5	169.5	169.3	169.0	168.7	168.3	168.0	167.6	167.3
107.5°	201.0	201.8	202.7	203.1	203.0	202.8	202.7	202.5	202.3	202.3	202.3
110°	236.2	236.7	237.2	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	270.2	270.5	270.8	271.0	271.3	271.8	272.3	272.8	273.3	273.5	273.7
115°	306.4	306.9	307.4	307.7	307.8	307.9	308.1	308.2	308.4	308.8	309.1
117.5°	340.0	340.5	341.0	341.3	341.6	342.1	342.6	343.1	343.6	344.4	345.3
120°	375.9	376.4	376.9	377.2	377.2	377.2	377.2	377.2	377.2	378.6	379.9
122.5°	410.7	411.0	411.3	411.5	411.8	412.3	412.8	413.3	413.8	414.6	415.5
125°	446.2	446.4	446.5	446.6	446.9	447.4	447.9	448.4	448.9	449.4	449.9
127.5°	478.9	479.4	479.9	480.2	480.5	481.2	481.9	482.6	483.3	484.0	484.6
130°	514.4	515.1	515.8	516.1	516.3	516.6	516.9	517.3	517.6	518.0	518.3
132.5°	547.6	548.1	548.6	548.9	549.3	550.2	551.1	551.9	552.8	552.6	552.4
135°	582.8	583.3	583.8	584.1	584.2	584.3	584.5	584.6	584.8	584.5	584.1
137.5°	614.4	615.1	615.8	616.1	616.2	616.4	616.5	616.7	616.9	616.6	616.2
140°	647.3	648.0	648.7	649.0	649.0	649.0	649.0	649.0	649.0	648.1	647.3
142.5°	677.0	677.7	678.4	678.7	678.6	678.5	678.3	678.2	678.0	677.5	677.0
145°	706.8	707.5	708.2	708.5	708.4	708.2	708.1	707.9	707.7	706.7	705.7
147.5°	733.5	734.2	734.9	735.2	735.0	734.7	734.4	734.0	733.7	733.0	732.3
150°	759.1	759.6	760.1	760.4	760.1	759.6	759.1	758.6	758.1	757.4	756.8
152.5°	783.9	784.6	785.3	785.6	785.3	784.6	783.9	783.3	782.6	781.7	780.9
155°	804.9	805.4	805.9	806.2	805.8	804.9	804.1	803.2	802.4	801.9	801.4
157.5°	824.7	825.5	826.4	826.8	826.2	825.0	823.9	822.7	821.5	821.2	820.8
160°	841.9	842.6	843.3	843.6	843.1	842.1	841.1	840.1	839.1	838.9	838.7
162.5°	857.6	858.4	859.3	859.7	859.1	857.9	856.7	855.5	854.3	854.1	854.0
165°	870.5	871.4	872.3	872.7	872.1	870.9	869.7	868.5	867.3	867.3	867.3
167.5°	882.0	882.8	883.7	884.1	883.5	882.3	881.2	880.0	878.8	878.8	878.8
170°	890.7	891.8	892.8	893.3	892.7	891.5	890.3	889.1	887.9	888.1	888.3
172.5°	897.6	898.6	899.6	900.1	899.5	898.3	897.2	896.0	894.8	895.0	895.2
175°	902.1	903.2	904.2	904.7	904.1	902.9	901.8	900.6	899.4	899.7	900.1
177.5°	904.4	905.5	906.5	907.0	906.5	905.5	904.4	903.4	902.4	902.8	903.1
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	993.0	989.3	987.0	988.5	984.0	972.9	972.9	976.6	972.1	967.7	961.0
5°	1020.5	1013.1	1008.6	1007.8	997.4	979.6	975.9	972.1	962.5	952.1	940.9
7.5°	1047.3	1033.9	1026.4	1021.2	1006.4	983.3	973.6	965.5	949.8	934.2	920.1
10°	1069.6	1050.2	1041.3	1033.1	1013.8	984.8	969.2	954.3	934.2	914.1	896.3
12.5°	1087.4	1065.1	1054.0	1042.1	1018.3	980.3	961.0	937.2	917.1	890.3	872.5
15°	1117.2	1071.1	1060.7	1049.5	1025.0	972.9	949.1	922.3	894.8	859.1	839.7
17.5°	1141.0	1079.3	1078.5	1054.7	1022.7	969.9	933.5	898.5	868.8	833.1	802.6
20°	1155.1	1091.9	1080.0	1055.4	1015.3	949.8	911.9	873.2	841.2	798.1	767.6
22.5°	1167.0	1109.7	1078.5	1048.8	999.7	943.1	887.4	850.9	807.0	760.2	731.2
25°	1171.5	1113.5	1080.7	1046.5	988.5	923.8	860.6	821.2	772.1	729.7	690.2
27.5°	1172.2	1112.7	1072.6	1036.9	972.9	898.5	833.8	792.1	737.8	688.8	649.3
30°	1164.8	1104.5	1068.1	1029.4	958.0	875.5	801.1	755.0	696.9	647.8	606.9
32.5°	1142.5	1088.2	1058.4	1016.0	938.7	843.5	769.8	718.5	657.5	609.2	569.7
35°	1105.3	1068.1	1035.4	995.9	913.4	813.7	738.6	678.3	616.6	570.5	533.3
37.5°	1059.2	1039.1	1008.6	969.9	884.4	786.9	703.6	636.7	575.0	530.3	493.9
40°	996.7	1001.9	972.1	937.2	850.2	750.5	658.3	594.3	536.3	494.6	458.9
42.5°	929.0	950.6	933.5	900.0	812.2	710.3	624.8	554.1	497.6	454.5	424.7
45°	856.1	893.3	882.9	858.3	772.8	667.9	577.2	508.8	458.9	417.3	391.2
47.5°	776.5	829.3	829.3	811.5	728.9	625.5	536.3	466.4	417.3	387.5	362.2
50°	695.5	755.0	764.6	752.7	679.8	577.2	486.4	423.2	380.8	351.8	333.2
52.5°	610.7	679.8	697.7	691.7	627.8	531.1	445.5	383.8	345.1	319.8	303.5
55°	529.6	609.9	629.3	631.5	572.0	480.5	400.2	345.9	308.7	291.6	277.4
57.5°	453.0	530.3	551.9	555.6	515.5	434.4	357.8	310.2	276.7	262.6	251.4
60°	387.5	452.2	480.5	488.7	453.7	380.8	318.3	272.2	246.9	233.6	223.1
62.5°	334.0	386.0	415.8	418.0	402.4	334.0	277.4	238.8	217.2	205.3	200.1
65°	281.9	328.8	346.6	355.5	342.9	289.3	239.5	207.5	190.4	180.0	174.8
67.5°	240.2	270.0	284.9	296.8	284.1	244.0	203.8	177.8	165.1	154.7	151.7
70°	197.1	221.7	232.8	244.7	233.6	203.1	174.0	150.2	139.1	130.9	127.2
72.5°	157.7	177.0	187.4	194.9	188.2	162.9	139.1	122.7	114.5	108.6	106.4
75°	125.0	138.3	144.3	149.5	146.5	127.2	112.3	98.9	91.5	86.3	84.8
77.5°	95.2	104.9	111.6	113.1	109.3	96.7	84.0	75.9	69.9	66.9	65.5
80°	67.7	73.6	77.4	79.6	75.9	70.7	61.7	55.8	50.6	46.9	46.1
82.5°	45.4	48.3	51.3	50.6	49.1	44.6	39.4	36.4	34.2	31.2	31.2
85°	26.0	26.8	28.3	29.0	28.3	25.3	22.3	20.8	19.3	17.1	17.1
87.5°	11.2	11.9	11.9	12.6	11.2	11.2	9.7	8.2	8.2	7.4	6.7
90°	15.5	11.8	9.9	8.9	6.9	4.8	2.8	0.8	2.8	4.8	6.9
92.5°	23.2	23.0	22.9	22.2	20.9	19.5	18.2	16.8	18.2	19.5	20.9
95°	47.8	47.5	47.3	46.5	44.8	43.1	41.4	39.7	41.4	43.1	44.8
97.5°	74.3	73.6	73.3	72.5	71.0	69.5	67.9	66.4	67.9	69.5	71.0
100°	103.9	103.4	103.1	102.4	101.1	99.7	98.4	97.0	98.4	99.7	101.1
102.5°	134.6	133.9	133.6	133.1	132.1	131.0	130.0	129.0	130.0	131.0	132.1
105°	166.9	166.6	166.4	166.1	165.6	165.1	164.6	164.1	164.6	165.1	165.6
107.5°	202.3	202.3	202.3	202.0	201.3	200.6	200.0	199.3	200.0	200.6	201.3
110°	237.4	237.4	237.4	236.9	235.9	234.9	233.9	232.9	233.9	234.9	235.9

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	273.8	274.0	274.1	273.6	272.6	271.5	270.5	269.5	270.5	271.5	272.6
115°	309.5	309.8	310.0	309.5	308.5	307.4	306.4	305.4	306.4	307.4	308.5
117.5°	346.1	347.0	347.4	346.7	345.4	344.0	342.7	341.3	342.7	344.0	345.4
120°	381.3	382.6	383.3	382.6	381.3	379.9	378.6	377.2	378.6	379.9	381.3
122.5°	416.3	417.2	417.6	416.8	415.1	413.4	411.7	410.0	411.7	413.4	415.1
125°	450.4	450.9	451.2	450.4	448.9	447.4	445.8	444.3	445.8	447.4	448.9
127.5°	485.3	486.0	486.3	485.4	483.5	481.6	479.8	477.9	479.8	481.6	483.5
130°	518.7	519.0	519.2	518.1	515.9	513.6	511.4	509.2	511.4	513.6	515.9
132.5°	552.3	552.1	552.0	551.2	549.5	547.8	546.1	544.4	546.1	547.8	549.5
135°	583.8	583.5	583.3	582.4	580.5	578.6	576.8	574.9	576.8	578.6	580.5
137.5°	615.9	615.6	615.4	614.6	613.1	611.6	610.0	608.5	610.0	611.6	613.1
140°	646.4	645.5	645.1	644.3	642.8	641.3	639.8	638.3	639.8	641.3	642.8
142.5°	676.5	676.0	675.7	674.9	673.4	671.9	670.3	668.8	670.3	671.9	673.4
145°	704.7	703.7	703.2	702.6	701.4	700.2	699.0	697.8	699.0	700.2	701.4
147.5°	731.6	730.9	730.6	729.8	728.3	726.8	725.3	723.8	725.3	726.8	728.3
150°	756.1	755.4	755.1	754.6	753.6	752.5	751.5	750.5	751.5	752.5	753.6
152.5°	780.0	779.1	778.7	778.2	777.2	776.2	775.2	774.2	775.2	776.2	777.2
155°	800.9	800.4	800.1	799.8	799.3	798.8	798.3	797.8	798.3	798.8	799.3
157.5°	820.5	820.2	820.0	819.8	819.5	819.1	818.8	818.4	818.8	819.1	819.5
160°	838.6	838.4	838.3	838.1	837.8	837.5	837.1	836.8	837.1	837.5	837.8
162.5°	853.8	853.7	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.6
165°	867.3	867.3	867.3	867.4	867.6	867.7	867.9	868.1	867.9	867.7	867.6
167.5°	878.8	878.8	878.8	879.1	879.6	880.1	880.6	881.1	880.6	880.1	879.6
170°	888.4	888.6	888.7	889.0	889.5	890.0	890.5	891.0	890.5	890.0	889.5
172.5°	895.3	895.5	895.6	895.8	896.3	896.8	897.3	897.8	897.3	896.8	896.3
175°	900.4	900.7	900.9	901.2	901.7	902.2	902.7	903.2	902.7	902.2	901.7
177.5°	903.5	903.8	904.0	904.2	904.7	905.2	905.7	906.2	905.7	905.2	904.7
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	957.3	961.0	960.2	952.8	944.6	937.9	925.3	926.8	922.3	923.1	927.5
5°	933.5	933.5	930.5	920.1	906.7	899.3	885.1	881.4	872.5	871.7	871.0
7.5°	908.2	904.5	900.7	885.9	869.5	857.6	838.3	833.8	824.9	818.9	815.9
10°	878.4	873.2	865.8	848.7	828.6	813.7	793.6	787.7	770.6	763.1	758.7
12.5°	845.7	842.7	830.8	816.7	784.0	767.6	738.6	744.5	727.4	712.6	710.3
15°	813.0	801.8	795.1	772.1	732.6	725.2	702.1	690.2	674.6	662.7	662.7
17.5°	781.0	763.9	749.0	724.5	695.5	674.6	657.5	651.6	632.2	620.3	618.1
20°	738.6	719.3	715.5	680.6	660.5	637.4	621.1	606.2	592.1	586.9	583.1
22.5°	698.4	676.1	670.2	640.4	620.3	597.3	580.9	570.5	560.1	556.4	549.7
25°	655.3	641.9	633.0	601.0	578.7	557.1	545.9	538.5	528.8	528.1	523.6
27.5°	613.6	601.0	592.1	561.6	545.2	525.1	516.2	508.0	502.8	500.6	498.3
30°	577.9	563.8	553.4	531.1	511.0	494.6	487.2	482.0	479.0	475.3	474.5
32.5°	538.5	530.3	516.2	499.1	483.5	467.8	463.4	459.7	455.2	453.7	453.0
35°	505.0	493.9	485.0	465.6	458.9	445.5	440.3	437.4	431.4	429.9	428.4
37.5°	472.3	461.9	452.2	440.3	427.7	420.2	417.3	412.8	409.8	410.6	409.1
40°	439.6	431.4	424.0	411.3	403.9	400.2	394.2	389.8	388.3	389.0	388.3
42.5°	407.6	400.2	395.7	386.0	378.6	374.9	371.2	366.7	368.9	368.9	371.2
45°	378.6	371.9	368.9	361.5	357.0	351.1	347.4	346.6	349.6	348.8	348.8
47.5°	348.8	346.6	342.9	336.2	330.2	326.5	325.8	325.8	328.8	330.2	329.5
50°	325.8	321.3	316.9	311.7	307.2	305.7	303.5	305.0	307.9	307.9	309.4
52.5°	296.8	293.8	292.3	287.8	284.9	284.9	284.9	285.6	287.8	290.1	289.3
55°	271.5	269.3	267.8	265.5	261.8	262.6	261.8	263.3	265.5	267.8	269.3
57.5°	244.7	244.0	242.5	238.8	238.8	238.0	240.2	241.0	244.7	246.2	248.4
60°	220.9	218.7	218.7	215.7	215.7	215.7	217.9	220.2	223.1	223.9	225.4
62.5°	195.6	195.6	194.9	192.6	192.6	194.9	195.6	198.6	200.1	200.1	202.3
65°	171.8	171.1	170.3	171.1	171.8	171.8	174.0	175.5	177.0	177.8	178.5
67.5°	148.0	147.3	148.8	148.0	149.5	152.5	151.7	154.0	156.2	156.2	156.9
70°	125.7	127.2	126.4	127.9	127.2	128.7	130.9	131.7	131.7	132.4	134.6
72.5°	104.9	104.9	104.9	104.1	104.9	106.4	107.9	108.6	110.1	110.8	113.1
75°	84.8	84.8	83.3	84.8	84.8	86.3	87.8	87.8	87.8	89.3	91.5
77.5°	64.0	64.7	64.0	65.5	65.5	66.2	67.7	66.9	68.4	69.2	69.9
80°	46.9	46.1	46.1	46.1	46.9	46.9	48.3	49.1	49.1	51.3	49.8
82.5°	29.8	30.5	29.8	30.5	30.5	31.2	30.5	31.2	32.0	33.5	32.7
85°	17.1	16.4	16.4	17.1	16.4	16.4	17.1	16.4	17.1	16.4	17.1
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	8.9	9.9	11.8	15.5	19.2	23.0	26.7	26.4	26.0	25.7	25.4
92.5°	22.2	22.9	23.0	23.2	23.3	23.5	23.7	23.9	24.0	24.2	24.3
95°	46.5	47.3	47.5	47.8	48.2	48.5	48.9	48.9	48.9	48.9	48.9
97.5°	72.5	73.3	73.6	74.3	75.0	75.6	76.3	76.3	76.3	76.3	76.3
100°	102.4	103.1	103.4	103.9	104.4	104.9	105.4	105.4	105.4	105.4	105.4
102.5°	133.1	133.6	133.9	134.6	135.3	136.0	136.7	136.9	137.0	137.2	137.3
105°	166.1	166.4	166.6	166.9	167.3	167.6	168.0	168.3	168.7	169.0	169.3
107.5°	202.0	202.3	202.3	202.3	202.3	202.3	202.3	202.5	202.7	202.8	203.0
110°	236.9	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	273.6	274.1	274.0	273.8	273.7	273.5	273.3	272.8	272.3	271.8	271.3
115°	309.5	310.0	309.8	309.5	309.1	308.8	308.4	308.2	308.1	307.9	307.8
117.5°	346.7	347.4	347.0	346.1	345.3	344.4	343.6	343.1	342.6	342.1	341.6
120°	382.6	383.3	382.6	381.3	379.9	378.6	377.2	377.2	377.2	377.2	377.2
122.5°	416.8	417.6	417.2	416.3	415.5	414.6	413.8	413.3	412.8	412.3	411.8
125°	450.4	451.2	450.9	450.4	449.9	449.4	448.9	448.4	447.9	447.4	446.9
127.5°	485.4	486.3	486.0	485.3	484.6	484.0	483.3	482.6	481.9	481.2	480.5
130°	518.1	519.2	519.0	518.7	518.3	518.0	517.6	517.3	516.9	516.6	516.3
132.5°	551.2	552.0	552.1	552.3	552.4	552.6	552.8	551.9	551.1	550.2	549.3
135°	582.4	583.3	583.5	583.8	584.1	584.5	584.8	584.6	584.5	584.3	584.2
137.5°	614.6	615.4	615.6	615.9	616.2	616.6	616.9	616.7	616.5	616.4	616.2
140°	644.3	645.1	645.5	646.4	647.3	648.1	649.0	649.0	649.0	649.0	649.0
142.5°	674.9	675.7	676.0	676.5	677.0	677.5	678.0	678.2	678.3	678.5	678.6
145°	702.6	703.2	703.7	704.7	705.7	706.7	707.7	707.9	708.1	708.2	708.4
147.5°	729.8	730.6	730.9	731.6	732.3	733.0	733.7	734.0	734.4	734.7	735.0
150°	754.6	755.1	755.4	756.1	756.8	757.4	758.1	758.6	759.1	759.6	760.1
152.5°	778.2	778.7	779.1	780.0	780.9	781.7	782.6	783.3	783.9	784.6	785.3
155°	799.8	800.1	800.4	800.9	801.4	801.9	802.4	803.2	804.1	804.9	805.8
157.5°	819.8	820.0	820.2	820.5	820.8	821.2	821.5	822.7	823.9	825.0	826.2
160°	838.1	838.3	838.4	838.6	838.7	838.9	839.1	840.1	841.1	842.1	843.1
162.5°	853.6	853.6	853.7	853.8	854.0	854.1	854.3	855.5	856.7	857.9	859.1
165°	867.4	867.3	867.3	867.3	867.3	867.3	867.3	868.5	869.7	870.9	872.1
167.5°	879.1	878.8	878.8	878.8	878.8	878.8	878.8	880.0	881.2	882.3	883.5
170°	889.0	888.7	888.6	888.4	888.3	888.1	887.9	889.1	890.3	891.5	892.7
172.5°	895.8	895.6	895.5	895.3	895.2	895.0	894.8	896.0	897.2	898.3	899.5
175°	901.2	900.9	900.7	900.4	900.1	899.7	899.4	900.6	901.8	902.9	904.1
177.5°	904.2	904.0	903.8	903.5	903.1	902.8	902.4	903.4	904.4	905.5	906.5
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	922.3	924.5	919.3	917.8	919.3	914.1	915.6	917.1	917.1	919.3	920.8
5°	868.8	865.8	860.6	859.1	857.6	859.8	858.3	860.6	861.3	866.5	867.3
7.5°	815.9	811.5	807.0	802.6	801.1	797.4	801.1	801.1	806.3	804.8	808.5
10°	753.5	752.7	746.8	744.5	741.6	735.6	743.8	741.6	745.3	752.0	753.5
12.5°	707.4	699.2	702.9	692.5	696.2	690.2	691.0	691.0	696.9	697.7	696.2
15°	663.5	656.8	647.1	642.6	640.4	637.4	647.1	647.8	643.4	653.8	650.1
17.5°	618.8	618.8	609.9	607.7	601.7	604.7	603.2	604.0	602.5	609.9	613.6
20°	580.2	576.4	573.5	574.2	566.8	565.3	563.8	565.3	570.5	575.7	577.2
22.5°	548.9	546.7	539.3	540.7	534.8	537.0	535.5	539.3	540.0	540.0	545.2
25°	519.2	516.2	516.9	514.0	511.7	511.7	509.5	511.7	514.7	516.2	516.9
27.5°	496.9	494.6	490.9	488.7	490.2	486.4	489.4	491.7	491.7	490.2	491.7
30°	470.1	471.6	471.6	464.1	467.1	465.6	467.8	469.3	469.3	470.1	468.6
32.5°	452.2	447.8	447.0	446.3	446.3	443.3	443.3	445.5	446.3	447.0	449.3
35°	428.4	428.4	424.7	426.9	424.0	424.7	424.0	424.7	426.2	424.0	426.2
37.5°	406.9	407.6	406.1	407.6	408.3	406.9	405.4	408.3	406.9	406.9	405.4
40°	388.3	387.5	388.3	388.3	388.3	389.0	387.5	387.5	387.5	386.0	384.5
42.5°	372.6	368.2	369.7	370.4	368.2	368.2	368.9	368.2	370.4	365.9	365.9
45°	350.3	348.8	349.6	349.6	351.1	348.8	350.3	351.1	348.8	348.1	346.6
47.5°	330.2	331.7	330.2	331.7	331.7	333.2	330.2	331.0	331.7	328.8	326.5
50°	310.2	310.2	312.4	311.7	312.4	310.9	310.9	310.2	310.9	309.4	307.2
52.5°	291.6	289.3	293.1	292.3	291.6	290.8	290.1	290.8	289.3	287.8	287.8
55°	268.5	268.5	270.7	271.5	271.5	270.0	268.5	269.3	268.5	267.8	267.0
57.5°	249.9	246.9	248.4	249.2	249.2	246.9	248.4	246.9	246.9	247.7	245.5
60°	226.1	226.1	224.6	226.9	226.9	225.4	225.4	226.1	224.6	223.9	223.1
62.5°	200.8	201.6	203.8	204.5	205.3	203.8	202.3	203.1	203.1	200.8	201.6
65°	179.3	180.7	183.7	183.0	181.5	182.2	180.7	181.5	179.3	180.0	177.8
67.5°	158.4	157.7	158.4	158.4	159.9	159.2	157.7	157.7	156.9	159.2	156.9
70°	136.1	136.1	136.1	136.1	136.9	137.6	136.1	134.6	135.4	133.9	133.1
72.5°	113.1	113.8	113.1	114.5	112.3	113.8	113.8	113.1	112.3	112.3	112.3
75°	91.5	93.0	90.7	91.5	90.7	92.2	91.5	91.5	90.0	89.3	90.0
77.5°	69.9	70.7	69.2	69.9	69.2	69.9	69.9	69.2	69.2	69.2	69.2
80°	49.8	50.6	49.8	49.1	48.3	49.8	48.3	49.1	49.8	49.1	50.6
82.5°	32.0	32.0	31.2	32.0	30.5	30.5	31.2	31.2	30.5	32.0	30.5
85°	15.6	15.6	17.1	15.6	14.9	14.9	14.9	15.6	14.9	16.4	15.6
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	25.2	25.3	25.5	25.6	25.8	26.0	25.8	25.6	25.5	25.3	25.2
92.5°	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4
95°	48.9	48.7	48.4	48.0	47.7	47.3	47.7	48.0	48.4	48.7	48.9
97.5°	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3
100°	105.4	105.3	105.1	105.0	104.8	104.6	104.8	105.0	105.1	105.3	105.4
102.5°	137.4	137.3	137.2	137.0	136.9	136.7	136.9	137.0	137.2	137.3	137.4
105°	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5
107.5°	203.1	202.7	201.8	201.0	200.1	199.3	200.1	201.0	201.8	202.7	203.1
110°	237.4	237.2	236.7	236.2	235.7	235.2	235.7	236.2	236.7	237.2	237.4

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	271.0	270.8	270.5	270.2	269.8	269.5	269.8	270.2	270.5	270.8	271.0
115°	307.7	307.4	306.9	306.4	305.9	305.4	305.9	306.4	306.9	307.4	307.7
117.5°	341.3	341.0	340.5	340.0	339.5	339.0	339.5	340.0	340.5	341.0	341.3
120°	377.2	376.9	376.4	375.9	375.4	374.9	375.4	375.9	376.4	376.9	377.2
122.5°	411.5	411.3	411.0	410.7	410.3	410.0	410.3	410.7	411.0	411.3	411.5
125°	446.6	446.5	446.4	446.2	446.1	445.9	446.1	446.2	446.4	446.5	446.6
127.5°	480.2	479.9	479.4	478.9	478.4	477.9	478.4	478.9	479.4	479.9	480.2
130°	516.1	515.8	515.1	514.4	513.8	513.1	513.8	514.4	515.1	515.8	516.1
132.5°	548.9	548.6	548.1	547.6	547.1	546.6	547.1	547.6	548.1	548.6	548.9
135°	584.1	583.8	583.3	582.8	582.3	581.8	582.3	582.8	583.3	583.8	584.1
137.5°	616.1	615.8	615.1	614.4	613.8	613.1	613.8	614.4	615.1	615.8	616.1
140°	649.0	648.7	648.0	647.3	646.6	645.9	646.6	647.3	648.0	648.7	649.0
142.5°	678.7	678.4	677.7	677.0	676.4	675.7	676.4	677.0	677.7	678.4	678.7
145°	708.5	708.2	707.5	706.8	706.2	705.5	706.2	706.8	707.5	708.2	708.5
147.5°	735.2	734.9	734.2	733.5	732.9	732.2	732.9	733.5	734.2	734.9	735.2
150°	760.4	760.1	759.6	759.1	758.6	758.1	758.6	759.1	759.6	760.1	760.4
152.5°	785.6	785.3	784.6	783.9	783.3	782.6	783.3	783.9	784.6	785.3	785.6
155°	806.2	805.9	805.4	804.9	804.4	803.9	804.4	804.9	805.4	805.9	806.2
157.5°	826.8	826.4	825.5	824.7	823.8	823.0	823.8	824.7	825.5	826.4	826.8
160°	843.6	843.3	842.6	841.9	841.3	840.6	841.3	841.9	842.6	843.3	843.6
162.5°	859.7	859.3	858.4	857.6	856.7	855.9	856.7	857.6	858.4	859.3	859.7
165°	872.7	872.3	871.4	870.5	869.7	868.8	869.7	870.5	871.4	872.3	872.7
167.5°	884.1	883.7	882.8	882.0	881.1	880.3	881.1	882.0	882.8	883.7	884.1
170°	893.3	892.8	891.8	890.7	889.7	888.7	889.7	890.7	891.8	892.8	893.3
172.5°	900.1	899.6	898.6	897.6	896.6	895.6	896.6	897.6	898.6	899.6	900.1
175°	904.7	904.2	903.2	902.1	901.1	900.1	901.1	902.1	903.2	904.2	904.7
177.5°	907.0	906.5	905.5	904.4	903.4	902.4	903.4	904.4	905.5	906.5	907.0
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	918.6	924.5	922.3	914.1	923.8	923.8	930.5	930.5	938.7	941.6	946.1
5°	866.5	871.0	874.7	871.0	877.7	888.1	894.0	899.3	910.4	914.9	921.6
7.5°	810.7	818.9	822.6	822.6	833.8	845.7	857.6	865.0	880.7	886.6	893.3
10°	756.4	766.1	773.6	772.8	791.4	798.8	813.7	830.8	846.4	855.4	865.0
12.5°	699.2	704.4	714.8	729.7	734.1	747.5	764.6	786.2	814.5	822.6	836.8
15°	651.6	665.7	673.9	680.6	691.0	703.6	722.2	743.1	771.3	789.2	804.0
17.5°	611.4	630.0	635.2	633.7	647.1	666.4	688.0	703.6	728.9	750.5	764.6
20°	578.7	586.1	595.0	598.8	609.2	630.0	650.8	668.7	689.5	706.6	723.0
22.5°	545.9	551.9	559.3	566.0	574.2	586.1	606.2	628.5	648.6	665.0	683.6
25°	519.2	522.9	529.6	534.8	543.7	551.9	566.0	590.6	614.4	624.0	640.4
27.5°	493.1	496.1	500.6	506.5	511.0	519.2	531.8	551.9	576.4	586.1	608.4
30°	470.1	472.3	476.8	479.7	482.0	491.7	501.3	516.9	535.5	548.9	565.3
32.5°	448.5	450.7	455.2	455.9	458.9	464.1	473.1	487.2	503.6	514.7	528.8
35°	424.7	426.2	430.7	432.1	434.4	438.8	445.5	455.9	470.8	479.0	491.7
37.5°	406.1	405.4	408.3	410.6	413.6	415.8	418.0	428.4	439.6	447.0	456.7
40°	386.0	384.5	385.3	388.3	389.8	392.7	392.7	403.1	410.6	416.5	424.0
42.5°	365.9	365.2	363.7	365.2	366.7	367.4	368.2	375.6	383.1	388.3	396.4
45°	345.9	345.1	343.6	344.4	344.4	345.9	348.1	351.1	356.3	360.7	365.2
47.5°	327.3	325.8	323.6	322.8	324.3	324.3	324.3	327.3	332.5	334.0	338.4
50°	307.9	305.7	302.7	301.2	301.2	300.5	302.0	302.7	307.2	308.7	312.4
52.5°	287.1	285.6	282.6	279.7	280.4	278.9	279.7	280.4	281.9	284.1	286.4
55°	266.3	263.3	261.1	260.3	258.1	258.1	255.9	258.8	258.1	258.8	261.8
57.5°	246.2	243.2	239.5	238.0	235.8	235.0	233.6	232.8	233.6	235.8	238.0
60°	222.4	220.9	218.7	216.4	215.0	212.7	211.2	211.2	210.5	210.5	211.2
62.5°	199.3	198.6	195.6	194.9	193.4	191.9	189.7	188.2	188.2	189.7	190.4
65°	177.0	176.3	174.0	173.3	169.6	168.1	167.4	166.6	165.1	165.1	165.1
67.5°	156.2	154.0	154.0	150.2	147.3	145.8	144.3	143.6	143.6	143.6	144.3
70°	133.1	133.1	130.9	128.7	125.7	126.4	124.2	122.0	122.0	120.5	121.2
72.5°	110.8	110.1	107.9	107.1	104.9	102.6	101.2	102.6	100.4	99.7	100.4
75°	89.3	88.5	87.0	85.5	86.3	84.0	81.8	81.1	81.1	79.6	79.6
77.5°	68.4	69.9	66.9	66.2	64.7	63.2	62.5	61.7	61.7	61.7	63.2
80°	47.6	48.3	48.3	46.9	47.6	45.4	45.4	45.4	43.1	43.9	44.6
82.5°	30.5	30.5	29.8	30.5	29.8	29.8	29.0	29.0	28.3	28.3	29.0
85°	17.1	16.4	15.6	17.1	16.4	16.4	15.6	15.6	15.6	15.6	15.6
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	25.4	25.7	26.0	26.4	26.7	23.0	19.2	15.5	11.8	9.9	8.9
92.5°	24.3	24.2	24.0	23.9	23.7	23.5	23.3	23.2	23.0	22.9	22.2
95°	48.9	48.9	48.9	48.9	48.9	48.5	48.2	47.8	47.5	47.3	46.5
97.5°	76.3	76.3	76.3	76.3	76.3	75.6	75.0	74.3	73.6	73.3	72.5
100°	105.4	105.4	105.4	105.4	105.4	104.9	104.4	103.9	103.4	103.1	102.4
102.5°	137.3	137.2	137.0	136.9	136.7	136.0	135.3	134.6	133.9	133.6	133.1
105°	169.3	169.0	168.7	168.3	168.0	167.6	167.3	166.9	166.6	166.4	166.1
107.5°	203.0	202.8	202.7	202.5	202.3	202.3	202.3	202.3	202.3	202.3	202.0
110°	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	236.9

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	271.3	271.8	272.3	272.8	273.3	273.5	273.7	273.8	274.0	274.1	273.6
115°	307.8	307.9	308.1	308.2	308.4	308.8	309.1	309.5	309.8	310.0	309.5
117.5°	341.6	342.1	342.6	343.1	343.6	344.4	345.3	346.1	347.0	347.4	346.7
120°	377.2	377.2	377.2	377.2	377.2	378.6	379.9	381.3	382.6	383.3	382.6
122.5°	411.8	412.3	412.8	413.3	413.8	414.6	415.5	416.3	417.2	417.6	416.8
125°	446.9	447.4	447.9	448.4	448.9	449.4	449.9	450.4	450.9	451.2	450.4
127.5°	480.5	481.2	481.9	482.6	483.3	484.0	484.6	485.3	486.0	486.3	485.4
130°	516.3	516.6	516.9	517.3	517.6	518.0	518.3	518.7	519.0	519.2	518.1
132.5°	549.3	550.2	551.1	551.9	552.8	552.6	552.4	552.3	552.1	552.0	551.2
135°	584.2	584.3	584.5	584.6	584.8	584.5	584.1	583.8	583.5	583.3	582.4
137.5°	616.2	616.4	616.5	616.7	616.9	616.6	616.2	615.9	615.6	615.4	614.6
140°	649.0	649.0	649.0	649.0	649.0	648.1	647.3	646.4	645.5	645.1	644.3
142.5°	678.6	678.5	678.3	678.2	678.0	677.5	677.0	676.5	676.0	675.7	674.9
145°	708.4	708.2	708.1	707.9	707.7	706.7	705.7	704.7	703.7	703.2	702.6
147.5°	735.0	734.7	734.4	734.0	733.7	733.0	732.3	731.6	730.9	730.6	729.8
150°	760.1	759.6	759.1	758.6	758.1	757.4	756.8	756.1	755.4	755.1	754.6
152.5°	785.3	784.6	783.9	783.3	782.6	781.7	780.9	780.0	779.1	778.7	778.2
155°	805.8	804.9	804.1	803.2	802.4	801.9	801.4	800.9	800.4	800.1	799.8
157.5°	826.2	825.0	823.9	822.7	821.5	821.2	820.8	820.5	820.2	820.0	819.8
160°	843.1	842.1	841.1	840.1	839.1	838.9	838.7	838.6	838.4	838.3	838.1
162.5°	859.1	857.9	856.7	855.5	854.3	854.1	854.0	853.8	853.7	853.6	853.6
165°	872.1	870.9	869.7	868.5	867.3	867.3	867.3	867.3	867.3	867.3	867.4
167.5°	883.5	882.3	881.2	880.0	878.8	878.8	878.8	878.8	878.8	878.8	879.1
170°	892.7	891.5	890.3	889.1	887.9	888.1	888.3	888.4	888.6	888.7	889.0
172.5°	899.5	898.3	897.2	896.0	894.8	895.0	895.2	895.3	895.5	895.6	895.8
175°	904.1	902.9	901.8	900.6	899.4	899.7	900.1	900.4	900.7	900.9	901.2
177.5°	906.5	905.5	904.4	903.4	902.4	902.8	903.1	903.5	903.8	904.0	904.2
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	967.7	967.7	967.7	967.7
2.5°	949.8	949.8	961.0	972.9
5°	929.0	934.2	952.1	968.4
7.5°	908.9	917.8	940.2	961.0
10°	884.4	896.3	923.8	948.3
12.5°	860.6	871.7	903.7	931.2
15°	827.1	841.2	875.5	909.7
17.5°	793.6	807.8	849.4	889.6
20°	754.2	772.8	819.7	873.2
22.5°	717.8	740.8	792.9	836.0
25°	677.6	713.3	761.6	817.4
27.5°	641.9	677.6	726.7	783.2
30°	601.7	638.2	688.8	740.8
32.5°	563.1	596.5	645.6	709.6
35°	522.9	554.9	602.5	667.2
37.5°	486.4	517.7	569.7	629.3
40°	450.7	483.5	528.1	587.6
42.5°	417.3	446.3	486.4	545.9
45°	386.8	407.6	444.8	500.6
47.5°	354.8	373.4	407.6	463.4
50°	325.0	340.7	370.4	422.5
52.5°	296.0	309.4	336.9	378.6
55°	270.0	282.6	302.7	343.6
57.5°	243.2	252.9	272.2	305.0
60°	217.2	226.1	241.7	268.5
62.5°	191.2	198.6	213.5	235.0
65°	168.1	174.0	185.2	203.8
67.5°	145.8	149.5	158.4	173.3
70°	124.2	127.2	134.6	146.5
72.5°	101.2	104.1	112.3	120.5
75°	81.8	82.6	88.5	95.2
77.5°	64.0	63.2	67.7	72.9
80°	43.9	46.1	49.8	52.1
82.5°	29.8	30.5	32.0	33.5
85°	16.4	17.1	17.1	19.3
87.5°	6.7	7.4	7.4	8.2
90°	6.9	4.8	2.8	0.8
92.5°	20.9	19.5	18.2	16.8
95°	44.8	43.1	41.4	39.7
97.5°	71.0	69.5	67.9	66.4
100°	101.1	99.7	98.4	97.0
102.5°	132.1	131.0	130.0	129.0
105°	165.6	165.1	164.6	164.1
107.5°	201.3	200.6	200.0	199.3
110°	235.9	234.9	233.9	232.9



TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	272.6	271.5	270.5	269.5
115°	308.5	307.4	306.4	305.4
117.5°	345.4	344.0	342.7	341.3
120°	381.3	379.9	378.6	377.2
122.5°	415.1	413.4	411.7	410.0
125°	448.9	447.4	445.8	444.3
127.5°	483.5	481.6	479.8	477.9
130°	515.9	513.6	511.4	509.2
132.5°	549.5	547.8	546.1	544.4
135°	580.5	578.6	576.8	574.9
137.5°	613.1	611.6	610.0	608.5
140°	642.8	641.3	639.8	638.3
142.5°	673.4	671.9	670.3	668.8
145°	701.4	700.2	699.0	697.8
147.5°	728.3	726.8	725.3	723.8
150°	753.6	752.5	751.5	750.5
152.5°	777.2	776.2	775.2	774.2
155°	799.3	798.8	798.3	797.8
157.5°	819.5	819.1	818.8	818.4
160°	837.8	837.5	837.1	836.8
162.5°	853.6	853.6	853.6	853.6
165°	867.6	867.7	867.9	868.1
167.5°	879.6	880.1	880.6	881.1
170°	889.5	890.0	890.5	891.0
172.5°	896.3	896.8	897.3	897.8
175°	901.7	902.2	902.7	903.2
177.5°	904.7	905.2	905.7	906.2
180°	904.7	904.7	904.7	904.7

TEST NUMBER: P998580

CATALOG NUMBER: SA2XXDIP-B485D725UB30-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.92	15.71	15.92	16.72	18.05	12.41	13.21	13.41	14.21	15.55
	3H	15.72	16.44	16.73	17.45	18.80	13.75	14.46	14.76	15.48	16.83
	4H	15.89	16.56	16.91	17.58	18.94	14.21	14.88	15.23	15.90	17.26
	6H	15.93	16.55	16.97	17.57	18.95	14.51	15.13	15.55	16.16	17.53
	8H	15.91	16.50	16.95	17.54	18.91	14.60	15.19	15.63	16.22	17.59
	12H	15.87	16.43	16.91	17.46	18.86	14.64	15.20	15.68	16.23	17.62
4H	2H	14.95	15.62	15.98	16.64	18.00	12.85	13.52	13.88	14.54	15.90
	3H	15.93	16.49	16.96	17.53	18.91	14.30	14.86	15.34	15.91	17.28
	4H	16.20	16.71	17.24	17.75	19.15	14.84	15.35	15.88	16.39	17.78
	6H	16.33	16.77	17.38	17.83	19.22	15.21	15.65	16.27	16.71	18.11
	8H	16.32	16.73	17.38	17.79	19.20	15.32	15.73	16.38	16.79	18.19
	12H	16.29	16.66	17.36	17.72	19.14	15.38	15.75	16.45	16.81	18.23
8H	4H	16.20	16.62	17.26	17.67	19.08	14.97	15.38	16.03	16.44	17.85
	6H	16.38	16.72	17.46	17.82	19.22	15.41	15.74	16.48	16.84	18.25
	8H	16.41	16.71	17.50	17.79	19.21	15.56	15.85	16.64	16.93	18.36
	12H	16.39	16.65	17.48	17.73	19.19	15.65	15.91	16.73	16.98	18.45
12H	4H	16.16	16.53	17.23	17.60	19.01	14.94	15.32	16.02	16.38	17.80
	6H	16.36	16.66	17.44	17.74	19.16	15.41	15.70	16.49	16.78	18.21
	8H	16.39	16.65	17.48	17.72	19.19	15.56	15.82	16.65	16.90	18.36