

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998641

Luminaire Tested: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998641
REPORT IS A COMBINATION OF REPORTS P984384 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5716.0 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	31	29	26	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15318	15318	15318	15318
5°	15354	16332	15413	12993
10°	15176	17829	15272	10713
15°	14809	18805	15014	9023
20°	14577	17657	14577	7843
25°	14112	15170	14178	7013
30°	13348	11925	13604	6353
35°	12671	8246	12882	5813
40°	11892	6226	12028	5382
45°	10933	5116	11112	4916
50°	10103	4491	10120	4501
55°	9156	3826	9217	4049
60°	8148	3196	8260	3535
65°	7245	2599	7376	3018
70°	6344	2040	6505	2434
75°	5326	1481	5533	1765
80°	4160	938	4455	1047
85°	2726	473	2938	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15834 cd/sqm

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	1.6
10°-20°	268.3	4.7
20°-30°	389.3	6.8
30°-40°	410.4	7.2
40°-50°	363.2	6.4
50°-60°	290.0	5.1
60°-70°	197.0	3.4
70°-80°	100.8	1.8
80°-90°	27.1	0.5
90°-100°	200.3	3.5
100°-110°	705.3	12.3
110°-120°	740.7	13.0
120°-130°	609.4	10.7
130°-140°	489.5	8.6
140°-150°	369.8	6.5
150°-160°	260.0	4.5
160°-170°	153.0	2.7
170°-180°	49.8	0.9
0°-30°	749.8	13.1
0°-40°	1160.2	20.3
0°-60°	1813.4	31.7
0°-90°	2138.3	37.4
90°-120°	1646.3	28.8
90°-150°	3115.0	54.5
90°-180°	3578.0	62.6
0°-180°	5716.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	968	968	968	968	968	
5°	968	1081	972	860	968	92
15°	910	1328	922	637	910	257
25°	817	1107	821	512	817	374
35°	667	602	678	425	667	417
45°	501	363	509	349	501	388
55°	344	255	346	270	344	307
65°	204	157	208	182	204	203
75°	95	77	99	92	95	102
85°	19	20	21	15	19	23
90°	1	33	1	33	1	3
95°	35	113	35	113	35	36
105°	120	1113	120	1113	120	128
115°	212	1465	212	1465	212	211
125°	296	1188	296	1188	296	263
135°	348	985	348	985	348	269
145°	397	786	397	786	397	249
155°	452	661	452	661	452	208
165°	492	580	492	580	492	139
175°	513	523	513	523	513	49
180°	514	514	514	514	514	

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	972.9	975.1	978.8	979.6	987.0	993.0	999.7	999.7	1001.9	1001.2	995.2
5°	968.4	975.1	984.8	993.0	1006.4	1012.3	1021.2	1027.9	1033.9	1038.3	1037.6
7.5°	961.0	972.9	987.0	1002.6	1020.5	1030.9	1043.5	1055.4	1063.6	1071.1	1076.3
10°	948.3	968.4	987.8	1008.6	1031.6	1045.8	1060.7	1076.3	1088.9	1103.1	1116.4
12.5°	931.2	960.2	984.0	1011.6	1039.8	1055.4	1079.3	1091.2	1115.7	1151.4	1161.1
15°	909.7	949.1	971.4	1006.4	1043.5	1056.2	1088.9	1108.3	1158.8	1181.2	1207.9
17.5°	889.6	933.5	963.2	1003.4	1039.8	1064.4	1096.4	1135.8	1178.2	1210.2	1239.9
20°	873.2	915.6	951.3	995.9	1042.1	1073.3	1106.8	1154.4	1200.5	1233.2	1256.3
22.5°	836.0	890.3	932.0	981.8	1037.6	1080.7	1112.7	1164.8	1214.6	1234.7	1254.8
25°	817.4	864.3	912.6	969.2	1034.6	1085.9	1113.5	1171.5	1215.4	1222.8	1227.3
27.5°	783.2	836.0	892.6	957.3	1033.9	1077.0	1112.0	1164.8	1199.7	1194.5	1181.2
30°	740.8	805.5	868.0	937.9	1023.5	1070.3	1103.1	1151.4	1169.3	1142.5	1118.7
32.5°	709.6	770.6	839.7	920.8	1011.6	1056.2	1088.2	1126.1	1129.8	1081.5	1041.3
35°	667.2	734.9	813.0	898.5	991.5	1031.6	1061.4	1084.5	1066.6	998.9	951.3
37.5°	629.3	696.2	779.5	866.5	964.0	1003.4	1027.2	1030.9	987.0	927.5	857.6
40°	587.6	656.8	743.8	835.3	933.5	967.7	982.6	971.4	908.2	839.0	757.9
42.5°	545.9	614.4	708.1	801.8	894.8	923.8	929.7	899.3	821.9	740.8	647.1
45°	500.6	572.0	665.7	760.2	850.2	866.5	867.3	823.4	731.9	647.1	560.1
47.5°	463.4	529.6	622.6	717.0	792.9	804.0	799.6	749.0	649.3	554.1	478.3
50°	422.5	485.7	577.9	670.9	735.6	738.6	727.4	655.3	557.8	470.8	410.6
52.5°	378.6	442.6	527.4	616.6	674.6	670.2	648.6	571.2	479.7	407.6	361.5
55°	343.6	400.2	479.7	566.8	607.7	595.0	571.2	492.4	420.2	359.3	319.1
57.5°	305.0	354.8	432.9	508.8	532.6	520.7	496.9	423.2	356.3	310.2	283.4
60°	268.5	313.9	382.3	445.5	464.1	451.5	424.0	357.8	309.4	270.7	250.7
62.5°	235.0	274.5	331.7	389.8	397.2	384.5	360.7	307.2	265.5	235.0	220.2
65°	203.8	241.0	287.1	331.0	337.7	324.3	299.8	261.1	226.1	206.8	192.6
67.5°	173.3	203.1	244.0	275.9	279.7	267.0	246.9	215.7	194.1	173.3	162.9
70°	146.5	168.8	200.8	226.9	228.3	216.4	206.0	177.8	161.4	146.5	138.3
72.5°	120.5	136.1	160.7	180.0	180.7	173.3	163.6	145.8	131.7	121.2	113.1
75°	95.2	108.6	123.5	140.6	139.8	133.9	126.4	115.3	103.4	96.7	93.0
77.5°	72.9	81.1	93.0	104.1	104.1	101.2	96.7	88.5	81.1	74.4	70.7
80°	52.1	57.3	66.9	70.7	72.1	71.4	67.7	61.7	58.8	53.6	52.1
82.5°	33.5	37.2	41.7	45.4	47.6	46.1	45.4	42.4	37.9	36.4	35.0
85°	19.3	20.8	23.1	25.3	26.0	25.3	26.8	24.5	22.3	22.3	21.6
87.5°	8.2	8.9	10.4	10.4	11.2	11.2	10.4	11.2	11.2	10.4	9.7
90°	1.0	4.0	7.9	9.9	11.9	13.4	14.8	19.8	26.7	32.6	33.6
92.5°	14.8	20.7	28.7	33.6	41.5	47.0	52.4	79.0	116.6	150.2	152.1
95°	34.6	38.5	48.4	57.3	73.1	84.9	96.8	142.3	228.2	342.8	387.3
97.5°	51.4	57.3	68.2	81.0	98.8	112.2	125.5	183.8	303.3	488.1	631.3
100°	76.1	79.0	87.9	103.7	123.5	137.4	151.2	203.5	324.1	537.5	780.5
102.5°	98.8	100.8	109.7	125.5	146.2	160.0	173.9	221.3	325.0	518.7	785.4
105°	120.5	124.5	131.4	146.2	168.0	181.8	195.6	242.1	330.0	493.0	732.1
107.5°	144.2	147.2	154.1	168.0	189.7	203.6	217.4	262.8	340.8	479.2	682.7
110°	168.0	171.9	177.8	190.7	211.4	225.8	240.1	283.5	354.7	475.2	649.1

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	189.7	193.6	200.6	212.4	232.2	247.0	261.8	303.3	369.5	476.2	627.4
115°	212.4	217.4	223.3	235.1	254.9	268.2	281.6	324.1	384.3	480.1	612.5
117.5°	236.1	240.1	246.0	256.9	275.6	289.5	303.3	342.8	400.1	486.1	604.6
120°	257.9	261.8	267.7	276.6	296.4	310.2	324.1	362.6	415.9	492.0	597.7
122.5°	278.6	281.6	287.5	297.4	317.1	331.5	345.8	381.4	429.8	498.9	593.8
125°	296.4	299.4	305.3	317.1	336.9	350.8	364.6	400.1	444.6	505.8	588.8
127.5°	311.2	315.2	323.1	335.9	354.7	369.0	383.3	417.9	458.4	512.8	585.9
130°	324.1	328.0	337.9	351.7	371.5	385.3	399.1	433.7	471.3	520.7	583.9
132.5°	335.9	340.8	351.7	366.5	387.3	401.1	414.9	447.5	484.1	528.6	582.9
135°	347.8	351.7	363.6	378.4	401.1	415.0	428.8	460.4	495.0	534.5	581.9
137.5°	358.6	363.6	375.4	391.2	414.0	426.8	439.6	471.3	503.9	540.4	581.9
140°	371.5	375.4	387.3	403.1	424.8	437.6	450.5	480.1	510.8	544.4	580.9
142.5°	384.3	387.3	398.1	414.0	434.7	446.6	458.4	487.1	516.7	547.3	580.9
145°	397.2	401.1	411.0	425.8	445.6	456.4	467.3	494.0	521.6	549.3	578.9
147.5°	411.0	414.0	423.8	437.7	454.5	464.4	474.2	499.9	524.6	550.3	576.0
150°	424.8	427.8	435.7	448.5	463.4	472.2	481.1	503.9	526.6	549.3	573.0
152.5°	438.7	439.6	447.5	458.4	472.2	480.2	488.1	507.8	527.6	547.3	568.1
155°	451.5	452.5	458.4	469.3	480.1	487.6	495.0	511.8	528.6	545.4	562.2
157.5°	462.4	463.4	468.3	478.2	487.1	493.5	499.9	514.7	528.6	541.4	556.2
160°	473.2	474.2	478.2	486.1	494.0	499.4	504.8	516.7	528.6	538.4	550.3
162.5°	484.1	483.1	487.1	493.0	499.9	503.8	507.8	517.7	527.6	535.5	545.4
165°	492.0	491.0	493.0	498.9	503.9	506.8	509.8	518.7	525.6	531.5	538.4
167.5°	498.9	497.9	499.9	503.9	507.8	509.8	511.8	518.7	524.6	527.6	532.5
170°	505.8	503.9	504.8	507.8	509.8	511.3	512.8	517.7	522.6	524.6	527.6
172.5°	509.8	508.8	507.8	510.8	511.8	512.8	513.7	516.7	519.7	520.7	521.6
175°	512.8	511.8	510.8	512.8	512.8	513.2	513.7	515.7	517.7	516.7	517.7
177.5°	514.7	512.8	511.8	513.7	513.7	513.7	513.7	514.7	516.7	514.7	513.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1005.6	1006.4	1007.8	1015.3	1019.0	1019.7	1016.8	1023.5	1025.7	1023.5	1022.0
5°	1053.2	1057.7	1066.6	1076.3	1075.5	1076.3	1080.7	1085.2	1086.7	1080.7	1083.0
7.5°	1094.9	1103.8	1113.5	1128.3	1128.3	1135.8	1138.8	1142.5	1151.4	1146.9	1145.4
10°	1142.5	1154.4	1172.2	1196.0	1196.8	1204.2	1211.6	1223.5	1227.3	1224.3	1225.8
12.5°	1202.0	1225.0	1226.5	1252.6	1264.5	1265.9	1277.8	1275.6	1283.1	1283.1	1295.7
15°	1228.0	1263.7	1283.8	1309.1	1316.5	1307.6	1317.3	1327.7	1328.4	1328.4	1327.7
17.5°	1274.9	1289.0	1309.1	1322.5	1325.4	1325.4	1326.2	1330.7	1327.7	1321.7	1326.2
20°	1284.5	1290.5	1297.9	1296.4	1297.9	1290.5	1283.1	1275.6	1276.4	1272.6	1283.8
22.5°	1266.7	1265.2	1248.1	1236.9	1236.9	1222.1	1207.9	1201.2	1194.5	1196.8	1200.5
25°	1222.1	1199.0	1178.2	1161.8	1158.1	1134.3	1115.0	1109.0	1097.8	1106.8	1108.3
27.5°	1150.7	1124.6	1091.2	1077.0	1057.7	1048.0	1034.6	1016.8	993.7	1007.1	1004.9
30°	1074.0	1035.4	1007.8	973.6	943.1	940.9	915.6	885.9	874.0	874.0	880.7
32.5°	988.5	937.2	897.0	848.7	818.9	806.3	775.8	746.0	752.7	730.4	738.6
35°	888.8	821.2	770.6	723.7	701.4	686.5	647.1	630.7	612.9	602.5	621.8
37.5°	793.6	715.5	650.8	599.5	591.3	564.5	537.8	527.4	516.9	521.4	520.7
40°	677.6	608.4	550.4	510.2	496.1	483.5	465.6	453.0	446.3	450.0	450.7
42.5°	572.7	514.7	471.6	443.3	431.4	422.5	413.6	403.1	400.9	400.9	403.9
45°	491.7	444.0	415.0	392.0	385.3	378.6	371.9	367.4	365.9	363.0	365.2
47.5°	426.9	389.0	371.2	354.0	346.6	345.1	339.2	336.9	334.0	333.2	334.0
50°	372.6	348.8	332.5	322.8	317.6	315.4	312.4	307.9	306.4	310.2	308.7
52.5°	334.7	312.4	303.5	293.8	290.8	287.8	283.4	284.1	283.4	281.9	281.9
55°	296.8	282.6	273.7	266.3	265.5	262.6	258.8	257.4	256.6	255.1	257.4
57.5°	266.3	255.1	246.9	240.2	237.3	237.3	233.6	230.6	230.6	229.8	230.6
60°	235.8	224.6	219.4	212.7	210.5	209.8	207.5	206.0	203.8	203.8	203.8
62.5°	207.5	198.6	192.6	186.7	187.4	183.7	180.7	179.3	179.3	180.0	180.0
65°	180.7	174.8	167.4	162.1	160.7	159.9	158.4	157.7	155.5	156.9	156.9
67.5°	156.2	148.0	143.6	141.3	139.1	138.3	136.9	135.4	134.6	133.9	135.4
70°	131.7	125.0	121.2	119.8	117.5	116.8	116.0	113.8	114.5	115.3	116.0
72.5°	109.3	103.4	102.6	98.2	98.2	98.2	95.2	96.7	95.9	94.5	95.9
75°	86.3	83.3	81.8	79.6	80.3	79.6	78.8	76.6	76.6	77.4	78.1
77.5°	68.4	65.5	64.7	62.5	61.0	62.5	61.0	60.2	60.2	61.0	61.0
80°	50.6	49.1	46.9	46.9	46.9	46.1	46.1	46.1	45.4	44.6	45.4
82.5°	33.5	33.5	32.7	32.0	32.7	31.2	32.0	32.0	32.0	32.0	32.0
85°	21.6	20.8	20.8	20.1	20.1	20.1	20.8	19.3	19.3	20.1	20.1
87.5°	9.7	9.7	9.7	10.4	9.7	9.7	9.7	10.4	9.7	9.7	9.7
90°	32.6	31.6	29.6	31.6	32.1	32.6	32.6	32.6	32.6	32.6	32.6
92.5°	127.4	99.8	85.0	74.1	70.2	66.2	65.2	61.3	62.2	60.3	62.2
95°	338.9	258.8	198.6	157.1	146.2	135.4	122.5	114.6	111.6	112.6	111.6
97.5°	636.2	529.5	422.8	323.1	293.5	263.8	225.3	205.5	194.6	188.7	194.6
100°	922.8	902.0	779.5	644.2	584.4	524.6	442.6	400.1	371.5	353.7	371.5
102.5°	1029.5	1146.0	1142.1	1052.2	988.0	923.7	832.9	752.8	715.3	689.6	715.3
105°	994.9	1200.4	1312.0	1324.9	1308.6	1292.3	1231.0	1169.7	1127.3	1113.4	1127.3
107.5°	921.8	1142.1	1308.1	1404.9	1424.6	1444.4	1443.4	1434.5	1421.7	1399.0	1421.7
110°	853.6	1062.1	1238.9	1365.4	1405.9	1446.4	1488.9	1507.6	1516.5	1515.5	1516.5

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	806.2	988.9	1156.9	1294.2	1342.2	1390.1	1453.3	1487.9	1506.6	1513.6	1506.6
115°	768.6	931.6	1083.8	1213.2	1264.1	1315.0	1385.1	1430.6	1456.3	1465.1	1456.3
117.5°	742.9	884.2	1020.6	1141.1	1189.5	1237.9	1310.0	1358.4	1385.1	1392.0	1385.1
120°	723.2	850.6	973.1	1077.9	1122.8	1167.8	1236.9	1283.4	1312.0	1321.9	1312.0
122.5°	706.4	824.0	933.6	1031.4	1071.0	1110.5	1170.7	1216.2	1240.9	1248.8	1240.9
125°	690.6	798.3	900.0	987.0	1024.0	1061.1	1118.4	1155.9	1180.6	1188.5	1180.6
127.5°	675.8	772.6	866.4	949.4	984.0	1018.6	1069.0	1104.5	1126.3	1132.2	1126.3
130°	660.9	747.9	832.9	910.9	943.5	976.1	1024.5	1058.1	1077.9	1085.8	1077.9
132.5°	649.1	724.2	801.2	871.4	901.5	931.6	979.1	1012.7	1030.4	1037.4	1030.4
135°	638.2	702.4	767.6	832.9	860.6	888.2	930.7	963.3	981.0	985.0	981.0
137.5°	630.3	684.7	741.0	794.3	819.0	843.7	884.2	912.9	928.7	934.6	928.7
140°	623.4	667.9	715.3	760.7	782.4	804.2	835.8	861.5	876.3	882.2	876.3
142.5°	616.5	654.0	692.6	730.1	747.4	764.7	794.3	817.0	829.9	829.9	829.9
145°	610.6	641.2	673.8	704.4	718.8	733.1	756.8	773.6	783.5	786.4	783.5
147.5°	604.6	631.3	658.0	682.7	693.6	704.4	725.2	739.0	745.9	747.9	745.9
150°	596.7	620.4	642.2	662.9	671.8	680.7	695.5	707.4	713.3	714.3	713.3
152.5°	589.8	609.6	629.3	646.1	653.5	660.9	671.8	681.7	685.6	685.6	685.6
155°	580.9	599.7	615.5	630.3	635.8	641.2	652.1	659.0	662.9	660.9	662.9
157.5°	573.0	587.8	601.7	614.5	619.0	623.4	631.3	637.2	639.2	639.2	639.2
160°	564.1	577.0	587.8	598.7	602.2	605.6	612.5	617.5	618.5	618.5	618.5
162.5°	556.2	566.1	575.0	583.9	586.3	588.8	595.7	598.7	599.7	598.7	599.7
165°	547.3	555.2	562.2	569.1	571.0	573.0	577.0	580.9	580.9	579.9	580.9
167.5°	538.4	544.4	550.3	555.2	557.2	559.2	561.2	563.1	563.1	562.2	563.1
170°	531.5	536.5	539.4	543.4	544.4	545.4	546.3	549.3	548.3	546.3	548.3
172.5°	524.6	527.6	529.5	532.5	533.0	533.5	534.5	535.5	534.5	533.5	534.5
175°	518.7	521.6	522.6	523.6	524.1	524.6	524.6	525.6	524.6	522.6	524.6
177.5°	514.7	516.7	516.7	517.7	517.7	517.7	517.7	517.7	516.7	514.7	516.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1025.7	1020.5	1016.0	1016.8	1020.5	1017.5	1010.1	1000.4	996.7	992.2	996.7
5°	1087.4	1083.0	1074.0	1074.8	1072.6	1069.6	1057.7	1042.8	1042.8	1030.9	1029.4
7.5°	1148.4	1141.7	1135.8	1134.3	1126.1	1120.2	1109.7	1088.9	1080.7	1066.6	1058.4
10°	1216.9	1211.6	1205.0	1196.8	1192.3	1181.9	1164.8	1134.3	1119.4	1100.1	1085.9
12.5°	1286.0	1285.3	1270.4	1254.0	1253.3	1236.9	1225.0	1184.1	1164.0	1138.0	1104.5
15°	1329.9	1326.2	1318.0	1309.8	1312.1	1294.2	1267.4	1219.1	1205.7	1174.5	1138.8
17.5°	1329.2	1329.2	1326.9	1325.4	1323.2	1318.0	1303.1	1271.2	1249.6	1210.2	1176.7
20°	1286.8	1296.4	1298.7	1297.9	1305.4	1309.1	1308.3	1288.3	1271.2	1236.2	1202.0
22.5°	1202.0	1224.3	1234.0	1239.9	1255.5	1263.7	1283.1	1275.6	1271.2	1245.1	1216.1
25°	1123.1	1130.6	1159.6	1161.1	1182.6	1202.7	1222.1	1234.7	1251.1	1241.4	1216.9
27.5°	1021.2	1038.3	1059.2	1074.8	1079.3	1120.2	1152.1	1175.9	1213.1	1216.1	1207.9
30°	905.9	914.1	948.3	969.2	993.0	1022.7	1068.8	1109.7	1143.2	1173.7	1184.1
32.5°	765.4	798.8	818.9	844.2	865.0	917.8	974.4	1027.2	1065.9	1117.2	1139.5
35°	636.7	662.7	696.9	707.4	745.3	789.9	863.5	931.2	990.0	1042.1	1087.4
37.5°	530.3	551.2	587.6	604.0	626.3	683.6	745.3	829.3	900.0	964.0	1020.5
40°	457.4	473.1	500.6	505.8	524.4	576.4	626.3	705.1	798.8	885.1	946.9
42.5°	407.6	415.0	433.6	440.3	452.2	487.2	531.8	606.2	693.2	782.5	869.5
45°	371.9	377.1	388.3	394.2	409.1	424.7	461.2	520.7	589.1	679.1	772.8
47.5°	339.9	346.6	351.1	354.8	363.0	380.1	403.9	447.8	513.2	595.8	686.5
50°	313.1	315.4	323.6	324.3	329.5	340.7	363.0	389.8	441.8	508.8	596.5
52.5°	286.4	288.6	293.8	299.0	301.2	310.2	325.0	347.4	386.0	438.8	516.9
55°	259.6	262.6	267.8	271.5	273.7	281.2	290.1	311.7	342.1	379.3	443.3
57.5°	232.8	239.5	241.0	243.2	246.9	255.1	263.3	275.9	299.8	334.0	380.8
60°	207.5	209.8	215.0	217.2	220.9	225.4	235.8	245.5	262.6	289.3	331.7
62.5°	181.5	186.7	188.9	191.2	194.1	199.3	206.0	216.4	231.3	252.9	286.4
65°	159.2	159.9	164.4	167.4	170.3	174.0	180.7	190.4	199.3	219.4	244.0
67.5°	137.6	139.1	140.6	143.6	147.3	151.0	156.9	162.1	173.3	186.7	206.0
70°	116.8	116.8	120.5	122.7	122.0	126.4	130.9	136.9	145.0	157.7	173.3
72.5°	98.2	97.4	100.4	101.2	102.6	105.6	108.6	114.5	119.0	128.7	140.6
75°	78.1	79.6	81.1	81.1	83.3	85.5	88.5	91.5	96.7	102.6	111.6
77.5°	61.7	61.7	63.2	64.0	66.2	65.5	68.4	71.4	75.1	80.3	87.0
80°	45.4	46.9	46.9	46.9	47.6	48.3	51.3	53.6	55.8	59.5	62.5
82.5°	32.0	32.0	33.5	33.5	33.5	35.0	35.0	35.7	37.2	39.4	41.7
85°	20.1	20.1	20.1	20.8	20.1	20.8	22.3	21.6	22.3	23.8	23.8
87.5°	9.7	9.7	9.7	9.7	9.7	10.4	9.7	10.4	11.2	11.2	11.2
90°	32.6	32.6	32.6	32.1	31.6	29.6	31.6	32.6	33.6	32.6	26.7
92.5°	61.3	65.2	66.2	70.2	74.1	85.0	99.8	127.4	152.1	150.2	116.6
95°	114.6	122.5	135.4	146.2	157.1	198.6	258.8	338.9	387.3	342.8	228.2
97.5°	205.5	225.3	263.8	293.5	323.1	422.8	529.5	636.2	631.3	488.1	303.3
100°	400.1	442.6	524.6	584.4	644.2	779.5	902.0	922.8	780.5	537.5	324.1
102.5°	752.8	832.9	923.7	988.0	1052.2	1142.1	1146.0	1029.5	785.4	518.7	325.0
105°	1169.7	1231.0	1292.3	1308.6	1324.9	1312.0	1200.4	994.9	732.1	493.0	330.0
107.5°	1434.5	1443.4	1444.4	1424.6	1404.9	1308.1	1142.1	921.8	682.7	479.2	340.8
110°	1507.6	1488.9	1446.4	1405.9	1365.4	1238.9	1062.1	853.6	649.1	475.2	354.7

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1487.9	1453.3	1390.1	1342.2	1294.2	1156.9	988.9	806.2	627.4	476.2	369.5
115°	1430.6	1385.1	1315.0	1264.1	1213.2	1083.8	931.6	768.6	612.5	480.1	384.3
117.5°	1358.4	1310.0	1237.9	1189.5	1141.1	1020.6	884.2	742.9	604.6	486.1	400.1
120°	1283.4	1236.9	1167.8	1122.8	1077.9	973.1	850.6	723.2	597.7	492.0	415.9
122.5°	1216.2	1170.7	1110.5	1071.0	1031.4	933.6	824.0	706.4	593.8	498.9	429.8
125°	1155.9	1118.4	1061.1	1024.0	987.0	900.0	798.3	690.6	588.8	505.8	444.6
127.5°	1104.5	1069.0	1018.6	984.0	949.4	866.4	772.6	675.8	585.9	512.8	458.4
130°	1058.1	1024.5	976.1	943.5	910.9	832.9	747.9	660.9	583.9	520.7	471.3
132.5°	1012.7	979.1	931.6	901.5	871.4	801.2	724.2	649.1	582.9	528.6	484.1
135°	963.3	930.7	888.2	860.6	832.9	767.6	702.4	638.2	581.9	534.5	495.0
137.5°	912.9	884.2	843.7	819.0	794.3	741.0	684.7	630.3	581.9	540.4	503.9
140°	861.5	835.8	804.2	782.4	760.7	715.3	667.9	623.4	580.9	544.4	510.8
142.5°	817.0	794.3	764.7	747.4	730.1	692.6	654.0	616.5	580.9	547.3	516.7
145°	773.6	756.8	733.1	718.8	704.4	673.8	641.2	610.6	578.9	549.3	521.6
147.5°	739.0	725.2	704.4	693.6	682.7	658.0	631.3	604.6	576.0	550.3	524.6
150°	707.4	695.5	680.7	671.8	662.9	642.2	620.4	596.7	573.0	549.3	526.6
152.5°	681.7	671.8	660.9	653.5	646.1	629.3	609.6	589.8	568.1	547.3	527.6
155°	659.0	652.1	641.2	635.8	630.3	615.5	599.7	580.9	562.2	545.4	528.6
157.5°	637.2	631.3	623.4	619.0	614.5	601.7	587.8	573.0	556.2	541.4	528.6
160°	617.5	612.5	605.6	602.2	598.7	587.8	577.0	564.1	550.3	538.4	528.6
162.5°	598.7	595.7	588.8	586.3	583.9	575.0	566.1	556.2	545.4	535.5	527.6
165°	580.9	577.0	573.0	571.0	569.1	562.2	555.2	547.3	538.4	531.5	525.6
167.5°	563.1	561.2	559.2	557.2	555.2	550.3	544.4	538.4	532.5	527.6	524.6
170°	549.3	546.3	545.4	544.4	543.4	539.4	536.5	531.5	527.6	524.6	522.6
172.5°	535.5	534.5	533.5	533.0	532.5	529.5	527.6	524.6	521.6	520.7	519.7
175°	525.6	524.6	524.6	524.1	523.6	522.6	521.6	518.7	517.7	516.7	517.7
177.5°	517.7	517.7	517.7	517.7	517.7	516.7	516.7	514.7	513.7	514.7	516.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	993.0	989.3	987.0	988.5	984.0	972.9	972.9	976.6	972.1	967.7	961.0
5°	1020.5	1013.1	1008.6	1007.8	997.4	979.6	975.9	972.1	962.5	952.1	940.9
7.5°	1047.3	1033.9	1026.4	1021.2	1006.4	983.3	973.6	965.5	949.8	934.2	920.1
10°	1069.6	1050.2	1041.3	1033.1	1013.8	984.8	969.2	954.3	934.2	914.1	896.3
12.5°	1087.4	1065.1	1054.0	1042.1	1018.3	980.3	961.0	937.2	917.1	890.3	872.5
15°	1117.2	1071.1	1060.7	1049.5	1025.0	972.9	949.1	922.3	894.8	859.1	839.7
17.5°	1141.0	1079.3	1078.5	1054.7	1022.7	969.9	933.5	898.5	868.8	833.1	802.6
20°	1155.1	1091.9	1080.0	1055.4	1015.3	949.8	911.9	873.2	841.2	798.1	767.6
22.5°	1167.0	1109.7	1078.5	1048.8	999.7	943.1	887.4	850.9	807.0	760.2	731.2
25°	1171.5	1113.5	1080.7	1046.5	988.5	923.8	860.6	821.2	772.1	729.7	690.2
27.5°	1172.2	1112.7	1072.6	1036.9	972.9	898.5	833.8	792.1	737.8	688.8	649.3
30°	1164.8	1104.5	1068.1	1029.4	958.0	875.5	801.1	755.0	696.9	647.8	606.9
32.5°	1142.5	1088.2	1058.4	1016.0	938.7	843.5	769.8	718.5	657.5	609.2	569.7
35°	1105.3	1068.1	1035.4	995.9	913.4	813.7	738.6	678.3	616.6	570.5	533.3
37.5°	1059.2	1039.1	1008.6	969.9	884.4	786.9	703.6	636.7	575.0	530.3	493.9
40°	996.7	1001.9	972.1	937.2	850.2	750.5	658.3	594.3	536.3	494.6	458.9
42.5°	929.0	950.6	933.5	900.0	812.2	710.3	624.8	554.1	497.6	454.5	424.7
45°	856.1	893.3	882.9	858.3	772.8	667.9	577.2	508.8	458.9	417.3	391.2
47.5°	776.5	829.3	829.3	811.5	728.9	625.5	536.3	466.4	417.3	387.5	362.2
50°	695.5	755.0	764.6	752.7	679.8	577.2	486.4	423.2	380.8	351.8	333.2
52.5°	610.7	679.8	697.7	691.7	627.8	531.1	445.5	383.8	345.1	319.8	303.5
55°	529.6	609.9	629.3	631.5	572.0	480.5	400.2	345.9	308.7	291.6	277.4
57.5°	453.0	530.3	551.9	555.6	515.5	434.4	357.8	310.2	276.7	262.6	251.4
60°	387.5	452.2	480.5	488.7	453.7	380.8	318.3	272.2	246.9	233.6	223.1
62.5°	334.0	386.0	415.8	418.0	402.4	334.0	277.4	238.8	217.2	205.3	200.1
65°	281.9	328.8	346.6	355.5	342.9	289.3	239.5	207.5	190.4	180.0	174.8
67.5°	240.2	270.0	284.9	296.8	284.1	244.0	203.8	177.8	165.1	154.7	151.7
70°	197.1	221.7	232.8	244.7	233.6	203.1	174.0	150.2	139.1	130.9	127.2
72.5°	157.7	177.0	187.4	194.9	188.2	162.9	139.1	122.7	114.5	108.6	106.4
75°	125.0	138.3	144.3	149.5	146.5	127.2	112.3	98.9	91.5	86.3	84.8
77.5°	95.2	104.9	111.6	113.1	109.3	96.7	84.0	75.9	69.9	66.9	65.5
80°	67.7	73.6	77.4	79.6	75.9	70.7	61.7	55.8	50.6	46.9	46.1
82.5°	45.4	48.3	51.3	50.6	49.1	44.6	39.4	36.4	34.2	31.2	31.2
85°	26.0	26.8	28.3	29.0	28.3	25.3	22.3	20.8	19.3	17.1	17.1
87.5°	11.2	11.9	11.9	12.6	11.2	11.2	9.7	8.2	8.2	7.4	6.7
90°	19.8	14.8	13.4	11.9	9.9	7.9	4.0	1.0	4.0	7.9	9.9
92.5°	79.0	52.4	47.0	41.5	33.6	28.7	20.7	14.8	20.7	28.7	33.6
95°	142.3	96.8	84.9	73.1	57.3	48.4	38.5	34.6	38.5	48.4	57.3
97.5°	183.8	125.5	112.2	98.8	81.0	68.2	57.3	51.4	57.3	68.2	81.0
100°	203.5	151.2	137.4	123.5	103.7	87.9	79.0	76.1	79.0	87.9	103.7
102.5°	221.3	173.9	160.0	146.2	125.5	109.7	100.8	98.8	100.8	109.7	125.5
105°	242.1	195.6	181.8	168.0	146.2	131.4	124.5	120.5	124.5	131.4	146.2
107.5°	262.8	217.4	203.6	189.7	168.0	154.1	147.2	144.2	147.2	154.1	168.0
110°	283.5	240.1	225.8	211.4	190.7	177.8	171.9	168.0	171.9	177.8	190.7

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	303.3	261.8	247.0	232.2	212.4	200.6	193.6	189.7	193.6	200.6	212.4
115°	324.1	281.6	268.2	254.9	235.1	223.3	217.4	212.4	217.4	223.3	235.1
117.5°	342.8	303.3	289.5	275.6	256.9	246.0	240.1	236.1	240.1	246.0	256.9
120°	362.6	324.1	310.2	296.4	276.6	267.7	261.8	257.9	261.8	267.7	276.6
122.5°	381.4	345.8	331.5	317.1	297.4	287.5	281.6	278.6	281.6	287.5	297.4
125°	400.1	364.6	350.8	336.9	317.1	305.3	299.4	296.4	299.4	305.3	317.1
127.5°	417.9	383.3	369.0	354.7	335.9	323.1	315.2	311.2	315.2	323.1	335.9
130°	433.7	399.1	385.3	371.5	351.7	337.9	328.0	324.1	328.0	337.9	351.7
132.5°	447.5	414.9	401.1	387.3	366.5	351.7	340.8	335.9	340.8	351.7	366.5
135°	460.4	428.8	415.0	401.1	378.4	363.6	351.7	347.8	351.7	363.6	378.4
137.5°	471.3	439.6	426.8	414.0	391.2	375.4	363.6	358.6	363.6	375.4	391.2
140°	480.1	450.5	437.6	424.8	403.1	387.3	375.4	371.5	375.4	387.3	403.1
142.5°	487.1	458.4	446.6	434.7	414.0	398.1	387.3	384.3	387.3	398.1	414.0
145°	494.0	467.3	456.4	445.6	425.8	411.0	401.1	397.2	401.1	411.0	425.8
147.5°	499.9	474.2	464.4	454.5	437.7	423.8	414.0	411.0	414.0	423.8	437.7
150°	503.9	481.1	472.2	463.4	448.5	435.7	427.8	424.8	427.8	435.7	448.5
152.5°	507.8	488.1	480.2	472.2	458.4	447.5	439.6	438.7	439.6	447.5	458.4
155°	511.8	495.0	487.6	480.1	469.3	458.4	452.5	451.5	452.5	458.4	469.3
157.5°	514.7	499.9	493.5	487.1	478.2	468.3	463.4	462.4	463.4	468.3	478.2
160°	516.7	504.8	499.4	494.0	486.1	478.2	474.2	473.2	474.2	478.2	486.1
162.5°	517.7	507.8	503.8	499.9	493.0	487.1	483.1	484.1	483.1	487.1	493.0
165°	518.7	509.8	506.8	503.9	498.9	493.0	491.0	492.0	491.0	493.0	498.9
167.5°	518.7	511.8	509.8	507.8	503.9	499.9	497.9	498.9	497.9	499.9	503.9
170°	517.7	512.8	511.3	509.8	507.8	504.8	503.9	505.8	503.9	504.8	507.8
172.5°	516.7	513.7	512.8	511.8	510.8	507.8	508.8	509.8	508.8	507.8	510.8
175°	515.7	513.7	513.2	512.8	512.8	510.8	511.8	512.8	511.8	510.8	512.8
177.5°	514.7	513.7	513.7	513.7	513.7	511.8	512.8	514.7	512.8	511.8	513.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	957.3	961.0	960.2	952.8	944.6	937.9	925.3	926.8	922.3	923.1	927.5
5°	933.5	933.5	930.5	920.1	906.7	899.3	885.1	881.4	872.5	871.7	871.0
7.5°	908.2	904.5	900.7	885.9	869.5	857.6	838.3	833.8	824.9	818.9	815.9
10°	878.4	873.2	865.8	848.7	828.6	813.7	793.6	787.7	770.6	763.1	758.7
12.5°	845.7	842.7	830.8	816.7	784.0	767.6	738.6	744.5	727.4	712.6	710.3
15°	813.0	801.8	795.1	772.1	732.6	725.2	702.1	690.2	674.6	662.7	662.7
17.5°	781.0	763.9	749.0	724.5	695.5	674.6	657.5	651.6	632.2	620.3	618.1
20°	738.6	719.3	715.5	680.6	660.5	637.4	621.1	606.2	592.1	586.9	583.1
22.5°	698.4	676.1	670.2	640.4	620.3	597.3	580.9	570.5	560.1	556.4	549.7
25°	655.3	641.9	633.0	601.0	578.7	557.1	545.9	538.5	528.8	528.1	523.6
27.5°	613.6	601.0	592.1	561.6	545.2	525.1	516.2	508.0	502.8	500.6	498.3
30°	577.9	563.8	553.4	531.1	511.0	494.6	487.2	482.0	479.0	475.3	474.5
32.5°	538.5	530.3	516.2	499.1	483.5	467.8	463.4	459.7	455.2	453.7	453.0
35°	505.0	493.9	485.0	465.6	458.9	445.5	440.3	437.4	431.4	429.9	428.4
37.5°	472.3	461.9	452.2	440.3	427.7	420.2	417.3	412.8	409.8	410.6	409.1
40°	439.6	431.4	424.0	411.3	403.9	400.2	394.2	389.8	388.3	389.0	388.3
42.5°	407.6	400.2	395.7	386.0	378.6	374.9	371.2	366.7	368.9	368.9	371.2
45°	378.6	371.9	368.9	361.5	357.0	351.1	347.4	346.6	349.6	348.8	348.8
47.5°	348.8	346.6	342.9	336.2	330.2	326.5	325.8	325.8	328.8	330.2	329.5
50°	325.8	321.3	316.9	311.7	307.2	305.7	303.5	305.0	307.9	307.9	309.4
52.5°	296.8	293.8	292.3	287.8	284.9	284.9	284.9	285.6	287.8	290.1	289.3
55°	271.5	269.3	267.8	265.5	261.8	262.6	261.8	263.3	265.5	267.8	269.3
57.5°	244.7	244.0	242.5	238.8	238.8	238.0	240.2	241.0	244.7	246.2	248.4
60°	220.9	218.7	218.7	215.7	215.7	215.7	217.9	220.2	223.1	223.9	225.4
62.5°	195.6	195.6	194.9	192.6	192.6	194.9	195.6	198.6	200.1	200.1	202.3
65°	171.8	171.1	170.3	171.1	171.8	171.8	174.0	175.5	177.0	177.8	178.5
67.5°	148.0	147.3	148.8	148.0	149.5	152.5	151.7	154.0	156.2	156.2	156.9
70°	125.7	127.2	126.4	127.9	127.2	128.7	130.9	131.7	131.7	132.4	134.6
72.5°	104.9	104.9	104.9	104.1	104.9	106.4	107.9	108.6	110.1	110.8	113.1
75°	84.8	84.8	83.3	84.8	84.8	86.3	87.8	87.8	87.8	89.3	91.5
77.5°	64.0	64.7	64.0	65.5	65.5	66.2	67.7	66.9	68.4	69.2	69.9
80°	46.9	46.1	46.1	46.1	46.9	46.9	48.3	49.1	49.1	51.3	49.8
82.5°	29.8	30.5	29.8	30.5	30.5	31.2	30.5	31.2	32.0	33.5	32.7
85°	17.1	16.4	16.4	17.1	16.4	16.4	17.1	16.4	17.1	16.4	17.1
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	11.9	13.4	14.8	19.8	26.7	32.6	33.6	32.6	31.6	29.6	31.6
92.5°	41.5	47.0	52.4	79.0	116.6	150.2	152.1	127.4	99.8	85.0	74.1
95°	73.1	84.9	96.8	142.3	228.2	342.8	387.3	338.9	258.8	198.6	157.1
97.5°	98.8	112.2	125.5	183.8	303.3	488.1	631.3	636.2	529.5	422.8	323.1
100°	123.5	137.4	151.2	203.5	324.1	537.5	780.5	922.8	902.0	779.5	644.2
102.5°	146.2	160.0	173.9	221.3	325.0	518.7	785.4	1029.5	1146.0	1142.1	1052.2
105°	168.0	181.8	195.6	242.1	330.0	493.0	732.1	994.9	1200.4	1312.0	1324.9
107.5°	189.7	203.6	217.4	262.8	340.8	479.2	682.7	921.8	1142.1	1308.1	1404.9
110°	211.4	225.8	240.1	283.5	354.7	475.2	649.1	853.6	1062.1	1238.9	1365.4

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	232.2	247.0	261.8	303.3	369.5	476.2	627.4	806.2	988.9	1156.9	1294.2
115°	254.9	268.2	281.6	324.1	384.3	480.1	612.5	768.6	931.6	1083.8	1213.2
117.5°	275.6	289.5	303.3	342.8	400.1	486.1	604.6	742.9	884.2	1020.6	1141.1
120°	296.4	310.2	324.1	362.6	415.9	492.0	597.7	723.2	850.6	973.1	1077.9
122.5°	317.1	331.5	345.8	381.4	429.8	498.9	593.8	706.4	824.0	933.6	1031.4
125°	336.9	350.8	364.6	400.1	444.6	505.8	588.8	690.6	798.3	900.0	987.0
127.5°	354.7	369.0	383.3	417.9	458.4	512.8	585.9	675.8	772.6	866.4	949.4
130°	371.5	385.3	399.1	433.7	471.3	520.7	583.9	660.9	747.9	832.9	910.9
132.5°	387.3	401.1	414.9	447.5	484.1	528.6	582.9	649.1	724.2	801.2	871.4
135°	401.1	415.0	428.8	460.4	495.0	534.5	581.9	638.2	702.4	767.6	832.9
137.5°	414.0	426.8	439.6	471.3	503.9	540.4	581.9	630.3	684.7	741.0	794.3
140°	424.8	437.6	450.5	480.1	510.8	544.4	580.9	623.4	667.9	715.3	760.7
142.5°	434.7	446.6	458.4	487.1	516.7	547.3	580.9	616.5	654.0	692.6	730.1
145°	445.6	456.4	467.3	494.0	521.6	549.3	578.9	610.6	641.2	673.8	704.4
147.5°	454.5	464.4	474.2	499.9	524.6	550.3	576.0	604.6	631.3	658.0	682.7
150°	463.4	472.2	481.1	503.9	526.6	549.3	573.0	596.7	620.4	642.2	662.9
152.5°	472.2	480.2	488.1	507.8	527.6	547.3	568.1	589.8	609.6	629.3	646.1
155°	480.1	487.6	495.0	511.8	528.6	545.4	562.2	580.9	599.7	615.5	630.3
157.5°	487.1	493.5	499.9	514.7	528.6	541.4	556.2	573.0	587.8	601.7	614.5
160°	494.0	499.4	504.8	516.7	528.6	538.4	550.3	564.1	577.0	587.8	598.7
162.5°	499.9	503.8	507.8	517.7	527.6	535.5	545.4	556.2	566.1	575.0	583.9
165°	503.9	506.8	509.8	518.7	525.6	531.5	538.4	547.3	555.2	562.2	569.1
167.5°	507.8	509.8	511.8	518.7	524.6	527.6	532.5	538.4	544.4	550.3	555.2
170°	509.8	511.3	512.8	517.7	522.6	524.6	527.6	531.5	536.5	539.4	543.4
172.5°	511.8	512.8	513.7	516.7	519.7	520.7	521.6	524.6	527.6	529.5	532.5
175°	512.8	513.2	513.7	515.7	517.7	516.7	517.7	518.7	521.6	522.6	523.6
177.5°	513.7	513.7	513.7	514.7	516.7	514.7	513.7	514.7	516.7	516.7	517.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	922.3	924.5	919.3	917.8	919.3	914.1	915.6	917.1	917.1	919.3	920.8
5°	868.8	865.8	860.6	859.1	857.6	859.8	858.3	860.6	861.3	866.5	867.3
7.5°	815.9	811.5	807.0	802.6	801.1	797.4	801.1	801.1	806.3	804.8	808.5
10°	753.5	752.7	746.8	744.5	741.6	735.6	743.8	741.6	745.3	752.0	753.5
12.5°	707.4	699.2	702.9	692.5	696.2	690.2	691.0	691.0	696.9	697.7	696.2
15°	663.5	656.8	647.1	642.6	640.4	637.4	647.1	647.8	643.4	653.8	650.1
17.5°	618.8	618.8	609.9	607.7	601.7	604.7	603.2	604.0	602.5	609.9	613.6
20°	580.2	576.4	573.5	574.2	566.8	565.3	563.8	565.3	570.5	575.7	577.2
22.5°	548.9	546.7	539.3	540.7	534.8	537.0	535.5	539.3	540.0	540.0	545.2
25°	519.2	516.2	516.9	514.0	511.7	511.7	509.5	511.7	514.7	516.2	516.9
27.5°	496.9	494.6	490.9	488.7	490.2	486.4	489.4	491.7	491.7	490.2	491.7
30°	470.1	471.6	471.6	464.1	467.1	465.6	467.8	469.3	469.3	470.1	468.6
32.5°	452.2	447.8	447.0	446.3	446.3	443.3	443.3	445.5	446.3	447.0	449.3
35°	428.4	428.4	424.7	426.9	424.0	424.7	424.0	424.7	426.2	424.0	426.2
37.5°	406.9	407.6	406.1	407.6	408.3	406.9	405.4	408.3	406.9	406.9	405.4
40°	388.3	387.5	388.3	388.3	388.3	389.0	387.5	387.5	387.5	386.0	384.5
42.5°	372.6	368.2	369.7	370.4	368.2	368.2	368.9	368.2	370.4	365.9	365.9
45°	350.3	348.8	349.6	349.6	351.1	348.8	350.3	351.1	348.8	348.1	346.6
47.5°	330.2	331.7	330.2	331.7	331.7	333.2	330.2	331.0	331.7	328.8	326.5
50°	310.2	310.2	312.4	311.7	312.4	310.9	310.9	310.2	310.9	309.4	307.2
52.5°	291.6	289.3	293.1	292.3	291.6	290.8	290.1	290.8	289.3	287.8	287.8
55°	268.5	268.5	270.7	271.5	271.5	270.0	268.5	269.3	268.5	267.8	267.0
57.5°	249.9	246.9	248.4	249.2	249.2	246.9	248.4	246.9	246.9	247.7	245.5
60°	226.1	226.1	224.6	226.9	226.9	225.4	225.4	226.1	224.6	223.9	223.1
62.5°	200.8	201.6	203.8	204.5	205.3	203.8	202.3	203.1	203.1	200.8	201.6
65°	179.3	180.7	183.7	183.0	181.5	182.2	180.7	181.5	179.3	180.0	177.8
67.5°	158.4	157.7	158.4	158.4	159.9	159.2	157.7	157.7	156.9	159.2	156.9
70°	136.1	136.1	136.1	136.1	136.9	137.6	136.1	134.6	135.4	133.9	133.1
72.5°	113.1	113.8	113.1	114.5	112.3	113.8	113.8	113.1	112.3	112.3	112.3
75°	91.5	93.0	90.7	91.5	90.7	92.2	91.5	91.5	90.0	89.3	90.0
77.5°	69.9	70.7	69.2	69.9	69.2	69.9	69.9	69.2	69.2	69.2	69.2
80°	49.8	50.6	49.8	49.1	48.3	49.8	48.3	49.1	49.8	49.1	50.6
82.5°	32.0	32.0	31.2	32.0	30.5	30.5	31.2	31.2	30.5	32.0	30.5
85°	15.6	15.6	17.1	15.6	14.9	14.9	14.9	15.6	14.9	16.4	15.6
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	32.1	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.1
92.5°	70.2	66.2	65.2	61.3	62.2	60.3	62.2	61.3	65.2	66.2	70.2
95°	146.2	135.4	122.5	114.6	111.6	112.6	111.6	114.6	122.5	135.4	146.2
97.5°	293.5	263.8	225.3	205.5	194.6	188.7	194.6	205.5	225.3	263.8	293.5
100°	584.4	524.6	442.6	400.1	371.5	353.7	371.5	400.1	442.6	524.6	584.4
102.5°	988.0	923.7	832.9	752.8	715.3	689.6	715.3	752.8	832.9	923.7	988.0
105°	1308.6	1292.3	1231.0	1169.7	1127.3	1113.4	1127.3	1169.7	1231.0	1292.3	1308.6
107.5°	1424.6	1444.4	1443.4	1434.5	1421.7	1399.0	1421.7	1434.5	1443.4	1444.4	1424.6
110°	1405.9	1446.4	1488.9	1507.6	1516.5	1515.5	1516.5	1507.6	1488.9	1446.4	1405.9

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1342.2	1390.1	1453.3	1487.9	1506.6	1513.6	1506.6	1487.9	1453.3	1390.1	1342.2
115°	1264.1	1315.0	1385.1	1430.6	1456.3	1465.1	1456.3	1430.6	1385.1	1315.0	1264.1
117.5°	1189.5	1237.9	1310.0	1358.4	1385.1	1392.0	1385.1	1358.4	1310.0	1237.9	1189.5
120°	1122.8	1167.8	1236.9	1283.4	1312.0	1321.9	1312.0	1283.4	1236.9	1167.8	1122.8
122.5°	1071.0	1110.5	1170.7	1216.2	1240.9	1248.8	1240.9	1216.2	1170.7	1110.5	1071.0
125°	1024.0	1061.1	1118.4	1155.9	1180.6	1188.5	1180.6	1155.9	1118.4	1061.1	1024.0
127.5°	984.0	1018.6	1069.0	1104.5	1126.3	1132.2	1126.3	1104.5	1069.0	1018.6	984.0
130°	943.5	976.1	1024.5	1058.1	1077.9	1085.8	1077.9	1058.1	1024.5	976.1	943.5
132.5°	901.5	931.6	979.1	1012.7	1030.4	1037.4	1030.4	1012.7	979.1	931.6	901.5
135°	860.6	888.2	930.7	963.3	981.0	985.0	981.0	963.3	930.7	888.2	860.6
137.5°	819.0	843.7	884.2	912.9	928.7	934.6	928.7	912.9	884.2	843.7	819.0
140°	782.4	804.2	835.8	861.5	876.3	882.2	876.3	861.5	835.8	804.2	782.4
142.5°	747.4	764.7	794.3	817.0	829.9	829.9	829.9	817.0	794.3	764.7	747.4
145°	718.8	733.1	756.8	773.6	783.5	786.4	783.5	773.6	756.8	733.1	718.8
147.5°	693.6	704.4	725.2	739.0	745.9	747.9	745.9	739.0	725.2	704.4	693.6
150°	671.8	680.7	695.5	707.4	713.3	714.3	713.3	707.4	695.5	680.7	671.8
152.5°	653.5	660.9	671.8	681.7	685.6	685.6	685.6	681.7	671.8	660.9	653.5
155°	635.8	641.2	652.1	659.0	662.9	660.9	662.9	659.0	652.1	641.2	635.8
157.5°	619.0	623.4	631.3	637.2	639.2	639.2	639.2	637.2	631.3	623.4	619.0
160°	602.2	605.6	612.5	617.5	618.5	618.5	618.5	617.5	612.5	605.6	602.2
162.5°	586.3	588.8	595.7	598.7	599.7	598.7	599.7	598.7	595.7	588.8	586.3
165°	571.0	573.0	577.0	580.9	580.9	579.9	580.9	580.9	577.0	573.0	571.0
167.5°	557.2	559.2	561.2	563.1	563.1	562.2	563.1	563.1	561.2	559.2	557.2
170°	544.4	545.4	546.3	549.3	548.3	546.3	548.3	549.3	546.3	545.4	544.4
172.5°	533.0	533.5	534.5	535.5	534.5	533.5	534.5	535.5	534.5	533.5	533.0
175°	524.1	524.6	524.6	525.6	524.6	522.6	524.6	525.6	524.6	524.6	524.1
177.5°	517.7	517.7	517.7	517.7	516.7	514.7	516.7	517.7	517.7	517.7	517.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	918.6	924.5	922.3	914.1	923.8	923.8	930.5	930.5	938.7	941.6	946.1
5°	866.5	871.0	874.7	871.0	877.7	888.1	894.0	899.3	910.4	914.9	921.6
7.5°	810.7	818.9	822.6	822.6	833.8	845.7	857.6	865.0	880.7	886.6	893.3
10°	756.4	766.1	773.6	772.8	791.4	798.8	813.7	830.8	846.4	855.4	865.0
12.5°	699.2	704.4	714.8	729.7	734.1	747.5	764.6	786.2	814.5	822.6	836.8
15°	651.6	665.7	673.9	680.6	691.0	703.6	722.2	743.1	771.3	789.2	804.0
17.5°	611.4	630.0	635.2	633.7	647.1	666.4	688.0	703.6	728.9	750.5	764.6
20°	578.7	586.1	595.0	598.8	609.2	630.0	650.8	668.7	689.5	706.6	723.0
22.5°	545.9	551.9	559.3	566.0	574.2	586.1	606.2	628.5	648.6	665.0	683.6
25°	519.2	522.9	529.6	534.8	543.7	551.9	566.0	590.6	614.4	624.0	640.4
27.5°	493.1	496.1	500.6	506.5	511.0	519.2	531.8	551.9	576.4	586.1	608.4
30°	470.1	472.3	476.8	479.7	482.0	491.7	501.3	516.9	535.5	548.9	565.3
32.5°	448.5	450.7	455.2	455.9	458.9	464.1	473.1	487.2	503.6	514.7	528.8
35°	424.7	426.2	430.7	432.1	434.4	438.8	445.5	455.9	470.8	479.0	491.7
37.5°	406.1	405.4	408.3	410.6	413.6	415.8	418.0	428.4	439.6	447.0	456.7
40°	386.0	384.5	385.3	388.3	389.8	392.7	392.7	403.1	410.6	416.5	424.0
42.5°	365.9	365.2	363.7	365.2	366.7	367.4	368.2	375.6	383.1	388.3	396.4
45°	345.9	345.1	343.6	344.4	344.4	345.9	348.1	351.1	356.3	360.7	365.2
47.5°	327.3	325.8	323.6	322.8	324.3	324.3	324.3	327.3	332.5	334.0	338.4
50°	307.9	305.7	302.7	301.2	301.2	300.5	302.0	302.7	307.2	308.7	312.4
52.5°	287.1	285.6	282.6	279.7	280.4	278.9	279.7	280.4	281.9	284.1	286.4
55°	266.3	263.3	261.1	260.3	258.1	258.1	255.9	258.8	258.1	258.8	261.8
57.5°	246.2	243.2	239.5	238.0	235.8	235.0	233.6	232.8	233.6	235.8	238.0
60°	222.4	220.9	218.7	216.4	215.0	212.7	211.2	211.2	210.5	210.5	211.2
62.5°	199.3	198.6	195.6	194.9	193.4	191.9	189.7	188.2	188.2	189.7	190.4
65°	177.0	176.3	174.0	173.3	169.6	168.1	167.4	166.6	165.1	165.1	165.1
67.5°	156.2	154.0	154.0	150.2	147.3	145.8	144.3	143.6	143.6	143.6	144.3
70°	133.1	133.1	130.9	128.7	125.7	126.4	124.2	122.0	122.0	120.5	121.2
72.5°	110.8	110.1	107.9	107.1	104.9	102.6	101.2	102.6	100.4	99.7	100.4
75°	89.3	88.5	87.0	85.5	86.3	84.0	81.8	81.1	81.1	79.6	79.6
77.5°	68.4	69.9	66.9	66.2	64.7	63.2	62.5	61.7	61.7	61.7	63.2
80°	47.6	48.3	48.3	46.9	47.6	45.4	45.4	45.4	43.1	43.9	44.6
82.5°	30.5	30.5	29.8	30.5	29.8	29.8	29.0	29.0	28.3	28.3	29.0
85°	17.1	16.4	15.6	17.1	16.4	16.4	15.6	15.6	15.6	15.6	15.6
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	31.6	29.6	31.6	32.6	33.6	32.6	26.7	19.8	14.8	13.4	11.9
92.5°	74.1	85.0	99.8	127.4	152.1	150.2	116.6	79.0	52.4	47.0	41.5
95°	157.1	198.6	258.8	338.9	387.3	342.8	228.2	142.3	96.8	84.9	73.1
97.5°	323.1	422.8	529.5	636.2	631.3	488.1	303.3	183.8	125.5	112.2	98.8
100°	644.2	779.5	902.0	922.8	780.5	537.5	324.1	203.5	151.2	137.4	123.5
102.5°	1052.2	1142.1	1146.0	1029.5	785.4	518.7	325.0	221.3	173.9	160.0	146.2
105°	1324.9	1312.0	1200.4	994.9	732.1	493.0	330.0	242.1	195.6	181.8	168.0
107.5°	1404.9	1308.1	1142.1	921.8	682.7	479.2	340.8	262.8	217.4	203.6	189.7
110°	1365.4	1238.9	1062.1	853.6	649.1	475.2	354.7	283.5	240.1	225.8	211.4

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1294.2	1156.9	988.9	806.2	627.4	476.2	369.5	303.3	261.8	247.0	232.2
115°	1213.2	1083.8	931.6	768.6	612.5	480.1	384.3	324.1	281.6	268.2	254.9
117.5°	1141.1	1020.6	884.2	742.9	604.6	486.1	400.1	342.8	303.3	289.5	275.6
120°	1077.9	973.1	850.6	723.2	597.7	492.0	415.9	362.6	324.1	310.2	296.4
122.5°	1031.4	933.6	824.0	706.4	593.8	498.9	429.8	381.4	345.8	331.5	317.1
125°	987.0	900.0	798.3	690.6	588.8	505.8	444.6	400.1	364.6	350.8	336.9
127.5°	949.4	866.4	772.6	675.8	585.9	512.8	458.4	417.9	383.3	369.0	354.7
130°	910.9	832.9	747.9	660.9	583.9	520.7	471.3	433.7	399.1	385.3	371.5
132.5°	871.4	801.2	724.2	649.1	582.9	528.6	484.1	447.5	414.9	401.1	387.3
135°	832.9	767.6	702.4	638.2	581.9	534.5	495.0	460.4	428.8	415.0	401.1
137.5°	794.3	741.0	684.7	630.3	581.9	540.4	503.9	471.3	439.6	426.8	414.0
140°	760.7	715.3	667.9	623.4	580.9	544.4	510.8	480.1	450.5	437.6	424.8
142.5°	730.1	692.6	654.0	616.5	580.9	547.3	516.7	487.1	458.4	446.6	434.7
145°	704.4	673.8	641.2	610.6	578.9	549.3	521.6	494.0	467.3	456.4	445.6
147.5°	682.7	658.0	631.3	604.6	576.0	550.3	524.6	499.9	474.2	464.4	454.5
150°	662.9	642.2	620.4	596.7	573.0	549.3	526.6	503.9	481.1	472.2	463.4
152.5°	646.1	629.3	609.6	589.8	568.1	547.3	527.6	507.8	488.1	480.2	472.2
155°	630.3	615.5	599.7	580.9	562.2	545.4	528.6	511.8	495.0	487.6	480.1
157.5°	614.5	601.7	587.8	573.0	556.2	541.4	528.6	514.7	499.9	493.5	487.1
160°	598.7	587.8	577.0	564.1	550.3	538.4	528.6	516.7	504.8	499.4	494.0
162.5°	583.9	575.0	566.1	556.2	545.4	535.5	527.6	517.7	507.8	503.8	499.9
165°	569.1	562.2	555.2	547.3	538.4	531.5	525.6	518.7	509.8	506.8	503.9
167.5°	555.2	550.3	544.4	538.4	532.5	527.6	524.6	518.7	511.8	509.8	507.8
170°	543.4	539.4	536.5	531.5	527.6	524.6	522.6	517.7	512.8	511.3	509.8
172.5°	532.5	529.5	527.6	524.6	521.6	520.7	519.7	516.7	513.7	512.8	511.8
175°	523.6	522.6	521.6	518.7	517.7	516.7	517.7	515.7	513.7	513.2	512.8
177.5°	517.7	516.7	516.7	514.7	513.7	514.7	516.7	514.7	513.7	513.7	513.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	967.7	967.7	967.7	967.7
2.5°	949.8	949.8	961.0	972.9
5°	929.0	934.2	952.1	968.4
7.5°	908.9	917.8	940.2	961.0
10°	884.4	896.3	923.8	948.3
12.5°	860.6	871.7	903.7	931.2
15°	827.1	841.2	875.5	909.7
17.5°	793.6	807.8	849.4	889.6
20°	754.2	772.8	819.7	873.2
22.5°	717.8	740.8	792.9	836.0
25°	677.6	713.3	761.6	817.4
27.5°	641.9	677.6	726.7	783.2
30°	601.7	638.2	688.8	740.8
32.5°	563.1	596.5	645.6	709.6
35°	522.9	554.9	602.5	667.2
37.5°	486.4	517.7	569.7	629.3
40°	450.7	483.5	528.1	587.6
42.5°	417.3	446.3	486.4	545.9
45°	386.8	407.6	444.8	500.6
47.5°	354.8	373.4	407.6	463.4
50°	325.0	340.7	370.4	422.5
52.5°	296.0	309.4	336.9	378.6
55°	270.0	282.6	302.7	343.6
57.5°	243.2	252.9	272.2	305.0
60°	217.2	226.1	241.7	268.5
62.5°	191.2	198.6	213.5	235.0
65°	168.1	174.0	185.2	203.8
67.5°	145.8	149.5	158.4	173.3
70°	124.2	127.2	134.6	146.5
72.5°	101.2	104.1	112.3	120.5
75°	81.8	82.6	88.5	95.2
77.5°	64.0	63.2	67.7	72.9
80°	43.9	46.1	49.8	52.1
82.5°	29.8	30.5	32.0	33.5
85°	16.4	17.1	17.1	19.3
87.5°	6.7	7.4	7.4	8.2
90°	9.9	7.9	4.0	1.0
92.5°	33.6	28.7	20.7	14.8
95°	57.3	48.4	38.5	34.6
97.5°	81.0	68.2	57.3	51.4
100°	103.7	87.9	79.0	76.1
102.5°	125.5	109.7	100.8	98.8
105°	146.2	131.4	124.5	120.5
107.5°	168.0	154.1	147.2	144.2
110°	190.7	177.8	171.9	168.0

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	212.4	200.6	193.6	189.7
115°	235.1	223.3	217.4	212.4
117.5°	256.9	246.0	240.1	236.1
120°	276.6	267.7	261.8	257.9
122.5°	297.4	287.5	281.6	278.6
125°	317.1	305.3	299.4	296.4
127.5°	335.9	323.1	315.2	311.2
130°	351.7	337.9	328.0	324.1
132.5°	366.5	351.7	340.8	335.9
135°	378.4	363.6	351.7	347.8
137.5°	391.2	375.4	363.6	358.6
140°	403.1	387.3	375.4	371.5
142.5°	414.0	398.1	387.3	384.3
145°	425.8	411.0	401.1	397.2
147.5°	437.7	423.8	414.0	411.0
150°	448.5	435.7	427.8	424.8
152.5°	458.4	447.5	439.6	438.7
155°	469.3	458.4	452.5	451.5
157.5°	478.2	468.3	463.4	462.4
160°	486.1	478.2	474.2	473.2
162.5°	493.0	487.1	483.1	484.1
165°	498.9	493.0	491.0	492.0
167.5°	503.9	499.9	497.9	498.9
170°	507.8	504.8	503.9	505.8
172.5°	510.8	507.8	508.8	509.8
175°	512.8	510.8	511.8	512.8
177.5°	513.7	511.8	512.8	514.7
180°	513.7	513.7	513.7	513.7

TEST NUMBER: P998641

CATALOG NUMBER: SA2XXDIP-B485D925UB30-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.02	14.76	15.09	15.82	17.26	11.51	12.25	12.58	13.31	14.76
	3H	14.82	15.48	15.90	16.55	18.01	12.85	13.51	13.92	14.58	16.04
	4H	14.99	15.61	16.07	16.68	18.15	13.31	13.93	14.39	15.00	16.47
	6H	15.03	15.60	16.12	16.68	18.15	13.61	14.18	14.70	15.26	16.74
	8H	15.00	15.55	16.10	16.64	18.11	13.69	14.23	14.78	15.32	16.80
	12H	14.96	15.48	16.06	16.56	18.06	13.73	14.24	14.83	15.33	16.83
4H	2H	14.05	14.67	15.14	15.74	17.21	11.94	12.57	13.04	13.64	15.11
	3H	15.02	15.54	16.11	16.64	18.12	13.39	13.91	14.49	15.01	16.49
	4H	15.29	15.76	16.39	16.85	18.36	13.92	14.40	15.03	15.49	16.99
	6H	15.41	15.82	16.52	16.93	18.43	14.30	14.70	15.41	15.82	17.31
	8H	15.41	15.79	16.52	16.89	18.40	14.40	14.79	15.51	15.89	17.40
	12H	15.37	15.71	16.49	16.83	18.34	14.46	14.80	15.58	15.92	17.43
8H	4H	15.29	15.67	16.40	16.77	18.28	14.06	14.44	15.17	15.54	17.05
	6H	15.46	15.78	16.59	16.92	18.43	14.49	14.80	15.62	15.95	17.46
	8H	15.49	15.77	16.63	16.89	18.42	14.64	14.91	15.77	16.04	17.57
	12H	15.47	15.71	16.61	16.84	18.40	14.72	14.96	15.86	16.09	17.65
12H	4H	15.24	15.58	16.37	16.70	18.22	14.03	14.37	15.15	15.49	17.00
	6H	15.44	15.71	16.58	16.84	18.37	14.49	14.76	15.62	15.89	17.42
	8H	15.47	15.71	16.61	16.83	18.40	14.64	14.88	15.78	16.00	17.57