

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999871

Luminaire Tested: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999871
REPORT IS A COMBINATION OF REPORTS P988426 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6888.0 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44
1	95	91	88	85	87	83	80	77	68	66	64	53	52	51	40	39	39
2	87	81	75	70	79	73	69	64	60	57	54	48	45	43	36	35	33
3	80	71	65	59	73	65	59	55	53	49	46	43	40	37	33	31	29
4	74	64	56	51	67	58	52	47	48	43	40	38	35	33	29	27	26
5	68	57	49	44	61	52	46	41	43	38	35	35	31	29	27	25	23
6	63	51	44	38	57	47	40	36	39	34	30	32	28	25	25	22	20
7	58	46	39	34	53	43	36	31	36	31	27	29	25	23	23	20	18
8	54	42	35	30	49	39	32	28	33	28	24	27	23	20	21	19	17
9	50	39	32	27	46	36	29	25	30	25	22	25	21	19	20	17	15
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23476	23476	23476	23476
5°	23531	24936	23613	19921
10°	23273	26356	23438	16450
15°	22767	26365	23153	12359
20°	22160	21793	22641	10196
25°	21423	13618	21886	8673
30°	20483	8719	21040	7468
35°	19339	6701	19966	6390
40°	18063	5632	18837	5589
45°	16701	4794	17400	4692
50°	15305	4074	16020	4058
55°	13760	3540	14501	3493
60°	12384	2699	13042	2667
65°	11102	2031	11760	2304
70°	9688	1622	10446	1879
75°	8190	1242	8939	1420
80°	6499	845	6994	931
85°	4520	437	4944	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21476 cd/sqm

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.7	2.0
10°-20°	392.7	5.7
20°-30°	505.4	7.3
30°-40°	479.4	7.0
40°-50°	410.9	6.0
50°-60°	312.9	4.5
60°-70°	197.3	2.9
70°-80°	98.4	1.4
80°-90°	27.9	0.4
90°-100°	48.6	0.7
100°-110°	181.2	2.6
110°-120°	480.7	7.0
120°-130°	797.2	11.6
130°-140°	846.8	12.3
140°-150°	787.0	11.4
150°-160°	632.7	9.2
160°-170°	407.7	5.9
170°-180°	140.3	2.0
0°-30°	1038.7	15.1
0°-40°	1518.1	22.0
0°-60°	2241.9	32.5
0°-90°	2565.6	37.2
90°-120°	710.5	10.3
90°-150°	3141.6	45.6
90°-180°	4322.0	62.7
0°-180°	6888.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1483	1483	1483	1483	1483	
5°	1484	1650	1489	1318	1484	141
15°	1399	1862	1422	873	1399	393
25°	1241	994	1268	633	1241	570
35°	1018	490	1051	467	1018	637
45°	765	340	797	333	765	590
55°	516	236	544	233	516	465
65°	312	123	331	139	312	310
75°	146	65	160	74	146	158
85°	32	19	35	20	32	36
90°	1	29	1	29	1	6
95°	69	46	69	46	69	82
105°	324	81	324	81	324	347
115°	613	88	613	88	613	604
125°	867	912	867	912	867	774
135°	1073	1108	1073	1108	1073	829
145°	1245	1264	1245	1264	1245	779
155°	1371	1372	1371	1372	1371	632
165°	1444	1441	1444	1441	1444	408
175°	1478	1469	1478	1469	1478	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1492.4	1498.6	1501.7	1505.8	1515.1	1521.2	1530.5	1532.6	1531.6	1535.7	1524.3
5°	1484.1	1497.5	1509.9	1520.2	1536.7	1547.0	1558.3	1571.7	1574.8	1590.3	1581.0
7.5°	1472.8	1492.4	1509.9	1530.5	1555.3	1568.7	1586.2	1606.8	1616.1	1634.6	1639.8
10°	1454.3	1482.1	1512.0	1533.6	1567.6	1591.3	1607.8	1640.8	1662.4	1690.3	1686.1
12.5°	1424.4	1460.4	1500.6	1536.7	1581.0	1596.5	1627.4	1661.4	1689.2	1715.0	1737.7
15°	1398.6	1439.8	1484.1	1528.5	1579.0	1607.8	1638.7	1683.1	1712.9	1758.3	1777.9
17.5°	1363.6	1416.1	1468.7	1518.2	1577.9	1610.9	1649.0	1692.3	1736.7	1779.9	1795.4
20°	1327.5	1384.2	1440.9	1507.8	1575.9	1607.8	1647.0	1700.6	1743.9	1777.9	1777.9
22.5°	1284.2	1353.2	1418.2	1482.1	1556.3	1602.7	1642.9	1705.7	1736.7	1743.9	1716.0
25°	1240.9	1310.0	1381.1	1460.4	1545.0	1586.2	1631.5	1690.3	1700.6	1671.7	1599.6
27.5°	1189.4	1266.7	1347.1	1432.6	1521.2	1572.8	1614.0	1653.2	1633.6	1556.3	1443.9
30°	1136.8	1220.3	1311.0	1392.4	1499.6	1547.0	1582.1	1593.4	1531.6	1405.8	1260.5
32.5°	1082.2	1163.6	1259.5	1357.4	1465.6	1510.9	1533.6	1503.7	1390.4	1231.6	1054.4
35°	1018.3	1110.0	1210.0	1312.0	1419.2	1453.2	1466.6	1393.4	1248.1	1043.0	866.8
37.5°	960.6	1052.3	1159.5	1263.6	1367.7	1386.2	1372.8	1258.4	1073.9	870.9	698.8
40°	892.5	990.5	1095.6	1212.0	1297.6	1302.7	1269.8	1121.4	892.5	701.9	595.7
42.5°	829.7	928.6	1033.7	1152.3	1217.2	1199.7	1155.4	960.6	745.2	605.0	519.4
45°	764.7	858.5	971.9	1077.0	1123.4	1082.2	1015.2	808.0	625.6	520.5	454.5
47.5°	701.9	789.5	901.8	1002.8	1011.1	964.7	885.3	677.1	542.1	457.6	404.0
50°	640.0	727.6	832.8	916.3	908.0	844.1	754.4	588.5	471.0	404.0	359.7
52.5°	578.2	657.6	759.6	825.6	790.5	728.7	640.0	498.8	411.2	352.5	318.5
55°	516.4	590.6	678.2	732.8	677.1	606.0	543.2	427.7	356.6	309.2	283.4
57.5°	464.8	523.6	604.0	636.9	570.0	514.3	459.7	367.9	309.2	275.2	245.3
60°	408.1	461.7	527.7	547.3	478.2	432.9	386.5	311.3	264.9	235.0	215.4
62.5°	359.7	404.0	454.5	454.5	393.7	359.7	324.7	260.8	222.6	198.9	189.6
65°	312.3	344.2	380.3	376.2	324.7	294.8	266.9	215.4	186.5	170.1	160.8
67.5°	265.9	290.6	314.3	299.9	262.8	237.1	211.3	174.2	154.6	143.3	130.9
70°	223.7	243.2	255.6	242.2	205.1	183.5	164.9	140.2	124.7	110.3	103.1
72.5°	187.6	195.8	199.9	183.5	152.5	140.2	126.8	109.2	95.9	88.6	86.6
75°	146.4	153.6	150.5	138.1	112.3	103.1	92.8	80.4	77.3	73.2	71.1
77.5°	114.4	114.4	109.2	97.9	80.4	73.2	69.1	62.9	59.8	58.7	56.7
80°	81.4	80.4	77.3	64.9	54.6	50.5	50.5	46.4	45.3	43.3	43.3
82.5°	53.6	53.6	49.5	39.2	36.1	35.0	34.0	32.0	32.0	30.9	30.9
85°	32.0	29.9	24.7	21.6	20.6	20.6	19.6	18.6	19.6	18.6	18.6
87.5°	14.4	11.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	1.1	3.7	6.3	8.9	11.5	12.8	13.7	15.6	17.5	19.4	21.3
92.5°	26.7	25.7	24.8	23.8	22.9	22.4	22.8	23.5	24.2	24.9	25.6
95°	69.3	61.5	53.7	45.8	38.0	34.1	34.9	36.6	38.3	39.9	41.6
97.5°	124.8	105.4	85.9	66.5	47.0	37.3	39.2	43.0	46.8	50.6	54.4
100°	188.8	156.3	123.9	91.4	58.9	42.7	44.7	48.7	52.8	56.8	60.8
102.5°	259.2	258.7	258.3	257.8	257.3	257.1	235.5	192.4	149.2	106.1	62.9
105°	324.3	331.4	338.5	345.6	352.7	356.3	323.9	259.2	194.5	129.8	65.1
107.5°	400.1	406.0	411.9	417.8	423.7	426.7	386.8	306.9	227.0	147.1	67.2
110°	472.6	477.6	482.6	487.5	492.5	495.0	460.7	392.2	323.7	255.2	186.7

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	540.9	545.2	549.4	553.7	558.0	560.1	558.1	554.1	550.0	546.0	542.0
115°	613.4	617.4	621.5	625.5	629.6	631.6	634.6	640.5	646.4	652.3	658.2
117.5°	676.4	681.1	685.9	690.6	695.3	697.7	699.7	703.8	707.8	711.9	715.9
120°	746.8	750.4	753.9	757.5	761.0	762.8	764.9	769.2	773.5	777.7	782.0
122.5°	806.5	810.3	814.1	817.9	821.7	823.6	826.0	830.7	835.4	840.2	844.9
125°	867.4	870.5	873.5	876.6	879.7	881.2	883.5	888.0	892.5	897.0	901.5
127.5°	922.8	926.1	929.5	932.8	936.1	937.8	939.6	943.1	946.7	950.2	953.8
130°	975.1	978.9	982.7	986.5	990.3	992.2	993.5	996.1	998.7	1001.3	1003.9
132.5°	1028.4	1031.5	1034.6	1037.7	1040.8	1042.3	1043.6	1046.2	1048.9	1051.5	1054.1
135°	1073.3	1077.1	1080.9	1084.6	1088.4	1090.3	1091.4	1093.5	1095.6	1097.8	1099.9
137.5°	1120.2	1123.0	1125.9	1128.7	1131.6	1133.0	1134.2	1136.6	1138.9	1141.3	1143.7
140°	1166.1	1168.0	1169.9	1171.8	1173.7	1174.6	1175.9	1178.5	1181.1	1183.7	1186.3
142.5°	1204.5	1206.1	1207.8	1209.4	1211.1	1211.9	1213.4	1216.5	1219.6	1222.7	1225.8
145°	1245.0	1244.8	1244.6	1244.3	1244.1	1244.0	1246.0	1250.0	1254.1	1258.1	1262.1
147.5°	1280.2	1279.5	1278.8	1278.1	1277.4	1277.0	1279.0	1283.1	1287.1	1291.2	1295.2
150°	1314.4	1312.7	1311.1	1309.4	1307.7	1306.9	1308.8	1312.6	1316.4	1320.2	1324.0
152.5°	1343.2	1341.3	1339.4	1337.5	1335.6	1334.6	1336.4	1339.9	1343.5	1347.0	1350.6
155°	1370.9	1368.8	1366.6	1364.5	1362.4	1361.3	1362.7	1365.6	1368.4	1371.3	1374.1
157.5°	1393.3	1391.4	1389.5	1387.6	1385.7	1384.8	1385.9	1388.0	1390.1	1392.3	1394.4
160°	1412.5	1411.1	1409.7	1408.2	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5
162.5°	1429.6	1428.2	1426.8	1425.3	1423.9	1423.2	1423.8	1425.0	1426.1	1427.3	1428.5
165°	1444.5	1443.1	1441.7	1440.2	1438.8	1438.1	1438.5	1439.2	1439.9	1440.6	1441.3
167.5°	1456.3	1454.9	1453.5	1452.0	1450.6	1449.9	1450.3	1451.0	1451.7	1452.4	1453.1
170°	1465.9	1464.5	1463.1	1461.6	1460.2	1459.5	1459.7	1460.2	1460.7	1461.1	1461.6
172.5°	1472.3	1470.9	1469.5	1468.0	1466.6	1465.9	1466.1	1466.6	1467.1	1467.5	1468.0
175°	1477.6	1475.9	1474.3	1472.6	1470.9	1470.1	1470.3	1470.8	1471.3	1471.8	1472.3
177.5°	1479.7	1478.1	1476.4	1474.8	1473.1	1472.3	1472.4	1472.6	1472.9	1473.1	1473.3
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1535.7	1537.7	1540.8	1555.3	1557.3	1561.4	1559.4	1559.4	1560.4	1558.3	1559.4
5°	1601.6	1604.7	1620.2	1637.7	1641.8	1637.7	1642.9	1650.1	1650.1	1650.1	1648.0
7.5°	1663.5	1674.8	1692.3	1718.1	1723.3	1728.4	1737.7	1731.5	1733.6	1742.8	1739.7
10°	1723.3	1739.7	1759.3	1781.0	1792.3	1799.5	1803.6	1812.9	1834.6	1809.8	1819.1
12.5°	1779.9	1803.6	1824.3	1848.0	1856.2	1865.5	1868.6	1876.8	1876.8	1875.8	1883.0
15°	1817.0	1838.7	1857.2	1872.7	1874.8	1872.7	1870.6	1871.7	1874.8	1862.4	1869.6
17.5°	1825.3	1827.3	1833.5	1827.3	1828.4	1806.7	1794.4	1791.3	1762.4	1763.4	1787.2
20°	1785.1	1750.1	1740.8	1706.8	1686.1	1630.5	1628.4	1613.0	1552.2	1570.7	1566.6
22.5°	1674.8	1615.0	1535.7	1496.5	1476.9	1418.2	1372.8	1340.9	1319.2	1297.6	1288.3
25°	1529.5	1432.6	1320.3	1243.0	1231.6	1177.0	1093.5	1054.4	1008.0	993.6	1018.3
27.5°	1341.9	1216.2	1089.4	970.9	949.2	899.8	857.5	829.7	776.1	773.0	775.1
30°	1087.3	960.6	854.4	777.1	723.5	700.8	673.0	652.4	630.8	639.0	641.1
32.5°	893.6	773.0	674.0	632.8	608.1	593.7	570.0	556.6	547.3	544.2	543.2
35°	710.1	629.7	585.4	545.2	530.8	520.5	503.0	496.8	488.5	489.6	489.6
37.5°	608.1	541.1	508.1	487.5	474.1	468.9	457.6	451.4	446.3	444.2	447.3
40°	524.6	478.2	457.6	439.1	427.7	425.7	419.5	412.3	406.1	407.1	410.2
42.5°	463.8	437.0	412.3	397.8	389.6	386.5	381.3	376.2	376.2	373.1	372.1
45°	415.4	393.7	373.1	359.7	354.5	350.4	344.2	343.2	339.1	340.1	341.1
47.5°	372.1	354.5	339.1	325.7	320.5	319.5	313.3	309.2	309.2	308.2	307.1
50°	332.9	315.4	302.0	294.8	287.6	285.5	284.5	283.4	281.4	281.4	282.4
52.5°	301.0	283.4	273.1	266.9	262.8	260.8	260.8	259.7	259.7	259.7	258.7
55°	265.9	251.5	243.2	241.2	239.1	238.1	237.1	235.0	234.0	236.0	234.0
57.5°	232.9	227.8	220.6	218.5	213.3	213.3	210.3	208.2	206.1	208.2	208.2
60°	207.2	199.9	195.8	189.6	185.5	181.4	176.2	175.2	173.1	172.1	171.1
62.5°	180.4	174.2	163.9	154.6	148.4	144.3	142.2	141.2	141.2	140.2	140.2
65°	150.5	136.0	130.9	127.8	126.8	125.7	123.7	122.6	123.7	122.6	123.7
67.5°	117.5	115.4	112.3	110.3	109.2	108.2	108.2	107.2	107.2	107.2	107.2
70°	102.0	96.9	95.9	93.8	93.8	92.8	92.8	92.8	92.8	91.7	93.8
72.5°	84.5	81.4	80.4	79.4	79.4	79.4	78.3	78.3	78.3	77.3	78.3
75°	69.1	68.0	66.0	66.0	64.9	66.0	64.9	64.9	63.9	64.9	64.9
77.5°	55.7	54.6	53.6	53.6	52.6	52.6	52.6	52.6	52.6	52.6	53.6
80°	42.3	41.2	40.2	41.2	40.2	41.2	40.2	40.2	41.2	40.2	40.2
82.5°	30.9	29.9	29.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9
85°	18.6	17.5	17.5	18.6	17.5	18.6	17.5	17.5	17.5	18.6	18.6
87.5°	8.2	9.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	9.3
90°	22.5	23.7	24.9	26.1	26.7	26.9	27.4	27.9	28.3	28.8	28.3
92.5°	26.1	26.5	27.0	27.5	27.7	27.8	28.1	28.3	28.6	28.8	28.6
95°	42.8	44.0	45.1	46.3	46.9	46.8	46.6	46.3	46.1	45.9	46.1
97.5°	55.1	55.8	56.5	57.2	57.6	57.7	58.0	58.2	58.5	58.7	58.5
100°	62.7	64.6	66.5	68.4	69.3	69.5	70.0	70.5	71.0	71.5	71.0
102.5°	65.5	68.1	70.8	73.4	74.7	75.1	75.8	76.5	77.2	77.9	77.2
105°	67.7	70.3	72.9	75.5	76.8	77.3	78.2	79.2	80.1	81.1	80.1
107.5°	69.8	72.4	75.0	77.6	78.9	79.4	80.3	81.3	82.2	83.2	82.2
110°	163.0	139.3	115.6	91.9	80.0	80.5	81.4	82.4	83.3	84.3	83.3

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	439.8	337.6	235.4	133.2	82.1	82.5	83.2	83.9	84.6	85.3	84.6
115°	548.4	438.7	328.9	219.2	164.3	155.8	138.7	121.6	104.6	87.5	104.6
117.5°	682.0	648.1	614.2	580.3	563.3	532.2	470.1	408.0	345.9	283.8	345.9
120°	784.8	787.7	790.5	793.4	794.8	778.8	746.8	714.8	682.8	650.8	682.8
122.5°	846.3	847.8	849.2	850.7	851.4	851.5	851.7	852.0	852.2	852.4	852.2
125°	903.2	904.8	906.5	908.2	909.0	909.4	910.1	910.8	911.5	912.2	911.5
127.5°	956.2	958.5	960.9	963.2	964.4	964.5	964.8	965.0	965.3	965.5	965.3
130°	1006.5	1009.1	1011.7	1014.3	1015.6	1015.5	1015.3	1015.0	1014.8	1014.6	1014.8
132.5°	1056.2	1058.4	1060.5	1062.6	1063.7	1063.6	1063.3	1063.1	1062.8	1062.6	1062.8
135°	1102.3	1104.7	1107.0	1109.4	1110.6	1110.4	1109.9	1109.4	1109.0	1108.5	1109.0
137.5°	1146.1	1148.4	1150.8	1153.1	1154.3	1153.9	1153.2	1152.5	1151.8	1151.1	1151.8
140°	1188.4	1190.6	1192.7	1194.8	1195.9	1195.3	1194.1	1193.0	1191.8	1190.6	1191.8
142.5°	1227.7	1229.6	1231.5	1233.4	1234.4	1233.8	1232.6	1231.4	1230.2	1229.0	1230.2
145°	1263.8	1265.4	1267.1	1268.8	1269.6	1269.0	1267.8	1266.6	1265.4	1264.2	1265.4
147.5°	1296.4	1297.6	1298.7	1299.9	1300.5	1300.0	1299.1	1298.1	1297.2	1296.2	1297.2
150°	1325.4	1326.8	1328.3	1329.7	1330.4	1329.8	1328.6	1327.4	1326.2	1325.0	1326.2
152.5°	1352.0	1353.4	1354.9	1356.3	1357.0	1356.2	1354.5	1352.9	1351.2	1349.6	1351.2
155°	1375.5	1376.9	1378.4	1379.8	1380.5	1379.6	1377.7	1375.8	1373.9	1372.0	1373.9
157.5°	1396.0	1397.7	1399.3	1401.0	1401.8	1400.9	1399.0	1397.1	1395.2	1393.3	1395.2
160°	1413.9	1415.3	1416.8	1418.2	1418.9	1418.1	1416.4	1414.7	1413.1	1411.4	1413.1
162.5°	1430.2	1431.8	1433.5	1435.2	1436.0	1434.9	1432.8	1430.7	1428.5	1426.4	1428.5
165°	1443.0	1444.6	1446.3	1448.0	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1443.0
167.5°	1454.7	1456.4	1458.0	1459.7	1460.5	1459.4	1457.3	1455.2	1453.0	1450.9	1453.0
170°	1463.3	1464.9	1466.6	1468.3	1469.1	1468.0	1465.9	1463.8	1461.6	1459.5	1461.6
172.5°	1469.7	1471.3	1473.0	1474.7	1475.5	1474.4	1472.3	1470.2	1468.0	1465.9	1468.0
175°	1473.9	1475.6	1477.2	1478.9	1479.7	1478.5	1476.2	1473.8	1471.5	1469.1	1471.5
177.5°	1475.0	1476.6	1478.3	1480.0	1480.8	1479.7	1477.6	1475.5	1473.3	1471.2	1473.3
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1563.5	1556.3	1554.2	1556.3	1554.2	1555.3	1548.0	1521.2	1528.5	1517.1	1523.3
5°	1652.1	1646.0	1632.6	1630.5	1628.4	1626.4	1616.1	1592.4	1583.1	1567.6	1566.6
7.5°	1736.7	1736.7	1726.3	1719.1	1709.9	1702.6	1689.2	1654.2	1639.8	1621.2	1610.9
10°	1820.1	1793.3	1804.7	1797.5	1774.8	1770.7	1745.9	1725.3	1697.5	1678.9	1662.4
12.5°	1879.9	1871.7	1861.4	1855.2	1849.0	1835.6	1819.1	1766.5	1752.1	1715.0	1696.5
15°	1877.9	1872.7	1875.8	1875.8	1873.7	1870.6	1857.2	1819.1	1794.4	1758.3	1726.3
17.5°	1776.8	1790.2	1803.6	1812.9	1833.5	1842.8	1855.2	1832.5	1817.0	1786.1	1752.1
20°	1600.6	1633.6	1672.8	1681.0	1699.5	1754.2	1778.9	1798.5	1804.7	1794.4	1766.5
22.5°	1355.3	1383.1	1478.0	1475.9	1502.7	1567.6	1639.8	1698.5	1744.9	1770.7	1760.4
25°	1061.6	1100.7	1151.2	1189.4	1277.0	1373.9	1463.5	1557.3	1637.7	1708.8	1726.3
27.5°	802.9	854.4	894.6	945.1	989.4	1103.8	1219.3	1365.6	1459.4	1594.4	1664.5
30°	649.3	673.0	713.2	736.9	758.6	846.2	977.1	1121.4	1286.3	1441.9	1562.5
32.5°	554.5	571.0	600.9	611.2	633.9	692.6	775.1	907.0	1077.0	1265.6	1424.4
35°	497.8	515.3	521.5	530.8	549.3	586.4	643.1	739.0	892.5	1077.0	1266.7
37.5°	449.4	458.6	476.2	482.3	488.5	516.4	554.5	621.5	723.5	875.0	1085.3
40°	415.4	420.5	429.8	434.9	439.1	458.6	492.7	538.0	613.2	728.7	922.4
42.5°	379.3	385.5	391.6	397.8	403.0	418.4	439.1	482.3	532.8	620.5	760.6
45°	344.2	348.4	355.6	359.7	366.9	379.3	397.8	427.7	473.1	528.7	642.1
47.5°	312.3	317.4	320.5	325.7	330.8	344.2	361.8	381.3	418.4	473.1	555.5
50°	283.4	289.6	293.7	294.8	298.9	311.3	325.7	347.3	371.0	413.3	485.4
52.5°	262.8	263.8	266.9	271.1	270.0	277.2	290.6	307.1	331.9	365.9	418.4
55°	239.1	242.2	244.3	245.3	245.3	251.5	258.7	274.2	293.7	321.6	365.9
57.5°	209.2	212.3	218.5	220.6	223.7	226.7	229.8	240.1	256.6	283.4	319.5
60°	178.3	180.4	186.5	190.7	192.7	201.0	205.1	213.3	222.6	242.2	276.2
62.5°	143.3	145.3	148.4	152.5	156.7	169.0	179.3	187.6	194.8	208.2	236.0
65°	124.7	125.7	127.8	128.8	129.9	135.0	144.3	155.6	169.0	179.3	195.8
67.5°	108.2	109.2	110.3	112.3	113.4	114.4	118.5	121.6	135.0	149.4	161.8
70°	92.8	94.8	95.9	95.9	96.9	98.9	101.0	105.1	109.2	116.5	131.9
72.5°	78.3	79.4	81.4	81.4	81.4	83.5	85.5	87.6	89.7	93.8	100.0
75°	64.9	67.0	67.0	67.0	68.0	68.0	70.1	72.1	74.2	77.3	79.4
77.5°	53.6	53.6	53.6	53.6	54.6	54.6	55.7	57.7	58.7	59.8	61.8
80°	40.2	41.2	41.2	41.2	42.3	42.3	42.3	44.3	45.3	45.3	47.4
82.5°	29.9	29.9	29.9	30.9	29.9	30.9	30.9	32.0	30.9	32.0	33.0
85°	18.6	18.6	18.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	20.6
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	10.3	9.3	9.3
90°	27.9	27.4	26.9	26.7	26.1	24.9	23.7	22.5	21.3	19.4	17.5
92.5°	28.3	28.1	27.8	27.7	27.5	27.0	26.5	26.1	25.6	24.9	24.2
95°	46.3	46.6	46.8	46.9	46.3	45.1	44.0	42.8	41.6	39.9	38.3
97.5°	58.2	58.0	57.7	57.6	57.2	56.5	55.8	55.1	54.4	50.6	46.8
100°	70.5	70.0	69.5	69.3	68.4	66.5	64.6	62.7	60.8	56.8	52.8
102.5°	76.5	75.8	75.1	74.7	73.4	70.8	68.1	65.5	62.9	106.1	149.2
105°	79.2	78.2	77.3	76.8	75.5	72.9	70.3	67.7	65.1	129.8	194.5
107.5°	81.3	80.3	79.4	78.9	77.6	75.0	72.4	69.8	67.2	147.1	227.0
110°	82.4	81.4	80.5	80.0	91.9	115.6	139.3	163.0	186.7	255.2	323.7

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	83.9	83.2	82.5	82.1	133.2	235.4	337.6	439.8	542.0	546.0	550.0
115°	121.6	138.7	155.8	164.3	219.2	328.9	438.7	548.4	658.2	652.3	646.4
117.5°	408.0	470.1	532.2	563.3	580.3	614.2	648.1	682.0	715.9	711.9	707.8
120°	714.8	746.8	778.8	794.8	793.4	790.5	787.7	784.8	782.0	777.7	773.5
122.5°	852.0	851.7	851.5	851.4	850.7	849.2	847.8	846.3	844.9	840.2	835.4
125°	910.8	910.1	909.4	909.0	908.2	906.5	904.8	903.2	901.5	897.0	892.5
127.5°	965.0	964.8	964.5	964.4	963.2	960.9	958.5	956.2	953.8	950.2	946.7
130°	1015.0	1015.3	1015.5	1015.6	1014.3	1011.7	1009.1	1006.5	1003.9	1001.3	998.7
132.5°	1063.1	1063.3	1063.6	1063.7	1062.6	1060.5	1058.4	1056.2	1054.1	1051.5	1048.9
135°	1109.4	1109.9	1110.4	1110.6	1109.4	1107.0	1104.7	1102.3	1099.9	1097.8	1095.6
137.5°	1152.5	1153.2	1153.9	1154.3	1153.1	1150.8	1148.4	1146.1	1143.7	1141.3	1138.9
140°	1193.0	1194.1	1195.3	1195.9	1194.8	1192.7	1190.6	1188.4	1186.3	1183.7	1181.1
142.5°	1231.4	1232.6	1233.8	1234.4	1233.4	1231.5	1229.6	1227.7	1225.8	1222.7	1219.6
145°	1266.6	1267.8	1269.0	1269.6	1268.8	1267.1	1265.4	1263.8	1262.1	1258.1	1254.1
147.5°	1298.1	1299.1	1300.0	1300.5	1299.9	1298.7	1297.6	1296.4	1295.2	1291.2	1287.1
150°	1327.4	1328.6	1329.8	1330.4	1329.7	1328.3	1326.8	1325.4	1324.0	1320.2	1316.4
152.5°	1352.9	1354.5	1356.2	1357.0	1356.3	1354.9	1353.4	1352.0	1350.6	1347.0	1343.5
155°	1375.8	1377.7	1379.6	1380.5	1379.8	1378.4	1376.9	1375.5	1374.1	1371.3	1368.4
157.5°	1397.1	1399.0	1400.9	1401.8	1401.0	1399.3	1397.7	1396.0	1394.4	1392.3	1390.1
160°	1414.7	1416.4	1418.1	1418.9	1418.2	1416.8	1415.3	1413.9	1412.5	1411.1	1409.7
162.5°	1430.7	1432.8	1434.9	1436.0	1435.2	1433.5	1431.8	1430.2	1428.5	1427.3	1426.1
165°	1444.6	1446.3	1448.0	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1440.6	1439.9
167.5°	1455.2	1457.3	1459.4	1460.5	1459.7	1458.0	1456.4	1454.7	1453.1	1452.4	1451.7
170°	1463.8	1465.9	1468.0	1469.1	1468.3	1466.6	1464.9	1463.3	1461.6	1461.1	1460.7
172.5°	1470.2	1472.3	1474.4	1475.5	1474.7	1473.0	1471.3	1469.7	1468.0	1467.5	1467.1
175°	1473.8	1476.2	1478.5	1479.7	1478.9	1477.2	1475.6	1473.9	1472.3	1471.8	1471.3
177.5°	1475.5	1477.6	1479.7	1480.8	1480.0	1478.3	1476.6	1475.0	1473.3	1473.1	1472.9
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1514.0	1508.9	1508.9	1505.8	1505.8	1489.3	1489.3	1494.4	1488.3	1481.0	1470.7
5°	1553.2	1541.9	1538.8	1534.6	1521.2	1500.6	1492.4	1489.3	1476.9	1461.5	1443.9
7.5°	1590.3	1571.7	1562.5	1553.2	1535.7	1506.8	1490.3	1479.0	1460.4	1436.7	1414.1
10°	1626.4	1602.7	1579.0	1567.6	1542.9	1506.8	1483.1	1464.6	1437.8	1405.8	1373.9
12.5°	1659.4	1609.9	1605.8	1583.1	1547.0	1505.8	1469.7	1442.9	1408.9	1371.8	1334.7
15°	1688.2	1637.7	1613.0	1592.4	1545.0	1493.4	1455.3	1422.3	1377.0	1334.7	1289.3
17.5°	1702.6	1648.0	1631.5	1597.5	1549.1	1482.1	1430.5	1390.4	1340.9	1290.4	1238.8
20°	1717.1	1653.2	1626.4	1602.7	1536.7	1460.4	1402.7	1356.3	1301.7	1241.9	1185.3
22.5°	1724.3	1653.2	1621.2	1588.2	1524.3	1436.7	1368.7	1314.1	1250.2	1189.4	1121.4
25°	1711.9	1647.0	1608.9	1574.8	1502.7	1407.9	1329.5	1267.7	1199.7	1130.6	1061.6
27.5°	1681.0	1632.6	1588.2	1553.2	1472.8	1370.8	1288.3	1218.2	1148.1	1070.8	1000.8
30°	1623.3	1601.6	1566.6	1527.4	1439.8	1337.8	1239.9	1167.7	1090.4	1013.1	940.0
32.5°	1533.6	1552.2	1529.5	1495.5	1400.7	1292.4	1188.3	1115.2	1030.7	947.2	880.2
35°	1424.4	1490.3	1478.0	1454.3	1359.4	1244.0	1139.9	1051.3	966.8	882.2	815.2
37.5°	1304.8	1404.8	1415.1	1400.7	1312.0	1194.5	1080.1	993.6	907.0	821.4	753.4
40°	1140.9	1294.5	1327.5	1333.7	1262.6	1134.8	1015.2	930.7	845.1	761.7	679.2
42.5°	990.5	1184.2	1225.4	1251.2	1199.7	1076.0	955.4	861.6	777.1	701.9	619.4
45°	849.3	1051.3	1118.3	1151.2	1128.6	1009.0	884.3	796.7	719.4	650.3	571.0
47.5°	703.9	907.0	1000.8	1053.3	1053.3	941.0	816.3	729.7	655.5	596.7	526.7
50°	607.1	776.1	873.0	942.0	960.6	871.9	754.4	669.9	599.8	535.9	482.3
52.5°	517.4	668.9	749.3	821.4	875.0	797.7	685.4	609.1	540.1	480.3	438.0
55°	447.3	560.7	633.9	713.2	773.0	722.5	618.4	544.2	484.4	434.9	398.9
57.5°	380.3	479.3	539.0	609.1	673.0	634.9	551.4	487.5	434.9	391.6	359.7
60°	323.6	404.0	450.4	505.0	584.4	557.6	488.5	429.8	387.5	348.4	321.6
62.5°	275.2	339.1	378.3	417.4	489.6	477.2	423.6	378.3	342.2	309.2	286.5
65°	225.7	278.3	309.2	343.2	400.9	406.1	362.8	330.8	297.9	269.0	248.4
67.5°	182.4	223.7	251.5	280.3	326.7	341.1	311.3	284.5	256.6	232.9	214.4
70°	147.4	176.2	196.9	219.5	257.7	275.2	259.7	241.2	218.5	198.9	182.4
72.5°	116.5	135.0	147.4	164.9	195.8	213.3	212.3	195.8	179.3	165.9	152.5
75°	85.5	100.0	110.3	121.6	146.4	162.8	167.0	159.8	143.3	133.0	122.6
77.5°	64.9	73.2	78.3	86.6	104.1	118.5	124.7	122.6	111.3	103.1	95.9
80°	49.5	51.5	53.6	56.7	71.1	84.5	88.6	87.6	81.4	78.3	70.1
82.5°	35.0	36.1	37.1	38.1	43.3	54.6	58.7	60.8	55.7	52.6	45.3
85°	20.6	21.6	21.6	23.7	24.7	27.8	35.0	35.0	34.0	29.9	28.9
87.5°	10.3	10.3	9.3	9.3	10.3	11.3	13.4	15.5	13.4	12.4	11.3
90°	15.6	13.7	12.8	11.5	8.9	6.3	3.7	1.1	3.7	6.3	8.9
92.5°	23.5	22.8	22.4	22.9	23.8	24.8	25.7	26.7	25.7	24.8	23.8
95°	36.6	34.9	34.1	38.0	45.8	53.7	61.5	69.3	61.5	53.7	45.8
97.5°	43.0	39.2	37.3	47.0	66.5	85.9	105.4	124.8	105.4	85.9	66.5
100°	48.7	44.7	42.7	58.9	91.4	123.9	156.3	188.8	156.3	123.9	91.4
102.5°	192.4	235.5	257.1	257.3	257.8	258.3	258.7	259.2	258.7	258.3	257.8
105°	259.2	323.9	356.3	352.7	345.6	338.5	331.4	324.3	331.4	338.5	345.6
107.5°	306.9	386.8	426.7	423.7	417.8	411.9	406.0	400.1	406.0	411.9	417.8
110°	392.2	460.7	495.0	492.5	487.5	482.6	477.6	472.6	477.6	482.6	487.5

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	554.1	558.1	560.1	558.0	553.7	549.4	545.2	540.9	545.2	549.4	553.7
115°	640.5	634.6	631.6	629.6	625.5	621.5	617.4	613.4	617.4	621.5	625.5
117.5°	703.8	699.7	697.7	695.3	690.6	685.9	681.1	676.4	681.1	685.9	690.6
120°	769.2	764.9	762.8	761.0	757.5	753.9	750.4	746.8	750.4	753.9	757.5
122.5°	830.7	826.0	823.6	821.7	817.9	814.1	810.3	806.5	810.3	814.1	817.9
125°	888.0	883.5	881.2	879.7	876.6	873.5	870.5	867.4	870.5	873.5	876.6
127.5°	943.1	939.6	937.8	936.1	932.8	929.5	926.1	922.8	926.1	929.5	932.8
130°	996.1	993.5	992.2	990.3	986.5	982.7	978.9	975.1	978.9	982.7	986.5
132.5°	1046.2	1043.6	1042.3	1040.8	1037.7	1034.6	1031.5	1028.4	1031.5	1034.6	1037.7
135°	1093.5	1091.4	1090.3	1088.4	1084.6	1080.9	1077.1	1073.3	1077.1	1080.9	1084.6
137.5°	1136.6	1134.2	1133.0	1131.6	1128.7	1125.9	1123.0	1120.2	1123.0	1125.9	1128.7
140°	1178.5	1175.9	1174.6	1173.7	1171.8	1169.9	1168.0	1166.1	1168.0	1169.9	1171.8
142.5°	1216.5	1213.4	1211.9	1211.1	1209.4	1207.8	1206.1	1204.5	1206.1	1207.8	1209.4
145°	1250.0	1246.0	1244.0	1244.1	1244.3	1244.6	1244.8	1245.0	1244.8	1244.6	1244.3
147.5°	1283.1	1279.0	1277.0	1277.4	1278.1	1278.8	1279.5	1280.2	1279.5	1278.8	1278.1
150°	1312.6	1308.8	1306.9	1307.7	1309.4	1311.1	1312.7	1314.4	1312.7	1311.1	1309.4
152.5°	1339.9	1336.4	1334.6	1335.6	1337.5	1339.4	1341.3	1343.2	1341.3	1339.4	1337.5
155°	1365.6	1362.7	1361.3	1362.4	1364.5	1366.6	1368.8	1370.9	1368.8	1366.6	1364.5
157.5°	1388.0	1385.9	1384.8	1385.7	1387.6	1389.5	1391.4	1393.3	1391.4	1389.5	1387.6
160°	1408.2	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5	1411.1	1409.7	1408.2
162.5°	1425.0	1423.8	1423.2	1423.9	1425.3	1426.8	1428.2	1429.6	1428.2	1426.8	1425.3
165°	1439.2	1438.5	1438.1	1438.8	1440.2	1441.7	1443.1	1444.5	1443.1	1441.7	1440.2
167.5°	1451.0	1450.3	1449.9	1450.6	1452.0	1453.5	1454.9	1456.3	1454.9	1453.5	1452.0
170°	1460.2	1459.7	1459.5	1460.2	1461.6	1463.1	1464.5	1465.9	1464.5	1463.1	1461.6
172.5°	1466.6	1466.1	1465.9	1466.6	1468.0	1469.5	1470.9	1472.3	1470.9	1469.5	1468.0
175°	1470.8	1470.3	1470.1	1470.9	1472.6	1474.3	1475.9	1477.6	1475.9	1474.3	1472.6
177.5°	1472.6	1472.4	1472.3	1473.1	1474.8	1476.4	1478.1	1479.7	1478.1	1476.4	1474.8
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1466.6	1467.7	1470.7	1461.5	1447.0	1440.9	1422.3	1419.2	1416.1	1416.1	1419.2
5°	1433.6	1429.5	1430.5	1413.0	1392.4	1380.0	1354.3	1358.4	1345.0	1336.8	1338.8
7.5°	1397.6	1386.2	1385.2	1362.5	1336.8	1314.1	1287.3	1281.1	1268.7	1254.3	1248.1
10°	1352.2	1344.0	1328.5	1302.7	1269.8	1251.2	1215.1	1193.5	1190.4	1168.8	1160.5
12.5°	1305.8	1291.4	1275.9	1239.9	1202.8	1172.9	1146.1	1122.4	1105.9	1087.3	1075.0
15°	1252.2	1234.7	1217.2	1179.1	1135.8	1105.9	1065.7	1030.7	982.2	944.1	922.4
17.5°	1193.5	1173.9	1150.2	1108.0	1065.7	1024.5	950.3	909.0	875.0	852.4	839.0
20°	1132.7	1111.0	1087.3	1045.1	971.9	899.8	858.5	826.6	806.0	783.3	766.8
22.5°	1068.8	1046.1	1020.3	954.4	877.1	826.6	794.6	764.7	734.9	722.5	714.2
25°	1009.0	988.4	955.4	865.7	804.9	758.6	722.5	702.9	687.4	671.0	655.5
27.5°	947.2	909.0	862.7	787.4	749.3	701.9	676.1	661.7	634.9	623.5	616.3
30°	873.0	830.7	786.4	732.8	688.5	655.5	631.8	608.1	592.6	581.3	568.9
32.5°	797.7	757.5	729.7	674.0	641.1	607.1	584.4	570.0	547.3	540.1	534.9
35°	732.8	698.8	674.0	628.7	597.8	566.9	550.4	528.7	514.3	500.9	492.7
37.5°	668.9	650.3	624.6	586.4	553.5	528.7	506.1	498.8	479.3	472.0	463.8
40°	624.6	596.7	575.1	542.1	514.3	487.5	473.1	456.6	443.2	431.8	428.8
42.5°	571.0	550.4	538.0	501.9	473.1	457.6	440.1	421.5	411.2	402.0	390.6
45°	530.8	512.2	494.7	465.9	440.1	420.5	405.0	392.7	375.2	371.0	353.5
47.5°	488.5	470.0	456.6	427.7	404.0	385.5	374.1	357.6	343.2	333.9	325.7
50°	446.3	430.8	418.4	393.7	373.1	353.5	338.1	321.6	315.4	299.9	294.8
52.5°	406.1	395.8	382.4	358.7	338.1	321.6	305.1	291.7	282.4	274.2	268.0
55°	372.1	355.6	349.4	323.6	306.1	288.6	274.2	265.9	254.6	249.4	244.3
57.5°	333.9	324.7	314.3	294.8	275.2	258.7	248.4	236.0	229.8	223.7	219.5
60°	301.0	287.6	279.3	262.8	245.3	229.8	220.6	211.3	203.0	197.9	189.6
62.5°	262.8	252.5	247.4	229.8	215.4	201.0	192.7	183.5	177.3	168.0	157.7
65°	229.8	221.6	215.4	201.0	187.6	174.2	165.9	154.6	146.4	141.2	140.2
67.5°	201.0	194.8	185.5	172.1	158.7	148.4	139.1	129.9	128.8	126.8	126.8
70°	169.0	162.8	157.7	143.3	131.9	120.6	118.5	115.4	112.3	111.3	109.2
72.5°	141.2	136.0	129.9	117.5	106.2	103.1	101.0	98.9	95.9	94.8	93.8
75°	114.4	107.2	103.1	91.7	88.6	86.6	84.5	81.4	79.4	78.3	76.3
77.5°	87.6	80.4	80.4	74.2	72.1	69.1	67.0	64.9	63.9	61.8	61.8
80°	61.8	61.8	59.8	56.7	53.6	52.6	49.5	48.4	47.4	48.4	46.4
82.5°	45.3	41.2	41.2	39.2	37.1	36.1	34.0	34.0	33.0	33.0	33.0
85°	25.8	25.8	24.7	22.7	21.6	21.6	20.6	20.6	19.6	19.6	18.6
87.5°	10.3	9.3	10.3	9.3	9.3	8.2	8.2	8.2	7.2	8.2	7.2
90°	11.5	12.8	13.7	15.6	17.5	19.4	21.3	22.5	23.7	24.9	26.1
92.5°	22.9	22.4	22.8	23.5	24.2	24.9	25.6	26.1	26.5	27.0	27.5
95°	38.0	34.1	34.9	36.6	38.3	39.9	41.6	42.8	44.0	45.1	46.3
97.5°	47.0	37.3	39.2	43.0	46.8	50.6	54.4	55.1	55.8	56.5	57.2
100°	58.9	42.7	44.7	48.7	52.8	56.8	60.8	62.7	64.6	66.5	68.4
102.5°	257.3	257.1	235.5	192.4	149.2	106.1	62.9	65.5	68.1	70.8	73.4
105°	352.7	356.3	323.9	259.2	194.5	129.8	65.1	67.7	70.3	72.9	75.5
107.5°	423.7	426.7	386.8	306.9	227.0	147.1	67.2	69.8	72.4	75.0	77.6
110°	492.5	495.0	460.7	392.2	323.7	255.2	186.7	163.0	139.3	115.6	91.9

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	558.0	560.1	558.1	554.1	550.0	546.0	542.0	439.8	337.6	235.4	133.2
115°	629.6	631.6	634.6	640.5	646.4	652.3	658.2	548.4	438.7	328.9	219.2
117.5°	695.3	697.7	699.7	703.8	707.8	711.9	715.9	682.0	648.1	614.2	580.3
120°	761.0	762.8	764.9	769.2	773.5	777.7	782.0	784.8	787.7	790.5	793.4
122.5°	821.7	823.6	826.0	830.7	835.4	840.2	844.9	846.3	847.8	849.2	850.7
125°	879.7	881.2	883.5	888.0	892.5	897.0	901.5	903.2	904.8	906.5	908.2
127.5°	936.1	937.8	939.6	943.1	946.7	950.2	953.8	956.2	958.5	960.9	963.2
130°	990.3	992.2	993.5	996.1	998.7	1001.3	1003.9	1006.5	1009.1	1011.7	1014.3
132.5°	1040.8	1042.3	1043.6	1046.2	1048.9	1051.5	1054.1	1056.2	1058.4	1060.5	1062.6
135°	1088.4	1090.3	1091.4	1093.5	1095.6	1097.8	1099.9	1102.3	1104.7	1107.0	1109.4
137.5°	1131.6	1133.0	1134.2	1136.6	1138.9	1141.3	1143.7	1146.1	1148.4	1150.8	1153.1
140°	1173.7	1174.6	1175.9	1178.5	1181.1	1183.7	1186.3	1188.4	1190.6	1192.7	1194.8
142.5°	1211.1	1211.9	1213.4	1216.5	1219.6	1222.7	1225.8	1227.7	1229.6	1231.5	1233.4
145°	1244.1	1244.0	1246.0	1250.0	1254.1	1258.1	1262.1	1263.8	1265.4	1267.1	1268.8
147.5°	1277.4	1277.0	1279.0	1283.1	1287.1	1291.2	1295.2	1296.4	1297.6	1298.7	1299.9
150°	1307.7	1306.9	1308.8	1312.6	1316.4	1320.2	1324.0	1325.4	1326.8	1328.3	1329.7
152.5°	1335.6	1334.6	1336.4	1339.9	1343.5	1347.0	1350.6	1352.0	1353.4	1354.9	1356.3
155°	1362.4	1361.3	1362.7	1365.6	1368.4	1371.3	1374.1	1375.5	1376.9	1378.4	1379.8
157.5°	1385.7	1384.8	1385.9	1388.0	1390.1	1392.3	1394.4	1396.0	1397.7	1399.3	1401.0
160°	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5	1413.9	1415.3	1416.8	1418.2
162.5°	1423.9	1423.2	1423.8	1425.0	1426.1	1427.3	1428.5	1430.2	1431.8	1433.5	1435.2
165°	1438.8	1438.1	1438.5	1439.2	1439.9	1440.6	1441.3	1443.0	1444.6	1446.3	1448.0
167.5°	1450.6	1449.9	1450.3	1451.0	1451.7	1452.4	1453.1	1454.7	1456.4	1458.0	1459.7
170°	1460.2	1459.5	1459.7	1460.2	1460.7	1461.1	1461.6	1463.3	1464.9	1466.6	1468.3
172.5°	1466.6	1465.9	1466.1	1466.6	1467.1	1467.5	1468.0	1469.7	1471.3	1473.0	1474.7
175°	1470.9	1470.1	1470.3	1470.8	1471.3	1471.8	1472.3	1473.9	1475.6	1477.2	1478.9
177.5°	1473.1	1472.3	1472.4	1472.6	1472.9	1473.1	1473.3	1475.0	1476.6	1478.3	1480.0
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1419.2	1417.1	1411.0	1413.0	1409.9	1409.9	1407.9	1407.9	1407.9	1413.0	1409.9
5°	1341.9	1334.7	1327.5	1324.4	1321.3	1318.2	1318.2	1317.2	1326.5	1324.4	1332.6
7.5°	1246.1	1244.0	1229.6	1229.6	1224.4	1222.4	1227.5	1228.5	1229.6	1231.6	1236.8
10°	1160.5	1155.4	1134.8	1136.8	1133.7	1129.6	1132.7	1130.6	1137.8	1139.9	1137.8
12.5°	1059.5	1050.2	1027.6	1016.2	1003.9	994.6	1005.9	997.7	1026.5	1034.8	1057.5
15°	925.5	908.0	892.5	892.5	881.2	873.0	878.1	887.4	893.6	902.9	907.0
17.5°	835.9	828.6	816.3	809.1	806.0	802.9	802.9	807.0	820.4	819.4	827.6
20°	759.6	755.5	749.3	740.0	736.9	734.9	734.9	734.9	744.1	752.4	757.5
22.5°	707.0	703.9	699.8	687.4	681.3	679.2	684.4	687.4	694.7	700.8	706.0
25°	654.5	647.3	640.0	635.9	632.8	632.8	634.9	635.9	639.0	642.1	648.3
27.5°	611.2	606.0	595.7	584.4	584.4	581.3	583.4	585.4	592.6	602.9	608.1
30°	562.7	561.7	557.6	553.5	549.3	547.3	551.4	554.5	555.5	560.7	560.7
32.5°	527.7	520.5	513.3	509.1	507.1	506.1	507.1	511.2	511.2	517.4	524.6
35°	492.7	488.5	481.3	474.1	472.0	466.9	471.0	475.1	482.3	485.4	488.5
37.5°	454.5	449.4	446.3	444.2	440.1	441.1	438.0	444.2	450.4	449.4	451.4
40°	425.7	416.4	407.1	406.1	405.0	404.0	404.0	405.0	409.2	413.3	419.5
42.5°	388.6	385.5	377.2	369.0	366.9	364.9	362.8	366.9	375.2	382.4	385.5
45°	350.4	346.3	344.2	338.1	333.9	332.9	330.8	336.0	343.2	346.3	348.4
47.5°	315.4	314.3	308.2	309.2	306.1	307.1	306.1	309.2	309.2	312.3	314.3
50°	291.7	288.6	285.5	283.4	280.3	280.3	279.3	280.3	284.5	288.6	287.6
52.5°	268.0	262.8	261.8	260.8	258.7	260.8	257.7	258.7	262.8	264.9	263.8
55°	240.1	239.1	237.1	235.0	234.0	232.9	232.9	232.9	237.1	240.1	241.2
57.5°	218.5	213.3	209.2	209.2	205.1	204.1	206.1	207.2	210.3	212.3	214.4
60°	188.6	186.5	180.4	177.3	171.1	170.1	170.1	174.2	179.3	186.5	188.6
62.5°	156.7	153.6	152.5	152.5	152.5	152.5	152.5	152.5	152.5	153.6	153.6
65°	139.1	140.2	139.1	138.1	139.1	139.1	138.1	138.1	138.1	139.1	140.2
67.5°	124.7	123.7	124.7	123.7	122.6	122.6	121.6	122.6	123.7	124.7	124.7
70°	108.2	108.2	107.2	108.2	107.2	106.2	105.1	105.1	107.2	108.2	108.2
72.5°	92.8	92.8	91.7	91.7	89.7	89.7	90.7	89.7	89.7	92.8	92.8
75°	77.3	76.3	75.2	75.2	74.2	74.2	74.2	73.2	75.2	75.2	76.3
77.5°	60.8	60.8	60.8	59.8	59.8	58.7	58.7	59.8	59.8	59.8	60.8
80°	46.4	46.4	46.4	45.3	44.3	44.3	44.3	44.3	44.3	45.3	44.3
82.5°	32.0	32.0	32.0	32.0	32.0	30.9	30.9	30.9	32.0	32.0	30.9
85°	19.6	18.6	19.6	19.6	18.6	19.6	18.6	18.6	17.5	17.5	18.6
87.5°	8.2	7.2	6.2	6.2	7.2	6.2	6.2	6.2	7.2	6.2	6.2
90°	26.7	26.9	27.4	27.9	28.3	28.8	28.3	27.9	27.4	26.9	26.7
92.5°	27.7	27.8	28.1	28.3	28.6	28.8	28.6	28.3	28.1	27.8	27.7
95°	46.9	46.8	46.6	46.3	46.1	45.9	46.1	46.3	46.6	46.8	46.9
97.5°	57.6	57.7	58.0	58.2	58.5	58.7	58.5	58.2	58.0	57.7	57.6
100°	69.3	69.5	70.0	70.5	71.0	71.5	71.0	70.5	70.0	69.5	69.3
102.5°	74.7	75.1	75.8	76.5	77.2	77.9	77.2	76.5	75.8	75.1	74.7
105°	76.8	77.3	78.2	79.2	80.1	81.1	80.1	79.2	78.2	77.3	76.8
107.5°	78.9	79.4	80.3	81.3	82.2	83.2	82.2	81.3	80.3	79.4	78.9
110°	80.0	80.5	81.4	82.4	83.3	84.3	83.3	82.4	81.4	80.5	80.0

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	82.1	82.5	83.2	83.9	84.6	85.3	84.6	83.9	83.2	82.5	82.1
115°	164.3	155.8	138.7	121.6	104.6	87.5	104.6	121.6	138.7	155.8	164.3
117.5°	563.3	532.2	470.1	408.0	345.9	283.8	345.9	408.0	470.1	532.2	563.3
120°	794.8	778.8	746.8	714.8	682.8	650.8	682.8	714.8	746.8	778.8	794.8
122.5°	851.4	851.5	851.7	852.0	852.2	852.4	852.2	852.0	851.7	851.5	851.4
125°	909.0	909.4	910.1	910.8	911.5	912.2	911.5	910.8	910.1	909.4	909.0
127.5°	964.4	964.5	964.8	965.0	965.3	965.5	965.3	965.0	964.8	964.5	964.4
130°	1015.6	1015.5	1015.3	1015.0	1014.8	1014.6	1014.8	1015.0	1015.3	1015.5	1015.6
132.5°	1063.7	1063.6	1063.3	1063.1	1062.8	1062.6	1062.8	1063.1	1063.3	1063.6	1063.7
135°	1110.6	1110.4	1109.9	1109.4	1109.0	1108.5	1109.0	1109.4	1109.9	1110.4	1110.6
137.5°	1154.3	1153.9	1153.2	1152.5	1151.8	1151.1	1151.8	1152.5	1153.2	1153.9	1154.3
140°	1195.9	1195.3	1194.1	1193.0	1191.8	1190.6	1191.8	1193.0	1194.1	1195.3	1195.9
142.5°	1234.4	1233.8	1232.6	1231.4	1230.2	1229.0	1230.2	1231.4	1232.6	1233.8	1234.4
145°	1269.6	1269.0	1267.8	1266.6	1265.4	1264.2	1265.4	1266.6	1267.8	1269.0	1269.6
147.5°	1300.5	1300.0	1299.1	1298.1	1297.2	1296.2	1297.2	1298.1	1299.1	1300.0	1300.5
150°	1330.4	1329.8	1328.6	1327.4	1326.2	1325.0	1326.2	1327.4	1328.6	1329.8	1330.4
152.5°	1357.0	1356.2	1354.5	1352.9	1351.2	1349.6	1351.2	1352.9	1354.5	1356.2	1357.0
155°	1380.5	1379.6	1377.7	1375.8	1373.9	1372.0	1373.9	1375.8	1377.7	1379.6	1380.5
157.5°	1401.8	1400.9	1399.0	1397.1	1395.2	1393.3	1395.2	1397.1	1399.0	1400.9	1401.8
160°	1418.9	1418.1	1416.4	1414.7	1413.1	1411.4	1413.1	1414.7	1416.4	1418.1	1418.9
162.5°	1436.0	1434.9	1432.8	1430.7	1428.5	1426.4	1428.5	1430.7	1432.8	1434.9	1436.0
165°	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1443.0	1444.6	1446.3	1448.0	1448.8
167.5°	1460.5	1459.4	1457.3	1455.2	1453.0	1450.9	1453.0	1455.2	1457.3	1459.4	1460.5
170°	1469.1	1468.0	1465.9	1463.8	1461.6	1459.5	1461.6	1463.8	1465.9	1468.0	1469.1
172.5°	1475.5	1474.4	1472.3	1470.2	1468.0	1465.9	1468.0	1470.2	1472.3	1474.4	1475.5
175°	1479.7	1478.5	1476.2	1473.8	1471.5	1469.1	1471.5	1473.8	1476.2	1478.5	1479.7
177.5°	1480.8	1479.7	1477.6	1475.5	1473.3	1471.2	1473.3	1475.5	1477.6	1479.7	1480.8
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1413.0	1418.2	1416.1	1404.8	1416.1	1419.2	1425.4	1431.6	1435.7	1441.9	1447.0
5°	1324.4	1334.7	1340.9	1334.7	1355.3	1358.4	1372.8	1381.1	1393.4	1403.8	1412.0
7.5°	1240.9	1249.2	1261.5	1263.6	1275.9	1290.4	1311.0	1331.6	1351.2	1361.5	1370.8
10°	1151.2	1165.7	1184.2	1180.1	1198.7	1221.3	1243.0	1275.9	1292.4	1311.0	1327.5
12.5°	1061.6	1070.8	1095.6	1103.8	1130.6	1148.1	1178.0	1198.7	1239.9	1261.5	1275.9
15°	904.9	943.0	974.0	1011.1	1046.1	1079.1	1105.9	1143.0	1179.1	1195.6	1219.3
17.5°	833.8	851.3	869.9	888.4	933.8	992.5	1039.9	1080.1	1111.0	1132.7	1160.5
20°	759.6	777.1	797.7	815.2	843.1	885.3	944.1	1013.1	1050.2	1072.9	1099.7
22.5°	707.0	723.5	736.9	752.4	774.0	804.9	849.3	934.8	984.3	1012.1	1035.8
25°	650.3	671.0	685.4	696.7	714.2	748.3	784.3	832.8	921.4	943.0	976.0
27.5°	611.2	617.4	633.9	651.4	668.9	687.4	724.5	765.8	825.6	873.0	913.2
30°	564.8	580.3	595.7	602.9	618.4	645.2	667.9	712.2	758.6	795.7	844.1
32.5°	529.8	539.0	549.3	566.9	581.3	599.8	622.5	659.6	698.8	722.5	759.6
35°	490.6	496.8	518.4	525.6	540.1	558.6	581.3	610.1	652.4	671.0	697.8
37.5°	453.5	467.9	474.1	490.6	504.0	522.5	539.0	572.0	599.8	621.5	646.2
40°	424.6	430.8	442.2	456.6	467.9	482.3	503.0	526.7	556.6	574.1	595.7
42.5°	389.6	394.7	409.2	417.4	436.0	449.4	461.7	490.6	517.4	530.8	552.4
45°	351.5	363.8	373.1	389.6	399.9	416.4	431.8	452.5	477.2	492.7	505.0
47.5°	318.5	330.8	340.1	355.6	372.1	379.3	395.8	417.4	440.1	452.5	470.0
50°	291.7	295.8	313.3	320.5	338.1	352.5	363.8	382.4	407.1	414.3	428.8
52.5°	265.9	269.0	280.3	289.6	305.1	317.4	331.9	349.4	370.0	381.3	392.7
55°	243.2	245.3	250.4	260.8	271.1	286.5	299.9	316.4	333.9	346.3	356.6
57.5°	217.5	221.6	225.7	231.9	242.2	256.6	271.1	286.5	301.0	309.2	322.6
60°	187.6	193.8	201.0	208.2	215.4	225.7	242.2	256.6	270.0	277.2	287.6
62.5°	155.6	168.0	174.2	182.4	188.6	197.9	210.3	226.7	236.0	245.3	253.5
65°	140.2	141.2	142.2	150.5	161.8	171.1	182.4	194.8	209.2	215.4	221.6
67.5°	124.7	125.7	127.8	128.8	133.0	143.3	155.6	169.0	180.4	184.5	190.7
70°	109.2	109.2	113.4	114.4	115.4	116.5	126.8	140.2	150.5	155.6	162.8
72.5°	92.8	93.8	95.9	96.9	98.9	101.0	104.1	111.3	123.7	128.8	137.1
75°	76.3	77.3	78.3	79.4	82.5	83.5	86.6	90.7	95.9	102.0	107.2
77.5°	60.8	60.8	61.8	63.9	66.0	67.0	70.1	72.1	74.2	77.3	81.4
80°	45.3	46.4	46.4	48.4	48.4	49.5	50.5	53.6	55.7	57.7	59.8
82.5°	30.9	33.0	33.0	33.0	34.0	35.0	36.1	36.1	38.1	39.2	42.3
85°	18.6	19.6	19.6	19.6	18.6	20.6	20.6	21.6	21.6	21.6	22.7
87.5°	7.2	6.2	7.2	7.2	7.2	8.2	7.2	7.2	8.2	9.3	9.3
90°	26.1	24.9	23.7	22.5	21.3	19.4	17.5	15.6	13.7	12.8	11.5
92.5°	27.5	27.0	26.5	26.1	25.6	24.9	24.2	23.5	22.8	22.4	22.9
95°	46.3	45.1	44.0	42.8	41.6	39.9	38.3	36.6	34.9	34.1	38.0
97.5°	57.2	56.5	55.8	55.1	54.4	50.6	46.8	43.0	39.2	37.3	47.0
100°	68.4	66.5	64.6	62.7	60.8	56.8	52.8	48.7	44.7	42.7	58.9
102.5°	73.4	70.8	68.1	65.5	62.9	106.1	149.2	192.4	235.5	257.1	257.3
105°	75.5	72.9	70.3	67.7	65.1	129.8	194.5	259.2	323.9	356.3	352.7
107.5°	77.6	75.0	72.4	69.8	67.2	147.1	227.0	306.9	386.8	426.7	423.7
110°	91.9	115.6	139.3	163.0	186.7	255.2	323.7	392.2	460.7	495.0	492.5

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	133.2	235.4	337.6	439.8	542.0	546.0	550.0	554.1	558.1	560.1	558.0
115°	219.2	328.9	438.7	548.4	658.2	652.3	646.4	640.5	634.6	631.6	629.6
117.5°	580.3	614.2	648.1	682.0	715.9	711.9	707.8	703.8	699.7	697.7	695.3
120°	793.4	790.5	787.7	784.8	782.0	777.7	773.5	769.2	764.9	762.8	761.0
122.5°	850.7	849.2	847.8	846.3	844.9	840.2	835.4	830.7	826.0	823.6	821.7
125°	908.2	906.5	904.8	903.2	901.5	897.0	892.5	888.0	883.5	881.2	879.7
127.5°	963.2	960.9	958.5	956.2	953.8	950.2	946.7	943.1	939.6	937.8	936.1
130°	1014.3	1011.7	1009.1	1006.5	1003.9	1001.3	998.7	996.1	993.5	992.2	990.3
132.5°	1062.6	1060.5	1058.4	1056.2	1054.1	1051.5	1048.9	1046.2	1043.6	1042.3	1040.8
135°	1109.4	1107.0	1104.7	1102.3	1099.9	1097.8	1095.6	1093.5	1091.4	1090.3	1088.4
137.5°	1153.1	1150.8	1148.4	1146.1	1143.7	1141.3	1138.9	1136.6	1134.2	1133.0	1131.6
140°	1194.8	1192.7	1190.6	1188.4	1186.3	1183.7	1181.1	1178.5	1175.9	1174.6	1173.7
142.5°	1233.4	1231.5	1229.6	1227.7	1225.8	1222.7	1219.6	1216.5	1213.4	1211.9	1211.1
145°	1268.8	1267.1	1265.4	1263.8	1262.1	1258.1	1254.1	1250.0	1246.0	1244.0	1244.1
147.5°	1299.9	1298.7	1297.6	1296.4	1295.2	1291.2	1287.1	1283.1	1279.0	1277.0	1277.4
150°	1329.7	1328.3	1326.8	1325.4	1324.0	1320.2	1316.4	1312.6	1308.8	1306.9	1307.7
152.5°	1356.3	1354.9	1353.4	1352.0	1350.6	1347.0	1343.5	1339.9	1336.4	1334.6	1335.6
155°	1379.8	1378.4	1376.9	1375.5	1374.1	1371.3	1368.4	1365.6	1362.7	1361.3	1362.4
157.5°	1401.0	1399.3	1397.7	1396.0	1394.4	1392.3	1390.1	1388.0	1385.9	1384.8	1385.7
160°	1418.2	1416.8	1415.3	1413.9	1412.5	1411.1	1409.7	1408.2	1406.8	1406.1	1406.8
162.5°	1435.2	1433.5	1431.8	1430.2	1428.5	1427.3	1426.1	1425.0	1423.8	1423.2	1423.9
165°	1448.0	1446.3	1444.6	1443.0	1441.3	1440.6	1439.9	1439.2	1438.5	1438.1	1438.8
167.5°	1459.7	1458.0	1456.4	1454.7	1453.1	1452.4	1451.7	1451.0	1450.3	1449.9	1450.6
170°	1468.3	1466.6	1464.9	1463.3	1461.6	1461.1	1460.7	1460.2	1459.7	1459.5	1460.2
172.5°	1474.7	1473.0	1471.3	1469.7	1468.0	1467.5	1467.1	1466.6	1466.1	1465.9	1466.6
175°	1478.9	1477.2	1475.6	1473.9	1472.3	1471.8	1471.3	1470.8	1470.3	1470.1	1470.9
177.5°	1480.0	1478.3	1476.6	1475.0	1473.3	1473.1	1472.9	1472.6	1472.4	1472.3	1473.1
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1483.1	1483.1	1483.1	1483.1
2.5°	1456.3	1453.2	1471.8	1492.4
5°	1426.4	1431.6	1455.3	1484.1
7.5°	1395.5	1406.8	1434.7	1472.8
10°	1352.2	1372.8	1415.1	1454.3
12.5°	1310.0	1337.8	1378.0	1424.4
15°	1262.6	1293.5	1342.9	1398.6
17.5°	1210.0	1245.0	1302.7	1363.6
20°	1154.3	1200.7	1261.5	1327.5
22.5°	1092.5	1148.1	1211.0	1284.2
25°	1032.7	1093.5	1156.4	1240.9
27.5°	974.0	1033.7	1103.8	1189.4
30°	915.2	969.8	1045.1	1136.8
32.5°	852.4	909.0	988.4	1082.2
35°	794.6	851.3	925.5	1018.3
37.5°	732.8	793.6	864.7	960.6
40°	660.6	731.8	800.8	892.5
42.5°	600.9	676.1	743.1	829.7
45°	553.5	624.6	680.2	764.7
47.5°	509.1	566.9	623.5	701.9
50°	466.9	511.2	570.0	640.0
52.5°	423.6	461.7	512.2	578.2
55°	384.4	420.5	465.9	516.4
57.5°	348.4	374.1	419.5	464.8
60°	308.2	335.0	370.0	408.1
62.5°	274.2	294.8	327.7	359.7
65°	238.1	257.7	282.4	312.3
67.5°	205.1	222.6	242.2	265.9
70°	175.2	188.6	203.0	223.7
72.5°	143.3	157.7	171.1	187.6
75°	117.5	123.7	135.0	146.4
77.5°	90.7	98.9	105.1	114.4
80°	64.9	72.1	74.2	81.4
82.5°	43.3	47.4	51.5	53.6
85°	24.7	26.8	30.9	32.0
87.5°	9.3	10.3	12.4	14.4
90°	8.9	6.3	3.7	1.1
92.5°	23.8	24.8	25.7	26.7
95°	45.8	53.7	61.5	69.3
97.5°	66.5	85.9	105.4	124.8
100°	91.4	123.9	156.3	188.8
102.5°	257.8	258.3	258.7	259.2
105°	345.6	338.5	331.4	324.3
107.5°	417.8	411.9	406.0	400.1
110°	487.5	482.6	477.6	472.6

TEST NUMBER: P999871

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	553.7	549.4	545.2	540.9
115°	625.5	621.5	617.4	613.4
117.5°	690.6	685.9	681.1	676.4
120°	757.5	753.9	750.4	746.8
122.5°	817.9	814.1	810.3	806.5
125°	876.6	873.5	870.5	867.4
127.5°	932.8	929.5	926.1	922.8
130°	986.5	982.7	978.9	975.1
132.5°	1037.7	1034.6	1031.5	1028.4
135°	1084.6	1080.9	1077.1	1073.3
137.5°	1128.7	1125.9	1123.0	1120.2
140°	1171.8	1169.9	1168.0	1166.1
142.5°	1209.4	1207.8	1206.1	1204.5
145°	1244.3	1244.6	1244.8	1245.0
147.5°	1278.1	1278.8	1279.5	1280.2
150°	1309.4	1311.1	1312.7	1314.4
152.5°	1337.5	1339.4	1341.3	1343.2
155°	1364.5	1366.6	1368.8	1370.9
157.5°	1387.6	1389.5	1391.4	1393.3
160°	1408.2	1409.7	1411.1	1412.5
162.5°	1425.3	1426.8	1428.2	1429.6
165°	1440.2	1441.7	1443.1	1444.5
167.5°	1452.0	1453.5	1454.9	1456.3
170°	1461.6	1463.1	1464.5	1465.9
172.5°	1468.0	1469.5	1470.9	1472.3
175°	1472.6	1474.3	1475.9	1477.6
177.5°	1474.8	1476.4	1478.1	1479.7
180°	1474.4	1474.4	1474.4	1474.4

(END OF REPORT)