

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998659

Luminaire Tested: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998659
REPORT IS A COMBINATION OF REPORTS P984402 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5684.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	31	29	26	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15231	15231	15231	15231
5°	15268	16241	15327	12921
10°	15091	17729	15185	10653
15°	14726	18701	14929	8974
20°	14495	17558	14495	7799
25°	14033	15085	14096	6975
30°	13274	11858	13526	6317
35°	12599	8200	12810	5780
40°	11826	6191	11961	5351
45°	10872	5087	11049	4890
50°	10046	4465	10063	4476
55°	9105	3805	9164	4027
60°	8102	3179	8214	3514
65°	7206	2585	7337	3001
70°	6310	2027	6470	2420
75°	5298	1472	5505	1755
80°	4136	933	4431	1043
85°	2712	470	2924	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15745 cd/sqm

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.7	1.6
10°-20°	266.8	4.7
20°-30°	387.2	6.8
30°-40°	408.1	7.2
40°-50°	361.2	6.4
50°-60°	288.4	5.1
60°-70°	195.9	3.4
70°-80°	100.2	1.8
80°-90°	27.0	0.5
90°-100°	199.1	3.5
100°-110°	701.3	12.3
110°-120°	736.6	13.0
120°-130°	606.0	10.7
130°-140°	486.8	8.6
140°-150°	367.7	6.5
150°-160°	258.5	4.5
160°-170°	152.2	2.7
170°-180°	49.5	0.9
0°-30°	745.6	13.1
0°-40°	1153.7	20.3
0°-60°	1803.2	31.7
0°-90°	2126.3	37.4
90°-120°	1637.0	28.8
90°-150°	3097.5	54.5
90°-180°	3558.0	62.6
0°-180°	5684.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	962	962	962	962	962	
5°	963	1075	967	855	963	91
15°	905	1321	917	634	905	255
25°	813	1101	816	509	813	372
35°	663	599	674	422	663	415
45°	498	361	506	347	498	386
55°	342	254	344	268	342	305
65°	203	156	206	181	203	201
75°	95	77	98	92	95	102
85°	19	20	21	15	19	22
90°	1	32	1	32	1	3
95°	34	112	34	112	34	36
105°	120	1107	120	1107	120	127
115°	211	1457	211	1457	211	209
125°	295	1182	295	1182	295	262
135°	346	980	346	980	346	267
145°	395	782	395	782	395	248
155°	449	657	449	657	449	207
165°	489	577	489	577	489	138
175°	510	520	510	520	510	48
180°	511	511	511	511	511	

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	967.4	969.6	973.3	974.1	981.5	987.4	994.0	994.0	996.3	995.5	989.6
5°	963.0	969.6	979.3	987.4	1000.7	1006.6	1015.5	1022.2	1028.1	1032.5	1031.8
7.5°	955.6	967.4	981.5	997.0	1014.8	1025.1	1037.7	1049.5	1057.7	1065.0	1070.2
10°	943.0	963.0	982.2	1002.9	1025.8	1039.9	1054.7	1070.2	1082.8	1096.9	1110.2
12.5°	926.0	954.8	978.5	1005.9	1034.0	1049.5	1073.2	1085.0	1109.4	1144.9	1154.5
15°	904.6	943.8	965.9	1000.7	1037.7	1050.3	1082.8	1102.0	1152.3	1174.5	1201.1
17.5°	884.6	928.2	957.8	997.7	1034.0	1058.4	1090.2	1129.4	1171.6	1203.4	1232.9
20°	868.3	910.5	946.0	990.3	1036.2	1067.3	1100.6	1147.9	1193.7	1226.3	1249.2
22.5°	831.3	885.3	926.7	976.3	1031.8	1074.7	1106.5	1158.2	1207.8	1227.8	1247.7
25°	812.8	859.4	907.5	963.7	1028.8	1079.8	1107.2	1164.9	1208.5	1215.9	1220.4
27.5°	778.8	831.3	887.5	951.9	1028.1	1071.0	1105.7	1158.2	1193.0	1187.8	1174.5
30°	736.7	801.0	863.1	932.7	1017.7	1064.3	1096.9	1144.9	1162.7	1136.1	1112.4
32.5°	705.6	766.2	835.0	915.6	1005.9	1050.3	1082.1	1119.8	1123.5	1075.4	1035.5
35°	663.4	730.7	808.4	893.5	985.9	1025.8	1055.4	1078.4	1060.6	993.3	946.0
37.5°	625.7	692.3	775.1	861.7	958.5	997.7	1021.4	1025.1	981.5	922.3	852.8
40°	584.3	653.1	739.6	830.6	928.2	962.2	977.0	965.9	903.1	834.3	753.7
42.5°	542.9	610.9	704.1	797.3	889.8	918.6	924.5	894.2	817.3	736.7	643.5
45°	497.8	568.8	662.0	755.9	845.4	861.7	862.4	818.8	727.8	643.5	556.9
47.5°	460.8	526.6	619.1	713.0	788.4	799.5	795.1	744.8	645.7	551.0	475.6
50°	420.1	483.0	574.7	667.1	731.5	734.4	723.3	651.6	554.7	468.2	408.3
52.5°	376.5	440.1	524.4	613.1	670.8	666.4	644.9	568.0	477.1	405.3	359.5
55°	341.7	397.9	477.1	563.6	604.3	591.7	568.0	489.6	417.9	357.2	317.3
57.5°	303.2	352.8	430.5	505.9	529.6	517.7	494.1	420.8	354.3	308.4	281.8
60°	267.0	312.1	380.2	443.0	461.5	448.9	421.6	355.8	307.7	269.2	249.3
62.5°	233.7	272.9	329.9	387.6	395.0	382.4	358.7	305.5	264.0	233.7	218.9
65°	202.7	239.6	285.5	329.1	335.8	322.5	298.1	259.6	224.8	205.6	191.6
67.5°	172.3	201.9	242.6	274.4	278.1	265.5	245.6	214.5	193.0	172.3	162.0
70°	145.7	167.9	199.7	225.6	227.1	215.2	204.9	176.8	160.5	145.7	137.6
72.5°	119.8	135.4	159.8	179.0	179.7	172.3	162.7	145.0	130.9	120.6	112.4
75°	94.7	108.0	122.8	139.8	139.0	133.1	125.7	114.6	102.8	96.2	92.5
77.5°	72.5	80.6	92.5	103.5	103.5	100.6	96.2	88.0	80.6	74.0	70.3
80°	51.8	57.0	66.6	70.3	71.7	71.0	67.3	61.4	58.4	53.3	51.8
82.5°	33.3	37.0	41.4	45.1	47.3	45.9	45.1	42.2	37.7	36.2	34.8
85°	19.2	20.7	22.9	25.1	25.9	25.1	26.6	24.4	22.2	22.2	21.4
87.5°	8.1	8.9	10.4	10.4	11.1	11.1	10.4	11.1	11.1	10.4	9.6
90°	1.0	3.9	7.9	9.8	11.8	13.2	14.7	19.6	26.5	32.4	33.4
92.5°	14.7	20.6	28.5	33.4	41.3	46.7	52.1	78.6	115.9	149.3	151.3
95°	34.4	38.3	48.1	57.0	72.7	84.5	96.3	141.5	226.9	340.9	385.1
97.5°	51.1	57.0	67.8	80.6	98.2	111.5	124.8	182.7	301.6	485.3	627.8
100°	75.6	78.6	87.4	103.2	122.8	136.6	150.3	202.4	322.2	534.4	776.1
102.5°	98.2	100.2	109.1	124.8	145.4	159.2	172.9	220.1	323.2	515.8	781.0
105°	119.9	123.8	130.7	145.4	167.0	180.8	194.5	240.7	328.1	490.2	728.0
107.5°	143.4	146.4	153.3	167.0	188.6	202.4	216.1	261.3	338.9	476.5	678.9
110°	167.0	170.9	176.8	189.6	210.2	224.4	238.7	282.0	352.7	472.6	645.5

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	188.6	192.6	199.4	211.2	230.9	245.6	260.3	301.6	367.4	473.5	623.9
115°	211.2	216.1	222.0	233.8	253.5	266.8	280.0	322.2	382.2	477.5	609.1
117.5°	234.8	238.7	244.6	255.4	274.1	287.8	301.6	340.9	397.9	483.4	601.3
120°	256.4	260.3	266.2	275.1	294.7	308.4	322.2	360.6	413.6	489.3	594.4
122.5°	277.0	280.0	285.9	295.7	315.4	329.6	343.9	379.2	427.4	496.1	590.4
125°	294.7	297.7	303.6	315.4	335.0	348.8	362.5	397.9	442.1	503.0	585.5
127.5°	309.5	313.4	321.3	334.0	352.7	367.0	381.2	415.6	455.9	509.9	582.6
130°	322.2	326.2	336.0	349.7	369.4	383.2	396.9	431.3	468.6	517.7	580.6
132.5°	334.0	338.9	349.7	364.5	385.1	398.8	412.6	445.0	481.4	525.6	579.6
135°	345.8	349.7	361.5	376.3	398.9	412.6	426.4	457.8	492.2	531.5	578.7
137.5°	356.6	361.5	373.3	389.0	411.6	424.4	437.2	468.6	501.0	537.4	578.7
140°	369.4	373.3	385.1	400.8	422.5	435.2	448.0	477.5	507.9	541.3	577.7
142.5°	382.2	385.1	395.9	411.6	432.3	444.1	455.9	484.3	513.8	544.3	577.7
145°	394.9	398.9	408.7	423.4	443.1	453.9	464.7	491.2	518.7	546.2	575.7
147.5°	408.7	411.6	421.5	435.2	451.9	461.8	471.6	497.1	521.7	547.2	572.8
150°	422.5	425.4	433.3	446.0	460.8	469.6	478.5	501.0	523.6	546.2	569.8
152.5°	436.2	437.2	445.0	455.9	469.6	477.4	485.3	505.0	524.6	544.3	564.9
155°	449.0	450.0	455.9	466.7	477.5	484.8	492.2	508.9	525.6	542.3	559.0
157.5°	459.8	460.8	465.7	475.5	484.3	490.7	497.1	511.9	525.6	538.4	553.1
160°	470.6	471.6	475.5	483.4	491.2	496.6	502.0	513.8	525.6	535.4	547.2
162.5°	481.4	480.4	484.3	490.2	497.1	501.0	505.0	514.8	524.6	532.5	542.3
165°	489.3	488.3	490.2	496.1	501.0	504.0	506.9	515.8	522.7	528.6	535.4
167.5°	496.1	495.2	497.1	501.0	505.0	507.0	508.9	515.8	521.7	524.6	529.5
170°	503.0	501.0	502.0	505.0	506.9	508.4	509.9	514.8	519.7	521.7	524.6
172.5°	506.9	506.0	505.0	507.9	508.9	509.9	510.9	513.8	516.8	517.7	518.7
175°	509.9	508.9	507.9	509.9	509.9	510.4	510.9	512.8	514.8	513.8	514.8
177.5°	511.9	509.9	508.9	510.9	510.9	510.9	510.9	511.9	513.8	511.9	510.9
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	1000.0	1000.7	1002.2	1009.6	1013.3	1014.0	1011.1	1017.7	1019.9	1017.7	1016.2
5°	1047.3	1051.7	1060.6	1070.2	1069.5	1070.2	1074.7	1079.1	1080.6	1074.7	1076.9
7.5°	1088.7	1097.6	1107.2	1122.0	1122.0	1129.4	1132.4	1136.1	1144.9	1140.5	1139.0
10°	1136.1	1147.9	1165.6	1189.3	1190.0	1197.4	1204.8	1216.7	1220.4	1217.4	1218.9
12.5°	1195.2	1218.2	1219.6	1245.5	1257.3	1258.8	1270.7	1268.4	1275.8	1275.8	1288.4
15°	1221.1	1256.6	1276.6	1301.7	1309.1	1300.2	1309.9	1320.2	1321.0	1321.0	1320.2
17.5°	1267.7	1281.8	1301.7	1315.0	1318.0	1318.0	1318.7	1323.2	1320.2	1314.3	1318.7
20°	1277.3	1283.2	1290.6	1289.2	1290.6	1283.2	1275.8	1268.4	1269.2	1265.5	1276.6
22.5°	1259.6	1258.1	1241.1	1230.0	1230.0	1215.2	1201.1	1194.5	1187.8	1190.0	1193.7
25°	1215.2	1192.3	1171.6	1155.3	1151.6	1127.9	1108.7	1102.8	1091.7	1100.6	1102.0
27.5°	1144.2	1118.3	1085.0	1071.0	1051.7	1042.1	1028.8	1011.1	988.1	1001.4	999.2
30°	1068.0	1029.5	1002.2	968.2	937.8	935.6	910.5	880.9	869.1	869.1	875.7
32.5°	983.0	931.9	892.0	843.9	814.3	801.7	771.4	741.8	748.5	726.3	734.4
35°	883.8	816.5	766.2	719.6	697.5	682.7	643.5	627.2	609.4	599.1	618.3
37.5°	789.2	711.5	647.2	596.1	588.0	561.4	534.7	524.4	514.0	518.5	517.7
40°	673.8	605.0	547.3	507.4	493.3	480.8	463.0	450.4	443.8	447.5	448.2
42.5°	569.5	511.8	468.9	440.8	429.0	420.1	411.2	400.9	398.7	398.7	401.6
45°	488.9	441.6	412.7	389.8	383.1	376.5	369.8	365.4	363.9	360.9	363.2
47.5°	424.5	386.8	369.1	352.1	344.7	343.2	337.3	335.0	332.1	331.3	332.1
50°	370.5	346.9	330.6	321.0	315.8	313.6	310.6	306.2	304.7	308.4	306.9
52.5°	332.8	310.6	301.8	292.1	289.2	286.2	281.8	282.5	281.8	280.3	280.3
55°	295.1	281.1	272.2	264.8	264.0	261.1	257.4	255.9	255.2	253.7	255.9
57.5°	264.8	253.7	245.6	238.9	235.9	235.9	232.2	229.3	229.3	228.5	229.3
60°	234.5	223.4	218.2	211.5	209.3	208.6	206.4	204.9	202.7	202.7	202.7
62.5°	206.4	197.5	191.6	185.6	186.4	182.7	179.7	178.2	178.2	179.0	179.0
65°	179.7	173.8	166.4	161.2	159.8	159.0	157.5	156.8	154.6	156.1	156.1
67.5°	155.3	147.2	142.7	140.5	138.3	137.6	136.1	134.6	133.9	133.1	134.6
70°	130.9	124.3	120.6	119.1	116.9	116.1	115.4	113.2	113.9	114.6	115.4
72.5°	108.7	102.8	102.1	97.6	97.6	97.6	94.7	96.2	95.4	93.9	95.4
75°	85.8	82.8	81.4	79.1	79.9	79.1	78.4	76.2	76.2	76.9	77.7
77.5°	68.0	65.1	64.3	62.1	60.6	62.1	60.6	59.9	59.9	60.6	60.6
80°	50.3	48.8	46.6	46.6	46.6	45.9	45.9	45.9	45.1	44.4	45.1
82.5°	33.3	33.3	32.5	31.8	32.5	31.1	31.8	31.8	31.8	31.8	31.8
85°	21.4	20.7	20.7	20.0	20.0	20.0	20.7	19.2	19.2	20.0	20.0
87.5°	9.6	9.6	9.6	10.4	9.6	9.6	9.6	10.4	9.6	9.6	9.6
90°	32.4	31.4	29.5	31.4	31.9	32.4	32.4	32.4	32.4	32.4	32.4
92.5°	126.7	99.2	84.5	73.7	69.8	65.8	64.8	60.9	61.9	59.9	61.9
95°	337.0	257.4	197.5	156.2	145.4	134.6	121.8	114.0	111.0	112.0	111.0
97.5°	632.7	526.6	420.5	321.3	291.8	262.3	224.0	204.3	193.5	187.6	193.5
100°	917.6	897.0	775.1	640.6	581.2	521.7	440.1	397.9	369.4	351.7	369.4
102.5°	1023.7	1139.6	1135.7	1046.3	982.4	918.6	828.2	748.6	711.3	685.7	711.3
105°	989.3	1193.7	1304.7	1317.5	1301.2	1285.0	1224.1	1163.2	1121.0	1107.2	1121.0
107.5°	916.6	1135.7	1300.8	1397.0	1416.6	1436.3	1435.4	1426.5	1413.7	1391.1	1413.7
110°	848.8	1056.1	1232.0	1357.7	1398.0	1438.3	1480.5	1499.2	1508.1	1507.1	1508.1

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	801.7	983.4	1150.4	1287.0	1334.6	1382.3	1445.2	1479.6	1498.2	1505.1	1498.2
115°	764.3	926.4	1077.7	1206.4	1257.0	1307.6	1377.4	1422.6	1448.1	1457.0	1448.1
117.5°	738.8	879.3	1014.9	1134.7	1182.8	1231.0	1302.7	1350.9	1377.4	1384.3	1377.4
120°	719.1	845.9	967.7	1071.8	1116.5	1161.2	1230.0	1276.2	1304.7	1314.5	1304.7
122.5°	702.4	819.4	928.4	1025.7	1065.0	1104.3	1164.2	1209.4	1233.9	1241.8	1233.9
125°	686.7	793.8	895.0	981.5	1018.3	1055.1	1112.1	1149.5	1174.0	1181.9	1174.0
127.5°	672.0	768.3	861.6	944.1	978.5	1012.9	1063.0	1098.4	1120.0	1125.9	1120.0
130°	657.3	743.7	828.2	905.8	938.2	970.7	1018.8	1052.2	1071.8	1079.7	1071.8
132.5°	645.5	720.1	796.8	866.5	896.4	926.4	973.6	1007.0	1024.7	1031.6	1024.7
135°	634.7	698.5	763.4	828.2	855.7	883.2	925.5	957.9	975.6	979.5	975.6
137.5°	626.8	680.8	736.8	789.9	814.4	839.0	879.3	907.8	923.5	929.4	923.5
140°	619.9	664.1	711.3	756.5	778.1	799.7	831.1	856.7	871.4	877.3	871.4
142.5°	613.0	650.4	688.7	726.0	743.2	760.4	789.9	812.5	825.3	825.3	825.3
145°	607.2	637.6	670.0	700.5	714.8	729.0	752.6	769.3	779.1	782.0	779.1
147.5°	601.3	627.8	654.3	678.9	689.7	700.5	721.1	734.9	741.7	743.7	741.7
150°	593.4	617.0	638.6	659.2	668.0	676.9	691.6	703.4	709.3	710.3	709.3
152.5°	586.5	606.2	625.8	642.5	649.9	657.3	668.1	677.9	681.8	681.8	681.8
155°	577.7	596.3	612.1	626.8	632.2	637.6	648.4	655.3	659.2	657.3	659.2
157.5°	569.8	584.6	598.3	611.1	615.5	619.9	627.8	633.7	635.6	635.6	635.6
160°	561.0	573.7	584.6	595.4	598.8	602.2	609.1	614.0	615.0	615.0	615.0
162.5°	553.1	562.9	571.8	580.6	583.0	585.5	592.4	595.4	596.3	595.4	596.3
165°	544.3	552.1	559.0	565.9	567.8	569.8	573.7	577.7	577.7	576.7	577.7
167.5°	535.4	541.3	547.2	552.1	554.1	556.1	558.0	560.0	560.0	559.0	560.0
170°	528.6	533.5	536.4	540.3	541.3	542.3	543.3	546.2	545.3	543.3	545.3
172.5°	521.7	524.6	526.6	529.5	530.0	530.5	531.5	532.5	531.5	530.5	531.5
175°	515.8	518.7	519.7	520.7	521.2	521.7	521.7	522.7	521.7	519.7	521.7
177.5°	511.9	513.8	513.8	514.8	514.8	514.8	514.8	514.8	513.8	511.9	513.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	1019.9	1014.8	1010.3	1011.1	1014.8	1011.8	1004.4	994.8	991.1	986.6	991.1
5°	1081.3	1076.9	1068.0	1068.7	1066.5	1063.6	1051.7	1036.9	1036.9	1025.1	1023.6
7.5°	1142.0	1135.3	1129.4	1127.9	1119.8	1113.9	1103.5	1082.8	1074.7	1060.6	1052.5
10°	1210.0	1204.8	1198.2	1190.0	1185.6	1175.3	1158.2	1127.9	1113.1	1093.9	1079.8
12.5°	1278.8	1278.1	1263.3	1247.0	1246.3	1230.0	1218.2	1177.5	1157.5	1131.6	1098.3
15°	1322.4	1318.7	1310.6	1302.5	1304.7	1286.9	1260.3	1212.2	1198.9	1167.9	1132.4
17.5°	1321.7	1321.7	1319.5	1318.0	1315.8	1310.6	1295.8	1264.0	1242.6	1203.4	1170.1
20°	1279.5	1289.2	1291.4	1290.6	1298.0	1301.7	1301.0	1281.0	1264.0	1229.2	1195.2
22.5°	1195.2	1217.4	1227.0	1232.9	1248.5	1256.6	1275.8	1268.4	1264.0	1238.1	1209.3
25°	1116.8	1124.2	1153.1	1154.5	1176.0	1196.0	1215.2	1227.8	1244.0	1234.4	1210.0
27.5°	1015.5	1032.5	1053.2	1068.7	1073.2	1113.9	1145.7	1169.3	1206.3	1209.3	1201.1
30°	900.9	909.0	943.0	963.7	987.4	1017.0	1062.8	1103.5	1136.8	1167.1	1177.5
32.5°	761.1	794.3	814.3	839.5	860.2	912.7	968.9	1021.4	1059.9	1110.9	1133.1
35°	633.1	659.0	693.0	703.4	741.1	785.5	858.7	926.0	984.4	1036.2	1081.3
37.5°	527.3	548.1	584.3	600.6	622.8	679.7	741.1	824.7	894.9	958.5	1014.8
40°	454.9	470.4	497.8	502.9	521.4	573.2	622.8	701.2	794.3	880.1	941.5
42.5°	405.3	412.7	431.2	437.9	449.7	484.4	528.8	602.8	689.3	778.1	864.6
45°	369.8	375.0	386.1	392.0	406.8	422.3	458.6	517.7	585.8	675.3	768.5
47.5°	338.0	344.7	349.1	352.8	360.9	377.9	401.6	445.2	510.3	592.4	682.7
50°	311.4	313.6	321.7	322.5	327.7	338.7	360.9	387.6	439.3	505.9	593.2
52.5°	284.8	287.0	292.1	297.3	299.5	308.4	323.2	345.4	383.9	436.4	514.0
55°	258.1	261.1	266.3	270.0	272.2	279.6	288.5	309.9	340.2	377.2	440.8
57.5°	231.5	238.2	239.6	241.9	245.6	253.7	261.8	274.4	298.1	332.1	378.7
60°	206.4	208.6	213.7	216.0	219.7	224.1	234.5	244.1	261.1	287.7	329.9
62.5°	180.5	185.6	187.9	190.1	193.0	198.2	204.9	215.2	230.0	251.5	284.8
65°	158.3	159.0	163.5	166.4	169.4	173.1	179.7	189.3	198.2	218.2	242.6
67.5°	136.8	138.3	139.8	142.7	146.4	150.1	156.1	161.2	172.3	185.6	204.9
70°	116.1	116.1	119.8	122.0	121.3	125.7	130.2	136.1	144.2	156.8	172.3
72.5°	97.6	96.9	99.8	100.6	102.1	105.0	108.0	113.9	118.3	128.0	139.8
75°	77.7	79.1	80.6	80.6	82.8	85.1	88.0	91.0	96.2	102.1	110.9
77.5°	61.4	61.4	62.9	63.6	65.8	65.1	68.0	71.0	74.7	79.9	86.5
80°	45.1	46.6	46.6	46.6	47.3	48.1	51.0	53.3	55.5	59.2	62.1
82.5°	31.8	31.8	33.3	33.3	33.3	34.8	34.8	35.5	37.0	39.2	41.4
85°	20.0	20.0	20.0	20.7	20.0	20.7	22.2	21.4	22.2	23.7	23.7
87.5°	9.6	9.6	9.6	9.6	9.6	10.4	9.6	10.4	11.1	11.1	11.1
90°	32.4	32.4	32.4	31.9	31.4	29.5	31.4	32.4	33.4	32.4	26.5
92.5°	60.9	64.8	65.8	69.8	73.7	84.5	99.2	126.7	151.3	149.3	115.9
95°	114.0	121.8	134.6	145.4	156.2	197.5	257.4	337.0	385.1	340.9	226.9
97.5°	204.3	224.0	262.3	291.8	321.3	420.5	526.6	632.7	627.8	485.3	301.6
100°	397.9	440.1	521.7	581.2	640.6	775.1	897.0	917.6	776.1	534.4	322.2
102.5°	748.6	828.2	918.6	982.4	1046.3	1135.7	1139.6	1023.7	781.0	515.8	323.2
105°	1163.2	1224.1	1285.0	1301.2	1317.5	1304.7	1193.7	989.3	728.0	490.2	328.1
107.5°	1426.5	1435.4	1436.3	1416.6	1397.0	1300.8	1135.7	916.6	678.9	476.5	338.9
110°	1499.2	1480.5	1438.3	1398.0	1357.7	1232.0	1056.1	848.8	645.5	472.6	352.7

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1479.6	1445.2	1382.3	1334.6	1287.0	1150.4	983.4	801.7	623.9	473.5	367.4
115°	1422.6	1377.4	1307.6	1257.0	1206.4	1077.7	926.4	764.3	609.1	477.5	382.2
117.5°	1350.9	1302.7	1231.0	1182.8	1134.7	1014.9	879.3	738.8	601.3	483.4	397.9
120°	1276.2	1230.0	1161.2	1116.5	1071.8	967.7	845.9	719.1	594.4	489.3	413.6
122.5°	1209.4	1164.2	1104.3	1065.0	1025.7	928.4	819.4	702.4	590.4	496.1	427.4
125°	1149.5	1112.1	1055.1	1018.3	981.5	895.0	793.8	686.7	585.5	503.0	442.1
127.5°	1098.4	1063.0	1012.9	978.5	944.1	861.6	768.3	672.0	582.6	509.9	455.9
130°	1052.2	1018.8	970.7	938.2	905.8	828.2	743.7	657.3	580.6	517.7	468.6
132.5°	1007.0	973.6	926.4	896.4	866.5	796.8	720.1	645.5	579.6	525.6	481.4
135°	957.9	925.5	883.2	855.7	828.2	763.4	698.5	634.7	578.7	531.5	492.2
137.5°	907.8	879.3	839.0	814.4	789.9	736.8	680.8	626.8	578.7	537.4	501.0
140°	856.7	831.1	799.7	778.1	756.5	711.3	664.1	619.9	577.7	541.3	507.9
142.5°	812.5	789.9	760.4	743.2	726.0	688.7	650.4	613.0	577.7	544.3	513.8
145°	769.3	752.6	729.0	714.8	700.5	670.0	637.6	607.2	575.7	546.2	518.7
147.5°	734.9	721.1	700.5	689.7	678.9	654.3	627.8	601.3	572.8	547.2	521.7
150°	703.4	691.6	676.9	668.0	659.2	638.6	617.0	593.4	569.8	546.2	523.6
152.5°	677.9	668.1	657.3	649.9	642.5	625.8	606.2	586.5	564.9	544.3	524.6
155°	655.3	648.4	637.6	632.2	626.8	612.1	596.3	577.7	559.0	542.3	525.6
157.5°	633.7	627.8	619.9	615.5	611.1	598.3	584.6	569.8	553.1	538.4	525.6
160°	614.0	609.1	602.2	598.8	595.4	584.6	573.7	561.0	547.2	535.4	525.6
162.5°	595.4	592.4	585.5	583.0	580.6	571.8	562.9	553.1	542.3	532.5	524.6
165°	577.7	573.7	569.8	567.8	565.9	559.0	552.1	544.3	535.4	528.6	522.7
167.5°	560.0	558.0	556.1	554.1	552.1	547.2	541.3	535.4	529.5	524.6	521.7
170°	546.2	543.3	542.3	541.3	540.3	536.4	533.5	528.6	524.6	521.7	519.7
172.5°	532.5	531.5	530.5	530.0	529.5	526.6	524.6	521.7	518.7	517.7	516.8
175°	522.7	521.7	521.7	521.2	520.7	519.7	518.7	515.8	514.8	513.8	514.8
177.5°	514.8	514.8	514.8	514.8	514.8	513.8	513.8	511.9	510.9	511.9	513.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	987.4	983.7	981.5	983.0	978.5	967.4	967.4	971.1	966.7	962.2	955.6
5°	1014.8	1007.4	1002.9	1002.2	991.8	974.1	970.4	966.7	957.1	946.7	935.6
7.5°	1041.4	1028.1	1020.7	1015.5	1000.7	977.8	968.2	960.0	944.5	929.0	914.9
10°	1063.6	1044.3	1035.5	1027.3	1008.1	979.3	963.7	948.9	929.0	909.0	891.2
12.5°	1081.3	1059.1	1048.0	1036.2	1012.5	974.8	955.6	931.9	911.9	885.3	867.6
15°	1110.9	1065.0	1054.7	1043.6	1019.2	967.4	943.8	917.1	889.8	854.3	835.0
17.5°	1134.6	1073.2	1072.4	1048.8	1017.0	964.5	928.2	893.5	863.9	828.4	798.0
20°	1148.6	1085.8	1073.9	1049.5	1009.6	944.5	906.8	868.3	836.5	793.6	763.3
22.5°	1160.5	1103.5	1072.4	1042.9	994.0	937.8	882.4	846.1	802.5	755.9	727.0
25°	1164.9	1107.2	1074.7	1040.6	983.0	918.6	855.7	816.5	767.7	725.6	686.4
27.5°	1165.6	1106.5	1066.5	1031.0	967.4	893.5	829.1	787.7	733.7	684.9	645.7
30°	1158.2	1098.3	1062.1	1023.6	952.6	870.5	796.6	750.7	693.0	644.2	603.5
32.5°	1136.1	1082.1	1052.5	1010.3	933.4	838.7	765.5	714.5	653.8	605.7	566.5
35°	1099.1	1062.1	1029.5	990.3	908.3	809.1	734.4	674.5	613.1	567.3	530.3
37.5°	1053.2	1033.2	1002.9	964.5	879.4	782.5	699.7	633.1	571.7	527.3	491.1
40°	991.1	996.3	966.7	931.9	845.4	746.3	654.6	591.0	533.3	491.8	456.3
42.5°	923.8	945.2	928.2	894.9	807.7	706.3	621.3	551.0	494.8	451.9	422.3
45°	851.3	888.3	877.9	853.5	768.5	664.2	573.9	505.9	456.3	414.9	389.0
47.5°	772.2	824.7	824.7	806.9	724.8	622.0	533.3	463.7	414.9	385.3	360.2
50°	691.5	750.7	760.3	748.5	676.0	573.9	483.7	420.8	378.7	349.8	331.3
52.5°	607.2	676.0	693.8	687.8	624.2	528.1	443.0	381.6	343.2	318.0	301.8
55°	526.6	606.5	625.7	627.9	568.8	477.8	397.9	343.9	306.9	289.9	275.9
57.5°	450.4	527.3	548.8	552.5	512.6	431.9	355.8	308.4	275.1	261.1	250.0
60°	385.3	449.7	477.8	485.9	451.2	378.7	316.6	270.7	245.6	232.2	221.9
62.5°	332.1	383.9	413.4	415.7	400.1	332.1	275.9	237.4	216.0	204.1	199.0
65°	280.3	326.9	344.7	353.5	341.0	287.7	238.2	206.4	189.3	179.0	173.8
67.5°	238.9	268.5	283.3	295.1	282.5	242.6	202.7	176.8	164.2	153.8	150.9
70°	196.0	220.4	231.5	243.3	232.2	201.9	173.1	149.4	138.3	130.2	126.5
72.5°	156.8	176.0	186.4	193.8	187.1	162.0	138.3	122.0	113.9	108.0	105.8
75°	124.3	137.6	143.5	148.7	145.7	126.5	111.7	98.4	91.0	85.8	84.3
77.5°	94.7	104.3	110.9	112.4	108.7	96.2	83.6	75.4	69.5	66.6	65.1
80°	67.3	73.2	76.9	79.1	75.4	70.3	61.4	55.5	50.3	46.6	45.9
82.5°	45.1	48.1	51.0	50.3	48.8	44.4	39.2	36.2	34.0	31.1	31.1
85°	25.9	26.6	28.1	28.8	28.1	25.1	22.2	20.7	19.2	17.0	17.0
87.5°	11.1	11.8	11.8	12.6	11.1	11.1	9.6	8.1	8.1	7.4	6.7
90°	19.6	14.7	13.2	11.8	9.8	7.9	3.9	1.0	3.9	7.9	9.8
92.5°	78.6	52.1	46.7	41.3	33.4	28.5	20.6	14.7	20.6	28.5	33.4
95°	141.5	96.3	84.5	72.7	57.0	48.1	38.3	34.4	38.3	48.1	57.0
97.5°	182.7	124.8	111.5	98.2	80.6	67.8	57.0	51.1	57.0	67.8	80.6
100°	202.4	150.3	136.6	122.8	103.2	87.4	78.6	75.6	78.6	87.4	103.2
102.5°	220.1	172.9	159.2	145.4	124.8	109.1	100.2	98.2	100.2	109.1	124.8
105°	240.7	194.5	180.8	167.0	145.4	130.7	123.8	119.9	123.8	130.7	145.4
107.5°	261.3	216.1	202.4	188.6	167.0	153.3	146.4	143.4	146.4	153.3	167.0
110°	282.0	238.7	224.4	210.2	189.6	176.8	170.9	167.0	170.9	176.8	189.6

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	301.6	260.3	245.6	230.9	211.2	199.4	192.6	188.6	192.6	199.4	211.2
115°	322.2	280.0	266.8	253.5	233.8	222.0	216.1	211.2	216.1	222.0	233.8
117.5°	340.9	301.6	287.8	274.1	255.4	244.6	238.7	234.8	238.7	244.6	255.4
120°	360.6	322.2	308.4	294.7	275.1	266.2	260.3	256.4	260.3	266.2	275.1
122.5°	379.2	343.9	329.6	315.4	295.7	285.9	280.0	277.0	280.0	285.9	295.7
125°	397.9	362.5	348.8	335.0	315.4	303.6	297.7	294.7	297.7	303.6	315.4
127.5°	415.6	381.2	367.0	352.7	334.0	321.3	313.4	309.5	313.4	321.3	334.0
130°	431.3	396.9	383.2	369.4	349.7	336.0	326.2	322.2	326.2	336.0	349.7
132.5°	445.0	412.6	398.8	385.1	364.5	349.7	338.9	334.0	338.9	349.7	364.5
135°	457.8	426.4	412.6	398.9	376.3	361.5	349.7	345.8	349.7	361.5	376.3
137.5°	468.6	437.2	424.4	411.6	389.0	373.3	361.5	356.6	361.5	373.3	389.0
140°	477.5	448.0	435.2	422.5	400.8	385.1	373.3	369.4	373.3	385.1	400.8
142.5°	484.3	455.9	444.1	432.3	411.6	395.9	385.1	382.2	385.1	395.9	411.6
145°	491.2	464.7	453.9	443.1	423.4	408.7	398.9	394.9	398.9	408.7	423.4
147.5°	497.1	471.6	461.8	451.9	435.2	421.5	411.6	408.7	411.6	421.5	435.2
150°	501.0	478.5	469.6	460.8	446.0	433.3	425.4	422.5	425.4	433.3	446.0
152.5°	505.0	485.3	477.4	469.6	455.9	445.0	437.2	436.2	437.2	445.0	455.9
155°	508.9	492.2	484.8	477.5	466.7	455.9	450.0	449.0	450.0	455.9	466.7
157.5°	511.9	497.1	490.7	484.3	475.5	465.7	460.8	459.8	460.8	465.7	475.5
160°	513.8	502.0	496.6	491.2	483.4	475.5	471.6	470.6	471.6	475.5	483.4
162.5°	514.8	505.0	501.0	497.1	490.2	484.3	480.4	481.4	480.4	484.3	490.2
165°	515.8	506.9	504.0	501.0	496.1	490.2	488.3	489.3	488.3	490.2	496.1
167.5°	515.8	508.9	507.0	505.0	501.0	497.1	495.2	496.1	495.2	497.1	501.0
170°	514.8	509.9	508.4	506.9	505.0	502.0	501.0	503.0	501.0	502.0	505.0
172.5°	513.8	510.9	509.9	508.9	507.9	505.0	506.0	506.9	506.0	505.0	507.9
175°	512.8	510.9	510.4	509.9	509.9	507.9	508.9	509.9	508.9	507.9	509.9
177.5°	511.9	510.9	510.9	510.9	510.9	508.9	509.9	511.9	509.9	508.9	510.9
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	951.9	955.6	954.8	947.5	939.3	932.7	920.1	921.6	917.1	917.9	922.3
5°	928.2	928.2	925.3	914.9	901.6	894.2	880.1	876.4	867.6	866.8	866.1
7.5°	903.1	899.4	895.7	880.9	864.6	852.8	833.5	829.1	820.2	814.3	811.4
10°	873.5	868.3	860.9	843.9	823.9	809.1	789.2	783.3	766.2	758.8	754.4
12.5°	840.9	838.0	826.2	812.1	779.6	763.3	734.4	740.4	723.3	708.6	706.3
15°	808.4	797.3	790.7	767.7	728.5	721.1	698.2	686.4	670.8	659.0	659.0
17.5°	776.6	759.6	744.8	720.4	691.5	670.8	653.8	647.9	628.7	616.8	614.6
20°	734.4	715.2	711.5	676.8	656.8	633.9	617.6	602.8	588.7	583.6	579.9
22.5°	694.5	672.3	666.4	636.8	616.8	593.9	577.6	567.3	556.9	553.2	546.6
25°	651.6	638.3	629.4	597.6	575.4	554.0	542.9	535.5	525.9	525.1	520.7
27.5°	610.2	597.6	588.7	558.4	542.1	522.2	513.3	505.2	500.0	497.8	495.5
30°	574.7	560.6	550.3	528.1	508.1	491.8	484.4	479.3	476.3	472.6	471.9
32.5°	535.5	527.3	513.3	496.3	480.8	465.2	460.8	457.1	452.6	451.2	450.4
35°	502.2	491.1	482.2	463.0	456.3	443.0	437.9	434.9	429.0	427.5	426.0
37.5°	469.7	459.3	449.7	437.9	425.3	417.9	414.9	410.5	407.5	408.3	406.8
40°	437.1	429.0	421.6	409.0	401.6	397.9	392.0	387.6	386.1	386.8	386.1
42.5°	405.3	397.9	393.5	383.9	376.5	372.8	369.1	364.6	366.9	366.9	369.1
45°	376.5	369.8	366.9	359.5	355.0	349.1	345.4	344.7	347.6	346.9	346.9
47.5°	346.9	344.7	341.0	334.3	328.4	324.7	324.0	324.0	326.9	328.4	327.7
50°	324.0	319.5	315.1	309.9	305.5	304.0	301.8	303.2	306.2	306.2	307.7
52.5°	295.1	292.1	290.7	286.2	283.3	283.3	283.3	284.0	286.2	288.5	287.7
55°	270.0	267.7	266.3	264.0	260.3	261.1	260.3	261.8	264.0	266.3	267.7
57.5°	243.3	242.6	241.1	237.4	237.4	236.7	238.9	239.6	243.3	244.8	247.0
60°	219.7	217.4	217.4	214.5	214.5	214.5	216.7	218.9	221.9	222.6	224.1
62.5°	194.5	194.5	193.8	191.6	191.6	193.8	194.5	197.5	199.0	199.0	201.2
65°	170.9	170.1	169.4	170.1	170.9	170.9	173.1	174.5	176.0	176.8	177.5
67.5°	147.2	146.4	147.9	147.2	148.7	151.6	150.9	153.1	155.3	155.3	156.1
70°	125.0	126.5	125.7	127.2	126.5	128.0	130.2	130.9	130.9	131.7	133.9
72.5°	104.3	104.3	104.3	103.5	104.3	105.8	107.2	108.0	109.5	110.2	112.4
75°	84.3	84.3	82.8	84.3	84.3	85.8	87.3	87.3	87.3	88.8	91.0
77.5°	63.6	64.3	63.6	65.1	65.1	65.8	67.3	66.6	68.0	68.8	69.5
80°	46.6	45.9	45.9	45.9	46.6	46.6	48.1	48.8	48.8	51.0	49.6
82.5°	29.6	30.3	29.6	30.3	30.3	31.1	30.3	31.1	31.8	33.3	32.5
85°	17.0	16.3	16.3	17.0	16.3	16.3	17.0	16.3	17.0	16.3	17.0
87.5°	6.7	5.9	5.9	5.9	5.9	5.2	5.2	4.4	4.4	4.4	3.7
90°	11.8	13.2	14.7	19.6	26.5	32.4	33.4	32.4	31.4	29.5	31.4
92.5°	41.3	46.7	52.1	78.6	115.9	149.3	151.3	126.7	99.2	84.5	73.7
95°	72.7	84.5	96.3	141.5	226.9	340.9	385.1	337.0	257.4	197.5	156.2
97.5°	98.2	111.5	124.8	182.7	301.6	485.3	627.8	632.7	526.6	420.5	321.3
100°	122.8	136.6	150.3	202.4	322.2	534.4	776.1	917.6	897.0	775.1	640.6
102.5°	145.4	159.2	172.9	220.1	323.2	515.8	781.0	1023.7	1139.6	1135.7	1046.3
105°	167.0	180.8	194.5	240.7	328.1	490.2	728.0	989.3	1193.7	1304.7	1317.5
107.5°	188.6	202.4	216.1	261.3	338.9	476.5	678.9	916.6	1135.7	1300.8	1397.0
110°	210.2	224.4	238.7	282.0	352.7	472.6	645.5	848.8	1056.1	1232.0	1357.7

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	230.9	245.6	260.3	301.6	367.4	473.5	623.9	801.7	983.4	1150.4	1287.0
115°	253.5	266.8	280.0	322.2	382.2	477.5	609.1	764.3	926.4	1077.7	1206.4
117.5°	274.1	287.8	301.6	340.9	397.9	483.4	601.3	738.8	879.3	1014.9	1134.7
120°	294.7	308.4	322.2	360.6	413.6	489.3	594.4	719.1	845.9	967.7	1071.8
122.5°	315.4	329.6	343.9	379.2	427.4	496.1	590.4	702.4	819.4	928.4	1025.7
125°	335.0	348.8	362.5	397.9	442.1	503.0	585.5	686.7	793.8	895.0	981.5
127.5°	352.7	367.0	381.2	415.6	455.9	509.9	582.6	672.0	768.3	861.6	944.1
130°	369.4	383.2	396.9	431.3	468.6	517.7	580.6	657.3	743.7	828.2	905.8
132.5°	385.1	398.8	412.6	445.0	481.4	525.6	579.6	645.5	720.1	796.8	866.5
135°	398.9	412.6	426.4	457.8	492.2	531.5	578.7	634.7	698.5	763.4	828.2
137.5°	411.6	424.4	437.2	468.6	501.0	537.4	578.7	626.8	680.8	736.8	789.9
140°	422.5	435.2	448.0	477.5	507.9	541.3	577.7	619.9	664.1	711.3	756.5
142.5°	432.3	444.1	455.9	484.3	513.8	544.3	577.7	613.0	650.4	688.7	726.0
145°	443.1	453.9	464.7	491.2	518.7	546.2	575.7	607.2	637.6	670.0	700.5
147.5°	451.9	461.8	471.6	497.1	521.7	547.2	572.8	601.3	627.8	654.3	678.9
150°	460.8	469.6	478.5	501.0	523.6	546.2	569.8	593.4	617.0	638.6	659.2
152.5°	469.6	477.4	485.3	505.0	524.6	544.3	564.9	586.5	606.2	625.8	642.5
155°	477.5	484.8	492.2	508.9	525.6	542.3	559.0	577.7	596.3	612.1	626.8
157.5°	484.3	490.7	497.1	511.9	525.6	538.4	553.1	569.8	584.6	598.3	611.1
160°	491.2	496.6	502.0	513.8	525.6	535.4	547.2	561.0	573.7	584.6	595.4
162.5°	497.1	501.0	505.0	514.8	524.6	532.5	542.3	553.1	562.9	571.8	580.6
165°	501.0	504.0	506.9	515.8	522.7	528.6	535.4	544.3	552.1	559.0	565.9
167.5°	505.0	507.0	508.9	515.8	521.7	524.6	529.5	535.4	541.3	547.2	552.1
170°	506.9	508.4	509.9	514.8	519.7	521.7	524.6	528.6	533.5	536.4	540.3
172.5°	508.9	509.9	510.9	513.8	516.8	517.7	518.7	521.7	524.6	526.6	529.5
175°	509.9	510.4	510.9	512.8	514.8	513.8	514.8	515.8	518.7	519.7	520.7
177.5°	510.9	510.9	510.9	511.9	513.8	511.9	510.9	511.9	513.8	513.8	514.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	917.1	919.3	914.2	912.7	914.2	909.0	910.5	911.9	911.9	914.2	915.6
5°	863.9	860.9	855.7	854.3	852.8	855.0	853.5	855.7	856.5	861.7	862.4
7.5°	811.4	806.9	802.5	798.0	796.6	792.9	796.6	796.6	801.7	800.3	804.0
10°	749.2	748.5	742.6	740.4	737.4	731.5	739.6	737.4	741.1	747.8	749.2
12.5°	703.4	695.2	698.9	688.6	692.3	686.4	687.1	687.1	693.0	693.8	692.3
15°	659.7	653.1	643.5	639.0	636.8	633.9	643.5	644.2	639.8	650.1	646.4
17.5°	615.4	615.4	606.5	604.3	598.4	601.3	599.8	600.6	599.1	606.5	610.2
20°	576.9	573.2	570.2	571.0	563.6	562.1	560.6	562.1	567.3	572.5	573.9
22.5°	545.8	543.6	536.2	537.7	531.8	534.0	532.5	536.2	537.0	537.0	542.1
25°	516.3	513.3	514.0	511.1	508.9	508.9	506.6	508.9	511.8	513.3	514.0
27.5°	494.1	491.8	488.1	485.9	487.4	483.7	486.7	488.9	488.9	487.4	488.9
30°	467.4	468.9	468.9	461.5	464.5	463.0	465.2	466.7	466.7	467.4	466.0
32.5°	449.7	445.2	444.5	443.8	443.8	440.8	440.8	443.0	443.8	444.5	446.7
35°	426.0	426.0	422.3	424.5	421.6	422.3	421.6	422.3	423.8	421.6	423.8
37.5°	404.6	405.3	403.8	405.3	406.1	404.6	403.1	406.1	404.6	404.6	403.1
40°	386.1	385.3	386.1	386.1	386.1	386.8	385.3	385.3	385.3	383.9	382.4
42.5°	370.5	366.1	367.6	368.3	366.1	366.1	366.9	366.1	368.3	363.9	363.9
45°	348.4	346.9	347.6	347.6	349.1	346.9	348.4	349.1	346.9	346.1	344.7
47.5°	328.4	329.9	328.4	329.9	329.9	331.3	328.4	329.1	329.9	326.9	324.7
50°	308.4	308.4	310.6	309.9	310.6	309.2	309.2	308.4	309.2	307.7	305.5
52.5°	289.9	287.7	291.4	290.7	289.9	289.2	288.5	289.2	287.7	286.2	286.2
55°	267.0	267.0	269.2	270.0	270.0	268.5	267.0	267.7	267.0	266.3	265.5
57.5°	248.5	245.6	247.0	247.8	247.8	245.6	247.0	245.6	245.6	246.3	244.1
60°	224.8	224.8	223.4	225.6	225.6	224.1	224.1	224.8	223.4	222.6	221.9
62.5°	199.7	200.4	202.7	203.4	204.1	202.7	201.2	201.9	201.9	199.7	200.4
65°	178.2	179.7	182.7	181.9	180.5	181.2	179.7	180.5	178.2	179.0	176.8
67.5°	157.5	156.8	157.5	157.5	159.0	158.3	156.8	156.8	156.1	158.3	156.1
70°	135.4	135.4	135.4	135.4	136.1	136.8	135.4	133.9	134.6	133.1	132.4
72.5°	112.4	113.2	112.4	113.9	111.7	113.2	113.2	112.4	111.7	111.7	111.7
75°	91.0	92.5	90.2	91.0	90.2	91.7	91.0	91.0	89.5	88.8	89.5
77.5°	69.5	70.3	68.8	69.5	68.8	69.5	69.5	68.8	68.8	68.8	68.8
80°	49.6	50.3	49.6	48.8	48.1	49.6	48.1	48.8	49.6	48.8	50.3
82.5°	31.8	31.8	31.1	31.8	30.3	30.3	31.1	31.1	30.3	31.8	30.3
85°	15.5	15.5	17.0	15.5	14.8	14.8	14.8	15.5	14.8	16.3	15.5
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.4	3.0
90°	31.9	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	31.9
92.5°	69.8	65.8	64.8	60.9	61.9	59.9	61.9	60.9	64.8	65.8	69.8
95°	145.4	134.6	121.8	114.0	111.0	112.0	111.0	114.0	121.8	134.6	145.4
97.5°	291.8	262.3	224.0	204.3	193.5	187.6	193.5	204.3	224.0	262.3	291.8
100°	581.2	521.7	440.1	397.9	369.4	351.7	369.4	397.9	440.1	521.7	581.2
102.5°	982.4	918.6	828.2	748.6	711.3	685.7	711.3	748.6	828.2	918.6	982.4
105°	1301.2	1285.0	1224.1	1163.2	1121.0	1107.2	1121.0	1163.2	1224.1	1285.0	1301.2
107.5°	1416.6	1436.3	1435.4	1426.5	1413.7	1391.1	1413.7	1426.5	1435.4	1436.3	1416.6
110°	1398.0	1438.3	1480.5	1499.2	1508.1	1507.1	1508.1	1499.2	1480.5	1438.3	1398.0

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1334.6	1382.3	1445.2	1479.6	1498.2	1505.1	1498.2	1479.6	1445.2	1382.3	1334.6
115°	1257.0	1307.6	1377.4	1422.6	1448.1	1457.0	1448.1	1422.6	1377.4	1307.6	1257.0
117.5°	1182.8	1231.0	1302.7	1350.9	1377.4	1384.3	1377.4	1350.9	1302.7	1231.0	1182.8
120°	1116.5	1161.2	1230.0	1276.2	1304.7	1314.5	1304.7	1276.2	1230.0	1161.2	1116.5
122.5°	1065.0	1104.3	1164.2	1209.4	1233.9	1241.8	1233.9	1209.4	1164.2	1104.3	1065.0
125°	1018.3	1055.1	1112.1	1149.5	1174.0	1181.9	1174.0	1149.5	1112.1	1055.1	1018.3
127.5°	978.5	1012.9	1063.0	1098.4	1120.0	1125.9	1120.0	1098.4	1063.0	1012.9	978.5
130°	938.2	970.7	1018.8	1052.2	1071.8	1079.7	1071.8	1052.2	1018.8	970.7	938.2
132.5°	896.4	926.4	973.6	1007.0	1024.7	1031.6	1024.7	1007.0	973.6	926.4	896.4
135°	855.7	883.2	925.5	957.9	975.6	979.5	975.6	957.9	925.5	883.2	855.7
137.5°	814.4	839.0	879.3	907.8	923.5	929.4	923.5	907.8	879.3	839.0	814.4
140°	778.1	799.7	831.1	856.7	871.4	877.3	871.4	856.7	831.1	799.7	778.1
142.5°	743.2	760.4	789.9	812.5	825.3	825.3	825.3	812.5	789.9	760.4	743.2
145°	714.8	729.0	752.6	769.3	779.1	782.0	779.1	769.3	752.6	729.0	714.8
147.5°	689.7	700.5	721.1	734.9	741.7	743.7	741.7	734.9	721.1	700.5	689.7
150°	668.0	676.9	691.6	703.4	709.3	710.3	709.3	703.4	691.6	676.9	668.0
152.5°	649.9	657.3	668.1	677.9	681.8	681.8	681.8	677.9	668.1	657.3	649.9
155°	632.2	637.6	648.4	655.3	659.2	657.3	659.2	655.3	648.4	637.6	632.2
157.5°	615.5	619.9	627.8	633.7	635.6	635.6	635.6	633.7	627.8	619.9	615.5
160°	598.8	602.2	609.1	614.0	615.0	615.0	615.0	614.0	609.1	602.2	598.8
162.5°	583.0	585.5	592.4	595.4	596.3	595.4	596.3	595.4	592.4	585.5	583.0
165°	567.8	569.8	573.7	577.7	577.7	576.7	577.7	577.7	573.7	569.8	567.8
167.5°	554.1	556.1	558.0	560.0	560.0	559.0	560.0	560.0	558.0	556.1	554.1
170°	541.3	542.3	543.3	546.2	545.3	543.3	545.3	546.2	543.3	542.3	541.3
172.5°	530.0	530.5	531.5	532.5	531.5	530.5	531.5	532.5	531.5	530.5	530.0
175°	521.2	521.7	521.7	522.7	521.7	519.7	521.7	522.7	521.7	521.7	521.2
177.5°	514.8	514.8	514.8	514.8	513.8	511.9	513.8	514.8	514.8	514.8	514.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	913.4	919.3	917.1	909.0	918.6	918.6	925.3	925.3	933.4	936.4	940.8
5°	861.7	866.1	869.8	866.1	872.7	883.1	889.0	894.2	905.3	909.7	916.4
7.5°	806.2	814.3	818.0	818.0	829.1	840.9	852.8	860.2	875.7	881.6	888.3
10°	752.2	761.8	769.2	768.5	787.0	794.3	809.1	826.2	841.7	850.6	860.2
12.5°	695.2	700.4	710.8	725.6	730.0	743.3	760.3	781.8	809.9	818.0	832.1
15°	647.9	662.0	670.1	676.8	687.1	699.7	718.2	738.9	767.0	784.7	799.5
17.5°	608.0	626.5	631.6	630.2	643.5	662.7	684.1	699.7	724.8	746.3	760.3
20°	575.4	582.8	591.7	595.4	605.7	626.5	647.2	664.9	685.6	702.6	718.9
22.5°	542.9	548.8	556.2	562.8	571.0	582.8	602.8	625.0	644.9	661.2	679.7
25°	516.3	520.0	526.6	531.8	540.7	548.8	562.8	587.3	610.9	620.5	636.8
27.5°	490.4	493.3	497.8	503.7	508.1	516.3	528.8	548.8	573.2	582.8	605.0
30°	467.4	469.7	474.1	477.1	479.3	488.9	498.5	514.0	532.5	545.8	562.1
32.5°	446.0	448.2	452.6	453.4	456.3	461.5	470.4	484.4	500.7	511.8	525.9
35°	422.3	423.8	428.2	429.7	431.9	436.4	443.0	453.4	468.2	476.3	488.9
37.5°	403.8	403.1	406.1	408.3	411.2	413.4	415.7	426.0	437.1	444.5	454.1
40°	383.9	382.4	383.1	386.1	387.6	390.5	390.5	400.9	408.3	414.2	421.6
42.5°	363.9	363.2	361.7	363.2	364.6	365.4	366.1	373.5	380.9	386.1	394.2
45°	343.9	343.2	341.7	342.4	342.4	343.9	346.1	349.1	354.3	358.7	363.2
47.5°	325.4	324.0	321.7	321.0	322.5	322.5	322.5	325.4	330.6	332.1	336.5
50°	306.2	304.0	301.0	299.5	299.5	298.8	300.3	301.0	305.5	306.9	310.6
52.5°	285.5	284.0	281.1	278.1	278.8	277.4	278.1	278.8	280.3	282.5	284.8
55°	264.8	261.8	259.6	258.9	256.6	256.6	254.4	257.4	256.6	257.4	260.3
57.5°	244.8	241.9	238.2	236.7	234.5	233.7	232.2	231.5	232.2	234.5	236.7
60°	221.1	219.7	217.4	215.2	213.7	211.5	210.1	210.1	209.3	209.3	210.1
62.5°	198.2	197.5	194.5	193.8	192.3	190.8	188.6	187.1	187.1	188.6	189.3
65°	176.0	175.3	173.1	172.3	168.6	167.2	166.4	165.7	164.2	164.2	164.2
67.5°	155.3	153.1	153.1	149.4	146.4	145.0	143.5	142.7	142.7	142.7	143.5
70°	132.4	132.4	130.2	128.0	125.0	125.7	123.5	121.3	121.3	119.8	120.6
72.5°	110.2	109.5	107.2	106.5	104.3	102.1	100.6	102.1	99.8	99.1	99.8
75°	88.8	88.0	86.5	85.1	85.8	83.6	81.4	80.6	80.6	79.1	79.1
77.5°	68.0	69.5	66.6	65.8	64.3	62.9	62.1	61.4	61.4	61.4	62.9
80°	47.3	48.1	48.1	46.6	47.3	45.1	45.1	45.1	42.9	43.6	44.4
82.5°	30.3	30.3	29.6	30.3	29.6	29.6	28.8	28.8	28.1	28.1	28.8
85°	17.0	16.3	15.5	17.0	16.3	16.3	15.5	15.5	15.5	15.5	15.5
87.5°	3.7	4.4	4.4	4.4	4.4	5.2	5.2	5.2	5.9	5.9	5.9
90°	31.4	29.5	31.4	32.4	33.4	32.4	26.5	19.6	14.7	13.2	11.8
92.5°	73.7	84.5	99.2	126.7	151.3	149.3	115.9	78.6	52.1	46.7	41.3
95°	156.2	197.5	257.4	337.0	385.1	340.9	226.9	141.5	96.3	84.5	72.7
97.5°	321.3	420.5	526.6	632.7	627.8	485.3	301.6	182.7	124.8	111.5	98.2
100°	640.6	775.1	897.0	917.6	776.1	534.4	322.2	202.4	150.3	136.6	122.8
102.5°	1046.3	1135.7	1139.6	1023.7	781.0	515.8	323.2	220.1	172.9	159.2	145.4
105°	1317.5	1304.7	1193.7	989.3	728.0	490.2	328.1	240.7	194.5	180.8	167.0
107.5°	1397.0	1300.8	1135.7	916.6	678.9	476.5	338.9	261.3	216.1	202.4	188.6
110°	1357.7	1232.0	1056.1	848.8	645.5	472.6	352.7	282.0	238.7	224.4	210.2

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1287.0	1150.4	983.4	801.7	623.9	473.5	367.4	301.6	260.3	245.6	230.9
115°	1206.4	1077.7	926.4	764.3	609.1	477.5	382.2	322.2	280.0	266.8	253.5
117.5°	1134.7	1014.9	879.3	738.8	601.3	483.4	397.9	340.9	301.6	287.8	274.1
120°	1071.8	967.7	845.9	719.1	594.4	489.3	413.6	360.6	322.2	308.4	294.7
122.5°	1025.7	928.4	819.4	702.4	590.4	496.1	427.4	379.2	343.9	329.6	315.4
125°	981.5	895.0	793.8	686.7	585.5	503.0	442.1	397.9	362.5	348.8	335.0
127.5°	944.1	861.6	768.3	672.0	582.6	509.9	455.9	415.6	381.2	367.0	352.7
130°	905.8	828.2	743.7	657.3	580.6	517.7	468.6	431.3	396.9	383.2	369.4
132.5°	866.5	796.8	720.1	645.5	579.6	525.6	481.4	445.0	412.6	398.8	385.1
135°	828.2	763.4	698.5	634.7	578.7	531.5	492.2	457.8	426.4	412.6	398.9
137.5°	789.9	736.8	680.8	626.8	578.7	537.4	501.0	468.6	437.2	424.4	411.6
140°	756.5	711.3	664.1	619.9	577.7	541.3	507.9	477.5	448.0	435.2	422.5
142.5°	726.0	688.7	650.4	613.0	577.7	544.3	513.8	484.3	455.9	444.1	432.3
145°	700.5	670.0	637.6	607.2	575.7	546.2	518.7	491.2	464.7	453.9	443.1
147.5°	678.9	654.3	627.8	601.3	572.8	547.2	521.7	497.1	471.6	461.8	451.9
150°	659.2	638.6	617.0	593.4	569.8	546.2	523.6	501.0	478.5	469.6	460.8
152.5°	642.5	625.8	606.2	586.5	564.9	544.3	524.6	505.0	485.3	477.4	469.6
155°	626.8	612.1	596.3	577.7	559.0	542.3	525.6	508.9	492.2	484.8	477.5
157.5°	611.1	598.3	584.6	569.8	553.1	538.4	525.6	511.9	497.1	490.7	484.3
160°	595.4	584.6	573.7	561.0	547.2	535.4	525.6	513.8	502.0	496.6	491.2
162.5°	580.6	571.8	562.9	553.1	542.3	532.5	524.6	514.8	505.0	501.0	497.1
165°	565.9	559.0	552.1	544.3	535.4	528.6	522.7	515.8	506.9	504.0	501.0
167.5°	552.1	547.2	541.3	535.4	529.5	524.6	521.7	515.8	508.9	507.0	505.0
170°	540.3	536.4	533.5	528.6	524.6	521.7	519.7	514.8	509.9	508.4	506.9
172.5°	529.5	526.6	524.6	521.7	518.7	517.7	516.8	513.8	510.9	509.9	508.9
175°	520.7	519.7	518.7	515.8	514.8	513.8	514.8	512.8	510.9	510.4	509.9
177.5°	514.8	513.8	513.8	511.9	510.9	511.9	513.8	511.9	510.9	510.9	510.9
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	962.2	962.2	962.2	962.2
2.5°	944.5	944.5	955.6	967.4
5°	923.8	929.0	946.7	963.0
7.5°	903.8	912.7	934.9	955.6
10°	879.4	891.2	918.6	943.0
12.5°	855.7	866.8	898.6	926.0
15°	822.5	836.5	870.5	904.6
17.5°	789.2	803.2	844.6	884.6
20°	750.0	768.5	815.1	868.3
22.5°	713.7	736.7	788.4	831.3
25°	673.8	709.3	757.4	812.8
27.5°	638.3	673.8	722.6	778.8
30°	598.4	634.6	684.9	736.7
32.5°	559.9	593.2	642.0	705.6
35°	520.0	551.8	599.1	663.4
37.5°	483.7	514.8	566.5	625.7
40°	448.2	480.8	525.1	584.3
42.5°	414.9	443.8	483.7	542.9
45°	384.6	405.3	442.3	497.8
47.5°	352.8	371.3	405.3	460.8
50°	323.2	338.7	368.3	420.1
52.5°	294.4	307.7	335.0	376.5
55°	268.5	281.1	301.0	341.7
57.5°	241.9	251.5	270.7	303.2
60°	216.0	224.8	240.4	267.0
62.5°	190.1	197.5	212.3	233.7
65°	167.2	173.1	184.2	202.7
67.5°	145.0	148.7	157.5	172.3
70°	123.5	126.5	133.9	145.7
72.5°	100.6	103.5	111.7	119.8
75°	81.4	82.1	88.0	94.7
77.5°	63.6	62.9	67.3	72.5
80°	43.6	45.9	49.6	51.8
82.5°	29.6	30.3	31.8	33.3
85°	16.3	17.0	17.0	19.2
87.5°	6.7	7.4	7.4	8.1
90°	9.8	7.9	3.9	1.0
92.5°	33.4	28.5	20.6	14.7
95°	57.0	48.1	38.3	34.4
97.5°	80.6	67.8	57.0	51.1
100°	103.2	87.4	78.6	75.6
102.5°	124.8	109.1	100.2	98.2
105°	145.4	130.7	123.8	119.9
107.5°	167.0	153.3	146.4	143.4
110°	189.6	176.8	170.9	167.0



TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	211.2	199.4	192.6	188.6
115°	233.8	222.0	216.1	211.2
117.5°	255.4	244.6	238.7	234.8
120°	275.1	266.2	260.3	256.4
122.5°	295.7	285.9	280.0	277.0
125°	315.4	303.6	297.7	294.7
127.5°	334.0	321.3	313.4	309.5
130°	349.7	336.0	326.2	322.2
132.5°	364.5	349.7	338.9	334.0
135°	376.3	361.5	349.7	345.8
137.5°	389.0	373.3	361.5	356.6
140°	400.8	385.1	373.3	369.4
142.5°	411.6	395.9	385.1	382.2
145°	423.4	408.7	398.9	394.9
147.5°	435.2	421.5	411.6	408.7
150°	446.0	433.3	425.4	422.5
152.5°	455.9	445.0	437.2	436.2
155°	466.7	455.9	450.0	449.0
157.5°	475.5	465.7	460.8	459.8
160°	483.4	475.5	471.6	470.6
162.5°	490.2	484.3	480.4	481.4
165°	496.1	490.2	488.3	489.3
167.5°	501.0	497.1	495.2	496.1
170°	505.0	502.0	501.0	503.0
172.5°	507.9	505.0	506.0	506.9
175°	509.9	507.9	508.9	509.9
177.5°	510.9	508.9	509.9	511.9
180°	510.9	510.9	510.9	510.9

TEST NUMBER: P998659

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.00	14.74	15.07	15.80	17.24	11.49	12.23	12.56	13.29	14.73
	3H	14.80	15.46	15.88	16.53	17.99	12.83	13.49	13.90	14.56	16.02
	4H	14.97	15.59	16.05	16.66	18.13	13.29	13.91	14.37	14.98	16.45
	6H	15.01	15.58	16.10	16.66	18.14	13.59	14.16	14.68	15.24	16.72
	8H	14.98	15.53	16.08	16.62	18.09	13.67	14.21	14.76	15.30	16.78
	12H	14.94	15.46	16.04	16.54	18.04	13.70	14.22	14.81	15.31	16.80
4H	2H	14.03	14.65	15.12	15.72	17.19	11.92	12.55	13.02	13.62	15.09
	3H	15.00	15.52	16.09	16.62	18.10	13.37	13.89	14.47	14.99	16.47
	4H	15.27	15.74	16.37	16.84	18.34	13.90	14.38	15.01	15.47	16.97
	6H	15.39	15.80	16.50	16.91	18.41	14.28	14.68	15.39	15.80	17.29
	8H	15.39	15.77	16.50	16.87	18.38	14.38	14.77	15.49	15.87	17.38
	12H	15.35	15.69	16.47	16.81	18.32	14.44	14.78	15.56	15.90	17.41
8H	4H	15.27	15.65	16.38	16.75	18.26	14.04	14.42	15.15	15.52	17.03
	6H	15.44	15.76	16.57	16.90	18.41	14.47	14.78	15.60	15.93	17.44
	8H	15.47	15.75	16.61	16.87	18.40	14.62	14.89	15.75	16.02	17.55
	12H	15.45	15.69	16.59	16.82	18.38	14.70	14.94	15.84	16.07	17.63
12H	4H	15.22	15.56	16.35	16.68	18.20	14.01	14.35	15.13	15.47	16.98
	6H	15.42	15.70	16.56	16.82	18.35	14.47	14.74	15.60	15.87	17.40
	8H	15.45	15.69	16.59	16.81	18.38	14.62	14.86	15.76	15.98	17.55