

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999874

Luminaire Tested: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999874
REPORT IS A COMBINATION OF REPORTS P988429 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6582.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999874

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999874

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	36
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	29	27
4	73	62	55	49	65	57	50	45	46	41	38	36	33	31	27	25	24
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21
6	61	50	42	37	55	46	39	34	37	32	29	30	26	23	23	20	18
7	57	45	37	32	51	41	35	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17795	17795	17795
5°	17824	16930	16805
10°	17648	16056	15527
15°	17405	15027	14070
20°	17086	13854	12548
25°	16757	12653	11155
30°	16314	11481	9633
35°	15883	10299	8327
40°	15442	9141	6981
45°	14932	7943	5807
50°	14403	6788	4728
55°	13853	5634	3754
60°	13212	4507	2840
65°	12478	3435	2309
70°	11589	2492	1836
75°	10472	1901	1401
80°	8854	1286	942
85°	6173	588	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14932 cd/sqm

TEST NUMBER: P999874

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	1.6
10°-20°	289.2	4.4
20°-30°	406.1	6.2
30°-40°	442.6	6.7
40°-50°	406.8	6.2
50°-60°	319.5	4.9
60°-70°	208.0	3.2
70°-80°	107.1	1.6
80°-90°	29.9	0.5
90°-100°	48.0	0.7
100°-110°	178.9	2.7
110°-120°	474.6	7.2
120°-130°	787.1	12.0
130°-140°	836.1	12.7
140°-150°	777.0	11.8
150°-160°	624.7	9.5
160°-170°	402.5	6.1
170°-180°	138.5	2.1
0°-30°	800.7	12.2
0°-40°	1243.3	18.9
0°-60°	1969.7	29.9
0°-90°	2314.6	35.2
90°-120°	701.5	10.7
90°-150°	3101.6	47.1
90°-180°	4267.0	64.8
0°-180°	6582.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1124	1119	1106	1115	1112	107
15°	1069	1058	1024	1004	994	301
25°	971	938	871	829	814	446
35°	836	784	695	631	608	523
45°	684	616	509	436	412	528
55°	520	440	331	270	250	465
65°	351	269	177	142	139	348
75°	187	116	81	74	73	198
85°	44	22	19	19	19	50
90°	1	13	21	26	28	6
95°	68	34	41	46	45	81
105°	320	352	64	76	80	342
115°	606	624	650	162	86	596
125°	856	870	890	897	901	764
135°	1060	1076	1086	1096	1094	819
145°	1229	1228	1246	1253	1248	769
155°	1354	1344	1357	1363	1354	624
165°	1426	1420	1423	1430	1423	403
175°	1459	1451	1454	1461	1450	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P999874

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1124.2	1124.2	1124.2	1124.2	1124.2
2.5°	1129.3	1124.2	1113.0	1123.2	1121.1
5°	1124.2	1119.1	1105.9	1115.0	1112.0
7.5°	1115.0	1108.9	1094.7	1098.7	1093.6
10°	1102.8	1095.7	1075.3	1072.3	1066.2
12.5°	1087.5	1078.4	1050.9	1044.8	1033.6
15°	1069.2	1058.0	1023.5	1004.1	993.9
17.5°	1047.9	1031.6	988.9	966.5	950.2
20°	1023.5	1003.1	952.2	926.8	904.4
22.5°	997.0	973.6	914.6	880.0	864.7
25°	970.6	938.0	870.9	829.1	813.9
27.5°	939.0	904.4	830.2	782.3	758.9
30°	905.4	866.8	785.4	733.5	706.0
32.5°	872.9	826.1	742.7	681.6	656.2
35°	836.3	784.4	694.8	630.8	608.4
37.5°	800.7	744.7	650.1	579.9	554.5
40°	763.0	702.0	603.3	531.1	504.6
42.5°	724.4	659.2	556.5	481.2	455.8
45°	683.7	615.5	508.7	436.4	412.0
47.5°	645.0	572.8	462.9	390.7	368.3
50°	602.3	530.0	418.1	347.9	326.6
52.5°	560.6	484.3	375.4	308.3	288.9
55°	519.9	440.5	330.6	269.6	250.3
57.5°	478.2	396.8	291.0	234.0	217.7
60°	435.4	354.0	249.3	197.4	181.1
62.5°	393.7	312.3	213.6	164.8	156.7
65°	351.0	268.6	177.0	142.4	139.4
67.5°	310.3	227.9	142.4	125.1	122.1
70°	267.6	188.2	118.0	107.8	103.8
72.5°	226.9	151.6	98.7	90.5	88.5
75°	187.2	116.0	81.4	74.3	73.2
77.5°	147.5	82.4	64.1	60.0	58.0
80°	110.9	59.0	48.8	44.8	44.8
82.5°	77.3	39.7	33.6	31.5	31.5
85°	43.7	22.4	19.3	19.3	19.3
87.5°	16.3	8.1	8.1	7.1	7.1
90°	1.1	12.6	21.1	26.3	28.4
92.5°	26.3	22.1	25.3	27.4	28.4
95°	68.5	33.7	41.1	46.3	45.3
97.5°	123.2	36.9	53.7	56.9	57.9
100°	186.4	42.1	60.0	68.5	70.6
102.5°	255.9	253.8	62.1	73.7	76.9
105°	320.2	351.8	64.3	75.8	80.0
107.5°	395.0	421.3	66.4	77.9	82.2
110°	466.6	488.7	184.3	79.0	83.2

TEST NUMBER: P999874

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	534.0	553.0	535.1	81.1	84.3
115°	605.6	623.5	649.9	162.2	86.4
117.5°	667.8	688.9	706.8	556.1	280.2
120°	737.3	753.1	772.1	784.7	642.5
122.5°	796.3	813.1	834.2	840.5	841.6
125°	856.3	870.0	890.0	897.4	900.6
127.5°	911.1	925.8	941.6	952.2	953.2
130°	962.7	979.6	991.1	1002.7	1001.7
132.5°	1015.4	1029.1	1040.6	1050.1	1049.1
135°	1059.6	1076.5	1085.9	1096.5	1094.4
137.5°	1106.0	1118.6	1129.1	1139.7	1136.5
140°	1151.2	1159.7	1171.3	1180.7	1175.5
142.5°	1189.2	1196.5	1210.2	1218.7	1213.4
145°	1229.2	1228.1	1246.0	1253.4	1248.1
147.5°	1263.9	1260.8	1278.7	1284.0	1279.7
150°	1297.7	1290.3	1307.1	1313.5	1308.2
152.5°	1326.1	1317.7	1333.5	1339.8	1332.4
155°	1353.5	1344.0	1356.6	1363.0	1354.5
157.5°	1375.6	1367.2	1376.6	1384.0	1375.6
160°	1394.6	1388.2	1394.6	1400.9	1393.5
162.5°	1411.4	1405.1	1410.4	1417.7	1408.2
165°	1426.2	1419.8	1423.0	1430.4	1423.0
167.5°	1437.7	1431.4	1434.6	1442.0	1432.5
170°	1447.2	1440.9	1443.0	1450.4	1440.9
172.5°	1453.5	1447.2	1449.3	1456.7	1447.2
175°	1458.8	1451.4	1453.5	1460.9	1450.4
177.5°	1460.9	1453.5	1454.6	1462.0	1452.5
180°	1455.6	1455.6	1455.6	1455.6	1455.6

(END OF REPORT)