

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998662

Luminaire Tested: SA2XXDIP-B485D925UB40-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998662
REPORT IS A COMBINATION OF REPORTS P984405 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D925UB40-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5512.0 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998662

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P998662

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	93	88	84	80	83	79	76	72	62	60	58	47	46	44	33	32	31
2	84	76	70	65	75	69	63	59	54	50	47	41	38	36	28	27	25
3	76	67	59	53	68	60	54	48	47	43	39	36	33	30	25	23	21
4	70	59	51	45	62	53	46	41	42	37	33	32	28	25	22	20	18
5	64	52	44	38	57	47	40	35	37	32	28	28	25	22	20	17	15
6	59	46	38	33	52	42	35	30	33	28	24	25	22	19	18	15	13
7	54	42	34	28	48	38	31	26	30	25	21	23	19	16	16	14	12
8	50	38	30	25	45	34	27	23	27	22	19	21	17	15	15	12	11
9	46	34	27	22	42	31	25	20	25	20	17	19	16	13	14	11	9
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8078	8078	8078
5°	8113	7733	7689
10°	8059	7464	7356
15°	7946	7188	7014
20°	7802	6896	6690
25°	7660	6618	6395
30°	7461	6336	6104
35°	7260	6063	5891
40°	7049	5826	5678
45°	6849	5612	5493
50°	6631	5415	5310
55°	6403	5205	5125
60°	6127	4986	4929
65°	5837	4736	4704
70°	5509	4467	4462
75°	5091	4198	4232
80°	4431	3916	3996
85°	3757	3653	3791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6849 cd/sqm

TEST NUMBER: P998662

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	0.9
10°-20°	138.7	2.5
20°-30°	210.2	3.8
30°-40°	256.0	4.6
40°-50°	275.4	5.0
50°-60°	267.5	4.9
60°-70°	233.6	4.2
70°-80°	179.8	3.3
80°-90°	123.7	2.2
90°-100°	290.2	5.3
100°-110°	760.8	13.8
110°-120°	776.0	14.1
120°-130°	627.5	11.4
130°-140°	495.7	9.0
140°-150°	369.0	6.7
150°-160°	258.3	4.7
160°-170°	152.1	2.8
170°-180°	49.5	0.9
0°-30°	397.3	7.2
0°-40°	653.3	11.9
0°-60°	1196.2	21.7
0°-90°	1733.2	31.4
90°-120°	1827.0	33.1
90°-150°	3319.0	60.2
90°-180°	3779.0	68.6
0°-180°	5512.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	510	510	510	510	510	
5°	512	510	505	510	509	49
15°	488	490	490	496	496	137
25°	444	449	456	464	467	204
35°	382	395	409	425	430	239
45°	314	334	359	382	390	242
55°	240	267	305	332	342	215
65°	164	200	244	274	284	163
75°	91	132	180	212	221	96
85°	27	72	120	151	161	28
90°	8	64	131	159	168	7
95°	40	125	470	258	234	40
105°	124	206	792	1391	1205	132
115°	214	278	654	1324	1532	212
125°	296	350	611	1063	1234	264
135°	346	413	587	879	1009	268
145°	395	454	576	719	790	248
155°	449	485	559	632	657	207
165°	489	504	535	568	577	138
175°	510	510	515	521	520	48
180°	511	511	511	511	511	

TEST NUMBER: P998662

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	510.3	510.3	510.3	510.3	510.3
2.5°	514.0	511.7	506.6	510.3	508.8
5°	511.7	509.5	505.1	509.5	508.8
7.5°	508.0	506.6	502.9	508.0	507.3
10°	503.6	502.1	499.9	505.8	505.1
12.5°	496.2	497.0	495.5	501.4	500.7
15°	488.1	489.6	489.6	496.2	495.5
17.5°	477.7	480.7	482.9	489.6	489.6
20°	467.4	471.1	474.0	482.2	482.2
22.5°	456.3	460.7	465.2	473.3	474.8
25°	443.7	448.9	455.5	464.4	466.6
27.5°	428.9	437.1	444.4	455.5	457.0
30°	414.1	423.7	433.4	445.2	447.4
32.5°	397.9	409.0	420.8	434.8	439.3
35°	382.3	394.9	409.0	425.2	430.4
37.5°	365.3	379.4	397.1	414.9	420.0
40°	348.3	364.6	384.5	403.8	410.4
42.5°	332.0	348.3	372.0	393.4	400.1
45°	313.6	333.5	359.4	382.3	389.7
47.5°	295.8	317.3	346.8	370.5	378.6
50°	277.3	300.2	333.5	358.7	366.8
52.5°	259.6	284.0	319.5	345.4	354.2
55°	240.3	267.0	305.4	332.0	341.7
57.5°	221.9	251.4	289.9	318.7	328.3
60°	201.9	233.7	275.8	303.9	314.3
62.5°	184.1	217.4	259.6	289.9	299.5
65°	164.2	200.4	244.0	274.4	284.0
67.5°	146.4	184.1	228.5	258.8	269.2
70°	127.2	165.7	211.5	243.3	252.2
72.5°	109.4	149.4	196.0	227.0	238.1
75°	91.0	132.4	179.7	211.5	221.1
77.5°	73.2	116.1	164.2	196.0	206.3
80°	55.5	100.6	148.6	179.7	190.1
82.5°	40.7	85.0	133.9	164.9	174.5
85°	26.6	72.5	119.8	150.9	161.2
87.5°	16.3	60.6	108.0	138.3	147.9
90°	8.4	63.6	131.0	159.1	168.5
92.5°	21.4	92.6	242.3	189.6	188.6
95°	40.3	125.2	470.1	258.5	234.0
97.5°	56.3	148.5	707.7	399.0	303.7
100°	80.8	169.0	850.1	682.4	461.1
102.5°	102.6	188.0	849.8	1077.9	789.2
105°	123.6	205.8	791.6	1390.8	1204.8
107.5°	147.1	223.8	737.3	1500.2	1482.8
110°	170.0	242.2	699.5	1475.6	1592.9

TEST NUMBER: P998662

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	191.6	260.4	672.7	1407.2	1585.7
115°	214.2	277.8	653.5	1323.6	1531.7
117.5°	237.0	296.0	640.5	1244.2	1453.1
120°	258.6	313.6	629.2	1172.0	1378.1
122.5°	279.2	332.6	620.7	1115.3	1298.7
125°	296.2	350.2	610.6	1063.4	1233.7
127.5°	311.0	367.6	603.3	1017.7	1171.8
130°	323.7	383.8	596.9	972.2	1119.6
132.5°	335.5	399.6	591.4	925.2	1066.4
135°	346.5	413.4	586.8	879.4	1009.1
137.5°	357.3	425.1	583.1	833.0	953.1
140°	370.1	435.2	579.2	791.4	895.0
142.5°	382.9	444.1	577.7	752.1	837.9
145°	394.9	453.9	575.7	719.2	790.1
147.5°	408.7	461.8	572.8	690.4	746.7
150°	422.5	469.6	569.8	668.0	710.3
152.5°	436.2	477.4	564.9	649.9	681.8
155°	449.0	484.8	559.0	632.2	657.3
157.5°	459.8	490.7	553.1	615.5	635.6
160°	470.6	496.6	547.2	598.8	615.0
162.5°	481.4	501.0	542.3	583.0	595.4
165°	489.3	504.0	535.4	567.8	576.7
167.5°	496.1	507.0	529.5	554.1	559.0
170°	503.0	508.4	524.6	541.3	543.3
172.5°	506.9	509.9	518.7	530.0	530.5
175°	509.9	510.4	514.8	521.2	519.7
177.5°	511.9	510.9	510.9	514.8	511.9
180°	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P998662

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.47	11.21	11.56	12.31	13.82	13.55	14.29	14.64	15.39	16.90
	3H	11.92	12.59	13.03	13.70	15.23	16.13	16.80	17.23	17.90	19.43
	4H	12.39	13.03	13.51	14.14	15.67	17.38	18.01	18.49	19.12	20.65
	6H	12.67	13.26	13.79	14.37	15.92	18.67	19.26	19.79	20.37	21.91
	8H	12.73	13.29	13.85	14.42	15.95	19.32	19.89	20.45	21.01	22.55
	12H	12.74	13.28	13.87	14.40	15.96	20.04	20.58	21.17	21.70	23.26
4H	2H	11.51	12.15	12.63	13.25	14.79	13.86	14.50	14.98	15.61	17.14
	3H	13.21	13.75	14.33	14.88	16.42	16.65	17.18	17.77	18.32	19.86
	4H	13.83	14.32	14.95	15.44	17.01	18.06	18.56	19.19	19.68	21.24
	6H	14.24	14.67	15.37	15.81	17.36	19.52	19.95	20.65	21.09	22.65
	8H	14.34	14.74	15.48	15.88	17.45	20.27	20.68	21.41	21.81	23.39
	12H	14.38	14.74	15.53	15.89	17.47	21.10	21.46	22.25	22.61	24.19
8H	4H	14.61	15.01	15.74	16.15	17.72	18.19	18.60	19.33	19.73	21.31
	6H	15.23	15.57	16.39	16.75	18.32	19.82	20.15	20.97	21.33	22.90
	8H	15.46	15.75	16.62	16.91	18.50	20.71	21.00	21.87	22.16	23.75
	12H	15.58	15.84	16.75	17.00	18.62	21.69	21.96	22.86	23.11	24.73
12H	4H	14.80	15.17	15.95	16.31	17.89	18.16	18.53	19.31	19.68	21.25
	6H	15.57	15.86	16.73	17.02	18.61	19.84	20.14	21.00	21.29	22.88
	8H	15.87	16.13	17.03	17.28	18.90	20.76	21.03	21.93	22.18	23.80