

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999877

Luminaire Tested: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999877
REPORT IS A COMBINATION OF REPORTS P988432 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6601.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999877

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P999877

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	36
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	29	27
4	73	62	55	49	65	57	50	45	46	41	38	36	33	31	27	25	24
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21
6	61	50	42	37	55	46	39	34	37	32	29	30	26	23	23	20	18
7	57	45	37	32	51	41	35	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17849	17849	17849
5°	17878	16981	16854
10°	17701	16105	15574
15°	17459	15072	14114
20°	17137	13896	12587
25°	16807	12690	11188
30°	16364	11516	9663
35°	15930	10332	8352
40°	15489	9168	7002
45°	14976	7967	5825
50°	14446	6809	4743
55°	13893	5651	3764
60°	13251	4520	2848
65°	12513	3447	2315
70°	11624	2501	1842
75°	10506	1906	1407
80°	8878	1291	944
85°	6201	592	456

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14976 cd/sqm

TEST NUMBER: P999877

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.7	1.6
10°-20°	290.1	4.4
20°-30°	407.3	6.2
30°-40°	444.0	6.7
40°-50°	408.1	6.2
50°-60°	320.5	4.9
60°-70°	208.6	3.2
70°-80°	107.4	1.6
80°-90°	30.0	0.5
90°-100°	48.1	0.7
100°-110°	179.4	2.7
110°-120°	475.9	7.2
120°-130°	789.3	12.0
130°-140°	838.4	12.7
140°-150°	779.2	11.8
150°-160°	626.5	9.5
160°-170°	403.7	6.1
170°-180°	138.9	2.1
0°-30°	803.1	12.2
0°-40°	1247.1	18.9
0°-60°	1975.6	29.9
0°-90°	2321.6	35.2
90°-120°	703.5	10.7
90°-150°	3110.3	47.1
90°-180°	4279.0	64.8
0°-180°	6601.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1109	1118	1115	107
15°	1072	1061	1027	1007	997	302
25°	974	941	874	832	816	448
35°	839	787	697	633	610	525
45°	686	617	510	438	413	530
55°	521	442	332	270	251	466
65°	352	269	178	143	140	349
75°	188	116	82	74	74	199
85°	44	22	19	19	19	50
90°	1	13	21	26	28	6
95°	69	34	41	46	45	81
105°	321	353	64	76	80	343
115°	607	625	652	163	87	598
125°	859	872	892	900	903	766
135°	1063	1080	1089	1100	1097	821
145°	1233	1232	1250	1257	1252	771
155°	1357	1348	1360	1367	1358	625
165°	1430	1424	1427	1434	1427	404
175°	1463	1456	1458	1465	1454	139
180°	1460	1460	1460	1460	1460	

TEST NUMBER: P999877

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1127.6	1127.6	1127.6	1127.6	1127.6
2.5°	1132.7	1127.6	1116.3	1126.6	1124.5
5°	1127.6	1122.5	1109.2	1118.4	1115.3
7.5°	1118.4	1112.3	1098.0	1102.1	1097.0
10°	1106.1	1099.0	1078.6	1075.5	1069.4
12.5°	1090.8	1081.7	1054.1	1048.0	1036.8
15°	1072.5	1061.2	1026.6	1007.2	997.0
17.5°	1051.0	1034.7	991.9	969.4	953.1
20°	1026.6	1006.1	955.1	929.6	907.2
22.5°	1000.0	976.6	917.4	882.7	867.4
25°	973.5	940.8	873.5	831.6	816.3
27.5°	941.9	907.2	832.7	784.7	761.2
30°	908.2	869.4	787.8	735.7	708.2
32.5°	875.5	828.6	744.9	683.7	658.2
35°	838.8	786.8	697.0	632.7	610.2
37.5°	803.1	747.0	652.1	581.6	556.1
40°	765.3	704.1	605.1	532.7	506.1
42.5°	726.5	661.2	558.2	482.7	457.2
45°	685.7	617.4	510.2	437.8	413.3
47.5°	647.0	574.5	464.3	391.8	369.4
50°	604.1	531.6	419.4	349.0	327.6
52.5°	562.3	485.7	376.5	309.2	289.8
55°	521.4	441.8	331.6	270.4	251.0
57.5°	479.6	398.0	291.8	234.7	218.4
60°	436.7	355.1	250.0	198.0	181.6
62.5°	394.9	313.3	214.3	165.3	157.1
65°	352.0	269.4	177.6	142.9	139.8
67.5°	311.2	228.6	142.9	125.5	122.5
70°	268.4	188.8	118.4	108.2	104.1
72.5°	227.6	152.0	99.0	90.8	88.8
75°	187.8	116.3	81.6	74.5	73.5
77.5°	148.0	82.7	64.3	60.2	58.2
80°	111.2	59.2	49.0	44.9	44.9
82.5°	77.6	39.8	33.7	31.6	31.6
85°	43.9	22.4	19.4	19.4	19.4
87.5°	16.3	8.2	8.2	7.1	7.1
90°	1.1	12.7	21.1	26.4	28.5
92.5°	26.4	22.2	25.3	27.5	28.5
95°	68.7	33.8	41.2	46.5	45.4
97.5°	123.6	37.0	53.9	57.0	58.1
100°	187.0	42.2	60.2	68.7	70.8
102.5°	256.7	254.6	62.3	73.9	77.1
105°	321.1	352.8	64.4	76.0	80.3
107.5°	396.1	422.5	66.5	78.2	82.4
110°	467.9	490.1	184.8	79.2	83.4

TEST NUMBER: P999877

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	535.5	554.5	536.6	81.3	84.5
115°	607.3	625.3	651.7	162.7	86.6
117.5°	669.7	690.8	708.7	557.7	281.0
120°	739.4	755.2	774.2	786.9	644.3
122.5°	798.5	815.4	836.5	842.9	843.9
125°	858.7	872.5	892.5	899.9	903.1
127.5°	913.7	928.4	944.3	954.8	955.9
130°	965.4	982.3	993.9	1005.5	1004.5
132.5°	1018.2	1032.0	1043.6	1053.1	1052.0
135°	1062.6	1079.5	1089.0	1099.6	1097.4
137.5°	1109.1	1121.7	1132.3	1142.9	1139.7
140°	1154.5	1162.9	1174.5	1184.1	1178.8
142.5°	1192.5	1199.9	1213.6	1222.1	1216.8
145°	1232.6	1231.6	1249.5	1256.9	1251.7
147.5°	1267.5	1264.3	1282.3	1287.6	1283.3
150°	1301.3	1293.9	1310.8	1317.1	1311.9
152.5°	1329.8	1321.4	1337.2	1343.5	1336.2
155°	1357.3	1347.8	1360.4	1366.8	1358.3
157.5°	1379.5	1371.0	1380.5	1387.9	1379.5
160°	1398.5	1392.1	1398.5	1404.8	1397.4
162.5°	1415.4	1409.0	1414.3	1421.7	1412.2
165°	1430.2	1423.8	1427.0	1434.4	1427.0
167.5°	1441.8	1435.4	1438.6	1446.0	1436.5
170°	1451.3	1444.9	1447.1	1454.5	1444.9
172.5°	1457.6	1451.3	1453.4	1460.8	1451.3
175°	1462.9	1455.5	1457.6	1465.0	1454.5
177.5°	1465.0	1457.6	1458.7	1466.1	1456.6
180°	1459.7	1459.7	1459.7	1459.7	1459.7

(END OF REPORT)