

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998667

Luminaire Tested: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998667
REPORT IS A COMBINATION OF REPORTS P984410 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5204.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	46	46	46
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	42	41	40
2	88	80	75	70	79	73	69	64	60	57	54	48	46	44	37	36	34
3	80	71	64	59	73	65	59	54	54	49	46	43	40	37	33	31	30
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26
5	67	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	53	42	34	29	49	38	32	27	32	27	23	26	23	20	21	18	16
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14729	14729	14729	14729
5°	14764	15704	14821	12495
10°	14593	17145	14684	10302
15°	14239	18083	14438	8678
20°	14017	16980	14017	7542
25°	13570	14587	13632	6745
30°	12836	11467	13081	6109
35°	12185	7929	12388	5590
40°	11435	5986	11567	5176
45°	10514	4919	10684	4727
50°	9716	4319	9733	4329
55°	8804	3679	8863	3893
60°	7835	3074	7944	3398
65°	6968	2499	7092	2902
70°	6102	1962	6258	2340
75°	5119	1424	5320	1698
80°	4000	902	4279	1007
85°	2627	454	2825	336

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15226 cd/sqm

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.6	1.7
10°-20°	258.0	5.0
20°-30°	374.4	7.2
30°-40°	394.7	7.6
40°-50°	349.2	6.7
50°-60°	278.9	5.4
60°-70°	189.4	3.6
70°-80°	96.9	1.9
80°-90°	26.1	0.5
90°-100°	69.7	1.3
100°-110°	221.4	4.3
110°-120°	378.9	7.3
120°-130°	498.3	9.6
130°-140°	559.3	10.7
140°-150°	548.5	10.5
150°-160°	460.1	8.8
160°-170°	305.1	5.9
170°-180°	106.6	2.0
0°-30°	721.0	13.9
0°-40°	1115.7	21.4
0°-60°	1743.8	33.5
0°-90°	2056.2	39.5
90°-120°	670.0	12.9
90°-150°	2276.0	43.7
90°-180°	3148.0	60.5
0°-180°	5204.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	931	1039	935	827	931	88
15°	875	1277	887	613	875	247
25°	786	1064	790	492	786	359
35°	642	579	652	408	642	401
45°	481	349	489	335	481	373
55°	330	245	333	260	330	295
65°	196	151	200	175	196	195
75°	92	74	95	89	92	98
85°	19	19	20	14	19	22
90°	1	32	1	32	1	4
95°	49	59	49	59	49	55
105°	204	211	204	211	204	216
115°	380	380	380	380	380	376
125°	553	555	553	555	553	494
135°	715	724	715	724	715	553
145°	868	878	868	878	868	543
155°	993	1000	993	1000	993	457
165°	1080	1081	1080	1081	1080	305
175°	1124	1120	1124	1120	1124	107
180°	1126	1126	1126	1126	1126	

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	935.5	937.7	941.2	942.0	949.1	954.8	961.3	961.3	963.4	962.7	957.0
5°	931.2	937.7	947.0	954.8	967.7	973.4	982.0	988.4	994.2	998.5	997.7
7.5°	924.1	935.5	949.1	964.1	981.3	991.3	1003.5	1014.9	1022.8	1029.9	1034.9
10°	911.9	931.2	949.8	969.9	992.0	1005.6	1019.9	1034.9	1047.1	1060.7	1073.6
12.5°	895.5	923.4	946.3	972.7	999.9	1014.9	1037.8	1049.2	1072.8	1107.2	1116.5
15°	874.7	912.6	934.1	967.7	1003.5	1015.6	1047.1	1065.7	1114.3	1135.8	1161.5
17.5°	855.4	897.6	926.2	964.8	999.9	1023.5	1054.3	1092.2	1132.9	1163.7	1192.3
20°	839.7	880.4	914.8	957.7	1002.0	1032.1	1064.3	1110.0	1154.4	1185.9	1208.0
22.5°	803.9	856.1	896.2	944.1	997.7	1039.2	1070.0	1120.1	1168.0	1187.3	1206.6
25°	786.0	831.1	877.6	931.9	994.9	1044.2	1070.7	1126.5	1168.7	1175.8	1180.1
27.5°	753.1	803.9	858.3	920.5	994.2	1035.7	1069.3	1120.1	1153.7	1148.7	1135.8
30°	712.4	774.6	834.7	901.9	984.2	1029.2	1060.7	1107.2	1124.3	1098.6	1075.7
32.5°	682.3	741.0	807.5	885.5	972.7	1015.6	1046.4	1082.9	1086.4	1039.9	1001.3
35°	641.6	706.6	781.7	864.0	953.4	992.0	1020.6	1042.8	1025.6	960.6	914.8
37.5°	605.1	669.5	749.6	833.2	926.9	964.8	987.7	991.3	949.1	891.9	824.7
40°	565.0	631.5	715.2	803.2	897.6	930.5	944.8	934.1	873.3	806.8	728.8
42.5°	525.0	590.8	680.9	771.0	860.4	888.3	894.0	864.7	790.3	712.4	622.3
45°	481.4	550.0	640.1	731.0	817.5	833.2	834.0	791.8	703.8	622.3	538.6
47.5°	445.6	509.2	598.6	689.5	762.4	773.2	768.9	720.2	624.4	532.8	459.9
50°	406.3	467.0	555.7	645.1	707.4	710.2	699.5	630.1	536.4	452.7	394.8
52.5°	364.1	425.6	507.1	592.9	648.7	644.4	623.7	549.3	461.3	391.9	347.6
55°	330.4	384.8	461.3	545.0	584.3	572.2	549.3	473.5	404.1	345.5	306.8
57.5°	293.2	341.2	416.3	489.2	512.1	500.7	477.8	407.0	342.6	298.3	272.5
60°	258.2	301.8	367.6	428.4	446.3	434.1	407.7	344.0	297.5	260.3	241.0
62.5°	226.0	263.9	319.0	374.8	381.9	369.8	346.9	295.4	255.3	226.0	211.7
65°	196.0	231.7	276.1	318.3	324.7	311.8	288.2	251.0	217.4	198.8	185.2
67.5°	166.6	195.3	234.6	265.4	268.9	256.8	237.5	207.4	186.7	166.6	156.6
70°	140.9	162.4	193.1	218.1	219.6	208.1	198.1	170.9	155.2	140.9	133.0
72.5°	115.9	130.9	154.5	173.1	173.8	166.6	157.4	140.2	126.6	116.6	108.7
75°	91.5	104.4	118.7	135.2	134.5	128.7	121.6	110.9	99.4	93.0	89.4
77.5°	70.1	78.0	89.4	100.1	100.1	97.3	93.0	85.1	78.0	71.5	67.9
80°	50.1	55.1	64.4	67.9	69.4	68.7	65.1	59.4	56.5	51.5	50.1
82.5°	32.2	35.8	40.1	43.6	45.8	44.3	43.6	40.8	36.5	35.0	33.6
85°	18.6	20.0	22.2	24.3	25.0	24.3	25.7	23.6	21.5	21.5	20.7
87.5°	7.9	8.6	10.0	10.0	10.7	10.7	10.0	10.7	10.7	10.0	9.3
90°	1.0	3.5	6.1	8.6	11.1	12.4	14.7	19.4	24.0	28.7	33.3
92.5°	20.9	22.6	24.3	26.0	27.7	28.5	28.6	28.8	29.1	29.3	29.5
95°	49.4	51.5	53.6	55.7	57.8	58.9	59.1	59.5	60.0	60.4	60.8
97.5°	82.7	84.6	86.5	88.4	90.3	91.2	91.6	92.5	93.3	94.2	95.0
100°	120.7	122.4	124.1	125.8	127.5	128.3	128.6	129.2	129.9	130.5	131.1
102.5°	160.6	161.9	163.1	164.4	165.7	166.3	166.7	167.6	168.4	169.3	170.1
105°	204.3	204.9	205.5	206.2	206.8	207.1	207.3	207.7	208.2	208.6	209.0
107.5°	248.0	248.8	249.7	250.5	251.4	251.8	251.8	251.8	251.8	251.8	251.8
110°	289.8	291.1	292.3	293.6	294.9	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	335.4	336.7	337.9	339.2	340.5	341.1	341.0	340.8	340.5	340.3	340.1
115°	380.0	381.3	382.6	383.9	385.2	385.8	385.6	385.2	384.7	384.3	383.9
117.5°	424.7	426.4	428.1	429.8	431.5	432.3	431.8	430.7	429.7	428.6	427.6
120°	469.4	471.1	472.8	474.5	476.2	477.0	476.2	474.5	472.8	471.1	469.4
122.5°	510.2	512.3	514.4	516.5	518.6	519.7	519.2	518.1	517.1	516.0	515.0
125°	553.0	554.9	556.8	558.7	560.6	561.5	561.2	560.6	559.9	559.3	558.7
127.5°	594.8	597.1	599.4	601.7	604.0	605.2	604.8	603.9	603.1	602.2	601.4
130°	633.7	636.5	639.2	642.0	644.7	646.1	645.9	645.5	645.0	644.6	644.2
132.5°	677.4	679.5	681.6	683.7	685.8	686.9	687.0	687.2	687.5	687.7	687.9
135°	715.4	717.7	720.1	722.4	724.7	725.9	726.1	726.5	727.0	727.4	727.8
137.5°	757.2	759.1	761.0	762.9	764.8	765.8	766.0	766.4	766.9	767.3	767.7
140°	794.3	796.2	798.1	800.0	801.9	802.9	803.4	804.5	805.5	806.6	807.6
142.5°	832.3	834.2	836.1	838.0	839.9	840.9	841.2	841.8	842.5	843.1	843.7
145°	868.4	869.9	871.4	872.9	874.4	875.1	875.7	877.0	878.3	879.5	880.8
147.5°	900.7	902.6	904.5	906.4	908.3	909.3	909.7	910.6	911.4	912.3	913.1
150°	934.0	935.3	936.5	937.8	939.1	939.7	940.1	941.0	941.8	942.7	943.5
152.5°	963.4	964.7	965.9	967.2	968.5	969.1	969.6	970.7	971.8	972.8	973.9
155°	992.9	993.5	994.1	994.8	995.4	995.7	996.0	996.7	997.3	998.0	998.6
157.5°	1018.5	1018.9	1019.3	1019.8	1020.2	1020.4	1020.6	1021.0	1021.5	1021.9	1022.3
160°	1041.3	1041.7	1042.1	1042.6	1043.0	1043.2	1043.3	1043.5	1043.8	1044.0	1044.2
162.5°	1062.2	1062.2	1062.2	1062.2	1062.2	1062.2	1062.3	1062.5	1062.8	1063.0	1063.2
165°	1080.3	1080.1	1079.9	1079.6	1079.4	1079.3	1079.3	1079.3	1079.3	1079.3	1079.3
167.5°	1096.4	1095.8	1095.2	1094.5	1093.9	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
170°	1108.8	1108.2	1107.5	1106.9	1106.2	1105.9	1105.8	1105.6	1105.4	1105.2	1105.0
172.5°	1117.3	1116.7	1116.1	1115.4	1114.8	1114.5	1114.4	1114.2	1113.9	1113.7	1113.5
175°	1124.0	1123.4	1122.7	1122.1	1121.4	1121.1	1120.9	1120.5	1120.0	1119.6	1119.2
177.5°	1127.8	1127.2	1126.5	1125.9	1125.2	1124.9	1124.7	1124.3	1123.8	1123.4	1123.0
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	967.0	967.7	969.1	976.3	979.9	980.6	977.7	984.2	986.3	984.2	982.7
5°	1012.8	1017.1	1025.6	1034.9	1034.2	1034.9	1039.2	1043.5	1045.0	1039.2	1041.4
7.5°	1052.8	1061.4	1070.7	1085.0	1085.0	1092.2	1095.0	1098.6	1107.2	1102.9	1101.5
10°	1098.6	1110.0	1127.2	1150.1	1150.8	1158.0	1165.1	1176.6	1180.1	1177.3	1178.7
12.5°	1155.8	1178.0	1179.4	1204.4	1215.9	1217.3	1228.8	1226.6	1233.8	1233.8	1245.9
15°	1180.8	1215.2	1234.5	1258.8	1266.0	1257.4	1266.7	1276.7	1277.4	1277.4	1276.7
17.5°	1225.9	1239.5	1258.8	1271.7	1274.5	1274.5	1275.3	1279.5	1276.7	1271.0	1275.3
20°	1235.2	1240.9	1248.1	1246.6	1248.1	1240.9	1233.8	1226.6	1227.3	1223.8	1234.5
22.5°	1218.0	1216.6	1200.2	1189.4	1189.4	1175.1	1161.5	1155.1	1148.7	1150.8	1154.4
25°	1175.1	1153.0	1132.9	1117.2	1113.6	1090.7	1072.1	1066.4	1055.7	1064.3	1065.7
27.5°	1106.5	1081.4	1049.2	1035.7	1017.1	1007.8	994.9	977.7	955.5	968.4	966.3
30°	1032.8	995.6	969.1	936.2	906.9	904.8	880.4	851.8	840.4	840.4	846.8
32.5°	950.5	901.2	862.6	816.1	787.5	775.3	746.0	717.4	723.8	702.4	710.2
35°	854.7	789.6	741.0	695.9	674.5	660.2	622.3	606.5	589.4	579.3	597.9
37.5°	763.2	688.1	625.8	576.5	568.6	542.9	517.1	507.1	497.1	501.4	500.7
40°	651.6	585.1	529.3	490.6	477.1	464.9	447.7	435.6	429.1	432.7	433.4
42.5°	550.7	494.9	453.5	426.3	414.8	406.3	397.7	387.7	385.5	385.5	388.4
45°	472.8	427.0	399.1	376.9	370.5	364.1	357.6	353.3	351.9	349.0	351.2
47.5°	410.5	374.1	356.9	340.4	333.3	331.9	326.1	324.0	321.1	320.4	321.1
50°	358.3	335.4	319.7	310.4	305.4	303.3	300.4	296.1	294.7	298.3	296.8
52.5°	321.9	300.4	291.8	282.5	279.7	276.8	272.5	273.2	272.5	271.1	271.1
55°	285.4	271.8	263.2	256.1	255.3	252.5	248.9	247.5	246.8	245.3	247.5
57.5°	256.1	245.3	237.5	231.0	228.2	228.2	224.6	221.7	221.7	221.0	221.7
60°	226.7	216.0	211.0	204.6	202.4	201.7	199.5	198.1	196.0	196.0	196.0
62.5°	199.5	191.0	185.2	179.5	180.2	176.7	173.8	172.4	172.4	173.1	173.1
65°	173.8	168.1	160.9	155.9	154.5	153.8	152.3	151.6	149.5	150.9	150.9
67.5°	150.2	142.3	138.0	135.9	133.7	133.0	131.6	130.2	129.5	128.7	130.2
70°	126.6	120.2	116.6	115.2	113.0	112.3	111.6	109.4	110.1	110.9	111.6
72.5°	105.1	99.4	98.7	94.4	94.4	94.4	91.5	93.0	92.3	90.8	92.3
75°	83.0	80.1	78.7	76.5	77.2	76.5	75.8	73.7	73.7	74.4	75.1
77.5°	65.8	62.9	62.2	60.1	58.6	60.1	58.6	57.9	57.9	58.6	58.6
80°	48.6	47.2	45.1	45.1	45.1	44.3	44.3	44.3	43.6	42.9	43.6
82.5°	32.2	32.2	31.5	30.8	31.5	30.0	30.8	30.8	30.8	30.8	30.8
85°	20.7	20.0	20.0	19.3	19.3	19.3	20.0	18.6	18.6	19.3	19.3
87.5°	9.3	9.3	9.3	10.0	9.3	9.3	9.3	10.0	9.3	9.3	9.3
90°	32.9	32.5	32.0	31.6	31.4	31.5	31.7	31.9	32.1	32.3	32.1
92.5°	29.7	29.9	30.1	30.3	30.4	30.4	30.4	30.4	30.4	30.4	30.4
95°	60.8	60.8	60.8	60.8	60.8	60.6	60.2	59.7	59.3	58.9	59.3
97.5°	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0
100°	131.1	131.1	131.1	131.1	131.1	131.0	130.8	130.6	130.4	130.2	130.4
102.5°	170.3	170.5	170.7	170.9	171.0	170.9	170.7	170.5	170.3	170.1	170.3
105°	209.4	209.8	210.3	210.7	210.9	210.9	210.9	210.9	210.9	210.9	210.9
107.5°	252.0	252.2	252.4	252.6	252.7	252.2	251.1	250.1	249.0	248.0	249.0
110°	295.5	295.5	295.5	295.5	295.5	295.2	294.5	293.9	293.2	292.6	293.2

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	339.5	338.9	338.2	337.6	337.3	337.1	336.7	336.2	335.8	335.4	335.8
115°	383.7	383.5	383.2	383.0	382.9	382.6	381.9	381.3	380.6	380.0	380.6
117.5°	427.0	426.3	425.7	425.0	424.7	424.4	423.8	423.1	422.5	421.9	422.5
120°	469.4	469.4	469.4	469.4	469.4	469.1	468.4	467.8	467.1	466.5	467.1
122.5°	514.4	513.7	513.1	512.4	512.1	511.9	511.5	511.0	510.6	510.2	510.6
125°	558.1	557.4	556.8	556.1	555.8	555.7	555.5	555.3	555.1	554.9	555.1
127.5°	600.6	599.7	598.9	598.0	597.6	597.3	596.7	596.0	595.4	594.8	595.4
130°	643.8	643.4	642.9	642.5	642.3	641.9	641.0	640.2	639.3	638.5	639.3
132.5°	686.8	685.8	684.7	683.6	683.1	682.8	682.2	681.5	680.9	680.3	680.9
135°	727.6	727.4	727.1	726.9	726.8	726.5	725.9	725.2	724.6	724.0	724.6
137.5°	767.5	767.3	767.1	766.9	766.8	766.4	765.5	764.6	763.8	762.9	763.8
140°	807.6	807.6	807.6	807.6	807.6	807.2	806.3	805.5	804.6	803.8	804.6
142.5°	843.9	844.1	844.4	844.6	844.7	844.3	843.4	842.6	841.7	840.9	841.7
145°	881.0	881.2	881.4	881.6	881.7	881.3	880.4	879.6	878.7	877.9	878.7
147.5°	913.5	913.9	914.4	914.8	915.0	914.6	913.7	912.9	912.0	911.2	912.0
150°	944.1	944.7	945.4	946.0	946.3	946.0	945.4	944.7	944.1	943.5	944.1
152.5°	974.7	975.6	976.4	977.3	977.7	977.3	976.4	975.6	974.7	973.9	974.7
155°	999.6	1000.7	1001.7	1002.8	1003.3	1003.0	1002.4	1001.7	1001.1	1000.5	1001.1
157.5°	1023.8	1025.3	1026.8	1028.3	1029.0	1028.5	1027.4	1026.3	1025.3	1024.2	1025.3
160°	1045.5	1046.7	1048.0	1049.3	1049.9	1049.5	1048.6	1047.8	1046.9	1046.1	1046.9
162.5°	1064.7	1066.1	1067.6	1069.1	1069.8	1069.3	1068.2	1067.2	1066.1	1065.1	1066.1
165°	1080.8	1082.3	1083.8	1085.3	1086.0	1085.5	1084.4	1083.3	1082.3	1081.2	1082.3
167.5°	1095.1	1096.5	1098.0	1099.5	1100.2	1099.7	1098.6	1097.6	1096.5	1095.5	1096.5
170°	1106.5	1107.9	1109.4	1110.9	1111.6	1111.0	1109.7	1108.4	1107.2	1105.9	1107.2
172.5°	1115.0	1116.5	1118.0	1119.5	1120.2	1119.6	1118.3	1117.0	1115.8	1114.5	1115.8
175°	1120.7	1122.2	1123.7	1125.2	1125.9	1125.3	1124.0	1122.7	1121.5	1120.2	1121.5
177.5°	1124.3	1125.5	1126.8	1128.1	1128.7	1128.1	1126.8	1125.5	1124.3	1123.0	1124.3
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	986.3	981.3	977.0	977.7	981.3	978.4	971.3	962.0	958.4	954.1	958.4
5°	1045.7	1041.4	1032.8	1033.5	1031.4	1028.5	1017.1	1002.8	1002.8	991.3	989.9
7.5°	1104.3	1097.9	1092.2	1090.7	1082.9	1077.1	1067.1	1047.1	1039.2	1025.6	1017.8
10°	1170.1	1165.1	1158.7	1150.8	1146.5	1136.5	1120.1	1090.7	1076.4	1057.8	1044.2
12.5°	1236.6	1235.9	1221.6	1205.9	1205.2	1189.4	1178.0	1138.6	1119.3	1094.3	1062.1
15°	1278.8	1275.3	1267.4	1259.5	1261.7	1244.5	1218.8	1172.3	1159.4	1129.3	1095.0
17.5°	1278.1	1278.1	1276.0	1274.5	1272.4	1267.4	1253.1	1222.3	1201.6	1163.7	1131.5
20°	1237.3	1246.6	1248.8	1248.1	1255.2	1258.8	1258.1	1238.8	1222.3	1188.7	1155.8
22.5°	1155.8	1177.3	1186.6	1192.3	1207.3	1215.2	1233.8	1226.6	1222.3	1197.3	1169.4
25°	1080.0	1087.2	1115.0	1116.5	1137.2	1156.5	1175.1	1187.3	1203.0	1193.7	1170.1
27.5°	982.0	998.5	1018.5	1033.5	1037.8	1077.1	1107.9	1130.8	1166.5	1169.4	1161.5
30°	871.2	879.0	911.9	931.9	954.8	983.4	1027.8	1067.1	1099.3	1128.6	1138.6
32.5°	736.0	768.2	787.5	811.8	831.8	882.6	937.0	987.7	1024.9	1074.3	1095.7
35°	612.2	637.3	670.2	680.2	716.7	759.6	830.4	895.5	952.0	1002.0	1045.7
37.5°	510.0	530.0	565.0	580.8	602.2	657.3	716.7	797.5	865.4	926.9	981.3
40°	439.9	454.9	481.4	486.4	504.2	554.3	602.2	678.0	768.2	851.1	910.5
42.5°	391.9	399.1	417.0	423.4	434.9	468.5	511.4	582.9	666.6	752.4	836.1
45°	357.6	362.6	373.4	379.1	393.4	408.4	443.4	500.7	566.5	653.0	743.1
47.5°	326.9	333.3	337.6	341.2	349.0	365.5	388.4	430.6	493.5	572.9	660.2
50°	301.1	303.3	311.1	311.8	316.8	327.6	349.0	374.8	424.8	489.2	573.6
52.5°	275.4	277.5	282.5	287.5	289.7	298.3	312.6	334.0	371.2	422.0	497.1
55°	249.6	252.5	257.5	261.1	263.2	270.4	278.9	299.7	329.0	364.8	426.3
57.5°	223.9	230.3	231.7	233.9	237.5	245.3	253.2	265.4	288.2	321.1	366.2
60°	199.5	201.7	206.7	208.8	212.4	216.7	226.7	236.0	252.5	278.2	319.0
62.5°	174.5	179.5	181.7	183.8	186.7	191.7	198.1	208.1	222.4	243.2	275.4
65°	153.1	153.8	158.1	160.9	163.8	167.4	173.8	183.1	191.7	211.0	234.6
67.5°	132.3	133.7	135.2	138.0	141.6	145.2	150.9	155.9	166.6	179.5	198.1
70°	112.3	112.3	115.9	118.0	117.3	121.6	125.9	131.6	139.5	151.6	166.6
72.5°	94.4	93.7	96.6	97.3	98.7	101.6	104.4	110.1	114.4	123.7	135.2
75°	75.1	76.5	78.0	78.0	80.1	82.3	85.1	88.0	93.0	98.7	107.3
77.5°	59.4	59.4	60.8	61.5	63.7	62.9	65.8	68.7	72.2	77.2	83.7
80°	43.6	45.1	45.1	45.1	45.8	46.5	49.4	51.5	53.6	57.2	60.1
82.5°	30.8	30.8	32.2	32.2	32.2	33.6	33.6	34.3	35.8	37.9	40.1
85°	19.3	19.3	19.3	20.0	19.3	20.0	21.5	20.7	21.5	22.9	22.9
87.5°	9.3	9.3	9.3	9.3	9.3	10.0	9.3	10.0	10.7	10.7	10.7
90°	31.9	31.7	31.5	31.4	31.6	32.0	32.5	32.9	33.3	28.7	24.0
92.5°	30.4	30.4	30.4	30.4	30.3	30.1	29.9	29.7	29.5	29.3	29.1
95°	59.7	60.2	60.6	60.8	60.8	60.8	60.8	60.8	60.8	60.4	60.0
97.5°	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	94.2	93.3
100°	130.6	130.8	131.0	131.1	131.1	131.1	131.1	131.1	131.1	130.5	129.9
102.5°	170.5	170.7	170.9	171.0	170.9	170.7	170.5	170.3	170.1	169.3	168.4
105°	210.9	210.9	210.9	210.9	210.7	210.3	209.8	209.4	209.0	208.6	208.2
107.5°	250.1	251.1	252.2	252.7	252.6	252.4	252.2	252.0	251.8	251.8	251.8
110°	293.9	294.5	295.2	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	336.2	336.7	337.1	337.3	337.6	338.2	338.9	339.5	340.1	340.3	340.5
115°	381.3	381.9	382.6	382.9	383.0	383.2	383.5	383.7	383.9	384.3	384.7
117.5°	423.1	423.8	424.4	424.7	425.0	425.7	426.3	427.0	427.6	428.6	429.7
120°	467.8	468.4	469.1	469.4	469.4	469.4	469.4	469.4	469.4	471.1	472.8
122.5°	511.0	511.5	511.9	512.1	512.4	513.1	513.7	514.4	515.0	516.0	517.1
125°	555.3	555.5	555.7	555.8	556.1	556.8	557.4	558.1	558.7	559.3	559.9
127.5°	596.0	596.7	597.3	597.6	598.0	598.9	599.7	600.6	601.4	602.2	603.1
130°	640.2	641.0	641.9	642.3	642.5	642.9	643.4	643.8	644.2	644.6	645.0
132.5°	681.5	682.2	682.8	683.1	683.6	684.7	685.8	686.8	687.9	687.7	687.5
135°	725.2	725.9	726.5	726.8	726.9	727.1	727.4	727.6	727.8	727.4	727.0
137.5°	764.6	765.5	766.4	766.8	766.9	767.1	767.3	767.5	767.7	767.3	766.9
140°	805.5	806.3	807.2	807.6	807.6	807.6	807.6	807.6	807.6	806.6	805.5
142.5°	842.6	843.4	844.3	844.7	844.6	844.4	844.1	843.9	843.7	843.1	842.5
145°	879.6	880.4	881.3	881.7	881.6	881.4	881.2	881.0	880.8	879.5	878.3
147.5°	912.9	913.7	914.6	915.0	914.8	914.4	913.9	913.5	913.1	912.3	911.4
150°	944.7	945.4	946.0	946.3	946.0	945.4	944.7	944.1	943.5	942.7	941.8
152.5°	975.6	976.4	977.3	977.7	977.3	976.4	975.6	974.7	973.9	972.8	971.8
155°	1001.7	1002.4	1003.0	1003.3	1002.8	1001.7	1000.7	999.6	998.6	998.0	997.3
157.5°	1026.3	1027.4	1028.5	1029.0	1028.3	1026.8	1025.3	1023.8	1022.3	1021.9	1021.5
160°	1047.8	1048.6	1049.5	1049.9	1049.3	1048.0	1046.7	1045.5	1044.2	1044.0	1043.8
162.5°	1067.2	1068.2	1069.3	1069.8	1069.1	1067.6	1066.1	1064.7	1063.2	1063.0	1062.8
165°	1083.3	1084.4	1085.5	1086.0	1085.3	1083.8	1082.3	1080.8	1079.3	1079.3	1079.3
167.5°	1097.6	1098.6	1099.7	1100.2	1099.5	1098.0	1096.5	1095.1	1093.6	1093.6	1093.6
170°	1108.4	1109.7	1111.0	1111.6	1110.9	1109.4	1107.9	1106.5	1105.0	1105.2	1105.4
172.5°	1117.0	1118.3	1119.6	1120.2	1119.5	1118.0	1116.5	1115.0	1113.5	1113.7	1113.9
175°	1122.7	1124.0	1125.3	1125.9	1125.2	1123.7	1122.2	1120.7	1119.2	1119.6	1120.0
177.5°	1125.5	1126.8	1128.1	1128.7	1128.1	1126.8	1125.5	1124.3	1123.0	1123.4	1123.8
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	954.8	951.3	949.1	950.5	946.3	935.5	935.5	939.1	934.8	930.5	924.1
5°	981.3	974.1	969.9	969.1	959.1	942.0	938.4	934.8	925.5	915.5	904.8
7.5°	1007.0	994.2	987.0	982.0	967.7	945.5	936.2	928.4	913.3	898.3	884.7
10°	1028.5	1009.9	1001.3	993.5	974.9	947.0	931.9	917.6	898.3	879.0	861.9
12.5°	1045.7	1024.2	1013.5	1002.0	979.2	942.7	924.1	901.2	881.9	856.1	839.0
15°	1074.3	1029.9	1019.9	1009.2	985.6	935.5	912.6	886.9	860.4	826.1	807.5
17.5°	1097.2	1037.8	1037.1	1014.2	983.4	932.7	897.6	864.0	835.4	801.1	771.7
20°	1110.8	1050.0	1038.5	1014.9	976.3	913.3	876.9	839.7	808.9	767.4	738.1
22.5°	1122.2	1067.1	1037.1	1008.5	961.3	906.9	853.3	818.2	776.0	731.0	703.1
25°	1126.5	1070.7	1039.2	1006.3	950.5	888.3	827.5	789.6	742.4	701.6	663.7
27.5°	1127.2	1070.0	1031.4	997.0	935.5	864.0	801.8	761.7	709.5	662.3	624.4
30°	1120.1	1062.1	1027.1	989.9	921.2	841.8	770.3	726.0	670.2	623.0	583.6
32.5°	1098.6	1046.4	1017.8	977.0	902.6	811.1	740.3	690.9	632.3	585.8	547.9
35°	1062.8	1027.1	995.6	957.7	878.3	782.5	710.2	652.3	592.9	548.6	512.8
37.5°	1018.5	999.2	969.9	932.7	850.4	756.7	676.6	612.2	552.9	510.0	474.9
40°	958.4	963.4	934.8	901.2	817.5	721.7	633.0	571.5	515.7	475.6	441.3
42.5°	893.3	914.1	897.6	865.4	781.0	683.0	600.8	532.8	478.5	437.0	408.4
45°	823.2	859.0	849.0	825.4	743.1	642.3	555.0	489.2	441.3	401.2	376.2
47.5°	746.7	797.5	797.5	780.3	700.9	601.5	515.7	448.4	401.2	372.6	348.3
50°	668.7	726.0	735.3	723.8	653.7	555.0	467.8	407.0	366.2	338.3	320.4
52.5°	587.2	653.7	670.9	665.2	603.7	510.7	428.4	369.1	331.9	307.5	291.8
55°	509.2	586.5	605.1	607.2	550.0	462.0	384.8	332.6	296.8	280.4	266.8
57.5°	435.6	510.0	530.7	534.3	495.7	417.7	344.0	298.3	266.1	252.5	241.7
60°	372.6	434.9	462.0	469.9	436.3	366.2	306.1	261.8	237.5	224.6	214.6
62.5°	321.1	371.2	399.8	402.0	386.9	321.1	266.8	229.6	208.8	197.4	192.4
65°	271.1	316.1	333.3	341.9	329.7	278.2	230.3	199.5	183.1	173.1	168.1
67.5°	231.0	259.6	273.9	285.4	273.2	234.6	196.0	170.9	158.8	148.8	145.9
70°	189.5	213.1	223.9	235.3	224.6	195.3	167.4	144.5	133.7	125.9	122.3
72.5°	151.6	170.2	180.2	187.4	181.0	156.6	133.7	118.0	110.1	104.4	102.3
75°	120.2	133.0	138.8	143.8	140.9	122.3	108.0	95.1	88.0	83.0	81.5
77.5°	91.5	100.8	107.3	108.7	105.1	93.0	80.8	73.0	67.2	64.4	62.9
80°	65.1	70.8	74.4	76.5	73.0	67.9	59.4	53.6	48.6	45.1	44.3
82.5°	43.6	46.5	49.4	48.6	47.2	42.9	37.9	35.0	32.9	30.0	30.0
85°	25.0	25.7	27.2	27.9	27.2	24.3	21.5	20.0	18.6	16.5	16.5
87.5°	10.7	11.4	11.4	12.2	10.7	10.7	9.3	7.9	7.9	7.2	6.4
90°	19.4	14.7	12.4	11.1	8.6	6.1	3.5	1.0	3.5	6.1	8.6
92.5°	28.8	28.6	28.5	27.7	26.0	24.3	22.6	20.9	22.6	24.3	26.0
95°	59.5	59.1	58.9	57.8	55.7	53.6	51.5	49.4	51.5	53.6	55.7
97.5°	92.5	91.6	91.2	90.3	88.4	86.5	84.6	82.7	84.6	86.5	88.4
100°	129.2	128.6	128.3	127.5	125.8	124.1	122.4	120.7	122.4	124.1	125.8
102.5°	167.6	166.7	166.3	165.7	164.4	163.1	161.9	160.6	161.9	163.1	164.4
105°	207.7	207.3	207.1	206.8	206.2	205.5	204.9	204.3	204.9	205.5	206.2
107.5°	251.8	251.8	251.8	251.4	250.5	249.7	248.8	248.0	248.8	249.7	250.5
110°	295.5	295.5	295.5	294.9	293.6	292.3	291.1	289.8	291.1	292.3	293.6

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	340.8	341.0	341.1	340.5	339.2	337.9	336.7	335.4	336.7	337.9	339.2
115°	385.2	385.6	385.8	385.2	383.9	382.6	381.3	380.0	381.3	382.6	383.9
117.5°	430.7	431.8	432.3	431.5	429.8	428.1	426.4	424.7	426.4	428.1	429.8
120°	474.5	476.2	477.0	476.2	474.5	472.8	471.1	469.4	471.1	472.8	474.5
122.5°	518.1	519.2	519.7	518.6	516.5	514.4	512.3	510.2	512.3	514.4	516.5
125°	560.6	561.2	561.5	560.6	558.7	556.8	554.9	553.0	554.9	556.8	558.7
127.5°	603.9	604.8	605.2	604.0	601.7	599.4	597.1	594.8	597.1	599.4	601.7
130°	645.5	645.9	646.1	644.7	642.0	639.2	636.5	633.7	636.5	639.2	642.0
132.5°	687.2	687.0	686.9	685.8	683.7	681.6	679.5	677.4	679.5	681.6	683.7
135°	726.5	726.1	725.9	724.7	722.4	720.1	717.7	715.4	717.7	720.1	722.4
137.5°	766.4	766.0	765.8	764.8	762.9	761.0	759.1	757.2	759.1	761.0	762.9
140°	804.5	803.4	802.9	801.9	800.0	798.1	796.2	794.3	796.2	798.1	800.0
142.5°	841.8	841.2	840.9	839.9	838.0	836.1	834.2	832.3	834.2	836.1	838.0
145°	877.0	875.7	875.1	874.4	872.9	871.4	869.9	868.4	869.9	871.4	872.9
147.5°	910.6	909.7	909.3	908.3	906.4	904.5	902.6	900.7	902.6	904.5	906.4
150°	941.0	940.1	939.7	939.1	937.8	936.5	935.3	934.0	935.3	936.5	937.8
152.5°	970.7	969.6	969.1	968.5	967.2	965.9	964.7	963.4	964.7	965.9	967.2
155°	996.7	996.0	995.7	995.4	994.8	994.1	993.5	992.9	993.5	994.1	994.8
157.5°	1021.0	1020.6	1020.4	1020.2	1019.8	1019.3	1018.9	1018.5	1018.9	1019.3	1019.8
160°	1043.5	1043.3	1043.2	1043.0	1042.6	1042.1	1041.7	1041.3	1041.7	1042.1	1042.6
162.5°	1062.5	1062.3	1062.2	1062.2	1062.2	1062.2	1062.2	1062.2	1062.2	1062.2	1062.2
165°	1079.3	1079.3	1079.3	1079.4	1079.6	1079.9	1080.1	1080.3	1080.1	1079.9	1079.6
167.5°	1093.6	1093.6	1093.6	1093.9	1094.5	1095.2	1095.8	1096.4	1095.8	1095.2	1094.5
170°	1105.6	1105.8	1105.9	1106.2	1106.9	1107.5	1108.2	1108.8	1108.2	1107.5	1106.9
172.5°	1114.2	1114.4	1114.5	1114.8	1115.4	1116.1	1116.7	1117.3	1116.7	1116.1	1115.4
175°	1120.5	1120.9	1121.1	1121.4	1122.1	1122.7	1123.4	1124.0	1123.4	1122.7	1122.1
177.5°	1124.3	1124.7	1124.9	1125.2	1125.9	1126.5	1127.2	1127.8	1127.2	1126.5	1125.9
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	920.5	924.1	923.4	916.2	908.3	901.9	889.7	891.2	886.9	887.6	891.9
5°	897.6	897.6	894.8	884.7	871.9	864.7	851.1	847.5	839.0	838.3	837.5
7.5°	873.3	869.7	866.1	851.8	836.1	824.7	806.1	801.8	793.2	787.5	784.6
10°	844.7	839.7	832.5	816.1	796.8	782.5	763.2	757.4	741.0	733.8	729.5
12.5°	813.2	810.4	798.9	785.3	753.9	738.1	710.2	715.9	699.5	685.2	683.0
15°	781.7	771.0	764.6	742.4	704.5	697.3	675.2	663.7	648.7	637.3	637.3
17.5°	751.0	734.5	720.2	696.6	668.7	648.7	632.3	626.5	607.9	596.5	594.4
20°	710.2	691.6	688.1	654.4	635.1	613.0	597.2	582.9	569.3	564.3	560.7
22.5°	671.6	650.1	644.4	615.8	596.5	574.3	558.6	548.6	538.6	535.0	528.6
25°	630.1	617.2	608.7	577.9	556.4	535.7	525.0	517.8	508.5	507.8	503.5
27.5°	590.1	577.9	569.3	540.0	524.3	505.0	496.4	488.5	483.5	481.4	479.2
30°	555.7	542.1	532.1	510.7	491.4	475.6	468.5	463.5	460.6	457.0	456.3
32.5°	517.8	510.0	496.4	479.9	464.9	449.9	445.6	442.0	437.7	436.3	435.6
35°	485.6	474.9	466.3	447.7	441.3	428.4	423.4	420.6	414.8	413.4	412.0
37.5°	454.2	444.2	434.9	423.4	411.3	404.1	401.2	397.0	394.1	394.8	393.4
40°	422.7	414.8	407.7	395.5	388.4	384.8	379.1	374.8	373.4	374.1	373.4
42.5°	391.9	384.8	380.5	371.2	364.1	360.5	356.9	352.6	354.8	354.8	356.9
45°	364.1	357.6	354.8	347.6	343.3	337.6	334.0	333.3	336.2	335.4	335.4
47.5°	335.4	333.3	329.7	323.3	317.6	314.0	313.3	313.3	316.1	317.6	316.8
50°	313.3	309.0	304.7	299.7	295.4	294.0	291.8	293.2	296.1	296.1	297.5
52.5°	285.4	282.5	281.1	276.8	273.9	273.9	273.9	274.6	276.8	278.9	278.2
55°	261.1	258.9	257.5	255.3	251.8	252.5	251.8	253.2	255.3	257.5	258.9
57.5°	235.3	234.6	233.2	229.6	229.6	228.9	231.0	231.7	235.3	236.7	238.9
60°	212.4	210.3	210.3	207.4	207.4	207.4	209.6	211.7	214.6	215.3	216.7
62.5°	188.1	188.1	187.4	185.2	185.2	187.4	188.1	191.0	192.4	192.4	194.5
65°	165.2	164.5	163.8	164.5	165.2	165.2	167.4	168.8	170.2	170.9	171.7
67.5°	142.3	141.6	143.0	142.3	143.8	146.6	145.9	148.1	150.2	150.2	150.9
70°	120.9	122.3	121.6	123.0	122.3	123.7	125.9	126.6	126.6	127.3	129.5
72.5°	100.8	100.8	100.8	100.1	100.8	102.3	103.7	104.4	105.9	106.6	108.7
75°	81.5	81.5	80.1	81.5	81.5	83.0	84.4	84.4	84.4	85.8	88.0
77.5°	61.5	62.2	61.5	62.9	62.9	63.7	65.1	64.4	65.8	66.5	67.2
80°	45.1	44.3	44.3	44.3	45.1	45.1	46.5	47.2	47.2	49.4	47.9
82.5°	28.6	29.3	28.6	29.3	29.3	30.0	29.3	30.0	30.8	32.2	31.5
85°	16.5	15.7	15.7	16.5	15.7	15.7	16.5	15.7	16.5	15.7	16.5
87.5°	6.4	5.7	5.7	5.7	5.7	5.0	5.0	4.3	4.3	4.3	3.6
90°	11.1	12.4	14.7	19.4	24.0	28.7	33.3	32.9	32.5	32.0	31.6
92.5°	27.7	28.5	28.6	28.8	29.1	29.3	29.5	29.7	29.9	30.1	30.3
95°	57.8	58.9	59.1	59.5	60.0	60.4	60.8	60.8	60.8	60.8	60.8
97.5°	90.3	91.2	91.6	92.5	93.3	94.2	95.0	95.0	95.0	95.0	95.0
100°	127.5	128.3	128.6	129.2	129.9	130.5	131.1	131.1	131.1	131.1	131.1
102.5°	165.7	166.3	166.7	167.6	168.4	169.3	170.1	170.3	170.5	170.7	170.9
105°	206.8	207.1	207.3	207.7	208.2	208.6	209.0	209.4	209.8	210.3	210.7
107.5°	251.4	251.8	251.8	251.8	251.8	251.8	251.8	252.0	252.2	252.4	252.6
110°	294.9	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	340.5	341.1	341.0	340.8	340.5	340.3	340.1	339.5	338.9	338.2	337.6
115°	385.2	385.8	385.6	385.2	384.7	384.3	383.9	383.7	383.5	383.2	383.0
117.5°	431.5	432.3	431.8	430.7	429.7	428.6	427.6	427.0	426.3	425.7	425.0
120°	476.2	477.0	476.2	474.5	472.8	471.1	469.4	469.4	469.4	469.4	469.4
122.5°	518.6	519.7	519.2	518.1	517.1	516.0	515.0	514.4	513.7	513.1	512.4
125°	560.6	561.5	561.2	560.6	559.9	559.3	558.7	558.1	557.4	556.8	556.1
127.5°	604.0	605.2	604.8	603.9	603.1	602.2	601.4	600.6	599.7	598.9	598.0
130°	644.7	646.1	645.9	645.5	645.0	644.6	644.2	643.8	643.4	642.9	642.5
132.5°	685.8	686.9	687.0	687.2	687.5	687.7	687.9	686.8	685.8	684.7	683.6
135°	724.7	725.9	726.1	726.5	727.0	727.4	727.8	727.6	727.4	727.1	726.9
137.5°	764.8	765.8	766.0	766.4	766.9	767.3	767.7	767.5	767.3	767.1	766.9
140°	801.9	802.9	803.4	804.5	805.5	806.6	807.6	807.6	807.6	807.6	807.6
142.5°	839.9	840.9	841.2	841.8	842.5	843.1	843.7	843.9	844.1	844.4	844.6
145°	874.4	875.1	875.7	877.0	878.3	879.5	880.8	881.0	881.2	881.4	881.6
147.5°	908.3	909.3	909.7	910.6	911.4	912.3	913.1	913.5	913.9	914.4	914.8
150°	939.1	939.7	940.1	941.0	941.8	942.7	943.5	944.1	944.7	945.4	946.0
152.5°	968.5	969.1	969.6	970.7	971.8	972.8	973.9	974.7	975.6	976.4	977.3
155°	995.4	995.7	996.0	996.7	997.3	998.0	998.6	999.6	1000.7	1001.7	1002.8
157.5°	1020.2	1020.4	1020.6	1021.0	1021.5	1021.9	1022.3	1023.8	1025.3	1026.8	1028.3
160°	1043.0	1043.2	1043.3	1043.5	1043.8	1044.0	1044.2	1045.5	1046.7	1048.0	1049.3
162.5°	1062.2	1062.2	1062.3	1062.5	1062.8	1063.0	1063.2	1064.7	1066.1	1067.6	1069.1
165°	1079.4	1079.3	1079.3	1079.3	1079.3	1079.3	1079.3	1080.8	1082.3	1083.8	1085.3
167.5°	1093.9	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1095.1	1096.5	1098.0	1099.5
170°	1106.2	1105.9	1105.8	1105.6	1105.4	1105.2	1105.0	1106.5	1107.9	1109.4	1110.9
172.5°	1114.8	1114.5	1114.4	1114.2	1113.9	1113.7	1113.5	1115.0	1116.5	1118.0	1119.5
175°	1121.4	1121.1	1120.9	1120.5	1120.0	1119.6	1119.2	1120.7	1122.2	1123.7	1125.2
177.5°	1125.2	1124.9	1124.7	1124.3	1123.8	1123.4	1123.0	1124.3	1125.5	1126.8	1128.1
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	886.9	889.0	884.0	882.6	884.0	879.0	880.4	881.9	881.9	884.0	885.5
5°	835.4	832.5	827.5	826.1	824.7	826.8	825.4	827.5	828.2	833.2	834.0
7.5°	784.6	780.3	776.0	771.7	770.3	766.7	770.3	770.3	775.3	773.9	777.5
10°	724.5	723.8	718.1	715.9	713.1	707.4	715.2	713.1	716.7	723.1	724.5
12.5°	680.2	672.3	675.9	665.9	669.5	663.7	664.4	664.4	670.2	670.9	669.5
15°	638.0	631.5	622.3	618.0	615.8	613.0	622.3	623.0	618.7	628.7	625.1
17.5°	595.1	595.1	586.5	584.3	578.6	581.5	580.1	580.8	579.3	586.5	590.1
20°	557.9	554.3	551.4	552.2	545.0	543.6	542.1	543.6	548.6	553.6	555.0
22.5°	527.8	525.7	518.5	520.0	514.3	516.4	515.0	518.5	519.3	519.3	524.3
25°	499.2	496.4	497.1	494.2	492.1	492.1	489.9	492.1	494.9	496.4	497.1
27.5°	477.8	475.6	472.1	469.9	471.3	467.8	470.6	472.8	472.8	471.3	472.8
30°	452.0	453.5	453.5	446.3	449.2	447.7	449.9	451.3	451.3	452.0	450.6
32.5°	434.9	430.6	429.9	429.1	429.1	426.3	426.3	428.4	429.1	429.9	432.0
35°	412.0	412.0	408.4	410.5	407.7	408.4	407.7	408.4	409.8	407.7	409.8
37.5°	391.2	391.9	390.5	391.9	392.7	391.2	389.8	392.7	391.2	391.2	389.8
40°	373.4	372.6	373.4	373.4	373.4	374.1	372.6	372.6	372.6	371.2	369.8
42.5°	358.3	354.0	355.5	356.2	354.0	354.0	354.8	354.0	356.2	351.9	351.9
45°	336.9	335.4	336.2	336.2	337.6	335.4	336.9	337.6	335.4	334.7	333.3
47.5°	317.6	319.0	317.6	319.0	319.0	320.4	317.6	318.3	319.0	316.1	314.0
50°	298.3	298.3	300.4	299.7	300.4	299.0	299.0	298.3	299.0	297.5	295.4
52.5°	280.4	278.2	281.8	281.1	280.4	279.7	278.9	279.7	278.2	276.8	276.8
55°	258.2	258.2	260.3	261.1	261.1	259.6	258.2	258.9	258.2	257.5	256.8
57.5°	240.3	237.5	238.9	239.6	239.6	237.5	238.9	237.5	237.5	238.2	236.0
60°	217.4	217.4	216.0	218.1	218.1	216.7	216.7	217.4	216.0	215.3	214.6
62.5°	193.1	193.8	196.0	196.7	197.4	196.0	194.5	195.3	195.3	193.1	193.8
65°	172.4	173.8	176.7	175.9	174.5	175.2	173.8	174.5	172.4	173.1	170.9
67.5°	152.3	151.6	152.3	152.3	153.8	153.1	151.6	151.6	150.9	153.1	150.9
70°	130.9	130.9	130.9	130.9	131.6	132.3	130.9	129.5	130.2	128.7	128.0
72.5°	108.7	109.4	108.7	110.1	108.0	109.4	109.4	108.7	108.0	108.0	108.0
75°	88.0	89.4	87.3	88.0	87.3	88.7	88.0	88.0	86.5	85.8	86.5
77.5°	67.2	67.9	66.5	67.2	66.5	67.2	67.2	66.5	66.5	66.5	66.5
80°	47.9	48.6	47.9	47.2	46.5	47.9	46.5	47.2	47.9	47.2	48.6
82.5°	30.8	30.8	30.0	30.8	29.3	29.3	30.0	30.0	29.3	30.8	29.3
85°	15.0	15.0	16.5	15.0	14.3	14.3	14.3	15.0	14.3	15.7	15.0
87.5°	3.6	2.9	3.6	3.6	2.9	2.9	3.6	2.9	3.6	4.3	2.9
90°	31.4	31.5	31.7	31.9	32.1	32.3	32.1	31.9	31.7	31.5	31.4
92.5°	30.4	30.4	30.4	30.4	30.4	30.4	30.4	30.4	30.4	30.4	30.4
95°	60.8	60.6	60.2	59.7	59.3	58.9	59.3	59.7	60.2	60.6	60.8
97.5°	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0
100°	131.1	131.0	130.8	130.6	130.4	130.2	130.4	130.6	130.8	131.0	131.1
102.5°	171.0	170.9	170.7	170.5	170.3	170.1	170.3	170.5	170.7	170.9	171.0
105°	210.9	210.9	210.9	210.9	210.9	210.9	210.9	210.9	210.9	210.9	210.9
107.5°	252.7	252.2	251.1	250.1	249.0	248.0	249.0	250.1	251.1	252.2	252.7
110°	295.5	295.2	294.5	293.9	293.2	292.6	293.2	293.9	294.5	295.2	295.5

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	337.3	337.1	336.7	336.2	335.8	335.4	335.8	336.2	336.7	337.1	337.3
115°	382.9	382.6	381.9	381.3	380.6	380.0	380.6	381.3	381.9	382.6	382.9
117.5°	424.7	424.4	423.8	423.1	422.5	421.9	422.5	423.1	423.8	424.4	424.7
120°	469.4	469.1	468.4	467.8	467.1	466.5	467.1	467.8	468.4	469.1	469.4
122.5°	512.1	511.9	511.5	511.0	510.6	510.2	510.6	511.0	511.5	511.9	512.1
125°	555.8	555.7	555.5	555.3	555.1	554.9	555.1	555.3	555.5	555.7	555.8
127.5°	597.6	597.3	596.7	596.0	595.4	594.8	595.4	596.0	596.7	597.3	597.6
130°	642.3	641.9	641.0	640.2	639.3	638.5	639.3	640.2	641.0	641.9	642.3
132.5°	683.1	682.8	682.2	681.5	680.9	680.3	680.9	681.5	682.2	682.8	683.1
135°	726.8	726.5	725.9	725.2	724.6	724.0	724.6	725.2	725.9	726.5	726.8
137.5°	766.8	766.4	765.5	764.6	763.8	762.9	763.8	764.6	765.5	766.4	766.8
140°	807.6	807.2	806.3	805.5	804.6	803.8	804.6	805.5	806.3	807.2	807.6
142.5°	844.7	844.3	843.4	842.6	841.7	840.9	841.7	842.6	843.4	844.3	844.7
145°	881.7	881.3	880.4	879.6	878.7	877.9	878.7	879.6	880.4	881.3	881.7
147.5°	915.0	914.6	913.7	912.9	912.0	911.2	912.0	912.9	913.7	914.6	915.0
150°	946.3	946.0	945.4	944.7	944.1	943.5	944.1	944.7	945.4	946.0	946.3
152.5°	977.7	977.3	976.4	975.6	974.7	973.9	974.7	975.6	976.4	977.3	977.7
155°	1003.3	1003.0	1002.4	1001.7	1001.1	1000.5	1001.1	1001.7	1002.4	1003.0	1003.3
157.5°	1029.0	1028.5	1027.4	1026.3	1025.3	1024.2	1025.3	1026.3	1027.4	1028.5	1029.0
160°	1049.9	1049.5	1048.6	1047.8	1046.9	1046.1	1046.9	1047.8	1048.6	1049.5	1049.9
162.5°	1069.8	1069.3	1068.2	1067.2	1066.1	1065.1	1066.1	1067.2	1068.2	1069.3	1069.8
165°	1086.0	1085.5	1084.4	1083.3	1082.3	1081.2	1082.3	1083.3	1084.4	1085.5	1086.0
167.5°	1100.2	1099.7	1098.6	1097.6	1096.5	1095.5	1096.5	1097.6	1098.6	1099.7	1100.2
170°	1111.6	1111.0	1109.7	1108.4	1107.2	1105.9	1107.2	1108.4	1109.7	1111.0	1111.6
172.5°	1120.2	1119.6	1118.3	1117.0	1115.8	1114.5	1115.8	1117.0	1118.3	1119.6	1120.2
175°	1125.9	1125.3	1124.0	1122.7	1121.5	1120.2	1121.5	1122.7	1124.0	1125.3	1125.9
177.5°	1128.7	1128.1	1126.8	1125.5	1124.3	1123.0	1124.3	1125.5	1126.8	1128.1	1128.7
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	883.3	889.0	886.9	879.0	888.3	888.3	894.8	894.8	902.6	905.5	909.8
5°	833.2	837.5	841.1	837.5	844.0	854.0	859.7	864.7	875.4	879.7	886.2
7.5°	779.6	787.5	791.0	791.0	801.8	813.2	824.7	831.8	846.8	852.6	859.0
10°	727.4	736.7	743.8	743.1	761.0	768.2	782.5	798.9	813.9	822.5	831.8
12.5°	672.3	677.3	687.3	701.6	705.9	718.8	735.3	756.0	783.2	791.0	804.6
15°	626.5	640.1	648.0	654.4	664.4	676.6	694.5	714.5	741.7	758.9	773.2
17.5°	587.9	605.8	610.8	609.4	622.3	640.8	661.6	676.6	700.9	721.7	735.3
20°	556.4	563.6	572.2	575.8	585.8	605.8	625.8	643.0	663.0	679.5	695.2
22.5°	525.0	530.7	537.9	544.3	552.2	563.6	582.9	604.4	623.7	639.4	657.3
25°	499.2	502.8	509.2	514.3	522.8	530.7	544.3	567.9	590.8	600.1	615.8
27.5°	474.2	477.1	481.4	487.1	491.4	499.2	511.4	530.7	554.3	563.6	585.1
30°	452.0	454.2	458.5	461.3	463.5	472.8	482.1	497.1	515.0	527.8	543.6
32.5°	431.3	433.4	437.7	438.4	441.3	446.3	454.9	468.5	484.2	494.9	508.5
35°	408.4	409.8	414.1	415.5	417.7	422.0	428.4	438.4	452.7	460.6	472.8
37.5°	390.5	389.8	392.7	394.8	397.7	399.8	402.0	412.0	422.7	429.9	439.2
40°	371.2	369.8	370.5	373.4	374.8	377.6	377.6	387.7	394.8	400.5	407.7
42.5°	351.9	351.2	349.7	351.2	352.6	353.3	354.0	361.2	368.3	373.4	381.2
45°	332.6	331.9	330.4	331.2	331.2	332.6	334.7	337.6	342.6	346.9	351.2
47.5°	314.7	313.3	311.1	310.4	311.8	311.8	311.8	314.7	319.7	321.1	325.4
50°	296.1	294.0	291.1	289.7	289.7	289.0	290.4	291.1	295.4	296.8	300.4
52.5°	276.1	274.6	271.8	268.9	269.6	268.2	268.9	269.6	271.1	273.2	275.4
55°	256.1	253.2	251.0	250.3	248.2	248.2	246.0	248.9	248.2	248.9	251.8
57.5°	236.7	233.9	230.3	228.9	226.7	226.0	224.6	223.9	224.6	226.7	228.9
60°	213.9	212.4	210.3	208.1	206.7	204.6	203.1	203.1	202.4	202.4	203.1
62.5°	191.7	191.0	188.1	187.4	186.0	184.5	182.4	181.0	181.0	182.4	183.1
65°	170.2	169.5	167.4	166.6	163.1	161.6	160.9	160.2	158.8	158.8	158.8
67.5°	150.2	148.1	148.1	144.5	141.6	140.2	138.8	138.0	138.0	138.0	138.8
70°	128.0	128.0	125.9	123.7	120.9	121.6	119.4	117.3	117.3	115.9	116.6
72.5°	106.6	105.9	103.7	103.0	100.8	98.7	97.3	98.7	96.6	95.8	96.6
75°	85.8	85.1	83.7	82.3	83.0	80.8	78.7	78.0	78.0	76.5	76.5
77.5°	65.8	67.2	64.4	63.7	62.2	60.8	60.1	59.4	59.4	59.4	60.8
80°	45.8	46.5	46.5	45.1	45.8	43.6	43.6	43.6	41.5	42.2	42.9
82.5°	29.3	29.3	28.6	29.3	28.6	28.6	27.9	27.9	27.2	27.2	27.9
85°	16.5	15.7	15.0	16.5	15.7	15.7	15.0	15.0	15.0	15.0	15.0
87.5°	3.6	4.3	4.3	4.3	4.3	5.0	5.0	5.0	5.7	5.7	5.7
90°	31.6	32.0	32.5	32.9	33.3	28.7	24.0	19.4	14.7	12.4	11.1
92.5°	30.3	30.1	29.9	29.7	29.5	29.3	29.1	28.8	28.6	28.5	27.7
95°	60.8	60.8	60.8	60.8	60.8	60.4	60.0	59.5	59.1	58.9	57.8
97.5°	95.0	95.0	95.0	95.0	95.0	94.2	93.3	92.5	91.6	91.2	90.3
100°	131.1	131.1	131.1	131.1	131.1	130.5	129.9	129.2	128.6	128.3	127.5
102.5°	170.9	170.7	170.5	170.3	170.1	169.3	168.4	167.6	166.7	166.3	165.7
105°	210.7	210.3	209.8	209.4	209.0	208.6	208.2	207.7	207.3	207.1	206.8
107.5°	252.6	252.4	252.2	252.0	251.8	251.8	251.8	251.8	251.8	251.8	251.4
110°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	294.9

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	337.6	338.2	338.9	339.5	340.1	340.3	340.5	340.8	341.0	341.1	340.5
115°	383.0	383.2	383.5	383.7	383.9	384.3	384.7	385.2	385.6	385.8	385.2
117.5°	425.0	425.7	426.3	427.0	427.6	428.6	429.7	430.7	431.8	432.3	431.5
120°	469.4	469.4	469.4	469.4	469.4	471.1	472.8	474.5	476.2	477.0	476.2
122.5°	512.4	513.1	513.7	514.4	515.0	516.0	517.1	518.1	519.2	519.7	518.6
125°	556.1	556.8	557.4	558.1	558.7	559.3	559.9	560.6	561.2	561.5	560.6
127.5°	598.0	598.9	599.7	600.6	601.4	602.2	603.1	603.9	604.8	605.2	604.0
130°	642.5	642.9	643.4	643.8	644.2	644.6	645.0	645.5	645.9	646.1	644.7
132.5°	683.6	684.7	685.8	686.8	687.9	687.7	687.5	687.2	687.0	686.9	685.8
135°	726.9	727.1	727.4	727.6	727.8	727.4	727.0	726.5	726.1	725.9	724.7
137.5°	766.9	767.1	767.3	767.5	767.7	767.3	766.9	766.4	766.0	765.8	764.8
140°	807.6	807.6	807.6	807.6	807.6	806.6	805.5	804.5	803.4	802.9	801.9
142.5°	844.6	844.4	844.1	843.9	843.7	843.1	842.5	841.8	841.2	840.9	839.9
145°	881.6	881.4	881.2	881.0	880.8	879.5	878.3	877.0	875.7	875.1	874.4
147.5°	914.8	914.4	913.9	913.5	913.1	912.3	911.4	910.6	909.7	909.3	908.3
150°	946.0	945.4	944.7	944.1	943.5	942.7	941.8	941.0	940.1	939.7	939.1
152.5°	977.3	976.4	975.6	974.7	973.9	972.8	971.8	970.7	969.6	969.1	968.5
155°	1002.8	1001.7	1000.7	999.6	998.6	998.0	997.3	996.7	996.0	995.7	995.4
157.5°	1028.3	1026.8	1025.3	1023.8	1022.3	1021.9	1021.5	1021.0	1020.6	1020.4	1020.2
160°	1049.3	1048.0	1046.7	1045.5	1044.2	1044.0	1043.8	1043.5	1043.3	1043.2	1043.0
162.5°	1069.1	1067.6	1066.1	1064.7	1063.2	1063.0	1062.8	1062.5	1062.3	1062.2	1062.2
165°	1085.3	1083.8	1082.3	1080.8	1079.3	1079.3	1079.3	1079.3	1079.3	1079.3	1079.4
167.5°	1099.5	1098.0	1096.5	1095.1	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.9
170°	1110.9	1109.4	1107.9	1106.5	1105.0	1105.2	1105.4	1105.6	1105.8	1105.9	1106.2
172.5°	1119.5	1118.0	1116.5	1115.0	1113.5	1113.7	1113.9	1114.2	1114.4	1114.5	1114.8
175°	1125.2	1123.7	1122.2	1120.7	1119.2	1119.6	1120.0	1120.5	1120.9	1121.1	1121.4
177.5°	1128.1	1126.8	1125.5	1124.3	1123.0	1123.4	1123.8	1124.3	1124.7	1124.9	1125.2
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	930.5	930.5	930.5	930.5
2.5°	913.3	913.3	924.1	935.5
5°	893.3	898.3	915.5	931.2
7.5°	874.0	882.6	904.1	924.1
10°	850.4	861.9	888.3	911.9
12.5°	827.5	838.3	869.0	895.5
15°	795.3	808.9	841.8	874.7
17.5°	763.2	776.7	816.8	855.4
20°	725.2	743.1	788.2	839.7
22.5°	690.2	712.4	762.4	803.9
25°	651.6	685.9	732.4	786.0
27.5°	617.2	651.6	698.8	753.1
30°	578.6	613.7	662.3	712.4
32.5°	541.4	573.6	620.8	682.3
35°	502.8	533.6	579.3	641.6
37.5°	467.8	497.8	547.9	605.1
40°	433.4	464.9	507.8	565.0
42.5°	401.2	429.1	467.8	525.0
45°	371.9	391.9	427.7	481.4
47.5°	341.2	359.0	391.9	445.6
50°	312.6	327.6	356.2	406.3
52.5°	284.7	297.5	324.0	364.1
55°	259.6	271.8	291.1	330.4
57.5°	233.9	243.2	261.8	293.2
60°	208.8	217.4	232.4	258.2
62.5°	183.8	191.0	205.3	226.0
65°	161.6	167.4	178.1	196.0
67.5°	140.2	143.8	152.3	166.6
70°	119.4	122.3	129.5	140.9
72.5°	97.3	100.1	108.0	115.9
75°	78.7	79.4	85.1	91.5
77.5°	61.5	60.8	65.1	70.1
80°	42.2	44.3	47.9	50.1
82.5°	28.6	29.3	30.8	32.2
85°	15.7	16.5	16.5	18.6
87.5°	6.4	7.2	7.2	7.9
90°	8.6	6.1	3.5	1.0
92.5°	26.0	24.3	22.6	20.9
95°	55.7	53.6	51.5	49.4
97.5°	88.4	86.5	84.6	82.7
100°	125.8	124.1	122.4	120.7
102.5°	164.4	163.1	161.9	160.6
105°	206.2	205.5	204.9	204.3
107.5°	250.5	249.7	248.8	248.0
110°	293.6	292.3	291.1	289.8

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	339.2	337.9	336.7	335.4
115°	383.9	382.6	381.3	380.0
117.5°	429.8	428.1	426.4	424.7
120°	474.5	472.8	471.1	469.4
122.5°	516.5	514.4	512.3	510.2
125°	558.7	556.8	554.9	553.0
127.5°	601.7	599.4	597.1	594.8
130°	642.0	639.2	636.5	633.7
132.5°	683.7	681.6	679.5	677.4
135°	722.4	720.1	717.7	715.4
137.5°	762.9	761.0	759.1	757.2
140°	800.0	798.1	796.2	794.3
142.5°	838.0	836.1	834.2	832.3
145°	872.9	871.4	869.9	868.4
147.5°	906.4	904.5	902.6	900.7
150°	937.8	936.5	935.3	934.0
152.5°	967.2	965.9	964.7	963.4
155°	994.8	994.1	993.5	992.9
157.5°	1019.8	1019.3	1018.9	1018.5
160°	1042.6	1042.1	1041.7	1041.3
162.5°	1062.2	1062.2	1062.2	1062.2
165°	1079.6	1079.9	1080.1	1080.3
167.5°	1094.5	1095.2	1095.8	1096.4
170°	1106.9	1107.5	1108.2	1108.8
172.5°	1115.4	1116.1	1116.7	1117.3
175°	1122.1	1122.7	1123.4	1124.0
177.5°	1125.9	1126.5	1127.2	1127.8
180°	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P998667

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.12	14.87	15.17	15.92	17.34	11.61	12.36	12.66	13.41	14.83
	3H	14.93	15.60	15.98	16.65	18.09	12.95	13.62	14.01	14.68	16.12
	4H	15.09	15.72	16.16	16.78	18.23	13.41	14.04	14.48	15.10	16.55
	6H	15.13	15.71	16.21	16.78	18.23	13.71	14.29	14.79	15.36	16.81
	8H	15.10	15.66	16.19	16.74	18.19	13.79	14.35	14.87	15.43	16.87
	12H	15.06	15.59	16.15	16.66	18.14	13.83	14.36	14.92	15.43	16.90
4H	2H	14.15	14.79	15.23	15.84	17.29	12.05	12.68	13.12	13.74	15.18
	3H	15.12	15.65	16.20	16.74	18.19	13.50	14.03	14.58	15.11	16.57
	4H	15.39	15.88	16.48	16.96	18.43	14.03	14.51	15.12	15.59	17.07
	6H	15.52	15.93	16.61	17.03	18.50	14.40	14.82	15.50	15.92	17.39
	8H	15.51	15.90	16.61	16.99	18.48	14.51	14.90	15.61	15.99	17.48
	12H	15.47	15.82	16.59	16.93	18.42	14.56	14.91	15.68	16.02	17.51
8H	4H	15.39	15.78	16.49	16.87	18.36	14.16	14.55	15.26	15.64	17.13
	6H	15.57	15.89	16.69	17.02	18.51	14.59	14.91	15.71	16.05	17.53
	8H	15.60	15.88	16.72	16.99	18.50	14.74	15.02	15.87	16.14	17.64
	12H	15.58	15.82	16.71	16.94	18.48	14.83	15.08	15.96	16.19	17.73
12H	4H	15.35	15.70	16.46	16.80	18.29	14.13	14.48	15.25	15.59	17.08
	6H	15.55	15.83	16.67	16.94	18.45	14.59	14.87	15.72	15.99	17.49
	8H	15.57	15.82	16.70	16.93	18.47	14.75	14.99	15.87	16.10	17.64