

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998670

Luminaire Tested: SA2XXDIP-B485D925UB50-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998670
REPORT IS A COMBINATION OF REPORTS P984413 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D925UB50-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5034.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998670

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P998670

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	93	88	84	80	84	80	76	73	63	61	59	48	47	45	34	33	32
2	84	77	70	65	76	69	64	59	55	51	48	42	39	37	30	28	26
3	77	67	59	53	69	60	54	49	48	43	40	37	33	31	26	24	22
4	70	59	51	45	62	53	46	41	42	37	33	32	29	26	23	21	19
5	64	52	44	38	57	47	40	35	38	32	28	29	25	22	21	18	16
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14
7	54	42	34	28	49	38	31	26	30	25	21	23	20	17	17	14	12
8	50	38	30	25	45	34	28	23	28	23	19	21	18	15	15	13	11
9	47	34	27	22	42	31	25	20	25	20	17	20	16	13	14	12	10
10	43	31	24	20	39	29	22	18	23	18	15	18	14	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7812	7812	7812
5°	7847	7478	7437
10°	7795	7220	7114
15°	7684	6952	6784
20°	7545	6669	6470
25°	7408	6401	6186
30°	7216	6127	5904
35°	7023	5863	5698
40°	6819	5635	5491
45°	6622	5428	5312
50°	6414	5238	5135
55°	6193	5035	4955
60°	5926	4824	4767
65°	5645	4580	4548
70°	5327	4319	4315
75°	4923	4060	4092
80°	4279	3789	3864
85°	3630	3534	3666

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6622 cd/sqm

TEST NUMBER: P998670

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	0.9
10°-20°	134.2	2.7
20°-30°	203.3	4.0
30°-40°	247.6	4.9
40°-50°	266.4	5.3
50°-60°	258.7	5.1
60°-70°	225.9	4.5
70°-80°	173.9	3.5
80°-90°	119.7	2.4
90°-100°	150.0	3.0
100°-110°	280.1	5.6
110°-120°	417.6	8.3
120°-130°	519.8	10.3
130°-140°	568.3	11.3
140°-150°	550.0	10.9
150°-160°	460.1	9.1
160°-170°	305.1	6.1
170°-180°	106.6	2.1
0°-30°	384.3	7.6
0°-40°	631.8	12.6
0°-60°	1156.9	23.0
0°-90°	1676.3	33.3
90°-120°	847.7	16.8
90°-150°	2485.9	49.4
90°-180°	3358.0	66.7
0°-180°	5034.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	494	494	494	494	494	
5°	495	493	488	493	492	47
15°	472	474	474	480	479	133
25°	429	434	441	449	451	197
35°	370	382	396	411	416	231
45°	303	323	348	370	377	234
55°	232	258	295	321	330	208
65°	159	194	236	265	275	158
75°	88	128	174	204	214	93
85°	26	70	116	146	156	27
90°	8	61	128	154	164	8
95°	55	98	143	170	177	60
105°	208	231	270	297	305	220
115°	383	396	427	447	452	379
125°	554	563	583	599	605	496
135°	716	727	736	750	753	554
145°	868	875	881	886	886	543
155°	993	996	999	1003	1000	457
165°	1080	1079	1079	1086	1081	305
175°	1124	1121	1119	1126	1120	107
180°	1126	1126	1126	1126	1126	

TEST NUMBER: P998670

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	493.5	493.5	493.5	493.5	493.5
2.5°	497.1	494.9	489.9	493.5	492.1
5°	494.9	492.8	488.5	492.8	492.1
7.5°	491.3	489.9	486.3	491.3	490.6
10°	487.1	485.6	483.5	489.2	488.5
12.5°	479.9	480.6	479.2	484.9	484.2
15°	472.0	473.5	473.5	479.9	479.2
17.5°	462.0	464.9	467.0	473.5	473.5
20°	452.0	455.6	458.4	466.3	466.3
22.5°	441.3	445.6	449.9	457.7	459.2
25°	429.1	434.1	440.6	449.2	451.3
27.5°	414.8	422.7	429.8	440.6	442.0
30°	400.5	409.8	419.1	430.6	432.7
32.5°	384.8	395.5	407.0	420.5	424.8
35°	369.8	381.9	395.5	411.2	416.3
37.5°	353.3	366.9	384.1	401.2	406.2
40°	336.9	352.6	371.9	390.5	396.9
42.5°	321.1	336.9	359.7	380.5	386.9
45°	303.2	322.6	347.6	369.8	376.9
47.5°	286.1	306.8	335.4	358.3	366.2
50°	268.2	290.4	322.6	346.9	354.7
52.5°	251.0	274.6	309.0	334.0	342.6
55°	232.4	258.2	295.4	321.1	330.4
57.5°	214.6	243.2	280.4	308.3	317.6
60°	195.3	226.0	266.8	294.0	304.0
62.5°	178.1	210.3	251.0	280.4	289.7
65°	158.8	193.8	236.0	265.3	274.6
67.5°	141.6	178.1	221.0	250.3	260.3
70°	123.0	160.2	204.5	235.3	243.9
72.5°	105.9	144.5	189.5	219.6	230.3
75°	88.0	128.0	173.8	204.5	213.8
77.5°	70.8	112.3	158.8	189.5	199.5
80°	53.6	97.3	143.8	173.8	183.8
82.5°	39.3	82.2	129.5	159.5	168.8
85°	25.7	70.1	115.9	145.9	155.9
87.5°	15.7	58.6	104.4	133.7	143.0
90°	8.2	61.0	127.7	154.4	163.9
92.5°	27.3	72.8	117.5	146.3	154.8
95°	55.1	98.2	143.0	170.2	176.9
97.5°	87.7	127.0	172.2	198.7	207.3
100°	125.7	159.8	202.6	229.1	236.1
102.5°	164.9	194.2	236.6	263.3	270.2
105°	207.9	231.4	270.5	297.4	305.3
107.5°	251.6	272.5	308.3	333.5	336.7
110°	292.7	312.7	347.7	370.6	375.6

TEST NUMBER: P998670

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	338.3	355.4	387.3	407.4	413.4
115°	382.9	396.5	426.8	447.3	452.2
117.5°	426.8	440.2	465.5	484.1	488.4
120°	471.5	482.0	503.0	523.0	528.0
122.5°	512.3	522.6	544.3	560.7	565.3
125°	554.4	562.9	583.0	599.4	605.0
127.5°	596.2	605.9	621.4	635.5	639.1
130°	635.1	646.8	659.9	675.2	677.1
132.5°	678.8	687.6	699.3	711.0	713.9
135°	716.1	726.6	735.7	749.7	752.6
137.5°	757.9	766.5	772.0	784.7	785.8
140°	795.0	802.9	809.0	820.5	821.0
142.5°	833.0	840.9	843.7	853.3	853.1
145°	868.4	875.1	880.8	886.0	885.8
147.5°	900.7	909.3	913.1	915.7	914.1
150°	934.0	939.7	943.5	946.3	943.5
152.5°	963.4	969.1	973.9	977.7	973.9
155°	992.9	995.7	998.6	1003.3	1000.5
157.5°	1018.5	1020.4	1022.3	1029.0	1024.2
160°	1041.3	1043.2	1044.2	1049.9	1046.1
162.5°	1062.2	1062.2	1063.2	1069.8	1065.1
165°	1080.3	1079.3	1079.3	1086.0	1081.2
167.5°	1096.4	1093.6	1093.6	1100.2	1095.5
170°	1108.8	1105.9	1105.0	1111.6	1105.9
172.5°	1117.3	1114.5	1113.5	1120.2	1114.5
175°	1124.0	1121.1	1119.2	1125.9	1120.2
177.5°	1127.8	1124.9	1123.0	1128.7	1123.0
180°	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P998670

CATALOG NUMBER: SA2XXDIP-B485D925UB50-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.59	11.35	11.67	12.44	13.92	13.67	14.43	14.75	15.51	17.00
	3H	12.04	12.73	13.13	13.82	15.33	16.25	16.93	17.34	18.03	19.53
	4H	12.52	13.17	13.61	14.26	15.77	17.50	18.15	18.60	19.24	20.75
	6H	12.80	13.40	13.90	14.50	16.02	18.79	19.39	19.90	20.49	22.01
	8H	12.85	13.43	13.96	14.54	16.06	19.44	20.02	20.56	21.13	22.65
	12H	12.86	13.41	13.98	14.52	16.06	20.17	20.71	21.28	21.82	23.36
4H	2H	11.63	12.28	12.74	13.38	14.89	13.99	14.64	15.09	15.73	17.24
	3H	13.33	13.88	14.44	15.00	16.52	16.77	17.32	17.88	18.44	19.96
	4H	13.95	14.46	15.06	15.57	17.11	18.18	18.69	19.30	19.80	21.34
	6H	14.36	14.80	15.48	15.93	17.47	19.64	20.08	20.77	21.22	22.75
	8H	14.46	14.88	15.59	16.00	17.55	20.40	20.81	21.52	21.94	23.49
	12H	14.50	14.88	15.64	16.01	17.57	21.22	21.60	22.36	22.73	24.29
8H	4H	14.73	15.14	15.85	16.27	17.82	18.32	18.73	19.44	19.85	21.41
	6H	15.36	15.70	16.50	16.87	18.42	19.94	20.29	21.09	21.45	23.00
	8H	15.58	15.88	16.73	17.03	18.60	20.83	21.13	21.98	22.28	23.85
	12H	15.71	15.98	16.86	17.12	18.72	21.82	22.09	22.97	23.23	24.83
12H	4H	14.92	15.30	16.06	16.44	17.99	18.29	18.66	19.43	19.80	21.36
	6H	15.69	16.00	16.84	17.14	18.71	19.97	20.27	21.11	21.42	22.98
	8H	15.99	16.26	17.15	17.40	19.01	20.89	21.16	22.04	22.30	23.90