

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999912

Luminaire Tested: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999912
REPORT IS A COMBINATION OF REPORTS P988469 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3619.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999912

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999912

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	59
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	53	49	49	47	44
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	41	37	34
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	25
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	48	37	30	26	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17795	17795	17795
5°	17824	16930	16805
10°	17648	16056	15527
15°	17405	15027	14070
20°	17086	13854	12548
25°	16757	12653	11155
30°	16314	11481	9633
35°	15883	10299	8327
40°	15442	9141	6981
45°	14932	7943	5807
50°	14403	6788	4728
55°	13853	5634	3754
60°	13212	4507	2840
65°	12478	3435	2309
70°	11589	2492	1836
75°	10472	1901	1401
80°	8854	1286	942
85°	6173	588	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14932 cd/sqm

TEST NUMBER: P999912

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	2.9
10°-20°	289.2	8.0
20°-30°	406.1	11.2
30°-40°	442.6	12.2
40°-50°	406.8	11.2
50°-60°	319.5	8.8
60°-70°	208.0	5.7
70°-80°	107.1	3.0
80°-90°	28.1	0.8
90°-100°	14.7	0.4
100°-110°	54.8	1.5
110°-120°	145.3	4.0
120°-130°	240.9	6.7
130°-140°	255.9	7.1
140°-150°	237.8	6.6
150°-160°	191.2	5.3
160°-170°	123.2	3.4
170°-180°	42.4	1.2
0°-30°	800.7	22.1
0°-40°	1243.3	34.4
0°-60°	1969.7	54.4
0°-90°	2312.8	63.9
90°-120°	214.7	5.9
90°-150°	949.4	26.2
90°-180°	1306.0	36.1
0°-180°	3619.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1124	1119	1106	1115	1112	107
15°	1069	1058	1024	1004	994	301
25°	971	938	871	829	814	446
35°	836	784	695	631	608	523
45°	684	616	509	436	412	528
55°	520	440	331	270	250	465
65°	351	269	177	142	139	348
75°	187	116	81	74	73	198
85°	44	22	19	19	19	50
90°	0	4	6	8	9	3
95°	21	10	13	14	14	25
105°	98	108	20	23	24	105
115°	185	191	199	50	26	183
125°	262	266	272	275	276	234
135°	324	330	332	336	335	251
145°	376	376	381	384	382	235
155°	414	411	415	417	415	191
165°	436	435	436	438	436	123
175°	446	444	445	447	444	42
180°	446	446	446	446	446	

TEST NUMBER: P999912

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1124.2	1124.2	1124.2	1124.2	1124.2
2.5°	1129.3	1124.2	1113.0	1123.2	1121.1
5°	1124.2	1119.1	1105.9	1115.0	1112.0
7.5°	1115.0	1108.9	1094.7	1098.7	1093.6
10°	1102.8	1095.7	1075.3	1072.3	1066.2
12.5°	1087.5	1078.4	1050.9	1044.8	1033.6
15°	1069.2	1058.0	1023.5	1004.1	993.9
17.5°	1047.9	1031.6	988.9	966.5	950.2
20°	1023.5	1003.1	952.2	926.8	904.4
22.5°	997.0	973.6	914.6	880.0	864.7
25°	970.6	938.0	870.9	829.1	813.9
27.5°	939.0	904.4	830.2	782.3	758.9
30°	905.4	866.8	785.4	733.5	706.0
32.5°	872.9	826.1	742.7	681.6	656.2
35°	836.3	784.4	694.8	630.8	608.4
37.5°	800.7	744.7	650.1	579.9	554.5
40°	763.0	702.0	603.3	531.1	504.6
42.5°	724.4	659.2	556.5	481.2	455.8
45°	683.7	615.5	508.7	436.4	412.0
47.5°	645.0	572.8	462.9	390.7	368.3
50°	602.3	530.0	418.1	347.9	326.6
52.5°	560.6	484.3	375.4	308.3	288.9
55°	519.9	440.5	330.6	269.6	250.3
57.5°	478.2	396.8	291.0	234.0	217.7
60°	435.4	354.0	249.3	197.4	181.1
62.5°	393.7	312.3	213.6	164.8	156.7
65°	351.0	268.6	177.0	142.4	139.4
67.5°	310.3	227.9	142.4	125.1	122.1
70°	267.6	188.2	118.0	107.8	103.8
72.5°	226.9	151.6	98.7	90.5	88.5
75°	187.2	116.0	81.4	74.3	73.2
77.5°	147.5	82.4	64.1	60.0	58.0
80°	110.9	59.0	48.8	44.8	44.8
82.5°	77.3	39.7	33.6	31.5	31.5
85°	43.7	22.4	19.3	19.3	19.3
87.5°	16.3	8.1	8.1	7.1	7.1
90°	0.3	3.9	6.4	8.1	8.7
92.5°	8.1	6.8	7.7	8.4	8.7
95°	21.0	10.3	12.6	14.2	13.9
97.5°	37.7	11.3	16.4	17.4	17.7
100°	57.1	12.9	18.4	21.0	21.6
102.5°	78.3	77.7	19.0	22.6	23.5
105°	98.0	107.7	19.7	23.2	24.5
107.5°	120.9	129.0	20.3	23.9	25.1
110°	142.8	149.6	56.4	24.2	25.5

TEST NUMBER: P999912

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	163.5	169.3	163.8	24.8	25.8
115°	185.4	190.9	198.9	49.6	26.4
117.5°	204.4	210.8	216.3	170.2	85.8
120°	225.7	230.5	236.3	240.2	196.7
122.5°	243.7	248.9	255.3	257.3	257.6
125°	262.1	266.3	272.4	274.7	275.7
127.5°	278.9	283.4	288.2	291.4	291.8
130°	294.7	299.8	303.4	306.9	306.6
132.5°	310.8	315.0	318.5	321.4	321.1
135°	324.3	329.5	332.4	335.6	335.0
137.5°	338.5	342.4	345.6	348.8	347.9
140°	352.4	355.0	358.5	361.4	359.8
142.5°	364.0	366.2	370.4	373.0	371.4
145°	376.2	375.9	381.4	383.7	382.0
147.5°	386.9	385.9	391.4	393.0	391.7
150°	397.2	394.9	400.1	402.0	400.4
152.5°	405.9	403.3	408.2	410.1	407.8
155°	414.3	411.4	415.3	417.2	414.6
157.5°	421.1	418.5	421.4	423.6	421.1
160°	426.9	424.9	426.9	428.8	426.5
162.5°	432.0	430.1	431.7	434.0	431.0
165°	436.5	434.6	435.6	437.8	435.6
167.5°	440.1	438.1	439.1	441.4	438.5
170°	443.0	441.0	441.7	443.9	441.0
172.5°	444.9	443.0	443.6	445.9	443.0
175°	446.5	444.3	444.9	447.2	443.9
177.5°	447.2	444.9	445.2	447.5	444.6
180°	445.6	445.6	445.6	445.6	445.6

(END OF REPORT)