

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999913

Luminaire Tested: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999913
REPORT IS A COMBINATION OF REPORTS P988470 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3651.0 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999913

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P999913

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	59
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	53	49	49	47	44
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	41	37	34
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	25
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	48	37	30	26	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17949	17949	17949
5°	17978	17076	16950
10°	17800	16195	15661
15°	17557	15156	14192
20°	17232	13974	12656
25°	16900	12761	11251
30°	16456	11581	9716
35°	16019	10390	8398
40°	15576	9219	7042
45°	15061	8012	5858
50°	14527	6847	4769
55°	13973	5684	3785
60°	13327	4545	2865
65°	12584	3464	2329
70°	11689	2513	1852
75°	10562	1918	1414
80°	8934	1299	950
85°	6229	595	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15061 cd/sqm

TEST NUMBER: P999913

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	2.9
10°-20°	291.7	8.0
20°-30°	409.6	11.2
30°-40°	446.5	12.2
40°-50°	410.3	11.2
50°-60°	322.3	8.8
60°-70°	209.8	5.7
70°-80°	108.0	3.0
80°-90°	28.4	0.8
90°-100°	14.8	0.4
100°-110°	55.3	1.5
110°-120°	146.6	4.0
120°-130°	243.1	6.7
130°-140°	258.3	7.1
140°-150°	240.0	6.6
150°-160°	193.0	5.3
160°-170°	124.3	3.4
170°-180°	42.8	1.2
0°-30°	807.6	22.1
0°-40°	1254.0	34.3
0°-60°	1986.6	54.4
0°-90°	2332.8	63.9
90°-120°	216.7	5.9
90°-150°	958.1	26.2
90°-180°	1318.0	36.1
0°-180°	3651.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1134	1134	1134	1134	1134	
5°	1134	1129	1115	1125	1122	108
15°	1078	1067	1032	1013	1002	304
25°	979	946	878	836	821	450
35°	844	791	701	636	614	528
45°	690	621	513	440	416	533
55°	524	444	334	272	252	469
65°	354	271	178	144	141	351
75°	189	117	82	75	74	200
85°	44	23	20	20	20	51
90°	0	4	6	8	9	3
95°	21	10	13	14	14	25
105°	99	109	20	23	25	106
115°	187	193	201	50	27	184
125°	264	269	275	277	278	236
135°	327	332	335	339	338	253
145°	380	379	385	387	386	237
155°	418	415	419	421	418	193
165°	440	439	440	442	440	124
175°	451	448	449	451	448	43
180°	450	450	450	450	450	

TEST NUMBER: P999913

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1133.9	1133.9	1133.9	1133.9	1133.9
2.5°	1139.0	1133.9	1122.6	1132.9	1130.8
5°	1133.9	1128.8	1115.4	1124.7	1121.6
7.5°	1124.7	1118.5	1104.1	1108.2	1103.1
10°	1112.3	1105.2	1084.6	1081.6	1075.4
12.5°	1097.0	1087.7	1060.0	1053.9	1042.6
15°	1078.5	1067.2	1032.3	1012.8	1002.5
17.5°	1056.9	1040.5	997.4	974.8	958.4
20°	1032.3	1011.8	960.5	934.8	912.2
22.5°	1005.6	982.0	922.5	887.6	872.2
25°	978.9	946.1	878.4	836.3	820.9
27.5°	947.1	912.2	837.3	789.1	765.5
30°	913.3	874.3	792.2	739.9	712.1
32.5°	880.4	833.2	749.1	687.5	661.9
35°	843.5	791.2	700.9	636.2	613.6
37.5°	807.6	751.1	655.7	584.9	559.3
40°	769.6	708.0	608.5	535.6	509.0
42.5°	730.6	664.9	561.3	485.4	459.7
45°	689.6	620.8	513.1	440.2	415.6
47.5°	650.6	577.7	466.9	394.0	371.5
50°	607.5	534.6	421.7	350.9	329.4
52.5°	565.4	488.4	378.6	310.9	291.4
55°	524.4	444.3	333.5	271.9	252.4
57.5°	482.3	400.2	293.5	236.0	219.6
60°	439.2	357.1	251.4	199.1	182.7
62.5°	397.1	315.0	215.5	166.2	158.0
65°	354.0	270.9	178.5	143.7	140.6
67.5°	313.0	229.9	143.7	126.2	123.1
70°	269.9	189.8	119.0	108.8	104.7
72.5°	228.8	152.9	99.5	91.3	89.3
75°	188.8	117.0	82.1	74.9	73.9
77.5°	148.8	83.1	64.6	60.5	58.5
80°	111.9	59.5	49.3	45.2	45.2
82.5°	78.0	40.0	33.9	31.8	31.8
85°	44.1	22.6	19.5	19.5	19.5
87.5°	16.4	8.2	8.2	7.2	7.2
90°	0.3	3.9	6.5	8.1	8.8
92.5°	8.1	6.8	7.8	8.5	8.8
95°	21.1	10.4	12.7	14.3	14.0
97.5°	38.1	11.4	16.6	17.6	17.9
100°	57.6	13.0	18.5	21.1	21.8
102.5°	79.1	78.4	19.2	22.8	23.8
105°	98.9	108.7	19.8	23.4	24.7
107.5°	122.0	130.1	20.5	24.1	25.4
110°	144.1	151.0	56.9	24.4	25.7

TEST NUMBER: P999913

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.0	170.8	165.3	25.1	26.0
115°	187.1	192.6	200.7	50.1	26.7
117.5°	206.3	212.8	218.3	171.8	86.5
120°	227.8	232.6	238.5	242.4	198.5
122.5°	246.0	251.2	257.7	259.6	260.0
125°	264.5	268.7	274.9	277.2	278.2
127.5°	281.4	286.0	290.9	294.1	294.5
130°	297.4	302.6	306.2	309.7	309.4
132.5°	313.6	317.9	321.5	324.4	324.1
135°	327.3	332.5	335.4	338.7	338.0
137.5°	341.6	345.5	348.8	352.0	351.1
140°	355.6	358.2	361.8	364.7	363.1
142.5°	367.3	369.6	373.8	376.4	374.8
145°	379.7	379.4	384.9	387.2	385.6
147.5°	390.4	389.5	395.0	396.6	395.3
150°	400.8	398.6	403.8	405.7	404.1
152.5°	409.6	407.0	411.9	413.9	411.6
155°	418.1	415.2	419.1	421.0	418.4
157.5°	424.9	422.3	425.2	427.5	424.9
160°	430.8	428.8	430.8	432.7	430.5
162.5°	436.0	434.0	435.7	437.9	435.0
165°	440.5	438.6	439.6	441.8	439.6
167.5°	444.1	442.2	443.1	445.4	442.5
170°	447.0	445.1	445.7	448.0	445.1
172.5°	449.0	447.0	447.7	450.0	447.0
175°	450.6	448.3	449.0	451.3	448.0
177.5°	451.3	449.0	449.3	451.6	448.7
180°	449.6	449.6	449.6	449.6	449.6

(END OF REPORT)