

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998699

Luminaire Tested: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998699
REPORT IS A COMBINATION OF REPORTS P984442 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7253.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41		
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35		
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35	30		
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26		
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	23		
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20		
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18		
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	18	16		
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14		
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13		
10	47	35	28	23	43	32	26	22	27	23	19	23	19	17	18	16	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21137	21137	21137	21137
5°	21187	22537	21268	17929
10°	20941	24603	21073	14781
15°	20433	25949	20718	12452
20°	20114	24365	20114	10822
25°	19473	20932	19562	9678
30°	18418	16454	18769	8766
35°	17484	11378	17776	8020
40°	16410	8590	16596	7427
45°	15085	7060	15332	6785
50°	13942	6196	13965	6211
55°	12636	5279	12716	5588
60°	11243	4410	11397	4877
65°	9996	3587	10178	4165
70°	8757	2815	8978	3359
75°	7351	2042	7636	2437
80°	5732	1295	6148	1446
85°	3772	651	4054	482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21850 cd/sqm

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.2	1.8
10°-20°	370.2	5.1
20°-30°	537.2	7.4
30°-40°	566.3	7.8
40°-50°	501.2	6.9
50°-60°	400.2	5.5
60°-70°	271.8	3.7
70°-80°	139.1	1.9
80°-90°	35.4	0.5
90°-100°	48.4	0.7
100°-110°	180.5	2.5
110°-120°	478.7	6.6
120°-130°	793.9	10.9
130°-140°	843.3	11.6
140°-150°	783.8	10.8
150°-160°	630.1	8.7
160°-170°	406.0	5.6
170°-180°	139.7	1.9
0°-30°	1034.6	14.3
0°-40°	1600.9	22.1
0°-60°	2502.3	34.5
0°-90°	2948.6	40.7
90°-120°	707.6	9.8
90°-150°	3128.5	43.1
90°-180°	4304.0	59.3
0°-180°	7253.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1335	1335	1335	1335	1335	
5°	1336	1491	1341	1186	1336	127
15°	1255	1833	1273	880	1255	355
25°	1128	1527	1133	706	1128	516
35°	921	831	936	586	921	576
45°	691	501	702	481	691	536
55°	474	352	477	373	474	423
65°	281	217	286	252	281	280
75°	131	107	136	127	131	141
85°	27	28	29	20	27	31
90°	1	29	1	29	1	5
95°	69	46	69	46	69	82
105°	323	81	323	81	323	345
115°	611	87	611	87	611	601
125°	864	908	864	908	864	770
135°	1069	1104	1069	1104	1069	826
145°	1240	1259	1240	1259	1240	775
155°	1365	1366	1365	1366	1365	629
165°	1438	1435	1438	1435	1438	406
175°	1471	1463	1471	1463	1471	140
180°	1468	1468	1468	1468	1468	

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1342.4	1345.5	1350.7	1351.7	1361.9	1370.2	1379.4	1379.4	1382.5	1381.4	1373.2
5°	1336.3	1345.5	1358.9	1370.2	1388.6	1396.8	1409.2	1418.4	1426.6	1432.8	1431.7
7.5°	1326.0	1342.4	1361.9	1383.5	1408.1	1422.5	1440.0	1456.4	1467.7	1477.9	1485.1
10°	1308.6	1336.3	1363.0	1391.7	1423.5	1443.0	1463.6	1485.1	1502.6	1522.1	1540.5
12.5°	1285.0	1325.0	1357.8	1395.8	1434.8	1456.4	1489.2	1505.6	1539.5	1588.8	1602.1
15°	1255.2	1309.6	1340.4	1388.6	1440.0	1457.4	1502.6	1529.2	1599.0	1629.8	1666.8
17.5°	1227.5	1288.1	1329.1	1384.5	1434.8	1468.7	1512.8	1567.2	1625.7	1669.9	1710.9
20°	1204.9	1263.4	1312.7	1374.3	1437.9	1481.0	1527.2	1592.9	1656.5	1701.7	1733.5
22.5°	1153.6	1228.5	1286.0	1354.8	1431.7	1491.3	1535.4	1607.2	1676.0	1703.7	1731.4
25°	1127.9	1192.6	1259.3	1337.3	1427.6	1498.5	1536.4	1616.5	1677.0	1687.3	1693.5
27.5°	1080.7	1153.6	1231.6	1320.9	1426.6	1486.1	1534.4	1607.2	1655.5	1648.3	1629.8
30°	1022.2	1111.5	1197.7	1294.2	1412.2	1476.9	1522.1	1588.8	1613.4	1576.5	1543.6
32.5°	979.1	1063.3	1158.7	1270.6	1395.8	1457.4	1501.5	1553.9	1559.0	1492.3	1436.9
35°	920.6	1014.0	1121.8	1239.8	1368.1	1423.5	1464.6	1496.4	1471.8	1378.4	1312.7
37.5°	868.3	960.7	1075.6	1195.7	1330.1	1384.5	1417.4	1422.5	1361.9	1279.8	1183.4
40°	810.8	906.3	1026.3	1152.6	1288.1	1335.3	1355.8	1340.4	1253.2	1157.7	1045.8
42.5°	753.3	847.8	977.1	1106.4	1234.7	1274.7	1282.9	1240.8	1134.1	1022.2	892.9
45°	690.7	789.3	918.6	1048.9	1173.1	1195.7	1196.7	1136.2	1009.9	892.9	772.8
47.5°	639.4	730.8	859.0	989.4	1094.1	1109.5	1103.3	1033.5	896.0	764.6	659.9
50°	583.0	670.2	797.5	925.8	1015.0	1019.2	1003.8	904.2	769.8	649.7	566.5
52.5°	522.4	610.7	727.7	850.8	930.9	924.7	895.0	788.2	662.0	562.4	498.8
55°	474.2	552.2	662.0	782.1	838.5	821.1	788.2	679.4	579.9	495.7	440.3
57.5°	420.8	489.6	597.3	702.0	734.9	718.4	685.6	584.0	491.6	428.0	391.0
60°	370.5	433.1	527.5	614.8	640.4	623.0	585.0	493.7	427.0	373.6	345.9
62.5°	324.3	378.7	457.7	537.8	548.1	530.6	497.8	423.9	366.4	324.3	303.8
65°	281.2	332.5	396.2	456.7	466.0	447.5	413.6	360.2	312.0	285.3	265.8
67.5°	239.1	280.2	336.6	380.8	385.9	368.5	340.7	297.6	267.9	239.1	224.8
70°	202.2	233.0	277.1	313.0	315.1	298.7	284.3	245.3	222.7	202.2	190.9
72.5°	166.3	187.8	221.7	248.4	249.4	239.1	225.8	201.2	181.7	167.3	156.0
75°	131.4	149.8	170.4	194.0	193.0	184.7	174.5	159.1	142.7	133.4	128.3
77.5°	100.6	111.9	128.3	143.7	143.7	139.6	133.4	122.1	111.9	102.6	97.5
80°	71.8	79.0	92.4	97.5	99.6	98.5	93.4	85.2	81.1	73.9	71.8
82.5°	46.2	51.3	57.5	62.6	65.7	63.6	62.6	58.5	52.3	50.3	48.2
85°	26.7	28.7	31.8	34.9	35.9	34.9	36.9	33.9	30.8	30.8	29.8
87.5°	11.3	12.3	14.4	14.4	15.4	15.4	14.4	15.4	15.4	14.4	13.3
90°	1.1	3.7	6.3	8.8	11.4	12.7	13.6	15.5	17.4	19.3	21.2
92.5°	26.6	25.6	24.7	23.7	22.8	22.3	22.7	23.4	24.1	24.8	25.5
95°	69.1	61.3	53.5	45.7	37.9	34.0	34.8	36.5	38.1	39.8	41.4
97.5°	124.3	104.9	85.6	66.2	46.9	37.2	39.1	42.9	46.6	50.4	54.2
100°	188.0	155.7	123.3	91.0	58.7	42.5	44.5	48.5	52.6	56.6	60.6
102.5°	258.2	257.7	257.2	256.7	256.2	256.0	234.5	191.6	148.6	105.7	62.7
105°	323.0	330.1	337.1	344.2	351.3	354.8	322.6	258.1	193.7	129.2	64.8
107.5°	398.4	404.3	410.2	416.1	422.0	425.0	385.2	305.6	226.1	146.5	66.9
110°	470.6	475.6	480.6	485.5	490.5	493.0	458.9	390.6	322.4	254.1	185.9

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	538.6	542.9	547.1	551.4	555.7	557.8	555.8	551.8	547.7	543.7	539.7
115°	610.9	614.9	618.9	622.9	626.9	628.9	631.9	637.8	643.7	649.6	655.5
117.5°	673.6	678.3	683.0	687.7	692.4	694.8	696.8	700.8	704.9	708.9	712.9
120°	743.7	747.2	750.8	754.3	757.8	759.6	761.7	766.0	770.3	774.5	778.8
122.5°	803.2	807.0	810.8	814.5	818.3	820.2	822.6	827.3	832.0	836.7	841.4
125°	863.7	866.8	869.9	873.0	876.1	877.6	879.8	884.3	888.8	893.2	897.7
127.5°	919.0	922.3	925.6	928.9	932.2	933.9	935.7	939.2	942.7	946.3	949.8
130°	971.0	974.8	978.6	982.3	986.1	988.0	989.3	991.9	994.5	997.1	999.7
132.5°	1024.2	1027.3	1030.3	1033.4	1036.5	1038.0	1039.3	1041.9	1044.5	1047.1	1049.7
135°	1068.8	1072.6	1076.4	1080.1	1083.9	1085.8	1086.9	1089.0	1091.1	1093.2	1095.3
137.5°	1115.5	1118.3	1121.2	1124.0	1126.9	1128.3	1129.5	1131.8	1134.2	1136.5	1138.9
140°	1161.2	1163.1	1165.0	1166.9	1168.8	1169.7	1171.0	1173.6	1176.2	1178.8	1181.4
142.5°	1199.5	1201.1	1202.8	1204.4	1206.1	1206.9	1208.4	1211.5	1214.6	1217.6	1220.7
145°	1239.8	1239.6	1239.4	1239.1	1238.9	1238.8	1240.8	1244.8	1248.8	1252.8	1256.8
147.5°	1274.9	1274.2	1273.5	1272.8	1272.1	1271.7	1273.7	1277.7	1281.8	1285.8	1289.8
150°	1308.9	1307.3	1305.6	1304.0	1302.3	1301.5	1303.4	1307.2	1310.9	1314.7	1318.5
152.5°	1337.6	1335.7	1333.8	1331.9	1330.0	1329.1	1330.9	1334.4	1337.9	1341.5	1345.0
155°	1365.2	1363.1	1360.9	1358.8	1356.7	1355.6	1357.0	1359.9	1362.7	1365.6	1368.4
157.5°	1387.5	1385.6	1383.7	1381.8	1379.9	1379.0	1380.1	1382.2	1384.3	1386.5	1388.6
160°	1406.6	1405.2	1403.8	1402.4	1401.0	1400.3	1401.0	1402.4	1403.8	1405.2	1406.6
162.5°	1423.6	1422.2	1420.8	1419.4	1418.0	1417.3	1417.9	1419.1	1420.2	1421.4	1422.6
165°	1438.5	1437.1	1435.7	1434.2	1432.8	1432.1	1432.5	1433.2	1433.9	1434.6	1435.3
167.5°	1450.2	1448.8	1447.4	1445.9	1444.5	1443.8	1444.2	1444.9	1445.6	1446.3	1447.0
170°	1459.8	1458.4	1457.0	1455.5	1454.1	1453.4	1453.6	1454.1	1454.6	1455.0	1455.5
172.5°	1466.1	1464.7	1463.3	1461.9	1460.5	1459.8	1460.0	1460.5	1461.0	1461.4	1461.9
175°	1471.4	1469.8	1468.1	1466.5	1464.8	1464.0	1464.2	1464.7	1465.2	1465.6	1466.1
177.5°	1473.6	1471.9	1470.3	1468.6	1466.9	1466.1	1466.2	1466.5	1466.7	1467.0	1467.2
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1387.6	1388.6	1390.7	1400.9	1406.1	1407.1	1403.0	1412.2	1415.3	1412.2	1410.2
5°	1453.3	1459.5	1471.8	1485.1	1484.1	1485.1	1491.3	1497.4	1499.5	1491.3	1494.3
7.5°	1510.8	1523.1	1536.4	1557.0	1557.0	1567.2	1571.3	1576.5	1588.8	1582.6	1580.6
10°	1576.5	1592.9	1617.5	1650.3	1651.4	1661.6	1671.9	1688.3	1693.5	1689.4	1691.4
12.5°	1658.6	1690.4	1692.4	1728.4	1744.8	1746.8	1763.2	1760.2	1770.4	1770.4	1787.9
15°	1694.5	1743.7	1771.5	1806.4	1816.6	1804.3	1817.6	1832.0	1833.0	1833.0	1832.0
17.5°	1759.1	1778.6	1806.4	1824.8	1828.9	1828.9	1830.0	1836.1	1832.0	1823.8	1830.0
20°	1772.5	1780.7	1791.0	1788.9	1791.0	1780.7	1770.4	1760.2	1761.2	1756.1	1771.5
22.5°	1747.9	1745.8	1722.2	1706.8	1706.8	1686.3	1666.8	1657.5	1648.3	1651.4	1656.5
25°	1686.3	1654.5	1625.7	1603.1	1598.0	1565.2	1538.5	1530.3	1514.9	1527.2	1529.2
27.5°	1587.7	1551.8	1505.6	1486.1	1459.5	1446.1	1427.6	1403.0	1371.2	1389.7	1386.6
30°	1482.0	1428.7	1390.7	1343.5	1301.4	1298.3	1263.4	1222.4	1205.9	1205.9	1215.2
32.5°	1364.0	1293.2	1237.8	1171.1	1130.0	1112.5	1070.5	1029.4	1038.7	1007.9	1019.2
35°	1226.5	1133.1	1063.3	998.6	967.8	947.3	892.9	870.3	845.7	831.3	858.0
37.5°	1095.1	987.3	898.0	827.2	815.9	779.0	742.0	727.7	713.3	719.5	718.4
40°	935.0	839.5	759.5	704.1	684.6	667.1	642.5	625.0	615.8	620.9	622.0
42.5°	790.3	710.2	650.7	611.7	595.3	583.0	570.6	556.3	553.2	553.2	557.3
45°	678.4	612.7	572.7	540.9	531.6	522.4	513.2	507.0	505.0	500.9	503.9
47.5°	589.1	536.8	512.1	488.5	478.3	476.2	468.0	464.9	460.8	459.8	460.8
50°	514.2	481.4	458.8	445.4	438.2	435.2	431.1	424.9	422.9	428.0	425.9
52.5°	461.9	431.1	418.7	405.4	401.3	397.2	391.0	392.1	391.0	389.0	389.0
55°	409.5	390.0	377.7	367.4	366.4	362.3	357.2	355.1	354.1	352.0	355.1
57.5°	367.4	352.0	340.7	331.5	327.4	327.4	322.3	318.2	318.2	317.1	318.2
60°	325.3	310.0	302.8	293.5	290.5	289.4	286.3	284.3	281.2	281.2	281.2
62.5°	286.3	274.0	265.8	257.6	258.6	253.5	249.4	247.3	247.3	248.4	248.4
65°	249.4	241.2	230.9	223.7	221.7	220.7	218.6	217.6	214.5	216.6	216.6
67.5°	215.5	204.2	198.1	195.0	191.9	190.9	188.8	186.8	185.8	184.7	186.8
70°	181.7	172.4	167.3	165.2	162.2	161.1	160.1	157.0	158.1	159.1	160.1
72.5°	150.9	142.7	141.6	135.5	135.5	135.5	131.4	133.4	132.4	130.3	132.4
75°	119.1	114.9	112.9	109.8	110.8	109.8	108.8	105.7	105.7	106.7	107.8
77.5°	94.4	90.3	89.3	86.2	84.2	86.2	84.2	83.1	83.1	84.2	84.2
80°	69.8	67.7	64.7	64.7	64.7	63.6	63.6	63.6	62.6	61.6	62.6
82.5°	46.2	46.2	45.2	44.1	45.2	43.1	44.1	44.1	44.1	44.1	44.1
85°	29.8	28.7	28.7	27.7	27.7	27.7	28.7	26.7	26.7	27.7	27.7
87.5°	13.3	13.3	13.3	14.4	13.3	13.3	13.3	14.4	13.3	13.3	13.3
90°	22.4	23.6	24.8	26.0	26.6	26.8	27.3	27.8	28.2	28.7	28.2
92.5°	26.0	26.4	26.9	27.4	27.6	27.7	28.0	28.2	28.5	28.7	28.5
95°	42.6	43.8	44.9	46.1	46.7	46.6	46.4	46.1	45.9	45.7	45.9
97.5°	54.9	55.6	56.3	57.0	57.4	57.5	57.7	58.0	58.2	58.4	58.2
100°	62.5	64.4	66.3	68.2	69.1	69.3	69.8	70.3	70.7	71.2	70.7
102.5°	65.3	67.9	70.5	73.1	74.4	74.8	75.5	76.2	76.9	77.6	76.9
105°	67.4	70.0	72.6	75.2	76.5	77.0	77.9	78.8	79.8	80.7	79.8
107.5°	69.5	72.1	74.7	77.3	78.6	79.1	80.0	81.0	81.9	82.9	81.9
110°	162.3	138.7	115.1	91.5	79.7	80.2	81.1	82.0	83.0	83.9	83.0

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	437.9	336.2	234.4	132.7	81.8	82.2	82.9	83.6	84.3	85.0	84.3
115°	546.2	436.9	327.6	218.3	163.6	155.1	138.1	121.1	104.1	87.1	104.1
117.5°	679.1	645.4	611.6	577.9	561.0	530.1	468.2	406.3	344.5	282.6	344.5
120°	781.6	784.4	787.3	790.1	791.5	775.6	743.7	711.8	680.0	648.1	680.0
122.5°	842.8	844.2	845.7	847.1	847.8	847.9	848.2	848.4	848.7	848.9	848.7
125°	899.4	901.0	902.7	904.4	905.2	905.6	906.3	907.0	907.7	908.4	907.7
127.5°	952.2	954.5	956.9	959.2	960.4	960.5	960.8	961.0	961.3	961.5	961.3
130°	1002.3	1004.9	1007.5	1010.1	1011.4	1011.3	1011.1	1010.8	1010.6	1010.4	1010.6
132.5°	1051.8	1053.9	1056.0	1058.1	1059.2	1059.1	1058.9	1058.6	1058.4	1058.2	1058.4
135°	1097.7	1100.1	1102.4	1104.8	1106.0	1105.8	1105.3	1104.8	1104.3	1103.8	1104.3
137.5°	1141.3	1143.6	1146.0	1148.3	1149.5	1149.1	1148.4	1147.7	1147.0	1146.3	1147.0
140°	1183.5	1185.7	1187.8	1189.9	1191.0	1190.4	1189.2	1188.1	1186.9	1185.7	1186.9
142.5°	1222.6	1224.5	1226.4	1228.3	1229.2	1228.6	1227.4	1226.3	1225.1	1223.9	1225.1
145°	1258.5	1260.1	1261.8	1263.5	1264.3	1263.7	1262.5	1261.4	1260.2	1259.0	1260.2
147.5°	1291.0	1292.2	1293.3	1294.5	1295.1	1294.6	1293.7	1292.7	1291.8	1290.8	1291.8
150°	1319.9	1321.3	1322.7	1324.1	1324.8	1324.2	1323.0	1321.9	1320.7	1319.5	1320.7
152.5°	1346.4	1347.8	1349.3	1350.7	1351.4	1350.6	1348.9	1347.3	1345.6	1344.0	1345.6
155°	1369.8	1371.2	1372.7	1374.1	1374.8	1373.9	1372.0	1370.1	1368.2	1366.3	1368.2
157.5°	1390.2	1391.9	1393.5	1395.2	1396.0	1395.1	1393.2	1391.3	1389.4	1387.5	1389.4
160°	1408.0	1409.4	1410.9	1412.3	1413.0	1412.2	1410.5	1408.9	1407.2	1405.6	1407.2
162.5°	1424.2	1425.9	1427.5	1429.2	1430.0	1428.9	1426.8	1424.7	1422.5	1420.4	1422.5
165°	1437.0	1438.6	1440.3	1442.0	1442.8	1442.0	1440.3	1438.6	1437.0	1435.3	1437.0
167.5°	1448.6	1450.3	1451.9	1453.6	1454.4	1453.3	1451.2	1449.1	1447.0	1444.9	1447.0
170°	1457.1	1458.8	1460.4	1462.1	1462.9	1461.8	1459.7	1457.6	1455.5	1453.4	1455.5
172.5°	1463.5	1465.2	1466.8	1468.5	1469.3	1468.2	1466.1	1464.0	1461.9	1459.8	1461.9
175°	1467.8	1469.4	1471.1	1472.8	1473.6	1472.4	1470.0	1467.7	1465.3	1462.9	1465.3
177.5°	1468.8	1470.5	1472.1	1473.8	1474.6	1473.5	1471.4	1469.3	1467.2	1465.1	1467.2
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1415.3	1408.1	1402.0	1403.0	1408.1	1404.0	1393.8	1380.4	1375.3	1369.1	1375.3
5°	1500.5	1494.3	1482.0	1483.1	1480.0	1475.9	1459.5	1438.9	1438.9	1422.5	1420.5
7.5°	1584.7	1575.4	1567.2	1565.2	1553.9	1545.7	1531.3	1502.6	1491.3	1471.8	1460.5
10°	1679.1	1671.9	1662.7	1651.4	1645.2	1630.8	1607.2	1565.2	1544.6	1518.0	1498.5
12.5°	1774.5	1773.5	1753.0	1730.4	1729.4	1706.8	1690.4	1633.9	1606.2	1570.3	1524.1
15°	1835.1	1830.0	1818.7	1807.4	1810.5	1785.8	1748.9	1682.2	1663.7	1620.6	1571.3
17.5°	1834.1	1834.1	1831.0	1828.9	1825.9	1818.7	1798.1	1754.0	1724.2	1669.9	1623.7
20°	1775.6	1788.9	1792.0	1791.0	1801.2	1806.4	1805.3	1777.6	1754.0	1705.8	1658.6
22.5°	1658.6	1689.4	1702.7	1710.9	1732.5	1743.7	1770.4	1760.2	1754.0	1718.1	1678.1
25°	1549.8	1560.0	1600.1	1602.1	1631.9	1659.6	1686.3	1703.7	1726.3	1713.0	1679.1
27.5°	1409.2	1432.8	1461.5	1483.1	1489.2	1545.7	1589.8	1622.6	1674.0	1678.1	1666.8
30°	1250.1	1261.4	1308.6	1337.3	1370.2	1411.2	1474.8	1531.3	1577.5	1619.6	1633.9
32.5°	1056.1	1102.3	1130.0	1164.9	1193.6	1266.5	1344.5	1417.4	1470.7	1541.6	1572.3
35°	878.5	914.5	961.7	976.0	1028.4	1090.0	1191.6	1285.0	1366.1	1437.9	1500.5
37.5°	731.8	760.5	810.8	833.4	864.2	943.2	1028.4	1144.4	1241.9	1330.1	1408.1
40°	631.2	652.8	690.7	697.9	723.6	795.4	864.2	973.0	1102.3	1221.3	1306.5
42.5°	562.4	572.7	598.4	607.6	624.0	672.3	733.8	836.5	956.5	1079.7	1199.8
45°	513.2	520.4	535.7	544.0	564.5	586.0	636.3	718.4	812.9	937.0	1066.4
47.5°	469.0	478.3	484.4	489.6	500.9	524.5	557.3	617.9	708.2	822.1	947.3
50°	432.1	435.2	446.5	447.5	454.7	470.1	500.9	537.8	609.6	702.0	823.1
52.5°	395.1	398.2	405.4	412.6	415.7	428.0	448.5	479.3	532.7	605.5	713.3
55°	358.2	362.3	369.5	374.6	377.7	388.0	400.3	430.0	472.1	523.4	611.7
57.5°	321.2	330.5	332.5	335.6	340.7	352.0	363.3	380.8	413.6	460.8	525.5
60°	286.3	289.4	296.6	299.7	304.8	311.0	325.3	338.7	362.3	399.2	457.7
62.5°	250.4	257.6	260.7	263.8	267.9	275.1	284.3	298.7	319.2	349.0	395.1
65°	219.6	220.7	226.8	230.9	235.0	240.2	249.4	262.7	275.1	302.8	336.6
67.5°	189.9	191.9	194.0	198.1	203.2	208.3	216.6	223.7	239.1	257.6	284.3
70°	161.1	161.1	166.3	169.3	168.3	174.5	180.6	188.8	200.1	217.6	239.1
72.5°	135.5	134.5	138.6	139.6	141.6	145.7	149.8	158.1	164.2	177.6	194.0
75°	107.8	109.8	111.9	111.9	114.9	118.0	122.1	126.2	133.4	141.6	154.0
77.5°	85.2	85.2	87.2	88.3	91.3	90.3	94.4	98.5	103.7	110.8	120.1
80°	62.6	64.7	64.7	64.7	65.7	66.7	70.8	73.9	77.0	82.1	86.2
82.5°	44.1	44.1	46.2	46.2	46.2	48.2	48.2	49.3	51.3	54.4	57.5
85°	27.7	27.7	27.7	28.7	27.7	28.7	30.8	29.8	30.8	32.8	32.8
87.5°	13.3	13.3	13.3	13.3	13.3	14.4	13.3	14.4	15.4	15.4	15.4
90°	27.8	27.3	26.8	26.6	26.0	24.8	23.6	22.4	21.2	19.3	17.4
92.5°	28.2	28.0	27.7	27.6	27.4	26.9	26.4	26.0	25.5	24.8	24.1
95°	46.1	46.4	46.6	46.7	46.1	44.9	43.8	42.6	41.4	39.8	38.1
97.5°	58.0	57.7	57.5	57.4	57.0	56.3	55.6	54.9	54.2	50.4	46.6
100°	70.3	69.8	69.3	69.1	68.2	66.3	64.4	62.5	60.6	56.6	52.6
102.5°	76.2	75.5	74.8	74.4	73.1	70.5	67.9	65.3	62.7	105.7	148.6
105°	78.8	77.9	77.0	76.5	75.2	72.6	70.0	67.4	64.8	129.2	193.7
107.5°	81.0	80.0	79.1	78.6	77.3	74.7	72.1	69.5	66.9	146.5	226.1
110°	82.0	81.1	80.2	79.7	91.5	115.1	138.7	162.3	185.9	254.1	322.4

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	83.6	82.9	82.2	81.8	132.7	234.4	336.2	437.9	539.7	543.7	547.7
115°	121.1	138.1	155.1	163.6	218.3	327.6	436.9	546.2	655.5	649.6	643.7
117.5°	406.3	468.2	530.1	561.0	577.9	611.6	645.4	679.1	712.9	708.9	704.9
120°	711.8	743.7	775.6	791.5	790.1	787.3	784.4	781.6	778.8	774.5	770.3
122.5°	848.4	848.2	847.9	847.8	847.1	845.7	844.2	842.8	841.4	836.7	832.0
125°	907.0	906.3	905.6	905.2	904.4	902.7	901.0	899.4	897.7	893.2	888.8
127.5°	961.0	960.8	960.5	960.4	959.2	956.9	954.5	952.2	949.8	946.3	942.7
130°	1010.8	1011.1	1011.3	1011.4	1010.1	1007.5	1004.9	1002.3	999.7	997.1	994.5
132.5°	1058.6	1058.9	1059.1	1059.2	1058.1	1056.0	1053.9	1051.8	1049.7	1047.1	1044.5
135°	1104.8	1105.3	1105.8	1106.0	1104.8	1102.4	1100.1	1097.7	1095.3	1093.2	1091.1
137.5°	1147.7	1148.4	1149.1	1149.5	1148.3	1146.0	1143.6	1141.3	1138.9	1136.5	1134.2
140°	1188.1	1189.2	1190.4	1191.0	1189.9	1187.8	1185.7	1183.5	1181.4	1178.8	1176.2
142.5°	1226.3	1227.4	1228.6	1229.2	1228.3	1226.4	1224.5	1222.6	1220.7	1217.6	1214.6
145°	1261.4	1262.5	1263.7	1264.3	1263.5	1261.8	1260.1	1258.5	1256.8	1252.8	1248.8
147.5°	1292.7	1293.7	1294.6	1295.1	1294.5	1293.3	1292.2	1291.0	1289.8	1285.8	1281.8
150°	1321.9	1323.0	1324.2	1324.8	1324.1	1322.7	1321.3	1319.9	1318.5	1314.7	1310.9
152.5°	1347.3	1348.9	1350.6	1351.4	1350.7	1349.3	1347.8	1346.4	1345.0	1341.5	1337.9
155°	1370.1	1372.0	1373.9	1374.8	1374.1	1372.7	1371.2	1369.8	1368.4	1365.6	1362.7
157.5°	1391.3	1393.2	1395.1	1396.0	1395.2	1393.5	1391.9	1390.2	1388.6	1386.5	1384.3
160°	1408.9	1410.5	1412.2	1413.0	1412.3	1410.9	1409.4	1408.0	1406.6	1405.2	1403.8
162.5°	1424.7	1426.8	1428.9	1430.0	1429.2	1427.5	1425.9	1424.2	1422.6	1421.4	1420.2
165°	1438.6	1440.3	1442.0	1442.8	1442.0	1440.3	1438.6	1437.0	1435.3	1434.6	1433.9
167.5°	1449.1	1451.2	1453.3	1454.4	1453.6	1451.9	1450.3	1448.6	1447.0	1446.3	1445.6
170°	1457.6	1459.7	1461.8	1462.9	1462.1	1460.4	1458.8	1457.1	1455.5	1455.0	1454.6
172.5°	1464.0	1466.1	1468.2	1469.3	1468.5	1466.8	1465.2	1463.5	1461.9	1461.4	1461.0
175°	1467.7	1470.0	1472.4	1473.6	1472.8	1471.1	1469.4	1467.8	1466.1	1465.6	1465.2
177.5°	1469.3	1471.4	1473.5	1474.6	1473.8	1472.1	1470.5	1468.8	1467.2	1467.0	1466.7
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1370.2	1365.0	1361.9	1364.0	1357.8	1342.4	1342.4	1347.6	1341.4	1335.3	1326.0
5°	1408.1	1397.9	1391.7	1390.7	1376.3	1351.7	1346.6	1341.4	1328.1	1313.7	1298.3
7.5°	1445.1	1426.6	1416.3	1409.2	1388.6	1356.8	1343.5	1332.2	1310.6	1289.1	1269.6
10°	1475.9	1449.2	1436.9	1425.6	1398.9	1358.9	1337.3	1316.8	1289.1	1261.4	1236.7
12.5°	1500.5	1469.7	1454.3	1437.9	1405.1	1352.7	1326.0	1293.2	1265.5	1228.5	1203.9
15°	1541.6	1477.9	1463.6	1448.2	1414.3	1342.4	1309.6	1272.7	1234.7	1185.4	1158.7
17.5°	1574.4	1489.2	1488.2	1455.3	1411.2	1338.3	1288.1	1239.8	1198.8	1149.5	1107.4
20°	1593.9	1506.7	1490.2	1456.4	1400.9	1310.6	1258.3	1204.9	1160.8	1101.3	1059.2
22.5°	1610.3	1531.3	1488.2	1447.1	1379.4	1301.4	1224.4	1174.1	1113.6	1048.9	1008.9
25°	1616.5	1536.4	1491.3	1444.1	1364.0	1274.7	1187.5	1133.1	1065.3	1006.8	952.4
27.5°	1617.5	1535.4	1480.0	1430.7	1342.4	1239.8	1150.5	1093.0	1018.1	950.4	896.0
30°	1607.2	1524.1	1473.8	1420.5	1321.9	1208.0	1105.4	1041.7	961.7	893.9	837.5
32.5°	1576.5	1501.5	1460.5	1402.0	1295.2	1163.9	1062.3	991.4	907.3	840.6	786.2
35°	1525.1	1473.8	1428.7	1374.3	1260.3	1122.8	1019.2	936.0	850.8	787.2	735.9
37.5°	1461.5	1433.8	1391.7	1338.3	1220.3	1085.9	970.9	878.5	793.4	731.8	681.5
40°	1375.3	1382.5	1341.4	1293.2	1173.1	1035.6	908.3	820.0	740.0	682.5	633.2
42.5°	1281.9	1311.7	1288.1	1241.9	1120.8	980.2	862.1	764.6	686.6	627.1	586.0
45°	1181.3	1232.6	1218.3	1184.4	1066.4	921.7	796.4	702.0	633.2	575.8	539.9
47.5°	1071.5	1144.4	1144.4	1119.7	1005.8	863.1	740.0	643.5	575.8	534.7	499.8
50°	959.6	1041.7	1055.1	1038.7	938.1	796.4	671.2	584.0	525.5	485.5	459.8
52.5°	842.6	938.1	962.7	954.5	866.2	732.8	614.8	529.6	476.2	441.3	418.7
55°	730.8	841.6	868.3	871.4	789.3	663.0	552.2	477.2	425.9	402.3	382.8
57.5°	625.0	731.8	761.5	766.7	711.3	599.4	493.7	428.0	381.8	362.3	346.9
60°	534.7	624.0	663.0	674.3	626.1	525.5	439.3	375.6	340.7	322.3	307.9
62.5°	460.8	532.7	573.7	576.8	555.2	460.8	382.8	329.5	299.7	283.3	276.1
65°	389.0	453.6	478.3	490.6	473.1	399.2	330.5	286.3	262.7	248.4	241.2
67.5°	331.5	372.6	393.1	409.5	392.1	336.6	281.2	245.3	227.8	213.5	209.4
70°	272.0	305.8	321.2	337.7	322.3	280.2	240.2	207.3	191.9	180.6	175.5
72.5°	217.6	244.3	258.6	268.9	259.7	224.8	191.9	169.3	158.1	149.8	146.8
75°	172.4	190.9	199.1	206.3	202.2	175.5	155.0	136.5	126.2	119.1	117.0
77.5°	131.4	144.7	154.0	156.0	150.9	133.4	116.0	104.7	96.5	92.4	90.3
80°	93.4	101.6	106.7	109.8	104.7	97.5	85.2	77.0	69.8	64.7	63.6
82.5°	62.6	66.7	70.8	69.8	67.7	61.6	54.4	50.3	47.2	43.1	43.1
85°	35.9	36.9	39.0	40.0	39.0	34.9	30.8	28.7	26.7	23.6	23.6
87.5°	15.4	16.4	16.4	17.4	15.4	15.4	13.3	11.3	11.3	10.3	9.2
90°	15.5	13.6	12.7	11.4	8.8	6.3	3.7	1.1	3.7	6.3	8.8
92.5°	23.4	22.7	22.3	22.8	23.7	24.7	25.6	26.6	25.6	24.7	23.7
95°	36.5	34.8	34.0	37.9	45.7	53.5	61.3	69.1	61.3	53.5	45.7
97.5°	42.9	39.1	37.2	46.9	66.2	85.6	104.9	124.3	104.9	85.6	66.2
100°	48.5	44.5	42.5	58.7	91.0	123.3	155.7	188.0	155.7	123.3	91.0
102.5°	191.6	234.5	256.0	256.2	256.7	257.2	257.7	258.2	257.7	257.2	256.7
105°	258.1	322.6	354.8	351.3	344.2	337.1	330.1	323.0	330.1	337.1	344.2
107.5°	305.6	385.2	425.0	422.0	416.1	410.2	404.3	398.4	404.3	410.2	416.1
110°	390.6	458.9	493.0	490.5	485.5	480.6	475.6	470.6	475.6	480.6	485.5

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	551.8	555.8	557.8	555.7	551.4	547.1	542.9	538.6	542.9	547.1	551.4
115°	637.8	631.9	628.9	626.9	622.9	618.9	614.9	610.9	614.9	618.9	622.9
117.5°	700.8	696.8	694.8	692.4	687.7	683.0	678.3	673.6	678.3	683.0	687.7
120°	766.0	761.7	759.6	757.8	754.3	750.8	747.2	743.7	747.2	750.8	754.3
122.5°	827.3	822.6	820.2	818.3	814.5	810.8	807.0	803.2	807.0	810.8	814.5
125°	884.3	879.8	877.6	876.1	873.0	869.9	866.8	863.7	866.8	869.9	873.0
127.5°	939.2	935.7	933.9	932.2	928.9	925.6	922.3	919.0	922.3	925.6	928.9
130°	991.9	989.3	988.0	986.1	982.3	978.6	974.8	971.0	974.8	978.6	982.3
132.5°	1041.9	1039.3	1038.0	1036.5	1033.4	1030.3	1027.3	1024.2	1027.3	1030.3	1033.4
135°	1089.0	1086.9	1085.8	1083.9	1080.1	1076.4	1072.6	1068.8	1072.6	1076.4	1080.1
137.5°	1131.8	1129.5	1128.3	1126.9	1124.0	1121.2	1118.3	1115.5	1118.3	1121.2	1124.0
140°	1173.6	1171.0	1169.7	1168.8	1166.9	1165.0	1163.1	1161.2	1163.1	1165.0	1166.9
142.5°	1211.5	1208.4	1206.9	1206.1	1204.4	1202.8	1201.1	1199.5	1201.1	1202.8	1204.4
145°	1244.8	1240.8	1238.8	1238.9	1239.1	1239.4	1239.6	1239.8	1239.6	1239.4	1239.1
147.5°	1277.7	1273.7	1271.7	1272.1	1272.8	1273.5	1274.2	1274.9	1274.2	1273.5	1272.8
150°	1307.2	1303.4	1301.5	1302.3	1304.0	1305.6	1307.3	1308.9	1307.3	1305.6	1304.0
152.5°	1334.4	1330.9	1329.1	1330.0	1331.9	1333.8	1335.7	1337.6	1335.7	1333.8	1331.9
155°	1359.9	1357.0	1355.6	1356.7	1358.8	1360.9	1363.1	1365.2	1363.1	1360.9	1358.8
157.5°	1382.2	1380.1	1379.0	1379.9	1381.8	1383.7	1385.6	1387.5	1385.6	1383.7	1381.8
160°	1402.4	1401.0	1400.3	1401.0	1402.4	1403.8	1405.2	1406.6	1405.2	1403.8	1402.4
162.5°	1419.1	1417.9	1417.3	1418.0	1419.4	1420.8	1422.2	1423.6	1422.2	1420.8	1419.4
165°	1433.2	1432.5	1432.1	1432.8	1434.2	1435.7	1437.1	1438.5	1437.1	1435.7	1434.2
167.5°	1444.9	1444.2	1443.8	1444.5	1445.9	1447.4	1448.8	1450.2	1448.8	1447.4	1445.9
170°	1454.1	1453.6	1453.4	1454.1	1455.5	1457.0	1458.4	1459.8	1458.4	1457.0	1455.5
172.5°	1460.5	1460.0	1459.8	1460.5	1461.9	1463.3	1464.7	1466.1	1464.7	1463.3	1461.9
175°	1464.7	1464.2	1464.0	1464.8	1466.5	1468.1	1469.8	1471.4	1469.8	1468.1	1466.5
177.5°	1466.5	1466.2	1466.1	1466.9	1468.6	1470.3	1471.9	1473.6	1471.9	1470.3	1468.6
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1320.9	1326.0	1325.0	1314.7	1303.4	1294.2	1276.8	1278.8	1272.7	1273.7	1279.8
5°	1288.1	1288.1	1283.9	1269.6	1251.1	1240.8	1221.3	1216.2	1203.9	1202.9	1201.8
7.5°	1253.2	1248.0	1242.9	1222.4	1199.8	1183.4	1156.7	1150.5	1138.2	1130.0	1125.9
10°	1212.1	1204.9	1194.7	1171.1	1143.3	1122.8	1095.1	1086.9	1063.3	1053.0	1046.9
12.5°	1166.9	1162.8	1146.4	1126.9	1081.8	1059.2	1019.2	1027.4	1003.8	983.2	980.2
15°	1121.8	1106.4	1097.2	1065.3	1010.9	1000.7	968.9	952.4	930.9	914.5	914.5
17.5°	1077.7	1054.0	1033.5	999.7	959.6	930.9	907.3	899.1	872.4	856.0	852.9
20°	1019.2	992.5	987.3	939.1	911.4	879.6	857.0	836.5	817.0	809.8	804.6
22.5°	963.7	932.9	924.7	883.7	856.0	824.1	801.6	787.2	772.8	767.7	758.5
25°	904.2	885.7	873.4	829.3	798.5	768.7	753.3	743.1	729.7	728.7	722.5
27.5°	846.7	829.3	817.0	774.9	752.3	724.6	712.3	701.0	693.8	690.7	687.6
30°	797.5	778.0	763.6	732.8	705.1	682.5	672.3	665.1	661.0	655.8	654.8
32.5°	743.1	731.8	712.3	688.7	667.1	645.6	639.4	634.3	628.1	626.1	625.0
35°	696.9	681.5	669.2	642.5	633.2	614.8	607.6	603.5	595.3	593.2	591.2
37.5°	651.7	637.4	624.0	607.6	590.1	579.9	575.8	569.6	565.5	566.5	564.5
40°	606.6	595.3	585.0	567.6	557.3	552.2	544.0	537.8	535.7	536.8	535.7
42.5°	562.4	552.2	546.0	532.7	522.4	517.3	512.1	506.0	509.1	509.1	512.1
45°	522.4	513.2	509.1	498.8	492.6	484.4	479.3	478.3	482.4	481.4	481.4
47.5°	481.4	478.3	473.1	463.9	455.7	450.6	449.5	449.5	453.6	455.7	454.7
50°	449.5	443.4	437.2	430.0	423.9	421.8	418.7	420.8	424.9	424.9	427.0
52.5°	409.5	405.4	403.4	397.2	393.1	393.1	393.1	394.1	397.2	400.3	399.2
55°	374.6	371.5	369.5	366.4	361.3	362.3	361.3	363.3	366.4	369.5	371.5
57.5°	337.7	336.6	334.6	329.5	329.5	328.4	331.5	332.5	337.7	339.7	342.8
60°	304.8	301.7	301.7	297.6	297.6	297.6	300.7	303.8	307.9	308.9	311.0
62.5°	269.9	269.9	268.9	265.8	265.8	268.9	269.9	274.0	276.1	276.1	279.2
65°	237.1	236.1	235.0	236.1	237.1	237.1	240.2	242.2	244.3	245.3	246.3
67.5°	204.2	203.2	205.3	204.2	206.3	210.4	209.4	212.5	215.5	215.5	216.6
70°	173.5	175.5	174.5	176.5	175.5	177.6	180.6	181.7	181.7	182.7	185.8
72.5°	144.7	144.7	144.7	143.7	144.7	146.8	148.8	149.8	151.9	152.9	156.0
75°	117.0	117.0	114.9	117.0	117.0	119.1	121.1	121.1	121.1	123.2	126.2
77.5°	88.3	89.3	88.3	90.3	90.3	91.3	93.4	92.4	94.4	95.4	96.5
80°	64.7	63.6	63.6	63.6	64.7	64.7	66.7	67.7	67.7	70.8	68.8
82.5°	41.1	42.1	41.1	42.1	42.1	43.1	42.1	43.1	44.1	46.2	45.2
85°	23.6	22.6	22.6	23.6	22.6	22.6	23.6	22.6	23.6	22.6	23.6
87.5°	9.2	8.2	8.2	8.2	8.2	7.2	7.2	6.2	6.2	6.2	5.1
90°	11.4	12.7	13.6	15.5	17.4	19.3	21.2	22.4	23.6	24.8	26.0
92.5°	22.8	22.3	22.7	23.4	24.1	24.8	25.5	26.0	26.4	26.9	27.4
95°	37.9	34.0	34.8	36.5	38.1	39.8	41.4	42.6	43.8	44.9	46.1
97.5°	46.9	37.2	39.1	42.9	46.6	50.4	54.2	54.9	55.6	56.3	57.0
100°	58.7	42.5	44.5	48.5	52.6	56.6	60.6	62.5	64.4	66.3	68.2
102.5°	256.2	256.0	234.5	191.6	148.6	105.7	62.7	65.3	67.9	70.5	73.1
105°	351.3	354.8	322.6	258.1	193.7	129.2	64.8	67.4	70.0	72.6	75.2
107.5°	422.0	425.0	385.2	305.6	226.1	146.5	66.9	69.5	72.1	74.7	77.3
110°	490.5	493.0	458.9	390.6	322.4	254.1	185.9	162.3	138.7	115.1	91.5

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	555.7	557.8	555.8	551.8	547.7	543.7	539.7	437.9	336.2	234.4	132.7
115°	626.9	628.9	631.9	637.8	643.7	649.6	655.5	546.2	436.9	327.6	218.3
117.5°	692.4	694.8	696.8	700.8	704.9	708.9	712.9	679.1	645.4	611.6	577.9
120°	757.8	759.6	761.7	766.0	770.3	774.5	778.8	781.6	784.4	787.3	790.1
122.5°	818.3	820.2	822.6	827.3	832.0	836.7	841.4	842.8	844.2	845.7	847.1
125°	876.1	877.6	879.8	884.3	888.8	893.2	897.7	899.4	901.0	902.7	904.4
127.5°	932.2	933.9	935.7	939.2	942.7	946.3	949.8	952.2	954.5	956.9	959.2
130°	986.1	988.0	989.3	991.9	994.5	997.1	999.7	1002.3	1004.9	1007.5	1010.1
132.5°	1036.5	1038.0	1039.3	1041.9	1044.5	1047.1	1049.7	1051.8	1053.9	1056.0	1058.1
135°	1083.9	1085.8	1086.9	1089.0	1091.1	1093.2	1095.3	1097.7	1100.1	1102.4	1104.8
137.5°	1126.9	1128.3	1129.5	1131.8	1134.2	1136.5	1138.9	1141.3	1143.6	1146.0	1148.3
140°	1168.8	1169.7	1171.0	1173.6	1176.2	1178.8	1181.4	1183.5	1185.7	1187.8	1189.9
142.5°	1206.1	1206.9	1208.4	1211.5	1214.6	1217.6	1220.7	1222.6	1224.5	1226.4	1228.3
145°	1238.9	1238.8	1240.8	1244.8	1248.8	1252.8	1256.8	1258.5	1260.1	1261.8	1263.5
147.5°	1272.1	1271.7	1273.7	1277.7	1281.8	1285.8	1289.8	1291.0	1292.2	1293.3	1294.5
150°	1302.3	1301.5	1303.4	1307.2	1310.9	1314.7	1318.5	1319.9	1321.3	1322.7	1324.1
152.5°	1330.0	1329.1	1330.9	1334.4	1337.9	1341.5	1345.0	1346.4	1347.8	1349.3	1350.7
155°	1356.7	1355.6	1357.0	1359.9	1362.7	1365.6	1368.4	1369.8	1371.2	1372.7	1374.1
157.5°	1379.9	1379.0	1380.1	1382.2	1384.3	1386.5	1388.6	1390.2	1391.9	1393.5	1395.2
160°	1401.0	1400.3	1401.0	1402.4	1403.8	1405.2	1406.6	1408.0	1409.4	1410.9	1412.3
162.5°	1418.0	1417.3	1417.9	1419.1	1420.2	1421.4	1422.6	1424.2	1425.9	1427.5	1429.2
165°	1432.8	1432.1	1432.5	1433.2	1433.9	1434.6	1435.3	1437.0	1438.6	1440.3	1442.0
167.5°	1444.5	1443.8	1444.2	1444.9	1445.6	1446.3	1447.0	1448.6	1450.3	1451.9	1453.6
170°	1454.1	1453.4	1453.6	1454.1	1454.6	1455.0	1455.5	1457.1	1458.8	1460.4	1462.1
172.5°	1460.5	1459.8	1460.0	1460.5	1461.0	1461.4	1461.9	1463.5	1465.2	1466.8	1468.5
175°	1464.8	1464.0	1464.2	1464.7	1465.2	1465.6	1466.1	1467.8	1469.4	1471.1	1472.8
177.5°	1466.9	1466.1	1466.2	1466.5	1466.7	1467.0	1467.2	1468.8	1470.5	1472.1	1473.8
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1272.7	1275.7	1268.6	1266.5	1268.6	1261.4	1263.4	1265.5	1265.5	1268.6	1270.6
5°	1198.8	1194.7	1187.5	1185.4	1183.4	1186.4	1184.4	1187.5	1188.5	1195.7	1196.7
7.5°	1125.9	1119.7	1113.6	1107.4	1105.4	1100.2	1105.4	1105.4	1112.5	1110.5	1115.6
10°	1039.7	1038.7	1030.4	1027.4	1023.3	1015.0	1026.3	1023.3	1028.4	1037.6	1039.7
12.5°	976.0	964.8	969.9	955.5	960.7	952.4	953.5	953.5	961.7	962.7	960.7
15°	915.5	906.3	892.9	886.8	883.7	879.6	892.9	893.9	887.8	902.2	897.0
17.5°	853.9	853.9	841.6	838.5	830.3	834.4	832.4	833.4	831.3	841.6	846.7
20°	800.5	795.4	791.3	792.3	782.1	780.0	778.0	780.0	787.2	794.4	796.4
22.5°	757.4	754.4	744.1	746.1	737.9	741.0	739.0	744.1	745.1	745.1	752.3
25°	716.4	712.3	713.3	709.2	706.1	706.1	703.0	706.1	710.2	712.3	713.3
27.5°	685.6	682.5	677.4	674.3	676.4	671.2	675.3	678.4	678.4	676.4	678.4
30°	648.6	650.7	650.7	640.4	644.5	642.5	645.6	647.6	647.6	648.6	646.6
32.5°	624.0	617.9	616.8	615.8	615.8	611.7	611.7	614.8	615.8	616.8	619.9
35°	591.2	591.2	586.0	589.1	585.0	586.0	585.0	586.0	588.1	585.0	588.1
37.5°	561.4	562.4	560.4	562.4	563.5	561.4	559.4	563.5	561.4	561.4	559.4
40°	535.7	534.7	535.7	535.7	535.7	536.8	534.7	534.7	534.7	532.7	530.6
42.5°	514.2	508.0	510.1	511.1	508.0	508.0	509.1	508.0	511.1	505.0	505.0
45°	483.4	481.4	482.4	482.4	484.4	481.4	483.4	484.4	481.4	480.3	478.3
47.5°	455.7	457.7	455.7	457.7	457.7	459.8	455.7	456.7	457.7	453.6	450.6
50°	428.0	428.0	431.1	430.0	431.1	429.0	429.0	428.0	429.0	427.0	423.9
52.5°	402.3	399.2	404.4	403.4	402.3	401.3	400.3	401.3	399.2	397.2	397.2
55°	370.5	370.5	373.6	374.6	374.6	372.6	370.5	371.5	370.5	369.5	368.5
57.5°	344.8	340.7	342.8	343.8	343.8	340.7	342.8	340.7	340.7	341.8	338.7
60°	312.0	312.0	310.0	313.0	313.0	311.0	311.0	312.0	310.0	308.9	307.9
62.5°	277.1	278.1	281.2	282.2	283.3	281.2	279.2	280.2	280.2	277.1	278.1
65°	247.3	249.4	253.5	252.5	250.4	251.5	249.4	250.4	247.3	248.4	245.3
67.5°	218.6	217.6	218.6	218.6	220.7	219.6	217.6	217.6	216.6	219.6	216.6
70°	187.8	187.8	187.8	187.8	188.8	189.9	187.8	185.8	186.8	184.7	183.7
72.5°	156.0	157.0	156.0	158.1	155.0	157.0	157.0	156.0	155.0	155.0	155.0
75°	126.2	128.3	125.2	126.2	125.2	127.3	126.2	126.2	124.2	123.2	124.2
77.5°	96.5	97.5	95.4	96.5	95.4	96.5	96.5	95.4	95.4	95.4	95.4
80°	68.8	69.8	68.8	67.7	66.7	68.8	66.7	67.7	68.8	67.7	69.8
82.5°	44.1	44.1	43.1	44.1	42.1	42.1	43.1	43.1	42.1	44.1	42.1
85°	21.6	21.6	23.6	21.6	20.5	20.5	20.5	21.6	20.5	22.6	21.6
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.2	4.1
90°	26.6	26.8	27.3	27.8	28.2	28.7	28.2	27.8	27.3	26.8	26.6
92.5°	27.6	27.7	28.0	28.2	28.5	28.7	28.5	28.2	28.0	27.7	27.6
95°	46.7	46.6	46.4	46.1	45.9	45.7	45.9	46.1	46.4	46.6	46.7
97.5°	57.4	57.5	57.7	58.0	58.2	58.4	58.2	58.0	57.7	57.5	57.4
100°	69.1	69.3	69.8	70.3	70.7	71.2	70.7	70.3	69.8	69.3	69.1
102.5°	74.4	74.8	75.5	76.2	76.9	77.6	76.9	76.2	75.5	74.8	74.4
105°	76.5	77.0	77.9	78.8	79.8	80.7	79.8	78.8	77.9	77.0	76.5
107.5°	78.6	79.1	80.0	81.0	81.9	82.9	81.9	81.0	80.0	79.1	78.6
110°	79.7	80.2	81.1	82.0	83.0	83.9	83.0	82.0	81.1	80.2	79.7

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	81.8	82.2	82.9	83.6	84.3	85.0	84.3	83.6	82.9	82.2	81.8
115°	163.6	155.1	138.1	121.1	104.1	87.1	104.1	121.1	138.1	155.1	163.6
117.5°	561.0	530.1	468.2	406.3	344.5	282.6	344.5	406.3	468.2	530.1	561.0
120°	791.5	775.6	743.7	711.8	680.0	648.1	680.0	711.8	743.7	775.6	791.5
122.5°	847.8	847.9	848.2	848.4	848.7	848.9	848.7	848.4	848.2	847.9	847.8
125°	905.2	905.6	906.3	907.0	907.7	908.4	907.7	907.0	906.3	905.6	905.2
127.5°	960.4	960.5	960.8	961.0	961.3	961.5	961.3	961.0	960.8	960.5	960.4
130°	1011.4	1011.3	1011.1	1010.8	1010.6	1010.4	1010.6	1010.8	1011.1	1011.3	1011.4
132.5°	1059.2	1059.1	1058.9	1058.6	1058.4	1058.2	1058.4	1058.6	1058.9	1059.1	1059.2
135°	1106.0	1105.8	1105.3	1104.8	1104.3	1103.8	1104.3	1104.8	1105.3	1105.8	1106.0
137.5°	1149.5	1149.1	1148.4	1147.7	1147.0	1146.3	1147.0	1147.7	1148.4	1149.1	1149.5
140°	1191.0	1190.4	1189.2	1188.1	1186.9	1185.7	1186.9	1188.1	1189.2	1190.4	1191.0
142.5°	1229.2	1228.6	1227.4	1226.3	1225.1	1223.9	1225.1	1226.3	1227.4	1228.6	1229.2
145°	1264.3	1263.7	1262.5	1261.4	1260.2	1259.0	1260.2	1261.4	1262.5	1263.7	1264.3
147.5°	1295.1	1294.6	1293.7	1292.7	1291.8	1290.8	1291.8	1292.7	1293.7	1294.6	1295.1
150°	1324.8	1324.2	1323.0	1321.9	1320.7	1319.5	1320.7	1321.9	1323.0	1324.2	1324.8
152.5°	1351.4	1350.6	1348.9	1347.3	1345.6	1344.0	1345.6	1347.3	1348.9	1350.6	1351.4
155°	1374.8	1373.9	1372.0	1370.1	1368.2	1366.3	1368.2	1370.1	1372.0	1373.9	1374.8
157.5°	1396.0	1395.1	1393.2	1391.3	1389.4	1387.5	1389.4	1391.3	1393.2	1395.1	1396.0
160°	1413.0	1412.2	1410.5	1408.9	1407.2	1405.6	1407.2	1408.9	1410.5	1412.2	1413.0
162.5°	1430.0	1428.9	1426.8	1424.7	1422.5	1420.4	1422.5	1424.7	1426.8	1428.9	1430.0
165°	1442.8	1442.0	1440.3	1438.6	1437.0	1435.3	1437.0	1438.6	1440.3	1442.0	1442.8
167.5°	1454.4	1453.3	1451.2	1449.1	1447.0	1444.9	1447.0	1449.1	1451.2	1453.3	1454.4
170°	1462.9	1461.8	1459.7	1457.6	1455.5	1453.4	1455.5	1457.6	1459.7	1461.8	1462.9
172.5°	1469.3	1468.2	1466.1	1464.0	1461.9	1459.8	1461.9	1464.0	1466.1	1468.2	1469.3
175°	1473.6	1472.4	1470.0	1467.7	1465.3	1462.9	1465.3	1467.7	1470.0	1472.4	1473.6
177.5°	1474.6	1473.5	1471.4	1469.3	1467.2	1465.1	1467.2	1469.3	1471.4	1473.5	1474.6
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1267.5	1275.7	1272.7	1261.4	1274.7	1274.7	1283.9	1283.9	1295.2	1299.3	1305.5
5°	1195.7	1201.8	1207.0	1201.8	1211.1	1225.4	1233.7	1240.8	1256.2	1262.4	1271.6
7.5°	1118.7	1130.0	1135.1	1135.1	1150.5	1166.9	1183.4	1193.6	1215.2	1223.4	1232.6
10°	1043.8	1057.1	1067.4	1066.4	1092.0	1102.3	1122.8	1146.4	1168.0	1180.3	1193.6
12.5°	964.8	971.9	986.3	1006.8	1013.0	1031.5	1055.1	1084.8	1123.8	1135.1	1154.6
15°	899.1	918.6	929.9	939.1	953.5	970.9	996.6	1025.3	1064.3	1088.9	1109.5
17.5°	843.6	869.3	876.5	874.4	892.9	919.6	949.4	970.9	1005.8	1035.6	1055.1
20°	798.5	808.8	821.1	826.2	840.6	869.3	898.0	922.7	951.4	975.0	997.6
22.5°	753.3	761.5	771.8	781.0	792.3	808.8	836.5	867.3	895.0	917.5	943.2
25°	716.4	721.5	730.8	737.9	750.3	761.5	781.0	814.9	847.8	861.1	883.7
27.5°	680.5	684.6	690.7	698.9	705.1	716.4	733.8	761.5	795.4	808.8	839.5
30°	648.6	651.7	657.9	662.0	665.1	678.4	691.8	713.3	739.0	757.4	780.0
32.5°	618.9	622.0	628.1	629.1	633.2	640.4	652.8	672.3	694.8	710.2	729.7
35°	586.0	588.1	594.2	596.3	599.4	605.5	614.8	629.1	649.7	661.0	678.4
37.5°	560.4	559.4	563.5	566.5	570.6	573.7	576.8	591.2	606.6	616.8	630.2
40°	532.7	530.6	531.6	535.7	537.8	541.9	541.9	556.3	566.5	574.7	585.0
42.5°	505.0	503.9	501.9	503.9	506.0	507.0	508.0	518.3	528.6	535.7	547.0
45°	477.2	476.2	474.2	475.2	475.2	477.2	480.3	484.4	491.6	497.8	503.9
47.5°	451.6	449.5	446.5	445.4	447.5	447.5	447.5	451.6	458.8	460.8	467.0
50°	424.9	421.8	417.7	415.7	415.7	414.6	416.7	417.7	423.9	425.9	431.1
52.5°	396.2	394.1	390.0	385.9	386.9	384.9	385.9	386.9	389.0	392.1	395.1
55°	367.4	363.3	360.2	359.2	356.1	356.1	353.1	357.2	356.1	357.2	361.3
57.5°	339.7	335.6	330.5	328.4	325.3	324.3	322.3	321.2	322.3	325.3	328.4
60°	306.9	304.8	301.7	298.7	296.6	293.5	291.5	291.5	290.5	290.5	291.5
62.5°	275.1	274.0	269.9	268.9	266.8	264.8	261.7	259.7	259.7	261.7	262.7
65°	244.3	243.2	240.2	239.1	234.0	232.0	230.9	229.9	227.8	227.8	227.8
67.5°	215.5	212.5	212.5	207.3	203.2	201.2	199.1	198.1	198.1	198.1	199.1
70°	183.7	183.7	180.6	177.6	173.5	174.5	171.4	168.3	168.3	166.3	167.3
72.5°	152.9	151.9	148.8	147.8	144.7	141.6	139.6	141.6	138.6	137.5	138.6
75°	123.2	122.1	120.1	118.0	119.1	116.0	112.9	111.9	111.9	109.8	109.8
77.5°	94.4	96.5	92.4	91.3	89.3	87.2	86.2	85.2	85.2	85.2	87.2
80°	65.7	66.7	66.7	64.7	65.7	62.6	62.6	62.6	59.5	60.6	61.6
82.5°	42.1	42.1	41.1	42.1	41.1	41.1	40.0	40.0	39.0	39.0	40.0
85°	23.6	22.6	21.6	23.6	22.6	22.6	21.6	21.6	21.6	21.6	21.6
87.5°	5.1	6.2	6.2	6.2	6.2	7.2	7.2	7.2	8.2	8.2	8.2
90°	26.0	24.8	23.6	22.4	21.2	19.3	17.4	15.5	13.6	12.7	11.4
92.5°	27.4	26.9	26.4	26.0	25.5	24.8	24.1	23.4	22.7	22.3	22.8
95°	46.1	44.9	43.8	42.6	41.4	39.8	38.1	36.5	34.8	34.0	37.9
97.5°	57.0	56.3	55.6	54.9	54.2	50.4	46.6	42.9	39.1	37.2	46.9
100°	68.2	66.3	64.4	62.5	60.6	56.6	52.6	48.5	44.5	42.5	58.7
102.5°	73.1	70.5	67.9	65.3	62.7	105.7	148.6	191.6	234.5	256.0	256.2
105°	75.2	72.6	70.0	67.4	64.8	129.2	193.7	258.1	322.6	354.8	351.3
107.5°	77.3	74.7	72.1	69.5	66.9	146.5	226.1	305.6	385.2	425.0	422.0
110°	91.5	115.1	138.7	162.3	185.9	254.1	322.4	390.6	458.9	493.0	490.5

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	132.7	234.4	336.2	437.9	539.7	543.7	547.7	551.8	555.8	557.8	555.7
115°	218.3	327.6	436.9	546.2	655.5	649.6	643.7	637.8	631.9	628.9	626.9
117.5°	577.9	611.6	645.4	679.1	712.9	708.9	704.9	700.8	696.8	694.8	692.4
120°	790.1	787.3	784.4	781.6	778.8	774.5	770.3	766.0	761.7	759.6	757.8
122.5°	847.1	845.7	844.2	842.8	841.4	836.7	832.0	827.3	822.6	820.2	818.3
125°	904.4	902.7	901.0	899.4	897.7	893.2	888.8	884.3	879.8	877.6	876.1
127.5°	959.2	956.9	954.5	952.2	949.8	946.3	942.7	939.2	935.7	933.9	932.2
130°	1010.1	1007.5	1004.9	1002.3	999.7	997.1	994.5	991.9	989.3	988.0	986.1
132.5°	1058.1	1056.0	1053.9	1051.8	1049.7	1047.1	1044.5	1041.9	1039.3	1038.0	1036.5
135°	1104.8	1102.4	1100.1	1097.7	1095.3	1093.2	1091.1	1089.0	1086.9	1085.8	1083.9
137.5°	1148.3	1146.0	1143.6	1141.3	1138.9	1136.5	1134.2	1131.8	1129.5	1128.3	1126.9
140°	1189.9	1187.8	1185.7	1183.5	1181.4	1178.8	1176.2	1173.6	1171.0	1169.7	1168.8
142.5°	1228.3	1226.4	1224.5	1222.6	1220.7	1217.6	1214.6	1211.5	1208.4	1206.9	1206.1
145°	1263.5	1261.8	1260.1	1258.5	1256.8	1252.8	1248.8	1244.8	1240.8	1238.8	1238.9
147.5°	1294.5	1293.3	1292.2	1291.0	1289.8	1285.8	1281.8	1277.7	1273.7	1271.7	1272.1
150°	1324.1	1322.7	1321.3	1319.9	1318.5	1314.7	1310.9	1307.2	1303.4	1301.5	1302.3
152.5°	1350.7	1349.3	1347.8	1346.4	1345.0	1341.5	1337.9	1334.4	1330.9	1329.1	1330.0
155°	1374.1	1372.7	1371.2	1369.8	1368.4	1365.6	1362.7	1359.9	1357.0	1355.6	1356.7
157.5°	1395.2	1393.5	1391.9	1390.2	1388.6	1386.5	1384.3	1382.2	1380.1	1379.0	1379.9
160°	1412.3	1410.9	1409.4	1408.0	1406.6	1405.2	1403.8	1402.4	1401.0	1400.3	1401.0
162.5°	1429.2	1427.5	1425.9	1424.2	1422.6	1421.4	1420.2	1419.1	1417.9	1417.3	1418.0
165°	1442.0	1440.3	1438.6	1437.0	1435.3	1434.6	1433.9	1433.2	1432.5	1432.1	1432.8
167.5°	1453.6	1451.9	1450.3	1448.6	1447.0	1446.3	1445.6	1444.9	1444.2	1443.8	1444.5
170°	1462.1	1460.4	1458.8	1457.1	1455.5	1455.0	1454.6	1454.1	1453.6	1453.4	1454.1
172.5°	1468.5	1466.8	1465.2	1463.5	1461.9	1461.4	1461.0	1460.5	1460.0	1459.8	1460.5
175°	1472.8	1471.1	1469.4	1467.8	1466.1	1465.6	1465.2	1464.7	1464.2	1464.0	1464.8
177.5°	1473.8	1472.1	1470.5	1468.8	1467.2	1467.0	1466.7	1466.5	1466.2	1466.1	1466.9
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1335.3	1335.3	1335.3	1335.3
2.5°	1310.6	1310.6	1326.0	1342.4
5°	1281.9	1289.1	1313.7	1336.3
7.5°	1254.2	1266.5	1297.3	1326.0
10°	1220.3	1236.7	1274.7	1308.6
12.5°	1187.5	1202.9	1247.0	1285.0
15°	1141.3	1160.8	1208.0	1255.2
17.5°	1095.1	1114.6	1172.1	1227.5
20°	1040.7	1066.4	1131.0	1204.9
22.5°	990.4	1022.2	1094.1	1153.6
25°	935.0	984.3	1051.0	1127.9
27.5°	885.7	935.0	1002.7	1080.7
30°	830.3	880.6	950.4	1022.2
32.5°	776.9	823.1	890.9	979.1
35°	721.5	765.6	831.3	920.6
37.5°	671.2	714.3	786.2	868.3
40°	622.0	667.1	728.7	810.8
42.5°	575.8	615.8	671.2	753.3
45°	533.7	562.4	613.7	690.7
47.5°	489.6	515.2	562.4	639.4
50°	448.5	470.1	511.1	583.0
52.5°	408.5	427.0	464.9	522.4
55°	372.6	390.0	417.7	474.2
57.5°	335.6	349.0	375.6	420.8
60°	299.7	312.0	333.6	370.5
62.5°	263.8	274.0	294.6	324.3
65°	232.0	240.2	255.6	281.2
67.5°	201.2	206.3	218.6	239.1
70°	171.4	175.5	185.8	202.2
72.5°	139.6	143.7	155.0	166.3
75°	112.9	113.9	122.1	131.4
77.5°	88.3	87.2	93.4	100.6
80°	60.6	63.6	68.8	71.8
82.5°	41.1	42.1	44.1	46.2
85°	22.6	23.6	23.6	26.7
87.5°	9.2	10.3	10.3	11.3
90°	8.8	6.3	3.7	1.1
92.5°	23.7	24.7	25.6	26.6
95°	45.7	53.5	61.3	69.1
97.5°	66.2	85.6	104.9	124.3
100°	91.0	123.3	155.7	188.0
102.5°	256.7	257.2	257.7	258.2
105°	344.2	337.1	330.1	323.0
107.5°	416.1	410.2	404.3	398.4
110°	485.5	480.6	475.6	470.6

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	551.4	547.1	542.9	538.6
115°	622.9	618.9	614.9	610.9
117.5°	687.7	683.0	678.3	673.6
120°	754.3	750.8	747.2	743.7
122.5°	814.5	810.8	807.0	803.2
125°	873.0	869.9	866.8	863.7
127.5°	928.9	925.6	922.3	919.0
130°	982.3	978.6	974.8	971.0
132.5°	1033.4	1030.3	1027.3	1024.2
135°	1080.1	1076.4	1072.6	1068.8
137.5°	1124.0	1121.2	1118.3	1115.5
140°	1166.9	1165.0	1163.1	1161.2
142.5°	1204.4	1202.8	1201.1	1199.5
145°	1239.1	1239.4	1239.6	1239.8
147.5°	1272.8	1273.5	1274.2	1274.9
150°	1304.0	1305.6	1307.3	1308.9
152.5°	1331.9	1333.8	1335.7	1337.6
155°	1358.8	1360.9	1363.1	1365.2
157.5°	1381.8	1383.7	1385.6	1387.5
160°	1402.4	1403.8	1405.2	1406.6
162.5°	1419.4	1420.8	1422.2	1423.6
165°	1434.2	1435.7	1437.1	1438.5
167.5°	1445.9	1447.4	1448.8	1450.2
170°	1455.5	1457.0	1458.4	1459.8
172.5°	1461.9	1463.3	1464.7	1466.1
175°	1466.5	1468.1	1469.8	1471.4
177.5°	1468.6	1470.3	1471.9	1473.6
180°	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P998699

CATALOG NUMBER: SA2XXDIP-B675D1080UB30-4F0-XX-W2A-A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.50	16.26	16.54	17.30	18.70	13.00	13.75	14.04	14.80	16.20
	3H	16.31	16.99	17.36	18.04	19.46	14.33	15.01	15.38	16.06	17.48
	4H	16.47	17.11	17.53	18.17	19.59	14.79	15.43	15.85	16.49	17.91
	6H	16.51	17.10	17.58	18.16	19.60	15.09	15.68	16.16	16.74	18.18
	8H	16.49	17.05	17.56	18.12	19.56	15.17	15.74	16.25	16.81	18.24
	12H	16.45	16.98	17.53	18.05	19.50	15.21	15.75	16.29	16.81	18.27
4H	2H	15.53	16.17	16.60	17.23	18.66	13.43	14.07	14.50	15.12	16.55
	3H	16.50	17.04	17.58	18.12	19.56	14.88	15.42	15.96	16.50	17.94
	4H	16.78	17.27	17.86	18.34	19.80	15.41	15.90	16.49	16.97	18.44
	6H	16.90	17.32	17.99	18.42	19.87	15.79	16.21	16.88	17.30	18.76
	8H	16.90	17.29	17.99	18.38	19.85	15.90	16.29	16.98	17.37	18.84
	12H	16.86	17.21	17.96	18.31	19.79	15.95	16.30	17.05	17.40	18.88
8H	4H	16.78	17.17	17.87	18.26	19.73	15.55	15.94	16.64	17.02	18.50
	6H	16.95	17.28	18.06	18.40	19.87	15.98	16.30	17.09	17.43	18.90
	8H	16.98	17.27	18.10	18.38	19.86	16.13	16.41	17.25	17.52	19.01
	12H	16.96	17.21	18.08	18.32	19.84	16.22	16.46	17.34	17.57	19.10
12H	4H	16.73	17.08	17.84	18.18	19.66	15.52	15.87	16.62	16.97	18.45
	6H	16.93	17.21	18.05	18.32	19.81	15.98	16.26	17.10	17.37	18.86
	8H	16.96	17.21	18.08	18.31	19.84	16.13	16.38	17.25	17.48	19.01