

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999914

Luminaire Tested: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999914
REPORT IS A COMBINATION OF REPORTS P988471 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3666.0 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999914

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P999914

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	59
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	53	49	49	47	44
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	41	37	34
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	25
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	48	37	30	26	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18026	18026	18026
5°	18056	17149	17022
10°	17877	16265	15728
15°	17631	15221	14253
20°	17306	14034	12712
25°	16973	12817	11299
30°	16526	11630	9758
35°	16088	10434	8435
40°	15643	9259	7072
45°	15124	8046	5883
50°	14590	6877	4789
55°	14032	5708	3802
60°	13385	4565	2876
65°	12638	3480	2339
70°	11736	2524	1859
75°	10606	1925	1420
80°	8966	1304	952
85°	6258	598	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15124 cd/sqm

TEST NUMBER: P999914

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.7	2.9
10°-20°	293.0	8.0
20°-30°	411.3	11.2
30°-40°	448.4	12.2
40°-50°	412.1	11.2
50°-60°	323.6	8.8
60°-70°	210.7	5.7
70°-80°	108.4	3.0
80°-90°	28.5	0.8
90°-100°	14.9	0.4
100°-110°	55.5	1.5
110°-120°	147.1	4.0
120°-130°	244.0	6.7
130°-140°	259.2	7.1
140°-150°	240.9	6.6
150°-160°	193.7	5.3
160°-170°	124.8	3.4
170°-180°	43.0	1.2
0°-30°	811.1	22.1
0°-40°	1259.4	34.4
0°-60°	1995.2	54.4
0°-90°	2342.8	63.9
90°-120°	217.5	5.9
90°-150°	961.7	26.2
90°-180°	1323.0	36.1
0°-180°	3666.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1120	1130	1126	108
15°	1083	1072	1037	1017	1007	305
25°	983	950	882	840	824	452
35°	847	795	704	639	616	530
45°	692	624	515	442	417	535
55°	527	446	335	273	254	471
65°	356	272	179	144	141	352
75°	190	118	82	75	74	201
85°	44	23	20	20	20	51
90°	0	4	6	8	9	3
95°	21	10	13	14	14	25
105°	99	109	20	24	25	106
115°	188	193	202	50	27	185
125°	266	270	276	278	279	237
135°	329	334	337	340	339	254
145°	381	381	386	389	387	238
155°	420	417	421	423	420	193
165°	442	440	441	444	441	125
175°	452	450	451	453	450	43
180°	451	451	451	451	451	

TEST NUMBER: P999914

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1138.8	1138.8	1138.8	1138.8	1138.8
2.5°	1143.9	1138.8	1127.4	1137.7	1135.7
5°	1138.8	1133.6	1120.2	1129.5	1126.4
7.5°	1129.5	1123.3	1108.9	1113.0	1107.8
10°	1117.1	1109.9	1089.3	1086.2	1080.0
12.5°	1101.7	1092.4	1064.6	1058.4	1047.0
15°	1083.1	1071.8	1036.7	1017.2	1006.8
17.5°	1061.5	1045.0	1001.7	979.0	962.5
20°	1036.7	1016.1	964.6	938.8	916.2
22.5°	1009.9	986.2	926.5	891.4	876.0
25°	983.1	950.2	882.2	839.9	824.4
27.5°	951.2	916.2	840.9	792.5	768.8
30°	917.2	878.0	795.6	743.0	715.2
32.5°	884.2	836.8	752.3	690.5	664.7
35°	847.1	794.6	703.9	638.9	616.3
37.5°	811.0	754.4	658.5	587.4	561.6
40°	772.9	711.1	611.1	537.9	511.2
42.5°	733.8	667.8	563.7	487.4	461.7
45°	692.5	623.5	515.3	442.1	417.4
47.5°	653.4	580.2	468.9	395.7	373.1
50°	610.1	536.9	423.6	352.4	330.8
52.5°	567.8	490.5	380.3	312.3	292.7
55°	526.6	446.2	334.9	273.1	253.5
57.5°	484.4	401.9	294.7	237.0	220.5
60°	441.1	358.6	252.5	199.9	183.4
62.5°	398.8	316.4	216.4	166.9	158.7
65°	355.5	272.1	179.3	144.3	141.2
67.5°	314.3	230.8	144.3	126.8	123.7
70°	271.0	190.7	119.5	109.2	105.1
72.5°	229.8	153.6	100.0	91.7	89.7
75°	189.6	117.5	82.4	75.2	74.2
77.5°	149.4	83.5	64.9	60.8	58.7
80°	112.3	59.8	49.5	45.3	45.3
82.5°	78.3	40.2	34.0	31.9	31.9
85°	44.3	22.7	19.6	19.6	19.6
87.5°	16.5	8.2	8.2	7.2	7.2
90°	0.3	3.9	6.5	8.2	8.8
92.5°	8.2	6.9	7.8	8.5	8.8
95°	21.2	10.5	12.7	14.4	14.0
97.5°	38.2	11.4	16.7	17.6	18.0
100°	57.8	13.1	18.6	21.2	21.9
102.5°	79.4	78.7	19.3	22.9	23.8
105°	99.3	109.1	19.9	23.5	24.8
107.5°	122.5	130.6	20.6	24.2	25.5
110°	144.7	151.5	57.2	24.5	25.8



TEST NUMBER: P999914

CATALOG NUMBER: SA2XXRDIP-B675D330UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.6	171.5	165.9	25.1	26.1
115°	187.8	193.3	201.5	50.3	26.8
117.5°	207.1	213.6	219.1	172.4	86.9
120°	228.6	233.5	239.4	243.3	199.2
122.5°	246.9	252.1	258.7	260.6	260.9
125°	265.5	269.8	276.0	278.3	279.2
127.5°	282.5	287.1	292.0	295.2	295.6
130°	298.5	303.7	307.3	310.9	310.6
132.5°	314.8	319.1	322.7	325.6	325.3
135°	328.6	333.8	336.7	340.0	339.3
137.5°	342.9	346.8	350.1	353.4	352.4
140°	357.0	359.6	363.2	366.1	364.5
142.5°	368.7	371.0	375.3	377.9	376.2
145°	381.1	380.8	386.4	388.6	387.0
147.5°	391.9	390.9	396.5	398.1	396.8
150°	402.4	400.1	405.3	407.3	405.6
152.5°	411.2	408.6	413.5	415.4	413.1
155°	419.7	416.7	420.7	422.6	420.0
157.5°	426.5	423.9	426.9	429.1	426.5
160°	432.4	430.5	432.4	434.4	432.1
162.5°	437.6	435.7	437.3	439.6	436.7
165°	442.2	440.2	441.2	443.5	441.2
167.5°	445.8	443.8	444.8	447.1	444.2
170°	448.7	446.8	447.4	449.7	446.8
172.5°	450.7	448.7	449.4	451.7	448.7
175°	452.3	450.0	450.7	453.0	449.7
177.5°	453.0	450.7	451.0	453.3	450.4
180°	451.4	451.4	451.4	451.4	451.4

(END OF REPORT)