

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999952

Luminaire Tested: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999952
REPORT IS A COMBINATION OF REPORTS P988509 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4414.0 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999952

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999952

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50
2	90	83	77	72	83	77	72	68	66	63	59	56	53	51	47	45	43
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	26
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	26	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19
10	49	37	30	25	45	35	28	24	30	25	22	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17795	17795	17795
5°	17824	16930	16805
10°	17648	16056	15527
15°	17405	15027	14070
20°	17086	13854	12548
25°	16757	12653	11155
30°	16314	11481	9633
35°	15883	10299	8327
40°	15442	9141	6981
45°	14932	7943	5807
50°	14403	6788	4728
55°	13853	5634	3754
60°	13212	4507	2840
65°	12478	3435	2309
70°	11589	2492	1836
75°	10472	1901	1401
80°	8854	1286	942
85°	6173	588	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14932 cd/sqm

TEST NUMBER: P999952

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	2.4
10°-20°	289.2	6.6
20°-30°	406.1	9.2
30°-40°	442.6	10.0
40°-50°	406.8	9.2
50°-60°	319.5	7.2
60°-70°	208.0	4.7
70°-80°	107.1	2.4
80°-90°	28.6	0.6
90°-100°	23.6	0.5
100°-110°	88.1	2.0
110°-120°	233.6	5.3
120°-130°	387.5	8.8
130°-140°	411.6	9.3
140°-150°	382.5	8.7
150°-160°	307.5	7.0
160°-170°	198.2	4.5
170°-180°	68.2	1.5
0°-30°	800.7	18.1
0°-40°	1243.3	28.2
0°-60°	1969.7	44.6
0°-90°	2313.3	52.4
90°-120°	345.3	7.8
90°-150°	1526.9	34.6
90°-180°	2101.0	47.6
0°-180°	4414.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1124	1119	1106	1115	1112	107
15°	1069	1058	1024	1004	994	301
25°	971	938	871	829	814	446
35°	836	784	695	631	608	523
45°	684	616	509	436	412	528
55°	520	440	331	270	250	465
65°	351	269	177	142	139	348
75°	187	116	81	74	73	198
85°	44	22	19	19	19	50
90°	0	6	10	13	14	4
95°	34	17	20	23	22	40
105°	158	173	32	37	39	168
115°	298	307	320	80	42	293
125°	422	428	438	442	443	376
135°	522	530	535	540	539	403
145°	605	605	613	617	614	378
155°	666	662	668	671	667	307
165°	702	699	700	704	700	198
175°	718	714	716	719	714	68
180°	717	717	717	717	717	

TEST NUMBER: P999952

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1124.2	1124.2	1124.2	1124.2	1124.2
2.5°	1129.3	1124.2	1113.0	1123.2	1121.1
5°	1124.2	1119.1	1105.9	1115.0	1112.0
7.5°	1115.0	1108.9	1094.7	1098.7	1093.6
10°	1102.8	1095.7	1075.3	1072.3	1066.2
12.5°	1087.5	1078.4	1050.9	1044.8	1033.6
15°	1069.2	1058.0	1023.5	1004.1	993.9
17.5°	1047.9	1031.6	988.9	966.5	950.2
20°	1023.5	1003.1	952.2	926.8	904.4
22.5°	997.0	973.6	914.6	880.0	864.7
25°	970.6	938.0	870.9	829.1	813.9
27.5°	939.0	904.4	830.2	782.3	758.9
30°	905.4	866.8	785.4	733.5	706.0
32.5°	872.9	826.1	742.7	681.6	656.2
35°	836.3	784.4	694.8	630.8	608.4
37.5°	800.7	744.7	650.1	579.9	554.5
40°	763.0	702.0	603.3	531.1	504.6
42.5°	724.4	659.2	556.5	481.2	455.8
45°	683.7	615.5	508.7	436.4	412.0
47.5°	645.0	572.8	462.9	390.7	368.3
50°	602.3	530.0	418.1	347.9	326.6
52.5°	560.6	484.3	375.4	308.3	288.9
55°	519.9	440.5	330.6	269.6	250.3
57.5°	478.2	396.8	291.0	234.0	217.7
60°	435.4	354.0	249.3	197.4	181.1
62.5°	393.7	312.3	213.6	164.8	156.7
65°	351.0	268.6	177.0	142.4	139.4
67.5°	310.3	227.9	142.4	125.1	122.1
70°	267.6	188.2	118.0	107.8	103.8
72.5°	226.9	151.6	98.7	90.5	88.5
75°	187.2	116.0	81.4	74.3	73.2
77.5°	147.5	82.4	64.1	60.0	58.0
80°	110.9	59.0	48.8	44.8	44.8
82.5°	77.3	39.7	33.6	31.5	31.5
85°	43.7	22.4	19.3	19.3	19.3
87.5°	16.3	8.1	8.1	7.1	7.1
90°	0.5	6.2	10.4	13.0	14.0
92.5°	13.0	10.9	12.4	13.5	14.0
95°	33.7	16.6	20.2	22.8	22.3
97.5°	60.7	18.1	26.4	28.0	28.5
100°	91.8	20.7	29.6	33.7	34.7
102.5°	126.0	125.0	30.6	36.3	37.9
105°	157.6	173.2	31.6	37.3	39.4
107.5°	194.4	207.4	32.7	38.4	40.4
110°	229.7	240.6	90.7	38.9	41.0



TEST NUMBER: P999952

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	262.9	272.2	263.4	39.9	41.5
115°	298.1	307.0	319.9	79.8	42.5
117.5°	328.7	339.1	347.9	273.8	137.9
120°	363.0	370.7	380.1	386.3	316.3
122.5°	392.0	400.3	410.7	413.8	414.3
125°	421.5	428.3	438.1	441.8	443.3
127.5°	448.5	455.8	463.5	468.7	469.2
130°	473.9	482.2	487.9	493.6	493.1
132.5°	499.8	506.6	512.3	516.9	516.4
135°	521.6	529.9	534.6	539.8	538.7
137.5°	544.4	550.7	555.8	561.0	559.5
140°	566.7	570.9	576.6	581.2	578.7
142.5°	585.4	589.0	595.8	599.9	597.3
145°	605.1	604.6	613.4	617.0	614.4
147.5°	622.2	620.6	629.5	632.1	630.0
150°	638.8	635.2	643.5	646.6	644.0
152.5°	652.8	648.6	656.4	659.5	655.9
155°	666.3	661.6	667.8	670.9	666.8
157.5°	677.2	673.0	677.7	681.3	677.2
160°	686.5	683.4	686.5	689.6	686.0
162.5°	694.8	691.7	694.3	697.9	693.2
165°	702.1	698.9	700.5	704.1	700.5
167.5°	707.8	704.6	706.2	709.8	705.2
170°	712.4	709.3	710.4	714.0	709.3
172.5°	715.5	712.4	713.5	717.1	712.4
175°	718.1	714.5	715.5	719.2	714.0
177.5°	719.2	715.5	716.1	719.7	715.0
180°	716.6	716.6	716.6	716.6	716.6

(END OF REPORT)