

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998717

Luminaire Tested: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998717
REPORT IS A COMBINATION OF REPORTS P984461 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6757.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21015	21015	21015	21015
5°	21065	22407	21146	17826
10°	20820	24460	20951	14697
15°	20316	25800	20597	12380
20°	19999	24224	19999	10760
25°	19360	20811	19448	9622
30°	18312	16359	18661	8716
35°	17383	11312	17674	7975
40°	16315	8542	16501	7384
45°	14998	7019	15244	6746
50°	13860	6160	13884	6174
55°	12561	5249	12644	5555
60°	11179	4385	11334	4849
65°	9940	3566	10121	4141
70°	8705	2799	8926	3340
75°	7306	2031	7591	2421
80°	5700	1287	6108	1438
85°	3743	649	4040	480

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21722 cd/sqm

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.4	1.9
10°-20°	368.0	5.4
20°-30°	534.1	7.9
30°-40°	563.1	8.3
40°-50°	498.3	7.4
50°-60°	397.9	5.9
60°-70°	270.2	4.0
70°-80°	138.3	2.0
80°-90°	36.6	0.5
90°-100°	84.6	1.3
100°-110°	269.0	4.0
110°-120°	460.3	6.8
120°-130°	605.3	9.0
130°-140°	679.5	10.1
140°-150°	666.3	9.9
150°-160°	558.9	8.3
160°-170°	370.7	5.5
170°-180°	129.6	1.9
0°-30°	1028.6	15.2
0°-40°	1591.7	23.6
0°-60°	2487.8	36.8
0°-90°	2932.9	43.4
90°-120°	813.9	12.0
90°-150°	2764.9	40.9
90°-180°	3824.0	56.6
0°-180°	6757.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1329	1483	1334	1180	1329	126
15°	1248	1822	1265	874	1248	352
25°	1121	1518	1126	702	1121	513
35°	915	826	931	583	915	573
45°	687	498	698	479	687	533
55°	471	350	474	370	471	421
65°	280	215	285	250	280	278
75°	131	106	136	126	131	140
85°	26	28	29	20	26	31
90°	1	39	1	39	1	5
95°	60	72	60	72	60	67
105°	248	256	248	256	248	262
115°	462	462	462	462	462	457
125°	672	674	672	674	672	600
135°	869	880	869	880	869	672
145°	1055	1066	1055	1066	1055	659
155°	1206	1215	1206	1215	1206	555
165°	1312	1314	1312	1314	1312	370
175°	1366	1361	1366	1361	1366	130
180°	1368	1368	1368	1368	1368	

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1334.7	1337.8	1342.9	1343.9	1354.1	1362.3	1371.4	1371.4	1374.5	1373.5	1365.3
5°	1328.6	1337.8	1351.0	1362.3	1380.6	1388.8	1401.0	1410.2	1418.4	1424.5	1423.5
7.5°	1318.4	1334.7	1354.1	1375.5	1400.0	1414.3	1431.6	1448.0	1459.2	1469.4	1476.5
10°	1301.0	1328.6	1355.1	1383.7	1415.3	1434.7	1455.1	1476.5	1493.9	1513.3	1531.6
12.5°	1277.6	1317.4	1350.0	1387.8	1426.5	1448.0	1480.6	1496.9	1530.6	1579.6	1592.9
15°	1248.0	1302.0	1332.7	1380.6	1431.6	1449.0	1493.9	1520.4	1589.8	1620.4	1657.2
17.5°	1220.4	1280.6	1321.4	1376.5	1426.5	1460.2	1504.1	1558.2	1616.3	1660.2	1701.0
20°	1198.0	1256.1	1305.1	1366.3	1429.6	1472.5	1518.4	1583.7	1646.9	1691.8	1723.5
22.5°	1146.9	1221.4	1278.6	1346.9	1423.5	1482.7	1526.5	1598.0	1666.3	1693.9	1721.4
25°	1121.4	1185.7	1252.0	1329.6	1419.4	1489.8	1527.6	1607.2	1667.4	1677.6	1683.7
27.5°	1074.5	1146.9	1224.5	1313.3	1418.4	1477.6	1525.5	1598.0	1645.9	1638.8	1620.4
30°	1016.3	1105.1	1190.8	1286.7	1404.1	1468.4	1513.3	1579.6	1604.1	1567.4	1534.7
32.5°	973.5	1057.1	1152.0	1263.3	1387.8	1449.0	1492.9	1544.9	1550.0	1483.7	1428.6
35°	915.3	1008.2	1115.3	1232.7	1360.2	1415.3	1456.1	1487.8	1463.3	1370.4	1305.1
37.5°	863.3	955.1	1069.4	1188.8	1322.5	1376.5	1409.2	1414.3	1354.1	1272.5	1176.5
40°	806.1	901.0	1020.4	1145.9	1280.6	1327.6	1348.0	1332.7	1245.9	1151.0	1039.8
42.5°	749.0	842.9	971.4	1100.0	1227.6	1267.4	1275.5	1233.7	1127.6	1016.3	887.8
45°	686.7	784.7	913.3	1042.9	1166.3	1188.8	1189.8	1129.6	1004.1	887.8	768.4
47.5°	635.7	726.5	854.1	983.7	1087.8	1103.1	1096.9	1027.6	890.8	760.2	656.1
50°	579.6	666.3	792.9	920.4	1009.2	1013.3	998.0	899.0	765.3	645.9	563.3
52.5°	519.4	607.1	723.5	845.9	925.5	919.4	889.8	783.7	658.2	559.2	495.9
55°	471.4	549.0	658.2	777.6	833.7	816.3	783.7	675.5	576.5	492.9	437.8
57.5°	418.4	486.7	593.9	698.0	730.6	714.3	681.6	580.6	488.8	425.5	388.8
60°	368.4	430.6	524.5	611.2	636.7	619.4	581.6	490.8	424.5	371.4	343.9
62.5°	322.5	376.5	455.1	534.7	544.9	527.6	494.9	421.4	364.3	322.5	302.0
65°	279.6	330.6	393.9	454.1	463.3	444.9	411.2	358.2	310.2	283.7	264.3
67.5°	237.8	278.6	334.7	378.6	383.7	366.3	338.8	295.9	266.3	237.8	223.5
70°	201.0	231.6	275.5	311.2	313.3	296.9	282.7	243.9	221.4	201.0	189.8
72.5°	165.3	186.7	220.4	246.9	248.0	237.8	224.5	200.0	180.6	166.3	155.1
75°	130.6	149.0	169.4	192.9	191.8	183.7	173.5	158.2	141.8	132.7	127.6
77.5°	100.0	111.2	127.6	142.9	142.9	138.8	132.7	121.4	111.2	102.0	96.9
80°	71.4	78.6	91.8	96.9	99.0	98.0	92.9	84.7	80.6	73.5	71.4
82.5°	45.9	51.0	57.1	62.2	65.3	63.3	62.2	58.2	52.0	50.0	48.0
85°	26.5	28.6	31.6	34.7	35.7	34.7	36.7	33.7	30.6	30.6	29.6
87.5°	11.2	12.2	14.3	14.3	15.3	15.3	14.3	15.3	15.3	14.3	13.3
90°	1.2	4.3	7.3	10.4	13.5	15.0	17.8	23.5	29.1	34.8	40.4
92.5°	25.4	27.4	29.5	31.5	33.6	34.6	34.7	35.0	35.3	35.5	35.8
95°	60.0	62.6	65.2	67.7	70.3	71.6	71.9	72.4	72.9	73.4	73.9
97.5°	100.4	102.7	105.0	107.3	109.6	110.8	111.3	112.3	113.4	114.4	115.4
100°	146.6	148.6	150.7	152.7	154.8	155.8	156.2	157.0	157.7	158.5	159.3
102.5°	195.1	196.6	198.2	199.7	201.2	202.0	202.5	203.5	204.6	205.6	206.6
105°	248.2	249.0	249.7	250.5	251.2	251.6	251.9	252.4	252.9	253.4	253.9
107.5°	301.3	302.3	303.3	304.4	305.4	305.9	305.9	305.9	305.9	305.9	305.9
110°	352.0	353.6	355.1	356.7	358.2	359.0	359.0	359.0	359.0	359.0	359.0

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	407.5	409.0	410.6	412.1	413.6	414.4	414.3	414.0	413.7	413.5	413.2
115°	461.7	463.2	464.8	466.3	467.8	468.6	468.3	467.8	467.3	466.8	466.3
117.5°	516.0	518.0	520.1	522.1	524.2	525.2	524.6	523.3	522.0	520.7	519.4
120°	570.2	572.2	574.3	576.3	578.4	579.4	578.4	576.3	574.3	572.2	570.2
122.5°	619.8	622.4	625.0	627.5	630.1	631.4	630.8	629.5	628.2	626.9	625.6
125°	671.8	674.1	676.4	678.7	681.0	682.2	681.8	681.0	680.3	679.5	678.7
127.5°	722.6	725.4	728.2	731.1	733.9	735.3	734.8	733.7	732.7	731.6	730.6
130°	769.9	773.2	776.6	779.9	783.2	784.9	784.6	784.1	783.6	783.1	782.6
132.5°	823.0	825.6	828.1	830.7	833.2	834.5	834.6	834.9	835.2	835.4	835.7
135°	869.2	872.0	874.8	877.7	880.5	881.9	882.2	882.7	883.2	883.7	884.2
137.5°	919.9	922.2	924.5	926.8	929.1	930.3	930.6	931.1	931.6	932.1	932.6
140°	965.0	967.3	969.6	971.9	974.2	975.4	976.0	977.3	978.6	979.8	981.1
142.5°	1011.1	1013.4	1015.7	1018.0	1020.3	1021.5	1021.9	1022.7	1023.4	1024.2	1025.0
145°	1055.0	1056.8	1058.6	1060.4	1062.2	1063.1	1063.9	1065.4	1066.9	1068.5	1070.0
147.5°	1094.2	1096.5	1098.8	1101.1	1103.4	1104.6	1105.1	1106.1	1107.2	1108.2	1109.2
150°	1134.6	1136.2	1137.7	1139.3	1140.8	1141.6	1142.1	1143.1	1144.2	1145.2	1146.2
152.5°	1170.4	1171.9	1173.5	1175.0	1176.5	1177.3	1177.9	1179.2	1180.5	1181.8	1183.1
155°	1206.2	1207.0	1207.8	1208.5	1209.3	1209.7	1210.1	1210.8	1211.6	1212.3	1213.1
157.5°	1237.4	1237.9	1238.4	1238.9	1239.4	1239.7	1240.0	1240.5	1241.0	1241.5	1242.0
160°	1265.1	1265.6	1266.1	1266.6	1267.1	1267.4	1267.5	1267.8	1268.0	1268.3	1268.5
162.5°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.6	1290.9	1291.1	1291.4	1291.6
165°	1312.4	1312.1	1311.9	1311.6	1311.3	1311.2	1311.2	1311.2	1311.2	1311.2	1311.2
167.5°	1332.0	1331.2	1330.5	1329.7	1329.0	1328.6	1328.6	1328.6	1328.6	1328.6	1328.6
170°	1347.0	1346.2	1345.5	1344.7	1344.0	1343.6	1343.5	1343.2	1342.9	1342.7	1342.4
172.5°	1357.4	1356.6	1355.8	1355.1	1354.3	1353.9	1353.8	1353.5	1353.3	1353.0	1352.8
175°	1365.5	1364.7	1363.9	1363.2	1362.4	1362.0	1361.7	1361.2	1360.7	1360.2	1359.7
177.5°	1370.1	1369.3	1368.5	1367.8	1367.0	1366.6	1366.3	1365.8	1365.3	1364.8	1364.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1379.6	1380.6	1382.7	1392.9	1398.0	1399.0	1394.9	1404.1	1407.2	1404.1	1402.0
5°	1444.9	1451.0	1463.3	1476.5	1475.5	1476.5	1482.7	1488.8	1490.8	1482.7	1485.7
7.5°	1502.1	1514.3	1527.6	1548.0	1548.0	1558.2	1562.3	1567.4	1579.6	1573.5	1571.4
10°	1567.4	1583.7	1608.2	1640.8	1641.8	1652.1	1662.3	1678.6	1683.7	1679.6	1681.6
12.5°	1649.0	1680.6	1682.7	1718.4	1734.7	1736.7	1753.1	1750.0	1760.2	1760.2	1777.6
15°	1684.7	1733.7	1761.2	1795.9	1806.1	1793.9	1807.2	1821.4	1822.5	1822.5	1821.4
17.5°	1749.0	1768.4	1795.9	1814.3	1818.4	1818.4	1819.4	1825.5	1821.4	1813.3	1819.4
20°	1762.3	1770.4	1780.6	1778.6	1780.6	1770.4	1760.2	1750.0	1751.0	1745.9	1761.2
22.5°	1737.8	1735.7	1712.3	1696.9	1696.9	1676.5	1657.2	1648.0	1638.8	1641.8	1646.9
25°	1676.5	1644.9	1616.3	1593.9	1588.8	1556.1	1529.6	1521.4	1506.1	1518.4	1520.4
27.5°	1578.6	1542.9	1496.9	1477.6	1451.0	1437.8	1419.4	1394.9	1363.3	1381.6	1378.6
30°	1473.5	1420.4	1382.7	1335.7	1293.9	1290.8	1256.1	1215.3	1199.0	1199.0	1208.2
32.5°	1356.1	1285.7	1230.6	1164.3	1123.5	1106.1	1064.3	1023.5	1032.7	1002.0	1013.3
35°	1219.4	1126.5	1057.1	992.9	962.3	941.8	887.8	865.3	840.8	826.5	853.1
37.5°	1088.8	981.6	892.9	822.5	811.2	774.5	737.8	723.5	709.2	715.3	714.3
40°	929.6	834.7	755.1	700.0	680.6	663.3	638.8	621.4	612.2	617.4	618.4
42.5°	785.7	706.1	646.9	608.2	591.8	579.6	567.4	553.1	550.0	550.0	554.1
45°	674.5	609.2	569.4	537.8	528.6	519.4	510.2	504.1	502.0	498.0	501.0
47.5°	585.7	533.7	509.2	485.7	475.5	473.5	465.3	462.2	458.2	457.1	458.2
50°	511.2	478.6	456.1	442.9	435.7	432.7	428.6	422.5	420.4	425.5	423.5
52.5°	459.2	428.6	416.3	403.1	399.0	394.9	388.8	389.8	388.8	386.7	386.7
55°	407.1	387.8	375.5	365.3	364.3	360.2	355.1	353.1	352.0	350.0	353.1
57.5°	365.3	350.0	338.8	329.6	325.5	325.5	320.4	316.3	316.3	315.3	316.3
60°	323.5	308.2	301.0	291.8	288.8	287.8	284.7	282.7	279.6	279.6	279.6
62.5°	284.7	272.5	264.3	256.1	257.1	252.0	248.0	245.9	245.9	246.9	246.9
65°	248.0	239.8	229.6	222.5	220.4	219.4	217.3	216.3	213.3	215.3	215.3
67.5°	214.3	203.1	196.9	193.9	190.8	189.8	187.8	185.7	184.7	183.7	185.7
70°	180.6	171.4	166.3	164.3	161.2	160.2	159.2	156.1	157.1	158.2	159.2
72.5°	150.0	141.8	140.8	134.7	134.7	134.7	130.6	132.7	131.6	129.6	131.6
75°	118.4	114.3	112.2	109.2	110.2	109.2	108.2	105.1	105.1	106.1	107.1
77.5°	93.9	89.8	88.8	85.7	83.7	85.7	83.7	82.7	82.7	83.7	83.7
80°	69.4	67.3	64.3	64.3	64.3	63.3	63.3	63.3	62.2	61.2	62.2
82.5°	45.9	45.9	44.9	43.9	44.9	42.9	43.9	43.9	43.9	43.9	43.9
85°	29.6	28.6	28.6	27.6	27.6	27.6	28.6	26.5	26.5	27.6	27.6
87.5°	13.3	13.3	13.3	14.3	13.3	13.3	13.3	14.3	13.3	13.3	13.3
90°	39.9	39.4	38.9	38.4	38.1	38.2	38.5	38.7	39.0	39.2	39.0
92.5°	36.0	36.3	36.5	36.8	36.9	36.9	36.9	36.9	36.9	36.9	36.9
95°	73.9	73.9	73.9	73.9	73.9	73.6	73.1	72.6	72.1	71.6	72.1
97.5°	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4
100°	159.3	159.3	159.3	159.3	159.3	159.2	158.9	158.6	158.4	158.1	158.4
102.5°	206.9	207.1	207.4	207.7	207.8	207.7	207.4	207.1	206.9	206.6	206.9
105°	254.4	254.9	255.4	255.9	256.2	256.2	256.2	256.2	256.2	256.2	256.2
107.5°	306.1	306.4	306.6	306.9	307.0	306.4	305.1	303.8	302.6	301.3	302.6
110°	359.0	359.0	359.0	359.0	359.0	358.6	357.8	357.1	356.3	355.5	356.3

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	412.4	411.7	410.9	410.2	409.8	409.5	409.0	408.5	408.0	407.5	408.0
115°	466.1	465.8	465.6	465.3	465.2	464.8	464.0	463.3	462.5	461.7	462.5
117.5°	518.6	517.9	517.1	516.4	516.0	515.6	514.8	514.1	513.3	512.5	513.3
120°	570.2	570.2	570.2	570.2	570.2	569.8	569.0	568.3	567.5	566.7	567.5
122.5°	624.8	624.0	623.3	622.5	622.1	621.8	621.3	620.8	620.3	619.8	620.3
125°	677.9	677.1	676.4	675.6	675.2	675.1	674.8	674.6	674.3	674.1	674.3
127.5°	729.6	728.6	727.5	726.5	726.0	725.6	724.9	724.1	723.4	722.6	723.4
130°	782.1	781.6	781.1	780.6	780.3	779.8	778.8	777.7	776.7	775.7	776.7
132.5°	834.4	833.1	831.8	830.5	829.9	829.5	828.8	828.0	827.3	826.5	827.3
135°	883.9	883.7	883.4	883.1	883.0	882.6	881.8	881.1	880.3	879.5	880.3
137.5°	932.4	932.1	931.9	931.6	931.5	931.0	930.0	928.9	927.9	926.9	927.9
140°	981.1	981.1	981.1	981.1	981.1	980.6	979.6	978.5	977.5	976.5	977.5
142.5°	1025.2	1025.5	1025.7	1026.0	1026.1	1025.6	1024.6	1023.5	1022.5	1021.5	1022.5
145°	1070.3	1070.5	1070.8	1071.1	1071.2	1070.7	1069.6	1068.6	1067.5	1066.5	1067.5
147.5°	1109.7	1110.3	1110.8	1111.3	1111.6	1111.1	1110.0	1109.0	1107.9	1106.9	1107.9
150°	1147.0	1147.7	1148.5	1149.2	1149.6	1149.2	1148.5	1147.7	1147.0	1146.2	1147.0
152.5°	1184.1	1185.1	1186.2	1187.2	1187.7	1187.2	1186.2	1185.1	1184.1	1183.1	1184.1
155°	1214.4	1215.7	1217.0	1218.3	1218.9	1218.5	1217.7	1217.0	1216.2	1215.4	1216.2
157.5°	1243.8	1245.6	1247.4	1249.2	1250.1	1249.5	1248.2	1246.9	1245.6	1244.3	1245.6
160°	1270.1	1271.6	1273.2	1274.7	1275.5	1275.0	1273.9	1272.9	1271.8	1270.8	1271.8
162.5°	1293.4	1295.2	1297.0	1298.8	1299.7	1299.1	1297.8	1296.5	1295.2	1293.9	1295.2
165°	1313.0	1314.8	1316.6	1318.4	1319.3	1318.7	1317.4	1316.1	1314.8	1313.5	1314.8
167.5°	1330.4	1332.2	1333.9	1335.7	1336.6	1336.0	1334.7	1333.4	1332.2	1330.9	1332.2
170°	1344.2	1346.0	1347.8	1349.6	1350.5	1349.7	1348.2	1346.7	1345.1	1343.6	1345.1
172.5°	1354.6	1356.4	1358.2	1360.0	1360.9	1360.1	1358.6	1357.0	1355.5	1353.9	1355.5
175°	1361.5	1363.3	1365.1	1366.9	1367.8	1367.0	1365.5	1364.0	1362.4	1360.9	1362.4
177.5°	1365.9	1367.4	1369.0	1370.5	1371.3	1370.5	1369.0	1367.4	1365.9	1364.3	1365.9
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1407.2	1400.0	1393.9	1394.9	1400.0	1395.9	1385.7	1372.5	1367.4	1361.2	1367.4
5°	1491.8	1485.7	1473.5	1474.5	1471.4	1467.4	1451.0	1430.6	1430.6	1414.3	1412.3
7.5°	1575.5	1566.3	1558.2	1556.1	1544.9	1536.7	1522.5	1493.9	1482.7	1463.3	1452.0
10°	1669.4	1662.3	1653.1	1641.8	1635.7	1621.4	1598.0	1556.1	1535.7	1509.2	1489.8
12.5°	1764.3	1763.3	1742.9	1720.4	1719.4	1696.9	1680.6	1624.5	1596.9	1561.2	1515.3
15°	1824.5	1819.4	1808.2	1796.9	1800.0	1775.5	1738.8	1672.5	1654.1	1611.2	1562.3
17.5°	1823.5	1823.5	1820.4	1818.4	1815.3	1808.2	1787.8	1743.9	1714.3	1660.2	1614.3
20°	1765.3	1778.6	1781.6	1780.6	1790.8	1795.9	1794.9	1767.4	1743.9	1695.9	1649.0
22.5°	1649.0	1679.6	1692.9	1701.0	1722.5	1733.7	1760.2	1750.0	1743.9	1708.2	1668.4
25°	1540.8	1551.0	1590.8	1592.9	1622.5	1650.0	1676.5	1693.9	1716.3	1703.1	1669.4
27.5°	1401.0	1424.5	1453.1	1474.5	1480.6	1536.7	1580.6	1613.3	1664.3	1668.4	1657.2
30°	1242.9	1254.1	1301.0	1329.6	1362.3	1403.1	1466.3	1522.5	1568.4	1610.2	1624.5
32.5°	1050.0	1095.9	1123.5	1158.2	1186.7	1259.2	1336.7	1409.2	1462.3	1532.7	1563.3
35°	873.5	909.2	956.1	970.4	1022.5	1083.7	1184.7	1277.6	1358.2	1429.6	1491.8
37.5°	727.6	756.1	806.1	828.6	859.2	937.8	1022.5	1137.8	1234.7	1322.5	1400.0
40°	627.6	649.0	686.7	693.9	719.4	790.8	859.2	967.4	1095.9	1214.3	1299.0
42.5°	559.2	569.4	594.9	604.1	620.4	668.4	729.6	831.6	951.0	1073.5	1192.9
45°	510.2	517.4	532.7	540.8	561.2	582.7	632.7	714.3	808.2	931.6	1060.2
47.5°	466.3	475.5	481.6	486.7	498.0	521.4	554.1	614.3	704.1	817.4	941.8
50°	429.6	432.7	443.9	444.9	452.0	467.3	498.0	534.7	606.1	698.0	818.4
52.5°	392.9	395.9	403.1	410.2	413.3	425.5	445.9	476.5	529.6	602.0	709.2
55°	356.1	360.2	367.3	372.5	375.5	385.7	398.0	427.6	469.4	520.4	608.2
57.5°	319.4	328.6	330.6	333.7	338.8	350.0	361.2	378.6	411.2	458.2	522.5
60°	284.7	287.8	294.9	298.0	303.1	309.2	323.5	336.7	360.2	396.9	455.1
62.5°	249.0	256.1	259.2	262.2	266.3	273.5	282.7	296.9	317.3	346.9	392.9
65°	218.4	219.4	225.5	229.6	233.7	238.8	248.0	261.2	273.5	301.0	334.7
67.5°	188.8	190.8	192.9	196.9	202.0	207.1	215.3	222.5	237.8	256.1	282.7
70°	160.2	160.2	165.3	168.4	167.3	173.5	179.6	187.8	199.0	216.3	237.8
72.5°	134.7	133.7	137.8	138.8	140.8	144.9	149.0	157.1	163.3	176.5	192.9
75°	107.1	109.2	111.2	111.2	114.3	117.3	121.4	125.5	132.7	140.8	153.1
77.5°	84.7	84.7	86.7	87.8	90.8	89.8	93.9	98.0	103.1	110.2	119.4
80°	62.2	64.3	64.3	64.3	65.3	66.3	70.4	73.5	76.5	81.6	85.7
82.5°	43.9	43.9	45.9	45.9	45.9	48.0	48.0	49.0	51.0	54.1	57.1
85°	27.6	27.6	27.6	28.6	27.6	28.6	30.6	29.6	30.6	32.7	32.7
87.5°	13.3	13.3	13.3	13.3	13.3	14.3	13.3	14.3	15.3	15.3	15.3
90°	38.7	38.5	38.2	38.1	38.4	38.9	39.4	39.9	40.4	34.8	29.1
92.5°	36.9	36.9	36.9	36.9	36.8	36.5	36.3	36.0	35.8	35.5	35.3
95°	72.6	73.1	73.6	73.9	73.9	73.9	73.9	73.9	73.9	73.4	72.9
97.5°	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	114.4	113.4
100°	158.6	158.9	159.2	159.3	159.3	159.3	159.3	159.3	159.3	158.5	157.7
102.5°	207.1	207.4	207.7	207.8	207.7	207.4	207.1	206.9	206.6	205.6	204.6
105°	256.2	256.2	256.2	256.2	255.9	255.4	254.9	254.4	253.9	253.4	252.9
107.5°	303.8	305.1	306.4	307.0	306.9	306.6	306.4	306.1	305.9	305.9	305.9
110°	357.1	357.8	358.6	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	408.5	409.0	409.5	409.8	410.2	410.9	411.7	412.4	413.2	413.5	413.7
115°	463.3	464.0	464.8	465.2	465.3	465.6	465.8	466.1	466.3	466.8	467.3
117.5°	514.1	514.8	515.6	516.0	516.4	517.1	517.9	518.6	519.4	520.7	522.0
120°	568.3	569.0	569.8	570.2	570.2	570.2	570.2	570.2	570.2	572.2	574.3
122.5°	620.8	621.3	621.8	622.1	622.5	623.3	624.0	624.8	625.6	626.9	628.2
125°	674.6	674.8	675.1	675.2	675.6	676.4	677.1	677.9	678.7	679.5	680.3
127.5°	724.1	724.9	725.6	726.0	726.5	727.5	728.6	729.6	730.6	731.6	732.7
130°	777.7	778.8	779.8	780.3	780.6	781.1	781.6	782.1	782.6	783.1	783.6
132.5°	828.0	828.8	829.5	829.9	830.5	831.8	833.1	834.4	835.7	835.4	835.2
135°	881.1	881.8	882.6	883.0	883.1	883.4	883.7	883.9	884.2	883.7	883.2
137.5°	928.9	930.0	931.0	931.5	931.6	931.9	932.1	932.4	932.6	932.1	931.6
140°	978.5	979.6	980.6	981.1	981.1	981.1	981.1	981.1	981.1	979.8	978.6
142.5°	1023.5	1024.6	1025.6	1026.1	1026.0	1025.7	1025.5	1025.2	1025.0	1024.2	1023.4
145°	1068.6	1069.6	1070.7	1071.2	1071.1	1070.8	1070.5	1070.3	1070.0	1068.5	1066.9
147.5°	1109.0	1110.0	1111.1	1111.6	1111.3	1110.8	1110.3	1109.7	1109.2	1108.2	1107.2
150°	1147.7	1148.5	1149.2	1149.6	1149.2	1148.5	1147.7	1147.0	1146.2	1145.2	1144.2
152.5°	1185.1	1186.2	1187.2	1187.7	1187.2	1186.2	1185.1	1184.1	1183.1	1181.8	1180.5
155°	1217.0	1217.7	1218.5	1218.9	1218.3	1217.0	1215.7	1214.4	1213.1	1212.3	1211.6
157.5°	1246.9	1248.2	1249.5	1250.1	1249.2	1247.4	1245.6	1243.8	1242.0	1241.5	1241.0
160°	1272.9	1273.9	1275.0	1275.5	1274.7	1273.2	1271.6	1270.1	1268.5	1268.3	1268.0
162.5°	1296.5	1297.8	1299.1	1299.7	1298.8	1297.0	1295.2	1293.4	1291.6	1291.4	1291.1
165°	1316.1	1317.4	1318.7	1319.3	1318.4	1316.6	1314.8	1313.0	1311.2	1311.2	1311.2
167.5°	1333.4	1334.7	1336.0	1336.6	1335.7	1333.9	1332.2	1330.4	1328.6	1328.6	1328.6
170°	1346.7	1348.2	1349.7	1350.5	1349.6	1347.8	1346.0	1344.2	1342.4	1342.7	1342.9
172.5°	1357.0	1358.6	1360.1	1360.9	1360.0	1358.2	1356.4	1354.6	1352.8	1353.0	1353.3
175°	1364.0	1365.5	1367.0	1367.8	1366.9	1365.1	1363.3	1361.5	1359.7	1360.2	1360.7
177.5°	1367.4	1369.0	1370.5	1371.3	1370.5	1369.0	1367.4	1365.9	1364.3	1364.8	1365.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1362.3	1357.2	1354.1	1356.1	1350.0	1334.7	1334.7	1339.8	1333.7	1327.6	1318.4
5°	1400.0	1389.8	1383.7	1382.7	1368.4	1343.9	1338.8	1333.7	1320.4	1306.1	1290.8
7.5°	1436.7	1418.4	1408.2	1401.0	1380.6	1349.0	1335.7	1324.5	1303.1	1281.6	1262.3
10°	1467.4	1440.8	1428.6	1417.4	1390.8	1351.0	1329.6	1309.2	1281.6	1254.1	1229.6
12.5°	1491.8	1461.2	1445.9	1429.6	1396.9	1344.9	1318.4	1285.7	1258.2	1221.4	1196.9
15°	1532.7	1469.4	1455.1	1439.8	1406.1	1334.7	1302.0	1265.3	1227.6	1178.6	1152.0
17.5°	1565.3	1480.6	1479.6	1446.9	1403.1	1330.6	1280.6	1232.7	1191.8	1142.9	1101.0
20°	1584.7	1498.0	1481.6	1448.0	1392.9	1303.1	1251.0	1198.0	1154.1	1094.9	1053.1
22.5°	1601.0	1522.5	1479.6	1438.8	1371.4	1293.9	1217.4	1167.4	1107.1	1042.9	1003.1
25°	1607.2	1527.6	1482.7	1435.7	1356.1	1267.4	1180.6	1126.5	1059.2	1001.0	946.9
27.5°	1608.2	1526.5	1471.4	1422.5	1334.7	1232.7	1143.9	1086.7	1012.3	944.9	890.8
30°	1598.0	1515.3	1465.3	1412.3	1314.3	1201.0	1099.0	1035.7	956.1	888.8	832.7
32.5°	1567.4	1492.9	1452.0	1393.9	1287.8	1157.2	1056.1	985.7	902.0	835.7	781.6
35°	1516.3	1465.3	1420.4	1366.3	1253.1	1116.3	1013.3	930.6	845.9	782.7	731.6
37.5°	1453.1	1425.5	1383.7	1330.6	1213.3	1079.6	965.3	873.5	788.8	727.6	677.6
40°	1367.4	1374.5	1333.7	1285.7	1166.3	1029.6	903.1	815.3	735.7	678.6	629.6
42.5°	1274.5	1304.1	1280.6	1234.7	1114.3	974.5	857.1	760.2	682.7	623.5	582.7
45°	1174.5	1225.5	1211.2	1177.6	1060.2	916.3	791.8	698.0	629.6	572.5	536.7
47.5°	1065.3	1137.8	1137.8	1113.3	1000.0	858.2	735.7	639.8	572.5	531.6	496.9
50°	954.1	1035.7	1049.0	1032.7	932.7	791.8	667.4	580.6	522.5	482.7	457.1
52.5°	837.8	932.7	957.1	949.0	861.2	728.6	611.2	526.5	473.5	438.8	416.3
55°	726.5	836.7	863.3	866.3	784.7	659.2	549.0	474.5	423.5	400.0	380.6
57.5°	621.4	727.6	757.1	762.2	707.1	595.9	490.8	425.5	379.6	360.2	344.9
60°	531.6	620.4	659.2	670.4	622.5	522.5	436.7	373.5	338.8	320.4	306.1
62.5°	458.2	529.6	570.4	573.5	552.0	458.2	380.6	327.6	298.0	281.6	274.5
65°	386.7	451.0	475.5	487.8	470.4	396.9	328.6	284.7	261.2	246.9	239.8
67.5°	329.6	370.4	390.8	407.1	389.8	334.7	279.6	243.9	226.5	212.2	208.2
70°	270.4	304.1	319.4	335.7	320.4	278.6	238.8	206.1	190.8	179.6	174.5
72.5°	216.3	242.9	257.1	267.3	258.2	223.5	190.8	168.4	157.1	149.0	145.9
75°	171.4	189.8	198.0	205.1	201.0	174.5	154.1	135.7	125.5	118.4	116.3
77.5°	130.6	143.9	153.1	155.1	150.0	132.7	115.3	104.1	95.9	91.8	89.8
80°	92.9	101.0	106.1	109.2	104.1	96.9	84.7	76.5	69.4	64.3	63.3
82.5°	62.2	66.3	70.4	69.4	67.3	61.2	54.1	50.0	46.9	42.9	42.9
85°	35.7	36.7	38.8	39.8	38.8	34.7	30.6	28.6	26.5	23.5	23.5
87.5°	15.3	16.3	16.3	17.3	15.3	15.3	13.3	11.2	11.2	10.2	9.2
90°	23.5	17.8	15.0	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	35.0	34.7	34.6	33.6	31.5	29.5	27.4	25.4	27.4	29.5	31.5
95°	72.4	71.9	71.6	70.3	67.7	65.2	62.6	60.0	62.6	65.2	67.7
97.5°	112.3	111.3	110.8	109.6	107.3	105.0	102.7	100.4	102.7	105.0	107.3
100°	157.0	156.2	155.8	154.8	152.7	150.7	148.6	146.6	148.6	150.7	152.7
102.5°	203.5	202.5	202.0	201.2	199.7	198.2	196.6	195.1	196.6	198.2	199.7
105°	252.4	251.9	251.6	251.2	250.5	249.7	249.0	248.2	249.0	249.7	250.5
107.5°	305.9	305.9	305.9	305.4	304.4	303.3	302.3	301.3	302.3	303.3	304.4
110°	359.0	359.0	359.0	358.2	356.7	355.1	353.6	352.0	353.6	355.1	356.7

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	414.0	414.3	414.4	413.6	412.1	410.6	409.0	407.5	409.0	410.6	412.1
115°	467.8	468.3	468.6	467.8	466.3	464.8	463.2	461.7	463.2	464.8	466.3
117.5°	523.3	524.6	525.2	524.2	522.1	520.1	518.0	516.0	518.0	520.1	522.1
120°	576.3	578.4	579.4	578.4	576.3	574.3	572.2	570.2	572.2	574.3	576.3
122.5°	629.5	630.8	631.4	630.1	627.5	625.0	622.4	619.8	622.4	625.0	627.5
125°	681.0	681.8	682.2	681.0	678.7	676.4	674.1	671.8	674.1	676.4	678.7
127.5°	733.7	734.8	735.3	733.9	731.1	728.2	725.4	722.6	725.4	728.2	731.1
130°	784.1	784.6	784.9	783.2	779.9	776.6	773.2	769.9	773.2	776.6	779.9
132.5°	834.9	834.6	834.5	833.2	830.7	828.1	825.6	823.0	825.6	828.1	830.7
135°	882.7	882.2	881.9	880.5	877.7	874.8	872.0	869.2	872.0	874.8	877.7
137.5°	931.1	930.6	930.3	929.1	926.8	924.5	922.2	919.9	922.2	924.5	926.8
140°	977.3	976.0	975.4	974.2	971.9	969.6	967.3	965.0	967.3	969.6	971.9
142.5°	1022.7	1021.9	1021.5	1020.3	1018.0	1015.7	1013.4	1011.1	1013.4	1015.7	1018.0
145°	1065.4	1063.9	1063.1	1062.2	1060.4	1058.6	1056.8	1055.0	1056.8	1058.6	1060.4
147.5°	1106.1	1105.1	1104.6	1103.4	1101.1	1098.8	1096.5	1094.2	1096.5	1098.8	1101.1
150°	1143.1	1142.1	1141.6	1140.8	1139.3	1137.7	1136.2	1134.6	1136.2	1137.7	1139.3
152.5°	1179.2	1177.9	1177.3	1176.5	1175.0	1173.5	1171.9	1170.4	1171.9	1173.5	1175.0
155°	1210.8	1210.1	1209.7	1209.3	1208.5	1207.8	1207.0	1206.2	1207.0	1207.8	1208.5
157.5°	1240.5	1240.0	1239.7	1239.4	1238.9	1238.4	1237.9	1237.4	1237.9	1238.4	1238.9
160°	1267.8	1267.5	1267.4	1267.1	1266.6	1266.1	1265.6	1265.1	1265.6	1266.1	1266.6
162.5°	1290.9	1290.6	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
165°	1311.2	1311.2	1311.2	1311.3	1311.6	1311.9	1312.1	1312.4	1312.1	1311.9	1311.6
167.5°	1328.6	1328.6	1328.6	1329.0	1329.7	1330.5	1331.2	1332.0	1331.2	1330.5	1329.7
170°	1343.2	1343.5	1343.6	1344.0	1344.7	1345.5	1346.2	1347.0	1346.2	1345.5	1344.7
172.5°	1353.5	1353.8	1353.9	1354.3	1355.1	1355.8	1356.6	1357.4	1356.6	1355.8	1355.1
175°	1361.2	1361.7	1362.0	1362.4	1363.2	1363.9	1364.7	1365.5	1364.7	1363.9	1363.2
177.5°	1365.8	1366.3	1366.6	1367.0	1367.8	1368.5	1369.3	1370.1	1369.3	1368.5	1367.8
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1313.3	1318.4	1317.4	1307.2	1295.9	1286.7	1269.4	1271.4	1265.3	1266.3	1272.5
5°	1280.6	1280.6	1276.5	1262.3	1243.9	1233.7	1214.3	1209.2	1196.9	1195.9	1194.9
7.5°	1245.9	1240.8	1235.7	1215.3	1192.9	1176.5	1150.0	1143.9	1131.6	1123.5	1119.4
10°	1205.1	1198.0	1187.8	1164.3	1136.7	1116.3	1088.8	1080.6	1057.1	1046.9	1040.8
12.5°	1160.2	1156.1	1139.8	1120.4	1075.5	1053.1	1013.3	1021.4	998.0	977.6	974.5
15°	1115.3	1100.0	1090.8	1059.2	1005.1	994.9	963.3	946.9	925.5	909.2	909.2
17.5°	1071.4	1048.0	1027.6	993.9	954.1	925.5	902.0	893.9	867.4	851.0	848.0
20°	1013.3	986.7	981.6	933.7	906.1	874.5	852.0	831.6	812.2	805.1	800.0
22.5°	958.2	927.6	919.4	878.6	851.0	819.4	796.9	782.7	768.4	763.3	754.1
25°	899.0	880.6	868.4	824.5	793.9	764.3	749.0	738.8	725.5	724.5	718.4
27.5°	841.8	824.5	812.2	770.4	748.0	720.4	708.2	696.9	689.8	686.7	683.7
30°	792.9	773.5	759.2	728.6	701.0	678.6	668.4	661.2	657.1	652.0	651.0
32.5°	738.8	727.6	708.2	684.7	663.3	641.8	635.7	630.6	624.5	622.5	621.4
35°	692.9	677.6	665.3	638.8	629.6	611.2	604.1	600.0	591.8	589.8	587.8
37.5°	648.0	633.7	620.4	604.1	586.7	576.5	572.5	566.3	562.2	563.3	561.2
40°	603.1	591.8	581.6	564.3	554.1	549.0	540.8	534.7	532.7	533.7	532.7
42.5°	559.2	549.0	542.9	529.6	519.4	514.3	509.2	503.1	506.1	506.1	509.2
45°	519.4	510.2	506.1	495.9	489.8	481.6	476.5	475.5	479.6	478.6	478.6
47.5°	478.6	475.5	470.4	461.2	453.1	448.0	446.9	446.9	451.0	453.1	452.0
50°	446.9	440.8	434.7	427.6	421.4	419.4	416.3	418.4	422.5	422.5	424.5
52.5°	407.1	403.1	401.0	394.9	390.8	390.8	390.8	391.8	394.9	398.0	396.9
55°	372.5	369.4	367.3	364.3	359.2	360.2	359.2	361.2	364.3	367.3	369.4
57.5°	335.7	334.7	332.7	327.6	327.6	326.5	329.6	330.6	335.7	337.8	340.8
60°	303.1	300.0	300.0	295.9	295.9	295.9	299.0	302.0	306.1	307.1	309.2
62.5°	268.4	268.4	267.3	264.3	264.3	267.3	268.4	272.5	274.5	274.5	277.6
65°	235.7	234.7	233.7	234.7	235.7	235.7	238.8	240.8	242.9	243.9	244.9
67.5°	203.1	202.0	204.1	203.1	205.1	209.2	208.2	211.2	214.3	214.3	215.3
70°	172.5	174.5	173.5	175.5	174.5	176.5	179.6	180.6	180.6	181.6	184.7
72.5°	143.9	143.9	143.9	142.9	143.9	145.9	148.0	149.0	151.0	152.0	155.1
75°	116.3	116.3	114.3	116.3	116.3	118.4	120.4	120.4	120.4	122.4	125.5
77.5°	87.8	88.8	87.8	89.8	89.8	90.8	92.9	91.8	93.9	94.9	95.9
80°	64.3	63.3	63.3	63.3	64.3	64.3	66.3	67.3	67.3	70.4	68.4
82.5°	40.8	41.8	40.8	41.8	41.8	42.9	41.8	42.9	43.9	45.9	44.9
85°	23.5	22.4	22.4	23.5	22.4	22.4	23.5	22.4	23.5	22.4	23.5
87.5°	9.2	8.2	8.2	8.2	8.2	7.1	7.1	6.1	6.1	6.1	5.1
90°	13.5	15.0	17.8	23.5	29.1	34.8	40.4	39.9	39.4	38.9	38.4
92.5°	33.6	34.6	34.7	35.0	35.3	35.5	35.8	36.0	36.3	36.5	36.8
95°	70.3	71.6	71.9	72.4	72.9	73.4	73.9	73.9	73.9	73.9	73.9
97.5°	109.6	110.8	111.3	112.3	113.4	114.4	115.4	115.4	115.4	115.4	115.4
100°	154.8	155.8	156.2	157.0	157.7	158.5	159.3	159.3	159.3	159.3	159.3
102.5°	201.2	202.0	202.5	203.5	204.6	205.6	206.6	206.9	207.1	207.4	207.7
105°	251.2	251.6	251.9	252.4	252.9	253.4	253.9	254.4	254.9	255.4	255.9
107.5°	305.4	305.9	305.9	305.9	305.9	305.9	305.9	306.1	306.4	306.6	306.9
110°	358.2	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	413.6	414.4	414.3	414.0	413.7	413.5	413.2	412.4	411.7	410.9	410.2
115°	467.8	468.6	468.3	467.8	467.3	466.8	466.3	466.1	465.8	465.6	465.3
117.5°	524.2	525.2	524.6	523.3	522.0	520.7	519.4	518.6	517.9	517.1	516.4
120°	578.4	579.4	578.4	576.3	574.3	572.2	570.2	570.2	570.2	570.2	570.2
122.5°	630.1	631.4	630.8	629.5	628.2	626.9	625.6	624.8	624.0	623.3	622.5
125°	681.0	682.2	681.8	681.0	680.3	679.5	678.7	677.9	677.1	676.4	675.6
127.5°	733.9	735.3	734.8	733.7	732.7	731.6	730.6	729.6	728.6	727.5	726.5
130°	783.2	784.9	784.6	784.1	783.6	783.1	782.6	782.1	781.6	781.1	780.6
132.5°	833.2	834.5	834.6	834.9	835.2	835.4	835.7	834.4	833.1	831.8	830.5
135°	880.5	881.9	882.2	882.7	883.2	883.7	884.2	883.9	883.7	883.4	883.1
137.5°	929.1	930.3	930.6	931.1	931.6	932.1	932.6	932.4	932.1	931.9	931.6
140°	974.2	975.4	976.0	977.3	978.6	979.8	981.1	981.1	981.1	981.1	981.1
142.5°	1020.3	1021.5	1021.9	1022.7	1023.4	1024.2	1025.0	1025.2	1025.5	1025.7	1026.0
145°	1062.2	1063.1	1063.9	1065.4	1066.9	1068.5	1070.0	1070.3	1070.5	1070.8	1071.1
147.5°	1103.4	1104.6	1105.1	1106.1	1107.2	1108.2	1109.2	1109.7	1110.3	1110.8	1111.3
150°	1140.8	1141.6	1142.1	1143.1	1144.2	1145.2	1146.2	1147.0	1147.7	1148.5	1149.2
152.5°	1176.5	1177.3	1177.9	1179.2	1180.5	1181.8	1183.1	1184.1	1185.1	1186.2	1187.2
155°	1209.3	1209.7	1210.1	1210.8	1211.6	1212.3	1213.1	1214.4	1215.7	1217.0	1218.3
157.5°	1239.4	1239.7	1240.0	1240.5	1241.0	1241.5	1242.0	1243.8	1245.6	1247.4	1249.2
160°	1267.1	1267.4	1267.5	1267.8	1268.0	1268.3	1268.5	1270.1	1271.6	1273.2	1274.7
162.5°	1290.5	1290.5	1290.6	1290.9	1291.1	1291.4	1291.6	1293.4	1295.2	1297.0	1298.8
165°	1311.3	1311.2	1311.2	1311.2	1311.2	1311.2	1311.2	1313.0	1314.8	1316.6	1318.4
167.5°	1329.0	1328.6	1328.6	1328.6	1328.6	1328.6	1328.6	1330.4	1332.2	1333.9	1335.7
170°	1344.0	1343.6	1343.5	1343.2	1342.9	1342.7	1342.4	1344.2	1346.0	1347.8	1349.6
172.5°	1354.3	1353.9	1353.8	1353.5	1353.3	1353.0	1352.8	1354.6	1356.4	1358.2	1360.0
175°	1362.4	1362.0	1361.7	1361.2	1360.7	1360.2	1359.7	1361.5	1363.3	1365.1	1366.9
177.5°	1367.0	1366.6	1366.3	1365.8	1365.3	1364.8	1364.3	1365.9	1367.4	1369.0	1370.5
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1265.3	1268.4	1261.2	1259.2	1261.2	1254.1	1256.1	1258.2	1258.2	1261.2	1263.3
5°	1191.8	1187.8	1180.6	1178.6	1176.5	1179.6	1177.6	1180.6	1181.6	1188.8	1189.8
7.5°	1119.4	1113.3	1107.1	1101.0	1099.0	1093.9	1099.0	1099.0	1106.1	1104.1	1109.2
10°	1033.7	1032.7	1024.5	1021.4	1017.4	1009.2	1020.4	1017.4	1022.5	1031.6	1033.7
12.5°	970.4	959.2	964.3	950.0	955.1	946.9	948.0	948.0	956.1	957.1	955.1
15°	910.2	901.0	887.8	881.6	878.6	874.5	887.8	888.8	882.7	896.9	891.8
17.5°	849.0	849.0	836.7	833.7	825.5	829.6	827.6	828.6	826.5	836.7	841.8
20°	795.9	790.8	786.7	787.8	777.6	775.5	773.5	775.5	782.7	789.8	791.8
22.5°	753.1	750.0	739.8	741.8	733.7	736.7	734.7	739.8	740.8	740.8	748.0
25°	712.2	708.2	709.2	705.1	702.0	702.0	699.0	702.0	706.1	708.2	709.2
27.5°	681.6	678.6	673.5	670.4	672.5	667.4	671.4	674.5	674.5	672.5	674.5
30°	644.9	646.9	646.9	636.7	640.8	638.8	641.8	643.9	643.9	644.9	642.9
32.5°	620.4	614.3	613.3	612.2	612.2	608.2	608.2	611.2	612.2	613.3	616.3
35°	587.8	587.8	582.7	585.7	581.6	582.7	581.6	582.7	584.7	581.6	584.7
37.5°	558.2	559.2	557.1	559.2	560.2	558.2	556.1	560.2	558.2	558.2	556.1
40°	532.7	531.6	532.7	532.7	532.7	533.7	531.6	531.6	531.6	529.6	527.6
42.5°	511.2	505.1	507.1	508.2	505.1	505.1	506.1	505.1	508.2	502.0	502.0
45°	480.6	478.6	479.6	479.6	481.6	478.6	480.6	481.6	478.6	477.6	475.5
47.5°	453.1	455.1	453.1	455.1	455.1	457.1	453.1	454.1	455.1	451.0	448.0
50°	425.5	425.5	428.6	427.6	428.6	426.5	426.5	425.5	426.5	424.5	421.4
52.5°	400.0	396.9	402.0	401.0	400.0	399.0	398.0	399.0	396.9	394.9	394.9
55°	368.4	368.4	371.4	372.5	372.5	370.4	368.4	369.4	368.4	367.3	366.3
57.5°	342.9	338.8	340.8	341.8	341.8	338.8	340.8	338.8	338.8	339.8	336.7
60°	310.2	310.2	308.2	311.2	311.2	309.2	309.2	310.2	308.2	307.1	306.1
62.5°	275.5	276.5	279.6	280.6	281.6	279.6	277.6	278.6	278.6	275.5	276.5
65°	245.9	248.0	252.0	251.0	249.0	250.0	248.0	249.0	245.9	246.9	243.9
67.5°	217.3	216.3	217.3	217.3	219.4	218.4	216.3	216.3	215.3	218.4	215.3
70°	186.7	186.7	186.7	186.7	187.8	188.8	186.7	184.7	185.7	183.7	182.7
72.5°	155.1	156.1	155.1	157.1	154.1	156.1	156.1	155.1	154.1	154.1	154.1
75°	125.5	127.6	124.5	125.5	124.5	126.5	125.5	125.5	123.5	122.4	123.5
77.5°	95.9	96.9	94.9	95.9	94.9	95.9	95.9	94.9	94.9	94.9	94.9
80°	68.4	69.4	68.4	67.3	66.3	68.4	66.3	67.3	68.4	67.3	69.4
82.5°	43.9	43.9	42.9	43.9	41.8	41.8	42.9	42.9	41.8	43.9	41.8
85°	21.4	21.4	23.5	21.4	20.4	20.4	20.4	21.4	20.4	22.4	21.4
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.1	4.1
90°	38.1	38.2	38.5	38.7	39.0	39.2	39.0	38.7	38.5	38.2	38.1
92.5°	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9
95°	73.9	73.6	73.1	72.6	72.1	71.6	72.1	72.6	73.1	73.6	73.9
97.5°	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4
100°	159.3	159.2	158.9	158.6	158.4	158.1	158.4	158.6	158.9	159.2	159.3
102.5°	207.8	207.7	207.4	207.1	206.9	206.6	206.9	207.1	207.4	207.7	207.8
105°	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2
107.5°	307.0	306.4	305.1	303.8	302.6	301.3	302.6	303.8	305.1	306.4	307.0
110°	359.0	358.6	357.8	357.1	356.3	355.5	356.3	357.1	357.8	358.6	359.0

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	409.8	409.5	409.0	408.5	408.0	407.5	408.0	408.5	409.0	409.5	409.8
115°	465.2	464.8	464.0	463.3	462.5	461.7	462.5	463.3	464.0	464.8	465.2
117.5°	516.0	515.6	514.8	514.1	513.3	512.5	513.3	514.1	514.8	515.6	516.0
120°	570.2	569.8	569.0	568.3	567.5	566.7	567.5	568.3	569.0	569.8	570.2
122.5°	622.1	621.8	621.3	620.8	620.3	619.8	620.3	620.8	621.3	621.8	622.1
125°	675.2	675.1	674.8	674.6	674.3	674.1	674.3	674.6	674.8	675.1	675.2
127.5°	726.0	725.6	724.9	724.1	723.4	722.6	723.4	724.1	724.9	725.6	726.0
130°	780.3	779.8	778.8	777.7	776.7	775.7	776.7	777.7	778.8	779.8	780.3
132.5°	829.9	829.5	828.8	828.0	827.3	826.5	827.3	828.0	828.8	829.5	829.9
135°	883.0	882.6	881.8	881.1	880.3	879.5	880.3	881.1	881.8	882.6	883.0
137.5°	931.5	931.0	930.0	928.9	927.9	926.9	927.9	928.9	930.0	931.0	931.5
140°	981.1	980.6	979.6	978.5	977.5	976.5	977.5	978.5	979.6	980.6	981.1
142.5°	1026.1	1025.6	1024.6	1023.5	1022.5	1021.5	1022.5	1023.5	1024.6	1025.6	1026.1
145°	1071.2	1070.7	1069.6	1068.6	1067.5	1066.5	1067.5	1068.6	1069.6	1070.7	1071.2
147.5°	1111.6	1111.1	1110.0	1109.0	1107.9	1106.9	1107.9	1109.0	1110.0	1111.1	1111.6
150°	1149.6	1149.2	1148.5	1147.7	1147.0	1146.2	1147.0	1147.7	1148.5	1149.2	1149.6
152.5°	1187.7	1187.2	1186.2	1185.1	1184.1	1183.1	1184.1	1185.1	1186.2	1187.2	1187.7
155°	1218.9	1218.5	1217.7	1217.0	1216.2	1215.4	1216.2	1217.0	1217.7	1218.5	1218.9
157.5°	1250.1	1249.5	1248.2	1246.9	1245.6	1244.3	1245.6	1246.9	1248.2	1249.5	1250.1
160°	1275.5	1275.0	1273.9	1272.9	1271.8	1270.8	1271.8	1272.9	1273.9	1275.0	1275.5
162.5°	1299.7	1299.1	1297.8	1296.5	1295.2	1293.9	1295.2	1296.5	1297.8	1299.1	1299.7
165°	1319.3	1318.7	1317.4	1316.1	1314.8	1313.5	1314.8	1316.1	1317.4	1318.7	1319.3
167.5°	1336.6	1336.0	1334.7	1333.4	1332.2	1330.9	1332.2	1333.4	1334.7	1336.0	1336.6
170°	1350.5	1349.7	1348.2	1346.7	1345.1	1343.6	1345.1	1346.7	1348.2	1349.7	1350.5
172.5°	1360.9	1360.1	1358.6	1357.0	1355.5	1353.9	1355.5	1357.0	1358.6	1360.1	1360.9
175°	1367.8	1367.0	1365.5	1364.0	1362.4	1360.9	1362.4	1364.0	1365.5	1367.0	1367.8
177.5°	1371.3	1370.5	1369.0	1367.4	1365.9	1364.3	1365.9	1367.4	1369.0	1370.5	1371.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1260.2	1268.4	1265.3	1254.1	1267.4	1267.4	1276.5	1276.5	1287.8	1291.8	1298.0
5°	1188.8	1194.9	1200.0	1194.9	1204.1	1218.4	1226.5	1233.7	1249.0	1255.1	1264.3
7.5°	1112.3	1123.5	1128.6	1128.6	1143.9	1160.2	1176.5	1186.7	1208.2	1216.3	1225.5
10°	1037.8	1051.0	1061.2	1060.2	1085.7	1095.9	1116.3	1139.8	1161.2	1173.5	1186.7
12.5°	959.2	966.3	980.6	1001.0	1007.1	1025.5	1049.0	1078.6	1117.4	1128.6	1148.0
15°	893.9	913.3	924.5	933.7	948.0	965.3	990.8	1019.4	1058.2	1082.7	1103.1
17.5°	838.8	864.3	871.4	869.4	887.8	914.3	943.9	965.3	1000.0	1029.6	1049.0
20°	793.9	804.1	816.3	821.4	835.7	864.3	892.9	917.4	945.9	969.4	991.8
22.5°	749.0	757.1	767.4	776.5	787.8	804.1	831.6	862.3	889.8	912.3	937.8
25°	712.2	717.4	726.5	733.7	745.9	757.1	776.5	810.2	842.9	856.1	878.6
27.5°	676.5	680.6	686.7	694.9	701.0	712.2	729.6	757.1	790.8	804.1	834.7
30°	644.9	648.0	654.1	658.2	661.2	674.5	687.8	709.2	734.7	753.1	775.5
32.5°	615.3	618.4	624.5	625.5	629.6	636.7	649.0	668.4	690.8	706.1	725.5
35°	582.7	584.7	590.8	592.9	595.9	602.0	611.2	625.5	645.9	657.1	674.5
37.5°	557.1	556.1	560.2	563.3	567.4	570.4	573.5	587.8	603.1	613.3	626.5
40°	529.6	527.6	528.6	532.7	534.7	538.8	538.8	553.1	563.3	571.4	581.6
42.5°	502.0	501.0	499.0	501.0	503.1	504.1	505.1	515.3	525.5	532.7	543.9
45°	474.5	473.5	471.4	472.5	472.5	474.5	477.6	481.6	488.8	494.9	501.0
47.5°	449.0	446.9	443.9	442.9	444.9	444.9	444.9	449.0	456.1	458.2	464.3
50°	422.5	419.4	415.3	413.3	413.3	412.2	414.3	415.3	421.4	423.5	428.6
52.5°	393.9	391.8	387.8	383.7	384.7	382.7	383.7	384.7	386.7	389.8	392.9
55°	365.3	361.2	358.2	357.1	354.1	354.1	351.0	355.1	354.1	355.1	359.2
57.5°	337.8	333.7	328.6	326.5	323.5	322.5	320.4	319.4	320.4	323.5	326.5
60°	305.1	303.1	300.0	296.9	294.9	291.8	289.8	289.8	288.8	288.8	289.8
62.5°	273.5	272.5	268.4	267.3	265.3	263.3	260.2	258.2	258.2	260.2	261.2
65°	242.9	241.8	238.8	237.8	232.7	230.6	229.6	228.6	226.5	226.5	226.5
67.5°	214.3	211.2	211.2	206.1	202.0	200.0	198.0	196.9	196.9	196.9	198.0
70°	182.7	182.7	179.6	176.5	172.5	173.5	170.4	167.3	167.3	165.3	166.3
72.5°	152.0	151.0	148.0	146.9	143.9	140.8	138.8	140.8	137.8	136.7	137.8
75°	122.4	121.4	119.4	117.3	118.4	115.3	112.2	111.2	111.2	109.2	109.2
77.5°	93.9	95.9	91.8	90.8	88.8	86.7	85.7	84.7	84.7	84.7	86.7
80°	65.3	66.3	66.3	64.3	65.3	62.2	62.2	62.2	59.2	60.2	61.2
82.5°	41.8	41.8	40.8	41.8	40.8	40.8	39.8	39.8	38.8	38.8	39.8
85°	23.5	22.4	21.4	23.5	22.4	22.4	21.4	21.4	21.4	21.4	21.4
87.5°	5.1	6.1	6.1	6.1	6.1	7.1	7.1	7.1	8.2	8.2	8.2
90°	38.4	38.9	39.4	39.9	40.4	34.8	29.1	23.5	17.8	15.0	13.5
92.5°	36.8	36.5	36.3	36.0	35.8	35.5	35.3	35.0	34.7	34.6	33.6
95°	73.9	73.9	73.9	73.9	73.9	73.4	72.9	72.4	71.9	71.6	70.3
97.5°	115.4	115.4	115.4	115.4	115.4	114.4	113.4	112.3	111.3	110.8	109.6
100°	159.3	159.3	159.3	159.3	159.3	158.5	157.7	157.0	156.2	155.8	154.8
102.5°	207.7	207.4	207.1	206.9	206.6	205.6	204.6	203.5	202.5	202.0	201.2
105°	255.9	255.4	254.9	254.4	253.9	253.4	252.9	252.4	251.9	251.6	251.2
107.5°	306.9	306.6	306.4	306.1	305.9	305.9	305.9	305.9	305.9	305.9	305.4
110°	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	358.2

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	410.2	410.9	411.7	412.4	413.2	413.5	413.7	414.0	414.3	414.4	413.6
115°	465.3	465.6	465.8	466.1	466.3	466.8	467.3	467.8	468.3	468.6	467.8
117.5°	516.4	517.1	517.9	518.6	519.4	520.7	522.0	523.3	524.6	525.2	524.2
120°	570.2	570.2	570.2	570.2	570.2	572.2	574.3	576.3	578.4	579.4	578.4
122.5°	622.5	623.3	624.0	624.8	625.6	626.9	628.2	629.5	630.8	631.4	630.1
125°	675.6	676.4	677.1	677.9	678.7	679.5	680.3	681.0	681.8	682.2	681.0
127.5°	726.5	727.5	728.6	729.6	730.6	731.6	732.7	733.7	734.8	735.3	733.9
130°	780.6	781.1	781.6	782.1	782.6	783.1	783.6	784.1	784.6	784.9	783.2
132.5°	830.5	831.8	833.1	834.4	835.7	835.4	835.2	834.9	834.6	834.5	833.2
135°	883.1	883.4	883.7	883.9	884.2	883.7	883.2	882.7	882.2	881.9	880.5
137.5°	931.6	931.9	932.1	932.4	932.6	932.1	931.6	931.1	930.6	930.3	929.1
140°	981.1	981.1	981.1	981.1	981.1	979.8	978.6	977.3	976.0	975.4	974.2
142.5°	1026.0	1025.7	1025.5	1025.2	1025.0	1024.2	1023.4	1022.7	1021.9	1021.5	1020.3
145°	1071.1	1070.8	1070.5	1070.3	1070.0	1068.5	1066.9	1065.4	1063.9	1063.1	1062.2
147.5°	1111.3	1110.8	1110.3	1109.7	1109.2	1108.2	1107.2	1106.1	1105.1	1104.6	1103.4
150°	1149.2	1148.5	1147.7	1147.0	1146.2	1145.2	1144.2	1143.1	1142.1	1141.6	1140.8
152.5°	1187.2	1186.2	1185.1	1184.1	1183.1	1181.8	1180.5	1179.2	1177.9	1177.3	1176.5
155°	1218.3	1217.0	1215.7	1214.4	1213.1	1212.3	1211.6	1210.8	1210.1	1209.7	1209.3
157.5°	1249.2	1247.4	1245.6	1243.8	1242.0	1241.5	1241.0	1240.5	1240.0	1239.7	1239.4
160°	1274.7	1273.2	1271.6	1270.1	1268.5	1268.3	1268.0	1267.8	1267.5	1267.4	1267.1
162.5°	1298.8	1297.0	1295.2	1293.4	1291.6	1291.4	1291.1	1290.9	1290.6	1290.5	1290.5
165°	1318.4	1316.6	1314.8	1313.0	1311.2	1311.2	1311.2	1311.2	1311.2	1311.2	1311.3
167.5°	1335.7	1333.9	1332.2	1330.4	1328.6	1328.6	1328.6	1328.6	1328.6	1328.6	1329.0
170°	1349.6	1347.8	1346.0	1344.2	1342.4	1342.7	1342.9	1343.2	1343.5	1343.6	1344.0
172.5°	1360.0	1358.2	1356.4	1354.6	1352.8	1353.0	1353.3	1353.5	1353.8	1353.9	1354.3
175°	1366.9	1365.1	1363.3	1361.5	1359.7	1360.2	1360.7	1361.2	1361.7	1362.0	1362.4
177.5°	1370.5	1369.0	1367.4	1365.9	1364.3	1364.8	1365.3	1365.8	1366.3	1366.6	1367.0
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1327.6	1327.6	1327.6	1327.6
2.5°	1303.1	1303.1	1318.4	1334.7
5°	1274.5	1281.6	1306.1	1328.6
7.5°	1246.9	1259.2	1289.8	1318.4
10°	1213.3	1229.6	1267.4	1301.0
12.5°	1180.6	1195.9	1239.8	1277.6
15°	1134.7	1154.1	1201.0	1248.0
17.5°	1088.8	1108.2	1165.3	1220.4
20°	1034.7	1060.2	1124.5	1198.0
22.5°	984.7	1016.3	1087.8	1146.9
25°	929.6	978.6	1044.9	1121.4
27.5°	880.6	929.6	996.9	1074.5
30°	825.5	875.5	944.9	1016.3
32.5°	772.5	818.4	885.7	973.5
35°	717.4	761.2	826.5	915.3
37.5°	667.4	710.2	781.6	863.3
40°	618.4	663.3	724.5	806.1
42.5°	572.5	612.2	667.4	749.0
45°	530.6	559.2	610.2	686.7
47.5°	486.7	512.2	559.2	635.7
50°	445.9	467.3	508.2	579.6
52.5°	406.1	424.5	462.2	519.4
55°	370.4	387.8	415.3	471.4
57.5°	333.7	346.9	373.5	418.4
60°	298.0	310.2	331.6	368.4
62.5°	262.2	272.5	292.9	322.5
65°	230.6	238.8	254.1	279.6
67.5°	200.0	205.1	217.3	237.8
70°	170.4	174.5	184.7	201.0
72.5°	138.8	142.9	154.1	165.3
75°	112.2	113.3	121.4	130.6
77.5°	87.8	86.7	92.9	100.0
80°	60.2	63.3	68.4	71.4
82.5°	40.8	41.8	43.9	45.9
85°	22.4	23.5	23.5	26.5
87.5°	9.2	10.2	10.2	11.2
90°	10.4	7.3	4.3	1.2
92.5°	31.5	29.5	27.4	25.4
95°	67.7	65.2	62.6	60.0
97.5°	107.3	105.0	102.7	100.4
100°	152.7	150.7	148.6	146.6
102.5°	199.7	198.2	196.6	195.1
105°	250.5	249.7	249.0	248.2
107.5°	304.4	303.3	302.3	301.3
110°	356.7	355.1	353.6	352.0



TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	412.1	410.6	409.0	407.5
115°	466.3	464.8	463.2	461.7
117.5°	522.1	520.1	518.0	516.0
120°	576.3	574.3	572.2	570.2
122.5°	627.5	625.0	622.4	619.8
125°	678.7	676.4	674.1	671.8
127.5°	731.1	728.2	725.4	722.6
130°	779.9	776.6	773.2	769.9
132.5°	830.7	828.1	825.6	823.0
135°	877.7	874.8	872.0	869.2
137.5°	926.8	924.5	922.2	919.9
140°	971.9	969.6	967.3	965.0
142.5°	1018.0	1015.7	1013.4	1011.1
145°	1060.4	1058.6	1056.8	1055.0
147.5°	1101.1	1098.8	1096.5	1094.2
150°	1139.3	1137.7	1136.2	1134.6
152.5°	1175.0	1173.5	1171.9	1170.4
155°	1208.5	1207.8	1207.0	1206.2
157.5°	1238.9	1238.4	1237.9	1237.4
160°	1266.6	1266.1	1265.6	1265.1
162.5°	1290.5	1290.5	1290.5	1290.5
165°	1311.6	1311.9	1312.1	1312.4
167.5°	1329.7	1330.5	1331.2	1332.0
170°	1344.7	1345.5	1346.2	1347.0
172.5°	1355.1	1355.8	1356.6	1357.4
175°	1363.2	1363.9	1364.7	1365.5
177.5°	1367.8	1368.5	1369.3	1370.1
180°	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P998717

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.77	16.55	16.79	17.57	18.94	13.27	14.04	14.28	15.07	16.43
	3H	16.58	17.27	17.61	18.31	19.69	14.60	15.30	15.63	16.33	17.72
	4H	16.74	17.40	17.78	18.44	19.83	15.06	15.72	16.10	16.76	18.15
	6H	16.78	17.39	17.84	18.43	19.83	15.37	15.97	16.42	17.01	18.41
	8H	16.76	17.34	17.82	18.39	19.79	15.45	16.02	16.50	17.08	18.48
	12H	16.72	17.27	17.78	18.32	19.74	15.49	16.03	16.55	17.08	18.51
4H	2H	15.80	16.46	16.85	17.50	18.89	13.70	14.36	14.75	15.39	16.79
	3H	16.78	17.33	17.83	18.39	19.79	15.16	15.70	16.21	16.77	18.17
	4H	17.05	17.55	18.11	18.61	20.03	15.69	16.19	16.75	17.24	18.67
	6H	17.18	17.61	18.25	18.68	20.11	16.06	16.49	17.13	17.57	18.99
	8H	17.17	17.57	18.24	18.64	20.08	16.17	16.57	17.24	17.64	19.08
	12H	17.13	17.50	18.22	18.58	20.02	16.22	16.59	17.31	17.67	19.11
8H	4H	17.05	17.46	18.12	18.52	19.96	15.82	16.22	16.89	17.29	18.73
	6H	17.23	17.56	18.32	18.67	20.11	16.25	16.59	17.35	17.70	19.13
	8H	17.26	17.55	18.36	18.64	20.10	16.40	16.69	17.50	17.79	19.24
	12H	17.24	17.50	18.34	18.59	20.08	16.49	16.75	17.60	17.84	19.33
12H	4H	17.01	17.37	18.10	18.45	19.90	15.79	16.16	16.88	17.24	18.68
	6H	17.21	17.50	18.31	18.59	20.05	16.25	16.54	17.35	17.64	19.09
	8H	17.24	17.49	18.34	18.58	20.08	16.41	16.66	17.51	17.75	19.25