

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999955

Luminaire Tested: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999955
REPORT IS A COMBINATION OF REPORTS P988512 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4427.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999955

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P999955

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	58	58	58
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	50	50	45
2	90	83	77	72	83	77	72	68	66	63	59	56	53	51	47	45	43	43	43	39
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37	37	37	33
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	33	33	29
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29	29	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	26	26	26	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23	23	23	20
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	26	23	21	21	21	18
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19	19	19	17
10	49	37	30	25	45	35	28	24	30	25	22	27	22	19	23	20	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17849	17849	17849
5°	17878	16981	16854
10°	17701	16105	15574
15°	17459	15072	14114
20°	17137	13896	12587
25°	16807	12690	11188
30°	16364	11516	9663
35°	15930	10332	8352
40°	15489	9168	7002
45°	14976	7967	5825
50°	14446	6809	4743
55°	13893	5651	3764
60°	13251	4520	2848
65°	12513	3447	2315
70°	11624	2501	1842
75°	10506	1906	1407
80°	8878	1291	944
85°	6201	592	456

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14976 cd/sqm

TEST NUMBER: P999955

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.7	2.4
10°-20°	290.1	6.6
20°-30°	407.3	9.2
30°-40°	444.0	10.0
40°-50°	408.1	9.2
50°-60°	320.5	7.2
60°-70°	208.6	4.7
70°-80°	107.4	2.4
80°-90°	28.7	0.6
90°-100°	23.7	0.5
100°-110°	88.3	2.0
110°-120°	234.3	5.3
120°-130°	388.6	8.8
130°-140°	412.7	9.3
140°-150°	383.6	8.7
150°-160°	308.4	7.0
160°-170°	198.7	4.5
170°-180°	68.4	1.5
0°-30°	803.1	18.1
0°-40°	1247.1	28.2
0°-60°	1975.6	44.6
0°-90°	2320.3	52.4
90°-120°	346.3	7.8
90°-150°	1531.2	34.6
90°-180°	2107.0	47.6
0°-180°	4427.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1109	1118	1115	107
15°	1072	1061	1027	1007	997	302
25°	974	941	874	832	816	448
35°	839	787	697	633	610	525
45°	686	617	510	438	413	530
55°	521	442	332	270	251	466
65°	352	269	178	143	140	349
75°	188	116	82	74	74	199
85°	44	22	19	19	19	50
90°	0	6	10	13	14	4
95°	34	17	20	23	22	40
105°	158	174	32	37	40	169
115°	299	308	321	80	43	294
125°	423	430	439	443	445	377
135°	523	531	536	541	540	404
145°	607	606	615	619	616	380
155°	668	664	670	673	669	308
165°	704	701	702	706	702	199
175°	720	716	718	721	716	69
180°	719	719	719	719	719	

TEST NUMBER: P999955

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1127.6	1127.6	1127.6	1127.6	1127.6
2.5°	1132.7	1127.6	1116.3	1126.6	1124.5
5°	1127.6	1122.5	1109.2	1118.4	1115.3
7.5°	1118.4	1112.3	1098.0	1102.1	1097.0
10°	1106.1	1099.0	1078.6	1075.5	1069.4
12.5°	1090.8	1081.7	1054.1	1048.0	1036.8
15°	1072.5	1061.2	1026.6	1007.2	997.0
17.5°	1051.0	1034.7	991.9	969.4	953.1
20°	1026.6	1006.1	955.1	929.6	907.2
22.5°	1000.0	976.6	917.4	882.7	867.4
25°	973.5	940.8	873.5	831.6	816.3
27.5°	941.9	907.2	832.7	784.7	761.2
30°	908.2	869.4	787.8	735.7	708.2
32.5°	875.5	828.6	744.9	683.7	658.2
35°	838.8	786.8	697.0	632.7	610.2
37.5°	803.1	747.0	652.1	581.6	556.1
40°	765.3	704.1	605.1	532.7	506.1
42.5°	726.5	661.2	558.2	482.7	457.2
45°	685.7	617.4	510.2	437.8	413.3
47.5°	647.0	574.5	464.3	391.8	369.4
50°	604.1	531.6	419.4	349.0	327.6
52.5°	562.3	485.7	376.5	309.2	289.8
55°	521.4	441.8	331.6	270.4	251.0
57.5°	479.6	398.0	291.8	234.7	218.4
60°	436.7	355.1	250.0	198.0	181.6
62.5°	394.9	313.3	214.3	165.3	157.1
65°	352.0	269.4	177.6	142.9	139.8
67.5°	311.2	228.6	142.9	125.5	122.5
70°	268.4	188.8	118.4	108.2	104.1
72.5°	227.6	152.0	99.0	90.8	88.8
75°	187.8	116.3	81.6	74.5	73.5
77.5°	148.0	82.7	64.3	60.2	58.2
80°	111.2	59.2	49.0	44.9	44.9
82.5°	77.6	39.8	33.7	31.6	31.6
85°	43.9	22.4	19.4	19.4	19.4
87.5°	16.3	8.2	8.2	7.1	7.1
90°	0.5	6.2	10.4	13.0	14.0
92.5°	13.0	10.9	12.5	13.5	14.0
95°	33.8	16.6	20.3	22.9	22.4
97.5°	60.8	18.2	26.5	28.1	28.6
100°	92.0	20.8	29.6	33.8	34.8
102.5°	126.4	125.3	30.7	36.4	38.0
105°	158.1	173.7	31.7	37.4	39.5
107.5°	195.0	208.0	32.8	38.5	40.6
110°	230.4	241.3	91.0	39.0	41.1



TEST NUMBER: P999955

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	263.6	273.0	264.2	40.0	41.6
115°	299.0	307.8	320.8	80.1	42.6
117.5°	329.7	340.1	348.9	274.6	138.3
120°	364.0	371.8	381.1	387.4	317.2
122.5°	393.1	401.4	411.8	414.9	415.5
125°	422.7	429.5	439.4	443.0	444.6
127.5°	449.8	457.1	464.9	470.1	470.6
130°	475.3	483.6	489.3	495.0	494.5
132.5°	501.3	508.0	513.7	518.4	517.9
135°	523.1	531.4	536.1	541.3	540.3
137.5°	546.0	552.2	557.4	562.6	561.1
140°	568.3	572.5	578.2	582.9	580.3
142.5°	587.1	590.7	597.5	601.6	599.0
145°	606.8	606.3	615.1	618.8	616.2
147.5°	624.0	622.4	631.3	633.9	631.8
150°	640.6	637.0	645.3	648.4	645.8
152.5°	654.7	650.5	658.3	661.4	657.8
155°	668.2	663.5	669.7	672.9	668.7
157.5°	679.1	674.9	679.6	683.3	679.1
160°	688.5	685.3	688.5	691.6	687.9
162.5°	696.8	693.7	696.3	699.9	695.2
165°	704.1	700.9	702.5	706.1	702.5
167.5°	709.8	706.7	708.2	711.9	707.2
170°	714.5	711.3	712.4	716.0	711.3
172.5°	717.6	714.5	715.5	719.1	714.5
175°	720.2	716.5	717.6	721.2	716.0
177.5°	721.2	717.6	718.1	721.7	717.1
180°	718.6	718.6	718.6	718.6	718.6

(END OF REPORT)