

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000035

Luminaire Tested: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000035
REPORT IS A COMBINATION OF REPORTS P988592 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5964.0 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000035

CATALOG NUMBER: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000035

CATALOG NUMBER: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46			39
1	96	92	88	85	87	83	80	77	68	66	64	54	53	51	41	40	39			34
2	87	80	75	70	79	73	68	64	60	57	54	48	46	43	37	35	34			29
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29			25
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	25			22
5	67	56	48	43	61	52	45	40	43	38	34	34	31	28	27	24	22			19
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	24	22	20			17
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18			15
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	21	18	16			14
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15			12
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17849	17849	17849
5°	17878	16981	16854
10°	17701	16105	15574
15°	17459	15072	14114
20°	17137	13896	12587
25°	16807	12690	11188
30°	16364	11516	9663
35°	15930	10332	8352
40°	15489	9168	7002
45°	14976	7967	5825
50°	14446	6809	4743
55°	13893	5651	3764
60°	13251	4520	2848
65°	12513	3447	2315
70°	11624	2501	1842
75°	10506	1906	1407
80°	8878	1291	944
85°	6201	592	456

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14976 cd/sqm

TEST NUMBER: P1000035

CATALOG NUMBER: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.7	1.8
10°-20°	290.1	4.9
20°-30°	407.3	6.8
30°-40°	444.0	7.4
40°-50°	408.1	6.8
50°-60°	320.5	5.4
60°-70°	208.6	3.5
70°-80°	107.4	1.8
80°-90°	29.6	0.5
90°-100°	41.0	0.7
100°-110°	152.7	2.6
110°-120°	405.1	6.8
120°-130°	671.9	11.3
130°-140°	713.7	12.0
140°-150°	663.3	11.1
150°-160°	533.3	8.9
160°-170°	343.6	5.8
170°-180°	118.3	2.0
0°-30°	803.1	13.5
0°-40°	1247.1	20.9
0°-60°	1975.6	33.1
0°-90°	2321.2	38.9
90°-120°	598.8	10.0
90°-150°	2647.7	44.4
90°-180°	3643.0	61.1
0°-180°	5964.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1109	1118	1115	107
15°	1072	1061	1027	1007	997	302
25°	974	941	874	832	816	448
35°	839	787	697	633	610	525
45°	686	617	510	438	413	530
55°	521	442	332	270	251	466
65°	352	269	178	143	140	349
75°	188	116	82	74	74	199
85°	44	22	19	19	19	50
90°	1	11	18	22	24	6
95°	58	29	35	40	39	69
105°	273	300	55	65	68	292
115°	517	532	555	138	74	509
125°	731	743	760	766	769	652
135°	904	919	927	936	934	699
145°	1049	1048	1064	1070	1066	656
155°	1155	1147	1158	1164	1156	532
165°	1217	1212	1215	1221	1215	344
175°	1245	1239	1241	1247	1238	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P1000035

CATALOG NUMBER: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1127.6	1127.6	1127.6	1127.6	1127.6
2.5°	1132.7	1127.6	1116.3	1126.6	1124.5
5°	1127.6	1122.5	1109.2	1118.4	1115.3
7.5°	1118.4	1112.3	1098.0	1102.1	1097.0
10°	1106.1	1099.0	1078.6	1075.5	1069.4
12.5°	1090.8	1081.7	1054.1	1048.0	1036.8
15°	1072.5	1061.2	1026.6	1007.2	997.0
17.5°	1051.0	1034.7	991.9	969.4	953.1
20°	1026.6	1006.1	955.1	929.6	907.2
22.5°	1000.0	976.6	917.4	882.7	867.4
25°	973.5	940.8	873.5	831.6	816.3
27.5°	941.9	907.2	832.7	784.7	761.2
30°	908.2	869.4	787.8	735.7	708.2
32.5°	875.5	828.6	744.9	683.7	658.2
35°	838.8	786.8	697.0	632.7	610.2
37.5°	803.1	747.0	652.1	581.6	556.1
40°	765.3	704.1	605.1	532.7	506.1
42.5°	726.5	661.2	558.2	482.7	457.2
45°	685.7	617.4	510.2	437.8	413.3
47.5°	647.0	574.5	464.3	391.8	369.4
50°	604.1	531.6	419.4	349.0	327.6
52.5°	562.3	485.7	376.5	309.2	289.8
55°	521.4	441.8	331.6	270.4	251.0
57.5°	479.6	398.0	291.8	234.7	218.4
60°	436.7	355.1	250.0	198.0	181.6
62.5°	394.9	313.3	214.3	165.3	157.1
65°	352.0	269.4	177.6	142.9	139.8
67.5°	311.2	228.6	142.9	125.5	122.5
70°	268.4	188.8	118.4	108.2	104.1
72.5°	227.6	152.0	99.0	90.8	88.8
75°	187.8	116.3	81.6	74.5	73.5
77.5°	148.0	82.7	64.3	60.2	58.2
80°	111.2	59.2	49.0	44.9	44.9
82.5°	77.6	39.8	33.7	31.6	31.6
85°	43.9	22.4	19.4	19.4	19.4
87.5°	16.3	8.2	8.2	7.1	7.1
90°	0.9	10.8	18.0	22.5	24.3
92.5°	22.5	18.9	21.6	23.4	24.3
95°	58.4	28.8	35.1	39.6	38.7
97.5°	105.2	31.5	45.9	48.6	49.5
100°	159.1	36.0	51.2	58.4	60.2
102.5°	218.5	216.7	53.0	62.9	65.6
105°	273.3	300.3	54.8	64.7	68.3
107.5°	337.2	359.6	56.6	66.5	70.1
110°	398.3	417.2	157.3	67.4	71.0

TEST NUMBER: P1000035

CATALOG NUMBER: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	455.9	472.0	456.8	69.2	71.9
115°	517.0	532.3	554.8	138.5	73.7
117.5°	570.0	588.0	603.3	474.7	239.2
120°	629.4	642.9	659.1	669.8	548.5
122.5°	679.7	694.1	712.1	717.5	718.4
125°	731.0	742.7	759.8	766.0	768.7
127.5°	777.7	790.3	803.8	812.8	813.7
130°	821.8	836.2	846.1	856.0	855.1
132.5°	866.8	878.4	888.3	896.4	895.5
135°	904.5	918.9	927.0	936.0	934.2
137.5°	944.1	954.9	963.9	972.8	970.1
140°	982.7	989.9	999.8	1007.9	1003.4
142.5°	1015.1	1021.4	1033.1	1040.3	1035.8
145°	1049.3	1048.4	1063.7	1070.0	1065.5
147.5°	1078.9	1076.2	1091.5	1096.0	1092.4
150°	1107.7	1101.4	1115.8	1121.2	1116.7
152.5°	1132.0	1124.8	1138.3	1143.7	1137.4
155°	1155.4	1147.3	1158.1	1163.5	1156.3
157.5°	1174.2	1167.1	1175.1	1181.4	1174.2
160°	1190.4	1185.0	1190.4	1195.8	1189.5
162.5°	1204.8	1199.4	1203.9	1210.2	1202.1
165°	1217.4	1212.0	1214.7	1221.0	1214.7
167.5°	1227.3	1221.9	1224.6	1230.9	1222.8
170°	1235.4	1230.0	1231.8	1238.1	1230.0
172.5°	1240.8	1235.4	1237.2	1243.5	1235.4
175°	1245.3	1239.0	1240.8	1247.1	1238.1
177.5°	1247.1	1240.8	1241.7	1248.0	1239.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)