

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998734

Luminaire Tested: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998734
REPORT IS A COMBINATION OF REPORTS P984480 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4197.0 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74
1	103	99	95	92	97	93	90	87	84	81	79	75	73	71	67	65	64	64	64	60
2	94	87	81	76	89	83	77	73	74	70	66	67	63	61	59	57	55	55	55	51
3	86	77	70	64	82	73	67	62	66	61	57	59	55	52	53	50	48	48	48	44
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	45	42	42	42	39
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37	37	37	34
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	33	33	30
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29	29	29	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	27	27	24
9	55	43	35	30	52	41	34	29	38	32	27	34	29	26	31	27	24	24	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20950	20950	20950	20950
5°	21000	22337	21081	17772
10°	20756	24384	20887	14652
15°	20252	25721	20534	12342
20°	19937	24150	19937	10726
25°	19302	20747	19390	9593
30°	18256	16309	18604	8689
35°	17330	11278	17620	7951
40°	16266	8515	16450	7360
45°	14952	6997	15196	6725
50°	13817	6141	13841	6156
55°	12524	5233	12604	5539
60°	11143	4370	11297	4833
65°	9908	3554	10089	4127
70°	8679	2790	8900	3329
75°	7283	2025	7569	2414
80°	5684	1282	6092	1434
85°	3729	647	4026	477

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21656 cd/sqm

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	3.0
10°-20°	366.9	8.7
20°-30°	532.5	12.7
30°-40°	561.3	13.4
40°-50°	496.7	11.8
50°-60°	396.6	9.5
60°-70°	269.4	6.4
70°-80°	137.8	3.3
80°-90°	33.7	0.8
90°-100°	71.4	1.7
100°-110°	251.5	6.0
110°-120°	264.1	6.3
120°-130°	217.3	5.2
130°-140°	174.6	4.2
140°-150°	131.9	3.1
150°-160°	92.7	2.2
160°-170°	54.6	1.3
170°-180°	17.8	0.4
0°-30°	1025.5	24.4
0°-40°	1586.8	37.8
0°-60°	2480.2	59.1
0°-90°	2921.2	69.6
90°-120°	587.1	14.0
90°-150°	1110.8	26.5
90°-180°	1276.0	30.4
0°-180°	4197.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1324	1324	1324	1324	1324	
5°	1324	1478	1330	1176	1324	126
15°	1244	1817	1261	872	1244	351
25°	1118	1514	1123	700	1118	511
35°	912	824	928	581	912	571
45°	685	496	696	477	685	531
55°	470	349	473	369	470	419
65°	279	215	284	249	279	277
75°	130	106	135	126	130	140
85°	26	28	28	20	26	31
90°	0	12	0	12	0	2
95°	12	40	12	40	12	13
105°	43	397	43	397	43	46
115°	76	522	76	522	76	75
125°	106	424	106	424	106	94
135°	124	351	124	351	124	96
145°	142	280	142	280	142	89
155°	161	236	161	236	161	74
165°	176	207	176	207	176	49
175°	183	186	183	186	183	17
180°	183	183	183	183	183	

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1330.6	1333.7	1338.7	1339.8	1349.9	1358.1	1367.2	1367.2	1370.3	1369.3	1361.1
5°	1324.5	1333.7	1346.9	1358.1	1376.4	1384.5	1396.7	1405.9	1414.0	1420.1	1419.1
7.5°	1314.3	1330.6	1349.9	1371.3	1395.7	1409.9	1427.2	1443.5	1454.7	1464.9	1472.0
10°	1297.0	1324.5	1350.9	1379.4	1411.0	1430.3	1450.6	1472.0	1489.3	1508.6	1526.9
12.5°	1273.6	1313.3	1345.9	1383.5	1422.2	1443.5	1476.1	1492.3	1525.9	1574.7	1588.0
15°	1244.1	1298.0	1328.6	1376.4	1427.2	1444.5	1489.3	1515.7	1584.9	1615.4	1652.1
17.5°	1216.7	1276.7	1317.4	1372.3	1422.2	1455.7	1499.5	1553.4	1611.4	1655.1	1695.8
20°	1194.3	1252.3	1301.1	1362.1	1425.2	1467.9	1513.7	1578.8	1641.9	1686.6	1718.2
22.5°	1143.4	1217.7	1274.7	1342.8	1419.1	1478.1	1521.8	1593.1	1661.2	1688.7	1716.1
25°	1118.0	1182.1	1248.2	1325.5	1415.0	1485.2	1522.9	1602.2	1662.2	1672.4	1678.5
27.5°	1071.2	1143.4	1220.7	1309.2	1414.0	1473.0	1520.8	1593.1	1640.9	1633.8	1615.4
30°	1013.2	1101.7	1187.2	1282.8	1399.8	1463.9	1508.6	1574.7	1599.2	1562.5	1530.0
32.5°	970.5	1053.9	1148.5	1259.4	1383.5	1444.5	1488.3	1540.2	1545.2	1479.1	1424.2
35°	912.5	1005.1	1111.9	1228.9	1356.0	1411.0	1451.7	1483.2	1458.8	1366.2	1301.1
37.5°	860.6	952.2	1066.1	1185.1	1318.4	1372.3	1404.9	1409.9	1349.9	1268.5	1172.9
40°	803.7	898.3	1017.3	1142.4	1276.7	1323.5	1343.8	1328.6	1242.1	1147.5	1036.6
42.5°	746.7	840.3	968.4	1096.6	1223.8	1263.5	1271.6	1229.9	1124.1	1013.2	885.0
45°	684.6	782.3	910.5	1039.7	1162.7	1185.1	1186.1	1126.1	1001.0	885.0	766.0
47.5°	633.8	724.3	851.5	980.7	1084.4	1099.7	1093.6	1024.4	888.1	757.9	654.1
50°	577.8	664.3	790.4	917.6	1006.1	1010.2	994.9	896.2	763.0	643.9	561.5
52.5°	517.8	605.3	721.3	843.3	922.7	916.6	887.1	781.3	656.1	557.5	494.4
55°	470.0	547.3	656.1	775.2	831.1	813.8	781.3	673.4	574.8	491.3	436.4
57.5°	417.1	485.2	592.1	695.8	728.4	712.1	679.5	578.8	487.3	424.2	387.6
60°	367.2	429.3	522.9	609.4	634.8	617.5	579.8	489.3	423.2	370.3	342.8
62.5°	321.5	375.4	453.7	533.1	543.2	525.9	493.4	420.1	363.2	321.5	301.1
65°	278.7	329.6	392.7	452.7	461.8	443.5	410.0	357.1	309.3	282.8	263.5
67.5°	237.0	277.7	333.7	377.4	382.5	365.2	337.7	295.0	265.5	237.0	222.8
70°	200.4	230.9	274.7	310.3	312.3	296.0	281.8	243.1	220.7	200.4	189.2
72.5°	164.8	186.2	219.7	246.2	247.2	237.0	223.8	199.4	180.1	165.8	154.6
75°	130.2	148.5	168.9	192.3	191.2	183.1	172.9	157.7	141.4	132.2	127.2
77.5°	99.7	110.9	127.2	142.4	142.4	138.3	132.2	121.1	110.9	101.7	96.6
80°	71.2	78.3	91.6	96.6	98.7	97.7	92.6	84.4	80.4	73.2	71.2
82.5°	45.8	50.9	57.0	62.1	65.1	63.1	62.1	58.0	51.9	49.8	47.8
85°	26.4	28.5	31.5	34.6	35.6	34.6	36.6	33.6	30.5	30.5	29.5
87.5°	11.2	12.2	14.2	14.2	15.3	15.3	14.2	15.3	15.3	14.2	13.2
90°	0.4	1.4	2.8	3.5	4.2	4.8	5.3	7.0	9.5	11.6	12.0
92.5°	5.3	7.4	10.2	12.0	14.8	16.8	18.7	28.2	41.6	53.6	54.3
95°	12.3	13.7	17.3	20.4	26.1	30.3	34.5	50.7	81.4	122.3	138.1
97.5°	18.3	20.4	24.3	28.9	35.2	40.0	44.7	65.5	108.2	174.0	225.1
100°	27.1	28.2	31.4	37.0	44.0	49.0	53.9	72.6	115.6	191.7	278.3
102.5°	35.2	35.9	39.1	44.7	52.1	57.0	62.0	78.9	115.9	185.0	280.1
105°	43.0	44.4	46.9	52.1	59.9	64.8	69.8	86.3	117.7	175.8	261.1
107.5°	51.4	52.5	55.0	59.9	67.6	72.6	77.5	93.7	121.5	170.9	243.4
110°	59.9	61.3	63.4	68.0	75.4	80.5	85.6	101.1	126.5	169.5	231.5

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	67.6	69.1	71.5	75.7	82.8	88.1	93.4	108.2	131.8	169.8	223.7
115°	75.7	77.5	79.6	83.9	90.9	95.6	100.4	115.6	137.0	171.2	218.4
117.5°	84.2	85.6	87.7	91.6	98.3	103.2	108.2	122.3	142.7	173.3	215.6
120°	92.0	93.4	95.5	98.6	105.7	110.6	115.6	129.3	148.3	175.5	213.1
122.5°	99.4	100.4	102.5	106.0	113.1	118.2	123.3	136.0	153.3	177.9	211.7
125°	105.7	106.8	108.9	113.1	120.1	125.0	130.0	142.7	158.5	180.4	210.0
127.5°	111.0	112.4	115.2	119.8	126.5	131.6	136.7	149.0	163.5	182.8	208.9
130°	115.6	117.0	120.5	125.4	132.5	137.4	142.3	154.7	168.1	185.7	208.2
132.5°	119.8	121.5	125.4	130.7	138.1	143.0	148.0	159.6	172.6	188.5	207.9
135°	124.0	125.4	129.7	134.9	143.0	148.0	152.9	164.2	176.5	190.6	207.5
137.5°	127.9	129.7	133.9	139.5	147.6	152.2	156.8	168.1	179.7	192.7	207.5
140°	132.5	133.9	138.1	143.7	151.5	156.1	160.7	171.2	182.1	194.1	207.2
142.5°	137.0	138.1	142.0	147.6	155.0	159.2	163.5	173.7	184.3	195.2	207.2
145°	141.6	143.0	146.6	151.8	158.9	162.8	166.6	176.2	186.0	195.9	206.5
147.5°	146.6	147.6	151.1	156.1	162.1	165.6	169.1	178.3	187.1	196.2	205.4
150°	151.5	152.6	155.4	159.9	165.2	168.4	171.6	179.7	187.8	195.9	204.3
152.5°	156.4	156.8	159.6	163.5	168.4	171.2	174.0	181.1	188.1	195.2	202.6
155°	161.0	161.4	163.5	167.3	171.2	173.8	176.5	182.5	188.5	194.5	200.5
157.5°	164.9	165.2	167.0	170.5	173.7	176.0	178.3	183.6	188.5	193.1	198.4
160°	168.8	169.1	170.5	173.3	176.2	178.1	180.0	184.3	188.5	192.0	196.2
162.5°	172.6	172.3	173.7	175.8	178.3	179.7	181.1	184.6	188.1	191.0	194.5
165°	175.5	175.1	175.8	177.9	179.7	180.8	181.8	185.0	187.4	189.5	192.0
167.5°	177.9	177.6	178.3	179.7	181.1	181.8	182.5	185.0	187.1	188.1	189.9
170°	180.4	179.7	180.0	181.1	181.8	182.3	182.8	184.6	186.4	187.1	188.1
172.5°	181.8	181.4	181.1	182.1	182.5	182.8	183.2	184.3	185.3	185.7	186.0
175°	182.8	182.5	182.1	182.8	182.8	183.0	183.2	183.9	184.6	184.3	184.6
177.5°	183.6	182.8	182.5	183.2	183.2	183.2	183.2	183.6	184.3	183.6	183.2
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1375.4	1376.4	1378.4	1388.6	1393.7	1394.7	1390.6	1399.8	1402.8	1399.8	1397.7
5°	1440.5	1446.6	1458.8	1472.0	1471.0	1472.0	1478.1	1484.2	1486.2	1478.1	1481.2
7.5°	1497.4	1509.6	1522.9	1543.2	1543.2	1553.4	1557.5	1562.5	1574.7	1568.6	1566.6
10°	1562.5	1578.8	1603.2	1635.8	1636.8	1647.0	1657.1	1673.4	1678.5	1674.4	1676.5
12.5°	1643.9	1675.5	1677.5	1713.1	1729.4	1731.4	1747.7	1744.6	1754.8	1754.8	1772.1
15°	1679.5	1728.4	1755.8	1790.4	1800.6	1788.4	1801.6	1815.8	1816.9	1816.9	1815.8
17.5°	1743.6	1762.9	1790.4	1808.7	1812.8	1812.8	1813.8	1819.9	1815.8	1807.7	1813.8
20°	1756.8	1765.0	1775.2	1773.1	1775.2	1765.0	1754.8	1744.6	1745.7	1740.6	1755.8
22.5°	1732.4	1730.4	1707.0	1691.7	1691.7	1671.4	1652.1	1642.9	1633.8	1636.8	1641.9
25°	1671.4	1639.9	1611.4	1589.0	1583.9	1551.4	1524.9	1516.8	1501.5	1513.7	1515.7
27.5°	1573.7	1538.1	1492.3	1473.0	1446.6	1433.3	1415.0	1390.6	1359.1	1377.4	1374.3
30°	1469.0	1416.1	1378.4	1331.6	1289.9	1286.9	1252.3	1211.6	1195.3	1195.3	1204.5
32.5°	1352.0	1281.8	1226.8	1160.7	1120.0	1102.7	1061.0	1020.3	1029.5	999.0	1010.2
35°	1215.6	1123.1	1053.9	989.8	959.3	938.9	885.0	862.7	838.2	824.0	850.4
37.5°	1085.4	978.6	890.1	819.9	808.7	772.1	735.5	721.3	707.0	713.1	712.1
40°	926.7	832.1	752.8	697.9	678.5	661.2	636.8	619.5	610.4	615.5	616.5
42.5°	783.3	704.0	645.0	606.3	590.0	577.8	565.6	551.4	548.3	548.3	552.4
45°	672.4	607.3	567.6	536.1	527.0	517.8	508.6	502.5	500.5	496.4	499.5
47.5°	583.9	532.0	507.6	484.2	474.1	472.0	463.9	460.8	456.8	455.7	456.8
50°	509.7	477.1	454.7	441.5	434.4	431.3	427.3	421.2	419.1	424.2	422.2
52.5°	457.8	427.3	415.0	401.8	397.8	393.7	387.6	388.6	387.6	385.5	385.5
55°	405.9	386.6	374.4	364.2	363.2	359.1	354.0	352.0	351.0	348.9	352.0
57.5°	364.2	348.9	337.7	328.6	324.5	324.5	319.4	315.4	315.4	314.3	315.4
60°	322.5	307.2	300.1	290.9	287.9	286.9	283.8	281.8	278.7	278.7	278.7
62.5°	283.8	271.6	263.5	255.3	256.4	251.3	247.2	245.2	245.2	246.2	246.2
65°	247.2	239.1	228.9	221.8	219.7	218.7	216.7	215.7	212.6	214.6	214.6
67.5°	213.6	202.4	196.3	193.3	190.2	189.2	187.2	185.1	184.1	183.1	185.1
70°	180.1	170.9	165.8	163.8	160.7	159.7	158.7	155.6	156.7	157.7	158.7
72.5°	149.5	141.4	140.4	134.3	134.3	134.3	130.2	132.2	131.2	129.2	131.2
75°	118.0	113.9	111.9	108.8	109.9	108.8	107.8	104.8	104.8	105.8	106.8
77.5°	93.6	89.5	88.5	85.5	83.4	85.5	83.4	82.4	82.4	83.4	83.4
80°	69.2	67.1	64.1	64.1	64.1	63.1	63.1	63.1	62.1	61.0	62.1
82.5°	45.8	45.8	44.8	43.7	44.8	42.7	43.7	43.7	43.7	43.7	43.7
85°	29.5	28.5	28.5	27.5	27.5	27.5	28.5	26.4	26.4	27.5	27.5
87.5°	13.2	13.2	13.2	14.2	13.2	13.2	13.2	14.2	13.2	13.2	13.2
90°	11.6	11.3	10.6	11.3	11.4	11.6	11.6	11.6	11.6	11.6	11.6
92.5°	45.4	35.6	30.3	26.4	25.0	23.6	23.3	21.8	22.2	21.5	22.2
95°	120.8	92.3	70.8	56.0	52.2	48.3	43.7	40.9	39.8	40.2	39.8
97.5°	226.9	188.8	150.8	115.2	104.6	94.1	80.3	73.3	69.4	67.3	69.4
100°	329.1	321.7	278.0	229.7	208.4	187.1	157.8	142.7	132.5	126.1	132.5
102.5°	367.1	408.7	407.3	375.2	352.3	329.4	297.0	268.5	255.1	245.9	255.1
105°	354.8	428.1	467.9	472.4	466.6	460.8	439.0	417.1	402.0	397.1	402.0
107.5°	328.7	407.3	466.5	501.0	508.0	515.1	514.7	511.6	507.0	498.9	507.0
110°	304.4	378.7	441.8	486.9	501.4	515.8	530.9	537.6	540.8	540.4	540.8

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	287.5	352.7	412.6	461.5	478.6	495.7	518.2	530.6	537.3	539.7	537.3
115°	274.1	332.2	386.5	432.6	450.8	468.9	493.9	510.1	519.3	522.5	519.3
117.5°	264.9	315.3	363.9	406.9	424.2	441.4	467.2	484.4	493.9	496.4	493.9
120°	257.9	303.3	347.0	384.4	400.4	416.4	441.1	457.7	467.9	471.4	467.9
122.5°	251.9	293.8	332.9	367.8	381.9	396.0	417.5	433.7	442.5	445.3	442.5
125°	246.3	284.7	321.0	352.0	365.2	378.4	398.8	412.2	421.0	423.8	421.0
127.5°	241.0	275.5	309.0	338.6	350.9	363.2	381.2	393.9	401.6	403.7	401.6
130°	235.7	266.7	297.0	324.8	336.5	348.1	365.3	377.3	384.4	387.2	384.4
132.5°	231.5	258.2	285.7	310.7	321.4	332.2	349.1	361.1	367.5	369.9	367.5
135°	227.6	250.5	273.7	297.0	306.8	316.7	331.9	343.5	349.8	351.3	349.8
137.5°	224.8	244.2	264.2	283.3	292.1	300.9	315.3	325.5	331.2	333.3	331.2
140°	222.3	238.2	255.1	271.3	279.0	286.8	298.1	307.2	312.5	314.6	312.5
142.5°	219.8	233.2	247.0	260.4	266.5	272.7	283.3	291.4	295.9	295.9	295.9
145°	217.7	228.7	240.3	251.2	256.3	261.4	269.9	275.9	279.4	280.4	279.4
147.5°	215.6	225.1	234.6	243.4	247.3	251.2	258.6	263.5	266.0	266.7	266.0
150°	212.8	221.3	229.0	236.4	239.6	242.7	248.0	252.3	254.4	254.7	254.4
152.5°	210.3	217.4	224.4	230.4	233.0	235.7	239.6	243.1	244.5	244.5	244.5
155°	207.2	213.9	219.5	224.8	226.8	228.7	232.5	235.0	236.4	235.7	236.4
157.5°	204.3	209.6	214.6	219.1	220.7	222.3	225.1	227.2	227.9	227.9	227.9
160°	201.2	205.7	209.6	213.5	214.8	216.0	218.4	220.2	220.5	220.5	220.5
162.5°	198.4	201.9	205.0	208.2	209.1	210.0	212.4	213.5	213.9	213.5	213.9
165°	195.2	198.0	200.5	202.9	203.6	204.3	205.7	207.2	207.2	206.8	207.2
167.5°	192.0	194.1	196.2	198.0	198.7	199.4	200.1	200.8	200.8	200.5	200.8
170°	189.5	191.3	192.4	193.8	194.2	194.5	194.8	195.9	195.5	194.8	195.5
172.5°	187.1	188.1	188.8	189.9	190.0	190.2	190.6	191.0	190.6	190.2	190.6
175°	185.0	186.0	186.4	186.7	186.9	187.1	187.1	187.4	187.1	186.4	187.1
177.5°	183.6	184.3	184.3	184.6	184.6	184.6	184.6	184.6	184.3	183.6	184.3
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1402.8	1395.7	1389.6	1390.6	1395.7	1391.6	1381.5	1368.2	1363.2	1357.1	1363.2
5°	1487.3	1481.2	1469.0	1470.0	1466.9	1462.8	1446.6	1426.2	1426.2	1409.9	1407.9
7.5°	1570.7	1561.5	1553.4	1551.4	1540.2	1532.0	1517.8	1489.3	1478.1	1458.8	1447.6
10°	1664.3	1657.1	1648.0	1636.8	1630.7	1616.5	1593.1	1551.4	1531.0	1504.6	1485.2
12.5°	1758.9	1757.9	1737.5	1715.1	1714.1	1691.7	1675.5	1619.5	1592.0	1556.4	1510.7
15°	1818.9	1813.8	1802.6	1791.4	1794.5	1770.1	1733.4	1667.3	1649.0	1606.3	1557.5
17.5°	1817.9	1817.9	1814.8	1812.8	1809.7	1802.6	1782.3	1738.5	1709.0	1655.1	1609.3
20°	1759.9	1773.1	1776.2	1775.2	1785.3	1790.4	1789.4	1761.9	1738.5	1690.7	1643.9
22.5°	1643.9	1674.4	1687.7	1695.8	1717.2	1728.4	1754.8	1744.6	1738.5	1702.9	1663.3
25°	1536.1	1546.3	1585.9	1588.0	1617.5	1644.9	1671.4	1688.7	1711.1	1697.8	1664.3
27.5°	1396.7	1420.1	1448.6	1470.0	1476.1	1532.0	1575.8	1608.3	1659.2	1663.3	1652.1
30°	1239.0	1250.2	1297.0	1325.5	1358.1	1398.8	1461.8	1517.8	1563.6	1605.3	1619.5
32.5°	1046.8	1092.6	1120.0	1154.6	1183.1	1255.3	1332.6	1404.9	1457.8	1528.0	1558.5
35°	870.8	906.4	953.2	967.4	1019.3	1080.4	1181.1	1273.6	1354.0	1425.2	1487.3
37.5°	725.3	753.8	803.7	826.0	856.5	934.9	1019.3	1134.3	1230.9	1318.4	1395.7
40°	625.6	647.0	684.6	691.7	717.2	788.4	856.5	964.4	1092.6	1210.6	1295.0
42.5°	557.5	567.6	593.1	602.2	618.5	666.3	727.4	829.1	948.1	1070.2	1189.2
45°	508.6	515.8	531.0	539.2	559.5	580.9	630.7	712.1	805.7	928.8	1057.0
47.5°	464.9	474.1	480.2	485.2	496.4	519.8	552.4	612.4	701.9	814.8	938.9
50°	428.3	431.3	442.5	443.5	450.7	465.9	496.4	533.1	604.3	695.8	815.9
52.5°	391.7	394.7	401.8	408.9	412.0	424.2	444.6	475.1	528.0	600.2	707.0
55°	355.0	359.1	366.2	371.3	374.4	384.5	396.7	426.2	467.9	518.8	606.3
57.5°	318.4	327.6	329.6	332.7	337.7	348.9	360.1	377.4	410.0	456.8	520.8
60°	283.8	286.9	294.0	297.0	302.1	308.2	322.5	335.7	359.1	395.7	453.7
62.5°	248.2	255.3	258.4	261.4	265.5	272.6	281.8	296.0	316.4	345.9	391.7
65°	217.7	218.7	224.8	228.9	233.0	238.0	247.2	260.4	272.6	300.1	333.7
67.5°	188.2	190.2	192.3	196.3	201.4	206.5	214.6	221.8	237.0	255.3	281.8
70°	159.7	159.7	164.8	167.9	166.8	172.9	179.0	187.2	198.4	215.7	237.0
72.5°	134.3	133.3	137.3	138.3	140.4	144.5	148.5	156.7	162.8	176.0	192.3
75°	106.8	108.8	110.9	110.9	113.9	117.0	121.1	125.1	132.2	140.4	152.6
77.5°	84.4	84.4	86.5	87.5	90.5	89.5	93.6	97.7	102.7	109.9	119.0
80°	62.1	64.1	64.1	64.1	65.1	66.1	70.2	73.2	76.3	81.4	85.5
82.5°	43.7	43.7	45.8	45.8	45.8	47.8	47.8	48.8	50.9	53.9	57.0
85°	27.5	27.5	27.5	28.5	27.5	28.5	30.5	29.5	30.5	32.6	32.6
87.5°	13.2	13.2	13.2	13.2	13.2	14.2	13.2	14.2	15.3	15.3	15.3
90°	11.6	11.6	11.6	11.4	11.3	10.6	11.3	11.6	12.0	11.6	9.5
92.5°	21.8	23.3	23.6	25.0	26.4	30.3	35.6	45.4	54.3	53.6	41.6
95°	40.9	43.7	48.3	52.2	56.0	70.8	92.3	120.8	138.1	122.3	81.4
97.5°	73.3	80.3	94.1	104.6	115.2	150.8	188.8	226.9	225.1	174.0	108.2
100°	142.7	157.8	187.1	208.4	229.7	278.0	321.7	329.1	278.3	191.7	115.6
102.5°	268.5	297.0	329.4	352.3	375.2	407.3	408.7	367.1	280.1	185.0	115.9
105°	417.1	439.0	460.8	466.6	472.4	467.9	428.1	354.8	261.1	175.8	117.7
107.5°	511.6	514.7	515.1	508.0	501.0	466.5	407.3	328.7	243.4	170.9	121.5
110°	537.6	530.9	515.8	501.4	486.9	441.8	378.7	304.4	231.5	169.5	126.5

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	530.6	518.2	495.7	478.6	461.5	412.6	352.7	287.5	223.7	169.8	131.8
115°	510.1	493.9	468.9	450.8	432.6	386.5	332.2	274.1	218.4	171.2	137.0
117.5°	484.4	467.2	441.4	424.2	406.9	363.9	315.3	264.9	215.6	173.3	142.7
120°	457.7	441.1	416.4	400.4	384.4	347.0	303.3	257.9	213.1	175.5	148.3
122.5°	433.7	417.5	396.0	381.9	367.8	332.9	293.8	251.9	211.7	177.9	153.3
125°	412.2	398.8	378.4	365.2	352.0	321.0	284.7	246.3	210.0	180.4	158.5
127.5°	393.9	381.2	363.2	350.9	338.6	309.0	275.5	241.0	208.9	182.8	163.5
130°	377.3	365.3	348.1	336.5	324.8	297.0	266.7	235.7	208.2	185.7	168.1
132.5°	361.1	349.1	332.2	321.4	310.7	285.7	258.2	231.5	207.9	188.5	172.6
135°	343.5	331.9	316.7	306.8	297.0	273.7	250.5	227.6	207.5	190.6	176.5
137.5°	325.5	315.3	300.9	292.1	283.3	264.2	244.2	224.8	207.5	192.7	179.7
140°	307.2	298.1	286.8	279.0	271.3	255.1	238.2	222.3	207.2	194.1	182.1
142.5°	291.4	283.3	272.7	266.5	260.4	247.0	233.2	219.8	207.2	195.2	184.3
145°	275.9	269.9	261.4	256.3	251.2	240.3	228.7	217.7	206.5	195.9	186.0
147.5°	263.5	258.6	251.2	247.3	243.4	234.6	225.1	215.6	205.4	196.2	187.1
150°	252.3	248.0	242.7	239.6	236.4	229.0	221.3	212.8	204.3	195.9	187.8
152.5°	243.1	239.6	235.7	233.0	230.4	224.4	217.4	210.3	202.6	195.2	188.1
155°	235.0	232.5	228.7	226.8	224.8	219.5	213.9	207.2	200.5	194.5	188.5
157.5°	227.2	225.1	222.3	220.7	219.1	214.6	209.6	204.3	198.4	193.1	188.5
160°	220.2	218.4	216.0	214.8	213.5	209.6	205.7	201.2	196.2	192.0	188.5
162.5°	213.5	212.4	210.0	209.1	208.2	205.0	201.9	198.4	194.5	191.0	188.1
165°	207.2	205.7	204.3	203.6	202.9	200.5	198.0	195.2	192.0	189.5	187.4
167.5°	200.8	200.1	199.4	198.7	198.0	196.2	194.1	192.0	189.9	188.1	187.1
170°	195.9	194.8	194.5	194.2	193.8	192.4	191.3	189.5	188.1	187.1	186.4
172.5°	191.0	190.6	190.2	190.0	189.9	188.8	188.1	187.1	186.0	185.7	185.3
175°	187.4	187.1	187.1	186.9	186.7	186.4	186.0	185.0	184.6	184.3	184.6
177.5°	184.6	184.6	184.6	184.6	184.6	184.3	184.3	183.6	183.2	183.6	184.3
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1358.1	1353.0	1349.9	1352.0	1345.9	1330.6	1330.6	1335.7	1329.6	1323.5	1314.3
5°	1395.7	1385.5	1379.4	1378.4	1364.2	1339.8	1334.7	1329.6	1316.4	1302.1	1286.9
7.5°	1432.3	1414.0	1403.8	1396.7	1376.4	1344.8	1331.6	1320.4	1299.1	1277.7	1258.4
10°	1462.8	1436.4	1424.2	1413.0	1386.6	1346.9	1325.5	1305.2	1277.7	1250.2	1225.8
12.5°	1487.3	1456.7	1441.5	1425.2	1392.7	1340.8	1314.3	1281.8	1254.3	1217.7	1193.3
15°	1528.0	1464.9	1450.6	1435.4	1401.8	1330.6	1298.0	1261.4	1223.8	1175.0	1148.5
17.5°	1560.5	1476.1	1475.1	1442.5	1398.8	1326.5	1276.7	1228.9	1188.2	1139.4	1097.6
20°	1579.8	1493.4	1477.1	1443.5	1388.6	1299.1	1247.2	1194.3	1150.5	1091.5	1049.8
22.5°	1596.1	1517.8	1475.1	1434.4	1367.2	1289.9	1213.6	1163.8	1103.7	1039.7	1000.0
25°	1602.2	1522.9	1478.1	1431.3	1352.0	1263.5	1177.0	1123.1	1055.9	998.0	944.0
27.5°	1603.2	1521.8	1466.9	1418.1	1330.6	1228.9	1140.4	1083.4	1009.1	942.0	888.1
30°	1593.1	1510.7	1460.8	1407.9	1310.3	1197.3	1095.6	1032.5	953.2	886.1	830.1
32.5°	1562.5	1488.3	1447.6	1389.6	1283.8	1153.6	1052.9	982.7	899.3	833.2	779.2
35°	1511.7	1460.8	1416.1	1362.1	1249.2	1112.9	1010.2	927.8	843.3	780.3	729.4
37.5°	1448.6	1421.1	1379.4	1326.5	1209.5	1076.3	962.3	870.8	786.4	725.3	675.5
40°	1363.2	1370.3	1329.6	1281.8	1162.7	1026.4	900.3	812.8	733.5	676.5	627.7
42.5°	1270.6	1300.1	1276.7	1230.9	1110.9	971.5	854.5	757.9	680.6	621.6	580.9
45°	1170.9	1221.8	1207.5	1173.9	1057.0	913.5	789.4	695.8	627.7	570.7	535.1
47.5°	1062.0	1134.3	1134.3	1109.9	996.9	855.5	733.5	637.8	570.7	530.0	495.4
50°	951.2	1032.5	1045.8	1029.5	929.8	789.4	665.3	578.8	520.8	481.2	455.7
52.5°	835.2	929.8	954.2	946.1	858.6	726.3	609.4	524.9	472.0	437.4	415.0
55°	724.3	834.2	860.6	863.7	782.3	657.2	547.3	473.0	422.2	398.8	379.4
57.5°	619.5	725.3	754.8	759.9	705.0	594.1	489.3	424.2	378.4	359.1	343.8
60°	530.0	618.5	657.2	668.4	620.5	520.8	435.4	372.3	337.7	319.4	305.2
62.5°	456.8	528.0	568.7	571.7	550.3	456.8	379.4	326.5	297.0	280.8	273.6
65°	385.5	449.6	474.1	486.3	469.0	395.7	327.6	283.8	260.4	246.2	239.1
67.5°	328.6	369.3	389.6	405.9	388.6	333.7	278.7	243.1	225.8	211.6	207.5
70°	269.6	303.1	318.4	334.7	319.4	277.7	238.0	205.5	190.2	179.0	174.0
72.5°	215.7	242.1	256.4	266.5	257.4	222.8	190.2	167.9	156.7	148.5	145.5
75°	170.9	189.2	197.4	204.5	200.4	174.0	153.6	135.3	125.1	118.0	116.0
77.5°	130.2	143.4	152.6	154.6	149.5	132.2	115.0	103.8	95.6	91.6	89.5
80°	92.6	100.7	105.8	108.8	103.8	96.6	84.4	76.3	69.2	64.1	63.1
82.5°	62.1	66.1	70.2	69.2	67.1	61.0	53.9	49.8	46.8	42.7	42.7
85°	35.6	36.6	38.7	39.7	38.7	34.6	30.5	28.5	26.4	23.4	23.4
87.5°	15.3	16.3	16.3	17.3	15.3	15.3	13.2	11.2	11.2	10.2	9.2
90°	7.0	5.3	4.8	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	28.2	18.7	16.8	14.8	12.0	10.2	7.4	5.3	7.4	10.2	12.0
95°	50.7	34.5	30.3	26.1	20.4	17.3	13.7	12.3	13.7	17.3	20.4
97.5°	65.5	44.7	40.0	35.2	28.9	24.3	20.4	18.3	20.4	24.3	28.9
100°	72.6	53.9	49.0	44.0	37.0	31.4	28.2	27.1	28.2	31.4	37.0
102.5°	78.9	62.0	57.0	52.1	44.7	39.1	35.9	35.2	35.9	39.1	44.7
105°	86.3	69.8	64.8	59.9	52.1	46.9	44.4	43.0	44.4	46.9	52.1
107.5°	93.7	77.5	72.6	67.6	59.9	55.0	52.5	51.4	52.5	55.0	59.9
110°	101.1	85.6	80.5	75.4	68.0	63.4	61.3	59.9	61.3	63.4	68.0

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	108.2	93.4	88.1	82.8	75.7	71.5	69.1	67.6	69.1	71.5	75.7
115°	115.6	100.4	95.6	90.9	83.9	79.6	77.5	75.7	77.5	79.6	83.9
117.5°	122.3	108.2	103.2	98.3	91.6	87.7	85.6	84.2	85.6	87.7	91.6
120°	129.3	115.6	110.6	105.7	98.6	95.5	93.4	92.0	93.4	95.5	98.6
122.5°	136.0	123.3	118.2	113.1	106.0	102.5	100.4	99.4	100.4	102.5	106.0
125°	142.7	130.0	125.0	120.1	113.1	108.9	106.8	105.7	106.8	108.9	113.1
127.5°	149.0	136.7	131.6	126.5	119.8	115.2	112.4	111.0	112.4	115.2	119.8
130°	154.7	142.3	137.4	132.5	125.4	120.5	117.0	115.6	117.0	120.5	125.4
132.5°	159.6	148.0	143.0	138.1	130.7	125.4	121.5	119.8	121.5	125.4	130.7
135°	164.2	152.9	148.0	143.0	134.9	129.7	125.4	124.0	125.4	129.7	134.9
137.5°	168.1	156.8	152.2	147.6	139.5	133.9	129.7	127.9	129.7	133.9	139.5
140°	171.2	160.7	156.1	151.5	143.7	138.1	133.9	132.5	133.9	138.1	143.7
142.5°	173.7	163.5	159.2	155.0	147.6	142.0	138.1	137.0	138.1	142.0	147.6
145°	176.2	166.6	162.8	158.9	151.8	146.6	143.0	141.6	143.0	146.6	151.8
147.5°	178.3	169.1	165.6	162.1	156.1	151.1	147.6	146.6	147.6	151.1	156.1
150°	179.7	171.6	168.4	165.2	159.9	155.4	152.6	151.5	152.6	155.4	159.9
152.5°	181.1	174.0	171.2	168.4	163.5	159.6	156.8	156.4	156.8	159.6	163.5
155°	182.5	176.5	173.8	171.2	167.3	163.5	161.4	161.0	161.4	163.5	167.3
157.5°	183.6	178.3	176.0	173.7	170.5	167.0	165.2	164.9	165.2	167.0	170.5
160°	184.3	180.0	178.1	176.2	173.3	170.5	169.1	168.8	169.1	170.5	173.3
162.5°	184.6	181.1	179.7	178.3	175.8	173.7	172.3	172.6	172.3	173.7	175.8
165°	185.0	181.8	180.8	179.7	177.9	175.8	175.1	175.5	175.1	175.8	177.9
167.5°	185.0	182.5	181.8	181.1	179.7	178.3	177.6	177.9	177.6	178.3	179.7
170°	184.6	182.8	182.3	181.8	181.1	180.0	179.7	180.4	179.7	180.0	181.1
172.5°	184.3	183.2	182.8	182.5	182.1	181.1	181.4	181.8	181.4	181.1	182.1
175°	183.9	183.2	183.0	182.8	182.8	182.1	182.5	182.8	182.5	182.1	182.8
177.5°	183.6	183.2	183.2	183.2	183.2	182.5	182.8	183.6	182.8	182.5	183.2
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1309.2	1314.3	1313.3	1303.1	1291.9	1282.8	1265.5	1267.5	1261.4	1262.4	1268.5
5°	1276.7	1276.7	1272.6	1258.4	1240.1	1229.9	1210.6	1205.5	1193.3	1192.3	1191.2
7.5°	1242.1	1237.0	1231.9	1211.6	1189.2	1172.9	1146.5	1140.4	1128.2	1120.0	1116.0
10°	1201.4	1194.3	1184.1	1160.7	1133.2	1112.9	1085.4	1077.3	1053.9	1043.7	1037.6
12.5°	1156.6	1152.6	1136.3	1117.0	1072.2	1049.8	1010.2	1018.3	994.9	974.6	971.5
15°	1111.9	1096.6	1087.5	1055.9	1002.0	991.8	960.3	944.0	922.7	906.4	906.4
17.5°	1068.1	1044.7	1024.4	990.8	951.2	922.7	899.3	891.1	864.7	848.4	845.4
20°	1010.2	983.7	978.6	930.8	903.3	871.8	849.4	829.1	809.8	802.6	797.5
22.5°	955.2	924.7	916.6	875.9	848.4	816.9	794.5	780.3	766.0	760.9	751.8
25°	896.2	877.9	865.7	822.0	791.4	761.9	746.7	736.5	723.3	722.3	716.2
27.5°	839.3	822.0	809.8	768.0	745.7	718.2	706.0	694.8	687.7	684.6	681.6
30°	790.4	771.1	756.9	726.3	698.9	676.5	666.3	659.2	655.1	650.0	649.0
32.5°	736.5	725.3	706.0	682.6	661.2	639.9	633.8	628.7	622.6	620.5	619.5
35°	690.7	675.5	663.3	636.8	627.7	609.4	602.2	598.2	590.0	588.0	586.0
37.5°	646.0	631.7	618.5	602.2	584.9	574.8	570.7	564.6	560.5	561.5	559.5
40°	601.2	590.0	579.8	562.6	552.4	547.3	539.2	533.1	531.0	532.0	531.0
42.5°	557.5	547.3	541.2	528.0	517.8	512.7	507.6	501.5	504.6	504.6	507.6
45°	517.8	508.6	504.6	494.4	488.3	480.2	475.1	474.1	478.1	477.1	477.1
47.5°	477.1	474.1	469.0	459.8	451.7	446.6	445.6	445.6	449.6	451.7	450.7
50°	445.6	439.5	433.4	426.2	420.1	418.1	415.0	417.1	421.2	421.2	423.2
52.5°	405.9	401.8	399.8	393.7	389.6	389.6	389.6	390.6	393.7	396.7	395.7
55°	371.3	368.3	366.2	363.2	358.1	359.1	358.1	360.1	363.2	366.2	368.3
57.5°	334.7	333.7	331.6	326.5	326.5	325.5	328.6	329.6	334.7	336.7	339.8
60°	302.1	299.1	299.1	295.0	295.0	295.0	298.1	301.1	305.2	306.2	308.2
62.5°	267.5	267.5	266.5	263.5	263.5	266.5	267.5	271.6	273.6	273.6	276.7
65°	235.0	234.0	233.0	234.0	235.0	235.0	238.0	240.1	242.1	243.1	244.1
67.5°	202.4	201.4	203.5	202.4	204.5	208.5	207.5	210.6	213.6	213.6	214.6
70°	171.9	174.0	172.9	175.0	174.0	176.0	179.0	180.1	180.1	181.1	184.1
72.5°	143.4	143.4	143.4	142.4	143.4	145.5	147.5	148.5	150.6	151.6	154.6
75°	116.0	116.0	113.9	116.0	116.0	118.0	120.0	120.0	120.0	122.1	125.1
77.5°	87.5	88.5	87.5	89.5	89.5	90.5	92.6	91.6	93.6	94.6	95.6
80°	64.1	63.1	63.1	63.1	64.1	64.1	66.1	67.1	67.1	70.2	68.2
82.5°	40.7	41.7	40.7	41.7	41.7	42.7	41.7	42.7	43.7	45.8	44.8
85°	23.4	22.4	22.4	23.4	22.4	22.4	23.4	22.4	23.4	22.4	23.4
87.5°	9.2	8.1	8.1	8.1	8.1	7.1	7.1	6.1	6.1	6.1	5.1
90°	4.2	4.8	5.3	7.0	9.5	11.6	12.0	11.6	11.3	10.6	11.3
92.5°	14.8	16.8	18.7	28.2	41.6	53.6	54.3	45.4	35.6	30.3	26.4
95°	26.1	30.3	34.5	50.7	81.4	122.3	138.1	120.8	92.3	70.8	56.0
97.5°	35.2	40.0	44.7	65.5	108.2	174.0	225.1	226.9	188.8	150.8	115.2
100°	44.0	49.0	53.9	72.6	115.6	191.7	278.3	329.1	321.7	278.0	229.7
102.5°	52.1	57.0	62.0	78.9	115.9	185.0	280.1	367.1	408.7	407.3	375.2
105°	59.9	64.8	69.8	86.3	117.7	175.8	261.1	354.8	428.1	467.9	472.4
107.5°	67.6	72.6	77.5	93.7	121.5	170.9	243.4	328.7	407.3	466.5	501.0
110°	75.4	80.5	85.6	101.1	126.5	169.5	231.5	304.4	378.7	441.8	486.9

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	82.8	88.1	93.4	108.2	131.8	169.8	223.7	287.5	352.7	412.6	461.5
115°	90.9	95.6	100.4	115.6	137.0	171.2	218.4	274.1	332.2	386.5	432.6
117.5°	98.3	103.2	108.2	122.3	142.7	173.3	215.6	264.9	315.3	363.9	406.9
120°	105.7	110.6	115.6	129.3	148.3	175.5	213.1	257.9	303.3	347.0	384.4
122.5°	113.1	118.2	123.3	136.0	153.3	177.9	211.7	251.9	293.8	332.9	367.8
125°	120.1	125.0	130.0	142.7	158.5	180.4	210.0	246.3	284.7	321.0	352.0
127.5°	126.5	131.6	136.7	149.0	163.5	182.8	208.9	241.0	275.5	309.0	338.6
130°	132.5	137.4	142.3	154.7	168.1	185.7	208.2	235.7	266.7	297.0	324.8
132.5°	138.1	143.0	148.0	159.6	172.6	188.5	207.9	231.5	258.2	285.7	310.7
135°	143.0	148.0	152.9	164.2	176.5	190.6	207.5	227.6	250.5	273.7	297.0
137.5°	147.6	152.2	156.8	168.1	179.7	192.7	207.5	224.8	244.2	264.2	283.3
140°	151.5	156.1	160.7	171.2	182.1	194.1	207.2	222.3	238.2	255.1	271.3
142.5°	155.0	159.2	163.5	173.7	184.3	195.2	207.2	219.8	233.2	247.0	260.4
145°	158.9	162.8	166.6	176.2	186.0	195.9	206.5	217.7	228.7	240.3	251.2
147.5°	162.1	165.6	169.1	178.3	187.1	196.2	205.4	215.6	225.1	234.6	243.4
150°	165.2	168.4	171.6	179.7	187.8	195.9	204.3	212.8	221.3	229.0	236.4
152.5°	168.4	171.2	174.0	181.1	188.1	195.2	202.6	210.3	217.4	224.4	230.4
155°	171.2	173.8	176.5	182.5	188.5	194.5	200.5	207.2	213.9	219.5	224.8
157.5°	173.7	176.0	178.3	183.6	188.5	193.1	198.4	204.3	209.6	214.6	219.1
160°	176.2	178.1	180.0	184.3	188.5	192.0	196.2	201.2	205.7	209.6	213.5
162.5°	178.3	179.7	181.1	184.6	188.1	191.0	194.5	198.4	201.9	205.0	208.2
165°	179.7	180.8	181.8	185.0	187.4	189.5	192.0	195.2	198.0	200.5	202.9
167.5°	181.1	181.8	182.5	185.0	187.1	188.1	189.9	192.0	194.1	196.2	198.0
170°	181.8	182.3	182.8	184.6	186.4	187.1	188.1	189.5	191.3	192.4	193.8
172.5°	182.5	182.8	183.2	184.3	185.3	185.7	186.0	187.1	188.1	188.8	189.9
175°	182.8	183.0	183.2	183.9	184.6	184.3	184.6	185.0	186.0	186.4	186.7
177.5°	183.2	183.2	183.2	183.6	184.3	183.6	183.2	183.6	184.3	184.3	184.6
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1261.4	1264.5	1257.4	1255.3	1257.4	1250.2	1252.3	1254.3	1254.3	1257.4	1259.4
5°	1188.2	1184.1	1177.0	1175.0	1172.9	1176.0	1173.9	1177.0	1178.0	1185.1	1186.1
7.5°	1116.0	1109.9	1103.7	1097.6	1095.6	1090.5	1095.6	1095.6	1102.7	1100.7	1105.8
10°	1030.5	1029.5	1021.3	1018.3	1014.2	1006.1	1017.3	1014.2	1019.3	1028.5	1030.5
12.5°	967.4	956.2	961.3	947.1	952.2	944.0	945.1	945.1	953.2	954.2	952.2
15°	907.4	898.3	885.0	878.9	875.9	871.8	885.0	886.1	879.9	894.2	889.1
17.5°	846.4	846.4	834.2	831.1	823.0	827.0	825.0	826.0	824.0	834.2	839.3
20°	793.5	788.4	784.3	785.3	775.2	773.1	771.1	773.1	780.3	787.4	789.4
22.5°	750.8	747.7	737.5	739.6	731.4	734.5	732.4	737.5	738.5	738.5	745.7
25°	710.1	706.0	707.0	702.9	699.9	699.9	696.8	699.9	704.0	706.0	707.0
27.5°	679.5	676.5	671.4	668.4	670.4	665.3	669.4	672.4	672.4	670.4	672.4
30°	642.9	645.0	645.0	634.8	638.9	636.8	639.9	641.9	641.9	642.9	640.9
32.5°	618.5	612.4	611.4	610.4	610.4	606.3	606.3	609.4	610.4	611.4	614.4
35°	586.0	586.0	580.9	583.9	579.8	580.9	579.8	580.9	582.9	579.8	582.9
37.5°	556.5	557.5	555.4	557.5	558.5	556.5	554.4	558.5	556.5	556.5	554.4
40°	531.0	530.0	531.0	531.0	531.0	532.0	530.0	530.0	530.0	528.0	525.9
42.5°	509.7	503.6	505.6	506.6	503.6	503.6	504.6	503.6	506.6	500.5	500.5
45°	479.1	477.1	478.1	478.1	480.2	477.1	479.1	480.2	477.1	476.1	474.1
47.5°	451.7	453.7	451.7	453.7	453.7	455.7	451.7	452.7	453.7	449.6	446.6
50°	424.2	424.2	427.3	426.2	427.3	425.2	425.2	424.2	425.2	423.2	420.1
52.5°	398.8	395.7	400.8	399.8	398.8	397.8	396.7	397.8	395.7	393.7	393.7
55°	367.2	367.2	370.3	371.3	371.3	369.3	367.2	368.3	367.2	366.2	365.2
57.5°	341.8	337.7	339.8	340.8	340.8	337.7	339.8	337.7	337.7	338.8	335.7
60°	309.3	309.3	307.2	310.3	310.3	308.2	308.2	309.3	307.2	306.2	305.2
62.5°	274.7	275.7	278.7	279.8	280.8	278.7	276.7	277.7	277.7	274.7	275.7
65°	245.2	247.2	251.3	250.3	248.2	249.2	247.2	248.2	245.2	246.2	243.1
67.5°	216.7	215.7	216.7	216.7	218.7	217.7	215.7	215.7	214.6	217.7	214.6
70°	186.2	186.2	186.2	186.2	187.2	188.2	186.2	184.1	185.1	183.1	182.1
72.5°	154.6	155.6	154.6	156.7	153.6	155.6	155.6	154.6	153.6	153.6	153.6
75°	125.1	127.2	124.1	125.1	124.1	126.1	125.1	125.1	123.1	122.1	123.1
77.5°	95.6	96.6	94.6	95.6	94.6	95.6	95.6	94.6	94.6	94.6	94.6
80°	68.2	69.2	68.2	67.1	66.1	68.2	66.1	67.1	68.2	67.1	69.2
82.5°	43.7	43.7	42.7	43.7	41.7	41.7	42.7	42.7	41.7	43.7	41.7
85°	21.4	21.4	23.4	21.4	20.3	20.3	20.3	21.4	20.3	22.4	21.4
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.1	4.1
90°	11.4	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.4
92.5°	25.0	23.6	23.3	21.8	22.2	21.5	22.2	21.8	23.3	23.6	25.0
95°	52.2	48.3	43.7	40.9	39.8	40.2	39.8	40.9	43.7	48.3	52.2
97.5°	104.6	94.1	80.3	73.3	69.4	67.3	69.4	73.3	80.3	94.1	104.6
100°	208.4	187.1	157.8	142.7	132.5	126.1	132.5	142.7	157.8	187.1	208.4
102.5°	352.3	329.4	297.0	268.5	255.1	245.9	255.1	268.5	297.0	329.4	352.3
105°	466.6	460.8	439.0	417.1	402.0	397.1	402.0	417.1	439.0	460.8	466.6
107.5°	508.0	515.1	514.7	511.6	507.0	498.9	507.0	511.6	514.7	515.1	508.0
110°	501.4	515.8	530.9	537.6	540.8	540.4	540.8	537.6	530.9	515.8	501.4

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	478.6	495.7	518.2	530.6	537.3	539.7	537.3	530.6	518.2	495.7	478.6
115°	450.8	468.9	493.9	510.1	519.3	522.5	519.3	510.1	493.9	468.9	450.8
117.5°	424.2	441.4	467.2	484.4	493.9	496.4	493.9	484.4	467.2	441.4	424.2
120°	400.4	416.4	441.1	457.7	467.9	471.4	467.9	457.7	441.1	416.4	400.4
122.5°	381.9	396.0	417.5	433.7	442.5	445.3	442.5	433.7	417.5	396.0	381.9
125°	365.2	378.4	398.8	412.2	421.0	423.8	421.0	412.2	398.8	378.4	365.2
127.5°	350.9	363.2	381.2	393.9	401.6	403.7	401.6	393.9	381.2	363.2	350.9
130°	336.5	348.1	365.3	377.3	384.4	387.2	384.4	377.3	365.3	348.1	336.5
132.5°	321.4	332.2	349.1	361.1	367.5	369.9	367.5	361.1	349.1	332.2	321.4
135°	306.8	316.7	331.9	343.5	349.8	351.3	349.8	343.5	331.9	316.7	306.8
137.5°	292.1	300.9	315.3	325.5	331.2	333.3	331.2	325.5	315.3	300.9	292.1
140°	279.0	286.8	298.1	307.2	312.5	314.6	312.5	307.2	298.1	286.8	279.0
142.5°	266.5	272.7	283.3	291.4	295.9	295.9	295.9	291.4	283.3	272.7	266.5
145°	256.3	261.4	269.9	275.9	279.4	280.4	279.4	275.9	269.9	261.4	256.3
147.5°	247.3	251.2	258.6	263.5	266.0	266.7	266.0	263.5	258.6	251.2	247.3
150°	239.6	242.7	248.0	252.3	254.4	254.7	254.4	252.3	248.0	242.7	239.6
152.5°	233.0	235.7	239.6	243.1	244.5	244.5	244.5	243.1	239.6	235.7	233.0
155°	226.8	228.7	232.5	235.0	236.4	235.7	236.4	235.0	232.5	228.7	226.8
157.5°	220.7	222.3	225.1	227.2	227.9	227.9	227.9	227.2	225.1	222.3	220.7
160°	214.8	216.0	218.4	220.2	220.5	220.5	220.5	220.2	218.4	216.0	214.8
162.5°	209.1	210.0	212.4	213.5	213.9	213.5	213.9	213.5	212.4	210.0	209.1
165°	203.6	204.3	205.7	207.2	207.2	206.8	207.2	207.2	205.7	204.3	203.6
167.5°	198.7	199.4	200.1	200.8	200.8	200.5	200.8	200.8	200.1	199.4	198.7
170°	194.2	194.5	194.8	195.9	195.5	194.8	195.5	195.9	194.8	194.5	194.2
172.5°	190.0	190.2	190.6	191.0	190.6	190.2	190.6	191.0	190.6	190.2	190.0
175°	186.9	187.1	187.1	187.4	187.1	186.4	187.1	187.4	187.1	187.1	186.9
177.5°	184.6	184.6	184.6	184.6	184.3	183.6	184.3	184.6	184.6	184.6	184.6
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1256.3	1264.5	1261.4	1250.2	1263.5	1263.5	1272.6	1272.6	1283.8	1287.9	1294.0
5°	1185.1	1191.2	1196.3	1191.2	1200.4	1214.6	1222.8	1229.9	1245.1	1251.3	1260.4
7.5°	1108.8	1120.0	1125.1	1125.1	1140.4	1156.6	1172.9	1183.1	1204.5	1212.6	1221.8
10°	1034.6	1047.8	1058.0	1057.0	1082.4	1092.6	1112.9	1136.3	1157.7	1169.9	1183.1
12.5°	956.2	963.4	977.6	998.0	1004.1	1022.4	1045.8	1075.3	1113.9	1125.1	1144.4
15°	891.1	910.5	921.7	930.8	945.1	962.3	987.8	1016.3	1054.9	1079.3	1099.7
17.5°	836.2	861.6	868.8	866.7	885.0	911.5	941.0	962.3	996.9	1026.4	1045.8
20°	791.4	801.6	813.8	818.9	833.2	861.6	890.1	914.5	943.0	966.4	988.8
22.5°	746.7	754.8	765.0	774.1	785.3	801.6	829.1	859.6	887.1	909.4	934.9
25°	710.1	715.1	724.3	731.4	743.6	754.8	774.1	807.7	840.3	853.5	875.9
27.5°	674.5	678.5	684.6	692.8	698.9	710.1	727.4	754.8	788.4	801.6	832.1
30°	642.9	646.0	652.1	656.1	659.2	672.4	685.6	707.0	732.4	750.8	773.1
32.5°	613.4	616.5	622.6	623.6	627.7	634.8	647.0	666.3	688.7	704.0	723.3
35°	580.9	582.9	589.0	591.0	594.1	600.2	609.4	623.6	643.9	655.1	672.4
37.5°	555.4	554.4	558.5	561.5	565.6	568.7	571.7	586.0	601.2	611.4	624.6
40°	528.0	525.9	527.0	531.0	533.1	537.1	537.1	551.4	561.5	569.7	579.8
42.5°	500.5	499.5	497.4	499.5	501.5	502.5	503.6	513.7	523.9	531.0	542.2
45°	473.0	472.0	470.0	471.0	471.0	473.0	476.1	480.2	487.3	493.4	499.5
47.5°	447.6	445.6	442.5	441.5	443.5	443.5	443.5	447.6	454.7	456.8	462.9
50°	421.2	418.1	414.0	412.0	412.0	411.0	413.0	414.0	420.1	422.2	427.3
52.5°	392.7	390.6	386.6	382.5	383.5	381.5	382.5	383.5	385.5	388.6	391.7
55°	364.2	360.1	357.1	356.0	353.0	353.0	349.9	354.0	353.0	354.0	358.1
57.5°	336.7	332.7	327.6	325.5	322.5	321.5	319.4	318.4	319.4	322.5	325.5
60°	304.2	302.1	299.1	296.0	294.0	290.9	288.9	288.9	287.9	287.9	288.9
62.5°	272.6	271.6	267.5	266.5	264.5	262.5	259.4	257.4	257.4	259.4	260.4
65°	242.1	241.1	238.0	237.0	231.9	229.9	228.9	227.9	225.8	225.8	225.8
67.5°	213.6	210.6	210.6	205.5	201.4	199.4	197.4	196.3	196.3	196.3	197.4
70°	182.1	182.1	179.0	176.0	171.9	172.9	169.9	166.8	166.8	164.8	165.8
72.5°	151.6	150.6	147.5	146.5	143.4	140.4	138.3	140.4	137.3	136.3	137.3
75°	122.1	121.1	119.0	117.0	118.0	115.0	111.9	110.9	110.9	108.8	108.8
77.5°	93.6	95.6	91.6	90.5	88.5	86.5	85.5	84.4	84.4	84.4	86.5
80°	65.1	66.1	66.1	64.1	65.1	62.1	62.1	62.1	59.0	60.0	61.0
82.5°	41.7	41.7	40.7	41.7	40.7	40.7	39.7	39.7	38.7	38.7	39.7
85°	23.4	22.4	21.4	23.4	22.4	22.4	21.4	21.4	21.4	21.4	21.4
87.5°	5.1	6.1	6.1	6.1	6.1	7.1	7.1	7.1	8.1	8.1	8.1
90°	11.3	10.6	11.3	11.6	12.0	11.6	9.5	7.0	5.3	4.8	4.2
92.5°	26.4	30.3	35.6	45.4	54.3	53.6	41.6	28.2	18.7	16.8	14.8
95°	56.0	70.8	92.3	120.8	138.1	122.3	81.4	50.7	34.5	30.3	26.1
97.5°	115.2	150.8	188.8	226.9	225.1	174.0	108.2	65.5	44.7	40.0	35.2
100°	229.7	278.0	321.7	329.1	278.3	191.7	115.6	72.6	53.9	49.0	44.0
102.5°	375.2	407.3	408.7	367.1	280.1	185.0	115.9	78.9	62.0	57.0	52.1
105°	472.4	467.9	428.1	354.8	261.1	175.8	117.7	86.3	69.8	64.8	59.9
107.5°	501.0	466.5	407.3	328.7	243.4	170.9	121.5	93.7	77.5	72.6	67.6
110°	486.9	441.8	378.7	304.4	231.5	169.5	126.5	101.1	85.6	80.5	75.4

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	461.5	412.6	352.7	287.5	223.7	169.8	131.8	108.2	93.4	88.1	82.8
115°	432.6	386.5	332.2	274.1	218.4	171.2	137.0	115.6	100.4	95.6	90.9
117.5°	406.9	363.9	315.3	264.9	215.6	173.3	142.7	122.3	108.2	103.2	98.3
120°	384.4	347.0	303.3	257.9	213.1	175.5	148.3	129.3	115.6	110.6	105.7
122.5°	367.8	332.9	293.8	251.9	211.7	177.9	153.3	136.0	123.3	118.2	113.1
125°	352.0	321.0	284.7	246.3	210.0	180.4	158.5	142.7	130.0	125.0	120.1
127.5°	338.6	309.0	275.5	241.0	208.9	182.8	163.5	149.0	136.7	131.6	126.5
130°	324.8	297.0	266.7	235.7	208.2	185.7	168.1	154.7	142.3	137.4	132.5
132.5°	310.7	285.7	258.2	231.5	207.9	188.5	172.6	159.6	148.0	143.0	138.1
135°	297.0	273.7	250.5	227.6	207.5	190.6	176.5	164.2	152.9	148.0	143.0
137.5°	283.3	264.2	244.2	224.8	207.5	192.7	179.7	168.1	156.8	152.2	147.6
140°	271.3	255.1	238.2	222.3	207.2	194.1	182.1	171.2	160.7	156.1	151.5
142.5°	260.4	247.0	233.2	219.8	207.2	195.2	184.3	173.7	163.5	159.2	155.0
145°	251.2	240.3	228.7	217.7	206.5	195.9	186.0	176.2	166.6	162.8	158.9
147.5°	243.4	234.6	225.1	215.6	205.4	196.2	187.1	178.3	169.1	165.6	162.1
150°	236.4	229.0	221.3	212.8	204.3	195.9	187.8	179.7	171.6	168.4	165.2
152.5°	230.4	224.4	217.4	210.3	202.6	195.2	188.1	181.1	174.0	171.2	168.4
155°	224.8	219.5	213.9	207.2	200.5	194.5	188.5	182.5	176.5	173.8	171.2
157.5°	219.1	214.6	209.6	204.3	198.4	193.1	188.5	183.6	178.3	176.0	173.7
160°	213.5	209.6	205.7	201.2	196.2	192.0	188.5	184.3	180.0	178.1	176.2
162.5°	208.2	205.0	201.9	198.4	194.5	191.0	188.1	184.6	181.1	179.7	178.3
165°	202.9	200.5	198.0	195.2	192.0	189.5	187.4	185.0	181.8	180.8	179.7
167.5°	198.0	196.2	194.1	192.0	189.9	188.1	187.1	185.0	182.5	181.8	181.1
170°	193.8	192.4	191.3	189.5	188.1	187.1	186.4	184.6	182.8	182.3	181.8
172.5°	189.9	188.8	188.1	187.1	186.0	185.7	185.3	184.3	183.2	182.8	182.5
175°	186.7	186.4	186.0	185.0	184.6	184.3	184.6	183.9	183.2	183.0	182.8
177.5°	184.6	184.3	184.3	183.6	183.2	183.6	184.3	183.6	183.2	183.2	183.2
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1323.5	1323.5	1323.5	1323.5
2.5°	1299.1	1299.1	1314.3	1330.6
5°	1270.6	1277.7	1302.1	1324.5
7.5°	1243.1	1255.3	1285.8	1314.3
10°	1209.5	1225.8	1263.5	1297.0
12.5°	1177.0	1192.3	1236.0	1273.6
15°	1131.2	1150.5	1197.3	1244.1
17.5°	1085.4	1104.8	1161.7	1216.7
20°	1031.5	1057.0	1121.0	1194.3
22.5°	981.7	1013.2	1084.4	1143.4
25°	926.7	975.6	1041.7	1118.0
27.5°	877.9	926.7	993.9	1071.2
30°	823.0	872.8	942.0	1013.2
32.5°	770.1	815.9	883.0	970.5
35°	715.1	758.9	824.0	912.5
37.5°	665.3	708.0	779.2	860.6
40°	616.5	661.2	722.3	803.7
42.5°	570.7	610.4	665.3	746.7
45°	529.0	557.5	608.3	684.6
47.5°	485.2	510.7	557.5	633.8
50°	444.6	465.9	506.6	577.8
52.5°	404.9	423.2	460.8	517.8
55°	369.3	386.6	414.0	470.0
57.5°	332.7	345.9	372.3	417.1
60°	297.0	309.3	330.6	367.2
62.5°	261.4	271.6	292.0	321.5
65°	229.9	238.0	253.3	278.7
67.5°	199.4	204.5	216.7	237.0
70°	169.9	174.0	184.1	200.4
72.5°	138.3	142.4	153.6	164.8
75°	111.9	112.9	121.1	130.2
77.5°	87.5	86.5	92.6	99.7
80°	60.0	63.1	68.2	71.2
82.5°	40.7	41.7	43.7	45.8
85°	22.4	23.4	23.4	26.4
87.5°	9.2	10.2	10.2	11.2
90°	3.5	2.8	1.4	0.4
92.5°	12.0	10.2	7.4	5.3
95°	20.4	17.3	13.7	12.3
97.5°	28.9	24.3	20.4	18.3
100°	37.0	31.4	28.2	27.1
102.5°	44.7	39.1	35.9	35.2
105°	52.1	46.9	44.4	43.0
107.5°	59.9	55.0	52.5	51.4
110°	68.0	63.4	61.3	59.9

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	75.7	71.5	69.1	67.6
115°	83.9	79.6	77.5	75.7
117.5°	91.6	87.7	85.6	84.2
120°	98.6	95.5	93.4	92.0
122.5°	106.0	102.5	100.4	99.4
125°	113.1	108.9	106.8	105.7
127.5°	119.8	115.2	112.4	111.0
130°	125.4	120.5	117.0	115.6
132.5°	130.7	125.4	121.5	119.8
135°	134.9	129.7	125.4	124.0
137.5°	139.5	133.9	129.7	127.9
140°	143.7	138.1	133.9	132.5
142.5°	147.6	142.0	138.1	137.0
145°	151.8	146.6	143.0	141.6
147.5°	156.1	151.1	147.6	146.6
150°	159.9	155.4	152.6	151.5
152.5°	163.5	159.6	156.8	156.4
155°	167.3	163.5	161.4	161.0
157.5°	170.5	167.0	165.2	164.9
160°	173.3	170.5	169.1	168.8
162.5°	175.8	173.7	172.3	172.6
165°	177.9	175.8	175.1	175.5
167.5°	179.7	178.3	177.6	177.9
170°	181.1	180.0	179.7	180.4
172.5°	182.1	181.1	181.4	181.8
175°	182.8	182.1	182.5	182.8
177.5°	183.2	182.5	182.8	183.6
180°	183.2	183.2	183.2	183.2

TEST NUMBER: P998734

CATALOG NUMBER: SA2XXDIP-B675D330UB27-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.08	19.09	18.85	19.89	20.85	15.57	16.59	16.34	17.38	18.34
	3H	18.90	19.81	19.69	20.61	21.61	16.93	17.84	17.71	18.64	19.63
	4H	19.08	19.93	19.88	20.74	21.75	17.39	18.25	18.20	19.06	20.07
	6H	19.13	19.92	19.95	20.74	21.76	17.71	18.50	18.53	19.32	20.34
	8H	19.11	19.86	19.94	20.70	21.72	17.80	18.55	18.63	19.39	20.41
	12H	19.08	19.80	19.91	20.63	21.67	17.84	18.56	18.68	19.39	20.44
4H	2H	18.14	18.99	18.95	19.81	20.81	16.03	16.89	16.84	17.70	18.71
	3H	19.13	19.84	19.95	20.69	21.71	17.51	18.22	18.33	19.07	20.09
	4H	19.41	20.06	20.25	20.90	21.95	18.05	18.70	18.88	19.54	20.59
	6H	19.55	20.11	20.40	20.98	22.03	18.44	19.00	19.29	19.86	20.92
	8H	19.55	20.08	20.41	20.94	22.00	18.55	19.07	19.41	19.93	21.00
	12H	19.52	19.99	20.40	20.88	21.95	18.61	19.08	19.49	19.97	21.04
8H	4H	19.43	19.96	20.29	20.82	21.88	18.20	18.72	19.06	19.59	20.65
	6H	19.62	20.05	20.50	20.95	22.02	18.64	19.07	19.53	19.98	21.05
	8H	19.65	20.03	20.54	20.93	22.01	18.79	19.18	19.69	20.08	21.16
	12H	19.64	19.98	20.54	20.87	22.01	18.89	19.23	19.79	20.12	21.26
12H	4H	19.40	19.87	20.27	20.75	21.82	18.18	18.65	19.06	19.54	20.61
	6H	19.60	19.98	20.49	20.88	21.96	18.64	19.03	19.54	19.93	21.01
	8H	19.64	19.97	20.53	20.86	22.00	18.81	19.14	19.70	20.03	21.17