

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998775

Luminaire Tested: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998775
REPORT IS A COMBINATION OF REPORTS P984521 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4101.0 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	74	72	68	67	65
2	95	87	81	76	89	83	78	73	75	71	67	68	64	62	61	58	56
3	87	77	70	64	82	74	67	62	67	62	57	60	56	53	55	51	49
4	80	69	61	55	75	66	59	53	60	54	50	54	50	46	49	46	43
5	74	62	54	48	70	59	52	46	54	48	43	49	44	40	45	41	38
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	33
7	63	51	43	37	60	49	42	36	45	39	34	41	36	32	38	33	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25
10	52	40	32	27	49	38	31	27	35	29	25	32	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21015	21015	21015	21015
5°	21065	22407	21146	17826
10°	20820	24460	20951	14697
15°	20316	25800	20597	12380
20°	19999	24224	19999	10760
25°	19360	20811	19448	9622
30°	18312	16359	18661	8716
35°	17383	11312	17674	7975
40°	16315	8542	16501	7384
45°	14998	7019	15244	6746
50°	13860	6160	13884	6174
55°	12561	5249	12644	5555
60°	11179	4385	11334	4849
65°	9940	3566	10121	4141
70°	8705	2799	8926	3340
75°	7306	2031	7591	2421
80°	5700	1287	6108	1438
85°	3743	649	4040	480

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21722 cd/sqm

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.4	3.1
10°-20°	368.0	9.0
20°-30°	534.1	13.0
30°-40°	563.1	13.7
40°-50°	498.3	12.2
50°-60°	397.9	9.7
60°-70°	270.2	6.6
70°-80°	138.3	3.4
80°-90°	33.9	0.8
90°-100°	25.9	0.6
100°-110°	82.3	2.0
110°-120°	140.9	3.4
120°-130°	185.3	4.5
130°-140°	208.0	5.1
140°-150°	204.0	5.0
150°-160°	171.1	4.2
160°-170°	113.5	2.8
170°-180°	39.7	1.0
0°-30°	1028.6	25.1
0°-40°	1591.7	38.8
0°-60°	2487.8	60.7
0°-90°	2930.2	71.5
90°-120°	249.2	6.1
90°-150°	846.5	20.6
90°-180°	1171.0	28.6
0°-180°	4101.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1329	1483	1334	1180	1329	126
15°	1248	1822	1265	874	1248	352
25°	1121	1518	1126	702	1121	513
35°	915	826	931	583	915	573
45°	687	498	698	479	687	533
55°	471	350	474	370	471	421
65°	280	215	285	250	280	278
75°	131	106	136	126	131	140
85°	26	28	29	20	26	31
90°	0	12	0	12	0	3
95°	18	22	18	22	18	21
105°	76	78	76	78	76	80
115°	141	141	141	141	141	140
125°	206	206	206	206	206	184
135°	266	269	266	269	266	206
145°	323	326	323	326	323	202
155°	369	372	369	372	369	170
165°	402	402	402	402	402	113
175°	418	417	418	417	418	40
180°	419	419	419	419	419	

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1334.7	1337.8	1342.9	1343.9	1354.1	1362.3	1371.4	1371.4	1374.5	1373.5	1365.3
5°	1328.6	1337.8	1351.0	1362.3	1380.6	1388.8	1401.0	1410.2	1418.4	1424.5	1423.5
7.5°	1318.4	1334.7	1354.1	1375.5	1400.0	1414.3	1431.6	1448.0	1459.2	1469.4	1476.5
10°	1301.0	1328.6	1355.1	1383.7	1415.3	1434.7	1455.1	1476.5	1493.9	1513.3	1531.6
12.5°	1277.6	1317.4	1350.0	1387.8	1426.5	1448.0	1480.6	1496.9	1530.6	1579.6	1592.9
15°	1248.0	1302.0	1332.7	1380.6	1431.6	1449.0	1493.9	1520.4	1589.8	1620.4	1657.2
17.5°	1220.4	1280.6	1321.4	1376.5	1426.5	1460.2	1504.1	1558.2	1616.3	1660.2	1701.0
20°	1198.0	1256.1	1305.1	1366.3	1429.6	1472.5	1518.4	1583.7	1646.9	1691.8	1723.5
22.5°	1146.9	1221.4	1278.6	1346.9	1423.5	1482.7	1526.5	1598.0	1666.3	1693.9	1721.4
25°	1121.4	1185.7	1252.0	1329.6	1419.4	1489.8	1527.6	1607.2	1667.4	1677.6	1683.7
27.5°	1074.5	1146.9	1224.5	1313.3	1418.4	1477.6	1525.5	1598.0	1645.9	1638.8	1620.4
30°	1016.3	1105.1	1190.8	1286.7	1404.1	1468.4	1513.3	1579.6	1604.1	1567.4	1534.7
32.5°	973.5	1057.1	1152.0	1263.3	1387.8	1449.0	1492.9	1544.9	1550.0	1483.7	1428.6
35°	915.3	1008.2	1115.3	1232.7	1360.2	1415.3	1456.1	1487.8	1463.3	1370.4	1305.1
37.5°	863.3	955.1	1069.4	1188.8	1322.5	1376.5	1409.2	1414.3	1354.1	1272.5	1176.5
40°	806.1	901.0	1020.4	1145.9	1280.6	1327.6	1348.0	1332.7	1245.9	1151.0	1039.8
42.5°	749.0	842.9	971.4	1100.0	1227.6	1267.4	1275.5	1233.7	1127.6	1016.3	887.8
45°	686.7	784.7	913.3	1042.9	1166.3	1188.8	1189.8	1129.6	1004.1	887.8	768.4
47.5°	635.7	726.5	854.1	983.7	1087.8	1103.1	1096.9	1027.6	890.8	760.2	656.1
50°	579.6	666.3	792.9	920.4	1009.2	1013.3	998.0	899.0	765.3	645.9	563.3
52.5°	519.4	607.1	723.5	845.9	925.5	919.4	889.8	783.7	658.2	559.2	495.9
55°	471.4	549.0	658.2	777.6	833.7	816.3	783.7	675.5	576.5	492.9	437.8
57.5°	418.4	486.7	593.9	698.0	730.6	714.3	681.6	580.6	488.8	425.5	388.8
60°	368.4	430.6	524.5	611.2	636.7	619.4	581.6	490.8	424.5	371.4	343.9
62.5°	322.5	376.5	455.1	534.7	544.9	527.6	494.9	421.4	364.3	322.5	302.0
65°	279.6	330.6	393.9	454.1	463.3	444.9	411.2	358.2	310.2	283.7	264.3
67.5°	237.8	278.6	334.7	378.6	383.7	366.3	338.8	295.9	266.3	237.8	223.5
70°	201.0	231.6	275.5	311.2	313.3	296.9	282.7	243.9	221.4	201.0	189.8
72.5°	165.3	186.7	220.4	246.9	248.0	237.8	224.5	200.0	180.6	166.3	155.1
75°	130.6	149.0	169.4	192.9	191.8	183.7	173.5	158.2	141.8	132.7	127.6
77.5°	100.0	111.2	127.6	142.9	142.9	138.8	132.7	121.4	111.2	102.0	96.9
80°	71.4	78.6	91.8	96.9	99.0	98.0	92.9	84.7	80.6	73.5	71.4
82.5°	45.9	51.0	57.1	62.2	65.3	63.3	62.2	58.2	52.0	50.0	48.0
85°	26.5	28.6	31.6	34.7	35.7	34.7	36.7	33.7	30.6	30.6	29.6
87.5°	11.2	12.2	14.3	14.3	15.3	15.3	14.3	15.3	15.3	14.3	13.3
90°	0.4	1.3	2.3	3.2	4.1	4.6	5.5	7.2	8.9	10.7	12.4
92.5°	7.8	8.4	9.0	9.7	10.3	10.6	10.6	10.7	10.8	10.9	11.0
95°	18.4	19.2	20.0	20.7	21.5	21.9	22.0	22.1	22.3	22.4	22.6
97.5°	30.7	31.4	32.1	32.8	33.5	33.9	34.1	34.4	34.7	35.0	35.3
100°	44.9	45.5	46.1	46.8	47.4	47.7	47.8	48.1	48.3	48.6	48.8
102.5°	59.7	60.2	60.6	61.1	61.6	61.8	62.0	62.3	62.6	63.0	63.3
105°	76.0	76.2	76.4	76.7	76.9	77.0	77.1	77.2	77.4	77.5	77.7
107.5°	92.2	92.5	92.8	93.1	93.4	93.6	93.6	93.6	93.6	93.6	93.6
110°	107.8	108.3	108.7	109.2	109.7	109.9	109.9	109.9	109.9	109.9	109.9

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	124.7	125.2	125.7	126.2	126.7	126.9	126.9	126.8	126.7	126.6	126.5
115°	141.4	141.9	142.3	142.8	143.3	143.5	143.4	143.3	143.1	143.0	142.8
117.5°	158.0	158.6	159.2	159.9	160.5	160.8	160.6	160.2	159.8	159.4	159.0
120°	174.6	175.2	175.8	176.5	177.1	177.4	177.1	176.5	175.8	175.2	174.6
122.5°	189.8	190.6	191.4	192.1	192.9	193.3	193.1	192.7	192.3	191.9	191.5
125°	205.7	206.4	207.1	207.8	208.5	208.9	208.8	208.5	208.3	208.0	207.8
127.5°	221.2	222.1	222.9	223.8	224.7	225.1	224.9	224.6	224.3	224.0	223.7
130°	235.7	236.7	237.7	238.8	239.8	240.3	240.2	240.1	239.9	239.8	239.6
132.5°	252.0	252.8	253.6	254.3	255.1	255.5	255.5	255.6	255.7	255.8	255.9
135°	266.1	267.0	267.8	268.7	269.6	270.0	270.1	270.2	270.4	270.5	270.7
137.5°	281.7	282.4	283.1	283.8	284.5	284.8	284.9	285.0	285.2	285.3	285.5
140°	295.4	296.1	296.8	297.5	298.2	298.6	298.8	299.2	299.6	300.0	300.4
142.5°	309.6	310.3	311.0	311.7	312.4	312.8	312.9	313.1	313.4	313.6	313.8
145°	323.0	323.6	324.1	324.7	325.2	325.5	325.7	326.2	326.7	327.1	327.6
147.5°	335.0	335.7	336.4	337.1	337.8	338.2	338.4	338.7	339.0	339.3	339.6
150°	347.4	347.9	348.3	348.8	349.3	349.5	349.7	350.0	350.3	350.6	350.9
152.5°	358.3	358.8	359.3	359.8	360.3	360.5	360.7	361.1	361.4	361.8	362.2
155°	369.3	369.5	369.8	370.0	370.3	370.4	370.5	370.7	371.0	371.2	371.4
157.5°	378.8	379.0	379.1	379.3	379.4	379.5	379.6	379.8	379.9	380.1	380.3
160°	387.3	387.5	387.6	387.8	387.9	388.0	388.0	388.1	388.2	388.3	388.4
162.5°	395.1	395.1	395.1	395.1	395.1	395.1	395.1	395.2	395.3	395.3	395.4
165°	401.8	401.7	401.7	401.6	401.5	401.5	401.5	401.5	401.5	401.5	401.5
167.5°	407.8	407.6	407.4	407.1	406.9	406.8	406.8	406.8	406.8	406.8	406.8
170°	412.4	412.2	412.0	411.7	411.5	411.4	411.4	411.3	411.2	411.1	411.0
172.5°	415.6	415.4	415.1	414.9	414.6	414.5	414.5	414.4	414.3	414.3	414.2
175°	418.1	417.9	417.6	417.4	417.1	417.0	416.9	416.8	416.6	416.5	416.3
177.5°	419.5	419.3	419.0	418.8	418.5	418.4	418.3	418.2	418.0	417.9	417.7
180°	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1379.6	1380.6	1382.7	1392.9	1398.0	1399.0	1394.9	1404.1	1407.2	1404.1	1402.0
5°	1444.9	1451.0	1463.3	1476.5	1475.5	1476.5	1482.7	1488.8	1490.8	1482.7	1485.7
7.5°	1502.1	1514.3	1527.6	1548.0	1548.0	1558.2	1562.3	1567.4	1579.6	1573.5	1571.4
10°	1567.4	1583.7	1608.2	1640.8	1641.8	1652.1	1662.3	1678.6	1683.7	1679.6	1681.6
12.5°	1649.0	1680.6	1682.7	1718.4	1734.7	1736.7	1753.1	1750.0	1760.2	1760.2	1777.6
15°	1684.7	1733.7	1761.2	1795.9	1806.1	1793.9	1807.2	1821.4	1822.5	1822.5	1821.4
17.5°	1749.0	1768.4	1795.9	1814.3	1818.4	1818.4	1819.4	1825.5	1821.4	1813.3	1819.4
20°	1762.3	1770.4	1780.6	1778.6	1780.6	1770.4	1760.2	1750.0	1751.0	1745.9	1761.2
22.5°	1737.8	1735.7	1712.3	1696.9	1696.9	1676.5	1657.2	1648.0	1638.8	1641.8	1646.9
25°	1676.5	1644.9	1616.3	1593.9	1588.8	1556.1	1529.6	1521.4	1506.1	1518.4	1520.4
27.5°	1578.6	1542.9	1496.9	1477.6	1451.0	1437.8	1419.4	1394.9	1363.3	1381.6	1378.6
30°	1473.5	1420.4	1382.7	1335.7	1293.9	1290.8	1256.1	1215.3	1199.0	1199.0	1208.2
32.5°	1356.1	1285.7	1230.6	1164.3	1123.5	1106.1	1064.3	1023.5	1032.7	1002.0	1013.3
35°	1219.4	1126.5	1057.1	992.9	962.3	941.8	887.8	865.3	840.8	826.5	853.1
37.5°	1088.8	981.6	892.9	822.5	811.2	774.5	737.8	723.5	709.2	715.3	714.3
40°	929.6	834.7	755.1	700.0	680.6	663.3	638.8	621.4	612.2	617.4	618.4
42.5°	785.7	706.1	646.9	608.2	591.8	579.6	567.4	553.1	550.0	550.0	554.1
45°	674.5	609.2	569.4	537.8	528.6	519.4	510.2	504.1	502.0	498.0	501.0
47.5°	585.7	533.7	509.2	485.7	475.5	473.5	465.3	462.2	458.2	457.1	458.2
50°	511.2	478.6	456.1	442.9	435.7	432.7	428.6	422.5	420.4	425.5	423.5
52.5°	459.2	428.6	416.3	403.1	399.0	394.9	388.8	389.8	388.8	386.7	386.7
55°	407.1	387.8	375.5	365.3	364.3	360.2	355.1	353.1	352.0	350.0	353.1
57.5°	365.3	350.0	338.8	329.6	325.5	325.5	320.4	316.3	316.3	315.3	316.3
60°	323.5	308.2	301.0	291.8	288.8	287.8	284.7	282.7	279.6	279.6	279.6
62.5°	284.7	272.5	264.3	256.1	257.1	252.0	248.0	245.9	245.9	246.9	246.9
65°	248.0	239.8	229.6	222.5	220.4	219.4	217.3	216.3	213.3	215.3	215.3
67.5°	214.3	203.1	196.9	193.9	190.8	189.8	187.8	185.7	184.7	183.7	185.7
70°	180.6	171.4	166.3	164.3	161.2	160.2	159.2	156.1	157.1	158.2	159.2
72.5°	150.0	141.8	140.8	134.7	134.7	134.7	130.6	132.7	131.6	129.6	131.6
75°	118.4	114.3	112.2	109.2	110.2	109.2	108.2	105.1	105.1	106.1	107.1
77.5°	93.9	89.8	88.8	85.7	83.7	85.7	83.7	82.7	82.7	83.7	83.7
80°	69.4	67.3	64.3	64.3	64.3	63.3	63.3	63.3	62.2	61.2	62.2
82.5°	45.9	45.9	44.9	43.9	44.9	42.9	43.9	43.9	43.9	43.9	43.9
85°	29.6	28.6	28.6	27.6	27.6	27.6	28.6	26.5	26.5	27.6	27.6
87.5°	13.3	13.3	13.3	14.3	13.3	13.3	13.3	14.3	13.3	13.3	13.3
90°	12.2	12.1	11.9	11.8	11.7	11.7	11.8	11.9	11.9	12.0	11.9
92.5°	11.1	11.1	11.2	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3
95°	22.6	22.6	22.6	22.6	22.6	22.5	22.4	22.2	22.1	21.9	22.1
97.5°	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.3
100°	48.8	48.8	48.8	48.8	48.8	48.8	48.7	48.6	48.5	48.4	48.5
102.5°	63.4	63.4	63.5	63.6	63.6	63.6	63.5	63.4	63.4	63.3	63.4
105°	77.9	78.1	78.2	78.4	78.5	78.5	78.5	78.5	78.5	78.5	78.5
107.5°	93.7	93.8	93.9	94.0	94.0	93.8	93.4	93.0	92.6	92.2	92.6
110°	109.9	109.9	109.9	109.9	109.9	109.8	109.5	109.3	109.0	108.8	109.0

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	126.3	126.1	125.8	125.6	125.5	125.4	125.2	125.1	124.9	124.7	124.9
115°	142.7	142.6	142.5	142.4	142.4	142.3	142.1	141.8	141.6	141.4	141.6
117.5°	158.8	158.6	158.3	158.1	158.0	157.9	157.6	157.4	157.1	156.9	157.1
120°	174.6	174.6	174.6	174.6	174.6	174.5	174.2	174.0	173.7	173.5	173.7
122.5°	191.3	191.1	190.8	190.6	190.5	190.4	190.3	190.1	190.0	189.8	190.0
125°	207.6	207.3	207.1	206.8	206.7	206.7	206.6	206.5	206.5	206.4	206.5
127.5°	223.4	223.1	222.8	222.5	222.3	222.2	221.9	221.7	221.4	221.2	221.4
130°	239.4	239.3	239.1	239.0	238.9	238.7	238.4	238.1	237.8	237.5	237.8
132.5°	255.5	255.1	254.7	254.3	254.1	254.0	253.7	253.5	253.2	253.0	253.2
135°	270.6	270.5	270.4	270.3	270.3	270.2	270.0	269.7	269.5	269.3	269.5
137.5°	285.4	285.4	285.3	285.2	285.2	285.0	284.7	284.4	284.1	283.8	284.1
140°	300.4	300.4	300.4	300.4	300.4	300.2	299.9	299.6	299.3	299.0	299.3
142.5°	313.9	314.0	314.1	314.2	314.2	314.0	313.7	313.4	313.1	312.8	313.1
145°	327.7	327.8	327.9	328.0	328.0	327.8	327.5	327.2	326.8	326.5	326.8
147.5°	339.8	339.9	340.1	340.2	340.3	340.1	339.8	339.5	339.2	338.9	339.2
150°	351.1	351.4	351.6	351.9	352.0	351.9	351.6	351.4	351.1	350.9	351.1
152.5°	362.5	362.8	363.1	363.4	363.6	363.4	363.1	362.8	362.5	362.2	362.5
155°	371.8	372.2	372.6	373.0	373.2	373.1	372.8	372.6	372.3	372.1	372.3
157.5°	380.8	381.4	381.9	382.4	382.7	382.5	382.1	381.8	381.4	381.0	381.4
160°	388.9	389.3	389.8	390.3	390.5	390.3	390.0	389.7	389.4	389.1	389.4
162.5°	396.0	396.5	397.1	397.6	397.9	397.7	397.3	397.0	396.6	396.2	396.6
165°	402.0	402.6	403.1	403.6	403.9	403.7	403.3	403.0	402.6	402.2	402.6
167.5°	407.3	407.9	408.4	408.9	409.2	409.0	408.6	408.3	407.9	407.5	407.9
170°	411.6	412.1	412.7	413.2	413.5	413.3	412.8	412.3	411.9	411.4	411.9
172.5°	414.8	415.3	415.9	416.4	416.7	416.5	416.0	415.5	415.0	414.5	415.0
175°	416.9	417.4	418.0	418.5	418.8	418.6	418.1	417.6	417.2	416.7	417.2
177.5°	418.2	418.6	419.1	419.6	419.8	419.6	419.1	418.6	418.2	417.7	418.2
180°	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1407.2	1400.0	1393.9	1394.9	1400.0	1395.9	1385.7	1372.5	1367.4	1361.2	1367.4
5°	1491.8	1485.7	1473.5	1474.5	1471.4	1467.4	1451.0	1430.6	1430.6	1414.3	1412.3
7.5°	1575.5	1566.3	1558.2	1556.1	1544.9	1536.7	1522.5	1493.9	1482.7	1463.3	1452.0
10°	1669.4	1662.3	1653.1	1641.8	1635.7	1621.4	1598.0	1556.1	1535.7	1509.2	1489.8
12.5°	1764.3	1763.3	1742.9	1720.4	1719.4	1696.9	1680.6	1624.5	1596.9	1561.2	1515.3
15°	1824.5	1819.4	1808.2	1796.9	1800.0	1775.5	1738.8	1672.5	1654.1	1611.2	1562.3
17.5°	1823.5	1823.5	1820.4	1818.4	1815.3	1808.2	1787.8	1743.9	1714.3	1660.2	1614.3
20°	1765.3	1778.6	1781.6	1780.6	1790.8	1795.9	1794.9	1767.4	1743.9	1695.9	1649.0
22.5°	1649.0	1679.6	1692.9	1701.0	1722.5	1733.7	1760.2	1750.0	1743.9	1708.2	1668.4
25°	1540.8	1551.0	1590.8	1592.9	1622.5	1650.0	1676.5	1693.9	1716.3	1703.1	1669.4
27.5°	1401.0	1424.5	1453.1	1474.5	1480.6	1536.7	1580.6	1613.3	1664.3	1668.4	1657.2
30°	1242.9	1254.1	1301.0	1329.6	1362.3	1403.1	1466.3	1522.5	1568.4	1610.2	1624.5
32.5°	1050.0	1095.9	1123.5	1158.2	1186.7	1259.2	1336.7	1409.2	1462.3	1532.7	1563.3
35°	873.5	909.2	956.1	970.4	1022.5	1083.7	1184.7	1277.6	1358.2	1429.6	1491.8
37.5°	727.6	756.1	806.1	828.6	859.2	937.8	1022.5	1137.8	1234.7	1322.5	1400.0
40°	627.6	649.0	686.7	693.9	719.4	790.8	859.2	967.4	1095.9	1214.3	1299.0
42.5°	559.2	569.4	594.9	604.1	620.4	668.4	729.6	831.6	951.0	1073.5	1192.9
45°	510.2	517.4	532.7	540.8	561.2	582.7	632.7	714.3	808.2	931.6	1060.2
47.5°	466.3	475.5	481.6	486.7	498.0	521.4	554.1	614.3	704.1	817.4	941.8
50°	429.6	432.7	443.9	444.9	452.0	467.3	498.0	534.7	606.1	698.0	818.4
52.5°	392.9	395.9	403.1	410.2	413.3	425.5	445.9	476.5	529.6	602.0	709.2
55°	356.1	360.2	367.3	372.5	375.5	385.7	398.0	427.6	469.4	520.4	608.2
57.5°	319.4	328.6	330.6	333.7	338.8	350.0	361.2	378.6	411.2	458.2	522.5
60°	284.7	287.8	294.9	298.0	303.1	309.2	323.5	336.7	360.2	396.9	455.1
62.5°	249.0	256.1	259.2	262.2	266.3	273.5	282.7	296.9	317.3	346.9	392.9
65°	218.4	219.4	225.5	229.6	233.7	238.8	248.0	261.2	273.5	301.0	334.7
67.5°	188.8	190.8	192.9	196.9	202.0	207.1	215.3	222.5	237.8	256.1	282.7
70°	160.2	160.2	165.3	168.4	167.3	173.5	179.6	187.8	199.0	216.3	237.8
72.5°	134.7	133.7	137.8	138.8	140.8	144.9	149.0	157.1	163.3	176.5	192.9
75°	107.1	109.2	111.2	111.2	114.3	117.3	121.4	125.5	132.7	140.8	153.1
77.5°	84.7	84.7	86.7	87.8	90.8	89.8	93.9	98.0	103.1	110.2	119.4
80°	62.2	64.3	64.3	64.3	65.3	66.3	70.4	73.5	76.5	81.6	85.7
82.5°	43.9	43.9	45.9	45.9	45.9	48.0	48.0	49.0	51.0	54.1	57.1
85°	27.6	27.6	27.6	28.6	27.6	28.6	30.6	29.6	30.6	32.7	32.7
87.5°	13.3	13.3	13.3	13.3	13.3	14.3	13.3	14.3	15.3	15.3	15.3
90°	11.9	11.8	11.7	11.7	11.8	11.9	12.1	12.2	12.4	10.7	8.9
92.5°	11.3	11.3	11.3	11.3	11.3	11.2	11.1	11.1	11.0	10.9	10.8
95°	22.2	22.4	22.5	22.6	22.6	22.6	22.6	22.6	22.6	22.4	22.3
97.5°	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.0	34.7
100°	48.6	48.7	48.8	48.8	48.8	48.8	48.8	48.8	48.8	48.6	48.3
102.5°	63.4	63.5	63.6	63.6	63.6	63.5	63.4	63.4	63.3	63.0	62.6
105°	78.5	78.5	78.5	78.5	78.4	78.2	78.1	77.9	77.7	77.5	77.4
107.5°	93.0	93.4	93.8	94.0	94.0	93.9	93.8	93.7	93.6	93.6	93.6
110°	109.3	109.5	109.8	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	125.1	125.2	125.4	125.5	125.6	125.8	126.1	126.3	126.5	126.6	126.7
115°	141.8	142.1	142.3	142.4	142.4	142.5	142.6	142.7	142.8	143.0	143.1
117.5°	157.4	157.6	157.9	158.0	158.1	158.3	158.6	158.8	159.0	159.4	159.8
120°	174.0	174.2	174.5	174.6	174.6	174.6	174.6	174.6	174.6	175.2	175.8
122.5°	190.1	190.3	190.4	190.5	190.6	190.8	191.1	191.3	191.5	191.9	192.3
125°	206.5	206.6	206.7	206.7	206.8	207.1	207.3	207.6	207.8	208.0	208.3
127.5°	221.7	221.9	222.2	222.3	222.5	222.8	223.1	223.4	223.7	224.0	224.3
130°	238.1	238.4	238.7	238.9	239.0	239.1	239.3	239.4	239.6	239.8	239.9
132.5°	253.5	253.7	254.0	254.1	254.3	254.7	255.1	255.5	255.9	255.8	255.7
135°	269.7	270.0	270.2	270.3	270.3	270.4	270.5	270.6	270.7	270.5	270.4
137.5°	284.4	284.7	285.0	285.2	285.2	285.3	285.4	285.4	285.5	285.3	285.2
140°	299.6	299.9	300.2	300.4	300.4	300.4	300.4	300.4	300.4	300.0	299.6
142.5°	313.4	313.7	314.0	314.2	314.2	314.1	314.0	313.9	313.8	313.6	313.4
145°	327.2	327.5	327.8	328.0	328.0	327.9	327.8	327.7	327.6	327.1	326.7
147.5°	339.5	339.8	340.1	340.3	340.2	340.1	339.9	339.8	339.6	339.3	339.0
150°	351.4	351.6	351.9	352.0	351.9	351.6	351.4	351.1	350.9	350.6	350.3
152.5°	362.8	363.1	363.4	363.6	363.4	363.1	362.8	362.5	362.2	361.8	361.4
155°	372.6	372.8	373.1	373.2	373.0	372.6	372.2	371.8	371.4	371.2	371.0
157.5°	381.8	382.1	382.5	382.7	382.4	381.9	381.4	380.8	380.3	380.1	379.9
160°	389.7	390.0	390.3	390.5	390.3	389.8	389.3	388.9	388.4	388.3	388.2
162.5°	397.0	397.3	397.7	397.9	397.6	397.1	396.5	396.0	395.4	395.3	395.3
165°	403.0	403.3	403.7	403.9	403.6	403.1	402.6	402.0	401.5	401.5	401.5
167.5°	408.3	408.6	409.0	409.2	408.9	408.4	407.9	407.3	406.8	406.8	406.8
170°	412.3	412.8	413.3	413.5	413.2	412.7	412.1	411.6	411.0	411.1	411.2
172.5°	415.5	416.0	416.5	416.7	416.4	415.9	415.3	414.8	414.2	414.3	414.3
175°	417.6	418.1	418.6	418.8	418.5	418.0	417.4	416.9	416.3	416.5	416.6
177.5°	418.6	419.1	419.6	419.8	419.6	419.1	418.6	418.2	417.7	417.9	418.0
180°	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1362.3	1357.2	1354.1	1356.1	1350.0	1334.7	1334.7	1339.8	1333.7	1327.6	1318.4
5°	1400.0	1389.8	1383.7	1382.7	1368.4	1343.9	1338.8	1333.7	1320.4	1306.1	1290.8
7.5°	1436.7	1418.4	1408.2	1401.0	1380.6	1349.0	1335.7	1324.5	1303.1	1281.6	1262.3
10°	1467.4	1440.8	1428.6	1417.4	1390.8	1351.0	1329.6	1309.2	1281.6	1254.1	1229.6
12.5°	1491.8	1461.2	1445.9	1429.6	1396.9	1344.9	1318.4	1285.7	1258.2	1221.4	1196.9
15°	1532.7	1469.4	1455.1	1439.8	1406.1	1334.7	1302.0	1265.3	1227.6	1178.6	1152.0
17.5°	1565.3	1480.6	1479.6	1446.9	1403.1	1330.6	1280.6	1232.7	1191.8	1142.9	1101.0
20°	1584.7	1498.0	1481.6	1448.0	1392.9	1303.1	1251.0	1198.0	1154.1	1094.9	1053.1
22.5°	1601.0	1522.5	1479.6	1438.8	1371.4	1293.9	1217.4	1167.4	1107.1	1042.9	1003.1
25°	1607.2	1527.6	1482.7	1435.7	1356.1	1267.4	1180.6	1126.5	1059.2	1001.0	946.9
27.5°	1608.2	1526.5	1471.4	1422.5	1334.7	1232.7	1143.9	1086.7	1012.3	944.9	890.8
30°	1598.0	1515.3	1465.3	1412.3	1314.3	1201.0	1099.0	1035.7	956.1	888.8	832.7
32.5°	1567.4	1492.9	1452.0	1393.9	1287.8	1157.2	1056.1	985.7	902.0	835.7	781.6
35°	1516.3	1465.3	1420.4	1366.3	1253.1	1116.3	1013.3	930.6	845.9	782.7	731.6
37.5°	1453.1	1425.5	1383.7	1330.6	1213.3	1079.6	965.3	873.5	788.8	727.6	677.6
40°	1367.4	1374.5	1333.7	1285.7	1166.3	1029.6	903.1	815.3	735.7	678.6	629.6
42.5°	1274.5	1304.1	1280.6	1234.7	1114.3	974.5	857.1	760.2	682.7	623.5	582.7
45°	1174.5	1225.5	1211.2	1177.6	1060.2	916.3	791.8	698.0	629.6	572.5	536.7
47.5°	1065.3	1137.8	1137.8	1113.3	1000.0	858.2	735.7	639.8	572.5	531.6	496.9
50°	954.1	1035.7	1049.0	1032.7	932.7	791.8	667.4	580.6	522.5	482.7	457.1
52.5°	837.8	932.7	957.1	949.0	861.2	728.6	611.2	526.5	473.5	438.8	416.3
55°	726.5	836.7	863.3	866.3	784.7	659.2	549.0	474.5	423.5	400.0	380.6
57.5°	621.4	727.6	757.1	762.2	707.1	595.9	490.8	425.5	379.6	360.2	344.9
60°	531.6	620.4	659.2	670.4	622.5	522.5	436.7	373.5	338.8	320.4	306.1
62.5°	458.2	529.6	570.4	573.5	552.0	458.2	380.6	327.6	298.0	281.6	274.5
65°	386.7	451.0	475.5	487.8	470.4	396.9	328.6	284.7	261.2	246.9	239.8
67.5°	329.6	370.4	390.8	407.1	389.8	334.7	279.6	243.9	226.5	212.2	208.2
70°	270.4	304.1	319.4	335.7	320.4	278.6	238.8	206.1	190.8	179.6	174.5
72.5°	216.3	242.9	257.1	267.3	258.2	223.5	190.8	168.4	157.1	149.0	145.9
75°	171.4	189.8	198.0	205.1	201.0	174.5	154.1	135.7	125.5	118.4	116.3
77.5°	130.6	143.9	153.1	155.1	150.0	132.7	115.3	104.1	95.9	91.8	89.8
80°	92.9	101.0	106.1	109.2	104.1	96.9	84.7	76.5	69.4	64.3	63.3
82.5°	62.2	66.3	70.4	69.4	67.3	61.2	54.1	50.0	46.9	42.9	42.9
85°	35.7	36.7	38.8	39.8	38.8	34.7	30.6	28.6	26.5	23.5	23.5
87.5°	15.3	16.3	16.3	17.3	15.3	15.3	13.3	11.2	11.2	10.2	9.2
90°	7.2	5.5	4.6	4.1	3.2	2.3	1.3	0.4	1.3	2.3	3.2
92.5°	10.7	10.6	10.6	10.3	9.7	9.0	8.4	7.8	8.4	9.0	9.7
95°	22.1	22.0	21.9	21.5	20.7	20.0	19.2	18.4	19.2	20.0	20.7
97.5°	34.4	34.1	33.9	33.5	32.8	32.1	31.4	30.7	31.4	32.1	32.8
100°	48.1	47.8	47.7	47.4	46.8	46.1	45.5	44.9	45.5	46.1	46.8
102.5°	62.3	62.0	61.8	61.6	61.1	60.6	60.2	59.7	60.2	60.6	61.1
105°	77.2	77.1	77.0	76.9	76.7	76.4	76.2	76.0	76.2	76.4	76.7
107.5°	93.6	93.6	93.6	93.4	93.1	92.8	92.5	92.2	92.5	92.8	93.1
110°	109.9	109.9	109.9	109.7	109.2	108.7	108.3	107.8	108.3	108.7	109.2

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	126.8	126.9	126.9	126.7	126.2	125.7	125.2	124.7	125.2	125.7	126.2
115°	143.3	143.4	143.5	143.3	142.8	142.3	141.9	141.4	141.9	142.3	142.8
117.5°	160.2	160.6	160.8	160.5	159.9	159.2	158.6	158.0	158.6	159.2	159.9
120°	176.5	177.1	177.4	177.1	176.5	175.8	175.2	174.6	175.2	175.8	176.5
122.5°	192.7	193.1	193.3	192.9	192.1	191.4	190.6	189.8	190.6	191.4	192.1
125°	208.5	208.8	208.9	208.5	207.8	207.1	206.4	205.7	206.4	207.1	207.8
127.5°	224.6	224.9	225.1	224.7	223.8	222.9	222.1	221.2	222.1	222.9	223.8
130°	240.1	240.2	240.3	239.8	238.8	237.7	236.7	235.7	236.7	237.7	238.8
132.5°	255.6	255.5	255.5	255.1	254.3	253.6	252.8	252.0	252.8	253.6	254.3
135°	270.2	270.1	270.0	269.6	268.7	267.8	267.0	266.1	267.0	267.8	268.7
137.5°	285.0	284.9	284.8	284.5	283.8	283.1	282.4	281.7	282.4	283.1	283.8
140°	299.2	298.8	298.6	298.2	297.5	296.8	296.1	295.4	296.1	296.8	297.5
142.5°	313.1	312.9	312.8	312.4	311.7	311.0	310.3	309.6	310.3	311.0	311.7
145°	326.2	325.7	325.5	325.2	324.7	324.1	323.6	323.0	323.6	324.1	324.7
147.5°	338.7	338.4	338.2	337.8	337.1	336.4	335.7	335.0	335.7	336.4	337.1
150°	350.0	349.7	349.5	349.3	348.8	348.3	347.9	347.4	347.9	348.3	348.8
152.5°	361.1	360.7	360.5	360.3	359.8	359.3	358.8	358.3	358.8	359.3	359.8
155°	370.7	370.5	370.4	370.3	370.0	369.8	369.5	369.3	369.5	369.8	370.0
157.5°	379.8	379.6	379.5	379.4	379.3	379.1	379.0	378.8	379.0	379.1	379.3
160°	388.1	388.0	388.0	387.9	387.8	387.6	387.5	387.3	387.5	387.6	387.8
162.5°	395.2	395.1	395.1	395.1	395.1	395.1	395.1	395.1	395.1	395.1	395.1
165°	401.5	401.5	401.5	401.5	401.6	401.7	401.7	401.8	401.7	401.7	401.6
167.5°	406.8	406.8	406.8	406.9	407.1	407.4	407.6	407.8	407.6	407.4	407.1
170°	411.3	411.4	411.4	411.5	411.7	412.0	412.2	412.4	412.2	412.0	411.7
172.5°	414.4	414.5	414.5	414.6	414.9	415.1	415.4	415.6	415.4	415.1	414.9
175°	416.8	416.9	417.0	417.1	417.4	417.6	417.9	418.1	417.9	417.6	417.4
177.5°	418.2	418.3	418.4	418.5	418.8	419.0	419.3	419.5	419.3	419.0	418.8
180°	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1313.3	1318.4	1317.4	1307.2	1295.9	1286.7	1269.4	1271.4	1265.3	1266.3	1272.5
5°	1280.6	1280.6	1276.5	1262.3	1243.9	1233.7	1214.3	1209.2	1196.9	1195.9	1194.9
7.5°	1245.9	1240.8	1235.7	1215.3	1192.9	1176.5	1150.0	1143.9	1131.6	1123.5	1119.4
10°	1205.1	1198.0	1187.8	1164.3	1136.7	1116.3	1088.8	1080.6	1057.1	1046.9	1040.8
12.5°	1160.2	1156.1	1139.8	1120.4	1075.5	1053.1	1013.3	1021.4	998.0	977.6	974.5
15°	1115.3	1100.0	1090.8	1059.2	1005.1	994.9	963.3	946.9	925.5	909.2	909.2
17.5°	1071.4	1048.0	1027.6	993.9	954.1	925.5	902.0	893.9	867.4	851.0	848.0
20°	1013.3	986.7	981.6	933.7	906.1	874.5	852.0	831.6	812.2	805.1	800.0
22.5°	958.2	927.6	919.4	878.6	851.0	819.4	796.9	782.7	768.4	763.3	754.1
25°	899.0	880.6	868.4	824.5	793.9	764.3	749.0	738.8	725.5	724.5	718.4
27.5°	841.8	824.5	812.2	770.4	748.0	720.4	708.2	696.9	689.8	686.7	683.7
30°	792.9	773.5	759.2	728.6	701.0	678.6	668.4	661.2	657.1	652.0	651.0
32.5°	738.8	727.6	708.2	684.7	663.3	641.8	635.7	630.6	624.5	622.5	621.4
35°	692.9	677.6	665.3	638.8	629.6	611.2	604.1	600.0	591.8	589.8	587.8
37.5°	648.0	633.7	620.4	604.1	586.7	576.5	572.5	566.3	562.2	563.3	561.2
40°	603.1	591.8	581.6	564.3	554.1	549.0	540.8	534.7	532.7	533.7	532.7
42.5°	559.2	549.0	542.9	529.6	519.4	514.3	509.2	503.1	506.1	506.1	509.2
45°	519.4	510.2	506.1	495.9	489.8	481.6	476.5	475.5	479.6	478.6	478.6
47.5°	478.6	475.5	470.4	461.2	453.1	448.0	446.9	446.9	451.0	453.1	452.0
50°	446.9	440.8	434.7	427.6	421.4	419.4	416.3	418.4	422.5	422.5	424.5
52.5°	407.1	403.1	401.0	394.9	390.8	390.8	390.8	391.8	394.9	398.0	396.9
55°	372.5	369.4	367.3	364.3	359.2	360.2	359.2	361.2	364.3	367.3	369.4
57.5°	335.7	334.7	332.7	327.6	327.6	326.5	329.6	330.6	335.7	337.8	340.8
60°	303.1	300.0	300.0	295.9	295.9	295.9	299.0	302.0	306.1	307.1	309.2
62.5°	268.4	268.4	267.3	264.3	264.3	267.3	268.4	272.5	274.5	274.5	277.6
65°	235.7	234.7	233.7	234.7	235.7	235.7	238.8	240.8	242.9	243.9	244.9
67.5°	203.1	202.0	204.1	203.1	205.1	209.2	208.2	211.2	214.3	214.3	215.3
70°	172.5	174.5	173.5	175.5	174.5	176.5	179.6	180.6	180.6	181.6	184.7
72.5°	143.9	143.9	143.9	142.9	143.9	145.9	148.0	149.0	151.0	152.0	155.1
75°	116.3	116.3	114.3	116.3	116.3	118.4	120.4	120.4	120.4	122.4	125.5
77.5°	87.8	88.8	87.8	89.8	89.8	90.8	92.9	91.8	93.9	94.9	95.9
80°	64.3	63.3	63.3	63.3	64.3	64.3	66.3	67.3	67.3	70.4	68.4
82.5°	40.8	41.8	40.8	41.8	41.8	42.9	41.8	42.9	43.9	45.9	44.9
85°	23.5	22.4	22.4	23.5	22.4	22.4	23.5	22.4	23.5	22.4	23.5
87.5°	9.2	8.2	8.2	8.2	8.2	7.1	7.1	6.1	6.1	6.1	5.1
90°	4.1	4.6	5.5	7.2	8.9	10.7	12.4	12.2	12.1	11.9	11.8
92.5°	10.3	10.6	10.6	10.7	10.8	10.9	11.0	11.1	11.1	11.2	11.3
95°	21.5	21.9	22.0	22.1	22.3	22.4	22.6	22.6	22.6	22.6	22.6
97.5°	33.5	33.9	34.1	34.4	34.7	35.0	35.3	35.3	35.3	35.3	35.3
100°	47.4	47.7	47.8	48.1	48.3	48.6	48.8	48.8	48.8	48.8	48.8
102.5°	61.6	61.8	62.0	62.3	62.6	63.0	63.3	63.4	63.4	63.5	63.6
105°	76.9	77.0	77.1	77.2	77.4	77.5	77.7	77.9	78.1	78.2	78.4
107.5°	93.4	93.6	93.6	93.6	93.6	93.6	93.6	93.7	93.8	93.9	94.0
110°	109.7	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	126.7	126.9	126.9	126.8	126.7	126.6	126.5	126.3	126.1	125.8	125.6
115°	143.3	143.5	143.4	143.3	143.1	143.0	142.8	142.7	142.6	142.5	142.4
117.5°	160.5	160.8	160.6	160.2	159.8	159.4	159.0	158.8	158.6	158.3	158.1
120°	177.1	177.4	177.1	176.5	175.8	175.2	174.6	174.6	174.6	174.6	174.6
122.5°	192.9	193.3	193.1	192.7	192.3	191.9	191.5	191.3	191.1	190.8	190.6
125°	208.5	208.9	208.8	208.5	208.3	208.0	207.8	207.6	207.3	207.1	206.8
127.5°	224.7	225.1	224.9	224.6	224.3	224.0	223.7	223.4	223.1	222.8	222.5
130°	239.8	240.3	240.2	240.1	239.9	239.8	239.6	239.4	239.3	239.1	239.0
132.5°	255.1	255.5	255.5	255.6	255.7	255.8	255.9	255.5	255.1	254.7	254.3
135°	269.6	270.0	270.1	270.2	270.4	270.5	270.7	270.6	270.5	270.4	270.3
137.5°	284.5	284.8	284.9	285.0	285.2	285.3	285.5	285.4	285.4	285.3	285.2
140°	298.2	298.6	298.8	299.2	299.6	300.0	300.4	300.4	300.4	300.4	300.4
142.5°	312.4	312.8	312.9	313.1	313.4	313.6	313.8	313.9	314.0	314.1	314.2
145°	325.2	325.5	325.7	326.2	326.7	327.1	327.6	327.7	327.8	327.9	328.0
147.5°	337.8	338.2	338.4	338.7	339.0	339.3	339.6	339.8	339.9	340.1	340.2
150°	349.3	349.5	349.7	350.0	350.3	350.6	350.9	351.1	351.4	351.6	351.9
152.5°	360.3	360.5	360.7	361.1	361.4	361.8	362.2	362.5	362.8	363.1	363.4
155°	370.3	370.4	370.5	370.7	371.0	371.2	371.4	371.8	372.2	372.6	373.0
157.5°	379.4	379.5	379.6	379.8	379.9	380.1	380.3	380.8	381.4	381.9	382.4
160°	387.9	388.0	388.0	388.1	388.2	388.3	388.4	388.9	389.3	389.8	390.3
162.5°	395.1	395.1	395.1	395.2	395.3	395.3	395.4	396.0	396.5	397.1	397.6
165°	401.5	401.5	401.5	401.5	401.5	401.5	401.5	402.0	402.6	403.1	403.6
167.5°	406.9	406.8	406.8	406.8	406.8	406.8	406.8	407.3	407.9	408.4	408.9
170°	411.5	411.4	411.4	411.3	411.2	411.1	411.0	411.6	412.1	412.7	413.2
172.5°	414.6	414.5	414.5	414.4	414.3	414.3	414.2	414.8	415.3	415.9	416.4
175°	417.1	417.0	416.9	416.8	416.6	416.5	416.3	416.9	417.4	418.0	418.5
177.5°	418.5	418.4	418.3	418.2	418.0	417.9	417.7	418.2	418.6	419.1	419.6
180°	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1265.3	1268.4	1261.2	1259.2	1261.2	1254.1	1256.1	1258.2	1258.2	1261.2	1263.3
5°	1191.8	1187.8	1180.6	1178.6	1176.5	1179.6	1177.6	1180.6	1181.6	1188.8	1189.8
7.5°	1119.4	1113.3	1107.1	1101.0	1099.0	1093.9	1099.0	1099.0	1106.1	1104.1	1109.2
10°	1033.7	1032.7	1024.5	1021.4	1017.4	1009.2	1020.4	1017.4	1022.5	1031.6	1033.7
12.5°	970.4	959.2	964.3	950.0	955.1	946.9	948.0	948.0	956.1	957.1	955.1
15°	910.2	901.0	887.8	881.6	878.6	874.5	887.8	888.8	882.7	896.9	891.8
17.5°	849.0	849.0	836.7	833.7	825.5	829.6	827.6	828.6	826.5	836.7	841.8
20°	795.9	790.8	786.7	787.8	777.6	775.5	773.5	775.5	782.7	789.8	791.8
22.5°	753.1	750.0	739.8	741.8	733.7	736.7	734.7	739.8	740.8	740.8	748.0
25°	712.2	708.2	709.2	705.1	702.0	702.0	699.0	702.0	706.1	708.2	709.2
27.5°	681.6	678.6	673.5	670.4	672.5	667.4	671.4	674.5	674.5	672.5	674.5
30°	644.9	646.9	646.9	636.7	640.8	638.8	641.8	643.9	643.9	644.9	642.9
32.5°	620.4	614.3	613.3	612.2	612.2	608.2	608.2	611.2	612.2	613.3	616.3
35°	587.8	587.8	582.7	585.7	581.6	582.7	581.6	582.7	584.7	581.6	584.7
37.5°	558.2	559.2	557.1	559.2	560.2	558.2	556.1	560.2	558.2	558.2	556.1
40°	532.7	531.6	532.7	532.7	532.7	533.7	531.6	531.6	531.6	529.6	527.6
42.5°	511.2	505.1	507.1	508.2	505.1	505.1	506.1	505.1	508.2	502.0	502.0
45°	480.6	478.6	479.6	479.6	481.6	478.6	480.6	481.6	478.6	477.6	475.5
47.5°	453.1	455.1	453.1	455.1	455.1	457.1	453.1	454.1	455.1	451.0	448.0
50°	425.5	425.5	428.6	427.6	428.6	426.5	426.5	425.5	426.5	424.5	421.4
52.5°	400.0	396.9	402.0	401.0	400.0	399.0	398.0	399.0	396.9	394.9	394.9
55°	368.4	368.4	371.4	372.5	372.5	370.4	368.4	369.4	368.4	367.3	366.3
57.5°	342.9	338.8	340.8	341.8	341.8	338.8	340.8	338.8	338.8	339.8	336.7
60°	310.2	310.2	308.2	311.2	311.2	309.2	309.2	310.2	308.2	307.1	306.1
62.5°	275.5	276.5	279.6	280.6	281.6	279.6	277.6	278.6	278.6	275.5	276.5
65°	245.9	248.0	252.0	251.0	249.0	250.0	248.0	249.0	245.9	246.9	243.9
67.5°	217.3	216.3	217.3	217.3	219.4	218.4	216.3	216.3	215.3	218.4	215.3
70°	186.7	186.7	186.7	186.7	187.8	188.8	186.7	184.7	185.7	183.7	182.7
72.5°	155.1	156.1	155.1	157.1	154.1	156.1	156.1	155.1	154.1	154.1	154.1
75°	125.5	127.6	124.5	125.5	124.5	126.5	125.5	125.5	123.5	122.4	123.5
77.5°	95.9	96.9	94.9	95.9	94.9	95.9	95.9	94.9	94.9	94.9	94.9
80°	68.4	69.4	68.4	67.3	66.3	68.4	66.3	67.3	68.4	67.3	69.4
82.5°	43.9	43.9	42.9	43.9	41.8	41.8	42.9	42.9	41.8	43.9	41.8
85°	21.4	21.4	23.5	21.4	20.4	20.4	20.4	21.4	20.4	22.4	21.4
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.1	4.1
90°	11.7	11.7	11.8	11.9	11.9	12.0	11.9	11.9	11.8	11.7	11.7
92.5°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3
95°	22.6	22.5	22.4	22.2	22.1	21.9	22.1	22.2	22.4	22.5	22.6
97.5°	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.3	35.3
100°	48.8	48.8	48.7	48.6	48.5	48.4	48.5	48.6	48.7	48.8	48.8
102.5°	63.6	63.6	63.5	63.4	63.4	63.3	63.4	63.4	63.5	63.6	63.6
105°	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5
107.5°	94.0	93.8	93.4	93.0	92.6	92.2	92.6	93.0	93.4	93.8	94.0
110°	109.9	109.8	109.5	109.3	109.0	108.8	109.0	109.3	109.5	109.8	109.9

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	125.5	125.4	125.2	125.1	124.9	124.7	124.9	125.1	125.2	125.4	125.5
115°	142.4	142.3	142.1	141.8	141.6	141.4	141.6	141.8	142.1	142.3	142.4
117.5°	158.0	157.9	157.6	157.4	157.1	156.9	157.1	157.4	157.6	157.9	158.0
120°	174.6	174.5	174.2	174.0	173.7	173.5	173.7	174.0	174.2	174.5	174.6
122.5°	190.5	190.4	190.3	190.1	190.0	189.8	190.0	190.1	190.3	190.4	190.5
125°	206.7	206.7	206.6	206.5	206.5	206.4	206.5	206.5	206.6	206.7	206.7
127.5°	222.3	222.2	221.9	221.7	221.4	221.2	221.4	221.7	221.9	222.2	222.3
130°	238.9	238.7	238.4	238.1	237.8	237.5	237.8	238.1	238.4	238.7	238.9
132.5°	254.1	254.0	253.7	253.5	253.2	253.0	253.2	253.5	253.7	254.0	254.1
135°	270.3	270.2	270.0	269.7	269.5	269.3	269.5	269.7	270.0	270.2	270.3
137.5°	285.2	285.0	284.7	284.4	284.1	283.8	284.1	284.4	284.7	285.0	285.2
140°	300.4	300.2	299.9	299.6	299.3	299.0	299.3	299.6	299.9	300.2	300.4
142.5°	314.2	314.0	313.7	313.4	313.1	312.8	313.1	313.4	313.7	314.0	314.2
145°	328.0	327.8	327.5	327.2	326.8	326.5	326.8	327.2	327.5	327.8	328.0
147.5°	340.3	340.1	339.8	339.5	339.2	338.9	339.2	339.5	339.8	340.1	340.3
150°	352.0	351.9	351.6	351.4	351.1	350.9	351.1	351.4	351.6	351.9	352.0
152.5°	363.6	363.4	363.1	362.8	362.5	362.2	362.5	362.8	363.1	363.4	363.6
155°	373.2	373.1	372.8	372.6	372.3	372.1	372.3	372.6	372.8	373.1	373.2
157.5°	382.7	382.5	382.1	381.8	381.4	381.0	381.4	381.8	382.1	382.5	382.7
160°	390.5	390.3	390.0	389.7	389.4	389.1	389.4	389.7	390.0	390.3	390.5
162.5°	397.9	397.7	397.3	397.0	396.6	396.2	396.6	397.0	397.3	397.7	397.9
165°	403.9	403.7	403.3	403.0	402.6	402.2	402.6	403.0	403.3	403.7	403.9
167.5°	409.2	409.0	408.6	408.3	407.9	407.5	407.9	408.3	408.6	409.0	409.2
170°	413.5	413.3	412.8	412.3	411.9	411.4	411.9	412.3	412.8	413.3	413.5
172.5°	416.7	416.5	416.0	415.5	415.0	414.5	415.0	415.5	416.0	416.5	416.7
175°	418.8	418.6	418.1	417.6	417.2	416.7	417.2	417.6	418.1	418.6	418.8
177.5°	419.8	419.6	419.1	418.6	418.2	417.7	418.2	418.6	419.1	419.6	419.8
180°	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1260.2	1268.4	1265.3	1254.1	1267.4	1267.4	1276.5	1276.5	1287.8	1291.8	1298.0
5°	1188.8	1194.9	1200.0	1194.9	1204.1	1218.4	1226.5	1233.7	1249.0	1255.1	1264.3
7.5°	1112.3	1123.5	1128.6	1128.6	1143.9	1160.2	1176.5	1186.7	1208.2	1216.3	1225.5
10°	1037.8	1051.0	1061.2	1060.2	1085.7	1095.9	1116.3	1139.8	1161.2	1173.5	1186.7
12.5°	959.2	966.3	980.6	1001.0	1007.1	1025.5	1049.0	1078.6	1117.4	1128.6	1148.0
15°	893.9	913.3	924.5	933.7	948.0	965.3	990.8	1019.4	1058.2	1082.7	1103.1
17.5°	838.8	864.3	871.4	869.4	887.8	914.3	943.9	965.3	1000.0	1029.6	1049.0
20°	793.9	804.1	816.3	821.4	835.7	864.3	892.9	917.4	945.9	969.4	991.8
22.5°	749.0	757.1	767.4	776.5	787.8	804.1	831.6	862.3	889.8	912.3	937.8
25°	712.2	717.4	726.5	733.7	745.9	757.1	776.5	810.2	842.9	856.1	878.6
27.5°	676.5	680.6	686.7	694.9	701.0	712.2	729.6	757.1	790.8	804.1	834.7
30°	644.9	648.0	654.1	658.2	661.2	674.5	687.8	709.2	734.7	753.1	775.5
32.5°	615.3	618.4	624.5	625.5	629.6	636.7	649.0	668.4	690.8	706.1	725.5
35°	582.7	584.7	590.8	592.9	595.9	602.0	611.2	625.5	645.9	657.1	674.5
37.5°	557.1	556.1	560.2	563.3	567.4	570.4	573.5	587.8	603.1	613.3	626.5
40°	529.6	527.6	528.6	532.7	534.7	538.8	538.8	553.1	563.3	571.4	581.6
42.5°	502.0	501.0	499.0	501.0	503.1	504.1	505.1	515.3	525.5	532.7	543.9
45°	474.5	473.5	471.4	472.5	472.5	474.5	477.6	481.6	488.8	494.9	501.0
47.5°	449.0	446.9	443.9	442.9	444.9	444.9	444.9	449.0	456.1	458.2	464.3
50°	422.5	419.4	415.3	413.3	413.3	412.2	414.3	415.3	421.4	423.5	428.6
52.5°	393.9	391.8	387.8	383.7	384.7	382.7	383.7	384.7	386.7	389.8	392.9
55°	365.3	361.2	358.2	357.1	354.1	354.1	351.0	355.1	354.1	355.1	359.2
57.5°	337.8	333.7	328.6	326.5	323.5	322.5	320.4	319.4	320.4	323.5	326.5
60°	305.1	303.1	300.0	296.9	294.9	291.8	289.8	289.8	288.8	288.8	289.8
62.5°	273.5	272.5	268.4	267.3	265.3	263.3	260.2	258.2	258.2	260.2	261.2
65°	242.9	241.8	238.8	237.8	232.7	230.6	229.6	228.6	226.5	226.5	226.5
67.5°	214.3	211.2	211.2	206.1	202.0	200.0	198.0	196.9	196.9	196.9	198.0
70°	182.7	182.7	179.6	176.5	172.5	173.5	170.4	167.3	167.3	165.3	166.3
72.5°	152.0	151.0	148.0	146.9	143.9	140.8	138.8	140.8	137.8	136.7	137.8
75°	122.4	121.4	119.4	117.3	118.4	115.3	112.2	111.2	111.2	109.2	109.2
77.5°	93.9	95.9	91.8	90.8	88.8	86.7	85.7	84.7	84.7	84.7	86.7
80°	65.3	66.3	66.3	64.3	65.3	62.2	62.2	62.2	59.2	60.2	61.2
82.5°	41.8	41.8	40.8	41.8	40.8	40.8	39.8	39.8	38.8	38.8	39.8
85°	23.5	22.4	21.4	23.5	22.4	22.4	21.4	21.4	21.4	21.4	21.4
87.5°	5.1	6.1	6.1	6.1	6.1	7.1	7.1	7.1	8.2	8.2	8.2
90°	11.8	11.9	12.1	12.2	12.4	10.7	8.9	7.2	5.5	4.6	4.1
92.5°	11.3	11.2	11.1	11.1	11.0	10.9	10.8	10.7	10.6	10.6	10.3
95°	22.6	22.6	22.6	22.6	22.6	22.4	22.3	22.1	22.0	21.9	21.5
97.5°	35.3	35.3	35.3	35.3	35.3	35.0	34.7	34.4	34.1	33.9	33.5
100°	48.8	48.8	48.8	48.8	48.8	48.6	48.3	48.1	47.8	47.7	47.4
102.5°	63.6	63.5	63.4	63.4	63.3	63.0	62.6	62.3	62.0	61.8	61.6
105°	78.4	78.2	78.1	77.9	77.7	77.5	77.4	77.2	77.1	77.0	76.9
107.5°	94.0	93.9	93.8	93.7	93.6	93.6	93.6	93.6	93.6	93.6	93.4
110°	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.7

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	125.6	125.8	126.1	126.3	126.5	126.6	126.7	126.8	126.9	126.9	126.7
115°	142.4	142.5	142.6	142.7	142.8	143.0	143.1	143.3	143.4	143.5	143.3
117.5°	158.1	158.3	158.6	158.8	159.0	159.4	159.8	160.2	160.6	160.8	160.5
120°	174.6	174.6	174.6	174.6	174.6	175.2	175.8	176.5	177.1	177.4	177.1
122.5°	190.6	190.8	191.1	191.3	191.5	191.9	192.3	192.7	193.1	193.3	192.9
125°	206.8	207.1	207.3	207.6	207.8	208.0	208.3	208.5	208.8	208.9	208.5
127.5°	222.5	222.8	223.1	223.4	223.7	224.0	224.3	224.6	224.9	225.1	224.7
130°	239.0	239.1	239.3	239.4	239.6	239.8	239.9	240.1	240.2	240.3	239.8
132.5°	254.3	254.7	255.1	255.5	255.9	255.8	255.7	255.6	255.5	255.5	255.1
135°	270.3	270.4	270.5	270.6	270.7	270.5	270.4	270.2	270.1	270.0	269.6
137.5°	285.2	285.3	285.4	285.4	285.5	285.3	285.2	285.0	284.9	284.8	284.5
140°	300.4	300.4	300.4	300.4	300.4	300.0	299.6	299.2	298.8	298.6	298.2
142.5°	314.2	314.1	314.0	313.9	313.8	313.6	313.4	313.1	312.9	312.8	312.4
145°	328.0	327.9	327.8	327.7	327.6	327.1	326.7	326.2	325.7	325.5	325.2
147.5°	340.2	340.1	339.9	339.8	339.6	339.3	339.0	338.7	338.4	338.2	337.8
150°	351.9	351.6	351.4	351.1	350.9	350.6	350.3	350.0	349.7	349.5	349.3
152.5°	363.4	363.1	362.8	362.5	362.2	361.8	361.4	361.1	360.7	360.5	360.3
155°	373.0	372.6	372.2	371.8	371.4	371.2	371.0	370.7	370.5	370.4	370.3
157.5°	382.4	381.9	381.4	380.8	380.3	380.1	379.9	379.8	379.6	379.5	379.4
160°	390.3	389.8	389.3	388.9	388.4	388.3	388.2	388.1	388.0	388.0	387.9
162.5°	397.6	397.1	396.5	396.0	395.4	395.3	395.3	395.2	395.1	395.1	395.1
165°	403.6	403.1	402.6	402.0	401.5	401.5	401.5	401.5	401.5	401.5	401.5
167.5°	408.9	408.4	407.9	407.3	406.8	406.8	406.8	406.8	406.8	406.8	406.9
170°	413.2	412.7	412.1	411.6	411.0	411.1	411.2	411.3	411.4	411.4	411.5
172.5°	416.4	415.9	415.3	414.8	414.2	414.3	414.3	414.4	414.5	414.5	414.6
175°	418.5	418.0	417.4	416.9	416.3	416.5	416.6	416.8	416.9	417.0	417.1
177.5°	419.6	419.1	418.6	418.2	417.7	417.9	418.0	418.2	418.3	418.4	418.5
180°	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8	418.8

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1327.6	1327.6	1327.6	1327.6
2.5°	1303.1	1303.1	1318.4	1334.7
5°	1274.5	1281.6	1306.1	1328.6
7.5°	1246.9	1259.2	1289.8	1318.4
10°	1213.3	1229.6	1267.4	1301.0
12.5°	1180.6	1195.9	1239.8	1277.6
15°	1134.7	1154.1	1201.0	1248.0
17.5°	1088.8	1108.2	1165.3	1220.4
20°	1034.7	1060.2	1124.5	1198.0
22.5°	984.7	1016.3	1087.8	1146.9
25°	929.6	978.6	1044.9	1121.4
27.5°	880.6	929.6	996.9	1074.5
30°	825.5	875.5	944.9	1016.3
32.5°	772.5	818.4	885.7	973.5
35°	717.4	761.2	826.5	915.3
37.5°	667.4	710.2	781.6	863.3
40°	618.4	663.3	724.5	806.1
42.5°	572.5	612.2	667.4	749.0
45°	530.6	559.2	610.2	686.7
47.5°	486.7	512.2	559.2	635.7
50°	445.9	467.3	508.2	579.6
52.5°	406.1	424.5	462.2	519.4
55°	370.4	387.8	415.3	471.4
57.5°	333.7	346.9	373.5	418.4
60°	298.0	310.2	331.6	368.4
62.5°	262.2	272.5	292.9	322.5
65°	230.6	238.8	254.1	279.6
67.5°	200.0	205.1	217.3	237.8
70°	170.4	174.5	184.7	201.0
72.5°	138.8	142.9	154.1	165.3
75°	112.2	113.3	121.4	130.6
77.5°	87.8	86.7	92.9	100.0
80°	60.2	63.3	68.4	71.4
82.5°	40.8	41.8	43.9	45.9
85°	22.4	23.5	23.5	26.5
87.5°	9.2	10.2	10.2	11.2
90°	3.2	2.3	1.3	0.4
92.5°	9.7	9.0	8.4	7.8
95°	20.7	20.0	19.2	18.4
97.5°	32.8	32.1	31.4	30.7
100°	46.8	46.1	45.5	44.9
102.5°	61.1	60.6	60.2	59.7
105°	76.7	76.4	76.2	76.0
107.5°	93.1	92.8	92.5	92.2
110°	109.2	108.7	108.3	107.8



TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	126.2	125.7	125.2	124.7
115°	142.8	142.3	141.9	141.4
117.5°	159.9	159.2	158.6	158.0
120°	176.5	175.8	175.2	174.6
122.5°	192.1	191.4	190.6	189.8
125°	207.8	207.1	206.4	205.7
127.5°	223.8	222.9	222.1	221.2
130°	238.8	237.7	236.7	235.7
132.5°	254.3	253.6	252.8	252.0
135°	268.7	267.8	267.0	266.1
137.5°	283.8	283.1	282.4	281.7
140°	297.5	296.8	296.1	295.4
142.5°	311.7	311.0	310.3	309.6
145°	324.7	324.1	323.6	323.0
147.5°	337.1	336.4	335.7	335.0
150°	348.8	348.3	347.9	347.4
152.5°	359.8	359.3	358.8	358.3
155°	370.0	369.8	369.5	369.3
157.5°	379.3	379.1	379.0	378.8
160°	387.8	387.6	387.5	387.3
162.5°	395.1	395.1	395.1	395.1
165°	401.6	401.7	401.7	401.8
167.5°	407.1	407.4	407.6	407.8
170°	411.7	412.0	412.2	412.4
172.5°	414.9	415.1	415.4	415.6
175°	417.4	417.6	417.9	418.1
177.5°	418.8	419.0	419.3	419.5
180°	418.8	418.8	418.8	418.8

TEST NUMBER: P998775

CATALOG NUMBER: SA2XXDIP-B675D330UB40-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.23	19.27	18.99	20.04	20.97	15.72	16.76	16.48	17.53	18.47
	3H	19.05	19.99	19.82	20.77	21.73	17.08	18.01	17.85	18.79	19.76
	4H	19.23	20.11	20.02	20.90	21.87	17.55	18.43	18.34	19.22	20.19
	6H	19.29	20.09	20.09	20.89	21.88	17.87	18.68	18.67	19.47	20.46
	8H	19.27	20.04	20.08	20.86	21.84	17.96	18.72	18.77	19.54	20.53
	12H	19.24	19.97	20.05	20.78	21.80	18.00	18.74	18.82	19.55	20.56
4H	2H	18.29	19.17	19.08	19.96	20.93	16.19	17.07	16.98	17.86	18.83
	3H	19.29	20.02	20.09	20.84	21.83	17.67	18.40	18.47	19.22	20.21
	4H	19.57	20.23	20.39	21.06	22.08	18.21	18.87	19.03	19.69	20.71
	6H	19.71	20.28	20.55	21.13	22.16	18.60	19.17	19.43	20.02	21.04
	8H	19.71	20.25	20.55	21.09	22.13	18.71	19.24	19.55	20.09	21.12
	12H	19.69	20.16	20.54	21.03	22.07	18.78	19.25	19.63	20.12	21.16
8H	4H	19.59	20.13	20.43	20.97	22.01	18.36	18.90	19.20	19.74	20.78
	6H	19.78	20.22	20.65	21.11	22.14	18.81	19.24	19.67	20.13	21.17
	8H	19.81	20.20	20.69	21.08	22.14	18.96	19.35	19.83	20.23	21.28
	12H	19.80	20.15	20.68	21.02	22.13	19.06	19.40	19.93	20.27	21.38
12H	4H	19.56	20.04	20.42	20.90	21.94	18.35	18.82	19.20	19.69	20.73
	6H	19.76	20.15	20.64	21.03	22.09	18.81	19.20	19.68	20.08	21.13
	8H	19.80	20.14	20.68	21.02	22.12	18.97	19.31	19.85	20.19	21.30