

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998796

Luminaire Tested: SA2XXDIP-B675D530UB27-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998796
REPORT IS A COMBINATION OF REPORTS P984542 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D530UB27-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4558.0 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998796

CATALOG NUMBER: SA2XXDIP-B675D530UB27-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P998796

CATALOG NUMBER: SA2XXDIP-B675D530UB27-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	97	92	87	83	89	85	81	77	72	69	66	60	58	56	49	47	46
2	87	79	72	67	80	73	67	62	62	58	54	52	48	45	42	40	38
3	79	69	61	55	73	64	57	51	54	49	44	45	41	38	37	34	31
4	72	61	52	46	66	56	49	43	48	42	37	40	35	32	33	29	27
5	66	54	45	39	61	50	42	37	43	37	32	36	31	27	29	26	23
6	61	48	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20
7	56	43	35	29	52	40	33	28	35	29	24	29	24	21	24	20	18
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16
9	49	36	28	23	45	33	26	22	29	23	19	24	20	17	20	17	14
10	45	33	25	20	42	31	24	19	27	21	17	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11114	11114	11114
5°	11164	10640	10580
10°	11090	10272	10121
15°	10933	9890	9652
20°	10735	9489	9204
25°	10540	9106	8801
30°	10267	8717	8399
35°	9991	8341	8105
40°	9701	8016	7813
45°	9422	7722	7558
50°	9125	7451	7307
55°	8812	7162	7051
60°	8430	6861	6782
65°	8031	6517	6471
70°	7579	6146	6139
75°	7004	5777	5822
80°	6092	5389	5498
85°	5170	5025	5216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9422 cd/sqm

TEST NUMBER: P998796

CATALOG NUMBER: SA2XXDIP-B675D530UB27-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.6	1.5
10°-20°	190.9	4.2
20°-30°	289.2	6.3
30°-40°	352.2	7.7
40°-50°	379.0	8.3
50°-60°	368.0	8.1
60°-70°	321.4	7.1
70°-80°	247.4	5.4
80°-90°	167.6	3.7
90°-100°	155.9	3.4
100°-110°	215.5	4.7
110°-120°	281.0	6.2
120°-130°	327.8	7.2
130°-140°	346.4	7.6
140°-150°	329.2	7.2
150°-160°	274.3	6.0
160°-170°	182.0	4.0
170°-180°	63.6	1.4
0°-30°	546.7	12.0
0°-40°	898.9	19.7
0°-60°	1645.9	36.1
0°-90°	2382.3	52.3
90°-120°	652.4	14.3
90°-150°	1655.9	36.3
90°-180°	2176.0	47.7
0°-180°	4558.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	702	702	702	702	702	
5°	704	701	695	701	700	67
15°	672	674	674	683	682	189
25°	610	618	627	639	642	281
35°	526	543	563	585	592	329
45°	431	459	494	526	536	333
55°	331	367	420	457	470	296
65°	226	276	336	378	391	224
75°	125	182	247	291	304	132
85°	37	100	165	208	222	39
90°	11	77	154	194	206	9
95°	38	91	153	192	203	39
105°	127	158	212	249	260	134
115°	231	245	290	320	329	228
125°	332	337	368	394	402	297
135°	428	434	445	466	472	331
145°	518	522	525	532	535	324
155°	592	594	596	598	597	273
165°	644	644	644	648	645	182
175°	670	669	667	671	668	64
180°	671	671	671	671	671	

TEST NUMBER: P998796

CATALOG NUMBER: SA2XXDIP-B675D530UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	702.1	702.1	702.1	702.1	702.1
2.5°	707.2	704.1	697.0	702.1	700.1
5°	704.1	701.1	695.0	701.1	700.1
7.5°	699.1	697.0	691.9	699.1	698.0
10°	693.0	690.9	687.9	696.0	695.0
12.5°	682.8	683.8	681.8	689.9	688.9
15°	671.6	673.6	673.6	682.8	681.8
17.5°	657.3	661.4	664.5	673.6	673.6
20°	643.1	648.2	652.2	663.4	663.4
22.5°	627.8	633.9	640.0	651.2	653.3
25°	610.5	617.7	626.8	639.0	642.1
27.5°	590.2	601.4	611.5	626.8	628.8
30°	569.8	583.1	596.3	612.6	615.6
32.5°	547.4	562.7	579.0	598.3	604.4
35°	526.1	543.4	562.7	585.1	592.2
37.5°	502.7	522.0	546.4	570.8	578.0
40°	479.3	501.7	529.1	555.6	564.7
42.5°	456.9	479.3	511.8	541.3	550.5
45°	431.4	458.9	494.5	526.1	536.2
47.5°	407.0	436.5	477.2	509.8	521.0
50°	381.6	413.1	458.9	493.5	504.7
52.5°	357.2	390.7	439.6	475.2	487.4
55°	330.7	367.3	420.2	456.9	470.1
57.5°	305.3	346.0	398.9	438.6	451.8
60°	277.8	321.5	379.5	418.2	432.5
62.5°	253.4	299.2	357.2	398.9	412.1
65°	225.9	275.8	335.8	377.5	390.7
67.5°	201.5	253.4	314.4	356.1	370.4
70°	175.0	227.9	291.0	334.8	347.0
72.5°	150.6	205.5	269.7	312.4	327.7
75°	125.2	182.1	247.3	291.0	304.2
77.5°	100.7	159.8	225.9	269.7	283.9
80°	76.3	138.4	204.5	247.3	261.5
82.5°	56.0	117.0	184.2	226.9	240.1
85°	36.6	99.7	164.8	207.6	221.8
87.5°	22.4	83.4	148.6	190.3	203.5
90°	10.8	76.6	154.1	193.7	206.5
92.5°	21.7	80.1	142.8	182.9	195.2
95°	37.6	91.1	153.3	192.0	203.0
97.5°	56.4	105.3	166.6	204.2	216.5
100°	79.1	121.3	180.0	217.6	228.2
102.5°	101.9	138.9	196.0	233.3	243.9
105°	126.9	158.1	212.1	248.9	260.1
107.5°	153.0	179.6	230.5	265.7	274.1
110°	176.9	200.6	250.5	283.0	292.5

TEST NUMBER: P998796

CATALOG NUMBER: SA2XXDIP-B675D530UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	204.1	223.8	270.0	300.8	310.9
115°	230.7	245.3	290.0	319.9	329.4
117.5°	256.4	269.0	308.9	337.8	346.2
120°	283.0	291.5	327.7	356.2	365.7
122.5°	307.4	314.0	348.8	374.6	382.7
125°	331.7	336.8	367.7	393.5	402.1
127.5°	356.7	361.9	387.1	410.3	417.8
130°	379.9	386.3	406.5	429.8	435.6
132.5°	406.0	410.6	426.5	447.1	453.5
135°	427.6	433.9	445.2	466.0	472.4
137.5°	452.6	457.7	463.9	482.6	487.6
140°	474.7	478.8	483.6	499.9	503.7
142.5°	497.3	501.4	503.1	515.9	518.7
145°	517.9	521.8	525.2	531.9	534.7
147.5°	537.1	542.2	544.5	546.6	547.4
150°	556.9	560.3	562.6	564.3	562.6
152.5°	574.5	577.9	580.7	583.0	580.7
155°	592.1	593.8	595.5	598.3	596.6
157.5°	607.4	608.5	609.6	613.6	610.8
160°	621.0	622.1	622.7	626.1	623.8
162.5°	633.4	633.4	634.0	638.0	635.1
165°	644.2	643.6	643.6	647.6	644.8
167.5°	653.8	652.1	652.1	656.1	653.3
170°	661.2	659.5	658.9	662.9	659.5
172.5°	666.3	664.6	664.0	668.0	664.6
175°	670.3	668.6	667.4	671.4	668.0
177.5°	672.5	670.8	669.7	673.1	669.7
180°	671.4	671.4	671.4	671.4	671.4

TEST NUMBER: P998796

CATALOG NUMBER: SA2XXDIP-B675D530UB27-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.78	14.71	14.70	15.67	16.90	16.85	17.79	17.78	18.74	19.98
	3H	15.24	16.09	16.18	17.05	18.31	19.45	20.29	20.38	21.25	22.51
	4H	15.72	16.53	16.67	17.49	18.76	20.70	21.51	21.65	22.47	23.74
	6H	16.01	16.76	16.97	17.73	19.00	22.00	22.75	22.97	23.72	25.00
	8H	16.07	16.78	17.04	17.77	19.05	22.66	23.38	23.63	24.37	25.64
	12H	16.09	16.77	17.06	17.75	19.05	23.39	24.07	24.37	25.05	26.36
4H	2H	14.84	15.64	15.79	16.61	17.87	17.19	18.00	18.15	18.96	20.23
	3H	16.55	17.23	17.52	18.23	19.51	19.99	20.67	20.95	21.66	22.94
	4H	17.17	17.80	18.15	18.79	20.09	21.41	22.04	22.38	23.02	24.33
	6H	17.59	18.14	18.58	19.15	20.45	22.88	23.43	23.86	24.44	25.74
	8H	17.70	18.22	18.69	19.22	20.54	23.64	24.15	24.63	25.16	26.47
	12H	17.75	18.22	18.76	19.24	20.56	24.47	24.94	25.48	25.96	27.28
8H	4H	17.97	18.49	18.96	19.49	20.81	21.56	22.07	22.54	23.08	24.39
	6H	18.61	19.04	19.62	20.09	21.40	23.19	23.62	24.20	24.67	25.98
	8H	18.83	19.21	19.85	20.25	21.58	24.08	24.47	25.10	25.50	26.83
	12H	18.97	19.31	19.99	20.34	21.71	25.08	25.42	26.10	26.45	27.82
12H	4H	18.17	18.64	19.18	19.66	20.98	21.53	22.00	22.54	23.02	24.35
	6H	18.94	19.33	19.96	20.36	21.69	23.22	23.60	24.23	24.63	25.96
	8H	19.25	19.59	20.27	20.62	21.99	24.15	24.49	25.17	25.52	26.89

END OF REPORT