

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000112

Luminaire Tested: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000112
REPORT IS A COMBINATION OF REPORTS P988672 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4334.0 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000112

CATALOG NUMBER: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1000112

CATALOG NUMBER: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74			69
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	66	65	64			60
2	94	87	81	76	89	82	77	73	74	70	66	66	63	61	59	57	55			51
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47			44
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	44	41			39
5	73	62	54	48	69	59	52	46	53	47	43	48	43	40	44	40	37			34
6	68	56	48	42	64	53	46	41	48	42	38	44	39	35	40	36	33			30
7	63	51	43	37	60	48	41	36	44	38	34	40	35	31	37	32	29			27
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	30	26			24
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24			22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22			20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23168	23168	23168
5°	23205	22040	21878
10°	22975	20905	20215
15°	22660	19562	18318
20°	22242	18036	16337
25°	21815	16472	14523
30°	21240	14947	12542
35°	20676	13409	10840
40°	20106	11900	9088
45°	19440	10340	7560
50°	18751	8839	6156
55°	18034	7337	4886
60°	17202	5867	3698
65°	16243	4474	3006
70°	15084	3244	2390
75°	13633	2476	1826
80°	11529	1676	1226
85°	8052	768	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19440 cd/sqm

TEST NUMBER: P1000112

CATALOG NUMBER: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	3.2
10°-20°	376.6	8.7
20°-30°	528.7	12.2
30°-40°	576.3	13.3
40°-50°	529.7	12.2
50°-60°	416.0	9.6
60°-70°	270.7	6.2
70°-80°	139.4	3.2
80°-90°	36.4	0.8
90°-100°	14.9	0.3
100°-110°	55.5	1.3
110°-120°	147.1	3.4
120°-130°	244.0	5.6
130°-140°	259.2	6.0
140°-150°	240.9	5.6
150°-160°	193.7	4.5
160°-170°	124.8	2.9
170°-180°	43.0	1.0
0°-30°	1042.4	24.1
0°-40°	1618.7	37.3
0°-60°	2564.3	59.2
0°-90°	3010.8	69.5
90°-120°	217.5	5.0
90°-150°	961.7	22.2
90°-180°	1323.0	30.5
0°-180°	4334.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1464	1464	1464	1464	1464	
5°	1464	1457	1440	1452	1448	139
15°	1392	1378	1332	1307	1294	392
25°	1264	1221	1134	1080	1060	581
35°	1089	1021	905	821	792	681
45°	890	801	662	568	536	687
55°	677	574	430	351	326	605
65°	457	350	230	185	182	453
75°	244	151	106	97	95	258
85°	57	29	25	25	25	65
90°	0	4	6	8	9	4
95°	21	10	13	14	14	25
105°	99	109	20	24	25	106
115°	188	193	202	50	27	185
125°	266	270	276	278	279	237
135°	329	334	337	340	339	254
145°	381	381	386	389	387	238
155°	420	417	421	423	420	193
165°	442	440	441	444	441	125
175°	452	450	451	453	450	43
180°	451	451	451	451	451	

TEST NUMBER: P1000112

CATALOG NUMBER: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1463.6	1463.6	1463.6	1463.6	1463.6
2.5°	1470.2	1463.6	1449.0	1462.2	1459.6
5°	1463.6	1456.9	1439.7	1451.6	1447.7
7.5°	1451.6	1443.7	1425.2	1430.4	1423.8
10°	1435.7	1426.5	1400.0	1396.0	1388.1
12.5°	1415.9	1404.0	1368.2	1360.3	1345.7
15°	1392.0	1377.5	1332.4	1307.3	1294.0
17.5°	1364.2	1343.0	1287.4	1258.3	1237.1
20°	1332.4	1305.9	1239.7	1206.6	1177.5
22.5°	1298.0	1267.5	1190.7	1145.7	1125.8
25°	1263.6	1221.2	1133.8	1079.5	1059.6
27.5°	1222.5	1177.5	1080.8	1018.5	988.1
30°	1178.8	1128.5	1022.5	955.0	919.2
32.5°	1136.4	1075.5	966.9	887.4	854.3
35°	1088.7	1021.2	904.6	821.2	792.0
37.5°	1042.4	969.5	846.3	755.0	721.8
40°	993.4	913.9	785.4	691.4	656.9
42.5°	943.0	858.3	724.5	626.5	593.4
45°	890.1	801.3	662.2	568.2	536.4
47.5°	839.7	745.7	602.6	508.6	479.5
50°	784.1	690.1	544.4	453.0	425.2
52.5°	729.8	630.5	488.7	401.3	376.2
55°	676.8	573.5	430.5	351.0	325.8
57.5°	622.5	516.6	378.8	304.6	283.4
60°	566.9	460.9	324.5	257.0	235.8
62.5°	512.6	406.6	278.1	214.6	204.0
65°	456.9	349.7	230.5	185.4	181.5
67.5°	404.0	296.7	185.4	162.9	158.9
70°	348.3	245.0	153.6	140.4	135.1
72.5°	295.4	197.3	128.5	117.9	115.2
75°	243.7	151.0	106.0	96.7	95.4
77.5°	192.1	107.3	83.4	78.1	75.5
80°	144.4	76.8	63.6	58.3	58.3
82.5°	100.7	51.7	43.7	41.1	41.1
85°	57.0	29.1	25.2	25.2	25.2
87.5°	21.2	10.6	10.6	9.3	9.3
90°	0.3	3.9	6.5	8.2	8.8
92.5°	8.2	6.9	7.8	8.5	8.8
95°	21.2	10.5	12.7	14.4	14.0
97.5°	38.2	11.4	16.7	17.6	18.0
100°	57.8	13.1	18.6	21.2	21.9
102.5°	79.4	78.7	19.3	22.9	23.8
105°	99.3	109.1	19.9	23.5	24.8
107.5°	122.5	130.6	20.6	24.2	25.5
110°	144.7	151.5	57.2	24.5	25.8



TEST NUMBER: P1000112

CATALOG NUMBER: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.6	171.5	165.9	25.1	26.1
115°	187.8	193.3	201.5	50.3	26.8
117.5°	207.1	213.6	219.1	172.4	86.9
120°	228.6	233.5	239.4	243.3	199.2
122.5°	246.9	252.1	258.7	260.6	260.9
125°	265.5	269.8	276.0	278.3	279.2
127.5°	282.5	287.1	292.0	295.2	295.6
130°	298.5	303.7	307.3	310.9	310.6
132.5°	314.8	319.1	322.7	325.6	325.3
135°	328.6	333.8	336.7	340.0	339.3
137.5°	342.9	346.8	350.1	353.4	352.4
140°	357.0	359.6	363.2	366.1	364.5
142.5°	368.7	371.0	375.3	377.9	376.2
145°	381.1	380.8	386.4	388.6	387.0
147.5°	391.9	390.9	396.5	398.1	396.8
150°	402.4	400.1	405.3	407.3	405.6
152.5°	411.2	408.6	413.5	415.4	413.1
155°	419.7	416.7	420.7	422.6	420.0
157.5°	426.5	423.9	426.9	429.1	426.5
160°	432.4	430.5	432.4	434.4	432.1
162.5°	437.6	435.7	437.3	439.6	436.7
165°	442.2	440.2	441.2	443.5	441.2
167.5°	445.8	443.8	444.8	447.1	444.2
170°	448.7	446.8	447.4	449.7	446.8
172.5°	450.7	448.7	449.4	451.7	448.7
175°	452.3	450.0	450.7	453.0	449.7
177.5°	453.0	450.7	451.0	453.3	450.4
180°	451.4	451.4	451.4	451.4	451.4

(END OF REPORT)