

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998821

Luminaire Tested: SA2XXDIP-B675D530UB30-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998821
REPORT IS A COMBINATION OF REPORTS P984567 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D530UB30-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4775.4 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998821

CATALOG NUMBER: SA2XXDIP-B675D530UB30-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P998821

CATALOG NUMBER: SA2XXDIP-B675D530UB30-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56
1	96	91	87	83	89	84	80	77	71	68	65	59	57	55	47	46	45
2	87	79	72	66	80	73	67	62	61	57	53	51	47	45	41	39	36
3	79	69	61	55	72	64	57	51	54	48	44	44	40	37	36	33	30
4	72	61	52	46	66	56	49	43	47	42	37	39	35	31	32	28	26
5	66	54	45	39	60	50	42	36	42	36	32	35	30	27	28	25	22
6	61	48	40	34	56	45	37	31	38	32	27	32	27	23	26	22	19
7	56	43	35	29	51	40	33	27	34	28	24	29	24	20	23	20	17
8	52	39	31	26	48	36	29	24	31	25	21	26	21	18	21	18	15
9	48	36	28	23	44	33	26	21	28	23	19	24	19	16	20	16	14
10	45	33	25	20	42	30	24	19	26	21	17	22	18	15	18	15	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11209	11209	11209
5°	11260	10732	10671
10°	11184	10360	10209
15°	11026	9975	9734
20°	10827	9570	9284
25°	10631	9185	8876
30°	10355	8791	8472
35°	10077	8412	8175
40°	9784	8086	7880
45°	9503	7789	7624
50°	9204	7516	7369
55°	8886	7225	7111
60°	8503	6921	6840
65°	8098	6573	6527
70°	7644	6199	6192
75°	7060	5826	5874
80°	6148	5436	5546
85°	5212	5071	5260

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9503 cd/sqm

TEST NUMBER: P998821

CATALOG NUMBER: SA2XXDIP-B675D530UB30-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.1	1.4
10°-20°	192.5	4.0
20°-30°	291.7	6.1
30°-40°	355.2	7.4
40°-50°	382.2	8.0
50°-60°	371.2	7.8
60°-70°	324.2	6.8
70°-80°	249.5	5.2
80°-90°	169.0	3.5
90°-100°	235.7	4.9
100°-110°	491.4	10.3
110°-120°	483.6	10.1
120°-130°	382.9	8.0
130°-140°	295.8	6.2
140°-150°	215.8	4.5
150°-160°	150.2	3.1
160°-170°	88.4	1.9
170°-180°	28.8	0.6
0°-30°	551.4	11.5
0°-40°	906.6	19.0
0°-60°	1660.0	34.8
0°-90°	2402.7	50.3
90°-120°	1210.7	25.4
90°-150°	2105.3	44.1
90°-180°	2373.0	49.7
0°-180°	4775.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	708	708	708	708	708	
5°	710	707	701	707	706	67
15°	677	679	679	689	688	191
25°	616	623	632	644	648	283
35°	531	548	568	590	597	332
45°	435	463	499	531	541	336
55°	334	370	424	461	474	298
65°	228	278	339	381	394	226
75°	126	184	249	294	307	134
85°	37	101	166	209	224	39
90°	11	78	155	195	208	9
95°	28	106	342	242	234	27
105°	75	140	512	881	779	80
115°	127	170	416	823	951	126
125°	174	205	375	655	759	155
135°	202	241	348	530	611	156
145°	230	264	335	422	466	144
155°	261	282	325	368	382	120
165°	284	293	311	330	335	80
175°	296	297	299	303	302	28
180°	297	297	297	297	297	

TEST NUMBER: P998821

CATALOG NUMBER: SA2XXDIP-B675D530UB30-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	708.1	708.1	708.1	708.1	708.1
2.5°	713.3	710.2	703.0	708.1	706.1
5°	710.2	707.1	701.0	707.1	706.1
7.5°	705.1	703.0	697.9	705.1	704.0
10°	698.9	696.8	693.8	702.0	701.0
12.5°	688.6	689.7	687.6	695.8	694.8
15°	677.3	679.4	679.4	688.6	687.6
17.5°	663.0	667.1	670.2	679.4	679.4
20°	648.6	653.7	657.8	669.1	669.1
22.5°	633.2	639.4	645.5	656.8	658.9
25°	615.8	623.0	632.2	644.5	647.6
27.5°	595.2	606.5	616.8	632.2	634.2
30°	574.7	588.1	601.4	617.8	620.9
32.5°	552.1	567.5	584.0	603.5	609.6
35°	530.6	548.0	567.5	590.1	597.3
37.5°	507.0	526.5	551.1	575.7	582.9
40°	483.4	506.0	533.7	560.4	569.6
42.5°	460.8	483.4	516.2	546.0	555.2
45°	435.1	462.9	498.8	530.6	540.9
47.5°	410.5	440.3	481.3	514.2	525.5
50°	384.9	416.7	462.9	497.7	509.0
52.5°	360.2	394.1	443.4	479.3	491.6
55°	333.5	370.5	423.9	460.8	474.1
57.5°	307.9	348.9	402.3	442.3	455.7
60°	280.2	324.3	382.8	421.8	436.2
62.5°	255.5	301.7	360.2	402.3	415.6
65°	227.8	278.1	338.7	380.8	394.1
67.5°	203.2	255.5	317.1	359.2	373.6
70°	176.5	229.9	293.5	337.6	350.0
72.5°	151.9	207.3	272.0	315.1	330.5
75°	126.2	183.7	249.4	293.5	306.9
77.5°	101.6	161.1	227.8	272.0	286.3
80°	77.0	139.6	206.3	249.4	263.8
82.5°	56.4	118.0	185.8	228.9	242.2
85°	36.9	100.6	166.3	209.4	223.7
87.5°	22.6	84.2	149.8	191.9	205.3
90°	10.9	77.6	154.9	195.1	207.7
92.5°	17.8	90.8	214.2	206.9	213.5
95°	28.2	105.6	342.0	241.6	234.4
97.5°	36.9	116.2	475.9	318.5	270.2
100°	51.2	124.6	554.0	478.6	356.4
102.5°	63.3	132.6	549.6	703.8	542.5
105°	74.8	140.0	511.7	881.0	779.4
107.5°	88.5	147.5	475.9	939.9	936.4
110°	101.2	155.2	450.3	920.8	995.5

TEST NUMBER: P998821

CATALOG NUMBER: SA2XXDIP-B675D530UB30-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	113.8	163.4	430.5	876.8	987.2
115°	126.9	170.5	415.8	823.4	951.0
117.5°	139.7	178.7	404.1	773.1	900.5
120°	152.2	186.6	393.9	726.4	852.8
122.5°	164.2	195.8	385.5	689.2	801.2
125°	173.5	204.9	375.4	654.8	759.2
127.5°	182.1	214.4	367.5	623.5	718.4
130°	189.5	223.8	360.3	592.8	683.3
132.5°	196.4	233.0	353.5	561.3	648.1
135°	202.1	241.0	347.8	530.5	610.8
137.5°	208.4	247.8	342.7	499.4	573.3
140°	215.8	253.1	338.1	471.0	534.8
142.5°	223.3	258.2	336.0	444.5	497.3
145°	229.7	264.0	334.8	421.9	466.1
147.5°	237.7	268.6	333.1	402.1	436.6
150°	245.7	273.2	331.4	388.5	413.1
152.5°	253.7	277.7	328.5	378.0	396.5
155°	261.1	282.0	325.1	367.6	382.2
157.5°	267.4	285.4	321.7	358.0	369.7
160°	273.7	288.8	318.3	348.2	357.7
162.5°	280.0	291.4	315.4	339.1	346.2
165°	284.5	293.1	311.4	330.2	335.4
167.5°	288.5	294.8	308.0	322.2	325.1
170°	292.5	295.6	305.1	314.8	316.0
172.5°	294.8	296.6	301.7	308.2	308.5
175°	296.5	296.8	299.4	303.1	302.3
177.5°	297.7	297.1	297.1	299.4	297.7
180°	297.1	297.1	297.1	297.1	297.1

TEST NUMBER: P998821

CATALOG NUMBER: SA2XXDIP-B675D530UB30-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.63	14.55	14.58	15.51	16.78	16.71	17.62	17.65	18.59	19.85
	3H	15.10	15.92	16.05	16.90	18.18	19.30	20.13	20.25	21.10	22.39
	4H	15.57	16.36	16.54	17.34	18.63	20.56	21.34	21.52	22.32	23.62
	6H	15.86	16.59	16.84	17.58	18.88	21.86	22.58	22.83	23.57	24.88
	8H	15.92	16.62	16.91	17.62	18.92	22.52	23.21	23.50	24.22	25.52
	12H	15.94	16.60	16.93	17.60	18.93	23.24	23.91	24.23	24.90	26.23
4H	2H	14.69	15.48	15.66	16.46	17.75	17.04	17.83	18.02	18.81	20.10
	3H	16.40	17.07	17.38	18.08	19.38	19.84	20.51	20.82	21.52	22.82
	4H	17.02	17.64	18.01	18.64	19.97	21.26	21.87	22.25	22.87	24.20
	6H	17.44	17.98	18.44	19.00	20.33	22.73	23.26	23.73	24.29	25.62
	8H	17.55	18.06	18.56	19.07	20.42	23.49	23.99	24.49	25.01	26.35
	12H	17.60	18.06	18.62	19.09	20.44	24.32	24.78	25.34	25.81	27.16
8H	4H	17.82	18.32	18.82	19.34	20.68	21.41	21.91	22.41	22.93	24.27
	6H	18.45	18.88	19.48	19.94	21.28	23.04	23.46	24.06	24.52	25.86
	8H	18.68	19.05	19.71	20.10	21.46	23.93	24.30	24.96	25.35	26.71
	12H	18.81	19.15	19.85	20.19	21.59	24.93	25.26	25.97	26.30	27.70
12H	4H	18.02	18.48	19.04	19.51	20.86	21.38	21.84	22.41	22.87	24.22
	6H	18.79	19.17	19.82	20.21	21.57	23.06	23.44	24.10	24.48	25.84
	8H	19.10	19.43	20.14	20.47	21.87	23.99	24.33	25.04	25.37	26.77