

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000190

Luminaire Tested: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000190
REPORT IS A COMBINATION OF REPORTS P988750 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5780.0 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000190

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1000190

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	99	94	91	87	91	88	84	81	75	72	70	63	61	59	52	50	49	49	49	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	50	46	44	42	42	42	38
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	37	37	33
4	76	65	58	52	70	61	54	49	52	47	43	44	41	38	37	34	32	32	32	29
5	70	58	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	28	28	25
6	64	53	45	39	60	49	42	37	43	37	33	36	32	29	31	28	25	25	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	23	23	23	20
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	20	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	18	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22875	22875	22875
5°	22912	21762	21601
10°	22686	20640	19959
15°	22375	19315	18088
20°	21962	17809	16131
25°	21539	16263	14339
30°	20971	14759	12384
35°	20416	13240	10703
40°	19851	11750	8975
45°	19193	10211	7465
50°	18514	8727	6077
55°	17808	7243	4825
60°	16984	5793	3651
65°	16040	4417	2968
70°	14893	3204	2360
75°	13459	2443	1803
80°	11377	1655	1209
85°	7939	756	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19193 cd/sqm

TEST NUMBER: P1000190

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	2.3
10°-20°	371.8	6.4
20°-30°	522.0	9.0
30°-40°	569.0	9.8
40°-50°	523.0	9.0
50°-60°	410.7	7.1
60°-70°	267.3	4.6
70°-80°	137.6	2.4
80°-90°	36.8	0.6
90°-100°	31.6	0.5
100°-110°	117.7	2.0
110°-120°	312.1	5.4
120°-130°	517.6	9.0
130°-140°	549.8	9.5
140°-150°	511.0	8.8
150°-160°	410.8	7.1
160°-170°	264.7	4.6
170°-180°	91.1	1.6
0°-30°	1029.2	17.8
0°-40°	1598.2	27.7
0°-60°	2531.9	43.8
0°-90°	2973.7	51.4
90°-120°	461.3	8.0
90°-150°	2039.7	35.3
90°-180°	2806.0	48.5
0°-180°	5780.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1438	1422	1433	1429	137
15°	1374	1360	1316	1291	1278	387
25°	1248	1206	1119	1066	1046	574
35°	1075	1008	893	811	782	673
45°	879	791	654	561	530	679
55°	668	566	425	347	322	597
65°	451	345	228	183	179	447
75°	241	149	105	96	94	254
85°	56	29	25	25	25	65
90°	1	8	14	17	19	5
95°	45	22	27	30	30	53
105°	211	231	42	50	53	225
115°	398	410	427	107	57	392
125°	563	572	585	590	592	502
135°	697	708	714	721	720	538
145°	808	808	819	824	821	506
155°	890	884	892	896	891	410
165°	938	934	936	941	936	265
175°	959	954	956	961	954	91
180°	957	957	957	957	957	

TEST NUMBER: P1000190

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1445.1	1445.1	1445.1	1445.1	1445.1
2.5°	1451.6	1445.1	1430.7	1443.8	1441.2
5°	1445.1	1438.5	1421.5	1433.3	1429.4
7.5°	1433.3	1425.5	1407.2	1412.4	1405.9
10°	1417.6	1408.5	1382.3	1378.4	1370.5
12.5°	1398.0	1386.2	1350.9	1343.1	1328.7
15°	1374.5	1360.1	1315.6	1290.8	1277.7
17.5°	1347.0	1326.1	1271.2	1242.4	1221.5
20°	1315.6	1289.5	1224.1	1191.4	1162.6
22.5°	1281.6	1251.5	1175.7	1131.2	1111.6
25°	1247.6	1205.8	1119.4	1065.8	1046.2
27.5°	1207.1	1162.6	1067.1	1005.7	975.6
30°	1163.9	1114.2	1009.6	942.9	907.6
32.5°	1122.1	1061.9	954.7	876.2	843.5
35°	1075.0	1008.3	893.2	810.8	782.0
37.5°	1029.2	957.3	835.7	745.4	712.7
40°	980.8	902.4	775.5	682.7	648.7
42.5°	931.1	847.4	715.3	618.6	585.9
45°	878.8	791.2	653.9	561.0	529.6
47.5°	829.1	736.3	595.0	502.2	473.4
50°	774.2	681.3	537.5	447.3	419.8
52.5°	720.6	622.5	482.6	396.3	371.4
55°	668.3	566.3	425.0	346.6	321.7
57.5°	614.7	510.0	374.0	300.8	279.9
60°	559.7	455.1	320.4	253.7	232.8
62.5°	506.1	401.5	274.6	211.9	201.4
65°	451.2	345.3	227.6	183.1	179.2
67.5°	398.9	292.9	183.1	160.9	156.9
70°	343.9	241.9	151.7	138.6	133.4
72.5°	291.6	194.9	126.9	116.4	113.8
75°	240.6	149.1	104.6	95.5	94.2
77.5°	189.6	105.9	82.4	77.2	74.5
80°	142.5	75.9	62.8	57.5	57.5
82.5°	99.4	51.0	43.2	40.5	40.5
85°	56.2	28.8	24.8	24.8	24.8
87.5°	20.9	10.5	10.5	9.2	9.2
90°	0.7	8.3	13.9	17.3	18.7
92.5°	17.3	14.5	16.6	18.0	18.7
95°	45.0	22.2	27.0	30.5	29.8
97.5°	81.0	24.2	35.3	37.4	38.1
100°	122.6	27.7	39.5	45.0	46.4
102.5°	168.3	166.9	40.9	48.5	50.6
105°	210.6	231.3	42.3	49.9	52.6
107.5°	259.7	277.1	43.6	51.3	54.0
110°	306.8	321.4	121.2	51.9	54.7



TEST NUMBER: P1000190

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	351.2	363.6	351.9	53.3	55.4
115°	398.3	410.1	427.4	106.7	56.8
117.5°	439.1	453.0	464.8	365.7	184.2
120°	484.9	495.2	507.7	516.0	422.5
122.5°	523.6	534.7	548.6	552.7	553.4
125°	563.1	572.1	585.3	590.1	592.2
127.5°	599.1	608.8	619.2	626.2	626.9
130°	633.1	644.2	651.8	659.4	658.7
132.5°	667.7	676.7	684.3	690.6	689.9
135°	696.8	707.9	714.1	721.1	719.7
137.5°	727.3	735.6	742.5	749.5	747.4
140°	757.1	762.6	770.2	776.5	773.0
142.5°	782.0	786.9	795.9	801.4	797.9
145°	808.3	807.6	819.4	824.3	820.8
147.5°	831.2	829.1	840.9	844.3	841.6
150°	853.3	848.5	859.6	863.7	860.3
152.5°	872.1	866.5	876.9	881.1	876.2
155°	890.1	883.8	892.1	896.3	890.8
157.5°	904.6	899.1	905.3	910.1	904.6
160°	917.1	912.9	917.1	921.2	916.4
162.5°	928.2	924.0	927.5	932.3	926.1
165°	937.9	933.7	935.8	940.6	935.8
167.5°	945.5	941.3	943.4	948.2	942.0
170°	951.7	947.6	948.9	953.8	947.6
172.5°	955.9	951.7	953.1	957.9	951.7
175°	959.3	954.5	955.9	960.7	953.8
177.5°	960.7	955.9	956.6	961.4	955.2
180°	957.2	957.2	957.2	957.2	957.2

(END OF REPORT)