

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000191

Luminaire Tested: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000191
REPORT IS A COMBINATION OF REPORTS P988751 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5830.0 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000191

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000191

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	99	94	91	87	91	88	84	81	75	72	70	63	61	59	52	50	49	49	49	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	50	46	44	42	42	42	38
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	37	37	33
4	76	65	58	52	70	61	54	49	52	47	43	44	41	38	37	34	32	32	32	29
5	70	58	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	28	28	25
6	64	53	45	39	60	49	42	37	43	37	33	36	32	29	31	28	25	25	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	23	23	23	20
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	20	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	18	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23074	23074	23074
5°	23112	21953	21790
10°	22884	20821	20133
15°	22570	19484	18246
20°	22154	17965	16272
25°	21727	16405	14465
30°	21155	14887	12491
35°	20594	13356	10797
40°	20025	11853	9052
45°	19361	10300	7531
50°	18676	8803	6131
55°	17962	7306	4867
60°	17133	5843	3682
65°	16179	4454	2993
70°	15028	3231	2381
75°	13577	2464	1818
80°	11481	1668	1219
85°	8009	765	590

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19361 cd/sqm

TEST NUMBER: P1000191

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.6	2.3
10°-20°	375.1	6.4
20°-30°	526.6	9.0
30°-40°	574.0	9.8
40°-50°	527.5	9.0
50°-60°	414.3	7.1
60°-70°	269.7	4.6
70°-80°	138.8	2.4
80°-90°	37.2	0.6
90°-100°	31.8	0.5
100°-110°	118.7	2.0
110°-120°	314.7	5.4
120°-130°	522.0	9.0
130°-140°	554.5	9.5
140°-150°	515.4	8.8
150°-160°	414.3	7.1
160°-170°	267.0	4.6
170°-180°	91.9	1.6
0°-30°	1038.2	17.8
0°-40°	1612.2	27.7
0°-60°	2554.0	43.8
0°-90°	2999.7	51.5
90°-120°	465.3	8.0
90°-150°	2057.1	35.3
90°-180°	2830.0	48.5
0°-180°	5830.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1458	1451	1434	1446	1442	138
15°	1386	1372	1327	1302	1289	391
25°	1258	1216	1129	1075	1055	579
35°	1084	1017	901	818	789	679
45°	886	798	660	566	534	685
55°	674	571	429	350	324	602
65°	455	348	230	185	181	451
75°	243	150	106	96	95	257
85°	57	29	25	25	25	65
90°	1	8	14	18	19	5
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	395
125°	568	577	590	595	597	507
135°	703	714	720	727	726	543
145°	815	814	826	831	828	510
155°	898	891	900	904	898	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	965	965	965	965	965	

TEST NUMBER: P1000191

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1464.3	1457.7	1443.2	1456.4	1453.8
5°	1457.7	1451.1	1434.0	1445.9	1441.9
7.5°	1445.9	1437.9	1419.5	1424.7	1418.1
10°	1430.0	1420.8	1394.4	1390.4	1382.5
12.5°	1410.2	1398.4	1362.7	1354.8	1340.3
15°	1386.5	1372.0	1327.1	1302.1	1288.9
17.5°	1358.8	1337.7	1282.3	1253.2	1232.1
20°	1327.1	1300.7	1234.8	1201.8	1172.8
22.5°	1292.8	1262.5	1186.0	1141.1	1121.3
25°	1258.5	1216.3	1129.2	1075.2	1055.4
27.5°	1217.6	1172.8	1076.5	1014.5	984.1
30°	1174.1	1124.0	1018.4	951.1	915.5
32.5°	1131.9	1071.2	963.0	883.9	850.9
35°	1084.4	1017.1	901.0	817.9	788.9
37.5°	1038.2	965.7	843.0	751.9	719.0
40°	989.4	910.3	782.3	688.6	654.3
42.5°	939.3	854.8	721.6	624.0	591.0
45°	886.5	798.1	659.6	565.9	534.3
47.5°	836.4	742.7	600.2	506.6	477.6
50°	781.0	687.3	542.2	451.2	423.5
52.5°	726.9	627.9	486.8	399.7	374.7
55°	674.1	571.2	428.7	349.6	324.5
57.5°	620.0	514.5	377.3	303.4	282.3
60°	564.6	459.1	323.2	255.9	234.8
62.5°	510.5	405.0	277.0	213.7	203.2
65°	455.1	348.3	229.5	184.7	180.7
67.5°	402.4	295.5	184.7	162.3	158.3
70°	347.0	244.1	153.0	139.8	134.6
72.5°	294.2	196.6	128.0	117.4	114.8
75°	242.7	150.4	105.5	96.3	95.0
77.5°	191.3	106.9	83.1	77.8	75.2
80°	143.8	76.5	63.3	58.0	58.0
82.5°	100.3	51.4	43.5	40.9	40.9
85°	56.7	29.0	25.1	25.1	25.1
87.5°	21.1	10.6	10.6	9.2	9.2
90°	0.7	8.4	14.0	17.5	18.9
92.5°	17.5	14.7	16.8	18.2	18.9
95°	45.4	22.4	27.2	30.7	30.0
97.5°	81.7	24.5	35.6	37.7	38.4
100°	123.6	27.9	39.8	45.4	46.8
102.5°	169.8	168.4	41.2	48.9	51.0
105°	212.4	233.3	42.6	50.3	53.1
107.5°	262.0	279.4	44.0	51.7	54.5
110°	309.5	324.1	122.3	52.4	55.2

TEST NUMBER: P1000191

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.2	366.8	354.9	53.8	55.9
115°	401.7	413.6	431.0	107.6	57.3
117.5°	442.9	456.9	468.7	368.8	185.8
120°	489.0	499.5	512.1	520.4	426.1
122.5°	528.1	539.3	553.3	557.5	558.2
125°	567.9	577.0	590.3	595.2	597.3
127.5°	604.3	614.0	624.5	631.5	632.2
130°	638.5	649.7	657.4	665.0	664.3
132.5°	673.4	682.5	690.2	696.5	695.8
135°	702.8	713.9	720.2	727.2	725.8
137.5°	733.5	741.9	748.9	755.9	753.8
140°	763.5	769.1	776.8	783.1	779.6
142.5°	788.7	793.6	802.7	808.3	804.8
145°	815.2	814.5	826.4	831.3	827.8
147.5°	838.3	836.2	848.1	851.6	848.8
150°	860.6	855.8	866.9	871.1	867.6
152.5°	879.5	873.9	884.4	888.6	883.7
155°	897.7	891.4	899.8	904.0	898.4
157.5°	912.3	906.7	913.0	917.9	912.3
160°	924.9	920.7	924.9	929.1	924.2
162.5°	936.1	931.9	935.4	940.3	934.0
165°	945.9	941.7	943.8	948.7	943.8
167.5°	953.6	949.4	951.5	956.3	950.1
170°	959.8	955.6	957.0	961.9	955.6
172.5°	964.0	959.8	961.2	966.1	959.8
175°	967.5	962.6	964.0	968.9	961.9
177.5°	968.9	964.0	964.7	969.6	963.3
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)