

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000192

Luminaire Tested: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000192
REPORT IS A COMBINATION OF REPORTS P988752 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5854.0 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000192

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1000192

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	94	91	87	91	88	84	81	75	72	70	63	61	59	52	50	49
2	90	83	77	72	83	77	72	68	66	62	59	56	53	50	46	44	42
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	44	41	38	37	34	32
5	70	58	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28
6	64	53	45	39	60	49	42	37	43	37	33	36	32	29	31	28	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	23
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23168	23168	23168
5°	23205	22040	21878
10°	22975	20905	20215
15°	22660	19562	18318
20°	22242	18036	16337
25°	21815	16472	14523
30°	21240	14947	12542
35°	20676	13409	10840
40°	20106	11900	9088
45°	19440	10340	7560
50°	18751	8839	6156
55°	18034	7337	4886
60°	17202	5867	3698
65°	16243	4474	3006
70°	15084	3244	2390
75°	13633	2476	1826
80°	11529	1676	1226
85°	8052	768	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19440 cd/sqm

TEST NUMBER: P1000192

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	2.3
10°-20°	376.6	6.4
20°-30°	528.7	9.0
30°-40°	576.3	9.8
40°-50°	529.7	9.0
50°-60°	416.0	7.1
60°-70°	270.7	4.6
70°-80°	139.4	2.4
80°-90°	37.3	0.6
90°-100°	32.0	0.5
100°-110°	119.2	2.0
110°-120°	316.1	5.4
120°-130°	524.2	9.0
130°-140°	556.8	9.5
140°-150°	517.5	8.8
150°-160°	416.1	7.1
160°-170°	268.1	4.6
170°-180°	92.3	1.6
0°-30°	1042.4	17.8
0°-40°	1618.7	27.7
0°-60°	2564.3	43.8
0°-90°	3011.7	51.4
90°-120°	467.2	8.0
90°-150°	2065.8	35.3
90°-180°	2842.0	48.5
0°-180°	5854.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1464	1464	1464	1464	1464	
5°	1464	1457	1440	1452	1448	139
15°	1392	1378	1332	1307	1294	392
25°	1264	1221	1134	1080	1060	581
35°	1089	1021	905	821	792	681
45°	890	801	662	568	536	687
55°	677	574	430	351	326	605
65°	457	350	230	185	182	453
75°	244	151	106	97	95	258
85°	57	29	25	25	25	65
90°	1	8	14	18	19	5
95°	46	22	27	31	30	54
105°	213	234	43	50	53	228
115°	403	415	433	108	58	397
125°	570	580	593	598	600	509
135°	706	717	723	730	729	545
145°	819	818	830	835	831	512
155°	902	895	904	908	902	415
165°	950	946	948	953	948	268
175°	972	967	968	973	966	92
180°	970	970	970	970	970	

TEST NUMBER: P1000192

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1463.6	1463.6	1463.6	1463.6	1463.6
2.5°	1470.2	1463.6	1449.0	1462.2	1459.6
5°	1463.6	1456.9	1439.7	1451.6	1447.7
7.5°	1451.6	1443.7	1425.2	1430.4	1423.8
10°	1435.7	1426.5	1400.0	1396.0	1388.1
12.5°	1415.9	1404.0	1368.2	1360.3	1345.7
15°	1392.0	1377.5	1332.4	1307.3	1294.0
17.5°	1364.2	1343.0	1287.4	1258.3	1237.1
20°	1332.4	1305.9	1239.7	1206.6	1177.5
22.5°	1298.0	1267.5	1190.7	1145.7	1125.8
25°	1263.6	1221.2	1133.8	1079.5	1059.6
27.5°	1222.5	1177.5	1080.8	1018.5	988.1
30°	1178.8	1128.5	1022.5	955.0	919.2
32.5°	1136.4	1075.5	966.9	887.4	854.3
35°	1088.7	1021.2	904.6	821.2	792.0
37.5°	1042.4	969.5	846.3	755.0	721.8
40°	993.4	913.9	785.4	691.4	656.9
42.5°	943.0	858.3	724.5	626.5	593.4
45°	890.1	801.3	662.2	568.2	536.4
47.5°	839.7	745.7	602.6	508.6	479.5
50°	784.1	690.1	544.4	453.0	425.2
52.5°	729.8	630.5	488.7	401.3	376.2
55°	676.8	573.5	430.5	351.0	325.8
57.5°	622.5	516.6	378.8	304.6	283.4
60°	566.9	460.9	324.5	257.0	235.8
62.5°	512.6	406.6	278.1	214.6	204.0
65°	456.9	349.7	230.5	185.4	181.5
67.5°	404.0	296.7	185.4	162.9	158.9
70°	348.3	245.0	153.6	140.4	135.1
72.5°	295.4	197.3	128.5	117.9	115.2
75°	243.7	151.0	106.0	96.7	95.4
77.5°	192.1	107.3	83.4	78.1	75.5
80°	144.4	76.8	63.6	58.3	58.3
82.5°	100.7	51.7	43.7	41.1	41.1
85°	57.0	29.1	25.2	25.2	25.2
87.5°	21.2	10.6	10.6	9.3	9.3
90°	0.7	8.4	14.0	17.5	18.9
92.5°	17.5	14.7	16.8	18.2	18.9
95°	45.6	22.4	27.4	30.9	30.2
97.5°	82.1	24.6	35.8	37.9	38.6
100°	124.2	28.1	40.0	45.6	47.0
102.5°	170.5	169.1	41.4	49.1	51.2
105°	213.3	234.3	42.8	50.5	53.3
107.5°	263.1	280.6	44.2	51.9	54.7
110°	310.8	325.5	122.8	52.6	55.4

TEST NUMBER: P1000192

CATALOG NUMBER: SA2XXRDIP-B865D725UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.7	368.3	356.4	54.0	56.1
115°	403.4	415.3	432.8	108.0	57.5
117.5°	444.8	458.8	470.7	370.4	186.6
120°	491.1	501.6	514.2	522.6	427.9
122.5°	530.4	541.6	555.6	559.8	560.5
125°	570.3	579.5	592.8	597.7	599.8
127.5°	606.8	616.6	627.2	634.2	634.9
130°	641.2	652.4	660.1	667.9	667.2
132.5°	676.3	685.4	693.1	699.4	698.7
135°	705.7	717.0	723.3	730.3	728.9
137.5°	736.6	745.0	752.0	759.1	757.0
140°	766.8	772.4	780.1	786.4	782.9
142.5°	792.0	796.9	806.1	811.7	808.2
145°	818.7	818.0	829.9	834.8	831.3
147.5°	841.8	839.7	851.7	855.2	852.4
150°	864.3	859.4	870.6	874.8	871.3
152.5°	883.2	877.6	888.1	892.4	887.4
155°	901.5	895.2	903.6	907.8	902.2
157.5°	916.2	910.6	916.9	921.8	916.2
160°	928.8	924.6	928.8	933.0	928.1
162.5°	940.1	935.8	939.4	944.3	938.0
165°	949.9	945.7	947.8	952.7	947.8
167.5°	957.6	953.4	955.5	960.4	954.1
170°	963.9	959.7	961.1	966.0	959.7
172.5°	968.1	963.9	965.3	970.2	963.9
175°	971.6	966.7	968.1	973.0	966.0
177.5°	973.0	968.1	968.8	973.7	967.4
180°	969.5	969.5	969.5	969.5	969.5

(END OF REPORT)