

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000226

Luminaire Tested: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000226
REPORT IS A COMBINATION OF REPORTS P988786 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6945.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	94	90	87	90	87	83	81	73	71	69	60	59	57	48	48	47
2	90	83	77	72	82	77	72	67	65	61	58	54	51	49	44	42	41
3	82	74	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35
4	76	66	58	53	70	61	54	49	52	47	43	44	40	37	36	33	31
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28
6	65	53	46	40	60	50	43	38	43	37	33	36	32	29	30	27	25
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	23
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21
9	52	41	33	29	48	38	31	27	33	28	24	28	24	22	24	21	19
10	49	37	30	26	45	35	29	25	31	26	22	26	22	20	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30044	30044	30044	30044
5°	30114	31912	30218	25494
10°	29783	33729	29994	21052
15°	29137	33740	29630	15816
20°	28359	27889	28976	13048
25°	27418	17427	28008	11101
30°	26213	11158	26926	9556
35°	24750	8575	25551	8178
40°	23117	7208	24105	7153
45°	21375	6136	22268	6004
50°	19588	5213	20501	5194
55°	17608	4529	18556	4471
60°	15849	3455	16690	3412
65°	14209	2600	15052	2950
70°	12394	2077	13365	2404
75°	10478	1591	11434	1818
80°	8319	1081	8950	1192
85°	5777	557	6328	590

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 27484 cd/sqm

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	2.6
10°-20°	502.5	7.2
20°-30°	646.7	9.3
30°-40°	613.5	8.8
40°-50°	525.8	7.6
50°-60°	400.4	5.8
60°-70°	252.5	3.6
70°-80°	126.0	1.8
80°-90°	34.6	0.5
90°-100°	41.2	0.6
100°-110°	153.6	2.2
110°-120°	407.3	5.9
120°-130°	675.6	9.7
130°-140°	717.6	10.3
140°-150°	666.9	9.6
150°-160°	536.2	7.7
160°-170°	345.5	5.0
170°-180°	118.9	1.7
0°-30°	1329.3	19.1
0°-40°	1942.8	28.0
0°-60°	2869.1	41.3
0°-90°	3282.2	47.3
90°-120°	602.1	8.7
90°-150°	2662.2	38.3
90°-180°	3663.0	52.7
0°-180°	6945.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1898	1898	1898	1898	1898	
5°	1899	2112	1906	1687	1899	180
15°	1790	2383	1820	1117	1790	504
25°	1588	1272	1622	810	1588	729
35°	1303	626	1345	598	1303	815
45°	979	435	1020	426	979	755
55°	661	302	696	298	661	596
65°	400	157	423	178	400	397
75°	187	83	204	95	187	203
85°	41	24	45	25	41	46
90°	1	24	1	24	1	6
95°	59	39	59	39	59	70
105°	275	69	275	69	275	294
115°	520	74	520	74	520	512
125°	735	773	735	773	735	656
135°	910	939	910	939	910	703
145°	1055	1071	1055	1071	1055	660
155°	1162	1163	1162	1163	1162	535
165°	1224	1221	1224	1221	1224	346
175°	1252	1245	1252	1245	1252	119
180°	1249	1249	1249	1249	1249	

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0
2.5°	1909.9	1917.8	1921.8	1927.0	1938.9	1946.8	1958.7	1961.3	1960.0	1965.3	1950.8
5°	1899.3	1916.5	1932.3	1945.5	1966.6	1979.8	1994.3	2011.4	2015.4	2035.2	2023.3
7.5°	1884.8	1909.9	1932.3	1958.7	1990.3	2007.5	2029.9	2056.3	2068.2	2091.9	2098.5
10°	1861.1	1896.7	1934.9	1962.6	2006.2	2036.5	2057.6	2099.8	2127.5	2163.1	2157.9
12.5°	1822.8	1869.0	1920.4	1966.6	2023.3	2043.1	2082.7	2126.2	2161.8	2194.8	2223.8
15°	1789.9	1842.6	1899.3	1956.0	2020.7	2057.6	2097.2	2153.9	2192.1	2250.2	2275.2
17.5°	1745.0	1812.3	1879.5	1942.9	2019.4	2061.6	2110.4	2165.8	2222.5	2277.9	2297.7
20°	1698.8	1771.4	1843.9	1929.7	2016.7	2057.6	2107.7	2176.3	2231.7	2275.2	2275.2
22.5°	1643.4	1731.8	1814.9	1896.7	1991.7	2051.0	2102.5	2182.9	2222.5	2231.7	2196.1
25°	1588.1	1676.4	1767.4	1869.0	1977.2	2029.9	2087.9	2163.1	2176.3	2139.4	2047.1
27.5°	1522.1	1621.0	1723.9	1833.4	1946.8	2012.8	2065.5	2115.6	2090.6	1991.7	1847.9
30°	1454.8	1561.7	1677.7	1781.9	1919.1	1979.8	2024.6	2039.1	1960.0	1799.1	1613.1
32.5°	1384.9	1489.1	1611.8	1737.1	1875.6	1933.6	1962.6	1924.4	1779.3	1576.2	1349.3
35°	1303.2	1420.5	1548.5	1679.1	1816.2	1859.8	1876.9	1783.3	1597.3	1334.8	1109.3
37.5°	1229.3	1346.7	1483.9	1617.1	1750.3	1774.0	1756.9	1610.5	1374.4	1114.5	894.3
40°	1142.2	1267.5	1402.1	1551.1	1660.6	1667.2	1625.0	1435.0	1142.2	898.2	762.4
42.5°	1061.8	1188.4	1322.9	1474.6	1557.7	1535.3	1478.6	1229.3	953.6	774.2	664.8
45°	978.7	1098.7	1243.8	1378.3	1437.7	1384.9	1299.2	1034.1	800.6	666.1	581.7
47.5°	898.2	1010.3	1154.1	1283.4	1293.9	1234.6	1133.0	866.6	693.8	585.6	517.0
50°	819.1	931.2	1065.7	1172.6	1162.0	1080.2	965.5	753.1	602.8	517.0	460.3
52.5°	739.9	841.5	972.1	1056.5	1011.7	932.5	819.1	638.4	526.3	451.1	407.6
55°	660.8	755.8	867.9	937.8	866.6	775.6	695.1	547.4	456.4	395.7	362.7
57.5°	594.9	670.0	772.9	815.1	729.4	658.2	588.3	470.9	395.7	352.2	313.9
60°	522.3	590.9	675.3	700.4	612.0	554.0	494.6	398.3	339.0	300.7	275.7
62.5°	460.3	517.0	581.7	581.7	503.9	460.3	415.5	333.7	284.9	254.6	242.7
65°	399.7	440.5	486.7	481.4	415.5	377.2	341.6	275.7	238.7	217.6	205.8
67.5°	340.3	372.0	402.3	383.8	336.3	303.4	270.4	222.9	197.8	183.3	167.5
70°	286.2	311.3	327.1	310.0	262.5	234.8	211.0	179.4	159.6	141.1	131.9
72.5°	240.1	250.6	255.9	234.8	195.2	179.4	162.2	139.8	122.7	113.4	110.8
75°	187.3	196.5	192.6	176.7	143.8	131.9	118.7	102.9	98.9	93.6	91.0
77.5°	146.4	146.4	139.8	125.3	102.9	93.6	88.4	80.5	76.5	75.2	72.5
80°	104.2	102.9	98.9	83.1	69.9	64.6	64.6	59.4	58.0	55.4	55.4
82.5°	68.6	68.6	63.3	50.1	46.2	44.8	43.5	40.9	40.9	39.6	39.6
85°	40.9	38.3	31.7	27.7	26.4	26.4	25.1	23.7	25.1	23.7	23.7
87.5°	18.5	14.5	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
90°	0.9	3.1	5.3	7.5	9.7	10.8	11.6	13.2	14.9	16.5	18.1
92.5°	22.6	21.8	21.0	20.2	19.4	19.0	19.3	19.9	20.5	21.1	21.7
95°	58.8	52.2	45.5	38.9	32.2	28.9	29.6	31.0	32.5	33.9	35.3
97.5°	105.8	89.3	72.8	56.3	39.8	31.6	33.2	36.4	39.7	42.9	46.1
100°	160.0	132.5	105.0	77.5	50.0	36.2	37.9	41.3	44.7	48.1	51.5
102.5°	219.7	219.3	218.9	218.5	218.1	217.9	199.6	163.0	126.5	89.9	53.3
105°	274.8	280.8	286.9	292.9	299.0	302.0	274.6	219.7	164.8	110.0	55.1
107.5°	339.0	344.0	349.0	354.1	359.1	361.6	327.8	260.1	192.4	124.7	57.0
110°	400.5	404.7	408.9	413.2	417.4	419.5	390.5	332.4	274.3	216.3	158.2

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	458.4	462.0	465.6	469.2	472.8	474.6	472.9	469.5	466.1	462.7	459.3
115°	519.8	523.2	526.6	530.1	533.5	535.2	537.7	542.7	547.8	552.8	557.8
117.5°	573.2	577.2	581.2	585.2	589.2	591.2	592.9	596.3	599.8	603.2	606.6
120°	632.8	635.8	638.8	641.9	644.9	646.4	648.2	651.8	655.5	659.1	662.7
122.5°	683.5	686.7	689.9	693.1	696.3	697.9	699.9	703.9	708.0	712.0	716.0
125°	735.0	737.6	740.2	742.8	745.4	746.7	748.6	752.4	756.3	760.1	763.9
127.5°	782.0	784.8	787.6	790.5	793.3	794.7	796.2	799.2	802.2	805.2	808.2
130°	826.3	829.5	832.7	836.0	839.2	840.8	841.9	844.1	846.3	848.5	850.7
132.5°	871.5	874.1	876.7	879.4	882.0	883.3	884.4	886.6	888.8	891.0	893.2
135°	909.5	912.7	915.9	919.1	922.3	923.9	924.8	926.6	928.5	930.3	932.1
137.5°	949.3	951.7	954.1	956.5	958.9	960.1	961.1	963.1	965.1	967.1	969.1
140°	988.1	989.7	991.3	993.0	994.6	995.4	996.5	998.7	1000.9	1003.1	1005.3
142.5°	1020.7	1022.1	1023.5	1024.9	1026.3	1027.0	1028.3	1030.9	1033.6	1036.2	1038.8
145°	1055.0	1054.8	1054.6	1054.4	1054.2	1054.1	1055.8	1059.2	1062.7	1066.1	1069.5
147.5°	1084.9	1084.3	1083.7	1083.1	1082.5	1082.2	1083.9	1087.3	1090.7	1094.1	1097.5
150°	1113.8	1112.4	1111.0	1109.6	1108.2	1107.5	1109.1	1112.3	1115.5	1118.7	1121.9
152.5°	1138.2	1136.6	1135.0	1133.4	1131.8	1131.0	1132.5	1135.5	1138.5	1141.5	1144.5
155°	1161.7	1159.9	1158.1	1156.3	1154.5	1153.6	1154.8	1157.2	1159.6	1162.0	1164.4
157.5°	1180.7	1179.1	1177.5	1175.9	1174.3	1173.5	1174.4	1176.2	1178.0	1179.8	1181.6
160°	1197.0	1195.8	1194.6	1193.3	1192.1	1191.5	1192.1	1193.3	1194.6	1195.8	1197.0
162.5°	1211.4	1210.2	1209.0	1207.8	1206.6	1206.0	1206.5	1207.5	1208.5	1209.5	1210.5
165°	1224.1	1222.9	1221.7	1220.5	1219.3	1218.7	1219.0	1219.6	1220.2	1220.8	1221.4
167.5°	1234.0	1232.8	1231.6	1230.4	1229.2	1228.6	1228.9	1229.5	1230.1	1230.7	1231.3
170°	1242.2	1241.0	1239.8	1238.5	1237.3	1236.7	1236.9	1237.3	1237.8	1238.2	1238.6
172.5°	1247.6	1246.4	1245.2	1244.0	1242.8	1242.2	1242.4	1242.8	1243.2	1243.6	1244.0
175°	1252.1	1250.7	1249.3	1247.9	1246.5	1245.8	1246.0	1246.4	1246.8	1247.2	1247.6
177.5°	1253.9	1252.5	1251.1	1249.7	1248.3	1247.6	1247.7	1247.9	1248.1	1248.3	1248.5
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0
2.5°	1965.3	1967.9	1971.9	1990.3	1993.0	1998.3	1995.6	1995.6	1996.9	1994.3	1995.6
5°	2049.7	2053.7	2073.4	2095.9	2101.1	2095.9	2102.5	2111.7	2111.7	2111.7	2109.0
7.5°	2128.8	2143.3	2165.8	2198.7	2205.3	2211.9	2223.8	2215.9	2218.5	2230.4	2226.4
10°	2205.3	2226.4	2251.5	2279.2	2293.7	2302.9	2308.2	2320.1	2347.8	2316.1	2328.0
12.5°	2277.9	2308.2	2334.6	2364.9	2375.5	2387.4	2391.3	2401.9	2401.9	2400.5	2409.8
15°	2325.4	2353.1	2376.8	2396.6	2399.2	2396.6	2393.9	2395.3	2399.2	2383.4	2392.6
17.5°	2335.9	2338.6	2346.5	2338.6	2339.9	2312.2	2296.3	2292.4	2255.5	2256.8	2287.1
20°	2284.5	2239.6	2227.8	2184.2	2157.9	2086.6	2084.0	2064.2	1986.4	2010.1	2004.8
22.5°	2143.3	2066.8	1965.3	1915.2	1890.1	1814.9	1756.9	1716.0	1688.3	1660.6	1648.7
25°	1957.4	1833.4	1689.6	1590.7	1576.2	1506.3	1399.4	1349.3	1290.0	1271.5	1303.2
27.5°	1717.3	1556.4	1394.2	1242.5	1214.8	1151.5	1097.4	1061.8	993.2	989.2	991.9
30°	1391.5	1229.3	1093.4	994.5	925.9	896.9	861.3	834.9	807.2	817.8	820.4
32.5°	1143.6	989.2	862.6	809.9	778.2	759.7	729.4	712.2	700.4	696.4	695.1
35°	908.8	805.9	749.2	697.7	679.3	666.1	643.7	635.7	625.2	626.5	626.5
37.5°	778.2	692.5	650.3	623.9	606.7	600.1	585.6	577.7	571.1	568.5	572.4
40°	671.4	612.0	585.6	561.9	547.4	544.7	536.8	527.6	519.7	521.0	525.0
42.5°	593.5	559.2	527.6	509.1	498.6	494.6	488.0	481.4	481.4	477.5	476.2
45°	531.5	503.9	477.5	460.3	453.7	448.5	440.5	439.2	433.9	435.3	436.6
47.5°	476.2	453.7	433.9	416.8	410.2	408.9	401.0	395.7	395.7	394.4	393.1
50°	426.0	403.6	386.5	377.2	368.0	365.4	364.0	362.7	360.1	360.1	361.4
52.5°	385.1	362.7	349.5	341.6	336.3	333.7	333.7	332.4	332.4	332.4	331.1
55°	340.3	321.8	311.3	308.6	306.0	304.7	303.4	300.7	299.4	302.0	299.4
57.5°	298.1	291.5	282.3	279.6	273.0	273.0	269.1	266.4	263.8	266.4	266.4
60°	265.1	255.9	250.6	242.7	237.4	232.1	225.5	224.2	221.6	220.3	219.0
62.5°	230.8	222.9	209.7	197.8	189.9	184.7	182.0	180.7	180.7	179.4	179.4
65°	192.6	174.1	167.5	163.6	162.2	160.9	158.3	157.0	158.3	157.0	158.3
67.5°	150.4	147.7	143.8	141.1	139.8	138.5	138.5	137.2	137.2	137.2	137.2
70°	130.6	124.0	122.7	120.0	120.0	118.7	118.7	118.7	118.7	117.4	120.0
72.5°	108.2	104.2	102.9	101.6	101.6	101.6	100.2	100.2	100.2	98.9	100.2
75°	88.4	87.1	84.4	84.4	83.1	84.4	83.1	83.1	81.8	83.1	83.1
77.5°	71.2	69.9	68.6	68.6	67.3	67.3	67.3	67.3	67.3	67.3	68.6
80°	54.1	52.8	51.4	52.8	51.4	52.8	51.4	51.4	52.8	51.4	51.4
82.5°	39.6	38.3	38.3	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9
85°	23.7	22.4	22.4	23.7	22.4	23.7	22.4	22.4	22.4	23.7	23.7
87.5°	10.6	11.9	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	11.9
90°	19.1	20.1	21.1	22.1	22.6	22.8	23.2	23.6	24.0	24.4	24.0
92.5°	22.1	22.5	22.9	23.3	23.5	23.6	23.8	24.0	24.2	24.4	24.2
95°	36.3	37.3	38.3	39.3	39.8	39.7	39.5	39.3	39.1	38.9	39.1
97.5°	46.7	47.3	47.9	48.5	48.8	48.9	49.1	49.3	49.5	49.7	49.5
100°	53.1	54.7	56.4	58.0	58.8	59.0	59.4	59.8	60.2	60.6	60.2
102.5°	55.5	57.7	60.0	62.2	63.3	63.6	64.2	64.8	65.4	66.0	65.4
105°	57.3	59.5	61.8	64.0	65.1	65.5	66.3	67.1	67.9	68.7	67.9
107.5°	59.2	61.4	63.6	65.8	66.9	67.3	68.1	68.9	69.7	70.5	69.7
110°	138.1	118.0	97.9	77.8	67.8	68.2	69.0	69.8	70.6	71.4	70.6

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	372.7	286.1	199.5	112.9	69.6	69.9	70.5	71.1	71.7	72.3	71.7
115°	464.8	371.8	278.7	185.7	139.2	132.0	117.5	103.0	88.6	74.1	88.6
117.5°	577.9	549.1	520.4	491.7	477.3	451.0	398.4	345.7	293.1	240.5	293.1
120°	665.1	667.5	669.9	672.3	673.5	659.9	632.8	605.7	578.6	551.5	578.6
122.5°	717.2	718.4	719.6	720.8	721.4	721.5	721.7	721.9	722.1	722.3	722.1
125°	765.3	766.7	768.2	769.6	770.3	770.6	771.2	771.8	772.4	773.0	772.4
127.5°	810.2	812.2	814.3	816.3	817.3	817.4	817.6	817.8	818.0	818.2	818.0
130°	852.9	855.1	857.4	859.6	860.7	860.6	860.4	860.2	860.0	859.8	860.0
132.5°	895.0	896.8	898.6	900.4	901.3	901.2	901.0	900.8	900.6	900.4	900.6
135°	934.1	936.1	938.1	940.1	941.1	940.9	940.5	940.1	939.7	939.3	939.7
137.5°	971.1	973.1	975.2	977.2	978.2	977.9	977.3	976.7	976.1	975.5	976.1
140°	1007.1	1008.9	1010.7	1012.5	1013.4	1012.9	1011.9	1010.9	1009.9	1008.9	1009.9
142.5°	1040.4	1042.0	1043.6	1045.2	1046.0	1045.5	1044.5	1043.5	1042.5	1041.5	1042.5
145°	1070.9	1072.3	1073.7	1075.1	1075.8	1075.3	1074.3	1073.3	1072.3	1071.3	1072.3
147.5°	1098.5	1099.5	1100.5	1101.5	1102.0	1101.6	1100.8	1100.0	1099.2	1098.4	1099.2
150°	1123.1	1124.3	1125.6	1126.8	1127.4	1126.9	1125.9	1124.8	1123.8	1122.8	1123.8
152.5°	1145.7	1146.9	1148.2	1149.4	1150.0	1149.3	1147.9	1146.4	1145.0	1143.6	1145.0
155°	1165.6	1166.8	1168.0	1169.2	1169.8	1169.0	1167.4	1165.8	1164.2	1162.6	1164.2
157.5°	1183.0	1184.4	1185.8	1187.2	1187.9	1187.1	1185.5	1183.9	1182.3	1180.7	1182.3
160°	1198.2	1199.4	1200.6	1201.8	1202.4	1201.7	1200.3	1198.9	1197.5	1196.1	1197.5
162.5°	1211.9	1213.3	1214.8	1216.2	1216.9	1216.0	1214.2	1212.3	1210.5	1208.7	1210.5
165°	1222.8	1224.2	1225.6	1227.0	1227.7	1227.0	1225.6	1224.2	1222.8	1221.4	1222.8
167.5°	1232.7	1234.1	1235.5	1236.9	1237.6	1236.7	1234.9	1233.1	1231.3	1229.5	1231.3
170°	1240.0	1241.4	1242.8	1244.2	1244.9	1244.0	1242.2	1240.3	1238.5	1236.7	1238.5
172.5°	1245.4	1246.8	1248.2	1249.6	1250.3	1249.4	1247.6	1245.8	1244.0	1242.2	1244.0
175°	1249.0	1250.4	1251.8	1253.2	1253.9	1252.9	1250.9	1248.9	1246.9	1244.9	1246.9
177.5°	1249.9	1251.3	1252.7	1254.1	1254.8	1253.9	1252.1	1250.3	1248.5	1246.7	1248.5
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0
2.5°	2000.9	1991.7	1989.0	1991.7	1989.0	1990.3	1981.1	1946.8	1956.0	1941.5	1949.5
5°	2114.3	2106.4	2089.3	2086.6	2084.0	2081.4	2068.2	2037.8	2026.0	2006.2	2004.8
7.5°	2222.5	2222.5	2209.3	2200.1	2188.2	2179.0	2161.8	2117.0	2098.5	2074.8	2061.6
10°	2329.3	2295.0	2309.5	2300.3	2271.3	2266.0	2234.4	2208.0	2172.4	2148.6	2127.5
12.5°	2405.8	2395.3	2382.1	2374.2	2366.2	2349.1	2328.0	2260.7	2242.3	2194.8	2171.0
15°	2403.2	2396.6	2400.5	2400.5	2397.9	2393.9	2376.8	2328.0	2296.3	2250.2	2209.3
17.5°	2273.9	2291.1	2308.2	2320.1	2346.5	2358.3	2374.2	2345.1	2325.4	2285.8	2242.3
20°	2048.4	2090.6	2140.7	2151.3	2175.0	2244.9	2276.6	2301.6	2309.5	2296.3	2260.7
22.5°	1734.5	1770.1	1891.4	1888.8	1923.1	2006.2	2098.5	2173.7	2233.0	2266.0	2252.8
25°	1358.5	1408.7	1473.3	1522.1	1634.2	1758.2	1873.0	1993.0	2095.9	2186.9	2209.3
27.5°	1027.5	1093.4	1144.9	1209.5	1266.2	1412.6	1560.4	1747.6	1867.7	2040.5	2130.2
30°	831.0	861.3	912.7	943.1	970.8	1082.9	1250.4	1435.0	1646.1	1845.3	1999.6
32.5°	709.6	730.7	769.0	782.2	811.2	886.4	991.9	1160.7	1378.3	1619.7	1822.8
35°	637.1	659.5	667.4	679.3	703.0	750.5	823.0	945.7	1142.2	1378.3	1621.0
37.5°	575.1	586.9	609.4	617.3	625.2	660.8	709.6	795.3	925.9	1119.8	1388.9
40°	531.5	538.1	550.0	556.6	561.9	586.9	630.5	688.5	784.8	932.5	1180.5
42.5°	485.4	493.3	501.2	509.1	515.7	535.5	561.9	617.3	681.9	794.0	973.4
45°	440.5	445.8	455.0	460.3	469.6	485.4	509.1	547.4	605.4	676.6	821.7
47.5°	399.7	406.2	410.2	416.8	423.4	440.5	463.0	488.0	535.5	605.4	710.9
50°	362.7	370.6	375.9	377.2	382.5	398.3	416.8	444.5	474.8	528.9	621.2
52.5°	336.3	337.7	341.6	346.9	345.6	354.8	372.0	393.1	424.7	468.2	535.5
55°	306.0	310.0	312.6	313.9	313.9	321.8	331.1	350.8	375.9	411.5	468.2
57.5°	267.8	271.7	279.6	282.3	286.2	290.2	294.1	307.3	328.4	362.7	408.9
60°	228.2	230.8	238.7	244.0	246.6	257.2	262.5	273.0	284.9	310.0	353.5
62.5°	183.3	186.0	189.9	195.2	200.5	216.3	229.5	240.1	249.3	266.4	302.0
65°	159.6	160.9	163.6	164.9	166.2	172.8	184.7	199.2	216.3	229.5	250.6
67.5°	138.5	139.8	141.1	143.8	145.1	146.4	151.7	155.6	172.8	191.3	207.1
70°	118.7	121.3	122.7	122.7	124.0	126.6	129.3	134.5	139.8	149.0	168.8
72.5°	100.2	101.6	104.2	104.2	104.2	106.8	109.5	112.1	114.8	120.0	127.9
75°	83.1	85.7	85.7	85.7	87.1	87.1	89.7	92.3	95.0	98.9	101.6
77.5°	68.6	68.6	68.6	68.6	69.9	69.9	71.2	73.9	75.2	76.5	79.1
80°	51.4	52.8	52.8	52.8	54.1	54.1	54.1	56.7	58.0	58.0	60.7
82.5°	38.3	38.3	38.3	39.6	38.3	39.6	39.6	40.9	39.6	40.9	42.2
85°	23.7	23.7	23.7	25.1	25.1	25.1	25.1	25.1	25.1	25.1	26.4
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	13.2	11.9	11.9
90°	23.6	23.2	22.8	22.6	22.1	21.1	20.1	19.1	18.1	16.5	14.9
92.5°	24.0	23.8	23.6	23.5	23.3	22.9	22.5	22.1	21.7	21.1	20.5
95°	39.3	39.5	39.7	39.8	39.3	38.3	37.3	36.3	35.3	33.9	32.5
97.5°	49.3	49.1	48.9	48.8	48.5	47.9	47.3	46.7	46.1	42.9	39.7
100°	59.8	59.4	59.0	58.8	58.0	56.4	54.7	53.1	51.5	48.1	44.7
102.5°	64.8	64.2	63.6	63.3	62.2	60.0	57.7	55.5	53.3	49.9	46.5
105°	67.1	66.3	65.5	65.1	64.0	61.8	59.5	57.3	55.1	51.0	47.8
107.5°	68.9	68.1	67.3	66.9	65.8	63.6	61.4	59.2	57.0	52.7	49.5
110°	69.8	69.0	68.2	67.8	77.8	97.9	118.0	138.1	158.2	216.3	274.3

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	71.1	70.5	69.9	69.6	112.9	199.5	286.1	372.7	459.3	462.7	466.1
115°	103.0	117.5	132.0	139.2	185.7	278.7	371.8	464.8	557.8	552.8	547.8
117.5°	345.7	398.4	451.0	477.3	491.7	520.4	549.1	577.9	606.6	603.2	599.8
120°	605.7	632.8	659.9	673.5	672.3	669.9	667.5	665.1	662.7	659.1	655.5
122.5°	721.9	721.7	721.5	721.4	720.8	719.6	718.4	717.2	716.0	712.0	708.0
125°	771.8	771.2	770.6	770.3	769.6	768.2	766.7	765.3	763.9	760.1	756.3
127.5°	817.8	817.6	817.4	817.3	816.3	814.3	812.2	810.2	808.2	805.2	802.2
130°	860.2	860.4	860.6	860.7	859.6	857.4	855.1	852.9	850.7	848.5	846.3
132.5°	900.8	901.0	901.2	901.3	900.4	898.6	896.8	895.0	893.2	891.0	888.8
135°	940.1	940.5	940.9	941.1	940.1	938.1	936.1	934.1	932.1	930.3	928.5
137.5°	976.7	977.3	977.9	978.2	977.2	975.2	973.1	971.1	969.1	967.1	965.1
140°	1010.9	1011.9	1012.9	1013.4	1012.5	1010.7	1008.9	1007.1	1005.3	1003.1	1000.9
142.5°	1043.5	1044.5	1045.5	1046.0	1045.2	1043.6	1042.0	1040.4	1038.8	1036.2	1033.6
145°	1073.3	1074.3	1075.3	1075.8	1075.1	1073.7	1072.3	1070.9	1069.5	1066.1	1062.7
147.5°	1100.0	1100.8	1101.6	1102.0	1101.5	1100.5	1099.5	1098.5	1097.5	1094.1	1090.7
150°	1124.8	1125.9	1126.9	1127.4	1126.8	1125.6	1124.3	1123.1	1121.9	1118.7	1115.5
152.5°	1146.4	1147.9	1149.3	1150.0	1149.4	1148.2	1146.9	1145.7	1144.5	1141.5	1138.5
155°	1165.8	1167.4	1169.0	1169.8	1169.2	1168.0	1166.8	1165.6	1164.4	1162.0	1159.6
157.5°	1183.9	1185.5	1187.1	1187.9	1187.2	1185.8	1184.4	1183.0	1181.6	1179.8	1178.0
160°	1198.9	1200.3	1201.7	1202.4	1201.8	1200.6	1199.4	1198.2	1197.0	1195.8	1194.6
162.5°	1212.3	1214.2	1216.0	1216.9	1216.2	1214.8	1213.3	1211.9	1210.5	1209.5	1208.5
165°	1224.2	1225.6	1227.0	1227.7	1227.0	1225.6	1224.2	1222.8	1221.4	1220.8	1220.2
167.5°	1233.1	1234.9	1236.7	1237.6	1236.9	1235.5	1234.1	1232.7	1231.3	1230.7	1230.1
170°	1240.3	1242.2	1244.0	1244.9	1244.2	1242.8	1241.4	1240.0	1238.6	1238.2	1237.8
172.5°	1245.8	1247.6	1249.4	1250.3	1249.6	1248.2	1246.8	1245.4	1244.0	1243.6	1243.2
175°	1248.9	1250.9	1252.9	1253.9	1253.2	1251.8	1250.4	1249.0	1247.6	1247.2	1246.8
177.5°	1250.3	1252.1	1253.9	1254.8	1254.1	1252.7	1251.3	1249.9	1248.5	1248.3	1248.1
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0
2.5°	1937.6	1931.0	1931.0	1927.0	1927.0	1905.9	1905.9	1912.5	1904.6	1895.4	1882.2
5°	1987.7	1973.2	1969.2	1964.0	1946.8	1920.4	1909.9	1905.9	1890.1	1870.3	1847.9
7.5°	2035.2	2011.4	1999.6	1987.7	1965.3	1928.3	1907.2	1892.7	1869.0	1838.7	1809.6
10°	2081.4	2051.0	2020.7	2006.2	1974.5	1928.3	1898.0	1874.3	1840.0	1799.1	1758.2
12.5°	2123.6	2060.2	2055.0	2026.0	1979.8	1927.0	1880.9	1846.6	1803.0	1755.6	1708.1
15°	2160.5	2095.9	2064.2	2037.8	1977.2	1911.2	1862.4	1820.2	1762.2	1708.1	1650.0
17.5°	2179.0	2109.0	2087.9	2044.4	1982.4	1896.7	1830.7	1779.3	1716.0	1651.4	1585.4
20°	2197.4	2115.6	2081.4	2051.0	1966.6	1869.0	1795.1	1735.8	1665.9	1589.4	1516.8
22.5°	2206.7	2115.6	2074.8	2032.5	1950.8	1838.7	1751.6	1681.7	1599.9	1522.1	1435.0
25°	2190.8	2107.7	2058.9	2015.4	1923.1	1801.7	1701.5	1622.3	1535.3	1446.9	1358.5
27.5°	2151.3	2089.3	2032.5	1987.7	1884.8	1754.2	1648.7	1559.0	1469.3	1370.4	1280.7
30°	2077.4	2049.7	2004.8	1954.7	1842.6	1712.0	1586.7	1494.4	1395.5	1296.6	1202.9
32.5°	1962.6	1986.4	1957.4	1913.8	1792.5	1654.0	1520.8	1427.1	1319.0	1212.1	1126.4
35°	1822.8	1907.2	1891.4	1861.1	1739.7	1592.0	1458.8	1345.4	1237.2	1129.0	1043.3
37.5°	1669.8	1797.8	1811.0	1792.5	1679.1	1528.7	1382.3	1271.5	1160.7	1051.2	964.2
40°	1460.1	1656.6	1698.8	1706.8	1615.8	1452.2	1299.2	1191.0	1081.6	974.7	869.2
42.5°	1267.5	1515.5	1568.3	1601.2	1535.3	1377.0	1222.7	1102.7	994.5	898.2	792.7
45°	1086.8	1345.4	1431.1	1473.3	1444.3	1291.3	1131.7	1019.6	920.6	832.3	730.7
47.5°	900.9	1160.7	1280.7	1348.0	1348.0	1204.2	1044.6	933.8	838.9	763.7	674.0
50°	776.9	993.2	1117.2	1205.5	1229.3	1115.9	965.5	857.3	767.6	685.9	617.3
52.5°	662.1	856.0	958.9	1051.2	1119.8	1020.9	877.1	779.5	691.1	614.6	560.6
55°	572.4	717.5	811.2	912.7	989.2	924.6	791.4	696.4	619.9	556.6	510.4
57.5°	486.7	613.3	689.8	779.5	861.3	812.5	705.7	623.9	556.6	501.2	460.3
60°	414.2	517.0	576.4	646.3	747.9	713.6	625.2	550.0	495.9	445.8	411.5
62.5°	352.2	433.9	484.1	534.2	626.5	610.7	542.1	484.1	437.9	395.7	366.7
65°	288.9	356.1	395.7	439.2	513.1	519.7	464.3	423.4	381.2	344.3	317.9
67.5°	233.5	286.2	321.8	358.8	418.1	436.6	398.3	364.0	328.4	298.1	274.3
70°	188.6	225.5	251.9	280.9	329.7	352.2	332.4	308.6	279.6	254.6	233.5
72.5°	149.0	172.8	188.6	211.0	250.6	273.0	271.7	250.6	229.5	212.4	195.2
75°	109.5	127.9	141.1	155.6	187.3	208.4	213.7	204.4	183.3	170.1	157.0
77.5°	83.1	93.6	100.2	110.8	133.2	151.7	159.6	157.0	142.4	131.9	122.7
80°	63.3	65.9	68.6	72.5	91.0	108.2	113.4	112.1	104.2	100.2	89.7
82.5°	44.8	46.2	47.5	48.8	55.4	69.9	75.2	77.8	71.2	67.3	58.0
85°	26.4	27.7	27.7	30.3	31.7	35.6	44.8	44.8	43.5	38.3	36.9
87.5°	13.2	13.2	11.9	11.9	13.2	14.5	17.1	19.8	17.1	15.8	14.5
90°	13.2	11.6	10.8	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.9	19.3	19.0	19.4	20.2	21.0	21.8	22.6	21.8	21.0	20.2
95°	31.0	29.6	28.9	32.2	38.9	45.5	52.2	58.8	52.2	45.5	38.9
97.5°	36.4	33.2	31.6	39.8	56.3	72.8	89.3	105.8	89.3	72.8	56.3
100°	41.3	37.9	36.2	50.0	77.5	105.0	132.5	160.0	132.5	105.0	77.5
102.5°	163.0	199.6	217.9	218.1	218.5	218.9	219.3	219.7	219.3	218.9	218.5
105°	219.7	274.6	302.0	299.0	292.9	286.9	280.8	274.8	280.8	286.9	292.9
107.5°	260.1	327.8	361.6	359.1	354.1	349.0	344.0	339.0	344.0	349.0	354.1
110°	332.4	390.5	419.5	417.4	413.2	408.9	404.7	400.5	404.7	408.9	413.2

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	469.5	472.9	474.6	472.8	469.2	465.6	462.0	458.4	462.0	465.6	469.2
115°	542.7	537.7	535.2	533.5	530.1	526.6	523.2	519.8	523.2	526.6	530.1
117.5°	596.3	592.9	591.2	589.2	585.2	581.2	577.2	573.2	577.2	581.2	585.2
120°	651.8	648.2	646.4	644.9	641.9	638.8	635.8	632.8	635.8	638.8	641.9
122.5°	703.9	699.9	697.9	696.3	693.1	689.9	686.7	683.5	686.7	689.9	693.1
125°	752.4	748.6	746.7	745.4	742.8	740.2	737.6	735.0	737.6	740.2	742.8
127.5°	799.2	796.2	794.7	793.3	790.5	787.6	784.8	782.0	784.8	787.6	790.5
130°	844.1	841.9	840.8	839.2	836.0	832.7	829.5	826.3	829.5	832.7	836.0
132.5°	886.6	884.4	883.3	882.0	879.4	876.7	874.1	871.5	874.1	876.7	879.4
135°	926.6	924.8	923.9	922.3	919.1	915.9	912.7	909.5	912.7	915.9	919.1
137.5°	963.1	961.1	960.1	958.9	956.5	954.1	951.7	949.3	951.7	954.1	956.5
140°	998.7	996.5	995.4	994.6	993.0	991.3	989.7	988.1	989.7	991.3	993.0
142.5°	1030.9	1028.3	1027.0	1026.3	1024.9	1023.5	1022.1	1020.7	1022.1	1023.5	1024.9
145°	1059.2	1055.8	1054.1	1054.2	1054.4	1054.6	1054.8	1055.0	1054.8	1054.6	1054.4
147.5°	1087.3	1083.9	1082.2	1082.5	1083.1	1083.7	1084.3	1084.9	1084.3	1083.7	1083.1
150°	1112.3	1109.1	1107.5	1108.2	1109.6	1111.0	1112.4	1113.8	1112.4	1111.0	1109.6
152.5°	1135.5	1132.5	1131.0	1131.8	1133.4	1135.0	1136.6	1138.2	1136.6	1135.0	1133.4
155°	1157.2	1154.8	1153.6	1154.5	1156.3	1158.1	1159.9	1161.7	1159.9	1158.1	1156.3
157.5°	1176.2	1174.4	1173.5	1174.3	1175.9	1177.5	1179.1	1180.7	1179.1	1177.5	1175.9
160°	1193.3	1192.1	1191.5	1192.1	1193.3	1194.6	1195.8	1197.0	1195.8	1194.6	1193.3
162.5°	1207.5	1206.5	1206.0	1206.6	1207.8	1209.0	1210.2	1211.4	1210.2	1209.0	1207.8
165°	1219.6	1219.0	1218.7	1219.3	1220.5	1221.7	1222.9	1224.1	1222.9	1221.7	1220.5
167.5°	1229.5	1228.9	1228.6	1229.2	1230.4	1231.6	1232.8	1234.0	1232.8	1231.6	1230.4
170°	1237.3	1236.9	1236.7	1237.3	1238.5	1239.8	1241.0	1242.2	1241.0	1239.8	1238.5
172.5°	1242.8	1242.4	1242.2	1242.8	1244.0	1245.2	1246.4	1247.6	1246.4	1245.2	1244.0
175°	1246.4	1246.0	1245.8	1246.5	1247.9	1249.3	1250.7	1252.1	1250.7	1249.3	1247.9
177.5°	1247.9	1247.7	1247.6	1248.3	1249.7	1251.1	1252.5	1253.9	1252.5	1251.1	1249.7
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0
2.5°	1876.9	1878.2	1882.2	1870.3	1851.8	1843.9	1820.2	1816.2	1812.3	1812.3	1816.2
5°	1834.7	1829.4	1830.7	1808.3	1781.9	1766.1	1733.1	1738.4	1721.3	1710.7	1713.4
7.5°	1788.5	1774.0	1772.7	1743.7	1710.7	1681.7	1647.4	1639.5	1623.7	1605.2	1597.3
10°	1730.5	1719.9	1700.2	1667.2	1625.0	1601.2	1555.1	1527.4	1523.4	1495.7	1485.2
12.5°	1671.1	1652.7	1632.9	1586.7	1539.2	1501.0	1466.7	1436.4	1415.3	1391.5	1375.7
15°	1602.6	1580.1	1557.7	1508.9	1453.5	1415.3	1363.8	1319.0	1257.0	1208.2	1180.5
17.5°	1527.4	1502.3	1472.0	1417.9	1363.8	1311.1	1216.1	1163.3	1119.8	1090.8	1073.6
20°	1449.6	1421.9	1391.5	1337.4	1243.8	1151.5	1098.7	1057.8	1031.4	1002.4	981.3
22.5°	1367.8	1338.8	1305.8	1221.4	1122.5	1057.8	1016.9	978.7	940.4	924.6	914.1
25°	1291.3	1264.9	1222.7	1107.9	1030.1	970.8	924.6	899.5	879.8	858.7	838.9
27.5°	1212.1	1163.3	1104.0	1007.7	958.9	898.2	865.3	846.8	812.5	798.0	788.7
30°	1117.2	1063.1	1006.4	937.8	881.1	838.9	808.5	778.2	758.4	743.9	728.1
32.5°	1020.9	969.5	933.8	862.6	820.4	776.9	747.9	729.4	700.4	691.1	684.6
35°	937.8	894.3	862.6	804.6	765.0	725.4	704.3	676.6	658.2	641.0	630.5
37.5°	856.0	832.3	799.3	750.5	708.3	676.6	647.6	638.4	613.3	604.1	593.5
40°	799.3	763.7	736.0	693.8	658.2	623.9	605.4	584.3	567.2	552.7	548.7
42.5°	730.7	704.3	688.5	642.3	605.4	585.6	563.2	539.5	526.3	514.4	499.9
45°	679.3	655.5	633.1	596.2	563.2	538.1	518.4	502.5	480.1	474.8	452.4
47.5°	625.2	601.5	584.3	547.4	517.0	493.3	478.8	457.7	439.2	427.3	416.8
50°	571.1	551.3	535.5	503.9	477.5	452.4	432.6	411.5	403.6	383.8	377.2
52.5°	519.7	506.5	489.3	459.0	432.6	411.5	390.4	373.3	361.4	350.8	342.9
55°	476.2	455.0	447.1	414.2	391.7	369.3	350.8	340.3	325.8	319.2	312.6
57.5°	427.3	415.5	402.3	377.2	352.2	331.1	317.9	302.0	294.1	286.2	280.9
60°	385.1	368.0	357.4	336.3	313.9	294.1	282.3	270.4	259.8	253.2	242.7
62.5°	336.3	323.2	316.6	294.1	275.7	257.2	246.6	234.8	226.9	215.0	201.8
65°	294.1	283.6	275.7	257.2	240.1	222.9	212.4	197.8	187.3	180.7	179.4
67.5°	257.2	249.3	237.4	220.3	203.1	189.9	178.1	166.2	164.9	162.2	162.2
70°	216.3	208.4	201.8	183.3	168.8	154.3	151.7	147.7	143.8	142.4	139.8
72.5°	180.7	174.1	166.2	150.4	135.9	131.9	129.3	126.6	122.7	121.3	120.0
75°	146.4	137.2	131.9	117.4	113.4	110.8	108.2	104.2	101.6	100.2	97.6
77.5°	112.1	102.9	102.9	95.0	92.3	88.4	85.7	83.1	81.8	79.1	79.1
80°	79.1	79.1	76.5	72.5	68.6	67.3	63.3	62.0	60.7	62.0	59.4
82.5°	58.0	52.8	52.8	50.1	47.5	46.2	43.5	43.5	42.2	42.2	42.2
85°	33.0	33.0	31.7	29.0	27.7	27.7	26.4	26.4	25.1	25.1	23.7
87.5°	13.2	11.9	13.2	11.9	11.9	10.6	10.6	10.6	9.2	10.6	9.2
90°	9.7	10.8	11.6	13.2	14.9	16.5	18.1	19.1	20.1	21.1	22.1
92.5°	19.4	19.0	19.3	19.9	20.5	21.1	21.7	22.1	22.5	22.9	23.3
95°	32.2	28.9	29.6	31.0	32.5	33.9	35.3	36.3	37.3	38.3	39.3
97.5°	39.8	31.6	33.2	36.4	39.7	42.9	46.1	46.7	47.3	47.9	48.5
100°	50.0	36.2	37.9	41.3	44.7	48.1	51.5	53.1	54.7	56.4	58.0
102.5°	218.1	217.9	199.6	163.0	126.5	89.9	53.3	55.5	57.7	60.0	62.2
105°	299.0	302.0	274.6	219.7	164.8	110.0	55.1	57.3	59.5	61.8	64.0
107.5°	359.1	361.6	327.8	260.1	192.4	124.7	57.0	59.2	61.4	63.6	65.8
110°	417.4	419.5	390.5	332.4	274.3	216.3	158.2	138.1	118.0	97.9	77.8

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	472.8	474.6	472.9	469.5	466.1	462.7	459.3	372.7	286.1	199.5	112.9
115°	533.5	535.2	537.7	542.7	547.8	552.8	557.8	464.8	371.8	278.7	185.7
117.5°	589.2	591.2	592.9	596.3	599.8	603.2	606.6	577.9	549.1	520.4	491.7
120°	644.9	646.4	648.2	651.8	655.5	659.1	662.7	665.1	667.5	669.9	672.3
122.5°	696.3	697.9	699.9	703.9	708.0	712.0	716.0	717.2	718.4	719.6	720.8
125°	745.4	746.7	748.6	752.4	756.3	760.1	763.9	765.3	766.7	768.2	769.6
127.5°	793.3	794.7	796.2	799.2	802.2	805.2	808.2	810.2	812.2	814.3	816.3
130°	839.2	840.8	841.9	844.1	846.3	848.5	850.7	852.9	855.1	857.4	859.6
132.5°	882.0	883.3	884.4	886.6	888.8	891.0	893.2	895.0	896.8	898.6	900.4
135°	922.3	923.9	924.8	926.6	928.5	930.3	932.1	934.1	936.1	938.1	940.1
137.5°	958.9	960.1	961.1	963.1	965.1	967.1	969.1	971.1	973.1	975.2	977.2
140°	994.6	995.4	996.5	998.7	1000.9	1003.1	1005.3	1007.1	1008.9	1010.7	1012.5
142.5°	1026.3	1027.0	1028.3	1030.9	1033.6	1036.2	1038.8	1040.4	1042.0	1043.6	1045.2
145°	1054.2	1054.1	1055.8	1059.2	1062.7	1066.1	1069.5	1070.9	1072.3	1073.7	1075.1
147.5°	1082.5	1082.2	1083.9	1087.3	1090.7	1094.1	1097.5	1098.5	1099.5	1100.5	1101.5
150°	1108.2	1107.5	1109.1	1112.3	1115.5	1118.7	1121.9	1123.1	1124.3	1125.6	1126.8
152.5°	1131.8	1131.0	1132.5	1135.5	1138.5	1141.5	1144.5	1145.7	1146.9	1148.2	1149.4
155°	1154.5	1153.6	1154.8	1157.2	1159.6	1162.0	1164.4	1165.6	1166.8	1168.0	1169.2
157.5°	1174.3	1173.5	1174.4	1176.2	1178.0	1179.8	1181.6	1183.0	1184.4	1185.8	1187.2
160°	1192.1	1191.5	1192.1	1193.3	1194.6	1195.8	1197.0	1198.2	1199.4	1200.6	1201.8
162.5°	1206.6	1206.0	1206.5	1207.5	1208.5	1209.5	1210.5	1211.9	1213.3	1214.8	1216.2
165°	1219.3	1218.7	1219.0	1219.6	1220.2	1220.8	1221.4	1222.8	1224.2	1225.6	1227.0
167.5°	1229.2	1228.6	1228.9	1229.5	1230.1	1230.7	1231.3	1232.7	1234.1	1235.5	1236.9
170°	1237.3	1236.7	1236.9	1237.3	1237.8	1238.2	1238.6	1240.0	1241.4	1242.8	1244.2
172.5°	1242.8	1242.2	1242.4	1242.8	1243.2	1243.6	1244.0	1245.4	1246.8	1248.2	1249.6
175°	1246.5	1245.8	1246.0	1246.4	1246.8	1247.2	1247.6	1249.0	1250.4	1251.8	1253.2
177.5°	1248.3	1247.6	1247.7	1247.9	1248.1	1248.3	1248.5	1249.9	1251.3	1252.7	1254.1
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0
2.5°	1816.2	1813.6	1805.7	1808.3	1804.4	1804.4	1801.7	1801.7	1801.7	1808.3	1804.4
5°	1717.3	1708.1	1698.8	1694.9	1690.9	1687.0	1687.0	1685.7	1697.5	1694.9	1705.4
7.5°	1594.6	1592.0	1573.5	1573.5	1566.9	1564.3	1570.9	1572.2	1573.5	1576.2	1582.8
10°	1485.2	1478.6	1452.2	1454.8	1450.9	1445.6	1449.6	1446.9	1456.2	1458.8	1456.2
12.5°	1355.9	1344.0	1315.0	1300.5	1284.7	1272.8	1287.3	1276.8	1313.7	1324.3	1353.3
15°	1184.4	1162.0	1142.2	1142.2	1127.7	1117.2	1123.8	1135.6	1143.6	1155.4	1160.7
17.5°	1069.7	1060.5	1044.6	1035.4	1031.4	1027.5	1027.5	1032.8	1049.9	1048.6	1059.1
20°	972.1	966.8	958.9	947.0	943.1	940.4	940.4	940.4	952.3	962.9	969.5
22.5°	904.8	900.9	895.6	879.8	871.8	869.2	875.8	879.8	889.0	896.9	903.5
25°	837.6	828.3	819.1	813.8	809.9	809.9	812.5	813.8	817.8	821.7	829.6
27.5°	782.2	775.6	762.4	747.9	747.9	743.9	746.5	749.2	758.4	771.6	778.2
30°	720.2	718.8	713.6	708.3	703.0	700.4	705.7	709.6	710.9	717.5	717.5
32.5°	675.3	666.1	656.9	651.6	648.9	647.6	648.9	654.2	654.2	662.1	671.4
35°	630.5	625.2	616.0	606.7	604.1	597.5	602.8	608.0	617.3	621.2	625.2
37.5°	581.7	575.1	571.1	568.5	563.2	564.5	560.6	568.5	576.4	575.1	577.7
40°	544.7	532.9	521.0	519.7	518.4	517.0	517.0	518.4	523.6	528.9	536.8
42.5°	497.3	493.3	482.7	472.2	469.6	466.9	464.3	469.6	480.1	489.3	493.3
45°	448.5	443.2	440.5	432.6	427.3	426.0	423.4	430.0	439.2	443.2	445.8
47.5°	403.6	402.3	394.4	395.7	391.7	393.1	391.7	395.7	395.7	399.7	402.3
50°	373.3	369.3	365.4	362.7	358.8	358.8	357.4	358.8	364.0	369.3	368.0
52.5°	342.9	336.3	335.0	333.7	331.1	333.7	329.7	331.1	336.3	339.0	337.7
55°	307.3	306.0	303.4	300.7	299.4	298.1	298.1	298.1	303.4	307.3	308.6
57.5°	279.6	273.0	267.8	267.8	262.5	261.2	263.8	265.1	269.1	271.7	274.3
60°	241.4	238.7	230.8	226.9	219.0	217.6	217.6	222.9	229.5	238.7	241.4
62.5°	200.5	196.5	195.2	195.2	195.2	195.2	195.2	195.2	195.2	196.5	196.5
65°	178.1	179.4	178.1	176.7	178.1	178.1	176.7	176.7	176.7	178.1	179.4
67.5°	159.6	158.3	159.6	158.3	157.0	157.0	155.6	157.0	158.3	159.6	159.6
70°	138.5	138.5	137.2	138.5	137.2	135.9	134.5	134.5	137.2	138.5	138.5
72.5°	118.7	118.7	117.4	117.4	114.8	114.8	116.1	114.8	114.8	118.7	118.7
75°	98.9	97.6	96.3	96.3	95.0	95.0	95.0	93.6	96.3	96.3	97.6
77.5°	77.8	77.8	77.8	76.5	76.5	75.2	75.2	76.5	76.5	76.5	77.8
80°	59.4	59.4	59.4	58.0	56.7	56.7	56.7	56.7	56.7	58.0	56.7
82.5°	40.9	40.9	40.9	40.9	40.9	39.6	39.6	39.6	40.9	40.9	39.6
85°	25.1	23.7	25.1	25.1	23.7	25.1	23.7	23.7	22.4	22.4	23.7
87.5°	10.6	9.2	7.9	7.9	9.2	7.9	7.9	7.9	9.2	7.9	7.9
90°	22.6	22.8	23.2	23.6	24.0	24.4	24.0	23.6	23.2	22.8	22.6
92.5°	23.5	23.6	23.8	24.0	24.2	24.4	24.2	24.0	23.8	23.6	23.5
95°	39.8	39.7	39.5	39.3	39.1	38.9	39.1	39.3	39.5	39.7	39.8
97.5°	48.8	48.9	49.1	49.3	49.5	49.7	49.5	49.3	49.1	48.9	48.8
100°	58.8	59.0	59.4	59.8	60.2	60.6	60.2	59.8	59.4	59.0	58.8
102.5°	63.3	63.6	64.2	64.8	65.4	66.0	65.4	64.8	64.2	63.6	63.3
105°	65.1	65.5	66.3	67.1	67.9	68.7	67.9	67.1	66.3	65.5	65.1
107.5°	66.9	67.3	68.1	68.9	69.7	70.5	69.7	68.9	68.1	67.3	66.9
110°	67.8	68.2	69.0	69.8	70.6	71.4	70.6	69.8	69.0	68.2	67.8

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	69.6	69.9	70.5	71.1	71.7	72.3	71.7	71.1	70.5	69.9	69.6
115°	139.2	132.0	117.5	103.0	88.6	74.1	88.6	103.0	117.5	132.0	139.2
117.5°	477.3	451.0	398.4	345.7	293.1	240.5	293.1	345.7	398.4	451.0	477.3
120°	673.5	659.9	632.8	605.7	578.6	551.5	578.6	605.7	632.8	659.9	673.5
122.5°	721.4	721.5	721.7	721.9	722.1	722.3	722.1	721.9	721.7	721.5	721.4
125°	770.3	770.6	771.2	771.8	772.4	773.0	772.4	771.8	771.2	770.6	770.3
127.5°	817.3	817.4	817.6	817.8	818.0	818.2	818.0	817.8	817.6	817.4	817.3
130°	860.7	860.6	860.4	860.2	860.0	859.8	860.0	860.2	860.4	860.6	860.7
132.5°	901.3	901.2	901.0	900.8	900.6	900.4	900.6	900.8	901.0	901.2	901.3
135°	941.1	940.9	940.5	940.1	939.7	939.3	939.7	940.1	940.5	940.9	941.1
137.5°	978.2	977.9	977.3	976.7	976.1	975.5	976.1	976.7	977.3	977.9	978.2
140°	1013.4	1012.9	1011.9	1010.9	1009.9	1008.9	1009.9	1010.9	1011.9	1012.9	1013.4
142.5°	1046.0	1045.5	1044.5	1043.5	1042.5	1041.5	1042.5	1043.5	1044.5	1045.5	1046.0
145°	1075.8	1075.3	1074.3	1073.3	1072.3	1071.3	1072.3	1073.3	1074.3	1075.3	1075.8
147.5°	1102.0	1101.6	1100.8	1100.0	1099.2	1098.4	1099.2	1100.0	1100.8	1101.6	1102.0
150°	1127.4	1126.9	1125.9	1124.8	1123.8	1122.8	1123.8	1124.8	1125.9	1126.9	1127.4
152.5°	1150.0	1149.3	1147.9	1146.4	1145.0	1143.6	1145.0	1146.4	1147.9	1149.3	1150.0
155°	1169.8	1169.0	1167.4	1165.8	1164.2	1162.6	1164.2	1165.8	1167.4	1169.0	1169.8
157.5°	1187.9	1187.1	1185.5	1183.9	1182.3	1180.7	1182.3	1183.9	1185.5	1187.1	1187.9
160°	1202.4	1201.7	1200.3	1198.9	1197.5	1196.1	1197.5	1198.9	1200.3	1201.7	1202.4
162.5°	1216.9	1216.0	1214.2	1212.3	1210.5	1208.7	1210.5	1212.3	1214.2	1216.0	1216.9
165°	1227.7	1227.0	1225.6	1224.2	1222.8	1221.4	1222.8	1224.2	1225.6	1227.0	1227.7
167.5°	1237.6	1236.7	1234.9	1233.1	1231.3	1229.5	1231.3	1233.1	1234.9	1236.7	1237.6
170°	1244.9	1244.0	1242.2	1240.3	1238.5	1236.7	1238.5	1240.3	1242.2	1244.0	1244.9
172.5°	1250.3	1249.4	1247.6	1245.8	1244.0	1242.2	1244.0	1245.8	1247.6	1249.4	1250.3
175°	1253.9	1252.9	1250.9	1248.9	1246.9	1244.9	1246.9	1248.9	1250.9	1252.9	1253.9
177.5°	1254.8	1253.9	1252.1	1250.3	1248.5	1246.7	1248.5	1250.3	1252.1	1253.9	1254.8
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0	1898.0
2.5°	1808.3	1814.9	1812.3	1797.8	1812.3	1816.2	1824.1	1832.1	1837.3	1845.3	1851.8
5°	1694.9	1708.1	1716.0	1708.1	1734.5	1738.4	1756.9	1767.4	1783.3	1796.5	1807.0
7.5°	1588.1	1598.6	1614.4	1617.1	1632.9	1651.4	1677.7	1704.1	1729.2	1742.4	1754.2
10°	1473.3	1491.8	1515.5	1510.2	1534.0	1563.0	1590.7	1632.9	1654.0	1677.7	1698.8
12.5°	1358.5	1370.4	1402.1	1412.6	1446.9	1469.3	1507.6	1534.0	1586.7	1614.4	1632.9
15°	1158.1	1206.9	1246.4	1293.9	1338.8	1381.0	1415.3	1462.7	1508.9	1530.0	1560.4
17.5°	1067.1	1089.5	1113.2	1137.0	1195.0	1270.2	1330.9	1382.3	1421.9	1449.6	1485.2
20°	972.1	994.5	1020.9	1043.3	1078.9	1133.0	1208.2	1296.6	1344.0	1373.1	1407.4
22.5°	904.8	925.9	943.1	962.9	990.6	1030.1	1086.8	1196.3	1259.6	1295.2	1325.6
25°	832.3	858.7	877.1	891.6	914.1	957.6	1003.7	1065.7	1179.2	1206.9	1249.1
27.5°	782.2	790.1	811.2	833.6	856.0	879.8	927.2	980.0	1056.5	1117.2	1168.6
30°	722.8	742.6	762.4	771.6	791.4	825.7	854.7	911.4	970.8	1018.3	1080.2
32.5°	678.0	689.8	703.0	725.4	743.9	767.6	796.7	844.1	894.3	924.6	972.1
35°	627.8	635.7	663.4	672.7	691.1	714.9	743.9	780.8	834.9	858.7	892.9
37.5°	580.4	598.8	606.7	627.8	645.0	668.7	689.8	732.0	767.6	795.3	827.0
40°	543.4	551.3	565.8	584.3	598.8	617.3	643.7	674.0	712.2	734.7	762.4
42.5°	498.6	505.2	523.6	534.2	557.9	575.1	590.9	627.8	662.1	679.3	707.0
45°	449.8	465.6	477.5	498.6	511.8	532.9	552.7	579.0	610.7	630.5	646.3
47.5°	407.6	423.4	435.3	455.0	476.2	485.4	506.5	534.2	563.2	579.0	601.5
50°	373.3	378.5	401.0	410.2	432.6	451.1	465.6	489.3	521.0	530.2	548.7
52.5°	340.3	344.3	358.8	370.6	390.4	406.2	424.7	447.1	473.5	488.0	502.5
55°	311.3	313.9	320.5	333.7	346.9	366.7	383.8	404.9	427.3	443.2	456.4
57.5°	278.3	283.6	288.9	296.8	310.0	328.4	346.9	366.7	385.1	395.7	412.8
60°	240.1	248.0	257.2	266.4	275.7	288.9	310.0	328.4	345.6	354.8	368.0
62.5°	199.2	215.0	222.9	233.5	241.4	253.2	269.1	290.2	302.0	313.9	324.5
65°	179.4	180.7	182.0	192.6	207.1	219.0	233.5	249.3	267.8	275.7	283.6
67.5°	159.6	160.9	163.6	164.9	170.1	183.3	199.2	216.3	230.8	236.1	244.0
70°	139.8	139.8	145.1	146.4	147.7	149.0	162.2	179.4	192.6	199.2	208.4
72.5°	118.7	120.0	122.7	124.0	126.6	129.3	133.2	142.4	158.3	164.9	175.4
75°	97.6	98.9	100.2	101.6	105.5	106.8	110.8	116.1	122.7	130.6	137.2
77.5°	77.8	77.8	79.1	81.8	84.4	85.7	89.7	92.3	95.0	98.9	104.2
80°	58.0	59.4	59.4	62.0	62.0	63.3	64.6	68.6	71.2	73.9	76.5
82.5°	39.6	42.2	42.2	42.2	43.5	44.8	46.2	46.2	48.8	50.1	54.1
85°	23.7	25.1	25.1	25.1	23.7	26.4	26.4	27.7	27.7	27.7	29.0
87.5°	9.2	7.9	9.2	9.2	9.2	10.6	9.2	9.2	10.6	11.9	11.9
90°	22.1	21.1	20.1	19.1	18.1	16.5	14.9	13.2	11.6	10.8	9.7
92.5°	23.3	22.9	22.5	22.1	21.7	21.1	20.5	19.9	19.3	19.0	19.4
95°	39.3	38.3	37.3	36.3	35.3	33.9	32.5	31.0	29.6	28.9	32.2
97.5°	48.5	47.9	47.3	46.7	46.1	42.9	39.7	36.4	33.2	31.6	39.8
100°	58.0	56.4	54.7	53.1	51.5	48.1	44.7	41.3	37.9	36.2	50.0
102.5°	62.2	60.0	57.7	55.5	53.3	89.9	126.5	163.0	199.6	217.9	218.1
105°	64.0	61.8	59.5	57.3	55.1	110.0	164.8	219.7	274.6	302.0	299.0
107.5°	65.8	63.6	61.4	59.2	57.0	124.7	192.4	260.1	327.8	361.6	359.1
110°	77.8	97.9	118.0	138.1	158.2	216.3	274.3	332.4	390.5	419.5	417.4

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	112.9	199.5	286.1	372.7	459.3	462.7	466.1	469.5	472.9	474.6	472.8
115°	185.7	278.7	371.8	464.8	557.8	552.8	547.8	542.7	537.7	535.2	533.5
117.5°	491.7	520.4	549.1	577.9	606.6	603.2	599.8	596.3	592.9	591.2	589.2
120°	672.3	669.9	667.5	665.1	662.7	659.1	655.5	651.8	648.2	646.4	644.9
122.5°	720.8	719.6	718.4	717.2	716.0	712.0	708.0	703.9	699.9	697.9	696.3
125°	769.6	768.2	766.7	765.3	763.9	760.1	756.3	752.4	748.6	746.7	745.4
127.5°	816.3	814.3	812.2	810.2	808.2	805.2	802.2	799.2	796.2	794.7	793.3
130°	859.6	857.4	855.1	852.9	850.7	848.5	846.3	844.1	841.9	840.8	839.2
132.5°	900.4	898.6	896.8	895.0	893.2	891.0	888.8	886.6	884.4	883.3	882.0
135°	940.1	938.1	936.1	934.1	932.1	930.3	928.5	926.6	924.8	923.9	922.3
137.5°	977.2	975.2	973.1	971.1	969.1	967.1	965.1	963.1	961.1	960.1	958.9
140°	1012.5	1010.7	1008.9	1007.1	1005.3	1003.1	1000.9	998.7	996.5	995.4	994.6
142.5°	1045.2	1043.6	1042.0	1040.4	1038.8	1036.2	1033.6	1030.9	1028.3	1027.0	1026.3
145°	1075.1	1073.7	1072.3	1070.9	1069.5	1066.1	1062.7	1059.2	1055.8	1054.1	1054.2
147.5°	1101.5	1100.5	1099.5	1098.5	1097.5	1094.1	1090.7	1087.3	1083.9	1082.2	1082.5
150°	1126.8	1125.6	1124.3	1123.1	1121.9	1118.7	1115.5	1112.3	1109.1	1107.5	1108.2
152.5°	1149.4	1148.2	1146.9	1145.7	1144.5	1141.5	1138.5	1135.5	1132.5	1131.0	1131.8
155°	1169.2	1168.0	1166.8	1165.6	1164.4	1162.0	1159.6	1157.2	1154.8	1153.6	1154.5
157.5°	1187.2	1185.8	1184.4	1183.0	1181.6	1179.8	1178.0	1176.2	1174.4	1173.5	1174.3
160°	1201.8	1200.6	1199.4	1198.2	1197.0	1195.8	1194.6	1193.3	1192.1	1191.5	1192.1
162.5°	1216.2	1214.8	1213.3	1211.9	1210.5	1209.5	1208.5	1207.5	1206.5	1206.0	1206.6
165°	1227.0	1225.6	1224.2	1222.8	1221.4	1220.8	1220.2	1219.6	1219.0	1218.7	1219.3
167.5°	1236.9	1235.5	1234.1	1232.7	1231.3	1230.7	1230.1	1229.5	1228.9	1228.6	1229.2
170°	1244.2	1242.8	1241.4	1240.0	1238.6	1238.2	1237.8	1237.3	1236.9	1236.7	1237.3
172.5°	1249.6	1248.2	1246.8	1245.4	1244.0	1243.6	1243.2	1242.8	1242.4	1242.2	1242.8
175°	1253.2	1251.8	1250.4	1249.0	1247.6	1247.2	1246.8	1246.4	1246.0	1245.8	1246.5
177.5°	1254.1	1252.7	1251.3	1249.9	1248.5	1248.3	1248.1	1247.9	1247.7	1247.6	1248.3
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1898.0	1898.0	1898.0	1898.0
2.5°	1863.7	1859.8	1883.5	1909.9
5°	1825.5	1832.1	1862.4	1899.3
7.5°	1785.9	1800.4	1836.0	1884.8
10°	1730.5	1756.9	1811.0	1861.1
12.5°	1676.4	1712.0	1763.5	1822.8
15°	1615.8	1655.3	1718.6	1789.9
17.5°	1548.5	1593.3	1667.2	1745.0
20°	1477.3	1536.6	1614.4	1698.8
22.5°	1398.1	1469.3	1549.8	1643.4
25°	1321.6	1399.4	1479.9	1588.1
27.5°	1246.4	1322.9	1412.6	1522.1
30°	1171.3	1241.2	1337.4	1454.8
32.5°	1090.8	1163.3	1264.9	1384.9
35°	1016.9	1089.5	1184.4	1303.2
37.5°	937.8	1015.6	1106.6	1229.3
40°	845.5	936.5	1024.8	1142.2
42.5°	769.0	865.3	951.0	1061.8
45°	708.3	799.3	870.5	978.7
47.5°	651.6	725.4	798.0	898.2
50°	597.5	654.2	729.4	819.1
52.5°	542.1	590.9	655.5	739.9
55°	492.0	538.1	596.2	660.8
57.5°	445.8	478.8	536.8	594.9
60°	394.4	428.7	473.5	522.3
62.5°	350.8	377.2	419.4	460.3
65°	304.7	329.7	361.4	399.7
67.5°	262.5	284.9	310.0	340.3
70°	224.2	241.4	259.8	286.2
72.5°	183.3	201.8	219.0	240.1
75°	150.4	158.3	172.8	187.3
77.5°	116.1	126.6	134.5	146.4
80°	83.1	92.3	95.0	104.2
82.5°	55.4	60.7	65.9	68.6
85°	31.7	34.3	39.6	40.9
87.5°	11.9	13.2	15.8	18.5
90°	7.5	5.3	3.1	0.9
92.5°	20.2	21.0	21.8	22.6
95°	38.9	45.5	52.2	58.8
97.5°	56.3	72.8	89.3	105.8
100°	77.5	105.0	132.5	160.0
102.5°	218.5	218.9	219.3	219.7
105°	292.9	286.9	280.8	274.8
107.5°	354.1	349.0	344.0	339.0
110°	413.2	408.9	404.7	400.5



TEST NUMBER: P1000226

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	469.2	465.6	462.0	458.4
115°	530.1	526.6	523.2	519.8
117.5°	585.2	581.2	577.2	573.2
120°	641.9	638.8	635.8	632.8
122.5°	693.1	689.9	686.7	683.5
125°	742.8	740.2	737.6	735.0
127.5°	790.5	787.6	784.8	782.0
130°	836.0	832.7	829.5	826.3
132.5°	879.4	876.7	874.1	871.5
135°	919.1	915.9	912.7	909.5
137.5°	956.5	954.1	951.7	949.3
140°	993.0	991.3	989.7	988.1
142.5°	1024.9	1023.5	1022.1	1020.7
145°	1054.4	1054.6	1054.8	1055.0
147.5°	1083.1	1083.7	1084.3	1084.9
150°	1109.6	1111.0	1112.4	1113.8
152.5°	1133.4	1135.0	1136.6	1138.2
155°	1156.3	1158.1	1159.9	1161.7
157.5°	1175.9	1177.5	1179.1	1180.7
160°	1193.3	1194.6	1195.8	1197.0
162.5°	1207.8	1209.0	1210.2	1211.4
165°	1220.5	1221.7	1222.9	1224.1
167.5°	1230.4	1231.6	1232.8	1234.0
170°	1238.5	1239.8	1241.0	1242.2
172.5°	1244.0	1245.2	1246.4	1247.6
175°	1247.9	1249.3	1250.7	1252.1
177.5°	1249.7	1251.1	1252.5	1253.9
180°	1249.4	1249.4	1249.4	1249.4

(END OF REPORT)