

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000231

Luminaire Tested: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000231
REPORT IS A COMBINATION OF REPORTS P988791 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6663.0 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000231

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000231

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52			45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44			39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38			33
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33			29
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29			25
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25			22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22			20
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20			17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18			16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16			14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23074	23074	23074
5°	23112	21953	21790
10°	22884	20821	20133
15°	22570	19484	18246
20°	22154	17965	16272
25°	21727	16405	14465
30°	21155	14887	12491
35°	20594	13356	10797
40°	20025	11853	9052
45°	19361	10300	7531
50°	18676	8803	6131
55°	17962	7306	4867
60°	17133	5843	3682
65°	16179	4454	2993
70°	15028	3231	2381
75°	13577	2464	1818
80°	11481	1668	1219
85°	8009	765	590

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19361 cd/sqm

TEST NUMBER: P1000231

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.6	2.1
10°-20°	375.1	5.6
20°-30°	526.6	7.9
30°-40°	574.0	8.6
40°-50°	527.5	7.9
50°-60°	414.3	6.2
60°-70°	269.7	4.0
70°-80°	138.8	2.1
80°-90°	37.7	0.6
90°-100°	41.2	0.6
100°-110°	153.6	2.3
110°-120°	407.3	6.1
120°-130°	675.6	10.1
130°-140°	717.6	10.8
140°-150°	666.9	10.0
150°-160°	536.2	8.0
160°-170°	345.5	5.2
170°-180°	118.9	1.8
0°-30°	1038.2	15.6
0°-40°	1612.2	24.2
0°-60°	2554.0	38.3
0°-90°	3000.2	45.0
90°-120°	602.1	9.0
90°-150°	2662.2	40.0
90°-180°	3663.0	55.0
0°-180°	6663.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1458	1451	1434	1446	1442	138
15°	1386	1372	1327	1302	1289	391
25°	1258	1216	1129	1075	1055	579
35°	1084	1017	901	818	789	679
45°	886	798	660	566	534	685
55°	674	571	429	350	324	602
65°	455	348	230	185	181	451
75°	243	150	106	96	95	257
85°	57	29	25	25	25	65
90°	1	11	18	23	24	6
95°	59	29	35	40	39	70
105°	275	302	55	65	69	294
115°	520	535	558	139	74	512
125°	735	747	764	770	773	656
135°	910	924	932	941	939	703
145°	1055	1054	1070	1076	1071	660
155°	1162	1154	1164	1170	1163	535
165°	1224	1219	1221	1228	1221	346
175°	1252	1246	1248	1254	1245	119
180°	1249	1249	1249	1249	1249	

TEST NUMBER: P1000231

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1464.3	1457.7	1443.2	1456.4	1453.8
5°	1457.7	1451.1	1434.0	1445.9	1441.9
7.5°	1445.9	1437.9	1419.5	1424.7	1418.1
10°	1430.0	1420.8	1394.4	1390.4	1382.5
12.5°	1410.2	1398.4	1362.7	1354.8	1340.3
15°	1386.5	1372.0	1327.1	1302.1	1288.9
17.5°	1358.8	1337.7	1282.3	1253.2	1232.1
20°	1327.1	1300.7	1234.8	1201.8	1172.8
22.5°	1292.8	1262.5	1186.0	1141.1	1121.3
25°	1258.5	1216.3	1129.2	1075.2	1055.4
27.5°	1217.6	1172.8	1076.5	1014.5	984.1
30°	1174.1	1124.0	1018.4	951.1	915.5
32.5°	1131.9	1071.2	963.0	883.9	850.9
35°	1084.4	1017.1	901.0	817.9	788.9
37.5°	1038.2	965.7	843.0	751.9	719.0
40°	989.4	910.3	782.3	688.6	654.3
42.5°	939.3	854.8	721.6	624.0	591.0
45°	886.5	798.1	659.6	565.9	534.3
47.5°	836.4	742.7	600.2	506.6	477.6
50°	781.0	687.3	542.2	451.2	423.5
52.5°	726.9	627.9	486.8	399.7	374.7
55°	674.1	571.2	428.7	349.6	324.5
57.5°	620.0	514.5	377.3	303.4	282.3
60°	564.6	459.1	323.2	255.9	234.8
62.5°	510.5	405.0	277.0	213.7	203.2
65°	455.1	348.3	229.5	184.7	180.7
67.5°	402.4	295.5	184.7	162.3	158.3
70°	347.0	244.1	153.0	139.8	134.6
72.5°	294.2	196.6	128.0	117.4	114.8
75°	242.7	150.4	105.5	96.3	95.0
77.5°	191.3	106.9	83.1	77.8	75.2
80°	143.8	76.5	63.3	58.0	58.0
82.5°	100.3	51.4	43.5	40.9	40.9
85°	56.7	29.0	25.1	25.1	25.1
87.5°	21.1	10.6	10.6	9.2	9.2
90°	0.9	10.8	18.1	22.6	24.4
92.5°	22.6	19.0	21.7	23.5	24.4
95°	58.8	28.9	35.3	39.8	38.9
97.5°	105.8	31.6	46.1	48.8	49.7
100°	160.0	36.2	51.5	58.8	60.6
102.5°	219.7	217.9	53.3	63.3	66.0
105°	274.8	302.0	55.1	65.1	68.7
107.5°	339.0	361.6	57.0	66.9	70.5
110°	400.5	419.5	158.2	67.8	71.4

TEST NUMBER: P1000231

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	458.4	474.6	459.3	69.6	72.3
115°	519.8	535.2	557.8	139.2	74.1
117.5°	573.2	591.2	606.6	477.3	240.5
120°	632.8	646.4	662.7	673.5	551.5
122.5°	683.5	697.9	716.0	721.4	722.3
125°	735.0	746.7	763.9	770.3	773.0
127.5°	782.0	794.7	808.2	817.3	818.2
130°	826.3	840.8	850.7	860.7	859.8
132.5°	871.5	883.3	893.2	901.3	900.4
135°	909.5	923.9	932.1	941.1	939.3
137.5°	949.3	960.1	969.1	978.2	975.5
140°	988.1	995.4	1005.3	1013.4	1008.9
142.5°	1020.7	1027.0	1038.8	1046.0	1041.5
145°	1055.0	1054.1	1069.5	1075.8	1071.3
147.5°	1084.9	1082.2	1097.5	1102.0	1098.4
150°	1113.8	1107.5	1121.9	1127.4	1122.8
152.5°	1138.2	1131.0	1144.5	1150.0	1143.6
155°	1161.7	1153.6	1164.4	1169.8	1162.6
157.5°	1180.7	1173.5	1181.6	1187.9	1180.7
160°	1197.0	1191.5	1197.0	1202.4	1196.1
162.5°	1211.4	1206.0	1210.5	1216.9	1208.7
165°	1224.1	1218.7	1221.4	1227.7	1221.4
167.5°	1234.0	1228.6	1231.3	1237.6	1229.5
170°	1242.2	1236.7	1238.6	1244.9	1236.7
172.5°	1247.6	1242.2	1244.0	1250.3	1242.2
175°	1252.1	1245.8	1247.6	1253.9	1244.9
177.5°	1253.9	1247.6	1248.5	1254.8	1246.7
180°	1249.4	1249.4	1249.4	1249.4	1249.4

(END OF REPORT)