

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998904

Luminaire Tested: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998904
REPORT IS A COMBINATION OF REPORTS P984650 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5266.0 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	52	51
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	60	55	51	51	47	44	43	40	38
4	76	66	58	52	71	61	55	49	53	48	44	46	42	39	39	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	38	43	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20318	20318	20318	20318
5°	20367	21665	20445	17235
10°	20130	23650	20257	14211
15°	19642	24945	19915	11969
20°	19336	23422	19336	10403
25°	18720	20122	18804	9304
30°	17706	15818	18043	8427
35°	16808	10938	17089	7711
40°	15774	8258	15954	7139
45°	14502	6787	14738	6522
50°	13401	5956	13425	5970
55°	12145	5075	12225	5371
60°	10809	4239	10957	4687
65°	9609	3448	9787	4003
70°	8419	2705	8631	3229
75°	7065	1964	7339	2341
80°	5517	1245	5908	1390
85°	3630	626	3899	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21003 cd/sqm

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	2.3
10°-20°	355.8	6.8
20°-30°	516.4	9.8
30°-40°	544.4	10.3
40°-50°	481.8	9.1
50°-60°	384.7	7.3
60°-70°	261.3	5.0
70°-80°	133.7	2.5
80°-90°	34.1	0.6
90°-100°	53.8	1.0
100°-110°	171.0	3.2
110°-120°	292.7	5.6
120°-130°	384.9	7.3
130°-140°	432.0	8.2
140°-150°	423.7	8.0
150°-160°	355.4	6.7
160°-170°	235.7	4.5
170°-180°	82.4	1.6
0°-30°	994.6	18.9
0°-40°	1539.0	29.2
0°-60°	2405.4	45.7
0°-90°	2834.5	53.8
90°-120°	517.5	9.8
90°-150°	1758.1	33.4
90°-180°	2432.0	46.2
0°-180°	5266.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1285	1434	1290	1140	1285	122
15°	1207	1762	1223	846	1207	341
25°	1084	1468	1089	679	1084	496
35°	885	799	900	563	885	554
45°	664	482	675	463	664	515
55°	456	338	459	358	456	407
65°	270	208	275	242	270	269
75°	126	103	131	122	126	136
85°	26	27	28	20	26	30
90°	1	25	1	25	1	4
95°	38	46	38	46	38	43
105°	158	163	158	163	158	167
115°	294	294	294	294	294	290
125°	427	429	427	429	427	382
135°	553	559	553	559	553	427
145°	671	678	671	678	671	419
155°	767	773	767	773	767	353
165°	834	835	834	835	834	235
175°	868	865	868	865	868	82
180°	870	870	870	870	870	

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1290.5	1293.5	1298.4	1299.4	1309.2	1317.1	1326.0	1326.0	1329.0	1328.0	1320.1
5°	1284.6	1293.5	1306.3	1317.1	1334.9	1342.8	1354.6	1363.5	1371.4	1377.3	1376.3
7.5°	1274.7	1290.5	1309.2	1330.0	1353.6	1367.5	1384.2	1400.0	1410.9	1420.7	1427.6
10°	1257.9	1284.6	1310.2	1337.9	1368.4	1387.2	1406.9	1427.6	1444.4	1463.2	1480.9
12.5°	1235.2	1273.7	1305.3	1341.8	1379.3	1400.0	1431.6	1447.4	1479.9	1527.3	1540.1
15°	1206.6	1258.9	1288.5	1334.9	1384.2	1401.0	1444.4	1470.1	1537.2	1566.8	1602.3
17.5°	1180.0	1238.2	1277.7	1331.0	1379.3	1411.9	1454.3	1506.6	1562.8	1605.2	1644.7
20°	1158.3	1214.5	1261.9	1321.1	1382.3	1423.7	1468.1	1531.2	1592.4	1635.8	1666.4
22.5°	1109.0	1181.0	1236.2	1302.3	1376.3	1433.6	1476.0	1545.0	1611.2	1637.8	1664.4
25°	1084.3	1146.5	1210.6	1285.6	1372.4	1440.5	1477.0	1553.9	1612.1	1622.0	1627.9
27.5°	1038.9	1109.0	1183.9	1269.8	1371.4	1428.6	1475.0	1545.0	1591.4	1584.5	1566.8
30°	982.7	1068.5	1151.4	1244.1	1357.6	1419.7	1463.2	1527.3	1551.0	1515.5	1483.9
32.5°	941.2	1022.1	1113.9	1221.4	1341.8	1401.0	1443.4	1493.7	1498.7	1434.5	1381.3
35°	885.0	974.8	1078.4	1191.8	1315.2	1368.4	1407.9	1438.5	1414.8	1325.0	1261.9
37.5°	834.7	923.5	1034.0	1149.4	1278.7	1331.0	1362.5	1367.5	1309.2	1230.3	1137.6
40°	779.4	871.2	986.6	1108.0	1238.2	1283.6	1303.3	1288.5	1204.7	1112.9	1005.4
42.5°	724.2	814.9	939.3	1063.6	1186.9	1225.4	1233.3	1192.8	1090.2	982.7	858.4
45°	664.0	758.7	883.0	1008.3	1127.7	1149.4	1150.4	1092.2	970.8	858.4	742.9
47.5°	614.7	702.5	825.8	951.1	1051.7	1066.5	1060.6	993.5	861.3	735.0	634.4
50°	560.4	644.3	766.6	889.9	975.8	979.7	964.9	869.2	740.0	624.5	544.6
52.5°	502.2	587.0	699.5	817.9	894.9	888.9	860.3	757.7	636.4	540.7	479.5
55°	455.8	530.8	636.4	751.8	806.1	789.3	757.7	653.1	557.4	476.5	423.3
57.5°	404.5	470.6	574.2	674.8	706.4	690.6	659.1	561.4	472.6	411.4	375.9
60°	356.2	416.4	507.1	591.0	615.7	598.9	562.4	474.6	410.4	359.1	332.5
62.5°	311.8	364.1	440.0	517.0	526.9	510.1	478.5	407.5	352.2	311.8	292.0
65°	270.3	319.7	380.8	439.0	447.9	430.2	397.6	346.3	299.9	274.3	255.5
67.5°	229.9	269.3	323.6	366.0	371.0	354.2	327.6	286.1	257.5	229.9	216.1
70°	194.4	224.0	266.4	300.9	302.9	287.1	273.3	235.8	214.1	194.4	183.5
72.5°	159.8	180.6	213.1	238.8	239.7	229.9	217.1	193.4	174.6	160.8	150.0
75°	126.3	144.0	163.8	186.5	185.5	177.6	167.7	152.9	137.1	128.3	123.3
77.5°	96.7	107.5	123.3	138.1	138.1	134.2	128.3	117.4	107.5	98.7	93.7
80°	69.1	76.0	88.8	93.7	95.7	94.7	89.8	81.9	77.9	71.0	69.1
82.5°	44.4	49.3	55.3	60.2	63.1	61.2	60.2	56.2	50.3	48.3	46.4
85°	25.7	27.6	30.6	33.5	34.5	33.5	35.5	32.6	29.6	29.6	28.6
87.5°	10.9	11.8	13.8	13.8	14.8	14.8	13.8	14.8	14.8	13.8	12.8
90°	0.7	2.7	4.6	6.6	8.5	9.5	11.3	14.9	18.5	22.1	25.7
92.5°	16.1	17.4	18.7	20.0	21.3	22.0	22.1	22.3	22.4	22.6	22.8
95°	38.2	39.8	41.4	43.1	44.7	45.5	45.7	46.0	46.3	46.7	47.0
97.5°	63.9	65.4	66.8	68.3	69.8	70.5	70.8	71.5	72.1	72.8	73.4
100°	93.2	94.5	95.8	97.1	98.4	99.1	99.3	99.8	100.3	100.8	101.3
102.5°	124.0	125.0	126.0	126.9	127.9	128.4	128.7	129.4	130.1	130.7	131.4
105°	157.8	158.3	158.8	159.3	159.8	160.0	160.2	160.5	160.8	161.2	161.5
107.5°	191.6	192.2	192.9	193.5	194.2	194.5	194.5	194.5	194.5	194.5	194.5
110°	223.8	224.8	225.8	226.8	227.8	228.3	228.3	228.3	228.3	228.3	228.3

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	259.1	260.1	261.1	262.0	263.0	263.5	263.4	263.2	263.1	262.9	262.7
115°	293.6	294.6	295.6	296.5	297.5	298.0	297.8	297.5	297.2	296.8	296.5
117.5°	328.1	329.4	330.7	332.0	333.3	333.9	333.5	332.7	331.9	331.1	330.3
120°	362.6	363.9	365.2	366.5	367.8	368.4	367.8	366.5	365.2	363.9	362.6
122.5°	394.1	395.7	397.4	399.0	400.7	401.5	401.1	400.3	399.4	398.6	397.8
125°	427.1	428.6	430.1	431.6	433.1	433.8	433.5	433.0	432.5	432.0	431.5
127.5°	459.4	461.2	463.0	464.8	466.6	467.5	467.2	466.5	465.9	465.2	464.6
130°	489.5	491.6	493.8	495.9	498.0	499.1	498.9	498.6	498.3	497.9	497.6
132.5°	523.3	524.9	526.5	528.2	529.8	530.6	530.7	530.9	531.0	531.2	531.4
135°	552.6	554.4	556.2	558.0	559.8	560.7	560.9	561.2	561.5	561.9	562.2
137.5°	584.9	586.4	587.8	589.3	590.8	591.5	591.7	592.0	592.3	592.7	593.0
140°	613.6	615.1	616.5	618.0	619.5	620.2	620.6	621.4	622.2	623.0	623.8
142.5°	642.9	644.4	645.8	647.3	648.8	649.5	649.7	650.2	650.7	651.2	651.7
145°	670.8	671.9	673.1	674.2	675.3	675.9	676.4	677.4	678.4	679.4	680.4
147.5°	695.8	697.3	698.7	700.2	701.7	702.4	702.7	703.4	704.0	704.7	705.3
150°	721.4	722.4	723.4	724.4	725.4	725.9	726.2	726.9	727.5	728.2	728.8
152.5°	744.2	745.2	746.2	747.1	748.1	748.6	749.0	749.8	750.7	751.5	752.3
155°	767.0	767.5	768.0	768.5	769.0	769.2	769.4	769.9	770.4	770.9	771.4
157.5°	786.8	787.1	787.4	787.7	788.0	788.2	788.4	788.7	789.0	789.4	789.7
160°	804.4	804.7	805.1	805.4	805.7	805.9	806.0	806.1	806.3	806.4	806.6
162.5°	820.5	820.5	820.5	820.5	820.5	820.5	820.6	820.8	820.9	821.1	821.3
165°	834.5	834.3	834.1	834.0	833.8	833.7	833.7	833.7	833.7	833.7	833.7
167.5°	847.0	846.5	846.0	845.5	845.0	844.7	844.7	844.7	844.7	844.7	844.7
170°	856.5	856.0	855.5	855.0	854.5	854.3	854.2	854.1	853.9	853.8	853.6
172.5°	863.1	862.6	862.1	861.6	861.1	860.9	860.8	860.7	860.5	860.4	860.2
175°	868.2	867.7	867.2	866.7	866.2	866.0	865.8	865.5	865.2	864.9	864.6
177.5°	871.2	870.7	870.2	869.7	869.2	869.0	868.8	868.5	868.2	867.8	867.5
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1333.9	1334.9	1336.9	1346.7	1351.7	1352.7	1348.7	1357.6	1360.6	1357.6	1355.6
5°	1397.1	1403.0	1414.8	1427.6	1426.7	1427.6	1433.6	1439.5	1441.5	1433.6	1436.5
7.5°	1452.3	1464.1	1477.0	1496.7	1496.7	1506.6	1510.5	1515.5	1527.3	1521.4	1519.4
10°	1515.5	1531.2	1554.9	1586.5	1587.5	1597.3	1607.2	1623.0	1627.9	1624.0	1626.0
12.5°	1594.4	1625.0	1626.9	1661.5	1677.3	1679.2	1695.0	1692.1	1701.9	1701.9	1718.7
15°	1628.9	1676.3	1702.9	1736.5	1746.3	1734.5	1747.3	1761.1	1762.1	1762.1	1761.1
17.5°	1691.1	1709.8	1736.5	1754.2	1758.2	1758.2	1759.1	1765.1	1761.1	1753.2	1759.1
20°	1703.9	1711.8	1721.7	1719.7	1721.7	1711.8	1701.9	1692.1	1693.0	1688.1	1702.9
22.5°	1680.2	1678.2	1655.6	1640.8	1640.8	1621.0	1602.3	1593.4	1584.5	1587.5	1592.4
25°	1621.0	1590.4	1562.8	1541.1	1536.2	1504.6	1478.9	1471.1	1456.3	1468.1	1470.1
27.5°	1526.3	1491.8	1447.4	1428.6	1403.0	1390.1	1372.4	1348.7	1318.1	1335.9	1332.9
30°	1424.7	1373.4	1336.9	1291.5	1251.0	1248.1	1214.5	1175.1	1159.3	1159.3	1168.2
32.5°	1311.2	1243.1	1189.9	1125.7	1086.3	1069.5	1029.0	989.6	998.5	968.9	979.7
35°	1179.0	1089.2	1022.1	960.0	930.4	910.7	858.4	836.7	813.0	799.2	824.8
37.5°	1052.7	949.1	863.3	795.2	784.4	748.8	713.3	699.5	685.7	691.6	690.6
40°	898.8	807.1	730.1	676.8	658.1	641.3	617.6	600.9	592.0	596.9	597.9
42.5°	759.7	682.7	625.5	588.0	572.2	560.4	548.6	534.7	531.8	531.8	535.7
45°	652.2	589.0	550.5	519.9	511.1	502.2	493.3	487.4	485.4	481.5	484.4
47.5°	566.3	516.0	492.3	469.6	459.8	457.8	449.9	446.9	443.0	442.0	443.0
50°	494.3	462.7	441.0	428.2	421.3	418.3	414.4	408.5	406.5	411.4	409.4
52.5°	444.0	414.4	402.5	389.7	385.8	381.8	375.9	376.9	375.9	373.9	373.9
55°	393.7	374.9	363.1	353.2	352.2	348.3	343.3	341.4	340.4	338.4	341.4
57.5°	353.2	338.4	327.6	318.7	314.7	314.7	309.8	305.9	305.9	304.9	305.9
60°	312.8	298.0	291.1	282.2	279.2	278.2	275.3	273.3	270.3	270.3	270.3
62.5°	275.3	263.4	255.5	247.6	248.6	243.7	239.7	237.8	237.8	238.8	238.8
65°	239.7	231.9	222.0	215.1	213.1	212.1	210.2	209.2	206.2	208.2	208.2
67.5°	207.2	196.3	190.4	187.5	184.5	183.5	181.5	179.6	178.6	177.6	179.6
70°	174.6	165.8	160.8	158.8	155.9	154.9	153.9	151.0	151.9	152.9	153.9
72.5°	145.0	137.1	136.2	130.2	130.2	130.2	126.3	128.3	127.3	125.3	127.3
75°	114.4	110.5	108.5	105.6	106.6	105.6	104.6	101.6	101.6	102.6	103.6
77.5°	90.8	86.8	85.8	82.9	80.9	82.9	80.9	79.9	79.9	80.9	80.9
80°	67.1	65.1	62.2	62.2	62.2	61.2	61.2	61.2	60.2	59.2	60.2
82.5°	44.4	44.4	43.4	42.4	43.4	41.4	42.4	42.4	42.4	42.4	42.4
85°	28.6	27.6	27.6	26.6	26.6	26.6	27.6	25.7	25.7	26.6	26.6
87.5°	12.8	12.8	12.8	13.8	12.8	12.8	12.8	13.8	12.8	12.8	12.8
90°	25.4	25.0	24.7	24.4	24.2	24.3	24.5	24.6	24.8	25.0	24.8
92.5°	23.0	23.1	23.3	23.4	23.5	23.5	23.5	23.5	23.5	23.5	23.5
95°	47.0	47.0	47.0	47.0	47.0	46.8	46.5	46.2	45.8	45.5	45.8
97.5°	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4
100°	101.3	101.3	101.3	101.3	101.3	101.2	101.0	100.9	100.7	100.5	100.7
102.5°	131.6	131.7	131.9	132.0	132.1	132.0	131.9	131.7	131.6	131.4	131.6
105°	161.8	162.1	162.4	162.7	162.9	162.9	162.9	162.9	162.9	162.9	162.9
107.5°	194.7	194.8	195.0	195.1	195.2	194.8	194.0	193.2	192.4	191.6	192.4
110°	228.3	228.3	228.3	228.3	228.3	228.0	227.5	227.0	226.5	226.0	226.5

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	262.2	261.7	261.2	260.7	260.5	260.3	260.0	259.7	259.4	259.1	259.4
115°	296.3	296.2	296.0	295.9	295.8	295.6	295.1	294.6	294.1	293.6	294.1
117.5°	329.8	329.3	328.8	328.3	328.1	327.9	327.4	326.9	326.4	325.9	326.4
120°	362.6	362.6	362.6	362.6	362.6	362.4	361.9	361.4	360.9	360.4	360.9
122.5°	397.3	396.8	396.3	395.8	395.6	395.4	395.1	394.8	394.4	394.1	394.4
125°	431.0	430.5	430.0	429.5	429.3	429.2	429.1	428.9	428.8	428.6	428.8
127.5°	463.9	463.3	462.6	461.9	461.6	461.4	460.9	460.4	459.9	459.4	459.9
130°	497.3	496.9	496.6	496.3	496.1	495.8	495.1	494.5	493.8	493.2	493.8
132.5°	530.6	529.8	528.9	528.1	527.7	527.5	527.0	526.5	526.0	525.5	526.0
135°	562.0	561.9	561.7	561.6	561.5	561.3	560.8	560.3	559.8	559.3	559.8
137.5°	592.8	592.7	592.5	592.4	592.3	592.0	591.3	590.6	590.0	589.3	590.0
140°	623.8	623.8	623.8	623.8	623.8	623.5	622.8	622.2	621.5	620.9	621.5
142.5°	651.9	652.1	652.2	652.4	652.5	652.2	651.5	650.8	650.2	649.5	650.2
145°	680.6	680.7	680.9	681.0	681.1	680.8	680.1	679.4	678.8	678.1	678.8
147.5°	705.6	706.0	706.3	706.6	706.8	706.5	705.8	705.1	704.5	703.8	704.5
150°	729.3	729.8	730.3	730.8	731.0	730.8	730.3	729.8	729.3	728.8	729.3
152.5°	752.9	753.6	754.2	754.9	755.2	754.9	754.2	753.6	752.9	752.3	752.9
155°	772.2	773.0	773.8	774.6	775.0	774.8	774.3	773.8	773.3	772.8	773.3
157.5°	790.8	792.0	793.1	794.2	794.8	794.4	793.6	792.8	792.0	791.2	792.0
160°	807.6	808.6	809.5	810.5	811.0	810.7	810.0	809.4	808.7	808.1	808.7
162.5°	822.4	823.6	824.7	825.8	826.4	826.0	825.2	824.3	823.5	822.7	823.5
165°	834.9	836.0	837.2	838.3	838.9	838.5	837.7	836.8	836.0	835.2	836.0
167.5°	845.9	847.0	848.2	849.3	849.9	849.5	848.7	847.8	847.0	846.2	847.0
170°	854.7	855.9	857.0	858.1	858.7	858.2	857.2	856.3	855.3	854.3	855.3
172.5°	861.3	862.5	863.6	864.7	865.3	864.8	863.8	862.9	861.9	860.9	861.9
175°	865.7	866.9	868.0	869.1	869.7	869.2	868.2	867.3	866.3	865.3	866.3
177.5°	868.5	869.5	870.4	871.4	871.9	871.4	870.4	869.5	868.5	867.5	868.5
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1360.6	1353.6	1347.7	1348.7	1353.6	1349.7	1339.8	1327.0	1322.1	1316.2	1322.1
5°	1442.4	1436.5	1424.7	1425.7	1422.7	1418.8	1403.0	1383.2	1383.2	1367.5	1365.5
7.5°	1523.3	1514.5	1506.6	1504.6	1493.7	1485.9	1472.0	1444.4	1433.6	1414.8	1404.0
10°	1614.1	1607.2	1598.3	1587.5	1581.6	1567.7	1545.0	1504.6	1484.9	1459.2	1440.5
12.5°	1705.9	1704.9	1685.1	1663.4	1662.5	1640.8	1625.0	1570.7	1544.1	1509.5	1465.1
15°	1764.1	1759.1	1748.3	1737.4	1740.4	1716.7	1681.2	1617.1	1599.3	1557.9	1510.5
17.5°	1763.1	1763.1	1760.1	1758.2	1755.2	1748.3	1728.6	1686.1	1657.5	1605.2	1560.8
20°	1706.9	1719.7	1722.6	1721.7	1731.5	1736.5	1735.5	1708.8	1686.1	1639.8	1594.4
22.5°	1594.4	1624.0	1636.8	1644.7	1665.4	1676.3	1701.9	1692.1	1686.1	1651.6	1613.1
25°	1489.8	1499.7	1538.1	1540.1	1568.7	1595.4	1621.0	1637.8	1659.5	1646.7	1614.1
27.5°	1354.6	1377.3	1404.9	1425.7	1431.6	1485.9	1528.3	1559.8	1609.2	1613.1	1602.3
30°	1201.7	1212.6	1257.9	1285.6	1317.1	1356.6	1417.8	1472.0	1516.4	1556.9	1570.7
32.5°	1015.2	1059.6	1086.3	1119.8	1147.4	1217.5	1292.5	1362.5	1413.8	1481.9	1511.5
35°	844.5	879.1	924.5	938.3	988.6	1047.8	1145.5	1235.2	1313.2	1382.3	1442.4
37.5°	703.5	731.1	779.4	801.1	830.7	906.7	988.6	1100.1	1193.8	1278.7	1353.6
40°	606.8	627.5	664.0	670.9	695.6	764.6	830.7	935.3	1059.6	1174.1	1256.0
42.5°	540.7	550.5	575.2	584.1	599.9	646.2	705.4	804.1	919.5	1037.9	1153.4
45°	493.3	500.2	515.0	522.9	542.6	563.4	611.7	690.6	781.4	900.8	1025.1
47.5°	450.9	459.8	465.7	470.6	481.5	504.2	535.7	593.9	680.8	790.3	910.7
50°	415.4	418.3	429.2	430.2	437.1	451.9	481.5	517.0	586.1	674.8	791.3
52.5°	379.8	382.8	389.7	396.6	399.6	411.4	431.2	460.8	512.1	582.1	685.7
55°	344.3	348.3	355.2	360.1	363.1	372.9	384.8	413.4	453.8	503.2	588.0
57.5°	308.8	317.7	319.7	322.6	327.6	338.4	349.3	366.0	397.6	443.0	505.2
60°	275.3	278.2	285.1	288.1	293.0	298.9	312.8	325.6	348.3	383.8	440.0
62.5°	240.7	247.6	250.6	253.6	257.5	264.4	273.3	287.1	306.8	335.5	379.8
65°	211.1	212.1	218.0	222.0	225.9	230.9	239.7	252.6	264.4	291.1	323.6
67.5°	182.5	184.5	186.5	190.4	195.4	200.3	208.2	215.1	229.9	247.6	273.3
70°	154.9	154.9	159.8	162.8	161.8	167.7	173.6	181.5	192.4	209.2	229.9
72.5°	130.2	129.2	133.2	134.2	136.2	140.1	144.0	151.9	157.9	170.7	186.5
75°	103.6	105.6	107.5	107.5	110.5	113.5	117.4	121.4	128.3	136.2	148.0
77.5°	81.9	81.9	83.9	84.8	87.8	86.8	90.8	94.7	99.6	106.6	115.4
80°	60.2	62.2	62.2	62.2	63.1	64.1	68.1	71.0	74.0	78.9	82.9
82.5°	42.4	42.4	44.4	44.4	44.4	46.4	46.4	47.4	49.3	52.3	55.3
85°	26.6	26.6	26.6	27.6	26.6	27.6	29.6	28.6	29.6	31.6	31.6
87.5°	12.8	12.8	12.8	12.8	12.8	13.8	12.8	13.8	14.8	14.8	14.8
90°	24.6	24.5	24.3	24.2	24.4	24.7	25.0	25.4	25.7	22.1	18.5
92.5°	23.5	23.5	23.5	23.5	23.4	23.3	23.1	23.0	22.8	22.6	22.4
95°	46.2	46.5	46.8	47.0	47.0	47.0	47.0	47.0	47.0	46.7	46.3
97.5°	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	72.8	72.1
100°	100.9	101.0	101.2	101.3	101.3	101.3	101.3	101.3	101.3	100.8	100.3
102.5°	131.7	131.9	132.0	132.1	132.0	131.9	131.7	131.6	131.4	130.7	130.1
105°	162.9	162.9	162.9	162.9	162.7	162.4	162.1	161.8	161.5	161.2	160.8
107.5°	193.2	194.0	194.8	195.2	195.1	195.0	194.8	194.7	194.5	194.5	194.5
110°	227.0	227.5	228.0	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	259.7	260.0	260.3	260.5	260.7	261.2	261.7	262.2	262.7	262.9	263.1
115°	294.6	295.1	295.6	295.8	295.9	296.0	296.2	296.3	296.5	296.8	297.2
117.5°	326.9	327.4	327.9	328.1	328.3	328.8	329.3	329.8	330.3	331.1	331.9
120°	361.4	361.9	362.4	362.6	362.6	362.6	362.6	362.6	362.6	363.9	365.2
122.5°	394.8	395.1	395.4	395.6	395.8	396.3	396.8	397.3	397.8	398.6	399.4
125°	428.9	429.1	429.2	429.3	429.5	430.0	430.5	431.0	431.5	432.0	432.5
127.5°	460.4	460.9	461.4	461.6	461.9	462.6	463.3	463.9	464.6	465.2	465.9
130°	494.5	495.1	495.8	496.1	496.3	496.6	496.9	497.3	497.6	497.9	498.3
132.5°	526.5	527.0	527.5	527.7	528.1	528.9	529.8	530.6	531.4	531.2	531.0
135°	560.3	560.8	561.3	561.5	561.6	561.7	561.9	562.0	562.2	561.9	561.5
137.5°	590.6	591.3	592.0	592.3	592.4	592.5	592.7	592.8	593.0	592.7	592.3
140°	622.2	622.8	623.5	623.8	623.8	623.8	623.8	623.8	623.8	623.0	622.2
142.5°	650.8	651.5	652.2	652.5	652.4	652.2	652.1	651.9	651.7	651.2	650.7
145°	679.4	680.1	680.8	681.1	681.0	680.9	680.7	680.6	680.4	679.4	678.4
147.5°	705.1	705.8	706.5	706.8	706.6	706.3	706.0	705.6	705.3	704.7	704.0
150°	729.8	730.3	730.8	731.0	730.8	730.3	729.8	729.3	728.8	728.2	727.5
152.5°	753.6	754.2	754.9	755.2	754.9	754.2	753.6	752.9	752.3	751.5	750.7
155°	773.8	774.3	774.8	775.0	774.6	773.8	773.0	772.2	771.4	770.9	770.4
157.5°	792.8	793.6	794.4	794.8	794.2	793.1	792.0	790.8	789.7	789.4	789.0
160°	809.4	810.0	810.7	811.0	810.5	809.5	808.6	807.6	806.6	806.4	806.3
162.5°	824.3	825.2	826.0	826.4	825.8	824.7	823.6	822.4	821.3	821.1	820.9
165°	836.8	837.7	838.5	838.9	838.3	837.2	836.0	834.9	833.7	833.7	833.7
167.5°	847.8	848.7	849.5	849.9	849.3	848.2	847.0	845.9	844.7	844.7	844.7
170°	856.3	857.2	858.2	858.7	858.1	857.0	855.9	854.7	853.6	853.8	853.9
172.5°	862.9	863.8	864.8	865.3	864.7	863.6	862.5	861.3	860.2	860.4	860.5
175°	867.3	868.2	869.2	869.7	869.1	868.0	866.9	865.7	864.6	864.9	865.2
177.5°	869.5	870.4	871.4	871.9	871.4	870.4	869.5	868.5	867.5	867.8	868.2
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1317.1	1312.2	1309.2	1311.2	1305.3	1290.5	1290.5	1295.4	1289.5	1283.6	1274.7
5°	1353.6	1343.8	1337.9	1336.9	1323.1	1299.4	1294.4	1289.5	1276.7	1262.9	1248.1
7.5°	1389.2	1371.4	1361.5	1354.6	1334.9	1304.3	1291.5	1280.6	1259.9	1239.2	1220.5
10°	1418.8	1393.1	1381.3	1370.4	1344.8	1306.3	1285.6	1265.8	1239.2	1212.6	1188.9
12.5°	1442.4	1412.8	1398.0	1382.3	1350.7	1300.4	1274.7	1243.1	1216.5	1181.0	1157.3
15°	1481.9	1420.7	1406.9	1392.1	1359.6	1290.5	1258.9	1223.4	1186.9	1139.5	1113.9
17.5°	1513.5	1431.6	1430.6	1399.0	1356.6	1286.6	1238.2	1191.8	1152.4	1105.0	1064.6
20°	1532.2	1448.4	1432.6	1400.0	1346.7	1259.9	1209.6	1158.3	1115.9	1058.6	1018.2
22.5°	1548.0	1472.0	1430.6	1391.1	1326.0	1251.0	1177.0	1128.7	1070.5	1008.3	969.8
25°	1553.9	1477.0	1433.6	1388.2	1311.2	1225.4	1141.5	1089.2	1024.1	967.9	915.6
27.5°	1554.9	1476.0	1422.7	1375.4	1290.5	1191.8	1106.0	1050.8	978.7	913.6	861.3
30°	1545.0	1465.1	1416.8	1365.5	1270.8	1161.3	1062.6	1001.4	924.5	859.3	805.1
32.5°	1515.5	1443.4	1404.0	1347.7	1245.1	1118.8	1021.2	953.1	872.2	808.0	755.8
35°	1466.1	1416.8	1373.4	1321.1	1211.6	1079.4	979.7	899.8	817.9	756.7	707.4
37.5°	1404.9	1378.3	1337.9	1286.6	1173.1	1043.8	933.3	844.5	762.7	703.5	655.1
40°	1322.1	1329.0	1289.5	1243.1	1127.7	995.5	873.2	788.3	711.4	656.1	608.7
42.5°	1232.3	1260.9	1238.2	1193.8	1077.4	942.2	828.8	735.0	660.0	602.8	563.4
45°	1135.6	1184.9	1171.1	1138.6	1025.1	886.0	765.6	674.8	608.7	553.5	519.0
47.5°	1030.0	1100.1	1100.1	1076.4	966.9	829.7	711.4	618.6	553.5	514.0	480.5
50°	922.5	1001.4	1014.2	998.5	901.8	765.6	645.3	561.4	505.2	466.7	442.0
52.5°	810.0	901.8	925.5	917.6	832.7	704.4	591.0	509.1	457.8	424.2	402.5
55°	702.5	809.0	834.7	837.6	758.7	637.4	530.8	458.8	409.4	386.8	368.0
57.5°	600.9	703.5	732.1	737.0	683.7	576.2	474.6	411.4	367.0	348.3	333.5
60°	514.0	599.9	637.4	648.2	601.8	505.2	422.3	361.1	327.6	309.8	296.0
62.5°	443.0	512.1	551.5	554.5	533.8	443.0	368.0	316.7	288.1	272.3	265.4
65°	373.9	436.1	459.8	471.6	454.8	383.8	317.7	275.3	252.6	238.8	231.9
67.5°	318.7	358.1	377.9	393.7	376.9	323.6	270.3	235.8	219.0	205.2	201.3
70°	261.5	294.0	308.8	324.6	309.8	269.3	230.9	199.3	184.5	173.6	168.7
72.5°	209.2	234.8	248.6	258.5	249.6	216.1	184.5	162.8	151.9	144.0	141.1
75°	165.8	183.5	191.4	198.3	194.4	168.7	149.0	131.2	121.4	114.4	112.5
77.5°	126.3	139.1	148.0	150.0	145.0	128.3	111.5	100.6	92.7	88.8	86.8
80°	89.8	97.7	102.6	105.6	100.6	93.7	81.9	74.0	67.1	62.2	61.2
82.5°	60.2	64.1	68.1	67.1	65.1	59.2	52.3	48.3	45.4	41.4	41.4
85°	34.5	35.5	37.5	38.5	37.5	33.5	29.6	27.6	25.7	22.7	22.7
87.5°	14.8	15.8	15.8	16.8	14.8	14.8	12.8	10.9	10.9	9.9	8.9
90°	14.9	11.3	9.5	8.5	6.6	4.6	2.7	0.7	2.7	4.6	6.6
92.5°	22.3	22.1	22.0	21.3	20.0	18.7	17.4	16.1	17.4	18.7	20.0
95°	46.0	45.7	45.5	44.7	43.1	41.4	39.8	38.2	39.8	41.4	43.1
97.5°	71.5	70.8	70.5	69.8	68.3	66.8	65.4	63.9	65.4	66.8	68.3
100°	99.8	99.3	99.1	98.4	97.1	95.8	94.5	93.2	94.5	95.8	97.1
102.5°	129.4	128.7	128.4	127.9	126.9	126.0	125.0	124.0	125.0	126.0	126.9
105°	160.5	160.2	160.0	159.8	159.3	158.8	158.3	157.8	158.3	158.8	159.3
107.5°	194.5	194.5	194.5	194.2	193.5	192.9	192.2	191.6	192.2	192.9	193.5
110°	228.3	228.3	228.3	227.8	226.8	225.8	224.8	223.8	224.8	225.8	226.8

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	263.2	263.4	263.5	263.0	262.0	261.1	260.1	259.1	260.1	261.1	262.0
115°	297.5	297.8	298.0	297.5	296.5	295.6	294.6	293.6	294.6	295.6	296.5
117.5°	332.7	333.5	333.9	333.3	332.0	330.7	329.4	328.1	329.4	330.7	332.0
120°	366.5	367.8	368.4	367.8	366.5	365.2	363.9	362.6	363.9	365.2	366.5
122.5°	400.3	401.1	401.5	400.7	399.0	397.4	395.7	394.1	395.7	397.4	399.0
125°	433.0	433.5	433.8	433.1	431.6	430.1	428.6	427.1	428.6	430.1	431.6
127.5°	466.5	467.2	467.5	466.6	464.8	463.0	461.2	459.4	461.2	463.0	464.8
130°	498.6	498.9	499.1	498.0	495.9	493.8	491.6	489.5	491.6	493.8	495.9
132.5°	530.9	530.7	530.6	529.8	528.2	526.5	524.9	523.3	524.9	526.5	528.2
135°	561.2	560.9	560.7	559.8	558.0	556.2	554.4	552.6	554.4	556.2	558.0
137.5°	592.0	591.7	591.5	590.8	589.3	587.8	586.4	584.9	586.4	587.8	589.3
140°	621.4	620.6	620.2	619.5	618.0	616.5	615.1	613.6	615.1	616.5	618.0
142.5°	650.2	649.7	649.5	648.8	647.3	645.8	644.4	642.9	644.4	645.8	647.3
145°	677.4	676.4	675.9	675.3	674.2	673.1	671.9	670.8	671.9	673.1	674.2
147.5°	703.4	702.7	702.4	701.7	700.2	698.7	697.3	695.8	697.3	698.7	700.2
150°	726.9	726.2	725.9	725.4	724.4	723.4	722.4	721.4	722.4	723.4	724.4
152.5°	749.8	749.0	748.6	748.1	747.1	746.2	745.2	744.2	745.2	746.2	747.1
155°	769.9	769.4	769.2	769.0	768.5	768.0	767.5	767.0	767.5	768.0	768.5
157.5°	788.7	788.4	788.2	788.0	787.7	787.4	787.1	786.8	787.1	787.4	787.7
160°	806.1	806.0	805.9	805.7	805.4	805.1	804.7	804.4	804.7	805.1	805.4
162.5°	820.8	820.6	820.5	820.5	820.5	820.5	820.5	820.5	820.5	820.5	820.5
165°	833.7	833.7	833.7	833.8	834.0	834.1	834.3	834.5	834.3	834.1	834.0
167.5°	844.7	844.7	844.7	845.0	845.5	846.0	846.5	847.0	846.5	846.0	845.5
170°	854.1	854.2	854.3	854.5	855.0	855.5	856.0	856.5	856.0	855.5	855.0
172.5°	860.7	860.8	860.9	861.1	861.6	862.1	862.6	863.1	862.6	862.1	861.6
175°	865.5	865.8	866.0	866.2	866.7	867.2	867.7	868.2	867.7	867.2	866.7
177.5°	868.5	868.8	869.0	869.2	869.7	870.2	870.7	871.2	870.7	870.2	869.7
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1269.8	1274.7	1273.7	1263.9	1253.0	1244.1	1227.4	1229.3	1223.4	1224.4	1230.3
5°	1238.2	1238.2	1234.3	1220.5	1202.7	1192.8	1174.1	1169.1	1157.3	1156.3	1155.3
7.5°	1204.7	1199.7	1194.8	1175.1	1153.4	1137.6	1111.9	1106.0	1094.2	1086.3	1082.3
10°	1165.2	1158.3	1148.4	1125.7	1099.1	1079.4	1052.7	1044.8	1022.1	1012.3	1006.4
12.5°	1121.8	1117.8	1102.1	1083.3	1039.9	1018.2	979.7	987.6	964.9	945.2	942.2
15°	1078.4	1063.6	1054.7	1024.1	971.8	962.0	931.4	915.6	894.9	879.1	879.1
17.5°	1036.0	1013.3	993.5	961.0	922.5	894.9	872.2	864.3	838.6	822.8	819.9
20°	979.7	954.1	949.1	902.8	876.1	845.5	823.8	804.1	785.4	778.4	773.5
22.5°	926.4	896.8	888.9	849.5	822.8	792.3	770.6	756.7	742.9	738.0	729.1
25°	869.2	851.5	839.6	797.2	767.6	739.0	724.2	714.3	701.5	700.5	694.6
27.5°	814.0	797.2	785.4	744.9	723.2	696.6	684.7	673.9	667.0	664.0	661.0
30°	766.6	747.9	734.0	704.4	677.8	656.1	646.2	639.3	635.4	630.5	629.5
32.5°	714.3	703.5	684.7	662.0	641.3	620.6	614.7	609.7	603.8	601.8	600.9
35°	669.9	655.1	643.3	617.6	608.7	591.0	584.1	580.1	572.2	570.3	568.3
37.5°	626.5	612.7	599.9	584.1	567.3	557.4	553.5	547.6	543.6	544.6	542.6
40°	583.1	572.2	562.4	545.6	535.7	530.8	522.9	517.0	515.0	516.0	515.0
42.5°	540.7	530.8	524.9	512.1	502.2	497.3	492.3	486.4	489.4	489.4	492.3
45°	502.2	493.3	489.4	479.5	473.6	465.7	460.8	459.8	463.7	462.7	462.7
47.5°	462.7	459.8	454.8	446.0	438.1	433.1	432.1	432.1	436.1	438.1	437.1
50°	432.1	426.2	420.3	413.4	407.5	405.5	402.5	404.5	408.5	408.5	410.4
52.5°	393.7	389.7	387.7	381.8	377.9	377.9	377.9	378.9	381.8	384.8	383.8
55°	360.1	357.2	355.2	352.2	347.3	348.3	347.3	349.3	352.2	355.2	357.2
57.5°	324.6	323.6	321.6	316.7	316.7	315.7	318.7	319.7	324.6	326.6	329.5
60°	293.0	290.1	290.1	286.1	286.1	286.1	289.1	292.0	296.0	297.0	298.9
62.5°	259.5	259.5	258.5	255.5	255.5	258.5	259.5	263.4	265.4	265.4	268.4
65°	227.9	226.9	225.9	226.9	227.9	227.9	230.9	232.8	234.8	235.8	236.8
67.5°	196.3	195.4	197.3	196.3	198.3	202.3	201.3	204.2	207.2	207.2	208.2
70°	166.7	168.7	167.7	169.7	168.7	170.7	173.6	174.6	174.6	175.6	178.6
72.5°	139.1	139.1	139.1	138.1	139.1	141.1	143.1	144.0	146.0	147.0	150.0
75°	112.5	112.5	110.5	112.5	112.5	114.4	116.4	116.4	116.4	118.4	121.4
77.5°	84.8	85.8	84.8	86.8	86.8	87.8	89.8	88.8	90.8	91.8	92.7
80°	62.2	61.2	61.2	61.2	62.2	62.2	64.1	65.1	65.1	68.1	66.1
82.5°	39.5	40.5	39.5	40.5	40.5	41.4	40.5	41.4	42.4	44.4	43.4
85°	22.7	21.7	21.7	22.7	21.7	21.7	22.7	21.7	22.7	21.7	22.7
87.5°	8.9	7.9	7.9	7.9	7.9	6.9	6.9	5.9	5.9	5.9	4.9
90°	8.5	9.5	11.3	14.9	18.5	22.1	25.7	25.4	25.0	24.7	24.4
92.5°	21.3	22.0	22.1	22.3	22.4	22.6	22.8	23.0	23.1	23.3	23.4
95°	44.7	45.5	45.7	46.0	46.3	46.7	47.0	47.0	47.0	47.0	47.0
97.5°	69.8	70.5	70.8	71.5	72.1	72.8	73.4	73.4	73.4	73.4	73.4
100°	98.4	99.1	99.3	99.8	100.3	100.8	101.3	101.3	101.3	101.3	101.3
102.5°	127.9	128.4	128.7	129.4	130.1	130.7	131.4	131.6	131.7	131.9	132.0
105°	159.8	160.0	160.2	160.5	160.8	161.2	161.5	161.8	162.1	162.4	162.7
107.5°	194.2	194.5	194.5	194.5	194.5	194.5	194.5	194.7	194.8	195.0	195.1
110°	227.8	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	263.0	263.5	263.4	263.2	263.1	262.9	262.7	262.2	261.7	261.2	260.7
115°	297.5	298.0	297.8	297.5	297.2	296.8	296.5	296.3	296.2	296.0	295.9
117.5°	333.3	333.9	333.5	332.7	331.9	331.1	330.3	329.8	329.3	328.8	328.3
120°	367.8	368.4	367.8	366.5	365.2	363.9	362.6	362.6	362.6	362.6	362.6
122.5°	400.7	401.5	401.1	400.3	399.4	398.6	397.8	397.3	396.8	396.3	395.8
125°	433.1	433.8	433.5	433.0	432.5	432.0	431.5	431.0	430.5	430.0	429.5
127.5°	466.6	467.5	467.2	466.5	465.9	465.2	464.6	463.9	463.3	462.6	461.9
130°	498.0	499.1	498.9	498.6	498.3	497.9	497.6	497.3	496.9	496.6	496.3
132.5°	529.8	530.6	530.7	530.9	531.0	531.2	531.4	530.6	529.8	528.9	528.1
135°	559.8	560.7	560.9	561.2	561.5	561.9	562.2	562.0	561.9	561.7	561.6
137.5°	590.8	591.5	591.7	592.0	592.3	592.7	593.0	592.8	592.7	592.5	592.4
140°	619.5	620.2	620.6	621.4	622.2	623.0	623.8	623.8	623.8	623.8	623.8
142.5°	648.8	649.5	649.7	650.2	650.7	651.2	651.7	651.9	652.1	652.2	652.4
145°	675.3	675.9	676.4	677.4	678.4	679.4	680.4	680.6	680.7	680.9	681.0
147.5°	701.7	702.4	702.7	703.4	704.0	704.7	705.3	705.6	706.0	706.3	706.6
150°	725.4	725.9	726.2	726.9	727.5	728.2	728.8	729.3	729.8	730.3	730.8
152.5°	748.1	748.6	749.0	749.8	750.7	751.5	752.3	752.9	753.6	754.2	754.9
155°	769.0	769.2	769.4	769.9	770.4	770.9	771.4	772.2	773.0	773.8	774.6
157.5°	788.0	788.2	788.4	788.7	789.0	789.4	789.7	790.8	792.0	793.1	794.2
160°	805.7	805.9	806.0	806.1	806.3	806.4	806.6	807.6	808.6	809.5	810.5
162.5°	820.5	820.5	820.6	820.8	820.9	821.1	821.3	822.4	823.6	824.7	825.8
165°	833.8	833.7	833.7	833.7	833.7	833.7	833.7	834.9	836.0	837.2	838.3
167.5°	845.0	844.7	844.7	844.7	844.7	844.7	844.7	845.9	847.0	848.2	849.3
170°	854.5	854.3	854.2	854.1	853.9	853.8	853.6	854.7	855.9	857.0	858.1
172.5°	861.1	860.9	860.8	860.7	860.5	860.4	860.2	861.3	862.5	863.6	864.7
175°	866.2	866.0	865.8	865.5	865.2	864.9	864.6	865.7	866.9	868.0	869.1
177.5°	869.2	869.0	868.8	868.5	868.2	867.8	867.5	868.5	869.5	870.4	871.4
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1223.4	1226.4	1219.5	1217.5	1219.5	1212.6	1214.5	1216.5	1216.5	1219.5	1221.4
5°	1152.4	1148.4	1141.5	1139.5	1137.6	1140.5	1138.6	1141.5	1142.5	1149.4	1150.4
7.5°	1082.3	1076.4	1070.5	1064.6	1062.6	1057.7	1062.6	1062.6	1069.5	1067.5	1072.5
10°	999.4	998.5	990.6	987.6	983.7	975.8	986.6	983.7	988.6	997.5	999.4
12.5°	938.3	927.4	932.4	918.5	923.5	915.6	916.6	916.6	924.5	925.5	923.5
15°	880.1	871.2	858.4	852.4	849.5	845.5	858.4	859.3	853.4	867.2	862.3
17.5°	820.9	820.9	809.0	806.1	798.2	802.1	800.1	801.1	799.2	809.0	814.0
20°	769.6	764.6	760.7	761.7	751.8	749.8	747.9	749.8	756.7	763.6	765.6
22.5°	728.1	725.2	715.3	717.3	709.4	712.3	710.4	715.3	716.3	716.3	723.2
25°	688.7	684.7	685.7	681.8	678.8	678.8	675.8	678.8	682.7	684.7	685.7
27.5°	659.1	656.1	651.2	648.2	650.2	645.3	649.2	652.2	652.2	650.2	652.2
30°	623.5	625.5	625.5	615.7	619.6	617.6	620.6	622.6	622.6	623.5	621.6
32.5°	599.9	593.9	593.0	592.0	592.0	588.0	588.0	591.0	592.0	593.0	595.9
35°	568.3	568.3	563.4	566.3	562.4	563.4	562.4	563.4	565.3	562.4	565.3
37.5°	539.7	540.7	538.7	540.7	541.7	539.7	537.7	541.7	539.7	539.7	537.7
40°	515.0	514.0	515.0	515.0	515.0	516.0	514.0	514.0	514.0	512.1	510.1
42.5°	494.3	488.4	490.4	491.3	488.4	488.4	489.4	488.4	491.3	485.4	485.4
45°	464.7	462.7	463.7	463.7	465.7	462.7	464.7	465.7	462.7	461.7	459.8
47.5°	438.1	440.0	438.1	440.0	440.0	442.0	438.1	439.0	440.0	436.1	433.1
50°	411.4	411.4	414.4	413.4	414.4	412.4	412.4	411.4	412.4	410.4	407.5
52.5°	386.8	383.8	388.7	387.7	386.8	385.8	384.8	385.8	383.8	381.8	381.8
55°	356.2	356.2	359.1	360.1	360.1	358.1	356.2	357.2	356.2	355.2	354.2
57.5°	331.5	327.6	329.5	330.5	330.5	327.6	329.5	327.6	327.6	328.5	325.6
60°	299.9	299.9	298.0	300.9	300.9	298.9	298.9	299.9	298.0	297.0	296.0
62.5°	266.4	267.4	270.3	271.3	272.3	270.3	268.4	269.3	269.3	266.4	267.4
65°	237.8	239.7	243.7	242.7	240.7	241.7	239.7	240.7	237.8	238.8	235.8
67.5°	210.2	209.2	210.2	210.2	212.1	211.1	209.2	209.2	208.2	211.1	208.2
70°	180.6	180.6	180.6	180.6	181.5	182.5	180.6	178.6	179.6	177.6	176.6
72.5°	150.0	151.0	150.0	151.9	149.0	151.0	151.0	150.0	149.0	149.0	149.0
75°	121.4	123.3	120.4	121.4	120.4	122.3	121.4	121.4	119.4	118.4	119.4
77.5°	92.7	93.7	91.8	92.7	91.8	92.7	92.7	91.8	91.8	91.8	91.8
80°	66.1	67.1	66.1	65.1	64.1	66.1	64.1	65.1	66.1	65.1	67.1
82.5°	42.4	42.4	41.4	42.4	40.5	40.5	41.4	41.4	40.5	42.4	40.5
85°	20.7	20.7	22.7	20.7	19.7	19.7	19.7	20.7	19.7	21.7	20.7
87.5°	4.9	3.9	4.9	4.9	3.9	3.9	4.9	3.9	4.9	5.9	3.9
90°	24.2	24.3	24.5	24.6	24.8	25.0	24.8	24.6	24.5	24.3	24.2
92.5°	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5
95°	47.0	46.8	46.5	46.2	45.8	45.5	45.8	46.2	46.5	46.8	47.0
97.5°	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4
100°	101.3	101.2	101.0	100.9	100.7	100.5	100.7	100.9	101.0	101.2	101.3
102.5°	132.1	132.0	131.9	131.7	131.6	131.4	131.6	131.7	131.9	132.0	132.1
105°	162.9	162.9	162.9	162.9	162.9	162.9	162.9	162.9	162.9	162.9	162.9
107.5°	195.2	194.8	194.0	193.2	192.4	191.6	192.4	193.2	194.0	194.8	195.2
110°	228.3	228.0	227.5	227.0	226.5	226.0	226.5	227.0	227.5	228.0	228.3

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	260.5	260.3	260.0	259.7	259.4	259.1	259.4	259.7	260.0	260.3	260.5
115°	295.8	295.6	295.1	294.6	294.1	293.6	294.1	294.6	295.1	295.6	295.8
117.5°	328.1	327.9	327.4	326.9	326.4	325.9	326.4	326.9	327.4	327.9	328.1
120°	362.6	362.4	361.9	361.4	360.9	360.4	360.9	361.4	361.9	362.4	362.6
122.5°	395.6	395.4	395.1	394.8	394.4	394.1	394.4	394.8	395.1	395.4	395.6
125°	429.3	429.2	429.1	428.9	428.8	428.6	428.8	428.9	429.1	429.2	429.3
127.5°	461.6	461.4	460.9	460.4	459.9	459.4	459.9	460.4	460.9	461.4	461.6
130°	496.1	495.8	495.1	494.5	493.8	493.2	493.8	494.5	495.1	495.8	496.1
132.5°	527.7	527.5	527.0	526.5	526.0	525.5	526.0	526.5	527.0	527.5	527.7
135°	561.5	561.3	560.8	560.3	559.8	559.3	559.8	560.3	560.8	561.3	561.5
137.5°	592.3	592.0	591.3	590.6	590.0	589.3	590.0	590.6	591.3	592.0	592.3
140°	623.8	623.5	622.8	622.2	621.5	620.9	621.5	622.2	622.8	623.5	623.8
142.5°	652.5	652.2	651.5	650.8	650.2	649.5	650.2	650.8	651.5	652.2	652.5
145°	681.1	680.8	680.1	679.4	678.8	678.1	678.8	679.4	680.1	680.8	681.1
147.5°	706.8	706.5	705.8	705.1	704.5	703.8	704.5	705.1	705.8	706.5	706.8
150°	731.0	730.8	730.3	729.8	729.3	728.8	729.3	729.8	730.3	730.8	731.0
152.5°	755.2	754.9	754.2	753.6	752.9	752.3	752.9	753.6	754.2	754.9	755.2
155°	775.0	774.8	774.3	773.8	773.3	772.8	773.3	773.8	774.3	774.8	775.0
157.5°	794.8	794.4	793.6	792.8	792.0	791.2	792.0	792.8	793.6	794.4	794.8
160°	811.0	810.7	810.0	809.4	808.7	808.1	808.7	809.4	810.0	810.7	811.0
162.5°	826.4	826.0	825.2	824.3	823.5	822.7	823.5	824.3	825.2	826.0	826.4
165°	838.9	838.5	837.7	836.8	836.0	835.2	836.0	836.8	837.7	838.5	838.9
167.5°	849.9	849.5	848.7	847.8	847.0	846.2	847.0	847.8	848.7	849.5	849.9
170°	858.7	858.2	857.2	856.3	855.3	854.3	855.3	856.3	857.2	858.2	858.7
172.5°	865.3	864.8	863.8	862.9	861.9	860.9	861.9	862.9	863.8	864.8	865.3
175°	869.7	869.2	868.2	867.3	866.3	865.3	866.3	867.3	868.2	869.2	869.7
177.5°	871.9	871.4	870.4	869.5	868.5	867.5	868.5	869.5	870.4	871.4	871.9
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1218.5	1226.4	1223.4	1212.6	1225.4	1225.4	1234.3	1234.3	1245.1	1249.1	1255.0
5°	1149.4	1155.3	1160.3	1155.3	1164.2	1178.0	1185.9	1192.8	1207.6	1213.5	1222.4
7.5°	1075.4	1086.3	1091.2	1091.2	1106.0	1121.8	1137.6	1147.4	1168.2	1176.1	1184.9
10°	1003.4	1016.2	1026.1	1025.1	1049.8	1059.6	1079.4	1102.1	1122.8	1134.6	1147.4
12.5°	927.4	934.3	948.1	967.9	973.8	991.6	1014.2	1042.9	1080.4	1091.2	1109.9
15°	864.3	883.0	893.9	902.8	916.6	933.3	958.0	985.6	1023.1	1046.8	1066.5
17.5°	811.0	835.7	842.6	840.6	858.4	884.0	912.6	933.3	966.9	995.5	1014.2
20°	767.6	777.5	789.3	794.2	808.0	835.7	863.3	887.0	914.6	937.3	959.0
22.5°	724.2	732.1	741.9	750.8	761.7	777.5	804.1	833.7	860.3	882.0	906.7
25°	688.7	693.6	702.5	709.4	721.2	732.1	750.8	783.4	814.9	827.8	849.5
27.5°	654.1	658.1	664.0	671.9	677.8	688.7	705.4	732.1	764.6	777.5	807.1
30°	623.5	626.5	632.4	636.4	639.3	652.2	665.0	685.7	710.4	728.1	749.8
32.5°	594.9	597.9	603.8	604.8	608.7	615.7	627.5	646.2	667.9	682.7	701.5
35°	563.4	565.3	571.3	573.2	576.2	582.1	591.0	604.8	624.5	635.4	652.2
37.5°	538.7	537.7	541.7	544.6	548.6	551.5	554.5	568.3	583.1	593.0	605.8
40°	512.1	510.1	511.1	515.0	517.0	520.9	520.9	534.7	544.6	552.5	562.4
42.5°	485.4	484.4	482.5	484.4	486.4	487.4	488.4	498.2	508.1	515.0	525.9
45°	458.8	457.8	455.8	456.8	456.8	458.8	461.7	465.7	472.6	478.5	484.4
47.5°	434.1	432.1	429.2	428.2	430.2	430.2	430.2	434.1	441.0	443.0	448.9
50°	408.5	405.5	401.6	399.6	399.6	398.6	400.6	401.6	407.5	409.4	414.4
52.5°	380.8	378.9	374.9	371.0	372.0	370.0	371.0	372.0	373.9	376.9	379.8
55°	353.2	349.3	346.3	345.3	342.4	342.4	339.4	343.3	342.4	343.3	347.3
57.5°	326.6	322.6	317.7	315.7	312.8	311.8	309.8	308.8	309.8	312.8	315.7
60°	295.0	293.0	290.1	287.1	285.1	282.2	280.2	280.2	279.2	279.2	280.2
62.5°	264.4	263.4	259.5	258.5	256.5	254.5	251.6	249.6	249.6	251.6	252.6
65°	234.8	233.8	230.9	229.9	224.9	223.0	222.0	221.0	219.0	219.0	219.0
67.5°	207.2	204.2	204.2	199.3	195.4	193.4	191.4	190.4	190.4	190.4	191.4
70°	176.6	176.6	173.6	170.7	166.7	167.7	164.8	161.8	161.8	159.8	160.8
72.5°	147.0	146.0	143.1	142.1	139.1	136.2	134.2	136.2	133.2	132.2	133.2
75°	118.4	117.4	115.4	113.5	114.4	111.5	108.5	107.5	107.5	105.6	105.6
77.5°	90.8	92.7	88.8	87.8	85.8	83.9	82.9	81.9	81.9	81.9	83.9
80°	63.1	64.1	64.1	62.2	63.1	60.2	60.2	60.2	57.2	58.2	59.2
82.5°	40.5	40.5	39.5	40.5	39.5	39.5	38.5	38.5	37.5	37.5	38.5
85°	22.7	21.7	20.7	22.7	21.7	21.7	20.7	20.7	20.7	20.7	20.7
87.5°	4.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	7.9
90°	24.4	24.7	25.0	25.4	25.7	22.1	18.5	14.9	11.3	9.5	8.5
92.5°	23.4	23.3	23.1	23.0	22.8	22.6	22.4	22.3	22.1	22.0	21.3
95°	47.0	47.0	47.0	47.0	47.0	46.7	46.3	46.0	45.7	45.5	44.7
97.5°	73.4	73.4	73.4	73.4	73.4	72.8	72.1	71.5	70.8	70.5	69.8
100°	101.3	101.3	101.3	101.3	101.3	100.8	100.3	99.8	99.3	99.1	98.4
102.5°	132.0	131.9	131.7	131.6	131.4	130.7	130.1	129.4	128.7	128.4	127.9
105°	162.7	162.4	162.1	161.8	161.5	161.2	160.8	160.5	160.2	160.0	159.8
107.5°	195.1	195.0	194.8	194.7	194.5	194.5	194.5	194.5	194.5	194.5	194.2
110°	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	227.8

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	260.7	261.2	261.7	262.2	262.7	262.9	263.1	263.2	263.4	263.5	263.0
115°	295.9	296.0	296.2	296.3	296.5	296.8	297.2	297.5	297.8	298.0	297.5
117.5°	328.3	328.8	329.3	329.8	330.3	331.1	331.9	332.7	333.5	333.9	333.3
120°	362.6	362.6	362.6	362.6	362.6	363.9	365.2	366.5	367.8	368.4	367.8
122.5°	395.8	396.3	396.8	397.3	397.8	398.6	399.4	400.3	401.1	401.5	400.7
125°	429.5	430.0	430.5	431.0	431.5	432.0	432.5	433.0	433.5	433.8	433.1
127.5°	461.9	462.6	463.3	463.9	464.6	465.2	465.9	466.5	467.2	467.5	466.6
130°	496.3	496.6	496.9	497.3	497.6	497.9	498.3	498.6	498.9	499.1	498.0
132.5°	528.1	528.9	529.8	530.6	531.4	531.2	531.0	530.9	530.7	530.6	529.8
135°	561.6	561.7	561.9	562.0	562.2	561.9	561.5	561.2	560.9	560.7	559.8
137.5°	592.4	592.5	592.7	592.8	593.0	592.7	592.3	592.0	591.7	591.5	590.8
140°	623.8	623.8	623.8	623.8	623.8	623.0	622.2	621.4	620.6	620.2	619.5
142.5°	652.4	652.2	652.1	651.9	651.7	651.2	650.7	650.2	649.7	649.5	648.8
145°	681.0	680.9	680.7	680.6	680.4	679.4	678.4	677.4	676.4	675.9	675.3
147.5°	706.6	706.3	706.0	705.6	705.3	704.7	704.0	703.4	702.7	702.4	701.7
150°	730.8	730.3	729.8	729.3	728.8	728.2	727.5	726.9	726.2	725.9	725.4
152.5°	754.9	754.2	753.6	752.9	752.3	751.5	750.7	749.8	749.0	748.6	748.1
155°	774.6	773.8	773.0	772.2	771.4	770.9	770.4	769.9	769.4	769.2	769.0
157.5°	794.2	793.1	792.0	790.8	789.7	789.4	789.0	788.7	788.4	788.2	788.0
160°	810.5	809.5	808.6	807.6	806.6	806.4	806.3	806.1	806.0	805.9	805.7
162.5°	825.8	824.7	823.6	822.4	821.3	821.1	820.9	820.8	820.6	820.5	820.5
165°	838.3	837.2	836.0	834.9	833.7	833.7	833.7	833.7	833.7	833.7	833.8
167.5°	849.3	848.2	847.0	845.9	844.7	844.7	844.7	844.7	844.7	844.7	845.0
170°	858.1	857.0	855.9	854.7	853.6	853.8	853.9	854.1	854.2	854.3	854.5
172.5°	864.7	863.6	862.5	861.3	860.2	860.4	860.5	860.7	860.8	860.9	861.1
175°	869.1	868.0	866.9	865.7	864.6	864.9	865.2	865.5	865.8	866.0	866.2
177.5°	871.4	870.4	869.5	868.5	867.5	867.8	868.2	868.5	868.8	869.0	869.2
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1283.6	1283.6	1283.6	1283.6
2.5°	1259.9	1259.9	1274.7	1290.5
5°	1232.3	1239.2	1262.9	1284.6
7.5°	1205.7	1217.5	1247.1	1274.7
10°	1173.1	1188.9	1225.4	1257.9
12.5°	1141.5	1156.3	1198.7	1235.2
15°	1097.1	1115.9	1161.3	1206.6
17.5°	1052.7	1071.5	1126.7	1180.0
20°	1000.4	1025.1	1087.3	1158.3
22.5°	952.1	982.7	1051.7	1109.0
25°	898.8	946.2	1010.3	1084.3
27.5°	851.5	898.8	963.9	1038.9
30°	798.2	846.5	913.6	982.7
32.5°	746.9	791.3	856.4	941.2
35°	693.6	736.0	799.2	885.0
37.5°	645.3	686.7	755.8	834.7
40°	597.9	641.3	700.5	779.4
42.5°	553.5	592.0	645.3	724.2
45°	513.0	540.7	590.0	664.0
47.5°	470.6	495.3	540.7	614.7
50°	431.2	451.9	491.3	560.4
52.5°	392.7	410.4	446.9	502.2
55°	358.1	374.9	401.6	455.8
57.5°	322.6	335.5	361.1	404.5
60°	288.1	299.9	320.7	356.2
62.5°	253.6	263.4	283.2	311.8
65°	223.0	230.9	245.7	270.3
67.5°	193.4	198.3	210.2	229.9
70°	164.8	168.7	178.6	194.4
72.5°	134.2	138.1	149.0	159.8
75°	108.5	109.5	117.4	126.3
77.5°	84.8	83.9	89.8	96.7
80°	58.2	61.2	66.1	69.1
82.5°	39.5	40.5	42.4	44.4
85°	21.7	22.7	22.7	25.7
87.5°	8.9	9.9	9.9	10.9
90°	6.6	4.6	2.7	0.7
92.5°	20.0	18.7	17.4	16.1
95°	43.1	41.4	39.8	38.2
97.5°	68.3	66.8	65.4	63.9
100°	97.1	95.8	94.5	93.2
102.5°	126.9	126.0	125.0	124.0
105°	159.3	158.8	158.3	157.8
107.5°	193.5	192.9	192.2	191.6
110°	226.8	225.8	224.8	223.8

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	262.0	261.1	260.1	259.1
115°	296.5	295.6	294.6	293.6
117.5°	332.0	330.7	329.4	328.1
120°	366.5	365.2	363.9	362.6
122.5°	399.0	397.4	395.7	394.1
125°	431.6	430.1	428.6	427.1
127.5°	464.8	463.0	461.2	459.4
130°	495.9	493.8	491.6	489.5
132.5°	528.2	526.5	524.9	523.3
135°	558.0	556.2	554.4	552.6
137.5°	589.3	587.8	586.4	584.9
140°	618.0	616.5	615.1	613.6
142.5°	647.3	645.8	644.4	642.9
145°	674.2	673.1	671.9	670.8
147.5°	700.2	698.7	697.3	695.8
150°	724.4	723.4	722.4	721.4
152.5°	747.1	746.2	745.2	744.2
155°	768.5	768.0	767.5	767.0
157.5°	787.7	787.4	787.1	786.8
160°	805.4	805.1	804.7	804.4
162.5°	820.5	820.5	820.5	820.5
165°	834.0	834.1	834.3	834.5
167.5°	845.5	846.0	846.5	847.0
170°	855.0	855.5	856.0	856.5
172.5°	861.6	862.1	862.6	863.1
175°	866.7	867.2	867.7	868.2
177.5°	869.7	870.2	870.7	871.2
180°	869.7	869.7	869.7	869.7

TEST NUMBER: P998904

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.66	17.52	17.59	18.46	19.68	14.15	15.01	15.08	15.95	17.17
	3H	17.47	18.24	18.41	19.19	20.43	15.49	16.26	16.44	17.22	18.46
	4H	17.64	18.36	18.59	19.32	20.57	15.96	16.68	16.91	17.64	18.89
	6H	17.68	18.35	18.65	19.31	20.58	16.26	16.93	17.23	17.90	19.16
	8H	17.66	18.30	18.64	19.28	20.54	16.35	16.98	17.32	17.96	19.22
	12H	17.62	18.23	18.60	19.20	20.49	16.39	17.00	17.37	17.97	19.25
4H	2H	16.70	17.42	17.66	18.38	19.63	14.60	15.32	15.56	16.28	17.53
	3H	17.68	18.28	18.65	19.27	20.54	16.06	16.66	17.03	17.65	18.91
	4H	17.96	18.51	18.94	19.49	20.78	16.59	17.14	17.57	18.12	19.41
	6H	18.09	18.56	19.08	19.56	20.85	16.97	17.44	17.96	18.45	19.74
	8H	18.08	18.53	19.08	19.52	20.83	17.08	17.52	18.08	18.52	19.82
	12H	18.05	18.45	19.06	19.46	20.77	17.14	17.54	18.15	18.55	19.86
8H	4H	17.96	18.41	18.96	19.40	20.71	16.73	17.18	17.73	18.17	19.48
	6H	18.14	18.51	19.16	19.55	20.85	17.17	17.53	18.19	18.57	19.87
	8H	18.17	18.49	19.20	19.52	20.84	17.32	17.64	18.35	18.67	19.99
	12H	18.16	18.44	19.19	19.46	20.82	17.41	17.69	18.44	18.71	20.08
12H	4H	17.92	18.32	18.93	19.33	20.64	16.71	17.11	17.72	18.12	19.43
	6H	18.12	18.44	19.15	19.47	20.79	17.17	17.49	18.20	18.52	19.84
	8H	18.15	18.44	19.18	19.46	20.82	17.33	17.61	18.36	18.63	19.99