

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997788

Luminaire Tested: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997788
REPORT IS A COMBINATION OF REPORTS P983522 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7826.0 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997788

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P997788

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	95	91	86	82	87	83	79	76	69	66	64	56	54	52	44	42	41
2	86	78	72	66	79	72	66	61	59	55	51	48	45	42	38	36	34
3	78	68	61	54	71	63	56	50	52	47	43	42	38	35	33	30	28
4	71	60	52	46	65	55	48	42	46	40	36	37	33	30	29	26	24
5	65	53	45	39	60	49	42	36	41	35	31	33	29	26	26	23	20
6	60	48	39	33	55	44	36	31	37	31	27	30	26	22	24	20	18
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	22	18	16
8	51	39	31	25	47	36	29	24	30	25	20	25	20	17	20	16	14
9	48	35	28	23	44	33	26	21	28	22	18	23	18	15	18	15	13
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	14	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16632	16632	16632
5°	16706	15921	15831
10°	16595	15371	15146
15°	16360	14799	14442
20°	16066	14201	13775
25°	15773	13627	13169
30°	15364	13044	12569
35°	14950	12483	12129
40°	14515	11997	11692
45°	14100	11555	11311
50°	13655	11149	10935
55°	13187	10718	10551
60°	12614	10269	10149
65°	12016	9752	9684
70°	11342	9198	9185
75°	10478	8643	8715
80°	9117	8066	8226
85°	7741	7522	7807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14100 cd/sqm

TEST NUMBER: P997788

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	1.3
10°-20°	285.7	3.7
20°-30°	432.8	5.5
30°-40°	527.1	6.7
40°-50°	567.1	7.2
50°-60°	550.7	7.0
60°-70°	481.0	6.1
70°-80°	370.2	4.7
80°-90°	251.8	3.2
90°-100°	255.4	3.3
100°-110°	393.1	5.0
110°-120°	541.4	6.9
120°-130°	649.5	8.3
130°-140°	696.8	8.9
140°-150°	667.6	8.5
150°-160°	557.3	7.1
160°-170°	369.6	4.7
170°-180°	129.2	1.7
0°-30°	818.1	10.5
0°-40°	1345.2	17.2
0°-60°	2463.0	31.5
0°-90°	3566.0	45.6
90°-120°	1190.0	15.2
90°-150°	3203.9	40.9
90°-180°	4260.0	54.4
0°-180°	7826.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1051	1051	1051	1051	1051	
5°	1054	1049	1040	1049	1048	100
15°	1005	1008	1008	1022	1020	283
25°	914	924	938	956	961	420
35°	787	813	842	876	886	492
45°	646	687	740	787	802	498
55°	495	550	629	684	704	443
65°	338	413	502	565	585	336
75°	187	273	370	436	455	198
85°	55	149	247	311	332	58
90°	16	118	241	300	319	14
95°	72	155	249	307	323	76
105°	255	303	384	440	456	270
115°	466	490	556	601	614	461
125°	673	683	729	766	779	602
135°	868	881	898	929	938	671
145°	1052	1060	1067	1077	1080	658
155°	1203	1206	1210	1215	1212	554
165°	1309	1308	1308	1316	1310	369
175°	1362	1358	1356	1364	1357	129
180°	1364	1364	1364	1364	1364	

TEST NUMBER: P997788

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1050.7	1050.7	1050.7	1050.7	1050.7
2.5°	1058.3	1053.7	1043.1	1050.7	1047.6
5°	1053.7	1049.2	1040.0	1049.2	1047.6
7.5°	1046.1	1043.1	1035.4	1046.1	1044.6
10°	1037.0	1033.9	1029.4	1041.5	1040.0
12.5°	1021.7	1023.3	1020.2	1032.4	1030.9
15°	1005.0	1008.0	1008.0	1021.7	1020.2
17.5°	983.7	989.8	994.3	1008.0	1008.0
20°	962.4	970.0	976.1	992.8	992.8
22.5°	939.5	948.7	957.8	974.5	977.6
25°	913.6	924.3	938.0	956.3	960.8
27.5°	883.2	899.9	915.2	938.0	941.0
30°	852.7	872.5	892.3	916.7	921.2
32.5°	819.2	842.1	866.4	895.4	904.5
35°	787.2	813.1	842.1	875.6	886.2
37.5°	752.2	781.2	817.7	854.2	864.9
40°	717.2	750.7	791.8	831.4	845.1
42.5°	683.7	717.2	765.9	810.1	823.8
45°	645.6	686.7	740.0	787.2	802.5
47.5°	609.1	653.2	714.2	762.9	779.6
50°	571.0	618.2	686.7	738.5	755.3
52.5°	534.5	584.7	657.8	711.1	729.4
55°	494.9	549.7	628.9	683.7	703.5
57.5°	456.8	517.7	596.9	656.3	676.1
60°	415.7	481.2	568.0	625.8	647.2
62.5°	379.2	447.7	534.5	596.9	616.7
65°	338.0	412.7	502.5	564.9	584.7
67.5°	301.5	379.2	470.5	533.0	554.3
70°	261.9	341.1	435.5	501.0	519.2
72.5°	225.4	307.6	403.5	467.5	490.3
75°	187.3	272.6	370.0	435.5	455.3
77.5°	150.7	239.1	338.0	403.5	424.8
80°	114.2	207.1	306.1	370.0	391.3
82.5°	83.7	175.1	275.6	339.6	359.4
85°	54.8	149.2	246.7	310.6	332.0
87.5°	33.5	124.9	222.3	284.7	304.5
90°	16.4	118.5	241.3	299.9	319.3
92.5°	39.0	128.9	223.0	283.5	301.8
95°	72.0	155.1	248.8	306.7	322.6
97.5°	110.8	186.6	279.6	335.9	354.2
100°	156.9	222.4	311.1	367.4	383.1
102.5°	203.6	260.8	347.6	403.6	419.2
105°	255.1	302.7	384.2	439.7	456.5
107.5°	308.0	349.2	425.3	478.3	489.2
110°	357.1	394.4	469.1	517.8	531.1

TEST NUMBER: P997788

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	412.4	443.7	512.5	557.8	572.3
115°	466.5	490.1	556.4	600.8	614.2
117.5°	519.1	540.4	598.6	640.9	652.6
120°	573.2	588.5	640.2	682.8	696.1
122.5°	622.7	635.7	686.2	723.9	735.3
125°	672.8	683.2	728.6	766.2	778.8
127.5°	723.5	734.7	771.1	804.6	814.9
130°	770.7	784.1	813.8	848.0	855.6
132.5°	823.6	833.6	857.7	886.9	895.7
135°	868.2	880.8	898.3	929.2	937.9
137.5°	918.8	929.2	939.1	966.9	972.9
140°	963.7	972.5	981.3	1005.7	1010.2
142.5°	1009.7	1018.6	1022.0	1041.5	1044.5
145°	1052.0	1060.0	1066.9	1077.2	1080.2
147.5°	1091.1	1101.5	1106.1	1109.9	1109.9
150°	1131.4	1138.3	1142.9	1146.3	1142.9
152.5°	1167.1	1174.0	1179.7	1184.3	1179.7
155°	1202.7	1206.2	1209.6	1215.4	1211.9
157.5°	1233.8	1236.1	1238.4	1246.5	1240.7
160°	1261.4	1263.7	1264.9	1271.8	1267.2
162.5°	1286.8	1286.8	1287.9	1296.0	1290.2
165°	1308.6	1307.5	1307.5	1315.5	1309.8
167.5°	1328.2	1324.7	1324.7	1332.8	1327.0
170°	1343.2	1339.7	1338.5	1346.6	1339.7
172.5°	1353.5	1350.1	1348.9	1357.0	1350.1
175°	1361.6	1358.1	1355.8	1363.9	1357.0
177.5°	1366.2	1362.7	1360.4	1367.3	1360.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P997788

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.56	15.42	15.54	16.43	17.76	17.63	18.50	18.62	19.50	20.83
	3H	16.02	16.80	17.01	17.81	19.16	20.22	21.01	21.22	22.02	23.37
	4H	16.49	17.24	17.50	18.26	19.61	21.48	22.22	22.48	23.24	24.59
	6H	16.78	17.47	17.79	18.49	19.86	22.77	23.46	23.79	24.48	25.85
	8H	16.84	17.50	17.86	18.53	19.90	23.43	24.09	24.45	25.13	26.49
	12H	16.85	17.48	17.88	18.51	19.90	24.16	24.79	25.19	25.82	27.21
4H	2H	15.61	16.35	16.62	17.37	18.73	17.96	18.71	18.97	19.72	21.08
	3H	17.32	17.95	18.34	18.99	20.36	20.75	21.39	21.78	22.43	23.80
	4H	17.94	18.52	18.97	19.56	20.95	22.17	22.75	23.20	23.79	25.18
	6H	18.35	18.86	19.39	19.92	21.31	23.64	24.15	24.68	25.20	26.59
	8H	18.46	18.94	19.50	19.99	21.39	24.40	24.87	25.44	25.92	27.33
	12H	18.51	18.94	19.56	20.00	21.41	25.23	25.66	26.28	26.72	28.13
8H	4H	18.73	19.20	19.77	20.26	21.66	22.32	22.79	23.35	23.84	25.25
	6H	19.36	19.76	20.42	20.85	22.25	23.95	24.34	25.01	25.44	26.84
	8H	19.58	19.94	20.65	21.01	22.43	24.84	25.19	25.90	26.27	27.68
	12H	19.72	20.03	20.79	21.10	22.56	25.83	26.14	26.90	27.22	28.68
12H	4H	18.93	19.36	19.99	20.43	21.84	22.29	22.72	23.35	23.79	25.20
	6H	19.70	20.05	20.77	21.13	22.55	23.97	24.32	25.04	25.40	26.82
	8H	20.00	20.31	21.08	21.39	22.85	24.90	25.21	25.97	26.29	27.74