

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997827

Luminaire Tested: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997827
REPORT IS A COMBINATION OF REPORTS P983562 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8568.0 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32
5	70	58	51	45	64	54	48	42	47	42	37	40	36	33	34	31	28
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31453	31453	31453	31453
5°	31529	33537	31650	26682
10°	31163	36611	31358	21997
15°	30407	38616	30830	18529
20°	29933	36257	29933	16106
25°	28978	31149	29111	14402
30°	27409	24486	27932	13045
35°	26018	16932	26453	11936
40°	24420	12783	24698	11051
45°	22449	10505	22816	10096
50°	20745	9220	20781	9242
55°	18802	7857	18924	8315
60°	16732	6563	16963	7257
65°	14877	5338	15148	6198
70°	13031	4187	13360	4999
75°	10936	3039	11361	3625
80°	8535	1926	9141	2151
85°	5608	969	6046	717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 32514 cd/sqm

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.3	2.2
10°-20°	550.9	6.4
20°-30°	799.5	9.3
30°-40°	842.8	9.8
40°-50°	745.8	8.7
50°-60°	595.5	7.0
60°-70°	404.5	4.7
70°-80°	207.0	2.4
80°-90°	52.8	0.6
90°-100°	234.0	2.7
100°-110°	824.0	9.6
110°-120°	865.4	10.1
120°-130°	712.0	8.3
130°-140°	572.0	6.7
140°-150°	432.0	5.0
150°-160°	303.7	3.5
160°-170°	178.8	2.1
170°-180°	58.2	0.7
0°-30°	1539.6	18.0
0°-40°	2382.4	27.8
0°-60°	3723.7	43.5
0°-90°	4387.9	51.2
90°-120°	1923.5	22.4
90°-150°	3639.5	42.5
90°-180°	4180.0	48.8
0°-180°	8568.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1987	1987	1987	1987	1987	
5°	1989	2219	1996	1766	1989	189
15°	1868	2728	1894	1309	1868	528
25°	1678	2273	1686	1051	1678	767
35°	1370	1237	1393	872	1370	857
45°	1028	745	1045	716	1028	797
55°	706	524	710	554	706	630
65°	418	322	426	374	418	416
75°	196	159	203	189	196	210
85°	40	41	43	30	40	46
90°	1	38	1	38	1	5
95°	40	132	40	132	40	42
105°	141	1301	141	1301	141	150
115°	248	1712	248	1712	248	246
125°	346	1389	346	1389	346	308
135°	406	1151	406	1151	406	314
145°	464	919	464	919	464	291
155°	528	772	528	772	528	243
165°	575	678	575	678	575	162
175°	599	611	599	611	599	57
180°	600	600	600	600	600	

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1997.7	2002.3	2009.9	2011.5	2026.7	2039.0	2052.7	2052.7	2057.3	2055.8	2043.5
5°	1988.6	2002.3	2022.2	2039.0	2066.5	2078.7	2097.0	2110.7	2123.0	2132.1	2130.6
7.5°	1973.3	1997.7	2026.7	2058.8	2095.5	2116.9	2142.8	2167.3	2184.1	2199.3	2210.0
10°	1947.3	1988.6	2028.3	2071.0	2118.4	2147.4	2177.9	2210.0	2236.0	2265.0	2292.5
12.5°	1912.2	1971.8	2020.6	2077.1	2135.2	2167.3	2216.1	2240.6	2291.0	2364.3	2384.1
15°	1867.9	1948.9	1994.7	2066.5	2142.8	2168.8	2236.0	2275.7	2379.6	2425.4	2480.4
17.5°	1826.7	1916.8	1977.9	2060.3	2135.2	2185.6	2251.3	2332.2	2419.3	2484.9	2546.0
20°	1793.1	1880.1	1953.4	2045.1	2139.8	2203.9	2272.6	2370.4	2465.1	2532.3	2579.6
22.5°	1716.7	1828.2	1913.7	2016.1	2130.6	2219.2	2284.9	2391.8	2494.1	2535.3	2576.6
25°	1678.5	1774.7	1874.0	1990.1	2124.5	2229.9	2286.4	2405.5	2495.6	2510.9	2520.1
27.5°	1608.3	1716.7	1832.8	1965.7	2123.0	2211.5	2283.3	2391.8	2463.6	2452.9	2425.4
30°	1521.2	1654.1	1782.4	1925.9	2101.6	2197.8	2265.0	2364.3	2400.9	2346.0	2297.1
32.5°	1457.1	1582.3	1724.3	1890.8	2077.1	2168.8	2234.5	2312.4	2320.0	2220.7	2138.2
35°	1370.0	1509.0	1669.4	1845.0	2035.9	2118.4	2179.5	2226.8	2190.2	2051.2	1953.4
37.5°	1292.1	1429.6	1600.6	1779.3	1979.4	2060.3	2109.2	2116.9	2026.7	1904.6	1761.0
40°	1206.6	1348.6	1527.3	1715.2	1916.8	1987.0	2017.6	1994.7	1864.8	1722.8	1556.3
42.5°	1121.0	1261.6	1454.0	1646.4	1837.4	1896.9	1909.1	1846.5	1687.7	1521.2	1328.8
45°	1027.9	1174.5	1366.9	1560.9	1745.7	1779.3	1780.8	1690.7	1502.9	1328.8	1150.1
47.5°	951.5	1087.4	1278.4	1472.3	1628.1	1651.0	1641.9	1538.0	1333.3	1137.8	982.1
50°	867.5	997.3	1186.7	1377.6	1510.5	1516.6	1493.7	1345.6	1145.5	966.8	843.1
52.5°	777.4	908.8	1082.9	1266.1	1385.3	1376.1	1331.8	1173.0	985.1	837.0	742.3
55°	705.6	821.7	985.1	1163.8	1247.8	1221.8	1173.0	1011.1	862.9	737.7	655.2
57.5°	626.2	728.5	888.9	1044.7	1093.6	1069.1	1020.2	869.0	731.6	636.9	581.9
60°	551.4	644.5	785.0	914.9	953.0	927.1	870.6	734.6	635.4	555.9	514.7
62.5°	482.6	563.6	681.2	800.3	815.6	789.6	740.7	630.8	545.3	482.6	452.1
65°	418.5	494.8	589.5	679.7	693.4	665.9	615.5	536.1	464.3	424.6	395.6
67.5°	355.9	417.0	501.0	566.6	574.3	548.3	507.1	442.9	398.6	355.9	334.5
70°	300.9	346.7	412.4	465.8	468.9	444.4	423.1	365.0	331.4	300.9	284.1
72.5°	247.4	279.5	329.9	369.6	371.1	355.9	336.0	299.4	270.3	249.0	232.2
75°	195.5	223.0	253.5	288.7	287.1	274.9	259.6	236.7	212.3	198.6	190.9
77.5°	149.7	166.5	190.9	213.8	213.8	207.7	198.6	181.8	166.5	152.7	145.1
80°	106.9	117.6	137.5	145.1	148.1	146.6	139.0	126.8	120.7	110.0	106.9
82.5°	68.7	76.4	85.5	93.2	97.7	94.7	93.2	87.1	77.9	74.8	71.8
85°	39.7	42.8	47.3	51.9	53.5	51.9	55.0	50.4	45.8	45.8	44.3
87.5°	16.8	18.3	21.4	21.4	22.9	22.9	21.4	22.9	22.9	21.4	19.9
90°	1.2	4.6	9.2	11.5	13.9	15.6	17.3	23.1	31.2	38.1	39.2
92.5°	17.3	24.2	33.5	39.2	48.5	54.8	61.2	92.3	136.2	175.5	177.8
95°	40.4	45.0	56.6	67.0	85.4	99.2	113.1	166.2	266.6	400.6	452.5
97.5°	60.0	67.0	79.6	94.7	115.4	131.0	146.6	214.7	354.4	570.2	737.6
100°	88.9	92.3	102.7	121.2	144.3	160.4	176.6	237.8	378.6	628.0	911.9
102.5°	115.4	117.7	128.1	146.6	170.8	187.0	203.2	258.6	379.8	606.0	917.7
105°	140.8	145.4	153.5	170.8	196.2	212.4	228.6	282.8	385.5	576.0	855.4
107.5°	168.5	172.0	180.1	196.2	221.6	237.8	254.0	307.0	398.2	559.8	797.6
110°	196.2	200.9	207.8	222.8	247.0	263.8	280.5	331.3	414.4	555.2	758.4

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	221.6	226.2	234.3	248.2	271.3	288.6	305.9	354.4	431.7	556.4	733.0
115°	248.2	254.0	260.9	274.7	297.8	313.4	329.0	378.6	449.0	561.0	715.7
117.5°	275.9	280.5	287.4	300.1	322.1	338.2	354.4	400.6	467.5	567.9	706.4
120°	301.3	305.9	312.8	323.2	346.3	362.5	378.6	423.6	486.0	574.9	698.4
122.5°	325.5	329.0	335.9	347.5	370.5	387.2	404.0	445.6	502.1	582.9	693.7
125°	346.3	349.8	356.7	370.5	393.6	409.8	425.9	467.5	519.4	591.0	688.0
127.5°	363.6	368.2	377.5	392.5	414.4	431.2	447.9	488.3	535.6	599.1	684.5
130°	378.6	383.2	394.8	410.9	434.0	450.2	466.3	506.7	550.6	608.3	682.2
132.5°	392.5	398.2	410.9	428.3	452.5	468.6	484.8	522.9	565.6	617.6	681.1
135°	406.3	410.9	424.8	442.1	468.7	484.8	501.0	537.9	578.3	624.5	679.9
137.5°	419.0	424.8	438.6	457.1	483.7	498.7	513.7	550.6	588.7	631.4	679.9
140°	434.0	438.6	452.5	471.0	496.4	511.4	526.4	561.0	596.8	636.0	678.7
142.5°	449.0	452.5	465.2	483.7	507.9	521.8	535.6	569.1	603.7	639.5	678.7
145°	464.0	468.7	480.2	497.5	520.6	533.3	546.0	577.2	609.5	641.8	676.4
147.5°	480.2	483.7	495.2	511.4	531.0	542.6	554.1	584.1	612.9	643.0	673.0
150°	496.4	499.8	509.1	524.1	541.4	551.8	562.2	588.7	615.3	641.8	669.5
152.5°	512.5	513.7	522.9	535.6	551.8	561.0	570.2	593.3	616.4	639.5	663.7
155°	527.5	528.7	535.6	548.3	561.0	569.6	578.3	597.9	617.6	637.2	656.8
157.5°	540.2	541.4	547.1	558.7	569.1	576.6	584.1	601.4	617.6	632.6	649.9
160°	552.9	554.1	558.7	567.9	577.2	583.6	589.9	603.7	617.6	629.1	643.0
162.5°	565.6	564.5	569.1	576.0	584.1	588.7	593.3	604.9	616.4	625.6	637.2
165°	574.9	573.7	576.0	582.9	588.7	592.2	595.6	606.0	614.1	621.0	629.1
167.5°	582.9	581.8	584.1	588.7	593.3	595.6	597.9	606.0	612.9	616.4	622.2
170°	591.0	588.7	589.9	593.3	595.6	597.4	599.1	604.9	610.6	612.9	616.4
172.5°	595.6	594.5	593.3	596.8	597.9	599.0	600.2	603.7	607.2	608.3	609.5
175°	599.1	597.9	596.8	599.1	599.1	599.7	600.2	602.6	604.9	603.7	604.9
177.5°	601.4	599.1	597.9	600.2	600.2	600.2	600.2	601.4	603.7	601.4	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	2064.9	2066.5	2069.5	2084.8	2092.4	2093.9	2087.8	2101.6	2106.2	2101.6	2098.5
5°	2162.7	2171.8	2190.2	2210.0	2208.5	2210.0	2219.2	2228.3	2231.4	2219.2	2223.8
7.5°	2248.2	2266.5	2286.4	2316.9	2316.9	2332.2	2338.3	2346.0	2364.3	2355.1	2352.1
10°	2346.0	2370.4	2407.0	2455.9	2457.4	2472.7	2488.0	2512.4	2520.1	2514.0	2517.0
12.5°	2468.1	2515.5	2518.5	2572.0	2596.4	2599.5	2623.9	2619.3	2634.6	2634.6	2660.6
15°	2521.6	2594.9	2636.1	2688.1	2703.3	2685.0	2704.9	2726.3	2727.8	2727.8	2726.3
17.5°	2617.8	2646.8	2688.1	2715.6	2721.7	2721.7	2723.2	2732.4	2726.3	2714.0	2723.2
20°	2637.7	2649.9	2665.2	2662.1	2665.2	2649.9	2634.6	2619.3	2620.9	2613.2	2636.1
22.5°	2601.0	2598.0	2562.8	2539.9	2539.9	2509.4	2480.4	2466.6	2452.9	2457.4	2465.1
25°	2509.4	2462.0	2419.3	2385.7	2378.0	2329.2	2289.4	2277.2	2254.3	2272.6	2275.7
27.5°	2362.8	2309.3	2240.6	2211.5	2171.8	2152.0	2124.5	2087.8	2040.5	2068.0	2063.4
30°	2205.4	2126.0	2069.5	1999.3	1936.6	1932.0	1880.1	1819.0	1794.6	1794.6	1808.3
32.5°	2029.8	1924.4	1841.9	1742.7	1681.6	1655.6	1593.0	1531.9	1545.6	1499.8	1516.6
35°	1825.1	1686.2	1582.3	1486.1	1440.3	1409.7	1328.8	1295.2	1258.5	1237.1	1276.8
37.5°	1629.6	1469.3	1336.4	1231.0	1214.2	1159.2	1104.2	1082.9	1061.5	1070.6	1069.1
40°	1391.4	1249.3	1130.2	1047.7	1018.7	992.8	956.1	930.1	916.4	924.0	925.6
42.5°	1176.0	1056.9	968.3	910.3	885.8	867.5	849.2	827.8	823.2	823.2	829.3
45°	1009.6	911.8	852.2	804.9	791.1	777.4	763.7	754.5	751.4	745.3	749.9
47.5°	876.7	798.8	762.1	727.0	711.7	708.7	696.5	691.9	685.8	684.2	685.8
50°	765.2	716.3	682.7	662.9	652.2	647.6	641.5	632.3	629.3	636.9	633.8
52.5°	687.3	641.5	623.1	603.3	597.2	591.1	581.9	583.4	581.9	578.9	578.9
55°	609.4	580.4	562.1	546.8	545.3	539.1	531.5	528.4	526.9	523.9	528.4
57.5°	546.8	523.9	507.1	493.3	487.2	487.2	479.6	473.5	473.5	471.9	473.5
60°	484.2	461.2	450.6	436.8	432.2	430.7	426.1	423.1	418.5	418.5	418.5
62.5°	426.1	407.8	395.6	383.4	384.9	377.2	371.1	368.1	368.1	369.6	369.6
65°	371.1	358.9	343.6	333.0	329.9	328.4	325.3	323.8	319.2	322.3	322.3
67.5°	320.7	303.9	294.8	290.2	285.6	284.1	281.0	278.0	276.4	274.9	278.0
70°	270.3	256.6	249.0	245.9	241.3	239.8	238.3	233.7	235.2	236.7	238.3
72.5°	224.5	212.3	210.8	201.6	201.6	201.6	195.5	198.6	197.0	194.0	197.0
75°	177.2	171.1	168.0	163.4	164.9	163.4	161.9	157.3	157.3	158.8	160.4
77.5°	140.5	134.4	132.9	128.3	125.2	128.3	125.2	123.7	123.7	125.2	125.2
80°	103.9	100.8	96.2	96.2	96.2	94.7	94.7	94.7	93.2	91.6	93.2
82.5°	68.7	68.7	67.2	65.7	67.2	64.1	65.7	65.7	65.7	65.7	65.7
85°	44.3	42.8	42.8	41.2	41.2	41.2	42.8	39.7	39.7	41.2	41.2
87.5°	19.9	19.9	19.9	21.4	19.9	19.9	19.9	21.4	19.9	19.9	19.9
90°	38.1	36.9	34.6	36.9	37.5	38.1	38.1	38.1	38.1	38.1	38.1
92.5°	148.9	116.6	99.3	86.6	81.9	77.3	76.2	71.6	72.7	70.4	72.7
95°	395.9	302.4	232.0	183.5	170.8	158.1	143.1	133.9	130.4	131.6	130.4
97.5°	743.4	618.7	494.1	377.5	342.8	308.2	263.2	240.1	227.4	220.5	227.4
100°	1078.1	1053.9	910.8	752.6	682.8	612.9	517.1	467.5	434.0	413.2	434.0
102.5°	1202.8	1339.0	1334.4	1229.4	1154.4	1079.3	973.1	879.6	835.7	805.7	835.7
105°	1162.4	1402.5	1532.9	1547.9	1528.9	1509.9	1438.3	1366.7	1317.1	1300.9	1317.1
107.5°	1077.0	1334.4	1528.3	1641.4	1664.5	1687.6	1686.5	1676.1	1661.1	1634.5	1661.1
110°	997.3	1240.9	1447.5	1595.3	1642.6	1689.9	1739.6	1761.5	1771.9	1770.7	1771.9

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	941.9	1155.5	1351.7	1512.2	1568.2	1624.1	1698.0	1738.4	1760.3	1768.4	1760.3
115°	898.1	1088.5	1266.3	1417.5	1477.0	1536.4	1618.4	1671.5	1701.5	1711.9	1701.5
117.5°	868.1	1033.1	1192.4	1333.2	1389.8	1446.4	1530.6	1587.2	1618.4	1626.4	1618.4
120°	845.0	993.9	1137.0	1259.4	1311.9	1364.4	1445.2	1499.5	1532.9	1544.5	1532.9
122.5°	825.3	962.7	1090.8	1205.1	1251.3	1297.5	1367.9	1421.0	1449.8	1459.1	1449.8
125°	806.9	932.7	1051.6	1153.2	1196.4	1239.7	1306.7	1350.6	1379.4	1388.7	1379.4
127.5°	789.6	902.7	1012.3	1109.3	1149.7	1190.1	1249.0	1290.5	1315.9	1322.9	1315.9
130°	772.2	873.8	973.1	1064.3	1102.4	1140.5	1197.0	1236.3	1259.4	1268.6	1259.4
132.5°	758.4	846.1	936.2	1018.1	1053.3	1088.5	1143.9	1183.2	1204.0	1212.0	1204.0
135°	745.7	820.7	896.9	973.1	1005.4	1037.7	1087.4	1125.5	1146.2	1150.9	1146.2
137.5°	736.5	799.9	865.7	928.1	957.0	985.8	1033.1	1066.6	1085.1	1092.0	1085.1
140°	728.4	780.3	835.7	888.8	914.2	939.6	976.6	1006.6	1023.9	1030.8	1023.9
142.5°	720.3	764.2	809.2	853.0	873.2	893.4	928.1	954.6	969.6	969.6	969.6
145°	713.4	749.2	787.2	823.0	839.8	856.5	884.2	903.8	915.4	918.8	915.4
147.5°	706.4	737.6	768.8	797.6	810.3	823.0	847.3	863.4	871.5	873.8	871.5
150°	697.2	724.9	750.3	774.6	785.0	795.3	812.6	826.5	833.4	834.6	833.4
152.5°	689.1	712.2	735.3	754.9	763.6	772.2	784.9	796.5	801.1	801.1	801.1
155°	678.7	700.7	719.1	736.5	742.8	749.2	761.9	769.9	774.6	772.2	774.6
157.5°	669.5	686.8	703.0	718.0	723.2	728.4	737.6	744.5	746.8	746.8	746.8
160°	659.1	674.1	686.8	699.5	703.6	707.6	715.7	721.5	722.6	722.6	722.6
162.5°	649.9	661.4	671.8	682.2	685.1	688.0	696.1	699.5	700.7	699.5	700.7
165°	639.5	648.7	656.8	664.9	667.2	669.5	674.1	678.7	678.7	677.6	678.7
167.5°	629.1	636.0	643.0	648.7	651.0	653.3	655.7	658.0	658.0	656.8	658.0
170°	621.0	626.8	630.3	634.9	636.0	637.2	638.3	641.8	640.6	638.3	640.6
172.5°	612.9	616.4	618.7	622.2	622.8	623.3	624.5	625.6	624.5	623.3	624.5
175°	606.0	609.5	610.6	611.8	612.3	612.9	612.9	614.1	612.9	610.6	612.9
177.5°	601.4	603.7	603.7	604.9	604.9	604.9	604.9	604.9	603.7	601.4	603.7
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	2106.2	2095.5	2086.3	2087.8	2095.5	2089.4	2074.1	2054.2	2046.6	2037.4	2046.6
5°	2232.9	2223.8	2205.4	2207.0	2202.4	2196.3	2171.8	2141.3	2141.3	2116.9	2113.8
7.5°	2358.2	2344.4	2332.2	2329.2	2312.4	2300.1	2278.7	2236.0	2219.2	2190.2	2173.4
10°	2498.7	2488.0	2474.2	2457.4	2448.3	2426.9	2391.8	2329.2	2298.6	2258.9	2229.9
12.5°	2640.7	2639.2	2608.6	2575.0	2573.5	2539.9	2515.5	2431.5	2390.2	2336.8	2268.1
15°	2730.8	2723.2	2706.4	2689.6	2694.2	2657.5	2602.5	2503.3	2475.8	2411.6	2338.3
17.5°	2729.3	2729.3	2724.7	2721.7	2717.1	2706.4	2675.9	2610.2	2565.9	2484.9	2416.2
20°	2642.2	2662.1	2666.7	2665.2	2680.4	2688.1	2686.5	2645.3	2610.2	2538.4	2468.1
22.5°	2468.1	2514.0	2533.8	2546.0	2578.1	2594.9	2634.6	2619.3	2610.2	2556.7	2497.2
25°	2306.2	2321.5	2381.1	2384.1	2428.4	2469.7	2509.4	2535.3	2568.9	2549.1	2498.7
27.5°	2097.0	2132.1	2174.9	2207.0	2216.1	2300.1	2365.8	2414.7	2491.0	2497.2	2480.4
30°	1860.3	1877.1	1947.3	1990.1	2039.0	2100.1	2194.7	2278.7	2347.5	2410.1	2431.5
32.5°	1571.6	1640.3	1681.6	1733.5	1776.3	1884.7	2000.8	2109.2	2188.6	2294.0	2339.8
35°	1307.4	1360.8	1431.1	1452.5	1530.4	1622.0	1773.2	1912.2	2032.9	2139.8	2232.9
37.5°	1089.0	1131.7	1206.6	1240.2	1286.0	1403.6	1530.4	1703.0	1848.0	1979.4	2095.5
40°	939.3	971.4	1027.9	1038.6	1076.8	1183.7	1286.0	1447.9	1640.3	1817.5	1944.3
42.5°	837.0	852.2	890.4	904.2	928.6	1000.4	1092.0	1244.8	1423.5	1606.7	1785.4
45°	763.7	774.3	797.3	809.5	840.0	872.1	946.9	1069.1	1209.6	1394.4	1586.9
47.5°	698.0	711.7	720.9	728.5	745.3	780.5	829.3	919.4	1053.8	1223.4	1409.7
50°	643.0	647.6	664.4	665.9	676.6	699.5	745.3	800.3	907.2	1044.7	1224.9
52.5°	588.0	592.6	603.3	614.0	618.6	636.9	667.4	713.3	792.7	901.1	1061.5
55°	533.0	539.1	549.8	557.5	562.1	577.3	595.7	639.9	702.6	778.9	910.3
57.5°	478.0	491.8	494.8	499.4	507.1	523.9	540.7	566.6	615.5	685.8	782.0
60°	426.1	430.7	441.4	446.0	453.6	462.8	484.2	504.0	539.1	594.1	681.2
62.5°	372.7	383.4	387.9	392.5	398.6	409.3	423.1	444.4	475.0	519.3	588.0
65°	326.8	328.4	337.5	343.6	349.8	357.4	371.1	391.0	409.3	450.6	501.0
67.5°	282.6	285.6	288.7	294.8	302.4	310.0	322.3	333.0	355.9	383.4	423.1
70°	239.8	239.8	247.4	252.0	250.5	259.6	268.8	281.0	297.8	323.8	355.9
72.5°	201.6	200.1	206.2	207.7	210.8	216.9	223.0	235.2	244.4	264.2	288.7
75°	160.4	163.4	166.5	166.5	171.1	175.6	181.8	187.9	198.6	210.8	229.1
77.5°	126.8	126.8	129.8	131.3	135.9	134.4	140.5	146.6	154.3	164.9	178.7
80°	93.2	96.2	96.2	96.2	97.7	99.3	105.4	110.0	114.5	122.2	128.3
82.5°	65.7	65.7	68.7	68.7	68.7	71.8	71.8	73.3	76.4	80.9	85.5
85°	41.2	41.2	41.2	42.8	41.2	42.8	45.8	44.3	45.8	48.9	48.9
87.5°	19.9	19.9	19.9	19.9	19.9	21.4	19.9	21.4	22.9	22.9	22.9
90°	38.1	38.1	38.1	37.5	36.9	34.6	36.9	38.1	39.2	38.1	31.2
92.5°	71.6	76.2	77.3	81.9	86.6	99.3	116.6	148.9	177.8	175.5	136.2
95°	133.9	143.1	158.1	170.8	183.5	232.0	302.4	395.9	452.5	400.6	266.6
97.5°	240.1	263.2	308.2	342.8	377.5	494.1	618.7	743.4	737.6	570.2	354.4
100°	467.5	517.1	612.9	682.8	752.6	910.8	1053.9	1078.1	911.9	628.0	378.6
102.5°	879.6	973.1	1079.3	1154.4	1229.4	1334.4	1339.0	1202.8	917.7	606.0	379.8
105°	1366.7	1438.3	1509.9	1528.9	1547.9	1532.9	1402.5	1162.4	855.4	576.0	385.5
107.5°	1676.1	1686.5	1687.6	1664.5	1641.4	1528.3	1334.4	1077.0	797.6	559.8	398.2
110°	1761.5	1739.6	1689.9	1642.6	1595.3	1447.5	1240.9	997.3	758.4	555.2	414.4

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1738.4	1698.0	1624.1	1568.2	1512.2	1351.7	1155.5	941.9	733.0	556.4	431.7
115°	1671.5	1618.4	1536.4	1477.0	1417.5	1266.3	1088.5	898.1	715.7	561.0	449.0
117.5°	1587.2	1530.6	1446.4	1389.8	1333.2	1192.4	1033.1	868.1	706.4	567.9	467.5
120°	1499.5	1445.2	1364.4	1311.9	1259.4	1137.0	993.9	845.0	698.4	574.9	486.0
122.5°	1421.0	1367.9	1297.5	1251.3	1205.1	1090.8	962.7	825.3	693.7	582.9	502.1
125°	1350.6	1306.7	1239.7	1196.4	1153.2	1051.6	932.7	806.9	688.0	591.0	519.4
127.5°	1290.5	1249.0	1190.1	1149.7	1109.3	1012.3	902.7	789.6	684.5	599.1	535.6
130°	1236.3	1197.0	1140.5	1102.4	1064.3	973.1	873.8	772.2	682.2	608.3	550.6
132.5°	1183.2	1143.9	1088.5	1053.3	1018.1	936.2	846.1	758.4	681.1	617.6	565.6
135°	1125.5	1087.4	1037.7	1005.4	973.1	896.9	820.7	745.7	679.9	624.5	578.3
137.5°	1066.6	1033.1	985.8	957.0	928.1	865.7	799.9	736.5	679.9	631.4	588.7
140°	1006.6	976.6	939.6	914.2	888.8	835.7	780.3	728.4	678.7	636.0	596.8
142.5°	954.6	928.1	893.4	873.2	853.0	809.2	764.2	720.3	678.7	639.5	603.7
145°	903.8	884.2	856.5	839.8	823.0	787.2	749.2	713.4	676.4	641.8	609.5
147.5°	863.4	847.3	823.0	810.3	797.6	768.8	737.6	706.4	673.0	643.0	612.9
150°	826.5	812.6	795.3	785.0	774.6	750.3	724.9	697.2	669.5	641.8	615.3
152.5°	796.5	784.9	772.2	763.6	754.9	735.3	712.2	689.1	663.7	639.5	616.4
155°	769.9	761.9	749.2	742.8	736.5	719.1	700.7	678.7	656.8	637.2	617.6
157.5°	744.5	737.6	728.4	723.2	718.0	703.0	686.8	669.5	649.9	632.6	617.6
160°	721.5	715.7	707.6	703.6	699.5	686.8	674.1	659.1	643.0	629.1	617.6
162.5°	699.5	696.1	688.0	685.1	682.2	671.8	661.4	649.9	637.2	625.6	616.4
165°	678.7	674.1	669.5	667.2	664.9	656.8	648.7	639.5	629.1	621.0	614.1
167.5°	658.0	655.7	653.3	651.0	648.7	643.0	636.0	629.1	622.2	616.4	612.9
170°	641.8	638.3	637.2	636.0	634.9	630.3	626.8	621.0	616.4	612.9	610.6
172.5°	625.6	624.5	623.3	622.8	622.2	618.7	616.4	612.9	609.5	608.3	607.2
175°	614.1	612.9	612.9	612.3	611.8	610.6	609.5	606.0	604.9	603.7	604.9
177.5°	604.9	604.9	604.9	604.9	604.9	603.7	603.7	601.4	600.2	601.4	603.7
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	2039.0	2031.3	2026.7	2029.8	2020.6	1997.7	1997.7	2005.4	1996.2	1987.0	1973.3
5°	2095.5	2080.2	2071.0	2069.5	2048.1	2011.5	2003.8	1996.2	1976.3	1955.0	1932.0
7.5°	2150.5	2123.0	2107.7	2097.0	2066.5	2019.1	1999.3	1982.5	1950.4	1918.3	1889.3
10°	2196.3	2156.6	2138.2	2121.4	2081.7	2022.2	1990.1	1959.5	1918.3	1877.1	1840.4
12.5°	2232.9	2187.1	2164.2	2139.8	2090.9	2013.0	1973.3	1924.4	1883.2	1828.2	1791.5
15°	2294.0	2199.3	2177.9	2155.0	2104.6	1997.7	1948.9	1893.9	1837.4	1764.0	1724.3
17.5°	2342.9	2216.1	2214.6	2165.7	2100.1	1991.6	1916.8	1845.0	1783.9	1710.6	1648.0
20°	2371.9	2242.1	2217.7	2167.3	2084.8	1950.4	1872.5	1793.1	1727.4	1638.8	1576.2
22.5°	2396.4	2278.7	2214.6	2153.5	2052.7	1936.6	1822.1	1747.2	1657.1	1560.9	1501.3
25°	2405.5	2286.4	2219.2	2148.9	2029.8	1896.9	1767.1	1686.2	1585.3	1498.3	1417.3
27.5°	2407.0	2284.9	2202.4	2129.1	1997.7	1845.0	1712.1	1626.6	1515.1	1414.3	1333.3
30°	2391.8	2268.1	2193.2	2113.8	1967.2	1797.6	1644.9	1550.2	1431.1	1330.3	1246.3
32.5°	2346.0	2234.5	2173.4	2086.3	1927.5	1732.0	1580.8	1475.4	1350.1	1250.9	1169.9
35°	2269.6	2193.2	2126.0	2045.1	1875.5	1670.9	1516.6	1392.9	1266.1	1171.4	1095.1
37.5°	2174.9	2133.7	2071.0	1991.6	1816.0	1615.9	1444.8	1307.4	1180.6	1089.0	1014.1
40°	2046.6	2057.3	1996.2	1924.4	1745.7	1541.1	1351.7	1220.3	1101.2	1015.7	942.4
42.5°	1907.6	1951.9	1916.8	1848.0	1667.8	1458.6	1282.9	1137.8	1021.8	933.2	872.1
45°	1757.9	1834.3	1812.9	1762.5	1586.9	1371.5	1185.2	1044.7	942.4	856.8	803.4
47.5°	1594.5	1703.0	1703.0	1666.3	1496.8	1284.5	1101.2	957.6	856.8	795.7	743.8
50°	1428.0	1550.2	1570.1	1545.6	1396.0	1185.2	998.9	869.0	782.0	722.4	684.2
52.5°	1253.9	1396.0	1432.6	1420.4	1289.1	1090.5	914.9	788.1	708.7	656.7	623.1
55°	1087.4	1252.4	1292.1	1296.7	1174.5	986.6	821.7	710.2	633.8	598.7	569.7
57.5°	930.1	1089.0	1133.3	1140.9	1058.4	892.0	734.6	636.9	568.2	539.1	516.2
60°	795.7	928.6	986.6	1003.4	931.7	782.0	653.7	559.0	507.1	479.6	458.2
62.5°	685.8	792.7	853.8	858.3	826.3	685.8	569.7	490.3	446.0	421.5	410.8
65°	578.9	675.1	711.7	730.1	704.1	594.1	491.8	426.1	391.0	369.6	358.9
67.5°	493.3	554.4	585.0	609.4	583.4	501.0	418.5	365.0	339.1	317.7	311.6
70°	404.7	455.1	478.0	502.5	479.6	417.0	357.4	308.5	285.6	268.8	261.2
72.5°	323.8	363.5	384.9	400.2	386.4	334.5	285.6	252.0	235.2	223.0	218.4
75°	256.6	284.1	296.3	307.0	300.9	261.2	230.6	203.1	187.9	177.2	174.1
77.5°	195.5	215.4	229.1	232.2	224.5	198.6	172.6	155.8	143.6	137.5	134.4
80°	139.0	151.2	158.8	163.4	155.8	145.1	126.8	114.5	103.9	96.2	94.7
82.5°	93.2	99.3	105.4	103.9	100.8	91.6	80.9	74.8	70.3	64.1	64.1
85°	53.5	55.0	58.0	59.6	58.0	51.9	45.8	42.8	39.7	35.1	35.1
87.5°	22.9	24.4	24.4	26.0	22.9	22.9	19.9	16.8	16.8	15.3	13.7
90°	23.1	17.3	15.6	13.9	11.5	9.2	4.6	1.2	4.6	9.2	11.5
92.5°	92.3	61.2	54.8	48.5	39.2	33.5	24.2	17.3	24.2	33.5	39.2
95°	166.2	113.1	99.2	85.4	67.0	56.6	45.0	40.4	45.0	56.6	67.0
97.5°	214.7	146.6	131.0	115.4	94.7	79.6	67.0	60.0	67.0	79.6	94.7
100°	237.8	176.6	160.4	144.3	121.2	102.7	92.3	88.9	92.3	102.7	121.2
102.5°	258.6	203.2	187.0	170.8	146.6	128.1	117.7	115.4	117.7	128.1	146.6
105°	282.8	228.6	212.4	196.2	170.8	153.5	145.4	140.8	145.4	153.5	170.8
107.5°	307.0	254.0	237.8	221.6	196.2	180.1	172.0	168.5	172.0	180.1	196.2
110°	331.3	280.5	263.8	247.0	222.8	207.8	200.9	196.2	200.9	207.8	222.8

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	354.4	305.9	288.6	271.3	248.2	234.3	226.2	221.6	226.2	234.3	248.2
115°	378.6	329.0	313.4	297.8	274.7	260.9	254.0	248.2	254.0	260.9	274.7
117.5°	400.6	354.4	338.2	322.1	300.1	287.4	280.5	275.9	280.5	287.4	300.1
120°	423.6	378.6	362.5	346.3	323.2	312.8	305.9	301.3	305.9	312.8	323.2
122.5°	445.6	404.0	387.2	370.5	347.5	335.9	329.0	325.5	329.0	335.9	347.5
125°	467.5	425.9	409.8	393.6	370.5	356.7	349.8	346.3	349.8	356.7	370.5
127.5°	488.3	447.9	431.2	414.4	392.5	377.5	368.2	363.6	368.2	377.5	392.5
130°	506.7	466.3	450.2	434.0	410.9	394.8	383.2	378.6	383.2	394.8	410.9
132.5°	522.9	484.8	468.6	452.5	428.3	410.9	398.2	392.5	398.2	410.9	428.3
135°	537.9	501.0	484.8	468.7	442.1	424.8	410.9	406.3	410.9	424.8	442.1
137.5°	550.6	513.7	498.7	483.7	457.1	438.6	424.8	419.0	424.8	438.6	457.1
140°	561.0	526.4	511.4	496.4	471.0	452.5	438.6	434.0	438.6	452.5	471.0
142.5°	569.1	535.6	521.8	507.9	483.7	465.2	452.5	449.0	452.5	465.2	483.7
145°	577.2	546.0	533.3	520.6	497.5	480.2	468.7	464.0	468.7	480.2	497.5
147.5°	584.1	554.1	542.6	531.0	511.4	495.2	483.7	480.2	483.7	495.2	511.4
150°	588.7	562.2	551.8	541.4	524.1	509.1	499.8	496.4	499.8	509.1	524.1
152.5°	593.3	570.2	561.0	551.8	535.6	522.9	513.7	512.5	513.7	522.9	535.6
155°	597.9	578.3	569.6	561.0	548.3	535.6	528.7	527.5	528.7	535.6	548.3
157.5°	601.4	584.1	576.6	569.1	558.7	547.1	541.4	540.2	541.4	547.1	558.7
160°	603.7	589.9	583.6	577.2	567.9	558.7	554.1	552.9	554.1	558.7	567.9
162.5°	604.9	593.3	588.7	584.1	576.0	569.1	564.5	565.6	564.5	569.1	576.0
165°	606.0	595.6	592.2	588.7	582.9	576.0	573.7	574.9	573.7	576.0	582.9
167.5°	606.0	597.9	595.6	593.3	588.7	584.1	581.8	582.9	581.8	584.1	588.7
170°	604.9	599.1	597.4	595.6	593.3	589.9	588.7	591.0	588.7	589.9	593.3
172.5°	603.7	600.2	599.0	597.9	596.8	593.3	594.5	595.6	594.5	593.3	596.8
175°	602.6	600.2	599.7	599.1	599.1	596.8	597.9	599.1	597.9	596.8	599.1
177.5°	601.4	600.2	600.2	600.2	600.2	597.9	599.1	601.4	599.1	597.9	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1965.7	1973.3	1971.8	1956.5	1939.7	1925.9	1900.0	1903.0	1893.9	1895.4	1904.6
5°	1916.8	1916.8	1910.7	1889.3	1861.8	1846.5	1817.5	1809.9	1791.5	1790.0	1788.5
7.5°	1864.8	1857.2	1849.6	1819.0	1785.4	1761.0	1721.3	1712.1	1693.8	1681.6	1675.5
10°	1803.8	1793.1	1777.8	1742.7	1701.4	1670.9	1629.6	1617.4	1582.3	1567.0	1557.9
12.5°	1736.6	1730.4	1706.0	1677.0	1609.8	1576.2	1516.6	1528.8	1493.7	1463.2	1458.6
15°	1669.4	1646.4	1632.7	1585.3	1504.4	1489.1	1441.8	1417.3	1385.3	1360.8	1360.8
17.5°	1603.7	1568.5	1538.0	1487.6	1428.0	1385.3	1350.1	1337.9	1298.2	1273.8	1269.2
20°	1516.6	1476.9	1469.3	1397.5	1356.3	1308.9	1275.3	1244.8	1215.7	1205.0	1197.4
22.5°	1434.1	1388.3	1376.1	1315.0	1273.8	1226.4	1192.8	1171.4	1150.1	1142.4	1128.7
25°	1345.6	1318.1	1299.7	1234.1	1188.2	1144.0	1121.0	1105.8	1085.9	1084.4	1075.2
27.5°	1260.0	1234.1	1215.7	1153.1	1119.5	1078.3	1060.0	1043.2	1032.5	1027.9	1023.3
30°	1186.7	1157.7	1136.3	1090.5	1049.3	1015.7	1000.4	989.7	983.6	976.0	974.4
32.5°	1105.8	1089.0	1060.0	1024.8	992.8	960.7	951.5	943.9	934.7	931.7	930.1
35°	1037.0	1014.1	995.8	956.1	942.4	914.9	904.2	898.1	885.8	882.8	879.7
37.5°	969.8	948.5	928.6	904.2	878.2	862.9	856.8	847.7	841.5	843.1	840.0
40°	902.6	885.8	870.6	844.6	829.3	821.7	809.5	800.3	797.3	798.8	797.3
42.5°	837.0	821.7	812.5	792.7	777.4	769.8	762.1	753.0	757.5	757.5	762.1
45°	777.4	763.7	757.5	742.3	733.1	720.9	713.3	711.7	717.8	716.3	716.3
47.5°	716.3	711.7	704.1	690.3	678.1	670.5	669.0	669.0	675.1	678.1	676.6
50°	669.0	659.8	650.6	639.9	630.8	627.7	623.1	626.2	632.3	632.3	635.4
52.5°	609.4	603.3	600.2	591.1	585.0	585.0	585.0	586.5	591.1	595.7	594.1
55°	557.5	552.9	549.8	545.3	537.6	539.1	537.6	540.7	545.3	549.8	552.9
57.5°	502.5	501.0	497.9	490.3	490.3	488.7	493.3	494.8	502.5	505.5	510.1
60°	453.6	449.0	449.0	442.9	442.9	442.9	447.5	452.1	458.2	459.7	462.8
62.5°	401.7	401.7	400.2	395.6	395.6	400.2	401.7	407.8	410.8	410.8	415.4
65°	352.8	351.3	349.8	351.3	352.8	352.8	357.4	360.4	363.5	365.0	366.6
67.5°	303.9	302.4	305.5	303.9	307.0	313.1	311.6	316.2	320.7	320.7	322.3
70°	258.1	261.2	259.6	262.7	261.2	264.2	268.8	270.3	270.3	271.9	276.4
72.5°	215.4	215.4	215.4	213.8	215.4	218.4	221.5	223.0	226.0	227.6	232.2
75°	174.1	174.1	171.1	174.1	174.1	177.2	180.2	180.2	180.2	183.3	187.9
77.5°	131.3	132.9	131.3	134.4	134.4	135.9	139.0	137.5	140.5	142.0	143.6
80°	96.2	94.7	94.7	94.7	96.2	96.2	99.3	100.8	100.8	105.4	102.3
82.5°	61.1	62.6	61.1	62.6	62.6	64.1	62.6	64.1	65.7	68.7	67.2
85°	35.1	33.6	33.6	35.1	33.6	33.6	35.1	33.6	35.1	33.6	35.1
87.5°	13.7	12.2	12.2	12.2	12.2	10.7	10.7	9.2	9.2	9.2	7.6
90°	13.9	15.6	17.3	23.1	31.2	38.1	39.2	38.1	36.9	34.6	36.9
92.5°	48.5	54.8	61.2	92.3	136.2	175.5	177.8	148.9	116.6	99.3	86.6
95°	85.4	99.2	113.1	166.2	266.6	400.6	452.5	395.9	302.4	232.0	183.5
97.5°	115.4	131.0	146.6	214.7	354.4	570.2	737.6	743.4	618.7	494.1	377.5
100°	144.3	160.4	176.6	237.8	378.6	628.0	911.9	1078.1	1053.9	910.8	752.6
102.5°	170.8	187.0	203.2	258.6	379.8	606.0	917.7	1202.8	1339.0	1334.4	1229.4
105°	196.2	212.4	228.6	282.8	385.5	576.0	855.4	1162.4	1402.5	1532.9	1547.9
107.5°	221.6	237.8	254.0	307.0	398.2	559.8	797.6	1077.0	1334.4	1528.3	1641.4
110°	247.0	263.8	280.5	331.3	414.4	555.2	758.4	997.3	1240.9	1447.5	1595.3

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	271.3	288.6	305.9	354.4	431.7	556.4	733.0	941.9	1155.5	1351.7	1512.2
115°	297.8	313.4	329.0	378.6	449.0	561.0	715.7	898.1	1088.5	1266.3	1417.5
117.5°	322.1	338.2	354.4	400.6	467.5	567.9	706.4	868.1	1033.1	1192.4	1333.2
120°	346.3	362.5	378.6	423.6	486.0	574.9	698.4	845.0	993.9	1137.0	1259.4
122.5°	370.5	387.2	404.0	445.6	502.1	582.9	693.7	825.3	962.7	1090.8	1205.1
125°	393.6	409.8	425.9	467.5	519.4	591.0	688.0	806.9	932.7	1051.6	1153.2
127.5°	414.4	431.2	447.9	488.3	535.6	599.1	684.5	789.6	902.7	1012.3	1109.3
130°	434.0	450.2	466.3	506.7	550.6	608.3	682.2	772.2	873.8	973.1	1064.3
132.5°	452.5	468.6	484.8	522.9	565.6	617.6	681.1	758.4	846.1	936.2	1018.1
135°	468.7	484.8	501.0	537.9	578.3	624.5	679.9	745.7	820.7	896.9	973.1
137.5°	483.7	498.7	513.7	550.6	588.7	631.4	679.9	736.5	799.9	865.7	928.1
140°	496.4	511.4	526.4	561.0	596.8	636.0	678.7	728.4	780.3	835.7	888.8
142.5°	507.9	521.8	535.6	569.1	603.7	639.5	678.7	720.3	764.2	809.2	853.0
145°	520.6	533.3	546.0	577.2	609.5	641.8	676.4	713.4	749.2	787.2	823.0
147.5°	531.0	542.6	554.1	584.1	612.9	643.0	673.0	706.4	737.6	768.8	797.6
150°	541.4	551.8	562.2	588.7	615.3	641.8	669.5	697.2	724.9	750.3	774.6
152.5°	551.8	561.0	570.2	593.3	616.4	639.5	663.7	689.1	712.2	735.3	754.9
155°	561.0	569.6	578.3	597.9	617.6	637.2	656.8	678.7	700.7	719.1	736.5
157.5°	569.1	576.6	584.1	601.4	617.6	632.6	649.9	669.5	686.8	703.0	718.0
160°	577.2	583.6	589.9	603.7	617.6	629.1	643.0	659.1	674.1	686.8	699.5
162.5°	584.1	588.7	593.3	604.9	616.4	625.6	637.2	649.9	661.4	671.8	682.2
165°	588.7	592.2	595.6	606.0	614.1	621.0	629.1	639.5	648.7	656.8	664.9
167.5°	593.3	595.6	597.9	606.0	612.9	616.4	622.2	629.1	636.0	643.0	648.7
170°	595.6	597.4	599.1	604.9	610.6	612.9	616.4	621.0	626.8	630.3	634.9
172.5°	597.9	599.0	600.2	603.7	607.2	608.3	609.5	612.9	616.4	618.7	622.2
175°	599.1	599.7	600.2	602.6	604.9	603.7	604.9	606.0	609.5	610.6	611.8
177.5°	600.2	600.2	600.2	601.4	603.7	601.4	600.2	601.4	603.7	603.7	604.9
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1893.9	1898.4	1887.8	1884.7	1887.8	1877.1	1880.1	1883.2	1883.2	1887.8	1890.8
5°	1783.9	1777.8	1767.1	1764.0	1761.0	1765.6	1762.5	1767.1	1768.6	1779.3	1780.8
7.5°	1675.5	1666.3	1657.1	1648.0	1644.9	1637.3	1644.9	1644.9	1655.6	1652.6	1660.2
10°	1547.2	1545.6	1533.4	1528.8	1522.7	1510.5	1527.3	1522.7	1530.4	1544.1	1547.2
12.5°	1452.5	1435.7	1443.3	1421.9	1429.6	1417.3	1418.9	1418.9	1431.1	1432.6	1429.6
15°	1362.4	1348.6	1328.8	1319.6	1315.0	1308.9	1328.8	1330.3	1321.1	1342.5	1334.9
17.5°	1270.7	1270.7	1252.4	1247.8	1235.6	1241.7	1238.7	1240.2	1237.1	1252.4	1260.0
20°	1191.3	1183.7	1177.6	1179.1	1163.8	1160.8	1157.7	1160.8	1171.4	1182.1	1185.2
22.5°	1127.2	1122.6	1107.3	1110.4	1098.1	1102.7	1099.7	1107.3	1108.8	1108.8	1119.5
25°	1066.1	1060.0	1061.5	1055.4	1050.8	1050.8	1046.2	1050.8	1056.9	1060.0	1061.5
27.5°	1020.2	1015.7	1008.0	1003.4	1006.5	998.9	1005.0	1009.6	1009.6	1006.5	1009.6
30°	965.3	968.3	968.3	953.0	959.2	956.1	960.7	963.7	963.7	965.3	962.2
32.5°	928.6	919.4	917.9	916.4	916.4	910.3	910.3	914.9	916.4	917.9	922.5
35°	879.7	879.7	872.1	876.7	870.6	872.1	870.6	872.1	875.1	870.6	875.1
37.5°	835.4	837.0	833.9	837.0	838.5	835.4	832.4	838.5	835.4	835.4	832.4
40°	797.3	795.7	797.3	797.3	797.3	798.8	795.7	795.7	795.7	792.7	789.6
42.5°	765.2	756.0	759.1	760.6	756.0	756.0	757.5	756.0	760.6	751.4	751.4
45°	719.4	716.3	717.8	717.8	720.9	716.3	719.4	720.9	716.3	714.8	711.7
47.5°	678.1	681.2	678.1	681.2	681.2	684.2	678.1	679.7	681.2	675.1	670.5
50°	636.9	636.9	641.5	639.9	641.5	638.4	638.4	636.9	638.4	635.4	630.8
52.5°	598.7	594.1	601.8	600.2	598.7	597.2	595.7	597.2	594.1	591.1	591.1
55°	551.4	551.4	555.9	557.5	557.5	554.4	551.4	552.9	551.4	549.8	548.3
57.5°	513.2	507.1	510.1	511.6	511.6	507.1	510.1	507.1	507.1	508.6	504.0
60°	464.3	464.3	461.2	465.8	465.8	462.8	462.8	464.3	461.2	459.7	458.2
62.5°	412.4	413.9	418.5	420.0	421.5	418.5	415.4	417.0	417.0	412.4	413.9
65°	368.1	371.1	377.2	375.7	372.7	374.2	371.1	372.7	368.1	369.6	365.0
67.5°	325.3	323.8	325.3	325.3	328.4	326.8	323.8	323.8	322.3	326.8	322.3
70°	279.5	279.5	279.5	279.5	281.0	282.6	279.5	276.4	278.0	274.9	273.4
72.5°	232.2	233.7	232.2	235.2	230.6	233.7	233.7	232.2	230.6	230.6	230.6
75°	187.9	190.9	186.3	187.9	186.3	189.4	187.9	187.9	184.8	183.3	184.8
77.5°	143.6	145.1	142.0	143.6	142.0	143.6	143.6	142.0	142.0	142.0	142.0
80°	102.3	103.9	102.3	100.8	99.3	102.3	99.3	100.8	102.3	100.8	103.9
82.5°	65.7	65.7	64.1	65.7	62.6	62.6	64.1	64.1	62.6	65.7	62.6
85°	32.1	32.1	35.1	32.1	30.5	30.5	30.5	32.1	30.5	33.6	32.1
87.5°	7.6	6.1	7.6	7.6	6.1	6.1	7.6	6.1	7.6	9.2	6.1
90°	37.5	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	37.5
92.5°	81.9	77.3	76.2	71.6	72.7	70.4	72.7	71.6	76.2	77.3	81.9
95°	170.8	158.1	143.1	133.9	130.4	131.6	130.4	133.9	143.1	158.1	170.8
97.5°	342.8	308.2	263.2	240.1	227.4	220.5	227.4	240.1	263.2	308.2	342.8
100°	682.8	612.9	517.1	467.5	434.0	413.2	434.0	467.5	517.1	612.9	682.8
102.5°	1154.4	1079.3	973.1	879.6	835.7	805.7	835.7	879.6	973.1	1079.3	1154.4
105°	1528.9	1509.9	1438.3	1366.7	1317.1	1300.9	1317.1	1366.7	1438.3	1509.9	1528.9
107.5°	1664.5	1687.6	1686.5	1676.1	1661.1	1634.5	1661.1	1676.1	1686.5	1687.6	1664.5
110°	1642.6	1689.9	1739.6	1761.5	1771.9	1770.7	1771.9	1761.5	1739.6	1689.9	1642.6

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1568.2	1624.1	1698.0	1738.4	1760.3	1768.4	1760.3	1738.4	1698.0	1624.1	1568.2
115°	1477.0	1536.4	1618.4	1671.5	1701.5	1711.9	1701.5	1671.5	1618.4	1536.4	1477.0
117.5°	1389.8	1446.4	1530.6	1587.2	1618.4	1626.4	1618.4	1587.2	1530.6	1446.4	1389.8
120°	1311.9	1364.4	1445.2	1499.5	1532.9	1544.5	1532.9	1499.5	1445.2	1364.4	1311.9
122.5°	1251.3	1297.5	1367.9	1421.0	1449.8	1459.1	1449.8	1421.0	1367.9	1297.5	1251.3
125°	1196.4	1239.7	1306.7	1350.6	1379.4	1388.7	1379.4	1350.6	1306.7	1239.7	1196.4
127.5°	1149.7	1190.1	1249.0	1290.5	1315.9	1322.9	1315.9	1290.5	1249.0	1190.1	1149.7
130°	1102.4	1140.5	1197.0	1236.3	1259.4	1268.6	1259.4	1236.3	1197.0	1140.5	1102.4
132.5°	1053.3	1088.5	1143.9	1183.2	1204.0	1212.0	1204.0	1183.2	1143.9	1088.5	1053.3
135°	1005.4	1037.7	1087.4	1125.5	1146.2	1150.9	1146.2	1125.5	1087.4	1037.7	1005.4
137.5°	957.0	985.8	1033.1	1066.6	1085.1	1092.0	1085.1	1066.6	1033.1	985.8	957.0
140°	914.2	939.6	976.6	1006.6	1023.9	1030.8	1023.9	1006.6	976.6	939.6	914.2
142.5°	873.2	893.4	928.1	954.6	969.6	969.6	969.6	954.6	928.1	893.4	873.2
145°	839.8	856.5	884.2	903.8	915.4	918.8	915.4	903.8	884.2	856.5	839.8
147.5°	810.3	823.0	847.3	863.4	871.5	873.8	871.5	863.4	847.3	823.0	810.3
150°	785.0	795.3	812.6	826.5	833.4	834.6	833.4	826.5	812.6	795.3	785.0
152.5°	763.6	772.2	784.9	796.5	801.1	801.1	801.1	796.5	784.9	772.2	763.6
155°	742.8	749.2	761.9	769.9	774.6	772.2	774.6	769.9	761.9	749.2	742.8
157.5°	723.2	728.4	737.6	744.5	746.8	746.8	746.8	744.5	737.6	728.4	723.2
160°	703.6	707.6	715.7	721.5	722.6	722.6	722.6	721.5	715.7	707.6	703.6
162.5°	685.1	688.0	696.1	699.5	700.7	699.5	700.7	699.5	696.1	688.0	685.1
165°	667.2	669.5	674.1	678.7	678.7	677.6	678.7	678.7	674.1	669.5	667.2
167.5°	651.0	653.3	655.7	658.0	658.0	656.8	658.0	658.0	655.7	653.3	651.0
170°	636.0	637.2	638.3	641.8	640.6	638.3	640.6	641.8	638.3	637.2	636.0
172.5°	622.8	623.3	624.5	625.6	624.5	623.3	624.5	625.6	624.5	623.3	622.8
175°	612.3	612.9	612.9	614.1	612.9	610.6	612.9	614.1	612.9	612.9	612.3
177.5°	604.9	604.9	604.9	604.9	603.7	601.4	603.7	604.9	604.9	604.9	604.9
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1886.2	1898.4	1893.9	1877.1	1896.9	1896.9	1910.7	1910.7	1927.5	1933.6	1942.7
5°	1779.3	1788.5	1796.1	1788.5	1802.2	1823.6	1835.8	1846.5	1869.4	1878.6	1892.3
7.5°	1664.8	1681.6	1689.2	1689.2	1712.1	1736.6	1761.0	1776.3	1808.3	1820.6	1834.3
10°	1553.3	1573.1	1588.4	1586.9	1625.1	1640.3	1670.9	1706.0	1738.1	1756.4	1776.3
12.5°	1435.7	1446.4	1467.7	1498.3	1507.5	1534.9	1570.1	1614.4	1672.4	1689.2	1718.2
15°	1337.9	1366.9	1383.7	1397.5	1418.9	1444.8	1483.0	1525.8	1583.8	1620.5	1651.0
17.5°	1255.5	1293.6	1304.3	1301.3	1328.8	1368.5	1412.8	1444.8	1496.8	1541.1	1570.1
20°	1188.2	1203.5	1221.8	1229.5	1250.9	1293.6	1336.4	1373.1	1415.8	1450.9	1484.5
22.5°	1121.0	1133.3	1148.5	1162.3	1179.1	1203.5	1244.8	1290.6	1331.8	1365.4	1403.6
25°	1066.1	1073.7	1087.4	1098.1	1116.5	1133.3	1162.3	1212.7	1261.6	1281.4	1315.0
27.5°	1012.6	1018.7	1027.9	1040.1	1049.3	1066.1	1092.0	1133.3	1183.7	1203.5	1249.3
30°	965.3	969.8	979.0	985.1	989.7	1009.6	1029.4	1061.5	1099.7	1127.2	1160.8
32.5°	921.0	925.6	934.7	936.2	942.4	953.0	971.4	1000.4	1034.0	1056.9	1085.9
35°	872.1	875.1	884.3	887.4	892.0	901.1	914.9	936.2	966.8	983.6	1009.6
37.5°	833.9	832.4	838.5	843.1	849.2	853.8	858.3	879.7	902.6	917.9	937.8
40°	792.7	789.6	791.1	797.3	800.3	806.4	806.4	827.8	843.1	855.3	870.6
42.5°	751.4	749.9	746.9	749.9	753.0	754.5	756.0	771.3	786.6	797.3	814.1
45°	710.2	708.7	705.6	707.1	707.1	710.2	714.8	720.9	731.6	740.7	749.9
47.5°	672.0	669.0	664.4	662.9	665.9	665.9	665.9	672.0	682.7	685.8	694.9
50°	632.3	627.7	621.6	618.6	618.6	617.0	620.1	621.6	630.8	633.8	641.5
52.5°	589.5	586.5	580.4	574.3	575.8	572.7	574.3	575.8	578.9	583.4	588.0
55°	546.8	540.7	536.1	534.6	530.0	530.0	525.4	531.5	530.0	531.5	537.6
57.5°	505.5	499.4	491.8	488.7	484.2	482.6	479.6	478.0	479.6	484.2	488.7
60°	456.7	453.6	449.0	444.4	441.4	436.8	433.8	433.8	432.2	432.2	433.8
62.5°	409.3	407.8	401.7	400.2	397.1	394.0	389.5	386.4	386.4	389.5	391.0
65°	363.5	362.0	357.4	355.9	348.2	345.2	343.6	342.1	339.1	339.1	339.1
67.5°	320.7	316.2	316.2	308.5	302.4	299.4	296.3	294.8	294.8	294.8	296.3
70°	273.4	273.4	268.8	264.2	258.1	259.6	255.1	250.5	250.5	247.4	249.0
72.5°	227.6	226.0	221.5	219.9	215.4	210.8	207.7	210.8	206.2	204.7	206.2
75°	183.3	181.8	178.7	175.6	177.2	172.6	168.0	166.5	166.5	163.4	163.4
77.5°	140.5	143.6	137.5	135.9	132.9	129.8	128.3	126.8	126.8	126.8	129.8
80°	97.7	99.3	99.3	96.2	97.7	93.2	93.2	93.2	88.6	90.1	91.6
82.5°	62.6	62.6	61.1	62.6	61.1	61.1	59.6	59.6	58.0	58.0	59.6
85°	35.1	33.6	32.1	35.1	33.6	33.6	32.1	32.1	32.1	32.1	32.1
87.5°	7.6	9.2	9.2	9.2	9.2	10.7	10.7	10.7	12.2	12.2	12.2
90°	36.9	34.6	36.9	38.1	39.2	38.1	31.2	23.1	17.3	15.6	13.9
92.5°	86.6	99.3	116.6	148.9	177.8	175.5	136.2	92.3	61.2	54.8	48.5
95°	183.5	232.0	302.4	395.9	452.5	400.6	266.6	166.2	113.1	99.2	85.4
97.5°	377.5	494.1	618.7	743.4	737.6	570.2	354.4	214.7	146.6	131.0	115.4
100°	752.6	910.8	1053.9	1078.1	911.9	628.0	378.6	237.8	176.6	160.4	144.3
102.5°	1229.4	1334.4	1339.0	1202.8	917.7	606.0	379.8	258.6	203.2	187.0	170.8
105°	1547.9	1532.9	1402.5	1162.4	855.4	576.0	385.5	282.8	228.6	212.4	196.2
107.5°	1641.4	1528.3	1334.4	1077.0	797.6	559.8	398.2	307.0	254.0	237.8	221.6
110°	1595.3	1447.5	1240.9	997.3	758.4	555.2	414.4	331.3	280.5	263.8	247.0

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1512.2	1351.7	1155.5	941.9	733.0	556.4	431.7	354.4	305.9	288.6	271.3
115°	1417.5	1266.3	1088.5	898.1	715.7	561.0	449.0	378.6	329.0	313.4	297.8
117.5°	1333.2	1192.4	1033.1	868.1	706.4	567.9	467.5	400.6	354.4	338.2	322.1
120°	1259.4	1137.0	993.9	845.0	698.4	574.9	486.0	423.6	378.6	362.5	346.3
122.5°	1205.1	1090.8	962.7	825.3	693.7	582.9	502.1	445.6	404.0	387.2	370.5
125°	1153.2	1051.6	932.7	806.9	688.0	591.0	519.4	467.5	425.9	409.8	393.6
127.5°	1109.3	1012.3	902.7	789.6	684.5	599.1	535.6	488.3	447.9	431.2	414.4
130°	1064.3	973.1	873.8	772.2	682.2	608.3	550.6	506.7	466.3	450.2	434.0
132.5°	1018.1	936.2	846.1	758.4	681.1	617.6	565.6	522.9	484.8	468.6	452.5
135°	973.1	896.9	820.7	745.7	679.9	624.5	578.3	537.9	501.0	484.8	468.7
137.5°	928.1	865.7	799.9	736.5	679.9	631.4	588.7	550.6	513.7	498.7	483.7
140°	888.8	835.7	780.3	728.4	678.7	636.0	596.8	561.0	526.4	511.4	496.4
142.5°	853.0	809.2	764.2	720.3	678.7	639.5	603.7	569.1	535.6	521.8	507.9
145°	823.0	787.2	749.2	713.4	676.4	641.8	609.5	577.2	546.0	533.3	520.6
147.5°	797.6	768.8	737.6	706.4	673.0	643.0	612.9	584.1	554.1	542.6	531.0
150°	774.6	750.3	724.9	697.2	669.5	641.8	615.3	588.7	562.2	551.8	541.4
152.5°	754.9	735.3	712.2	689.1	663.7	639.5	616.4	593.3	570.2	561.0	551.8
155°	736.5	719.1	700.7	678.7	656.8	637.2	617.6	597.9	578.3	569.6	561.0
157.5°	718.0	703.0	686.8	669.5	649.9	632.6	617.6	601.4	584.1	576.6	569.1
160°	699.5	686.8	674.1	659.1	643.0	629.1	617.6	603.7	589.9	583.6	577.2
162.5°	682.2	671.8	661.4	649.9	637.2	625.6	616.4	604.9	593.3	588.7	584.1
165°	664.9	656.8	648.7	639.5	629.1	621.0	614.1	606.0	595.6	592.2	588.7
167.5°	648.7	643.0	636.0	629.1	622.2	616.4	612.9	606.0	597.9	595.6	593.3
170°	634.9	630.3	626.8	621.0	616.4	612.9	610.6	604.9	599.1	597.4	595.6
172.5°	622.2	618.7	616.4	612.9	609.5	608.3	607.2	603.7	600.2	599.0	597.9
175°	611.8	610.6	609.5	606.0	604.9	603.7	604.9	602.6	600.2	599.7	599.1
177.5°	604.9	603.7	603.7	601.4	600.2	601.4	603.7	601.4	600.2	600.2	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1987.0	1987.0	1987.0	1987.0
2.5°	1950.4	1950.4	1973.3	1997.7
5°	1907.6	1918.3	1955.0	1988.6
7.5°	1866.4	1884.7	1930.5	1973.3
10°	1816.0	1840.4	1896.9	1947.3
12.5°	1767.1	1790.0	1855.7	1912.2
15°	1698.4	1727.4	1797.6	1867.9
17.5°	1629.6	1658.7	1744.2	1826.7
20°	1548.7	1586.9	1683.1	1793.1
22.5°	1473.9	1521.2	1628.1	1716.7
25°	1391.4	1464.7	1564.0	1678.5
27.5°	1318.1	1391.4	1492.2	1608.3
30°	1235.6	1310.4	1414.3	1521.2
32.5°	1156.2	1224.9	1325.7	1457.1
35°	1073.7	1139.4	1237.1	1370.0
37.5°	998.9	1063.0	1169.9	1292.1
40°	925.6	992.8	1084.4	1206.6
42.5°	856.8	916.4	998.9	1121.0
45°	794.2	837.0	913.3	1027.9
47.5°	728.5	766.7	837.0	951.5
50°	667.4	699.5	760.6	867.5
52.5°	607.9	635.4	691.9	777.4
55°	554.4	580.4	621.6	705.6
57.5°	499.4	519.3	559.0	626.2
60°	446.0	464.3	496.4	551.4
62.5°	392.5	407.8	438.3	482.6
65°	345.2	357.4	380.3	418.5
67.5°	299.4	307.0	325.3	355.9
70°	255.1	261.2	276.4	300.9
72.5°	207.7	213.8	230.6	247.4
75°	168.0	169.5	181.8	195.5
77.5°	131.3	129.8	139.0	149.7
80°	90.1	94.7	102.3	106.9
82.5°	61.1	62.6	65.7	68.7
85°	33.6	35.1	35.1	39.7
87.5°	13.7	15.3	15.3	16.8
90°	11.5	9.2	4.6	1.2
92.5°	39.2	33.5	24.2	17.3
95°	67.0	56.6	45.0	40.4
97.5°	94.7	79.6	67.0	60.0
100°	121.2	102.7	92.3	88.9
102.5°	146.6	128.1	117.7	115.4
105°	170.8	153.5	145.4	140.8
107.5°	196.2	180.1	172.0	168.5
110°	222.8	207.8	200.9	196.2

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	248.2	234.3	226.2	221.6
115°	274.7	260.9	254.0	248.2
117.5°	300.1	287.4	280.5	275.9
120°	323.2	312.8	305.9	301.3
122.5°	347.5	335.9	329.0	325.5
125°	370.5	356.7	349.8	346.3
127.5°	392.5	377.5	368.2	363.6
130°	410.9	394.8	383.2	378.6
132.5°	428.3	410.9	398.2	392.5
135°	442.1	424.8	410.9	406.3
137.5°	457.1	438.6	424.8	419.0
140°	471.0	452.5	438.6	434.0
142.5°	483.7	465.2	452.5	449.0
145°	497.5	480.2	468.7	464.0
147.5°	511.4	495.2	483.7	480.2
150°	524.1	509.1	499.8	496.4
152.5°	535.6	522.9	513.7	512.5
155°	548.3	535.6	528.7	527.5
157.5°	558.7	547.1	541.4	540.2
160°	567.9	558.7	554.1	552.9
162.5°	576.0	569.1	564.5	565.6
165°	582.9	576.0	573.7	574.9
167.5°	588.7	584.1	581.8	582.9
170°	593.3	589.9	588.7	591.0
172.5°	596.8	593.3	594.5	595.6
175°	599.1	596.8	597.9	599.1
177.5°	600.2	597.9	599.1	601.4
180°	600.2	600.2	600.2	600.2

TEST NUMBER: P997827

CATALOG NUMBER: SA2XXDIP-B1005D1080UB40-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.94	18.78	18.89	19.74	21.00	15.43	16.27	16.38	17.23	18.49
	3H	18.75	19.50	19.71	20.47	21.75	16.77	17.52	17.74	18.50	19.78
	4H	18.91	19.62	19.89	20.60	21.89	17.23	17.94	18.21	18.92	20.21
	6H	18.96	19.61	19.95	20.59	21.89	17.54	18.19	18.53	19.18	20.48
	8H	18.94	19.56	19.93	20.56	21.85	17.62	18.24	18.62	19.24	20.54
	12H	18.90	19.49	19.90	20.48	21.80	17.67	18.26	18.67	19.25	20.57
4H	2H	17.98	18.68	18.96	19.66	20.95	15.87	16.58	16.86	17.56	18.85
	3H	18.95	19.54	19.95	20.55	21.85	17.33	17.92	18.33	18.93	20.23
	4H	19.23	19.77	20.23	20.77	22.09	17.87	18.40	18.87	19.40	20.73
	6H	19.36	19.82	20.37	20.85	22.17	18.24	18.71	19.26	19.73	21.05
	8H	19.36	19.79	20.37	20.81	22.14	18.35	18.79	19.37	19.80	21.14
	12H	19.32	19.71	20.35	20.74	22.08	18.41	18.80	19.44	19.83	21.17
8H	4H	19.24	19.67	20.25	20.69	22.02	18.01	18.44	19.02	19.46	20.79
	6H	19.42	19.77	20.45	20.83	22.17	18.44	18.80	19.48	19.86	21.19
	8H	19.45	19.76	20.49	20.80	22.16	18.59	18.90	19.64	19.95	21.30
	12H	19.43	19.70	20.48	20.74	22.14	18.68	18.96	19.73	20.00	21.39
12H	4H	19.19	19.58	20.23	20.62	21.96	17.98	18.37	19.01	19.40	20.74
	6H	19.39	19.71	20.44	20.75	22.11	18.44	18.75	19.49	19.80	21.15
	8H	19.43	19.70	20.48	20.74	22.14	18.60	18.87	19.65	19.91	21.31