

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997843

Luminaire Tested: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P997843
REPORT IS A COMBINATION OF REPORTS P983580 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5648.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81
1	105	100	97	93	100	96	93	90	88	85	83	80	78	76	73	72	70
2	96	89	83	78	91	85	79	75	78	73	70	71	68	65	65	63	60
3	88	79	71	66	84	75	69	64	69	64	60	64	59	56	59	55	52
4	81	70	62	56	77	67	60	55	62	56	52	57	53	49	53	49	46
5	75	63	55	49	71	61	53	48	56	50	45	52	47	43	48	44	40
6	69	57	49	43	66	55	48	42	51	45	40	47	42	38	44	39	36
7	64	52	44	38	61	50	43	37	47	40	36	43	38	34	40	36	32
8	60	48	40	34	57	46	39	34	43	37	32	40	35	31	37	33	29
9	56	44	36	31	54	42	35	30	40	33	29	37	32	28	35	30	27
10	53	40	33	28	50	39	32	28	37	31	27	34	29	25	32	28	24

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31359	31359	31359	31359
5°	31436	33437	31556	26602
10°	31070	36502	31265	21932
15°	30317	38501	30739	18474
20°	29843	36150	29843	16057
25°	28892	31057	29025	14360
30°	27328	24414	27849	13007
35°	25941	16882	26375	11901
40°	24348	12746	24625	11018
45°	22382	10474	22749	10067
50°	20683	9193	20721	9215
55°	18746	7833	18868	8291
60°	16680	6542	16911	7235
65°	14831	5321	15105	6179
70°	12992	4175	13321	4983
75°	10903	3032	11328	3614
80°	8511	1922	9117	2144
85°	5594	966	6018	717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 32417 cd/sqm

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.7	3.3
10°-20°	549.2	9.7
20°-30°	797.1	14.1
30°-40°	840.3	14.9
40°-50°	743.6	13.2
50°-60°	593.7	10.5
60°-70°	403.3	7.1
70°-80°	206.3	3.7
80°-90°	49.9	0.9
90°-100°	71.4	1.3
100°-110°	251.5	4.5
110°-120°	264.1	4.7
120°-130°	217.3	3.8
130°-140°	174.6	3.1
140°-150°	131.9	2.3
150°-160°	92.7	1.6
160°-170°	54.6	1.0
170°-180°	17.8	0.3
0°-30°	1535.0	27.2
0°-40°	2375.3	42.1
0°-60°	3712.6	65.7
0°-90°	4372.2	77.4
90°-120°	587.1	10.4
90°-150°	1110.8	19.7
90°-180°	1276.0	22.6
0°-180°	5648.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1981	1981	1981	1981	1981	
5°	1983	2213	1990	1760	1983	188
15°	1862	2720	1888	1305	1862	526
25°	1674	2266	1681	1048	1674	765
35°	1366	1234	1389	870	1366	855
45°	1025	743	1042	714	1025	795
55°	704	522	708	553	704	628
65°	417	321	425	373	417	415
75°	195	158	202	189	195	209
85°	40	41	43	30	40	46
90°	0	12	0	12	0	3
95°	12	40	12	40	12	13
105°	43	397	43	397	43	46
115°	76	522	76	522	76	75
125°	106	424	106	424	106	94
135°	124	351	124	351	124	96
145°	142	280	142	280	142	89
155°	161	236	161	236	161	74
165°	176	207	176	207	176	49
175°	183	186	183	186	183	17
180°	183	183	183	183	183	

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	1991.8	1996.4	2004.0	2005.5	2020.7	2032.9	2046.6	2046.6	2051.2	2049.7	2037.5
5°	1982.7	1996.4	2016.2	2032.9	2060.3	2072.5	2090.8	2104.5	2116.7	2125.8	2124.3
7.5°	1967.4	1991.8	2020.7	2052.7	2089.3	2110.6	2136.5	2160.8	2177.6	2192.8	2203.5
10°	1941.5	1982.7	2022.3	2064.9	2112.1	2141.0	2171.5	2203.5	2229.4	2258.3	2285.7
12.5°	1906.5	1965.9	2014.6	2071.0	2128.9	2160.8	2209.6	2233.9	2284.2	2357.3	2377.1
15°	1862.4	1943.1	1988.8	2060.3	2136.5	2162.4	2229.4	2268.9	2372.5	2418.2	2473.0
17.5°	1821.2	1911.1	1972.0	2054.2	2128.9	2179.1	2244.6	2325.3	2412.1	2477.6	2538.5
20°	1787.7	1874.5	1947.6	2039.0	2133.4	2197.4	2265.9	2363.4	2457.8	2524.8	2572.0
22.5°	1711.6	1822.8	1908.0	2010.1	2124.3	2212.6	2278.1	2384.7	2486.7	2527.8	2568.9
25°	1673.5	1769.5	1868.5	1984.2	2118.2	2223.3	2279.6	2398.4	2488.2	2503.5	2512.6
27.5°	1603.5	1711.6	1827.3	1959.8	2116.7	2205.0	2276.6	2384.7	2456.2	2445.6	2418.2
30°	1516.7	1649.2	1777.1	1920.2	2095.3	2191.3	2258.3	2357.3	2393.8	2339.0	2290.3
32.5°	1452.7	1577.6	1719.2	1885.2	2071.0	2162.4	2227.8	2305.5	2313.1	2214.1	2131.9
35°	1365.9	1504.5	1664.4	1839.5	2029.9	2112.1	2173.0	2220.2	2183.7	2045.1	1947.6
37.5°	1288.3	1425.3	1595.9	1774.0	1973.5	2054.2	2103.0	2110.6	2020.7	1898.9	1755.8
40°	1203.0	1344.6	1522.8	1710.1	1911.1	1981.1	2011.6	1988.8	1859.3	1717.7	1551.7
42.5°	1117.7	1257.8	1449.7	1641.6	1831.9	1891.3	1903.5	1841.0	1682.7	1516.7	1324.8
45°	1024.8	1171.0	1362.9	1556.3	1740.5	1774.0	1775.6	1685.7	1498.4	1324.8	1146.7
47.5°	948.7	1084.2	1274.6	1468.0	1623.3	1646.1	1637.0	1533.4	1329.4	1134.5	979.1
50°	864.9	994.4	1183.2	1373.6	1506.0	1512.1	1489.3	1341.6	1142.1	963.9	840.6
52.5°	775.1	906.1	1079.7	1262.4	1381.2	1372.0	1327.9	1169.5	982.2	834.5	740.1
55°	703.5	819.3	982.2	1160.4	1244.1	1218.2	1169.5	1008.1	860.4	735.5	653.3
57.5°	624.3	726.4	886.3	1041.6	1090.3	1065.9	1017.2	866.5	729.4	635.0	580.2
60°	549.7	642.6	782.7	912.1	950.2	924.3	868.0	732.5	633.5	554.3	513.2
62.5°	481.2	561.9	679.2	797.9	813.2	787.3	738.5	628.9	543.6	481.2	450.7
65°	417.2	493.4	587.8	677.6	691.3	663.9	613.7	534.5	462.9	423.3	394.4
67.5°	354.8	415.7	499.5	565.0	572.6	546.7	505.6	441.6	397.4	354.8	333.5
70°	300.0	345.7	411.2	464.4	467.5	443.1	421.8	363.9	330.4	300.0	283.2
72.5°	246.7	278.7	328.9	368.5	370.0	354.8	335.0	298.5	269.5	248.2	231.5
75°	194.9	222.3	252.8	287.8	286.3	274.1	258.9	236.0	211.7	198.0	190.3
77.5°	149.2	166.0	190.3	213.2	213.2	207.1	198.0	181.2	166.0	152.3	144.7
80°	106.6	117.3	137.1	144.7	147.7	146.2	138.6	126.4	120.3	109.6	106.6
82.5°	68.5	76.1	85.3	92.9	97.5	94.4	92.9	86.8	77.7	74.6	71.6
85°	39.6	42.6	47.2	51.8	53.3	51.8	54.8	50.3	45.7	45.7	44.2
87.5°	16.8	18.3	21.3	21.3	22.8	22.8	21.3	22.8	22.8	21.3	19.8
90°	0.4	1.4	2.8	3.5	4.2	4.8	5.3	7.0	9.5	11.6	12.0
92.5°	5.3	7.4	10.2	12.0	14.8	16.8	18.7	28.2	41.6	53.6	54.3
95°	12.3	13.7	17.3	20.4	26.1	30.3	34.5	50.7	81.4	122.3	138.1
97.5°	18.3	20.4	24.3	28.9	35.2	40.0	44.7	65.5	108.2	174.0	225.1
100°	27.1	28.2	31.4	37.0	44.0	49.0	53.9	72.6	115.6	191.7	278.3
102.5°	35.2	35.9	39.1	44.7	52.1	57.0	62.0	78.9	115.9	185.0	280.1
105°	43.0	44.4	46.9	52.1	59.9	64.8	69.8	86.3	117.7	175.8	261.1
107.5°	51.4	52.5	55.0	59.9	67.6	72.6	77.5	93.7	121.5	170.9	243.4
110°	59.9	61.3	63.4	68.0	75.4	80.5	85.6	101.1	126.5	169.5	231.5

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	67.6	69.1	71.5	75.7	82.8	88.1	93.4	108.2	131.8	169.8	223.7
115°	75.7	77.5	79.6	83.9	90.9	95.6	100.4	115.6	137.0	171.2	218.4
117.5°	84.2	85.6	87.7	91.6	98.3	103.2	108.2	122.3	142.7	173.3	215.6
120°	92.0	93.4	95.5	98.6	105.7	110.6	115.6	129.3	148.3	175.5	213.1
122.5°	99.4	100.4	102.5	106.0	113.1	118.2	123.3	136.0	153.3	177.9	211.7
125°	105.7	106.8	108.9	113.1	120.1	125.0	130.0	142.7	158.5	180.4	210.0
127.5°	111.0	112.4	115.2	119.8	126.5	131.6	136.7	149.0	163.5	182.8	208.9
130°	115.6	117.0	120.5	125.4	132.5	137.4	142.3	154.7	168.1	185.7	208.2
132.5°	119.8	121.5	125.4	130.7	138.1	143.0	148.0	159.6	172.6	188.5	207.9
135°	124.0	125.4	129.7	134.9	143.0	148.0	152.9	164.2	176.5	190.6	207.5
137.5°	127.9	129.7	133.9	139.5	147.6	152.2	156.8	168.1	179.7	192.7	207.5
140°	132.5	133.9	138.1	143.7	151.5	156.1	160.7	171.2	182.1	194.1	207.2
142.5°	137.0	138.1	142.0	147.6	155.0	159.2	163.5	173.7	184.3	195.2	207.2
145°	141.6	143.0	146.6	151.8	158.9	162.8	166.6	176.2	186.0	195.9	206.5
147.5°	146.6	147.6	151.1	156.1	162.1	165.6	169.1	178.3	187.1	196.2	205.4
150°	151.5	152.6	155.4	159.9	165.2	168.4	171.6	179.7	187.8	195.9	204.3
152.5°	156.4	156.8	159.6	163.5	168.4	171.2	174.0	181.1	188.1	195.2	202.6
155°	161.0	161.4	163.5	167.3	171.2	173.8	176.5	182.5	188.5	194.5	200.5
157.5°	164.9	165.2	167.0	170.5	173.7	176.0	178.3	183.6	188.5	193.1	198.4
160°	168.8	169.1	170.5	173.3	176.2	178.1	180.0	184.3	188.5	192.0	196.2
162.5°	172.6	172.3	173.7	175.8	178.3	179.7	181.1	184.6	188.1	191.0	194.5
165°	175.5	175.1	175.8	177.9	179.7	180.8	181.8	185.0	187.4	189.5	192.0
167.5°	177.9	177.6	178.3	179.7	181.1	181.8	182.5	185.0	187.1	188.1	189.9
170°	180.4	179.7	180.0	181.1	181.8	182.3	182.8	184.6	186.4	187.1	188.1
172.5°	181.8	181.4	181.1	182.1	182.5	182.8	183.2	184.3	185.3	185.7	186.0
175°	182.8	182.5	182.1	182.8	182.8	183.0	183.2	183.9	184.6	184.3	184.6
177.5°	183.6	182.8	182.5	183.2	183.2	183.2	183.2	183.6	184.3	183.6	183.2
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	2058.8	2060.3	2063.4	2078.6	2086.2	2087.7	2081.6	2095.3	2099.9	2095.3	2092.3
5°	2156.3	2165.4	2183.7	2203.5	2201.9	2203.5	2212.6	2221.7	2224.8	2212.6	2217.2
7.5°	2241.5	2259.8	2279.6	2310.1	2310.1	2325.3	2331.4	2339.0	2357.3	2348.1	2345.1
10°	2339.0	2363.4	2399.9	2448.6	2450.2	2465.4	2480.6	2505.0	2512.6	2506.5	2509.5
12.5°	2460.8	2508.0	2511.1	2564.4	2588.7	2591.8	2616.1	2611.6	2626.8	2626.8	2652.7
15°	2514.1	2587.2	2628.3	2680.1	2695.3	2677.1	2696.8	2718.2	2719.7	2719.7	2718.2
17.5°	2610.1	2639.0	2680.1	2707.5	2713.6	2713.6	2715.1	2724.3	2718.2	2706.0	2715.1
20°	2629.8	2642.0	2657.3	2654.2	2657.3	2642.0	2626.8	2611.6	2613.1	2605.5	2628.3
22.5°	2593.3	2590.3	2555.2	2532.4	2532.4	2501.9	2473.0	2459.3	2445.6	2450.2	2457.8
25°	2501.9	2454.7	2412.1	2378.6	2371.0	2322.2	2282.7	2270.5	2247.6	2265.9	2268.9
27.5°	2355.7	2302.4	2233.9	2205.0	2165.4	2145.6	2118.2	2081.6	2034.4	2061.8	2057.3
30°	2198.9	2119.7	2063.4	1993.3	1930.9	1926.3	1874.5	1813.6	1789.3	1789.3	1803.0
32.5°	2023.8	1918.7	1836.5	1737.5	1676.6	1650.7	1588.3	1527.4	1541.1	1495.4	1512.1
35°	1819.7	1681.2	1577.6	1481.7	1436.0	1405.5	1324.8	1291.3	1254.8	1233.5	1273.0
37.5°	1624.8	1464.9	1332.4	1227.4	1210.6	1155.8	1101.0	1079.7	1058.3	1067.5	1065.9
40°	1387.3	1245.6	1126.9	1044.6	1015.7	989.8	953.3	927.4	913.7	921.3	922.8
42.5°	1172.5	1053.8	965.4	907.6	883.2	864.9	846.7	825.3	820.8	820.8	826.9
45°	1006.6	909.1	849.7	802.5	788.8	775.1	761.4	752.3	749.2	743.1	747.7
47.5°	874.1	796.4	759.9	724.8	709.6	706.6	694.4	689.8	683.7	682.2	683.7
50°	762.9	714.2	680.7	660.9	650.2	645.7	639.6	630.4	627.4	635.0	632.0
52.5°	685.3	639.6	621.3	601.5	595.4	589.3	580.2	581.7	580.2	577.1	577.1
55°	607.6	578.7	560.4	545.2	543.6	537.5	529.9	526.9	525.4	522.3	526.9
57.5°	545.2	522.3	505.6	491.9	485.8	485.8	478.2	472.1	472.1	470.5	472.1
60°	482.7	459.9	449.2	435.5	430.9	429.4	424.9	421.8	417.2	417.2	417.2
62.5°	424.9	406.6	394.4	382.2	383.7	376.1	370.0	367.0	367.0	368.5	368.5
65°	370.0	357.9	342.6	332.0	328.9	327.4	324.4	322.8	318.3	321.3	321.3
67.5°	319.8	303.0	293.9	289.3	284.8	283.2	280.2	277.1	275.6	274.1	277.1
70°	269.5	255.8	248.2	245.2	240.6	239.1	237.6	233.0	234.5	236.0	237.6
72.5°	223.8	211.7	210.1	201.0	201.0	201.0	194.9	198.0	196.4	193.4	196.4
75°	176.6	170.6	167.5	162.9	164.5	162.9	161.4	156.8	156.8	158.4	159.9
77.5°	140.1	134.0	132.5	127.9	124.9	127.9	124.9	123.3	123.3	124.9	124.9
80°	103.5	100.5	95.9	95.9	95.9	94.4	94.4	94.4	92.9	91.4	92.9
82.5°	68.5	68.5	67.0	65.5	67.0	64.0	65.5	65.5	65.5	65.5	65.5
85°	44.2	42.6	42.6	41.1	41.1	41.1	42.6	39.6	39.6	41.1	41.1
87.5°	19.8	19.8	19.8	21.3	19.8	19.8	19.8	21.3	19.8	19.8	19.8
90°	11.6	11.3	10.6	11.3	11.4	11.6	11.6	11.6	11.6	11.6	11.6
92.5°	45.4	35.6	30.3	26.4	25.0	23.6	23.3	21.8	22.2	21.5	22.2
95°	120.8	92.3	70.8	56.0	52.2	48.3	43.7	40.9	39.8	40.2	39.8
97.5°	226.9	188.8	150.8	115.2	104.6	94.1	80.3	73.3	69.4	67.3	69.4
100°	329.1	321.7	278.0	229.7	208.4	187.1	157.8	142.7	132.5	126.1	132.5
102.5°	367.1	408.7	407.3	375.2	352.3	329.4	297.0	268.5	255.1	245.9	255.1
105°	354.8	428.1	467.9	472.4	466.6	460.8	439.0	417.1	402.0	397.1	402.0
107.5°	328.7	407.3	466.5	501.0	508.0	515.1	514.7	511.6	507.0	498.9	507.0
110°	304.4	378.7	441.8	486.9	501.4	515.8	530.9	537.6	540.8	540.4	540.8

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	287.5	352.7	412.6	461.5	478.6	495.7	518.2	530.6	537.3	539.7	537.3
115°	274.1	332.2	386.5	432.6	450.8	468.9	493.9	510.1	519.3	522.5	519.3
117.5°	264.9	315.3	363.9	406.9	424.2	441.4	467.2	484.4	493.9	496.4	493.9
120°	257.9	303.3	347.0	384.4	400.4	416.4	441.1	457.7	467.9	471.4	467.9
122.5°	251.9	293.8	332.9	367.8	381.9	396.0	417.5	433.7	442.5	445.3	442.5
125°	246.3	284.7	321.0	352.0	365.2	378.4	398.8	412.2	421.0	423.8	421.0
127.5°	241.0	275.5	309.0	338.6	350.9	363.2	381.2	393.9	401.6	403.7	401.6
130°	235.7	266.7	297.0	324.8	336.5	348.1	365.3	377.3	384.4	387.2	384.4
132.5°	231.5	258.2	285.7	310.7	321.4	332.2	349.1	361.1	367.5	369.9	367.5
135°	227.6	250.5	273.7	297.0	306.8	316.7	331.9	343.5	349.8	351.3	349.8
137.5°	224.8	244.2	264.2	283.3	292.1	300.9	315.3	325.5	331.2	333.3	331.2
140°	222.3	238.2	255.1	271.3	279.0	286.8	298.1	307.2	312.5	314.6	312.5
142.5°	219.8	233.2	247.0	260.4	266.5	272.7	283.3	291.4	295.9	295.9	295.9
145°	217.7	228.7	240.3	251.2	256.3	261.4	269.9	275.9	279.4	280.4	279.4
147.5°	215.6	225.1	234.6	243.4	247.3	251.2	258.6	263.5	266.0	266.7	266.0
150°	212.8	221.3	229.0	236.4	239.6	242.7	248.0	252.3	254.4	254.7	254.4
152.5°	210.3	217.4	224.4	230.4	233.0	235.7	239.6	243.1	244.5	244.5	244.5
155°	207.2	213.9	219.5	224.8	226.8	228.7	232.5	235.0	236.4	235.7	236.4
157.5°	204.3	209.6	214.6	219.1	220.7	222.3	225.1	227.2	227.9	227.9	227.9
160°	201.2	205.7	209.6	213.5	214.8	216.0	218.4	220.2	220.5	220.5	220.5
162.5°	198.4	201.9	205.0	208.2	209.1	210.0	212.4	213.5	213.9	213.5	213.9
165°	195.2	198.0	200.5	202.9	203.6	204.3	205.7	207.2	207.2	206.8	207.2
167.5°	192.0	194.1	196.2	198.0	198.7	199.4	200.1	200.8	200.8	200.5	200.8
170°	189.5	191.3	192.4	193.8	194.2	194.5	194.8	195.9	195.5	194.8	195.5
172.5°	187.1	188.1	188.8	189.9	190.0	190.2	190.6	191.0	190.6	190.2	190.6
175°	185.0	186.0	186.4	186.7	186.9	187.1	187.1	187.4	187.1	186.4	187.1
177.5°	183.6	184.3	184.3	184.6	184.6	184.6	184.6	184.6	184.3	183.6	184.3
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	2099.9	2089.3	2080.1	2081.6	2089.3	2083.2	2067.9	2048.1	2040.5	2031.4	2040.5
5°	2226.3	2217.2	2198.9	2200.4	2195.9	2189.8	2165.4	2134.9	2134.9	2110.6	2107.5
7.5°	2351.2	2337.5	2325.3	2322.2	2305.5	2293.3	2272.0	2229.4	2212.6	2183.7	2166.9
10°	2491.3	2480.6	2466.9	2450.2	2441.0	2419.7	2384.7	2322.2	2291.8	2252.2	2223.3
12.5°	2632.9	2631.4	2600.9	2567.4	2565.9	2532.4	2508.0	2424.3	2383.2	2329.9	2261.3
15°	2722.7	2715.1	2698.4	2681.6	2686.2	2649.6	2594.8	2495.8	2468.4	2404.5	2331.4
17.5°	2721.2	2721.2	2716.6	2713.6	2709.0	2698.4	2667.9	2602.4	2558.3	2477.6	2409.0
20°	2634.4	2654.2	2658.8	2657.3	2672.5	2680.1	2678.6	2637.5	2602.4	2530.9	2460.8
22.5°	2460.8	2506.5	2526.3	2538.5	2570.5	2587.2	2626.8	2611.6	2602.4	2549.1	2489.8
25°	2299.4	2314.6	2374.0	2377.1	2421.2	2462.3	2501.9	2527.8	2561.3	2541.5	2491.3
27.5°	2090.8	2125.8	2168.4	2200.4	2209.6	2293.3	2358.8	2407.5	2483.7	2489.8	2473.0
30°	1854.7	1871.5	1941.5	1984.2	2032.9	2093.8	2188.2	2272.0	2340.5	2403.0	2424.3
32.5°	1566.9	1635.5	1676.6	1728.4	1771.0	1879.1	1994.8	2103.0	2182.1	2287.2	2332.9
35°	1303.5	1356.8	1426.8	1448.2	1525.8	1617.2	1768.0	1906.5	2026.8	2133.4	2226.3
37.5°	1085.7	1128.4	1203.0	1236.5	1282.2	1399.4	1525.8	1697.9	1842.6	1973.5	2089.3
40°	936.5	968.5	1024.8	1035.5	1073.6	1180.2	1282.2	1443.6	1635.5	1812.1	1938.5
42.5°	834.5	849.7	887.8	901.5	925.9	997.4	1088.8	1241.1	1419.2	1602.0	1780.1
45°	761.4	772.1	794.9	807.1	837.5	869.5	944.1	1065.9	1206.0	1390.3	1582.2
47.5°	695.9	709.6	718.8	726.4	743.1	778.1	826.9	916.7	1050.7	1219.7	1405.5
50°	641.1	645.7	662.4	663.9	674.6	697.4	743.1	797.9	904.5	1041.6	1221.3
52.5°	586.3	590.8	601.5	612.2	616.7	635.0	665.5	711.1	790.3	898.4	1058.3
55°	531.5	537.5	548.2	555.8	560.4	575.6	593.9	638.0	700.5	776.6	907.6
57.5°	476.6	490.3	493.4	498.0	505.6	522.3	539.1	565.0	613.7	683.7	779.7
60°	424.9	429.4	440.1	444.7	452.3	461.4	482.7	502.5	537.5	592.4	679.2
62.5°	371.6	382.2	386.8	391.4	397.4	408.1	421.8	443.1	473.6	517.7	586.3
65°	325.9	327.4	336.5	342.6	348.7	356.3	370.0	389.8	408.1	449.2	499.5
67.5°	281.7	284.8	287.8	293.9	301.5	309.1	321.3	332.0	354.8	382.2	421.8
70°	239.1	239.1	246.7	251.3	249.7	258.9	268.0	280.2	296.9	322.8	354.8
72.5°	201.0	199.5	205.6	207.1	210.1	216.2	222.3	234.5	243.6	263.4	287.8
75°	159.9	162.9	166.0	166.0	170.6	175.1	181.2	187.3	198.0	210.1	228.4
77.5°	126.4	126.4	129.4	131.0	135.5	134.0	140.1	146.2	153.8	164.5	178.2
80°	92.9	95.9	95.9	95.9	97.5	99.0	105.1	109.6	114.2	121.8	127.9
82.5°	65.5	65.5	68.5	68.5	68.5	71.6	71.6	73.1	76.1	80.7	85.3
85°	41.1	41.1	41.1	42.6	41.1	42.6	45.7	44.2	45.7	48.7	48.7
87.5°	19.8	19.8	19.8	19.8	19.8	21.3	19.8	21.3	22.8	22.8	22.8
90°	11.6	11.6	11.6	11.4	11.3	10.6	11.3	11.6	12.0	11.6	9.5
92.5°	21.8	23.3	23.6	25.0	26.4	30.3	35.6	45.4	54.3	53.6	41.6
95°	40.9	43.7	48.3	52.2	56.0	70.8	92.3	120.8	138.1	122.3	81.4
97.5°	73.3	80.3	94.1	104.6	115.2	150.8	188.8	226.9	225.1	174.0	108.2
100°	142.7	157.8	187.1	208.4	229.7	278.0	321.7	329.1	278.3	191.7	115.6
102.5°	268.5	297.0	329.4	352.3	375.2	407.3	408.7	367.1	280.1	185.0	115.9
105°	417.1	439.0	460.8	466.6	472.4	467.9	428.1	354.8	261.1	175.8	117.7
107.5°	511.6	514.7	515.1	508.0	501.0	466.5	407.3	328.7	243.4	170.9	121.5
110°	537.6	530.9	515.8	501.4	486.9	441.8	378.7	304.4	231.5	169.5	126.5

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	530.6	518.2	495.7	478.6	461.5	412.6	352.7	287.5	223.7	169.8	131.8
115°	510.1	493.9	468.9	450.8	432.6	386.5	332.2	274.1	218.4	171.2	137.0
117.5°	484.4	467.2	441.4	424.2	406.9	363.9	315.3	264.9	215.6	173.3	142.7
120°	457.7	441.1	416.4	400.4	384.4	347.0	303.3	257.9	213.1	175.5	148.3
122.5°	433.7	417.5	396.0	381.9	367.8	332.9	293.8	251.9	211.7	177.9	153.3
125°	412.2	398.8	378.4	365.2	352.0	321.0	284.7	246.3	210.0	180.4	158.5
127.5°	393.9	381.2	363.2	350.9	338.6	309.0	275.5	241.0	208.9	182.8	163.5
130°	377.3	365.3	348.1	336.5	324.8	297.0	266.7	235.7	208.2	185.7	168.1
132.5°	361.1	349.1	332.2	321.4	310.7	285.7	258.2	231.5	207.9	188.5	172.6
135°	343.5	331.9	316.7	306.8	297.0	273.7	250.5	227.6	207.5	190.6	176.5
137.5°	325.5	315.3	300.9	292.1	283.3	264.2	244.2	224.8	207.5	192.7	179.7
140°	307.2	298.1	286.8	279.0	271.3	255.1	238.2	222.3	207.2	194.1	182.1
142.5°	291.4	283.3	272.7	266.5	260.4	247.0	233.2	219.8	207.2	195.2	184.3
145°	275.9	269.9	261.4	256.3	251.2	240.3	228.7	217.7	206.5	195.9	186.0
147.5°	263.5	258.6	251.2	247.3	243.4	234.6	225.1	215.6	205.4	196.2	187.1
150°	252.3	248.0	242.7	239.6	236.4	229.0	221.3	212.8	204.3	195.9	187.8
152.5°	243.1	239.6	235.7	233.0	230.4	224.4	217.4	210.3	202.6	195.2	188.1
155°	235.0	232.5	228.7	226.8	224.8	219.5	213.9	207.2	200.5	194.5	188.5
157.5°	227.2	225.1	222.3	220.7	219.1	214.6	209.6	204.3	198.4	193.1	188.5
160°	220.2	218.4	216.0	214.8	213.5	209.6	205.7	201.2	196.2	192.0	188.5
162.5°	213.5	212.4	210.0	209.1	208.2	205.0	201.9	198.4	194.5	191.0	188.1
165°	207.2	205.7	204.3	203.6	202.9	200.5	198.0	195.2	192.0	189.5	187.4
167.5°	200.8	200.1	199.4	198.7	198.0	196.2	194.1	192.0	189.9	188.1	187.1
170°	195.9	194.8	194.5	194.2	193.8	192.4	191.3	189.5	188.1	187.1	186.4
172.5°	191.0	190.6	190.2	190.0	189.9	188.8	188.1	187.1	186.0	185.7	185.3
175°	187.4	187.1	187.1	186.9	186.7	186.4	186.0	185.0	184.6	184.3	184.6
177.5°	184.6	184.6	184.6	184.6	184.6	184.3	184.3	183.6	183.2	183.6	184.3
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	2032.9	2025.3	2020.7	2023.8	2014.6	1991.8	1991.8	1999.4	1990.3	1981.1	1967.4
5°	2089.3	2074.0	2064.9	2063.4	2042.1	2005.5	1997.9	1990.3	1970.5	1949.2	1926.3
7.5°	2144.1	2116.7	2101.4	2090.8	2060.3	2013.1	1993.3	1976.6	1944.6	1912.6	1883.7
10°	2189.8	2150.2	2131.9	2115.1	2075.6	2016.2	1984.2	1953.7	1912.6	1871.5	1835.0
12.5°	2226.3	2180.6	2157.8	2133.4	2084.7	2007.0	1967.4	1918.7	1877.6	1822.8	1786.2
15°	2287.2	2192.8	2171.5	2148.6	2098.4	1991.8	1943.1	1888.3	1831.9	1758.8	1719.2
17.5°	2335.9	2209.6	2208.0	2159.3	2093.8	1985.7	1911.1	1839.5	1778.6	1705.5	1643.1
20°	2364.9	2235.4	2211.1	2160.8	2078.6	1944.6	1866.9	1787.7	1722.3	1633.9	1571.5
22.5°	2389.2	2272.0	2208.0	2147.1	2046.6	1930.9	1816.7	1742.1	1652.2	1556.3	1496.9
25°	2398.4	2279.6	2212.6	2142.6	2023.8	1891.3	1761.9	1681.2	1580.6	1493.9	1413.1
27.5°	2399.9	2278.1	2195.9	2122.8	1991.8	1839.5	1707.0	1621.8	1510.6	1410.1	1329.4
30°	2384.7	2261.3	2186.7	2107.5	1961.3	1792.3	1640.0	1545.6	1426.8	1326.3	1242.6
32.5°	2339.0	2227.8	2166.9	2080.1	1921.8	1726.8	1576.1	1471.0	1346.1	1247.2	1166.5
35°	2262.9	2186.7	2119.7	2039.0	1870.0	1665.9	1512.1	1388.8	1262.4	1168.0	1091.8
37.5°	2168.4	2127.3	2064.9	1985.7	1810.6	1611.1	1440.6	1303.5	1177.1	1085.7	1011.1
40°	2040.5	2051.2	1990.3	1918.7	1740.5	1536.5	1347.7	1216.7	1097.9	1012.7	939.6
42.5°	1902.0	1946.1	1911.1	1842.6	1662.9	1454.3	1279.1	1134.5	1018.7	930.4	869.5
45°	1752.7	1828.9	1807.5	1757.3	1582.2	1367.5	1181.7	1041.6	939.6	854.3	801.0
47.5°	1589.8	1697.9	1697.9	1661.4	1492.3	1280.7	1097.9	954.8	854.3	793.4	741.6
50°	1423.8	1545.6	1565.4	1541.1	1391.8	1181.7	995.9	866.5	779.7	720.3	682.2
52.5°	1250.2	1391.8	1428.4	1416.2	1285.2	1087.3	912.1	785.8	706.6	654.8	621.3
55°	1084.2	1248.7	1288.3	1292.8	1171.0	983.7	819.3	708.1	632.0	596.9	568.0
57.5°	927.4	1085.7	1129.9	1137.5	1055.3	889.3	732.5	635.0	566.5	537.5	514.7
60°	793.4	925.9	983.7	1000.5	928.9	779.7	651.8	557.3	505.6	478.2	456.8
62.5°	683.7	790.3	851.2	855.8	823.8	683.7	568.0	488.8	444.7	420.3	409.6
65°	577.1	673.1	709.6	727.9	702.0	592.4	490.3	424.9	389.8	368.5	357.9
67.5°	491.9	552.8	583.2	607.6	581.7	499.5	417.2	363.9	338.1	316.7	310.6
70°	403.5	453.8	476.6	501.0	478.2	415.7	356.3	307.6	284.8	268.0	260.4
72.5°	322.8	362.4	383.7	399.0	385.3	333.5	284.8	251.3	234.5	222.3	217.8
75°	255.8	283.2	295.4	306.1	300.0	260.4	229.9	202.5	187.3	176.6	173.6
77.5°	194.9	214.7	228.4	231.5	223.8	198.0	172.1	155.3	143.1	137.1	134.0
80°	138.6	150.8	158.4	162.9	155.3	144.7	126.4	114.2	103.5	95.9	94.4
82.5°	92.9	99.0	105.1	103.5	100.5	91.4	80.7	74.6	70.0	64.0	64.0
85°	53.3	54.8	57.9	59.4	57.9	51.8	45.7	42.6	39.6	35.0	35.0
87.5°	22.8	24.4	24.4	25.9	22.8	22.8	19.8	16.8	16.8	15.2	13.7
90°	7.0	5.3	4.8	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	28.2	18.7	16.8	14.8	12.0	10.2	7.4	5.3	7.4	10.2	12.0
95°	50.7	34.5	30.3	26.1	20.4	17.3	13.7	12.3	13.7	17.3	20.4
97.5°	65.5	44.7	40.0	35.2	28.9	24.3	20.4	18.3	20.4	24.3	28.9
100°	72.6	53.9	49.0	44.0	37.0	31.4	28.2	27.1	28.2	31.4	37.0
102.5°	78.9	62.0	57.0	52.1	44.7	39.1	35.9	35.2	35.9	39.1	44.7
105°	86.3	69.8	64.8	59.9	52.1	46.9	44.4	43.0	44.4	46.9	52.1
107.5°	93.7	77.5	72.6	67.6	59.9	55.0	52.5	51.4	52.5	55.0	59.9
110°	101.1	85.6	80.5	75.4	68.0	63.4	61.3	59.9	61.3	63.4	68.0

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	108.2	93.4	88.1	82.8	75.7	71.5	69.1	67.6	69.1	71.5	75.7
115°	115.6	100.4	95.6	90.9	83.9	79.6	77.5	75.7	77.5	79.6	83.9
117.5°	122.3	108.2	103.2	98.3	91.6	87.7	85.6	84.2	85.6	87.7	91.6
120°	129.3	115.6	110.6	105.7	98.6	95.5	93.4	92.0	93.4	95.5	98.6
122.5°	136.0	123.3	118.2	113.1	106.0	102.5	100.4	99.4	100.4	102.5	106.0
125°	142.7	130.0	125.0	120.1	113.1	108.9	106.8	105.7	106.8	108.9	113.1
127.5°	149.0	136.7	131.6	126.5	119.8	115.2	112.4	111.0	112.4	115.2	119.8
130°	154.7	142.3	137.4	132.5	125.4	120.5	117.0	115.6	117.0	120.5	125.4
132.5°	159.6	148.0	143.0	138.1	130.7	125.4	121.5	119.8	121.5	125.4	130.7
135°	164.2	152.9	148.0	143.0	134.9	129.7	125.4	124.0	125.4	129.7	134.9
137.5°	168.1	156.8	152.2	147.6	139.5	133.9	129.7	127.9	129.7	133.9	139.5
140°	171.2	160.7	156.1	151.5	143.7	138.1	133.9	132.5	133.9	138.1	143.7
142.5°	173.7	163.5	159.2	155.0	147.6	142.0	138.1	137.0	138.1	142.0	147.6
145°	176.2	166.6	162.8	158.9	151.8	146.6	143.0	141.6	143.0	146.6	151.8
147.5°	178.3	169.1	165.6	162.1	156.1	151.1	147.6	146.6	147.6	151.1	156.1
150°	179.7	171.6	168.4	165.2	159.9	155.4	152.6	151.5	152.6	155.4	159.9
152.5°	181.1	174.0	171.2	168.4	163.5	159.6	156.8	156.4	156.8	159.6	163.5
155°	182.5	176.5	173.8	171.2	167.3	163.5	161.4	161.0	161.4	163.5	167.3
157.5°	183.6	178.3	176.0	173.7	170.5	167.0	165.2	164.9	165.2	167.0	170.5
160°	184.3	180.0	178.1	176.2	173.3	170.5	169.1	168.8	169.1	170.5	173.3
162.5°	184.6	181.1	179.7	178.3	175.8	173.7	172.3	172.6	172.3	173.7	175.8
165°	185.0	181.8	180.8	179.7	177.9	175.8	175.1	175.5	175.1	175.8	177.9
167.5°	185.0	182.5	181.8	181.1	179.7	178.3	177.6	177.9	177.6	178.3	179.7
170°	184.6	182.8	182.3	181.8	181.1	180.0	179.7	180.4	179.7	180.0	181.1
172.5°	184.3	183.2	182.8	182.5	182.1	181.1	181.4	181.8	181.4	181.1	182.1
175°	183.9	183.2	183.0	182.8	182.8	182.1	182.5	182.8	182.5	182.1	182.8
177.5°	183.6	183.2	183.2	183.2	183.2	182.5	182.8	183.6	182.8	182.5	183.2
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	1959.8	1967.4	1965.9	1950.7	1933.9	1920.2	1894.3	1897.4	1888.3	1889.8	1898.9
5°	1911.1	1911.1	1905.0	1883.7	1856.3	1841.0	1812.1	1804.5	1786.2	1784.7	1783.2
7.5°	1859.3	1851.7	1844.1	1813.6	1780.1	1755.8	1716.2	1707.0	1688.8	1676.6	1670.5
10°	1798.4	1787.7	1772.5	1737.5	1696.4	1665.9	1624.8	1612.6	1577.6	1562.4	1553.2
12.5°	1731.4	1725.3	1700.9	1672.0	1605.0	1571.5	1512.1	1524.3	1489.3	1458.8	1454.3
15°	1664.4	1641.6	1627.9	1580.6	1499.9	1484.7	1437.5	1413.1	1381.2	1356.8	1356.8
17.5°	1598.9	1563.9	1533.4	1483.2	1423.8	1381.2	1346.1	1334.0	1294.4	1270.0	1265.4
20°	1512.1	1472.5	1464.9	1393.3	1352.2	1305.0	1271.5	1241.1	1212.1	1201.5	1193.9
22.5°	1429.9	1384.2	1372.0	1311.1	1270.0	1222.8	1189.3	1168.0	1146.7	1139.0	1125.3
25°	1341.6	1314.2	1295.9	1230.4	1184.7	1140.6	1117.7	1102.5	1082.7	1081.2	1072.0
27.5°	1256.3	1230.4	1212.1	1149.7	1116.2	1075.1	1056.8	1040.1	1029.4	1024.8	1020.3
30°	1183.2	1154.3	1133.0	1087.3	1046.2	1012.7	997.4	986.8	980.7	973.1	971.5
32.5°	1102.5	1085.7	1056.8	1021.8	989.8	957.8	948.7	941.1	931.9	928.9	927.4
35°	1034.0	1011.1	992.9	953.3	939.6	912.1	901.5	895.4	883.2	880.2	877.1
37.5°	967.0	945.6	925.9	901.5	875.6	860.4	854.3	845.1	839.1	840.6	837.5
40°	900.0	883.2	868.0	842.1	826.9	819.3	807.1	797.9	794.9	796.4	794.9
42.5°	834.5	819.3	810.1	790.3	775.1	767.5	759.9	750.7	755.3	755.3	759.9
45°	775.1	761.4	755.3	740.1	730.9	718.8	711.1	709.6	715.7	714.2	714.2
47.5°	714.2	709.6	702.0	688.3	676.1	668.5	667.0	667.0	673.1	676.1	674.6
50°	667.0	657.8	648.7	638.0	628.9	625.9	621.3	624.3	630.4	630.4	633.5
52.5°	607.6	601.5	598.5	589.3	583.2	583.2	583.2	584.7	589.3	593.9	592.4
55°	555.8	551.2	548.2	543.6	536.0	537.5	536.0	539.1	543.6	548.2	551.2
57.5°	501.0	499.5	496.4	488.8	488.8	487.3	491.9	493.4	501.0	504.0	508.6
60°	452.3	447.7	447.7	441.6	441.6	441.6	446.2	450.7	456.8	458.4	461.4
62.5°	400.5	400.5	399.0	394.4	394.4	399.0	400.5	406.6	409.6	409.6	414.2
65°	351.8	350.2	348.7	350.2	351.8	351.8	356.3	359.4	362.4	363.9	365.5
67.5°	303.0	301.5	304.6	303.0	306.1	312.2	310.6	315.2	319.8	319.8	321.3
70°	257.4	260.4	258.9	261.9	260.4	263.4	268.0	269.5	269.5	271.1	275.6
72.5°	214.7	214.7	214.7	213.2	214.7	217.8	220.8	222.3	225.4	226.9	231.5
75°	173.6	173.6	170.6	173.6	173.6	176.6	179.7	179.7	179.7	182.7	187.3
77.5°	131.0	132.5	131.0	134.0	134.0	135.5	138.6	137.1	140.1	141.6	143.1
80°	95.9	94.4	94.4	94.4	95.9	95.9	99.0	100.5	100.5	105.1	102.0
82.5°	60.9	62.4	60.9	62.4	62.4	64.0	62.4	64.0	65.5	68.5	67.0
85°	35.0	33.5	33.5	35.0	33.5	33.5	35.0	33.5	35.0	33.5	35.0
87.5°	13.7	12.2	12.2	12.2	12.2	10.7	10.7	9.1	9.1	9.1	7.6
90°	4.2	4.8	5.3	7.0	9.5	11.6	12.0	11.6	11.3	10.6	11.3
92.5°	14.8	16.8	18.7	28.2	41.6	53.6	54.3	45.4	35.6	30.3	26.4
95°	26.1	30.3	34.5	50.7	81.4	122.3	138.1	120.8	92.3	70.8	56.0
97.5°	35.2	40.0	44.7	65.5	108.2	174.0	225.1	226.9	188.8	150.8	115.2
100°	44.0	49.0	53.9	72.6	115.6	191.7	278.3	329.1	321.7	278.0	229.7
102.5°	52.1	57.0	62.0	78.9	115.9	185.0	280.1	367.1	408.7	407.3	375.2
105°	59.9	64.8	69.8	86.3	117.7	175.8	261.1	354.8	428.1	467.9	472.4
107.5°	67.6	72.6	77.5	93.7	121.5	170.9	243.4	328.7	407.3	466.5	501.0
110°	75.4	80.5	85.6	101.1	126.5	169.5	231.5	304.4	378.7	441.8	486.9

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	82.8	88.1	93.4	108.2	131.8	169.8	223.7	287.5	352.7	412.6	461.5
115°	90.9	95.6	100.4	115.6	137.0	171.2	218.4	274.1	332.2	386.5	432.6
117.5°	98.3	103.2	108.2	122.3	142.7	173.3	215.6	264.9	315.3	363.9	406.9
120°	105.7	110.6	115.6	129.3	148.3	175.5	213.1	257.9	303.3	347.0	384.4
122.5°	113.1	118.2	123.3	136.0	153.3	177.9	211.7	251.9	293.8	332.9	367.8
125°	120.1	125.0	130.0	142.7	158.5	180.4	210.0	246.3	284.7	321.0	352.0
127.5°	126.5	131.6	136.7	149.0	163.5	182.8	208.9	241.0	275.5	309.0	338.6
130°	132.5	137.4	142.3	154.7	168.1	185.7	208.2	235.7	266.7	297.0	324.8
132.5°	138.1	143.0	148.0	159.6	172.6	188.5	207.9	231.5	258.2	285.7	310.7
135°	143.0	148.0	152.9	164.2	176.5	190.6	207.5	227.6	250.5	273.7	297.0
137.5°	147.6	152.2	156.8	168.1	179.7	192.7	207.5	224.8	244.2	264.2	283.3
140°	151.5	156.1	160.7	171.2	182.1	194.1	207.2	222.3	238.2	255.1	271.3
142.5°	155.0	159.2	163.5	173.7	184.3	195.2	207.2	219.8	233.2	247.0	260.4
145°	158.9	162.8	166.6	176.2	186.0	195.9	206.5	217.7	228.7	240.3	251.2
147.5°	162.1	165.6	169.1	178.3	187.1	196.2	205.4	215.6	225.1	234.6	243.4
150°	165.2	168.4	171.6	179.7	187.8	195.9	204.3	212.8	221.3	229.0	236.4
152.5°	168.4	171.2	174.0	181.1	188.1	195.2	202.6	210.3	217.4	224.4	230.4
155°	171.2	173.8	176.5	182.5	188.5	194.5	200.5	207.2	213.9	219.5	224.8
157.5°	173.7	176.0	178.3	183.6	188.5	193.1	198.4	204.3	209.6	214.6	219.1
160°	176.2	178.1	180.0	184.3	188.5	192.0	196.2	201.2	205.7	209.6	213.5
162.5°	178.3	179.7	181.1	184.6	188.1	191.0	194.5	198.4	201.9	205.0	208.2
165°	179.7	180.8	181.8	185.0	187.4	189.5	192.0	195.2	198.0	200.5	202.9
167.5°	181.1	181.8	182.5	185.0	187.1	188.1	189.9	192.0	194.1	196.2	198.0
170°	181.8	182.3	182.8	184.6	186.4	187.1	188.1	189.5	191.3	192.4	193.8
172.5°	182.5	182.8	183.2	184.3	185.3	185.7	186.0	187.1	188.1	188.8	189.9
175°	182.8	183.0	183.2	183.9	184.6	184.3	184.6	185.0	186.0	186.4	186.7
177.5°	183.2	183.2	183.2	183.6	184.3	183.6	183.2	183.6	184.3	184.3	184.6
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	1888.3	1892.8	1882.2	1879.1	1882.2	1871.5	1874.5	1877.6	1877.6	1882.2	1885.2
5°	1778.6	1772.5	1761.9	1758.8	1755.8	1760.3	1757.3	1761.9	1763.4	1774.0	1775.6
7.5°	1670.5	1661.4	1652.2	1643.1	1640.0	1632.4	1640.0	1640.0	1650.7	1647.7	1655.3
10°	1542.6	1541.1	1528.9	1524.3	1518.2	1506.0	1522.8	1518.2	1525.8	1539.5	1542.6
12.5°	1448.2	1431.4	1439.0	1417.7	1425.3	1413.1	1414.7	1414.7	1426.8	1428.4	1425.3
15°	1358.3	1344.6	1324.8	1315.7	1311.1	1305.0	1324.8	1326.3	1317.2	1338.5	1330.9
17.5°	1267.0	1267.0	1248.7	1244.1	1231.9	1238.0	1235.0	1236.5	1233.5	1248.7	1256.3
20°	1187.8	1180.2	1174.1	1175.6	1160.4	1157.3	1154.3	1157.3	1168.0	1178.6	1181.7
22.5°	1123.8	1119.2	1104.0	1107.1	1094.9	1099.4	1096.4	1104.0	1105.5	1105.5	1116.2
25°	1062.9	1056.8	1058.3	1052.2	1047.7	1047.7	1043.1	1047.7	1053.8	1056.8	1058.3
27.5°	1017.2	1012.7	1005.0	1000.5	1003.5	995.9	1002.0	1006.6	1006.6	1003.5	1006.6
30°	962.4	965.4	965.4	950.2	956.3	953.3	957.8	960.9	960.9	962.4	959.4
32.5°	925.9	916.7	915.2	913.7	913.7	907.6	907.6	912.1	913.7	915.2	919.8
35°	877.1	877.1	869.5	874.1	868.0	869.5	868.0	869.5	872.6	868.0	872.6
37.5°	833.0	834.5	831.4	834.5	836.0	833.0	829.9	836.0	833.0	833.0	829.9
40°	794.9	793.4	794.9	794.9	794.9	796.4	793.4	793.4	793.4	790.3	787.3
42.5°	762.9	753.8	756.8	758.3	753.8	753.8	755.3	753.8	758.3	749.2	749.2
45°	717.2	714.2	715.7	715.7	718.8	714.2	717.2	718.8	714.2	712.7	709.6
47.5°	676.1	679.2	676.1	679.2	679.2	682.2	676.1	677.6	679.2	673.1	668.5
50°	635.0	635.0	639.6	638.0	639.6	636.5	636.5	635.0	636.5	633.5	628.9
52.5°	596.9	592.4	600.0	598.5	596.9	595.4	593.9	595.4	592.4	589.3	589.3
55°	549.7	549.7	554.3	555.8	555.8	552.8	549.7	551.2	549.7	548.2	546.7
57.5°	511.7	505.6	508.6	510.1	510.1	505.6	508.6	505.6	505.6	507.1	502.5
60°	462.9	462.9	459.9	464.4	464.4	461.4	461.4	462.9	459.9	458.4	456.8
62.5°	411.2	412.7	417.2	418.8	420.3	417.2	414.2	415.7	415.7	411.2	412.7
65°	367.0	370.0	376.1	374.6	371.6	373.1	370.0	371.6	367.0	368.5	363.9
67.5°	324.4	322.8	324.4	324.4	327.4	325.9	322.8	322.8	321.3	325.9	321.3
70°	278.7	278.7	278.7	278.7	280.2	281.7	278.7	275.6	277.1	274.1	272.6
72.5°	231.5	233.0	231.5	234.5	229.9	233.0	233.0	231.5	229.9	229.9	229.9
75°	187.3	190.3	185.8	187.3	185.8	188.8	187.3	187.3	184.3	182.7	184.3
77.5°	143.1	144.7	141.6	143.1	141.6	143.1	143.1	141.6	141.6	141.6	141.6
80°	102.0	103.5	102.0	100.5	99.0	102.0	99.0	100.5	102.0	100.5	103.5
82.5°	65.5	65.5	64.0	65.5	62.4	62.4	64.0	64.0	62.4	65.5	62.4
85°	32.0	32.0	35.0	32.0	30.5	30.5	30.5	32.0	30.5	33.5	32.0
87.5°	7.6	6.1	7.6	7.6	6.1	6.1	7.6	6.1	7.6	9.1	6.1
90°	11.4	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.4
92.5°	25.0	23.6	23.3	21.8	22.2	21.5	22.2	21.8	23.3	23.6	25.0
95°	52.2	48.3	43.7	40.9	39.8	40.2	39.8	40.9	43.7	48.3	52.2
97.5°	104.6	94.1	80.3	73.3	69.4	67.3	69.4	73.3	80.3	94.1	104.6
100°	208.4	187.1	157.8	142.7	132.5	126.1	132.5	142.7	157.8	187.1	208.4
102.5°	352.3	329.4	297.0	268.5	255.1	245.9	255.1	268.5	297.0	329.4	352.3
105°	466.6	460.8	439.0	417.1	402.0	397.1	402.0	417.1	439.0	460.8	466.6
107.5°	508.0	515.1	514.7	511.6	507.0	498.9	507.0	511.6	514.7	515.1	508.0
110°	501.4	515.8	530.9	537.6	540.8	540.4	540.8	537.6	530.9	515.8	501.4

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	478.6	495.7	518.2	530.6	537.3	539.7	537.3	530.6	518.2	495.7	478.6
115°	450.8	468.9	493.9	510.1	519.3	522.5	519.3	510.1	493.9	468.9	450.8
117.5°	424.2	441.4	467.2	484.4	493.9	496.4	493.9	484.4	467.2	441.4	424.2
120°	400.4	416.4	441.1	457.7	467.9	471.4	467.9	457.7	441.1	416.4	400.4
122.5°	381.9	396.0	417.5	433.7	442.5	445.3	442.5	433.7	417.5	396.0	381.9
125°	365.2	378.4	398.8	412.2	421.0	423.8	421.0	412.2	398.8	378.4	365.2
127.5°	350.9	363.2	381.2	393.9	401.6	403.7	401.6	393.9	381.2	363.2	350.9
130°	336.5	348.1	365.3	377.3	384.4	387.2	384.4	377.3	365.3	348.1	336.5
132.5°	321.4	332.2	349.1	361.1	367.5	369.9	367.5	361.1	349.1	332.2	321.4
135°	306.8	316.7	331.9	343.5	349.8	351.3	349.8	343.5	331.9	316.7	306.8
137.5°	292.1	300.9	315.3	325.5	331.2	333.3	331.2	325.5	315.3	300.9	292.1
140°	279.0	286.8	298.1	307.2	312.5	314.6	312.5	307.2	298.1	286.8	279.0
142.5°	266.5	272.7	283.3	291.4	295.9	295.9	295.9	291.4	283.3	272.7	266.5
145°	256.3	261.4	269.9	275.9	279.4	280.4	279.4	275.9	269.9	261.4	256.3
147.5°	247.3	251.2	258.6	263.5	266.0	266.7	266.0	263.5	258.6	251.2	247.3
150°	239.6	242.7	248.0	252.3	254.4	254.7	254.4	252.3	248.0	242.7	239.6
152.5°	233.0	235.7	239.6	243.1	244.5	244.5	244.5	243.1	239.6	235.7	233.0
155°	226.8	228.7	232.5	235.0	236.4	235.7	236.4	235.0	232.5	228.7	226.8
157.5°	220.7	222.3	225.1	227.2	227.9	227.9	227.9	227.2	225.1	222.3	220.7
160°	214.8	216.0	218.4	220.2	220.5	220.5	220.5	220.2	218.4	216.0	214.8
162.5°	209.1	210.0	212.4	213.5	213.9	213.5	213.9	213.5	212.4	210.0	209.1
165°	203.6	204.3	205.7	207.2	207.2	206.8	207.2	207.2	205.7	204.3	203.6
167.5°	198.7	199.4	200.1	200.8	200.8	200.5	200.8	200.8	200.1	199.4	198.7
170°	194.2	194.5	194.8	195.9	195.5	194.8	195.5	195.9	194.8	194.5	194.2
172.5°	190.0	190.2	190.6	191.0	190.6	190.2	190.6	191.0	190.6	190.2	190.0
175°	186.9	187.1	187.1	187.4	187.1	186.4	187.1	187.4	187.1	187.1	186.9
177.5°	184.6	184.6	184.6	184.6	184.3	183.6	184.3	184.6	184.6	184.6	184.6
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	1880.6	1892.8	1888.3	1871.5	1891.3	1891.3	1905.0	1905.0	1921.8	1927.8	1937.0
5°	1774.0	1783.2	1790.8	1783.2	1796.9	1818.2	1830.4	1841.0	1863.9	1873.0	1886.7
7.5°	1659.8	1676.6	1684.2	1684.2	1707.0	1731.4	1755.8	1771.0	1803.0	1815.2	1828.9
10°	1548.7	1568.5	1583.7	1582.2	1620.2	1635.5	1665.9	1700.9	1732.9	1751.2	1771.0
12.5°	1431.4	1442.1	1463.4	1493.9	1503.0	1530.4	1565.4	1609.6	1667.4	1684.2	1713.1
15°	1334.0	1362.9	1379.6	1393.3	1414.7	1440.6	1478.6	1521.3	1579.1	1615.7	1646.1
17.5°	1251.7	1289.8	1300.5	1297.4	1324.8	1364.4	1408.6	1440.6	1492.3	1536.5	1565.4
20°	1184.7	1200.0	1218.2	1225.8	1247.2	1289.8	1332.4	1369.0	1411.6	1446.6	1480.1
22.5°	1117.7	1129.9	1145.1	1158.8	1175.6	1200.0	1241.1	1286.8	1327.9	1361.4	1399.4
25°	1062.9	1070.5	1084.2	1094.9	1113.2	1129.9	1158.8	1209.1	1257.8	1277.6	1311.1
27.5°	1009.6	1015.7	1024.8	1037.0	1046.2	1062.9	1088.8	1129.9	1180.2	1200.0	1245.6
30°	962.4	967.0	976.1	982.2	986.8	1006.6	1026.4	1058.3	1096.4	1123.8	1157.3
32.5°	918.2	922.8	931.9	933.5	939.6	950.2	968.5	997.4	1030.9	1053.8	1082.7
35°	869.5	872.6	881.7	884.7	889.3	898.4	912.1	933.5	963.9	980.7	1006.6
37.5°	831.4	829.9	836.0	840.6	846.7	851.2	855.8	877.1	900.0	915.2	935.0
40°	790.3	787.3	788.8	794.9	797.9	804.0	804.0	825.3	840.6	852.8	868.0
42.5°	749.2	747.7	744.6	747.7	750.7	752.3	753.8	769.0	784.2	794.9	811.6
45°	708.1	706.6	703.5	705.0	705.0	708.1	712.7	718.8	729.4	738.5	747.7
47.5°	670.0	667.0	662.4	660.9	663.9	663.9	663.9	670.0	680.7	683.7	692.9
50°	630.4	625.9	619.8	616.7	616.7	615.2	618.2	619.8	628.9	632.0	639.6
52.5°	587.8	584.7	578.7	572.6	574.1	571.0	572.6	574.1	577.1	581.7	586.3
55°	545.2	539.1	534.5	533.0	528.4	528.4	523.8	529.9	528.4	529.9	536.0
57.5°	504.0	498.0	490.3	487.3	482.7	481.2	478.2	476.6	478.2	482.7	487.3
60°	455.3	452.3	447.7	443.1	440.1	435.5	432.5	432.5	430.9	430.9	432.5
62.5°	408.1	406.6	400.5	399.0	395.9	392.9	388.3	385.3	385.3	388.3	389.8
65°	362.4	360.9	356.3	354.8	347.2	344.1	342.6	341.1	338.1	338.1	338.1
67.5°	319.8	315.2	315.2	307.6	301.5	298.5	295.4	293.9	293.9	293.9	295.4
70°	272.6	272.6	268.0	263.4	257.4	258.9	254.3	249.7	249.7	246.7	248.2
72.5°	226.9	225.4	220.8	219.3	214.7	210.1	207.1	210.1	205.6	204.1	205.6
75°	182.7	181.2	178.2	175.1	176.6	172.1	167.5	166.0	166.0	162.9	162.9
77.5°	140.1	143.1	137.1	135.5	132.5	129.4	127.9	126.4	126.4	126.4	129.4
80°	97.5	99.0	99.0	95.9	97.5	92.9	92.9	92.9	88.3	89.8	91.4
82.5°	62.4	62.4	60.9	62.4	60.9	60.9	59.4	59.4	57.9	57.9	59.4
85°	35.0	33.5	32.0	35.0	33.5	33.5	32.0	32.0	32.0	32.0	32.0
87.5°	7.6	9.1	9.1	9.1	9.1	10.7	10.7	10.7	12.2	12.2	12.2
90°	11.3	10.6	11.3	11.6	12.0	11.6	9.5	7.0	5.3	4.8	4.2
92.5°	26.4	30.3	35.6	45.4	54.3	53.6	41.6	28.2	18.7	16.8	14.8
95°	56.0	70.8	92.3	120.8	138.1	122.3	81.4	50.7	34.5	30.3	26.1
97.5°	115.2	150.8	188.8	226.9	225.1	174.0	108.2	65.5	44.7	40.0	35.2
100°	229.7	278.0	321.7	329.1	278.3	191.7	115.6	72.6	53.9	49.0	44.0
102.5°	375.2	407.3	408.7	367.1	280.1	185.0	115.9	78.9	62.0	57.0	52.1
105°	472.4	467.9	428.1	354.8	261.1	175.8	117.7	86.3	69.8	64.8	59.9
107.5°	501.0	466.5	407.3	328.7	243.4	170.9	121.5	93.7	77.5	72.6	67.6
110°	486.9	441.8	378.7	304.4	231.5	169.5	126.5	101.1	85.6	80.5	75.4

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	461.5	412.6	352.7	287.5	223.7	169.8	131.8	108.2	93.4	88.1	82.8
115°	432.6	386.5	332.2	274.1	218.4	171.2	137.0	115.6	100.4	95.6	90.9
117.5°	406.9	363.9	315.3	264.9	215.6	173.3	142.7	122.3	108.2	103.2	98.3
120°	384.4	347.0	303.3	257.9	213.1	175.5	148.3	129.3	115.6	110.6	105.7
122.5°	367.8	332.9	293.8	251.9	211.7	177.9	153.3	136.0	123.3	118.2	113.1
125°	352.0	321.0	284.7	246.3	210.0	180.4	158.5	142.7	130.0	125.0	120.1
127.5°	338.6	309.0	275.5	241.0	208.9	182.8	163.5	149.0	136.7	131.6	126.5
130°	324.8	297.0	266.7	235.7	208.2	185.7	168.1	154.7	142.3	137.4	132.5
132.5°	310.7	285.7	258.2	231.5	207.9	188.5	172.6	159.6	148.0	143.0	138.1
135°	297.0	273.7	250.5	227.6	207.5	190.6	176.5	164.2	152.9	148.0	143.0
137.5°	283.3	264.2	244.2	224.8	207.5	192.7	179.7	168.1	156.8	152.2	147.6
140°	271.3	255.1	238.2	222.3	207.2	194.1	182.1	171.2	160.7	156.1	151.5
142.5°	260.4	247.0	233.2	219.8	207.2	195.2	184.3	173.7	163.5	159.2	155.0
145°	251.2	240.3	228.7	217.7	206.5	195.9	186.0	176.2	166.6	162.8	158.9
147.5°	243.4	234.6	225.1	215.6	205.4	196.2	187.1	178.3	169.1	165.6	162.1
150°	236.4	229.0	221.3	212.8	204.3	195.9	187.8	179.7	171.6	168.4	165.2
152.5°	230.4	224.4	217.4	210.3	202.6	195.2	188.1	181.1	174.0	171.2	168.4
155°	224.8	219.5	213.9	207.2	200.5	194.5	188.5	182.5	176.5	173.8	171.2
157.5°	219.1	214.6	209.6	204.3	198.4	193.1	188.5	183.6	178.3	176.0	173.7
160°	213.5	209.6	205.7	201.2	196.2	192.0	188.5	184.3	180.0	178.1	176.2
162.5°	208.2	205.0	201.9	198.4	194.5	191.0	188.1	184.6	181.1	179.7	178.3
165°	202.9	200.5	198.0	195.2	192.0	189.5	187.4	185.0	181.8	180.8	179.7
167.5°	198.0	196.2	194.1	192.0	189.9	188.1	187.1	185.0	182.5	181.8	181.1
170°	193.8	192.4	191.3	189.5	188.1	187.1	186.4	184.6	182.8	182.3	181.8
172.5°	189.9	188.8	188.1	187.1	186.0	185.7	185.3	184.3	183.2	182.8	182.5
175°	186.7	186.4	186.0	185.0	184.6	184.3	184.6	183.9	183.2	183.0	182.8
177.5°	184.6	184.3	184.3	183.6	183.2	183.6	184.3	183.6	183.2	183.2	183.2
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1981.1	1981.1	1981.1	1981.1
2.5°	1944.6	1944.6	1967.4	1991.8
5°	1902.0	1912.6	1949.2	1982.7
7.5°	1860.8	1879.1	1924.8	1967.4
10°	1810.6	1835.0	1891.3	1941.5
12.5°	1761.9	1784.7	1850.2	1906.5
15°	1693.3	1722.3	1792.3	1862.4
17.5°	1624.8	1653.7	1739.0	1821.2
20°	1544.1	1582.2	1678.1	1787.7
22.5°	1469.5	1516.7	1623.3	1711.6
25°	1387.3	1460.3	1559.3	1673.5
27.5°	1314.2	1387.3	1487.8	1603.5
30°	1231.9	1306.5	1410.1	1516.7
32.5°	1152.7	1221.3	1321.8	1452.7
35°	1070.5	1136.0	1233.5	1365.9
37.5°	995.9	1059.9	1166.5	1288.3
40°	922.8	989.8	1081.2	1203.0
42.5°	854.3	913.7	995.9	1117.7
45°	791.8	834.5	910.6	1024.8
47.5°	726.4	764.4	834.5	948.7
50°	665.5	697.4	758.3	864.9
52.5°	606.1	633.5	689.8	775.1
55°	552.8	578.7	619.8	703.5
57.5°	498.0	517.7	557.3	624.3
60°	444.7	462.9	494.9	549.7
62.5°	391.4	406.6	437.0	481.2
65°	344.1	356.3	379.2	417.2
67.5°	298.5	306.1	324.4	354.8
70°	254.3	260.4	275.6	300.0
72.5°	207.1	213.2	229.9	246.7
75°	167.5	169.0	181.2	194.9
77.5°	131.0	129.4	138.6	149.2
80°	89.8	94.4	102.0	106.6
82.5°	60.9	62.4	65.5	68.5
85°	33.5	35.0	35.0	39.6
87.5°	13.7	15.2	15.2	16.8
90°	3.5	2.8	1.4	0.4
92.5°	12.0	10.2	7.4	5.3
95°	20.4	17.3	13.7	12.3
97.5°	28.9	24.3	20.4	18.3
100°	37.0	31.4	28.2	27.1
102.5°	44.7	39.1	35.9	35.2
105°	52.1	46.9	44.4	43.0
107.5°	59.9	55.0	52.5	51.4
110°	68.0	63.4	61.3	59.9

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	75.7	71.5	69.1	67.6
115°	83.9	79.6	77.5	75.7
117.5°	91.6	87.7	85.6	84.2
120°	98.6	95.5	93.4	92.0
122.5°	106.0	102.5	100.4	99.4
125°	113.1	108.9	106.8	105.7
127.5°	119.8	115.2	112.4	111.0
130°	125.4	120.5	117.0	115.6
132.5°	130.7	125.4	121.5	119.8
135°	134.9	129.7	125.4	124.0
137.5°	139.5	133.9	129.7	127.9
140°	143.7	138.1	133.9	132.5
142.5°	147.6	142.0	138.1	137.0
145°	151.8	146.6	143.0	141.6
147.5°	156.1	151.1	147.6	146.6
150°	159.9	155.4	152.6	151.5
152.5°	163.5	159.6	156.8	156.4
155°	167.3	163.5	161.4	161.0
157.5°	170.5	167.0	165.2	164.9
160°	173.3	170.5	169.1	168.8
162.5°	175.8	173.7	172.3	172.6
165°	177.9	175.8	175.1	175.5
167.5°	179.7	178.3	177.6	177.9
170°	181.1	180.0	179.7	180.4
172.5°	182.1	181.1	181.4	181.8
175°	182.8	182.1	182.5	182.8
177.5°	183.2	182.5	182.8	183.6
180°	183.2	183.2	183.2	183.2

TEST NUMBER: P997843

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.07	21.19	20.76	21.89	22.71	17.57	18.68	18.26	19.38	20.20
	3H	20.90	21.90	21.61	22.61	23.47	18.93	19.93	19.63	20.64	21.49
	4H	21.09	22.02	21.81	22.75	23.61	19.41	20.34	20.13	21.07	21.93
	6H	21.14	22.01	21.88	22.74	23.62	19.72	20.59	20.46	21.32	22.20
	8H	21.13	21.95	21.87	22.70	23.59	19.82	20.64	20.56	21.39	22.27
	12H	21.10	21.89	21.85	22.63	23.54	19.87	20.65	20.61	21.39	22.30
4H	2H	20.15	21.09	20.87	21.81	22.67	18.04	18.98	18.77	19.70	20.57
	3H	21.15	21.93	21.88	22.69	23.57	19.53	20.31	20.26	21.07	21.95
	4H	21.44	22.14	22.19	22.90	23.82	20.07	20.78	20.82	21.54	22.45
	6H	21.58	22.19	22.35	22.97	23.90	20.46	21.08	21.23	21.86	22.78
	8H	21.58	22.15	22.36	22.93	23.87	20.58	21.15	21.35	21.93	22.86
	12H	21.56	22.07	22.35	22.87	23.81	20.65	21.16	21.44	21.96	22.90
8H	4H	21.46	22.03	22.24	22.81	23.75	20.23	20.80	21.01	21.58	22.52
	6H	21.65	22.12	22.45	22.94	23.88	20.68	21.15	21.48	21.97	22.90
	8H	21.68	22.10	22.50	22.92	23.87	20.83	21.25	21.64	22.07	23.02
	12H	21.68	22.05	22.49	22.86	23.87	20.93	21.30	21.75	22.11	23.12
12H	4H	21.43	21.94	22.23	22.75	23.68	20.22	20.73	21.01	21.53	22.47
	6H	21.63	22.05	22.45	22.87	23.82	20.68	21.10	21.49	21.92	22.87
	8H	21.67	22.04	22.49	22.85	23.86	20.85	21.21	21.66	22.03	23.04