

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997846

Luminaire Tested: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P997846
REPORT IS A COMBINATION OF REPORTS P983583 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5287.4 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997846

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P997846

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	100	94	90	85	94	89	85	81	79	75	72	69	67	64	61	59	57
2	90	81	74	68	84	77	70	65	68	63	58	60	56	52	52	49	46
3	82	71	62	56	76	67	59	53	59	53	48	52	47	43	46	42	39
4	74	62	53	47	70	59	51	45	52	46	41	46	41	37	40	36	33
5	68	55	46	40	64	52	44	38	47	40	35	41	36	31	36	32	28
6	63	50	41	34	59	47	39	33	42	35	30	37	32	27	33	28	25
7	58	45	36	30	54	42	34	29	38	31	26	34	28	24	30	25	22
8	54	41	32	27	50	38	31	25	35	28	23	31	25	21	27	23	19
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16632	16632	16632
5°	16706	15921	15831
10°	16595	15371	15146
15°	16360	14799	14442
20°	16066	14201	13775
25°	15773	13627	13169
30°	15364	13044	12569
35°	14950	12483	12129
40°	14515	11997	11692
45°	14100	11555	11311
50°	13655	11149	10935
55°	13187	10718	10551
60°	12614	10269	10149
65°	12016	9752	9684
70°	11342	9198	9185
75°	10478	8643	8715
80°	9117	8066	8226
85°	7741	7522	7807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14100 cd/sqm

TEST NUMBER: P997846

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	1.9
10°-20°	285.7	5.4
20°-30°	432.8	8.2
30°-40°	527.1	10.0
40°-50°	567.1	10.7
50°-60°	550.7	10.4
60°-70°	481.0	9.1
70°-80°	370.2	7.0
80°-90°	249.1	4.7
90°-100°	245.3	4.6
100°-110°	376.0	7.1
110°-120°	346.4	6.6
120°-130°	263.0	5.0
130°-140°	193.7	3.7
140°-150°	135.0	2.6
150°-160°	92.6	1.8
160°-170°	54.5	1.0
170°-180°	17.7	0.3
0°-30°	818.1	15.5
0°-40°	1345.2	25.4
0°-60°	2463.0	46.6
0°-90°	3563.2	67.4
90°-120°	967.7	18.3
90°-150°	1559.3	29.5
90°-180°	1724.0	32.6
0°-180°	5287.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1051	1051	1051	1051	1051	
5°	1054	1049	1040	1049	1048	100
15°	1005	1008	1008	1022	1020	283
25°	914	924	938	956	961	420
35°	787	813	842	876	886	492
45°	646	687	740	787	802	498
55°	495	550	629	684	704	443
65°	338	413	502	565	585	336
75°	187	273	370	436	455	198
85°	55	149	247	311	332	58
90°	16	108	213	273	292	11
95°	24	114	313	285	291	22
105°	51	117	392	651	598	54
115°	82	118	310	588	676	81
125°	109	128	262	458	530	97
135°	126	149	224	356	412	97
145°	142	163	206	265	297	89
155°	161	174	200	227	236	74
165°	176	181	192	204	207	49
175°	183	183	185	187	186	17
180°	183	183	183	183	183	

TEST NUMBER: P997846

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1050.7	1050.7	1050.7	1050.7	1050.7
2.5°	1058.3	1053.7	1043.1	1050.7	1047.6
5°	1053.7	1049.2	1040.0	1049.2	1047.6
7.5°	1046.1	1043.1	1035.4	1046.1	1044.6
10°	1037.0	1033.9	1029.4	1041.5	1040.0
12.5°	1021.7	1023.3	1020.2	1032.4	1030.9
15°	1005.0	1008.0	1008.0	1021.7	1020.2
17.5°	983.7	989.8	994.3	1008.0	1008.0
20°	962.4	970.0	976.1	992.8	992.8
22.5°	939.5	948.7	957.8	974.5	977.6
25°	913.6	924.3	938.0	956.3	960.8
27.5°	883.2	899.9	915.2	938.0	941.0
30°	852.7	872.5	892.3	916.7	921.2
32.5°	819.2	842.1	866.4	895.4	904.5
35°	787.2	813.1	842.1	875.6	886.2
37.5°	752.2	781.2	817.7	854.2	864.9
40°	717.2	750.7	791.8	831.4	845.1
42.5°	683.7	717.2	765.9	810.1	823.8
45°	645.6	686.7	740.0	787.2	802.5
47.5°	609.1	653.2	714.2	762.9	779.6
50°	571.0	618.2	686.7	738.5	755.3
52.5°	534.5	584.7	657.8	711.1	729.4
55°	494.9	549.7	628.9	683.7	703.5
57.5°	456.8	517.7	596.9	656.3	676.1
60°	415.7	481.2	568.0	625.8	647.2
62.5°	379.2	447.7	534.5	596.9	616.7
65°	338.0	412.7	502.5	564.9	584.7
67.5°	301.5	379.2	470.5	533.0	554.3
70°	261.9	341.1	435.5	501.0	519.2
72.5°	225.4	307.6	403.5	467.5	490.3
75°	187.3	272.6	370.0	435.5	455.3
77.5°	150.7	239.1	338.0	403.5	424.8
80°	114.2	207.1	306.1	370.0	391.3
82.5°	83.7	175.1	275.6	339.6	359.4
85°	54.8	149.2	246.7	310.6	332.0
87.5°	33.5	124.9	222.3	284.7	304.5
90°	15.6	108.2	213.0	273.3	291.8
92.5°	19.0	111.2	241.6	271.7	286.5
95°	24.5	114.0	313.2	285.2	291.4
97.5°	29.0	116.0	389.6	325.5	306.4
100°	37.8	116.0	430.6	417.0	351.5
102.5°	44.3	116.4	421.7	548.7	459.1
105°	50.6	116.6	392.1	650.8	598.1
107.5°	59.0	116.8	363.7	680.2	687.7
110°	66.0	117.0	342.7	661.2	717.0



TEST NUMBER: P997846

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	73.7	118.6	324.2	627.8	705.7
115°	81.8	118.4	309.8	587.8	676.3
117.5°	88.8	120.0	296.3	550.6	638.0
120°	96.6	121.4	284.7	514.6	602.4
122.5°	104.0	124.3	274.1	485.4	562.5
125°	108.7	128.0	261.8	458.1	530.4
127.5°	114.0	133.1	251.5	431.6	498.1
130°	118.6	138.9	241.7	406.5	469.4
132.5°	122.8	144.6	232.3	380.8	441.5
135°	125.5	149.4	224.2	355.6	412.2
137.5°	129.4	153.7	216.6	330.2	382.0
140°	134.0	156.1	210.2	306.4	351.1
142.5°	138.5	159.2	207.2	284.8	321.8
145°	141.6	162.8	206.5	265.4	297.1
147.5°	146.6	165.6	205.4	248.8	272.8
150°	151.5	168.4	204.3	239.6	254.7
152.5°	156.4	171.2	202.6	233.0	244.5
155°	161.0	173.8	200.5	226.8	235.7
157.5°	164.9	176.0	198.4	220.7	227.9
160°	168.8	178.1	196.2	214.8	220.5
162.5°	172.6	179.7	194.5	209.1	213.5
165°	175.5	180.8	192.0	203.6	206.8
167.5°	177.9	181.8	189.9	198.7	200.5
170°	180.4	182.3	188.1	194.2	194.8
172.5°	181.8	182.8	186.0	190.0	190.2
175°	182.8	183.0	184.6	186.9	186.4
177.5°	183.6	183.2	183.2	184.6	183.6
180°	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P997846

CATALOG NUMBER: SA2XXDIP-B1005D330UB27-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.41	17.53	17.19	18.34	19.34	19.49	20.60	20.27	21.42	22.41
	3H	17.89	18.90	18.68	19.72	20.75	22.09	23.11	22.88	23.93	24.95
	4H	18.37	19.34	19.18	20.17	21.20	23.35	24.32	24.16	25.15	26.18
	6H	18.67	19.57	19.49	20.40	21.45	24.66	25.56	25.48	26.40	27.44
	8H	18.74	19.59	19.57	20.45	21.50	25.33	26.19	26.16	27.04	28.09
	12H	18.76	19.58	19.60	20.43	21.51	26.06	26.88	26.90	27.73	28.81
4H	2H	17.49	18.45	18.30	19.28	20.31	19.84	20.81	20.65	21.64	22.67
	3H	19.21	20.04	20.04	20.90	21.95	22.65	23.47	23.48	24.34	25.39
	4H	19.85	20.60	20.68	21.46	22.54	24.08	24.83	24.92	25.69	26.77
	6H	20.27	20.94	21.13	21.82	22.90	25.56	26.22	26.41	27.11	28.18
	8H	20.39	21.01	21.25	21.89	22.99	26.32	26.95	27.18	27.83	28.92
	12H	20.45	21.01	21.32	21.91	23.01	27.17	27.73	28.04	28.63	29.73
8H	4H	20.66	21.28	21.51	22.16	23.25	24.24	24.87	25.10	25.75	26.84
	6H	21.30	21.83	22.18	22.75	23.84	25.88	26.41	26.77	27.33	28.42
	8H	21.52	22.00	22.42	22.91	24.02	26.78	27.25	27.67	28.16	29.27
	12H	21.67	22.09	22.57	23.00	24.16	27.78	28.20	28.68	29.11	30.27
12H	4H	20.87	21.43	21.74	22.33	23.43	24.23	24.80	25.11	25.70	26.79
	6H	21.64	22.11	22.53	23.02	24.13	25.91	26.38	26.80	27.30	28.40
	8H	21.95	22.37	22.85	23.28	24.44	26.85	27.27	27.75	28.18	29.34