

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997893

Luminaire Tested: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997893
REPORT IS A COMBINATION OF REPORTS P983630 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5372.0 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83
1	105	101	97	94	100	97	93	90	89	86	84	81	79	77	74	73	71
2	96	89	83	78	92	85	80	75	78	74	70	72	69	66	66	64	61
3	88	79	72	66	84	76	69	64	70	65	60	65	60	57	60	56	53
4	81	71	63	57	78	68	61	55	63	57	52	58	53	49	54	50	46
5	75	63	55	49	72	61	54	48	57	50	46	53	47	43	49	45	41
6	70	57	49	43	66	55	48	42	52	45	40	48	43	38	45	40	37
7	65	52	44	39	62	51	43	38	47	41	36	44	39	34	41	36	33
8	60	48	40	35	58	46	39	34	43	37	32	41	35	31	38	33	30
9	56	44	36	31	54	43	36	31	40	34	29	37	32	28	35	30	27
10	53	41	33	28	51	39	33	28	37	31	27	35	30	26	33	28	25

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30413	30413	30413	30413
5°	30486	32427	30603	25799
10°	30132	35400	30321	21271
15°	29401	37339	29809	17916
20°	28943	35058	28943	15573
25°	28020	30119	28148	13925
30°	26503	23676	27007	12614
35°	25158	16372	25578	11542
40°	23613	12361	23882	10686
45°	21707	10158	22061	9762
50°	20059	8915	20095	8937
55°	18181	7596	18298	8040
60°	16177	6345	16401	7017
65°	14383	5161	14646	5992
70°	12598	4049	12919	4833
75°	10573	2940	10987	3505
80°	8255	1863	8846	2079
85°	5424	938	5848	694

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 31439 cd/sqm

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	3.4
10°-20°	532.6	9.9
20°-30°	773.0	14.4
30°-40°	814.9	15.2
40°-50°	721.1	13.4
50°-60°	575.8	10.7
60°-70°	391.1	7.3
70°-80°	200.1	3.7
80°-90°	48.4	0.9
90°-100°	25.0	0.5
100°-110°	79.6	1.5
110°-120°	136.2	2.5
120°-130°	179.2	3.3
130°-140°	201.1	3.7
140°-150°	197.2	3.7
150°-160°	165.4	3.1
160°-170°	109.7	2.0
170°-180°	38.3	0.7
0°-30°	1488.7	27.7
0°-40°	2303.6	42.9
0°-60°	3600.5	67.0
0°-90°	4240.2	78.9
90°-120°	240.9	4.5
90°-150°	818.4	15.2
90°-180°	1132.0	21.1
0°-180°	5372.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1921	1921	1921	1921	1921	
5°	1923	2146	1930	1707	1923	182
15°	1806	2638	1831	1266	1806	510
25°	1623	2198	1630	1016	1623	742
35°	1325	1196	1347	843	1325	829
45°	994	721	1010	693	994	771
55°	682	506	687	536	682	609
65°	405	312	412	362	405	402
75°	189	154	196	183	189	203
85°	38	40	41	30	38	45
90°	0	12	0	12	0	3
95°	18	21	18	21	18	20
105°	74	76	74	76	74	78
115°	137	137	137	137	137	135
125°	199	200	199	200	199	178
135°	257	260	257	260	257	199
145°	312	316	312	316	312	195
155°	357	360	357	360	357	164
165°	388	389	388	389	388	110
175°	404	403	404	403	404	38
180°	405	405	405	405	405	

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1931.6	1936.1	1943.5	1944.9	1959.7	1971.5	1984.8	1984.8	1989.2	1987.8	1976.0
5°	1922.8	1936.1	1955.3	1971.5	1998.1	2009.9	2027.6	2040.9	2052.7	2061.6	2060.1
7.5°	1908.0	1931.6	1959.7	1990.7	2026.2	2046.8	2071.9	2095.6	2111.8	2126.6	2136.9
10°	1882.9	1922.8	1961.2	2002.5	2048.3	2076.4	2105.9	2136.9	2162.0	2190.1	2216.7
12.5°	1848.9	1906.5	1953.8	2008.4	2064.6	2095.6	2142.8	2166.5	2215.2	2286.1	2305.3
15°	1806.1	1884.4	1928.7	1998.1	2071.9	2097.1	2162.0	2200.4	2300.8	2345.2	2398.3
17.5°	1766.2	1853.4	1912.5	1992.2	2064.6	2113.3	2176.8	2255.1	2339.2	2402.7	2461.8
20°	1733.8	1817.9	1888.8	1977.4	2069.0	2131.0	2197.5	2292.0	2383.5	2448.5	2494.3
22.5°	1659.9	1767.7	1850.4	1949.4	2060.1	2145.8	2209.3	2312.7	2411.6	2451.5	2491.4
25°	1623.0	1716.0	1812.0	1924.3	2054.2	2156.1	2210.8	2326.0	2413.1	2427.9	2436.7
27.5°	1555.1	1659.9	1772.2	1900.6	2052.7	2138.4	2207.8	2312.7	2382.1	2371.7	2345.2
30°	1470.9	1599.4	1723.4	1862.2	2032.1	2125.1	2190.1	2286.1	2321.5	2268.4	2221.1
32.5°	1408.9	1530.0	1667.3	1828.3	2008.4	2097.1	2160.6	2235.9	2243.3	2147.3	2067.5
35°	1324.7	1459.1	1614.1	1784.0	1968.6	2048.3	2107.4	2153.2	2117.7	1983.3	1888.8
37.5°	1249.4	1382.3	1547.7	1720.5	1913.9	1992.2	2039.5	2046.8	1959.7	1841.6	1702.7
40°	1166.7	1304.0	1476.8	1658.4	1853.4	1921.3	1950.8	1928.7	1803.2	1665.8	1504.9
42.5°	1084.0	1219.8	1405.9	1592.0	1776.6	1834.2	1846.0	1785.4	1631.9	1470.9	1284.8
45°	993.9	1135.7	1321.7	1509.3	1688.0	1720.5	1721.9	1634.8	1453.2	1284.8	1112.0
47.5°	920.0	1051.5	1236.1	1423.6	1574.3	1596.4	1587.6	1487.1	1289.2	1100.2	949.6
50°	838.8	964.3	1147.5	1332.1	1460.6	1466.5	1444.3	1301.1	1107.6	934.8	815.2
52.5°	751.7	878.7	1047.0	1224.3	1339.5	1330.6	1287.8	1134.2	952.5	809.3	717.7
55°	682.3	794.5	952.5	1125.3	1206.5	1181.4	1134.2	977.6	834.4	713.3	633.5
57.5°	605.5	704.4	859.5	1010.1	1057.4	1033.8	986.5	840.3	707.4	615.8	562.7
60°	533.1	623.2	759.1	884.6	921.5	896.4	841.8	710.3	614.3	537.6	497.7
62.5°	466.7	544.9	658.7	773.8	788.6	763.5	716.2	609.9	527.2	466.7	437.1
65°	404.6	478.5	570.0	657.2	670.5	643.9	595.1	518.4	448.9	410.5	382.5
67.5°	344.1	403.2	484.4	547.9	555.3	530.2	490.3	428.3	385.4	344.1	323.4
70°	290.9	335.2	398.7	450.4	453.4	429.7	409.1	353.0	320.5	290.9	274.7
72.5°	239.2	270.3	319.0	357.4	358.9	344.1	324.9	289.5	261.4	240.7	224.5
75°	189.0	215.6	245.1	279.1	277.6	265.8	251.1	228.9	205.3	192.0	184.6
77.5°	144.7	161.0	184.6	206.8	206.8	200.8	192.0	175.7	161.0	147.7	140.3
80°	103.4	113.7	132.9	140.3	143.2	141.8	134.4	122.6	116.7	106.3	103.4
82.5°	66.5	73.8	82.7	90.1	94.5	91.6	90.1	84.2	75.3	72.4	69.4
85°	38.4	41.4	45.8	50.2	51.7	50.2	53.2	48.7	44.3	44.3	42.8
87.5°	16.2	17.7	20.7	20.7	22.2	22.2	20.7	22.2	22.2	20.7	19.2
90°	0.3	1.2	2.1	3.0	3.9	4.4	5.2	6.9	8.6	10.3	12.0
92.5°	7.5	8.1	8.7	9.3	9.9	10.2	10.2	10.3	10.4	10.5	10.6
95°	17.8	18.6	19.3	20.1	20.8	21.2	21.3	21.4	21.6	21.7	21.9
97.5°	29.7	30.4	31.1	31.8	32.5	32.8	33.0	33.3	33.6	33.9	34.2
100°	43.4	44.0	44.6	45.2	45.8	46.1	46.2	46.4	46.7	46.9	47.1
102.5°	57.7	58.2	58.6	59.1	59.6	59.8	60.0	60.3	60.6	60.9	61.2
105°	73.5	73.7	73.9	74.2	74.4	74.5	74.6	74.7	74.9	75.0	75.2
107.5°	89.2	89.5	89.8	90.1	90.4	90.5	90.5	90.5	90.5	90.5	90.5
110°	104.2	104.6	105.1	105.5	106.0	106.2	106.2	106.2	106.2	106.2	106.2

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	120.6	121.0	121.5	121.9	122.4	122.6	122.6	122.5	122.4	122.4	122.3
115°	136.7	137.1	137.6	138.0	138.5	138.7	138.6	138.5	138.3	138.2	138.0
117.5°	152.7	153.3	153.9	154.5	155.1	155.4	155.2	154.8	154.5	154.1	153.7
120°	168.8	169.4	170.0	170.6	171.2	171.5	171.2	170.6	170.0	169.4	168.8
122.5°	183.5	184.3	185.0	185.8	186.5	186.9	186.7	186.3	186.0	185.6	185.2
125°	198.8	199.5	200.2	200.9	201.6	201.9	201.8	201.6	201.3	201.1	200.9
127.5°	213.9	214.7	215.5	216.4	217.2	217.6	217.5	217.2	216.9	216.6	216.3
130°	227.9	228.9	229.9	230.8	231.8	232.3	232.2	232.1	231.9	231.8	231.6
132.5°	243.6	244.4	245.1	245.9	246.6	247.0	247.0	247.1	247.2	247.2	247.3
135°	257.3	258.1	258.9	259.8	260.6	261.0	261.1	261.2	261.4	261.5	261.7
137.5°	272.3	273.0	273.7	274.4	275.1	275.4	275.5	275.6	275.7	275.9	276.0
140°	285.6	286.3	287.0	287.7	288.4	288.7	288.9	289.3	289.6	290.0	290.4
142.5°	299.3	300.0	300.6	301.3	302.0	302.3	302.4	302.7	302.9	303.2	303.4
145°	312.3	312.8	313.3	313.8	314.3	314.6	314.8	315.3	315.8	316.2	316.7
147.5°	323.9	324.6	325.2	325.9	326.6	326.9	327.1	327.4	327.7	328.0	328.3
150°	335.8	336.3	336.7	337.2	337.7	337.9	338.0	338.3	338.6	338.9	339.2
152.5°	346.4	346.9	347.3	347.8	348.3	348.5	348.7	349.1	349.4	349.8	350.2
155°	357.0	357.2	357.4	357.7	357.9	358.0	358.1	358.4	358.6	358.9	359.1
157.5°	366.2	366.4	366.5	366.7	366.8	366.9	367.0	367.1	367.3	367.4	367.6
160°	374.4	374.6	374.7	374.9	375.0	375.1	375.1	375.2	375.3	375.4	375.5
162.5°	381.9	381.9	381.9	381.9	381.9	381.9	381.9	382.0	382.1	382.2	382.3
165°	388.4	388.3	388.3	388.2	388.1	388.1	388.1	388.1	388.1	388.1	388.1
167.5°	394.2	394.0	393.8	393.5	393.3	393.2	393.2	393.2	393.2	393.2	393.2
170°	398.7	398.5	398.3	398.0	397.8	397.7	397.7	397.6	397.5	397.4	397.3
172.5°	401.8	401.6	401.3	401.1	400.8	400.7	400.7	400.6	400.5	400.5	400.4
175°	404.2	404.0	403.7	403.5	403.2	403.1	403.0	402.9	402.7	402.6	402.4
177.5°	405.5	405.3	405.1	404.8	404.6	404.5	404.4	404.3	404.1	404.0	403.8
180°	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1996.6	1998.1	2001.1	2015.8	2023.2	2024.7	2018.8	2032.1	2036.5	2032.1	2029.1
5°	2091.1	2100.0	2117.7	2136.9	2135.4	2136.9	2145.8	2154.6	2157.6	2145.8	2150.2
7.5°	2173.8	2191.6	2210.8	2240.3	2240.3	2255.1	2261.0	2268.4	2286.1	2277.2	2274.3
10°	2268.4	2292.0	2327.4	2374.7	2376.2	2390.9	2405.7	2429.3	2436.7	2430.8	2433.8
12.5°	2386.5	2432.3	2435.2	2486.9	2510.6	2513.5	2537.1	2532.7	2547.5	2547.5	2572.6
15°	2438.2	2509.1	2549.0	2599.2	2613.9	2596.2	2615.4	2636.1	2637.6	2637.6	2636.1
17.5°	2531.2	2559.3	2599.2	2625.7	2631.7	2631.7	2633.1	2642.0	2636.1	2624.3	2633.1
20°	2550.4	2562.2	2577.0	2574.1	2577.0	2562.2	2547.5	2532.7	2534.2	2526.8	2549.0
22.5°	2515.0	2512.0	2478.1	2455.9	2455.9	2426.4	2398.3	2385.0	2371.7	2376.2	2383.5
25°	2426.4	2380.6	2339.2	2306.8	2299.4	2252.1	2213.7	2201.9	2179.8	2197.5	2200.4
27.5°	2284.6	2232.9	2166.5	2138.4	2100.0	2080.8	2054.2	2018.8	1973.0	1999.6	1995.2
30°	2132.5	2055.7	2001.1	1933.1	1872.6	1868.1	1817.9	1758.9	1735.2	1735.2	1748.5
32.5°	1962.7	1860.8	1781.0	1685.0	1626.0	1600.8	1540.3	1481.2	1494.5	1450.2	1466.5
35°	1764.8	1630.4	1530.0	1436.9	1392.6	1363.1	1284.8	1252.3	1216.9	1196.2	1234.6
37.5°	1575.7	1420.7	1292.2	1190.3	1174.1	1120.9	1067.7	1047.0	1026.4	1035.2	1033.8
40°	1345.4	1208.0	1092.8	1013.1	985.0	959.9	924.5	899.4	886.1	893.5	894.9
42.5°	1137.1	1021.9	936.3	880.2	856.5	838.8	821.1	800.4	796.0	796.0	801.9
45°	976.2	881.6	824.1	778.3	765.0	751.7	738.4	729.5	726.6	720.7	725.1
47.5°	847.7	772.4	736.9	703.0	688.2	685.2	673.4	669.0	663.1	661.6	663.1
50°	739.9	692.6	660.1	640.9	630.6	626.2	620.3	611.4	608.4	615.8	612.9
52.5°	664.6	620.3	602.5	583.3	577.4	571.5	562.7	564.1	562.7	559.7	559.7
55°	589.2	561.2	543.5	528.7	527.2	521.3	513.9	511.0	509.5	506.5	511.0
57.5°	528.7	506.5	490.3	477.0	471.1	471.1	463.7	457.8	457.8	456.3	457.8
60°	468.1	446.0	435.7	422.4	417.9	416.5	412.0	409.1	404.6	404.6	404.6
62.5°	412.0	394.3	382.5	370.7	372.2	364.8	358.9	355.9	355.9	357.4	357.4
65°	358.9	347.0	332.3	321.9	319.0	317.5	314.6	313.1	308.7	311.6	311.6
67.5°	310.1	293.9	285.0	280.6	276.2	274.7	271.7	268.8	267.3	265.8	268.8
70°	261.4	248.1	240.7	237.8	233.3	231.9	230.4	225.9	227.4	228.9	230.4
72.5°	217.1	205.3	203.8	194.9	194.9	194.9	189.0	192.0	190.5	187.6	190.5
75°	171.3	165.4	162.4	158.0	159.5	158.0	156.5	152.1	152.1	153.6	155.1
77.5°	135.9	130.0	128.5	124.1	121.1	124.1	121.1	119.6	119.6	121.1	121.1
80°	100.4	97.5	93.0	93.0	93.0	91.6	91.6	91.6	90.1	88.6	90.1
82.5°	66.5	66.5	65.0	63.5	65.0	62.0	63.5	63.5	63.5	63.5	63.5
85°	42.8	41.4	41.4	39.9	39.9	39.9	41.4	38.4	38.4	39.9	39.9
87.5°	19.2	19.2	19.2	20.7	19.2	19.2	19.2	20.7	19.2	19.2	19.2
90°	11.8	11.7	11.5	11.4	11.3	11.3	11.4	11.5	11.5	11.6	11.5
92.5°	10.7	10.7	10.8	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9
95°	21.9	21.9	21.9	21.9	21.9	21.8	21.7	21.5	21.4	21.2	21.4
97.5°	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2
100°	47.1	47.1	47.1	47.1	47.1	47.1	47.0	46.9	46.9	46.8	46.9
102.5°	61.3	61.3	61.4	61.5	61.5	61.5	61.4	61.3	61.3	61.2	61.3
105°	75.3	75.5	75.6	75.7	75.8	75.8	75.8	75.8	75.8	75.8	75.8
107.5°	90.6	90.7	90.8	90.9	90.9	90.7	90.3	90.0	89.6	89.2	89.6
110°	106.2	106.2	106.2	106.2	106.2	106.1	105.9	105.6	105.4	105.2	105.4

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	122.1	121.9	121.6	121.4	121.3	121.2	121.1	120.9	120.8	120.6	120.8
115°	137.9	137.9	137.8	137.7	137.7	137.6	137.4	137.1	136.9	136.7	136.9
117.5°	153.5	153.3	153.0	152.8	152.7	152.6	152.4	152.1	151.9	151.7	151.9
120°	168.8	168.8	168.8	168.8	168.8	168.7	168.4	168.2	167.9	167.7	167.9
122.5°	185.0	184.7	184.5	184.2	184.1	184.0	183.9	183.8	183.6	183.5	183.6
125°	200.7	200.5	200.2	200.0	199.9	199.9	199.8	199.7	199.6	199.5	199.6
127.5°	216.0	215.7	215.4	215.1	214.9	214.8	214.6	214.3	214.1	213.9	214.1
130°	231.4	231.3	231.1	231.0	230.9	230.8	230.5	230.2	229.9	229.6	229.9
132.5°	246.9	246.5	246.2	245.8	245.6	245.5	245.3	245.0	244.8	244.6	244.8
135°	261.6	261.6	261.5	261.4	261.4	261.3	261.0	260.8	260.5	260.3	260.5
137.5°	275.9	275.9	275.8	275.7	275.7	275.5	275.2	274.9	274.6	274.3	274.6
140°	290.4	290.4	290.4	290.4	290.4	290.2	289.9	289.6	289.3	289.0	289.3
142.5°	303.5	303.5	303.6	303.7	303.7	303.5	303.2	302.9	302.6	302.3	302.6
145°	316.8	316.8	316.9	317.0	317.0	316.9	316.6	316.3	316.0	315.7	316.0
147.5°	328.5	328.6	328.8	328.9	329.0	328.8	328.5	328.2	327.9	327.6	327.9
150°	339.4	339.7	339.9	340.2	340.3	340.2	339.9	339.7	339.4	339.2	339.4
152.5°	350.5	350.8	351.1	351.4	351.5	351.4	351.1	350.8	350.5	350.2	350.5
155°	359.5	359.9	360.2	360.6	360.8	360.7	360.4	360.2	359.9	359.7	359.9
157.5°	368.1	368.7	369.2	369.7	370.0	369.8	369.4	369.1	368.7	368.3	368.7
160°	375.9	376.4	376.8	377.3	377.5	377.3	377.0	376.7	376.4	376.1	376.4
162.5°	382.8	383.4	383.9	384.4	384.7	384.5	384.1	383.8	383.4	383.0	383.4
165°	388.6	389.2	389.7	390.2	390.5	390.3	389.9	389.6	389.2	388.8	389.2
167.5°	393.7	394.3	394.8	395.3	395.6	395.4	395.0	394.7	394.3	393.9	394.3
170°	397.8	398.4	398.9	399.4	399.7	399.5	399.0	398.6	398.1	397.7	398.1
172.5°	400.9	401.5	402.0	402.5	402.8	402.6	402.1	401.6	401.2	400.7	401.2
175°	402.9	403.5	404.0	404.5	404.8	404.6	404.1	403.7	403.2	402.8	403.2
177.5°	404.3	404.7	405.2	405.7	405.9	405.7	405.2	404.7	404.3	403.8	404.3
180°	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	2036.5	2026.2	2017.3	2018.8	2026.2	2020.3	2005.5	1986.3	1978.9	1970.0	1978.9
5°	2159.1	2150.2	2132.5	2134.0	2129.5	2123.6	2100.0	2070.5	2070.5	2046.8	2043.9
7.5°	2280.2	2266.9	2255.1	2252.1	2235.9	2224.1	2203.4	2162.0	2145.8	2117.7	2101.5
10°	2416.0	2405.7	2392.4	2376.2	2367.3	2346.6	2312.7	2252.1	2222.6	2184.2	2156.1
12.5°	2553.4	2551.9	2522.4	2489.9	2488.4	2455.9	2432.3	2351.1	2311.2	2259.5	2193.0
15°	2640.5	2633.1	2616.9	2600.6	2605.1	2569.6	2516.5	2420.5	2393.9	2331.9	2261.0
17.5°	2639.0	2639.0	2634.6	2631.7	2627.2	2616.9	2587.3	2523.8	2481.0	2402.7	2336.3
20°	2554.9	2574.1	2578.5	2577.0	2591.8	2599.2	2597.7	2557.8	2523.8	2454.4	2386.5
22.5°	2386.5	2430.8	2450.0	2461.8	2492.8	2509.1	2547.5	2532.7	2523.8	2472.2	2414.6
25°	2230.0	2244.7	2302.3	2305.3	2348.1	2388.0	2426.4	2451.5	2484.0	2464.8	2416.0
27.5°	2027.6	2061.6	2103.0	2134.0	2142.8	2224.1	2287.6	2334.8	2408.7	2414.6	2398.3
30°	1798.7	1815.0	1882.9	1924.3	1971.5	2030.6	2122.2	2203.4	2269.8	2330.4	2351.1
32.5°	1519.6	1586.1	1626.0	1676.2	1717.5	1822.4	1934.6	2039.5	2116.2	2218.1	2262.5
35°	1264.1	1315.8	1383.8	1404.4	1479.8	1568.4	1714.6	1848.9	1965.6	2069.0	2159.1
37.5°	1053.0	1094.3	1166.7	1199.2	1243.5	1357.2	1479.8	1646.6	1786.9	1913.9	2026.2
40°	908.2	939.2	993.9	1004.2	1041.1	1144.5	1243.5	1400.0	1586.1	1757.4	1880.0
42.5°	809.3	824.1	861.0	874.3	897.9	967.3	1055.9	1203.6	1376.4	1553.6	1726.4
45°	738.4	748.7	770.9	782.7	812.2	843.3	915.6	1033.8	1169.6	1348.3	1534.4
47.5°	674.9	688.2	697.0	704.4	720.7	754.6	801.9	889.0	1019.0	1182.9	1363.1
50°	621.7	626.2	642.4	643.9	654.2	676.4	720.7	773.8	877.2	1010.1	1184.4
52.5°	568.6	573.0	583.3	593.7	598.1	615.8	645.4	689.7	766.5	871.3	1026.4
55°	515.4	521.3	531.6	539.0	543.5	558.2	576.0	618.8	679.3	753.2	880.2
57.5°	462.2	475.5	478.5	482.9	490.3	506.5	522.8	547.9	595.1	663.1	756.1
60°	412.0	416.5	426.8	431.2	438.6	447.5	468.1	487.3	521.3	574.5	658.7
62.5°	360.3	370.7	375.1	379.5	385.4	395.8	409.1	429.7	459.3	502.1	568.6
65°	316.0	317.5	326.4	332.3	338.2	345.6	358.9	378.1	395.8	435.7	484.4
67.5°	273.2	276.2	279.1	285.0	292.4	299.8	311.6	321.9	344.1	370.7	409.1
70°	231.9	231.9	239.2	243.7	242.2	251.1	259.9	271.7	288.0	313.1	344.1
72.5°	194.9	193.5	199.4	200.8	203.8	209.7	215.6	227.4	236.3	255.5	279.1
75°	155.1	158.0	161.0	161.0	165.4	169.8	175.7	181.6	192.0	203.8	221.5
77.5°	122.6	122.6	125.5	127.0	131.4	130.0	135.9	141.8	149.2	159.5	172.8
80°	90.1	93.0	93.0	93.0	94.5	96.0	101.9	106.3	110.8	118.1	124.1
82.5°	63.5	63.5	66.5	66.5	66.5	69.4	69.4	70.9	73.8	78.3	82.7
85°	39.9	39.9	39.9	41.4	39.9	41.4	44.3	42.8	44.3	47.3	47.3
87.5°	19.2	19.2	19.2	19.2	19.2	20.7	19.2	20.7	22.2	22.2	22.2
90°	11.5	11.4	11.3	11.3	11.4	11.5	11.7	11.8	12.0	10.3	8.6
92.5°	10.9	10.9	10.9	10.9	10.9	10.8	10.7	10.7	10.6	10.5	10.4
95°	21.5	21.7	21.8	21.9	21.9	21.9	21.9	21.9	21.9	21.7	21.6
97.5°	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	33.9	33.6
100°	46.9	47.0	47.1	47.1	47.1	47.1	47.1	47.1	47.1	46.9	46.7
102.5°	61.3	61.4	61.5	61.5	61.5	61.4	61.3	61.3	61.2	60.9	60.6
105°	75.8	75.8	75.8	75.8	75.7	75.6	75.5	75.3	75.2	75.0	74.9
107.5°	90.0	90.3	90.7	90.9	90.9	90.8	90.7	90.6	90.5	90.5	90.5
110°	105.6	105.9	106.1	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	120.9	121.1	121.2	121.3	121.4	121.6	121.9	122.1	122.3	122.4	122.4
115°	137.1	137.4	137.6	137.7	137.7	137.8	137.9	137.9	138.0	138.2	138.3
117.5°	152.1	152.4	152.6	152.7	152.8	153.0	153.3	153.5	153.7	154.1	154.5
120°	168.2	168.4	168.7	168.8	168.8	168.8	168.8	168.8	168.8	169.4	170.0
122.5°	183.8	183.9	184.0	184.1	184.2	184.5	184.7	185.0	185.2	185.6	186.0
125°	199.7	199.8	199.9	199.9	200.0	200.2	200.5	200.7	200.9	201.1	201.3
127.5°	214.3	214.6	214.8	214.9	215.1	215.4	215.7	216.0	216.3	216.6	216.9
130°	230.2	230.5	230.8	230.9	231.0	231.1	231.3	231.4	231.6	231.8	231.9
132.5°	245.0	245.3	245.5	245.6	245.8	246.2	246.5	246.9	247.3	247.2	247.2
135°	260.8	261.0	261.3	261.4	261.4	261.5	261.6	261.6	261.7	261.5	261.4
137.5°	274.9	275.2	275.5	275.7	275.7	275.8	275.9	275.9	276.0	275.9	275.7
140°	289.6	289.9	290.2	290.4	290.4	290.4	290.4	290.4	290.4	290.0	289.6
142.5°	302.9	303.2	303.5	303.7	303.7	303.6	303.5	303.5	303.4	303.2	302.9
145°	316.3	316.6	316.9	317.0	317.0	316.9	316.8	316.8	316.7	316.2	315.8
147.5°	328.2	328.5	328.8	329.0	328.9	328.8	328.6	328.5	328.3	328.0	327.7
150°	339.7	339.9	340.2	340.3	340.2	339.9	339.7	339.4	339.2	338.9	338.6
152.5°	350.8	351.1	351.4	351.5	351.4	351.1	350.8	350.5	350.2	349.8	349.4
155°	360.2	360.4	360.7	360.8	360.6	360.2	359.9	359.5	359.1	358.9	358.6
157.5°	369.1	369.4	369.8	370.0	369.7	369.2	368.7	368.1	367.6	367.4	367.3
160°	376.7	377.0	377.3	377.5	377.3	376.8	376.4	375.9	375.5	375.4	375.3
162.5°	383.8	384.1	384.5	384.7	384.4	383.9	383.4	382.8	382.3	382.2	382.1
165°	389.6	389.9	390.3	390.5	390.2	389.7	389.2	388.6	388.1	388.1	388.1
167.5°	394.7	395.0	395.4	395.6	395.3	394.8	394.3	393.7	393.2	393.2	393.2
170°	398.6	399.0	399.5	399.7	399.4	398.9	398.4	397.8	397.3	397.4	397.5
172.5°	401.6	402.1	402.6	402.8	402.5	402.0	401.5	400.9	400.4	400.5	400.5
175°	403.7	404.1	404.6	404.8	404.5	404.0	403.5	402.9	402.4	402.6	402.7
177.5°	404.7	405.2	405.7	405.9	405.7	405.2	404.7	404.3	403.8	404.0	404.1
180°	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1971.5	1964.1	1959.7	1962.7	1953.8	1931.6	1931.6	1939.0	1930.2	1921.3	1908.0
5°	2026.2	2011.4	2002.5	2001.1	1980.4	1944.9	1937.6	1930.2	1911.0	1890.3	1868.1
7.5°	2079.3	2052.7	2038.0	2027.6	1998.1	1952.3	1933.1	1916.9	1885.9	1854.9	1826.8
10°	2123.6	2085.2	2067.5	2051.3	2012.9	1955.3	1924.3	1894.7	1854.9	1815.0	1779.5
12.5°	2159.1	2114.8	2092.6	2069.0	2021.7	1946.4	1908.0	1860.8	1820.9	1767.7	1732.3
15°	2218.1	2126.6	2105.9	2083.8	2035.0	1931.6	1884.4	1831.2	1776.6	1705.7	1667.3
17.5°	2265.4	2142.8	2141.4	2094.1	2030.6	1925.7	1853.4	1784.0	1724.9	1654.0	1593.5
20°	2293.5	2167.9	2144.3	2095.6	2015.8	1885.9	1810.6	1733.8	1670.3	1584.6	1524.1
22.5°	2317.1	2203.4	2141.4	2082.3	1984.8	1872.6	1761.8	1689.5	1602.3	1509.3	1451.7
25°	2326.0	2210.8	2145.8	2077.9	1962.7	1834.2	1708.7	1630.4	1532.9	1448.7	1370.5
27.5°	2327.4	2209.3	2129.5	2058.7	1931.6	1784.0	1655.5	1572.8	1465.0	1367.5	1289.2
30°	2312.7	2193.0	2120.7	2043.9	1902.1	1738.2	1590.5	1498.9	1383.8	1286.3	1205.1
32.5°	2268.4	2160.6	2101.5	2017.3	1863.7	1674.7	1528.5	1426.6	1305.5	1209.5	1131.2
35°	2194.5	2120.7	2055.7	1977.4	1813.5	1615.6	1466.5	1346.8	1224.3	1132.7	1058.9
37.5°	2103.0	2063.1	2002.5	1925.7	1755.9	1562.5	1397.0	1264.1	1141.6	1053.0	980.6
40°	1978.9	1989.2	1930.2	1860.8	1688.0	1490.1	1307.0	1180.0	1064.8	982.1	911.2
42.5°	1844.5	1887.3	1853.4	1786.9	1612.7	1410.3	1240.5	1100.2	988.0	902.3	843.3
45°	1699.8	1773.6	1753.0	1704.2	1534.4	1326.2	1146.0	1010.1	911.2	828.5	776.8
47.5°	1541.8	1646.6	1646.6	1611.2	1447.3	1242.0	1064.8	926.0	828.5	769.4	719.2
50°	1380.8	1498.9	1518.1	1494.5	1349.8	1146.0	965.8	840.3	756.1	698.5	661.6
52.5°	1212.4	1349.8	1385.2	1373.4	1246.4	1054.4	884.6	762.0	685.2	635.0	602.5
55°	1051.5	1211.0	1249.4	1253.8	1135.7	954.0	794.5	686.7	612.9	578.9	550.8
57.5°	899.4	1053.0	1095.8	1103.2	1023.4	862.4	710.3	615.8	549.4	521.3	499.2
60°	769.4	897.9	954.0	970.3	900.8	756.1	632.1	540.5	490.3	463.7	443.0
62.5°	663.1	766.5	825.5	830.0	798.9	663.1	550.8	474.1	431.2	407.6	397.3
65°	559.7	652.7	688.2	705.9	680.8	574.5	475.5	412.0	378.1	357.4	347.0
67.5°	477.0	536.1	565.6	589.2	564.1	484.4	404.6	353.0	327.8	307.2	301.3
70°	391.4	440.1	462.2	485.9	463.7	403.2	345.6	298.3	276.2	259.9	252.5
72.5°	313.1	351.5	372.2	386.9	373.6	323.4	276.2	243.7	227.4	215.6	211.2
75°	248.1	274.7	286.5	296.8	290.9	252.5	223.0	196.4	181.6	171.3	168.4
77.5°	189.0	208.2	221.5	224.5	217.1	192.0	166.9	150.6	138.8	132.9	130.0
80°	134.4	146.2	153.6	158.0	150.6	140.3	122.6	110.8	100.4	93.0	91.6
82.5°	90.1	96.0	101.9	100.4	97.5	88.6	78.3	72.4	67.9	62.0	62.0
85°	51.7	53.2	56.1	57.6	56.1	50.2	44.3	41.4	38.4	34.0	34.0
87.5°	22.2	23.6	23.6	25.1	22.2	22.2	19.2	16.2	16.2	14.8	13.3
90°	6.9	5.2	4.4	3.9	3.0	2.1	1.2	0.3	1.2	2.1	3.0
92.5°	10.3	10.2	10.2	9.9	9.3	8.7	8.1	7.5	8.1	8.7	9.3
95°	21.4	21.3	21.2	20.8	20.1	19.3	18.6	17.8	18.6	19.3	20.1
97.5°	33.3	33.0	32.8	32.5	31.8	31.1	30.4	29.7	30.4	31.1	31.8
100°	46.4	46.2	46.1	45.8	45.2	44.6	44.0	43.4	44.0	44.6	45.2
102.5°	60.3	60.0	59.8	59.6	59.1	58.6	58.2	57.7	58.2	58.6	59.1
105°	74.7	74.6	74.5	74.4	74.2	73.9	73.7	73.5	73.7	73.9	74.2
107.5°	90.5	90.5	90.5	90.4	90.1	89.8	89.5	89.2	89.5	89.8	90.1
110°	106.2	106.2	106.2	106.0	105.5	105.1	104.6	104.2	104.6	105.1	105.5

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	122.5	122.6	122.6	122.4	121.9	121.5	121.0	120.6	121.0	121.5	121.9
115°	138.5	138.6	138.7	138.5	138.0	137.6	137.1	136.7	137.1	137.6	138.0
117.5°	154.8	155.2	155.4	155.1	154.5	153.9	153.3	152.7	153.3	153.9	154.5
120°	170.6	171.2	171.5	171.2	170.6	170.0	169.4	168.8	169.4	170.0	170.6
122.5°	186.3	186.7	186.9	186.5	185.8	185.0	184.3	183.5	184.3	185.0	185.8
125°	201.6	201.8	201.9	201.6	200.9	200.2	199.5	198.8	199.5	200.2	200.9
127.5°	217.2	217.5	217.6	217.2	216.4	215.5	214.7	213.9	214.7	215.5	216.4
130°	232.1	232.2	232.3	231.8	230.8	229.9	228.9	227.9	228.9	229.9	230.8
132.5°	247.1	247.0	247.0	246.6	245.9	245.1	244.4	243.6	244.4	245.1	245.9
135°	261.2	261.1	261.0	260.6	259.8	258.9	258.1	257.3	258.1	258.9	259.8
137.5°	275.6	275.5	275.4	275.1	274.4	273.7	273.0	272.3	273.0	273.7	274.4
140°	289.3	288.9	288.7	288.4	287.7	287.0	286.3	285.6	286.3	287.0	287.7
142.5°	302.7	302.4	302.3	302.0	301.3	300.6	300.0	299.3	300.0	300.6	301.3
145°	315.3	314.8	314.6	314.3	313.8	313.3	312.8	312.3	312.8	313.3	313.8
147.5°	327.4	327.1	326.9	326.6	325.9	325.2	324.6	323.9	324.6	325.2	325.9
150°	338.3	338.0	337.9	337.7	337.2	336.7	336.3	335.8	336.3	336.7	337.2
152.5°	349.1	348.7	348.5	348.3	347.8	347.3	346.9	346.4	346.9	347.3	347.8
155°	358.4	358.1	358.0	357.9	357.7	357.4	357.2	357.0	357.2	357.4	357.7
157.5°	367.1	367.0	366.9	366.8	366.7	366.5	366.4	366.2	366.4	366.5	366.7
160°	375.2	375.1	375.1	375.0	374.9	374.7	374.6	374.4	374.6	374.7	374.9
162.5°	382.0	381.9	381.9	381.9	381.9	381.9	381.9	381.9	381.9	381.9	381.9
165°	388.1	388.1	388.1	388.1	388.2	388.3	388.3	388.4	388.3	388.3	388.2
167.5°	393.2	393.2	393.2	393.3	393.5	393.8	394.0	394.2	394.0	393.8	393.5
170°	397.6	397.7	397.7	397.8	398.0	398.3	398.5	398.7	398.5	398.3	398.0
172.5°	400.6	400.7	400.7	400.8	401.1	401.3	401.6	401.8	401.6	401.3	401.1
175°	402.9	403.0	403.1	403.2	403.5	403.7	404.0	404.2	404.0	403.7	403.5
177.5°	404.3	404.4	404.5	404.6	404.8	405.1	405.3	405.5	405.3	405.1	404.8
180°	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1900.6	1908.0	1906.5	1891.8	1875.5	1862.2	1837.1	1840.1	1831.2	1832.7	1841.6
5°	1853.4	1853.4	1847.5	1826.8	1800.2	1785.4	1757.4	1750.0	1732.3	1730.8	1729.3
7.5°	1803.2	1795.8	1788.4	1758.9	1726.4	1702.7	1664.3	1655.5	1637.8	1626.0	1620.0
10°	1744.1	1733.8	1719.0	1685.0	1645.2	1615.6	1575.7	1563.9	1530.0	1515.2	1506.3
12.5°	1679.1	1673.2	1649.6	1621.5	1556.5	1524.1	1466.5	1478.3	1444.3	1414.8	1410.3
15°	1614.1	1592.0	1578.7	1532.9	1454.6	1439.9	1394.1	1370.5	1339.5	1315.8	1315.8
17.5°	1550.6	1516.7	1487.1	1438.4	1380.8	1339.5	1305.5	1293.7	1255.3	1231.6	1227.2
20°	1466.5	1428.1	1420.7	1351.3	1311.4	1265.6	1233.1	1203.6	1175.5	1165.2	1157.8
22.5°	1386.7	1342.4	1330.6	1271.5	1231.6	1185.9	1153.4	1132.7	1112.0	1104.6	1091.4
25°	1301.1	1274.5	1256.8	1193.3	1148.9	1106.1	1084.0	1069.2	1050.0	1048.5	1039.7
27.5°	1218.4	1193.3	1175.5	1115.0	1082.5	1042.6	1024.9	1008.7	998.3	993.9	989.5
30°	1147.5	1119.4	1098.7	1054.4	1014.6	982.1	967.3	957.0	951.1	943.7	942.2
32.5°	1069.2	1053.0	1024.9	990.9	959.9	928.9	920.0	912.7	903.8	900.8	899.4
35°	1002.7	980.6	962.9	924.5	911.2	884.6	874.3	868.4	856.5	853.6	850.6
37.5°	937.8	917.1	897.9	874.3	849.2	834.4	828.5	819.6	813.7	815.2	812.2
40°	872.8	856.5	841.8	816.7	801.9	794.5	782.7	773.8	770.9	772.4	770.9
42.5°	809.3	794.5	785.7	766.5	751.7	744.3	736.9	728.1	732.5	732.5	736.9
45°	751.7	738.4	732.5	717.7	708.9	697.0	689.7	688.2	694.1	692.6	692.6
47.5°	692.6	688.2	680.8	667.5	655.7	648.3	646.8	646.8	652.7	655.7	654.2
50°	646.8	638.0	629.1	618.8	609.9	607.0	602.5	605.5	611.4	611.4	614.3
52.5°	589.2	583.3	580.4	571.5	565.6	565.6	565.6	567.1	571.5	576.0	574.5
55°	539.0	534.6	531.6	527.2	519.8	521.3	519.8	522.8	527.2	531.6	534.6
57.5°	485.9	484.4	481.4	474.1	474.1	472.6	477.0	478.5	485.9	488.8	493.3
60°	438.6	434.2	434.2	428.3	428.3	428.3	432.7	437.1	443.0	444.5	447.5
62.5°	388.4	388.4	386.9	382.5	382.5	386.9	388.4	394.3	397.3	397.3	401.7
65°	341.1	339.7	338.2	339.7	341.1	341.1	345.6	348.5	351.5	353.0	354.4
67.5°	293.9	292.4	295.4	293.9	296.8	302.7	301.3	305.7	310.1	310.1	311.6
70°	249.6	252.5	251.1	254.0	252.5	255.5	259.9	261.4	261.4	262.9	267.3
72.5°	208.2	208.2	208.2	206.8	208.2	211.2	214.1	215.6	218.6	220.0	224.5
75°	168.4	168.4	165.4	168.4	168.4	171.3	174.3	174.3	174.3	177.2	181.6
77.5°	127.0	128.5	127.0	130.0	130.0	131.4	134.4	132.9	135.9	137.3	138.8
80°	93.0	91.6	91.6	91.6	93.0	93.0	96.0	97.5	97.5	101.9	98.9
82.5°	59.1	60.5	59.1	60.5	60.5	62.0	60.5	62.0	63.5	66.5	65.0
85°	34.0	32.5	32.5	34.0	32.5	32.5	34.0	32.5	34.0	32.5	34.0
87.5°	13.3	11.8	11.8	11.8	11.8	10.3	10.3	8.9	8.9	8.9	7.4
90°	3.9	4.4	5.2	6.9	8.6	10.3	12.0	11.8	11.7	11.5	11.4
92.5°	9.9	10.2	10.2	10.3	10.4	10.5	10.6	10.7	10.7	10.8	10.9
95°	20.8	21.2	21.3	21.4	21.6	21.7	21.9	21.9	21.9	21.9	21.9
97.5°	32.5	32.8	33.0	33.3	33.6	33.9	34.2	34.2	34.2	34.2	34.2
100°	45.8	46.1	46.2	46.4	46.7	46.9	47.1	47.1	47.1	47.1	47.1
102.5°	59.6	59.8	60.0	60.3	60.6	60.9	61.2	61.3	61.3	61.4	61.5
105°	74.4	74.5	74.6	74.7	74.9	75.0	75.2	75.3	75.5	75.6	75.7
107.5°	90.4	90.5	90.5	90.5	90.5	90.5	90.5	90.6	90.7	90.8	90.9
110°	106.0	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	122.4	122.6	122.6	122.5	122.4	122.4	122.3	122.1	121.9	121.6	121.4
115°	138.5	138.7	138.6	138.5	138.3	138.2	138.0	137.9	137.9	137.8	137.7
117.5°	155.1	155.4	155.2	154.8	154.5	154.1	153.7	153.5	153.3	153.0	152.8
120°	171.2	171.5	171.2	170.6	170.0	169.4	168.8	168.8	168.8	168.8	168.8
122.5°	186.5	186.9	186.7	186.3	186.0	185.6	185.2	185.0	184.7	184.5	184.2
125°	201.6	201.9	201.8	201.6	201.3	201.1	200.9	200.7	200.5	200.2	200.0
127.5°	217.2	217.6	217.5	217.2	216.9	216.6	216.3	216.0	215.7	215.4	215.1
130°	231.8	232.3	232.2	232.1	231.9	231.8	231.6	231.4	231.3	231.1	231.0
132.5°	246.6	247.0	247.0	247.1	247.2	247.2	247.3	246.9	246.5	246.2	245.8
135°	260.6	261.0	261.1	261.2	261.4	261.5	261.7	261.6	261.6	261.5	261.4
137.5°	275.1	275.4	275.5	275.6	275.7	275.9	276.0	275.9	275.9	275.8	275.7
140°	288.4	288.7	288.9	289.3	289.6	290.0	290.4	290.4	290.4	290.4	290.4
142.5°	302.0	302.3	302.4	302.7	302.9	303.2	303.4	303.5	303.5	303.6	303.7
145°	314.3	314.6	314.8	315.3	315.8	316.2	316.7	316.8	316.8	316.9	317.0
147.5°	326.6	326.9	327.1	327.4	327.7	328.0	328.3	328.5	328.6	328.8	328.9
150°	337.7	337.9	338.0	338.3	338.6	338.9	339.2	339.4	339.7	339.9	340.2
152.5°	348.3	348.5	348.7	349.1	349.4	349.8	350.2	350.5	350.8	351.1	351.4
155°	357.9	358.0	358.1	358.4	358.6	358.9	359.1	359.5	359.9	360.2	360.6
157.5°	366.8	366.9	367.0	367.1	367.3	367.4	367.6	368.1	368.7	369.2	369.7
160°	375.0	375.1	375.1	375.2	375.3	375.4	375.5	375.9	376.4	376.8	377.3
162.5°	381.9	381.9	381.9	382.0	382.1	382.2	382.3	382.8	383.4	383.9	384.4
165°	388.1	388.1	388.1	388.1	388.1	388.1	388.1	388.6	389.2	389.7	390.2
167.5°	393.3	393.2	393.2	393.2	393.2	393.2	393.2	393.7	394.3	394.8	395.3
170°	397.8	397.7	397.7	397.6	397.5	397.4	397.3	397.8	398.4	398.9	399.4
172.5°	400.8	400.7	400.7	400.6	400.5	400.5	400.4	400.9	401.5	402.0	402.5
175°	403.2	403.1	403.0	402.9	402.7	402.6	402.4	402.9	403.5	404.0	404.5
177.5°	404.6	404.5	404.4	404.3	404.1	404.0	403.8	404.3	404.7	405.2	405.7
180°	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1831.2	1835.7	1825.3	1822.4	1825.3	1815.0	1817.9	1820.9	1820.9	1825.3	1828.3
5°	1724.9	1719.0	1708.7	1705.7	1702.7	1707.2	1704.2	1708.7	1710.1	1720.5	1721.9
7.5°	1620.0	1611.2	1602.3	1593.5	1590.5	1583.1	1590.5	1590.5	1600.8	1597.9	1605.3
10°	1496.0	1494.5	1482.7	1478.3	1472.4	1460.6	1476.8	1472.4	1479.8	1493.0	1496.0
12.5°	1404.4	1388.2	1395.6	1374.9	1382.3	1370.5	1371.9	1371.9	1383.8	1385.2	1382.3
15°	1317.3	1304.0	1284.8	1276.0	1271.5	1265.6	1284.8	1286.3	1277.4	1298.1	1290.7
17.5°	1228.7	1228.7	1211.0	1206.5	1194.7	1200.6	1197.7	1199.2	1196.2	1211.0	1218.4
20°	1151.9	1144.5	1138.6	1140.1	1125.3	1122.4	1119.4	1122.4	1132.7	1143.0	1146.0
22.5°	1089.9	1085.4	1070.7	1073.6	1061.8	1066.2	1063.3	1070.7	1072.2	1072.2	1082.5
25°	1030.8	1024.9	1026.4	1020.5	1016.0	1016.0	1011.6	1016.0	1021.9	1024.9	1026.4
27.5°	986.5	982.1	974.7	970.3	973.2	965.8	971.7	976.2	976.2	973.2	976.2
30°	933.3	936.3	936.3	921.5	927.4	924.5	928.9	931.9	931.9	933.3	930.4
32.5°	897.9	889.0	887.6	886.1	886.1	880.2	880.2	884.6	886.1	887.6	892.0
35°	850.6	850.6	843.3	847.7	841.8	843.3	841.8	843.3	846.2	841.8	846.2
37.5°	807.8	809.3	806.3	809.3	810.8	807.8	804.9	810.8	807.8	807.8	804.9
40°	770.9	769.4	770.9	770.9	770.9	772.4	769.4	769.4	769.4	766.5	763.5
42.5°	739.9	731.0	734.0	735.4	731.0	731.0	732.5	731.0	735.4	726.6	726.6
45°	695.6	692.6	694.1	694.1	697.0	692.6	695.6	697.0	692.6	691.1	688.2
47.5°	655.7	658.7	655.7	658.7	658.7	661.6	655.7	657.2	658.7	652.7	648.3
50°	615.8	615.8	620.3	618.8	620.3	617.3	617.3	615.8	617.3	614.3	609.9
52.5°	578.9	574.5	581.9	580.4	578.9	577.4	576.0	577.4	574.5	571.5	571.5
55°	533.1	533.1	537.6	539.0	539.0	536.1	533.1	534.6	533.1	531.6	530.2
57.5°	496.2	490.3	493.3	494.7	494.7	490.3	493.3	490.3	490.3	491.8	487.3
60°	448.9	448.9	446.0	450.4	450.4	447.5	447.5	448.9	446.0	444.5	443.0
62.5°	398.7	400.2	404.6	406.1	407.6	404.6	401.7	403.2	403.2	398.7	400.2
65°	355.9	358.9	364.8	363.3	360.3	361.8	358.9	360.3	355.9	357.4	353.0
67.5°	314.6	313.1	314.6	314.6	317.5	316.0	313.1	313.1	311.6	316.0	311.6
70°	270.3	270.3	270.3	270.3	271.7	273.2	270.3	267.3	268.8	265.8	264.3
72.5°	224.5	225.9	224.5	227.4	223.0	225.9	225.9	224.5	223.0	223.0	223.0
75°	181.6	184.6	180.2	181.6	180.2	183.1	181.6	181.6	178.7	177.2	178.7
77.5°	138.8	140.3	137.3	138.8	137.3	138.8	138.8	137.3	137.3	137.3	137.3
80°	98.9	100.4	98.9	97.5	96.0	98.9	96.0	97.5	98.9	97.5	100.4
82.5°	63.5	63.5	62.0	63.5	60.5	60.5	62.0	62.0	60.5	63.5	60.5
85°	31.0	31.0	34.0	31.0	29.5	29.5	29.5	31.0	29.5	32.5	31.0
87.5°	7.4	5.9	7.4	7.4	5.9	5.9	7.4	5.9	7.4	8.9	5.9
90°	11.3	11.3	11.4	11.5	11.5	11.6	11.5	11.5	11.4	11.3	11.3
92.5°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9
95°	21.9	21.8	21.7	21.5	21.4	21.2	21.4	21.5	21.7	21.8	21.9
97.5°	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2
100°	47.1	47.1	47.0	46.9	46.9	46.8	46.9	46.9	47.0	47.1	47.1
102.5°	61.5	61.5	61.4	61.3	61.3	61.2	61.3	61.3	61.4	61.5	61.5
105°	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8
107.5°	90.9	90.7	90.3	90.0	89.6	89.2	89.6	90.0	90.3	90.7	90.9
110°	106.2	106.1	105.9	105.6	105.4	105.2	105.4	105.6	105.9	106.1	106.2

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	121.3	121.2	121.1	120.9	120.8	120.6	120.8	120.9	121.1	121.2	121.3
115°	137.7	137.6	137.4	137.1	136.9	136.7	136.9	137.1	137.4	137.6	137.7
117.5°	152.7	152.6	152.4	152.1	151.9	151.7	151.9	152.1	152.4	152.6	152.7
120°	168.8	168.7	168.4	168.2	167.9	167.7	167.9	168.2	168.4	168.7	168.8
122.5°	184.1	184.0	183.9	183.8	183.6	183.5	183.6	183.8	183.9	184.0	184.1
125°	199.9	199.9	199.8	199.7	199.6	199.5	199.6	199.7	199.8	199.9	199.9
127.5°	214.9	214.8	214.6	214.3	214.1	213.9	214.1	214.3	214.6	214.8	214.9
130°	230.9	230.8	230.5	230.2	229.9	229.6	229.9	230.2	230.5	230.8	230.9
132.5°	245.6	245.5	245.3	245.0	244.8	244.6	244.8	245.0	245.3	245.5	245.6
135°	261.4	261.3	261.0	260.8	260.5	260.3	260.5	260.8	261.0	261.3	261.4
137.5°	275.7	275.5	275.2	274.9	274.6	274.3	274.6	274.9	275.2	275.5	275.7
140°	290.4	290.2	289.9	289.6	289.3	289.0	289.3	289.6	289.9	290.2	290.4
142.5°	303.7	303.5	303.2	302.9	302.6	302.3	302.6	302.9	303.2	303.5	303.7
145°	317.0	316.9	316.6	316.3	316.0	315.7	316.0	316.3	316.6	316.9	317.0
147.5°	329.0	328.8	328.5	328.2	327.9	327.6	327.9	328.2	328.5	328.8	329.0
150°	340.3	340.2	339.9	339.7	339.4	339.2	339.4	339.7	339.9	340.2	340.3
152.5°	351.5	351.4	351.1	350.8	350.5	350.2	350.5	350.8	351.1	351.4	351.5
155°	360.8	360.7	360.4	360.2	359.9	359.7	359.9	360.2	360.4	360.7	360.8
157.5°	370.0	369.8	369.4	369.1	368.7	368.3	368.7	369.1	369.4	369.8	370.0
160°	377.5	377.3	377.0	376.7	376.4	376.1	376.4	376.7	377.0	377.3	377.5
162.5°	384.7	384.5	384.1	383.8	383.4	383.0	383.4	383.8	384.1	384.5	384.7
165°	390.5	390.3	389.9	389.6	389.2	388.8	389.2	389.6	389.9	390.3	390.5
167.5°	395.6	395.4	395.0	394.7	394.3	393.9	394.3	394.7	395.0	395.4	395.6
170°	399.7	399.5	399.0	398.6	398.1	397.7	398.1	398.6	399.0	399.5	399.7
172.5°	402.8	402.6	402.1	401.6	401.2	400.7	401.2	401.6	402.1	402.6	402.8
175°	404.8	404.6	404.1	403.7	403.2	402.8	403.2	403.7	404.1	404.6	404.8
177.5°	405.9	405.7	405.2	404.7	404.3	403.8	404.3	404.7	405.2	405.7	405.9
180°	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1823.8	1835.7	1831.2	1815.0	1834.2	1834.2	1847.5	1847.5	1863.7	1869.6	1878.5
5°	1720.5	1729.3	1736.7	1729.3	1742.6	1763.3	1775.1	1785.4	1807.6	1816.5	1829.8
7.5°	1609.7	1626.0	1633.3	1633.3	1655.5	1679.1	1702.7	1717.5	1748.5	1760.3	1773.6
10°	1501.9	1521.1	1535.9	1534.4	1571.3	1586.1	1615.6	1649.6	1680.6	1698.3	1717.5
12.5°	1388.2	1398.5	1419.2	1448.7	1457.6	1484.2	1518.1	1561.0	1617.1	1633.3	1661.4
15°	1293.7	1321.7	1338.0	1351.3	1371.9	1397.0	1434.0	1475.3	1531.4	1566.9	1596.4
17.5°	1213.9	1250.8	1261.2	1258.2	1284.8	1323.2	1366.0	1397.0	1447.3	1490.1	1518.1
20°	1148.9	1163.7	1181.4	1188.8	1209.5	1250.8	1292.2	1327.6	1369.0	1403.0	1435.4
22.5°	1084.0	1095.8	1110.6	1123.8	1140.1	1163.7	1203.6	1247.9	1287.8	1320.3	1357.2
25°	1030.8	1038.2	1051.5	1061.8	1079.5	1095.8	1123.8	1172.6	1219.8	1239.0	1271.5
27.5°	979.1	985.0	993.9	1005.7	1014.6	1030.8	1055.9	1095.8	1144.5	1163.7	1208.0
30°	933.3	937.8	946.6	952.5	957.0	976.2	995.4	1026.4	1063.3	1089.9	1122.4
32.5°	890.5	894.9	903.8	905.3	911.2	921.5	939.2	967.3	999.8	1021.9	1050.0
35°	843.3	846.2	855.1	858.0	862.4	871.3	884.6	905.3	934.8	951.1	976.2
37.5°	806.3	804.9	810.8	815.2	821.1	825.5	830.0	850.6	872.8	887.6	906.8
40°	766.5	763.5	765.0	770.9	773.8	779.7	779.7	800.4	815.2	827.0	841.8
42.5°	726.6	725.1	722.2	725.1	728.1	729.5	731.0	745.8	760.6	770.9	787.1
45°	686.7	685.2	682.3	683.8	683.8	686.7	691.1	697.0	707.4	716.2	725.1
47.5°	649.8	646.8	642.4	640.9	643.9	643.9	643.9	649.8	660.1	663.1	671.9
50°	611.4	607.0	601.1	598.1	598.1	596.6	599.6	601.1	609.9	612.9	620.3
52.5°	570.0	567.1	561.2	555.3	556.8	553.8	555.3	556.8	559.7	564.1	568.6
55°	528.7	522.8	518.4	516.9	512.4	512.4	508.0	513.9	512.4	513.9	519.8
57.5°	488.8	482.9	475.5	472.6	468.1	466.7	463.7	462.2	463.7	468.1	472.6
60°	441.6	438.6	434.2	429.7	426.8	422.4	419.4	419.4	417.9	417.9	419.4
62.5°	395.8	394.3	388.4	386.9	384.0	381.0	376.6	373.6	373.6	376.6	378.1
65°	351.5	350.0	345.6	344.1	336.7	333.8	332.3	330.8	327.8	327.8	327.8
67.5°	310.1	305.7	305.7	298.3	292.4	289.5	286.5	285.0	285.0	285.0	286.5
70°	264.3	264.3	259.9	255.5	249.6	251.1	246.6	242.2	242.2	239.2	240.7
72.5°	220.0	218.6	214.1	212.7	208.2	203.8	200.8	203.8	199.4	197.9	199.4
75°	177.2	175.7	172.8	169.8	171.3	166.9	162.4	161.0	161.0	158.0	158.0
77.5°	135.9	138.8	132.9	131.4	128.5	125.5	124.1	122.6	122.6	122.6	125.5
80°	94.5	96.0	96.0	93.0	94.5	90.1	90.1	90.1	85.7	87.1	88.6
82.5°	60.5	60.5	59.1	60.5	59.1	59.1	57.6	57.6	56.1	56.1	57.6
85°	34.0	32.5	31.0	34.0	32.5	32.5	31.0	31.0	31.0	31.0	31.0
87.5°	7.4	8.9	8.9	8.9	8.9	10.3	10.3	10.3	11.8	11.8	11.8
90°	11.4	11.5	11.7	11.8	12.0	10.3	8.6	6.9	5.2	4.4	3.9
92.5°	10.9	10.8	10.7	10.7	10.6	10.5	10.4	10.3	10.2	10.2	9.9
95°	21.9	21.9	21.9	21.9	21.9	21.7	21.6	21.4	21.3	21.2	20.8
97.5°	34.2	34.2	34.2	34.2	34.2	33.9	33.6	33.3	33.0	32.8	32.5
100°	47.1	47.1	47.1	47.1	47.1	46.9	46.7	46.4	46.2	46.1	45.8
102.5°	61.5	61.4	61.3	61.3	61.2	60.9	60.6	60.3	60.0	59.8	59.6
105°	75.7	75.6	75.5	75.3	75.2	75.0	74.9	74.7	74.6	74.5	74.4
107.5°	90.9	90.8	90.7	90.6	90.5	90.5	90.5	90.5	90.5	90.5	90.4
110°	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.0

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	121.4	121.6	121.9	122.1	122.3	122.4	122.4	122.5	122.6	122.6	122.4
115°	137.7	137.8	137.9	137.9	138.0	138.2	138.3	138.5	138.6	138.7	138.5
117.5°	152.8	153.0	153.3	153.5	153.7	154.1	154.5	154.8	155.2	155.4	155.1
120°	168.8	168.8	168.8	168.8	168.8	169.4	170.0	170.6	171.2	171.5	171.2
122.5°	184.2	184.5	184.7	185.0	185.2	185.6	186.0	186.3	186.7	186.9	186.5
125°	200.0	200.2	200.5	200.7	200.9	201.1	201.3	201.6	201.8	201.9	201.6
127.5°	215.1	215.4	215.7	216.0	216.3	216.6	216.9	217.2	217.5	217.6	217.2
130°	231.0	231.1	231.3	231.4	231.6	231.8	231.9	232.1	232.2	232.3	231.8
132.5°	245.8	246.2	246.5	246.9	247.3	247.2	247.2	247.1	247.0	247.0	246.6
135°	261.4	261.5	261.6	261.6	261.7	261.5	261.4	261.2	261.1	261.0	260.6
137.5°	275.7	275.8	275.9	275.9	276.0	275.9	275.7	275.6	275.5	275.4	275.1
140°	290.4	290.4	290.4	290.4	290.4	290.0	289.6	289.3	288.9	288.7	288.4
142.5°	303.7	303.6	303.5	303.5	303.4	303.2	302.9	302.7	302.4	302.3	302.0
145°	317.0	316.9	316.8	316.8	316.7	316.2	315.8	315.3	314.8	314.6	314.3
147.5°	328.9	328.8	328.6	328.5	328.3	328.0	327.7	327.4	327.1	326.9	326.6
150°	340.2	339.9	339.7	339.4	339.2	338.9	338.6	338.3	338.0	337.9	337.7
152.5°	351.4	351.1	350.8	350.5	350.2	349.8	349.4	349.1	348.7	348.5	348.3
155°	360.6	360.2	359.9	359.5	359.1	358.9	358.6	358.4	358.1	358.0	357.9
157.5°	369.7	369.2	368.7	368.1	367.6	367.4	367.3	367.1	367.0	366.9	366.8
160°	377.3	376.8	376.4	375.9	375.5	375.4	375.3	375.2	375.1	375.1	375.0
162.5°	384.4	383.9	383.4	382.8	382.3	382.2	382.1	382.0	381.9	381.9	381.9
165°	390.2	389.7	389.2	388.6	388.1	388.1	388.1	388.1	388.1	388.1	388.1
167.5°	395.3	394.8	394.3	393.7	393.2	393.2	393.2	393.2	393.2	393.2	393.3
170°	399.4	398.9	398.4	397.8	397.3	397.4	397.5	397.6	397.7	397.7	397.8
172.5°	402.5	402.0	401.5	400.9	400.4	400.5	400.5	400.6	400.7	400.7	400.8
175°	404.5	404.0	403.5	402.9	402.4	402.6	402.7	402.9	403.0	403.1	403.2
177.5°	405.7	405.2	404.7	404.3	403.8	404.0	404.1	404.3	404.4	404.5	404.6
180°	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1921.3	1921.3	1921.3	1921.3
2.5°	1885.9	1885.9	1908.0	1931.6
5°	1844.5	1854.9	1890.3	1922.8
7.5°	1804.6	1822.4	1866.7	1908.0
10°	1755.9	1779.5	1834.2	1882.9
12.5°	1708.7	1730.8	1794.3	1848.9
15°	1642.2	1670.3	1738.2	1806.1
17.5°	1575.7	1603.8	1686.5	1766.2
20°	1497.5	1534.4	1627.4	1733.8
22.5°	1425.1	1470.9	1574.3	1659.9
25°	1345.4	1416.2	1512.2	1623.0
27.5°	1274.5	1345.4	1442.8	1555.1
30°	1194.7	1267.1	1367.5	1470.9
32.5°	1117.9	1184.4	1281.9	1408.9
35°	1038.2	1101.7	1196.2	1324.7
37.5°	965.8	1027.9	1131.2	1249.4
40°	894.9	959.9	1048.5	1166.7
42.5°	828.5	886.1	965.8	1084.0
45°	767.9	809.3	883.1	993.9
47.5°	704.4	741.4	809.3	920.0
50°	645.4	676.4	735.4	838.8
52.5°	587.8	614.3	669.0	751.7
55°	536.1	561.2	601.1	682.3
57.5°	482.9	502.1	540.5	605.5
60°	431.2	448.9	480.0	533.1
62.5°	379.5	394.3	423.8	466.7
65°	333.8	345.6	367.7	404.6
67.5°	289.5	296.8	314.6	344.1
70°	246.6	252.5	267.3	290.9
72.5°	200.8	206.8	223.0	239.2
75°	162.4	163.9	175.7	189.0
77.5°	127.0	125.5	134.4	144.7
80°	87.1	91.6	98.9	103.4
82.5°	59.1	60.5	63.5	66.5
85°	32.5	34.0	34.0	38.4
87.5°	13.3	14.8	14.8	16.2
90°	3.0	2.1	1.2	0.3
92.5°	9.3	8.7	8.1	7.5
95°	20.1	19.3	18.6	17.8
97.5°	31.8	31.1	30.4	29.7
100°	45.2	44.6	44.0	43.4
102.5°	59.1	58.6	58.2	57.7
105°	74.2	73.9	73.7	73.5
107.5°	90.1	89.8	89.5	89.2
110°	105.5	105.1	104.6	104.2

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	121.9	121.5	121.0	120.6
115°	138.0	137.6	137.1	136.7
117.5°	154.5	153.9	153.3	152.7
120°	170.6	170.0	169.4	168.8
122.5°	185.8	185.0	184.3	183.5
125°	200.9	200.2	199.5	198.8
127.5°	216.4	215.5	214.7	213.9
130°	230.8	229.9	228.9	227.9
132.5°	245.9	245.1	244.4	243.6
135°	259.8	258.9	258.1	257.3
137.5°	274.4	273.7	273.0	272.3
140°	287.7	287.0	286.3	285.6
142.5°	301.3	300.6	300.0	299.3
145°	313.8	313.3	312.8	312.3
147.5°	325.9	325.2	324.6	323.9
150°	337.2	336.7	336.3	335.8
152.5°	347.8	347.3	346.9	346.4
155°	357.7	357.4	357.2	357.0
157.5°	366.7	366.5	366.4	366.2
160°	374.9	374.7	374.6	374.4
162.5°	381.9	381.9	381.9	381.9
165°	388.2	388.3	388.3	388.4
167.5°	393.5	393.8	394.0	394.2
170°	398.0	398.3	398.5	398.7
172.5°	401.1	401.3	401.6	401.8
175°	403.5	403.7	404.0	404.2
177.5°	404.8	405.1	405.3	405.5
180°	404.8	404.8	404.8	404.8

TEST NUMBER: P997893

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.08	21.22	20.75	21.90	22.69	17.57	18.71	18.24	19.39	20.18
	3H	20.91	21.93	21.60	22.62	23.45	18.94	19.96	19.62	20.65	21.47
	4H	21.09	22.05	21.80	22.75	23.59	19.41	20.37	20.12	21.07	21.91
	6H	21.15	22.04	21.87	22.75	23.60	19.74	20.62	20.45	21.33	22.18
	8H	21.14	21.98	21.87	22.71	23.57	19.83	20.67	20.55	21.40	22.25
	12H	21.11	21.91	21.84	22.64	23.52	19.88	20.68	20.61	21.40	22.28
4H	2H	20.16	21.11	20.86	21.81	22.65	18.05	19.01	18.76	19.71	20.55
	3H	21.16	21.96	21.88	22.69	23.55	19.54	20.33	20.26	21.07	21.93
	4H	21.45	22.17	22.18	22.91	23.79	20.08	20.80	20.82	21.54	22.43
	6H	21.59	22.21	22.34	22.98	23.88	20.48	21.10	21.23	21.87	22.76
	8H	21.60	22.18	22.35	22.94	23.85	20.59	21.17	21.35	21.94	22.84
	12H	21.57	22.09	22.35	22.88	23.79	20.66	21.18	21.44	21.97	22.88
8H	4H	21.48	22.06	22.23	22.82	23.73	20.25	20.83	21.00	21.59	22.50
	6H	21.67	22.14	22.45	22.95	23.86	20.69	21.17	21.48	21.98	22.88
	8H	21.70	22.12	22.50	22.93	23.85	20.84	21.27	21.64	22.07	23.00
	12H	21.69	22.07	22.49	22.86	23.85	20.95	21.32	21.75	22.12	23.10
12H	4H	21.45	21.97	22.22	22.75	23.66	20.23	20.75	21.01	21.54	22.45
	6H	21.64	22.07	22.44	22.88	23.80	20.69	21.12	21.49	21.92	22.85
	8H	21.69	22.07	22.49	22.86	23.84	20.86	21.24	21.66	22.03	23.02